

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333171-840

Luminaire Tested: **S125DIP-S610D590U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333171-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4694.7 lumens
Efficiency: N/A
Efficacy: 143.1 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	54	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	40	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5837	5837	5837	5837
5°	6760	5857	5128	5857
10°	7864	5827	4494	5827
15°	8705	5784	4145	5784
20°	9745	5716	3865	5716
25°	11416	5640	3729	5640
30°	12331	5565	3610	5565
35°	10138	5423	3533	5423
40°	7206	5227	3447	5227
45°	5536	4961	3399	4961
50°	4725	4633	3392	4633
55°	4208	4310	3422	4310
60°	3796	3959	3509	3959
65°	3506	3605	3599	3605
70°	3186	3238	3652	3238
75°	2815	2852	3618	2852
80°	2369	2325	3310	2325
85°	1875	1675	2675	1675



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.9
10°-20°	259.1	5.5
20°-30°	420.7	9.0
30°-40°	513.1	10.9
40°-50°	466.8	9.9
50°-60°	371.8	7.9
60°-70°	259.0	5.5
70°-80°	138.1	2.9
80°-90°	36.4	0.8
90°-100°	207.1	4.4
100°-110°	445.2	9.5
110°-120°	417.8	8.9
120°-130°	338.6	7.2
130°-140°	271.7	5.8
140°-150°	205.1	4.4
150°-160°	144.3	3.1
160°-170°	85.1	1.8
170°-180°	27.7	0.6
0°-30°	766.7	16.3
0°-40°	1279.9	27.3
0°-60°	2118.5	45.1
0°-90°	2552.0	54.4
90°-120°	1070.2	22.8
90°-150°	1885.6	40.2
90°-180°	2143.0	45.6
0°-180°	4694.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1043	903	791	903	1043	105
15°	1302	865	620	865	1302	373
25°	1602	791	523	791	1602	732
35°	1286	688	448	688	1286	787
45°	606	543	372	543	606	485
55°	374	383	304	383	374	337
65°	229	236	236	236	229	228
75°	113	114	145	114	113	121
85°	25	23	36	23	25	30
90°	13	1	13	1	13	10
95°	135	19	135	19	135	192
105°	763	65	763	65	763	759
115°	850	116	850	116	850	831
125°	670	161	670	161	670	606
135°	556	189	556	189	556	431
145°	439	220	439	220	439	279
155°	368	251	368	251	368	172
165°	323	274	323	274	323	92
175°	290	285	290	285	290	28
180°	286	286	286	286	286	



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	956.0	954.7	953.5	951.1	952.9	947.7	945.2	941.0	935.7	933.9	931.7
5°	1042.7	1044.6	1046.5	1038.4	1039.3	1033.9	1021.6	1011.6	1003.6	993.2	985.9
7.5°	1147.0	1142.5	1142.2	1136.9	1127.9	1120.7	1107.8	1091.4	1075.5	1057.4	1042.5
10°	1199.2	1199.6	1196.2	1190.0	1180.4	1173.5	1156.6	1140.5	1121.0	1097.9	1081.5
12.5°	1238.5	1240.1	1235.8	1227.5	1222.7	1207.3	1194.1	1174.9	1151.7	1133.3	1108.1
15°	1302.0	1297.8	1294.7	1284.3	1276.3	1260.2	1239.1	1219.1	1193.9	1170.4	1147.0
17.5°	1363.2	1366.7	1360.9	1351.4	1326.5	1307.6	1279.3	1252.0	1220.4	1189.1	1161.1
20°	1417.9	1421.0	1412.1	1395.6	1365.7	1346.9	1309.7	1274.3	1238.0	1197.7	1167.0
22.5°	1486.0	1483.6	1471.7	1446.5	1420.7	1385.8	1345.6	1302.6	1257.0	1211.4	1170.6
25°	1602.0	1585.9	1578.6	1547.5	1513.4	1462.4	1407.1	1344.2	1287.5	1227.2	1175.1
27.5°	1666.3	1661.2	1653.1	1631.4	1595.6	1541.1	1475.9	1399.3	1319.1	1243.1	1174.8
30°	1653.5	1654.2	1655.0	1648.0	1625.1	1584.0	1519.1	1436.6	1341.5	1256.0	1177.0
32.5°	1539.2	1553.2	1566.6	1582.4	1588.8	1580.9	1540.3	1465.8	1368.0	1270.7	1175.7
35°	1285.9	1290.1	1333.5	1376.4	1434.7	1480.1	1510.4	1477.3	1394.8	1283.2	1174.3
37.5°	1002.6	1023.4	1053.4	1102.0	1186.1	1261.4	1358.4	1402.9	1376.2	1287.3	1171.5
40°	854.7	873.9	893.4	942.9	1013.9	1105.2	1215.3	1309.3	1331.2	1274.3	1162.4
42.5°	740.5	755.8	777.5	814.7	873.9	954.8	1060.1	1182.9	1258.4	1237.0	1143.1
45°	606.1	615.7	632.6	662.2	705.1	768.4	861.2	995.5	1112.5	1151.2	1097.1
47.5°	518.8	518.8	531.9	552.3	583.3	637.0	705.7	810.9	935.8	1028.3	1024.0
50°	470.3	468.4	478.8	496.4	521.0	556.6	622.3	706.3	826.4	931.1	960.2
52.5°	428.6	428.8	435.2	448.2	468.8	499.3	548.3	624.0	726.6	834.0	889.0
55°	373.7	372.1	379.4	388.2	403.2	423.1	458.5	516.3	599.6	705.5	776.8
57.5°	323.4	327.5	330.4	336.6	349.0	362.3	392.1	434.6	500.7	591.6	667.0
60°	293.9	298.1	300.3	306.5	316.5	328.0	351.0	385.6	441.2	519.5	594.2
62.5°	267.4	270.7	271.6	277.0	285.2	296.4	314.5	343.5	387.5	455.9	529.2
65°	229.4	229.4	231.0	236.7	240.5	250.5	264.3	285.4	320.7	374.1	436.6
67.5°	192.7	194.6	194.2	196.7	200.3	208.0	217.9	235.3	261.5	300.3	350.4
70°	168.7	170.4	170.0	171.9	175.7	180.7	188.7	205.2	224.0	257.4	300.3
72.5°	147.3	147.9	146.9	149.5	151.8	156.1	165.1	173.9	191.5	219.6	255.0
75°	112.8	113.5	114.3	115.8	118.2	120.5	125.0	133.9	145.4	166.5	189.1
77.5°	84.5	83.1	84.9	84.7	86.0	87.8	91.8	96.5	105.9	119.3	136.8
80°	63.7	64.0	64.0	64.4	66.3	67.6	71.0	74.4	81.7	91.7	103.9
82.5°	46.5	47.5	46.9	47.6	49.2	50.0	51.9	54.7	59.0	66.9	75.7
85°	25.3	23.4	24.1	24.9	24.9	25.3	26.9	28.0	30.3	33.3	36.9
87.5°	10.0	10.6	10.8	10.8	11.1	10.9	12.0	11.9	12.7	13.5	14.5
90°	13.2	13.2	12.6	12.6	12.6	11.5	10.9	10.4	9.8	9.2	8.1
92.5°	36.8	37.7	38.5	39.9	47.3	55.7	74.1	102.1	150.4	185.7	188.7
95°	135.4	144.6	149.2	166.5	207.4	255.8	326.6	414.1	499.5	510.4	416.5
97.5°	327.2	334.6	351.2	383.5	419.1	486.5	555.4	616.8	632.0	545.0	371.9
100°	449.3	458.6	479.9	521.3	561.1	621.0	680.3	708.5	664.2	520.2	331.8
102.5°	585.7	592.7	615.8	645.3	687.8	728.3	756.8	739.4	644.8	476.4	301.3
105°	763.3	770.2	781.7	800.7	819.1	825.5	800.1	721.2	583.0	417.7	271.9
107.5°	857.5	862.1	866.0	866.1	856.7	826.7	761.5	656.2	519.9	377.2	259.4
110°	888.9	888.9	884.8	873.8	848.0	799.0	717.8	608.3	483.9	358.3	255.8



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	885.1	881.0	871.0	852.2	814.4	756.6	674.5	570.6	457.2	347.3	255.8
115°	850.3	842.7	826.7	799.0	754.1	691.3	612.4	523.0	428.0	335.3	257.5
117.5°	789.1	784.5	768.5	739.9	695.0	637.3	569.4	492.4	410.6	329.4	261.3
120°	749.4	744.9	729.3	701.7	659.0	608.3	544.9	475.8	400.9	326.6	265.0
122.5°	714.4	710.2	694.7	669.3	631.4	583.9	527.5	463.4	392.6	324.4	268.2
125°	669.9	664.2	651.6	627.9	595.6	554.2	504.0	445.2	381.3	321.4	273.7
127.5°	632.0	629.3	617.4	596.5	567.3	528.5	481.7	426.9	371.0	320.0	279.7
130°	611.2	607.7	596.2	577.2	548.4	511.0	466.1	415.4	364.1	319.1	283.5
132.5°	590.5	586.5	575.9	556.9	528.2	492.1	451.3	403.8	358.5	319.1	287.6
135°	556.4	553.0	542.6	523.6	498.3	465.4	428.6	388.8	351.9	319.1	293.2
137.5°	520.2	516.3	506.9	489.5	466.9	439.0	408.3	376.2	346.1	319.8	298.4
140°	494.8	491.9	483.3	468.4	447.1	422.8	396.4	369.2	343.4	320.3	300.7
142.5°	471.3	468.9	460.7	448.1	430.0	409.0	386.2	363.2	341.0	320.7	302.1
145°	439.0	436.7	430.3	420.5	406.7	391.1	373.2	355.5	337.6	320.3	303.6
147.5°	411.5	410.5	406.8	399.0	388.0	376.3	362.5	348.1	334.0	318.8	304.2
150°	396.4	395.8	393.4	386.6	377.9	367.5	356.6	343.9	331.2	317.4	304.2
152.5°	384.4	383.7	381.4	376.0	368.7	360.6	350.6	339.3	328.0	315.6	303.7
155°	368.1	367.5	365.8	361.7	356.0	349.6	341.6	332.3	322.6	312.3	302.5
157.5°	353.6	353.7	352.0	348.7	344.3	339.3	333.1	325.5	317.5	308.7	300.9
160°	343.9	344.5	343.4	340.4	336.4	332.3	326.6	320.8	313.4	306.5	299.5
162.5°	335.2	335.3	335.1	332.6	329.5	325.9	321.1	315.8	309.7	303.7	298.2
165°	322.6	322.6	322.6	321.4	319.1	316.3	312.8	308.7	304.2	299.5	296.1
167.5°	311.0	311.1	311.6	310.6	309.4	307.4	304.8	302.1	298.7	295.5	292.9
170°	304.2	304.8	304.8	304.2	303.0	301.8	300.1	298.4	295.5	293.2	291.4
172.5°	297.7	298.3	299.2	298.2	297.9	297.2	296.0	294.3	292.3	290.4	289.6
175°	289.7	290.3	291.4	290.9	290.9	290.9	289.7	289.7	288.0	287.4	287.4
177.5°	285.7	285.7	287.1	286.6	287.1	287.1	287.1	286.6	286.2	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	929.9	927.8	925.3	921.0	915.7	913.0	908.8	905.9	900.4	895.9	890.9
5°	977.0	967.1	958.0	946.0	933.0	924.5	914.5	903.4	891.9	880.0	867.0
7.5°	1025.9	1008.4	989.2	968.5	948.4	929.8	912.0	894.6	878.4	858.7	842.0
10°	1058.8	1036.5	1012.8	984.7	957.6	933.7	909.6	888.5	867.0	843.9	823.6
12.5°	1091.7	1062.0	1028.4	997.6	964.9	936.2	907.8	880.8	853.8	828.3	804.7
15°	1114.8	1088.7	1057.6	1013.9	977.0	937.6	900.0	865.1	832.4	804.1	774.2
17.5°	1130.0	1096.5	1063.1	1021.2	972.9	928.7	886.1	846.2	809.4	773.4	744.6
20°	1132.9	1098.3	1063.4	1022.4	972.9	922.2	879.7	831.7	792.1	755.0	719.6
22.5°	1132.0	1092.8	1054.8	1012.5	964.3	917.7	866.2	817.3	774.4	737.8	700.9
25°	1123.3	1081.5	1033.9	991.3	943.7	894.2	842.0	791.4	747.7	705.9	669.4
27.5°	1116.0	1061.8	1007.9	958.3	912.3	867.0	817.1	765.2	716.7	674.3	640.0
30°	1107.1	1047.6	987.0	935.2	888.1	843.9	796.8	746.2	695.5	654.1	617.2
32.5°	1099.1	1029.9	965.9	909.5	859.6	816.7	773.2	725.0	675.3	633.2	596.4
35°	1083.8	1003.6	930.3	866.6	813.2	769.2	732.8	687.8	642.2	601.5	566.2
37.5°	1064.2	969.1	890.4	823.6	765.2	718.7	684.8	650.4	606.5	567.3	535.4
40°	1048.8	944.5	861.2	792.9	732.4	684.0	652.6	620.0	583.5	547.0	513.3
42.5°	1029.5	922.4	831.7	758.3	698.3	651.2	618.1	590.5	558.4	524.3	493.0
45°	994.0	882.3	784.2	705.1	644.5	598.0	563.9	543.2	519.1	486.9	460.4
47.5°	941.7	834.2	732.7	651.1	588.5	545.5	513.5	493.6	476.7	452.7	428.7
50°	895.3	798.3	695.5	614.6	552.0	508.7	479.2	461.1	446.6	428.1	407.8
52.5°	843.5	753.2	659.0	579.0	517.1	474.3	445.4	429.5	417.4	404.1	384.2
55°	761.1	684.4	596.9	521.0	463.8	422.0	396.7	382.8	372.8	362.9	350.6
57.5°	670.3	610.4	532.8	463.4	410.8	372.7	349.1	335.7	327.9	322.8	315.6
60°	606.5	555.1	488.4	425.1	373.7	339.9	316.9	306.5	300.0	295.8	290.4
62.5°	547.2	505.0	443.2	385.5	340.5	308.6	288.0	278.0	271.8	269.7	265.2
65°	460.0	427.4	376.4	328.4	290.0	262.8	245.5	235.9	232.1	229.7	230.1
67.5°	374.0	354.1	313.2	272.3	241.6	218.7	204.9	197.5	195.6	192.6	192.5
70°	321.4	306.5	272.0	236.3	209.0	191.5	179.2	171.5	169.6	168.0	167.6
72.5°	275.1	262.1	232.1	203.5	179.0	163.5	153.4	148.8	145.6	144.7	144.6
75°	206.8	199.4	175.7	153.1	136.2	125.4	118.6	114.3	112.0	111.6	112.0
77.5°	147.0	140.7	125.5	109.5	98.9	90.7	84.8	83.4	80.8	80.9	80.5
80°	110.5	106.2	96.6	84.0	75.2	68.3	65.2	62.5	61.8	60.6	61.8
82.5°	80.1	75.5	69.1	61.0	53.7	49.6	46.5	45.6	45.1	44.6	44.8
85°	39.5	39.9	36.1	29.9	26.9	24.5	22.6	22.6	22.2	21.9	22.2
87.5°	15.0	14.1	12.8	11.6	9.9	8.8	8.2	8.4	7.6	7.5	8.1
90°	7.5	6.4	5.8	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	131.5	78.7	47.3	30.4	20.5	13.3	8.5	7.1	8.5	13.3	20.5
95°	257.5	130.8	69.2	43.2	30.5	24.2	19.6	19.0	19.6	24.2	30.5
97.5°	205.5	112.7	71.9	53.2	41.8	35.4	32.2	31.6	32.2	35.4	41.8
100°	186.6	111.8	78.4	61.1	50.1	43.8	41.5	40.3	41.5	43.8	50.1
102.5°	178.8	115.9	86.1	69.4	59.4	52.5	50.7	50.0	50.7	52.5	59.4
105°	175.7	124.4	99.1	82.9	73.7	68.0	65.1	65.1	65.1	68.0	73.7
107.5°	181.0	137.1	112.6	98.1	88.5	83.7	81.0	79.9	81.0	83.7	88.5
110°	186.0	146.3	122.7	107.8	99.1	93.9	91.6	90.5	91.6	93.9	99.1



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	192.5	155.1	132.4	117.9	109.3	104.0	102.2	101.1	102.2	104.0	109.3
115°	202.2	168.7	147.4	133.1	124.4	119.3	117.5	116.3	117.5	119.3	124.4
117.5°	213.3	182.9	162.7	148.8	139.0	133.8	131.9	130.2	131.9	133.8	139.0
120°	220.7	193.0	172.8	158.4	148.7	143.4	141.2	139.4	141.2	143.4	148.7
122.5°	228.9	202.7	182.5	168.1	157.3	152.2	150.4	149.1	150.4	152.2	157.3
125°	240.2	215.4	196.4	181.5	170.5	165.3	162.5	161.3	162.5	165.3	170.5
127.5°	250.5	227.7	209.4	194.5	182.9	176.3	172.6	170.9	172.6	176.3	182.9
130°	257.5	235.6	217.7	202.8	190.7	183.2	178.5	176.8	178.5	183.2	190.7
132.5°	263.5	243.0	225.1	210.2	197.6	189.1	183.7	181.5	183.7	189.1	197.6
135°	271.9	252.9	235.0	219.4	207.4	198.1	191.3	188.9	191.3	198.1	207.4
137.5°	278.1	259.9	243.7	227.6	215.8	206.6	200.2	198.4	200.2	206.6	215.8
140°	282.3	265.0	248.3	232.8	221.8	212.6	205.6	203.9	205.6	212.6	221.8
142.5°	284.6	268.2	252.5	237.8	227.3	218.1	211.7	210.4	211.7	218.1	227.3
145°	288.0	273.7	258.6	245.4	235.0	226.9	221.2	220.0	221.2	226.9	235.0
147.5°	290.1	277.1	264.0	252.3	243.3	235.8	230.9	230.1	230.9	235.8	243.3
150°	291.4	279.4	266.7	256.9	248.8	241.4	237.3	236.2	237.3	241.4	248.8
152.5°	292.4	281.7	269.9	261.1	253.5	246.9	243.3	242.7	243.3	246.9	253.5
155°	293.2	284.0	274.2	266.1	260.3	254.6	251.2	251.2	251.2	254.6	260.3
157.5°	293.8	286.0	277.5	271.5	266.4	261.5	258.6	258.7	258.6	261.5	266.4
160°	293.8	286.9	279.4	274.2	269.6	265.6	263.3	263.9	263.3	265.6	269.6
162.5°	293.4	287.8	281.2	277.0	273.3	269.7	267.4	268.0	267.4	269.7	273.3
165°	292.7	288.0	283.5	279.9	277.6	274.8	273.1	274.2	273.1	274.8	277.6
167.5°	291.2	288.0	284.2	282.1	280.4	278.8	277.8	278.3	277.8	278.8	280.4
170°	290.3	288.0	285.2	283.5	282.3	281.1	280.5	281.1	280.5	281.1	282.3
172.5°	289.4	287.6	285.2	284.4	283.7	282.5	282.0	283.0	282.0	282.5	283.7
175°	288.0	286.9	285.2	285.2	285.2	284.6	284.0	285.2	284.0	284.6	285.2
177.5°	286.6	286.2	285.3	285.3	285.7	285.3	285.3	286.2	285.3	285.3	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	888.2	884.7	882.0	875.9	872.5	867.9	864.2	868.2	863.9	865.8	863.0
5°	860.5	849.7	842.0	830.9	821.3	812.5	806.0	804.9	801.7	800.2	795.7
7.5°	827.2	813.7	800.5	786.0	773.7	761.2	753.2	746.6	742.3	736.5	732.6
10°	807.5	789.5	774.2	756.5	741.1	727.7	717.0	711.7	706.6	699.3	696.7
12.5°	783.3	764.7	745.9	727.0	712.4	697.3	688.1	680.0	676.6	668.3	667.5
15°	754.2	726.2	707.8	688.6	668.2	656.0	648.3	639.5	635.7	630.0	625.7
17.5°	719.5	694.5	671.5	651.7	634.2	623.9	614.3	608.2	601.7	597.9	591.0
20°	694.4	670.6	647.5	626.4	613.0	601.2	593.5	587.7	580.8	578.9	572.0
22.5°	673.2	646.9	624.8	607.1	592.5	579.1	570.8	566.8	562.1	556.1	554.8
25°	638.7	611.5	592.7	575.0	562.0	549.8	544.0	539.0	534.4	530.2	528.7
27.5°	608.9	584.6	562.3	546.3	535.0	523.8	518.8	512.7	509.3	505.9	501.8
30°	588.1	563.2	543.6	528.3	515.9	506.0	500.6	496.4	493.3	490.3	488.0
32.5°	566.6	543.5	524.5	509.6	497.3	489.8	484.9	482.0	478.6	474.9	472.0
35°	538.3	512.9	494.5	481.4	471.8	466.1	460.7	458.1	454.2	454.2	451.1
37.5°	506.2	484.3	468.1	456.2	447.6	442.4	436.7	434.8	432.3	430.7	429.7
40°	487.2	466.9	451.5	439.6	430.4	426.2	421.6	418.5	417.0	415.1	414.3
42.5°	467.6	448.2	433.4	422.4	414.4	410.8	406.6	404.5	401.3	398.8	398.4
45°	437.7	418.9	405.5	396.7	389.8	385.6	382.8	378.3	376.7	373.7	373.2
47.5°	409.4	391.3	378.2	370.9	364.9	361.4	357.2	352.6	350.8	349.3	349.2
50°	388.2	371.7	359.4	352.5	346.8	341.8	337.6	334.6	333.4	333.4	334.2
52.5°	366.8	352.7	342.2	333.9	328.4	323.1	319.2	317.3	315.6	317.4	318.8
55°	335.3	321.1	313.5	305.4	300.0	293.9	292.0	291.1	290.0	293.1	294.6
57.5°	301.9	292.1	283.1	275.1	270.2	266.7	264.1	263.7	265.8	267.2	272.3
60°	280.8	269.3	261.3	255.1	249.3	247.0	246.3	245.5	247.0	251.3	257.8
62.5°	257.5	248.1	239.4	234.9	230.7	226.8	226.6	227.1	230.1	235.0	241.6
65°	223.3	215.2	209.4	204.1	200.7	198.3	199.1	200.7	204.1	210.7	217.9
67.5°	188.5	183.0	177.8	173.5	170.2	170.2	171.0	173.3	177.3	184.8	191.5
70°	166.1	160.0	155.7	153.8	151.2	149.7	151.9	155.7	159.2	166.1	171.9
72.5°	143.7	138.5	135.2	133.9	132.7	131.5	132.3	136.4	141.1	148.0	154.7
75°	110.5	108.6	106.2	104.7	103.6	104.3	105.1	109.0	112.8	120.1	127.7
77.5°	80.7	78.7	77.3	76.9	76.2	76.6	78.8	81.6	85.4	90.7	96.5
80°	61.0	60.2	59.5	59.1	59.1	59.5	62.5	64.4	67.9	72.9	77.5
82.5°	44.4	43.9	43.8	43.7	44.0	44.1	45.9	48.5	51.3	55.1	59.1
85°	23.4	22.6	23.8	24.1	23.4	24.5	25.3	26.9	28.0	29.9	31.8
87.5°	8.6	9.4	9.3	9.8	9.9	10.7	10.5	11.9	12.6	13.3	13.2
90°	4.6	5.8	6.4	7.5	8.1	9.2	9.8	10.4	10.9	11.5	12.6
92.5°	30.4	47.3	78.7	131.5	188.7	185.7	150.4	102.1	74.1	55.7	47.3
95°	43.2	69.2	130.8	257.5	416.5	510.4	499.5	414.1	326.6	255.8	207.4
97.5°	53.2	71.9	112.7	205.5	371.9	545.0	632.0	616.8	555.4	486.5	419.1
100°	61.1	78.4	111.8	186.6	331.8	520.2	664.2	708.5	680.3	621.0	561.1
102.5°	69.4	86.1	115.9	178.8	301.3	476.4	644.8	739.4	756.8	728.3	687.8
105°	82.9	99.1	124.4	175.7	271.9	417.7	583.0	721.2	800.1	825.5	819.1
107.5°	98.1	112.6	137.1	181.0	259.4	377.2	519.9	656.2	761.5	826.7	856.7
110°	107.8	122.7	146.3	186.0	255.8	358.3	483.9	608.3	717.8	799.0	848.0



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.9	132.4	155.1	192.5	255.8	347.3	457.2	570.6	674.5	756.6	814.4
115°	133.1	147.4	168.7	202.2	257.5	335.3	428.0	523.0	612.4	691.3	754.1
117.5°	148.8	162.7	182.9	213.3	261.3	329.4	410.6	492.4	569.4	637.3	695.0
120°	158.4	172.8	193.0	220.7	265.0	326.6	400.9	475.8	544.9	608.3	659.0
122.5°	168.1	182.5	202.7	228.9	268.2	324.4	392.6	463.4	527.5	583.9	631.4
125°	181.5	196.4	215.4	240.2	273.7	321.4	381.3	445.2	504.0	554.2	595.6
127.5°	194.5	209.4	227.7	250.5	279.7	320.0	371.0	426.9	481.7	528.5	567.3
130°	202.8	217.7	235.6	257.5	283.5	319.1	364.1	415.4	466.1	511.0	548.4
132.5°	210.2	225.1	243.0	263.5	287.6	319.1	358.5	403.8	451.3	492.1	528.2
135°	219.4	235.0	252.9	271.9	293.2	319.1	351.9	388.8	428.6	465.4	498.3
137.5°	227.6	243.7	259.9	278.1	298.4	319.8	346.1	376.2	408.3	439.0	466.9
140°	232.8	248.3	265.0	282.3	300.7	320.3	343.4	369.2	396.4	422.8	447.1
142.5°	237.8	252.5	268.2	284.6	302.1	320.7	341.0	363.2	386.2	409.0	430.0
145°	245.4	258.6	273.7	288.0	303.6	320.3	337.6	355.5	373.2	391.1	406.7
147.5°	252.3	264.0	277.1	290.1	304.2	318.8	334.0	348.1	362.5	376.3	388.0
150°	256.9	266.7	279.4	291.4	304.2	317.4	331.2	343.9	356.6	367.5	377.9
152.5°	261.1	269.9	281.7	292.4	303.7	315.6	328.0	339.3	350.6	360.6	368.7
155°	266.1	274.2	284.0	293.2	302.5	312.3	322.6	332.3	341.6	349.6	356.0
157.5°	271.5	277.5	286.0	293.8	300.9	308.7	317.5	325.5	333.1	339.3	344.3
160°	274.2	279.4	286.9	293.8	299.5	306.5	313.4	320.8	326.6	332.3	336.4
162.5°	277.0	281.2	287.8	293.4	298.2	303.7	309.7	315.8	321.1	325.9	329.5
165°	279.9	283.5	288.0	292.7	296.1	299.5	304.2	308.7	312.8	316.3	319.1
167.5°	282.1	284.2	288.0	291.2	292.9	295.5	298.7	302.1	304.8	307.4	309.4
170°	283.5	285.2	288.0	290.3	291.4	293.2	295.5	298.4	300.1	301.8	303.0
172.5°	284.4	285.2	287.6	289.4	289.6	290.4	292.3	294.3	296.0	297.2	297.9
175°	285.2	285.2	286.9	288.0	287.4	287.4	288.0	289.7	289.7	290.9	290.9
177.5°	285.3	285.3	286.2	286.6	285.7	285.7	286.2	286.6	287.1	287.1	287.1
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	861.1	863.3	861.5	863.9	861.5	863.3	861.1	863.0	865.8	863.9	868.2
5°	793.8	790.2	792.5	791.0	792.5	790.2	793.8	795.7	800.2	801.7	804.9
7.5°	731.4	728.1	724.4	722.6	724.4	728.1	731.4	732.6	736.5	742.3	746.6
10°	692.5	688.2	687.8	685.2	687.8	688.2	692.5	696.7	699.3	706.6	711.7
12.5°	663.9	659.9	655.6	654.5	655.6	659.9	663.9	667.5	668.3	676.6	680.0
15°	623.4	620.4	617.6	620.0	617.6	620.4	623.4	625.7	630.0	635.7	639.5
17.5°	589.7	587.1	586.7	583.9	586.7	587.1	589.7	591.0	597.9	601.7	608.2
20°	568.6	566.6	567.3	562.4	567.3	566.6	568.6	572.0	578.9	580.8	587.7
22.5°	551.7	547.9	547.4	546.4	547.4	547.9	551.7	554.8	556.1	562.1	566.8
25°	525.2	523.3	521.4	523.3	521.4	523.3	525.2	528.7	530.2	534.4	539.0
27.5°	502.1	499.8	499.3	499.5	499.3	499.8	502.1	501.8	505.9	509.3	512.7
30°	488.0	484.1	484.5	484.1	484.5	484.1	488.0	488.0	490.3	493.3	496.4
32.5°	472.6	470.0	469.5	468.8	469.5	470.0	472.6	472.0	474.9	478.6	482.0
35°	450.0	450.0	448.1	448.1	448.1	450.0	450.0	451.1	454.2	454.2	458.1
37.5°	428.7	428.4	427.2	427.4	427.2	428.4	428.7	429.7	430.7	432.3	434.8
40°	412.7	412.4	411.2	408.9	411.2	412.4	412.7	414.3	415.1	417.0	418.5
42.5°	397.5	396.2	395.6	394.9	395.6	396.2	397.5	398.4	398.8	401.3	404.5
45°	373.2	373.2	372.5	372.1	372.5	373.2	373.2	373.2	373.7	376.7	378.3
47.5°	349.8	350.5	351.9	351.7	351.9	350.5	349.8	349.2	349.3	350.8	352.6
50°	335.7	336.1	337.2	337.6	337.2	336.1	335.7	334.2	333.4	333.4	334.6
52.5°	320.0	322.2	323.7	323.5	323.7	322.2	320.0	318.8	317.4	315.6	317.3
55°	298.1	300.7	303.5	303.9	303.5	300.7	298.1	294.6	293.1	290.0	291.1
57.5°	276.4	280.1	283.0	283.9	283.0	280.1	276.4	272.3	267.2	265.8	263.7
60°	261.7	266.6	270.0	271.7	270.0	266.6	261.7	257.8	251.3	247.0	245.5
62.5°	247.5	253.1	256.6	256.9	256.6	253.1	247.5	241.6	235.0	230.1	227.1
65°	224.4	230.1	233.3	235.5	233.3	230.1	224.4	217.9	210.7	204.1	200.7
67.5°	199.5	205.3	208.7	210.6	208.7	205.3	199.5	191.5	184.8	177.3	173.3
70°	181.5	187.2	191.8	193.4	191.8	187.2	181.5	171.9	166.1	159.2	155.7
72.5°	163.7	168.7	172.5	174.3	172.5	168.7	163.7	154.7	148.0	141.1	136.4
75°	132.7	139.7	143.1	145.0	143.1	139.7	132.7	127.7	120.1	112.8	109.0
77.5°	102.4	108.7	110.7	111.7	110.7	108.7	102.4	96.5	90.7	85.4	81.6
80°	82.1	85.9	88.7	89.0	88.7	85.9	82.1	77.5	72.9	67.9	64.4
82.5°	63.1	66.2	67.2	68.2	67.2	66.2	63.1	59.1	55.1	51.3	48.5
85°	34.5	36.1	36.5	36.1	36.5	36.1	34.5	31.8	29.9	28.0	26.9
87.5°	13.9	13.6	13.7	14.3	13.7	13.6	13.9	13.2	13.3	12.6	11.9
90°	12.6	12.6	13.2	13.2	13.2	12.6	12.6	12.6	11.5	10.9	10.4
92.5°	39.9	38.5	37.7	36.8	37.7	38.5	39.9	47.3	55.7	74.1	102.1
95°	166.5	149.2	144.6	135.4	144.6	149.2	166.5	207.4	255.8	326.6	414.1
97.5°	383.5	351.2	334.6	327.2	334.6	351.2	383.5	419.1	486.5	555.4	616.8
100°	521.3	479.9	458.6	449.3	458.6	479.9	521.3	561.1	621.0	680.3	708.5
102.5°	645.3	615.8	592.7	585.7	592.7	615.8	645.3	687.8	728.3	756.8	739.4
105°	800.7	781.7	770.2	763.3	770.2	781.7	800.7	819.1	825.5	800.1	721.2
107.5°	866.1	866.0	862.1	857.5	862.1	866.0	866.1	856.7	826.7	761.5	656.2
110°	873.8	884.8	888.9	888.9	888.9	884.8	873.8	848.0	799.0	717.8	608.3



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	852.2	871.0	881.0	885.1	881.0	871.0	852.2	814.4	756.6	674.5	570.6
115°	799.0	826.7	842.7	850.3	842.7	826.7	799.0	754.1	691.3	612.4	523.0
117.5°	739.9	768.5	784.5	789.1	784.5	768.5	739.9	695.0	637.3	569.4	492.4
120°	701.7	729.3	744.9	749.4	744.9	729.3	701.7	659.0	608.3	544.9	475.8
122.5°	669.3	694.7	710.2	714.4	710.2	694.7	669.3	631.4	583.9	527.5	463.4
125°	627.9	651.6	664.2	669.9	664.2	651.6	627.9	595.6	554.2	504.0	445.2
127.5°	596.5	617.4	629.3	632.0	629.3	617.4	596.5	567.3	528.5	481.7	426.9
130°	577.2	596.2	607.7	611.2	607.7	596.2	577.2	548.4	511.0	466.1	415.4
132.5°	556.9	575.9	586.5	590.5	586.5	575.9	556.9	528.2	492.1	451.3	403.8
135°	523.6	542.6	553.0	556.4	553.0	542.6	523.6	498.3	465.4	428.6	388.8
137.5°	489.5	506.9	516.3	520.2	516.3	506.9	489.5	466.9	439.0	408.3	376.2
140°	468.4	483.3	491.9	494.8	491.9	483.3	468.4	447.1	422.8	396.4	369.2
142.5°	448.1	460.7	468.9	471.3	468.9	460.7	448.1	430.0	409.0	386.2	363.2
145°	420.5	430.3	436.7	439.0	436.7	430.3	420.5	406.7	391.1	373.2	355.5
147.5°	399.0	406.8	410.5	411.5	410.5	406.8	399.0	388.0	376.3	362.5	348.1
150°	386.6	393.4	395.8	396.4	395.8	393.4	386.6	377.9	367.5	356.6	343.9
152.5°	376.0	381.4	383.7	384.4	383.7	381.4	376.0	368.7	360.6	350.6	339.3
155°	361.7	365.8	367.5	368.1	367.5	365.8	361.7	356.0	349.6	341.6	332.3
157.5°	348.7	352.0	353.7	353.6	353.7	352.0	348.7	344.3	339.3	333.1	325.5
160°	340.4	343.4	344.5	343.9	344.5	343.4	340.4	336.4	332.3	326.6	320.8
162.5°	332.6	335.1	335.3	335.2	335.3	335.1	332.6	329.5	325.9	321.1	315.8
165°	321.4	322.6	322.6	322.6	322.6	322.6	321.4	319.1	316.3	312.8	308.7
167.5°	310.6	311.6	311.1	311.0	311.1	311.6	310.6	309.4	307.4	304.8	302.1
170°	304.2	304.8	304.8	304.2	304.8	304.8	304.2	303.0	301.8	300.1	298.4
172.5°	298.2	299.2	298.3	297.7	298.3	299.2	298.2	297.9	297.2	296.0	294.3
175°	290.9	291.4	290.3	289.7	290.3	291.4	290.9	290.9	290.9	289.7	289.7
177.5°	286.6	287.1	285.7	285.7	285.7	287.1	286.6	287.1	287.1	287.1	286.6
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	864.2	867.9	872.5	875.9	882.0	884.7	888.2	890.9	895.9	900.4	905.9
5°	806.0	812.5	821.3	830.9	842.0	849.7	860.5	867.0	880.0	891.9	903.4
7.5°	753.2	761.2	773.7	786.0	800.5	813.7	827.2	842.0	858.7	878.4	894.6
10°	717.0	727.7	741.1	756.5	774.2	789.5	807.5	823.6	843.9	867.0	888.5
12.5°	688.1	697.3	712.4	727.0	745.9	764.7	783.3	804.7	828.3	853.8	880.8
15°	648.3	656.0	668.2	688.6	707.8	726.2	754.2	774.2	804.1	832.4	865.1
17.5°	614.3	623.9	634.2	651.7	671.5	694.5	719.5	744.6	773.4	809.4	846.2
20°	593.5	601.2	613.0	626.4	647.5	670.6	694.4	719.6	755.0	792.1	831.7
22.5°	570.8	579.1	592.5	607.1	624.8	646.9	673.2	700.9	737.8	774.4	817.3
25°	544.0	549.8	562.0	575.0	592.7	611.5	638.7	669.4	705.9	747.7	791.4
27.5°	518.8	523.8	535.0	546.3	562.3	584.6	608.9	640.0	674.3	716.7	765.2
30°	500.6	506.0	515.9	528.3	543.6	563.2	588.1	617.2	654.1	695.5	746.2
32.5°	484.9	489.8	497.3	509.6	524.5	543.5	566.6	596.4	633.2	675.3	725.0
35°	460.7	466.1	471.8	481.4	494.5	512.9	538.3	566.2	601.5	642.2	687.8
37.5°	436.7	442.4	447.6	456.2	468.1	484.3	506.2	535.4	567.3	606.5	650.4
40°	421.6	426.2	430.4	439.6	451.5	466.9	487.2	513.3	547.0	583.5	620.0
42.5°	406.6	410.8	414.4	422.4	433.4	448.2	467.6	493.0	524.3	558.4	590.5
45°	382.8	385.6	389.8	396.7	405.5	418.9	437.7	460.4	486.9	519.1	543.2
47.5°	357.2	361.4	364.9	370.9	378.2	391.3	409.4	428.7	452.7	476.7	493.6
50°	337.6	341.8	346.8	352.5	359.4	371.7	388.2	407.8	428.1	446.6	461.1
52.5°	319.2	323.1	328.4	333.9	342.2	352.7	366.8	384.2	404.1	417.4	429.5
55°	292.0	293.9	300.0	305.4	313.5	321.1	335.3	350.6	362.9	372.8	382.8
57.5°	264.1	266.7	270.2	275.1	283.1	292.1	301.9	315.6	322.8	327.9	335.7
60°	246.3	247.0	249.3	255.1	261.3	269.3	280.8	290.4	295.8	300.0	306.5
62.5°	226.6	226.8	230.7	234.9	239.4	248.1	257.5	265.2	269.7	271.8	278.0
65°	199.1	198.3	200.7	204.1	209.4	215.2	223.3	230.1	229.7	232.1	235.9
67.5°	171.0	170.2	170.2	173.5	177.8	183.0	188.5	192.5	192.6	195.6	197.5
70°	151.9	149.7	151.2	153.8	155.7	160.0	166.1	167.6	168.0	169.6	171.5
72.5°	132.3	131.5	132.7	133.9	135.2	138.5	143.7	144.6	144.7	145.6	148.8
75°	105.1	104.3	103.6	104.7	106.2	108.6	110.5	112.0	111.6	112.0	114.3
77.5°	78.8	76.6	76.2	76.9	77.3	78.7	80.7	80.5	80.9	80.8	83.4
80°	62.5	59.5	59.1	59.1	59.5	60.2	61.0	61.8	60.6	61.8	62.5
82.5°	45.9	44.1	44.0	43.7	43.8	43.9	44.4	44.8	44.6	45.1	45.6
85°	25.3	24.5	23.4	24.1	23.8	22.6	23.4	22.2	21.9	22.2	22.6
87.5°	10.5	10.7	9.9	9.8	9.3	9.4	8.6	8.1	7.5	7.6	8.4
90°	9.8	9.2	8.1	7.5	6.4	5.8	4.6	3.4	2.3	1.1	0.6
92.5°	150.4	185.7	188.7	131.5	78.7	47.3	30.4	20.5	13.3	8.5	7.1
95°	499.5	510.4	416.5	257.5	130.8	69.2	43.2	30.5	24.2	19.6	19.0
97.5°	632.0	545.0	371.9	205.5	112.7	71.9	53.2	41.8	35.4	32.2	31.6
100°	664.2	520.2	331.8	186.6	111.8	78.4	61.1	50.1	43.8	41.5	40.3
102.5°	644.8	476.4	301.3	178.8	115.9	86.1	69.4	59.4	52.5	50.7	50.0
105°	583.0	417.7	271.9	175.7	124.4	99.1	82.9	73.7	68.0	65.1	65.1
107.5°	519.9	377.2	259.4	181.0	137.1	112.6	98.1	88.5	83.7	81.0	79.9
110°	483.9	358.3	255.8	186.0	146.3	122.7	107.8	99.1	93.9	91.6	90.5



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.2	347.3	255.8	192.5	155.1	132.4	117.9	109.3	104.0	102.2	101.1
115°	428.0	335.3	257.5	202.2	168.7	147.4	133.1	124.4	119.3	117.5	116.3
117.5°	410.6	329.4	261.3	213.3	182.9	162.7	148.8	139.0	133.8	131.9	130.2
120°	400.9	326.6	265.0	220.7	193.0	172.8	158.4	148.7	143.4	141.2	139.4
122.5°	392.6	324.4	268.2	228.9	202.7	182.5	168.1	157.3	152.2	150.4	149.1
125°	381.3	321.4	273.7	240.2	215.4	196.4	181.5	170.5	165.3	162.5	161.3
127.5°	371.0	320.0	279.7	250.5	227.7	209.4	194.5	182.9	176.3	172.6	170.9
130°	364.1	319.1	283.5	257.5	235.6	217.7	202.8	190.7	183.2	178.5	176.8
132.5°	358.5	319.1	287.6	263.5	243.0	225.1	210.2	197.6	189.1	183.7	181.5
135°	351.9	319.1	293.2	271.9	252.9	235.0	219.4	207.4	198.1	191.3	188.9
137.5°	346.1	319.8	298.4	278.1	259.9	243.7	227.6	215.8	206.6	200.2	198.4
140°	343.4	320.3	300.7	282.3	265.0	248.3	232.8	221.8	212.6	205.6	203.9
142.5°	341.0	320.7	302.1	284.6	268.2	252.5	237.8	227.3	218.1	211.7	210.4
145°	337.6	320.3	303.6	288.0	273.7	258.6	245.4	235.0	226.9	221.2	220.0
147.5°	334.0	318.8	304.2	290.1	277.1	264.0	252.3	243.3	235.8	230.9	230.1
150°	331.2	317.4	304.2	291.4	279.4	266.7	256.9	248.8	241.4	237.3	236.2
152.5°	328.0	315.6	303.7	292.4	281.7	269.9	261.1	253.5	246.9	243.3	242.7
155°	322.6	312.3	302.5	293.2	284.0	274.2	266.1	260.3	254.6	251.2	251.2
157.5°	317.5	308.7	300.9	293.8	286.0	277.5	271.5	266.4	261.5	258.6	258.7
160°	313.4	306.5	299.5	293.8	286.9	279.4	274.2	269.6	265.6	263.3	263.9
162.5°	309.7	303.7	298.2	293.4	287.8	281.2	277.0	273.3	269.7	267.4	268.0
165°	304.2	299.5	296.1	292.7	288.0	283.5	279.9	277.6	274.8	273.1	274.2
167.5°	298.7	295.5	292.9	291.2	288.0	284.2	282.1	280.4	278.8	277.8	278.3
170°	295.5	293.2	291.4	290.3	288.0	285.2	283.5	282.3	281.1	280.5	281.1
172.5°	292.3	290.4	289.6	289.4	287.6	285.2	284.4	283.7	282.5	282.0	283.0
175°	288.0	287.4	287.4	288.0	286.9	285.2	285.2	285.2	284.6	284.0	285.2
177.5°	286.2	285.7	285.7	286.6	286.2	285.3	285.3	285.7	285.3	285.3	286.2
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	908.8	913.0	915.7	921.0	925.3	927.8	929.9	931.7	933.9	935.7	941.0
5°	914.5	924.5	933.0	946.0	958.0	967.1	977.0	985.9	993.2	1003.6	1011.6
7.5°	912.0	929.8	948.4	968.5	989.2	1008.4	1025.9	1042.5	1057.4	1075.5	1091.4
10°	909.6	933.7	957.6	984.7	1012.8	1036.5	1058.8	1081.5	1097.9	1121.0	1140.5
12.5°	907.8	936.2	964.9	997.6	1028.4	1062.0	1091.7	1108.1	1133.3	1151.7	1174.9
15°	900.0	937.6	977.0	1013.9	1057.6	1088.7	1114.8	1147.0	1170.4	1193.9	1219.1
17.5°	886.1	928.7	972.9	1021.2	1063.1	1096.5	1130.0	1161.1	1189.1	1220.4	1252.0
20°	879.7	922.2	972.9	1022.4	1063.4	1098.3	1132.9	1167.0	1197.7	1238.0	1274.3
22.5°	866.2	917.7	964.3	1012.5	1054.8	1092.8	1132.0	1170.6	1211.4	1257.0	1302.6
25°	842.0	894.2	943.7	991.3	1033.9	1081.5	1123.3	1175.1	1227.2	1287.5	1344.2
27.5°	817.1	867.0	912.3	958.3	1007.9	1061.8	1116.0	1174.8	1243.1	1319.1	1399.3
30°	796.8	843.9	888.1	935.2	987.0	1047.6	1107.1	1177.0	1256.0	1341.5	1436.6
32.5°	773.2	816.7	859.6	909.5	965.9	1029.9	1099.1	1175.7	1270.7	1368.0	1465.8
35°	732.8	769.2	813.2	866.6	930.3	1003.6	1083.8	1174.3	1283.2	1394.8	1477.3
37.5°	684.8	718.7	765.2	823.6	890.4	969.1	1064.2	1171.5	1287.3	1376.2	1402.9
40°	652.6	684.0	732.4	792.9	861.2	944.5	1048.8	1162.4	1274.3	1331.2	1309.3
42.5°	618.1	651.2	698.3	758.3	831.7	922.4	1029.5	1143.1	1237.0	1258.4	1182.9
45°	563.9	598.0	644.5	705.1	784.2	882.3	994.0	1097.1	1151.2	1112.5	995.5
47.5°	513.5	545.5	588.5	651.1	732.7	834.2	941.7	1024.0	1028.3	935.8	810.9
50°	479.2	508.7	552.0	614.6	695.5	798.3	895.3	960.2	931.1	826.4	706.3
52.5°	445.4	474.3	517.1	579.0	659.0	753.2	843.5	889.0	834.0	726.6	624.0
55°	396.7	422.0	463.8	521.0	596.9	684.4	761.1	776.8	705.5	599.6	516.3
57.5°	349.1	372.7	410.8	463.4	532.8	610.4	670.3	667.0	591.6	500.7	434.6
60°	316.9	339.9	373.7	425.1	488.4	555.1	606.5	594.2	519.5	441.2	385.6
62.5°	288.0	308.6	340.5	385.5	443.2	505.0	547.2	529.2	455.9	387.5	343.5
65°	245.5	262.8	290.0	328.4	376.4	427.4	460.0	436.6	374.1	320.7	285.4
67.5°	204.9	218.7	241.6	272.3	313.2	354.1	374.0	350.4	300.3	261.5	235.3
70°	179.2	191.5	209.0	236.3	272.0	306.5	321.4	300.3	257.4	224.0	205.2
72.5°	153.4	163.5	179.0	203.5	232.1	262.1	275.1	255.0	219.6	191.5	173.9
75°	118.6	125.4	136.2	153.1	175.7	199.4	206.8	189.1	166.5	145.4	133.9
77.5°	84.8	90.7	98.9	109.5	125.5	140.7	147.0	136.8	119.3	105.9	96.5
80°	65.2	68.3	75.2	84.0	96.6	106.2	110.5	103.9	91.7	81.7	74.4
82.5°	46.5	49.6	53.7	61.0	69.1	75.5	80.1	75.7	66.9	59.0	54.7
85°	22.6	24.5	26.9	29.9	36.1	39.9	39.5	36.9	33.3	30.3	28.0
87.5°	8.2	8.8	9.9	11.6	12.8	14.1	15.0	14.5	13.5	12.7	11.9
90°	1.1	2.3	3.4	4.6	5.8	6.4	7.5	8.1	9.2	9.8	10.4
92.5°	8.5	13.3	20.5	30.4	47.3	78.7	131.5	188.7	185.7	150.4	102.1
95°	19.6	24.2	30.5	43.2	69.2	130.8	257.5	416.5	510.4	499.5	414.1
97.5°	32.2	35.4	41.8	53.2	71.9	112.7	205.5	371.9	545.0	632.0	616.8
100°	41.5	43.8	50.1	61.1	78.4	111.8	186.6	331.8	520.2	664.2	708.5
102.5°	50.7	52.5	59.4	69.4	86.1	115.9	178.8	301.3	476.4	644.8	739.4
105°	65.1	68.0	73.7	82.9	99.1	124.4	175.7	271.9	417.7	583.0	721.2
107.5°	81.0	83.7	88.5	98.1	112.6	137.1	181.0	259.4	377.2	519.9	656.2
110°	91.6	93.9	99.1	107.8	122.7	146.3	186.0	255.8	358.3	483.9	608.3



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	102.2	104.0	109.3	117.9	132.4	155.1	192.5	255.8	347.3	457.2	570.6
115°	117.5	119.3	124.4	133.1	147.4	168.7	202.2	257.5	335.3	428.0	523.0
117.5°	131.9	133.8	139.0	148.8	162.7	182.9	213.3	261.3	329.4	410.6	492.4
120°	141.2	143.4	148.7	158.4	172.8	193.0	220.7	265.0	326.6	400.9	475.8
122.5°	150.4	152.2	157.3	168.1	182.5	202.7	228.9	268.2	324.4	392.6	463.4
125°	162.5	165.3	170.5	181.5	196.4	215.4	240.2	273.7	321.4	381.3	445.2
127.5°	172.6	176.3	182.9	194.5	209.4	227.7	250.5	279.7	320.0	371.0	426.9
130°	178.5	183.2	190.7	202.8	217.7	235.6	257.5	283.5	319.1	364.1	415.4
132.5°	183.7	189.1	197.6	210.2	225.1	243.0	263.5	287.6	319.1	358.5	403.8
135°	191.3	198.1	207.4	219.4	235.0	252.9	271.9	293.2	319.1	351.9	388.8
137.5°	200.2	206.6	215.8	227.6	243.7	259.9	278.1	298.4	319.8	346.1	376.2
140°	205.6	212.6	221.8	232.8	248.3	265.0	282.3	300.7	320.3	343.4	369.2
142.5°	211.7	218.1	227.3	237.8	252.5	268.2	284.6	302.1	320.7	341.0	363.2
145°	221.2	226.9	235.0	245.4	258.6	273.7	288.0	303.6	320.3	337.6	355.5
147.5°	230.9	235.8	243.3	252.3	264.0	277.1	290.1	304.2	318.8	334.0	348.1
150°	237.3	241.4	248.8	256.9	266.7	279.4	291.4	304.2	317.4	331.2	343.9
152.5°	243.3	246.9	253.5	261.1	269.9	281.7	292.4	303.7	315.6	328.0	339.3
155°	251.2	254.6	260.3	266.1	274.2	284.0	293.2	302.5	312.3	322.6	332.3
157.5°	258.6	261.5	266.4	271.5	277.5	286.0	293.8	300.9	308.7	317.5	325.5
160°	263.3	265.6	269.6	274.2	279.4	286.9	293.8	299.5	306.5	313.4	320.8
162.5°	267.4	269.7	273.3	277.0	281.2	287.8	293.4	298.2	303.7	309.7	315.8
165°	273.1	274.8	277.6	279.9	283.5	288.0	292.7	296.1	299.5	304.2	308.7
167.5°	277.8	278.8	280.4	282.1	284.2	288.0	291.2	292.9	295.5	298.7	302.1
170°	280.5	281.1	282.3	283.5	285.2	288.0	290.3	291.4	293.2	295.5	298.4
172.5°	282.0	282.5	283.7	284.4	285.2	287.6	289.4	289.6	290.4	292.3	294.3
175°	284.0	284.6	285.2	285.2	285.2	286.9	288.0	287.4	287.4	288.0	289.7
177.5°	285.3	285.3	285.7	285.3	285.3	286.2	286.6	285.7	285.7	286.2	286.6
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	945.2	947.7	952.9	951.1	953.5	954.7	956.0
5°	1021.6	1033.9	1039.3	1038.4	1046.5	1044.6	1042.7
7.5°	1107.8	1120.7	1127.9	1136.9	1142.2	1142.5	1147.0
10°	1156.6	1173.5	1180.4	1190.0	1196.2	1199.6	1199.2
12.5°	1194.1	1207.3	1222.7	1227.5	1235.8	1240.1	1238.5
15°	1239.1	1260.2	1276.3	1284.3	1294.7	1297.8	1302.0
17.5°	1279.3	1307.6	1326.5	1351.4	1360.9	1366.7	1363.2
20°	1309.7	1346.9	1365.7	1395.6	1412.1	1421.0	1417.9
22.5°	1345.6	1385.8	1420.7	1446.5	1471.7	1483.6	1486.0
25°	1407.1	1462.4	1513.4	1547.5	1578.6	1585.9	1602.0
27.5°	1475.9	1541.1	1595.6	1631.4	1653.1	1661.2	1666.3
30°	1519.1	1584.0	1625.1	1648.0	1655.0	1654.2	1653.5
32.5°	1540.3	1580.9	1588.8	1582.4	1566.6	1553.2	1539.2
35°	1510.4	1480.1	1434.7	1376.4	1333.5	1290.1	1285.9
37.5°	1358.4	1261.4	1186.1	1102.0	1053.4	1023.4	1002.6
40°	1215.3	1105.2	1013.9	942.9	893.4	873.9	854.7
42.5°	1060.1	954.8	873.9	814.7	777.5	755.8	740.5
45°	861.2	768.4	705.1	662.2	632.6	615.7	606.1
47.5°	705.7	637.0	583.3	552.3	531.9	518.8	518.8
50°	622.3	556.6	521.0	496.4	478.8	468.4	470.3
52.5°	548.3	499.3	468.8	448.2	435.2	428.8	428.6
55°	458.5	423.1	403.2	388.2	379.4	372.1	373.7
57.5°	392.1	362.3	349.0	336.6	330.4	327.5	323.4
60°	351.0	328.0	316.5	306.5	300.3	298.1	293.9
62.5°	314.5	296.4	285.2	277.0	271.6	270.7	267.4
65°	264.3	250.5	240.5	236.7	231.0	229.4	229.4
67.5°	217.9	208.0	200.3	196.7	194.2	194.6	192.7
70°	188.7	180.7	175.7	171.9	170.0	170.4	168.7
72.5°	165.1	156.1	151.8	149.5	146.9	147.9	147.3
75°	125.0	120.5	118.2	115.8	114.3	113.5	112.8
77.5°	91.8	87.8	86.0	84.7	84.9	83.1	84.5
80°	71.0	67.6	66.3	64.4	64.0	64.0	63.7
82.5°	51.9	50.0	49.2	47.6	46.9	47.5	46.5
85°	26.9	25.3	24.9	24.9	24.1	23.4	25.3
87.5°	12.0	10.9	11.1	10.8	10.8	10.6	10.0
90°	10.9	11.5	12.6	12.6	12.6	13.2	13.2
92.5°	74.1	55.7	47.3	39.9	38.5	37.7	36.8
95°	326.6	255.8	207.4	166.5	149.2	144.6	135.4
97.5°	555.4	486.5	419.1	383.5	351.2	334.6	327.2
100°	680.3	621.0	561.1	521.3	479.9	458.6	449.3
102.5°	756.8	728.3	687.8	645.3	615.8	592.7	585.7
105°	800.1	825.5	819.1	800.7	781.7	770.2	763.3
107.5°	761.5	826.7	856.7	866.1	866.0	862.1	857.5
110°	717.8	799.0	848.0	873.8	884.8	888.9	888.9



TEST NUMBER: P333171-840

CATALOG NUMBER: S125DIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	674.5	756.6	814.4	852.2	871.0	881.0	885.1
115°	612.4	691.3	754.1	799.0	826.7	842.7	850.3
117.5°	569.4	637.3	695.0	739.9	768.5	784.5	789.1
120°	544.9	608.3	659.0	701.7	729.3	744.9	749.4
122.5°	527.5	583.9	631.4	669.3	694.7	710.2	714.4
125°	504.0	554.2	595.6	627.9	651.6	664.2	669.9
127.5°	481.7	528.5	567.3	596.5	617.4	629.3	632.0
130°	466.1	511.0	548.4	577.2	596.2	607.7	611.2
132.5°	451.3	492.1	528.2	556.9	575.9	586.5	590.5
135°	428.6	465.4	498.3	523.6	542.6	553.0	556.4
137.5°	408.3	439.0	466.9	489.5	506.9	516.3	520.2
140°	396.4	422.8	447.1	468.4	483.3	491.9	494.8
142.5°	386.2	409.0	430.0	448.1	460.7	468.9	471.3
145°	373.2	391.1	406.7	420.5	430.3	436.7	439.0
147.5°	362.5	376.3	388.0	399.0	406.8	410.5	411.5
150°	356.6	367.5	377.9	386.6	393.4	395.8	396.4
152.5°	350.6	360.6	368.7	376.0	381.4	383.7	384.4
155°	341.6	349.6	356.0	361.7	365.8	367.5	368.1
157.5°	333.1	339.3	344.3	348.7	352.0	353.7	353.6
160°	326.6	332.3	336.4	340.4	343.4	344.5	343.9
162.5°	321.1	325.9	329.5	332.6	335.1	335.3	335.2
165°	312.8	316.3	319.1	321.4	322.6	322.6	322.6
167.5°	304.8	307.4	309.4	310.6	311.6	311.1	311.0
170°	300.1	301.8	303.0	304.2	304.8	304.8	304.2
172.5°	296.0	297.2	297.9	298.2	299.2	298.3	297.7
175°	289.7	290.9	290.9	290.9	291.4	290.3	289.7
177.5°	287.1	287.1	287.1	286.6	287.1	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7

(END OF REPORT)