

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333582-840

Luminaire Tested: **S125RDIP-S1090D365U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333582-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D365U840-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5630.3 lumens  
Efficiency: N/A  
Efficacy: 129.4 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76
1	104	100	96	93	99	96	92	89	87	85	82	79	77	76	72	71	69	66
2	96	88	82	77	91	84	79	74	77	73	69	70	67	64	64	62	59	56
3	88	78	71	65	83	75	68	63	69	63	59	63	58	55	57	54	51	48
4	80	70	62	55	76	67	59	54	61	55	51	56	51	47	52	48	44	42
5	74	62	54	48	70	60	52	47	55	49	44	51	46	42	47	42	39	36
6	69	56	48	42	65	54	46	41	50	44	39	46	41	37	43	38	35	32
7	64	51	43	37	60	49	42	36	45	39	34	42	37	33	39	34	31	29
8	59	47	39	33	56	45	37	32	42	35	31	39	33	29	36	31	28	26
9	55	43	35	30	53	41	34	29	38	32	28	36	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10723	10723	10723	10723
5°	12337	10738	9483	10738
10°	14152	10683	8368	10683
15°	15285	10573	7438	10573
20°	16855	10446	6868	10446
25°	19506	10278	6372	10278
30°	21227	10100	6049	10100
35°	17906	9894	5750	9894
40°	12505	9522	5493	9522
45°	9276	9020	5242	9020
50°	7396	8499	5027	8499
55°	6277	7851	4835	7851
60°	5424	7272	4525	7272
65°	4834	6645	3895	6645
70°	4247	6086	3552	6086
75°	3673	5273	3334	5273
80°	2786	4437	2786	4437
85°	2319	3490	2623	3490



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.2	2.8
10°-20°	466.6	8.3
20°-30°	739.8	13.1
30°-40°	892.2	15.8
40°-50°	796.7	14.2
50°-60°	611.0	10.9
60°-70°	397.1	7.1
70°-80°	193.0	3.4
80°-90°	47.1	0.8
90°-100°	128.3	2.3
100°-110°	275.8	4.9
110°-120°	258.9	4.6
120°-130°	209.8	3.7
130°-140°	168.4	3.0
140°-150°	127.0	2.3
150°-160°	89.4	1.6
160°-170°	52.7	0.9
170°-180°	17.1	0.3
0°-30°	1365.7	24.3
0°-40°	2257.9	40.1
0°-60°	3665.6	65.1
0°-90°	4302.8	76.4
90°-120°	663.0	11.8
90°-150°	1168.2	20.7
90°-180°	1328.0	23.6
0°-180°	5630.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1660	1660	1660	1660	1660	
5°	1903	1656	1463	1656	1903	190
15°	2286	1581	1112	1581	2286	655
25°	2737	1442	894	1442	2737	1257
35°	2271	1255	729	1255	2271	1372
45°	1016	988	574	988	1016	810
55°	558	697	429	697	558	506
65°	316	435	255	435	316	315
75°	147	211	134	211	147	157
85°	31	47	35	47	31	36
90°	8	0	8	0	8	7
95°	84	12	84	12	84	119
105°	473	40	473	40	473	470
115°	527	72	527	72	527	515
125°	415	100	415	100	415	376
135°	345	117	345	117	345	267
145°	272	136	272	136	272	173
155°	228	156	228	156	228	106
165°	200	170	200	170	200	57
175°	180	177	180	177	180	17
180°	177	177	177	177	177	



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1746.6	1745.5	1747.7	1741.6	1742.2	1732.9	1732.9	1725.9	1716.6	1709.5	1706.2
5°	1903.0	1904.4	1901.7	1891.5	1884.6	1874.4	1862.8	1842.4	1825.3	1809.0	1796.0
7.5°	2064.2	2065.1	2056.1	2053.0	2035.8	2023.3	1997.5	1969.6	1945.0	1913.7	1889.7
10°	2158.0	2157.3	2147.7	2140.2	2125.3	2106.2	2080.9	2048.2	2017.5	1983.5	1950.8
12.5°	2212.5	2210.7	2207.7	2198.6	2184.6	2167.8	2146.4	2114.2	2076.4	2039.1	2000.9
15°	2286.1	2281.3	2272.5	2260.9	2241.1	2221.3	2197.5	2168.9	2132.7	2090.4	2055.1
17.5°	2377.1	2377.3	2363.7	2347.5	2320.7	2285.8	2249.0	2202.8	2153.7	2107.3	2069.5
20°	2452.4	2450.3	2436.7	2405.4	2374.7	2331.1	2288.9	2232.2	2172.2	2111.6	2064.6
22.5°	2560.4	2555.1	2540.8	2499.7	2452.2	2396.0	2331.4	2262.2	2189.7	2120.8	2059.1
25°	2737.3	2733.2	2705.2	2657.6	2590.8	2504.2	2419.6	2324.9	2220.7	2130.0	2055.1
27.5°	2858.3	2853.9	2833.2	2793.5	2731.9	2640.8	2526.4	2399.7	2269.6	2144.9	2036.8
30°	2846.4	2856.6	2853.9	2835.5	2789.1	2707.3	2601.7	2459.2	2304.5	2158.0	2029.1
32.5°	2675.1	2684.3	2708.3	2744.4	2747.1	2714.4	2635.4	2504.0	2343.8	2177.1	2023.2
35°	2271.1	2283.4	2329.8	2402.7	2498.1	2577.8	2594.1	2523.2	2379.4	2200.2	2014.2
37.5°	1746.0	1813.0	1852.1	1928.8	2073.1	2219.7	2360.8	2412.8	2351.5	2190.7	1999.5
40°	1483.2	1499.5	1569.0	1655.6	1777.0	1929.7	2130.7	2275.8	2280.7	2168.9	1976.6
42.5°	1269.4	1290.1	1337.9	1406.9	1510.9	1663.6	1871.2	2062.6	2151.4	2108.9	1946.6
45°	1015.6	1031.3	1066.0	1119.2	1198.9	1325.0	1503.6	1725.2	1901.0	1969.8	1866.2
47.5°	834.2	842.7	873.0	913.5	972.5	1064.4	1202.6	1394.9	1605.9	1753.7	1739.2
50°	736.1	745.7	768.8	799.5	849.3	927.0	1037.4	1197.6	1415.0	1595.6	1631.7
52.5°	659.7	667.7	682.2	711.1	752.2	811.9	901.1	1046.0	1241.6	1433.7	1517.2
55°	557.5	563.0	574.6	591.0	623.7	666.6	743.7	843.8	1002.0	1195.5	1318.2
57.5°	473.3	476.1	483.4	498.6	521.2	552.5	608.1	693.1	806.5	980.8	1116.2
60°	419.9	422.6	432.1	442.3	460.1	488.7	532.3	591.6	700.6	844.6	981.5
62.5°	377.3	379.0	383.0	393.2	408.8	430.9	465.2	513.6	600.4	726.7	856.1
65°	316.3	316.9	318.3	326.5	336.0	352.3	374.9	409.0	474.4	569.9	684.3
67.5°	257.6	258.6	263.4	266.2	276.2	284.8	298.0	324.1	370.1	434.4	523.5
70°	224.9	224.3	229.0	232.5	235.8	246.1	254.9	276.1	304.7	353.8	428.1
72.5°	194.4	192.6	194.7	195.9	200.4	207.3	216.2	229.1	251.3	285.1	341.9
75°	147.2	147.9	147.9	149.3	152.7	155.4	158.1	164.9	177.2	199.8	230.4
77.5°	103.3	102.2	105.1	105.5	107.6	110.6	112.9	115.6	120.7	129.9	145.7
80°	74.9	74.9	75.6	77.7	77.1	78.4	81.8	84.5	90.7	96.1	101.6
82.5°	57.6	57.0	57.7	58.1	58.0	59.3	60.5	61.1	63.4	66.1	69.9
85°	31.3	31.3	32.0	32.0	32.7	32.7	33.4	33.4	33.4	34.0	34.7
87.5°	13.6	13.1	12.5	12.5	13.0	13.9	13.3	12.7	12.6	12.6	13.0
90°	8.2	8.2	7.9	7.9	7.9	7.2	6.8	6.5	6.1	5.8	4.9
92.5°	22.7	23.3	23.8	24.7	29.3	34.5	45.8	63.2	93.1	115.0	116.9
95°	83.9	89.6	92.4	103.1	128.5	158.4	202.4	256.6	309.4	316.2	258.0
97.5°	202.7	207.3	217.6	237.6	259.6	301.3	344.2	382.1	391.5	337.7	230.5
100°	278.4	284.1	297.3	323.0	347.6	384.8	421.5	439.0	411.5	322.2	205.6
102.5°	362.9	367.2	381.5	399.8	426.2	451.3	468.9	458.1	399.5	295.2	186.7
105°	472.9	477.2	484.3	496.0	507.6	511.4	495.7	446.9	361.2	258.7	168.4
107.5°	531.3	534.1	536.5	536.5	530.8	512.1	471.8	406.6	322.0	233.7	160.8
110°	550.7	550.7	548.2	541.4	525.3	495.0	444.7	376.9	299.8	222.0	158.4



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	548.5	545.8	539.7	528.0	504.5	468.8	417.9	353.5	283.3	215.1	158.4
115°	526.7	522.1	512.1	495.0	467.2	428.3	379.4	324.1	265.2	207.7	159.6
117.5°	488.9	486.0	476.2	458.4	430.6	394.9	352.7	305.1	254.4	204.1	161.9
120°	464.3	461.5	451.8	434.7	408.3	376.9	337.6	294.8	248.4	202.4	164.2
122.5°	442.6	440.1	430.4	414.8	391.1	361.7	326.8	287.1	243.3	201.0	166.1
125°	415.1	411.5	403.6	389.0	369.0	343.4	312.3	275.9	236.3	199.1	169.6
127.5°	391.5	389.9	382.5	369.6	351.4	327.4	298.4	264.5	229.8	198.3	173.3
130°	378.7	376.6	369.4	357.6	339.8	316.6	288.7	257.3	225.6	197.7	175.6
132.5°	365.8	363.3	356.8	345.1	327.2	304.9	279.6	250.1	222.2	197.7	178.1
135°	344.8	342.6	336.2	324.5	308.7	288.4	265.5	241.0	218.0	197.7	181.7
137.5°	322.2	319.9	314.0	303.3	289.2	272.0	253.0	233.1	214.4	198.1	184.9
140°	306.6	304.8	299.4	290.1	276.9	262.0	245.5	228.7	212.7	198.4	186.3
142.5°	292.1	290.5	285.5	277.6	266.4	253.4	239.2	225.1	211.3	198.7	187.1
145°	272.0	270.5	266.6	260.5	252.0	242.4	231.3	220.3	209.1	198.4	188.0
147.5°	255.0	254.3	252.1	247.2	240.4	233.2	224.6	215.6	206.9	197.5	188.4
150°	245.5	245.2	243.8	239.4	234.1	227.7	221.0	213.1	205.2	196.6	188.4
152.5°	238.1	237.7	236.3	232.9	228.4	223.4	217.2	210.3	203.2	195.5	188.1
155°	228.0	227.7	226.6	224.1	220.6	216.6	211.7	205.9	199.9	193.5	187.3
157.5°	219.0	219.1	218.1	216.1	213.3	210.3	206.3	201.7	196.7	191.3	186.4
160°	213.1	213.4	212.7	211.0	208.4	205.9	202.4	198.8	194.2	189.9	185.6
162.5°	207.6	207.7	207.5	206.1	204.2	202.0	198.9	195.6	191.9	188.1	184.7
165°	199.9	199.9	199.9	199.1	197.7	195.9	193.8	191.3	188.4	185.6	183.5
167.5°	192.7	192.8	193.1	192.5	191.8	190.5	188.8	187.1	185.1	183.1	181.5
170°	188.4	188.8	188.8	188.4	187.7	187.0	185.9	184.9	183.1	181.7	180.6
172.5°	184.4	184.8	185.4	184.7	184.6	184.2	183.4	182.3	181.1	180.0	179.5
175°	179.6	179.9	180.6	180.3	180.3	180.3	179.6	179.6	178.4	178.1	178.1
177.5°	177.0	177.0	177.8	177.6	177.8	177.8	177.8	177.6	177.3	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1706.2	1702.3	1695.3	1688.7	1680.5	1673.4	1668.6	1662.5	1655.0	1645.7	1638.0
5°	1781.7	1766.7	1747.0	1729.9	1708.1	1691.0	1673.3	1656.3	1639.2	1617.4	1598.3
7.5°	1865.4	1834.4	1804.3	1766.5	1732.1	1701.4	1671.9	1642.1	1613.0	1582.0	1552.2
10°	1916.6	1879.2	1837.6	1789.9	1746.3	1704.7	1666.5	1629.0	1589.5	1554.7	1517.2
12.5°	1964.7	1916.2	1868.7	1808.5	1756.1	1705.3	1656.7	1609.9	1567.7	1522.6	1482.4
15°	2008.0	1960.2	1907.1	1833.5	1760.6	1699.2	1641.9	1581.3	1528.8	1478.3	1433.4
17.5°	2024.8	1974.7	1913.0	1842.2	1762.5	1685.4	1611.5	1545.1	1483.3	1424.5	1373.9
20°	2018.2	1969.8	1906.4	1839.0	1753.7	1673.3	1593.6	1519.9	1451.2	1389.1	1335.2
22.5°	2002.4	1952.4	1891.2	1819.9	1739.0	1653.7	1568.5	1490.0	1417.9	1353.6	1294.9
25°	1978.7	1910.6	1847.9	1778.3	1701.3	1616.8	1528.8	1442.3	1365.2	1299.8	1235.8
27.5°	1954.0	1869.0	1789.2	1720.1	1638.7	1563.3	1478.5	1389.8	1308.8	1242.1	1176.4
30°	1931.7	1836.2	1748.3	1669.9	1592.9	1521.4	1440.9	1354.3	1271.2	1202.3	1135.6
32.5°	1903.8	1802.4	1705.8	1615.4	1541.1	1470.1	1397.2	1314.5	1233.6	1162.6	1094.7
35°	1869.0	1739.5	1634.5	1538.3	1455.9	1387.0	1321.6	1254.9	1173.8	1100.1	1034.0
37.5°	1823.1	1676.2	1554.7	1450.1	1363.0	1293.9	1242.2	1181.2	1107.2	1036.7	975.3
40°	1795.3	1630.4	1497.4	1393.9	1302.5	1229.6	1181.2	1129.4	1062.0	995.8	934.4
42.5°	1758.3	1588.4	1439.7	1331.7	1239.8	1169.6	1120.6	1075.4	1018.9	956.5	890.8
45°	1685.6	1507.0	1350.9	1235.1	1142.4	1073.5	1027.8	987.6	944.7	887.5	830.2
47.5°	1590.9	1422.1	1258.8	1132.3	1041.5	977.5	933.2	901.5	870.8	822.1	766.5
50°	1515.2	1352.3	1192.8	1070.2	973.3	912.6	871.1	845.9	817.9	773.7	727.3
52.5°	1425.7	1280.3	1124.1	998.7	907.4	850.5	810.5	785.4	762.3	726.2	682.0
55°	1284.9	1157.4	1014.2	900.4	816.6	759.3	721.1	697.3	683.7	653.0	618.2
57.5°	1122.2	1030.9	904.6	794.9	720.7	664.2	636.2	615.9	600.5	578.9	554.3
60°	1008.8	944.7	831.5	727.3	659.1	605.2	580.1	563.0	548.7	530.3	511.2
62.5°	893.7	847.1	748.7	659.1	596.4	551.3	527.7	512.3	495.8	483.4	464.8
65°	739.5	697.9	629.8	559.6	501.7	465.5	448.5	434.8	424.6	411.0	398.1
67.5°	575.3	558.4	511.3	462.9	421.3	389.2	374.5	365.0	352.6	344.5	335.6
70°	474.4	466.3	432.8	400.8	361.9	340.1	326.5	322.3	307.4	299.2	293.1
72.5°	385.0	381.1	361.9	339.7	312.4	293.3	280.6	276.1	266.5	259.9	256.0
75°	263.8	265.2	261.8	247.4	237.2	224.9	214.0	211.3	204.5	199.0	195.6
77.5°	166.8	173.8	174.1	173.4	169.4	161.8	157.3	155.3	148.6	146.5	145.7
80°	114.5	122.0	128.9	128.2	126.7	124.7	121.3	119.3	115.8	113.8	112.5
82.5°	76.3	83.3	89.0	92.7	92.4	90.4	88.1	87.2	86.4	84.9	84.6
85°	36.2	37.5	39.5	44.3	47.7	48.4	47.7	47.1	44.9	45.6	46.4
87.5°	13.4	13.3	13.8	13.6	12.9	15.6	17.1	17.5	16.5	15.6	14.6
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	81.4	48.8	29.3	18.9	12.7	8.3	5.3	4.3	5.3	8.3	12.7
95°	159.6	81.0	42.8	26.8	18.9	14.9	12.1	11.8	12.1	14.9	18.9
97.5°	127.3	69.8	44.5	33.0	26.0	22.0	20.0	19.6	20.0	22.0	26.0
100°	115.6	69.3	48.6	37.9	31.0	27.2	25.7	24.9	25.7	27.2	31.0
102.5°	110.8	71.8	53.4	43.0	36.8	32.5	31.4	31.0	31.4	32.5	36.8
105°	108.9	77.1	61.4	51.4	45.6	42.1	40.3	40.3	40.3	42.1	45.6
107.5°	112.1	84.9	69.8	60.8	54.8	51.9	50.2	49.5	50.2	51.9	54.8
110°	115.3	90.7	76.0	66.8	61.4	58.2	56.8	56.0	56.8	58.2	61.4





TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	119.3	96.0	82.0	73.0	67.7	64.4	63.3	62.6	63.3	64.4	67.7
115°	125.2	104.6	91.4	82.4	77.1	73.9	72.8	72.1	72.8	73.9	77.1
117.5°	132.1	113.3	100.8	92.2	86.0	82.9	81.7	80.7	81.7	82.9	86.0
120°	136.7	119.6	107.0	98.2	92.1	88.9	87.5	86.3	87.5	88.9	92.1
122.5°	141.8	125.5	113.1	104.1	97.6	94.3	93.1	92.4	93.1	94.3	97.6
125°	148.9	133.5	121.7	112.4	105.6	102.4	100.7	100.0	100.7	102.4	105.6
127.5°	155.2	141.1	129.8	120.5	113.3	109.2	106.9	105.8	106.9	109.2	113.3
130°	159.6	145.9	134.9	125.6	118.2	113.5	110.7	109.6	110.7	113.5	118.2
132.5°	163.3	150.6	139.5	130.2	122.4	117.2	113.8	112.4	113.8	117.2	122.4
135°	168.4	156.6	145.6	136.0	128.5	122.8	118.5	117.0	118.5	122.8	128.5
137.5°	172.3	161.1	151.0	141.1	133.7	127.9	124.0	122.9	124.0	127.9	133.7
140°	174.9	164.2	153.8	144.2	137.4	131.7	127.4	126.3	127.4	131.7	137.4
142.5°	176.3	166.1	156.4	147.3	140.9	135.1	131.1	130.4	131.1	135.1	140.9
145°	178.4	169.6	160.3	152.1	145.6	140.6	137.0	136.3	137.0	140.6	145.6
147.5°	179.8	171.7	163.5	156.3	150.8	146.1	143.0	142.6	143.0	146.1	150.8
150°	180.6	173.1	165.2	159.2	154.2	149.6	147.0	146.3	147.0	149.6	154.2
152.5°	181.2	174.5	167.2	161.8	157.0	153.0	150.8	150.4	150.8	153.0	157.0
155°	181.7	175.9	169.9	164.9	161.3	157.7	155.6	155.6	155.6	157.7	161.3
157.5°	182.0	177.1	172.0	168.1	165.0	162.0	160.3	160.4	160.3	162.0	165.0
160°	182.0	177.7	173.1	169.9	167.0	164.5	163.1	163.5	163.1	164.5	167.0
162.5°	181.8	178.3	174.2	171.6	169.4	167.1	165.7	166.0	165.7	167.1	169.4
165°	181.3	178.4	175.6	173.5	172.0	170.3	169.2	169.9	169.2	170.3	172.0
167.5°	180.5	178.4	176.1	174.7	173.7	172.8	172.1	172.5	172.1	172.8	173.7
170°	179.9	178.4	176.6	175.6	174.9	174.2	173.8	174.2	173.8	174.2	174.9
172.5°	179.4	178.1	176.6	176.1	175.7	175.0	174.7	175.3	174.7	175.0	175.7
175°	178.4	177.7	176.6	176.6	176.6	176.3	175.9	176.6	175.9	176.3	176.6
177.5°	177.6	177.3	176.7	176.7	177.0	176.7	176.7	177.3	176.7	176.7	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1632.5	1625.0	1619.5	1608.6	1600.9	1597.7	1591.6	1590.0	1596.0	1591.6	1591.1
5°	1584.1	1564.3	1548.6	1532.9	1515.9	1505.0	1488.6	1485.9	1481.8	1475.6	1474.3
7.5°	1525.8	1500.1	1479.9	1454.0	1431.5	1413.4	1392.9	1383.2	1378.0	1370.0	1359.4
10°	1486.5	1455.9	1428.7	1402.7	1374.8	1352.3	1331.8	1316.2	1306.0	1296.4	1292.3
12.5°	1447.8	1416.6	1381.7	1350.4	1319.2	1293.9	1271.3	1261.1	1249.8	1238.6	1229.1
15°	1387.8	1346.2	1308.0	1271.8	1245.3	1218.0	1196.2	1181.2	1164.2	1159.4	1141.0
17.5°	1323.9	1283.1	1238.5	1200.4	1169.6	1139.6	1115.6	1098.6	1085.8	1068.2	1059.8
20°	1284.1	1235.8	1192.1	1157.4	1123.3	1087.8	1063.3	1048.9	1036.7	1022.4	1015.6
22.5°	1241.6	1194.3	1149.6	1108.8	1074.2	1039.4	1021.9	1007.0	993.1	979.9	970.9
25°	1179.1	1131.5	1084.4	1042.2	1006.0	980.8	960.4	943.3	935.8	922.9	913.3
27.5°	1117.4	1066.7	1017.9	975.7	947.5	922.5	905.7	892.2	878.7	867.4	859.1
30°	1077.6	1025.8	972.6	939.3	909.3	885.3	867.0	854.0	843.8	833.6	827.5
32.5°	1037.8	984.4	937.2	901.1	872.7	852.1	833.1	820.8	810.0	798.7	791.4
35°	974.0	919.5	881.3	845.9	817.9	798.8	785.9	768.2	759.3	751.1	743.7
37.5°	914.7	864.0	822.7	791.6	767.3	748.4	731.6	722.1	711.1	703.8	697.5
40°	871.1	824.8	787.3	754.6	736.8	715.7	700.0	687.7	679.5	670.0	663.2
42.5°	831.8	788.7	752.3	722.9	700.8	683.0	667.8	655.6	645.2	638.4	632.7
45°	776.4	733.4	697.9	670.7	650.3	633.2	617.5	611.4	597.7	589.6	586.8
47.5°	718.9	680.5	646.3	621.2	600.3	584.1	569.4	556.8	549.4	541.3	536.9
50°	680.2	643.4	611.4	586.8	566.4	548.7	535.0	526.8	516.6	509.2	503.7
52.5°	641.6	607.4	575.4	552.0	534.2	516.5	501.3	493.1	483.4	478.6	474.8
55°	586.2	550.1	522.8	499.6	481.2	464.8	450.5	442.3	436.3	431.4	430.1
57.5°	523.5	494.8	469.5	448.6	429.5	414.1	401.6	393.8	388.4	387.7	383.6
60°	482.6	456.7	433.5	411.0	394.7	380.3	369.4	360.5	355.1	354.5	353.0
62.5°	441.7	416.9	395.4	375.6	360.8	347.1	336.7	326.8	323.5	320.1	317.1
65°	381.0	358.5	340.8	325.1	309.4	297.8	287.6	281.6	274.0	269.9	262.5
67.5°	321.4	304.0	287.0	273.8	261.5	250.4	242.0	232.9	227.8	224.5	219.0
70°	282.2	268.5	251.6	237.2	227.6	218.8	212.0	201.8	198.3	195.6	192.9
72.5°	245.1	233.1	218.8	207.2	197.6	189.3	181.5	176.6	173.3	170.6	169.0
75°	192.9	181.3	169.1	160.9	154.0	147.2	143.1	139.8	138.4	137.6	134.9
77.5°	141.7	135.5	125.7	119.2	114.6	111.9	108.3	106.4	106.3	103.3	102.4
80°	108.4	104.9	96.7	94.0	90.7	88.0	85.8	82.5	79.1	77.7	75.6
82.5°	80.6	77.2	73.9	69.5	66.7	65.0	63.0	61.7	62.2	60.3	59.3
85°	42.9	39.5	38.2	37.5	36.2	37.5	36.8	36.2	35.4	34.7	35.4
87.5°	14.2	14.3	13.8	15.1	13.5	14.2	14.3	13.8	13.9	13.9	13.5
90°	2.8	3.5	3.9	4.6	4.9	5.8	6.1	6.5	6.8	7.2	7.9
92.5°	18.9	29.3	48.8	81.4	116.9	115.0	93.1	63.2	45.8	34.5	29.3
95°	26.8	42.8	81.0	159.6	258.0	316.2	309.4	256.6	202.4	158.4	128.5
97.5°	33.0	44.5	69.8	127.3	230.5	337.7	391.5	382.1	344.2	301.3	259.6
100°	37.9	48.6	69.3	115.6	205.6	322.2	411.5	439.0	421.5	384.8	347.6
102.5°	43.0	53.4	71.8	110.8	186.7	295.2	399.5	458.1	468.9	451.3	426.2
105°	51.4	61.4	77.1	108.9	168.4	258.7	361.2	446.9	495.7	511.4	507.6
107.5°	60.8	69.8	84.9	112.1	160.8	233.7	322.0	406.6	471.8	512.1	530.8
110°	66.8	76.0	90.7	115.3	158.4	222.0	299.8	376.9	444.7	495.0	525.3



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	73.0	82.0	96.0	119.3	158.4	215.1	283.3	353.5	417.9	468.8	504.5
115°	82.4	91.4	104.6	125.2	159.6	207.7	265.2	324.1	379.4	428.3	467.2
117.5°	92.2	100.8	113.3	132.1	161.9	204.1	254.4	305.1	352.7	394.9	430.6
120°	98.2	107.0	119.6	136.7	164.2	202.4	248.4	294.8	337.6	376.9	408.3
122.5°	104.1	113.1	125.5	141.8	166.1	201.0	243.3	287.1	326.8	361.7	391.1
125°	112.4	121.7	133.5	148.9	169.6	199.1	236.3	275.9	312.3	343.4	369.0
127.5°	120.5	129.8	141.1	155.2	173.3	198.3	229.8	264.5	298.4	327.4	351.4
130°	125.6	134.9	145.9	159.6	175.6	197.7	225.6	257.3	288.7	316.6	339.8
132.5°	130.2	139.5	150.6	163.3	178.1	197.7	222.2	250.1	279.6	304.9	327.2
135°	136.0	145.6	156.6	168.4	181.7	197.7	218.0	241.0	265.5	288.4	308.7
137.5°	141.1	151.0	161.1	172.3	184.9	198.1	214.4	233.1	253.0	272.0	289.2
140°	144.2	153.8	164.2	174.9	186.3	198.4	212.7	228.7	245.5	262.0	276.9
142.5°	147.3	156.4	166.1	176.3	187.1	198.7	211.3	225.1	239.2	253.4	266.4
145°	152.1	160.3	169.6	178.4	188.0	198.4	209.1	220.3	231.3	242.4	252.0
147.5°	156.3	163.5	171.7	179.8	188.4	197.5	206.9	215.6	224.6	233.2	240.4
150°	159.2	165.2	173.1	180.6	188.4	196.6	205.2	213.1	221.0	227.7	234.1
152.5°	161.8	167.2	174.5	181.2	188.1	195.5	203.2	210.3	217.2	223.4	228.4
155°	164.9	169.9	175.9	181.7	187.3	193.5	199.9	205.9	211.7	216.6	220.6
157.5°	168.1	172.0	177.1	182.0	186.4	191.3	196.7	201.7	206.3	210.3	213.3
160°	169.9	173.1	177.7	182.0	185.6	189.9	194.2	198.8	202.4	205.9	208.4
162.5°	171.6	174.2	178.3	181.8	184.7	188.1	191.9	195.6	198.9	202.0	204.2
165°	173.5	175.6	178.4	181.3	183.5	185.6	188.4	191.3	193.8	195.9	197.7
167.5°	174.7	176.1	178.4	180.5	181.5	183.1	185.1	187.1	188.8	190.5	191.8
170°	175.6	176.6	178.4	179.9	180.6	181.7	183.1	184.9	185.9	187.0	187.7
172.5°	176.1	176.6	178.1	179.4	179.5	180.0	181.1	182.3	183.4	184.2	184.6
175°	176.6	176.6	177.7	178.4	178.1	178.1	178.4	179.6	179.6	180.3	180.3
177.5°	176.7	176.7	177.3	177.6	177.0	177.0	177.3	177.6	177.8	177.8	177.8
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1590.5	1584.6	1583.0	1585.1	1583.0	1584.6	1590.5	1591.1	1591.6	1596.0	1590.0
5°	1467.5	1460.7	1464.1	1462.7	1464.1	1460.7	1467.5	1474.3	1475.6	1481.8	1485.9
7.5°	1359.3	1350.8	1341.8	1344.6	1341.8	1350.8	1359.3	1359.4	1370.0	1378.0	1383.2
10°	1283.4	1276.7	1272.5	1276.0	1272.5	1276.7	1283.4	1292.3	1296.4	1306.0	1316.2
12.5°	1219.6	1215.6	1212.0	1210.5	1212.0	1215.6	1219.6	1229.1	1238.6	1249.8	1261.1
15°	1132.9	1124.7	1121.3	1112.4	1121.3	1124.7	1132.9	1141.0	1159.4	1164.2	1181.2
17.5°	1052.8	1050.1	1041.2	1037.4	1041.2	1050.1	1052.8	1059.8	1068.2	1085.8	1098.6
20°	1005.3	1002.6	993.8	999.3	993.8	1002.6	1005.3	1015.6	1022.4	1036.7	1048.9
22.5°	966.1	960.1	957.3	955.6	957.3	960.1	966.1	970.9	979.9	993.1	1007.0
25°	910.6	901.7	898.4	894.2	898.4	901.7	910.6	913.3	922.9	935.8	943.3
27.5°	855.3	850.5	846.0	845.0	846.0	850.5	855.3	859.1	867.4	878.7	892.2
30°	819.3	814.6	811.1	811.1	811.1	814.6	819.3	827.5	833.6	843.8	854.0
32.5°	787.1	783.5	780.0	779.5	780.0	783.5	787.1	791.4	798.7	810.0	820.8
35°	740.2	734.8	733.4	729.3	733.4	734.8	740.2	743.7	751.1	759.3	768.2
37.5°	691.6	687.0	686.9	686.5	686.9	687.0	691.6	697.5	703.8	711.1	722.1
40°	660.5	657.0	656.4	651.6	656.4	657.0	660.5	663.2	670.0	679.5	687.7
42.5°	627.2	625.4	623.1	621.1	623.1	625.4	627.2	632.7	638.4	645.2	655.6
45°	582.1	577.3	577.3	573.9	577.3	577.3	582.1	586.8	589.6	597.7	611.4
47.5°	535.4	531.8	532.2	528.7	532.2	531.8	535.4	536.9	541.3	549.4	556.8
50°	504.4	502.3	501.7	500.3	501.7	502.3	504.4	503.7	509.2	516.6	526.8
52.5°	473.3	472.3	474.9	471.9	474.9	472.3	473.3	474.8	478.6	483.4	493.1
55°	431.4	429.4	433.5	429.4	433.5	429.4	431.4	430.1	431.4	436.3	442.3
57.5°	383.3	381.4	385.1	383.0	385.1	381.4	383.3	383.6	387.7	388.4	393.8
60°	351.7	347.6	349.6	350.3	349.6	347.6	351.7	353.0	354.5	355.1	360.5
62.5°	314.1	311.6	313.2	310.0	313.2	311.6	314.1	317.1	320.1	323.5	326.8
65°	261.1	259.0	256.3	254.9	256.3	259.0	261.1	262.5	269.9	274.0	281.6
67.5°	219.3	214.4	214.3	215.4	214.3	214.4	219.3	219.0	224.5	227.8	232.9
70°	188.8	188.8	188.1	188.1	188.1	188.8	188.8	192.9	195.6	198.3	201.8
72.5°	167.5	167.0	165.7	165.2	165.7	167.0	167.5	169.0	170.6	173.3	176.6
75°	134.9	135.6	134.3	133.6	134.3	135.6	134.9	134.9	137.6	138.4	139.8
77.5°	99.7	96.7	98.3	96.7	98.3	96.7	99.7	102.4	103.3	106.3	106.4
80°	75.6	74.9	77.1	74.9	77.1	74.9	75.6	75.6	77.7	79.1	82.5
82.5°	59.9	59.2	60.1	58.6	60.1	59.2	59.9	59.3	60.3	62.2	61.7
85°	36.2	35.4	34.7	35.4	34.7	35.4	36.2	35.4	34.7	35.4	36.2
87.5°	14.1	13.5	13.6	13.6	13.6	13.5	14.1	13.5	13.9	13.9	13.8
90°	7.9	7.9	8.2	8.2	8.2	7.9	7.9	7.9	7.2	6.8	6.5
92.5°	24.7	23.8	23.3	22.7	23.3	23.8	24.7	29.3	34.5	45.8	63.2
95°	103.1	92.4	89.6	83.9	89.6	92.4	103.1	128.5	158.4	202.4	256.6
97.5°	237.6	217.6	207.3	202.7	207.3	217.6	237.6	259.6	301.3	344.2	382.1
100°	323.0	297.3	284.1	278.4	284.1	297.3	323.0	347.6	384.8	421.5	439.0
102.5°	399.8	381.5	367.2	362.9	367.2	381.5	399.8	426.2	451.3	468.9	458.1
105°	496.0	484.3	477.2	472.9	477.2	484.3	496.0	507.6	511.4	495.7	446.9
107.5°	536.5	536.5	534.1	531.3	534.1	536.5	536.5	530.8	512.1	471.8	406.6
110°	541.4	548.2	550.7	550.7	550.7	548.2	541.4	525.3	495.0	444.7	376.9



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	528.0	539.7	545.8	548.5	545.8	539.7	528.0	504.5	468.8	417.9	353.5
115°	495.0	512.1	522.1	526.7	522.1	512.1	495.0	467.2	428.3	379.4	324.1
117.5°	458.4	476.2	486.0	488.9	486.0	476.2	458.4	430.6	394.9	352.7	305.1
120°	434.7	451.8	461.5	464.3	461.5	451.8	434.7	408.3	376.9	337.6	294.8
122.5°	414.8	430.4	440.1	442.6	440.1	430.4	414.8	391.1	361.7	326.8	287.1
125°	389.0	403.6	411.5	415.1	411.5	403.6	389.0	369.0	343.4	312.3	275.9
127.5°	369.6	382.5	389.9	391.5	389.9	382.5	369.6	351.4	327.4	298.4	264.5
130°	357.6	369.4	376.6	378.7	376.6	369.4	357.6	339.8	316.6	288.7	257.3
132.5°	345.1	356.8	363.3	365.8	363.3	356.8	345.1	327.2	304.9	279.6	250.1
135°	324.5	336.2	342.6	344.8	342.6	336.2	324.5	308.7	288.4	265.5	241.0
137.5°	303.3	314.0	319.9	322.2	319.9	314.0	303.3	289.2	272.0	253.0	233.1
140°	290.1	299.4	304.8	306.6	304.8	299.4	290.1	276.9	262.0	245.5	228.7
142.5°	277.6	285.5	290.5	292.1	290.5	285.5	277.6	266.4	253.4	239.2	225.1
145°	260.5	266.6	270.5	272.0	270.5	266.6	260.5	252.0	242.4	231.3	220.3
147.5°	247.2	252.1	254.3	255.0	254.3	252.1	247.2	240.4	233.2	224.6	215.6
150°	239.4	243.8	245.2	245.5	245.2	243.8	239.4	234.1	227.7	221.0	213.1
152.5°	232.9	236.3	237.7	238.1	237.7	236.3	232.9	228.4	223.4	217.2	210.3
155°	224.1	226.6	227.7	228.0	227.7	226.6	224.1	220.6	216.6	211.7	205.9
157.5°	216.1	218.1	219.1	219.0	219.1	218.1	216.1	213.3	210.3	206.3	201.7
160°	211.0	212.7	213.4	213.1	213.4	212.7	211.0	208.4	205.9	202.4	198.8
162.5°	206.1	207.5	207.7	207.6	207.7	207.5	206.1	204.2	202.0	198.9	195.6
165°	199.1	199.9	199.9	199.9	199.9	199.9	199.1	197.7	195.9	193.8	191.3
167.5°	192.5	193.1	192.8	192.7	192.8	193.1	192.5	191.8	190.5	188.8	187.1
170°	188.4	188.8	188.8	188.4	188.8	188.8	188.4	187.7	187.0	185.9	184.9
172.5°	184.7	185.4	184.8	184.4	184.8	185.4	184.7	184.6	184.2	183.4	182.3
175°	180.3	180.6	179.9	179.6	179.9	180.6	180.3	180.3	180.3	179.6	179.6
177.5°	177.6	177.8	177.0	177.0	177.0	177.8	177.6	177.8	177.8	177.8	177.6
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1591.6	1597.7	1600.9	1608.6	1619.5	1625.0	1632.5	1638.0	1645.7	1655.0	1662.5
5°	1488.6	1505.0	1515.9	1532.9	1548.6	1564.3	1584.1	1598.3	1617.4	1639.2	1656.3
7.5°	1392.9	1413.4	1431.5	1454.0	1479.9	1500.1	1525.8	1552.2	1582.0	1613.0	1642.1
10°	1331.8	1352.3	1374.8	1402.7	1428.7	1455.9	1486.5	1517.2	1554.7	1589.5	1629.0
12.5°	1271.3	1293.9	1319.2	1350.4	1381.7	1416.6	1447.8	1482.4	1522.6	1567.7	1609.9
15°	1196.2	1218.0	1245.3	1271.8	1308.0	1346.2	1387.8	1433.4	1478.3	1528.8	1581.3
17.5°	1115.6	1139.6	1169.6	1200.4	1238.5	1283.1	1323.9	1373.9	1424.5	1483.3	1545.1
20°	1063.3	1087.8	1123.3	1157.4	1192.1	1235.8	1284.1	1335.2	1389.1	1451.2	1519.9
22.5°	1021.9	1039.4	1074.2	1108.8	1149.6	1194.3	1241.6	1294.9	1353.6	1417.9	1490.0
25°	960.4	980.8	1006.0	1042.2	1084.4	1131.5	1179.1	1235.8	1299.8	1365.2	1442.3
27.5°	905.7	922.5	947.5	975.7	1017.9	1066.7	1117.4	1176.4	1242.1	1308.8	1389.8
30°	867.0	885.3	909.3	939.3	972.6	1025.8	1077.6	1135.6	1202.3	1271.2	1354.3
32.5°	833.1	852.1	872.7	901.1	937.2	984.4	1037.8	1094.7	1162.6	1233.6	1314.5
35°	785.9	798.8	817.9	845.9	881.3	919.5	974.0	1034.0	1100.1	1173.8	1254.9
37.5°	731.6	748.4	767.3	791.6	822.7	864.0	914.7	975.3	1036.7	1107.2	1181.2
40°	700.0	715.7	736.8	754.6	787.3	824.8	871.1	934.4	995.8	1062.0	1129.4
42.5°	667.8	683.0	700.8	722.9	752.3	788.7	831.8	890.8	956.5	1018.9	1075.4
45°	617.5	633.2	650.3	670.7	697.9	733.4	776.4	830.2	887.5	944.7	987.6
47.5°	569.4	584.1	600.3	621.2	646.3	680.5	718.9	766.5	822.1	870.8	901.5
50°	535.0	548.7	566.4	586.8	611.4	643.4	680.2	727.3	773.7	817.9	845.9
52.5°	501.3	516.5	534.2	552.0	575.4	607.4	641.6	682.0	726.2	762.3	785.4
55°	450.5	464.8	481.2	499.6	522.8	550.1	586.2	618.2	653.0	683.7	697.3
57.5°	401.6	414.1	429.5	448.6	469.5	494.8	523.5	554.3	578.9	600.5	615.9
60°	369.4	380.3	394.7	411.0	433.5	456.7	482.6	511.2	530.3	548.7	563.0
62.5°	336.7	347.1	360.8	375.6	395.4	416.9	441.7	464.8	483.4	495.8	512.3
65°	287.6	297.8	309.4	325.1	340.8	358.5	381.0	398.1	411.0	424.6	434.8
67.5°	242.0	250.4	261.5	273.8	287.0	304.0	321.4	335.6	344.5	352.6	365.0
70°	212.0	218.8	227.6	237.2	251.6	268.5	282.2	293.1	299.2	307.4	322.3
72.5°	181.5	189.3	197.6	207.2	218.8	233.1	245.1	256.0	259.9	266.5	276.1
75°	143.1	147.2	154.0	160.9	169.1	181.3	192.9	195.6	199.0	204.5	211.3
77.5°	108.3	111.9	114.6	119.2	125.7	135.5	141.7	145.7	146.5	148.6	155.3
80°	85.8	88.0	90.7	94.0	96.7	104.9	108.4	112.5	113.8	115.8	119.3
82.5°	63.0	65.0	66.7	69.5	73.9	77.2	80.6	84.6	84.9	86.4	87.2
85°	36.8	37.5	36.2	37.5	38.2	39.5	42.9	46.4	45.6	44.9	47.1
87.5°	14.3	14.2	13.5	15.1	13.8	14.3	14.2	14.6	15.6	16.5	17.5
90°	6.1	5.8	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	93.1	115.0	116.9	81.4	48.8	29.3	18.9	12.7	8.3	5.3	4.3
95°	309.4	316.2	258.0	159.6	81.0	42.8	26.8	18.9	14.9	12.1	11.8
97.5°	391.5	337.7	230.5	127.3	69.8	44.5	33.0	26.0	22.0	20.0	19.6
100°	411.5	322.2	205.6	115.6	69.3	48.6	37.9	31.0	27.2	25.7	24.9
102.5°	399.5	295.2	186.7	110.8	71.8	53.4	43.0	36.8	32.5	31.4	31.0
105°	361.2	258.7	168.4	108.9	77.1	61.4	51.4	45.6	42.1	40.3	40.3
107.5°	322.0	233.7	160.8	112.1	84.9	69.8	60.8	54.8	51.9	50.2	49.5
110°	299.8	222.0	158.4	115.3	90.7	76.0	66.8	61.4	58.2	56.8	56.0



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.3	215.1	158.4	119.3	96.0	82.0	73.0	67.7	64.4	63.3	62.6
115°	265.2	207.7	159.6	125.2	104.6	91.4	82.4	77.1	73.9	72.8	72.1
117.5°	254.4	204.1	161.9	132.1	113.3	100.8	92.2	86.0	82.9	81.7	80.7
120°	248.4	202.4	164.2	136.7	119.6	107.0	98.2	92.1	88.9	87.5	86.3
122.5°	243.3	201.0	166.1	141.8	125.5	113.1	104.1	97.6	94.3	93.1	92.4
125°	236.3	199.1	169.6	148.9	133.5	121.7	112.4	105.6	102.4	100.7	100.0
127.5°	229.8	198.3	173.3	155.2	141.1	129.8	120.5	113.3	109.2	106.9	105.8
130°	225.6	197.7	175.6	159.6	145.9	134.9	125.6	118.2	113.5	110.7	109.6
132.5°	222.2	197.7	178.1	163.3	150.6	139.5	130.2	122.4	117.2	113.8	112.4
135°	218.0	197.7	181.7	168.4	156.6	145.6	136.0	128.5	122.8	118.5	117.0
137.5°	214.4	198.1	184.9	172.3	161.1	151.0	141.1	133.7	127.9	124.0	122.9
140°	212.7	198.4	186.3	174.9	164.2	153.8	144.2	137.4	131.7	127.4	126.3
142.5°	211.3	198.7	187.1	176.3	166.1	156.4	147.3	140.9	135.1	131.1	130.4
145°	209.1	198.4	188.0	178.4	169.6	160.3	152.1	145.6	140.6	137.0	136.3
147.5°	206.9	197.5	188.4	179.8	171.7	163.5	156.3	150.8	146.1	143.0	142.6
150°	205.2	196.6	188.4	180.6	173.1	165.2	159.2	154.2	149.6	147.0	146.3
152.5°	203.2	195.5	188.1	181.2	174.5	167.2	161.8	157.0	153.0	150.8	150.4
155°	199.9	193.5	187.3	181.7	175.9	169.9	164.9	161.3	157.7	155.6	155.6
157.5°	196.7	191.3	186.4	182.0	177.1	172.0	168.1	165.0	162.0	160.3	160.4
160°	194.2	189.9	185.6	182.0	177.7	173.1	169.9	167.0	164.5	163.1	163.5
162.5°	191.9	188.1	184.7	181.8	178.3	174.2	171.6	169.4	167.1	165.7	166.0
165°	188.4	185.6	183.5	181.3	178.4	175.6	173.5	172.0	170.3	169.2	169.9
167.5°	185.1	183.1	181.5	180.5	178.4	176.1	174.7	173.7	172.8	172.1	172.5
170°	183.1	181.7	180.6	179.9	178.4	176.6	175.6	174.9	174.2	173.8	174.2
172.5°	181.1	180.0	179.5	179.4	178.1	176.6	176.1	175.7	175.0	174.7	175.3
175°	178.4	178.1	178.1	178.4	177.7	176.6	176.6	176.6	176.3	175.9	176.6
177.5°	177.3	177.0	177.0	177.6	177.3	176.7	176.7	177.0	176.7	176.7	177.3
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1668.6	1673.4	1680.5	1688.7	1695.3	1702.3	1706.2	1706.2	1709.5	1716.6	1725.9
5°	1673.3	1691.0	1708.1	1729.9	1747.0	1766.7	1781.7	1796.0	1809.0	1825.3	1842.4
7.5°	1671.9	1701.4	1732.1	1766.5	1804.3	1834.4	1865.4	1889.7	1913.7	1945.0	1969.6
10°	1666.5	1704.7	1746.3	1789.9	1837.6	1879.2	1916.6	1950.8	1983.5	2017.5	2048.2
12.5°	1656.7	1705.3	1756.1	1808.5	1868.7	1916.2	1964.7	2000.9	2039.1	2076.4	2114.2
15°	1641.9	1699.2	1760.6	1833.5	1907.1	1960.2	2008.0	2055.1	2090.4	2132.7	2168.9
17.5°	1611.5	1685.4	1762.5	1842.2	1913.0	1974.7	2024.8	2069.5	2107.3	2153.7	2202.8
20°	1593.6	1673.3	1753.7	1839.0	1906.4	1969.8	2018.2	2064.6	2111.6	2172.2	2232.2
22.5°	1568.5	1653.7	1739.0	1819.9	1891.2	1952.4	2002.4	2059.1	2120.8	2189.7	2262.2
25°	1528.8	1616.8	1701.3	1778.3	1847.9	1910.6	1978.7	2055.1	2130.0	2220.7	2324.9
27.5°	1478.5	1563.3	1638.7	1720.1	1789.2	1869.0	1954.0	2036.8	2144.9	2269.6	2399.7
30°	1440.9	1521.4	1592.9	1669.9	1748.3	1836.2	1931.7	2029.1	2158.0	2304.5	2459.2
32.5°	1397.2	1470.1	1541.1	1615.4	1705.8	1802.4	1903.8	2023.2	2177.1	2343.8	2504.0
35°	1321.6	1387.0	1455.9	1538.3	1634.5	1739.5	1869.0	2014.2	2200.2	2379.4	2523.2
37.5°	1242.2	1293.9	1363.0	1450.1	1554.7	1676.2	1823.1	1999.5	2190.7	2351.5	2412.8
40°	1181.2	1229.6	1302.5	1393.9	1497.4	1630.4	1795.3	1976.6	2168.9	2280.7	2275.8
42.5°	1120.6	1169.6	1239.8	1331.7	1439.7	1588.4	1758.3	1946.6	2108.9	2151.4	2062.6
45°	1027.8	1073.5	1142.4	1235.1	1350.9	1507.0	1685.6	1866.2	1969.8	1901.0	1725.2
47.5°	933.2	977.5	1041.5	1132.3	1258.8	1422.1	1590.9	1739.2	1753.7	1605.9	1394.9
50°	871.1	912.6	973.3	1070.2	1192.8	1352.3	1515.2	1631.7	1595.6	1415.0	1197.6
52.5°	810.5	850.5	907.4	998.7	1124.1	1280.3	1425.7	1517.2	1433.7	1241.6	1046.0
55°	721.1	759.3	816.6	900.4	1014.2	1157.4	1284.9	1318.2	1195.5	1002.0	843.8
57.5°	636.2	664.2	720.7	794.9	904.6	1030.9	1122.2	1116.2	980.8	806.5	693.1
60°	580.1	605.2	659.1	727.3	831.5	944.7	1008.8	981.5	844.6	700.6	591.6
62.5°	527.7	551.3	596.4	659.1	748.7	847.1	893.7	856.1	726.7	600.4	513.6
65°	448.5	465.5	501.7	559.6	629.8	697.9	739.5	684.3	569.9	474.4	409.0
67.5°	374.5	389.2	421.3	462.9	511.3	558.4	575.3	523.5	434.4	370.1	324.1
70°	326.5	340.1	361.9	400.8	432.8	466.3	474.4	428.1	353.8	304.7	276.1
72.5°	280.6	293.3	312.4	339.7	361.9	381.1	385.0	341.9	285.1	251.3	229.1
75°	214.0	224.9	237.2	247.4	261.8	265.2	263.8	230.4	199.8	177.2	164.9
77.5°	157.3	161.8	169.4	173.4	174.1	173.8	166.8	145.7	129.9	120.7	115.6
80°	121.3	124.7	126.7	128.2	128.9	122.0	114.5	101.6	96.1	90.7	84.5
82.5°	88.1	90.4	92.4	92.7	89.0	83.3	76.3	69.9	66.1	63.4	61.1
85°	47.7	48.4	47.7	44.3	39.5	37.5	36.2	34.7	34.0	33.4	33.4
87.5°	17.1	15.6	12.9	13.6	13.8	13.3	13.4	13.0	12.6	12.6	12.7
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.8	6.1	6.5
92.5°	5.3	8.3	12.7	18.9	29.3	48.8	81.4	116.9	115.0	93.1	63.2
95°	12.1	14.9	18.9	26.8	42.8	81.0	159.6	258.0	316.2	309.4	256.6
97.5°	20.0	22.0	26.0	33.0	44.5	69.8	127.3	230.5	337.7	391.5	382.1
100°	25.7	27.2	31.0	37.9	48.6	69.3	115.6	205.6	322.2	411.5	439.0
102.5°	31.4	32.5	36.8	43.0	53.4	71.8	110.8	186.7	295.2	399.5	458.1
105°	40.3	42.1	45.6	51.4	61.4	77.1	108.9	168.4	258.7	361.2	446.9
107.5°	50.2	51.9	54.8	60.8	69.8	84.9	112.1	160.8	233.7	322.0	406.6
110°	56.8	58.2	61.4	66.8	76.0	90.7	115.3	158.4	222.0	299.8	376.9





TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	63.3	64.4	67.7	73.0	82.0	96.0	119.3	158.4	215.1	283.3	353.5
115°	72.8	73.9	77.1	82.4	91.4	104.6	125.2	159.6	207.7	265.2	324.1
117.5°	81.7	82.9	86.0	92.2	100.8	113.3	132.1	161.9	204.1	254.4	305.1
120°	87.5	88.9	92.1	98.2	107.0	119.6	136.7	164.2	202.4	248.4	294.8
122.5°	93.1	94.3	97.6	104.1	113.1	125.5	141.8	166.1	201.0	243.3	287.1
125°	100.7	102.4	105.6	112.4	121.7	133.5	148.9	169.6	199.1	236.3	275.9
127.5°	106.9	109.2	113.3	120.5	129.8	141.1	155.2	173.3	198.3	229.8	264.5
130°	110.7	113.5	118.2	125.6	134.9	145.9	159.6	175.6	197.7	225.6	257.3
132.5°	113.8	117.2	122.4	130.2	139.5	150.6	163.3	178.1	197.7	222.2	250.1
135°	118.5	122.8	128.5	136.0	145.6	156.6	168.4	181.7	197.7	218.0	241.0
137.5°	124.0	127.9	133.7	141.1	151.0	161.1	172.3	184.9	198.1	214.4	233.1
140°	127.4	131.7	137.4	144.2	153.8	164.2	174.9	186.3	198.4	212.7	228.7
142.5°	131.1	135.1	140.9	147.3	156.4	166.1	176.3	187.1	198.7	211.3	225.1
145°	137.0	140.6	145.6	152.1	160.3	169.6	178.4	188.0	198.4	209.1	220.3
147.5°	143.0	146.1	150.8	156.3	163.5	171.7	179.8	188.4	197.5	206.9	215.6
150°	147.0	149.6	154.2	159.2	165.2	173.1	180.6	188.4	196.6	205.2	213.1
152.5°	150.8	153.0	157.0	161.8	167.2	174.5	181.2	188.1	195.5	203.2	210.3
155°	155.6	157.7	161.3	164.9	169.9	175.9	181.7	187.3	193.5	199.9	205.9
157.5°	160.3	162.0	165.0	168.1	172.0	177.1	182.0	186.4	191.3	196.7	201.7
160°	163.1	164.5	167.0	169.9	173.1	177.7	182.0	185.6	189.9	194.2	198.8
162.5°	165.7	167.1	169.4	171.6	174.2	178.3	181.8	184.7	188.1	191.9	195.6
165°	169.2	170.3	172.0	173.5	175.6	178.4	181.3	183.5	185.6	188.4	191.3
167.5°	172.1	172.8	173.7	174.7	176.1	178.4	180.5	181.5	183.1	185.1	187.1
170°	173.8	174.2	174.9	175.6	176.6	178.4	179.9	180.6	181.7	183.1	184.9
172.5°	174.7	175.0	175.7	176.1	176.6	178.1	179.4	179.5	180.0	181.1	182.3
175°	175.9	176.3	176.6	176.6	176.6	177.7	178.4	178.1	178.1	178.4	179.6
177.5°	176.7	176.7	177.0	176.7	176.7	177.3	177.6	177.0	177.0	177.3	177.6
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1732.9	1732.9	1742.2	1741.6	1747.7	1745.5	1746.6
5°	1862.8	1874.4	1884.6	1891.5	1901.7	1904.4	1903.0
7.5°	1997.5	2023.3	2035.8	2053.0	2056.1	2065.1	2064.2
10°	2080.9	2106.2	2125.3	2140.2	2147.7	2157.3	2158.0
12.5°	2146.4	2167.8	2184.6	2198.6	2207.7	2210.7	2212.5
15°	2197.5	2221.3	2241.1	2260.9	2272.5	2281.3	2286.1
17.5°	2249.0	2285.8	2320.7	2347.5	2363.7	2377.3	2377.1
20°	2288.9	2331.1	2374.7	2405.4	2436.7	2450.3	2452.4
22.5°	2331.4	2396.0	2452.2	2499.7	2540.8	2555.1	2560.4
25°	2419.6	2504.2	2590.8	2657.6	2705.2	2733.2	2737.3
27.5°	2526.4	2640.8	2731.9	2793.5	2833.2	2853.9	2858.3
30°	2601.7	2707.3	2789.1	2835.5	2853.9	2856.6	2846.4
32.5°	2635.4	2714.4	2747.1	2744.4	2708.3	2684.3	2675.1
35°	2594.1	2577.8	2498.1	2402.7	2329.8	2283.4	2271.1
37.5°	2360.8	2219.7	2073.1	1928.8	1852.1	1813.0	1746.0
40°	2130.7	1929.7	1777.0	1655.6	1569.0	1499.5	1483.2
42.5°	1871.2	1663.6	1510.9	1406.9	1337.9	1290.1	1269.4
45°	1503.6	1325.0	1198.9	1119.2	1066.0	1031.3	1015.6
47.5°	1202.6	1064.4	972.5	913.5	873.0	842.7	834.2
50°	1037.4	927.0	849.3	799.5	768.8	745.7	736.1
52.5°	901.1	811.9	752.2	711.1	682.2	667.7	659.7
55°	743.7	666.6	623.7	591.0	574.6	563.0	557.5
57.5°	608.1	552.5	521.2	498.6	483.4	476.1	473.3
60°	532.3	488.7	460.1	442.3	432.1	422.6	419.9
62.5°	465.2	430.9	408.8	393.2	383.0	379.0	377.3
65°	374.9	352.3	336.0	326.5	318.3	316.9	316.3
67.5°	298.0	284.8	276.2	266.2	263.4	258.6	257.6
70°	254.9	246.1	235.8	232.5	229.0	224.3	224.9
72.5°	216.2	207.3	200.4	195.9	194.7	192.6	194.4
75°	158.1	155.4	152.7	149.3	147.9	147.9	147.2
77.5°	112.9	110.6	107.6	105.5	105.1	102.2	103.3
80°	81.8	78.4	77.1	77.7	75.6	74.9	74.9
82.5°	60.5	59.3	58.0	58.1	57.7	57.0	57.6
85°	33.4	32.7	32.7	32.0	32.0	31.3	31.3
87.5°	13.3	13.9	13.0	12.5	12.5	13.1	13.6
90°	6.8	7.2	7.9	7.9	7.9	8.2	8.2
92.5°	45.8	34.5	29.3	24.7	23.8	23.3	22.7
95°	202.4	158.4	128.5	103.1	92.4	89.6	83.9
97.5°	344.2	301.3	259.6	237.6	217.6	207.3	202.7
100°	421.5	384.8	347.6	323.0	297.3	284.1	278.4
102.5°	468.9	451.3	426.2	399.8	381.5	367.2	362.9
105°	495.7	511.4	507.6	496.0	484.3	477.2	472.9
107.5°	471.8	512.1	530.8	536.5	536.5	534.1	531.3
110°	444.7	495.0	525.3	541.4	548.2	550.7	550.7



TEST NUMBER: P333582-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	417.9	468.8	504.5	528.0	539.7	545.8	548.5
115°	379.4	428.3	467.2	495.0	512.1	522.1	526.7
117.5°	352.7	394.9	430.6	458.4	476.2	486.0	488.9
120°	337.6	376.9	408.3	434.7	451.8	461.5	464.3
122.5°	326.8	361.7	391.1	414.8	430.4	440.1	442.6
125°	312.3	343.4	369.0	389.0	403.6	411.5	415.1
127.5°	298.4	327.4	351.4	369.6	382.5	389.9	391.5
130°	288.7	316.6	339.8	357.6	369.4	376.6	378.7
132.5°	279.6	304.9	327.2	345.1	356.8	363.3	365.8
135°	265.5	288.4	308.7	324.5	336.2	342.6	344.8
137.5°	253.0	272.0	289.2	303.3	314.0	319.9	322.2
140°	245.5	262.0	276.9	290.1	299.4	304.8	306.6
142.5°	239.2	253.4	266.4	277.6	285.5	290.5	292.1
145°	231.3	242.4	252.0	260.5	266.6	270.5	272.0
147.5°	224.6	233.2	240.4	247.2	252.1	254.3	255.0
150°	221.0	227.7	234.1	239.4	243.8	245.2	245.5
152.5°	217.2	223.4	228.4	232.9	236.3	237.7	238.1
155°	211.7	216.6	220.6	224.1	226.6	227.7	228.0
157.5°	206.3	210.3	213.3	216.1	218.1	219.1	219.0
160°	202.4	205.9	208.4	211.0	212.7	213.4	213.1
162.5°	198.9	202.0	204.2	206.1	207.5	207.7	207.6
165°	193.8	195.9	197.7	199.1	199.9	199.9	199.9
167.5°	188.8	190.5	191.8	192.5	193.1	192.8	192.7
170°	185.9	187.0	187.7	188.4	188.8	188.8	188.4
172.5°	183.4	184.2	184.6	184.7	185.4	184.8	184.4
175°	179.6	180.3	180.3	180.3	180.6	179.9	179.6
177.5°	177.8	177.8	177.8	177.6	177.8	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0

(END OF REPORT)