

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333584-840

Luminaire Tested: **S125RDIP-S1090D365U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333584-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D365U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5545.0 lumens  
Efficiency: N/A  
Efficacy: 127.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333584-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333584-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	71	69	66
2	95	88	81	76	90	84	78	73	77	72	68	70	66	63	64	61	59	55
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50	47
4	80	69	61	54	76	66	59	53	61	54	50	56	51	47	51	47	44	41
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38	36
6	68	56	47	41	65	53	46	40	49	43	38	46	40	36	42	37	34	31
7	63	50	42	36	60	48	41	35	45	38	34	42	36	32	38	34	30	28
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	35	31	27	25
9	55	42	34	29	52	41	33	29	38	32	27	35	30	26	33	28	25	23
10	51	39	31	26	49	38	31	26	35	29	25	33	27	24	30	26	22	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333584-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.7	3.1
10°-20°	474.3	8.6
20°-30°	687.8	12.4
30°-40°	783.9	14.1
40°-50°	764.1	13.8
50°-60°	643.2	11.6
60°-70°	450.9	8.1
70°-80°	231.8	4.2
80°-90°	59.5	1.1
90°-100°	30.7	0.6
100°-110°	90.7	1.6
110°-120°	153.6	2.8
120°-130°	202.2	3.6
130°-140°	226.6	4.1
140°-150°	222.1	4.0
150°-160°	186.5	3.4
160°-170°	124.0	2.2
170°-180°	43.4	0.8
0°-30°	1331.9	24.0
0°-40°	2115.8	38.2
0°-60°	3523.1	63.5
0°-90°	4265.2	76.9
90°-120°	275.1	5.0
90°-150°	925.9	16.7
90°-180°	1280.0	23.1
0°-180°	5545.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	0	3	6	7	9	5
95°	23	24	28	30	31	25
105°	81	83	85	87	89	87
115°	154	155	156	156	155	152
125°	224	227	227	226	226	201
135°	292	294	294	294	293	225
145°	354	355	356	356	355	221
155°	405	405	405	406	405	186
165°	440	439	440	441	439	124
175°	458	456	456	458	456	43
180°	459	459	459	459	459	



TEST NUMBER: P333584-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.1	23.6	22.0	20.4	18.9	18.1	17.9	17.8	17.7	17.5	17.6
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.2	5.8	6.1
92.5°	8.7	9.1	9.5	10.0	10.4	11.0	11.6	12.3	13.0	13.7	14.2
95°	23.2	23.3	23.5	23.6	23.8	24.3	25.1	25.9	26.7	27.5	28.1
97.5°	38.6	38.6	38.7	38.8	38.8	39.4	40.5	41.6	42.6	43.7	44.3
100°	50.0	50.0	50.0	50.0	50.0	50.5	51.5	52.5	53.6	54.6	55.3
102.5°	62.2	62.6	62.9	63.2	63.5	63.9	64.4	64.9	65.5	66.0	66.9
105°	81.4	81.8	82.2	82.6	83.0	83.4	83.9	84.3	84.8	85.3	85.7
107.5°	102.5	102.9	103.3	103.7	104.1	104.5	104.8	105.2	105.5	105.9	106.1
110°	117.0	117.4	117.9	118.3	118.7	119.0	119.2	119.5	119.7	120.0	120.2



TEST NUMBER: P333584-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	131.9	132.1	132.3	132.5	132.7	133.0	133.3	133.6	133.9	134.2	134.3
115°	153.8	154.1	154.5	154.8	155.1	155.3	155.5	155.6	155.8	156.0	155.9
117.5°	175.8	175.9	176.1	176.2	176.4	176.5	176.7	176.8	176.9	177.1	177.1
120°	189.6	190.0	190.4	190.8	191.1	191.4	191.5	191.5	191.6	191.7	191.7
122.5°	204.4	204.5	204.7	204.8	204.9	205.1	205.3	205.5	205.7	205.9	205.9
125°	224.5	225.0	225.5	225.9	226.4	226.7	226.8	226.8	226.9	227.0	226.8
127.5°	245.9	246.2	246.5	246.7	247.0	247.2	247.3	247.4	247.5	247.5	247.5
130°	258.7	259.1	259.5	259.9	260.3	260.6	260.7	260.9	261.2	261.3	261.2
132.5°	271.7	272.3	273.0	273.6	274.2	274.6	274.5	274.5	274.5	274.4	274.3
135°	292.0	292.5	293.0	293.4	293.9	294.2	294.3	294.3	294.4	294.5	294.5
137.5°	311.1	311.5	312.0	312.5	313.0	313.3	313.5	313.6	313.8	314.0	314.1
140°	323.4	323.8	324.2	324.6	325.0	325.3	325.5	325.8	326.0	326.2	326.4
142.5°	335.7	336.0	336.3	336.7	337.0	337.3	337.6	337.9	338.2	338.5	338.6
145°	353.8	354.1	354.4	354.7	355.0	355.3	355.5	355.8	356.0	356.2	356.2
147.5°	370.4	370.6	370.7	370.9	371.1	371.3	371.5	371.7	371.8	372.0	372.2
150°	381.5	381.5	381.4	381.3	381.2	381.3	381.6	382.0	382.3	382.6	382.6
152.5°	390.7	390.8	390.9	391.0	391.1	391.2	391.4	391.5	391.6	391.7	391.9
155°	404.8	404.8	404.8	404.8	404.8	404.8	404.9	405.0	405.1	405.2	405.5
157.5°	417.3	417.2	417.0	416.8	416.7	416.6	416.7	416.8	416.8	416.9	417.2
160°	424.7	424.5	424.2	424.0	423.8	423.7	423.8	423.8	423.9	424.0	424.3
162.5°	431.3	431.1	431.0	430.8	430.6	430.5	430.5	430.6	430.6	430.6	431.0
165°	440.1	439.9	439.8	439.6	439.5	439.4	439.5	439.6	439.7	439.7	440.1
167.5°	447.5	447.2	446.9	446.6	446.3	446.1	446.1	446.1	446.1	446.1	446.6
170°	451.5	451.2	450.9	450.6	450.2	450.1	450.1	450.1	450.1	450.1	450.6
172.5°	454.3	454.0	453.7	453.4	453.1	452.9	452.9	452.9	452.9	452.9	453.4
175°	457.6	457.3	457.0	456.7	456.4	456.2	456.2	456.2	456.2	456.2	456.7
177.5°	459.2	459.0	458.7	458.5	458.2	458.1	458.0	458.0	457.9	457.8	458.2
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7



TEST NUMBER: P333584-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	17.7	17.8	17.8	17.8	17.6	17.4	17.2	17.0
90°	6.5	6.9	7.3	7.6	7.9	8.1	8.3	8.6
92.5°	14.7	15.2	15.8	16.2	16.4	16.5	16.7	16.9
95°	28.6	29.2	29.7	30.1	30.2	30.4	30.5	30.7
97.5°	44.8	45.3	45.8	46.2	46.3	46.4	46.5	46.6
100°	56.0	56.8	57.5	57.9	58.1	58.3	58.4	58.6
102.5°	67.6	68.4	69.2	69.7	69.9	70.1	70.3	70.5
105°	86.2	86.7	87.3	87.6	87.8	88.1	88.3	88.6
107.5°	106.4	106.6	106.8	107.0	106.9	106.9	106.9	106.9
110°	120.4	120.7	120.9	121.0	120.9	120.8	120.7	120.7





TEST NUMBER: P333584-840

CATALOG NUMBER: S125RDIP-S1090D365U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	134.4	134.5	134.6	134.6	134.5	134.3	134.2	134.1
115°	155.8	155.7	155.6	155.6	155.5	155.4	155.3	155.2
117.5°	177.2	177.3	177.3	177.2	176.9	176.6	176.3	175.9
120°	191.7	191.7	191.7	191.5	191.2	190.9	190.6	190.3
122.5°	205.8	205.7	205.7	205.5	205.3	205.0	204.8	204.5
125°	226.7	226.5	226.4	226.2	226.2	226.1	226.0	225.9
127.5°	247.4	247.3	247.2	247.1	247.0	246.8	246.6	246.5
130°	261.2	261.1	260.9	260.8	260.6	260.5	260.3	260.2
132.5°	274.3	274.2	274.1	274.0	273.7	273.5	273.3	273.1
135°	294.5	294.5	294.5	294.3	294.0	293.7	293.4	293.1
137.5°	314.2	314.3	314.4	314.2	313.8	313.4	313.0	312.6
140°	326.6	326.7	326.9	326.8	326.4	326.0	325.6	325.2
142.5°	338.7	338.8	338.9	338.7	338.3	337.9	337.6	337.2
145°	356.2	356.2	356.2	356.1	355.9	355.6	355.4	355.2
147.5°	372.4	372.6	372.8	372.6	372.1	371.5	371.0	370.5
150°	382.6	382.6	382.6	382.5	382.4	382.2	382.0	381.9
152.5°	392.1	392.3	392.5	392.4	392.2	391.9	391.6	391.3
155°	405.8	406.1	406.4	406.4	406.0	405.6	405.2	404.8
157.5°	417.5	417.9	418.2	418.1	417.6	417.0	416.5	416.0
160°	424.6	425.0	425.3	425.3	424.9	424.4	424.0	423.6
162.5°	431.3	431.7	432.1	432.1	431.6	431.1	430.7	430.2
165°	440.4	440.7	441.0	440.9	440.4	440.0	439.5	439.0
167.5°	447.1	447.5	448.0	448.0	447.5	447.0	446.5	446.1
170°	451.0	451.5	452.0	451.9	451.4	450.8	450.3	449.7
172.5°	453.9	454.3	454.8	454.8	454.3	453.8	453.3	452.8
175°	457.1	457.6	458.1	458.0	457.5	456.9	456.4	455.8
177.5°	458.6	459.0	459.3	459.3	458.9	458.4	458.0	457.5
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

(END OF REPORT)