

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333589-840

Luminaire Tested: **S125RDIP-S1090D590U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333589-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D590U840-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6652.6 lumens  
Efficiency: N/A  
Efficacy: 136.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333589-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333589-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	62	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	62	59	56	54	52	50	46
3	84	75	68	62	79	71	64	59	63	58	53	55	51	48	49	45	43	39
4	77	67	59	52	73	63	56	50	56	50	46	50	45	41	44	40	37	34
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	39	36	33	30
6	66	54	45	39	62	51	43	38	45	39	35	40	36	32	36	32	29	26
7	61	49	40	35	57	46	39	33	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	40	33	28	50	38	32	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333589-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.7	2.6
10°-20°	474.3	7.1
20°-30°	687.8	10.3
30°-40°	783.9	11.8
40°-50°	764.1	11.5
50°-60°	643.2	9.7
60°-70°	450.9	6.8
70°-80°	231.8	3.5
80°-90°	60.1	0.9
90°-100°	28.3	0.4
100°-110°	174.1	2.6
110°-120°	315.7	4.7
120°-130°	405.2	6.1
130°-140°	435.8	6.6
140°-150°	409.1	6.1
150°-160°	330.9	5.0
160°-170°	214.0	3.2
170°-180°	73.8	1.1
0°-30°	1331.9	20.0
0°-40°	2115.8	31.8
0°-60°	3523.1	53.0
0°-90°	4265.8	64.1
90°-120°	518.0	7.8
90°-150°	1768.1	26.6
90°-180°	2387.0	35.9
0°-180°	6652.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	1	5	9	12	14	5
95°	33	30	9	12	12	42
105°	169	172	172	172	171	180
115°	318	321	322	319	316	315
125°	452	456	456	454	452	404
135°	564	567	566	565	562	435
145°	654	655	655	655	652	409
155°	720	717	718	719	715	332
165°	760	757	757	760	756	215
175°	777	774	774	778	774	74
180°	777	777	777	777	777	



TEST NUMBER: P333589-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.2	23.7	22.2	20.7	19.2	18.5	18.4	18.4	18.3	18.2	18.4
90°	0.6	1.6	2.6	3.6	4.6	5.7	6.6	7.5	8.3	9.2	9.9
92.5°	8.9	8.2	7.5	6.8	6.0	6.1	6.9	7.7	8.4	9.2	9.9
95°	32.8	32.4	32.1	31.7	31.3	28.7	23.8	19.0	14.0	9.2	9.9
97.5°	68.6	69.3	70.0	70.6	71.3	66.9	57.3	47.6	38.0	28.4	24.7
100°	96.2	96.6	96.9	97.4	97.8	98.2	98.8	99.3	99.8	100.3	81.2
102.5°	124.3	124.8	125.3	125.8	126.2	126.6	126.9	127.3	127.6	127.9	124.3
105°	169.4	169.9	170.5	171.0	171.5	171.7	171.7	171.7	171.7	171.7	171.7
107.5°	216.2	216.2	216.2	216.2	216.2	216.3	216.5	216.8	217.1	217.3	217.3
110°	246.6	246.6	246.6	246.6	246.6	246.7	247.0	247.2	247.5	247.7	247.4



TEST NUMBER: P333589-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.2	275.5	275.8	276.1	276.4	276.6	276.8	276.9	277.1	277.2	276.8
115°	318.0	318.7	319.3	319.9	320.6	321.0	321.1	321.2	321.3	321.5	321.0
117.5°	362.4	362.3	362.3	362.3	362.3	362.5	363.0	363.6	364.0	364.5	363.9
120°	390.1	389.9	389.8	389.7	389.5	389.7	390.1	390.4	390.8	391.2	390.9
122.5°	414.4	415.0	415.5	416.0	416.5	416.8	417.0	417.2	417.3	417.5	417.3
125°	452.3	453.2	454.0	454.9	455.9	456.4	456.4	456.4	456.4	456.4	455.9
127.5°	488.4	489.0	489.7	490.3	490.9	491.2	491.1	491.1	491.0	490.9	490.6
130°	510.5	511.1	511.8	512.4	513.0	513.4	513.5	513.7	513.8	513.9	513.5
132.5°	532.6	533.3	534.1	534.8	535.5	535.8	535.5	535.2	534.9	534.7	534.6
135°	564.1	564.8	565.6	566.3	567.1	567.4	567.1	566.8	566.6	566.3	566.1
137.5°	593.0	593.7	594.3	595.0	595.6	595.9	595.6	595.4	595.2	594.9	595.0
140°	611.9	612.2	612.4	612.7	612.9	613.0	612.9	612.7	612.6	612.5	612.7
142.5°	628.9	629.1	629.2	629.4	629.5	629.8	630.0	630.1	630.3	630.5	630.5
145°	654.0	654.2	654.5	654.7	655.0	655.1	655.1	655.1	655.1	655.1	655.2
147.5°	675.8	675.8	675.7	675.7	675.6	675.7	675.8	676.0	676.1	676.3	676.5
150°	689.6	689.4	689.1	688.9	688.6	688.6	688.9	689.1	689.4	689.6	689.9
152.5°	703.1	702.5	702.0	701.4	700.7	700.6	700.8	701.1	701.4	701.7	702.0
155°	720.2	719.4	718.7	717.9	717.1	716.9	717.1	717.4	717.6	717.9	718.3
157.5°	733.5	733.0	732.6	732.1	731.6	731.4	731.4	731.4	731.4	731.5	732.0
160°	742.7	741.9	741.1	740.3	739.6	739.3	739.4	739.5	739.6	739.8	740.3
162.5°	750.0	749.3	748.5	747.7	747.0	746.7	746.8	746.9	747.0	747.2	747.9
165°	759.9	759.2	758.4	757.7	756.9	756.6	756.7	756.8	757.0	757.1	757.8
167.5°	767.3	766.6	765.8	765.0	764.2	763.9	764.0	764.1	764.2	764.4	765.3
170°	771.5	770.6	769.7	768.8	767.9	767.5	767.6	767.8	767.9	768.0	769.0
172.5°	774.3	773.4	772.4	771.5	770.6	770.3	770.5	770.8	771.0	771.2	772.1
175°	777.3	776.5	775.7	775.0	774.2	773.9	774.0	774.2	774.3	774.4	775.4
177.5°	778.6	778.0	777.4	776.8	776.2	775.9	776.0	776.1	776.2	776.3	777.1
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3



TEST NUMBER: P333589-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	18.5	18.6	18.7	18.7	18.5	18.4	18.2	18.1
90°	10.5	11.1	11.8	12.3	12.7	13.0	13.4	13.8
92.5°	10.5	11.1	11.8	12.2	12.3	12.5	12.7	12.9
95°	10.5	11.1	11.8	12.1	12.1	12.1	12.1	12.1
97.5°	21.1	17.5	13.9	12.1	12.1	12.1	12.1	12.1
100°	62.1	43.0	23.9	14.1	13.6	13.1	12.6	12.1
102.5°	120.7	117.0	113.5	107.3	98.6	89.9	81.2	72.5
105°	171.7	171.7	171.7	171.7	171.5	171.4	171.3	171.1
107.5°	217.4	217.4	217.4	217.2	216.9	216.5	216.1	215.7
110°	247.0	246.6	246.2	246.1	246.2	246.3	246.5	246.6





TEST NUMBER: P333589-840

CATALOG NUMBER: S125RDIP-S1090D590U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	276.3	275.8	275.3	275.0	274.8	274.6	274.5	274.3
115°	320.4	319.9	319.4	318.8	318.0	317.3	316.5	315.8
117.5°	363.1	362.4	361.8	361.3	361.0	360.6	360.3	360.0
120°	390.7	390.4	390.2	389.7	389.1	388.5	387.8	387.2
122.5°	417.0	416.8	416.5	416.0	415.3	414.4	413.7	413.0
125°	455.3	454.7	454.2	453.8	453.4	453.0	452.7	452.3
127.5°	490.3	490.1	489.8	489.2	488.2	487.3	486.4	485.3
130°	513.2	512.8	512.4	511.9	511.3	510.6	510.0	509.4
132.5°	534.5	534.4	534.4	534.0	533.4	532.7	532.1	531.5
135°	565.8	565.6	565.3	564.8	564.1	563.3	562.5	561.8
137.5°	595.0	595.1	595.1	594.8	594.2	593.5	592.9	592.2
140°	613.0	613.2	613.5	613.2	612.5	611.7	611.0	610.2
142.5°	630.6	630.6	630.7	630.3	629.5	628.7	627.9	627.2
145°	655.4	655.5	655.6	655.3	654.5	653.8	653.0	652.2
147.5°	676.6	676.8	676.9	676.5	675.6	674.7	673.8	672.9
150°	690.1	690.4	690.6	690.3	689.3	688.2	687.2	686.2
152.5°	702.2	702.5	702.7	702.4	701.5	700.5	699.5	698.6
155°	718.7	719.0	719.4	719.1	718.1	717.1	716.1	715.0
157.5°	732.4	732.8	733.2	732.9	731.8	730.7	729.7	728.7
160°	740.8	741.3	741.8	741.5	740.5	739.5	738.5	737.5
162.5°	748.6	749.3	750.0	749.8	748.7	747.6	746.5	745.3
165°	758.6	759.4	760.1	760.0	759.0	758.0	757.0	755.9
167.5°	766.2	767.1	768.0	767.9	766.8	765.6	764.5	763.3
170°	770.1	771.1	772.1	772.0	770.9	769.7	768.6	767.5
172.5°	773.1	774.1	775.0	774.9	773.7	772.5	771.3	770.2
175°	776.4	777.4	778.5	778.4	777.3	776.1	775.0	773.8
177.5°	777.8	778.5	779.2	779.1	778.3	777.5	776.7	775.9
180°	777.3	777.3	777.3	777.3	777.3	777.3	777.3	777.3

(END OF REPORT)