

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333594-840

Luminaire Tested: **S125RDIP-S1090D810U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333594-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7241.0 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37
4	77	66	59	53	72	62	56	50	55	50	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28
6	65	53	45	40	61	50	43	38	45	39	34	39	35	31	34	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	31	28	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10723	10723	10723	10723
5°	12337	10738	9483	10738
10°	14152	10683	8368	10683
15°	15285	10573	7438	10573
20°	16855	10446	6868	10446
25°	19506	10278	6372	10278
30°	21227	10100	6049	10100
35°	17906	9894	5750	9894
40°	12505	9522	5493	9522
45°	9276	9020	5242	9020
50°	7396	8499	5027	8499
55°	6277	7851	4835	7851
60°	5424	7272	4525	7272
65°	4834	6645	3895	6645
70°	4247	6086	3552	6086
75°	3673	5273	3334	5273
80°	2786	4437	2786	4437
85°	2319	3490	2623	3490



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	2.2
10°-20°	466.6	6.4
20°-30°	739.8	10.2
30°-40°	892.2	12.3
40°-50°	796.7	11.0
50°-60°	611.0	8.4
60°-70°	397.1	5.5
70°-80°	193.0	2.7
80°-90°	48.3	0.7
90°-100°	283.9	3.9
100°-110°	610.3	8.4
110°-120°	572.7	7.9
120°-130°	464.2	6.4
130°-140°	372.5	5.1
140°-150°	281.1	3.9
150°-160°	197.9	2.7
160°-170°	116.6	1.6
170°-180°	37.9	0.5
0°-30°	1365.7	18.9
0°-40°	2257.9	31.2
0°-60°	3665.6	50.6
0°-90°	4304.0	59.4
90°-120°	1466.9	20.3
90°-150°	2584.6	35.7
90°-180°	2937.0	40.6
0°-180°	7241.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1660	1660	1660	1660	1660	
5°	1903	1656	1463	1656	1903	190
15°	2286	1581	1112	1581	2286	655
25°	2737	1442	894	1442	2737	1257
35°	2271	1255	729	1255	2271	1372
45°	1016	988	574	988	1016	810
55°	558	697	429	697	558	506
65°	316	435	255	435	316	315
75°	147	211	134	211	147	157
85°	31	47	35	47	31	36
90°	18	1	18	1	18	14
95°	186	26	186	26	186	263
105°	1046	89	1046	89	1046	1040
115°	1166	160	1166	160	1166	1139
125°	918	221	918	221	918	831
135°	763	259	763	259	763	591
145°	602	302	602	302	602	382
155°	504	344	504	344	504	235
165°	442	376	442	376	442	126
175°	397	391	397	391	397	39
180°	392	392	392	392	392	



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1746.6	1745.5	1747.7	1741.6	1742.2	1732.9	1732.9	1725.9	1716.6	1709.5	1706.2
5°	1903.0	1904.4	1901.7	1891.5	1884.6	1874.4	1862.8	1842.4	1825.3	1809.0	1796.0
7.5°	2064.2	2065.1	2056.1	2053.0	2035.8	2023.3	1997.5	1969.6	1945.0	1913.7	1889.7
10°	2158.0	2157.3	2147.7	2140.2	2125.3	2106.2	2080.9	2048.2	2017.5	1983.5	1950.8
12.5°	2212.5	2210.7	2207.7	2198.6	2184.6	2167.8	2146.4	2114.2	2076.4	2039.1	2000.9
15°	2286.1	2281.3	2272.5	2260.9	2241.1	2221.3	2197.5	2168.9	2132.7	2090.4	2055.1
17.5°	2377.1	2377.3	2363.7	2347.5	2320.7	2285.8	2249.0	2202.8	2153.7	2107.3	2069.5
20°	2452.4	2450.3	2436.7	2405.4	2374.7	2331.1	2288.9	2232.2	2172.2	2111.6	2064.6
22.5°	2560.4	2555.1	2540.8	2499.7	2452.2	2396.0	2331.4	2262.2	2189.7	2120.8	2059.1
25°	2737.3	2733.2	2705.2	2657.6	2590.8	2504.2	2419.6	2324.9	2220.7	2130.0	2055.1
27.5°	2858.3	2853.9	2833.2	2793.5	2731.9	2640.8	2526.4	2399.7	2269.6	2144.9	2036.8
30°	2846.4	2856.6	2853.9	2835.5	2789.1	2707.3	2601.7	2459.2	2304.5	2158.0	2029.1
32.5°	2675.1	2684.3	2708.3	2744.4	2747.1	2714.4	2635.4	2504.0	2343.8	2177.1	2023.2
35°	2271.1	2283.4	2329.8	2402.7	2498.1	2577.8	2594.1	2523.2	2379.4	2200.2	2014.2
37.5°	1746.0	1813.0	1852.1	1928.8	2073.1	2219.7	2360.8	2412.8	2351.5	2190.7	1999.5
40°	1483.2	1499.5	1569.0	1655.6	1777.0	1929.7	2130.7	2275.8	2280.7	2168.9	1976.6
42.5°	1269.4	1290.1	1337.9	1406.9	1510.9	1663.6	1871.2	2062.6	2151.4	2108.9	1946.6
45°	1015.6	1031.3	1066.0	1119.2	1198.9	1325.0	1503.6	1725.2	1901.0	1969.8	1866.2
47.5°	834.2	842.7	873.0	913.5	972.5	1064.4	1202.6	1394.9	1605.9	1753.7	1739.2
50°	736.1	745.7	768.8	799.5	849.3	927.0	1037.4	1197.6	1415.0	1595.6	1631.7
52.5°	659.7	667.7	682.2	711.1	752.2	811.9	901.1	1046.0	1241.6	1433.7	1517.2
55°	557.5	563.0	574.6	591.0	623.7	666.6	743.7	843.8	1002.0	1195.5	1318.2
57.5°	473.3	476.1	483.4	498.6	521.2	552.5	608.1	693.1	806.5	980.8	1116.2
60°	419.9	422.6	432.1	442.3	460.1	488.7	532.3	591.6	700.6	844.6	981.5
62.5°	377.3	379.0	383.0	393.2	408.8	430.9	465.2	513.6	600.4	726.7	856.1
65°	316.3	316.9	318.3	326.5	336.0	352.3	374.9	409.0	474.4	569.9	684.3
67.5°	257.6	258.6	263.4	266.2	276.2	284.8	298.0	324.1	370.1	434.4	523.5
70°	224.9	224.3	229.0	232.5	235.8	246.1	254.9	276.1	304.7	353.8	428.1
72.5°	194.4	192.6	194.7	195.9	200.4	207.3	216.2	229.1	251.3	285.1	341.9
75°	147.2	147.9	147.9	149.3	152.7	155.4	158.1	164.9	177.2	199.8	230.4
77.5°	103.3	102.2	105.1	105.5	107.6	110.6	112.9	115.6	120.7	129.9	145.7
80°	74.9	74.9	75.6	77.7	77.1	78.4	81.8	84.5	90.7	96.1	101.6
82.5°	57.6	57.0	57.7	58.1	58.0	59.3	60.5	61.1	63.4	66.1	69.9
85°	31.3	31.3	32.0	32.0	32.7	32.7	33.4	33.4	33.4	34.0	34.7
87.5°	15.7	15.0	14.3	14.3	14.9	15.7	15.0	14.3	14.1	13.9	14.2
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2	13.4	12.6	11.0
92.5°	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0	206.1	254.6	258.6
95°	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7	684.6	699.6	570.9
97.5°	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6	866.2	747.1	509.8
100°	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2	910.4	713.1	454.8
102.5°	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5	883.9	653.0	413.1
105°	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6	799.1	572.5	372.7
107.5°	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5	712.6	517.1	355.7
110°	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8	663.3	491.1	350.6



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0	626.6	475.9	350.6
115°	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0	586.6	459.6	352.9
117.5°	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0	562.8	451.5	358.2
120°	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2	549.6	447.7	363.2
122.5°	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2	538.2	444.5	367.6
125°	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4	522.7	440.6	375.1
127.5°	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1	508.5	438.7	383.4
130°	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3	499.1	437.5	388.5
132.5°	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5	491.5	437.5	394.2
135°	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0	482.4	437.5	401.9
137.5°	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6	474.4	438.4	409.0
140°	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1	470.6	439.0	412.1
142.5°	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0	467.5	439.7	414.0
145°	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2	462.7	439.0	416.2
147.5°	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1	457.8	437.0	416.9
150°	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4	454.0	435.0	416.9
152.5°	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0	449.6	432.5	416.3
155°	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7	442.2	428.0	414.5
157.5°	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2	435.3	423.2	412.5
160°	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8	429.6	420.1	410.6
162.5°	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8	424.4	416.3	408.7
165°	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2	416.9	410.6	405.9
167.5°	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0	409.5	405.1	401.4
170°	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0	405.1	401.9	399.5
172.5°	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3	400.6	398.1	397.0
175°	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2	394.8	394.0	394.0
177.5°	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9	392.2	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1706.2	1702.3	1695.3	1688.7	1680.5	1673.4	1668.6	1662.5	1655.0	1645.7	1638.0
5°	1781.7	1766.7	1747.0	1729.9	1708.1	1691.0	1673.3	1656.3	1639.2	1617.4	1598.3
7.5°	1865.4	1834.4	1804.3	1766.5	1732.1	1701.4	1671.9	1642.1	1613.0	1582.0	1552.2
10°	1916.6	1879.2	1837.6	1789.9	1746.3	1704.7	1666.5	1629.0	1589.5	1554.7	1517.2
12.5°	1964.7	1916.2	1868.7	1808.5	1756.1	1705.3	1656.7	1609.9	1567.7	1522.6	1482.4
15°	2008.0	1960.2	1907.1	1833.5	1760.6	1699.2	1641.9	1581.3	1528.8	1478.3	1433.4
17.5°	2024.8	1974.7	1913.0	1842.2	1762.5	1685.4	1611.5	1545.1	1483.3	1424.5	1373.9
20°	2018.2	1969.8	1906.4	1839.0	1753.7	1673.3	1593.6	1519.9	1451.2	1389.1	1335.2
22.5°	2002.4	1952.4	1891.2	1819.9	1739.0	1653.7	1568.5	1490.0	1417.9	1353.6	1294.9
25°	1978.7	1910.6	1847.9	1778.3	1701.3	1616.8	1528.8	1442.3	1365.2	1299.8	1235.8
27.5°	1954.0	1869.0	1789.2	1720.1	1638.7	1563.3	1478.5	1389.8	1308.8	1242.1	1176.4
30°	1931.7	1836.2	1748.3	1669.9	1592.9	1521.4	1440.9	1354.3	1271.2	1202.3	1135.6
32.5°	1903.8	1802.4	1705.8	1615.4	1541.1	1470.1	1397.2	1314.5	1233.6	1162.6	1094.7
35°	1869.0	1739.5	1634.5	1538.3	1455.9	1387.0	1321.6	1254.9	1173.8	1100.1	1034.0
37.5°	1823.1	1676.2	1554.7	1450.1	1363.0	1293.9	1242.2	1181.2	1107.2	1036.7	975.3
40°	1795.3	1630.4	1497.4	1393.9	1302.5	1229.6	1181.2	1129.4	1062.0	995.8	934.4
42.5°	1758.3	1588.4	1439.7	1331.7	1239.8	1169.6	1120.6	1075.4	1018.9	956.5	890.8
45°	1685.6	1507.0	1350.9	1235.1	1142.4	1073.5	1027.8	987.6	944.7	887.5	830.2
47.5°	1590.9	1422.1	1258.8	1132.3	1041.5	977.5	933.2	901.5	870.8	822.1	766.5
50°	1515.2	1352.3	1192.8	1070.2	973.3	912.6	871.1	845.9	817.9	773.7	727.3
52.5°	1425.7	1280.3	1124.1	998.7	907.4	850.5	810.5	785.4	762.3	726.2	682.0
55°	1284.9	1157.4	1014.2	900.4	816.6	759.3	721.1	697.3	683.7	653.0	618.2
57.5°	1122.2	1030.9	904.6	794.9	720.7	664.2	636.2	615.9	600.5	578.9	554.3
60°	1008.8	944.7	831.5	727.3	659.1	605.2	580.1	563.0	548.7	530.3	511.2
62.5°	893.7	847.1	748.7	659.1	596.4	551.3	527.7	512.3	495.8	483.4	464.8
65°	739.5	697.9	629.8	559.6	501.7	465.5	448.5	434.8	424.6	411.0	398.1
67.5°	575.3	558.4	511.3	462.9	421.3	389.2	374.5	365.0	352.6	344.5	335.6
70°	474.4	466.3	432.8	400.8	361.9	340.1	326.5	322.3	307.4	299.2	293.1
72.5°	385.0	381.1	361.9	339.7	312.4	293.3	280.6	276.1	266.5	259.9	256.0
75°	263.8	265.2	261.8	247.4	237.2	224.9	214.0	211.3	204.5	199.0	195.6
77.5°	166.8	173.8	174.1	173.4	169.4	161.8	157.3	155.3	148.6	146.5	145.7
80°	114.5	122.0	128.9	128.2	126.7	124.7	121.3	119.3	115.8	113.8	112.5
82.5°	76.3	83.3	89.0	92.7	92.4	90.4	88.1	87.2	86.4	84.9	84.6
85°	36.2	37.5	39.5	44.3	47.7	48.4	47.7	47.1	44.9	45.6	46.4
87.5°	14.6	14.2	14.6	14.3	13.5	15.9	17.3	17.6	16.7	15.9	15.1
90°	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6	11.7	18.3	28.1
95°	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1	26.9	33.1	41.8
97.5°	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2	44.2	48.7	57.4
100°	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2	56.9	60.0	68.7
102.5°	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6	69.5	72.0	81.3
105°	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3	89.3	93.2	101.1
107.5°	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5	111.0	114.8	121.3
110°	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0	125.5	128.7	135.8



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5	140.1	142.6	149.7
115°	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5	161.1	163.5	170.6
117.5°	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4	180.9	183.4	190.5
120°	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1	193.5	196.6	203.7
122.5°	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4	206.1	208.6	215.7
125°	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1	222.7	226.6	233.7
127.5°	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2	236.6	241.7	250.6
130°	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4	244.8	251.1	261.4
132.5°	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7	251.8	259.3	270.8
135°	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0	262.2	271.7	284.3
137.5°	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0	274.3	283.2	295.8
140°	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5	281.9	291.3	304.0
142.5°	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3	290.1	298.9	311.5
145°	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6	303.2	311.1	322.1
147.5°	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5	316.5	323.3	333.6
150°	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8	325.3	330.8	341.1
152.5°	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5	333.6	338.4	347.4
155°	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3	344.3	349.0	356.9
157.5°	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7	354.6	358.3	365.1
160°	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6	360.8	364.1	369.5
162.5°	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3	366.6	369.7	374.6
165°	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9	374.3	376.7	380.6
167.5°	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5	380.7	382.1	384.4
170°	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4	384.6	385.4	386.9
172.5°	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9	386.5	387.2	388.8
175°	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8	389.3	390.1	390.8
177.5°	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2	391.0	391.0	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1632.5	1625.0	1619.5	1608.6	1600.9	1597.7	1591.6	1590.0	1596.0	1591.6	1591.1
5°	1584.1	1564.3	1548.6	1532.9	1515.9	1505.0	1488.6	1485.9	1481.8	1475.6	1474.3
7.5°	1525.8	1500.1	1479.9	1454.0	1431.5	1413.4	1392.9	1383.2	1378.0	1370.0	1359.4
10°	1486.5	1455.9	1428.7	1402.7	1374.8	1352.3	1331.8	1316.2	1306.0	1296.4	1292.3
12.5°	1447.8	1416.6	1381.7	1350.4	1319.2	1293.9	1271.3	1261.1	1249.8	1238.6	1229.1
15°	1387.8	1346.2	1308.0	1271.8	1245.3	1218.0	1196.2	1181.2	1164.2	1159.4	1141.0
17.5°	1323.9	1283.1	1238.5	1200.4	1169.6	1139.6	1115.6	1098.6	1085.8	1068.2	1059.8
20°	1284.1	1235.8	1192.1	1157.4	1123.3	1087.8	1063.3	1048.9	1036.7	1022.4	1015.6
22.5°	1241.6	1194.3	1149.6	1108.8	1074.2	1039.4	1021.9	1007.0	993.1	979.9	970.9
25°	1179.1	1131.5	1084.4	1042.2	1006.0	980.8	960.4	943.3	935.8	922.9	913.3
27.5°	1117.4	1066.7	1017.9	975.7	947.5	922.5	905.7	892.2	878.7	867.4	859.1
30°	1077.6	1025.8	972.6	939.3	909.3	885.3	867.0	854.0	843.8	833.6	827.5
32.5°	1037.8	984.4	937.2	901.1	872.7	852.1	833.1	820.8	810.0	798.7	791.4
35°	974.0	919.5	881.3	845.9	817.9	798.8	785.9	768.2	759.3	751.1	743.7
37.5°	914.7	864.0	822.7	791.6	767.3	748.4	731.6	722.1	711.1	703.8	697.5
40°	871.1	824.8	787.3	754.6	736.8	715.7	700.0	687.7	679.5	670.0	663.2
42.5°	831.8	788.7	752.3	722.9	700.8	683.0	667.8	655.6	645.2	638.4	632.7
45°	776.4	733.4	697.9	670.7	650.3	633.2	617.5	611.4	597.7	589.6	586.8
47.5°	718.9	680.5	646.3	621.2	600.3	584.1	569.4	556.8	549.4	541.3	536.9
50°	680.2	643.4	611.4	586.8	566.4	548.7	535.0	526.8	516.6	509.2	503.7
52.5°	641.6	607.4	575.4	552.0	534.2	516.5	501.3	493.1	483.4	478.6	474.8
55°	586.2	550.1	522.8	499.6	481.2	464.8	450.5	442.3	436.3	431.4	430.1
57.5°	523.5	494.8	469.5	448.6	429.5	414.1	401.6	393.8	388.4	387.7	383.6
60°	482.6	456.7	433.5	411.0	394.7	380.3	369.4	360.5	355.1	354.5	353.0
62.5°	441.7	416.9	395.4	375.6	360.8	347.1	336.7	326.8	323.5	320.1	317.1
65°	381.0	358.5	340.8	325.1	309.4	297.8	287.6	281.6	274.0	269.9	262.5
67.5°	321.4	304.0	287.0	273.8	261.5	250.4	242.0	232.9	227.8	224.5	219.0
70°	282.2	268.5	251.6	237.2	227.6	218.8	212.0	201.8	198.3	195.6	192.9
72.5°	245.1	233.1	218.8	207.2	197.6	189.3	181.5	176.6	173.3	170.6	169.0
75°	192.9	181.3	169.1	160.9	154.0	147.2	143.1	139.8	138.4	137.6	134.9
77.5°	141.7	135.5	125.7	119.2	114.6	111.9	108.3	106.4	106.3	103.3	102.4
80°	108.4	104.9	96.7	94.0	90.7	88.0	85.8	82.5	79.1	77.7	75.6
82.5°	80.6	77.2	73.9	69.5	66.7	65.0	63.0	61.7	62.2	60.3	59.3
85°	42.9	39.5	38.2	37.5	36.2	37.5	36.8	36.2	35.4	34.7	35.4
87.5°	14.8	15.2	14.8	16.3	14.7	15.7	15.8	15.3	15.6	15.7	15.5
90°	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2	15.0	15.8	17.4
92.5°	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0	101.6	76.4	64.7
95°	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7	447.7	350.6	284.3
97.5°	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6	761.3	666.7	574.5
100°	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2	932.5	851.2	769.1
102.5°	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5	1037.4	998.4	942.8
105°	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6	1096.8	1131.6	1122.9
107.5°	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5	1043.9	1133.1	1174.3
110°	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8	983.8	1095.2	1162.3



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0	924.4	1037.0	1116.2
115°	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0	839.4	947.6	1033.6
117.5°	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0	780.4	873.6	952.6
120°	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2	747.0	833.8	903.3
122.5°	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2	723.0	800.3	865.5
125°	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4	690.9	759.6	816.5
127.5°	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1	660.2	724.4	777.6
130°	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3	638.8	700.3	751.7
132.5°	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5	618.5	674.5	723.9
135°	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0	587.4	638.0	683.0
137.5°	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6	559.7	601.7	639.9
140°	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1	543.2	579.6	612.7
142.5°	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0	529.4	560.6	589.4
145°	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2	511.7	536.1	557.4
147.5°	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1	497.0	515.7	531.9
150°	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4	488.8	503.7	518.0
152.5°	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0	480.6	494.3	505.3
155°	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7	468.3	479.3	488.0
157.5°	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2	456.6	465.0	471.9
160°	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8	447.7	455.7	461.1
162.5°	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8	440.1	446.8	451.6
165°	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2	428.8	433.5	437.5
167.5°	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0	417.7	421.3	424.1
170°	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0	411.4	413.7	415.4
172.5°	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3	405.7	407.5	408.4
175°	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2	397.2	398.8	398.8
177.5°	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9	393.5	393.5	393.5
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1590.5	1584.6	1583.0	1585.1	1583.0	1584.6	1590.5	1591.1	1591.6	1596.0	1590.0
5°	1467.5	1460.7	1464.1	1462.7	1464.1	1460.7	1467.5	1474.3	1475.6	1481.8	1485.9
7.5°	1359.3	1350.8	1341.8	1344.6	1341.8	1350.8	1359.3	1359.4	1370.0	1378.0	1383.2
10°	1283.4	1276.7	1272.5	1276.0	1272.5	1276.7	1283.4	1292.3	1296.4	1306.0	1316.2
12.5°	1219.6	1215.6	1212.0	1210.5	1212.0	1215.6	1219.6	1229.1	1238.6	1249.8	1261.1
15°	1132.9	1124.7	1121.3	1112.4	1121.3	1124.7	1132.9	1141.0	1159.4	1164.2	1181.2
17.5°	1052.8	1050.1	1041.2	1037.4	1041.2	1050.1	1052.8	1059.8	1068.2	1085.8	1098.6
20°	1005.3	1002.6	993.8	999.3	993.8	1002.6	1005.3	1015.6	1022.4	1036.7	1048.9
22.5°	966.1	960.1	957.3	955.6	957.3	960.1	966.1	970.9	979.9	993.1	1007.0
25°	910.6	901.7	898.4	894.2	898.4	901.7	910.6	913.3	922.9	935.8	943.3
27.5°	855.3	850.5	846.0	845.0	846.0	850.5	855.3	859.1	867.4	878.7	892.2
30°	819.3	814.6	811.1	811.1	811.1	814.6	819.3	827.5	833.6	843.8	854.0
32.5°	787.1	783.5	780.0	779.5	780.0	783.5	787.1	791.4	798.7	810.0	820.8
35°	740.2	734.8	733.4	729.3	733.4	734.8	740.2	743.7	751.1	759.3	768.2
37.5°	691.6	687.0	686.9	686.5	686.9	687.0	691.6	697.5	703.8	711.1	722.1
40°	660.5	657.0	656.4	651.6	656.4	657.0	660.5	663.2	670.0	679.5	687.7
42.5°	627.2	625.4	623.1	621.1	623.1	625.4	627.2	632.7	638.4	645.2	655.6
45°	582.1	577.3	577.3	573.9	577.3	577.3	582.1	586.8	589.6	597.7	611.4
47.5°	535.4	531.8	532.2	528.7	532.2	531.8	535.4	536.9	541.3	549.4	556.8
50°	504.4	502.3	501.7	500.3	501.7	502.3	504.4	503.7	509.2	516.6	526.8
52.5°	473.3	472.3	474.9	471.9	474.9	472.3	473.3	474.8	478.6	483.4	493.1
55°	431.4	429.4	433.5	429.4	433.5	429.4	431.4	430.1	431.4	436.3	442.3
57.5°	383.3	381.4	385.1	383.0	385.1	381.4	383.3	383.6	387.7	388.4	393.8
60°	351.7	347.6	349.6	350.3	349.6	347.6	351.7	353.0	354.5	355.1	360.5
62.5°	314.1	311.6	313.2	310.0	313.2	311.6	314.1	317.1	320.1	323.5	326.8
65°	261.1	259.0	256.3	254.9	256.3	259.0	261.1	262.5	269.9	274.0	281.6
67.5°	219.3	214.4	214.3	215.4	214.3	214.4	219.3	219.0	224.5	227.8	232.9
70°	188.8	188.8	188.1	188.1	188.1	188.8	188.8	192.9	195.6	198.3	201.8
72.5°	167.5	167.0	165.7	165.2	165.7	167.0	167.5	169.0	170.6	173.3	176.6
75°	134.9	135.6	134.3	133.6	134.3	135.6	134.9	134.9	137.6	138.4	139.8
77.5°	99.7	96.7	98.3	96.7	98.3	96.7	99.7	102.4	103.3	106.3	106.4
80°	75.6	74.9	77.1	74.9	77.1	74.9	75.6	75.6	77.7	79.1	82.5
82.5°	59.9	59.2	60.1	58.6	60.1	59.2	59.9	59.3	60.3	62.2	61.7
85°	36.2	35.4	34.7	35.4	34.7	35.4	36.2	35.4	34.7	35.4	36.2
87.5°	16.1	15.5	15.7	15.7	15.7	15.5	16.1	15.5	15.7	15.6	15.3
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2
92.5°	54.6	52.7	51.6	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0
95°	228.2	204.5	198.2	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7
97.5°	525.7	481.5	458.6	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6
100°	714.6	657.7	628.5	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2
102.5°	884.5	844.0	812.3	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5
105°	1097.5	1071.5	1055.7	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6
107.5°	1187.1	1186.9	1181.7	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5
110°	1197.8	1212.8	1218.4	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.1	1193.9	1207.6	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0
115°	1095.2	1133.1	1155.2	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0
117.5°	1014.2	1053.3	1075.3	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0
120°	961.7	999.7	1021.0	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2
122.5°	917.6	952.3	973.6	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2
125°	860.7	893.0	910.4	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4
127.5°	817.7	846.3	862.7	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1
130°	791.2	817.3	833.0	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3
132.5°	763.4	789.4	804.0	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5
135°	717.7	743.8	758.0	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0
137.5°	671.1	694.7	707.8	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6
140°	642.0	662.5	674.3	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1
142.5°	614.2	631.6	642.8	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0
145°	576.4	589.9	598.5	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2
147.5°	546.8	557.6	562.7	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1
150°	529.9	539.3	542.5	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4
152.5°	515.3	522.9	526.0	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0
155°	495.8	501.4	503.7	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7
157.5°	478.1	482.6	484.8	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2
160°	466.7	470.6	472.2	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8
162.5°	456.0	459.2	459.6	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8
165°	440.6	442.2	442.2	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2
167.5°	425.8	427.2	426.6	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0
170°	416.9	417.7	417.7	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0
172.5°	408.7	410.1	408.9	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3
175°	398.8	399.5	398.0	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2
177.5°	392.9	393.5	391.6	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1591.6	1597.7	1600.9	1608.6	1619.5	1625.0	1632.5	1638.0	1645.7	1655.0	1662.5
5°	1488.6	1505.0	1515.9	1532.9	1548.6	1564.3	1584.1	1598.3	1617.4	1639.2	1656.3
7.5°	1392.9	1413.4	1431.5	1454.0	1479.9	1500.1	1525.8	1552.2	1582.0	1613.0	1642.1
10°	1331.8	1352.3	1374.8	1402.7	1428.7	1455.9	1486.5	1517.2	1554.7	1589.5	1629.0
12.5°	1271.3	1293.9	1319.2	1350.4	1381.7	1416.6	1447.8	1482.4	1522.6	1567.7	1609.9
15°	1196.2	1218.0	1245.3	1271.8	1308.0	1346.2	1387.8	1433.4	1478.3	1528.8	1581.3
17.5°	1115.6	1139.6	1169.6	1200.4	1238.5	1283.1	1323.9	1373.9	1424.5	1483.3	1545.1
20°	1063.3	1087.8	1123.3	1157.4	1192.1	1235.8	1284.1	1335.2	1389.1	1451.2	1519.9
22.5°	1021.9	1039.4	1074.2	1108.8	1149.6	1194.3	1241.6	1294.9	1353.6	1417.9	1490.0
25°	960.4	980.8	1006.0	1042.2	1084.4	1131.5	1179.1	1235.8	1299.8	1365.2	1442.3
27.5°	905.7	922.5	947.5	975.7	1017.9	1066.7	1117.4	1176.4	1242.1	1308.8	1389.8
30°	867.0	885.3	909.3	939.3	972.6	1025.8	1077.6	1135.6	1202.3	1271.2	1354.3
32.5°	833.1	852.1	872.7	901.1	937.2	984.4	1037.8	1094.7	1162.6	1233.6	1314.5
35°	785.9	798.8	817.9	845.9	881.3	919.5	974.0	1034.0	1100.1	1173.8	1254.9
37.5°	731.6	748.4	767.3	791.6	822.7	864.0	914.7	975.3	1036.7	1107.2	1181.2
40°	700.0	715.7	736.8	754.6	787.3	824.8	871.1	934.4	995.8	1062.0	1129.4
42.5°	667.8	683.0	700.8	722.9	752.3	788.7	831.8	890.8	956.5	1018.9	1075.4
45°	617.5	633.2	650.3	670.7	697.9	733.4	776.4	830.2	887.5	944.7	987.6
47.5°	569.4	584.1	600.3	621.2	646.3	680.5	718.9	766.5	822.1	870.8	901.5
50°	535.0	548.7	566.4	586.8	611.4	643.4	680.2	727.3	773.7	817.9	845.9
52.5°	501.3	516.5	534.2	552.0	575.4	607.4	641.6	682.0	726.2	762.3	785.4
55°	450.5	464.8	481.2	499.6	522.8	550.1	586.2	618.2	653.0	683.7	697.3
57.5°	401.6	414.1	429.5	448.6	469.5	494.8	523.5	554.3	578.9	600.5	615.9
60°	369.4	380.3	394.7	411.0	433.5	456.7	482.6	511.2	530.3	548.7	563.0
62.5°	336.7	347.1	360.8	375.6	395.4	416.9	441.7	464.8	483.4	495.8	512.3
65°	287.6	297.8	309.4	325.1	340.8	358.5	381.0	398.1	411.0	424.6	434.8
67.5°	242.0	250.4	261.5	273.8	287.0	304.0	321.4	335.6	344.5	352.6	365.0
70°	212.0	218.8	227.6	237.2	251.6	268.5	282.2	293.1	299.2	307.4	322.3
72.5°	181.5	189.3	197.6	207.2	218.8	233.1	245.1	256.0	259.9	266.5	276.1
75°	143.1	147.2	154.0	160.9	169.1	181.3	192.9	195.6	199.0	204.5	211.3
77.5°	108.3	111.9	114.6	119.2	125.7	135.5	141.7	145.7	146.5	148.6	155.3
80°	85.8	88.0	90.7	94.0	96.7	104.9	108.4	112.5	113.8	115.8	119.3
82.5°	63.0	65.0	66.7	69.5	73.9	77.2	80.6	84.6	84.9	86.4	87.2
85°	36.8	37.5	36.2	37.5	38.2	39.5	42.9	46.4	45.6	44.9	47.1
87.5°	15.8	15.7	14.7	16.3	14.8	15.2	14.8	15.1	15.9	16.7	17.6
90°	13.4	12.6	11.0	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8
92.5°	206.1	254.6	258.6	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6
95°	684.6	699.6	570.9	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1
97.5°	866.2	747.1	509.8	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2
100°	910.4	713.1	454.8	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2
102.5°	883.9	653.0	413.1	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6
105°	799.1	572.5	372.7	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3
107.5°	712.6	517.1	355.7	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5
110°	663.3	491.1	350.6	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	626.6	475.9	350.6	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5
115°	586.6	459.6	352.9	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5
117.5°	562.8	451.5	358.2	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4
120°	549.6	447.7	363.2	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1
122.5°	538.2	444.5	367.6	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4
125°	522.7	440.6	375.1	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1
127.5°	508.5	438.7	383.4	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2
130°	499.1	437.5	388.5	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4
132.5°	491.5	437.5	394.2	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7
135°	482.4	437.5	401.9	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0
137.5°	474.4	438.4	409.0	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0
140°	470.6	439.0	412.1	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5
142.5°	467.5	439.7	414.0	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3
145°	462.7	439.0	416.2	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6
147.5°	457.8	437.0	416.9	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5
150°	454.0	435.0	416.9	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8
152.5°	449.6	432.5	416.3	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5
155°	442.2	428.0	414.5	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3
157.5°	435.3	423.2	412.5	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7
160°	429.6	420.1	410.6	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6
162.5°	424.4	416.3	408.7	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3
165°	416.9	410.6	405.9	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9
167.5°	409.5	405.1	401.4	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5
170°	405.1	401.9	399.5	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4
172.5°	400.6	398.1	397.0	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9
175°	394.8	394.0	394.0	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8
177.5°	392.2	391.6	391.6	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1668.6	1673.4	1680.5	1688.7	1695.3	1702.3	1706.2	1706.2	1709.5	1716.6	1725.9
5°	1673.3	1691.0	1708.1	1729.9	1747.0	1766.7	1781.7	1796.0	1809.0	1825.3	1842.4
7.5°	1671.9	1701.4	1732.1	1766.5	1804.3	1834.4	1865.4	1889.7	1913.7	1945.0	1969.6
10°	1666.5	1704.7	1746.3	1789.9	1837.6	1879.2	1916.6	1950.8	1983.5	2017.5	2048.2
12.5°	1656.7	1705.3	1756.1	1808.5	1868.7	1916.2	1964.7	2000.9	2039.1	2076.4	2114.2
15°	1641.9	1699.2	1760.6	1833.5	1907.1	1960.2	2008.0	2055.1	2090.4	2132.7	2168.9
17.5°	1611.5	1685.4	1762.5	1842.2	1913.0	1974.7	2024.8	2069.5	2107.3	2153.7	2202.8
20°	1593.6	1673.3	1753.7	1839.0	1906.4	1969.8	2018.2	2064.6	2111.6	2172.2	2232.2
22.5°	1568.5	1653.7	1739.0	1819.9	1891.2	1952.4	2002.4	2059.1	2120.8	2189.7	2262.2
25°	1528.8	1616.8	1701.3	1778.3	1847.9	1910.6	1978.7	2055.1	2130.0	2220.7	2324.9
27.5°	1478.5	1563.3	1638.7	1720.1	1789.2	1869.0	1954.0	2036.8	2144.9	2269.6	2399.7
30°	1440.9	1521.4	1592.9	1669.9	1748.3	1836.2	1931.7	2029.1	2158.0	2304.5	2459.2
32.5°	1397.2	1470.1	1541.1	1615.4	1705.8	1802.4	1903.8	2023.2	2177.1	2343.8	2504.0
35°	1321.6	1387.0	1455.9	1538.3	1634.5	1739.5	1869.0	2014.2	2200.2	2379.4	2523.2
37.5°	1242.2	1293.9	1363.0	1450.1	1554.7	1676.2	1823.1	1999.5	2190.7	2351.5	2412.8
40°	1181.2	1229.6	1302.5	1393.9	1497.4	1630.4	1795.3	1976.6	2168.9	2280.7	2275.8
42.5°	1120.6	1169.6	1239.8	1331.7	1439.7	1588.4	1758.3	1946.6	2108.9	2151.4	2062.6
45°	1027.8	1073.5	1142.4	1235.1	1350.9	1507.0	1685.6	1866.2	1969.8	1901.0	1725.2
47.5°	933.2	977.5	1041.5	1132.3	1258.8	1422.1	1590.9	1739.2	1753.7	1605.9	1394.9
50°	871.1	912.6	973.3	1070.2	1192.8	1352.3	1515.2	1631.7	1595.6	1415.0	1197.6
52.5°	810.5	850.5	907.4	998.7	1124.1	1280.3	1425.7	1517.2	1433.7	1241.6	1046.0
55°	721.1	759.3	816.6	900.4	1014.2	1157.4	1284.9	1318.2	1195.5	1002.0	843.8
57.5°	636.2	664.2	720.7	794.9	904.6	1030.9	1122.2	1116.2	980.8	806.5	693.1
60°	580.1	605.2	659.1	727.3	831.5	944.7	1008.8	981.5	844.6	700.6	591.6
62.5°	527.7	551.3	596.4	659.1	748.7	847.1	893.7	856.1	726.7	600.4	513.6
65°	448.5	465.5	501.7	559.6	629.8	697.9	739.5	684.3	569.9	474.4	409.0
67.5°	374.5	389.2	421.3	462.9	511.3	558.4	575.3	523.5	434.4	370.1	324.1
70°	326.5	340.1	361.9	400.8	432.8	466.3	474.4	428.1	353.8	304.7	276.1
72.5°	280.6	293.3	312.4	339.7	361.9	381.1	385.0	341.9	285.1	251.3	229.1
75°	214.0	224.9	237.2	247.4	261.8	265.2	263.8	230.4	199.8	177.2	164.9
77.5°	157.3	161.8	169.4	173.4	174.1	173.8	166.8	145.7	129.9	120.7	115.6
80°	121.3	124.7	126.7	128.2	128.9	122.0	114.5	101.6	96.1	90.7	84.5
82.5°	88.1	90.4	92.4	92.7	89.0	83.3	76.3	69.9	66.1	63.4	61.1
85°	47.7	48.4	47.7	44.3	39.5	37.5	36.2	34.7	34.0	33.4	33.4
87.5°	17.3	15.9	13.5	14.3	14.6	14.2	14.6	14.2	13.9	14.1	14.3
90°	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2
92.5°	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0
95°	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7
97.5°	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6
100°	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2
102.5°	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5
105°	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6
107.5°	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5
110°	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0
115°	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0
117.5°	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0
120°	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2
122.5°	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2
125°	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4
127.5°	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1
130°	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3
132.5°	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5
135°	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0
137.5°	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6
140°	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1
142.5°	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0
145°	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2
147.5°	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1
150°	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4
152.5°	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0
155°	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7
157.5°	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2
160°	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8
162.5°	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8
165°	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2
167.5°	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0
170°	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0
172.5°	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3
175°	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2
177.5°	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4	1660.4
2.5°	1732.9	1732.9	1742.2	1741.6	1747.7	1745.5	1746.6
5°	1862.8	1874.4	1884.6	1891.5	1901.7	1904.4	1903.0
7.5°	1997.5	2023.3	2035.8	2053.0	2056.1	2065.1	2064.2
10°	2080.9	2106.2	2125.3	2140.2	2147.7	2157.3	2158.0
12.5°	2146.4	2167.8	2184.6	2198.6	2207.7	2210.7	2212.5
15°	2197.5	2221.3	2241.1	2260.9	2272.5	2281.3	2286.1
17.5°	2249.0	2285.8	2320.7	2347.5	2363.7	2377.3	2377.1
20°	2288.9	2331.1	2374.7	2405.4	2436.7	2450.3	2452.4
22.5°	2331.4	2396.0	2452.2	2499.7	2540.8	2555.1	2560.4
25°	2419.6	2504.2	2590.8	2657.6	2705.2	2733.2	2737.3
27.5°	2526.4	2640.8	2731.9	2793.5	2833.2	2853.9	2858.3
30°	2601.7	2707.3	2789.1	2835.5	2853.9	2856.6	2846.4
32.5°	2635.4	2714.4	2747.1	2744.4	2708.3	2684.3	2675.1
35°	2594.1	2577.8	2498.1	2402.7	2329.8	2283.4	2271.1
37.5°	2360.8	2219.7	2073.1	1928.8	1852.1	1813.0	1746.0
40°	2130.7	1929.7	1777.0	1655.6	1569.0	1499.5	1483.2
42.5°	1871.2	1663.6	1510.9	1406.9	1337.9	1290.1	1269.4
45°	1503.6	1325.0	1198.9	1119.2	1066.0	1031.3	1015.6
47.5°	1202.6	1064.4	972.5	913.5	873.0	842.7	834.2
50°	1037.4	927.0	849.3	799.5	768.8	745.7	736.1
52.5°	901.1	811.9	752.2	711.1	682.2	667.7	659.7
55°	743.7	666.6	623.7	591.0	574.6	563.0	557.5
57.5°	608.1	552.5	521.2	498.6	483.4	476.1	473.3
60°	532.3	488.7	460.1	442.3	432.1	422.6	419.9
62.5°	465.2	430.9	408.8	393.2	383.0	379.0	377.3
65°	374.9	352.3	336.0	326.5	318.3	316.9	316.3
67.5°	298.0	284.8	276.2	266.2	263.4	258.6	257.6
70°	254.9	246.1	235.8	232.5	229.0	224.3	224.9
72.5°	216.2	207.3	200.4	195.9	194.7	192.6	194.4
75°	158.1	155.4	152.7	149.3	147.9	147.9	147.2
77.5°	112.9	110.6	107.6	105.5	105.1	102.2	103.3
80°	81.8	78.4	77.1	77.7	75.6	74.9	74.9
82.5°	60.5	59.3	58.0	58.1	57.7	57.0	57.6
85°	33.4	32.7	32.7	32.0	32.0	31.3	31.3
87.5°	15.0	15.7	14.9	14.3	14.3	15.0	15.7
90°	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4



TEST NUMBER: P333594-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)