

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333596-840

Luminaire Tested: **S125RDIP-S1090D810U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333596-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7097.9 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333596-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333596-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	71	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333596-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.7	2.4
10°-20°	474.3	6.7
20°-30°	687.8	9.7
30°-40°	783.9	11.0
40°-50°	764.1	10.8
50°-60°	643.2	9.1
60°-70°	450.9	6.4
70°-80°	231.8	3.3
80°-90°	60.7	0.9
90°-100°	68.0	1.0
100°-110°	200.7	2.8
110°-120°	339.9	4.8
120°-130°	447.4	6.3
130°-140°	501.3	7.1
140°-150°	491.3	6.9
150°-160°	412.7	5.8
160°-170°	274.3	3.9
170°-180°	96.0	1.4
0°-30°	1331.9	18.8
0°-40°	2115.8	29.8
0°-60°	3523.1	49.6
0°-90°	4266.4	60.1
90°-120°	608.6	8.6
90°-150°	2048.6	28.9
90°-180°	2832.0	39.9
0°-180°	7097.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	1	7	13	17	19	6
95°	51	53	61	66	68	55
105°	180	184	189	193	196	192
115°	340	343	345	344	344	336
125°	497	501	502	501	500	445
135°	646	650	652	651	648	498
145°	782	786	788	788	786	489
155°	895	895	896	899	895	412
165°	974	972	973	976	971	275
175°	1012	1009	1009	1013	1008	96
180°	1015	1015	1015	1015	1015	



TEST NUMBER: P333596-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.2	23.8	22.4	21.0	19.6	18.9	18.9	18.9	18.9	18.9	19.1
90°	0.8	2.2	3.6	5.0	6.4	7.7	9.0	10.2	11.4	12.6	13.5
92.5°	19.1	20.1	21.1	22.0	23.0	24.2	25.8	27.3	28.8	30.3	31.5
95°	51.3	51.7	52.0	52.4	52.7	53.8	55.5	57.3	59.1	60.8	62.0
97.5°	85.3	85.4	85.5	85.7	85.8	87.2	89.6	92.0	94.4	96.8	98.0
100°	110.6	110.6	110.6	110.6	110.6	111.7	114.0	116.2	118.6	120.8	122.4
102.5°	137.7	138.5	139.2	139.9	140.6	141.5	142.6	143.8	144.9	146.1	147.8
105°	180.1	181.0	181.8	182.7	183.6	184.5	185.6	186.6	187.6	188.7	189.8
107.5°	226.8	227.6	228.5	229.4	230.4	231.2	232.0	232.8	233.6	234.4	234.9
110°	259.0	259.9	260.7	261.7	262.6	263.3	263.8	264.3	264.8	265.3	265.9



TEST NUMBER: P333596-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	291.9	292.4	292.8	293.3	293.7	294.3	294.9	295.6	296.3	296.9	297.2
115°	340.3	341.0	341.7	342.4	343.2	343.7	344.1	344.4	344.8	345.1	344.9
117.5°	389.0	389.3	389.6	389.9	390.2	390.6	390.9	391.2	391.5	391.8	391.9
120°	419.3	420.2	421.1	421.9	422.8	423.3	423.5	423.7	423.8	424.0	424.0
122.5°	452.1	452.5	452.8	453.1	453.4	453.8	454.2	454.7	455.1	455.7	455.4
125°	496.7	497.8	498.8	499.9	500.9	501.5	501.7	501.9	502.0	502.2	501.9
127.5°	544.1	544.7	545.2	545.8	546.4	546.8	547.0	547.2	547.5	547.8	547.5
130°	572.5	573.4	574.3	575.1	576.0	576.6	576.9	577.3	577.6	578.0	577.8
132.5°	601.0	602.4	603.8	605.2	606.7	607.3	607.3	607.2	607.1	607.1	606.9
135°	645.9	647.0	648.0	649.1	650.2	650.8	651.0	651.2	651.3	651.5	651.5
137.5°	688.3	689.3	690.3	691.4	692.4	693.1	693.5	693.8	694.2	694.6	694.8
140°	715.5	716.3	717.2	718.1	718.9	719.6	720.1	720.7	721.2	721.8	722.2
142.5°	742.7	743.4	744.1	744.8	745.6	746.3	746.9	747.6	748.2	748.9	749.1
145°	782.5	783.3	784.0	784.7	785.4	786.0	786.5	787.0	787.6	788.1	788.1
147.5°	819.5	819.9	820.3	820.7	821.0	821.4	821.9	822.3	822.7	823.1	823.5
150°	844.1	843.9	843.8	843.6	843.4	843.7	844.4	845.2	845.9	846.6	846.6
152.5°	864.3	864.6	864.8	865.2	865.4	865.7	865.9	866.2	866.5	866.8	867.2
155°	895.4	895.4	895.4	895.4	895.4	895.5	895.8	896.0	896.1	896.3	897.0
157.5°	923.3	922.9	922.5	922.1	921.7	921.6	921.8	922.0	922.1	922.3	923.0
160°	939.7	939.2	938.7	938.2	937.6	937.5	937.6	937.8	938.0	938.2	938.9
162.5°	954.2	953.8	953.4	953.1	952.7	952.5	952.5	952.6	952.6	952.7	953.5
165°	973.7	973.3	973.0	972.6	972.3	972.2	972.3	972.5	972.7	972.9	973.6
167.5°	990.1	989.4	988.7	988.0	987.2	986.9	986.9	986.9	986.9	986.9	988.0
170°	999.0	998.3	997.5	996.8	996.1	995.7	995.7	995.7	995.7	995.7	996.8
172.5°	1005.2	1004.5	1003.8	1003.1	1002.4	1002.1	1002.1	1002.1	1002.1	1002.1	1003.1
175°	1012.4	1011.7	1011.0	1010.3	1009.6	1009.2	1009.2	1009.2	1009.2	1009.2	1010.3
177.5°	1016.0	1015.4	1014.9	1014.3	1013.7	1013.4	1013.3	1013.1	1013.0	1012.8	1013.7
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7



TEST NUMBER: P333596-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	19.2	19.4	19.6	19.6	19.5	19.3	19.2	19.1
90°	14.3	15.2	16.2	16.9	17.4	17.9	18.4	19.0
92.5°	32.6	33.8	34.9	35.7	36.2	36.5	36.9	37.3
95°	63.2	64.5	65.7	66.6	66.9	67.3	67.6	67.9
97.5°	99.2	100.3	101.5	102.1	102.3	102.5	102.8	103.0
100°	124.0	125.5	127.1	128.2	128.5	128.8	129.2	129.5
102.5°	149.6	151.3	153.0	154.1	154.6	155.0	155.5	156.0
105°	190.9	191.9	193.0	193.7	194.3	194.8	195.3	195.8
107.5°	235.4	235.9	236.5	236.7	236.7	236.6	236.6	236.6
110°	266.4	266.9	267.4	267.6	267.4	267.2	267.1	266.9



TEST NUMBER: P333596-840

CATALOG NUMBER: S125RDIP-S1090D810U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	297.4	297.6	297.9	297.9	297.5	297.2	296.9	296.6
115°	344.8	344.6	344.4	344.2	344.1	343.9	343.7	343.6
117.5°	392.1	392.2	392.4	392.1	391.4	390.7	390.0	389.3
120°	424.0	424.0	424.0	423.7	423.0	422.3	421.6	420.9
122.5°	455.3	455.2	455.0	454.7	454.1	453.6	453.0	452.5
125°	501.5	501.2	500.8	500.6	500.4	500.2	500.1	499.9
127.5°	547.3	547.1	547.0	546.7	546.4	546.0	545.7	545.3
130°	577.6	577.5	577.3	577.0	576.7	576.3	576.0	575.6
132.5°	606.7	606.5	606.4	606.0	605.6	605.1	604.6	604.1
135°	651.5	651.5	651.5	651.2	650.5	649.7	649.0	648.3
137.5°	695.0	695.2	695.4	695.1	694.2	693.4	692.5	691.6
140°	722.5	722.8	723.2	722.9	722.1	721.1	720.2	719.4
142.5°	749.3	749.5	749.7	749.4	748.5	747.7	746.8	745.9
145°	788.1	788.1	788.1	787.8	787.3	786.8	786.3	785.7
147.5°	823.9	824.5	824.9	824.5	823.2	822.0	820.9	819.7
150°	846.6	846.6	846.6	846.4	846.0	845.7	845.3	845.0
152.5°	867.6	868.0	868.4	868.3	867.7	867.1	866.5	865.8
155°	897.7	898.4	899.1	899.0	898.1	897.3	896.4	895.4
157.5°	923.7	924.4	925.1	924.9	923.7	922.6	921.4	920.3
160°	939.6	940.2	940.9	940.9	940.0	939.1	938.2	937.4
162.5°	954.3	955.2	956.0	955.9	954.9	953.9	952.9	951.9
165°	974.3	975.0	975.6	975.5	974.4	973.4	972.3	971.3
167.5°	989.1	990.1	991.2	991.1	990.1	989.0	987.8	986.7
170°	997.8	999.0	1000.0	999.9	998.7	997.4	996.2	995.0
172.5°	1004.2	1005.2	1006.3	1006.3	1005.2	1004.1	1003.0	1001.9
175°	1011.3	1012.4	1013.4	1013.3	1012.1	1010.9	1009.7	1008.5
177.5°	1014.5	1015.3	1016.2	1016.1	1015.1	1014.2	1013.2	1012.2
180°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7	1014.7

(END OF REPORT)