

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333636-840

Luminaire Tested: **S125RDIP-S1270D1205U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333636-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9336.1 lumens  
Efficiency: N/A  
Efficacy: 130.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	56	54	51	47	45	43	39
3	83	74	66	61	76	69	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	55	47	42	47	42	37	41	36	33	34	31	29	25
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12385	12385	12385	12385
5°	14249	12401	10952	12401
10°	16344	12338	9664	12338
15°	17653	12211	8590	12211
20°	19467	12065	7932	12065
25°	22528	11870	7360	11870
30°	24515	11665	6986	11665
35°	20679	11427	6641	11427
40°	14441	10997	6345	10997
45°	10714	10418	6054	10418
50°	8542	9815	5805	9815
55°	7250	9067	5584	9067
60°	6263	8400	5227	8400
65°	5582	7674	4499	7674
70°	4904	7030	4101	7030
75°	4245	6089	3850	6089
80°	3217	5121	3217	5121
85°	2690	4024	3031	4024



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.9	2.0
10°-20°	538.9	5.8
20°-30°	854.5	9.2
30°-40°	1030.4	11.0
40°-50°	920.2	9.9
50°-60°	705.7	7.6
60°-70°	458.6	4.9
70°-80°	223.0	2.4
80°-90°	56.5	0.6
90°-100°	421.9	4.5
100°-110°	906.9	9.7
110°-120°	851.1	9.1
120°-130°	689.8	7.4
130°-140°	553.5	5.9
140°-150°	417.7	4.5
150°-160°	294.0	3.1
160°-170°	173.3	1.9
170°-180°	56.4	0.6
0°-30°	1577.3	16.9
0°-40°	2607.7	27.9
0°-60°	4233.5	45.3
0°-90°	4971.5	53.3
90°-120°	2179.9	23.3
90°-150°	3840.9	41.1
90°-180°	4365.0	46.8
0°-180°	9336.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1918	1918	1918	1918	1918	
5°	2198	1913	1689	1913	2198	220
15°	2640	1826	1285	1826	2640	757
25°	3161	1666	1033	1666	3161	1452
35°	2623	1449	842	1449	2623	1584
45°	1173	1141	663	1141	1173	936
55°	644	805	496	805	644	584
65°	365	502	294	502	365	363
75°	170	244	154	244	170	181
85°	36	54	41	54	36	42
90°	27	1	27	1	27	20
95°	276	39	276	39	276	391
105°	1555	133	1555	133	1555	1545
115°	1732	237	1732	237	1732	1692
125°	1365	328	1365	328	1365	1235
135°	1134	385	1134	385	1134	878
145°	894	448	894	448	894	568
155°	750	512	750	512	750	349
165°	657	559	657	559	657	188
175°	590	581	590	581	590	57
180°	582	582	582	582	582	



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2017.1	2015.9	2018.4	2011.4	2012.1	2001.4	2001.4	1993.2	1982.5	1974.3	1970.5
5°	2197.9	2199.5	2196.3	2184.4	2176.7	2164.8	2151.4	2127.8	2108.1	2089.2	2074.3
7.5°	2384.0	2385.1	2374.7	2371.1	2351.2	2336.7	2306.9	2274.8	2246.3	2210.2	2182.4
10°	2492.2	2491.5	2480.4	2471.8	2454.5	2432.5	2403.4	2365.5	2330.2	2290.8	2253.0
12.5°	2555.3	2553.2	2549.7	2539.2	2523.1	2503.7	2478.9	2441.8	2398.1	2355.0	2310.9
15°	2640.3	2634.7	2624.5	2611.1	2588.3	2565.5	2537.9	2504.9	2463.2	2414.4	2373.4
17.5°	2745.4	2745.6	2729.9	2711.3	2680.3	2640.0	2597.5	2544.1	2487.4	2433.7	2390.1
20°	2832.4	2829.9	2814.3	2778.0	2742.6	2692.2	2643.4	2578.1	2508.8	2438.7	2384.4
22.5°	2957.1	2950.9	2934.6	2887.0	2832.1	2767.1	2692.5	2612.7	2529.0	2449.4	2378.1
25°	3161.4	3156.6	3124.4	3069.3	2992.1	2892.2	2794.6	2685.1	2564.8	2460.0	2373.4
27.5°	3301.2	3296.0	3272.1	3226.3	3155.1	3049.9	2917.8	2771.6	2621.2	2477.2	2352.3
30°	3287.3	3299.1	3296.0	3274.8	3221.3	3126.7	3004.8	2840.2	2661.5	2492.2	2343.5
32.5°	3089.6	3100.2	3127.9	3169.6	3172.7	3134.9	3043.8	2891.8	2706.8	2514.4	2336.5
35°	2622.9	2637.2	2690.7	2774.9	2885.1	2977.2	2996.1	2914.3	2748.1	2541.1	2326.2
37.5°	2016.5	2094.0	2139.0	2227.7	2394.2	2563.6	2726.5	2786.5	2715.8	2530.1	2309.4
40°	1712.9	1731.8	1812.1	1912.1	2052.2	2228.6	2460.8	2628.5	2633.9	2504.9	2282.9
42.5°	1466.1	1490.1	1545.1	1625.0	1744.9	1921.3	2161.0	2382.3	2484.8	2435.6	2248.3
45°	1173.0	1191.0	1231.2	1292.6	1384.7	1530.3	1736.6	1992.4	2195.5	2275.0	2155.4
47.5°	963.5	973.3	1008.2	1055.0	1123.2	1229.3	1389.0	1611.0	1854.6	2025.5	2008.6
50°	850.2	861.2	888.0	923.4	980.9	1070.6	1198.1	1383.1	1634.3	1842.8	1884.6
52.5°	762.0	771.1	787.8	821.3	868.8	937.8	1040.7	1208.0	1434.0	1655.8	1752.3
55°	643.9	650.3	663.6	682.5	720.3	769.9	858.8	974.5	1157.2	1380.8	1522.5
57.5°	546.6	549.8	558.3	575.7	601.9	638.1	702.4	800.4	931.4	1132.8	1289.1
60°	484.9	488.1	499.1	510.9	531.4	564.4	614.8	683.3	809.2	975.3	1133.6
62.5°	435.8	437.7	442.4	454.2	472.2	497.7	537.3	593.2	693.4	839.3	988.8
65°	365.3	366.1	367.6	377.1	388.1	407.0	432.9	472.3	547.9	658.1	790.3
67.5°	297.6	298.6	304.2	307.5	319.0	328.9	344.2	374.3	427.5	501.8	604.6
70°	259.7	259.0	264.5	268.4	272.4	284.2	294.4	318.8	351.8	408.6	494.3
72.5°	224.5	222.5	224.8	226.2	231.5	239.4	249.7	264.7	290.1	329.2	394.9
75°	170.1	170.9	170.9	172.4	176.3	179.5	182.6	190.5	204.7	230.7	266.1
77.5°	119.4	118.1	121.4	121.9	124.2	127.6	130.4	133.5	139.4	150.1	168.3
80°	86.5	86.5	87.4	89.8	89.0	90.5	94.4	97.7	104.7	111.0	117.2
82.5°	66.4	65.8	66.6	67.1	67.0	68.5	69.9	70.5	73.2	76.3	80.8
85°	36.3	36.3	37.0	37.0	37.8	37.8	38.6	38.6	38.6	39.4	40.2
87.5°	19.3	18.6	17.8	17.8	18.4	19.2	18.3	17.5	17.2	17.0	17.2
90°	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1	20.0	18.8	16.5
92.5°	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9	306.3	378.3	384.5
95°	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6	1017.3	1039.7	848.4
97.5°	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5	1287.3	1110.2	757.6
100°	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3	1352.9	1059.6	675.9
102.5°	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2	1313.5	970.4	613.9
105°	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2	1187.5	850.7	553.8
107.5°	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8	1058.9	768.3	528.5
110°	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1	985.6	729.8	521.0



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2	931.2	707.3	521.0
115°	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5	871.8	683.0	524.5
117.5°	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0	836.4	671.0	532.3
120°	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3	816.7	665.3	539.8
122.5°	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9	799.8	660.7	546.3
125°	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1	776.8	654.8	557.3
127.5°	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5	755.7	652.0	569.8
130°	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1	741.6	650.1	577.3
132.5°	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5	730.3	650.1	585.7
135°	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0	717.0	650.1	597.2
137.5°	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3	705.0	651.5	607.8
140°	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1	699.3	652.4	612.5
142.5°	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9	694.7	653.4	615.3
145°	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0	687.6	652.4	618.4
147.5°	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0	680.3	649.3	619.6
150°	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5	674.7	646.5	619.6
152.5°	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2	668.1	642.8	618.6
155°	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0	657.1	636.0	616.0
157.5°	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0	646.8	628.9	613.0
160°	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6	638.3	624.3	610.2
162.5°	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3	630.9	618.6	607.3
165°	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9	619.6	610.2	603.1
167.5°	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3	608.5	602.0	596.5
170°	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8	602.0	597.2	593.8
172.5°	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4	595.4	591.7	590.0
175°	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3	586.7	585.5	585.5
177.5°	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9	583.0	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1970.5	1966.1	1957.9	1950.4	1941.0	1932.8	1927.0	1920.2	1911.4	1900.7	1891.8
5°	2057.7	2040.4	2017.6	1997.9	1972.8	1953.1	1932.6	1912.9	1893.2	1868.0	1846.0
7.5°	2154.4	2118.7	2083.9	2040.1	2000.4	1965.0	1931.0	1896.5	1862.8	1827.0	1792.6
10°	2213.6	2170.3	2122.3	2067.2	2016.8	1968.8	1924.7	1881.4	1835.7	1795.6	1752.3
12.5°	2269.1	2213.1	2158.2	2088.6	2028.1	1969.4	1913.4	1859.4	1810.6	1758.5	1712.0
15°	2319.1	2264.0	2202.6	2117.6	2033.4	1962.5	1896.3	1826.3	1765.6	1707.5	1655.5
17.5°	2338.4	2280.7	2209.4	2127.7	2035.6	1946.4	1861.3	1784.4	1713.1	1645.3	1586.8
20°	2330.9	2275.0	2201.8	2123.8	2025.5	1932.6	1840.5	1755.4	1676.0	1604.3	1542.2
22.5°	2312.7	2254.8	2184.1	2101.8	2008.4	1910.0	1811.5	1720.8	1637.5	1563.4	1495.5
25°	2285.2	2206.6	2134.1	2053.8	1964.9	1867.2	1765.6	1665.7	1576.8	1501.2	1427.2
27.5°	2256.7	2158.5	2066.4	1986.6	1892.6	1805.5	1707.6	1605.1	1511.6	1434.6	1358.7
30°	2230.9	2120.7	2019.1	1928.6	1839.7	1757.1	1664.2	1564.2	1468.1	1388.7	1311.5
32.5°	2198.8	2081.6	1970.0	1865.6	1779.9	1697.9	1613.8	1518.2	1424.7	1342.6	1264.3
35°	2158.5	2008.9	1887.7	1776.8	1681.4	1601.9	1526.4	1449.3	1355.5	1270.5	1194.2
37.5°	2105.6	1935.9	1795.6	1674.7	1574.3	1494.4	1434.7	1364.2	1278.7	1197.3	1126.5
40°	2073.5	1883.0	1729.5	1609.8	1504.3	1420.1	1364.2	1304.4	1226.5	1150.1	1079.2
42.5°	2030.6	1834.5	1662.7	1538.0	1431.9	1350.8	1294.3	1242.0	1176.7	1104.8	1028.9
45°	1946.7	1740.5	1560.2	1426.4	1319.4	1239.8	1187.1	1140.6	1091.1	1024.9	958.8
47.5°	1837.4	1642.4	1453.8	1307.7	1202.9	1129.0	1077.8	1041.2	1005.7	949.5	885.2
50°	1750.0	1561.9	1377.6	1235.9	1124.1	1054.1	1006.0	976.9	944.6	893.4	839.9
52.5°	1646.7	1478.6	1298.3	1153.4	1047.9	982.3	936.1	907.1	880.4	838.7	787.7
55°	1483.9	1336.7	1171.3	1039.9	943.1	877.0	832.8	805.3	789.6	754.2	714.0
57.5°	1296.1	1190.5	1044.8	918.1	832.4	767.1	734.8	711.3	693.6	668.5	640.2
60°	1165.1	1091.1	960.4	839.9	761.2	699.0	669.9	650.3	633.7	612.5	590.4
62.5°	1032.2	978.4	864.6	761.2	688.8	636.7	609.5	591.7	572.6	558.3	536.8
65°	854.1	806.1	727.4	646.3	579.4	537.7	518.0	502.2	490.4	474.6	459.7
67.5°	664.4	644.9	590.6	534.6	486.7	449.5	432.5	421.5	407.3	397.9	387.6
70°	547.9	538.5	499.9	462.9	418.0	392.8	377.1	372.3	355.1	345.6	338.5
72.5°	444.6	440.2	418.0	392.3	360.7	338.6	324.2	318.8	307.8	300.2	295.7
75°	304.7	306.2	302.3	285.8	274.0	259.7	247.2	244.0	236.2	229.8	225.9
77.5°	192.7	200.8	201.1	200.3	195.5	186.9	181.7	179.4	171.6	169.3	168.3
80°	132.3	140.9	148.8	147.9	146.4	144.1	140.2	137.7	133.8	131.5	129.9
82.5°	88.2	96.2	102.8	107.0	106.7	104.4	101.7	100.6	99.8	98.1	97.8
85°	41.7	43.3	45.6	51.2	55.1	55.8	55.1	54.3	51.9	52.7	53.5
87.5°	17.6	17.1	17.5	17.0	15.9	18.6	20.0	20.4	19.4	18.6	17.8
90°	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2	2.3	4.6	7.1
92.5°	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3	17.4	27.3	41.8
95°	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7	39.9	49.3	62.2
97.5°	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3	65.7	72.3	85.2
100°	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1	84.5	89.2	102.1
102.5°	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9	103.3	107.0	120.9
105°	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6	132.6	138.5	150.2
107.5°	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6	165.0	170.6	180.3
110°	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2	186.6	191.3	201.9





TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8	208.1	211.9	222.5
115°	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0	239.3	242.9	253.5
117.5°	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2	268.7	272.5	283.1
120°	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0	287.5	292.2	302.8
122.5°	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7	306.3	310.0	320.5
125°	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5	330.9	336.8	347.3
127.5°	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0	351.5	359.1	372.4
130°	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2	363.8	373.1	388.4
132.5°	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6	374.1	385.4	402.5
135°	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9	389.6	403.6	422.4
137.5°	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1	407.7	420.8	439.6
140°	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4	418.9	433.0	451.8
142.5°	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5	431.1	444.2	463.0
145°	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3	450.6	462.3	478.8
147.5°	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9	470.3	480.4	495.6
150°	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1	483.4	491.7	507.0
152.5°	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2	495.6	502.9	516.3
155°	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6	511.6	518.7	530.4
157.5°	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1	526.8	532.5	542.6
160°	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5	536.2	541.0	549.2
162.5°	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8	544.7	549.4	556.6
165°	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6	556.2	559.8	565.6
167.5°	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0	565.8	567.9	571.2
170°	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6	571.5	572.6	575.0
172.5°	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4	574.3	575.4	577.7
175°	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9	578.5	579.7	580.9
177.5°	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0	581.1	581.1	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1885.5	1876.7	1870.4	1857.7	1849.0	1845.2	1838.3	1836.3	1843.3	1838.3	1837.7
5°	1829.5	1806.6	1788.6	1770.4	1750.7	1738.2	1719.3	1716.1	1711.4	1704.2	1702.7
7.5°	1762.2	1732.5	1709.2	1679.3	1653.3	1632.3	1608.7	1597.5	1591.4	1582.3	1570.0
10°	1716.9	1681.4	1650.0	1620.0	1587.8	1561.9	1538.2	1520.0	1508.2	1497.2	1492.6
12.5°	1672.1	1636.1	1595.8	1559.6	1523.6	1494.4	1468.2	1456.5	1443.4	1430.5	1419.5
15°	1602.8	1554.7	1510.7	1468.9	1438.2	1406.7	1381.5	1364.2	1344.5	1339.1	1317.8
17.5°	1529.0	1482.0	1430.4	1386.4	1350.8	1316.2	1288.5	1268.8	1254.1	1233.8	1224.0
20°	1483.1	1427.2	1376.8	1336.7	1297.3	1256.4	1228.0	1211.5	1197.3	1180.8	1173.0
22.5°	1434.0	1379.4	1327.7	1280.6	1240.6	1200.3	1180.1	1163.1	1146.9	1131.7	1121.3
25°	1361.9	1306.8	1252.4	1203.7	1162.0	1132.8	1109.1	1089.4	1080.9	1065.9	1054.8
27.5°	1290.5	1231.9	1175.6	1126.9	1094.2	1065.4	1046.0	1030.5	1014.8	1001.8	992.2
30°	1244.6	1184.8	1123.4	1084.8	1050.2	1022.6	1001.3	986.3	974.5	962.7	955.6
32.5°	1198.6	1136.9	1082.4	1040.7	1007.9	984.1	962.3	948.0	935.5	922.4	914.1
35°	1124.9	1062.0	1017.8	976.9	944.6	922.6	907.7	887.2	877.0	867.5	858.8
37.5°	1056.4	997.8	950.2	914.2	886.3	864.3	845.0	833.9	821.3	812.8	805.7
40°	1006.0	952.5	909.2	871.4	851.0	826.6	808.5	794.3	784.9	773.9	766.0
42.5°	960.7	911.0	868.9	835.0	809.4	788.8	771.3	757.1	745.2	737.3	730.6
45°	896.7	847.1	806.1	774.6	751.0	731.3	713.2	706.1	690.3	681.0	677.8
47.5°	830.3	786.0	746.4	717.4	693.2	674.6	657.6	643.2	634.5	625.2	620.2
50°	785.7	743.2	706.1	677.8	654.2	633.7	617.9	608.5	596.7	588.0	581.8
52.5°	740.9	701.6	664.6	637.4	617.0	596.5	579.0	569.5	558.3	552.8	548.4
55°	677.0	635.3	603.8	577.0	555.7	536.8	520.4	510.9	503.8	498.3	496.8
57.5°	604.6	571.5	542.2	518.2	496.0	478.3	463.8	454.8	448.6	447.8	443.0
60°	557.3	527.5	500.7	474.6	455.8	439.3	426.7	416.5	410.1	409.3	407.8
62.5°	510.1	481.4	456.6	433.7	416.8	400.8	388.9	377.4	373.7	369.7	366.2
65°	440.0	414.0	393.6	375.5	357.4	344.0	332.2	325.1	316.5	311.7	303.1
67.5°	371.2	351.1	331.4	316.2	301.9	289.2	279.4	268.9	263.1	259.3	253.0
70°	325.9	310.1	290.4	274.0	263.0	252.7	244.8	233.0	229.0	225.9	222.8
72.5°	283.1	269.2	252.7	239.3	228.3	218.6	209.5	204.0	200.2	196.9	195.1
75°	222.8	209.4	195.2	185.8	177.9	170.1	165.3	161.4	159.8	159.1	155.8
77.5°	163.6	156.5	145.1	137.6	132.4	129.3	125.0	123.0	122.8	119.4	118.3
80°	125.1	121.2	111.8	108.7	104.7	101.6	99.2	95.2	91.3	89.8	87.4
82.5°	93.0	89.1	85.3	80.3	77.0	75.1	72.7	71.3	71.8	69.6	68.5
85°	49.6	45.6	44.1	43.3	41.7	43.3	42.5	41.7	40.9	40.2	40.9
87.5°	17.6	18.1	17.7	19.4	17.8	18.9	19.1	18.7	19.0	19.2	19.0
90°	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1	22.3	23.4	25.9
92.5°	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9	150.9	113.6	96.2
95°	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6	665.3	521.0	422.4
97.5°	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5	1131.5	990.9	853.7
100°	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3	1385.8	1265.0	1142.9
102.5°	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2	1541.7	1483.7	1401.1
105°	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2	1629.9	1681.5	1668.6
107.5°	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8	1551.3	1683.8	1745.1
110°	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1	1462.1	1627.5	1727.3



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2	1373.8	1541.2	1658.7
115°	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5	1247.4	1408.1	1536.0
117.5°	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0	1159.8	1298.3	1415.6
120°	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3	1110.0	1239.1	1342.4
122.5°	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9	1074.4	1189.4	1286.1
125°	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1	1026.7	1128.8	1213.4
127.5°	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5	981.2	1076.5	1155.6
130°	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1	949.3	1040.9	1117.1
132.5°	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5	919.3	1002.3	1075.8
135°	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0	873.0	948.2	1015.0
137.5°	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3	831.7	894.1	951.0
140°	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1	807.3	861.3	910.6
142.5°	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9	786.7	833.1	875.9
145°	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0	760.3	796.8	828.4
147.5°	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0	738.5	766.5	790.4
150°	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5	726.4	748.6	769.7
152.5°	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2	714.2	734.6	751.0
155°	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0	695.8	712.3	725.2
157.5°	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0	678.4	691.2	701.3
160°	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6	665.3	677.0	685.3
162.5°	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3	654.1	663.9	671.2
165°	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9	637.1	644.2	650.1
167.5°	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3	620.8	626.1	630.4
170°	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8	611.4	614.9	617.2
172.5°	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4	602.9	605.5	606.9
175°	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3	590.3	592.6	592.6
177.5°	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9	584.8	584.8	584.8
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1837.0	1830.1	1828.2	1830.7	1828.2	1830.1	1837.0	1837.7	1838.3	1843.3	1836.3
5°	1694.9	1687.0	1690.9	1689.3	1690.9	1687.0	1694.9	1702.7	1704.2	1711.4	1716.1
7.5°	1569.8	1560.0	1549.6	1553.0	1549.6	1560.0	1569.8	1570.0	1582.3	1591.4	1597.5
10°	1482.3	1474.4	1469.7	1473.6	1469.7	1474.4	1482.3	1492.6	1497.2	1508.2	1520.0
12.5°	1408.7	1403.9	1399.8	1398.1	1399.8	1403.9	1408.7	1419.5	1430.5	1443.4	1456.5
15°	1308.3	1298.9	1294.9	1284.8	1294.9	1298.9	1308.3	1317.8	1339.1	1344.5	1364.2
17.5°	1215.9	1212.7	1202.5	1198.1	1202.5	1212.7	1215.9	1224.0	1233.8	1254.1	1268.8
20°	1161.1	1158.0	1147.7	1154.1	1147.7	1158.0	1161.1	1173.0	1180.8	1197.3	1211.5
22.5°	1115.8	1108.8	1105.5	1103.7	1105.5	1108.8	1115.8	1121.3	1131.7	1146.9	1163.1
25°	1051.7	1041.5	1037.5	1032.8	1037.5	1041.5	1051.7	1054.8	1065.9	1080.9	1089.4
27.5°	987.7	982.3	977.0	975.8	977.0	982.3	987.7	992.2	1001.8	1014.8	1030.5
30°	946.2	940.7	936.8	936.8	936.8	940.7	946.2	955.6	962.7	974.5	986.3
32.5°	909.1	904.8	900.9	900.3	900.9	904.8	909.1	914.1	922.4	935.5	948.0
35°	855.0	848.6	847.1	842.3	847.1	848.6	855.0	858.8	867.5	877.0	887.2
37.5°	798.7	793.5	793.3	792.8	793.3	793.5	798.7	805.7	812.8	821.3	833.9
40°	762.8	758.8	758.1	752.6	758.1	758.8	762.8	766.0	773.9	784.9	794.3
42.5°	724.4	722.4	719.6	717.3	719.6	722.4	724.4	730.6	737.3	745.2	757.1
45°	672.3	666.7	666.7	662.8	666.7	666.7	672.3	677.8	681.0	690.3	706.1
47.5°	618.4	614.2	614.6	610.6	614.6	614.2	618.4	620.2	625.2	634.5	643.2
50°	582.5	580.2	579.4	577.8	579.4	580.2	582.5	581.8	588.0	596.7	608.5
52.5°	546.6	545.5	548.6	545.0	548.6	545.5	546.6	548.4	552.8	558.3	569.5
55°	498.3	495.9	500.7	495.9	500.7	495.9	498.3	496.8	498.3	503.8	510.9
57.5°	442.7	440.5	444.7	442.4	444.7	440.5	442.7	443.0	447.8	448.6	454.8
60°	406.2	401.5	403.8	404.7	403.8	401.5	406.2	407.8	409.3	410.1	416.5
62.5°	362.7	359.9	361.6	358.0	361.6	359.9	362.7	366.2	369.7	373.7	377.4
65°	301.5	299.1	296.0	294.4	296.0	299.1	301.5	303.1	311.7	316.5	325.1
67.5°	253.3	247.6	247.5	248.7	247.5	247.6	253.3	253.0	259.3	263.1	268.9
70°	218.0	218.0	217.2	217.2	217.2	218.0	218.0	222.8	225.9	229.0	233.0
72.5°	193.5	192.9	191.5	190.9	191.5	192.9	193.5	195.1	196.9	200.2	204.0
75°	155.8	156.6	155.1	154.3	155.1	156.6	155.8	155.8	159.1	159.8	161.4
77.5°	115.1	111.8	113.5	111.8	113.5	111.8	115.1	118.3	119.4	122.8	123.0
80°	87.4	86.5	89.0	86.5	89.0	86.5	87.4	87.4	89.8	91.3	95.2
82.5°	69.1	68.4	69.5	67.7	69.5	68.4	69.1	68.5	69.6	71.8	71.3
85°	41.7	40.9	40.2	40.9	40.2	40.9	41.7	40.9	40.2	40.9	41.7
87.5°	19.7	19.0	19.3	19.3	19.3	19.0	19.7	19.0	19.2	19.0	18.7
90°	25.9	25.9	27.0	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1
92.5°	81.2	78.4	76.7	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9
95°	339.1	303.9	294.6	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6
97.5°	781.2	715.6	681.6	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5
100°	1062.0	977.4	934.0	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3
102.5°	1314.4	1254.4	1207.2	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2
105°	1631.0	1592.4	1568.8	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2
107.5°	1764.1	1763.9	1756.2	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8
110°	1780.1	1802.4	1810.6	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1736.0	1774.2	1794.6	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2
115°	1627.5	1683.8	1716.7	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5
117.5°	1507.1	1565.4	1598.0	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0
120°	1429.3	1485.5	1517.2	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3
122.5°	1363.5	1415.1	1446.8	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9
125°	1279.0	1327.2	1352.9	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1
127.5°	1215.2	1257.7	1282.1	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5
130°	1175.8	1214.5	1238.0	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1
132.5°	1134.5	1173.2	1194.8	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5
135°	1066.6	1105.4	1126.5	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0
137.5°	997.1	1032.4	1051.9	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3
140°	954.0	984.5	1002.1	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1
142.5°	912.7	938.5	955.1	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9
145°	856.6	876.6	889.5	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0
147.5°	812.7	828.7	836.2	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0
150°	787.4	801.4	806.2	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5
152.5°	765.8	777.0	781.7	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2
155°	736.9	745.1	748.6	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0
157.5°	710.3	717.2	720.4	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0
160°	693.5	699.3	701.8	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6
162.5°	677.5	682.5	683.0	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3
165°	654.8	657.1	657.1	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9
167.5°	632.7	634.8	633.9	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3
170°	619.6	620.8	620.8	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8
172.5°	607.3	609.5	607.6	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4
175°	592.6	593.8	591.4	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3
177.5°	583.9	584.8	582.0	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1838.3	1845.2	1849.0	1857.7	1870.4	1876.7	1885.5	1891.8	1900.7	1911.4	1920.2
5°	1719.3	1738.2	1750.7	1770.4	1788.6	1806.6	1829.5	1846.0	1868.0	1893.2	1912.9
7.5°	1608.7	1632.3	1653.3	1679.3	1709.2	1732.5	1762.2	1792.6	1827.0	1862.8	1896.5
10°	1538.2	1561.9	1587.8	1620.0	1650.0	1681.4	1716.9	1752.3	1795.6	1835.7	1881.4
12.5°	1468.2	1494.4	1523.6	1559.6	1595.8	1636.1	1672.1	1712.0	1758.5	1810.6	1859.4
15°	1381.5	1406.7	1438.2	1468.9	1510.7	1554.7	1602.8	1655.5	1707.5	1765.6	1826.3
17.5°	1288.5	1316.2	1350.8	1386.4	1430.4	1482.0	1529.0	1586.8	1645.3	1713.1	1784.4
20°	1228.0	1256.4	1297.3	1336.7	1376.8	1427.2	1483.1	1542.2	1604.3	1676.0	1755.4
22.5°	1180.1	1200.3	1240.6	1280.6	1327.7	1379.4	1434.0	1495.5	1563.4	1637.5	1720.8
25°	1109.1	1132.8	1162.0	1203.7	1252.4	1306.8	1361.9	1427.2	1501.2	1576.8	1665.7
27.5°	1046.0	1065.4	1094.2	1126.9	1175.6	1231.9	1290.5	1358.7	1434.6	1511.6	1605.1
30°	1001.3	1022.6	1050.2	1084.8	1123.4	1184.8	1244.6	1311.5	1388.7	1468.1	1564.2
32.5°	962.3	984.1	1007.9	1040.7	1082.4	1136.9	1198.6	1264.3	1342.6	1424.7	1518.2
35°	907.7	922.6	944.6	976.9	1017.8	1062.0	1124.9	1194.2	1270.5	1355.5	1449.3
37.5°	845.0	864.3	886.3	914.2	950.2	997.8	1056.4	1126.5	1197.3	1278.7	1364.2
40°	808.5	826.6	851.0	871.4	909.2	952.5	1006.0	1079.2	1150.1	1226.5	1304.4
42.5°	771.3	788.8	809.4	835.0	868.9	911.0	960.7	1028.9	1104.8	1176.7	1242.0
45°	713.2	731.3	751.0	774.6	806.1	847.1	896.7	958.8	1024.9	1091.1	1140.6
47.5°	657.6	674.6	693.2	717.4	746.4	786.0	830.3	885.2	949.5	1005.7	1041.2
50°	617.9	633.7	654.2	677.8	706.1	743.2	785.7	839.9	893.4	944.6	976.9
52.5°	579.0	596.5	617.0	637.4	664.6	701.6	740.9	787.7	838.7	880.4	907.1
55°	520.4	536.8	555.7	577.0	603.8	635.3	677.0	714.0	754.2	789.6	805.3
57.5°	463.8	478.3	496.0	518.2	542.2	571.5	604.6	640.2	668.5	693.6	711.3
60°	426.7	439.3	455.8	474.6	500.7	527.5	557.3	590.4	612.5	633.7	650.3
62.5°	388.9	400.8	416.8	433.7	456.6	481.4	510.1	536.8	558.3	572.6	591.7
65°	332.2	344.0	357.4	375.5	393.6	414.0	440.0	459.7	474.6	490.4	502.2
67.5°	279.4	289.2	301.9	316.2	331.4	351.1	371.2	387.6	397.9	407.3	421.5
70°	244.8	252.7	263.0	274.0	290.4	310.1	325.9	338.5	345.6	355.1	372.3
72.5°	209.5	218.6	228.3	239.3	252.7	269.2	283.1	295.7	300.2	307.8	318.8
75°	165.3	170.1	177.9	185.8	195.2	209.4	222.8	225.9	229.8	236.2	244.0
77.5°	125.0	129.3	132.4	137.6	145.1	156.5	163.6	168.3	169.3	171.6	179.4
80°	99.2	101.6	104.7	108.7	111.8	121.2	125.1	129.9	131.5	133.8	137.7
82.5°	72.7	75.1	77.0	80.3	85.3	89.1	93.0	97.8	98.1	99.8	100.6
85°	42.5	43.3	41.7	43.3	44.1	45.6	49.6	53.5	52.7	51.9	54.3
87.5°	19.1	18.9	17.8	19.4	17.7	18.1	17.6	17.8	18.6	19.4	20.4
90°	20.0	18.8	16.5	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2
92.5°	306.3	378.3	384.5	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3
95°	1017.3	1039.7	848.4	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7
97.5°	1287.3	1110.2	757.6	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3
100°	1352.9	1059.6	675.9	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1
102.5°	1313.5	970.4	613.9	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9
105°	1187.5	850.7	553.8	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6
107.5°	1058.9	768.3	528.5	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6
110°	985.6	729.8	521.0	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	931.2	707.3	521.0	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8
115°	871.8	683.0	524.5	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0
117.5°	836.4	671.0	532.3	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2
120°	816.7	665.3	539.8	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0
122.5°	799.8	660.7	546.3	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7
125°	776.8	654.8	557.3	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5
127.5°	755.7	652.0	569.8	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0
130°	741.6	650.1	577.3	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2
132.5°	730.3	650.1	585.7	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6
135°	717.0	650.1	597.2	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9
137.5°	705.0	651.5	607.8	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1
140°	699.3	652.4	612.5	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4
142.5°	694.7	653.4	615.3	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5
145°	687.6	652.4	618.4	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3
147.5°	680.3	649.3	619.6	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9
150°	674.7	646.5	619.6	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1
152.5°	668.1	642.8	618.6	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2
155°	657.1	636.0	616.0	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6
157.5°	646.8	628.9	613.0	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1
160°	638.3	624.3	610.2	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5
162.5°	630.9	618.6	607.3	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8
165°	619.6	610.2	603.1	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6
167.5°	608.5	602.0	596.5	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0
170°	602.0	597.2	593.8	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6
172.5°	595.4	591.7	590.0	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4
175°	586.7	585.5	585.5	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9
177.5°	583.0	582.0	582.0	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1927.0	1932.8	1941.0	1950.4	1957.9	1966.1	1970.5	1970.5	1974.3	1982.5	1993.2
5°	1932.6	1953.1	1972.8	1997.9	2017.6	2040.4	2057.7	2074.3	2089.2	2108.1	2127.8
7.5°	1931.0	1965.0	2000.4	2040.1	2083.9	2118.7	2154.4	2182.4	2210.2	2246.3	2274.8
10°	1924.7	1968.8	2016.8	2067.2	2122.3	2170.3	2213.6	2253.0	2290.8	2330.2	2365.5
12.5°	1913.4	1969.4	2028.1	2088.6	2158.2	2213.1	2269.1	2310.9	2355.0	2398.1	2441.8
15°	1896.3	1962.5	2033.4	2117.6	2202.6	2264.0	2319.1	2373.4	2414.4	2463.2	2504.9
17.5°	1861.3	1946.4	2035.6	2127.7	2209.4	2280.7	2338.4	2390.1	2433.7	2487.4	2544.1
20°	1840.5	1932.6	2025.5	2123.8	2201.8	2275.0	2330.9	2384.4	2438.7	2508.8	2578.1
22.5°	1811.5	1910.0	2008.4	2101.8	2184.1	2254.8	2312.7	2378.1	2449.4	2529.0	2612.7
25°	1765.6	1867.2	1964.9	2053.8	2134.1	2206.6	2285.2	2373.4	2460.0	2564.8	2685.1
27.5°	1707.6	1805.5	1892.6	1986.6	2066.4	2158.5	2256.7	2352.3	2477.2	2621.2	2771.6
30°	1664.2	1757.1	1839.7	1928.6	2019.1	2120.7	2230.9	2343.5	2492.2	2661.5	2840.2
32.5°	1613.8	1697.9	1779.9	1865.6	1970.0	2081.6	2198.8	2336.5	2514.4	2706.8	2891.8
35°	1526.4	1601.9	1681.4	1776.8	1887.7	2008.9	2158.5	2326.2	2541.1	2748.1	2914.3
37.5°	1434.7	1494.4	1574.3	1674.7	1795.6	1935.9	2105.6	2309.4	2530.1	2715.8	2786.5
40°	1364.2	1420.1	1504.3	1609.8	1729.5	1883.0	2073.5	2282.9	2504.9	2633.9	2628.5
42.5°	1294.3	1350.8	1431.9	1538.0	1662.7	1834.5	2030.6	2248.3	2435.6	2484.8	2382.3
45°	1187.1	1239.8	1319.4	1426.4	1560.2	1740.5	1946.7	2155.4	2275.0	2195.5	1992.4
47.5°	1077.8	1129.0	1202.9	1307.7	1453.8	1642.4	1837.4	2008.6	2025.5	1854.6	1611.0
50°	1006.0	1054.1	1124.1	1235.9	1377.6	1561.9	1750.0	1884.6	1842.8	1634.3	1383.1
52.5°	936.1	982.3	1047.9	1153.4	1298.3	1478.6	1646.7	1752.3	1655.8	1434.0	1208.0
55°	832.8	877.0	943.1	1039.9	1171.3	1336.7	1483.9	1522.5	1380.8	1157.2	974.5
57.5°	734.8	767.1	832.4	918.1	1044.8	1190.5	1296.1	1289.1	1132.8	931.4	800.4
60°	669.9	699.0	761.2	839.9	960.4	1091.1	1165.1	1133.6	975.3	809.2	683.3
62.5°	609.5	636.7	688.8	761.2	864.6	978.4	1032.2	988.8	839.3	693.4	593.2
65°	518.0	537.7	579.4	646.3	727.4	806.1	854.1	790.3	658.1	547.9	472.3
67.5°	432.5	449.5	486.7	534.6	590.6	644.9	664.4	604.6	501.8	427.5	374.3
70°	377.1	392.8	418.0	462.9	499.9	538.5	547.9	494.3	408.6	351.8	318.8
72.5°	324.2	338.6	360.7	392.3	418.0	440.2	444.6	394.9	329.2	290.1	264.7
75°	247.2	259.7	274.0	285.8	302.3	306.2	304.7	266.1	230.7	204.7	190.5
77.5°	181.7	186.9	195.5	200.3	201.1	200.8	192.7	168.3	150.1	139.4	133.5
80°	140.2	144.1	146.4	147.9	148.8	140.9	132.3	117.2	111.0	104.7	97.7
82.5°	101.7	104.4	106.7	107.0	102.8	96.2	88.2	80.8	76.3	73.2	70.5
85°	55.1	55.8	55.1	51.2	45.6	43.3	41.7	40.2	39.4	38.6	38.6
87.5°	20.0	18.6	15.9	17.0	17.5	17.1	17.6	17.2	17.0	17.2	17.5
90°	2.3	4.6	7.1	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1
92.5°	17.4	27.3	41.8	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9
95°	39.9	49.3	62.2	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6
97.5°	65.7	72.3	85.2	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5
100°	84.5	89.2	102.1	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3
102.5°	103.3	107.0	120.9	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2
105°	132.6	138.5	150.2	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2
107.5°	165.0	170.6	180.3	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8
110°	186.6	191.3	201.9	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1





TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	208.1	211.9	222.5	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2
115°	239.3	242.9	253.5	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5
117.5°	268.7	272.5	283.1	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0
120°	287.5	292.2	302.8	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3
122.5°	306.3	310.0	320.5	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9
125°	330.9	336.8	347.3	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1
127.5°	351.5	359.1	372.4	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5
130°	363.8	373.1	388.4	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1
132.5°	374.1	385.4	402.5	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5
135°	389.6	403.6	422.4	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0
137.5°	407.7	420.8	439.6	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3
140°	418.9	433.0	451.8	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1
142.5°	431.1	444.2	463.0	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9
145°	450.6	462.3	478.8	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0
147.5°	470.3	480.4	495.6	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0
150°	483.4	491.7	507.0	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5
152.5°	495.6	502.9	516.3	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2
155°	511.6	518.7	530.4	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0
157.5°	526.8	532.5	542.6	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0
160°	536.2	541.0	549.2	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6
162.5°	544.7	549.4	556.6	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3
165°	556.2	559.8	565.6	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9
167.5°	565.8	567.9	571.2	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3
170°	571.5	572.6	575.0	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8
172.5°	574.3	575.4	577.7	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4
175°	578.5	579.7	580.9	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3
177.5°	581.1	581.1	582.0	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2001.4	2001.4	2012.1	2011.4	2018.4	2015.9	2017.1
5°	2151.4	2164.8	2176.7	2184.4	2196.3	2199.5	2197.9
7.5°	2306.9	2336.7	2351.2	2371.1	2374.7	2385.1	2384.0
10°	2403.4	2432.5	2454.5	2471.8	2480.4	2491.5	2492.2
12.5°	2478.9	2503.7	2523.1	2539.2	2549.7	2553.2	2555.3
15°	2537.9	2565.5	2588.3	2611.1	2624.5	2634.7	2640.3
17.5°	2597.5	2640.0	2680.3	2711.3	2729.9	2745.6	2745.4
20°	2643.4	2692.2	2742.6	2778.0	2814.3	2829.9	2832.4
22.5°	2692.5	2767.1	2832.1	2887.0	2934.6	2950.9	2957.1
25°	2794.6	2892.2	2992.1	3069.3	3124.4	3156.6	3161.4
27.5°	2917.8	3049.9	3155.1	3226.3	3272.1	3296.0	3301.2
30°	3004.8	3126.7	3221.3	3274.8	3296.0	3299.1	3287.3
32.5°	3043.8	3134.9	3172.7	3169.6	3127.9	3100.2	3089.6
35°	2996.1	2977.2	2885.1	2774.9	2690.7	2637.2	2622.9
37.5°	2726.5	2563.6	2394.2	2227.7	2139.0	2094.0	2016.5
40°	2460.8	2228.6	2052.2	1912.1	1812.1	1731.8	1712.9
42.5°	2161.0	1921.3	1744.9	1625.0	1545.1	1490.1	1466.1
45°	1736.6	1530.3	1384.7	1292.6	1231.2	1191.0	1173.0
47.5°	1389.0	1229.3	1123.2	1055.0	1008.2	973.3	963.5
50°	1198.1	1070.6	980.9	923.4	888.0	861.2	850.2
52.5°	1040.7	937.8	868.8	821.3	787.8	771.1	762.0
55°	858.8	769.9	720.3	682.5	663.6	650.3	643.9
57.5°	702.4	638.1	601.9	575.7	558.3	549.8	546.6
60°	614.8	564.4	531.4	510.9	499.1	488.1	484.9
62.5°	537.3	497.7	472.2	454.2	442.4	437.7	435.8
65°	432.9	407.0	388.1	377.1	367.6	366.1	365.3
67.5°	344.2	328.9	319.0	307.5	304.2	298.6	297.6
70°	294.4	284.2	272.4	268.4	264.5	259.0	259.7
72.5°	249.7	239.4	231.5	226.2	224.8	222.5	224.5
75°	182.6	179.5	176.3	172.4	170.9	170.9	170.1
77.5°	130.4	127.6	124.2	121.9	121.4	118.1	119.4
80°	94.4	90.5	89.0	89.8	87.4	86.5	86.5
82.5°	69.9	68.5	67.0	67.1	66.6	65.8	66.4
85°	38.6	37.8	37.8	37.0	37.0	36.3	36.3
87.5°	18.3	19.2	18.4	17.8	17.8	18.6	19.3
90°	22.3	23.4	25.9	25.9	25.9	27.0	27.0
92.5°	150.9	113.6	96.2	81.2	78.4	76.7	74.8
95°	665.3	521.0	422.4	339.1	303.9	294.6	275.8
97.5°	1131.5	990.9	853.7	781.2	715.6	681.6	666.5
100°	1385.8	1265.0	1142.9	1062.0	977.4	934.0	915.2
102.5°	1541.7	1483.7	1401.1	1314.4	1254.4	1207.2	1193.2
105°	1629.9	1681.5	1668.6	1631.0	1592.4	1568.8	1554.8
107.5°	1551.3	1683.8	1745.1	1764.1	1763.9	1756.2	1746.8
110°	1462.1	1627.5	1727.3	1780.1	1802.4	1810.6	1810.6



TEST NUMBER: P333636-840

CATALOG NUMBER: S125RDIP-S1270D1205U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1373.8	1541.2	1658.7	1736.0	1774.2	1794.6	1803.1
115°	1247.4	1408.1	1536.0	1627.5	1683.8	1716.7	1731.9
117.5°	1159.8	1298.3	1415.6	1507.1	1565.4	1598.0	1607.3
120°	1110.0	1239.1	1342.4	1429.3	1485.5	1517.2	1526.6
122.5°	1074.4	1189.4	1286.1	1363.5	1415.1	1446.8	1455.3
125°	1026.7	1128.8	1213.4	1279.0	1327.2	1352.9	1364.7
127.5°	981.2	1076.5	1155.6	1215.2	1257.7	1282.1	1287.3
130°	949.3	1040.9	1117.1	1175.8	1214.5	1238.0	1245.0
132.5°	919.3	1002.3	1075.8	1134.5	1173.2	1194.8	1202.7
135°	873.0	948.2	1015.0	1066.6	1105.4	1126.5	1133.6
137.5°	831.7	894.1	951.0	997.1	1032.4	1051.9	1059.6
140°	807.3	861.3	910.6	954.0	984.5	1002.1	1007.9
142.5°	786.7	833.1	875.9	912.7	938.5	955.1	960.1
145°	760.3	796.8	828.4	856.6	876.6	889.5	894.1
147.5°	738.5	766.5	790.4	812.7	828.7	836.2	838.3
150°	726.4	748.6	769.7	787.4	801.4	806.2	807.3
152.5°	714.2	734.6	751.0	765.8	777.0	781.7	782.9
155°	695.8	712.3	725.2	736.9	745.1	748.6	749.8
157.5°	678.4	691.2	701.3	710.3	717.2	720.4	720.2
160°	665.3	677.0	685.3	693.5	699.3	701.8	700.5
162.5°	654.1	663.9	671.2	677.5	682.5	683.0	682.7
165°	637.1	644.2	650.1	654.8	657.1	657.1	657.1
167.5°	620.8	626.1	630.4	632.7	634.8	633.9	633.7
170°	611.4	614.9	617.2	619.6	620.8	620.8	619.6
172.5°	602.9	605.5	606.9	607.3	609.5	607.6	606.4
175°	590.3	592.6	592.6	592.6	593.8	591.4	590.3
177.5°	584.8	584.8	584.8	583.9	584.8	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0

(END OF REPORT)