

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333612-840

Luminaire Tested: **S125RDIP-S1270D365U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333612-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D365U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6296.8 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68
2	96	89	83	77	92	85	80	75	78	74	70	72	68	65	66	63	61	58
3	88	79	71	65	84	75	69	63	70	64	60	64	60	56	59	56	53	50
4	81	70	62	56	77	67	60	54	62	56	51	58	53	49	53	49	46	43
5	75	63	54	48	71	60	53	47	56	50	45	52	47	42	48	44	40	38
6	69	57	48	42	66	55	47	41	51	44	39	47	42	37	44	39	36	33
7	64	51	43	38	61	50	42	37	46	40	35	43	37	33	40	35	32	30
8	60	47	39	33	57	45	38	33	42	36	31	39	34	30	37	32	29	26
9	56	43	35	30	53	42	34	29	39	33	28	36	31	27	34	29	26	24
10	52	40	32	27	50	38	31	27	36	30	26	34	28	25	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12385	12385	12385	12385
5°	14249	12401	10952	12401
10°	16344	12338	9664	12338
15°	17653	12211	8590	12211
20°	19467	12065	7932	12065
25°	22528	11870	7360	11870
30°	24515	11665	6986	11665
35°	20679	11427	6641	11427
40°	14441	10997	6345	10997
45°	10714	10418	6054	10418
50°	8542	9815	5805	9815
55°	7250	9067	5584	9067
60°	6263	8400	5227	8400
65°	5582	7674	4499	7674
70°	4904	7030	4101	7030
75°	4245	6089	3850	6089
80°	3217	5121	3217	5121
85°	2690	4024	3031	4024



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.9	2.9
10°-20°	538.9	8.6
20°-30°	854.5	13.6
30°-40°	1030.4	16.4
40°-50°	920.2	14.6
50°-60°	705.7	11.2
60°-70°	458.6	7.3
70°-80°	223.0	3.5
80°-90°	54.2	0.9
90°-100°	128.3	2.0
100°-110°	275.8	4.4
110°-120°	258.9	4.1
120°-130°	209.8	3.3
130°-140°	168.4	2.7
140°-150°	127.0	2.0
150°-160°	89.4	1.4
160°-170°	52.7	0.8
170°-180°	17.1	0.3
0°-30°	1577.3	25.0
0°-40°	2607.7	41.4
0°-60°	4233.5	67.2
0°-90°	4969.3	78.9
90°-120°	663.0	10.5
90°-150°	1168.2	18.6
90°-180°	1328.0	21.1
0°-180°	6296.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1918	1918	1918	1918	1918	
5°	2198	1913	1689	1913	2198	220
15°	2640	1826	1285	1826	2640	757
25°	3161	1666	1033	1666	3161	1452
35°	2623	1449	842	1449	2623	1584
45°	1173	1141	663	1141	1173	936
55°	644	805	496	805	644	584
65°	365	502	294	502	365	363
75°	170	244	154	244	170	181
85°	36	54	41	54	36	42
90°	8	0	8	0	8	7
95°	84	12	84	12	84	119
105°	473	40	473	40	473	470
115°	527	72	527	72	527	515
125°	415	100	415	100	415	376
135°	345	117	345	117	345	267
145°	272	136	272	136	272	173
155°	228	156	228	156	228	106
165°	200	170	200	170	200	57
175°	180	177	180	177	180	17
180°	177	177	177	177	177	



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2017.1	2015.9	2018.4	2011.4	2012.1	2001.4	2001.4	1993.2	1982.5	1974.3	1970.5
5°	2197.9	2199.5	2196.3	2184.4	2176.7	2164.8	2151.4	2127.8	2108.1	2089.2	2074.3
7.5°	2384.0	2385.1	2374.7	2371.1	2351.2	2336.7	2306.9	2274.8	2246.3	2210.2	2182.4
10°	2492.2	2491.5	2480.4	2471.8	2454.5	2432.5	2403.4	2365.5	2330.2	2290.8	2253.0
12.5°	2555.3	2553.2	2549.7	2539.2	2523.1	2503.7	2478.9	2441.8	2398.1	2355.0	2310.9
15°	2640.3	2634.7	2624.5	2611.1	2588.3	2565.5	2537.9	2504.9	2463.2	2414.4	2373.4
17.5°	2745.4	2745.6	2729.9	2711.3	2680.3	2640.0	2597.5	2544.1	2487.4	2433.7	2390.1
20°	2832.4	2829.9	2814.3	2778.0	2742.6	2692.2	2643.4	2578.1	2508.8	2438.7	2384.4
22.5°	2957.1	2950.9	2934.6	2887.0	2832.1	2767.1	2692.5	2612.7	2529.0	2449.4	2378.1
25°	3161.4	3156.6	3124.4	3069.3	2992.1	2892.2	2794.6	2685.1	2564.8	2460.0	2373.4
27.5°	3301.2	3296.0	3272.1	3226.3	3155.1	3049.9	2917.8	2771.6	2621.2	2477.2	2352.3
30°	3287.3	3299.1	3296.0	3274.8	3221.3	3126.7	3004.8	2840.2	2661.5	2492.2	2343.5
32.5°	3089.6	3100.2	3127.9	3169.6	3172.7	3134.9	3043.8	2891.8	2706.8	2514.4	2336.5
35°	2622.9	2637.2	2690.7	2774.9	2885.1	2977.2	2996.1	2914.3	2748.1	2541.1	2326.2
37.5°	2016.5	2094.0	2139.0	2227.7	2394.2	2563.6	2726.5	2786.5	2715.8	2530.1	2309.4
40°	1712.9	1731.8	1812.1	1912.1	2052.2	2228.6	2460.8	2628.5	2633.9	2504.9	2282.9
42.5°	1466.1	1490.1	1545.1	1625.0	1744.9	1921.3	2161.0	2382.3	2484.8	2435.6	2248.3
45°	1173.0	1191.0	1231.2	1292.6	1384.7	1530.3	1736.6	1992.4	2195.5	2275.0	2155.4
47.5°	963.5	973.3	1008.2	1055.0	1123.2	1229.3	1389.0	1611.0	1854.6	2025.5	2008.6
50°	850.2	861.2	888.0	923.4	980.9	1070.6	1198.1	1383.1	1634.3	1842.8	1884.6
52.5°	762.0	771.1	787.8	821.3	868.8	937.8	1040.7	1208.0	1434.0	1655.8	1752.3
55°	643.9	650.3	663.6	682.5	720.3	769.9	858.8	974.5	1157.2	1380.8	1522.5
57.5°	546.6	549.8	558.3	575.7	601.9	638.1	702.4	800.4	931.4	1132.8	1289.1
60°	484.9	488.1	499.1	510.9	531.4	564.4	614.8	683.3	809.2	975.3	1133.6
62.5°	435.8	437.7	442.4	454.2	472.2	497.7	537.3	593.2	693.4	839.3	988.8
65°	365.3	366.1	367.6	377.1	388.1	407.0	432.9	472.3	547.9	658.1	790.3
67.5°	297.6	298.6	304.2	307.5	319.0	328.9	344.2	374.3	427.5	501.8	604.6
70°	259.7	259.0	264.5	268.4	272.4	284.2	294.4	318.8	351.8	408.6	494.3
72.5°	224.5	222.5	224.8	226.2	231.5	239.4	249.7	264.7	290.1	329.2	394.9
75°	170.1	170.9	170.9	172.4	176.3	179.5	182.6	190.5	204.7	230.7	266.1
77.5°	119.4	118.1	121.4	121.9	124.2	127.6	130.4	133.5	139.4	150.1	168.3
80°	86.5	86.5	87.4	89.8	89.0	90.5	94.4	97.7	104.7	111.0	117.2
82.5°	66.4	65.8	66.6	67.1	67.0	68.5	69.9	70.5	73.2	76.3	80.8
85°	36.3	36.3	37.0	37.0	37.8	37.8	38.6	38.6	38.6	39.4	40.2
87.5°	15.5	14.8	14.1	14.1	14.8	16.0	15.2	14.5	14.4	14.3	14.8
90°	8.2	8.2	7.9	7.9	7.9	7.2	6.8	6.5	6.1	5.8	4.9
92.5°	22.7	23.3	23.8	24.7	29.3	34.5	45.8	63.2	93.1	115.0	116.9
95°	83.9	89.6	92.4	103.1	128.5	158.4	202.4	256.6	309.4	316.2	258.0
97.5°	202.7	207.3	217.6	237.6	259.6	301.3	344.2	382.1	391.5	337.7	230.5
100°	278.4	284.1	297.3	323.0	347.6	384.8	421.5	439.0	411.5	322.2	205.6
102.5°	362.9	367.2	381.5	399.8	426.2	451.3	468.9	458.1	399.5	295.2	186.7
105°	472.9	477.2	484.3	496.0	507.6	511.4	495.7	446.9	361.2	258.7	168.4
107.5°	531.3	534.1	536.5	536.5	530.8	512.1	471.8	406.6	322.0	233.7	160.8
110°	550.7	550.7	548.2	541.4	525.3	495.0	444.7	376.9	299.8	222.0	158.4



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	548.5	545.8	539.7	528.0	504.5	468.8	417.9	353.5	283.3	215.1	158.4
115°	526.7	522.1	512.1	495.0	467.2	428.3	379.4	324.1	265.2	207.7	159.6
117.5°	488.9	486.0	476.2	458.4	430.6	394.9	352.7	305.1	254.4	204.1	161.9
120°	464.3	461.5	451.8	434.7	408.3	376.9	337.6	294.8	248.4	202.4	164.2
122.5°	442.6	440.1	430.4	414.8	391.1	361.7	326.8	287.1	243.3	201.0	166.1
125°	415.1	411.5	403.6	389.0	369.0	343.4	312.3	275.9	236.3	199.1	169.6
127.5°	391.5	389.9	382.5	369.6	351.4	327.4	298.4	264.5	229.8	198.3	173.3
130°	378.7	376.6	369.4	357.6	339.8	316.6	288.7	257.3	225.6	197.7	175.6
132.5°	365.8	363.3	356.8	345.1	327.2	304.9	279.6	250.1	222.2	197.7	178.1
135°	344.8	342.6	336.2	324.5	308.7	288.4	265.5	241.0	218.0	197.7	181.7
137.5°	322.2	319.9	314.0	303.3	289.2	272.0	253.0	233.1	214.4	198.1	184.9
140°	306.6	304.8	299.4	290.1	276.9	262.0	245.5	228.7	212.7	198.4	186.3
142.5°	292.1	290.5	285.5	277.6	266.4	253.4	239.2	225.1	211.3	198.7	187.1
145°	272.0	270.5	266.6	260.5	252.0	242.4	231.3	220.3	209.1	198.4	188.0
147.5°	255.0	254.3	252.1	247.2	240.4	233.2	224.6	215.6	206.9	197.5	188.4
150°	245.5	245.2	243.8	239.4	234.1	227.7	221.0	213.1	205.2	196.6	188.4
152.5°	238.1	237.7	236.3	232.9	228.4	223.4	217.2	210.3	203.2	195.5	188.1
155°	228.0	227.7	226.6	224.1	220.6	216.6	211.7	205.9	199.9	193.5	187.3
157.5°	219.0	219.1	218.1	216.1	213.3	210.3	206.3	201.7	196.7	191.3	186.4
160°	213.1	213.4	212.7	211.0	208.4	205.9	202.4	198.8	194.2	189.9	185.6
162.5°	207.6	207.7	207.5	206.1	204.2	202.0	198.9	195.6	191.9	188.1	184.7
165°	199.9	199.9	199.9	199.1	197.7	195.9	193.8	191.3	188.4	185.6	183.5
167.5°	192.7	192.8	193.1	192.5	191.8	190.5	188.8	187.1	185.1	183.1	181.5
170°	188.4	188.8	188.8	188.4	187.7	187.0	185.9	184.9	183.1	181.7	180.6
172.5°	184.4	184.8	185.4	184.7	184.6	184.2	183.4	182.3	181.1	180.0	179.5
175°	179.6	179.9	180.6	180.3	180.3	180.3	179.6	179.6	178.4	178.1	178.1
177.5°	177.0	177.0	177.8	177.6	177.8	177.8	177.8	177.6	177.3	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1970.5	1966.1	1957.9	1950.4	1941.0	1932.8	1927.0	1920.2	1911.4	1900.7	1891.8
5°	2057.7	2040.4	2017.6	1997.9	1972.8	1953.1	1932.6	1912.9	1893.2	1868.0	1846.0
7.5°	2154.4	2118.7	2083.9	2040.1	2000.4	1965.0	1931.0	1896.5	1862.8	1827.0	1792.6
10°	2213.6	2170.3	2122.3	2067.2	2016.8	1968.8	1924.7	1881.4	1835.7	1795.6	1752.3
12.5°	2269.1	2213.1	2158.2	2088.6	2028.1	1969.4	1913.4	1859.4	1810.6	1758.5	1712.0
15°	2319.1	2264.0	2202.6	2117.6	2033.4	1962.5	1896.3	1826.3	1765.6	1707.5	1655.5
17.5°	2338.4	2280.7	2209.4	2127.7	2035.6	1946.4	1861.3	1784.4	1713.1	1645.3	1586.8
20°	2330.9	2275.0	2201.8	2123.8	2025.5	1932.6	1840.5	1755.4	1676.0	1604.3	1542.2
22.5°	2312.7	2254.8	2184.1	2101.8	2008.4	1910.0	1811.5	1720.8	1637.5	1563.4	1495.5
25°	2285.2	2206.6	2134.1	2053.8	1964.9	1867.2	1765.6	1665.7	1576.8	1501.2	1427.2
27.5°	2256.7	2158.5	2066.4	1986.6	1892.6	1805.5	1707.6	1605.1	1511.6	1434.6	1358.7
30°	2230.9	2120.7	2019.1	1928.6	1839.7	1757.1	1664.2	1564.2	1468.1	1388.7	1311.5
32.5°	2198.8	2081.6	1970.0	1865.6	1779.9	1697.9	1613.8	1518.2	1424.7	1342.6	1264.3
35°	2158.5	2008.9	1887.7	1776.8	1681.4	1601.9	1526.4	1449.3	1355.5	1270.5	1194.2
37.5°	2105.6	1935.9	1795.6	1674.7	1574.3	1494.4	1434.7	1364.2	1278.7	1197.3	1126.5
40°	2073.5	1883.0	1729.5	1609.8	1504.3	1420.1	1364.2	1304.4	1226.5	1150.1	1079.2
42.5°	2030.6	1834.5	1662.7	1538.0	1431.9	1350.8	1294.3	1242.0	1176.7	1104.8	1028.9
45°	1946.7	1740.5	1560.2	1426.4	1319.4	1239.8	1187.1	1140.6	1091.1	1024.9	958.8
47.5°	1837.4	1642.4	1453.8	1307.7	1202.9	1129.0	1077.8	1041.2	1005.7	949.5	885.2
50°	1750.0	1561.9	1377.6	1235.9	1124.1	1054.1	1006.0	976.9	944.6	893.4	839.9
52.5°	1646.7	1478.6	1298.3	1153.4	1047.9	982.3	936.1	907.1	880.4	838.7	787.7
55°	1483.9	1336.7	1171.3	1039.9	943.1	877.0	832.8	805.3	789.6	754.2	714.0
57.5°	1296.1	1190.5	1044.8	918.1	832.4	767.1	734.8	711.3	693.6	668.5	640.2
60°	1165.1	1091.1	960.4	839.9	761.2	699.0	669.9	650.3	633.7	612.5	590.4
62.5°	1032.2	978.4	864.6	761.2	688.8	636.7	609.5	591.7	572.6	558.3	536.8
65°	854.1	806.1	727.4	646.3	579.4	537.7	518.0	502.2	490.4	474.6	459.7
67.5°	664.4	644.9	590.6	534.6	486.7	449.5	432.5	421.5	407.3	397.9	387.6
70°	547.9	538.5	499.9	462.9	418.0	392.8	377.1	372.3	355.1	345.6	338.5
72.5°	444.6	440.2	418.0	392.3	360.7	338.6	324.2	318.8	307.8	300.2	295.7
75°	304.7	306.2	302.3	285.8	274.0	259.7	247.2	244.0	236.2	229.8	225.9
77.5°	192.7	200.8	201.1	200.3	195.5	186.9	181.7	179.4	171.6	169.3	168.3
80°	132.3	140.9	148.8	147.9	146.4	144.1	140.2	137.7	133.8	131.5	129.9
82.5°	88.2	96.2	102.8	107.0	106.7	104.4	101.7	100.6	99.8	98.1	97.8
85°	41.7	43.3	45.6	51.2	55.1	55.8	55.1	54.3	51.9	52.7	53.5
87.5°	15.5	15.2	15.9	15.7	14.9	17.9	19.7	20.2	19.0	17.9	16.8
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	81.4	48.8	29.3	18.9	12.7	8.3	5.3	4.3	5.3	8.3	12.7
95°	159.6	81.0	42.8	26.8	18.9	14.9	12.1	11.8	12.1	14.9	18.9
97.5°	127.3	69.8	44.5	33.0	26.0	22.0	20.0	19.6	20.0	22.0	26.0
100°	115.6	69.3	48.6	37.9	31.0	27.2	25.7	24.9	25.7	27.2	31.0
102.5°	110.8	71.8	53.4	43.0	36.8	32.5	31.4	31.0	31.4	32.5	36.8
105°	108.9	77.1	61.4	51.4	45.6	42.1	40.3	40.3	40.3	42.1	45.6
107.5°	112.1	84.9	69.8	60.8	54.8	51.9	50.2	49.5	50.2	51.9	54.8
110°	115.3	90.7	76.0	66.8	61.4	58.2	56.8	56.0	56.8	58.2	61.4



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	119.3	96.0	82.0	73.0	67.7	64.4	63.3	62.6	63.3	64.4	67.7
115°	125.2	104.6	91.4	82.4	77.1	73.9	72.8	72.1	72.8	73.9	77.1
117.5°	132.1	113.3	100.8	92.2	86.0	82.9	81.7	80.7	81.7	82.9	86.0
120°	136.7	119.6	107.0	98.2	92.1	88.9	87.5	86.3	87.5	88.9	92.1
122.5°	141.8	125.5	113.1	104.1	97.6	94.3	93.1	92.4	93.1	94.3	97.6
125°	148.9	133.5	121.7	112.4	105.6	102.4	100.7	100.0	100.7	102.4	105.6
127.5°	155.2	141.1	129.8	120.5	113.3	109.2	106.9	105.8	106.9	109.2	113.3
130°	159.6	145.9	134.9	125.6	118.2	113.5	110.7	109.6	110.7	113.5	118.2
132.5°	163.3	150.6	139.5	130.2	122.4	117.2	113.8	112.4	113.8	117.2	122.4
135°	168.4	156.6	145.6	136.0	128.5	122.8	118.5	117.0	118.5	122.8	128.5
137.5°	172.3	161.1	151.0	141.1	133.7	127.9	124.0	122.9	124.0	127.9	133.7
140°	174.9	164.2	153.8	144.2	137.4	131.7	127.4	126.3	127.4	131.7	137.4
142.5°	176.3	166.1	156.4	147.3	140.9	135.1	131.1	130.4	131.1	135.1	140.9
145°	178.4	169.6	160.3	152.1	145.6	140.6	137.0	136.3	137.0	140.6	145.6
147.5°	179.8	171.7	163.5	156.3	150.8	146.1	143.0	142.6	143.0	146.1	150.8
150°	180.6	173.1	165.2	159.2	154.2	149.6	147.0	146.3	147.0	149.6	154.2
152.5°	181.2	174.5	167.2	161.8	157.0	153.0	150.8	150.4	150.8	153.0	157.0
155°	181.7	175.9	169.9	164.9	161.3	157.7	155.6	155.6	155.6	157.7	161.3
157.5°	182.0	177.1	172.0	168.1	165.0	162.0	160.3	160.4	160.3	162.0	165.0
160°	182.0	177.7	173.1	169.9	167.0	164.5	163.1	163.5	163.1	164.5	167.0
162.5°	181.8	178.3	174.2	171.6	169.4	167.1	165.7	166.0	165.7	167.1	169.4
165°	181.3	178.4	175.6	173.5	172.0	170.3	169.2	169.9	169.2	170.3	172.0
167.5°	180.5	178.4	176.1	174.7	173.7	172.8	172.1	172.5	172.1	172.8	173.7
170°	179.9	178.4	176.6	175.6	174.9	174.2	173.8	174.2	173.8	174.2	174.9
172.5°	179.4	178.1	176.6	176.1	175.7	175.0	174.7	175.3	174.7	175.0	175.7
175°	178.4	177.7	176.6	176.6	176.6	176.3	175.9	176.6	175.9	176.3	176.6
177.5°	177.6	177.3	176.7	176.7	177.0	176.7	176.7	177.3	176.7	176.7	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1885.5	1876.7	1870.4	1857.7	1849.0	1845.2	1838.3	1836.3	1843.3	1838.3	1837.7
5°	1829.5	1806.6	1788.6	1770.4	1750.7	1738.2	1719.3	1716.1	1711.4	1704.2	1702.7
7.5°	1762.2	1732.5	1709.2	1679.3	1653.3	1632.3	1608.7	1597.5	1591.4	1582.3	1570.0
10°	1716.9	1681.4	1650.0	1620.0	1587.8	1561.9	1538.2	1520.0	1508.2	1497.2	1492.6
12.5°	1672.1	1636.1	1595.8	1559.6	1523.6	1494.4	1468.2	1456.5	1443.4	1430.5	1419.5
15°	1602.8	1554.7	1510.7	1468.9	1438.2	1406.7	1381.5	1364.2	1344.5	1339.1	1317.8
17.5°	1529.0	1482.0	1430.4	1386.4	1350.8	1316.2	1288.5	1268.8	1254.1	1233.8	1224.0
20°	1483.1	1427.2	1376.8	1336.7	1297.3	1256.4	1228.0	1211.5	1197.3	1180.8	1173.0
22.5°	1434.0	1379.4	1327.7	1280.6	1240.6	1200.3	1180.1	1163.1	1146.9	1131.7	1121.3
25°	1361.9	1306.8	1252.4	1203.7	1162.0	1132.8	1109.1	1089.4	1080.9	1065.9	1054.8
27.5°	1290.5	1231.9	1175.6	1126.9	1094.2	1065.4	1046.0	1030.5	1014.8	1001.8	992.2
30°	1244.6	1184.8	1123.4	1084.8	1050.2	1022.6	1001.3	986.3	974.5	962.7	955.6
32.5°	1198.6	1136.9	1082.4	1040.7	1007.9	984.1	962.3	948.0	935.5	922.4	914.1
35°	1124.9	1062.0	1017.8	976.9	944.6	922.6	907.7	887.2	877.0	867.5	858.8
37.5°	1056.4	997.8	950.2	914.2	886.3	864.3	845.0	833.9	821.3	812.8	805.7
40°	1006.0	952.5	909.2	871.4	851.0	826.6	808.5	794.3	784.9	773.9	766.0
42.5°	960.7	911.0	868.9	835.0	809.4	788.8	771.3	757.1	745.2	737.3	730.6
45°	896.7	847.1	806.1	774.6	751.0	731.3	713.2	706.1	690.3	681.0	677.8
47.5°	830.3	786.0	746.4	717.4	693.2	674.6	657.6	643.2	634.5	625.2	620.2
50°	785.7	743.2	706.1	677.8	654.2	633.7	617.9	608.5	596.7	588.0	581.8
52.5°	740.9	701.6	664.6	637.4	617.0	596.5	579.0	569.5	558.3	552.8	548.4
55°	677.0	635.3	603.8	577.0	555.7	536.8	520.4	510.9	503.8	498.3	496.8
57.5°	604.6	571.5	542.2	518.2	496.0	478.3	463.8	454.8	448.6	447.8	443.0
60°	557.3	527.5	500.7	474.6	455.8	439.3	426.7	416.5	410.1	409.3	407.8
62.5°	510.1	481.4	456.6	433.7	416.8	400.8	388.9	377.4	373.7	369.7	366.2
65°	440.0	414.0	393.6	375.5	357.4	344.0	332.2	325.1	316.5	311.7	303.1
67.5°	371.2	351.1	331.4	316.2	301.9	289.2	279.4	268.9	263.1	259.3	253.0
70°	325.9	310.1	290.4	274.0	263.0	252.7	244.8	233.0	229.0	225.9	222.8
72.5°	283.1	269.2	252.7	239.3	228.3	218.6	209.5	204.0	200.2	196.9	195.1
75°	222.8	209.4	195.2	185.8	177.9	170.1	165.3	161.4	159.8	159.1	155.8
77.5°	163.6	156.5	145.1	137.6	132.4	129.3	125.0	123.0	122.8	119.4	118.3
80°	125.1	121.2	111.8	108.7	104.7	101.6	99.2	95.2	91.3	89.8	87.4
82.5°	93.0	89.1	85.3	80.3	77.0	75.1	72.7	71.3	71.8	69.6	68.5
85°	49.6	45.6	44.1	43.3	41.7	43.3	42.5	41.7	40.9	40.2	40.9
87.5°	16.4	16.5	15.9	17.3	15.5	16.3	16.4	15.8	15.9	16.0	15.5
90°	2.8	3.5	3.9	4.6	4.9	5.8	6.1	6.5	6.8	7.2	7.9
92.5°	18.9	29.3	48.8	81.4	116.9	115.0	93.1	63.2	45.8	34.5	29.3
95°	26.8	42.8	81.0	159.6	258.0	316.2	309.4	256.6	202.4	158.4	128.5
97.5°	33.0	44.5	69.8	127.3	230.5	337.7	391.5	382.1	344.2	301.3	259.6
100°	37.9	48.6	69.3	115.6	205.6	322.2	411.5	439.0	421.5	384.8	347.6
102.5°	43.0	53.4	71.8	110.8	186.7	295.2	399.5	458.1	468.9	451.3	426.2
105°	51.4	61.4	77.1	108.9	168.4	258.7	361.2	446.9	495.7	511.4	507.6
107.5°	60.8	69.8	84.9	112.1	160.8	233.7	322.0	406.6	471.8	512.1	530.8
110°	66.8	76.0	90.7	115.3	158.4	222.0	299.8	376.9	444.7	495.0	525.3



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	73.0	82.0	96.0	119.3	158.4	215.1	283.3	353.5	417.9	468.8	504.5
115°	82.4	91.4	104.6	125.2	159.6	207.7	265.2	324.1	379.4	428.3	467.2
117.5°	92.2	100.8	113.3	132.1	161.9	204.1	254.4	305.1	352.7	394.9	430.6
120°	98.2	107.0	119.6	136.7	164.2	202.4	248.4	294.8	337.6	376.9	408.3
122.5°	104.1	113.1	125.5	141.8	166.1	201.0	243.3	287.1	326.8	361.7	391.1
125°	112.4	121.7	133.5	148.9	169.6	199.1	236.3	275.9	312.3	343.4	369.0
127.5°	120.5	129.8	141.1	155.2	173.3	198.3	229.8	264.5	298.4	327.4	351.4
130°	125.6	134.9	145.9	159.6	175.6	197.7	225.6	257.3	288.7	316.6	339.8
132.5°	130.2	139.5	150.6	163.3	178.1	197.7	222.2	250.1	279.6	304.9	327.2
135°	136.0	145.6	156.6	168.4	181.7	197.7	218.0	241.0	265.5	288.4	308.7
137.5°	141.1	151.0	161.1	172.3	184.9	198.1	214.4	233.1	253.0	272.0	289.2
140°	144.2	153.8	164.2	174.9	186.3	198.4	212.7	228.7	245.5	262.0	276.9
142.5°	147.3	156.4	166.1	176.3	187.1	198.7	211.3	225.1	239.2	253.4	266.4
145°	152.1	160.3	169.6	178.4	188.0	198.4	209.1	220.3	231.3	242.4	252.0
147.5°	156.3	163.5	171.7	179.8	188.4	197.5	206.9	215.6	224.6	233.2	240.4
150°	159.2	165.2	173.1	180.6	188.4	196.6	205.2	213.1	221.0	227.7	234.1
152.5°	161.8	167.2	174.5	181.2	188.1	195.5	203.2	210.3	217.2	223.4	228.4
155°	164.9	169.9	175.9	181.7	187.3	193.5	199.9	205.9	211.7	216.6	220.6
157.5°	168.1	172.0	177.1	182.0	186.4	191.3	196.7	201.7	206.3	210.3	213.3
160°	169.9	173.1	177.7	182.0	185.6	189.9	194.2	198.8	202.4	205.9	208.4
162.5°	171.6	174.2	178.3	181.8	184.7	188.1	191.9	195.6	198.9	202.0	204.2
165°	173.5	175.6	178.4	181.3	183.5	185.6	188.4	191.3	193.8	195.9	197.7
167.5°	174.7	176.1	178.4	180.5	181.5	183.1	185.1	187.1	188.8	190.5	191.8
170°	175.6	176.6	178.4	179.9	180.6	181.7	183.1	184.9	185.9	187.0	187.7
172.5°	176.1	176.6	178.1	179.4	179.5	180.0	181.1	182.3	183.4	184.2	184.6
175°	176.6	176.6	177.7	178.4	178.1	178.1	178.4	179.6	179.6	180.3	180.3
177.5°	176.7	176.7	177.3	177.6	177.0	177.0	177.3	177.6	177.8	177.8	177.8
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1837.0	1830.1	1828.2	1830.7	1828.2	1830.1	1837.0	1837.7	1838.3	1843.3	1836.3
5°	1694.9	1687.0	1690.9	1689.3	1690.9	1687.0	1694.9	1702.7	1704.2	1711.4	1716.1
7.5°	1569.8	1560.0	1549.6	1553.0	1549.6	1560.0	1569.8	1570.0	1582.3	1591.4	1597.5
10°	1482.3	1474.4	1469.7	1473.6	1469.7	1474.4	1482.3	1492.6	1497.2	1508.2	1520.0
12.5°	1408.7	1403.9	1399.8	1398.1	1399.8	1403.9	1408.7	1419.5	1430.5	1443.4	1456.5
15°	1308.3	1298.9	1294.9	1284.8	1294.9	1298.9	1308.3	1317.8	1339.1	1344.5	1364.2
17.5°	1215.9	1212.7	1202.5	1198.1	1202.5	1212.7	1215.9	1224.0	1233.8	1254.1	1268.8
20°	1161.1	1158.0	1147.7	1154.1	1147.7	1158.0	1161.1	1173.0	1180.8	1197.3	1211.5
22.5°	1115.8	1108.8	1105.5	1103.7	1105.5	1108.8	1115.8	1121.3	1131.7	1146.9	1163.1
25°	1051.7	1041.5	1037.5	1032.8	1037.5	1041.5	1051.7	1054.8	1065.9	1080.9	1089.4
27.5°	987.7	982.3	977.0	975.8	977.0	982.3	987.7	992.2	1001.8	1014.8	1030.5
30°	946.2	940.7	936.8	936.8	936.8	940.7	946.2	955.6	962.7	974.5	986.3
32.5°	909.1	904.8	900.9	900.3	900.9	904.8	909.1	914.1	922.4	935.5	948.0
35°	855.0	848.6	847.1	842.3	847.1	848.6	855.0	858.8	867.5	877.0	887.2
37.5°	798.7	793.5	793.3	792.8	793.3	793.5	798.7	805.7	812.8	821.3	833.9
40°	762.8	758.8	758.1	752.6	758.1	758.8	762.8	766.0	773.9	784.9	794.3
42.5°	724.4	722.4	719.6	717.3	719.6	722.4	724.4	730.6	737.3	745.2	757.1
45°	672.3	666.7	666.7	662.8	666.7	666.7	672.3	677.8	681.0	690.3	706.1
47.5°	618.4	614.2	614.6	610.6	614.6	614.2	618.4	620.2	625.2	634.5	643.2
50°	582.5	580.2	579.4	577.8	579.4	580.2	582.5	581.8	588.0	596.7	608.5
52.5°	546.6	545.5	548.6	545.0	548.6	545.5	546.6	548.4	552.8	558.3	569.5
55°	498.3	495.9	500.7	495.9	500.7	495.9	498.3	496.8	498.3	503.8	510.9
57.5°	442.7	440.5	444.7	442.4	444.7	440.5	442.7	443.0	447.8	448.6	454.8
60°	406.2	401.5	403.8	404.7	403.8	401.5	406.2	407.8	409.3	410.1	416.5
62.5°	362.7	359.9	361.6	358.0	361.6	359.9	362.7	366.2	369.7	373.7	377.4
65°	301.5	299.1	296.0	294.4	296.0	299.1	301.5	303.1	311.7	316.5	325.1
67.5°	253.3	247.6	247.5	248.7	247.5	247.6	253.3	253.0	259.3	263.1	268.9
70°	218.0	218.0	217.2	217.2	217.2	218.0	218.0	222.8	225.9	229.0	233.0
72.5°	193.5	192.9	191.5	190.9	191.5	192.9	193.5	195.1	196.9	200.2	204.0
75°	155.8	156.6	155.1	154.3	155.1	156.6	155.8	155.8	159.1	159.8	161.4
77.5°	115.1	111.8	113.5	111.8	113.5	111.8	115.1	118.3	119.4	122.8	123.0
80°	87.4	86.5	89.0	86.5	89.0	86.5	87.4	87.4	89.8	91.3	95.2
82.5°	69.1	68.4	69.5	67.7	69.5	68.4	69.1	68.5	69.6	71.8	71.3
85°	41.7	40.9	40.2	40.9	40.2	40.9	41.7	40.9	40.2	40.9	41.7
87.5°	16.1	15.5	15.5	15.5	15.5	15.5	16.1	15.5	16.0	15.9	15.8
90°	7.9	7.9	8.2	8.2	8.2	7.9	7.9	7.9	7.2	6.8	6.5
92.5°	24.7	23.8	23.3	22.7	23.3	23.8	24.7	29.3	34.5	45.8	63.2
95°	103.1	92.4	89.6	83.9	89.6	92.4	103.1	128.5	158.4	202.4	256.6
97.5°	237.6	217.6	207.3	202.7	207.3	217.6	237.6	259.6	301.3	344.2	382.1
100°	323.0	297.3	284.1	278.4	284.1	297.3	323.0	347.6	384.8	421.5	439.0
102.5°	399.8	381.5	367.2	362.9	367.2	381.5	399.8	426.2	451.3	468.9	458.1
105°	496.0	484.3	477.2	472.9	477.2	484.3	496.0	507.6	511.4	495.7	446.9
107.5°	536.5	536.5	534.1	531.3	534.1	536.5	536.5	530.8	512.1	471.8	406.6
110°	541.4	548.2	550.7	550.7	550.7	548.2	541.4	525.3	495.0	444.7	376.9



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	528.0	539.7	545.8	548.5	545.8	539.7	528.0	504.5	468.8	417.9	353.5
115°	495.0	512.1	522.1	526.7	522.1	512.1	495.0	467.2	428.3	379.4	324.1
117.5°	458.4	476.2	486.0	488.9	486.0	476.2	458.4	430.6	394.9	352.7	305.1
120°	434.7	451.8	461.5	464.3	461.5	451.8	434.7	408.3	376.9	337.6	294.8
122.5°	414.8	430.4	440.1	442.6	440.1	430.4	414.8	391.1	361.7	326.8	287.1
125°	389.0	403.6	411.5	415.1	411.5	403.6	389.0	369.0	343.4	312.3	275.9
127.5°	369.6	382.5	389.9	391.5	389.9	382.5	369.6	351.4	327.4	298.4	264.5
130°	357.6	369.4	376.6	378.7	376.6	369.4	357.6	339.8	316.6	288.7	257.3
132.5°	345.1	356.8	363.3	365.8	363.3	356.8	345.1	327.2	304.9	279.6	250.1
135°	324.5	336.2	342.6	344.8	342.6	336.2	324.5	308.7	288.4	265.5	241.0
137.5°	303.3	314.0	319.9	322.2	319.9	314.0	303.3	289.2	272.0	253.0	233.1
140°	290.1	299.4	304.8	306.6	304.8	299.4	290.1	276.9	262.0	245.5	228.7
142.5°	277.6	285.5	290.5	292.1	290.5	285.5	277.6	266.4	253.4	239.2	225.1
145°	260.5	266.6	270.5	272.0	270.5	266.6	260.5	252.0	242.4	231.3	220.3
147.5°	247.2	252.1	254.3	255.0	254.3	252.1	247.2	240.4	233.2	224.6	215.6
150°	239.4	243.8	245.2	245.5	245.2	243.8	239.4	234.1	227.7	221.0	213.1
152.5°	232.9	236.3	237.7	238.1	237.7	236.3	232.9	228.4	223.4	217.2	210.3
155°	224.1	226.6	227.7	228.0	227.7	226.6	224.1	220.6	216.6	211.7	205.9
157.5°	216.1	218.1	219.1	219.0	219.1	218.1	216.1	213.3	210.3	206.3	201.7
160°	211.0	212.7	213.4	213.1	213.4	212.7	211.0	208.4	205.9	202.4	198.8
162.5°	206.1	207.5	207.7	207.6	207.7	207.5	206.1	204.2	202.0	198.9	195.6
165°	199.1	199.9	199.9	199.9	199.9	199.9	199.1	197.7	195.9	193.8	191.3
167.5°	192.5	193.1	192.8	192.7	192.8	193.1	192.5	191.8	190.5	188.8	187.1
170°	188.4	188.8	188.8	188.4	188.8	188.8	188.4	187.7	187.0	185.9	184.9
172.5°	184.7	185.4	184.8	184.4	184.8	185.4	184.7	184.6	184.2	183.4	182.3
175°	180.3	180.6	179.9	179.6	179.9	180.6	180.3	180.3	180.3	179.6	179.6
177.5°	177.6	177.8	177.0	177.0	177.0	177.8	177.6	177.8	177.8	177.8	177.6
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1838.3	1845.2	1849.0	1857.7	1870.4	1876.7	1885.5	1891.8	1900.7	1911.4	1920.2
5°	1719.3	1738.2	1750.7	1770.4	1788.6	1806.6	1829.5	1846.0	1868.0	1893.2	1912.9
7.5°	1608.7	1632.3	1653.3	1679.3	1709.2	1732.5	1762.2	1792.6	1827.0	1862.8	1896.5
10°	1538.2	1561.9	1587.8	1620.0	1650.0	1681.4	1716.9	1752.3	1795.6	1835.7	1881.4
12.5°	1468.2	1494.4	1523.6	1559.6	1595.8	1636.1	1672.1	1712.0	1758.5	1810.6	1859.4
15°	1381.5	1406.7	1438.2	1468.9	1510.7	1554.7	1602.8	1655.5	1707.5	1765.6	1826.3
17.5°	1288.5	1316.2	1350.8	1386.4	1430.4	1482.0	1529.0	1586.8	1645.3	1713.1	1784.4
20°	1228.0	1256.4	1297.3	1336.7	1376.8	1427.2	1483.1	1542.2	1604.3	1676.0	1755.4
22.5°	1180.1	1200.3	1240.6	1280.6	1327.7	1379.4	1434.0	1495.5	1563.4	1637.5	1720.8
25°	1109.1	1132.8	1162.0	1203.7	1252.4	1306.8	1361.9	1427.2	1501.2	1576.8	1665.7
27.5°	1046.0	1065.4	1094.2	1126.9	1175.6	1231.9	1290.5	1358.7	1434.6	1511.6	1605.1
30°	1001.3	1022.6	1050.2	1084.8	1123.4	1184.8	1244.6	1311.5	1388.7	1468.1	1564.2
32.5°	962.3	984.1	1007.9	1040.7	1082.4	1136.9	1198.6	1264.3	1342.6	1424.7	1518.2
35°	907.7	922.6	944.6	976.9	1017.8	1062.0	1124.9	1194.2	1270.5	1355.5	1449.3
37.5°	845.0	864.3	886.3	914.2	950.2	997.8	1056.4	1126.5	1197.3	1278.7	1364.2
40°	808.5	826.6	851.0	871.4	909.2	952.5	1006.0	1079.2	1150.1	1226.5	1304.4
42.5°	771.3	788.8	809.4	835.0	868.9	911.0	960.7	1028.9	1104.8	1176.7	1242.0
45°	713.2	731.3	751.0	774.6	806.1	847.1	896.7	958.8	1024.9	1091.1	1140.6
47.5°	657.6	674.6	693.2	717.4	746.4	786.0	830.3	885.2	949.5	1005.7	1041.2
50°	617.9	633.7	654.2	677.8	706.1	743.2	785.7	839.9	893.4	944.6	976.9
52.5°	579.0	596.5	617.0	637.4	664.6	701.6	740.9	787.7	838.7	880.4	907.1
55°	520.4	536.8	555.7	577.0	603.8	635.3	677.0	714.0	754.2	789.6	805.3
57.5°	463.8	478.3	496.0	518.2	542.2	571.5	604.6	640.2	668.5	693.6	711.3
60°	426.7	439.3	455.8	474.6	500.7	527.5	557.3	590.4	612.5	633.7	650.3
62.5°	388.9	400.8	416.8	433.7	456.6	481.4	510.1	536.8	558.3	572.6	591.7
65°	332.2	344.0	357.4	375.5	393.6	414.0	440.0	459.7	474.6	490.4	502.2
67.5°	279.4	289.2	301.9	316.2	331.4	351.1	371.2	387.6	397.9	407.3	421.5
70°	244.8	252.7	263.0	274.0	290.4	310.1	325.9	338.5	345.6	355.1	372.3
72.5°	209.5	218.6	228.3	239.3	252.7	269.2	283.1	295.7	300.2	307.8	318.8
75°	165.3	170.1	177.9	185.8	195.2	209.4	222.8	225.9	229.8	236.2	244.0
77.5°	125.0	129.3	132.4	137.6	145.1	156.5	163.6	168.3	169.3	171.6	179.4
80°	99.2	101.6	104.7	108.7	111.8	121.2	125.1	129.9	131.5	133.8	137.7
82.5°	72.7	75.1	77.0	80.3	85.3	89.1	93.0	97.8	98.1	99.8	100.6
85°	42.5	43.3	41.7	43.3	44.1	45.6	49.6	53.5	52.7	51.9	54.3
87.5°	16.4	16.3	15.5	17.3	15.9	16.5	16.4	16.8	17.9	19.0	20.2
90°	6.1	5.8	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	93.1	115.0	116.9	81.4	48.8	29.3	18.9	12.7	8.3	5.3	4.3
95°	309.4	316.2	258.0	159.6	81.0	42.8	26.8	18.9	14.9	12.1	11.8
97.5°	391.5	337.7	230.5	127.3	69.8	44.5	33.0	26.0	22.0	20.0	19.6
100°	411.5	322.2	205.6	115.6	69.3	48.6	37.9	31.0	27.2	25.7	24.9
102.5°	399.5	295.2	186.7	110.8	71.8	53.4	43.0	36.8	32.5	31.4	31.0
105°	361.2	258.7	168.4	108.9	77.1	61.4	51.4	45.6	42.1	40.3	40.3
107.5°	322.0	233.7	160.8	112.1	84.9	69.8	60.8	54.8	51.9	50.2	49.5
110°	299.8	222.0	158.4	115.3	90.7	76.0	66.8	61.4	58.2	56.8	56.0



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.3	215.1	158.4	119.3	96.0	82.0	73.0	67.7	64.4	63.3	62.6
115°	265.2	207.7	159.6	125.2	104.6	91.4	82.4	77.1	73.9	72.8	72.1
117.5°	254.4	204.1	161.9	132.1	113.3	100.8	92.2	86.0	82.9	81.7	80.7
120°	248.4	202.4	164.2	136.7	119.6	107.0	98.2	92.1	88.9	87.5	86.3
122.5°	243.3	201.0	166.1	141.8	125.5	113.1	104.1	97.6	94.3	93.1	92.4
125°	236.3	199.1	169.6	148.9	133.5	121.7	112.4	105.6	102.4	100.7	100.0
127.5°	229.8	198.3	173.3	155.2	141.1	129.8	120.5	113.3	109.2	106.9	105.8
130°	225.6	197.7	175.6	159.6	145.9	134.9	125.6	118.2	113.5	110.7	109.6
132.5°	222.2	197.7	178.1	163.3	150.6	139.5	130.2	122.4	117.2	113.8	112.4
135°	218.0	197.7	181.7	168.4	156.6	145.6	136.0	128.5	122.8	118.5	117.0
137.5°	214.4	198.1	184.9	172.3	161.1	151.0	141.1	133.7	127.9	124.0	122.9
140°	212.7	198.4	186.3	174.9	164.2	153.8	144.2	137.4	131.7	127.4	126.3
142.5°	211.3	198.7	187.1	176.3	166.1	156.4	147.3	140.9	135.1	131.1	130.4
145°	209.1	198.4	188.0	178.4	169.6	160.3	152.1	145.6	140.6	137.0	136.3
147.5°	206.9	197.5	188.4	179.8	171.7	163.5	156.3	150.8	146.1	143.0	142.6
150°	205.2	196.6	188.4	180.6	173.1	165.2	159.2	154.2	149.6	147.0	146.3
152.5°	203.2	195.5	188.1	181.2	174.5	167.2	161.8	157.0	153.0	150.8	150.4
155°	199.9	193.5	187.3	181.7	175.9	169.9	164.9	161.3	157.7	155.6	155.6
157.5°	196.7	191.3	186.4	182.0	177.1	172.0	168.1	165.0	162.0	160.3	160.4
160°	194.2	189.9	185.6	182.0	177.7	173.1	169.9	167.0	164.5	163.1	163.5
162.5°	191.9	188.1	184.7	181.8	178.3	174.2	171.6	169.4	167.1	165.7	166.0
165°	188.4	185.6	183.5	181.3	178.4	175.6	173.5	172.0	170.3	169.2	169.9
167.5°	185.1	183.1	181.5	180.5	178.4	176.1	174.7	173.7	172.8	172.1	172.5
170°	183.1	181.7	180.6	179.9	178.4	176.6	175.6	174.9	174.2	173.8	174.2
172.5°	181.1	180.0	179.5	179.4	178.1	176.6	176.1	175.7	175.0	174.7	175.3
175°	178.4	178.1	178.1	178.4	177.7	176.6	176.6	176.6	176.3	175.9	176.6
177.5°	177.3	177.0	177.0	177.6	177.3	176.7	176.7	177.0	176.7	176.7	177.3
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1927.0	1932.8	1941.0	1950.4	1957.9	1966.1	1970.5	1970.5	1974.3	1982.5	1993.2
5°	1932.6	1953.1	1972.8	1997.9	2017.6	2040.4	2057.7	2074.3	2089.2	2108.1	2127.8
7.5°	1931.0	1965.0	2000.4	2040.1	2083.9	2118.7	2154.4	2182.4	2210.2	2246.3	2274.8
10°	1924.7	1968.8	2016.8	2067.2	2122.3	2170.3	2213.6	2253.0	2290.8	2330.2	2365.5
12.5°	1913.4	1969.4	2028.1	2088.6	2158.2	2213.1	2269.1	2310.9	2355.0	2398.1	2441.8
15°	1896.3	1962.5	2033.4	2117.6	2202.6	2264.0	2319.1	2373.4	2414.4	2463.2	2504.9
17.5°	1861.3	1946.4	2035.6	2127.7	2209.4	2280.7	2338.4	2390.1	2433.7	2487.4	2544.1
20°	1840.5	1932.6	2025.5	2123.8	2201.8	2275.0	2330.9	2384.4	2438.7	2508.8	2578.1
22.5°	1811.5	1910.0	2008.4	2101.8	2184.1	2254.8	2312.7	2378.1	2449.4	2529.0	2612.7
25°	1765.6	1867.2	1964.9	2053.8	2134.1	2206.6	2285.2	2373.4	2460.0	2564.8	2685.1
27.5°	1707.6	1805.5	1892.6	1986.6	2066.4	2158.5	2256.7	2352.3	2477.2	2621.2	2771.6
30°	1664.2	1757.1	1839.7	1928.6	2019.1	2120.7	2230.9	2343.5	2492.2	2661.5	2840.2
32.5°	1613.8	1697.9	1779.9	1865.6	1970.0	2081.6	2198.8	2336.5	2514.4	2706.8	2891.8
35°	1526.4	1601.9	1681.4	1776.8	1887.7	2008.9	2158.5	2326.2	2541.1	2748.1	2914.3
37.5°	1434.7	1494.4	1574.3	1674.7	1795.6	1935.9	2105.6	2309.4	2530.1	2715.8	2786.5
40°	1364.2	1420.1	1504.3	1609.8	1729.5	1883.0	2073.5	2282.9	2504.9	2633.9	2628.5
42.5°	1294.3	1350.8	1431.9	1538.0	1662.7	1834.5	2030.6	2248.3	2435.6	2484.8	2382.3
45°	1187.1	1239.8	1319.4	1426.4	1560.2	1740.5	1946.7	2155.4	2275.0	2195.5	1992.4
47.5°	1077.8	1129.0	1202.9	1307.7	1453.8	1642.4	1837.4	2008.6	2025.5	1854.6	1611.0
50°	1006.0	1054.1	1124.1	1235.9	1377.6	1561.9	1750.0	1884.6	1842.8	1634.3	1383.1
52.5°	936.1	982.3	1047.9	1153.4	1298.3	1478.6	1646.7	1752.3	1655.8	1434.0	1208.0
55°	832.8	877.0	943.1	1039.9	1171.3	1336.7	1483.9	1522.5	1380.8	1157.2	974.5
57.5°	734.8	767.1	832.4	918.1	1044.8	1190.5	1296.1	1289.1	1132.8	931.4	800.4
60°	669.9	699.0	761.2	839.9	960.4	1091.1	1165.1	1133.6	975.3	809.2	683.3
62.5°	609.5	636.7	688.8	761.2	864.6	978.4	1032.2	988.8	839.3	693.4	593.2
65°	518.0	537.7	579.4	646.3	727.4	806.1	854.1	790.3	658.1	547.9	472.3
67.5°	432.5	449.5	486.7	534.6	590.6	644.9	664.4	604.6	501.8	427.5	374.3
70°	377.1	392.8	418.0	462.9	499.9	538.5	547.9	494.3	408.6	351.8	318.8
72.5°	324.2	338.6	360.7	392.3	418.0	440.2	444.6	394.9	329.2	290.1	264.7
75°	247.2	259.7	274.0	285.8	302.3	306.2	304.7	266.1	230.7	204.7	190.5
77.5°	181.7	186.9	195.5	200.3	201.1	200.8	192.7	168.3	150.1	139.4	133.5
80°	140.2	144.1	146.4	147.9	148.8	140.9	132.3	117.2	111.0	104.7	97.7
82.5°	101.7	104.4	106.7	107.0	102.8	96.2	88.2	80.8	76.3	73.2	70.5
85°	55.1	55.8	55.1	51.2	45.6	43.3	41.7	40.2	39.4	38.6	38.6
87.5°	19.7	17.9	14.9	15.7	15.9	15.2	15.5	14.8	14.3	14.4	14.5
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.8	6.1	6.5
92.5°	5.3	8.3	12.7	18.9	29.3	48.8	81.4	116.9	115.0	93.1	63.2
95°	12.1	14.9	18.9	26.8	42.8	81.0	159.6	258.0	316.2	309.4	256.6
97.5°	20.0	22.0	26.0	33.0	44.5	69.8	127.3	230.5	337.7	391.5	382.1
100°	25.7	27.2	31.0	37.9	48.6	69.3	115.6	205.6	322.2	411.5	439.0
102.5°	31.4	32.5	36.8	43.0	53.4	71.8	110.8	186.7	295.2	399.5	458.1
105°	40.3	42.1	45.6	51.4	61.4	77.1	108.9	168.4	258.7	361.2	446.9
107.5°	50.2	51.9	54.8	60.8	69.8	84.9	112.1	160.8	233.7	322.0	406.6
110°	56.8	58.2	61.4	66.8	76.0	90.7	115.3	158.4	222.0	299.8	376.9



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	63.3	64.4	67.7	73.0	82.0	96.0	119.3	158.4	215.1	283.3	353.5
115°	72.8	73.9	77.1	82.4	91.4	104.6	125.2	159.6	207.7	265.2	324.1
117.5°	81.7	82.9	86.0	92.2	100.8	113.3	132.1	161.9	204.1	254.4	305.1
120°	87.5	88.9	92.1	98.2	107.0	119.6	136.7	164.2	202.4	248.4	294.8
122.5°	93.1	94.3	97.6	104.1	113.1	125.5	141.8	166.1	201.0	243.3	287.1
125°	100.7	102.4	105.6	112.4	121.7	133.5	148.9	169.6	199.1	236.3	275.9
127.5°	106.9	109.2	113.3	120.5	129.8	141.1	155.2	173.3	198.3	229.8	264.5
130°	110.7	113.5	118.2	125.6	134.9	145.9	159.6	175.6	197.7	225.6	257.3
132.5°	113.8	117.2	122.4	130.2	139.5	150.6	163.3	178.1	197.7	222.2	250.1
135°	118.5	122.8	128.5	136.0	145.6	156.6	168.4	181.7	197.7	218.0	241.0
137.5°	124.0	127.9	133.7	141.1	151.0	161.1	172.3	184.9	198.1	214.4	233.1
140°	127.4	131.7	137.4	144.2	153.8	164.2	174.9	186.3	198.4	212.7	228.7
142.5°	131.1	135.1	140.9	147.3	156.4	166.1	176.3	187.1	198.7	211.3	225.1
145°	137.0	140.6	145.6	152.1	160.3	169.6	178.4	188.0	198.4	209.1	220.3
147.5°	143.0	146.1	150.8	156.3	163.5	171.7	179.8	188.4	197.5	206.9	215.6
150°	147.0	149.6	154.2	159.2	165.2	173.1	180.6	188.4	196.6	205.2	213.1
152.5°	150.8	153.0	157.0	161.8	167.2	174.5	181.2	188.1	195.5	203.2	210.3
155°	155.6	157.7	161.3	164.9	169.9	175.9	181.7	187.3	193.5	199.9	205.9
157.5°	160.3	162.0	165.0	168.1	172.0	177.1	182.0	186.4	191.3	196.7	201.7
160°	163.1	164.5	167.0	169.9	173.1	177.7	182.0	185.6	189.9	194.2	198.8
162.5°	165.7	167.1	169.4	171.6	174.2	178.3	181.8	184.7	188.1	191.9	195.6
165°	169.2	170.3	172.0	173.5	175.6	178.4	181.3	183.5	185.6	188.4	191.3
167.5°	172.1	172.8	173.7	174.7	176.1	178.4	180.5	181.5	183.1	185.1	187.1
170°	173.8	174.2	174.9	175.6	176.6	178.4	179.9	180.6	181.7	183.1	184.9
172.5°	174.7	175.0	175.7	176.1	176.6	178.1	179.4	179.5	180.0	181.1	182.3
175°	175.9	176.3	176.6	176.6	176.6	177.7	178.4	178.1	178.1	178.4	179.6
177.5°	176.7	176.7	177.0	176.7	176.7	177.3	177.6	177.0	177.0	177.3	177.6
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2001.4	2001.4	2012.1	2011.4	2018.4	2015.9	2017.1
5°	2151.4	2164.8	2176.7	2184.4	2196.3	2199.5	2197.9
7.5°	2306.9	2336.7	2351.2	2371.1	2374.7	2385.1	2384.0
10°	2403.4	2432.5	2454.5	2471.8	2480.4	2491.5	2492.2
12.5°	2478.9	2503.7	2523.1	2539.2	2549.7	2553.2	2555.3
15°	2537.9	2565.5	2588.3	2611.1	2624.5	2634.7	2640.3
17.5°	2597.5	2640.0	2680.3	2711.3	2729.9	2745.6	2745.4
20°	2643.4	2692.2	2742.6	2778.0	2814.3	2829.9	2832.4
22.5°	2692.5	2767.1	2832.1	2887.0	2934.6	2950.9	2957.1
25°	2794.6	2892.2	2992.1	3069.3	3124.4	3156.6	3161.4
27.5°	2917.8	3049.9	3155.1	3226.3	3272.1	3296.0	3301.2
30°	3004.8	3126.7	3221.3	3274.8	3296.0	3299.1	3287.3
32.5°	3043.8	3134.9	3172.7	3169.6	3127.9	3100.2	3089.6
35°	2996.1	2977.2	2885.1	2774.9	2690.7	2637.2	2622.9
37.5°	2726.5	2563.6	2394.2	2227.7	2139.0	2094.0	2016.5
40°	2460.8	2228.6	2052.2	1912.1	1812.1	1731.8	1712.9
42.5°	2161.0	1921.3	1744.9	1625.0	1545.1	1490.1	1466.1
45°	1736.6	1530.3	1384.7	1292.6	1231.2	1191.0	1173.0
47.5°	1389.0	1229.3	1123.2	1055.0	1008.2	973.3	963.5
50°	1198.1	1070.6	980.9	923.4	888.0	861.2	850.2
52.5°	1040.7	937.8	868.8	821.3	787.8	771.1	762.0
55°	858.8	769.9	720.3	682.5	663.6	650.3	643.9
57.5°	702.4	638.1	601.9	575.7	558.3	549.8	546.6
60°	614.8	564.4	531.4	510.9	499.1	488.1	484.9
62.5°	537.3	497.7	472.2	454.2	442.4	437.7	435.8
65°	432.9	407.0	388.1	377.1	367.6	366.1	365.3
67.5°	344.2	328.9	319.0	307.5	304.2	298.6	297.6
70°	294.4	284.2	272.4	268.4	264.5	259.0	259.7
72.5°	249.7	239.4	231.5	226.2	224.8	222.5	224.5
75°	182.6	179.5	176.3	172.4	170.9	170.9	170.1
77.5°	130.4	127.6	124.2	121.9	121.4	118.1	119.4
80°	94.4	90.5	89.0	89.8	87.4	86.5	86.5
82.5°	69.9	68.5	67.0	67.1	66.6	65.8	66.4
85°	38.6	37.8	37.8	37.0	37.0	36.3	36.3
87.5°	15.2	16.0	14.8	14.1	14.1	14.8	15.5
90°	6.8	7.2	7.9	7.9	7.9	8.2	8.2
92.5°	45.8	34.5	29.3	24.7	23.8	23.3	22.7
95°	202.4	158.4	128.5	103.1	92.4	89.6	83.9
97.5°	344.2	301.3	259.6	237.6	217.6	207.3	202.7
100°	421.5	384.8	347.6	323.0	297.3	284.1	278.4
102.5°	468.9	451.3	426.2	399.8	381.5	367.2	362.9
105°	495.7	511.4	507.6	496.0	484.3	477.2	472.9
107.5°	471.8	512.1	530.8	536.5	536.5	534.1	531.3
110°	444.7	495.0	525.3	541.4	548.2	550.7	550.7



TEST NUMBER: P333612-840

CATALOG NUMBER: S125RDIP-S1270D365U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	417.9	468.8	504.5	528.0	539.7	545.8	548.5
115°	379.4	428.3	467.2	495.0	512.1	522.1	526.7
117.5°	352.7	394.9	430.6	458.4	476.2	486.0	488.9
120°	337.6	376.9	408.3	434.7	451.8	461.5	464.3
122.5°	326.8	361.7	391.1	414.8	430.4	440.1	442.6
125°	312.3	343.4	369.0	389.0	403.6	411.5	415.1
127.5°	298.4	327.4	351.4	369.6	382.5	389.9	391.5
130°	288.7	316.6	339.8	357.6	369.4	376.6	378.7
132.5°	279.6	304.9	327.2	345.1	356.8	363.3	365.8
135°	265.5	288.4	308.7	324.5	336.2	342.6	344.8
137.5°	253.0	272.0	289.2	303.3	314.0	319.9	322.2
140°	245.5	262.0	276.9	290.1	299.4	304.8	306.6
142.5°	239.2	253.4	266.4	277.6	285.5	290.5	292.1
145°	231.3	242.4	252.0	260.5	266.6	270.5	272.0
147.5°	224.6	233.2	240.4	247.2	252.1	254.3	255.0
150°	221.0	227.7	234.1	239.4	243.8	245.2	245.5
152.5°	217.2	223.4	228.4	232.9	236.3	237.7	238.1
155°	211.7	216.6	220.6	224.1	226.6	227.7	228.0
157.5°	206.3	210.3	213.3	216.1	218.1	219.1	219.0
160°	202.4	205.9	208.4	211.0	212.7	213.4	213.1
162.5°	198.9	202.0	204.2	206.1	207.5	207.7	207.6
165°	193.8	195.9	197.7	199.1	199.9	199.9	199.9
167.5°	188.8	190.5	191.8	192.5	193.1	192.8	192.7
170°	185.9	187.0	187.7	188.4	188.8	188.8	188.4
172.5°	183.4	184.2	184.6	184.7	185.4	184.8	184.4
175°	179.6	180.3	180.3	180.3	180.6	179.9	179.6
177.5°	177.8	177.8	177.8	177.6	177.8	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0

(END OF REPORT)