

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333620-840

Luminaire Tested: **S125RDIP-S1270D590U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333620-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D590U840-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6992.2 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333620-840

CATALOG NUMBER: S125RDIP-S1270D590U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333620-840

CATALOG NUMBER: S125RDIP-S1270D590U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	98	94	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	57	54	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	49	47	43
4	79	68	60	53	74	64	57	51	58	52	48	53	48	44	47	43	40	37
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	43	39	35	33
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	39	35	31	29
7	62	49	41	36	59	47	40	34	43	37	32	39	34	30	36	31	28	26
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	33	28	25	23
9	54	41	34	28	51	40	32	28	36	30	26	33	28	24	30	26	23	21
10	50	38	31	26	48	36	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13464	13464	13464
5°	13494	13341	13422
10°	13392	13217	13217
15°	13233	12948	12843
20°	13029	12575	12423
25°	12790	12207	11938
30°	12493	11777	11401
35°	12191	11334	10800
40°	11907	10871	10208
45°	11562	10355	9563
50°	11216	9792	8890
55°	10815	9254	8173
60°	10413	8603	7403
65°	9938	7844	6521
70°	9396	6898	5620
75°	8644	5814	4674
80°	7613	4567	3924
85°	6417	3735	3505



TEST NUMBER: P333620-840

CATALOG NUMBER: S125RDIP-S1270D590U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	2.8
10°-20°	547.8	7.8
20°-30°	794.4	11.4
30°-40°	905.3	12.9
40°-50°	882.5	12.6
50°-60°	742.8	10.6
60°-70°	520.7	7.4
70°-80°	267.7	3.8
80°-90°	69.2	1.0
90°-100°	49.6	0.7
100°-110°	146.4	2.1
110°-120°	248.0	3.5
120°-130°	326.4	4.7
130°-140°	365.7	5.2
140°-150°	358.4	5.1
150°-160°	301.1	4.3
160°-170°	200.1	2.9
170°-180°	70.0	1.0
0°-30°	1538.2	22.0
0°-40°	2443.5	34.9
0°-60°	4068.9	58.2
0°-90°	4926.5	70.5
90°-120°	444.0	6.4
90°-150°	1494.5	21.4
90°-180°	2066.0	29.5
0°-180°	6992.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2085	2085	2085	2085	2085	
5°	2082	2075	2058	2073	2070	197
15°	1979	1968	1937	1934	1921	558
25°	1795	1769	1713	1693	1675	826
35°	1546	1507	1438	1393	1370	968
45°	1266	1218	1134	1073	1047	976
55°	960	908	822	754	726	859
65°	650	595	513	452	427	644
75°	346	298	233	200	187	367
85°	87	59	50	49	47	97
90°	1	5	9	12	14	6
95°	38	39	44	48	50	40
105°	131	134	138	141	143	140
115°	248	250	252	251	251	245
125°	362	366	366	365	365	324
135°	471	474	475	475	473	363
145°	571	573	575	575	573	357
155°	653	653	654	656	653	301
165°	710	709	710	712	709	200
175°	738	736	736	739	736	70
180°	740	740	740	740	740	



TEST NUMBER: P333620-840

CATALOG NUMBER: S125RDIP-S1270D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2088.4	2087.6	2086.7	2085.9	2085.1	2083.3	2080.4	2077.6	2074.9	2072.0	2074.9
5°	2081.5	2080.1	2078.7	2077.3	2075.9	2073.3	2069.4	2065.6	2061.7	2057.9	2061.3
7.5°	2061.0	2059.7	2058.4	2057.0	2055.7	2052.8	2048.1	2043.5	2038.9	2034.3	2036.7
10°	2042.1	2041.0	2040.0	2039.0	2037.9	2035.0	2030.0	2025.2	2020.2	2015.4	2016.4
12.5°	2020.7	2019.4	2018.0	2016.7	2015.4	2011.4	2004.9	1998.3	1991.7	1985.1	1985.9
15°	1979.1	1977.0	1975.0	1972.9	1970.8	1966.0	1958.6	1951.4	1944.0	1936.6	1936.3
17.5°	1932.2	1929.0	1925.8	1922.6	1919.3	1913.1	1903.9	1894.6	1885.4	1876.1	1874.4
20°	1895.7	1892.2	1888.6	1885.2	1881.7	1874.3	1863.2	1852.0	1840.8	1829.6	1827.9
22.5°	1855.4	1851.9	1848.4	1844.9	1841.4	1833.8	1822.0	1810.3	1798.5	1786.8	1783.3
25°	1794.9	1789.7	1784.4	1779.2	1773.9	1764.8	1751.9	1739.0	1726.0	1713.0	1708.5
27.5°	1725.7	1719.3	1712.9	1706.6	1700.2	1690.1	1676.2	1662.3	1648.5	1634.7	1628.3
30°	1675.3	1668.6	1661.9	1655.4	1648.7	1638.0	1623.3	1608.6	1593.9	1579.2	1571.1
32.5°	1626.2	1618.4	1610.6	1602.9	1595.1	1583.7	1568.7	1553.8	1538.7	1523.8	1514.9
35°	1546.2	1537.7	1529.3	1521.0	1512.6	1500.5	1484.7	1469.1	1453.3	1437.5	1427.3
37.5°	1467.7	1457.5	1447.3	1437.1	1426.8	1413.6	1397.5	1381.2	1364.9	1348.7	1336.6
40°	1412.3	1401.8	1391.3	1380.8	1370.4	1356.7	1339.9	1323.1	1306.3	1289.5	1276.3
42.5°	1354.4	1343.6	1332.8	1322.0	1311.3	1297.2	1279.9	1262.5	1245.2	1227.8	1215.1
45°	1265.9	1255.8	1245.6	1235.5	1225.3	1210.6	1191.3	1172.2	1152.9	1133.7	1119.6
47.5°	1174.3	1163.6	1152.9	1142.2	1131.5	1116.4	1097.0	1077.6	1058.2	1038.8	1024.4
50°	1116.3	1104.8	1093.2	1081.7	1070.2	1054.4	1034.4	1014.5	994.5	974.6	959.9
52.5°	1053.3	1041.5	1029.7	1017.8	1006.0	990.7	971.9	953.1	934.2	915.4	899.6
55°	960.5	949.3	938.1	926.9	915.6	900.3	880.7	861.1	841.5	821.9	806.2
57.5°	866.6	854.6	842.6	830.7	818.7	803.3	784.5	765.5	746.6	727.7	712.4
60°	806.2	793.9	781.6	769.4	757.2	741.5	722.7	703.8	684.9	666.0	650.7
62.5°	741.9	730.2	718.5	706.8	695.2	679.7	660.6	641.4	622.2	603.0	588.8
65°	650.3	638.3	626.5	614.6	602.7	587.4	569.0	550.4	531.8	513.3	499.3
67.5°	559.3	547.3	535.4	523.6	511.7	496.9	479.1	461.3	443.5	425.8	412.9
70°	497.6	485.6	473.7	461.8	450.0	435.3	417.8	400.3	382.7	365.3	354.5
72.5°	437.1	425.5	413.8	402.2	390.6	376.6	360.2	343.9	327.5	311.1	301.1
75°	346.4	335.9	325.4	314.9	304.4	291.9	277.1	262.5	247.7	233.0	225.3
77.5°	256.3	247.9	239.5	231.2	222.8	212.7	200.9	189.1	177.4	165.6	160.3
80°	204.7	196.3	187.9	179.5	171.1	162.0	152.2	142.4	132.6	122.8	119.7
82.5°	154.3	146.7	139.2	131.6	124.1	116.9	110.2	103.5	96.7	90.1	88.6
85°	86.6	80.3	74.0	67.7	61.4	57.4	55.6	53.9	52.1	50.4	50.0
87.5°	29.1	27.4	25.5	23.8	22.1	21.1	21.0	20.9	20.8	20.7	20.9
90°	0.6	1.6	2.6	3.6	4.6	5.7	6.6	7.5	8.3	9.2	9.9
92.5°	13.9	14.6	15.3	16.1	16.8	17.7	18.8	19.9	21.0	22.1	22.9
95°	37.5	37.7	38.0	38.2	38.5	39.3	40.5	41.8	43.1	44.3	45.2
97.5°	62.2	62.3	62.4	62.5	62.6	63.5	65.3	67.1	68.9	70.6	71.5
100°	80.7	80.7	80.7	80.7	80.7	81.5	83.1	84.8	86.4	88.2	89.3
102.5°	100.5	101.0	101.5	102.0	102.5	103.2	104.0	104.9	105.7	106.5	107.9
105°	131.4	132.0	132.6	133.3	133.9	134.6	135.4	136.1	136.9	137.6	138.5
107.5°	165.4	166.1	166.7	167.3	168.0	168.6	169.3	169.8	170.4	171.0	171.4
110°	188.9	189.6	190.3	190.9	191.6	192.1	192.4	192.8	193.2	193.6	194.0



TEST NUMBER: P333620-840

CATALOG NUMBER: S125RDIP-S1270D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.9	213.3	213.6	213.9	214.3	214.7	215.2	215.6	216.1	216.6	216.8
115°	248.3	248.8	249.3	249.8	250.3	250.7	251.0	251.3	251.5	251.8	251.7
117.5°	283.8	284.0	284.3	284.5	284.7	285.0	285.2	285.4	285.6	285.9	286.0
120°	305.9	306.6	307.2	307.8	308.5	308.8	309.0	309.1	309.2	309.3	309.3
122.5°	329.9	330.1	330.3	330.5	330.8	331.0	331.4	331.7	332.0	332.4	332.3
125°	362.3	363.1	363.9	364.7	365.5	365.9	366.0	366.2	366.3	366.4	366.2
127.5°	397.0	397.4	397.8	398.2	398.7	399.0	399.1	399.3	399.4	399.6	399.5
130°	417.7	418.3	419.0	419.6	420.2	420.7	420.9	421.2	421.4	421.7	421.6
132.5°	438.4	439.5	440.5	441.5	442.6	443.1	443.0	443.0	442.9	442.9	442.8
135°	471.2	472.0	472.8	473.5	474.3	474.7	474.9	475.0	475.1	475.2	475.2
137.5°	502.1	502.9	503.6	504.3	505.1	505.6	505.9	506.1	506.4	506.8	506.9
140°	521.9	522.6	523.2	523.8	524.5	525.0	525.4	525.8	526.1	526.5	526.8
142.5°	541.8	542.3	542.8	543.4	543.9	544.4	544.9	545.4	545.9	546.3	546.5
145°	570.9	571.4	572.0	572.5	573.0	573.4	573.8	574.2	574.6	574.9	574.9
147.5°	597.8	598.1	598.4	598.7	599.1	599.3	599.6	600.0	600.3	600.6	600.9
150°	615.8	615.7	615.6	615.5	615.3	615.5	616.0	616.5	617.0	617.5	617.5
152.5°	630.6	630.8	631.0	631.2	631.3	631.5	631.7	631.9	632.1	632.4	632.7
155°	653.3	653.3	653.3	653.3	653.3	653.4	653.5	653.6	653.8	653.9	654.4
157.5°	673.6	673.3	673.0	672.8	672.5	672.4	672.5	672.7	672.8	672.9	673.4
160°	685.6	685.2	684.8	684.4	684.0	683.9	684.0	684.2	684.3	684.4	684.9
162.5°	696.2	695.9	695.6	695.3	695.0	694.9	694.9	695.0	695.0	695.0	695.6
165°	710.3	710.0	709.8	709.5	709.3	709.2	709.3	709.5	709.6	709.7	710.2
167.5°	722.4	721.9	721.2	720.7	720.2	720.0	720.0	720.0	720.0	720.0	720.7
170°	728.7	728.2	727.7	727.2	726.7	726.5	726.5	726.5	726.5	726.5	727.2
172.5°	733.4	732.9	732.4	731.8	731.3	731.0	731.0	731.0	731.0	731.0	731.8
175°	738.5	738.0	737.5	737.0	736.5	736.3	736.3	736.3	736.3	736.3	737.0
177.5°	741.2	740.8	740.4	740.0	739.5	739.3	739.2	739.1	739.0	738.9	739.5
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3



TEST NUMBER: P333620-840

CATALOG NUMBER: S125RDIP-S1270D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7	2084.7
2.5°	2077.6	2080.4	2083.3	2084.5	2084.3	2084.0	2083.7	2083.4
5°	2064.9	2068.4	2071.8	2073.3	2072.5	2071.8	2071.1	2070.4
7.5°	2039.1	2041.6	2044.1	2044.9	2044.1	2043.4	2042.6	2041.8
10°	2017.4	2018.5	2019.5	2019.5	2018.5	2017.4	2016.4	2015.4
12.5°	1986.7	1987.4	1988.2	1987.8	1986.2	1984.6	1983.0	1981.4
15°	1935.9	1935.6	1935.2	1933.5	1930.4	1927.2	1924.0	1920.9
17.5°	1872.7	1870.9	1869.2	1867.0	1864.4	1861.8	1859.3	1856.6
20°	1826.0	1824.3	1822.6	1820.1	1816.9	1813.8	1810.7	1807.6
22.5°	1779.9	1776.5	1773.0	1770.0	1767.5	1764.8	1762.2	1759.7
25°	1703.9	1699.4	1694.9	1690.6	1686.8	1682.9	1679.1	1675.3
27.5°	1621.9	1615.6	1609.2	1604.2	1600.4	1596.7	1593.0	1589.3
30°	1563.2	1555.1	1547.0	1541.5	1538.3	1535.1	1532.0	1528.8
32.5°	1506.0	1497.1	1488.2	1481.8	1477.8	1473.8	1469.9	1465.8
35°	1417.2	1407.0	1396.9	1389.4	1384.5	1379.6	1374.7	1369.8
37.5°	1324.3	1312.2	1300.0	1291.5	1286.8	1282.0	1277.3	1272.5
40°	1262.9	1249.6	1236.4	1227.6	1223.4	1219.2	1215.0	1210.8
42.5°	1202.3	1189.6	1176.9	1167.4	1161.2	1155.1	1148.9	1142.8
45°	1105.6	1091.7	1077.6	1068.0	1062.8	1057.5	1052.3	1047.0
47.5°	1010.1	995.6	981.2	971.1	965.2	959.5	953.6	947.9
50°	945.2	930.5	915.8	905.8	900.6	895.3	890.1	884.8
52.5°	883.7	868.0	852.1	841.6	836.4	831.1	825.9	820.6
55°	790.4	774.7	758.9	748.2	742.7	737.0	731.4	725.9
57.5°	696.9	681.6	666.1	656.0	651.0	646.0	641.1	636.1
60°	635.2	619.9	604.4	594.1	588.9	583.6	578.3	573.1
62.5°	574.5	560.2	545.9	536.1	530.9	525.6	520.4	515.1
65°	485.3	471.3	457.3	447.7	442.4	437.2	431.9	426.7
67.5°	400.1	387.3	374.6	366.0	361.8	357.6	353.5	349.2
70°	343.6	332.8	321.9	314.4	310.1	306.0	301.7	297.6
72.5°	291.1	281.1	271.0	264.7	261.9	259.1	256.3	253.5
75°	217.6	210.0	202.3	197.1	194.7	192.3	189.9	187.3
77.5°	154.8	149.5	144.1	140.5	138.7	136.8	135.0	133.2
80°	116.5	113.4	110.2	108.3	107.6	106.8	106.2	105.5
82.5°	87.2	85.6	84.2	83.2	82.8	82.4	82.0	81.6
85°	49.7	49.4	49.0	48.7	48.3	48.0	47.6	47.3
87.5°	21.0	21.1	21.2	21.2	21.0	20.8	20.6	20.4
90°	10.5	11.1	11.8	12.3	12.7	13.0	13.4	13.8
92.5°	23.8	24.6	25.5	26.1	26.4	26.7	26.9	27.2
95°	46.2	47.1	48.0	48.5	48.8	49.1	49.3	49.6
97.5°	72.3	73.2	74.0	74.5	74.6	74.8	74.9	75.1
100°	90.5	91.6	92.7	93.4	93.7	94.0	94.2	94.5
102.5°	109.1	110.4	111.6	112.4	112.8	113.1	113.5	113.8
105°	139.3	140.0	140.8	141.4	141.7	142.1	142.5	142.9
107.5°	171.8	172.2	172.5	172.7	172.7	172.7	172.6	172.6
110°	194.3	194.7	195.1	195.2	195.1	195.0	194.8	194.7



TEST NUMBER: P333620-840

CATALOG NUMBER: S125RDIP-S1270D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	217.0	217.1	217.3	217.3	217.1	216.8	216.6	216.4
115°	251.5	251.4	251.3	251.2	251.0	250.9	250.7	250.6
117.5°	286.1	286.2	286.3	286.1	285.6	285.1	284.6	284.0
120°	309.3	309.3	309.3	309.1	308.6	308.1	307.6	307.1
122.5°	332.2	332.1	332.0	331.7	331.3	330.9	330.5	330.1
125°	365.9	365.7	365.4	365.2	365.1	365.0	364.8	364.7
127.5°	399.3	399.2	399.1	398.9	398.6	398.4	398.1	397.9
130°	421.4	421.3	421.2	421.0	420.7	420.5	420.2	420.0
132.5°	442.6	442.5	442.4	442.1	441.8	441.4	441.1	440.7
135°	475.2	475.2	475.2	475.0	474.5	474.0	473.5	473.0
137.5°	507.1	507.2	507.4	507.2	506.4	505.8	505.2	504.5
140°	527.0	527.4	527.6	527.4	526.7	526.1	525.4	524.8
142.5°	546.6	546.8	546.9	546.7	546.1	545.4	544.8	544.2
145°	574.9	574.9	574.9	574.7	574.4	574.0	573.6	573.2
147.5°	601.2	601.5	601.8	601.5	600.6	599.8	598.8	598.0
150°	617.5	617.5	617.5	617.4	617.2	616.9	616.7	616.4
152.5°	633.0	633.3	633.6	633.5	633.0	632.6	632.1	631.7
155°	654.9	655.4	655.9	655.9	655.2	654.6	653.9	653.3
157.5°	673.9	674.4	674.9	674.8	673.9	673.1	672.3	671.4
160°	685.4	685.9	686.4	686.4	685.8	685.1	684.5	683.9
162.5°	696.2	696.8	697.5	697.4	696.7	695.9	695.2	694.4
165°	710.7	711.2	711.9	711.7	710.9	710.1	709.3	708.6
167.5°	721.5	722.4	723.1	723.1	722.3	721.4	720.6	719.9
170°	728.0	728.7	729.5	729.4	728.6	727.7	726.8	725.9
172.5°	732.7	733.4	734.2	734.2	733.4	732.6	731.7	730.9
175°	737.8	738.5	739.3	739.2	738.4	737.5	736.6	735.7
177.5°	740.1	740.7	741.3	741.3	740.6	739.9	739.1	738.4
180°	740.3	740.3	740.3	740.3	740.3	740.3	740.3	740.3

(END OF REPORT)