

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333624-840

Luminaire Tested: **S125RDIP-S1270D810U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333624-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D810U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7907.5 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63					63			
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54					54			
2	93	85	79	74	87	80	75	71	71	67	63	62	59	57	54	52	50	46					46			
3	85	75	68	62	79	71	65	60	63	58	54	55	52	48	48	46	43	40					40			
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	37	34					34			
5	72	60	52	46	67	57	49	44	51	45	40	45	40	36	39	36	33	30					30			
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26					26			
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24					24			
8	57	45	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21					21			
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19					19			
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17					17			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12385	12385	12385	12385
5°	14249	12401	10952	12401
10°	16344	12338	9664	12338
15°	17653	12211	8590	12211
20°	19467	12065	7932	12065
25°	22528	11870	7360	11870
30°	24515	11665	6986	11665
35°	20679	11427	6641	11427
40°	14441	10997	6345	10997
45°	10714	10418	6054	10418
50°	8542	9815	5805	9815
55°	7250	9067	5584	9067
60°	6263	8400	5227	8400
65°	5582	7674	4499	7674
70°	4904	7030	4101	7030
75°	4245	6089	3850	6089
80°	3217	5121	3217	5121
85°	2690	4024	3031	4024



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.9	2.3
10°-20°	538.9	6.8
20°-30°	854.5	10.8
30°-40°	1030.4	13.0
40°-50°	920.2	11.6
50°-60°	705.7	8.9
60°-70°	458.6	5.8
70°-80°	223.0	2.8
80°-90°	55.4	0.7
90°-100°	283.9	3.6
100°-110°	610.3	7.7
110°-120°	572.7	7.2
120°-130°	464.2	5.9
130°-140°	372.5	4.7
140°-150°	281.1	3.6
150°-160°	197.9	2.5
160°-170°	116.6	1.5
170°-180°	37.9	0.5
0°-30°	1577.3	19.9
0°-40°	2607.7	33.0
0°-60°	4233.5	53.5
0°-90°	4970.5	62.9
90°-120°	1466.9	18.6
90°-150°	2584.6	32.7
90°-180°	2937.0	37.1
0°-180°	7907.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1918	1918	1918	1918	1918	
5°	2198	1913	1689	1913	2198	220
15°	2640	1826	1285	1826	2640	757
25°	3161	1666	1033	1666	3161	1452
35°	2623	1449	842	1449	2623	1584
45°	1173	1141	663	1141	1173	936
55°	644	805	496	805	644	584
65°	365	502	294	502	365	363
75°	170	244	154	244	170	181
85°	36	54	41	54	36	42
90°	18	1	18	1	18	14
95°	186	26	186	26	186	263
105°	1046	89	1046	89	1046	1040
115°	1166	160	1166	160	1166	1139
125°	918	221	918	221	918	831
135°	763	259	763	259	763	591
145°	602	302	602	302	602	382
155°	504	344	504	344	504	235
165°	442	376	442	376	442	126
175°	397	391	397	391	397	39
180°	392	392	392	392	392	



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2017.1	2015.9	2018.4	2011.4	2012.1	2001.4	2001.4	1993.2	1982.5	1974.3	1970.5
5°	2197.9	2199.5	2196.3	2184.4	2176.7	2164.8	2151.4	2127.8	2108.1	2089.2	2074.3
7.5°	2384.0	2385.1	2374.7	2371.1	2351.2	2336.7	2306.9	2274.8	2246.3	2210.2	2182.4
10°	2492.2	2491.5	2480.4	2471.8	2454.5	2432.5	2403.4	2365.5	2330.2	2290.8	2253.0
12.5°	2555.3	2553.2	2549.7	2539.2	2523.1	2503.7	2478.9	2441.8	2398.1	2355.0	2310.9
15°	2640.3	2634.7	2624.5	2611.1	2588.3	2565.5	2537.9	2504.9	2463.2	2414.4	2373.4
17.5°	2745.4	2745.6	2729.9	2711.3	2680.3	2640.0	2597.5	2544.1	2487.4	2433.7	2390.1
20°	2832.4	2829.9	2814.3	2778.0	2742.6	2692.2	2643.4	2578.1	2508.8	2438.7	2384.4
22.5°	2957.1	2950.9	2934.6	2887.0	2832.1	2767.1	2692.5	2612.7	2529.0	2449.4	2378.1
25°	3161.4	3156.6	3124.4	3069.3	2992.1	2892.2	2794.6	2685.1	2564.8	2460.0	2373.4
27.5°	3301.2	3296.0	3272.1	3226.3	3155.1	3049.9	2917.8	2771.6	2621.2	2477.2	2352.3
30°	3287.3	3299.1	3296.0	3274.8	3221.3	3126.7	3004.8	2840.2	2661.5	2492.2	2343.5
32.5°	3089.6	3100.2	3127.9	3169.6	3172.7	3134.9	3043.8	2891.8	2706.8	2514.4	2336.5
35°	2622.9	2637.2	2690.7	2774.9	2885.1	2977.2	2996.1	2914.3	2748.1	2541.1	2326.2
37.5°	2016.5	2094.0	2139.0	2227.7	2394.2	2563.6	2726.5	2786.5	2715.8	2530.1	2309.4
40°	1712.9	1731.8	1812.1	1912.1	2052.2	2228.6	2460.8	2628.5	2633.9	2504.9	2282.9
42.5°	1466.1	1490.1	1545.1	1625.0	1744.9	1921.3	2161.0	2382.3	2484.8	2435.6	2248.3
45°	1173.0	1191.0	1231.2	1292.6	1384.7	1530.3	1736.6	1992.4	2195.5	2275.0	2155.4
47.5°	963.5	973.3	1008.2	1055.0	1123.2	1229.3	1389.0	1611.0	1854.6	2025.5	2008.6
50°	850.2	861.2	888.0	923.4	980.9	1070.6	1198.1	1383.1	1634.3	1842.8	1884.6
52.5°	762.0	771.1	787.8	821.3	868.8	937.8	1040.7	1208.0	1434.0	1655.8	1752.3
55°	643.9	650.3	663.6	682.5	720.3	769.9	858.8	974.5	1157.2	1380.8	1522.5
57.5°	546.6	549.8	558.3	575.7	601.9	638.1	702.4	800.4	931.4	1132.8	1289.1
60°	484.9	488.1	499.1	510.9	531.4	564.4	614.8	683.3	809.2	975.3	1133.6
62.5°	435.8	437.7	442.4	454.2	472.2	497.7	537.3	593.2	693.4	839.3	988.8
65°	365.3	366.1	367.6	377.1	388.1	407.0	432.9	472.3	547.9	658.1	790.3
67.5°	297.6	298.6	304.2	307.5	319.0	328.9	344.2	374.3	427.5	501.8	604.6
70°	259.7	259.0	264.5	268.4	272.4	284.2	294.4	318.8	351.8	408.6	494.3
72.5°	224.5	222.5	224.8	226.2	231.5	239.4	249.7	264.7	290.1	329.2	394.9
75°	170.1	170.9	170.9	172.4	176.3	179.5	182.6	190.5	204.7	230.7	266.1
77.5°	119.4	118.1	121.4	121.9	124.2	127.6	130.4	133.5	139.4	150.1	168.3
80°	86.5	86.5	87.4	89.8	89.0	90.5	94.4	97.7	104.7	111.0	117.2
82.5°	66.4	65.8	66.6	67.1	67.0	68.5	69.9	70.5	73.2	76.3	80.8
85°	36.3	36.3	37.0	37.0	37.8	37.8	38.6	38.6	38.6	39.4	40.2
87.5°	17.5	16.9	16.1	16.1	16.7	17.7	16.9	16.1	16.0	15.8	16.1
90°	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2	13.4	12.6	11.0
92.5°	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0	206.1	254.6	258.6
95°	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7	684.6	699.6	570.9
97.5°	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6	866.2	747.1	509.8
100°	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2	910.4	713.1	454.8
102.5°	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5	883.9	653.0	413.1
105°	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6	799.1	572.5	372.7
107.5°	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5	712.6	517.1	355.7
110°	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8	663.3	491.1	350.6



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0	626.6	475.9	350.6
115°	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0	586.6	459.6	352.9
117.5°	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0	562.8	451.5	358.2
120°	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2	549.6	447.7	363.2
122.5°	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2	538.2	444.5	367.6
125°	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4	522.7	440.6	375.1
127.5°	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1	508.5	438.7	383.4
130°	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3	499.1	437.5	388.5
132.5°	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5	491.5	437.5	394.2
135°	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0	482.4	437.5	401.9
137.5°	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6	474.4	438.4	409.0
140°	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1	470.6	439.0	412.1
142.5°	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0	467.5	439.7	414.0
145°	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2	462.7	439.0	416.2
147.5°	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1	457.8	437.0	416.9
150°	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4	454.0	435.0	416.9
152.5°	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0	449.6	432.5	416.3
155°	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7	442.2	428.0	414.5
157.5°	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2	435.3	423.2	412.5
160°	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8	429.6	420.1	410.6
162.5°	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8	424.4	416.3	408.7
165°	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2	416.9	410.6	405.9
167.5°	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0	409.5	405.1	401.4
170°	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0	405.1	401.9	399.5
172.5°	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3	400.6	398.1	397.0
175°	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2	394.8	394.0	394.0
177.5°	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9	392.2	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1970.5	1966.1	1957.9	1950.4	1941.0	1932.8	1927.0	1920.2	1911.4	1900.7	1891.8
5°	2057.7	2040.4	2017.6	1997.9	1972.8	1953.1	1932.6	1912.9	1893.2	1868.0	1846.0
7.5°	2154.4	2118.7	2083.9	2040.1	2000.4	1965.0	1931.0	1896.5	1862.8	1827.0	1792.6
10°	2213.6	2170.3	2122.3	2067.2	2016.8	1968.8	1924.7	1881.4	1835.7	1795.6	1752.3
12.5°	2269.1	2213.1	2158.2	2088.6	2028.1	1969.4	1913.4	1859.4	1810.6	1758.5	1712.0
15°	2319.1	2264.0	2202.6	2117.6	2033.4	1962.5	1896.3	1826.3	1765.6	1707.5	1655.5
17.5°	2338.4	2280.7	2209.4	2127.7	2035.6	1946.4	1861.3	1784.4	1713.1	1645.3	1586.8
20°	2330.9	2275.0	2201.8	2123.8	2025.5	1932.6	1840.5	1755.4	1676.0	1604.3	1542.2
22.5°	2312.7	2254.8	2184.1	2101.8	2008.4	1910.0	1811.5	1720.8	1637.5	1563.4	1495.5
25°	2285.2	2206.6	2134.1	2053.8	1964.9	1867.2	1765.6	1665.7	1576.8	1501.2	1427.2
27.5°	2256.7	2158.5	2066.4	1986.6	1892.6	1805.5	1707.6	1605.1	1511.6	1434.6	1358.7
30°	2230.9	2120.7	2019.1	1928.6	1839.7	1757.1	1664.2	1564.2	1468.1	1388.7	1311.5
32.5°	2198.8	2081.6	1970.0	1865.6	1779.9	1697.9	1613.8	1518.2	1424.7	1342.6	1264.3
35°	2158.5	2008.9	1887.7	1776.8	1681.4	1601.9	1526.4	1449.3	1355.5	1270.5	1194.2
37.5°	2105.6	1935.9	1795.6	1674.7	1574.3	1494.4	1434.7	1364.2	1278.7	1197.3	1126.5
40°	2073.5	1883.0	1729.5	1609.8	1504.3	1420.1	1364.2	1304.4	1226.5	1150.1	1079.2
42.5°	2030.6	1834.5	1662.7	1538.0	1431.9	1350.8	1294.3	1242.0	1176.7	1104.8	1028.9
45°	1946.7	1740.5	1560.2	1426.4	1319.4	1239.8	1187.1	1140.6	1091.1	1024.9	958.8
47.5°	1837.4	1642.4	1453.8	1307.7	1202.9	1129.0	1077.8	1041.2	1005.7	949.5	885.2
50°	1750.0	1561.9	1377.6	1235.9	1124.1	1054.1	1006.0	976.9	944.6	893.4	839.9
52.5°	1646.7	1478.6	1298.3	1153.4	1047.9	982.3	936.1	907.1	880.4	838.7	787.7
55°	1483.9	1336.7	1171.3	1039.9	943.1	877.0	832.8	805.3	789.6	754.2	714.0
57.5°	1296.1	1190.5	1044.8	918.1	832.4	767.1	734.8	711.3	693.6	668.5	640.2
60°	1165.1	1091.1	960.4	839.9	761.2	699.0	669.9	650.3	633.7	612.5	590.4
62.5°	1032.2	978.4	864.6	761.2	688.8	636.7	609.5	591.7	572.6	558.3	536.8
65°	854.1	806.1	727.4	646.3	579.4	537.7	518.0	502.2	490.4	474.6	459.7
67.5°	664.4	644.9	590.6	534.6	486.7	449.5	432.5	421.5	407.3	397.9	387.6
70°	547.9	538.5	499.9	462.9	418.0	392.8	377.1	372.3	355.1	345.6	338.5
72.5°	444.6	440.2	418.0	392.3	360.7	338.6	324.2	318.8	307.8	300.2	295.7
75°	304.7	306.2	302.3	285.8	274.0	259.7	247.2	244.0	236.2	229.8	225.9
77.5°	192.7	200.8	201.1	200.3	195.5	186.9	181.7	179.4	171.6	169.3	168.3
80°	132.3	140.9	148.8	147.9	146.4	144.1	140.2	137.7	133.8	131.5	129.9
82.5°	88.2	96.2	102.8	107.0	106.7	104.4	101.7	100.6	99.8	98.1	97.8
85°	41.7	43.3	45.6	51.2	55.1	55.8	55.1	54.3	51.9	52.7	53.5
87.5°	16.6	16.3	16.7	16.4	15.5	18.3	19.8	20.3	19.2	18.3	17.4
90°	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6	11.7	18.3	28.1
95°	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1	26.9	33.1	41.8
97.5°	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2	44.2	48.7	57.4
100°	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2	56.9	60.0	68.7
102.5°	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6	69.5	72.0	81.3
105°	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3	89.3	93.2	101.1
107.5°	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5	111.0	114.8	121.3
110°	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0	125.5	128.7	135.8



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5	140.1	142.6	149.7
115°	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5	161.1	163.5	170.6
117.5°	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4	180.9	183.4	190.5
120°	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1	193.5	196.6	203.7
122.5°	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4	206.1	208.6	215.7
125°	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1	222.7	226.6	233.7
127.5°	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2	236.6	241.7	250.6
130°	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4	244.8	251.1	261.4
132.5°	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7	251.8	259.3	270.8
135°	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0	262.2	271.7	284.3
137.5°	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0	274.3	283.2	295.8
140°	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5	281.9	291.3	304.0
142.5°	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3	290.1	298.9	311.5
145°	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6	303.2	311.1	322.1
147.5°	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5	316.5	323.3	333.6
150°	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8	325.3	330.8	341.1
152.5°	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5	333.6	338.4	347.4
155°	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3	344.3	349.0	356.9
157.5°	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7	354.6	358.3	365.1
160°	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6	360.8	364.1	369.5
162.5°	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3	366.6	369.7	374.6
165°	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9	374.3	376.7	380.6
167.5°	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5	380.7	382.1	384.4
170°	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4	384.6	385.4	386.9
172.5°	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9	386.5	387.2	388.8
175°	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8	389.3	390.1	390.8
177.5°	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2	391.0	391.0	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1885.5	1876.7	1870.4	1857.7	1849.0	1845.2	1838.3	1836.3	1843.3	1838.3	1837.7
5°	1829.5	1806.6	1788.6	1770.4	1750.7	1738.2	1719.3	1716.1	1711.4	1704.2	1702.7
7.5°	1762.2	1732.5	1709.2	1679.3	1653.3	1632.3	1608.7	1597.5	1591.4	1582.3	1570.0
10°	1716.9	1681.4	1650.0	1620.0	1587.8	1561.9	1538.2	1520.0	1508.2	1497.2	1492.6
12.5°	1672.1	1636.1	1595.8	1559.6	1523.6	1494.4	1468.2	1456.5	1443.4	1430.5	1419.5
15°	1602.8	1554.7	1510.7	1468.9	1438.2	1406.7	1381.5	1364.2	1344.5	1339.1	1317.8
17.5°	1529.0	1482.0	1430.4	1386.4	1350.8	1316.2	1288.5	1268.8	1254.1	1233.8	1224.0
20°	1483.1	1427.2	1376.8	1336.7	1297.3	1256.4	1228.0	1211.5	1197.3	1180.8	1173.0
22.5°	1434.0	1379.4	1327.7	1280.6	1240.6	1200.3	1180.1	1163.1	1146.9	1131.7	1121.3
25°	1361.9	1306.8	1252.4	1203.7	1162.0	1132.8	1109.1	1089.4	1080.9	1065.9	1054.8
27.5°	1290.5	1231.9	1175.6	1126.9	1094.2	1065.4	1046.0	1030.5	1014.8	1001.8	992.2
30°	1244.6	1184.8	1123.4	1084.8	1050.2	1022.6	1001.3	986.3	974.5	962.7	955.6
32.5°	1198.6	1136.9	1082.4	1040.7	1007.9	984.1	962.3	948.0	935.5	922.4	914.1
35°	1124.9	1062.0	1017.8	976.9	944.6	922.6	907.7	887.2	877.0	867.5	858.8
37.5°	1056.4	997.8	950.2	914.2	886.3	864.3	845.0	833.9	821.3	812.8	805.7
40°	1006.0	952.5	909.2	871.4	851.0	826.6	808.5	794.3	784.9	773.9	766.0
42.5°	960.7	911.0	868.9	835.0	809.4	788.8	771.3	757.1	745.2	737.3	730.6
45°	896.7	847.1	806.1	774.6	751.0	731.3	713.2	706.1	690.3	681.0	677.8
47.5°	830.3	786.0	746.4	717.4	693.2	674.6	657.6	643.2	634.5	625.2	620.2
50°	785.7	743.2	706.1	677.8	654.2	633.7	617.9	608.5	596.7	588.0	581.8
52.5°	740.9	701.6	664.6	637.4	617.0	596.5	579.0	569.5	558.3	552.8	548.4
55°	677.0	635.3	603.8	577.0	555.7	536.8	520.4	510.9	503.8	498.3	496.8
57.5°	604.6	571.5	542.2	518.2	496.0	478.3	463.8	454.8	448.6	447.8	443.0
60°	557.3	527.5	500.7	474.6	455.8	439.3	426.7	416.5	410.1	409.3	407.8
62.5°	510.1	481.4	456.6	433.7	416.8	400.8	388.9	377.4	373.7	369.7	366.2
65°	440.0	414.0	393.6	375.5	357.4	344.0	332.2	325.1	316.5	311.7	303.1
67.5°	371.2	351.1	331.4	316.2	301.9	289.2	279.4	268.9	263.1	259.3	253.0
70°	325.9	310.1	290.4	274.0	263.0	252.7	244.8	233.0	229.0	225.9	222.8
72.5°	283.1	269.2	252.7	239.3	228.3	218.6	209.5	204.0	200.2	196.9	195.1
75°	222.8	209.4	195.2	185.8	177.9	170.1	165.3	161.4	159.8	159.1	155.8
77.5°	163.6	156.5	145.1	137.6	132.4	129.3	125.0	123.0	122.8	119.4	118.3
80°	125.1	121.2	111.8	108.7	104.7	101.6	99.2	95.2	91.3	89.8	87.4
82.5°	93.0	89.1	85.3	80.3	77.0	75.1	72.7	71.3	71.8	69.6	68.5
85°	49.6	45.6	44.1	43.3	41.7	43.3	42.5	41.7	40.9	40.2	40.9
87.5°	17.0	17.4	16.9	18.4	16.7	17.7	17.8	17.4	17.5	17.7	17.4
90°	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2	15.0	15.8	17.4
92.5°	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0	101.6	76.4	64.7
95°	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7	447.7	350.6	284.3
97.5°	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6	761.3	666.7	574.5
100°	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2	932.5	851.2	769.1
102.5°	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5	1037.4	998.4	942.8
105°	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6	1096.8	1131.6	1122.9
107.5°	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5	1043.9	1133.1	1174.3
110°	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8	983.8	1095.2	1162.3



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0	924.4	1037.0	1116.2
115°	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0	839.4	947.6	1033.6
117.5°	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0	780.4	873.6	952.6
120°	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2	747.0	833.8	903.3
122.5°	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2	723.0	800.3	865.5
125°	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4	690.9	759.6	816.5
127.5°	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1	660.2	724.4	777.6
130°	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3	638.8	700.3	751.7
132.5°	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5	618.5	674.5	723.9
135°	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0	587.4	638.0	683.0
137.5°	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6	559.7	601.7	639.9
140°	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1	543.2	579.6	612.7
142.5°	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0	529.4	560.6	589.4
145°	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2	511.7	536.1	557.4
147.5°	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1	497.0	515.7	531.9
150°	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4	488.8	503.7	518.0
152.5°	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0	480.6	494.3	505.3
155°	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7	468.3	479.3	488.0
157.5°	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2	456.6	465.0	471.9
160°	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8	447.7	455.7	461.1
162.5°	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8	440.1	446.8	451.6
165°	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2	428.8	433.5	437.5
167.5°	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0	417.7	421.3	424.1
170°	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0	411.4	413.7	415.4
172.5°	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3	405.7	407.5	408.4
175°	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2	397.2	398.8	398.8
177.5°	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9	393.5	393.5	393.5
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1837.0	1830.1	1828.2	1830.7	1828.2	1830.1	1837.0	1837.7	1838.3	1843.3	1836.3
5°	1694.9	1687.0	1690.9	1689.3	1690.9	1687.0	1694.9	1702.7	1704.2	1711.4	1716.1
7.5°	1569.8	1560.0	1549.6	1553.0	1549.6	1560.0	1569.8	1570.0	1582.3	1591.4	1597.5
10°	1482.3	1474.4	1469.7	1473.6	1469.7	1474.4	1482.3	1492.6	1497.2	1508.2	1520.0
12.5°	1408.7	1403.9	1399.8	1398.1	1399.8	1403.9	1408.7	1419.5	1430.5	1443.4	1456.5
15°	1308.3	1298.9	1294.9	1284.8	1294.9	1298.9	1308.3	1317.8	1339.1	1344.5	1364.2
17.5°	1215.9	1212.7	1202.5	1198.1	1202.5	1212.7	1215.9	1224.0	1233.8	1254.1	1268.8
20°	1161.1	1158.0	1147.7	1154.1	1147.7	1158.0	1161.1	1173.0	1180.8	1197.3	1211.5
22.5°	1115.8	1108.8	1105.5	1103.7	1105.5	1108.8	1115.8	1121.3	1131.7	1146.9	1163.1
25°	1051.7	1041.5	1037.5	1032.8	1037.5	1041.5	1051.7	1054.8	1065.9	1080.9	1089.4
27.5°	987.7	982.3	977.0	975.8	977.0	982.3	987.7	992.2	1001.8	1014.8	1030.5
30°	946.2	940.7	936.8	936.8	936.8	940.7	946.2	955.6	962.7	974.5	986.3
32.5°	909.1	904.8	900.9	900.3	900.9	904.8	909.1	914.1	922.4	935.5	948.0
35°	855.0	848.6	847.1	842.3	847.1	848.6	855.0	858.8	867.5	877.0	887.2
37.5°	798.7	793.5	793.3	792.8	793.3	793.5	798.7	805.7	812.8	821.3	833.9
40°	762.8	758.8	758.1	752.6	758.1	758.8	762.8	766.0	773.9	784.9	794.3
42.5°	724.4	722.4	719.6	717.3	719.6	722.4	724.4	730.6	737.3	745.2	757.1
45°	672.3	666.7	666.7	662.8	666.7	666.7	672.3	677.8	681.0	690.3	706.1
47.5°	618.4	614.2	614.6	610.6	614.6	614.2	618.4	620.2	625.2	634.5	643.2
50°	582.5	580.2	579.4	577.8	579.4	580.2	582.5	581.8	588.0	596.7	608.5
52.5°	546.6	545.5	548.6	545.0	548.6	545.5	546.6	548.4	552.8	558.3	569.5
55°	498.3	495.9	500.7	495.9	500.7	495.9	498.3	496.8	498.3	503.8	510.9
57.5°	442.7	440.5	444.7	442.4	444.7	440.5	442.7	443.0	447.8	448.6	454.8
60°	406.2	401.5	403.8	404.7	403.8	401.5	406.2	407.8	409.3	410.1	416.5
62.5°	362.7	359.9	361.6	358.0	361.6	359.9	362.7	366.2	369.7	373.7	377.4
65°	301.5	299.1	296.0	294.4	296.0	299.1	301.5	303.1	311.7	316.5	325.1
67.5°	253.3	247.6	247.5	248.7	247.5	247.6	253.3	253.0	259.3	263.1	268.9
70°	218.0	218.0	217.2	217.2	217.2	218.0	218.0	222.8	225.9	229.0	233.0
72.5°	193.5	192.9	191.5	190.9	191.5	192.9	193.5	195.1	196.9	200.2	204.0
75°	155.8	156.6	155.1	154.3	155.1	156.6	155.8	155.8	159.1	159.8	161.4
77.5°	115.1	111.8	113.5	111.8	113.5	111.8	115.1	118.3	119.4	122.8	123.0
80°	87.4	86.5	89.0	86.5	89.0	86.5	87.4	87.4	89.8	91.3	95.2
82.5°	69.1	68.4	69.5	67.7	69.5	68.4	69.1	68.5	69.6	71.8	71.3
85°	41.7	40.9	40.2	40.9	40.2	40.9	41.7	40.9	40.2	40.9	41.7
87.5°	18.0	17.4	17.5	17.5	17.5	17.4	18.0	17.4	17.7	17.5	17.4
90°	17.4	17.4	18.2	18.2	18.2	17.4	17.4	17.4	15.8	15.0	14.2
92.5°	54.6	52.7	51.6	50.4	51.6	52.7	54.6	64.7	76.4	101.6	140.0
95°	228.2	204.5	198.2	185.5	198.2	204.5	228.2	284.3	350.6	447.7	567.7
97.5°	525.7	481.5	458.6	448.5	458.6	481.5	525.7	574.5	666.7	761.3	845.6
100°	714.6	657.7	628.5	615.9	628.5	657.7	714.6	769.1	851.2	932.5	971.2
102.5°	884.5	844.0	812.3	802.8	812.3	844.0	884.5	942.8	998.4	1037.4	1013.5
105°	1097.5	1071.5	1055.7	1046.2	1055.7	1071.5	1097.5	1122.9	1131.6	1096.8	988.6
107.5°	1187.1	1186.9	1181.7	1175.4	1181.7	1186.9	1187.1	1174.3	1133.1	1043.9	899.5
110°	1197.8	1212.8	1218.4	1218.4	1218.4	1212.8	1197.8	1162.3	1095.2	983.8	833.8



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.1	1193.9	1207.6	1213.4	1207.6	1193.9	1168.1	1116.2	1037.0	924.4	782.0
115°	1095.2	1133.1	1155.2	1165.5	1155.2	1133.1	1095.2	1033.6	947.6	839.4	717.0
117.5°	1014.2	1053.3	1075.3	1081.6	1075.3	1053.3	1014.2	952.6	873.6	780.4	675.0
120°	961.7	999.7	1021.0	1027.2	1021.0	999.7	961.7	903.3	833.8	747.0	652.2
122.5°	917.6	952.3	973.6	979.3	973.6	952.3	917.6	865.5	800.3	723.0	635.2
125°	860.7	893.0	910.4	918.3	910.4	893.0	860.7	816.5	759.6	690.9	610.4
127.5°	817.7	846.3	862.7	866.2	862.7	846.3	817.7	777.6	724.4	660.2	585.1
130°	791.2	817.3	833.0	837.8	833.0	817.3	791.2	751.7	700.3	638.8	569.3
132.5°	763.4	789.4	804.0	809.3	804.0	789.4	763.4	723.9	674.5	618.5	553.5
135°	717.7	743.8	758.0	762.8	758.0	743.8	717.7	683.0	638.0	587.4	533.0
137.5°	671.1	694.7	707.8	713.1	707.8	694.7	671.1	639.9	601.7	559.7	515.6
140°	642.0	662.5	674.3	678.2	674.3	662.5	642.0	612.7	579.6	543.2	506.1
142.5°	614.2	631.6	642.8	646.0	642.8	631.6	614.2	589.4	560.6	529.4	498.0
145°	576.4	589.9	598.5	601.7	598.5	589.9	576.4	557.4	536.1	511.7	487.2
147.5°	546.8	557.6	562.7	564.1	562.7	557.6	546.8	531.9	515.7	497.0	477.1
150°	529.9	539.3	542.5	543.2	542.5	539.3	529.9	518.0	503.7	488.8	471.4
152.5°	515.3	522.9	526.0	526.8	526.0	522.9	515.3	505.3	494.3	480.6	465.0
155°	495.8	501.4	503.7	504.5	503.7	501.4	495.8	488.0	479.3	468.3	455.7
157.5°	478.1	482.6	484.8	484.6	484.8	482.6	478.1	471.9	465.0	456.6	446.2
160°	466.7	470.6	472.2	471.4	472.2	470.6	466.7	461.1	455.7	447.7	439.8
162.5°	456.0	459.2	459.6	459.4	459.6	459.2	456.0	451.6	446.8	440.1	432.8
165°	440.6	442.2	442.2	442.2	442.2	442.2	440.6	437.5	433.5	428.8	423.2
167.5°	425.8	427.2	426.6	426.4	426.6	427.2	425.8	424.1	421.3	417.7	414.0
170°	416.9	417.7	417.7	416.9	417.7	417.7	416.9	415.4	413.7	411.4	409.0
172.5°	408.7	410.1	408.9	408.1	408.9	410.1	408.7	408.4	407.5	405.7	403.3
175°	398.8	399.5	398.0	397.2	398.0	399.5	398.8	398.8	398.8	397.2	397.2
177.5°	392.9	393.5	391.6	391.6	391.6	393.5	392.9	393.5	393.5	393.5	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1838.3	1845.2	1849.0	1857.7	1870.4	1876.7	1885.5	1891.8	1900.7	1911.4	1920.2
5°	1719.3	1738.2	1750.7	1770.4	1788.6	1806.6	1829.5	1846.0	1868.0	1893.2	1912.9
7.5°	1608.7	1632.3	1653.3	1679.3	1709.2	1732.5	1762.2	1792.6	1827.0	1862.8	1896.5
10°	1538.2	1561.9	1587.8	1620.0	1650.0	1681.4	1716.9	1752.3	1795.6	1835.7	1881.4
12.5°	1468.2	1494.4	1523.6	1559.6	1595.8	1636.1	1672.1	1712.0	1758.5	1810.6	1859.4
15°	1381.5	1406.7	1438.2	1468.9	1510.7	1554.7	1602.8	1655.5	1707.5	1765.6	1826.3
17.5°	1288.5	1316.2	1350.8	1386.4	1430.4	1482.0	1529.0	1586.8	1645.3	1713.1	1784.4
20°	1228.0	1256.4	1297.3	1336.7	1376.8	1427.2	1483.1	1542.2	1604.3	1676.0	1755.4
22.5°	1180.1	1200.3	1240.6	1280.6	1327.7	1379.4	1434.0	1495.5	1563.4	1637.5	1720.8
25°	1109.1	1132.8	1162.0	1203.7	1252.4	1306.8	1361.9	1427.2	1501.2	1576.8	1665.7
27.5°	1046.0	1065.4	1094.2	1126.9	1175.6	1231.9	1290.5	1358.7	1434.6	1511.6	1605.1
30°	1001.3	1022.6	1050.2	1084.8	1123.4	1184.8	1244.6	1311.5	1388.7	1468.1	1564.2
32.5°	962.3	984.1	1007.9	1040.7	1082.4	1136.9	1198.6	1264.3	1342.6	1424.7	1518.2
35°	907.7	922.6	944.6	976.9	1017.8	1062.0	1124.9	1194.2	1270.5	1355.5	1449.3
37.5°	845.0	864.3	886.3	914.2	950.2	997.8	1056.4	1126.5	1197.3	1278.7	1364.2
40°	808.5	826.6	851.0	871.4	909.2	952.5	1006.0	1079.2	1150.1	1226.5	1304.4
42.5°	771.3	788.8	809.4	835.0	868.9	911.0	960.7	1028.9	1104.8	1176.7	1242.0
45°	713.2	731.3	751.0	774.6	806.1	847.1	896.7	958.8	1024.9	1091.1	1140.6
47.5°	657.6	674.6	693.2	717.4	746.4	786.0	830.3	885.2	949.5	1005.7	1041.2
50°	617.9	633.7	654.2	677.8	706.1	743.2	785.7	839.9	893.4	944.6	976.9
52.5°	579.0	596.5	617.0	637.4	664.6	701.6	740.9	787.7	838.7	880.4	907.1
55°	520.4	536.8	555.7	577.0	603.8	635.3	677.0	714.0	754.2	789.6	805.3
57.5°	463.8	478.3	496.0	518.2	542.2	571.5	604.6	640.2	668.5	693.6	711.3
60°	426.7	439.3	455.8	474.6	500.7	527.5	557.3	590.4	612.5	633.7	650.3
62.5°	388.9	400.8	416.8	433.7	456.6	481.4	510.1	536.8	558.3	572.6	591.7
65°	332.2	344.0	357.4	375.5	393.6	414.0	440.0	459.7	474.6	490.4	502.2
67.5°	279.4	289.2	301.9	316.2	331.4	351.1	371.2	387.6	397.9	407.3	421.5
70°	244.8	252.7	263.0	274.0	290.4	310.1	325.9	338.5	345.6	355.1	372.3
72.5°	209.5	218.6	228.3	239.3	252.7	269.2	283.1	295.7	300.2	307.8	318.8
75°	165.3	170.1	177.9	185.8	195.2	209.4	222.8	225.9	229.8	236.2	244.0
77.5°	125.0	129.3	132.4	137.6	145.1	156.5	163.6	168.3	169.3	171.6	179.4
80°	99.2	101.6	104.7	108.7	111.8	121.2	125.1	129.9	131.5	133.8	137.7
82.5°	72.7	75.1	77.0	80.3	85.3	89.1	93.0	97.8	98.1	99.8	100.6
85°	42.5	43.3	41.7	43.3	44.1	45.6	49.6	53.5	52.7	51.9	54.3
87.5°	17.8	17.7	16.7	18.4	16.9	17.4	17.0	17.4	18.3	19.2	20.3
90°	13.4	12.6	11.0	10.3	8.7	7.9	6.4	4.7	3.1	1.6	0.8
92.5°	206.1	254.6	258.6	180.2	107.9	64.7	41.7	28.1	18.3	11.7	9.6
95°	684.6	699.6	570.9	352.9	179.3	94.7	59.2	41.8	33.1	26.9	26.1
97.5°	866.2	747.1	509.8	281.8	154.4	98.6	72.9	57.4	48.7	44.2	43.2
100°	910.4	713.1	454.8	255.8	153.2	107.3	83.7	68.7	60.0	56.9	55.2
102.5°	883.9	653.0	413.1	245.1	158.9	118.2	95.0	81.3	72.0	69.5	68.6
105°	799.1	572.5	372.7	240.9	170.6	135.8	113.7	101.1	93.2	89.3	89.3
107.5°	712.6	517.1	355.7	248.1	187.9	154.3	134.4	121.3	114.8	111.0	109.5
110°	663.3	491.1	350.6	255.1	200.6	168.1	147.6	135.8	128.7	125.5	124.0



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	626.6	475.9	350.6	263.9	212.6	181.5	161.6	149.7	142.6	140.1	138.5
115°	586.6	459.6	352.9	277.1	231.4	202.2	182.4	170.6	163.5	161.1	159.5
117.5°	562.8	451.5	358.2	292.4	250.6	223.0	203.9	190.5	183.4	180.9	178.4
120°	549.6	447.7	363.2	302.5	264.5	236.9	217.1	203.7	196.6	193.5	191.1
122.5°	538.2	444.5	367.6	313.8	277.8	250.1	230.5	215.7	208.6	206.1	204.4
125°	522.7	440.6	375.1	329.2	295.3	269.2	248.7	233.7	226.6	222.7	221.1
127.5°	508.5	438.7	383.4	343.5	312.3	287.1	266.6	250.6	241.7	236.6	234.2
130°	499.1	437.5	388.5	352.9	323.0	298.5	277.9	261.4	251.1	244.8	242.4
132.5°	491.5	437.5	394.2	361.1	333.1	308.6	288.0	270.8	259.3	251.8	248.7
135°	482.4	437.5	401.9	372.7	346.7	322.1	300.8	284.3	271.7	262.2	259.0
137.5°	474.4	438.4	409.0	381.2	356.3	334.0	312.0	295.8	283.2	274.3	272.0
140°	470.6	439.0	412.1	386.9	363.2	340.3	319.0	304.0	291.3	281.9	279.5
142.5°	467.5	439.7	414.0	390.1	367.6	346.0	326.0	311.5	298.9	290.1	288.3
145°	462.7	439.0	416.2	394.8	375.1	354.6	336.4	322.1	311.1	303.2	301.6
147.5°	457.8	437.0	416.9	397.7	379.8	361.8	345.9	333.6	323.3	316.5	315.5
150°	454.0	435.0	416.9	399.5	382.9	365.6	352.1	341.1	330.8	325.3	323.8
152.5°	449.6	432.5	416.3	400.8	386.1	370.0	357.9	347.4	338.4	333.6	332.5
155°	442.2	428.0	414.5	401.9	389.3	375.9	364.8	356.9	349.0	344.3	344.3
157.5°	435.3	423.2	412.5	402.7	391.9	380.4	372.0	365.1	358.3	354.6	354.7
160°	429.6	420.1	410.6	402.7	393.2	382.9	375.9	369.5	364.1	360.8	361.6
162.5°	424.4	416.3	408.7	402.0	394.5	385.5	379.6	374.6	369.7	366.6	367.3
165°	416.9	410.6	405.9	401.1	394.8	388.5	383.7	380.6	376.7	374.3	375.9
167.5°	409.5	405.1	401.4	399.2	394.8	389.6	386.6	384.4	382.1	380.7	381.5
170°	405.1	401.9	399.5	398.0	394.8	390.8	388.5	386.9	385.4	384.6	385.4
172.5°	400.6	398.1	397.0	396.7	394.2	390.8	389.7	388.8	387.2	386.5	387.9
175°	394.8	394.0	394.0	394.8	393.2	390.8	390.8	390.8	390.1	389.3	390.8
177.5°	392.2	391.6	391.6	392.9	392.2	391.0	391.0	391.6	391.0	391.0	392.2
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	1927.0	1932.8	1941.0	1950.4	1957.9	1966.1	1970.5	1970.5	1974.3	1982.5	1993.2
5°	1932.6	1953.1	1972.8	1997.9	2017.6	2040.4	2057.7	2074.3	2089.2	2108.1	2127.8
7.5°	1931.0	1965.0	2000.4	2040.1	2083.9	2118.7	2154.4	2182.4	2210.2	2246.3	2274.8
10°	1924.7	1968.8	2016.8	2067.2	2122.3	2170.3	2213.6	2253.0	2290.8	2330.2	2365.5
12.5°	1913.4	1969.4	2028.1	2088.6	2158.2	2213.1	2269.1	2310.9	2355.0	2398.1	2441.8
15°	1896.3	1962.5	2033.4	2117.6	2202.6	2264.0	2319.1	2373.4	2414.4	2463.2	2504.9
17.5°	1861.3	1946.4	2035.6	2127.7	2209.4	2280.7	2338.4	2390.1	2433.7	2487.4	2544.1
20°	1840.5	1932.6	2025.5	2123.8	2201.8	2275.0	2330.9	2384.4	2438.7	2508.8	2578.1
22.5°	1811.5	1910.0	2008.4	2101.8	2184.1	2254.8	2312.7	2378.1	2449.4	2529.0	2612.7
25°	1765.6	1867.2	1964.9	2053.8	2134.1	2206.6	2285.2	2373.4	2460.0	2564.8	2685.1
27.5°	1707.6	1805.5	1892.6	1986.6	2066.4	2158.5	2256.7	2352.3	2477.2	2621.2	2771.6
30°	1664.2	1757.1	1839.7	1928.6	2019.1	2120.7	2230.9	2343.5	2492.2	2661.5	2840.2
32.5°	1613.8	1697.9	1779.9	1865.6	1970.0	2081.6	2198.8	2336.5	2514.4	2706.8	2891.8
35°	1526.4	1601.9	1681.4	1776.8	1887.7	2008.9	2158.5	2326.2	2541.1	2748.1	2914.3
37.5°	1434.7	1494.4	1574.3	1674.7	1795.6	1935.9	2105.6	2309.4	2530.1	2715.8	2786.5
40°	1364.2	1420.1	1504.3	1609.8	1729.5	1883.0	2073.5	2282.9	2504.9	2633.9	2628.5
42.5°	1294.3	1350.8	1431.9	1538.0	1662.7	1834.5	2030.6	2248.3	2435.6	2484.8	2382.3
45°	1187.1	1239.8	1319.4	1426.4	1560.2	1740.5	1946.7	2155.4	2275.0	2195.5	1992.4
47.5°	1077.8	1129.0	1202.9	1307.7	1453.8	1642.4	1837.4	2008.6	2025.5	1854.6	1611.0
50°	1006.0	1054.1	1124.1	1235.9	1377.6	1561.9	1750.0	1884.6	1842.8	1634.3	1383.1
52.5°	936.1	982.3	1047.9	1153.4	1298.3	1478.6	1646.7	1752.3	1655.8	1434.0	1208.0
55°	832.8	877.0	943.1	1039.9	1171.3	1336.7	1483.9	1522.5	1380.8	1157.2	974.5
57.5°	734.8	767.1	832.4	918.1	1044.8	1190.5	1296.1	1289.1	1132.8	931.4	800.4
60°	669.9	699.0	761.2	839.9	960.4	1091.1	1165.1	1133.6	975.3	809.2	683.3
62.5°	609.5	636.7	688.8	761.2	864.6	978.4	1032.2	988.8	839.3	693.4	593.2
65°	518.0	537.7	579.4	646.3	727.4	806.1	854.1	790.3	658.1	547.9	472.3
67.5°	432.5	449.5	486.7	534.6	590.6	644.9	664.4	604.6	501.8	427.5	374.3
70°	377.1	392.8	418.0	462.9	499.9	538.5	547.9	494.3	408.6	351.8	318.8
72.5°	324.2	338.6	360.7	392.3	418.0	440.2	444.6	394.9	329.2	290.1	264.7
75°	247.2	259.7	274.0	285.8	302.3	306.2	304.7	266.1	230.7	204.7	190.5
77.5°	181.7	186.9	195.5	200.3	201.1	200.8	192.7	168.3	150.1	139.4	133.5
80°	140.2	144.1	146.4	147.9	148.8	140.9	132.3	117.2	111.0	104.7	97.7
82.5°	101.7	104.4	106.7	107.0	102.8	96.2	88.2	80.8	76.3	73.2	70.5
85°	55.1	55.8	55.1	51.2	45.6	43.3	41.7	40.2	39.4	38.6	38.6
87.5°	19.8	18.3	15.5	16.4	16.7	16.3	16.6	16.1	15.8	16.0	16.1
90°	1.6	3.1	4.7	6.4	7.9	8.7	10.3	11.0	12.6	13.4	14.2
92.5°	11.7	18.3	28.1	41.7	64.7	107.9	180.2	258.6	254.6	206.1	140.0
95°	26.9	33.1	41.8	59.2	94.7	179.3	352.9	570.9	699.6	684.6	567.7
97.5°	44.2	48.7	57.4	72.9	98.6	154.4	281.8	509.8	747.1	866.2	845.6
100°	56.9	60.0	68.7	83.7	107.3	153.2	255.8	454.8	713.1	910.4	971.2
102.5°	69.5	72.0	81.3	95.0	118.2	158.9	245.1	413.1	653.0	883.9	1013.5
105°	89.3	93.2	101.1	113.7	135.8	170.6	240.9	372.7	572.5	799.1	988.6
107.5°	111.0	114.8	121.3	134.4	154.3	187.9	248.1	355.7	517.1	712.6	899.5
110°	125.5	128.7	135.8	147.6	168.1	200.6	255.1	350.6	491.1	663.3	833.8



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	140.1	142.6	149.7	161.6	181.5	212.6	263.9	350.6	475.9	626.6	782.0
115°	161.1	163.5	170.6	182.4	202.2	231.4	277.1	352.9	459.6	586.6	717.0
117.5°	180.9	183.4	190.5	203.9	223.0	250.6	292.4	358.2	451.5	562.8	675.0
120°	193.5	196.6	203.7	217.1	236.9	264.5	302.5	363.2	447.7	549.6	652.2
122.5°	206.1	208.6	215.7	230.5	250.1	277.8	313.8	367.6	444.5	538.2	635.2
125°	222.7	226.6	233.7	248.7	269.2	295.3	329.2	375.1	440.6	522.7	610.4
127.5°	236.6	241.7	250.6	266.6	287.1	312.3	343.5	383.4	438.7	508.5	585.1
130°	244.8	251.1	261.4	277.9	298.5	323.0	352.9	388.5	437.5	499.1	569.3
132.5°	251.8	259.3	270.8	288.0	308.6	333.1	361.1	394.2	437.5	491.5	553.5
135°	262.2	271.7	284.3	300.8	322.1	346.7	372.7	401.9	437.5	482.4	533.0
137.5°	274.3	283.2	295.8	312.0	334.0	356.3	381.2	409.0	438.4	474.4	515.6
140°	281.9	291.3	304.0	319.0	340.3	363.2	386.9	412.1	439.0	470.6	506.1
142.5°	290.1	298.9	311.5	326.0	346.0	367.6	390.1	414.0	439.7	467.5	498.0
145°	303.2	311.1	322.1	336.4	354.6	375.1	394.8	416.2	439.0	462.7	487.2
147.5°	316.5	323.3	333.6	345.9	361.8	379.8	397.7	416.9	437.0	457.8	477.1
150°	325.3	330.8	341.1	352.1	365.6	382.9	399.5	416.9	435.0	454.0	471.4
152.5°	333.6	338.4	347.4	357.9	370.0	386.1	400.8	416.3	432.5	449.6	465.0
155°	344.3	349.0	356.9	364.8	375.9	389.3	401.9	414.5	428.0	442.2	455.7
157.5°	354.6	358.3	365.1	372.0	380.4	391.9	402.7	412.5	423.2	435.3	446.2
160°	360.8	364.1	369.5	375.9	382.9	393.2	402.7	410.6	420.1	429.6	439.8
162.5°	366.6	369.7	374.6	379.6	385.5	394.5	402.0	408.7	416.3	424.4	432.8
165°	374.3	376.7	380.6	383.7	388.5	394.8	401.1	405.9	410.6	416.9	423.2
167.5°	380.7	382.1	384.4	386.6	389.6	394.8	399.2	401.4	405.1	409.5	414.0
170°	384.6	385.4	386.9	388.5	390.8	394.8	398.0	399.5	401.9	405.1	409.0
172.5°	386.5	387.2	388.8	389.7	390.8	394.2	396.7	397.0	398.1	400.6	403.3
175°	389.3	390.1	390.8	390.8	390.8	393.2	394.8	394.0	394.0	394.8	397.2
177.5°	391.0	391.0	391.6	391.0	391.0	392.2	392.9	391.6	391.6	392.2	392.9
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6	1917.6
2.5°	2001.4	2001.4	2012.1	2011.4	2018.4	2015.9	2017.1
5°	2151.4	2164.8	2176.7	2184.4	2196.3	2199.5	2197.9
7.5°	2306.9	2336.7	2351.2	2371.1	2374.7	2385.1	2384.0
10°	2403.4	2432.5	2454.5	2471.8	2480.4	2491.5	2492.2
12.5°	2478.9	2503.7	2523.1	2539.2	2549.7	2553.2	2555.3
15°	2537.9	2565.5	2588.3	2611.1	2624.5	2634.7	2640.3
17.5°	2597.5	2640.0	2680.3	2711.3	2729.9	2745.6	2745.4
20°	2643.4	2692.2	2742.6	2778.0	2814.3	2829.9	2832.4
22.5°	2692.5	2767.1	2832.1	2887.0	2934.6	2950.9	2957.1
25°	2794.6	2892.2	2992.1	3069.3	3124.4	3156.6	3161.4
27.5°	2917.8	3049.9	3155.1	3226.3	3272.1	3296.0	3301.2
30°	3004.8	3126.7	3221.3	3274.8	3296.0	3299.1	3287.3
32.5°	3043.8	3134.9	3172.7	3169.6	3127.9	3100.2	3089.6
35°	2996.1	2977.2	2885.1	2774.9	2690.7	2637.2	2622.9
37.5°	2726.5	2563.6	2394.2	2227.7	2139.0	2094.0	2016.5
40°	2460.8	2228.6	2052.2	1912.1	1812.1	1731.8	1712.9
42.5°	2161.0	1921.3	1744.9	1625.0	1545.1	1490.1	1466.1
45°	1736.6	1530.3	1384.7	1292.6	1231.2	1191.0	1173.0
47.5°	1389.0	1229.3	1123.2	1055.0	1008.2	973.3	963.5
50°	1198.1	1070.6	980.9	923.4	888.0	861.2	850.2
52.5°	1040.7	937.8	868.8	821.3	787.8	771.1	762.0
55°	858.8	769.9	720.3	682.5	663.6	650.3	643.9
57.5°	702.4	638.1	601.9	575.7	558.3	549.8	546.6
60°	614.8	564.4	531.4	510.9	499.1	488.1	484.9
62.5°	537.3	497.7	472.2	454.2	442.4	437.7	435.8
65°	432.9	407.0	388.1	377.1	367.6	366.1	365.3
67.5°	344.2	328.9	319.0	307.5	304.2	298.6	297.6
70°	294.4	284.2	272.4	268.4	264.5	259.0	259.7
72.5°	249.7	239.4	231.5	226.2	224.8	222.5	224.5
75°	182.6	179.5	176.3	172.4	170.9	170.9	170.1
77.5°	130.4	127.6	124.2	121.9	121.4	118.1	119.4
80°	94.4	90.5	89.0	89.8	87.4	86.5	86.5
82.5°	69.9	68.5	67.0	67.1	66.6	65.8	66.4
85°	38.6	37.8	37.8	37.0	37.0	36.3	36.3
87.5°	16.9	17.7	16.7	16.1	16.1	16.9	17.5
90°	15.0	15.8	17.4	17.4	17.4	18.2	18.2
92.5°	101.6	76.4	64.7	54.6	52.7	51.6	50.4
95°	447.7	350.6	284.3	228.2	204.5	198.2	185.5
97.5°	761.3	666.7	574.5	525.7	481.5	458.6	448.5
100°	932.5	851.2	769.1	714.6	657.7	628.5	615.9
102.5°	1037.4	998.4	942.8	884.5	844.0	812.3	802.8
105°	1096.8	1131.6	1122.9	1097.5	1071.5	1055.7	1046.2
107.5°	1043.9	1133.1	1174.3	1187.1	1186.9	1181.7	1175.4
110°	983.8	1095.2	1162.3	1197.8	1212.8	1218.4	1218.4



TEST NUMBER: P333624-840

CATALOG NUMBER: S125RDIP-S1270D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	924.4	1037.0	1116.2	1168.1	1193.9	1207.6	1213.4
115°	839.4	947.6	1033.6	1095.2	1133.1	1155.2	1165.5
117.5°	780.4	873.6	952.6	1014.2	1053.3	1075.3	1081.6
120°	747.0	833.8	903.3	961.7	999.7	1021.0	1027.2
122.5°	723.0	800.3	865.5	917.6	952.3	973.6	979.3
125°	690.9	759.6	816.5	860.7	893.0	910.4	918.3
127.5°	660.2	724.4	777.6	817.7	846.3	862.7	866.2
130°	638.8	700.3	751.7	791.2	817.3	833.0	837.8
132.5°	618.5	674.5	723.9	763.4	789.4	804.0	809.3
135°	587.4	638.0	683.0	717.7	743.8	758.0	762.8
137.5°	559.7	601.7	639.9	671.1	694.7	707.8	713.1
140°	543.2	579.6	612.7	642.0	662.5	674.3	678.2
142.5°	529.4	560.6	589.4	614.2	631.6	642.8	646.0
145°	511.7	536.1	557.4	576.4	589.9	598.5	601.7
147.5°	497.0	515.7	531.9	546.8	557.6	562.7	564.1
150°	488.8	503.7	518.0	529.9	539.3	542.5	543.2
152.5°	480.6	494.3	505.3	515.3	522.9	526.0	526.8
155°	468.3	479.3	488.0	495.8	501.4	503.7	504.5
157.5°	456.6	465.0	471.9	478.1	482.6	484.8	484.6
160°	447.7	455.7	461.1	466.7	470.6	472.2	471.4
162.5°	440.1	446.8	451.6	456.0	459.2	459.6	459.4
165°	428.8	433.5	437.5	440.6	442.2	442.2	442.2
167.5°	417.7	421.3	424.1	425.8	427.2	426.6	426.4
170°	411.4	413.7	415.4	416.9	417.7	417.7	416.9
172.5°	405.7	407.5	408.4	408.7	410.1	408.9	408.1
175°	397.2	398.8	398.8	398.8	399.5	398.0	397.2
177.5°	393.5	393.5	393.5	392.9	393.5	391.6	391.6
180°	391.6	391.6	391.6	391.6	391.6	391.6	391.6

(END OF REPORT)