

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333509-840

Luminaire Tested: **S125RDIP-S375D1035U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333509-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1035U840-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5090.7 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270° - · - · 135°-315°



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	53	53	53	37	37	37	29				
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18				
4	71	61	53	48	63	55	48	44	44	39	35	33	30	28	23	22	20	16				
5	65	54	46	41	58	49	42	37	39	34	31	30	26	24	21	19	17	14				
6	60	48	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15	12				
7	55	44	36	31	50	40	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3672	3672	3672	3672
5°	4224	3676	3247	3676
10°	4845	3657	2865	3657
15°	5233	3620	2546	3620
20°	5770	3577	2351	3577
25°	6678	3518	2182	3518
30°	7267	3457	2071	3457
35°	6130	3387	1968	3387
40°	4281	3260	1881	3260
45°	3176	3088	1795	3088
50°	2533	2910	1721	2910
55°	2149	2688	1655	2688
60°	1856	2490	1550	2490
65°	1655	2275	1334	2275
70°	1456	2085	1216	2085
75°	1258	1804	1140	1804
80°	956	1517	956	1517
85°	793	1193	897	1193



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	1.1
10°-20°	159.7	3.1
20°-30°	253.3	5.0
30°-40°	305.4	6.0
40°-50°	272.8	5.4
50°-60°	209.2	4.1
60°-70°	135.9	2.7
70°-80°	66.1	1.3
80°-90°	18.6	0.4
90°-100°	86.8	1.7
100°-110°	256.2	5.0
110°-120°	434.0	8.5
120°-130°	571.2	11.2
130°-140°	640.0	12.6
140°-150°	627.3	12.3
150°-160°	526.9	10.3
160°-170°	350.2	6.9
170°-180°	122.6	2.4
0°-30°	467.5	9.2
0°-40°	773.0	15.2
0°-60°	1254.9	24.7
0°-90°	1475.6	29.0
90°-120°	777.0	15.3
90°-150°	2615.5	51.4
90°-180°	3615.0	71.0
0°-180°	5090.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	568	568	568	568	568	
5°	652	567	501	567	652	65
15°	783	541	381	541	783	224
25°	937	494	306	494	937	430
35°	778	430	250	430	778	470
45°	348	338	196	338	348	277
55°	191	239	147	239	191	173
65°	108	149	87	149	108	108
75°	50	72	46	72	50	54
85°	11	16	12	16	11	13
90°	24	1	24	1	24	14
95°	87	66	87	66	87	88
105°	250	230	250	230	250	265
115°	439	434	439	434	439	434
125°	638	634	638	634	638	570
135°	828	825	828	825	828	638
145°	1003	999	1003	999	1003	626
155°	1143	1143	1143	1143	1143	526
165°	1240	1243	1240	1243	1240	350
175°	1288	1292	1288	1292	1288	122
180°	1296	1296	1296	1296	1296	



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	597.9	597.5	598.3	596.2	596.4	593.3	593.3	590.9	587.6	585.2	584.1
5°	651.5	652.0	651.1	647.5	645.2	641.7	637.7	630.8	624.9	619.2	614.9
7.5°	706.7	707.0	703.9	702.9	696.9	692.7	683.9	674.3	665.9	655.1	646.9
10°	738.8	738.5	735.3	732.7	727.6	721.0	712.4	701.3	690.7	679.0	667.8
12.5°	757.4	756.8	755.8	752.7	747.9	742.1	734.8	723.8	710.8	698.1	685.0
15°	782.6	781.0	778.0	774.0	767.2	760.4	752.3	742.6	730.1	715.7	703.6
17.5°	813.9	813.9	809.2	803.7	794.5	782.5	769.9	754.2	737.3	721.4	708.5
20°	839.6	838.9	834.2	823.4	812.9	798.0	783.6	764.2	743.7	722.9	706.8
22.5°	876.6	874.7	869.9	855.8	839.5	820.2	798.1	774.5	749.6	726.1	704.9
25°	937.2	935.7	926.1	909.8	887.0	857.3	828.4	796.0	760.2	729.2	703.6
27.5°	978.6	977.0	969.9	956.3	935.2	904.0	864.9	821.5	777.0	734.3	697.3
30°	974.4	978.0	977.0	970.7	954.8	926.9	890.7	841.9	788.9	738.8	694.7
32.5°	915.8	919.0	927.2	939.6	940.5	929.3	902.2	857.2	802.3	745.3	692.6
35°	777.5	781.7	797.6	822.5	855.3	882.5	888.1	863.8	814.6	753.3	689.5
37.5°	597.7	620.7	634.1	660.4	709.7	759.9	808.2	826.0	805.1	749.9	684.6
40°	507.8	513.3	537.1	566.8	608.3	660.6	729.4	779.1	780.7	742.6	676.7
42.5°	434.5	441.7	458.0	481.7	517.3	569.5	640.6	706.2	736.5	722.0	666.4
45°	347.7	353.0	365.0	383.1	410.4	453.6	514.7	590.6	650.8	674.4	638.9
47.5°	285.6	288.5	298.8	312.8	333.0	364.4	411.7	477.6	549.8	600.4	595.4
50°	252.1	255.3	263.2	273.7	290.7	317.3	355.2	410.0	484.4	546.2	558.7
52.5°	225.9	228.6	233.6	243.5	257.5	277.9	308.5	358.1	425.1	490.8	519.5
55°	190.9	192.8	196.7	202.3	213.5	228.2	254.6	288.9	343.1	409.3	451.3
57.5°	162.1	163.0	165.5	170.7	178.4	189.1	208.2	237.2	276.1	335.8	382.1
60°	143.7	144.7	147.9	151.5	157.5	167.3	182.3	202.6	239.8	289.1	336.0
62.5°	129.2	129.8	131.2	134.6	140.0	147.5	159.3	175.8	205.5	248.8	293.1
65°	108.3	108.5	109.0	111.8	115.0	120.7	128.4	140.0	162.4	195.1	234.3
67.5°	88.2	88.6	90.2	91.2	94.5	97.5	102.0	110.9	126.7	148.8	179.3
70°	77.1	76.7	78.4	79.6	80.7	84.2	87.3	94.5	104.3	121.1	146.5
72.5°	66.6	65.9	66.7	67.1	68.6	71.0	74.0	78.5	86.0	97.6	117.0
75°	50.4	50.6	50.6	51.1	52.3	53.2	54.1	56.5	60.7	68.4	78.9
77.5°	35.3	35.0	36.0	36.2	36.9	37.9	38.7	39.6	41.3	44.4	49.9
80°	25.7	25.7	25.9	26.6	26.4	26.9	28.0	29.0	31.0	32.9	34.7
82.5°	19.7	19.5	19.7	19.9	19.8	20.3	20.7	20.9	21.7	22.6	23.9
85°	10.7	10.7	11.0	11.0	11.2	11.2	11.4	11.4	11.4	11.7	11.9
87.5°	9.0	8.6	8.3	8.2	8.2	8.4	8.0	7.6	7.4	7.2	7.1
90°	24.2	23.5	22.8	22.2	21.5	20.6	19.5	18.4	17.3	16.2	14.5
92.5°	47.6	47.1	46.6	46.2	45.6	44.6	43.1	41.7	40.2	38.7	36.8
95°	86.7	86.2	85.8	85.3	84.9	83.9	82.3	80.8	79.2	77.7	75.4
97.5°	131.5	131.2	131.0	130.7	130.4	129.6	128.1	126.5	125.1	123.6	120.5
100°	165.3	164.9	164.4	164.0	163.6	162.3	160.3	158.2	156.2	154.2	151.4
102.5°	199.2	198.6	197.9	197.3	196.7	195.3	193.1	190.9	188.7	186.5	185.0
105°	250.0	249.3	248.7	248.0	247.3	246.3	245.0	243.7	242.3	241.0	239.6
107.5°	302.1	302.2	302.2	302.2	302.3	301.9	301.2	300.5	299.9	299.2	298.2
110°	340.7	341.0	341.2	341.4	341.6	341.4	340.7	340.1	339.4	338.7	338.1



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.7	379.1	379.5	379.9	380.3	380.3	380.0	379.7	379.4	379.1	378.2
115°	438.6	438.8	439.0	439.2	439.5	439.7	439.9	440.1	440.4	440.6	440.1
117.5°	497.1	498.0	498.9	499.7	500.6	501.0	500.8	500.6	500.5	500.3	499.9
120°	537.3	538.3	539.2	540.1	541.0	541.4	541.4	541.4	541.4	541.4	541.2
122.5°	577.7	578.5	579.2	579.9	580.6	581.0	581.2	581.4	581.6	581.7	581.2
125°	638.2	638.4	638.6	638.8	639.0	639.4	639.9	640.4	640.8	641.3	641.0
127.5°	696.3	696.7	697.1	697.6	698.0	698.4	698.6	698.8	699.0	699.3	699.0
130°	735.0	735.4	735.9	736.3	736.8	737.1	737.3	737.5	737.8	738.0	737.5
132.5°	771.2	771.9	772.5	773.2	773.8	774.2	774.5	774.7	774.9	775.1	775.2
135°	827.7	828.6	829.5	830.4	831.3	831.7	831.7	831.7	831.7	831.7	831.5
137.5°	883.0	884.1	885.2	886.4	887.5	887.9	887.6	887.4	887.1	886.8	886.4
140°	918.5	919.6	920.7	921.8	922.9	923.3	922.8	922.4	921.9	921.5	920.8
142.5°	952.3	953.5	954.6	955.7	956.8	957.3	956.9	956.7	956.4	956.1	955.3
145°	1003.2	1003.8	1004.5	1005.2	1005.8	1006.2	1006.2	1006.2	1006.2	1006.2	1005.5
147.5°	1046.5	1048.0	1049.6	1051.1	1052.6	1053.1	1052.6	1052.0	1051.5	1051.0	1050.4
150°	1078.7	1079.2	1079.6	1080.2	1080.6	1080.8	1080.8	1080.8	1080.8	1080.8	1079.8
152.5°	1105.4	1106.2	1107.0	1107.8	1108.6	1108.7	1108.2	1107.7	1107.1	1106.6	1106.2
155°	1143.3	1144.4	1145.5	1146.7	1147.8	1147.9	1147.0	1146.1	1145.2	1144.3	1144.1
157.5°	1175.0	1176.4	1177.9	1179.4	1180.8	1181.1	1180.2	1179.3	1178.5	1177.6	1177.4
160°	1196.7	1197.9	1199.0	1200.1	1201.2	1201.3	1200.4	1199.5	1198.6	1197.7	1197.5
162.5°	1215.3	1216.6	1217.9	1219.2	1220.5	1220.6	1219.5	1218.4	1217.4	1216.3	1216.3
165°	1240.1	1241.4	1242.7	1244.2	1245.5	1245.7	1244.8	1243.9	1243.0	1242.1	1241.8
167.5°	1259.8	1261.2	1262.6	1264.0	1265.4	1265.5	1264.0	1262.7	1261.4	1260.0	1260.0
170°	1270.3	1271.9	1273.4	1275.1	1276.6	1276.7	1275.4	1274.0	1272.7	1271.3	1271.3
172.5°	1279.2	1280.6	1282.0	1283.3	1284.8	1284.8	1283.4	1282.1	1280.7	1279.4	1279.4
175°	1287.5	1289.0	1290.6	1292.2	1293.7	1293.8	1292.5	1291.2	1289.8	1288.5	1288.5
177.5°	1292.3	1293.5	1294.8	1296.1	1297.4	1297.4	1296.4	1295.3	1294.2	1293.1	1293.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	584.1	582.8	580.4	578.1	575.3	572.9	571.2	569.2	566.5	563.4	560.8
5°	610.0	604.8	598.0	592.2	584.7	579.0	572.9	567.0	561.2	553.7	547.1
7.5°	638.6	628.0	617.7	604.7	593.0	582.5	572.4	562.2	552.2	541.6	531.4
10°	656.2	643.3	629.1	612.8	597.8	583.6	570.6	557.6	544.1	532.3	519.5
12.5°	672.6	656.0	639.7	619.1	601.2	583.8	567.1	551.2	536.7	521.3	507.5
15°	687.4	671.1	652.9	627.7	602.7	581.7	562.1	541.4	523.4	506.1	490.7
17.5°	693.2	676.0	654.9	630.7	603.4	576.9	551.7	529.0	507.8	487.7	470.4
20°	690.9	674.4	652.7	629.5	600.4	572.9	545.5	520.4	496.8	475.5	457.2
22.5°	685.5	668.4	647.4	623.0	595.3	566.1	536.9	510.1	485.4	463.4	443.3
25°	677.4	654.1	632.6	608.7	582.4	553.5	523.4	493.7	467.4	444.9	423.0
27.5°	668.9	639.9	612.5	588.9	561.0	535.2	506.1	475.7	448.1	425.3	402.7
30°	661.3	628.6	598.5	571.7	545.3	520.8	493.3	463.6	435.2	411.6	388.8
32.5°	651.8	617.0	584.0	553.0	527.6	503.3	478.4	450.0	422.3	398.0	374.8
35°	639.9	595.5	559.6	526.6	498.5	474.8	452.4	429.6	401.8	376.6	354.0
37.5°	624.2	573.8	532.3	496.4	466.7	443.0	425.3	404.3	379.0	355.0	334.0
40°	614.6	558.2	512.7	477.2	446.0	420.9	404.3	386.7	363.6	340.9	319.9
42.5°	602.0	543.8	492.9	456.0	424.4	400.4	383.6	368.2	348.8	327.5	305.0
45°	577.0	515.9	462.5	422.8	391.1	367.5	351.8	338.1	323.5	303.8	284.2
47.5°	544.7	486.9	430.9	387.6	356.6	334.7	319.5	308.6	298.1	281.4	262.5
50°	518.8	462.9	408.4	366.4	333.3	312.5	298.2	289.6	280.0	264.9	248.9
52.5°	488.1	438.3	384.9	341.9	310.6	291.1	277.5	268.8	260.9	248.6	233.5
55°	439.9	396.2	347.2	308.2	279.5	259.9	246.9	238.7	234.1	223.6	211.7
57.5°	384.2	352.9	309.7	272.2	246.7	227.4	217.8	210.9	205.6	198.1	189.8
60°	345.4	323.5	284.7	248.9	225.6	207.2	198.5	192.8	187.8	181.6	175.0
62.5°	306.0	290.0	256.3	225.6	204.2	188.7	180.7	175.4	169.8	165.5	159.2
65°	253.2	238.9	215.6	191.6	171.8	159.4	153.5	148.9	145.4	140.7	136.2
67.5°	196.9	191.2	175.0	158.4	144.2	133.2	128.2	124.9	120.8	118.0	114.9
70°	162.4	159.6	148.1	137.2	123.9	116.4	111.8	110.4	105.2	102.4	100.4
72.5°	131.8	130.5	123.9	116.3	106.9	100.4	96.1	94.5	91.2	89.0	87.7
75°	90.3	90.8	89.6	84.7	81.2	77.1	73.3	72.3	70.0	68.2	67.0
77.5°	57.2	59.5	59.6	59.4	58.0	55.4	53.8	53.1	50.9	50.2	49.9
80°	39.2	41.8	44.1	43.8	43.4	42.7	41.5	40.8	39.7	39.0	38.5
82.5°	26.2	28.5	30.5	31.7	31.6	30.9	30.2	29.8	29.6	29.1	29.0
85°	12.3	12.8	13.5	15.1	16.4	16.6	16.4	16.1	15.5	15.7	15.9
87.5°	6.9	6.6	6.5	6.2	5.6	6.2	6.4	6.2	6.2	6.2	6.2
90°	13.0	11.4	9.9	8.2	6.4	4.5	2.8	1.0	2.8	4.5	6.4
92.5°	34.8	32.9	31.0	29.4	28.2	26.9	25.7	24.4	25.7	26.9	28.2
95°	73.1	70.9	68.7	67.4	66.9	66.4	65.9	65.5	65.9	66.4	66.9
97.5°	117.4	114.3	111.3	109.6	109.5	109.3	109.1	108.9	109.1	109.3	109.5
100°	148.5	145.5	142.6	141.2	141.2	141.2	141.2	141.2	141.2	141.2	141.2
102.5°	183.6	182.1	180.6	179.5	178.5	177.6	176.7	175.8	176.7	177.6	178.5
105°	238.2	236.9	235.6	234.4	233.3	232.1	231.0	229.8	231.0	232.1	233.3
107.5°	297.2	296.1	295.1	294.1	293.0	291.8	290.6	289.5	290.6	291.8	293.0
110°	337.4	336.7	336.1	335.2	334.1	333.0	331.8	330.7	331.8	333.0	334.1



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	377.4	376.6	375.7	375.0	374.4	373.8	373.2	372.6	373.2	373.8	374.4
115°	439.7	439.2	438.8	438.1	437.3	436.4	435.5	434.5	435.5	436.4	437.3
117.5°	499.5	499.1	498.7	498.3	497.9	497.5	497.1	496.7	497.1	497.5	497.9
120°	541.0	540.7	540.5	539.9	538.8	537.6	536.4	535.3	536.4	537.6	538.8
122.5°	580.6	580.0	579.4	579.0	578.6	578.1	577.7	577.3	577.7	578.1	578.6
125°	640.8	640.6	640.4	639.5	638.2	636.8	635.5	634.2	635.5	636.8	638.2
127.5°	698.7	698.5	698.2	697.7	696.9	696.2	695.4	694.7	695.4	696.2	696.9
130°	737.1	736.7	736.2	735.4	734.3	733.2	732.1	730.9	732.1	733.2	734.3
132.5°	775.3	775.4	775.5	774.6	772.7	770.9	769.1	767.2	769.1	770.9	772.7
135°	831.3	831.1	830.9	830.1	828.7	827.4	826.1	824.8	826.1	827.4	828.7
137.5°	885.9	885.3	884.8	883.9	882.6	881.3	880.0	878.8	880.0	881.3	882.6
140°	920.2	919.5	918.8	917.9	916.8	915.6	914.5	913.4	914.5	915.6	916.8
142.5°	954.5	953.6	952.8	951.9	950.9	950.0	949.1	948.1	949.1	950.0	950.9
145°	1004.8	1004.2	1003.5	1002.7	1001.8	1000.9	1000.1	999.2	1000.1	1000.9	1001.8
147.5°	1049.9	1049.4	1048.8	1048.2	1047.8	1047.3	1046.8	1046.3	1046.8	1047.3	1047.8
150°	1079.0	1078.1	1077.2	1076.9	1077.1	1077.3	1077.5	1077.7	1077.5	1077.3	1077.1
152.5°	1105.9	1105.5	1105.2	1104.8	1104.5	1104.2	1103.9	1103.6	1103.9	1104.2	1104.5
155°	1143.9	1143.7	1143.4	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3
157.5°	1177.1	1176.9	1176.7	1176.8	1177.3	1177.8	1178.3	1178.8	1178.3	1177.8	1177.3
160°	1197.3	1197.1	1196.9	1197.1	1197.7	1198.4	1199.1	1199.7	1199.1	1198.4	1197.7
162.5°	1216.2	1216.2	1216.1	1216.4	1216.8	1217.3	1217.8	1218.3	1217.8	1217.3	1216.8
165°	1241.6	1241.4	1241.2	1241.3	1241.7	1242.2	1242.6	1243.1	1242.6	1242.2	1241.7
167.5°	1260.0	1260.0	1260.0	1260.5	1261.4	1262.3	1263.1	1264.0	1263.1	1262.3	1261.4
170°	1271.3	1271.3	1271.3	1271.8	1272.7	1273.5	1274.4	1275.4	1274.4	1273.5	1272.7
172.5°	1279.4	1279.4	1279.4	1279.9	1280.7	1281.6	1282.5	1283.4	1282.5	1281.6	1280.7
175°	1288.5	1288.5	1288.5	1288.9	1289.8	1290.7	1291.6	1292.5	1291.6	1290.7	1289.8
177.5°	1293.4	1293.6	1293.8	1294.2	1294.9	1295.8	1296.5	1297.2	1296.5	1295.8	1294.9
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	558.9	556.3	554.4	550.7	548.1	546.9	544.9	544.3	546.4	544.9	544.7
5°	542.3	535.5	530.2	524.8	519.0	515.2	509.6	508.7	507.3	505.2	504.7
7.5°	522.4	513.5	506.6	497.8	490.1	483.8	476.9	473.5	471.7	469.0	465.3
10°	509.0	498.5	489.1	480.2	470.7	462.9	456.0	450.6	447.1	443.8	442.4
12.5°	495.6	484.9	473.0	462.3	451.6	443.0	435.3	431.7	427.9	424.0	420.8
15°	475.0	460.9	447.8	435.5	426.4	417.0	409.5	404.3	398.6	396.9	390.6
17.5°	453.2	439.3	423.9	411.0	400.4	390.1	381.9	376.1	371.7	365.7	362.8
20°	439.6	423.0	408.1	396.2	384.6	372.4	364.1	359.1	355.0	350.0	347.7
22.5°	425.1	408.9	393.5	379.6	367.8	355.8	349.8	344.8	340.0	335.5	332.3
25°	403.6	387.4	371.2	356.8	344.5	335.8	328.8	323.0	320.4	316.0	312.7
27.5°	382.5	365.2	348.5	334.1	324.4	315.8	310.0	305.5	300.8	297.0	294.1
30°	368.9	351.2	333.0	321.5	311.2	303.2	296.8	292.4	288.9	285.4	283.3
32.5°	355.3	337.0	320.8	308.5	298.8	291.8	285.3	280.9	277.3	273.5	270.9
35°	333.5	314.8	301.7	289.6	280.0	273.5	269.0	263.0	259.9	257.1	254.6
37.5°	313.2	295.8	281.7	271.0	262.7	256.2	250.4	247.2	243.5	241.0	238.8
40°	298.2	282.4	269.5	258.3	252.3	245.0	239.6	235.4	232.7	229.3	227.0
42.5°	284.8	270.0	257.5	247.5	239.9	233.8	228.6	224.4	220.9	218.5	216.6
45°	265.8	251.1	238.9	229.6	222.6	216.8	211.4	209.3	204.6	201.9	200.9
47.5°	246.1	233.0	221.3	212.7	205.5	200.0	194.9	190.7	188.0	185.3	183.8
50°	232.9	220.3	209.3	200.9	193.9	187.8	183.2	180.4	176.8	174.3	172.5
52.5°	219.6	207.9	197.0	188.9	182.9	176.8	171.6	168.8	165.5	163.9	162.6
55°	200.7	188.3	178.9	171.1	164.7	159.2	154.2	151.5	149.4	147.7	147.2
57.5°	179.3	169.5	160.8	153.6	147.0	141.8	137.4	134.8	133.0	132.7	131.3
60°	165.2	156.3	148.5	140.7	135.1	130.2	126.4	123.4	121.6	121.4	120.9
62.5°	151.2	142.7	135.3	128.6	123.5	118.9	115.2	111.9	110.8	109.6	108.6
65°	130.5	122.7	116.6	111.3	105.9	102.0	98.5	96.3	93.8	92.4	89.9
67.5°	110.1	104.1	98.3	93.7	89.5	85.7	82.8	79.7	78.0	76.9	75.0
70°	96.6	91.9	86.1	81.2	78.0	74.9	72.6	69.1	67.9	67.0	66.0
72.5°	83.9	79.8	74.9	70.9	67.7	64.8	62.1	60.5	59.3	58.4	57.9
75°	66.0	62.1	57.9	55.0	52.7	50.4	49.0	47.9	47.4	47.2	46.3
77.5°	48.5	46.4	43.0	40.8	39.3	38.3	37.1	36.5	36.4	35.3	35.0
80°	37.1	36.0	33.1	32.2	31.0	30.1	29.4	28.3	27.1	26.6	25.9
82.5°	27.6	26.5	25.2	23.8	22.8	22.2	21.6	21.1	21.3	20.6	20.3
85°	14.7	13.5	13.0	12.8	12.3	12.8	12.6	12.3	12.1	11.9	12.1
87.5°	6.3	6.7	6.8	7.5	7.2	7.7	8.0	8.0	8.2	8.4	8.4
90°	8.2	9.9	11.4	13.0	14.5	16.2	17.3	18.4	19.5	20.6	21.5
92.5°	29.4	31.0	32.9	34.8	36.8	38.7	40.2	41.7	43.1	44.6	45.6
95°	67.4	68.7	70.9	73.1	75.4	77.7	79.2	80.8	82.3	83.9	84.9
97.5°	109.6	111.3	114.3	117.4	120.5	123.6	125.1	126.5	128.1	129.6	130.4
100°	141.2	142.6	145.5	148.5	151.4	154.2	156.2	158.2	160.3	162.3	163.6
102.5°	179.5	180.6	182.1	183.6	185.0	186.5	188.7	190.9	193.1	195.3	196.7
105°	234.4	235.6	236.9	238.2	239.6	241.0	242.3	243.7	245.0	246.3	247.3
107.5°	294.1	295.1	296.1	297.2	298.2	299.2	299.9	300.5	301.2	301.9	302.3
110°	335.2	336.1	336.7	337.4	338.1	338.7	339.4	340.1	340.7	341.4	341.6



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	375.0	375.7	376.6	377.4	378.2	379.1	379.4	379.7	380.0	380.3	380.3
115°	438.1	438.8	439.2	439.7	440.1	440.6	440.4	440.1	439.9	439.7	439.5
117.5°	498.3	498.7	499.1	499.5	499.9	500.3	500.5	500.6	500.8	501.0	500.6
120°	539.9	540.5	540.7	541.0	541.2	541.4	541.4	541.4	541.4	541.4	541.0
122.5°	579.0	579.4	580.0	580.6	581.2	581.7	581.6	581.4	581.2	581.0	580.6
125°	639.5	640.4	640.6	640.8	641.0	641.3	640.8	640.4	639.9	639.4	639.0
127.5°	697.7	698.2	698.5	698.7	699.0	699.3	699.0	698.8	698.6	698.4	698.0
130°	735.4	736.2	736.7	737.1	737.5	738.0	737.8	737.5	737.3	737.1	736.8
132.5°	774.6	775.5	775.4	775.3	775.2	775.1	774.9	774.7	774.5	774.2	773.8
135°	830.1	830.9	831.1	831.3	831.5	831.7	831.7	831.7	831.7	831.7	831.3
137.5°	883.9	884.8	885.3	885.9	886.4	886.8	887.1	887.4	887.6	887.9	887.5
140°	917.9	918.8	919.5	920.2	920.8	921.5	921.9	922.4	922.8	923.3	922.9
142.5°	951.9	952.8	953.6	954.5	955.3	956.1	956.4	956.7	956.9	957.3	956.8
145°	1002.7	1003.5	1004.2	1004.8	1005.5	1006.2	1006.2	1006.2	1006.2	1006.2	1005.8
147.5°	1048.2	1048.8	1049.4	1049.9	1050.4	1051.0	1051.5	1052.0	1052.6	1053.1	1052.6
150°	1076.9	1077.2	1078.1	1079.0	1079.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.6
152.5°	1104.8	1105.2	1105.5	1105.9	1106.2	1106.6	1107.1	1107.7	1108.2	1108.7	1108.6
155°	1143.3	1143.4	1143.7	1143.9	1144.1	1144.3	1145.2	1146.1	1147.0	1147.9	1147.8
157.5°	1176.8	1176.7	1176.9	1177.1	1177.4	1177.6	1178.5	1179.3	1180.2	1181.1	1180.8
160°	1197.1	1196.9	1197.1	1197.3	1197.5	1197.7	1198.6	1199.5	1200.4	1201.3	1201.2
162.5°	1216.4	1216.1	1216.2	1216.2	1216.3	1216.3	1217.4	1218.4	1219.5	1220.6	1220.5
165°	1241.3	1241.2	1241.4	1241.6	1241.8	1242.1	1243.0	1243.9	1244.8	1245.7	1245.5
167.5°	1260.5	1260.0	1260.0	1260.0	1260.0	1260.0	1261.4	1262.7	1264.0	1265.5	1265.4
170°	1271.8	1271.3	1271.3	1271.3	1271.3	1271.3	1272.7	1274.0	1275.4	1276.7	1276.6
172.5°	1279.9	1279.4	1279.4	1279.4	1279.4	1279.4	1280.7	1282.1	1283.4	1284.8	1284.8
175°	1288.9	1288.5	1288.5	1288.5	1288.5	1288.5	1289.8	1291.2	1292.5	1293.8	1293.7
177.5°	1294.2	1293.8	1293.6	1293.4	1293.3	1293.1	1294.2	1295.3	1296.4	1297.4	1297.4
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.5	542.5	541.9	542.7	541.9	542.5	544.5	544.7	544.9	546.4	544.3
5°	502.4	500.1	501.2	500.8	501.2	500.1	502.4	504.7	505.2	507.3	508.7
7.5°	465.3	462.4	459.4	460.3	459.4	462.4	465.3	465.3	469.0	471.7	473.5
10°	439.4	437.1	435.7	436.9	435.7	437.1	439.4	442.4	443.8	447.1	450.6
12.5°	417.6	416.2	415.0	414.4	415.0	416.2	417.6	420.8	424.0	427.9	431.7
15°	387.8	385.1	383.8	380.8	383.8	385.1	387.8	390.6	396.9	398.6	404.3
17.5°	360.4	359.5	356.5	355.2	356.5	359.5	360.4	362.8	365.7	371.7	376.1
20°	344.2	343.3	340.2	342.0	340.2	343.3	344.2	347.7	350.0	355.0	359.1
22.5°	330.7	328.7	327.7	327.2	327.7	328.7	330.7	332.3	335.5	340.0	344.8
25°	311.7	308.7	307.5	306.2	307.5	308.7	311.7	312.7	316.0	320.4	323.0
27.5°	292.8	291.1	289.6	289.2	289.6	291.1	292.8	294.1	297.0	300.8	305.5
30°	280.4	278.8	277.7	277.7	277.7	278.8	280.4	283.3	285.4	288.9	292.4
32.5°	269.4	268.2	267.0	266.8	267.0	268.2	269.4	270.9	273.5	277.3	280.9
35°	253.4	251.6	251.1	249.6	251.1	251.6	253.4	254.6	257.1	259.9	263.0
37.5°	236.7	235.2	235.2	235.0	235.2	235.2	236.7	238.8	241.0	243.5	247.2
40°	226.1	224.9	224.7	223.1	224.7	224.9	226.1	227.0	229.3	232.7	235.4
42.5°	214.7	214.1	213.3	212.6	213.3	214.1	214.7	216.6	218.5	220.9	224.4
45°	199.2	197.6	197.6	196.5	197.6	197.6	199.2	200.9	201.9	204.6	209.3
47.5°	183.3	182.1	182.2	181.0	182.2	182.1	183.3	183.8	185.3	188.0	190.7
50°	172.7	172.0	171.8	171.3	171.8	172.0	172.7	172.5	174.3	176.8	180.4
52.5°	162.1	161.7	162.6	161.6	162.6	161.7	162.1	162.6	163.9	165.5	168.8
55°	147.7	147.0	148.5	147.0	148.5	147.0	147.7	147.2	147.7	149.4	151.5
57.5°	131.3	130.6	131.9	131.2	131.9	130.6	131.3	131.3	132.7	133.0	134.8
60°	120.4	119.0	119.7	120.0	119.7	119.0	120.4	120.9	121.4	121.6	123.4
62.5°	107.6	106.6	107.2	106.1	107.2	106.6	107.6	108.6	109.6	110.8	111.9
65°	89.4	88.7	87.8	87.3	87.8	88.7	89.4	89.9	92.4	93.8	96.3
67.5°	75.1	73.4	73.3	73.7	73.3	73.4	75.1	75.0	76.9	78.0	79.7
70°	64.6	64.6	64.4	64.4	64.4	64.6	64.6	66.0	67.0	67.9	69.1
72.5°	57.4	57.2	56.8	56.6	56.8	57.2	57.4	57.9	58.4	59.3	60.5
75°	46.3	46.5	45.9	45.7	45.9	46.5	46.3	46.3	47.2	47.4	47.9
77.5°	34.1	33.1	33.6	33.1	33.6	33.1	34.1	35.0	35.3	36.4	36.5
80°	25.9	25.7	26.4	25.7	26.4	25.7	25.9	25.9	26.6	27.1	28.3
82.5°	20.5	20.3	20.6	20.1	20.6	20.3	20.5	20.3	20.6	21.3	21.1
85°	12.3	12.1	11.9	12.1	11.9	12.1	12.3	12.1	11.9	12.1	12.3
87.5°	8.7	8.7	8.8	9.0	8.8	8.7	8.7	8.4	8.4	8.2	8.0
90°	22.2	22.8	23.5	24.2	23.5	22.8	22.2	21.5	20.6	19.5	18.4
92.5°	46.2	46.6	47.1	47.6	47.1	46.6	46.2	45.6	44.6	43.1	41.7
95°	85.3	85.8	86.2	86.7	86.2	85.8	85.3	84.9	83.9	82.3	80.8
97.5°	130.7	131.0	131.2	131.5	131.2	131.0	130.7	130.4	129.6	128.1	126.5
100°	164.0	164.4	164.9	165.3	164.9	164.4	164.0	163.6	162.3	160.3	158.2
102.5°	197.3	197.9	198.6	199.2	198.6	197.9	197.3	196.7	195.3	193.1	190.9
105°	248.0	248.7	249.3	250.0	249.3	248.7	248.0	247.3	246.3	245.0	243.7
107.5°	302.2	302.2	302.2	302.1	302.2	302.2	302.2	302.3	301.9	301.2	300.5
110°	341.4	341.2	341.0	340.7	341.0	341.2	341.4	341.6	341.4	340.7	340.1



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	379.9	379.5	379.1	378.7	379.1	379.5	379.9	380.3	380.3	380.0	379.7
115°	439.2	439.0	438.8	438.6	438.8	439.0	439.2	439.5	439.7	439.9	440.1
117.5°	499.7	498.9	498.0	497.1	498.0	498.9	499.7	500.6	501.0	500.8	500.6
120°	540.1	539.2	538.3	537.3	538.3	539.2	540.1	541.0	541.4	541.4	541.4
122.5°	579.9	579.2	578.5	577.7	578.5	579.2	579.9	580.6	581.0	581.2	581.4
125°	638.8	638.6	638.4	638.2	638.4	638.6	638.8	639.0	639.4	639.9	640.4
127.5°	697.6	697.1	696.7	696.3	696.7	697.1	697.6	698.0	698.4	698.6	698.8
130°	736.3	735.9	735.4	735.0	735.4	735.9	736.3	736.8	737.1	737.3	737.5
132.5°	773.2	772.5	771.9	771.2	771.9	772.5	773.2	773.8	774.2	774.5	774.7
135°	830.4	829.5	828.6	827.7	828.6	829.5	830.4	831.3	831.7	831.7	831.7
137.5°	886.4	885.2	884.1	883.0	884.1	885.2	886.4	887.5	887.9	887.6	887.4
140°	921.8	920.7	919.6	918.5	919.6	920.7	921.8	922.9	923.3	922.8	922.4
142.5°	955.7	954.6	953.5	952.3	953.5	954.6	955.7	956.8	957.3	956.9	956.7
145°	1005.2	1004.5	1003.8	1003.2	1003.8	1004.5	1005.2	1005.8	1006.2	1006.2	1006.2
147.5°	1051.1	1049.6	1048.0	1046.5	1048.0	1049.6	1051.1	1052.6	1053.1	1052.6	1052.0
150°	1080.2	1079.6	1079.2	1078.7	1079.2	1079.6	1080.2	1080.6	1080.8	1080.8	1080.8
152.5°	1107.8	1107.0	1106.2	1105.4	1106.2	1107.0	1107.8	1108.6	1108.7	1108.2	1107.7
155°	1146.7	1145.5	1144.4	1143.3	1144.4	1145.5	1146.7	1147.8	1147.9	1147.0	1146.1
157.5°	1179.4	1177.9	1176.4	1175.0	1176.4	1177.9	1179.4	1180.8	1181.1	1180.2	1179.3
160°	1200.1	1199.0	1197.9	1196.7	1197.9	1199.0	1200.1	1201.2	1201.3	1200.4	1199.5
162.5°	1219.2	1217.9	1216.6	1215.3	1216.6	1217.9	1219.2	1220.5	1220.6	1219.5	1218.4
165°	1244.2	1242.7	1241.4	1240.1	1241.4	1242.7	1244.2	1245.5	1245.7	1244.8	1243.9
167.5°	1264.0	1262.6	1261.2	1259.8	1261.2	1262.6	1264.0	1265.4	1265.5	1264.0	1262.7
170°	1275.1	1273.4	1271.9	1270.3	1271.9	1273.4	1275.1	1276.6	1276.7	1275.4	1274.0
172.5°	1283.3	1282.0	1280.6	1279.2	1280.6	1282.0	1283.3	1284.8	1284.8	1283.4	1282.1
175°	1292.2	1290.6	1289.0	1287.5	1289.0	1290.6	1292.2	1293.7	1293.8	1292.5	1291.2
177.5°	1296.1	1294.8	1293.5	1292.3	1293.5	1294.8	1296.1	1297.4	1297.4	1296.4	1295.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.9	546.9	548.1	550.7	554.4	556.3	558.9	560.8	563.4	566.5	569.2
5°	509.6	515.2	519.0	524.8	530.2	535.5	542.3	547.1	553.7	561.2	567.0
7.5°	476.9	483.8	490.1	497.8	506.6	513.5	522.4	531.4	541.6	552.2	562.2
10°	456.0	462.9	470.7	480.2	489.1	498.5	509.0	519.5	532.3	544.1	557.6
12.5°	435.3	443.0	451.6	462.3	473.0	484.9	495.6	507.5	521.3	536.7	551.2
15°	409.5	417.0	426.4	435.5	447.8	460.9	475.0	490.7	506.1	523.4	541.4
17.5°	381.9	390.1	400.4	411.0	423.9	439.3	453.2	470.4	487.7	507.8	529.0
20°	364.1	372.4	384.6	396.2	408.1	423.0	439.6	457.2	475.5	496.8	520.4
22.5°	349.8	355.8	367.8	379.6	393.5	408.9	425.1	443.3	463.4	485.4	510.1
25°	328.8	335.8	344.5	356.8	371.2	387.4	403.6	423.0	444.9	467.4	493.7
27.5°	310.0	315.8	324.4	334.1	348.5	365.2	382.5	402.7	425.3	448.1	475.7
30°	296.8	303.2	311.2	321.5	333.0	351.2	368.9	388.8	411.6	435.2	463.6
32.5°	285.3	291.8	298.8	308.5	320.8	337.0	355.3	374.8	398.0	422.3	450.0
35°	269.0	273.5	280.0	289.6	301.7	314.8	333.5	354.0	376.6	401.8	429.6
37.5°	250.4	256.2	262.7	271.0	281.7	295.8	313.2	334.0	355.0	379.0	404.3
40°	239.6	245.0	252.3	258.3	269.5	282.4	298.2	319.9	340.9	363.6	386.7
42.5°	228.6	233.8	239.9	247.5	257.5	270.0	284.8	305.0	327.5	348.8	368.2
45°	211.4	216.8	222.6	229.6	238.9	251.1	265.8	284.2	303.8	323.5	338.1
47.5°	194.9	200.0	205.5	212.7	221.3	233.0	246.1	262.5	281.4	298.1	308.6
50°	183.2	187.8	193.9	200.9	209.3	220.3	232.9	248.9	264.9	280.0	289.6
52.5°	171.6	176.8	182.9	188.9	197.0	207.9	219.6	233.5	248.6	260.9	268.8
55°	154.2	159.2	164.7	171.1	178.9	188.3	200.7	211.7	223.6	234.1	238.7
57.5°	137.4	141.8	147.0	153.6	160.8	169.5	179.3	189.8	198.1	205.6	210.9
60°	126.4	130.2	135.1	140.7	148.5	156.3	165.2	175.0	181.6	187.8	192.8
62.5°	115.2	118.9	123.5	128.6	135.3	142.7	151.2	159.2	165.5	169.8	175.4
65°	98.5	102.0	105.9	111.3	116.6	122.7	130.5	136.2	140.7	145.4	148.9
67.5°	82.8	85.7	89.5	93.7	98.3	104.1	110.1	114.9	118.0	120.8	124.9
70°	72.6	74.9	78.0	81.2	86.1	91.9	96.6	100.4	102.4	105.2	110.4
72.5°	62.1	64.8	67.7	70.9	74.9	79.8	83.9	87.7	89.0	91.2	94.5
75°	49.0	50.4	52.7	55.0	57.9	62.1	66.0	67.0	68.2	70.0	72.3
77.5°	37.1	38.3	39.3	40.8	43.0	46.4	48.5	49.9	50.2	50.9	53.1
80°	29.4	30.1	31.0	32.2	33.1	36.0	37.1	38.5	39.0	39.7	40.8
82.5°	21.6	22.2	22.8	23.8	25.2	26.5	27.6	29.0	29.1	29.6	29.8
85°	12.6	12.8	12.3	12.8	13.0	13.5	14.7	15.9	15.7	15.5	16.1
87.5°	8.0	7.7	7.2	7.5	6.8	6.7	6.3	6.2	6.2	6.2	6.2
90°	17.3	16.2	14.5	13.0	11.4	9.9	8.2	6.4	4.5	2.8	1.0
92.5°	40.2	38.7	36.8	34.8	32.9	31.0	29.4	28.2	26.9	25.7	24.4
95°	79.2	77.7	75.4	73.1	70.9	68.7	67.4	66.9	66.4	65.9	65.5
97.5°	125.1	123.6	120.5	117.4	114.3	111.3	109.6	109.5	109.3	109.1	108.9
100°	156.2	154.2	151.4	148.5	145.5	142.6	141.2	141.2	141.2	141.2	141.2
102.5°	188.7	186.5	185.0	183.6	182.1	180.6	179.5	178.5	177.6	176.7	175.8
105°	242.3	241.0	239.6	238.2	236.9	235.6	234.4	233.3	232.1	231.0	229.8
107.5°	299.9	299.2	298.2	297.2	296.1	295.1	294.1	293.0	291.8	290.6	289.5
110°	339.4	338.7	338.1	337.4	336.7	336.1	335.2	334.1	333.0	331.8	330.7



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	379.4	379.1	378.2	377.4	376.6	375.7	375.0	374.4	373.8	373.2	372.6
115°	440.4	440.6	440.1	439.7	439.2	438.8	438.1	437.3	436.4	435.5	434.5
117.5°	500.5	500.3	499.9	499.5	499.1	498.7	498.3	497.9	497.5	497.1	496.7
120°	541.4	541.4	541.2	541.0	540.7	540.5	539.9	538.8	537.6	536.4	535.3
122.5°	581.6	581.7	581.2	580.6	580.0	579.4	579.0	578.6	578.1	577.7	577.3
125°	640.8	641.3	641.0	640.8	640.6	640.4	639.5	638.2	636.8	635.5	634.2
127.5°	699.0	699.3	699.0	698.7	698.5	698.2	697.7	696.9	696.2	695.4	694.7
130°	737.8	738.0	737.5	737.1	736.7	736.2	735.4	734.3	733.2	732.1	730.9
132.5°	774.9	775.1	775.2	775.3	775.4	775.5	774.6	772.7	770.9	769.1	767.2
135°	831.7	831.7	831.5	831.3	831.1	830.9	830.1	828.7	827.4	826.1	824.8
137.5°	887.1	886.8	886.4	885.9	885.3	884.8	883.9	882.6	881.3	880.0	878.8
140°	921.9	921.5	920.8	920.2	919.5	918.8	917.9	916.8	915.6	914.5	913.4
142.5°	956.4	956.1	955.3	954.5	953.6	952.8	951.9	950.9	950.0	949.1	948.1
145°	1006.2	1006.2	1005.5	1004.8	1004.2	1003.5	1002.7	1001.8	1000.9	1000.1	999.2
147.5°	1051.5	1051.0	1050.4	1049.9	1049.4	1048.8	1048.2	1047.8	1047.3	1046.8	1046.3
150°	1080.8	1080.8	1079.8	1079.0	1078.1	1077.2	1076.9	1077.1	1077.3	1077.5	1077.7
152.5°	1107.1	1106.6	1106.2	1105.9	1105.5	1105.2	1104.8	1104.5	1104.2	1103.9	1103.6
155°	1145.2	1144.3	1144.1	1143.9	1143.7	1143.4	1143.3	1143.3	1143.3	1143.3	1143.3
157.5°	1178.5	1177.6	1177.4	1177.1	1176.9	1176.7	1176.8	1177.3	1177.8	1178.3	1178.8
160°	1198.6	1197.7	1197.5	1197.3	1197.1	1196.9	1197.1	1197.7	1198.4	1199.1	1199.7
162.5°	1217.4	1216.3	1216.3	1216.2	1216.2	1216.1	1216.4	1216.8	1217.3	1217.8	1218.3
165°	1243.0	1242.1	1241.8	1241.6	1241.4	1241.2	1241.3	1241.7	1242.2	1242.6	1243.1
167.5°	1261.4	1260.0	1260.0	1260.0	1260.0	1260.0	1260.5	1261.4	1262.3	1263.1	1264.0
170°	1272.7	1271.3	1271.3	1271.3	1271.3	1271.3	1271.8	1272.7	1273.5	1274.4	1275.4
172.5°	1280.7	1279.4	1279.4	1279.4	1279.4	1279.4	1279.9	1280.7	1281.6	1282.5	1283.4
175°	1289.8	1288.5	1288.5	1288.5	1288.5	1288.5	1288.9	1289.8	1290.7	1291.6	1292.5
177.5°	1294.2	1293.1	1293.3	1293.4	1293.6	1293.8	1294.2	1294.9	1295.8	1296.5	1297.2
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	571.2	572.9	575.3	578.1	580.4	582.8	584.1	584.1	585.2	587.6	590.9
5°	572.9	579.0	584.7	592.2	598.0	604.8	610.0	614.9	619.2	624.9	630.8
7.5°	572.4	582.5	593.0	604.7	617.7	628.0	638.6	646.9	655.1	665.9	674.3
10°	570.6	583.6	597.8	612.8	629.1	643.3	656.2	667.8	679.0	690.7	701.3
12.5°	567.1	583.8	601.2	619.1	639.7	656.0	672.6	685.0	698.1	710.8	723.8
15°	562.1	581.7	602.7	627.7	652.9	671.1	687.4	703.6	715.7	730.1	742.6
17.5°	551.7	576.9	603.4	630.7	654.9	676.0	693.2	708.5	721.4	737.3	754.2
20°	545.5	572.9	600.4	629.5	652.7	674.4	690.9	706.8	722.9	743.7	764.2
22.5°	536.9	566.1	595.3	623.0	647.4	668.4	685.5	704.9	726.1	749.6	774.5
25°	523.4	553.5	582.4	608.7	632.6	654.1	677.4	703.6	729.2	760.2	796.0
27.5°	506.1	535.2	561.0	588.9	612.5	639.9	668.9	697.3	734.3	777.0	821.5
30°	493.3	520.8	545.3	571.7	598.5	628.6	661.3	694.7	738.8	788.9	841.9
32.5°	478.4	503.3	527.6	553.0	584.0	617.0	651.8	692.6	745.3	802.3	857.2
35°	452.4	474.8	498.5	526.6	559.6	595.5	639.9	689.5	753.3	814.6	863.8
37.5°	425.3	443.0	466.7	496.4	532.3	573.8	624.2	684.6	749.9	805.1	826.0
40°	404.3	420.9	446.0	477.2	512.7	558.2	614.6	676.7	742.6	780.7	779.1
42.5°	383.6	400.4	424.4	456.0	492.9	543.8	602.0	666.4	722.0	736.5	706.2
45°	351.8	367.5	391.1	422.8	462.5	515.9	577.0	638.9	674.4	650.8	590.6
47.5°	319.5	334.7	356.6	387.6	430.9	486.9	544.7	595.4	600.4	549.8	477.6
50°	298.2	312.5	333.3	366.4	408.4	462.9	518.8	558.7	546.2	484.4	410.0
52.5°	277.5	291.1	310.6	341.9	384.9	438.3	488.1	519.5	490.8	425.1	358.1
55°	246.9	259.9	279.5	308.2	347.2	396.2	439.9	451.3	409.3	343.1	288.9
57.5°	217.8	227.4	246.7	272.2	309.7	352.9	384.2	382.1	335.8	276.1	237.2
60°	198.5	207.2	225.6	248.9	284.7	323.5	345.4	336.0	289.1	239.8	202.6
62.5°	180.7	188.7	204.2	225.6	256.3	290.0	306.0	293.1	248.8	205.5	175.8
65°	153.5	159.4	171.8	191.6	215.6	238.9	253.2	234.3	195.1	162.4	140.0
67.5°	128.2	133.2	144.2	158.4	175.0	191.2	196.9	179.3	148.8	126.7	110.9
70°	111.8	116.4	123.9	137.2	148.1	159.6	162.4	146.5	121.1	104.3	94.5
72.5°	96.1	100.4	106.9	116.3	123.9	130.5	131.8	117.0	97.6	86.0	78.5
75°	73.3	77.1	81.2	84.7	89.6	90.8	90.3	78.9	68.4	60.7	56.5
77.5°	53.8	55.4	58.0	59.4	59.6	59.5	57.2	49.9	44.4	41.3	39.6
80°	41.5	42.7	43.4	43.8	44.1	41.8	39.2	34.7	32.9	31.0	29.0
82.5°	30.2	30.9	31.6	31.7	30.5	28.5	26.2	23.9	22.6	21.7	20.9
85°	16.4	16.6	16.4	15.1	13.5	12.8	12.3	11.9	11.7	11.4	11.4
87.5°	6.4	6.2	5.6	6.2	6.5	6.6	6.9	7.1	7.2	7.4	7.6
90°	2.8	4.5	6.4	8.2	9.9	11.4	13.0	14.5	16.2	17.3	18.4
92.5°	25.7	26.9	28.2	29.4	31.0	32.9	34.8	36.8	38.7	40.2	41.7
95°	65.9	66.4	66.9	67.4	68.7	70.9	73.1	75.4	77.7	79.2	80.8
97.5°	109.1	109.3	109.5	109.6	111.3	114.3	117.4	120.5	123.6	125.1	126.5
100°	141.2	141.2	141.2	141.2	142.6	145.5	148.5	151.4	154.2	156.2	158.2
102.5°	176.7	177.6	178.5	179.5	180.6	182.1	183.6	185.0	186.5	188.7	190.9
105°	231.0	232.1	233.3	234.4	235.6	236.9	238.2	239.6	241.0	242.3	243.7
107.5°	290.6	291.8	293.0	294.1	295.1	296.1	297.2	298.2	299.2	299.9	300.5
110°	331.8	333.0	334.1	335.2	336.1	336.7	337.4	338.1	338.7	339.4	340.1



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	373.2	373.8	374.4	375.0	375.7	376.6	377.4	378.2	379.1	379.4	379.7
115°	435.5	436.4	437.3	438.1	438.8	439.2	439.7	440.1	440.6	440.4	440.1
117.5°	497.1	497.5	497.9	498.3	498.7	499.1	499.5	499.9	500.3	500.5	500.6
120°	536.4	537.6	538.8	539.9	540.5	540.7	541.0	541.2	541.4	541.4	541.4
122.5°	577.7	578.1	578.6	579.0	579.4	580.0	580.6	581.2	581.7	581.6	581.4
125°	635.5	636.8	638.2	639.5	640.4	640.6	640.8	641.0	641.3	640.8	640.4
127.5°	695.4	696.2	696.9	697.7	698.2	698.5	698.7	699.0	699.3	699.0	698.8
130°	732.1	733.2	734.3	735.4	736.2	736.7	737.1	737.5	738.0	737.8	737.5
132.5°	769.1	770.9	772.7	774.6	775.5	775.4	775.3	775.2	775.1	774.9	774.7
135°	826.1	827.4	828.7	830.1	830.9	831.1	831.3	831.5	831.7	831.7	831.7
137.5°	880.0	881.3	882.6	883.9	884.8	885.3	885.9	886.4	886.8	887.1	887.4
140°	914.5	915.6	916.8	917.9	918.8	919.5	920.2	920.8	921.5	921.9	922.4
142.5°	949.1	950.0	950.9	951.9	952.8	953.6	954.5	955.3	956.1	956.4	956.7
145°	1000.1	1000.9	1001.8	1002.7	1003.5	1004.2	1004.8	1005.5	1006.2	1006.2	1006.2
147.5°	1046.8	1047.3	1047.8	1048.2	1048.8	1049.4	1049.9	1050.4	1051.0	1051.5	1052.0
150°	1077.5	1077.3	1077.1	1076.9	1077.2	1078.1	1079.0	1079.8	1080.8	1080.8	1080.8
152.5°	1103.9	1104.2	1104.5	1104.8	1105.2	1105.5	1105.9	1106.2	1106.6	1107.1	1107.7
155°	1143.3	1143.3	1143.3	1143.3	1143.4	1143.7	1143.9	1144.1	1144.3	1145.2	1146.1
157.5°	1178.3	1177.8	1177.3	1176.8	1176.7	1176.9	1177.1	1177.4	1177.6	1178.5	1179.3
160°	1199.1	1198.4	1197.7	1197.1	1196.9	1197.1	1197.3	1197.5	1197.7	1198.6	1199.5
162.5°	1217.8	1217.3	1216.8	1216.4	1216.1	1216.2	1216.2	1216.3	1216.3	1217.4	1218.4
165°	1242.6	1242.2	1241.7	1241.3	1241.2	1241.4	1241.6	1241.8	1242.1	1243.0	1243.9
167.5°	1263.1	1262.3	1261.4	1260.5	1260.0	1260.0	1260.0	1260.0	1260.0	1261.4	1262.7
170°	1274.4	1273.5	1272.7	1271.8	1271.3	1271.3	1271.3	1271.3	1271.3	1272.7	1274.0
172.5°	1282.5	1281.6	1280.7	1279.9	1279.4	1279.4	1279.4	1279.4	1279.4	1280.7	1282.1
175°	1291.6	1290.7	1289.8	1288.9	1288.5	1288.5	1288.5	1288.5	1288.5	1289.8	1291.2
177.5°	1296.5	1295.8	1294.9	1294.2	1293.8	1293.6	1293.4	1293.3	1293.1	1294.2	1295.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	593.3	593.3	596.4	596.2	598.3	597.5	597.9
5°	637.7	641.7	645.2	647.5	651.1	652.0	651.5
7.5°	683.9	692.7	696.9	702.9	703.9	707.0	706.7
10°	712.4	721.0	727.6	732.7	735.3	738.5	738.8
12.5°	734.8	742.1	747.9	752.7	755.8	756.8	757.4
15°	752.3	760.4	767.2	774.0	778.0	781.0	782.6
17.5°	769.9	782.5	794.5	803.7	809.2	813.9	813.9
20°	783.6	798.0	812.9	823.4	834.2	838.9	839.6
22.5°	798.1	820.2	839.5	855.8	869.9	874.7	876.6
25°	828.4	857.3	887.0	909.8	926.1	935.7	937.2
27.5°	864.9	904.0	935.2	956.3	969.9	977.0	978.6
30°	890.7	926.9	954.8	970.7	977.0	978.0	974.4
32.5°	902.2	929.3	940.5	939.6	927.2	919.0	915.8
35°	888.1	882.5	855.3	822.5	797.6	781.7	777.5
37.5°	808.2	759.9	709.7	660.4	634.1	620.7	597.7
40°	729.4	660.6	608.3	566.8	537.1	513.3	507.8
42.5°	640.6	569.5	517.3	481.7	458.0	441.7	434.5
45°	514.7	453.6	410.4	383.1	365.0	353.0	347.7
47.5°	411.7	364.4	333.0	312.8	298.8	288.5	285.6
50°	355.2	317.3	290.7	273.7	263.2	255.3	252.1
52.5°	308.5	277.9	257.5	243.5	233.6	228.6	225.9
55°	254.6	228.2	213.5	202.3	196.7	192.8	190.9
57.5°	208.2	189.1	178.4	170.7	165.5	163.0	162.1
60°	182.3	167.3	157.5	151.5	147.9	144.7	143.7
62.5°	159.3	147.5	140.0	134.6	131.2	129.8	129.2
65°	128.4	120.7	115.0	111.8	109.0	108.5	108.3
67.5°	102.0	97.5	94.5	91.2	90.2	88.6	88.2
70°	87.3	84.2	80.7	79.6	78.4	76.7	77.1
72.5°	74.0	71.0	68.6	67.1	66.7	65.9	66.6
75°	54.1	53.2	52.3	51.1	50.6	50.6	50.4
77.5°	38.7	37.9	36.9	36.2	36.0	35.0	35.3
80°	28.0	26.9	26.4	26.6	25.9	25.7	25.7
82.5°	20.7	20.3	19.8	19.9	19.7	19.5	19.7
85°	11.4	11.2	11.2	11.0	11.0	10.7	10.7
87.5°	8.0	8.4	8.2	8.2	8.3	8.6	9.0
90°	19.5	20.6	21.5	22.2	22.8	23.5	24.2
92.5°	43.1	44.6	45.6	46.2	46.6	47.1	47.6
95°	82.3	83.9	84.9	85.3	85.8	86.2	86.7
97.5°	128.1	129.6	130.4	130.7	131.0	131.2	131.5
100°	160.3	162.3	163.6	164.0	164.4	164.9	165.3
102.5°	193.1	195.3	196.7	197.3	197.9	198.6	199.2
105°	245.0	246.3	247.3	248.0	248.7	249.3	250.0
107.5°	301.2	301.9	302.3	302.2	302.2	302.2	302.1
110°	340.7	341.4	341.6	341.4	341.2	341.0	340.7



TEST NUMBER: P333509-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	380.0	380.3	380.3	379.9	379.5	379.1	378.7
115°	439.9	439.7	439.5	439.2	439.0	438.8	438.6
117.5°	500.8	501.0	500.6	499.7	498.9	498.0	497.1
120°	541.4	541.4	541.0	540.1	539.2	538.3	537.3
122.5°	581.2	581.0	580.6	579.9	579.2	578.5	577.7
125°	639.9	639.4	639.0	638.8	638.6	638.4	638.2
127.5°	698.6	698.4	698.0	697.6	697.1	696.7	696.3
130°	737.3	737.1	736.8	736.3	735.9	735.4	735.0
132.5°	774.5	774.2	773.8	773.2	772.5	771.9	771.2
135°	831.7	831.7	831.3	830.4	829.5	828.6	827.7
137.5°	887.6	887.9	887.5	886.4	885.2	884.1	883.0
140°	922.8	923.3	922.9	921.8	920.7	919.6	918.5
142.5°	956.9	957.3	956.8	955.7	954.6	953.5	952.3
145°	1006.2	1006.2	1005.8	1005.2	1004.5	1003.8	1003.2
147.5°	1052.6	1053.1	1052.6	1051.1	1049.6	1048.0	1046.5
150°	1080.8	1080.8	1080.6	1080.2	1079.6	1079.2	1078.7
152.5°	1108.2	1108.7	1108.6	1107.8	1107.0	1106.2	1105.4
155°	1147.0	1147.9	1147.8	1146.7	1145.5	1144.4	1143.3
157.5°	1180.2	1181.1	1180.8	1179.4	1177.9	1176.4	1175.0
160°	1200.4	1201.3	1201.2	1200.1	1199.0	1197.9	1196.7
162.5°	1219.5	1220.6	1220.5	1219.2	1217.9	1216.6	1215.3
165°	1244.8	1245.7	1245.5	1244.2	1242.7	1241.4	1240.1
167.5°	1264.0	1265.5	1265.4	1264.0	1262.6	1261.2	1259.8
170°	1275.4	1276.7	1276.6	1275.1	1273.4	1271.9	1270.3
172.5°	1283.4	1284.8	1284.8	1283.3	1282.0	1280.6	1279.2
175°	1292.5	1293.8	1293.7	1292.2	1290.6	1289.0	1287.5
177.5°	1296.4	1297.4	1297.4	1296.1	1294.8	1293.5	1292.3
180°	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6	1295.6

(END OF REPORT)