

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333510-840

Luminaire Tested: **S125RDIP-S375D1035U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333510-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1035U840-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5225.3 lumens  
Efficiency: N/A  
Efficacy: 140.1 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	48	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	48	36	29	24	43	33	26	22	26	21	18	20	17	15	14	12	11	9
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3672	3672	3672	3672
5°	4224	3676	3247	3676
10°	4845	3657	2865	3657
15°	5233	3620	2546	3620
20°	5770	3577	2351	3577
25°	6678	3518	2182	3518
30°	7267	3457	2071	3457
35°	6130	3387	1968	3387
40°	4281	3260	1881	3260
45°	3176	3088	1795	3088
50°	2533	2910	1721	2910
55°	2149	2688	1655	2688
60°	1856	2490	1550	2490
65°	1655	2275	1334	2275
70°	1456	2085	1216	2085
75°	1258	1804	1140	1804
80°	956	1517	956	1517
85°	793	1193	897	1193



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	1.0
10°-20°	159.7	3.1
20°-30°	253.3	4.8
30°-40°	305.4	5.8
40°-50°	272.8	5.2
50°-60°	209.2	4.0
60°-70°	135.9	2.6
70°-80°	66.1	1.3
80°-90°	18.6	0.4
90°-100°	362.4	6.9
100°-110°	779.1	14.9
110°-120°	731.2	14.0
120°-130°	592.6	11.3
130°-140°	475.6	9.1
140°-150°	358.9	6.9
150°-160°	252.6	4.8
160°-170°	148.9	2.8
170°-180°	48.4	0.9
0°-30°	467.5	8.9
0°-40°	773.0	14.8
0°-60°	1254.9	24.0
0°-90°	1475.5	28.2
90°-120°	1872.8	35.8
90°-150°	3299.8	63.2
90°-180°	3750.0	71.8
0°-180°	5225.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	568	568	568	568	568	
5°	652	567	501	567	652	65
15°	783	541	381	541	783	224
25°	937	494	306	494	937	430
35°	778	430	250	430	778	470
45°	348	338	196	338	348	277
55°	191	239	147	239	191	173
65°	108	149	87	149	108	108
75°	50	72	46	72	50	54
85°	11	16	12	16	11	13
90°	23	1	23	1	23	16
95°	237	33	237	33	237	336
105°	1336	114	1336	114	1336	1328
115°	1488	204	1488	204	1488	1454
125°	1172	282	1172	282	1172	1061
135°	974	331	974	331	974	755
145°	768	385	768	385	768	488
155°	644	440	644	440	644	300
165°	564	480	564	480	564	161
175°	507	499	507	499	507	49
180°	500	500	500	500	500	



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	597.9	597.5	598.3	596.2	596.4	593.3	593.3	590.9	587.6	585.2	584.1
5°	651.5	652.0	651.1	647.5	645.2	641.7	637.7	630.8	624.9	619.2	614.9
7.5°	706.7	707.0	703.9	702.9	696.9	692.7	683.9	674.3	665.9	655.1	646.9
10°	738.8	738.5	735.3	732.7	727.6	721.0	712.4	701.3	690.7	679.0	667.8
12.5°	757.4	756.8	755.8	752.7	747.9	742.1	734.8	723.8	710.8	698.1	685.0
15°	782.6	781.0	778.0	774.0	767.2	760.4	752.3	742.6	730.1	715.7	703.6
17.5°	813.9	813.9	809.2	803.7	794.5	782.5	769.9	754.2	737.3	721.4	708.5
20°	839.6	838.9	834.2	823.4	812.9	798.0	783.6	764.2	743.7	722.9	706.8
22.5°	876.6	874.7	869.9	855.8	839.5	820.2	798.1	774.5	749.6	726.1	704.9
25°	937.2	935.7	926.1	909.8	887.0	857.3	828.4	796.0	760.2	729.2	703.6
27.5°	978.6	977.0	969.9	956.3	935.2	904.0	864.9	821.5	777.0	734.3	697.3
30°	974.4	978.0	977.0	970.7	954.8	926.9	890.7	841.9	788.9	738.8	694.7
32.5°	915.8	919.0	927.2	939.6	940.5	929.3	902.2	857.2	802.3	745.3	692.6
35°	777.5	781.7	797.6	822.5	855.3	882.5	888.1	863.8	814.6	753.3	689.5
37.5°	597.7	620.7	634.1	660.4	709.7	759.9	808.2	826.0	805.1	749.9	684.6
40°	507.8	513.3	537.1	566.8	608.3	660.6	729.4	779.1	780.7	742.6	676.7
42.5°	434.5	441.7	458.0	481.7	517.3	569.5	640.6	706.2	736.5	722.0	666.4
45°	347.7	353.0	365.0	383.1	410.4	453.6	514.7	590.6	650.8	674.4	638.9
47.5°	285.6	288.5	298.8	312.8	333.0	364.4	411.7	477.6	549.8	600.4	595.4
50°	252.1	255.3	263.2	273.7	290.7	317.3	355.2	410.0	484.4	546.2	558.7
52.5°	225.9	228.6	233.6	243.5	257.5	277.9	308.5	358.1	425.1	490.8	519.5
55°	190.9	192.8	196.7	202.3	213.5	228.2	254.6	288.9	343.1	409.3	451.3
57.5°	162.1	163.0	165.5	170.7	178.4	189.1	208.2	237.2	276.1	335.8	382.1
60°	143.7	144.7	147.9	151.5	157.5	167.3	182.3	202.6	239.8	289.1	336.0
62.5°	129.2	129.8	131.2	134.6	140.0	147.5	159.3	175.8	205.5	248.8	293.1
65°	108.3	108.5	109.0	111.8	115.0	120.7	128.4	140.0	162.4	195.1	234.3
67.5°	88.2	88.6	90.2	91.2	94.5	97.5	102.0	110.9	126.7	148.8	179.3
70°	77.1	76.7	78.4	79.6	80.7	84.2	87.3	94.5	104.3	121.1	146.5
72.5°	66.6	65.9	66.7	67.1	68.6	71.0	74.0	78.5	86.0	97.6	117.0
75°	50.4	50.6	50.6	51.1	52.3	53.2	54.1	56.5	60.7	68.4	78.9
77.5°	35.3	35.0	36.0	36.2	36.9	37.9	38.7	39.6	41.3	44.4	49.9
80°	25.7	25.7	25.9	26.6	26.4	26.9	28.0	29.0	31.0	32.9	34.7
82.5°	19.7	19.5	19.7	19.9	19.8	20.3	20.7	20.9	21.7	22.6	23.9
85°	10.7	10.7	11.0	11.0	11.2	11.2	11.4	11.4	11.4	11.7	11.9
87.5°	8.8	8.6	8.2	8.2	8.4	8.3	8.0	7.6	7.4	7.2	7.0
90°	23.2	23.2	22.2	22.2	22.2	20.2	19.2	18.2	17.2	16.2	14.1
92.5°	64.3	65.9	67.4	69.8	82.7	97.6	129.7	178.6	263.1	325.0	330.2
95°	236.9	253.1	261.2	291.3	362.9	447.6	571.6	724.9	874.0	893.2	728.9
97.5°	572.6	585.5	614.7	671.3	733.5	851.2	972.0	1079.5	1105.9	953.9	650.9
100°	786.4	802.4	839.8	912.3	981.9	1086.7	1190.6	1240.0	1162.4	910.3	580.7
102.5°	1025.0	1037.1	1077.7	1129.3	1203.7	1274.7	1324.4	1294.0	1128.5	833.7	527.5
105°	1335.7	1347.9	1368.1	1401.3	1433.5	1444.6	1400.3	1262.1	1020.3	730.8	475.8
107.5°	1500.7	1508.7	1515.4	1515.6	1499.2	1446.6	1332.7	1148.4	909.7	660.1	454.0
110°	1555.5	1555.5	1548.4	1529.3	1484.0	1398.3	1256.1	1064.6	846.8	627.0	447.6



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1549.0	1541.9	1524.3	1491.4	1425.1	1324.0	1180.3	998.5	800.0	607.7	447.6
115°	1488.0	1474.9	1446.6	1398.3	1319.6	1209.7	1071.7	915.3	749.0	586.7	450.6
117.5°	1380.9	1372.8	1344.8	1294.8	1216.2	1115.4	996.4	861.7	718.6	576.4	457.3
120°	1311.6	1303.5	1276.3	1227.9	1153.3	1064.6	953.7	832.7	701.7	571.6	463.7
122.5°	1250.3	1243.0	1215.8	1171.4	1104.9	1021.8	923.0	810.9	687.1	567.5	469.4
125°	1172.5	1162.4	1140.1	1098.8	1042.4	969.8	882.1	779.3	667.4	562.5	478.9
127.5°	1105.9	1101.5	1080.5	1044.0	992.8	924.8	843.0	747.0	649.2	560.1	489.6
130°	1069.6	1063.6	1043.4	1010.2	959.8	894.2	815.6	726.9	637.1	558.5	496.0
132.5°	1033.3	1026.4	1007.9	974.6	924.2	861.1	789.7	706.7	627.4	558.5	503.2
135°	973.8	967.8	949.7	916.4	872.0	814.6	750.0	680.4	615.9	558.5	513.1
137.5°	910.3	903.7	887.0	856.7	817.0	768.2	714.6	658.3	605.7	559.7	522.2
140°	866.0	860.9	845.9	819.6	782.3	739.9	693.6	646.2	600.9	560.5	526.2
142.5°	824.9	820.6	806.3	784.2	752.5	715.8	675.8	635.7	596.8	561.3	528.7
145°	768.2	764.2	753.1	735.9	711.8	684.5	653.3	622.0	590.8	560.5	531.3
147.5°	720.2	718.4	712.0	698.2	679.0	658.5	634.5	609.2	584.5	557.8	532.3
150°	693.6	692.6	688.5	676.4	661.4	643.2	624.0	601.9	579.7	555.4	532.3
152.5°	672.6	671.6	667.6	657.9	645.2	631.1	613.5	593.8	574.0	552.3	531.5
155°	644.2	643.2	640.2	633.1	623.0	612.0	597.8	581.7	564.5	546.4	529.3
157.5°	618.7	618.9	616.1	610.4	602.5	593.8	582.9	569.6	555.6	540.4	526.6
160°	601.9	602.9	600.9	595.8	588.8	581.7	571.6	561.5	548.5	536.3	524.2
162.5°	586.5	586.7	586.3	582.1	576.6	570.4	561.9	552.7	542.0	531.5	521.8
165°	564.5	564.5	564.5	562.5	558.5	553.5	547.4	540.4	532.3	524.2	518.2
167.5°	544.4	544.6	545.4	543.6	541.6	538.0	533.3	528.7	522.8	517.2	512.5
170°	532.3	533.3	533.3	532.3	530.3	528.3	525.2	522.2	517.2	513.1	510.1
172.5°	521.0	522.0	523.6	521.8	521.4	520.2	518.0	514.9	511.5	508.3	506.9
175°	507.1	508.1	510.1	509.1	509.1	509.1	507.1	507.1	504.0	503.0	503.0
177.5°	500.0	500.0	502.4	501.6	502.4	502.4	502.4	501.6	500.8	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	584.1	582.8	580.4	578.1	575.3	572.9	571.2	569.2	566.5	563.4	560.8
5°	610.0	604.8	598.0	592.2	584.7	579.0	572.9	567.0	561.2	553.7	547.1
7.5°	638.6	628.0	617.7	604.7	593.0	582.5	572.4	562.2	552.2	541.6	531.4
10°	656.2	643.3	629.1	612.8	597.8	583.6	570.6	557.6	544.1	532.3	519.5
12.5°	672.6	656.0	639.7	619.1	601.2	583.8	567.1	551.2	536.7	521.3	507.5
15°	687.4	671.1	652.9	627.7	602.7	581.7	562.1	541.4	523.4	506.1	490.7
17.5°	693.2	676.0	654.9	630.7	603.4	576.9	551.7	529.0	507.8	487.7	470.4
20°	690.9	674.4	652.7	629.5	600.4	572.9	545.5	520.4	496.8	475.5	457.2
22.5°	685.5	668.4	647.4	623.0	595.3	566.1	536.9	510.1	485.4	463.4	443.3
25°	677.4	654.1	632.6	608.7	582.4	553.5	523.4	493.7	467.4	444.9	423.0
27.5°	668.9	639.9	612.5	588.9	561.0	535.2	506.1	475.7	448.1	425.3	402.7
30°	661.3	628.6	598.5	571.7	545.3	520.8	493.3	463.6	435.2	411.6	388.8
32.5°	651.8	617.0	584.0	553.0	527.6	503.3	478.4	450.0	422.3	398.0	374.8
35°	639.9	595.5	559.6	526.6	498.5	474.8	452.4	429.6	401.8	376.6	354.0
37.5°	624.2	573.8	532.3	496.4	466.7	443.0	425.3	404.3	379.0	355.0	334.0
40°	614.6	558.2	512.7	477.2	446.0	420.9	404.3	386.7	363.6	340.9	319.9
42.5°	602.0	543.8	492.9	456.0	424.4	400.4	383.6	368.2	348.8	327.5	305.0
45°	577.0	515.9	462.5	422.8	391.1	367.5	351.8	338.1	323.5	303.8	284.2
47.5°	544.7	486.9	430.9	387.6	356.6	334.7	319.5	308.6	298.1	281.4	262.5
50°	518.8	462.9	408.4	366.4	333.3	312.5	298.2	289.6	280.0	264.9	248.9
52.5°	488.1	438.3	384.9	341.9	310.6	291.1	277.5	268.8	260.9	248.6	233.5
55°	439.9	396.2	347.2	308.2	279.5	259.9	246.9	238.7	234.1	223.6	211.7
57.5°	384.2	352.9	309.7	272.2	246.7	227.4	217.8	210.9	205.6	198.1	189.8
60°	345.4	323.5	284.7	248.9	225.6	207.2	198.5	192.8	187.8	181.6	175.0
62.5°	306.0	290.0	256.3	225.6	204.2	188.7	180.7	175.4	169.8	165.5	159.2
65°	253.2	238.9	215.6	191.6	171.8	159.4	153.5	148.9	145.4	140.7	136.2
67.5°	196.9	191.2	175.0	158.4	144.2	133.2	128.2	124.9	120.8	118.0	114.9
70°	162.4	159.6	148.1	137.2	123.9	116.4	111.8	110.4	105.2	102.4	100.4
72.5°	131.8	130.5	123.9	116.3	106.9	100.4	96.1	94.5	91.2	89.0	87.7
75°	90.3	90.8	89.6	84.7	81.2	77.1	73.3	72.3	70.0	68.2	67.0
77.5°	57.2	59.5	59.6	59.4	58.0	55.4	53.8	53.1	50.9	50.2	49.9
80°	39.2	41.8	44.1	43.8	43.4	42.7	41.5	40.8	39.7	39.0	38.5
82.5°	26.2	28.5	30.5	31.7	31.6	30.9	30.2	29.8	29.6	29.1	29.0
85°	12.3	12.8	13.5	15.1	16.4	16.6	16.4	16.1	15.5	15.7	15.9
87.5°	6.9	6.5	6.5	6.1	5.5	6.1	6.2	6.2	6.0	6.1	6.1
90°	13.1	11.1	10.1	8.1	6.1	4.0	2.0	1.0	2.0	4.0	6.1
92.5°	230.0	137.7	82.7	53.2	35.9	23.4	14.9	12.3	14.9	23.4	35.9
95°	450.6	228.8	121.0	75.6	53.4	42.3	34.2	33.2	34.2	42.3	53.4
97.5°	359.7	197.2	125.8	93.1	73.2	62.1	56.5	55.2	56.5	62.1	73.2
100°	326.6	195.6	137.1	106.8	87.7	76.6	72.6	70.6	72.6	76.6	87.7
102.5°	313.0	202.9	150.8	121.4	103.8	91.9	88.7	87.6	88.7	91.9	103.8
105°	307.5	217.7	173.4	145.2	129.1	119.0	113.9	113.9	113.9	119.0	129.1
107.5°	316.8	239.9	197.0	171.6	154.8	146.5	141.8	139.8	141.8	146.5	154.8
110°	325.6	256.1	214.7	188.5	173.4	164.3	160.3	158.2	160.3	164.3	173.4





TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	336.9	271.4	231.7	206.2	191.2	182.1	178.8	176.8	178.8	182.1	191.2
115°	353.9	295.4	258.1	232.9	217.7	208.6	205.6	203.7	205.6	208.6	217.7
117.5°	373.2	320.0	284.7	260.3	243.2	234.1	230.9	227.8	230.9	234.1	243.2
120°	386.1	337.7	302.5	277.2	260.1	251.1	247.0	244.0	247.0	251.1	260.1
122.5°	400.6	354.7	319.4	294.2	275.4	266.3	263.1	260.9	263.1	266.3	275.4
125°	420.4	377.1	343.8	317.6	298.4	289.3	284.3	282.3	284.3	289.3	298.4
127.5°	438.5	398.6	366.6	340.3	320.0	308.5	302.1	299.0	302.1	308.5	320.0
130°	450.6	412.3	381.0	354.9	333.7	320.6	312.6	309.5	312.6	320.6	333.7
132.5°	461.1	425.3	393.9	367.8	345.8	331.0	321.3	317.6	321.3	331.0	345.8
135°	475.8	442.5	411.3	384.1	362.9	346.8	334.7	330.6	334.7	346.8	362.9
137.5°	486.8	454.8	426.5	398.4	377.7	361.5	350.2	347.2	350.2	361.5	377.7
140°	494.0	463.7	434.5	407.3	388.1	372.0	359.9	356.9	359.9	372.0	388.1
142.5°	498.0	469.4	441.7	416.2	397.8	381.6	370.4	368.2	370.4	381.6	397.8
145°	504.0	478.9	452.6	429.5	411.3	397.2	387.1	385.1	387.1	397.2	411.3
147.5°	507.7	484.9	461.9	441.5	425.9	412.7	404.0	402.8	404.0	412.7	425.9
150°	510.1	489.0	466.8	449.6	435.6	422.4	415.4	413.3	415.4	422.4	435.6
152.5°	511.7	493.0	472.4	456.9	443.5	432.1	425.9	424.6	425.9	432.1	443.5
155°	513.1	497.0	479.9	465.7	455.7	445.6	439.5	439.5	439.5	445.6	455.7
157.5°	514.1	500.4	485.7	475.0	466.2	457.5	452.6	452.8	452.6	457.5	466.2
160°	514.1	502.0	489.0	479.9	471.8	464.7	460.7	461.7	460.7	464.7	471.8
162.5°	513.3	503.6	492.2	484.7	478.3	472.0	468.0	469.0	468.0	472.0	478.3
165°	512.1	504.0	496.0	490.0	485.9	480.9	477.9	479.9	477.9	480.9	485.9
167.5°	509.7	504.0	497.4	493.6	490.8	488.0	486.1	487.2	486.1	488.0	490.8
170°	508.1	504.0	499.0	496.0	494.0	492.0	491.0	492.0	491.0	492.0	494.0
172.5°	506.4	503.2	499.0	497.6	496.3	494.4	493.4	495.2	493.4	494.4	496.3
175°	504.0	502.0	499.0	499.0	499.0	498.0	497.0	499.0	497.0	498.0	499.0
177.5°	501.6	500.8	499.2	499.2	500.0	499.2	499.2	500.8	499.2	499.2	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	558.9	556.3	554.4	550.7	548.1	546.9	544.9	544.3	546.4	544.9	544.7
5°	542.3	535.5	530.2	524.8	519.0	515.2	509.6	508.7	507.3	505.2	504.7
7.5°	522.4	513.5	506.6	497.8	490.1	483.8	476.9	473.5	471.7	469.0	465.3
10°	509.0	498.5	489.1	480.2	470.7	462.9	456.0	450.6	447.1	443.8	442.4
12.5°	495.6	484.9	473.0	462.3	451.6	443.0	435.3	431.7	427.9	424.0	420.8
15°	475.0	460.9	447.8	435.5	426.4	417.0	409.5	404.3	398.6	396.9	390.6
17.5°	453.2	439.3	423.9	411.0	400.4	390.1	381.9	376.1	371.7	365.7	362.8
20°	439.6	423.0	408.1	396.2	384.6	372.4	364.1	359.1	355.0	350.0	347.7
22.5°	425.1	408.9	393.5	379.6	367.8	355.8	349.8	344.8	340.0	335.5	332.3
25°	403.6	387.4	371.2	356.8	344.5	335.8	328.8	323.0	320.4	316.0	312.7
27.5°	382.5	365.2	348.5	334.1	324.4	315.8	310.0	305.5	300.8	297.0	294.1
30°	368.9	351.2	333.0	321.5	311.2	303.2	296.8	292.4	288.9	285.4	283.3
32.5°	355.3	337.0	320.8	308.5	298.8	291.8	285.3	280.9	277.3	273.5	270.9
35°	333.5	314.8	301.7	289.6	280.0	273.5	269.0	263.0	259.9	257.1	254.6
37.5°	313.2	295.8	281.7	271.0	262.7	256.2	250.4	247.2	243.5	241.0	238.8
40°	298.2	282.4	269.5	258.3	252.3	245.0	239.6	235.4	232.7	229.3	227.0
42.5°	284.8	270.0	257.5	247.5	239.9	233.8	228.6	224.4	220.9	218.5	216.6
45°	265.8	251.1	238.9	229.6	222.6	216.8	211.4	209.3	204.6	201.9	200.9
47.5°	246.1	233.0	221.3	212.7	205.5	200.0	194.9	190.7	188.0	185.3	183.8
50°	232.9	220.3	209.3	200.9	193.9	187.8	183.2	180.4	176.8	174.3	172.5
52.5°	219.6	207.9	197.0	188.9	182.9	176.8	171.6	168.8	165.5	163.9	162.6
55°	200.7	188.3	178.9	171.1	164.7	159.2	154.2	151.5	149.4	147.7	147.2
57.5°	179.3	169.5	160.8	153.6	147.0	141.8	137.4	134.8	133.0	132.7	131.3
60°	165.2	156.3	148.5	140.7	135.1	130.2	126.4	123.4	121.6	121.4	120.9
62.5°	151.2	142.7	135.3	128.6	123.5	118.9	115.2	111.9	110.8	109.6	108.6
65°	130.5	122.7	116.6	111.3	105.9	102.0	98.5	96.3	93.8	92.4	89.9
67.5°	110.1	104.1	98.3	93.7	89.5	85.7	82.8	79.7	78.0	76.9	75.0
70°	96.6	91.9	86.1	81.2	78.0	74.9	72.6	69.1	67.9	67.0	66.0
72.5°	83.9	79.8	74.9	70.9	67.7	64.8	62.1	60.5	59.3	58.4	57.9
75°	66.0	62.1	57.9	55.0	52.7	50.4	49.0	47.9	47.4	47.2	46.3
77.5°	48.5	46.4	43.0	40.8	39.3	38.3	37.1	36.5	36.4	35.3	35.0
80°	37.1	36.0	33.1	32.2	31.0	30.1	29.4	28.3	27.1	26.6	25.9
82.5°	27.6	26.5	25.2	23.8	22.8	22.2	21.6	21.1	21.3	20.6	20.3
85°	14.7	13.5	13.0	12.8	12.3	12.8	12.6	12.3	12.1	11.9	12.1
87.5°	6.3	6.7	6.7	7.5	7.1	7.7	7.9	7.9	8.1	8.3	8.6
90°	8.1	10.1	11.1	13.1	14.1	16.2	17.2	18.2	19.2	20.2	22.2
92.5°	53.2	82.7	137.7	230.0	330.2	325.0	263.1	178.6	129.7	97.6	82.7
95°	75.6	121.0	228.8	450.6	728.9	893.2	874.0	724.9	571.6	447.6	362.9
97.5°	93.1	125.8	197.2	359.7	650.9	953.9	1105.9	1079.5	972.0	851.2	733.5
100°	106.8	137.1	195.6	326.6	580.7	910.3	1162.4	1240.0	1190.6	1086.7	981.9
102.5°	121.4	150.8	202.9	313.0	527.5	833.7	1128.5	1294.0	1324.4	1274.7	1203.7
105°	145.2	173.4	217.7	307.5	475.8	730.8	1020.3	1262.1	1400.3	1444.6	1433.5
107.5°	171.6	197.0	239.9	316.8	454.0	660.1	909.7	1148.4	1332.7	1446.6	1499.2
110°	188.5	214.7	256.1	325.6	447.6	627.0	846.8	1064.6	1256.1	1398.3	1484.0



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	206.2	231.7	271.4	336.9	447.6	607.7	800.0	998.5	1180.3	1324.0	1425.1
115°	232.9	258.1	295.4	353.9	450.6	586.7	749.0	915.3	1071.7	1209.7	1319.6
117.5°	260.3	284.7	320.0	373.2	457.3	576.4	718.6	861.7	996.4	1115.4	1216.2
120°	277.2	302.5	337.7	386.1	463.7	571.6	701.7	832.7	953.7	1064.6	1153.3
122.5°	294.2	319.4	354.7	400.6	469.4	567.5	687.1	810.9	923.0	1021.8	1104.9
125°	317.6	343.8	377.1	420.4	478.9	562.5	667.4	779.3	882.1	969.8	1042.4
127.5°	340.3	366.6	398.6	438.5	489.6	560.1	649.2	747.0	843.0	924.8	992.8
130°	354.9	381.0	412.3	450.6	496.0	558.5	637.1	726.9	815.6	894.2	959.8
132.5°	367.8	393.9	425.3	461.1	503.2	558.5	627.4	706.7	789.7	861.1	924.2
135°	384.1	411.3	442.5	475.8	513.1	558.5	615.9	680.4	750.0	814.6	872.0
137.5°	398.4	426.5	454.8	486.8	522.2	559.7	605.7	658.3	714.6	768.2	817.0
140°	407.3	434.5	463.7	494.0	526.2	560.5	600.9	646.2	693.6	739.9	782.3
142.5°	416.2	441.7	469.4	498.0	528.7	561.3	596.8	635.7	675.8	715.8	752.5
145°	429.5	452.6	478.9	504.0	531.3	560.5	590.8	622.0	653.3	684.5	711.8
147.5°	441.5	461.9	484.9	507.7	532.3	557.8	584.5	609.2	634.5	658.5	679.0
150°	449.6	466.8	489.0	510.1	532.3	555.4	579.7	601.9	624.0	643.2	661.4
152.5°	456.9	472.4	493.0	511.7	531.5	552.3	574.0	593.8	613.5	631.1	645.2
155°	465.7	479.9	497.0	513.1	529.3	546.4	564.5	581.7	597.8	612.0	623.0
157.5°	475.0	485.7	500.4	514.1	526.6	540.4	555.6	569.6	582.9	593.8	602.5
160°	479.9	489.0	502.0	514.1	524.2	536.3	548.5	561.5	571.6	581.7	588.8
162.5°	484.7	492.2	503.6	513.3	521.8	531.5	542.0	552.7	561.9	570.4	576.6
165°	490.0	496.0	504.0	512.1	518.2	524.2	532.3	540.4	547.4	553.5	558.5
167.5°	493.6	497.4	504.0	509.7	512.5	517.2	522.8	528.7	533.3	538.0	541.6
170°	496.0	499.0	504.0	508.1	510.1	513.1	517.2	522.2	525.2	528.3	530.3
172.5°	497.6	499.0	503.2	506.4	506.9	508.3	511.5	514.9	518.0	520.2	521.4
175°	499.0	499.0	502.0	504.0	503.0	503.0	504.0	507.1	507.1	509.1	509.1
177.5°	499.2	499.2	500.8	501.6	500.0	500.0	500.8	501.6	502.4	502.4	502.4
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.5	542.5	541.9	542.7	541.9	542.5	544.5	544.7	544.9	546.4	544.3
5°	502.4	500.1	501.2	500.8	501.2	500.1	502.4	504.7	505.2	507.3	508.7
7.5°	465.3	462.4	459.4	460.3	459.4	462.4	465.3	465.3	469.0	471.7	473.5
10°	439.4	437.1	435.7	436.9	435.7	437.1	439.4	442.4	443.8	447.1	450.6
12.5°	417.6	416.2	415.0	414.4	415.0	416.2	417.6	420.8	424.0	427.9	431.7
15°	387.8	385.1	383.8	380.8	383.8	385.1	387.8	390.6	396.9	398.6	404.3
17.5°	360.4	359.5	356.5	355.2	356.5	359.5	360.4	362.8	365.7	371.7	376.1
20°	344.2	343.3	340.2	342.0	340.2	343.3	344.2	347.7	350.0	355.0	359.1
22.5°	330.7	328.7	327.7	327.2	327.7	328.7	330.7	332.3	335.5	340.0	344.8
25°	311.7	308.7	307.5	306.2	307.5	308.7	311.7	312.7	316.0	320.4	323.0
27.5°	292.8	291.1	289.6	289.2	289.6	291.1	292.8	294.1	297.0	300.8	305.5
30°	280.4	278.8	277.7	277.7	277.7	278.8	280.4	283.3	285.4	288.9	292.4
32.5°	269.4	268.2	267.0	266.8	267.0	268.2	269.4	270.9	273.5	277.3	280.9
35°	253.4	251.6	251.1	249.6	251.1	251.6	253.4	254.6	257.1	259.9	263.0
37.5°	236.7	235.2	235.2	235.0	235.2	235.2	236.7	238.8	241.0	243.5	247.2
40°	226.1	224.9	224.7	223.1	224.7	224.9	226.1	227.0	229.3	232.7	235.4
42.5°	214.7	214.1	213.3	212.6	213.3	214.1	214.7	216.6	218.5	220.9	224.4
45°	199.2	197.6	197.6	196.5	197.6	197.6	199.2	200.9	201.9	204.6	209.3
47.5°	183.3	182.1	182.2	181.0	182.2	182.1	183.3	183.8	185.3	188.0	190.7
50°	172.7	172.0	171.8	171.3	171.8	172.0	172.7	172.5	174.3	176.8	180.4
52.5°	162.1	161.7	162.6	161.6	162.6	161.7	162.1	162.6	163.9	165.5	168.8
55°	147.7	147.0	148.5	147.0	148.5	147.0	147.7	147.2	147.7	149.4	151.5
57.5°	131.3	130.6	131.9	131.2	131.9	130.6	131.3	131.3	132.7	133.0	134.8
60°	120.4	119.0	119.7	120.0	119.7	119.0	120.4	120.9	121.4	121.6	123.4
62.5°	107.6	106.6	107.2	106.1	107.2	106.6	107.6	108.6	109.6	110.8	111.9
65°	89.4	88.7	87.8	87.3	87.8	88.7	89.4	89.9	92.4	93.8	96.3
67.5°	75.1	73.4	73.3	73.7	73.3	73.4	75.1	75.0	76.9	78.0	79.7
70°	64.6	64.6	64.4	64.4	64.4	64.6	64.6	66.0	67.0	67.9	69.1
72.5°	57.4	57.2	56.8	56.6	56.8	57.2	57.4	57.9	58.4	59.3	60.5
75°	46.3	46.5	45.9	45.7	45.9	46.5	46.3	46.3	47.2	47.4	47.9
77.5°	34.1	33.1	33.6	33.1	33.6	33.1	34.1	35.0	35.3	36.4	36.5
80°	25.9	25.7	26.4	25.7	26.4	25.7	25.9	25.9	26.6	27.1	28.3
82.5°	20.5	20.3	20.6	20.1	20.6	20.3	20.5	20.3	20.6	21.3	21.1
85°	12.3	12.1	11.9	12.1	11.9	12.1	12.3	12.1	11.9	12.1	12.3
87.5°	8.7	8.6	8.8	8.8	8.8	8.6	8.7	8.6	8.3	8.1	7.9
90°	22.2	22.2	23.2	23.2	23.2	22.2	22.2	22.2	20.2	19.2	18.2
92.5°	69.8	67.4	65.9	64.3	65.9	67.4	69.8	82.7	97.6	129.7	178.6
95°	291.3	261.2	253.1	236.9	253.1	261.2	291.3	362.9	447.6	571.6	724.9
97.5°	671.3	614.7	585.5	572.6	585.5	614.7	671.3	733.5	851.2	972.0	1079.5
100°	912.3	839.8	802.4	786.4	802.4	839.8	912.3	981.9	1086.7	1190.6	1240.0
102.5°	1129.3	1077.7	1037.1	1025.0	1037.1	1077.7	1129.3	1203.7	1274.7	1324.4	1294.0
105°	1401.3	1368.1	1347.9	1335.7	1347.9	1368.1	1401.3	1433.5	1444.6	1400.3	1262.1
107.5°	1515.6	1515.4	1508.7	1500.7	1508.7	1515.4	1515.6	1499.2	1446.6	1332.7	1148.4
110°	1529.3	1548.4	1555.5	1555.5	1555.5	1548.4	1529.3	1484.0	1398.3	1256.1	1064.6



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1491.4	1524.3	1541.9	1549.0	1541.9	1524.3	1491.4	1425.1	1324.0	1180.3	998.5
115°	1398.3	1446.6	1474.9	1488.0	1474.9	1446.6	1398.3	1319.6	1209.7	1071.7	915.3
117.5°	1294.8	1344.8	1372.8	1380.9	1372.8	1344.8	1294.8	1216.2	1115.4	996.4	861.7
120°	1227.9	1276.3	1303.5	1311.6	1303.5	1276.3	1227.9	1153.3	1064.6	953.7	832.7
122.5°	1171.4	1215.8	1243.0	1250.3	1243.0	1215.8	1171.4	1104.9	1021.8	923.0	810.9
125°	1098.8	1140.1	1162.4	1172.5	1162.4	1140.1	1098.8	1042.4	969.8	882.1	779.3
127.5°	1044.0	1080.5	1101.5	1105.9	1101.5	1080.5	1044.0	992.8	924.8	843.0	747.0
130°	1010.2	1043.4	1063.6	1069.6	1063.6	1043.4	1010.2	959.8	894.2	815.6	726.9
132.5°	974.6	1007.9	1026.4	1033.3	1026.4	1007.9	974.6	924.2	861.1	789.7	706.7
135°	916.4	949.7	967.8	973.8	967.8	949.7	916.4	872.0	814.6	750.0	680.4
137.5°	856.7	887.0	903.7	910.3	903.7	887.0	856.7	817.0	768.2	714.6	658.3
140°	819.6	845.9	860.9	866.0	860.9	845.9	819.6	782.3	739.9	693.6	646.2
142.5°	784.2	806.3	820.6	824.9	820.6	806.3	784.2	752.5	715.8	675.8	635.7
145°	735.9	753.1	764.2	768.2	764.2	753.1	735.9	711.8	684.5	653.3	622.0
147.5°	698.2	712.0	718.4	720.2	718.4	712.0	698.2	679.0	658.5	634.5	609.2
150°	676.4	688.5	692.6	693.6	692.6	688.5	676.4	661.4	643.2	624.0	601.9
152.5°	657.9	667.6	671.6	672.6	671.6	667.6	657.9	645.2	631.1	613.5	593.8
155°	633.1	640.2	643.2	644.2	643.2	640.2	633.1	623.0	612.0	597.8	581.7
157.5°	610.4	616.1	618.9	618.7	618.9	616.1	610.4	602.5	593.8	582.9	569.6
160°	595.8	600.9	602.9	601.9	602.9	600.9	595.8	588.8	581.7	571.6	561.5
162.5°	582.1	586.3	586.7	586.5	586.7	586.3	582.1	576.6	570.4	561.9	552.7
165°	562.5	564.5	564.5	564.5	564.5	564.5	562.5	558.5	553.5	547.4	540.4
167.5°	543.6	545.4	544.6	544.4	544.6	545.4	543.6	541.6	538.0	533.3	528.7
170°	532.3	533.3	533.3	532.3	533.3	533.3	532.3	530.3	528.3	525.2	522.2
172.5°	521.8	523.6	522.0	521.0	522.0	523.6	521.8	521.4	520.2	518.0	514.9
175°	509.1	510.1	508.1	507.1	508.1	510.1	509.1	509.1	509.1	507.1	507.1
177.5°	501.6	502.4	500.0	500.0	500.0	502.4	501.6	502.4	502.4	502.4	501.6
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.9	546.9	548.1	550.7	554.4	556.3	558.9	560.8	563.4	566.5	569.2
5°	509.6	515.2	519.0	524.8	530.2	535.5	542.3	547.1	553.7	561.2	567.0
7.5°	476.9	483.8	490.1	497.8	506.6	513.5	522.4	531.4	541.6	552.2	562.2
10°	456.0	462.9	470.7	480.2	489.1	498.5	509.0	519.5	532.3	544.1	557.6
12.5°	435.3	443.0	451.6	462.3	473.0	484.9	495.6	507.5	521.3	536.7	551.2
15°	409.5	417.0	426.4	435.5	447.8	460.9	475.0	490.7	506.1	523.4	541.4
17.5°	381.9	390.1	400.4	411.0	423.9	439.3	453.2	470.4	487.7	507.8	529.0
20°	364.1	372.4	384.6	396.2	408.1	423.0	439.6	457.2	475.5	496.8	520.4
22.5°	349.8	355.8	367.8	379.6	393.5	408.9	425.1	443.3	463.4	485.4	510.1
25°	328.8	335.8	344.5	356.8	371.2	387.4	403.6	423.0	444.9	467.4	493.7
27.5°	310.0	315.8	324.4	334.1	348.5	365.2	382.5	402.7	425.3	448.1	475.7
30°	296.8	303.2	311.2	321.5	333.0	351.2	368.9	388.8	411.6	435.2	463.6
32.5°	285.3	291.8	298.8	308.5	320.8	337.0	355.3	374.8	398.0	422.3	450.0
35°	269.0	273.5	280.0	289.6	301.7	314.8	333.5	354.0	376.6	401.8	429.6
37.5°	250.4	256.2	262.7	271.0	281.7	295.8	313.2	334.0	355.0	379.0	404.3
40°	239.6	245.0	252.3	258.3	269.5	282.4	298.2	319.9	340.9	363.6	386.7
42.5°	228.6	233.8	239.9	247.5	257.5	270.0	284.8	305.0	327.5	348.8	368.2
45°	211.4	216.8	222.6	229.6	238.9	251.1	265.8	284.2	303.8	323.5	338.1
47.5°	194.9	200.0	205.5	212.7	221.3	233.0	246.1	262.5	281.4	298.1	308.6
50°	183.2	187.8	193.9	200.9	209.3	220.3	232.9	248.9	264.9	280.0	289.6
52.5°	171.6	176.8	182.9	188.9	197.0	207.9	219.6	233.5	248.6	260.9	268.8
55°	154.2	159.2	164.7	171.1	178.9	188.3	200.7	211.7	223.6	234.1	238.7
57.5°	137.4	141.8	147.0	153.6	160.8	169.5	179.3	189.8	198.1	205.6	210.9
60°	126.4	130.2	135.1	140.7	148.5	156.3	165.2	175.0	181.6	187.8	192.8
62.5°	115.2	118.9	123.5	128.6	135.3	142.7	151.2	159.2	165.5	169.8	175.4
65°	98.5	102.0	105.9	111.3	116.6	122.7	130.5	136.2	140.7	145.4	148.9
67.5°	82.8	85.7	89.5	93.7	98.3	104.1	110.1	114.9	118.0	120.8	124.9
70°	72.6	74.9	78.0	81.2	86.1	91.9	96.6	100.4	102.4	105.2	110.4
72.5°	62.1	64.8	67.7	70.9	74.9	79.8	83.9	87.7	89.0	91.2	94.5
75°	49.0	50.4	52.7	55.0	57.9	62.1	66.0	67.0	68.2	70.0	72.3
77.5°	37.1	38.3	39.3	40.8	43.0	46.4	48.5	49.9	50.2	50.9	53.1
80°	29.4	30.1	31.0	32.2	33.1	36.0	37.1	38.5	39.0	39.7	40.8
82.5°	21.6	22.2	22.8	23.8	25.2	26.5	27.6	29.0	29.1	29.6	29.8
85°	12.6	12.8	12.3	12.8	13.0	13.5	14.7	15.9	15.7	15.5	16.1
87.5°	7.9	7.7	7.1	7.5	6.7	6.7	6.3	6.1	6.1	6.0	6.2
90°	17.2	16.2	14.1	13.1	11.1	10.1	8.1	6.1	4.0	2.0	1.0
92.5°	263.1	325.0	330.2	230.0	137.7	82.7	53.2	35.9	23.4	14.9	12.3
95°	874.0	893.2	728.9	450.6	228.8	121.0	75.6	53.4	42.3	34.2	33.2
97.5°	1105.9	953.9	650.9	359.7	197.2	125.8	93.1	73.2	62.1	56.5	55.2
100°	1162.4	910.3	580.7	326.6	195.6	137.1	106.8	87.7	76.6	72.6	70.6
102.5°	1128.5	833.7	527.5	313.0	202.9	150.8	121.4	103.8	91.9	88.7	87.6
105°	1020.3	730.8	475.8	307.5	217.7	173.4	145.2	129.1	119.0	113.9	113.9
107.5°	909.7	660.1	454.0	316.8	239.9	197.0	171.6	154.8	146.5	141.8	139.8
110°	846.8	627.0	447.6	325.6	256.1	214.7	188.5	173.4	164.3	160.3	158.2



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	800.0	607.7	447.6	336.9	271.4	231.7	206.2	191.2	182.1	178.8	176.8
115°	749.0	586.7	450.6	353.9	295.4	258.1	232.9	217.7	208.6	205.6	203.7
117.5°	718.6	576.4	457.3	373.2	320.0	284.7	260.3	243.2	234.1	230.9	227.8
120°	701.7	571.6	463.7	386.1	337.7	302.5	277.2	260.1	251.1	247.0	244.0
122.5°	687.1	567.5	469.4	400.6	354.7	319.4	294.2	275.4	266.3	263.1	260.9
125°	667.4	562.5	478.9	420.4	377.1	343.8	317.6	298.4	289.3	284.3	282.3
127.5°	649.2	560.1	489.6	438.5	398.6	366.6	340.3	320.0	308.5	302.1	299.0
130°	637.1	558.5	496.0	450.6	412.3	381.0	354.9	333.7	320.6	312.6	309.5
132.5°	627.4	558.5	503.2	461.1	425.3	393.9	367.8	345.8	331.0	321.3	317.6
135°	615.9	558.5	513.1	475.8	442.5	411.3	384.1	362.9	346.8	334.7	330.6
137.5°	605.7	559.7	522.2	486.8	454.8	426.5	398.4	377.7	361.5	350.2	347.2
140°	600.9	560.5	526.2	494.0	463.7	434.5	407.3	388.1	372.0	359.9	356.9
142.5°	596.8	561.3	528.7	498.0	469.4	441.7	416.2	397.8	381.6	370.4	368.2
145°	590.8	560.5	531.3	504.0	478.9	452.6	429.5	411.3	397.2	387.1	385.1
147.5°	584.5	557.8	532.3	507.7	484.9	461.9	441.5	425.9	412.7	404.0	402.8
150°	579.7	555.4	532.3	510.1	489.0	466.8	449.6	435.6	422.4	415.4	413.3
152.5°	574.0	552.3	531.5	511.7	493.0	472.4	456.9	443.5	432.1	425.9	424.6
155°	564.5	546.4	529.3	513.1	497.0	479.9	465.7	455.7	445.6	439.5	439.5
157.5°	555.6	540.4	526.6	514.1	500.4	485.7	475.0	466.2	457.5	452.6	452.8
160°	548.5	536.3	524.2	514.1	502.0	489.0	479.9	471.8	464.7	460.7	461.7
162.5°	542.0	531.5	521.8	513.3	503.6	492.2	484.7	478.3	472.0	468.0	469.0
165°	532.3	524.2	518.2	512.1	504.0	496.0	490.0	485.9	480.9	477.9	479.9
167.5°	522.8	517.2	512.5	509.7	504.0	497.4	493.6	490.8	488.0	486.1	487.2
170°	517.2	513.1	510.1	508.1	504.0	499.0	496.0	494.0	492.0	491.0	492.0
172.5°	511.5	508.3	506.9	506.4	503.2	499.0	497.6	496.3	494.4	493.4	495.2
175°	504.0	503.0	503.0	504.0	502.0	499.0	499.0	499.0	498.0	497.0	499.0
177.5°	500.8	500.0	500.0	501.6	500.8	499.2	499.2	500.0	499.2	499.2	500.8
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	571.2	572.9	575.3	578.1	580.4	582.8	584.1	584.1	585.2	587.6	590.9
5°	572.9	579.0	584.7	592.2	598.0	604.8	610.0	614.9	619.2	624.9	630.8
7.5°	572.4	582.5	593.0	604.7	617.7	628.0	638.6	646.9	655.1	665.9	674.3
10°	570.6	583.6	597.8	612.8	629.1	643.3	656.2	667.8	679.0	690.7	701.3
12.5°	567.1	583.8	601.2	619.1	639.7	656.0	672.6	685.0	698.1	710.8	723.8
15°	562.1	581.7	602.7	627.7	652.9	671.1	687.4	703.6	715.7	730.1	742.6
17.5°	551.7	576.9	603.4	630.7	654.9	676.0	693.2	708.5	721.4	737.3	754.2
20°	545.5	572.9	600.4	629.5	652.7	674.4	690.9	706.8	722.9	743.7	764.2
22.5°	536.9	566.1	595.3	623.0	647.4	668.4	685.5	704.9	726.1	749.6	774.5
25°	523.4	553.5	582.4	608.7	632.6	654.1	677.4	703.6	729.2	760.2	796.0
27.5°	506.1	535.2	561.0	588.9	612.5	639.9	668.9	697.3	734.3	777.0	821.5
30°	493.3	520.8	545.3	571.7	598.5	628.6	661.3	694.7	738.8	788.9	841.9
32.5°	478.4	503.3	527.6	553.0	584.0	617.0	651.8	692.6	745.3	802.3	857.2
35°	452.4	474.8	498.5	526.6	559.6	595.5	639.9	689.5	753.3	814.6	863.8
37.5°	425.3	443.0	466.7	496.4	532.3	573.8	624.2	684.6	749.9	805.1	826.0
40°	404.3	420.9	446.0	477.2	512.7	558.2	614.6	676.7	742.6	780.7	779.1
42.5°	383.6	400.4	424.4	456.0	492.9	543.8	602.0	666.4	722.0	736.5	706.2
45°	351.8	367.5	391.1	422.8	462.5	515.9	577.0	638.9	674.4	650.8	590.6
47.5°	319.5	334.7	356.6	387.6	430.9	486.9	544.7	595.4	600.4	549.8	477.6
50°	298.2	312.5	333.3	366.4	408.4	462.9	518.8	558.7	546.2	484.4	410.0
52.5°	277.5	291.1	310.6	341.9	384.9	438.3	488.1	519.5	490.8	425.1	358.1
55°	246.9	259.9	279.5	308.2	347.2	396.2	439.9	451.3	409.3	343.1	288.9
57.5°	217.8	227.4	246.7	272.2	309.7	352.9	384.2	382.1	335.8	276.1	237.2
60°	198.5	207.2	225.6	248.9	284.7	323.5	345.4	336.0	289.1	239.8	202.6
62.5°	180.7	188.7	204.2	225.6	256.3	290.0	306.0	293.1	248.8	205.5	175.8
65°	153.5	159.4	171.8	191.6	215.6	238.9	253.2	234.3	195.1	162.4	140.0
67.5°	128.2	133.2	144.2	158.4	175.0	191.2	196.9	179.3	148.8	126.7	110.9
70°	111.8	116.4	123.9	137.2	148.1	159.6	162.4	146.5	121.1	104.3	94.5
72.5°	96.1	100.4	106.9	116.3	123.9	130.5	131.8	117.0	97.6	86.0	78.5
75°	73.3	77.1	81.2	84.7	89.6	90.8	90.3	78.9	68.4	60.7	56.5
77.5°	53.8	55.4	58.0	59.4	59.6	59.5	57.2	49.9	44.4	41.3	39.6
80°	41.5	42.7	43.4	43.8	44.1	41.8	39.2	34.7	32.9	31.0	29.0
82.5°	30.2	30.9	31.6	31.7	30.5	28.5	26.2	23.9	22.6	21.7	20.9
85°	16.4	16.6	16.4	15.1	13.5	12.8	12.3	11.9	11.7	11.4	11.4
87.5°	6.2	6.1	5.5	6.1	6.5	6.5	6.9	7.0	7.2	7.4	7.6
90°	2.0	4.0	6.1	8.1	10.1	11.1	13.1	14.1	16.2	17.2	18.2
92.5°	14.9	23.4	35.9	53.2	82.7	137.7	230.0	330.2	325.0	263.1	178.6
95°	34.2	42.3	53.4	75.6	121.0	228.8	450.6	728.9	893.2	874.0	724.9
97.5°	56.5	62.1	73.2	93.1	125.8	197.2	359.7	650.9	953.9	1105.9	1079.5
100°	72.6	76.6	87.7	106.8	137.1	195.6	326.6	580.7	910.3	1162.4	1240.0
102.5°	88.7	91.9	103.8	121.4	150.8	202.9	313.0	527.5	833.7	1128.5	1294.0
105°	113.9	119.0	129.1	145.2	173.4	217.7	307.5	475.8	730.8	1020.3	1262.1
107.5°	141.8	146.5	154.8	171.6	197.0	239.9	316.8	454.0	660.1	909.7	1148.4
110°	160.3	164.3	173.4	188.5	214.7	256.1	325.6	447.6	627.0	846.8	1064.6





TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	178.8	182.1	191.2	206.2	231.7	271.4	336.9	447.6	607.7	800.0	998.5
115°	205.6	208.6	217.7	232.9	258.1	295.4	353.9	450.6	586.7	749.0	915.3
117.5°	230.9	234.1	243.2	260.3	284.7	320.0	373.2	457.3	576.4	718.6	861.7
120°	247.0	251.1	260.1	277.2	302.5	337.7	386.1	463.7	571.6	701.7	832.7
122.5°	263.1	266.3	275.4	294.2	319.4	354.7	400.6	469.4	567.5	687.1	810.9
125°	284.3	289.3	298.4	317.6	343.8	377.1	420.4	478.9	562.5	667.4	779.3
127.5°	302.1	308.5	320.0	340.3	366.6	398.6	438.5	489.6	560.1	649.2	747.0
130°	312.6	320.6	333.7	354.9	381.0	412.3	450.6	496.0	558.5	637.1	726.9
132.5°	321.3	331.0	345.8	367.8	393.9	425.3	461.1	503.2	558.5	627.4	706.7
135°	334.7	346.8	362.9	384.1	411.3	442.5	475.8	513.1	558.5	615.9	680.4
137.5°	350.2	361.5	377.7	398.4	426.5	454.8	486.8	522.2	559.7	605.7	658.3
140°	359.9	372.0	388.1	407.3	434.5	463.7	494.0	526.2	560.5	600.9	646.2
142.5°	370.4	381.6	397.8	416.2	441.7	469.4	498.0	528.7	561.3	596.8	635.7
145°	387.1	397.2	411.3	429.5	452.6	478.9	504.0	531.3	560.5	590.8	622.0
147.5°	404.0	412.7	425.9	441.5	461.9	484.9	507.7	532.3	557.8	584.5	609.2
150°	415.4	422.4	435.6	449.6	466.8	489.0	510.1	532.3	555.4	579.7	601.9
152.5°	425.9	432.1	443.5	456.9	472.4	493.0	511.7	531.5	552.3	574.0	593.8
155°	439.5	445.6	455.7	465.7	479.9	497.0	513.1	529.3	546.4	564.5	581.7
157.5°	452.6	457.5	466.2	475.0	485.7	500.4	514.1	526.6	540.4	555.6	569.6
160°	460.7	464.7	471.8	479.9	489.0	502.0	514.1	524.2	536.3	548.5	561.5
162.5°	468.0	472.0	478.3	484.7	492.2	503.6	513.3	521.8	531.5	542.0	552.7
165°	477.9	480.9	485.9	490.0	496.0	504.0	512.1	518.2	524.2	532.3	540.4
167.5°	486.1	488.0	490.8	493.6	497.4	504.0	509.7	512.5	517.2	522.8	528.7
170°	491.0	492.0	494.0	496.0	499.0	504.0	508.1	510.1	513.1	517.2	522.2
172.5°	493.4	494.4	496.3	497.6	499.0	503.2	506.4	506.9	508.3	511.5	514.9
175°	497.0	498.0	499.0	499.0	499.0	502.0	504.0	503.0	503.0	504.0	507.1
177.5°	499.2	499.2	500.0	499.2	499.2	500.8	501.6	500.0	500.0	500.8	501.6
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	593.3	593.3	596.4	596.2	598.3	597.5	597.9
5°	637.7	641.7	645.2	647.5	651.1	652.0	651.5
7.5°	683.9	692.7	696.9	702.9	703.9	707.0	706.7
10°	712.4	721.0	727.6	732.7	735.3	738.5	738.8
12.5°	734.8	742.1	747.9	752.7	755.8	756.8	757.4
15°	752.3	760.4	767.2	774.0	778.0	781.0	782.6
17.5°	769.9	782.5	794.5	803.7	809.2	813.9	813.9
20°	783.6	798.0	812.9	823.4	834.2	838.9	839.6
22.5°	798.1	820.2	839.5	855.8	869.9	874.7	876.6
25°	828.4	857.3	887.0	909.8	926.1	935.7	937.2
27.5°	864.9	904.0	935.2	956.3	969.9	977.0	978.6
30°	890.7	926.9	954.8	970.7	977.0	978.0	974.4
32.5°	902.2	929.3	940.5	939.6	927.2	919.0	915.8
35°	888.1	882.5	855.3	822.5	797.6	781.7	777.5
37.5°	808.2	759.9	709.7	660.4	634.1	620.7	597.7
40°	729.4	660.6	608.3	566.8	537.1	513.3	507.8
42.5°	640.6	569.5	517.3	481.7	458.0	441.7	434.5
45°	514.7	453.6	410.4	383.1	365.0	353.0	347.7
47.5°	411.7	364.4	333.0	312.8	298.8	288.5	285.6
50°	355.2	317.3	290.7	273.7	263.2	255.3	252.1
52.5°	308.5	277.9	257.5	243.5	233.6	228.6	225.9
55°	254.6	228.2	213.5	202.3	196.7	192.8	190.9
57.5°	208.2	189.1	178.4	170.7	165.5	163.0	162.1
60°	182.3	167.3	157.5	151.5	147.9	144.7	143.7
62.5°	159.3	147.5	140.0	134.6	131.2	129.8	129.2
65°	128.4	120.7	115.0	111.8	109.0	108.5	108.3
67.5°	102.0	97.5	94.5	91.2	90.2	88.6	88.2
70°	87.3	84.2	80.7	79.6	78.4	76.7	77.1
72.5°	74.0	71.0	68.6	67.1	66.7	65.9	66.6
75°	54.1	53.2	52.3	51.1	50.6	50.6	50.4
77.5°	38.7	37.9	36.9	36.2	36.0	35.0	35.3
80°	28.0	26.9	26.4	26.6	25.9	25.7	25.7
82.5°	20.7	20.3	19.8	19.9	19.7	19.5	19.7
85°	11.4	11.2	11.2	11.0	11.0	10.7	10.7
87.5°	8.0	8.3	8.4	8.2	8.2	8.6	8.8
90°	19.2	20.2	22.2	22.2	22.2	23.2	23.2
92.5°	129.7	97.6	82.7	69.8	67.4	65.9	64.3
95°	571.6	447.6	362.9	291.3	261.2	253.1	236.9
97.5°	972.0	851.2	733.5	671.3	614.7	585.5	572.6
100°	1190.6	1086.7	981.9	912.3	839.8	802.4	786.4
102.5°	1324.4	1274.7	1203.7	1129.3	1077.7	1037.1	1025.0
105°	1400.3	1444.6	1433.5	1401.3	1368.1	1347.9	1335.7
107.5°	1332.7	1446.6	1499.2	1515.6	1515.4	1508.7	1500.7
110°	1256.1	1398.3	1484.0	1529.3	1548.4	1555.5	1555.5



TEST NUMBER: P333510-840

CATALOG NUMBER: S125RDIP-S375D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1180.3	1324.0	1425.1	1491.4	1524.3	1541.9	1549.0
115°	1071.7	1209.7	1319.6	1398.3	1446.6	1474.9	1488.0
117.5°	996.4	1115.4	1216.2	1294.8	1344.8	1372.8	1380.9
120°	953.7	1064.6	1153.3	1227.9	1276.3	1303.5	1311.6
122.5°	923.0	1021.8	1104.9	1171.4	1215.8	1243.0	1250.3
125°	882.1	969.8	1042.4	1098.8	1140.1	1162.4	1172.5
127.5°	843.0	924.8	992.8	1044.0	1080.5	1101.5	1105.9
130°	815.6	894.2	959.8	1010.2	1043.4	1063.6	1069.6
132.5°	789.7	861.1	924.2	974.6	1007.9	1026.4	1033.3
135°	750.0	814.6	872.0	916.4	949.7	967.8	973.8
137.5°	714.6	768.2	817.0	856.7	887.0	903.7	910.3
140°	693.6	739.9	782.3	819.6	845.9	860.9	866.0
142.5°	675.8	715.8	752.5	784.2	806.3	820.6	824.9
145°	653.3	684.5	711.8	735.9	753.1	764.2	768.2
147.5°	634.5	658.5	679.0	698.2	712.0	718.4	720.2
150°	624.0	643.2	661.4	676.4	688.5	692.6	693.6
152.5°	613.5	631.1	645.2	657.9	667.6	671.6	672.6
155°	597.8	612.0	623.0	633.1	640.2	643.2	644.2
157.5°	582.9	593.8	602.5	610.4	616.1	618.9	618.7
160°	571.6	581.7	588.8	595.8	600.9	602.9	601.9
162.5°	561.9	570.4	576.6	582.1	586.3	586.7	586.5
165°	547.4	553.5	558.5	562.5	564.5	564.5	564.5
167.5°	533.3	538.0	541.6	543.6	545.4	544.6	544.4
170°	525.2	528.3	530.3	532.3	533.3	533.3	532.3
172.5°	518.0	520.2	521.4	521.8	523.6	522.0	521.0
175°	507.1	509.1	509.1	509.1	510.1	508.1	507.1
177.5°	502.4	502.4	502.4	501.6	502.4	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0

(END OF REPORT)