

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333540-840

Luminaire Tested: **S125RDIP-S610D1035U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333540-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1035U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6173.7 lumens
Efficiency: N/A
Efficacy: 138.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39																				
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40	34																				
2	87	80	74	70	79	73	68	64	60	57	54	48	46	43	37	35	34	29																				
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25																				
4	73	63	55	49	66	57	51	46	47	43	39	38	35	32	29	27	25	21																				
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19																				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17																				
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15																				
8	53	41	34	28	48	38	31	27	32	26	23	26	22	19	20	18	16	13																				
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6035	6035	6035	6035
5°	6944	6043	5337	6043
10°	7965	6013	4709	6013
15°	8603	5951	4186	5951
20°	9487	5880	3865	5880
25°	10979	5784	3587	5784
30°	11946	5684	3404	5684
35°	10078	5568	3236	5568
40°	7038	5359	3092	5359
45°	5221	5076	2951	5076
50°	4163	4784	2829	4784
55°	3533	4418	2721	4418
60°	3052	4093	2547	4093
65°	2720	3741	2193	3741
70°	2391	3427	1998	3427
75°	2069	2969	1876	2969
80°	1570	2499	1570	2499
85°	1312	1964	1482	1964



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.5
10°-20°	262.6	4.3
20°-30°	416.4	6.7
30°-40°	502.1	8.1
40°-50°	448.4	7.3
50°-60°	343.9	5.6
60°-70°	223.5	3.6
70°-80°	108.6	1.8
80°-90°	28.7	0.5
90°-100°	362.4	5.9
100°-110°	779.1	12.6
110°-120°	731.2	11.8
120°-130°	592.6	9.6
130°-140°	475.6	7.7
140°-150°	358.9	5.8
150°-160°	252.6	4.1
160°-170°	148.9	2.4
170°-180°	48.4	0.8
0°-30°	768.6	12.5
0°-40°	1270.8	20.6
0°-60°	2063.1	33.4
0°-90°	2423.9	39.3
90°-120°	1872.8	30.3
90°-150°	3299.8	53.4
90°-180°	3750.0	60.7
0°-180°	6173.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	934	934	934	934	934	
5°	1071	932	823	932	1071	107
15°	1287	890	626	890	1287	369
25°	1541	812	503	812	1541	707
35°	1278	706	410	706	1278	772
45°	572	556	323	556	572	456
55°	314	392	242	392	314	285
65°	178	245	144	245	178	177
75°	83	119	75	119	83	88
85°	18	26	20	26	18	21
90°	23	1	23	1	23	17
95°	237	33	237	33	237	336
105°	1336	114	1336	114	1336	1328
115°	1488	204	1488	204	1488	1454
125°	1172	282	1172	282	1172	1061
135°	974	331	974	331	974	755
145°	768	385	768	385	768	488
155°	644	440	644	440	644	300
165°	564	480	564	480	564	161
175°	507	499	507	499	507	49
180°	500	500	500	500	500	



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	983.0	982.4	983.6	980.2	980.6	975.3	975.3	971.3	966.1	962.1	960.3
5°	1071.1	1071.9	1070.3	1064.5	1060.7	1054.9	1048.4	1036.9	1027.3	1018.1	1010.9
7.5°	1161.7	1162.3	1157.2	1155.5	1145.8	1138.7	1124.3	1108.6	1094.7	1077.0	1063.6
10°	1214.6	1214.2	1208.8	1204.6	1196.1	1185.4	1171.1	1152.8	1135.5	1116.3	1097.9
12.5°	1245.3	1244.3	1242.5	1237.4	1229.6	1220.0	1208.0	1189.9	1168.6	1147.6	1126.2
15°	1286.7	1283.9	1279.0	1272.4	1261.3	1250.2	1236.8	1220.7	1200.3	1176.6	1156.6
17.5°	1337.9	1338.0	1330.3	1321.3	1306.2	1286.5	1265.8	1239.8	1212.1	1186.0	1164.8
20°	1380.3	1379.1	1371.4	1353.8	1336.6	1312.0	1288.2	1256.4	1222.6	1188.4	1162.0
22.5°	1441.0	1438.0	1430.1	1406.8	1380.1	1348.5	1312.1	1273.2	1232.4	1193.7	1158.9
25°	1540.7	1538.3	1522.6	1495.7	1458.1	1409.4	1361.8	1308.5	1249.8	1198.8	1156.6
27.5°	1608.7	1606.2	1594.6	1572.3	1537.5	1486.3	1421.9	1350.7	1277.4	1207.2	1146.3
30°	1601.9	1607.7	1606.2	1595.9	1569.7	1523.7	1464.3	1384.1	1297.0	1214.6	1142.1
32.5°	1505.6	1510.8	1524.3	1544.6	1546.1	1527.7	1483.3	1409.3	1319.1	1225.3	1138.6
35°	1278.2	1285.2	1311.2	1352.2	1405.9	1450.9	1460.1	1420.2	1339.2	1238.3	1133.6
37.5°	982.7	1020.5	1042.4	1085.6	1166.7	1249.3	1328.7	1358.0	1323.5	1232.9	1125.4
40°	834.8	843.9	883.1	931.8	1000.1	1086.0	1199.2	1280.9	1283.5	1220.7	1112.5
42.5°	714.5	726.1	753.0	791.8	850.3	936.2	1053.1	1160.9	1210.8	1186.9	1095.6
45°	571.6	580.4	600.0	629.9	674.8	745.8	846.3	971.0	1070.0	1108.6	1050.4
47.5°	469.6	474.3	491.3	514.1	547.3	599.1	676.8	785.1	903.8	987.0	978.9
50°	414.3	419.7	432.7	450.0	478.0	521.7	583.9	674.0	796.4	898.1	918.4
52.5°	371.3	375.8	384.0	400.3	423.3	457.0	507.2	588.8	698.8	806.9	853.9
55°	313.8	316.9	323.4	332.5	351.0	375.2	418.5	474.9	563.9	672.9	741.9
57.5°	266.4	267.9	272.1	280.5	293.3	310.9	342.2	390.1	453.9	552.0	628.2
60°	236.3	237.8	243.2	248.9	258.9	275.1	299.6	333.0	394.4	475.3	552.4
62.5°	212.4	213.3	215.6	221.4	230.0	242.6	261.9	289.1	337.9	409.0	481.8
65°	178.0	178.3	179.2	183.8	189.1	198.3	211.0	230.1	267.0	320.7	385.2
67.5°	145.0	145.5	148.2	149.9	155.4	160.3	167.7	182.4	208.3	244.5	294.6
70°	126.6	126.2	128.9	130.8	132.7	138.5	143.5	155.3	171.5	199.1	241.0
72.5°	109.4	108.5	109.6	110.3	112.8	116.7	121.7	129.0	141.4	160.5	192.4
75°	82.9	83.2	83.2	84.0	85.9	87.5	89.0	92.8	99.8	112.4	129.7
77.5°	58.2	57.6	59.2	59.4	60.5	62.2	63.5	65.0	67.9	73.1	82.0
80°	42.2	42.2	42.6	43.7	43.3	44.1	46.0	47.6	51.0	54.1	57.2
82.5°	32.4	32.1	32.4	32.7	32.6	33.3	34.0	34.3	35.6	37.2	39.4
85°	17.7	17.7	18.1	18.1	18.4	18.4	18.8	18.8	18.8	19.2	19.6
87.5°	11.4	11.1	10.6	10.6	10.9	11.1	10.6	10.1	9.9	9.7	9.6
90°	23.2	23.2	22.2	22.2	22.2	20.2	19.2	18.2	17.2	16.2	14.1
92.5°	64.3	65.9	67.4	69.8	82.7	97.6	129.7	178.6	263.1	325.0	330.2
95°	236.9	253.1	261.2	291.3	362.9	447.6	571.6	724.9	874.0	893.2	728.9
97.5°	572.6	585.5	614.7	671.3	733.5	851.2	972.0	1079.5	1105.9	953.9	650.9
100°	786.4	802.4	839.8	912.3	981.9	1086.7	1190.6	1240.0	1162.4	910.3	580.7
102.5°	1025.0	1037.1	1077.7	1129.3	1203.7	1274.7	1324.4	1294.0	1128.5	833.7	527.5
105°	1335.7	1347.9	1368.1	1401.3	1433.5	1444.6	1400.3	1262.1	1020.3	730.8	475.8
107.5°	1500.7	1508.7	1515.4	1515.6	1499.2	1446.6	1332.7	1148.4	909.7	660.1	454.0
110°	1555.5	1555.5	1548.4	1529.3	1484.0	1398.3	1256.1	1064.6	846.8	627.0	447.6



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1549.0	1541.9	1524.3	1491.4	1425.1	1324.0	1180.3	998.5	800.0	607.7	447.6
115°	1488.0	1474.9	1446.6	1398.3	1319.6	1209.7	1071.7	915.3	749.0	586.7	450.6
117.5°	1380.9	1372.8	1344.8	1294.8	1216.2	1115.4	996.4	861.7	718.6	576.4	457.3
120°	1311.6	1303.5	1276.3	1227.9	1153.3	1064.6	953.7	832.7	701.7	571.6	463.7
122.5°	1250.3	1243.0	1215.8	1171.4	1104.9	1021.8	923.0	810.9	687.1	567.5	469.4
125°	1172.5	1162.4	1140.1	1098.8	1042.4	969.8	882.1	779.3	667.4	562.5	478.9
127.5°	1105.9	1101.5	1080.5	1044.0	992.8	924.8	843.0	747.0	649.2	560.1	489.6
130°	1069.6	1063.6	1043.4	1010.2	959.8	894.2	815.6	726.9	637.1	558.5	496.0
132.5°	1033.3	1026.4	1007.9	974.6	924.2	861.1	789.7	706.7	627.4	558.5	503.2
135°	973.8	967.8	949.7	916.4	872.0	814.6	750.0	680.4	615.9	558.5	513.1
137.5°	910.3	903.7	887.0	856.7	817.0	768.2	714.6	658.3	605.7	559.7	522.2
140°	866.0	860.9	845.9	819.6	782.3	739.9	693.6	646.2	600.9	560.5	526.2
142.5°	824.9	820.6	806.3	784.2	752.5	715.8	675.8	635.7	596.8	561.3	528.7
145°	768.2	764.2	753.1	735.9	711.8	684.5	653.3	622.0	590.8	560.5	531.3
147.5°	720.2	718.4	712.0	698.2	679.0	658.5	634.5	609.2	584.5	557.8	532.3
150°	693.6	692.6	688.5	676.4	661.4	643.2	624.0	601.9	579.7	555.4	532.3
152.5°	672.6	671.6	667.6	657.9	645.2	631.1	613.5	593.8	574.0	552.3	531.5
155°	644.2	643.2	640.2	633.1	623.0	612.0	597.8	581.7	564.5	546.4	529.3
157.5°	618.7	618.9	616.1	610.4	602.5	593.8	582.9	569.6	555.6	540.4	526.6
160°	601.9	602.9	600.9	595.8	588.8	581.7	571.6	561.5	548.5	536.3	524.2
162.5°	586.5	586.7	586.3	582.1	576.6	570.4	561.9	552.7	542.0	531.5	521.8
165°	564.5	564.5	564.5	562.5	558.5	553.5	547.4	540.4	532.3	524.2	518.2
167.5°	544.4	544.6	545.4	543.6	541.6	538.0	533.3	528.7	522.8	517.2	512.5
170°	532.3	533.3	533.3	532.3	530.3	528.3	525.2	522.2	517.2	513.1	510.1
172.5°	521.0	522.0	523.6	521.8	521.4	520.2	518.0	514.9	511.5	508.3	506.9
175°	507.1	508.1	510.1	509.1	509.1	509.1	507.1	507.1	504.0	503.0	503.0
177.5°	500.0	500.0	502.4	501.6	502.4	502.4	502.4	501.6	500.8	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	960.3	958.2	954.1	950.5	945.8	941.9	939.1	935.7	931.4	926.2	921.9
5°	1002.8	994.3	983.2	973.6	961.4	951.8	941.8	932.2	922.6	910.3	899.6
7.5°	1049.9	1032.5	1015.5	994.2	974.8	957.6	941.0	924.2	907.8	890.4	873.5
10°	1078.7	1057.6	1034.2	1007.3	982.8	959.5	938.0	916.9	894.6	875.0	853.9
12.5°	1105.7	1078.5	1051.8	1017.8	988.4	959.8	932.4	906.2	882.3	857.0	834.2
15°	1130.1	1103.3	1073.4	1032.0	990.9	956.3	924.1	890.0	860.5	832.0	806.8
17.5°	1139.5	1111.5	1076.6	1036.8	992.0	948.6	907.1	869.6	834.9	801.7	773.3
20°	1135.9	1108.6	1073.0	1035.0	987.0	941.8	896.9	855.5	816.7	781.8	751.5
22.5°	1127.0	1098.8	1064.4	1024.3	978.8	930.7	882.8	838.6	798.0	761.8	728.8
25°	1113.7	1075.3	1040.0	1000.9	957.6	910.0	860.5	811.7	768.4	731.5	695.5
27.5°	1099.7	1051.9	1007.0	968.1	922.3	879.9	832.1	782.2	736.6	699.1	662.2
30°	1087.2	1033.5	984.0	939.9	896.6	856.3	810.9	762.2	715.5	676.7	639.1
32.5°	1071.6	1014.4	960.1	909.2	867.4	827.4	786.4	739.8	694.3	654.3	616.1
35°	1051.9	979.0	919.9	865.9	819.4	780.6	743.9	706.2	660.6	619.1	582.0
37.5°	1026.1	943.4	875.0	816.1	767.2	728.2	699.2	664.8	623.2	583.5	549.0
40°	1010.5	917.7	842.8	784.5	733.1	692.1	664.8	635.6	597.6	560.5	525.9
42.5°	989.6	894.0	810.3	749.5	697.8	658.3	630.8	605.3	573.4	538.4	501.4
45°	948.7	848.2	760.3	695.1	643.0	604.2	578.5	555.8	531.7	499.5	467.3
47.5°	895.4	800.4	708.4	637.2	586.1	550.2	525.2	507.4	490.1	462.7	431.4
50°	852.8	761.1	671.4	602.3	547.9	513.6	490.3	476.1	460.3	435.5	409.3
52.5°	802.4	720.6	632.7	562.1	510.7	478.7	456.2	442.0	429.0	408.7	383.8
55°	723.2	651.4	570.8	506.8	459.6	427.4	405.9	392.4	384.8	367.5	347.9
57.5°	631.6	580.2	509.2	447.4	405.7	373.8	358.1	346.7	338.0	325.8	311.9
60°	567.7	531.7	468.0	409.3	370.9	340.6	326.5	316.9	308.8	298.4	287.7
62.5°	503.0	476.8	421.4	370.9	335.7	310.2	297.0	288.3	279.0	272.1	261.7
65°	416.3	392.8	354.5	315.0	282.4	262.1	252.5	244.8	239.0	231.4	224.0
67.5°	323.8	314.3	287.8	260.5	237.1	219.0	210.8	205.4	198.4	193.9	188.8
70°	267.0	262.4	243.6	225.6	203.7	191.5	183.8	181.5	173.0	168.4	164.9
72.5°	216.7	214.5	203.7	191.2	175.8	165.0	157.9	155.3	150.0	146.3	144.1
75°	148.5	149.3	147.3	139.3	133.5	126.6	120.5	119.0	115.1	112.0	110.1
77.5°	93.9	97.9	98.0	97.6	95.3	91.1	88.6	87.4	83.6	82.5	82.0
80°	64.4	68.7	72.5	72.1	71.4	70.2	68.3	67.2	65.2	64.0	63.3
82.5°	42.9	46.9	50.1	52.2	52.0	50.9	49.6	49.0	48.7	47.8	47.7
85°	20.3	21.1	22.2	24.9	26.9	27.3	26.9	26.5	25.3	25.8	26.1
87.5°	9.7	9.3	9.4	9.0	8.3	9.4	9.9	10.0	9.6	9.4	9.2
90°	13.1	11.1	10.1	8.1	6.1	4.0	2.0	1.0	2.0	4.0	6.1
92.5°	230.0	137.7	82.7	53.2	35.9	23.4	14.9	12.3	14.9	23.4	35.9
95°	450.6	228.8	121.0	75.6	53.4	42.3	34.2	33.2	34.2	42.3	53.4
97.5°	359.7	197.2	125.8	93.1	73.2	62.1	56.5	55.2	56.5	62.1	73.2
100°	326.6	195.6	137.1	106.8	87.7	76.6	72.6	70.6	72.6	76.6	87.7
102.5°	313.0	202.9	150.8	121.4	103.8	91.9	88.7	87.6	88.7	91.9	103.8
105°	307.5	217.7	173.4	145.2	129.1	119.0	113.9	113.9	113.9	119.0	129.1
107.5°	316.8	239.9	197.0	171.6	154.8	146.5	141.8	139.8	141.8	146.5	154.8
110°	325.6	256.1	214.7	188.5	173.4	164.3	160.3	158.2	160.3	164.3	173.4



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	336.9	271.4	231.7	206.2	191.2	182.1	178.8	176.8	178.8	182.1	191.2
115°	353.9	295.4	258.1	232.9	217.7	208.6	205.6	203.7	205.6	208.6	217.7
117.5°	373.2	320.0	284.7	260.3	243.2	234.1	230.9	227.8	230.9	234.1	243.2
120°	386.1	337.7	302.5	277.2	260.1	251.1	247.0	244.0	247.0	251.1	260.1
122.5°	400.6	354.7	319.4	294.2	275.4	266.3	263.1	260.9	263.1	266.3	275.4
125°	420.4	377.1	343.8	317.6	298.4	289.3	284.3	282.3	284.3	289.3	298.4
127.5°	438.5	398.6	366.6	340.3	320.0	308.5	302.1	299.0	302.1	308.5	320.0
130°	450.6	412.3	381.0	354.9	333.7	320.6	312.6	309.5	312.6	320.6	333.7
132.5°	461.1	425.3	393.9	367.8	345.8	331.0	321.3	317.6	321.3	331.0	345.8
135°	475.8	442.5	411.3	384.1	362.9	346.8	334.7	330.6	334.7	346.8	362.9
137.5°	486.8	454.8	426.5	398.4	377.7	361.5	350.2	347.2	350.2	361.5	377.7
140°	494.0	463.7	434.5	407.3	388.1	372.0	359.9	356.9	359.9	372.0	388.1
142.5°	498.0	469.4	441.7	416.2	397.8	381.6	370.4	368.2	370.4	381.6	397.8
145°	504.0	478.9	452.6	429.5	411.3	397.2	387.1	385.1	387.1	397.2	411.3
147.5°	507.7	484.9	461.9	441.5	425.9	412.7	404.0	402.8	404.0	412.7	425.9
150°	510.1	489.0	466.8	449.6	435.6	422.4	415.4	413.3	415.4	422.4	435.6
152.5°	511.7	493.0	472.4	456.9	443.5	432.1	425.9	424.6	425.9	432.1	443.5
155°	513.1	497.0	479.9	465.7	455.7	445.6	439.5	439.5	439.5	445.6	455.7
157.5°	514.1	500.4	485.7	475.0	466.2	457.5	452.6	452.8	452.6	457.5	466.2
160°	514.1	502.0	489.0	479.9	471.8	464.7	460.7	461.7	460.7	464.7	471.8
162.5°	513.3	503.6	492.2	484.7	478.3	472.0	468.0	469.0	468.0	472.0	478.3
165°	512.1	504.0	496.0	490.0	485.9	480.9	477.9	479.9	477.9	480.9	485.9
167.5°	509.7	504.0	497.4	493.6	490.8	488.0	486.1	487.2	486.1	488.0	490.8
170°	508.1	504.0	499.0	496.0	494.0	492.0	491.0	492.0	491.0	492.0	494.0
172.5°	506.4	503.2	499.0	497.6	496.3	494.4	493.4	495.2	493.4	494.4	496.3
175°	504.0	502.0	499.0	499.0	499.0	498.0	497.0	499.0	497.0	498.0	499.0
177.5°	501.6	500.8	499.2	499.2	500.0	499.2	499.2	500.8	499.2	499.2	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	918.9	914.5	911.5	905.3	901.0	899.2	895.9	894.9	898.3	895.9	895.5
5°	891.5	880.4	871.6	862.7	853.1	847.1	837.8	836.3	833.9	830.5	829.8
7.5°	858.8	844.2	832.9	818.3	805.7	795.5	784.0	778.5	775.5	771.0	765.1
10°	836.7	819.4	804.1	789.5	773.8	761.1	749.6	740.7	735.0	729.6	727.3
12.5°	814.9	797.3	777.7	760.0	742.5	728.2	715.5	709.7	703.4	697.1	691.8
15°	781.0	757.6	736.2	715.8	700.8	685.5	673.3	664.8	655.2	652.6	642.2
17.5°	745.2	722.2	697.0	675.6	658.3	641.4	627.9	618.3	611.1	601.2	596.4
20°	722.8	695.5	671.0	651.4	632.2	612.3	598.4	590.4	583.5	575.4	571.6
22.5°	698.8	672.2	647.0	624.1	604.6	584.9	575.1	566.7	559.0	551.5	546.4
25°	663.7	636.8	610.4	586.5	566.2	552.0	540.5	530.9	526.7	519.4	514.0
27.5°	628.9	600.4	572.9	549.2	533.2	519.2	509.8	502.2	494.5	488.2	483.5
30°	606.5	577.3	547.4	528.7	511.7	498.4	488.0	480.7	474.9	469.2	465.7
32.5°	584.1	554.0	527.5	507.2	491.2	479.6	469.0	461.9	455.9	449.5	445.5
35°	548.2	517.5	496.0	476.1	460.3	449.6	442.3	432.3	427.4	422.7	418.5
37.5°	514.8	486.3	463.0	445.6	431.9	421.2	411.8	406.4	400.3	396.2	392.6
40°	490.3	464.1	443.1	424.6	414.7	402.8	393.9	387.1	382.4	377.1	373.2
42.5°	468.2	443.9	423.4	406.9	394.5	384.4	375.9	369.0	363.1	359.3	356.1
45°	437.0	412.7	392.8	377.5	366.0	356.4	347.6	344.1	336.4	331.8	330.3
47.5°	404.7	383.0	363.8	349.6	337.8	328.7	320.4	313.5	309.2	304.7	302.3
50°	382.8	362.1	344.1	330.3	318.8	308.8	301.1	296.5	290.7	286.6	283.5
52.5°	361.0	341.8	323.9	310.6	300.6	290.7	282.2	277.5	272.1	269.3	267.2
55°	329.9	309.6	294.3	281.1	270.8	261.7	253.6	248.9	245.5	242.9	242.1
57.5°	294.6	278.5	264.3	252.5	241.8	233.1	226.0	221.7	218.6	218.2	215.9
60°	271.6	257.0	244.0	231.4	222.1	214.1	207.9	203.0	199.9	199.4	198.7
62.5°	248.6	234.6	222.5	211.4	203.1	195.3	189.6	183.9	182.1	180.2	178.4
65°	214.4	201.8	191.8	183.0	174.2	167.6	161.9	158.4	154.2	151.9	147.7
67.5°	180.9	171.1	161.5	154.1	147.1	141.0	136.2	131.1	128.3	126.3	123.3
70°	158.9	151.2	141.6	133.5	128.2	123.1	119.3	113.5	111.6	110.1	108.6
72.5°	137.9	131.2	123.1	116.6	111.3	106.5	102.1	99.5	97.6	95.9	95.0
75°	108.6	102.0	95.1	90.5	86.7	82.9	80.6	78.7	77.9	77.5	75.9
77.5°	79.7	76.2	70.7	67.1	64.5	63.0	60.9	59.9	59.9	58.2	57.7
80°	61.0	59.1	54.4	52.9	51.0	49.5	48.4	46.5	44.5	43.7	42.6
82.5°	45.3	43.4	41.6	39.1	37.6	36.6	35.4	34.7	34.9	33.9	33.3
85°	24.1	22.2	21.5	21.1	20.3	21.1	20.7	20.3	20.0	19.6	20.0
87.5°	9.3	9.7	9.6	10.6	9.9	10.6	10.8	10.7	10.9	11.1	11.2
90°	8.1	10.1	11.1	13.1	14.1	16.2	17.2	18.2	19.2	20.2	22.2
92.5°	53.2	82.7	137.7	230.0	330.2	325.0	263.1	178.6	129.7	97.6	82.7
95°	75.6	121.0	228.8	450.6	728.9	893.2	874.0	724.9	571.6	447.6	362.9
97.5°	93.1	125.8	197.2	359.7	650.9	953.9	1105.9	1079.5	972.0	851.2	733.5
100°	106.8	137.1	195.6	326.6	580.7	910.3	1162.4	1240.0	1190.6	1086.7	981.9
102.5°	121.4	150.8	202.9	313.0	527.5	833.7	1128.5	1294.0	1324.4	1274.7	1203.7
105°	145.2	173.4	217.7	307.5	475.8	730.8	1020.3	1262.1	1400.3	1444.6	1433.5
107.5°	171.6	197.0	239.9	316.8	454.0	660.1	909.7	1148.4	1332.7	1446.6	1499.2
110°	188.5	214.7	256.1	325.6	447.6	627.0	846.8	1064.6	1256.1	1398.3	1484.0



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	206.2	231.7	271.4	336.9	447.6	607.7	800.0	998.5	1180.3	1324.0	1425.1
115°	232.9	258.1	295.4	353.9	450.6	586.7	749.0	915.3	1071.7	1209.7	1319.6
117.5°	260.3	284.7	320.0	373.2	457.3	576.4	718.6	861.7	996.4	1115.4	1216.2
120°	277.2	302.5	337.7	386.1	463.7	571.6	701.7	832.7	953.7	1064.6	1153.3
122.5°	294.2	319.4	354.7	400.6	469.4	567.5	687.1	810.9	923.0	1021.8	1104.9
125°	317.6	343.8	377.1	420.4	478.9	562.5	667.4	779.3	882.1	969.8	1042.4
127.5°	340.3	366.6	398.6	438.5	489.6	560.1	649.2	747.0	843.0	924.8	992.8
130°	354.9	381.0	412.3	450.6	496.0	558.5	637.1	726.9	815.6	894.2	959.8
132.5°	367.8	393.9	425.3	461.1	503.2	558.5	627.4	706.7	789.7	861.1	924.2
135°	384.1	411.3	442.5	475.8	513.1	558.5	615.9	680.4	750.0	814.6	872.0
137.5°	398.4	426.5	454.8	486.8	522.2	559.7	605.7	658.3	714.6	768.2	817.0
140°	407.3	434.5	463.7	494.0	526.2	560.5	600.9	646.2	693.6	739.9	782.3
142.5°	416.2	441.7	469.4	498.0	528.7	561.3	596.8	635.7	675.8	715.8	752.5
145°	429.5	452.6	478.9	504.0	531.3	560.5	590.8	622.0	653.3	684.5	711.8
147.5°	441.5	461.9	484.9	507.7	532.3	557.8	584.5	609.2	634.5	658.5	679.0
150°	449.6	466.8	489.0	510.1	532.3	555.4	579.7	601.9	624.0	643.2	661.4
152.5°	456.9	472.4	493.0	511.7	531.5	552.3	574.0	593.8	613.5	631.1	645.2
155°	465.7	479.9	497.0	513.1	529.3	546.4	564.5	581.7	597.8	612.0	623.0
157.5°	475.0	485.7	500.4	514.1	526.6	540.4	555.6	569.6	582.9	593.8	602.5
160°	479.9	489.0	502.0	514.1	524.2	536.3	548.5	561.5	571.6	581.7	588.8
162.5°	484.7	492.2	503.6	513.3	521.8	531.5	542.0	552.7	561.9	570.4	576.6
165°	490.0	496.0	504.0	512.1	518.2	524.2	532.3	540.4	547.4	553.5	558.5
167.5°	493.6	497.4	504.0	509.7	512.5	517.2	522.8	528.7	533.3	538.0	541.6
170°	496.0	499.0	504.0	508.1	510.1	513.1	517.2	522.2	525.2	528.3	530.3
172.5°	497.6	499.0	503.2	506.4	506.9	508.3	511.5	514.9	518.0	520.2	521.4
175°	499.0	499.0	502.0	504.0	503.0	503.0	504.0	507.1	507.1	509.1	509.1
177.5°	499.2	499.2	500.8	501.6	500.0	500.0	500.8	501.6	502.4	502.4	502.4
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.2	891.8	890.9	892.1	890.9	891.8	895.2	895.5	895.9	898.3	894.9
5°	826.0	822.1	824.0	823.2	824.0	822.1	826.0	829.8	830.5	833.9	836.3
7.5°	765.0	760.2	755.2	756.8	755.2	760.2	765.0	765.1	771.0	775.5	778.5
10°	722.4	718.5	716.2	718.1	716.2	718.5	722.4	727.3	729.6	735.0	740.7
12.5°	686.4	684.2	682.2	681.4	682.2	684.2	686.4	691.8	697.1	703.4	709.7
15°	637.5	633.0	631.1	626.1	631.1	633.0	637.5	642.2	652.6	655.2	664.8
17.5°	592.5	591.0	586.0	583.9	586.0	591.0	592.5	596.4	601.2	611.1	618.3
20°	565.8	564.3	559.4	562.4	559.4	564.3	565.8	571.6	575.4	583.5	590.4
22.5°	543.7	540.4	538.8	537.9	538.8	540.4	543.7	546.4	551.5	559.0	566.7
25°	512.5	507.6	505.6	503.3	505.6	507.6	512.5	514.0	519.4	526.7	530.9
27.5°	481.4	478.7	476.2	475.5	476.2	478.7	481.4	483.5	488.2	494.5	502.2
30°	461.1	458.4	456.5	456.5	456.5	458.4	461.1	465.7	469.2	474.9	480.7
32.5°	443.0	440.9	439.0	438.7	439.0	440.9	443.0	445.5	449.5	455.9	461.9
35°	416.6	413.5	412.7	410.5	412.7	413.5	416.6	418.5	422.7	427.4	432.3
37.5°	389.2	386.7	386.6	386.4	386.6	386.7	389.2	392.6	396.2	400.3	406.4
40°	371.7	369.8	369.4	366.8	369.4	369.8	371.7	373.2	377.1	382.4	387.1
42.5°	353.0	352.0	350.7	349.5	350.7	352.0	353.0	356.1	359.3	363.1	369.0
45°	327.6	325.0	325.0	323.1	325.0	325.0	327.6	330.3	331.8	336.4	344.1
47.5°	301.3	299.3	299.5	297.5	299.5	299.3	301.3	302.3	304.7	309.2	313.5
50°	283.9	282.8	282.4	281.6	282.4	282.8	283.9	283.5	286.6	290.7	296.5
52.5°	266.4	265.9	267.3	265.6	267.3	265.9	266.4	267.2	269.3	272.1	277.5
55°	242.9	241.7	244.0	241.7	244.0	241.7	242.9	242.1	242.9	245.5	248.9
57.5°	215.7	214.7	216.7	215.6	216.7	214.7	215.7	215.9	218.2	218.6	221.7
60°	197.9	195.6	196.8	197.2	196.8	195.6	197.9	198.7	199.4	199.9	203.0
62.5°	176.7	175.4	176.2	174.5	176.2	175.4	176.7	178.4	180.2	182.1	183.9
65°	146.9	145.8	144.2	143.5	144.2	145.8	146.9	147.7	151.9	154.2	158.4
67.5°	123.4	120.7	120.6	121.2	120.6	120.7	123.4	123.3	126.3	128.3	131.1
70°	106.2	106.2	105.8	105.8	105.8	106.2	106.2	108.6	110.1	111.6	113.5
72.5°	94.3	94.0	93.3	93.0	93.3	94.0	94.3	95.0	95.9	97.6	99.5
75°	75.9	76.3	75.5	75.2	75.5	76.3	75.9	75.9	77.5	77.9	78.7
77.5°	56.0	54.4	55.3	54.4	55.3	54.4	56.0	57.7	58.2	59.9	59.9
80°	42.6	42.2	43.3	42.2	43.3	42.2	42.6	42.6	43.7	44.5	46.5
82.5°	33.7	33.3	33.8	33.0	33.8	33.3	33.7	33.3	33.9	34.9	34.7
85°	20.3	20.0	19.6	20.0	19.6	20.0	20.3	20.0	19.6	20.0	20.3
87.5°	11.5	11.2	11.4	11.4	11.4	11.2	11.5	11.2	11.1	10.9	10.7
90°	22.2	22.2	23.2	23.2	23.2	22.2	22.2	22.2	20.2	19.2	18.2
92.5°	69.8	67.4	65.9	64.3	65.9	67.4	69.8	82.7	97.6	129.7	178.6
95°	291.3	261.2	253.1	236.9	253.1	261.2	291.3	362.9	447.6	571.6	724.9
97.5°	671.3	614.7	585.5	572.6	585.5	614.7	671.3	733.5	851.2	972.0	1079.5
100°	912.3	839.8	802.4	786.4	802.4	839.8	912.3	981.9	1086.7	1190.6	1240.0
102.5°	1129.3	1077.7	1037.1	1025.0	1037.1	1077.7	1129.3	1203.7	1274.7	1324.4	1294.0
105°	1401.3	1368.1	1347.9	1335.7	1347.9	1368.1	1401.3	1433.5	1444.6	1400.3	1262.1
107.5°	1515.6	1515.4	1508.7	1500.7	1508.7	1515.4	1515.6	1499.2	1446.6	1332.7	1148.4
110°	1529.3	1548.4	1555.5	1555.5	1555.5	1548.4	1529.3	1484.0	1398.3	1256.1	1064.6



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1491.4	1524.3	1541.9	1549.0	1541.9	1524.3	1491.4	1425.1	1324.0	1180.3	998.5
115°	1398.3	1446.6	1474.9	1488.0	1474.9	1446.6	1398.3	1319.6	1209.7	1071.7	915.3
117.5°	1294.8	1344.8	1372.8	1380.9	1372.8	1344.8	1294.8	1216.2	1115.4	996.4	861.7
120°	1227.9	1276.3	1303.5	1311.6	1303.5	1276.3	1227.9	1153.3	1064.6	953.7	832.7
122.5°	1171.4	1215.8	1243.0	1250.3	1243.0	1215.8	1171.4	1104.9	1021.8	923.0	810.9
125°	1098.8	1140.1	1162.4	1172.5	1162.4	1140.1	1098.8	1042.4	969.8	882.1	779.3
127.5°	1044.0	1080.5	1101.5	1105.9	1101.5	1080.5	1044.0	992.8	924.8	843.0	747.0
130°	1010.2	1043.4	1063.6	1069.6	1063.6	1043.4	1010.2	959.8	894.2	815.6	726.9
132.5°	974.6	1007.9	1026.4	1033.3	1026.4	1007.9	974.6	924.2	861.1	789.7	706.7
135°	916.4	949.7	967.8	973.8	967.8	949.7	916.4	872.0	814.6	750.0	680.4
137.5°	856.7	887.0	903.7	910.3	903.7	887.0	856.7	817.0	768.2	714.6	658.3
140°	819.6	845.9	860.9	866.0	860.9	845.9	819.6	782.3	739.9	693.6	646.2
142.5°	784.2	806.3	820.6	824.9	820.6	806.3	784.2	752.5	715.8	675.8	635.7
145°	735.9	753.1	764.2	768.2	764.2	753.1	735.9	711.8	684.5	653.3	622.0
147.5°	698.2	712.0	718.4	720.2	718.4	712.0	698.2	679.0	658.5	634.5	609.2
150°	676.4	688.5	692.6	693.6	692.6	688.5	676.4	661.4	643.2	624.0	601.9
152.5°	657.9	667.6	671.6	672.6	671.6	667.6	657.9	645.2	631.1	613.5	593.8
155°	633.1	640.2	643.2	644.2	643.2	640.2	633.1	623.0	612.0	597.8	581.7
157.5°	610.4	616.1	618.9	618.7	618.9	616.1	610.4	602.5	593.8	582.9	569.6
160°	595.8	600.9	602.9	601.9	602.9	600.9	595.8	588.8	581.7	571.6	561.5
162.5°	582.1	586.3	586.7	586.5	586.7	586.3	582.1	576.6	570.4	561.9	552.7
165°	562.5	564.5	564.5	564.5	564.5	564.5	562.5	558.5	553.5	547.4	540.4
167.5°	543.6	545.4	544.6	544.4	544.6	545.4	543.6	541.6	538.0	533.3	528.7
170°	532.3	533.3	533.3	532.3	533.3	533.3	532.3	530.3	528.3	525.2	522.2
172.5°	521.8	523.6	522.0	521.0	522.0	523.6	521.8	521.4	520.2	518.0	514.9
175°	509.1	510.1	508.1	507.1	508.1	510.1	509.1	509.1	509.1	507.1	507.1
177.5°	501.6	502.4	500.0	500.0	500.0	502.4	501.6	502.4	502.4	502.4	501.6
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.9	899.2	901.0	905.3	911.5	914.5	918.9	921.9	926.2	931.4	935.7
5°	837.8	847.1	853.1	862.7	871.6	880.4	891.5	899.6	910.3	922.6	932.2
7.5°	784.0	795.5	805.7	818.3	832.9	844.2	858.8	873.5	890.4	907.8	924.2
10°	749.6	761.1	773.8	789.5	804.1	819.4	836.7	853.9	875.0	894.6	916.9
12.5°	715.5	728.2	742.5	760.0	777.7	797.3	814.9	834.2	857.0	882.3	906.2
15°	673.3	685.5	700.8	715.8	736.2	757.6	781.0	806.8	832.0	860.5	890.0
17.5°	627.9	641.4	658.3	675.6	697.0	722.2	745.2	773.3	801.7	834.9	869.6
20°	598.4	612.3	632.2	651.4	671.0	695.5	722.8	751.5	781.8	816.7	855.5
22.5°	575.1	584.9	604.6	624.1	647.0	672.2	698.8	728.8	761.8	798.0	838.6
25°	540.5	552.0	566.2	586.5	610.4	636.8	663.7	695.5	731.5	768.4	811.7
27.5°	509.8	519.2	533.2	549.2	572.9	600.4	628.9	662.2	699.1	736.6	782.2
30°	488.0	498.4	511.7	528.7	547.4	577.3	606.5	639.1	676.7	715.5	762.2
32.5°	469.0	479.6	491.2	507.2	527.5	554.0	584.1	616.1	654.3	694.3	739.8
35°	442.3	449.6	460.3	476.1	496.0	517.5	548.2	582.0	619.1	660.6	706.2
37.5°	411.8	421.2	431.9	445.6	463.0	486.3	514.8	549.0	583.5	623.2	664.8
40°	393.9	402.8	414.7	424.6	443.1	464.1	490.3	525.9	560.5	597.6	635.6
42.5°	375.9	384.4	394.5	406.9	423.4	443.9	468.2	501.4	538.4	573.4	605.3
45°	347.6	356.4	366.0	377.5	392.8	412.7	437.0	467.3	499.5	531.7	555.8
47.5°	320.4	328.7	337.8	349.6	363.8	383.0	404.7	431.4	462.7	490.1	507.4
50°	301.1	308.8	318.8	330.3	344.1	362.1	382.8	409.3	435.5	460.3	476.1
52.5°	282.2	290.7	300.6	310.6	323.9	341.8	361.0	383.8	408.7	429.0	442.0
55°	253.6	261.7	270.8	281.1	294.3	309.6	329.9	347.9	367.5	384.8	392.4
57.5°	226.0	233.1	241.8	252.5	264.3	278.5	294.6	311.9	325.8	338.0	346.7
60°	207.9	214.1	222.1	231.4	244.0	257.0	271.6	287.7	298.4	308.8	316.9
62.5°	189.6	195.3	203.1	211.4	222.5	234.6	248.6	261.7	272.1	279.0	288.3
65°	161.9	167.6	174.2	183.0	191.8	201.8	214.4	224.0	231.4	239.0	244.8
67.5°	136.2	141.0	147.1	154.1	161.5	171.1	180.9	188.8	193.9	198.4	205.4
70°	119.3	123.1	128.2	133.5	141.6	151.2	158.9	164.9	168.4	173.0	181.5
72.5°	102.1	106.5	111.3	116.6	123.1	131.2	137.9	144.1	146.3	150.0	155.3
75°	80.6	82.9	86.7	90.5	95.1	102.0	108.6	110.1	112.0	115.1	119.0
77.5°	60.9	63.0	64.5	67.1	70.7	76.2	79.7	82.0	82.5	83.6	87.4
80°	48.4	49.5	51.0	52.9	54.4	59.1	61.0	63.3	64.0	65.2	67.2
82.5°	35.4	36.6	37.6	39.1	41.6	43.4	45.3	47.7	47.8	48.7	49.0
85°	20.7	21.1	20.3	21.1	21.5	22.2	24.1	26.1	25.8	25.3	26.5
87.5°	10.8	10.6	9.9	10.6	9.6	9.7	9.3	9.2	9.4	9.6	10.0
90°	17.2	16.2	14.1	13.1	11.1	10.1	8.1	6.1	4.0	2.0	1.0
92.5°	263.1	325.0	330.2	230.0	137.7	82.7	53.2	35.9	23.4	14.9	12.3
95°	874.0	893.2	728.9	450.6	228.8	121.0	75.6	53.4	42.3	34.2	33.2
97.5°	1105.9	953.9	650.9	359.7	197.2	125.8	93.1	73.2	62.1	56.5	55.2
100°	1162.4	910.3	580.7	326.6	195.6	137.1	106.8	87.7	76.6	72.6	70.6
102.5°	1128.5	833.7	527.5	313.0	202.9	150.8	121.4	103.8	91.9	88.7	87.6
105°	1020.3	730.8	475.8	307.5	217.7	173.4	145.2	129.1	119.0	113.9	113.9
107.5°	909.7	660.1	454.0	316.8	239.9	197.0	171.6	154.8	146.5	141.8	139.8
110°	846.8	627.0	447.6	325.6	256.1	214.7	188.5	173.4	164.3	160.3	158.2



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	800.0	607.7	447.6	336.9	271.4	231.7	206.2	191.2	182.1	178.8	176.8
115°	749.0	586.7	450.6	353.9	295.4	258.1	232.9	217.7	208.6	205.6	203.7
117.5°	718.6	576.4	457.3	373.2	320.0	284.7	260.3	243.2	234.1	230.9	227.8
120°	701.7	571.6	463.7	386.1	337.7	302.5	277.2	260.1	251.1	247.0	244.0
122.5°	687.1	567.5	469.4	400.6	354.7	319.4	294.2	275.4	266.3	263.1	260.9
125°	667.4	562.5	478.9	420.4	377.1	343.8	317.6	298.4	289.3	284.3	282.3
127.5°	649.2	560.1	489.6	438.5	398.6	366.6	340.3	320.0	308.5	302.1	299.0
130°	637.1	558.5	496.0	450.6	412.3	381.0	354.9	333.7	320.6	312.6	309.5
132.5°	627.4	558.5	503.2	461.1	425.3	393.9	367.8	345.8	331.0	321.3	317.6
135°	615.9	558.5	513.1	475.8	442.5	411.3	384.1	362.9	346.8	334.7	330.6
137.5°	605.7	559.7	522.2	486.8	454.8	426.5	398.4	377.7	361.5	350.2	347.2
140°	600.9	560.5	526.2	494.0	463.7	434.5	407.3	388.1	372.0	359.9	356.9
142.5°	596.8	561.3	528.7	498.0	469.4	441.7	416.2	397.8	381.6	370.4	368.2
145°	590.8	560.5	531.3	504.0	478.9	452.6	429.5	411.3	397.2	387.1	385.1
147.5°	584.5	557.8	532.3	507.7	484.9	461.9	441.5	425.9	412.7	404.0	402.8
150°	579.7	555.4	532.3	510.1	489.0	466.8	449.6	435.6	422.4	415.4	413.3
152.5°	574.0	552.3	531.5	511.7	493.0	472.4	456.9	443.5	432.1	425.9	424.6
155°	564.5	546.4	529.3	513.1	497.0	479.9	465.7	455.7	445.6	439.5	439.5
157.5°	555.6	540.4	526.6	514.1	500.4	485.7	475.0	466.2	457.5	452.6	452.8
160°	548.5	536.3	524.2	514.1	502.0	489.0	479.9	471.8	464.7	460.7	461.7
162.5°	542.0	531.5	521.8	513.3	503.6	492.2	484.7	478.3	472.0	468.0	469.0
165°	532.3	524.2	518.2	512.1	504.0	496.0	490.0	485.9	480.9	477.9	479.9
167.5°	522.8	517.2	512.5	509.7	504.0	497.4	493.6	490.8	488.0	486.1	487.2
170°	517.2	513.1	510.1	508.1	504.0	499.0	496.0	494.0	492.0	491.0	492.0
172.5°	511.5	508.3	506.9	506.4	503.2	499.0	497.6	496.3	494.4	493.4	495.2
175°	504.0	503.0	503.0	504.0	502.0	499.0	499.0	499.0	498.0	497.0	499.0
177.5°	500.8	500.0	500.0	501.6	500.8	499.2	499.2	500.0	499.2	499.2	500.8
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	939.1	941.9	945.8	950.5	954.1	958.2	960.3	960.3	962.1	966.1	971.3
5°	941.8	951.8	961.4	973.6	983.2	994.3	1002.8	1010.9	1018.1	1027.3	1036.9
7.5°	941.0	957.6	974.8	994.2	1015.5	1032.5	1049.9	1063.6	1077.0	1094.7	1108.6
10°	938.0	959.5	982.8	1007.3	1034.2	1057.6	1078.7	1097.9	1116.3	1135.5	1152.8
12.5°	932.4	959.8	988.4	1017.8	1051.8	1078.5	1105.7	1126.2	1147.6	1168.6	1189.9
15°	924.1	956.3	990.9	1032.0	1073.4	1103.3	1130.1	1156.6	1176.6	1200.3	1220.7
17.5°	907.1	948.6	992.0	1036.8	1076.6	1111.5	1139.5	1164.8	1186.0	1212.1	1239.8
20°	896.9	941.8	987.0	1035.0	1073.0	1108.6	1135.9	1162.0	1188.4	1222.6	1256.4
22.5°	882.8	930.7	978.8	1024.3	1064.4	1098.8	1127.0	1158.9	1193.7	1232.4	1273.2
25°	860.5	910.0	957.6	1000.9	1040.0	1075.3	1113.7	1156.6	1198.8	1249.8	1308.5
27.5°	832.1	879.9	922.3	968.1	1007.0	1051.9	1099.7	1146.3	1207.2	1277.4	1350.7
30°	810.9	856.3	896.6	939.9	984.0	1033.5	1087.2	1142.1	1214.6	1297.0	1384.1
32.5°	786.4	827.4	867.4	909.2	960.1	1014.4	1071.6	1138.6	1225.3	1319.1	1409.3
35°	743.9	780.6	819.4	865.9	919.9	979.0	1051.9	1133.6	1238.3	1339.2	1420.2
37.5°	699.2	728.2	767.2	816.1	875.0	943.4	1026.1	1125.4	1232.9	1323.5	1358.0
40°	664.8	692.1	733.1	784.5	842.8	917.7	1010.5	1112.5	1220.7	1283.5	1280.9
42.5°	630.8	658.3	697.8	749.5	810.3	894.0	989.6	1095.6	1186.9	1210.8	1160.9
45°	578.5	604.2	643.0	695.1	760.3	848.2	948.7	1050.4	1108.6	1070.0	971.0
47.5°	525.2	550.2	586.1	637.2	708.4	800.4	895.4	978.9	987.0	903.8	785.1
50°	490.3	513.6	547.9	602.3	671.4	761.1	852.8	918.4	898.1	796.4	674.0
52.5°	456.2	478.7	510.7	562.1	632.7	720.6	802.4	853.9	806.9	698.8	588.8
55°	405.9	427.4	459.6	506.8	570.8	651.4	723.2	741.9	672.9	563.9	474.9
57.5°	358.1	373.8	405.7	447.4	509.2	580.2	631.6	628.2	552.0	453.9	390.1
60°	326.5	340.6	370.9	409.3	468.0	531.7	567.7	552.4	475.3	394.4	333.0
62.5°	297.0	310.2	335.7	370.9	421.4	476.8	503.0	481.8	409.0	337.9	289.1
65°	252.5	262.1	282.4	315.0	354.5	392.8	416.3	385.2	320.7	267.0	230.1
67.5°	210.8	219.0	237.1	260.5	287.8	314.3	323.8	294.6	244.5	208.3	182.4
70°	183.8	191.5	203.7	225.6	243.6	262.4	267.0	241.0	199.1	171.5	155.3
72.5°	157.9	165.0	175.8	191.2	203.7	214.5	216.7	192.4	160.5	141.4	129.0
75°	120.5	126.6	133.5	139.3	147.3	149.3	148.5	129.7	112.4	99.8	92.8
77.5°	88.6	91.1	95.3	97.6	98.0	97.9	93.9	82.0	73.1	67.9	65.0
80°	68.3	70.2	71.4	72.1	72.5	68.7	64.4	57.2	54.1	51.0	47.6
82.5°	49.6	50.9	52.0	52.2	50.1	46.9	42.9	39.4	37.2	35.6	34.3
85°	26.9	27.3	26.9	24.9	22.2	21.1	20.3	19.6	19.2	18.8	18.8
87.5°	9.9	9.4	8.3	9.0	9.4	9.3	9.7	9.6	9.7	9.9	10.1
90°	2.0	4.0	6.1	8.1	10.1	11.1	13.1	14.1	16.2	17.2	18.2
92.5°	14.9	23.4	35.9	53.2	82.7	137.7	230.0	330.2	325.0	263.1	178.6
95°	34.2	42.3	53.4	75.6	121.0	228.8	450.6	728.9	893.2	874.0	724.9
97.5°	56.5	62.1	73.2	93.1	125.8	197.2	359.7	650.9	953.9	1105.9	1079.5
100°	72.6	76.6	87.7	106.8	137.1	195.6	326.6	580.7	910.3	1162.4	1240.0
102.5°	88.7	91.9	103.8	121.4	150.8	202.9	313.0	527.5	833.7	1128.5	1294.0
105°	113.9	119.0	129.1	145.2	173.4	217.7	307.5	475.8	730.8	1020.3	1262.1
107.5°	141.8	146.5	154.8	171.6	197.0	239.9	316.8	454.0	660.1	909.7	1148.4
110°	160.3	164.3	173.4	188.5	214.7	256.1	325.6	447.6	627.0	846.8	1064.6



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	178.8	182.1	191.2	206.2	231.7	271.4	336.9	447.6	607.7	800.0	998.5
115°	205.6	208.6	217.7	232.9	258.1	295.4	353.9	450.6	586.7	749.0	915.3
117.5°	230.9	234.1	243.2	260.3	284.7	320.0	373.2	457.3	576.4	718.6	861.7
120°	247.0	251.1	260.1	277.2	302.5	337.7	386.1	463.7	571.6	701.7	832.7
122.5°	263.1	266.3	275.4	294.2	319.4	354.7	400.6	469.4	567.5	687.1	810.9
125°	284.3	289.3	298.4	317.6	343.8	377.1	420.4	478.9	562.5	667.4	779.3
127.5°	302.1	308.5	320.0	340.3	366.6	398.6	438.5	489.6	560.1	649.2	747.0
130°	312.6	320.6	333.7	354.9	381.0	412.3	450.6	496.0	558.5	637.1	726.9
132.5°	321.3	331.0	345.8	367.8	393.9	425.3	461.1	503.2	558.5	627.4	706.7
135°	334.7	346.8	362.9	384.1	411.3	442.5	475.8	513.1	558.5	615.9	680.4
137.5°	350.2	361.5	377.7	398.4	426.5	454.8	486.8	522.2	559.7	605.7	658.3
140°	359.9	372.0	388.1	407.3	434.5	463.7	494.0	526.2	560.5	600.9	646.2
142.5°	370.4	381.6	397.8	416.2	441.7	469.4	498.0	528.7	561.3	596.8	635.7
145°	387.1	397.2	411.3	429.5	452.6	478.9	504.0	531.3	560.5	590.8	622.0
147.5°	404.0	412.7	425.9	441.5	461.9	484.9	507.7	532.3	557.8	584.5	609.2
150°	415.4	422.4	435.6	449.6	466.8	489.0	510.1	532.3	555.4	579.7	601.9
152.5°	425.9	432.1	443.5	456.9	472.4	493.0	511.7	531.5	552.3	574.0	593.8
155°	439.5	445.6	455.7	465.7	479.9	497.0	513.1	529.3	546.4	564.5	581.7
157.5°	452.6	457.5	466.2	475.0	485.7	500.4	514.1	526.6	540.4	555.6	569.6
160°	460.7	464.7	471.8	479.9	489.0	502.0	514.1	524.2	536.3	548.5	561.5
162.5°	468.0	472.0	478.3	484.7	492.2	503.6	513.3	521.8	531.5	542.0	552.7
165°	477.9	480.9	485.9	490.0	496.0	504.0	512.1	518.2	524.2	532.3	540.4
167.5°	486.1	488.0	490.8	493.6	497.4	504.0	509.7	512.5	517.2	522.8	528.7
170°	491.0	492.0	494.0	496.0	499.0	504.0	508.1	510.1	513.1	517.2	522.2
172.5°	493.4	494.4	496.3	497.6	499.0	503.2	506.4	506.9	508.3	511.5	514.9
175°	497.0	498.0	499.0	499.0	499.0	502.0	504.0	503.0	503.0	504.0	507.1
177.5°	499.2	499.2	500.0	499.2	499.2	500.8	501.6	500.0	500.0	500.8	501.6
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0	500.0



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	975.3	975.3	980.6	980.2	983.6	982.4	983.0
5°	1048.4	1054.9	1060.7	1064.5	1070.3	1071.9	1071.1
7.5°	1124.3	1138.7	1145.8	1155.5	1157.2	1162.3	1161.7
10°	1171.1	1185.4	1196.1	1204.6	1208.8	1214.2	1214.6
12.5°	1208.0	1220.0	1229.6	1237.4	1242.5	1244.3	1245.3
15°	1236.8	1250.2	1261.3	1272.4	1279.0	1283.9	1286.7
17.5°	1265.8	1286.5	1306.2	1321.3	1330.3	1338.0	1337.9
20°	1288.2	1312.0	1336.6	1353.8	1371.4	1379.1	1380.3
22.5°	1312.1	1348.5	1380.1	1406.8	1430.1	1438.0	1441.0
25°	1361.8	1409.4	1458.1	1495.7	1522.6	1538.3	1540.7
27.5°	1421.9	1486.3	1537.5	1572.3	1594.6	1606.2	1608.7
30°	1464.3	1523.7	1569.7	1595.9	1606.2	1607.7	1601.9
32.5°	1483.3	1527.7	1546.1	1544.6	1524.3	1510.8	1505.6
35°	1460.1	1450.9	1405.9	1352.2	1311.2	1285.2	1278.2
37.5°	1328.7	1249.3	1166.7	1085.6	1042.4	1020.5	982.7
40°	1199.2	1086.0	1000.1	931.8	883.1	843.9	834.8
42.5°	1053.1	936.2	850.3	791.8	753.0	726.1	714.5
45°	846.3	745.8	674.8	629.9	600.0	580.4	571.6
47.5°	676.8	599.1	547.3	514.1	491.3	474.3	469.6
50°	583.9	521.7	478.0	450.0	432.7	419.7	414.3
52.5°	507.2	457.0	423.3	400.3	384.0	375.8	371.3
55°	418.5	375.2	351.0	332.5	323.4	316.9	313.8
57.5°	342.2	310.9	293.3	280.5	272.1	267.9	266.4
60°	299.6	275.1	258.9	248.9	243.2	237.8	236.3
62.5°	261.9	242.6	230.0	221.4	215.6	213.3	212.4
65°	211.0	198.3	189.1	183.8	179.2	178.3	178.0
67.5°	167.7	160.3	155.4	149.9	148.2	145.5	145.0
70°	143.5	138.5	132.7	130.8	128.9	126.2	126.6
72.5°	121.7	116.7	112.8	110.3	109.6	108.5	109.4
75°	89.0	87.5	85.9	84.0	83.2	83.2	82.9
77.5°	63.5	62.2	60.5	59.4	59.2	57.6	58.2
80°	46.0	44.1	43.3	43.7	42.6	42.2	42.2
82.5°	34.0	33.3	32.6	32.7	32.4	32.1	32.4
85°	18.8	18.4	18.4	18.1	18.1	17.7	17.7
87.5°	10.6	11.1	10.9	10.6	10.6	11.1	11.4
90°	19.2	20.2	22.2	22.2	22.2	23.2	23.2
92.5°	129.7	97.6	82.7	69.8	67.4	65.9	64.3
95°	571.6	447.6	362.9	291.3	261.2	253.1	236.9
97.5°	972.0	851.2	733.5	671.3	614.7	585.5	572.6
100°	1190.6	1086.7	981.9	912.3	839.8	802.4	786.4
102.5°	1324.4	1274.7	1203.7	1129.3	1077.7	1037.1	1025.0
105°	1400.3	1444.6	1433.5	1401.3	1368.1	1347.9	1335.7
107.5°	1332.7	1446.6	1499.2	1515.6	1515.4	1508.7	1500.7
110°	1256.1	1398.3	1484.0	1529.3	1548.4	1555.5	1555.5



TEST NUMBER: P333540-840

CATALOG NUMBER: S125RDIP-S610D1035U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1180.3	1324.0	1425.1	1491.4	1524.3	1541.9	1549.0
115°	1071.7	1209.7	1319.6	1398.3	1446.6	1474.9	1488.0
117.5°	996.4	1115.4	1216.2	1294.8	1344.8	1372.8	1380.9
120°	953.7	1064.6	1153.3	1227.9	1276.3	1303.5	1311.6
122.5°	923.0	1021.8	1104.9	1171.4	1215.8	1243.0	1250.3
125°	882.1	969.8	1042.4	1098.8	1140.1	1162.4	1172.5
127.5°	843.0	924.8	992.8	1044.0	1080.5	1101.5	1105.9
130°	815.6	894.2	959.8	1010.2	1043.4	1063.6	1069.6
132.5°	789.7	861.1	924.2	974.6	1007.9	1026.4	1033.3
135°	750.0	814.6	872.0	916.4	949.7	967.8	973.8
137.5°	714.6	768.2	817.0	856.7	887.0	903.7	910.3
140°	693.6	739.9	782.3	819.6	845.9	860.9	866.0
142.5°	675.8	715.8	752.5	784.2	806.3	820.6	824.9
145°	653.3	684.5	711.8	735.9	753.1	764.2	768.2
147.5°	634.5	658.5	679.0	698.2	712.0	718.4	720.2
150°	624.0	643.2	661.4	676.4	688.5	692.6	693.6
152.5°	613.5	631.1	645.2	657.9	667.6	671.6	672.6
155°	597.8	612.0	623.0	633.1	640.2	643.2	644.2
157.5°	582.9	593.8	602.5	610.4	616.1	618.9	618.7
160°	571.6	581.7	588.8	595.8	600.9	602.9	601.9
162.5°	561.9	570.4	576.6	582.1	586.3	586.7	586.5
165°	547.4	553.5	558.5	562.5	564.5	564.5	564.5
167.5°	533.3	538.0	541.6	543.6	545.4	544.6	544.4
170°	525.2	528.3	530.3	532.3	533.3	533.3	532.3
172.5°	518.0	520.2	521.4	521.8	523.6	522.0	521.0
175°	507.1	509.1	509.1	509.1	510.1	508.1	507.1
177.5°	502.4	502.4	502.4	501.6	502.4	500.0	500.0
180°	500.0	500.0	500.0	500.0	500.0	500.0	500.0

(END OF REPORT)