

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333546-840

Luminaire Tested: **S125RDIP-S610D1205U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333546-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1205U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6789.0 lumens
Efficiency: N/A
Efficacy: 137.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	38	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27	22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19
5	66	55	48	42	60	50	44	39	41	36	32	33	29	26	25	22	21	17
6	61	50	42	36	55	45	38	34	37	32	28	30	26	23	22	20	18	15
7	57	45	37	32	51	41	34	29	34	29	25	27	23	20	21	18	16	13
8	52	41	33	28	47	37	31	26	31	26	22	25	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6035	6035	6035	6035
5°	6944	6043	5337	6043
10°	7965	6013	4709	6013
15°	8603	5951	4186	5951
20°	9487	5880	3865	5880
25°	10979	5784	3587	5784
30°	11946	5684	3404	5684
35°	10078	5568	3236	5568
40°	7038	5359	3092	5359
45°	5221	5076	2951	5076
50°	4163	4784	2829	4784
55°	3533	4418	2721	4418
60°	3052	4093	2547	4093
65°	2720	3741	2193	3741
70°	2391	3427	1998	3427
75°	2069	2969	1876	2969
80°	1570	2499	1570	2499
85°	1312	1964	1482	1964



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.3
10°-20°	262.6	3.9
20°-30°	416.4	6.1
30°-40°	502.1	7.4
40°-50°	448.4	6.6
50°-60°	343.9	5.1
60°-70°	223.5	3.3
70°-80°	108.6	1.6
80°-90°	29.2	0.4
90°-100°	421.9	6.2
100°-110°	906.9	13.4
110°-120°	851.1	12.5
120°-130°	689.8	10.2
130°-140°	553.5	8.2
140°-150°	417.7	6.2
150°-160°	294.0	4.3
160°-170°	173.3	2.6
170°-180°	56.4	0.8
0°-30°	768.6	11.3
0°-40°	1270.8	18.7
0°-60°	2063.1	30.4
0°-90°	2424.4	35.7
90°-120°	2179.9	32.1
90°-150°	3840.9	56.6
90°-180°	4365.0	64.3
0°-180°	6789.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	934	934	934	934	934	
5°	1071	932	823	932	1071	107
15°	1287	890	626	890	1287	369
25°	1541	812	503	812	1541	707
35°	1278	706	410	706	1278	772
45°	572	556	323	556	572	456
55°	314	392	242	392	314	285
65°	178	245	144	245	178	177
75°	83	119	75	119	83	88
85°	18	26	20	26	18	21
90°	27	1	27	1	27	19
95°	276	39	276	39	276	391
105°	1555	133	1555	133	1555	1545
115°	1732	237	1732	237	1732	1692
125°	1365	328	1365	328	1365	1235
135°	1134	385	1134	385	1134	878
145°	894	448	894	448	894	568
155°	750	512	750	512	750	349
165°	657	559	657	559	657	188
175°	590	581	590	581	590	57
180°	582	582	582	582	582	



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	983.0	982.4	983.6	980.2	980.6	975.3	975.3	971.3	966.1	962.1	960.3
5°	1071.1	1071.9	1070.3	1064.5	1060.7	1054.9	1048.4	1036.9	1027.3	1018.1	1010.9
7.5°	1161.7	1162.3	1157.2	1155.5	1145.8	1138.7	1124.3	1108.6	1094.7	1077.0	1063.6
10°	1214.6	1214.2	1208.8	1204.6	1196.1	1185.4	1171.1	1152.8	1135.5	1116.3	1097.9
12.5°	1245.3	1244.3	1242.5	1237.4	1229.6	1220.0	1208.0	1189.9	1168.6	1147.6	1126.2
15°	1286.7	1283.9	1279.0	1272.4	1261.3	1250.2	1236.8	1220.7	1200.3	1176.6	1156.6
17.5°	1337.9	1338.0	1330.3	1321.3	1306.2	1286.5	1265.8	1239.8	1212.1	1186.0	1164.8
20°	1380.3	1379.1	1371.4	1353.8	1336.6	1312.0	1288.2	1256.4	1222.6	1188.4	1162.0
22.5°	1441.0	1438.0	1430.1	1406.8	1380.1	1348.5	1312.1	1273.2	1232.4	1193.7	1158.9
25°	1540.7	1538.3	1522.6	1495.7	1458.1	1409.4	1361.8	1308.5	1249.8	1198.8	1156.6
27.5°	1608.7	1606.2	1594.6	1572.3	1537.5	1486.3	1421.9	1350.7	1277.4	1207.2	1146.3
30°	1601.9	1607.7	1606.2	1595.9	1569.7	1523.7	1464.3	1384.1	1297.0	1214.6	1142.1
32.5°	1505.6	1510.8	1524.3	1544.6	1546.1	1527.7	1483.3	1409.3	1319.1	1225.3	1138.6
35°	1278.2	1285.2	1311.2	1352.2	1405.9	1450.9	1460.1	1420.2	1339.2	1238.3	1133.6
37.5°	982.7	1020.5	1042.4	1085.6	1166.7	1249.3	1328.7	1358.0	1323.5	1232.9	1125.4
40°	834.8	843.9	883.1	931.8	1000.1	1086.0	1199.2	1280.9	1283.5	1220.7	1112.5
42.5°	714.5	726.1	753.0	791.8	850.3	936.2	1053.1	1160.9	1210.8	1186.9	1095.6
45°	571.6	580.4	600.0	629.9	674.8	745.8	846.3	971.0	1070.0	1108.6	1050.4
47.5°	469.6	474.3	491.3	514.1	547.3	599.1	676.8	785.1	903.8	987.0	978.9
50°	414.3	419.7	432.7	450.0	478.0	521.7	583.9	674.0	796.4	898.1	918.4
52.5°	371.3	375.8	384.0	400.3	423.3	457.0	507.2	588.8	698.8	806.9	853.9
55°	313.8	316.9	323.4	332.5	351.0	375.2	418.5	474.9	563.9	672.9	741.9
57.5°	266.4	267.9	272.1	280.5	293.3	310.9	342.2	390.1	453.9	552.0	628.2
60°	236.3	237.8	243.2	248.9	258.9	275.1	299.6	333.0	394.4	475.3	552.4
62.5°	212.4	213.3	215.6	221.4	230.0	242.6	261.9	289.1	337.9	409.0	481.8
65°	178.0	178.3	179.2	183.8	189.1	198.3	211.0	230.1	267.0	320.7	385.2
67.5°	145.0	145.5	148.2	149.9	155.4	160.3	167.7	182.4	208.3	244.5	294.6
70°	126.6	126.2	128.9	130.8	132.7	138.5	143.5	155.3	171.5	199.1	241.0
72.5°	109.4	108.5	109.6	110.3	112.8	116.7	121.7	129.0	141.4	160.5	192.4
75°	82.9	83.2	83.2	84.0	85.9	87.5	89.0	92.8	99.8	112.4	129.7
77.5°	58.2	57.6	59.2	59.4	60.5	62.2	63.5	65.0	67.9	73.1	82.0
80°	42.2	42.2	42.6	43.7	43.3	44.1	46.0	47.6	51.0	54.1	57.2
82.5°	32.4	32.1	32.4	32.7	32.6	33.3	34.0	34.3	35.6	37.2	39.4
85°	17.7	17.7	18.1	18.1	18.4	18.4	18.8	18.8	18.8	19.2	19.6
87.5°	12.1	11.8	11.3	11.3	11.6	11.7	11.2	10.7	10.4	10.2	10.0
90°	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1	20.0	18.8	16.5
92.5°	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9	306.3	378.3	384.5
95°	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6	1017.3	1039.7	848.4
97.5°	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5	1287.3	1110.2	757.6
100°	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3	1352.9	1059.6	675.9
102.5°	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2	1313.5	970.4	613.9
105°	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2	1187.5	850.7	553.8
107.5°	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8	1058.9	768.3	528.5
110°	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1	985.6	729.8	521.0



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2	931.2	707.3	521.0
115°	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5	871.8	683.0	524.5
117.5°	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0	836.4	671.0	532.3
120°	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3	816.7	665.3	539.8
122.5°	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9	799.8	660.7	546.3
125°	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1	776.8	654.8	557.3
127.5°	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5	755.7	652.0	569.8
130°	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1	741.6	650.1	577.3
132.5°	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5	730.3	650.1	585.7
135°	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0	717.0	650.1	597.2
137.5°	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3	705.0	651.5	607.8
140°	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1	699.3	652.4	612.5
142.5°	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9	694.7	653.4	615.3
145°	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0	687.6	652.4	618.4
147.5°	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0	680.3	649.3	619.6
150°	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5	674.7	646.5	619.6
152.5°	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2	668.1	642.8	618.6
155°	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0	657.1	636.0	616.0
157.5°	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0	646.8	628.9	613.0
160°	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6	638.3	624.3	610.2
162.5°	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3	630.9	618.6	607.3
165°	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9	619.6	610.2	603.1
167.5°	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3	608.5	602.0	596.5
170°	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8	602.0	597.2	593.8
172.5°	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4	595.4	591.7	590.0
175°	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3	586.7	585.5	585.5
177.5°	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9	583.0	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	960.3	958.2	954.1	950.5	945.8	941.9	939.1	935.7	931.4	926.2	921.9
5°	1002.8	994.3	983.2	973.6	961.4	951.8	941.8	932.2	922.6	910.3	899.6
7.5°	1049.9	1032.5	1015.5	994.2	974.8	957.6	941.0	924.2	907.8	890.4	873.5
10°	1078.7	1057.6	1034.2	1007.3	982.8	959.5	938.0	916.9	894.6	875.0	853.9
12.5°	1105.7	1078.5	1051.8	1017.8	988.4	959.8	932.4	906.2	882.3	857.0	834.2
15°	1130.1	1103.3	1073.4	1032.0	990.9	956.3	924.1	890.0	860.5	832.0	806.8
17.5°	1139.5	1111.5	1076.6	1036.8	992.0	948.6	907.1	869.6	834.9	801.7	773.3
20°	1135.9	1108.6	1073.0	1035.0	987.0	941.8	896.9	855.5	816.7	781.8	751.5
22.5°	1127.0	1098.8	1064.4	1024.3	978.8	930.7	882.8	838.6	798.0	761.8	728.8
25°	1113.7	1075.3	1040.0	1000.9	957.6	910.0	860.5	811.7	768.4	731.5	695.5
27.5°	1099.7	1051.9	1007.0	968.1	922.3	879.9	832.1	782.2	736.6	699.1	662.2
30°	1087.2	1033.5	984.0	939.9	896.6	856.3	810.9	762.2	715.5	676.7	639.1
32.5°	1071.6	1014.4	960.1	909.2	867.4	827.4	786.4	739.8	694.3	654.3	616.1
35°	1051.9	979.0	919.9	865.9	819.4	780.6	743.9	706.2	660.6	619.1	582.0
37.5°	1026.1	943.4	875.0	816.1	767.2	728.2	699.2	664.8	623.2	583.5	549.0
40°	1010.5	917.7	842.8	784.5	733.1	692.1	664.8	635.6	597.6	560.5	525.9
42.5°	989.6	894.0	810.3	749.5	697.8	658.3	630.8	605.3	573.4	538.4	501.4
45°	948.7	848.2	760.3	695.1	643.0	604.2	578.5	555.8	531.7	499.5	467.3
47.5°	895.4	800.4	708.4	637.2	586.1	550.2	525.2	507.4	490.1	462.7	431.4
50°	852.8	761.1	671.4	602.3	547.9	513.6	490.3	476.1	460.3	435.5	409.3
52.5°	802.4	720.6	632.7	562.1	510.7	478.7	456.2	442.0	429.0	408.7	383.8
55°	723.2	651.4	570.8	506.8	459.6	427.4	405.9	392.4	384.8	367.5	347.9
57.5°	631.6	580.2	509.2	447.4	405.7	373.8	358.1	346.7	338.0	325.8	311.9
60°	567.7	531.7	468.0	409.3	370.9	340.6	326.5	316.9	308.8	298.4	287.7
62.5°	503.0	476.8	421.4	370.9	335.7	310.2	297.0	288.3	279.0	272.1	261.7
65°	416.3	392.8	354.5	315.0	282.4	262.1	252.5	244.8	239.0	231.4	224.0
67.5°	323.8	314.3	287.8	260.5	237.1	219.0	210.8	205.4	198.4	193.9	188.8
70°	267.0	262.4	243.6	225.6	203.7	191.5	183.8	181.5	173.0	168.4	164.9
72.5°	216.7	214.5	203.7	191.2	175.8	165.0	157.9	155.3	150.0	146.3	144.1
75°	148.5	149.3	147.3	139.3	133.5	126.6	120.5	119.0	115.1	112.0	110.1
77.5°	93.9	97.9	98.0	97.6	95.3	91.1	88.6	87.4	83.6	82.5	82.0
80°	64.4	68.7	72.5	72.1	71.4	70.2	68.3	67.2	65.2	64.0	63.3
82.5°	42.9	46.9	50.1	52.2	52.0	50.9	49.6	49.0	48.7	47.8	47.7
85°	20.3	21.1	22.2	24.9	26.9	27.3	26.9	26.5	25.3	25.8	26.1
87.5°	10.1	9.6	9.7	9.3	8.5	9.5	10.0	10.1	9.7	9.5	9.4
90°	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2	2.3	4.6	7.1
92.5°	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3	17.4	27.3	41.8
95°	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7	39.9	49.3	62.2
97.5°	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3	65.7	72.3	85.2
100°	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1	84.5	89.2	102.1
102.5°	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9	103.3	107.0	120.9
105°	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6	132.6	138.5	150.2
107.5°	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6	165.0	170.6	180.3
110°	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2	186.6	191.3	201.9



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8	208.1	211.9	222.5
115°	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0	239.3	242.9	253.5
117.5°	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2	268.7	272.5	283.1
120°	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0	287.5	292.2	302.8
122.5°	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7	306.3	310.0	320.5
125°	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5	330.9	336.8	347.3
127.5°	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0	351.5	359.1	372.4
130°	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2	363.8	373.1	388.4
132.5°	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6	374.1	385.4	402.5
135°	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9	389.6	403.6	422.4
137.5°	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1	407.7	420.8	439.6
140°	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4	418.9	433.0	451.8
142.5°	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5	431.1	444.2	463.0
145°	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3	450.6	462.3	478.8
147.5°	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9	470.3	480.4	495.6
150°	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1	483.4	491.7	507.0
152.5°	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2	495.6	502.9	516.3
155°	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6	511.6	518.7	530.4
157.5°	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1	526.8	532.5	542.6
160°	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5	536.2	541.0	549.2
162.5°	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8	544.7	549.4	556.6
165°	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6	556.2	559.8	565.6
167.5°	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0	565.8	567.9	571.2
170°	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6	571.5	572.6	575.0
172.5°	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4	574.3	575.4	577.7
175°	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9	578.5	579.7	580.9
177.5°	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0	581.1	581.1	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	918.9	914.5	911.5	905.3	901.0	899.2	895.9	894.9	898.3	895.9	895.5
5°	891.5	880.4	871.6	862.7	853.1	847.1	837.8	836.3	833.9	830.5	829.8
7.5°	858.8	844.2	832.9	818.3	805.7	795.5	784.0	778.5	775.5	771.0	765.1
10°	836.7	819.4	804.1	789.5	773.8	761.1	749.6	740.7	735.0	729.6	727.3
12.5°	814.9	797.3	777.7	760.0	742.5	728.2	715.5	709.7	703.4	697.1	691.8
15°	781.0	757.6	736.2	715.8	700.8	685.5	673.3	664.8	655.2	652.6	642.2
17.5°	745.2	722.2	697.0	675.6	658.3	641.4	627.9	618.3	611.1	601.2	596.4
20°	722.8	695.5	671.0	651.4	632.2	612.3	598.4	590.4	583.5	575.4	571.6
22.5°	698.8	672.2	647.0	624.1	604.6	584.9	575.1	566.7	559.0	551.5	546.4
25°	663.7	636.8	610.4	586.5	566.2	552.0	540.5	530.9	526.7	519.4	514.0
27.5°	628.9	600.4	572.9	549.2	533.2	519.2	509.8	502.2	494.5	488.2	483.5
30°	606.5	577.3	547.4	528.7	511.7	498.4	488.0	480.7	474.9	469.2	465.7
32.5°	584.1	554.0	527.5	507.2	491.2	479.6	469.0	461.9	455.9	449.5	445.5
35°	548.2	517.5	496.0	476.1	460.3	449.6	442.3	432.3	427.4	422.7	418.5
37.5°	514.8	486.3	463.0	445.6	431.9	421.2	411.8	406.4	400.3	396.2	392.6
40°	490.3	464.1	443.1	424.6	414.7	402.8	393.9	387.1	382.4	377.1	373.2
42.5°	468.2	443.9	423.4	406.9	394.5	384.4	375.9	369.0	363.1	359.3	356.1
45°	437.0	412.7	392.8	377.5	366.0	356.4	347.6	344.1	336.4	331.8	330.3
47.5°	404.7	383.0	363.8	349.6	337.8	328.7	320.4	313.5	309.2	304.7	302.3
50°	382.8	362.1	344.1	330.3	318.8	308.8	301.1	296.5	290.7	286.6	283.5
52.5°	361.0	341.8	323.9	310.6	300.6	290.7	282.2	277.5	272.1	269.3	267.2
55°	329.9	309.6	294.3	281.1	270.8	261.7	253.6	248.9	245.5	242.9	242.1
57.5°	294.6	278.5	264.3	252.5	241.8	233.1	226.0	221.7	218.6	218.2	215.9
60°	271.6	257.0	244.0	231.4	222.1	214.1	207.9	203.0	199.9	199.4	198.7
62.5°	248.6	234.6	222.5	211.4	203.1	195.3	189.6	183.9	182.1	180.2	178.4
65°	214.4	201.8	191.8	183.0	174.2	167.6	161.9	158.4	154.2	151.9	147.7
67.5°	180.9	171.1	161.5	154.1	147.1	141.0	136.2	131.1	128.3	126.3	123.3
70°	158.9	151.2	141.6	133.5	128.2	123.1	119.3	113.5	111.6	110.1	108.6
72.5°	137.9	131.2	123.1	116.6	111.3	106.5	102.1	99.5	97.6	95.9	95.0
75°	108.6	102.0	95.1	90.5	86.7	82.9	80.6	78.7	77.9	77.5	75.9
77.5°	79.7	76.2	70.7	67.1	64.5	63.0	60.9	59.9	59.9	58.2	57.7
80°	61.0	59.1	54.4	52.9	51.0	49.5	48.4	46.5	44.5	43.7	42.6
82.5°	45.3	43.4	41.6	39.1	37.6	36.6	35.4	34.7	34.9	33.9	33.3
85°	24.1	22.2	21.5	21.1	20.3	21.1	20.7	20.3	20.0	19.6	20.0
87.5°	9.6	10.0	9.9	11.0	10.3	11.1	11.3	11.3	11.5	11.7	11.9
90°	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1	22.3	23.4	25.9
92.5°	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9	150.9	113.6	96.2
95°	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6	665.3	521.0	422.4
97.5°	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5	1131.5	990.9	853.7
100°	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3	1385.8	1265.0	1142.9
102.5°	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2	1541.7	1483.7	1401.1
105°	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2	1629.9	1681.5	1668.6
107.5°	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8	1551.3	1683.8	1745.1
110°	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1	1462.1	1627.5	1727.3



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2	1373.8	1541.2	1658.7
115°	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5	1247.4	1408.1	1536.0
117.5°	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0	1159.8	1298.3	1415.6
120°	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3	1110.0	1239.1	1342.4
122.5°	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9	1074.4	1189.4	1286.1
125°	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1	1026.7	1128.8	1213.4
127.5°	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5	981.2	1076.5	1155.6
130°	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1	949.3	1040.9	1117.1
132.5°	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5	919.3	1002.3	1075.8
135°	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0	873.0	948.2	1015.0
137.5°	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3	831.7	894.1	951.0
140°	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1	807.3	861.3	910.6
142.5°	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9	786.7	833.1	875.9
145°	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0	760.3	796.8	828.4
147.5°	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0	738.5	766.5	790.4
150°	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5	726.4	748.6	769.7
152.5°	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2	714.2	734.6	751.0
155°	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0	695.8	712.3	725.2
157.5°	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0	678.4	691.2	701.3
160°	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6	665.3	677.0	685.3
162.5°	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3	654.1	663.9	671.2
165°	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9	637.1	644.2	650.1
167.5°	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3	620.8	626.1	630.4
170°	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8	611.4	614.9	617.2
172.5°	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4	602.9	605.5	606.9
175°	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3	590.3	592.6	592.6
177.5°	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9	584.8	584.8	584.8
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.2	891.8	890.9	892.1	890.9	891.8	895.2	895.5	895.9	898.3	894.9
5°	826.0	822.1	824.0	823.2	824.0	822.1	826.0	829.8	830.5	833.9	836.3
7.5°	765.0	760.2	755.2	756.8	755.2	760.2	765.0	765.1	771.0	775.5	778.5
10°	722.4	718.5	716.2	718.1	716.2	718.5	722.4	727.3	729.6	735.0	740.7
12.5°	686.4	684.2	682.2	681.4	682.2	684.2	686.4	691.8	697.1	703.4	709.7
15°	637.5	633.0	631.1	626.1	631.1	633.0	637.5	642.2	652.6	655.2	664.8
17.5°	592.5	591.0	586.0	583.9	586.0	591.0	592.5	596.4	601.2	611.1	618.3
20°	565.8	564.3	559.4	562.4	559.4	564.3	565.8	571.6	575.4	583.5	590.4
22.5°	543.7	540.4	538.8	537.9	538.8	540.4	543.7	546.4	551.5	559.0	566.7
25°	512.5	507.6	505.6	503.3	505.6	507.6	512.5	514.0	519.4	526.7	530.9
27.5°	481.4	478.7	476.2	475.5	476.2	478.7	481.4	483.5	488.2	494.5	502.2
30°	461.1	458.4	456.5	456.5	456.5	458.4	461.1	465.7	469.2	474.9	480.7
32.5°	443.0	440.9	439.0	438.7	439.0	440.9	443.0	445.5	449.5	455.9	461.9
35°	416.6	413.5	412.7	410.5	412.7	413.5	416.6	418.5	422.7	427.4	432.3
37.5°	389.2	386.7	386.6	386.4	386.6	386.7	389.2	392.6	396.2	400.3	406.4
40°	371.7	369.8	369.4	366.8	369.4	369.8	371.7	373.2	377.1	382.4	387.1
42.5°	353.0	352.0	350.7	349.5	350.7	352.0	353.0	356.1	359.3	363.1	369.0
45°	327.6	325.0	325.0	323.1	325.0	325.0	327.6	330.3	331.8	336.4	344.1
47.5°	301.3	299.3	299.5	297.5	299.5	299.3	301.3	302.3	304.7	309.2	313.5
50°	283.9	282.8	282.4	281.6	282.4	282.8	283.9	283.5	286.6	290.7	296.5
52.5°	266.4	265.9	267.3	265.6	267.3	265.9	266.4	267.2	269.3	272.1	277.5
55°	242.9	241.7	244.0	241.7	244.0	241.7	242.9	242.1	242.9	245.5	248.9
57.5°	215.7	214.7	216.7	215.6	216.7	214.7	215.7	215.9	218.2	218.6	221.7
60°	197.9	195.6	196.8	197.2	196.8	195.6	197.9	198.7	199.4	199.9	203.0
62.5°	176.7	175.4	176.2	174.5	176.2	175.4	176.7	178.4	180.2	182.1	183.9
65°	146.9	145.8	144.2	143.5	144.2	145.8	146.9	147.7	151.9	154.2	158.4
67.5°	123.4	120.7	120.6	121.2	120.6	120.7	123.4	123.3	126.3	128.3	131.1
70°	106.2	106.2	105.8	105.8	105.8	106.2	106.2	108.6	110.1	111.6	113.5
72.5°	94.3	94.0	93.3	93.0	93.3	94.0	94.3	95.0	95.9	97.6	99.5
75°	75.9	76.3	75.5	75.2	75.5	76.3	75.9	75.9	77.5	77.9	78.7
77.5°	56.0	54.4	55.3	54.4	55.3	54.4	56.0	57.7	58.2	59.9	59.9
80°	42.6	42.2	43.3	42.2	43.3	42.2	42.6	42.6	43.7	44.5	46.5
82.5°	33.7	33.3	33.8	33.0	33.8	33.3	33.7	33.3	33.9	34.9	34.7
85°	20.3	20.0	19.6	20.0	19.6	20.0	20.3	20.0	19.6	20.0	20.3
87.5°	12.2	11.9	12.1	12.1	12.1	11.9	12.2	11.9	11.7	11.5	11.3
90°	25.9	25.9	27.0	27.0	27.0	25.9	25.9	25.9	23.4	22.3	21.1
92.5°	81.2	78.4	76.7	74.8	76.7	78.4	81.2	96.2	113.6	150.9	207.9
95°	339.1	303.9	294.6	275.8	294.6	303.9	339.1	422.4	521.0	665.3	843.6
97.5°	781.2	715.6	681.6	666.5	681.6	715.6	781.2	853.7	990.9	1131.5	1256.5
100°	1062.0	977.4	934.0	915.2	934.0	977.4	1062.0	1142.9	1265.0	1385.8	1443.3
102.5°	1314.4	1254.4	1207.2	1193.2	1207.2	1254.4	1314.4	1401.1	1483.7	1541.7	1506.2
105°	1631.0	1592.4	1568.8	1554.8	1568.8	1592.4	1631.0	1668.6	1681.5	1629.9	1469.2
107.5°	1764.1	1763.9	1756.2	1746.8	1756.2	1763.9	1764.1	1745.1	1683.8	1551.3	1336.8
110°	1780.1	1802.4	1810.6	1810.6	1810.6	1802.4	1780.1	1727.3	1627.5	1462.1	1239.1



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1736.0	1774.2	1794.6	1803.1	1794.6	1774.2	1736.0	1658.7	1541.2	1373.8	1162.2
115°	1627.5	1683.8	1716.7	1731.9	1716.7	1683.8	1627.5	1536.0	1408.1	1247.4	1065.5
117.5°	1507.1	1565.4	1598.0	1607.3	1598.0	1565.4	1507.1	1415.6	1298.3	1159.8	1003.0
120°	1429.3	1485.5	1517.2	1526.6	1517.2	1485.5	1429.3	1342.4	1239.1	1110.0	969.3
122.5°	1363.5	1415.1	1446.8	1455.3	1446.8	1415.1	1363.5	1286.1	1189.4	1074.4	943.9
125°	1279.0	1327.2	1352.9	1364.7	1352.9	1327.2	1279.0	1213.4	1128.8	1026.7	907.1
127.5°	1215.2	1257.7	1282.1	1287.3	1282.1	1257.7	1215.2	1155.6	1076.5	981.2	869.5
130°	1175.8	1214.5	1238.0	1245.0	1238.0	1214.5	1175.8	1117.1	1040.9	949.3	846.1
132.5°	1134.5	1173.2	1194.8	1202.7	1194.8	1173.2	1134.5	1075.8	1002.3	919.3	822.5
135°	1066.6	1105.4	1126.5	1133.6	1126.5	1105.4	1066.6	1015.0	948.2	873.0	792.0
137.5°	997.1	1032.4	1051.9	1059.6	1051.9	1032.4	997.1	951.0	894.1	831.7	766.3
140°	954.0	984.5	1002.1	1007.9	1002.1	984.5	954.0	910.6	861.3	807.3	752.1
142.5°	912.7	938.5	955.1	960.1	955.1	938.5	912.7	875.9	833.1	786.7	739.9
145°	856.6	876.6	889.5	894.1	889.5	876.6	856.6	828.4	796.8	760.3	724.0
147.5°	812.7	828.7	836.2	838.3	836.2	828.7	812.7	790.4	766.5	738.5	709.0
150°	787.4	801.4	806.2	807.3	806.2	801.4	787.4	769.7	748.6	726.4	700.5
152.5°	765.8	777.0	781.7	782.9	781.7	777.0	765.8	751.0	734.6	714.2	691.2
155°	736.9	745.1	748.6	749.8	748.6	745.1	736.9	725.2	712.3	695.8	677.0
157.5°	710.3	717.2	720.4	720.2	720.4	717.2	710.3	701.3	691.2	678.4	663.0
160°	693.5	699.3	701.8	700.5	701.8	699.3	693.5	685.3	677.0	665.3	653.6
162.5°	677.5	682.5	683.0	682.7	683.0	682.5	677.5	671.2	663.9	654.1	643.3
165°	654.8	657.1	657.1	657.1	657.1	657.1	654.8	650.1	644.2	637.1	628.9
167.5°	632.7	634.8	633.9	633.7	633.9	634.8	632.7	630.4	626.1	620.8	615.3
170°	619.6	620.8	620.8	619.6	620.8	620.8	619.6	617.2	614.9	611.4	607.8
172.5°	607.3	609.5	607.6	606.4	607.6	609.5	607.3	606.9	605.5	602.9	599.4
175°	592.6	593.8	591.4	590.3	591.4	593.8	592.6	592.6	592.6	590.3	590.3
177.5°	583.9	584.8	582.0	582.0	582.0	584.8	583.9	584.8	584.8	584.8	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.9	899.2	901.0	905.3	911.5	914.5	918.9	921.9	926.2	931.4	935.7
5°	837.8	847.1	853.1	862.7	871.6	880.4	891.5	899.6	910.3	922.6	932.2
7.5°	784.0	795.5	805.7	818.3	832.9	844.2	858.8	873.5	890.4	907.8	924.2
10°	749.6	761.1	773.8	789.5	804.1	819.4	836.7	853.9	875.0	894.6	916.9
12.5°	715.5	728.2	742.5	760.0	777.7	797.3	814.9	834.2	857.0	882.3	906.2
15°	673.3	685.5	700.8	715.8	736.2	757.6	781.0	806.8	832.0	860.5	890.0
17.5°	627.9	641.4	658.3	675.6	697.0	722.2	745.2	773.3	801.7	834.9	869.6
20°	598.4	612.3	632.2	651.4	671.0	695.5	722.8	751.5	781.8	816.7	855.5
22.5°	575.1	584.9	604.6	624.1	647.0	672.2	698.8	728.8	761.8	798.0	838.6
25°	540.5	552.0	566.2	586.5	610.4	636.8	663.7	695.5	731.5	768.4	811.7
27.5°	509.8	519.2	533.2	549.2	572.9	600.4	628.9	662.2	699.1	736.6	782.2
30°	488.0	498.4	511.7	528.7	547.4	577.3	606.5	639.1	676.7	715.5	762.2
32.5°	469.0	479.6	491.2	507.2	527.5	554.0	584.1	616.1	654.3	694.3	739.8
35°	442.3	449.6	460.3	476.1	496.0	517.5	548.2	582.0	619.1	660.6	706.2
37.5°	411.8	421.2	431.9	445.6	463.0	486.3	514.8	549.0	583.5	623.2	664.8
40°	393.9	402.8	414.7	424.6	443.1	464.1	490.3	525.9	560.5	597.6	635.6
42.5°	375.9	384.4	394.5	406.9	423.4	443.9	468.2	501.4	538.4	573.4	605.3
45°	347.6	356.4	366.0	377.5	392.8	412.7	437.0	467.3	499.5	531.7	555.8
47.5°	320.4	328.7	337.8	349.6	363.8	383.0	404.7	431.4	462.7	490.1	507.4
50°	301.1	308.8	318.8	330.3	344.1	362.1	382.8	409.3	435.5	460.3	476.1
52.5°	282.2	290.7	300.6	310.6	323.9	341.8	361.0	383.8	408.7	429.0	442.0
55°	253.6	261.7	270.8	281.1	294.3	309.6	329.9	347.9	367.5	384.8	392.4
57.5°	226.0	233.1	241.8	252.5	264.3	278.5	294.6	311.9	325.8	338.0	346.7
60°	207.9	214.1	222.1	231.4	244.0	257.0	271.6	287.7	298.4	308.8	316.9
62.5°	189.6	195.3	203.1	211.4	222.5	234.6	248.6	261.7	272.1	279.0	288.3
65°	161.9	167.6	174.2	183.0	191.8	201.8	214.4	224.0	231.4	239.0	244.8
67.5°	136.2	141.0	147.1	154.1	161.5	171.1	180.9	188.8	193.9	198.4	205.4
70°	119.3	123.1	128.2	133.5	141.6	151.2	158.9	164.9	168.4	173.0	181.5
72.5°	102.1	106.5	111.3	116.6	123.1	131.2	137.9	144.1	146.3	150.0	155.3
75°	80.6	82.9	86.7	90.5	95.1	102.0	108.6	110.1	112.0	115.1	119.0
77.5°	60.9	63.0	64.5	67.1	70.7	76.2	79.7	82.0	82.5	83.6	87.4
80°	48.4	49.5	51.0	52.9	54.4	59.1	61.0	63.3	64.0	65.2	67.2
82.5°	35.4	36.6	37.6	39.1	41.6	43.4	45.3	47.7	47.8	48.7	49.0
85°	20.7	21.1	20.3	21.1	21.5	22.2	24.1	26.1	25.8	25.3	26.5
87.5°	11.3	11.1	10.3	11.0	9.9	10.0	9.6	9.4	9.5	9.7	10.1
90°	20.0	18.8	16.5	15.2	12.9	11.7	9.4	7.1	4.6	2.3	1.2
92.5°	306.3	378.3	384.5	267.8	160.3	96.2	62.0	41.8	27.3	17.4	14.3
95°	1017.3	1039.7	848.4	524.5	266.4	140.8	88.0	62.2	49.3	39.9	38.7
97.5°	1287.3	1110.2	757.6	418.7	229.5	146.4	108.5	85.2	72.3	65.7	64.3
100°	1352.9	1059.6	675.9	380.2	227.6	159.6	124.4	102.1	89.2	84.5	82.1
102.5°	1313.5	970.4	613.9	364.3	236.1	175.5	141.3	120.9	107.0	103.3	101.9
105°	1187.5	850.7	553.8	357.9	253.5	201.9	169.0	150.2	138.5	132.6	132.6
107.5°	1058.9	768.3	528.5	368.7	279.2	229.2	199.8	180.3	170.6	165.0	162.6
110°	985.6	729.8	521.0	379.0	298.0	249.9	219.4	201.9	191.3	186.6	184.2



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	931.2	707.3	521.0	392.1	315.9	269.6	240.0	222.5	211.9	208.1	205.8
115°	871.8	683.0	524.5	411.8	343.9	300.4	271.0	253.5	242.9	239.3	237.0
117.5°	836.4	671.0	532.3	434.4	372.4	331.3	303.0	283.1	272.5	268.7	265.2
120°	816.7	665.3	539.8	449.4	393.1	352.0	322.7	302.8	292.2	287.5	284.0
122.5°	799.8	660.7	546.3	466.4	412.8	371.7	342.4	320.5	310.0	306.3	303.7
125°	776.8	654.8	557.3	489.3	438.9	400.1	369.6	347.3	336.8	330.9	328.5
127.5°	755.7	652.0	569.8	510.5	463.9	426.7	396.2	372.4	359.1	351.5	348.0
130°	741.6	650.1	577.3	524.5	479.9	443.5	413.0	388.4	373.1	363.8	360.2
132.5°	730.3	650.1	585.7	536.7	494.9	458.6	428.1	402.5	385.4	374.1	369.6
135°	717.0	650.1	597.2	553.8	515.1	478.8	447.1	422.4	403.6	389.6	384.9
137.5°	705.0	651.5	607.8	566.5	529.5	496.3	463.7	439.6	420.8	407.7	404.1
140°	699.3	652.4	612.5	575.0	539.8	505.7	474.0	451.8	433.0	418.9	415.4
142.5°	694.7	653.4	615.3	579.7	546.3	514.2	484.4	463.0	444.2	431.1	428.5
145°	687.6	652.4	618.4	586.7	557.3	526.8	499.9	478.8	462.3	450.6	448.3
147.5°	680.3	649.3	619.6	591.0	564.4	537.7	513.9	495.6	480.4	470.3	468.9
150°	674.7	646.5	619.6	593.8	569.1	543.3	523.3	507.0	491.7	483.4	481.1
152.5°	668.1	642.8	618.6	595.6	573.8	549.9	531.8	516.3	502.9	495.6	494.2
155°	657.1	636.0	616.0	597.2	578.5	558.6	542.1	530.4	518.7	511.6	511.6
157.5°	646.8	628.9	613.0	598.4	582.5	565.3	552.9	542.6	532.5	526.8	527.1
160°	638.3	624.3	610.2	598.4	584.4	569.1	558.6	549.2	541.0	536.2	537.5
162.5°	630.9	618.6	607.3	597.5	586.2	572.9	564.2	556.6	549.4	544.7	545.8
165°	619.6	610.2	603.1	596.1	586.7	577.3	570.3	565.6	559.8	556.2	558.6
167.5°	608.5	602.0	596.5	593.3	586.7	579.0	574.5	571.2	567.9	565.8	567.0
170°	602.0	597.2	593.8	591.4	586.7	580.9	577.3	575.0	572.6	571.5	572.6
172.5°	595.4	591.7	590.0	589.6	585.7	580.9	579.2	577.7	575.4	574.3	576.4
175°	586.7	585.5	585.5	586.7	584.4	580.9	580.9	580.9	579.7	578.5	580.9
177.5°	583.0	582.0	582.0	583.9	583.0	581.1	581.1	582.0	581.1	581.1	583.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	939.1	941.9	945.8	950.5	954.1	958.2	960.3	960.3	962.1	966.1	971.3
5°	941.8	951.8	961.4	973.6	983.2	994.3	1002.8	1010.9	1018.1	1027.3	1036.9
7.5°	941.0	957.6	974.8	994.2	1015.5	1032.5	1049.9	1063.6	1077.0	1094.7	1108.6
10°	938.0	959.5	982.8	1007.3	1034.2	1057.6	1078.7	1097.9	1116.3	1135.5	1152.8
12.5°	932.4	959.8	988.4	1017.8	1051.8	1078.5	1105.7	1126.2	1147.6	1168.6	1189.9
15°	924.1	956.3	990.9	1032.0	1073.4	1103.3	1130.1	1156.6	1176.6	1200.3	1220.7
17.5°	907.1	948.6	992.0	1036.8	1076.6	1111.5	1139.5	1164.8	1186.0	1212.1	1239.8
20°	896.9	941.8	987.0	1035.0	1073.0	1108.6	1135.9	1162.0	1188.4	1222.6	1256.4
22.5°	882.8	930.7	978.8	1024.3	1064.4	1098.8	1127.0	1158.9	1193.7	1232.4	1273.2
25°	860.5	910.0	957.6	1000.9	1040.0	1075.3	1113.7	1156.6	1198.8	1249.8	1308.5
27.5°	832.1	879.9	922.3	968.1	1007.0	1051.9	1099.7	1146.3	1207.2	1277.4	1350.7
30°	810.9	856.3	896.6	939.9	984.0	1033.5	1087.2	1142.1	1214.6	1297.0	1384.1
32.5°	786.4	827.4	867.4	909.2	960.1	1014.4	1071.6	1138.6	1225.3	1319.1	1409.3
35°	743.9	780.6	819.4	865.9	919.9	979.0	1051.9	1133.6	1238.3	1339.2	1420.2
37.5°	699.2	728.2	767.2	816.1	875.0	943.4	1026.1	1125.4	1232.9	1323.5	1358.0
40°	664.8	692.1	733.1	784.5	842.8	917.7	1010.5	1112.5	1220.7	1283.5	1280.9
42.5°	630.8	658.3	697.8	749.5	810.3	894.0	989.6	1095.6	1186.9	1210.8	1160.9
45°	578.5	604.2	643.0	695.1	760.3	848.2	948.7	1050.4	1108.6	1070.0	971.0
47.5°	525.2	550.2	586.1	637.2	708.4	800.4	895.4	978.9	987.0	903.8	785.1
50°	490.3	513.6	547.9	602.3	671.4	761.1	852.8	918.4	898.1	796.4	674.0
52.5°	456.2	478.7	510.7	562.1	632.7	720.6	802.4	853.9	806.9	698.8	588.8
55°	405.9	427.4	459.6	506.8	570.8	651.4	723.2	741.9	672.9	563.9	474.9
57.5°	358.1	373.8	405.7	447.4	509.2	580.2	631.6	628.2	552.0	453.9	390.1
60°	326.5	340.6	370.9	409.3	468.0	531.7	567.7	552.4	475.3	394.4	333.0
62.5°	297.0	310.2	335.7	370.9	421.4	476.8	503.0	481.8	409.0	337.9	289.1
65°	252.5	262.1	282.4	315.0	354.5	392.8	416.3	385.2	320.7	267.0	230.1
67.5°	210.8	219.0	237.1	260.5	287.8	314.3	323.8	294.6	244.5	208.3	182.4
70°	183.8	191.5	203.7	225.6	243.6	262.4	267.0	241.0	199.1	171.5	155.3
72.5°	157.9	165.0	175.8	191.2	203.7	214.5	216.7	192.4	160.5	141.4	129.0
75°	120.5	126.6	133.5	139.3	147.3	149.3	148.5	129.7	112.4	99.8	92.8
77.5°	88.6	91.1	95.3	97.6	98.0	97.9	93.9	82.0	73.1	67.9	65.0
80°	68.3	70.2	71.4	72.1	72.5	68.7	64.4	57.2	54.1	51.0	47.6
82.5°	49.6	50.9	52.0	52.2	50.1	46.9	42.9	39.4	37.2	35.6	34.3
85°	26.9	27.3	26.9	24.9	22.2	21.1	20.3	19.6	19.2	18.8	18.8
87.5°	10.0	9.5	8.5	9.3	9.7	9.6	10.1	10.0	10.2	10.4	10.7
90°	2.3	4.6	7.1	9.4	11.7	12.9	15.2	16.5	18.8	20.0	21.1
92.5°	17.4	27.3	41.8	62.0	96.2	160.3	267.8	384.5	378.3	306.3	207.9
95°	39.9	49.3	62.2	88.0	140.8	266.4	524.5	848.4	1039.7	1017.3	843.6
97.5°	65.7	72.3	85.2	108.5	146.4	229.5	418.7	757.6	1110.2	1287.3	1256.5
100°	84.5	89.2	102.1	124.4	159.6	227.6	380.2	675.9	1059.6	1352.9	1443.3
102.5°	103.3	107.0	120.9	141.3	175.5	236.1	364.3	613.9	970.4	1313.5	1506.2
105°	132.6	138.5	150.2	169.0	201.9	253.5	357.9	553.8	850.7	1187.5	1469.2
107.5°	165.0	170.6	180.3	199.8	229.2	279.2	368.7	528.5	768.3	1058.9	1336.8
110°	186.6	191.3	201.9	219.4	249.9	298.0	379.0	521.0	729.8	985.6	1239.1



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	208.1	211.9	222.5	240.0	269.6	315.9	392.1	521.0	707.3	931.2	1162.2
115°	239.3	242.9	253.5	271.0	300.4	343.9	411.8	524.5	683.0	871.8	1065.5
117.5°	268.7	272.5	283.1	303.0	331.3	372.4	434.4	532.3	671.0	836.4	1003.0
120°	287.5	292.2	302.8	322.7	352.0	393.1	449.4	539.8	665.3	816.7	969.3
122.5°	306.3	310.0	320.5	342.4	371.7	412.8	466.4	546.3	660.7	799.8	943.9
125°	330.9	336.8	347.3	369.6	400.1	438.9	489.3	557.3	654.8	776.8	907.1
127.5°	351.5	359.1	372.4	396.2	426.7	463.9	510.5	569.8	652.0	755.7	869.5
130°	363.8	373.1	388.4	413.0	443.5	479.9	524.5	577.3	650.1	741.6	846.1
132.5°	374.1	385.4	402.5	428.1	458.6	494.9	536.7	585.7	650.1	730.3	822.5
135°	389.6	403.6	422.4	447.1	478.8	515.1	553.8	597.2	650.1	717.0	792.0
137.5°	407.7	420.8	439.6	463.7	496.3	529.5	566.5	607.8	651.5	705.0	766.3
140°	418.9	433.0	451.8	474.0	505.7	539.8	575.0	612.5	652.4	699.3	752.1
142.5°	431.1	444.2	463.0	484.4	514.2	546.3	579.7	615.3	653.4	694.7	739.9
145°	450.6	462.3	478.8	499.9	526.8	557.3	586.7	618.4	652.4	687.6	724.0
147.5°	470.3	480.4	495.6	513.9	537.7	564.4	591.0	619.6	649.3	680.3	709.0
150°	483.4	491.7	507.0	523.3	543.3	569.1	593.8	619.6	646.5	674.7	700.5
152.5°	495.6	502.9	516.3	531.8	549.9	573.8	595.6	618.6	642.8	668.1	691.2
155°	511.6	518.7	530.4	542.1	558.6	578.5	597.2	616.0	636.0	657.1	677.0
157.5°	526.8	532.5	542.6	552.9	565.3	582.5	598.4	613.0	628.9	646.8	663.0
160°	536.2	541.0	549.2	558.6	569.1	584.4	598.4	610.2	624.3	638.3	653.6
162.5°	544.7	549.4	556.6	564.2	572.9	586.2	597.5	607.3	618.6	630.9	643.3
165°	556.2	559.8	565.6	570.3	577.3	586.7	596.1	603.1	610.2	619.6	628.9
167.5°	565.8	567.9	571.2	574.5	579.0	586.7	593.3	596.5	602.0	608.5	615.3
170°	571.5	572.6	575.0	577.3	580.9	586.7	591.4	593.8	597.2	602.0	607.8
172.5°	574.3	575.4	577.7	579.2	580.9	585.7	589.6	590.0	591.7	595.4	599.4
175°	578.5	579.7	580.9	580.9	580.9	584.4	586.7	585.5	585.5	586.7	590.3
177.5°	581.1	581.1	582.0	581.1	581.1	583.0	583.9	582.0	582.0	583.0	583.9
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0	582.0



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	975.3	975.3	980.6	980.2	983.6	982.4	983.0
5°	1048.4	1054.9	1060.7	1064.5	1070.3	1071.9	1071.1
7.5°	1124.3	1138.7	1145.8	1155.5	1157.2	1162.3	1161.7
10°	1171.1	1185.4	1196.1	1204.6	1208.8	1214.2	1214.6
12.5°	1208.0	1220.0	1229.6	1237.4	1242.5	1244.3	1245.3
15°	1236.8	1250.2	1261.3	1272.4	1279.0	1283.9	1286.7
17.5°	1265.8	1286.5	1306.2	1321.3	1330.3	1338.0	1337.9
20°	1288.2	1312.0	1336.6	1353.8	1371.4	1379.1	1380.3
22.5°	1312.1	1348.5	1380.1	1406.8	1430.1	1438.0	1441.0
25°	1361.8	1409.4	1458.1	1495.7	1522.6	1538.3	1540.7
27.5°	1421.9	1486.3	1537.5	1572.3	1594.6	1606.2	1608.7
30°	1464.3	1523.7	1569.7	1595.9	1606.2	1607.7	1601.9
32.5°	1483.3	1527.7	1546.1	1544.6	1524.3	1510.8	1505.6
35°	1460.1	1450.9	1405.9	1352.2	1311.2	1285.2	1278.2
37.5°	1328.7	1249.3	1166.7	1085.6	1042.4	1020.5	982.7
40°	1199.2	1086.0	1000.1	931.8	883.1	843.9	834.8
42.5°	1053.1	936.2	850.3	791.8	753.0	726.1	714.5
45°	846.3	745.8	674.8	629.9	600.0	580.4	571.6
47.5°	676.8	599.1	547.3	514.1	491.3	474.3	469.6
50°	583.9	521.7	478.0	450.0	432.7	419.7	414.3
52.5°	507.2	457.0	423.3	400.3	384.0	375.8	371.3
55°	418.5	375.2	351.0	332.5	323.4	316.9	313.8
57.5°	342.2	310.9	293.3	280.5	272.1	267.9	266.4
60°	299.6	275.1	258.9	248.9	243.2	237.8	236.3
62.5°	261.9	242.6	230.0	221.4	215.6	213.3	212.4
65°	211.0	198.3	189.1	183.8	179.2	178.3	178.0
67.5°	167.7	160.3	155.4	149.9	148.2	145.5	145.0
70°	143.5	138.5	132.7	130.8	128.9	126.2	126.6
72.5°	121.7	116.7	112.8	110.3	109.6	108.5	109.4
75°	89.0	87.5	85.9	84.0	83.2	83.2	82.9
77.5°	63.5	62.2	60.5	59.4	59.2	57.6	58.2
80°	46.0	44.1	43.3	43.7	42.6	42.2	42.2
82.5°	34.0	33.3	32.6	32.7	32.4	32.1	32.4
85°	18.8	18.4	18.4	18.1	18.1	17.7	17.7
87.5°	11.2	11.7	11.6	11.3	11.3	11.8	12.1
90°	22.3	23.4	25.9	25.9	25.9	27.0	27.0
92.5°	150.9	113.6	96.2	81.2	78.4	76.7	74.8
95°	665.3	521.0	422.4	339.1	303.9	294.6	275.8
97.5°	1131.5	990.9	853.7	781.2	715.6	681.6	666.5
100°	1385.8	1265.0	1142.9	1062.0	977.4	934.0	915.2
102.5°	1541.7	1483.7	1401.1	1314.4	1254.4	1207.2	1193.2
105°	1629.9	1681.5	1668.6	1631.0	1592.4	1568.8	1554.8
107.5°	1551.3	1683.8	1745.1	1764.1	1763.9	1756.2	1746.8
110°	1462.1	1627.5	1727.3	1780.1	1802.4	1810.6	1810.6



TEST NUMBER: P333546-840

CATALOG NUMBER: S125RDIP-S610D1205U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1373.8	1541.2	1658.7	1736.0	1774.2	1794.6	1803.1
115°	1247.4	1408.1	1536.0	1627.5	1683.8	1716.7	1731.9
117.5°	1159.8	1298.3	1415.6	1507.1	1565.4	1598.0	1607.3
120°	1110.0	1239.1	1342.4	1429.3	1485.5	1517.2	1526.6
122.5°	1074.4	1189.4	1286.1	1363.5	1415.1	1446.8	1455.3
125°	1026.7	1128.8	1213.4	1279.0	1327.2	1352.9	1364.7
127.5°	981.2	1076.5	1155.6	1215.2	1257.7	1282.1	1287.3
130°	949.3	1040.9	1117.1	1175.8	1214.5	1238.0	1245.0
132.5°	919.3	1002.3	1075.8	1134.5	1173.2	1194.8	1202.7
135°	873.0	948.2	1015.0	1066.6	1105.4	1126.5	1133.6
137.5°	831.7	894.1	951.0	997.1	1032.4	1051.9	1059.6
140°	807.3	861.3	910.6	954.0	984.5	1002.1	1007.9
142.5°	786.7	833.1	875.9	912.7	938.5	955.1	960.1
145°	760.3	796.8	828.4	856.6	876.6	889.5	894.1
147.5°	738.5	766.5	790.4	812.7	828.7	836.2	838.3
150°	726.4	748.6	769.7	787.4	801.4	806.2	807.3
152.5°	714.2	734.6	751.0	765.8	777.0	781.7	782.9
155°	695.8	712.3	725.2	736.9	745.1	748.6	749.8
157.5°	678.4	691.2	701.3	710.3	717.2	720.4	720.2
160°	665.3	677.0	685.3	693.5	699.3	701.8	700.5
162.5°	654.1	663.9	671.2	677.5	682.5	683.0	682.7
165°	637.1	644.2	650.1	654.8	657.1	657.1	657.1
167.5°	620.8	626.1	630.4	632.7	634.8	633.9	633.7
170°	611.4	614.9	617.2	619.6	620.8	620.8	619.6
172.5°	602.9	605.5	606.9	607.3	609.5	607.6	606.4
175°	590.3	592.6	592.6	592.6	593.8	591.4	590.3
177.5°	584.8	584.8	584.8	583.9	584.8	582.0	582.0
180°	582.0	582.0	582.0	582.0	582.0	582.0	582.0

(END OF REPORT)