

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333528-840

Luminaire Tested: **S125RDIP-S610D590U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333528-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U840-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4565.4 lumens
Efficiency: N/A
Efficacy: 139.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	74	66	61	76	68	62	57	59	54	50	50	47	44	42	39	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6035	6035	6035	6035
5°	6944	6043	5337	6043
10°	7965	6013	4709	6013
15°	8603	5951	4186	5951
20°	9487	5880	3865	5880
25°	10979	5784	3587	5784
30°	11946	5684	3404	5684
35°	10078	5568	3236	5568
40°	7038	5359	3092	5359
45°	5221	5076	2951	5076
50°	4163	4784	2829	4784
55°	3533	4418	2721	4418
60°	3052	4093	2547	4093
65°	2720	3741	2193	3741
70°	2391	3427	1998	3427
75°	2069	2969	1876	2969
80°	1570	2499	1570	2499
85°	1312	1964	1482	1964



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	2.0
10°-20°	262.6	5.8
20°-30°	416.4	9.1
30°-40°	502.1	11.0
40°-50°	448.4	9.8
50°-60°	343.9	7.5
60°-70°	223.5	4.9
70°-80°	108.6	2.4
80°-90°	27.5	0.6
90°-100°	207.1	4.5
100°-110°	445.2	9.8
110°-120°	417.8	9.2
120°-130°	338.6	7.4
130°-140°	271.7	6.0
140°-150°	205.1	4.5
150°-160°	144.3	3.2
160°-170°	85.1	1.9
170°-180°	27.7	0.6
0°-30°	768.6	16.8
0°-40°	1270.8	27.8
0°-60°	2063.1	45.2
0°-90°	2422.7	53.1
90°-120°	1070.2	23.4
90°-150°	1885.6	41.3
90°-180°	2143.0	46.9
0°-180°	4565.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	934	934	934	934	934	
5°	1071	932	823	932	1071	107
15°	1287	890	626	890	1287	369
25°	1541	812	503	812	1541	707
35°	1278	706	410	706	1278	772
45°	572	556	323	556	572	456
55°	314	392	242	392	314	285
65°	178	245	144	245	178	177
75°	83	119	75	119	83	88
85°	18	26	20	26	18	21
90°	13	1	13	1	13	10
95°	135	19	135	19	135	192
105°	763	65	763	65	763	759
115°	850	116	850	116	850	831
125°	670	161	670	161	670	606
135°	556	189	556	189	556	431
145°	439	220	439	220	439	279
155°	368	251	368	251	368	172
165°	323	274	323	274	323	92
175°	290	285	290	285	290	28
180°	286	286	286	286	286	



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	983.0	982.4	983.6	980.2	980.6	975.3	975.3	971.3	966.1	962.1	960.3
5°	1071.1	1071.9	1070.3	1064.5	1060.7	1054.9	1048.4	1036.9	1027.3	1018.1	1010.9
7.5°	1161.7	1162.3	1157.2	1155.5	1145.8	1138.7	1124.3	1108.6	1094.7	1077.0	1063.6
10°	1214.6	1214.2	1208.8	1204.6	1196.1	1185.4	1171.1	1152.8	1135.5	1116.3	1097.9
12.5°	1245.3	1244.3	1242.5	1237.4	1229.6	1220.0	1208.0	1189.9	1168.6	1147.6	1126.2
15°	1286.7	1283.9	1279.0	1272.4	1261.3	1250.2	1236.8	1220.7	1200.3	1176.6	1156.6
17.5°	1337.9	1338.0	1330.3	1321.3	1306.2	1286.5	1265.8	1239.8	1212.1	1186.0	1164.8
20°	1380.3	1379.1	1371.4	1353.8	1336.6	1312.0	1288.2	1256.4	1222.6	1188.4	1162.0
22.5°	1441.0	1438.0	1430.1	1406.8	1380.1	1348.5	1312.1	1273.2	1232.4	1193.7	1158.9
25°	1540.7	1538.3	1522.6	1495.7	1458.1	1409.4	1361.8	1308.5	1249.8	1198.8	1156.6
27.5°	1608.7	1606.2	1594.6	1572.3	1537.5	1486.3	1421.9	1350.7	1277.4	1207.2	1146.3
30°	1601.9	1607.7	1606.2	1595.9	1569.7	1523.7	1464.3	1384.1	1297.0	1214.6	1142.1
32.5°	1505.6	1510.8	1524.3	1544.6	1546.1	1527.7	1483.3	1409.3	1319.1	1225.3	1138.6
35°	1278.2	1285.2	1311.2	1352.2	1405.9	1450.9	1460.1	1420.2	1339.2	1238.3	1133.6
37.5°	982.7	1020.5	1042.4	1085.6	1166.7	1249.3	1328.7	1358.0	1323.5	1232.9	1125.4
40°	834.8	843.9	883.1	931.8	1000.1	1086.0	1199.2	1280.9	1283.5	1220.7	1112.5
42.5°	714.5	726.1	753.0	791.8	850.3	936.2	1053.1	1160.9	1210.8	1186.9	1095.6
45°	571.6	580.4	600.0	629.9	674.8	745.8	846.3	971.0	1070.0	1108.6	1050.4
47.5°	469.6	474.3	491.3	514.1	547.3	599.1	676.8	785.1	903.8	987.0	978.9
50°	414.3	419.7	432.7	450.0	478.0	521.7	583.9	674.0	796.4	898.1	918.4
52.5°	371.3	375.8	384.0	400.3	423.3	457.0	507.2	588.8	698.8	806.9	853.9
55°	313.8	316.9	323.4	332.5	351.0	375.2	418.5	474.9	563.9	672.9	741.9
57.5°	266.4	267.9	272.1	280.5	293.3	310.9	342.2	390.1	453.9	552.0	628.2
60°	236.3	237.8	243.2	248.9	258.9	275.1	299.6	333.0	394.4	475.3	552.4
62.5°	212.4	213.3	215.6	221.4	230.0	242.6	261.9	289.1	337.9	409.0	481.8
65°	178.0	178.3	179.2	183.8	189.1	198.3	211.0	230.1	267.0	320.7	385.2
67.5°	145.0	145.5	148.2	149.9	155.4	160.3	167.7	182.4	208.3	244.5	294.6
70°	126.6	126.2	128.9	130.8	132.7	138.5	143.5	155.3	171.5	199.1	241.0
72.5°	109.4	108.5	109.6	110.3	112.8	116.7	121.7	129.0	141.4	160.5	192.4
75°	82.9	83.2	83.2	84.0	85.9	87.5	89.0	92.8	99.8	112.4	129.7
77.5°	58.2	57.6	59.2	59.4	60.5	62.2	63.5	65.0	67.9	73.1	82.0
80°	42.2	42.2	42.6	43.7	43.3	44.1	46.0	47.6	51.0	54.1	57.2
82.5°	32.4	32.1	32.4	32.7	32.6	33.3	34.0	34.3	35.6	37.2	39.4
85°	17.7	17.7	18.1	18.1	18.4	18.4	18.8	18.8	18.8	19.2	19.6
87.5°	9.4	9.1	8.7	8.7	9.0	9.4	9.0	8.5	8.4	8.3	8.4
90°	13.2	13.2	12.6	12.6	12.6	11.5	10.9	10.4	9.8	9.2	8.1
92.5°	36.8	37.7	38.5	39.9	47.3	55.7	74.1	102.1	150.4	185.7	188.7
95°	135.4	144.6	149.2	166.5	207.4	255.8	326.6	414.1	499.5	510.4	416.5
97.5°	327.2	334.6	351.2	383.5	419.1	486.5	555.4	616.8	632.0	545.0	371.9
100°	449.3	458.6	479.9	521.3	561.1	621.0	680.3	708.5	664.2	520.2	331.8
102.5°	585.7	592.7	615.8	645.3	687.8	728.3	756.8	739.4	644.8	476.4	301.3
105°	763.3	770.2	781.7	800.7	819.1	825.5	800.1	721.2	583.0	417.7	271.9
107.5°	857.5	862.1	866.0	866.1	856.7	826.7	761.5	656.2	519.9	377.2	259.4
110°	888.9	888.9	884.8	873.8	848.0	799.0	717.8	608.3	483.9	358.3	255.8



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	885.1	881.0	871.0	852.2	814.4	756.6	674.5	570.6	457.2	347.3	255.8
115°	850.3	842.7	826.7	799.0	754.1	691.3	612.4	523.0	428.0	335.3	257.5
117.5°	789.1	784.5	768.5	739.9	695.0	637.3	569.4	492.4	410.6	329.4	261.3
120°	749.4	744.9	729.3	701.7	659.0	608.3	544.9	475.8	400.9	326.6	265.0
122.5°	714.4	710.2	694.7	669.3	631.4	583.9	527.5	463.4	392.6	324.4	268.2
125°	669.9	664.2	651.6	627.9	595.6	554.2	504.0	445.2	381.3	321.4	273.7
127.5°	632.0	629.3	617.4	596.5	567.3	528.5	481.7	426.9	371.0	320.0	279.7
130°	611.2	607.7	596.2	577.2	548.4	511.0	466.1	415.4	364.1	319.1	283.5
132.5°	590.5	586.5	575.9	556.9	528.2	492.1	451.3	403.8	358.5	319.1	287.6
135°	556.4	553.0	542.6	523.6	498.3	465.4	428.6	388.8	351.9	319.1	293.2
137.5°	520.2	516.3	506.9	489.5	466.9	439.0	408.3	376.2	346.1	319.8	298.4
140°	494.8	491.9	483.3	468.4	447.1	422.8	396.4	369.2	343.4	320.3	300.7
142.5°	471.3	468.9	460.7	448.1	430.0	409.0	386.2	363.2	341.0	320.7	302.1
145°	439.0	436.7	430.3	420.5	406.7	391.1	373.2	355.5	337.6	320.3	303.6
147.5°	411.5	410.5	406.8	399.0	388.0	376.3	362.5	348.1	334.0	318.8	304.2
150°	396.4	395.8	393.4	386.6	377.9	367.5	356.6	343.9	331.2	317.4	304.2
152.5°	384.4	383.7	381.4	376.0	368.7	360.6	350.6	339.3	328.0	315.6	303.7
155°	368.1	367.5	365.8	361.7	356.0	349.6	341.6	332.3	322.6	312.3	302.5
157.5°	353.6	353.7	352.0	348.7	344.3	339.3	333.1	325.5	317.5	308.7	300.9
160°	343.9	344.5	343.4	340.4	336.4	332.3	326.6	320.8	313.4	306.5	299.5
162.5°	335.2	335.3	335.1	332.6	329.5	325.9	321.1	315.8	309.7	303.7	298.2
165°	322.6	322.6	322.6	321.4	319.1	316.3	312.8	308.7	304.2	299.5	296.1
167.5°	311.0	311.1	311.6	310.6	309.4	307.4	304.8	302.1	298.7	295.5	292.9
170°	304.2	304.8	304.8	304.2	303.0	301.8	300.1	298.4	295.5	293.2	291.4
172.5°	297.7	298.3	299.2	298.2	297.9	297.2	296.0	294.3	292.3	290.4	289.6
175°	289.7	290.3	291.4	290.9	290.9	290.9	289.7	289.7	288.0	287.4	287.4
177.5°	285.7	285.7	287.1	286.6	287.1	287.1	287.1	286.6	286.2	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	960.3	958.2	954.1	950.5	945.8	941.9	939.1	935.7	931.4	926.2	921.9
5°	1002.8	994.3	983.2	973.6	961.4	951.8	941.8	932.2	922.6	910.3	899.6
7.5°	1049.9	1032.5	1015.5	994.2	974.8	957.6	941.0	924.2	907.8	890.4	873.5
10°	1078.7	1057.6	1034.2	1007.3	982.8	959.5	938.0	916.9	894.6	875.0	853.9
12.5°	1105.7	1078.5	1051.8	1017.8	988.4	959.8	932.4	906.2	882.3	857.0	834.2
15°	1130.1	1103.3	1073.4	1032.0	990.9	956.3	924.1	890.0	860.5	832.0	806.8
17.5°	1139.5	1111.5	1076.6	1036.8	992.0	948.6	907.1	869.6	834.9	801.7	773.3
20°	1135.9	1108.6	1073.0	1035.0	987.0	941.8	896.9	855.5	816.7	781.8	751.5
22.5°	1127.0	1098.8	1064.4	1024.3	978.8	930.7	882.8	838.6	798.0	761.8	728.8
25°	1113.7	1075.3	1040.0	1000.9	957.6	910.0	860.5	811.7	768.4	731.5	695.5
27.5°	1099.7	1051.9	1007.0	968.1	922.3	879.9	832.1	782.2	736.6	699.1	662.2
30°	1087.2	1033.5	984.0	939.9	896.6	856.3	810.9	762.2	715.5	676.7	639.1
32.5°	1071.6	1014.4	960.1	909.2	867.4	827.4	786.4	739.8	694.3	654.3	616.1
35°	1051.9	979.0	919.9	865.9	819.4	780.6	743.9	706.2	660.6	619.1	582.0
37.5°	1026.1	943.4	875.0	816.1	767.2	728.2	699.2	664.8	623.2	583.5	549.0
40°	1010.5	917.7	842.8	784.5	733.1	692.1	664.8	635.6	597.6	560.5	525.9
42.5°	989.6	894.0	810.3	749.5	697.8	658.3	630.8	605.3	573.4	538.4	501.4
45°	948.7	848.2	760.3	695.1	643.0	604.2	578.5	555.8	531.7	499.5	467.3
47.5°	895.4	800.4	708.4	637.2	586.1	550.2	525.2	507.4	490.1	462.7	431.4
50°	852.8	761.1	671.4	602.3	547.9	513.6	490.3	476.1	460.3	435.5	409.3
52.5°	802.4	720.6	632.7	562.1	510.7	478.7	456.2	442.0	429.0	408.7	383.8
55°	723.2	651.4	570.8	506.8	459.6	427.4	405.9	392.4	384.8	367.5	347.9
57.5°	631.6	580.2	509.2	447.4	405.7	373.8	358.1	346.7	338.0	325.8	311.9
60°	567.7	531.7	468.0	409.3	370.9	340.6	326.5	316.9	308.8	298.4	287.7
62.5°	503.0	476.8	421.4	370.9	335.7	310.2	297.0	288.3	279.0	272.1	261.7
65°	416.3	392.8	354.5	315.0	282.4	262.1	252.5	244.8	239.0	231.4	224.0
67.5°	323.8	314.3	287.8	260.5	237.1	219.0	210.8	205.4	198.4	193.9	188.8
70°	267.0	262.4	243.6	225.6	203.7	191.5	183.8	181.5	173.0	168.4	164.9
72.5°	216.7	214.5	203.7	191.2	175.8	165.0	157.9	155.3	150.0	146.3	144.1
75°	148.5	149.3	147.3	139.3	133.5	126.6	120.5	119.0	115.1	112.0	110.1
77.5°	93.9	97.9	98.0	97.6	95.3	91.1	88.6	87.4	83.6	82.5	82.0
80°	64.4	68.7	72.5	72.1	71.4	70.2	68.3	67.2	65.2	64.0	63.3
82.5°	42.9	46.9	50.1	52.2	52.0	50.9	49.6	49.0	48.7	47.8	47.7
85°	20.3	21.1	22.2	24.9	26.9	27.3	26.9	26.5	25.3	25.8	26.1
87.5°	8.6	8.3	8.5	8.3	7.8	9.1	9.7	9.9	9.4	9.1	8.7
90°	7.5	6.4	5.8	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	131.5	78.7	47.3	30.4	20.5	13.3	8.5	7.1	8.5	13.3	20.5
95°	257.5	130.8	69.2	43.2	30.5	24.2	19.6	19.0	19.6	24.2	30.5
97.5°	205.5	112.7	71.9	53.2	41.8	35.4	32.2	31.6	32.2	35.4	41.8
100°	186.6	111.8	78.4	61.1	50.1	43.8	41.5	40.3	41.5	43.8	50.1
102.5°	178.8	115.9	86.1	69.4	59.4	52.5	50.7	50.0	50.7	52.5	59.4
105°	175.7	124.4	99.1	82.9	73.7	68.0	65.1	65.1	65.1	68.0	73.7
107.5°	181.0	137.1	112.6	98.1	88.5	83.7	81.0	79.9	81.0	83.7	88.5
110°	186.0	146.3	122.7	107.8	99.1	93.9	91.6	90.5	91.6	93.9	99.1



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	192.5	155.1	132.4	117.9	109.3	104.0	102.2	101.1	102.2	104.0	109.3
115°	202.2	168.7	147.4	133.1	124.4	119.3	117.5	116.3	117.5	119.3	124.4
117.5°	213.3	182.9	162.7	148.8	139.0	133.8	131.9	130.2	131.9	133.8	139.0
120°	220.7	193.0	172.8	158.4	148.7	143.4	141.2	139.4	141.2	143.4	148.7
122.5°	228.9	202.7	182.5	168.1	157.3	152.2	150.4	149.1	150.4	152.2	157.3
125°	240.2	215.4	196.4	181.5	170.5	165.3	162.5	161.3	162.5	165.3	170.5
127.5°	250.5	227.7	209.4	194.5	182.9	176.3	172.6	170.9	172.6	176.3	182.9
130°	257.5	235.6	217.7	202.8	190.7	183.2	178.5	176.8	178.5	183.2	190.7
132.5°	263.5	243.0	225.1	210.2	197.6	189.1	183.7	181.5	183.7	189.1	197.6
135°	271.9	252.9	235.0	219.4	207.4	198.1	191.3	188.9	191.3	198.1	207.4
137.5°	278.1	259.9	243.7	227.6	215.8	206.6	200.2	198.4	200.2	206.6	215.8
140°	282.3	265.0	248.3	232.8	221.8	212.6	205.6	203.9	205.6	212.6	221.8
142.5°	284.6	268.2	252.5	237.8	227.3	218.1	211.7	210.4	211.7	218.1	227.3
145°	288.0	273.7	258.6	245.4	235.0	226.9	221.2	220.0	221.2	226.9	235.0
147.5°	290.1	277.1	264.0	252.3	243.3	235.8	230.9	230.1	230.9	235.8	243.3
150°	291.4	279.4	266.7	256.9	248.8	241.4	237.3	236.2	237.3	241.4	248.8
152.5°	292.4	281.7	269.9	261.1	253.5	246.9	243.3	242.7	243.3	246.9	253.5
155°	293.2	284.0	274.2	266.1	260.3	254.6	251.2	251.2	251.2	254.6	260.3
157.5°	293.8	286.0	277.5	271.5	266.4	261.5	258.6	258.7	258.6	261.5	266.4
160°	293.8	286.9	279.4	274.2	269.6	265.6	263.3	263.9	263.3	265.6	269.6
162.5°	293.4	287.8	281.2	277.0	273.3	269.7	267.4	268.0	267.4	269.7	273.3
165°	292.7	288.0	283.5	279.9	277.6	274.8	273.1	274.2	273.1	274.8	277.6
167.5°	291.2	288.0	284.2	282.1	280.4	278.8	277.8	278.3	277.8	278.8	280.4
170°	290.3	288.0	285.2	283.5	282.3	281.1	280.5	281.1	280.5	281.1	282.3
172.5°	289.4	287.6	285.2	284.4	283.7	282.5	282.0	283.0	282.0	282.5	283.7
175°	288.0	286.9	285.2	285.2	285.2	284.6	284.0	285.2	284.0	284.6	285.2
177.5°	286.6	286.2	285.3	285.3	285.7	285.3	285.3	286.2	285.3	285.3	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	918.9	914.5	911.5	905.3	901.0	899.2	895.9	894.9	898.3	895.9	895.5
5°	891.5	880.4	871.6	862.7	853.1	847.1	837.8	836.3	833.9	830.5	829.8
7.5°	858.8	844.2	832.9	818.3	805.7	795.5	784.0	778.5	775.5	771.0	765.1
10°	836.7	819.4	804.1	789.5	773.8	761.1	749.6	740.7	735.0	729.6	727.3
12.5°	814.9	797.3	777.7	760.0	742.5	728.2	715.5	709.7	703.4	697.1	691.8
15°	781.0	757.6	736.2	715.8	700.8	685.5	673.3	664.8	655.2	652.6	642.2
17.5°	745.2	722.2	697.0	675.6	658.3	641.4	627.9	618.3	611.1	601.2	596.4
20°	722.8	695.5	671.0	651.4	632.2	612.3	598.4	590.4	583.5	575.4	571.6
22.5°	698.8	672.2	647.0	624.1	604.6	584.9	575.1	566.7	559.0	551.5	546.4
25°	663.7	636.8	610.4	586.5	566.2	552.0	540.5	530.9	526.7	519.4	514.0
27.5°	628.9	600.4	572.9	549.2	533.2	519.2	509.8	502.2	494.5	488.2	483.5
30°	606.5	577.3	547.4	528.7	511.7	498.4	488.0	480.7	474.9	469.2	465.7
32.5°	584.1	554.0	527.5	507.2	491.2	479.6	469.0	461.9	455.9	449.5	445.5
35°	548.2	517.5	496.0	476.1	460.3	449.6	442.3	432.3	427.4	422.7	418.5
37.5°	514.8	486.3	463.0	445.6	431.9	421.2	411.8	406.4	400.3	396.2	392.6
40°	490.3	464.1	443.1	424.6	414.7	402.8	393.9	387.1	382.4	377.1	373.2
42.5°	468.2	443.9	423.4	406.9	394.5	384.4	375.9	369.0	363.1	359.3	356.1
45°	437.0	412.7	392.8	377.5	366.0	356.4	347.6	344.1	336.4	331.8	330.3
47.5°	404.7	383.0	363.8	349.6	337.8	328.7	320.4	313.5	309.2	304.7	302.3
50°	382.8	362.1	344.1	330.3	318.8	308.8	301.1	296.5	290.7	286.6	283.5
52.5°	361.0	341.8	323.9	310.6	300.6	290.7	282.2	277.5	272.1	269.3	267.2
55°	329.9	309.6	294.3	281.1	270.8	261.7	253.6	248.9	245.5	242.9	242.1
57.5°	294.6	278.5	264.3	252.5	241.8	233.1	226.0	221.7	218.6	218.2	215.9
60°	271.6	257.0	244.0	231.4	222.1	214.1	207.9	203.0	199.9	199.4	198.7
62.5°	248.6	234.6	222.5	211.4	203.1	195.3	189.6	183.9	182.1	180.2	178.4
65°	214.4	201.8	191.8	183.0	174.2	167.6	161.9	158.4	154.2	151.9	147.7
67.5°	180.9	171.1	161.5	154.1	147.1	141.0	136.2	131.1	128.3	126.3	123.3
70°	158.9	151.2	141.6	133.5	128.2	123.1	119.3	113.5	111.6	110.1	108.6
72.5°	137.9	131.2	123.1	116.6	111.3	106.5	102.1	99.5	97.6	95.9	95.0
75°	108.6	102.0	95.1	90.5	86.7	82.9	80.6	78.7	77.9	77.5	75.9
77.5°	79.7	76.2	70.7	67.1	64.5	63.0	60.9	59.9	59.9	58.2	57.7
80°	61.0	59.1	54.4	52.9	51.0	49.5	48.4	46.5	44.5	43.7	42.6
82.5°	45.3	43.4	41.6	39.1	37.6	36.6	35.4	34.7	34.9	33.9	33.3
85°	24.1	22.2	21.5	21.1	20.3	21.1	20.7	20.3	20.0	19.6	20.0
87.5°	8.6	8.8	8.6	9.5	8.7	9.2	9.3	9.1	9.3	9.4	9.3
90°	4.6	5.8	6.4	7.5	8.1	9.2	9.8	10.4	10.9	11.5	12.6
92.5°	30.4	47.3	78.7	131.5	188.7	185.7	150.4	102.1	74.1	55.7	47.3
95°	43.2	69.2	130.8	257.5	416.5	510.4	499.5	414.1	326.6	255.8	207.4
97.5°	53.2	71.9	112.7	205.5	371.9	545.0	632.0	616.8	555.4	486.5	419.1
100°	61.1	78.4	111.8	186.6	331.8	520.2	664.2	708.5	680.3	621.0	561.1
102.5°	69.4	86.1	115.9	178.8	301.3	476.4	644.8	739.4	756.8	728.3	687.8
105°	82.9	99.1	124.4	175.7	271.9	417.7	583.0	721.2	800.1	825.5	819.1
107.5°	98.1	112.6	137.1	181.0	259.4	377.2	519.9	656.2	761.5	826.7	856.7
110°	107.8	122.7	146.3	186.0	255.8	358.3	483.9	608.3	717.8	799.0	848.0



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.9	132.4	155.1	192.5	255.8	347.3	457.2	570.6	674.5	756.6	814.4
115°	133.1	147.4	168.7	202.2	257.5	335.3	428.0	523.0	612.4	691.3	754.1
117.5°	148.8	162.7	182.9	213.3	261.3	329.4	410.6	492.4	569.4	637.3	695.0
120°	158.4	172.8	193.0	220.7	265.0	326.6	400.9	475.8	544.9	608.3	659.0
122.5°	168.1	182.5	202.7	228.9	268.2	324.4	392.6	463.4	527.5	583.9	631.4
125°	181.5	196.4	215.4	240.2	273.7	321.4	381.3	445.2	504.0	554.2	595.6
127.5°	194.5	209.4	227.7	250.5	279.7	320.0	371.0	426.9	481.7	528.5	567.3
130°	202.8	217.7	235.6	257.5	283.5	319.1	364.1	415.4	466.1	511.0	548.4
132.5°	210.2	225.1	243.0	263.5	287.6	319.1	358.5	403.8	451.3	492.1	528.2
135°	219.4	235.0	252.9	271.9	293.2	319.1	351.9	388.8	428.6	465.4	498.3
137.5°	227.6	243.7	259.9	278.1	298.4	319.8	346.1	376.2	408.3	439.0	466.9
140°	232.8	248.3	265.0	282.3	300.7	320.3	343.4	369.2	396.4	422.8	447.1
142.5°	237.8	252.5	268.2	284.6	302.1	320.7	341.0	363.2	386.2	409.0	430.0
145°	245.4	258.6	273.7	288.0	303.6	320.3	337.6	355.5	373.2	391.1	406.7
147.5°	252.3	264.0	277.1	290.1	304.2	318.8	334.0	348.1	362.5	376.3	388.0
150°	256.9	266.7	279.4	291.4	304.2	317.4	331.2	343.9	356.6	367.5	377.9
152.5°	261.1	269.9	281.7	292.4	303.7	315.6	328.0	339.3	350.6	360.6	368.7
155°	266.1	274.2	284.0	293.2	302.5	312.3	322.6	332.3	341.6	349.6	356.0
157.5°	271.5	277.5	286.0	293.8	300.9	308.7	317.5	325.5	333.1	339.3	344.3
160°	274.2	279.4	286.9	293.8	299.5	306.5	313.4	320.8	326.6	332.3	336.4
162.5°	277.0	281.2	287.8	293.4	298.2	303.7	309.7	315.8	321.1	325.9	329.5
165°	279.9	283.5	288.0	292.7	296.1	299.5	304.2	308.7	312.8	316.3	319.1
167.5°	282.1	284.2	288.0	291.2	292.9	295.5	298.7	302.1	304.8	307.4	309.4
170°	283.5	285.2	288.0	290.3	291.4	293.2	295.5	298.4	300.1	301.8	303.0
172.5°	284.4	285.2	287.6	289.4	289.6	290.4	292.3	294.3	296.0	297.2	297.9
175°	285.2	285.2	286.9	288.0	287.4	287.4	288.0	289.7	289.7	290.9	290.9
177.5°	285.3	285.3	286.2	286.6	285.7	285.7	286.2	286.6	287.1	287.1	287.1
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.2	891.8	890.9	892.1	890.9	891.8	895.2	895.5	895.9	898.3	894.9
5°	826.0	822.1	824.0	823.2	824.0	822.1	826.0	829.8	830.5	833.9	836.3
7.5°	765.0	760.2	755.2	756.8	755.2	760.2	765.0	765.1	771.0	775.5	778.5
10°	722.4	718.5	716.2	718.1	716.2	718.5	722.4	727.3	729.6	735.0	740.7
12.5°	686.4	684.2	682.2	681.4	682.2	684.2	686.4	691.8	697.1	703.4	709.7
15°	637.5	633.0	631.1	626.1	631.1	633.0	637.5	642.2	652.6	655.2	664.8
17.5°	592.5	591.0	586.0	583.9	586.0	591.0	592.5	596.4	601.2	611.1	618.3
20°	565.8	564.3	559.4	562.4	559.4	564.3	565.8	571.6	575.4	583.5	590.4
22.5°	543.7	540.4	538.8	537.9	538.8	540.4	543.7	546.4	551.5	559.0	566.7
25°	512.5	507.6	505.6	503.3	505.6	507.6	512.5	514.0	519.4	526.7	530.9
27.5°	481.4	478.7	476.2	475.5	476.2	478.7	481.4	483.5	488.2	494.5	502.2
30°	461.1	458.4	456.5	456.5	456.5	458.4	461.1	465.7	469.2	474.9	480.7
32.5°	443.0	440.9	439.0	438.7	439.0	440.9	443.0	445.5	449.5	455.9	461.9
35°	416.6	413.5	412.7	410.5	412.7	413.5	416.6	418.5	422.7	427.4	432.3
37.5°	389.2	386.7	386.6	386.4	386.6	386.7	389.2	392.6	396.2	400.3	406.4
40°	371.7	369.8	369.4	366.8	369.4	369.8	371.7	373.2	377.1	382.4	387.1
42.5°	353.0	352.0	350.7	349.5	350.7	352.0	353.0	356.1	359.3	363.1	369.0
45°	327.6	325.0	325.0	323.1	325.0	325.0	327.6	330.3	331.8	336.4	344.1
47.5°	301.3	299.3	299.5	297.5	299.5	299.3	301.3	302.3	304.7	309.2	313.5
50°	283.9	282.8	282.4	281.6	282.4	282.8	283.9	283.5	286.6	290.7	296.5
52.5°	266.4	265.9	267.3	265.6	267.3	265.9	266.4	267.2	269.3	272.1	277.5
55°	242.9	241.7	244.0	241.7	244.0	241.7	242.9	242.1	242.9	245.5	248.9
57.5°	215.7	214.7	216.7	215.6	216.7	214.7	215.7	215.9	218.2	218.6	221.7
60°	197.9	195.6	196.8	197.2	196.8	195.6	197.9	198.7	199.4	199.9	203.0
62.5°	176.7	175.4	176.2	174.5	176.2	175.4	176.7	178.4	180.2	182.1	183.9
65°	146.9	145.8	144.2	143.5	144.2	145.8	146.9	147.7	151.9	154.2	158.4
67.5°	123.4	120.7	120.6	121.2	120.6	120.7	123.4	123.3	126.3	128.3	131.1
70°	106.2	106.2	105.8	105.8	105.8	106.2	106.2	108.6	110.1	111.6	113.5
72.5°	94.3	94.0	93.3	93.0	93.3	94.0	94.3	95.0	95.9	97.6	99.5
75°	75.9	76.3	75.5	75.2	75.5	76.3	75.9	75.9	77.5	77.9	78.7
77.5°	56.0	54.4	55.3	54.4	55.3	54.4	56.0	57.7	58.2	59.9	59.9
80°	42.6	42.2	43.3	42.2	43.3	42.2	42.6	42.6	43.7	44.5	46.5
82.5°	33.7	33.3	33.8	33.0	33.8	33.3	33.7	33.3	33.9	34.9	34.7
85°	20.3	20.0	19.6	20.0	19.6	20.0	20.3	20.0	19.6	20.0	20.3
87.5°	9.6	9.3	9.4	9.4	9.4	9.3	9.6	9.3	9.4	9.3	9.1
90°	12.6	12.6	13.2	13.2	13.2	12.6	12.6	12.6	11.5	10.9	10.4
92.5°	39.9	38.5	37.7	36.8	37.7	38.5	39.9	47.3	55.7	74.1	102.1
95°	166.5	149.2	144.6	135.4	144.6	149.2	166.5	207.4	255.8	326.6	414.1
97.5°	383.5	351.2	334.6	327.2	334.6	351.2	383.5	419.1	486.5	555.4	616.8
100°	521.3	479.9	458.6	449.3	458.6	479.9	521.3	561.1	621.0	680.3	708.5
102.5°	645.3	615.8	592.7	585.7	592.7	615.8	645.3	687.8	728.3	756.8	739.4
105°	800.7	781.7	770.2	763.3	770.2	781.7	800.7	819.1	825.5	800.1	721.2
107.5°	866.1	866.0	862.1	857.5	862.1	866.0	866.1	856.7	826.7	761.5	656.2
110°	873.8	884.8	888.9	888.9	888.9	884.8	873.8	848.0	799.0	717.8	608.3



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	852.2	871.0	881.0	885.1	881.0	871.0	852.2	814.4	756.6	674.5	570.6
115°	799.0	826.7	842.7	850.3	842.7	826.7	799.0	754.1	691.3	612.4	523.0
117.5°	739.9	768.5	784.5	789.1	784.5	768.5	739.9	695.0	637.3	569.4	492.4
120°	701.7	729.3	744.9	749.4	744.9	729.3	701.7	659.0	608.3	544.9	475.8
122.5°	669.3	694.7	710.2	714.4	710.2	694.7	669.3	631.4	583.9	527.5	463.4
125°	627.9	651.6	664.2	669.9	664.2	651.6	627.9	595.6	554.2	504.0	445.2
127.5°	596.5	617.4	629.3	632.0	629.3	617.4	596.5	567.3	528.5	481.7	426.9
130°	577.2	596.2	607.7	611.2	607.7	596.2	577.2	548.4	511.0	466.1	415.4
132.5°	556.9	575.9	586.5	590.5	586.5	575.9	556.9	528.2	492.1	451.3	403.8
135°	523.6	542.6	553.0	556.4	553.0	542.6	523.6	498.3	465.4	428.6	388.8
137.5°	489.5	506.9	516.3	520.2	516.3	506.9	489.5	466.9	439.0	408.3	376.2
140°	468.4	483.3	491.9	494.8	491.9	483.3	468.4	447.1	422.8	396.4	369.2
142.5°	448.1	460.7	468.9	471.3	468.9	460.7	448.1	430.0	409.0	386.2	363.2
145°	420.5	430.3	436.7	439.0	436.7	430.3	420.5	406.7	391.1	373.2	355.5
147.5°	399.0	406.8	410.5	411.5	410.5	406.8	399.0	388.0	376.3	362.5	348.1
150°	386.6	393.4	395.8	396.4	395.8	393.4	386.6	377.9	367.5	356.6	343.9
152.5°	376.0	381.4	383.7	384.4	383.7	381.4	376.0	368.7	360.6	350.6	339.3
155°	361.7	365.8	367.5	368.1	367.5	365.8	361.7	356.0	349.6	341.6	332.3
157.5°	348.7	352.0	353.7	353.6	353.7	352.0	348.7	344.3	339.3	333.1	325.5
160°	340.4	343.4	344.5	343.9	344.5	343.4	340.4	336.4	332.3	326.6	320.8
162.5°	332.6	335.1	335.3	335.2	335.3	335.1	332.6	329.5	325.9	321.1	315.8
165°	321.4	322.6	322.6	322.6	322.6	322.6	321.4	319.1	316.3	312.8	308.7
167.5°	310.6	311.6	311.1	311.0	311.1	311.6	310.6	309.4	307.4	304.8	302.1
170°	304.2	304.8	304.8	304.2	304.8	304.8	304.2	303.0	301.8	300.1	298.4
172.5°	298.2	299.2	298.3	297.7	298.3	299.2	298.2	297.9	297.2	296.0	294.3
175°	290.9	291.4	290.3	289.7	290.3	291.4	290.9	290.9	290.9	289.7	289.7
177.5°	286.6	287.1	285.7	285.7	285.7	287.1	286.6	287.1	287.1	287.1	286.6
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	895.9	899.2	901.0	905.3	911.5	914.5	918.9	921.9	926.2	931.4	935.7
5°	837.8	847.1	853.1	862.7	871.6	880.4	891.5	899.6	910.3	922.6	932.2
7.5°	784.0	795.5	805.7	818.3	832.9	844.2	858.8	873.5	890.4	907.8	924.2
10°	749.6	761.1	773.8	789.5	804.1	819.4	836.7	853.9	875.0	894.6	916.9
12.5°	715.5	728.2	742.5	760.0	777.7	797.3	814.9	834.2	857.0	882.3	906.2
15°	673.3	685.5	700.8	715.8	736.2	757.6	781.0	806.8	832.0	860.5	890.0
17.5°	627.9	641.4	658.3	675.6	697.0	722.2	745.2	773.3	801.7	834.9	869.6
20°	598.4	612.3	632.2	651.4	671.0	695.5	722.8	751.5	781.8	816.7	855.5
22.5°	575.1	584.9	604.6	624.1	647.0	672.2	698.8	728.8	761.8	798.0	838.6
25°	540.5	552.0	566.2	586.5	610.4	636.8	663.7	695.5	731.5	768.4	811.7
27.5°	509.8	519.2	533.2	549.2	572.9	600.4	628.9	662.2	699.1	736.6	782.2
30°	488.0	498.4	511.7	528.7	547.4	577.3	606.5	639.1	676.7	715.5	762.2
32.5°	469.0	479.6	491.2	507.2	527.5	554.0	584.1	616.1	654.3	694.3	739.8
35°	442.3	449.6	460.3	476.1	496.0	517.5	548.2	582.0	619.1	660.6	706.2
37.5°	411.8	421.2	431.9	445.6	463.0	486.3	514.8	549.0	583.5	623.2	664.8
40°	393.9	402.8	414.7	424.6	443.1	464.1	490.3	525.9	560.5	597.6	635.6
42.5°	375.9	384.4	394.5	406.9	423.4	443.9	468.2	501.4	538.4	573.4	605.3
45°	347.6	356.4	366.0	377.5	392.8	412.7	437.0	467.3	499.5	531.7	555.8
47.5°	320.4	328.7	337.8	349.6	363.8	383.0	404.7	431.4	462.7	490.1	507.4
50°	301.1	308.8	318.8	330.3	344.1	362.1	382.8	409.3	435.5	460.3	476.1
52.5°	282.2	290.7	300.6	310.6	323.9	341.8	361.0	383.8	408.7	429.0	442.0
55°	253.6	261.7	270.8	281.1	294.3	309.6	329.9	347.9	367.5	384.8	392.4
57.5°	226.0	233.1	241.8	252.5	264.3	278.5	294.6	311.9	325.8	338.0	346.7
60°	207.9	214.1	222.1	231.4	244.0	257.0	271.6	287.7	298.4	308.8	316.9
62.5°	189.6	195.3	203.1	211.4	222.5	234.6	248.6	261.7	272.1	279.0	288.3
65°	161.9	167.6	174.2	183.0	191.8	201.8	214.4	224.0	231.4	239.0	244.8
67.5°	136.2	141.0	147.1	154.1	161.5	171.1	180.9	188.8	193.9	198.4	205.4
70°	119.3	123.1	128.2	133.5	141.6	151.2	158.9	164.9	168.4	173.0	181.5
72.5°	102.1	106.5	111.3	116.6	123.1	131.2	137.9	144.1	146.3	150.0	155.3
75°	80.6	82.9	86.7	90.5	95.1	102.0	108.6	110.1	112.0	115.1	119.0
77.5°	60.9	63.0	64.5	67.1	70.7	76.2	79.7	82.0	82.5	83.6	87.4
80°	48.4	49.5	51.0	52.9	54.4	59.1	61.0	63.3	64.0	65.2	67.2
82.5°	35.4	36.6	37.6	39.1	41.6	43.4	45.3	47.7	47.8	48.7	49.0
85°	20.7	21.1	20.3	21.1	21.5	22.2	24.1	26.1	25.8	25.3	26.5
87.5°	9.3	9.2	8.7	9.5	8.6	8.8	8.6	8.7	9.1	9.4	9.9
90°	9.8	9.2	8.1	7.5	6.4	5.8	4.6	3.4	2.3	1.1	0.6
92.5°	150.4	185.7	188.7	131.5	78.7	47.3	30.4	20.5	13.3	8.5	7.1
95°	499.5	510.4	416.5	257.5	130.8	69.2	43.2	30.5	24.2	19.6	19.0
97.5°	632.0	545.0	371.9	205.5	112.7	71.9	53.2	41.8	35.4	32.2	31.6
100°	664.2	520.2	331.8	186.6	111.8	78.4	61.1	50.1	43.8	41.5	40.3
102.5°	644.8	476.4	301.3	178.8	115.9	86.1	69.4	59.4	52.5	50.7	50.0
105°	583.0	417.7	271.9	175.7	124.4	99.1	82.9	73.7	68.0	65.1	65.1
107.5°	519.9	377.2	259.4	181.0	137.1	112.6	98.1	88.5	83.7	81.0	79.9
110°	483.9	358.3	255.8	186.0	146.3	122.7	107.8	99.1	93.9	91.6	90.5



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.2	347.3	255.8	192.5	155.1	132.4	117.9	109.3	104.0	102.2	101.1
115°	428.0	335.3	257.5	202.2	168.7	147.4	133.1	124.4	119.3	117.5	116.3
117.5°	410.6	329.4	261.3	213.3	182.9	162.7	148.8	139.0	133.8	131.9	130.2
120°	400.9	326.6	265.0	220.7	193.0	172.8	158.4	148.7	143.4	141.2	139.4
122.5°	392.6	324.4	268.2	228.9	202.7	182.5	168.1	157.3	152.2	150.4	149.1
125°	381.3	321.4	273.7	240.2	215.4	196.4	181.5	170.5	165.3	162.5	161.3
127.5°	371.0	320.0	279.7	250.5	227.7	209.4	194.5	182.9	176.3	172.6	170.9
130°	364.1	319.1	283.5	257.5	235.6	217.7	202.8	190.7	183.2	178.5	176.8
132.5°	358.5	319.1	287.6	263.5	243.0	225.1	210.2	197.6	189.1	183.7	181.5
135°	351.9	319.1	293.2	271.9	252.9	235.0	219.4	207.4	198.1	191.3	188.9
137.5°	346.1	319.8	298.4	278.1	259.9	243.7	227.6	215.8	206.6	200.2	198.4
140°	343.4	320.3	300.7	282.3	265.0	248.3	232.8	221.8	212.6	205.6	203.9
142.5°	341.0	320.7	302.1	284.6	268.2	252.5	237.8	227.3	218.1	211.7	210.4
145°	337.6	320.3	303.6	288.0	273.7	258.6	245.4	235.0	226.9	221.2	220.0
147.5°	334.0	318.8	304.2	290.1	277.1	264.0	252.3	243.3	235.8	230.9	230.1
150°	331.2	317.4	304.2	291.4	279.4	266.7	256.9	248.8	241.4	237.3	236.2
152.5°	328.0	315.6	303.7	292.4	281.7	269.9	261.1	253.5	246.9	243.3	242.7
155°	322.6	312.3	302.5	293.2	284.0	274.2	266.1	260.3	254.6	251.2	251.2
157.5°	317.5	308.7	300.9	293.8	286.0	277.5	271.5	266.4	261.5	258.6	258.7
160°	313.4	306.5	299.5	293.8	286.9	279.4	274.2	269.6	265.6	263.3	263.9
162.5°	309.7	303.7	298.2	293.4	287.8	281.2	277.0	273.3	269.7	267.4	268.0
165°	304.2	299.5	296.1	292.7	288.0	283.5	279.9	277.6	274.8	273.1	274.2
167.5°	298.7	295.5	292.9	291.2	288.0	284.2	282.1	280.4	278.8	277.8	278.3
170°	295.5	293.2	291.4	290.3	288.0	285.2	283.5	282.3	281.1	280.5	281.1
172.5°	292.3	290.4	289.6	289.4	287.6	285.2	284.4	283.7	282.5	282.0	283.0
175°	288.0	287.4	287.4	288.0	286.9	285.2	285.2	285.2	284.6	284.0	285.2
177.5°	286.2	285.7	285.7	286.6	286.2	285.3	285.3	285.7	285.3	285.3	286.2
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	939.1	941.9	945.8	950.5	954.1	958.2	960.3	960.3	962.1	966.1	971.3
5°	941.8	951.8	961.4	973.6	983.2	994.3	1002.8	1010.9	1018.1	1027.3	1036.9
7.5°	941.0	957.6	974.8	994.2	1015.5	1032.5	1049.9	1063.6	1077.0	1094.7	1108.6
10°	938.0	959.5	982.8	1007.3	1034.2	1057.6	1078.7	1097.9	1116.3	1135.5	1152.8
12.5°	932.4	959.8	988.4	1017.8	1051.8	1078.5	1105.7	1126.2	1147.6	1168.6	1189.9
15°	924.1	956.3	990.9	1032.0	1073.4	1103.3	1130.1	1156.6	1176.6	1200.3	1220.7
17.5°	907.1	948.6	992.0	1036.8	1076.6	1111.5	1139.5	1164.8	1186.0	1212.1	1239.8
20°	896.9	941.8	987.0	1035.0	1073.0	1108.6	1135.9	1162.0	1188.4	1222.6	1256.4
22.5°	882.8	930.7	978.8	1024.3	1064.4	1098.8	1127.0	1158.9	1193.7	1232.4	1273.2
25°	860.5	910.0	957.6	1000.9	1040.0	1075.3	1113.7	1156.6	1198.8	1249.8	1308.5
27.5°	832.1	879.9	922.3	968.1	1007.0	1051.9	1099.7	1146.3	1207.2	1277.4	1350.7
30°	810.9	856.3	896.6	939.9	984.0	1033.5	1087.2	1142.1	1214.6	1297.0	1384.1
32.5°	786.4	827.4	867.4	909.2	960.1	1014.4	1071.6	1138.6	1225.3	1319.1	1409.3
35°	743.9	780.6	819.4	865.9	919.9	979.0	1051.9	1133.6	1238.3	1339.2	1420.2
37.5°	699.2	728.2	767.2	816.1	875.0	943.4	1026.1	1125.4	1232.9	1323.5	1358.0
40°	664.8	692.1	733.1	784.5	842.8	917.7	1010.5	1112.5	1220.7	1283.5	1280.9
42.5°	630.8	658.3	697.8	749.5	810.3	894.0	989.6	1095.6	1186.9	1210.8	1160.9
45°	578.5	604.2	643.0	695.1	760.3	848.2	948.7	1050.4	1108.6	1070.0	971.0
47.5°	525.2	550.2	586.1	637.2	708.4	800.4	895.4	978.9	987.0	903.8	785.1
50°	490.3	513.6	547.9	602.3	671.4	761.1	852.8	918.4	898.1	796.4	674.0
52.5°	456.2	478.7	510.7	562.1	632.7	720.6	802.4	853.9	806.9	698.8	588.8
55°	405.9	427.4	459.6	506.8	570.8	651.4	723.2	741.9	672.9	563.9	474.9
57.5°	358.1	373.8	405.7	447.4	509.2	580.2	631.6	628.2	552.0	453.9	390.1
60°	326.5	340.6	370.9	409.3	468.0	531.7	567.7	552.4	475.3	394.4	333.0
62.5°	297.0	310.2	335.7	370.9	421.4	476.8	503.0	481.8	409.0	337.9	289.1
65°	252.5	262.1	282.4	315.0	354.5	392.8	416.3	385.2	320.7	267.0	230.1
67.5°	210.8	219.0	237.1	260.5	287.8	314.3	323.8	294.6	244.5	208.3	182.4
70°	183.8	191.5	203.7	225.6	243.6	262.4	267.0	241.0	199.1	171.5	155.3
72.5°	157.9	165.0	175.8	191.2	203.7	214.5	216.7	192.4	160.5	141.4	129.0
75°	120.5	126.6	133.5	139.3	147.3	149.3	148.5	129.7	112.4	99.8	92.8
77.5°	88.6	91.1	95.3	97.6	98.0	97.9	93.9	82.0	73.1	67.9	65.0
80°	68.3	70.2	71.4	72.1	72.5	68.7	64.4	57.2	54.1	51.0	47.6
82.5°	49.6	50.9	52.0	52.2	50.1	46.9	42.9	39.4	37.2	35.6	34.3
85°	26.9	27.3	26.9	24.9	22.2	21.1	20.3	19.6	19.2	18.8	18.8
87.5°	9.7	9.1	7.8	8.3	8.5	8.3	8.6	8.4	8.3	8.4	8.5
90°	1.1	2.3	3.4	4.6	5.8	6.4	7.5	8.1	9.2	9.8	10.4
92.5°	8.5	13.3	20.5	30.4	47.3	78.7	131.5	188.7	185.7	150.4	102.1
95°	19.6	24.2	30.5	43.2	69.2	130.8	257.5	416.5	510.4	499.5	414.1
97.5°	32.2	35.4	41.8	53.2	71.9	112.7	205.5	371.9	545.0	632.0	616.8
100°	41.5	43.8	50.1	61.1	78.4	111.8	186.6	331.8	520.2	664.2	708.5
102.5°	50.7	52.5	59.4	69.4	86.1	115.9	178.8	301.3	476.4	644.8	739.4
105°	65.1	68.0	73.7	82.9	99.1	124.4	175.7	271.9	417.7	583.0	721.2
107.5°	81.0	83.7	88.5	98.1	112.6	137.1	181.0	259.4	377.2	519.9	656.2
110°	91.6	93.9	99.1	107.8	122.7	146.3	186.0	255.8	358.3	483.9	608.3



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	102.2	104.0	109.3	117.9	132.4	155.1	192.5	255.8	347.3	457.2	570.6
115°	117.5	119.3	124.4	133.1	147.4	168.7	202.2	257.5	335.3	428.0	523.0
117.5°	131.9	133.8	139.0	148.8	162.7	182.9	213.3	261.3	329.4	410.6	492.4
120°	141.2	143.4	148.7	158.4	172.8	193.0	220.7	265.0	326.6	400.9	475.8
122.5°	150.4	152.2	157.3	168.1	182.5	202.7	228.9	268.2	324.4	392.6	463.4
125°	162.5	165.3	170.5	181.5	196.4	215.4	240.2	273.7	321.4	381.3	445.2
127.5°	172.6	176.3	182.9	194.5	209.4	227.7	250.5	279.7	320.0	371.0	426.9
130°	178.5	183.2	190.7	202.8	217.7	235.6	257.5	283.5	319.1	364.1	415.4
132.5°	183.7	189.1	197.6	210.2	225.1	243.0	263.5	287.6	319.1	358.5	403.8
135°	191.3	198.1	207.4	219.4	235.0	252.9	271.9	293.2	319.1	351.9	388.8
137.5°	200.2	206.6	215.8	227.6	243.7	259.9	278.1	298.4	319.8	346.1	376.2
140°	205.6	212.6	221.8	232.8	248.3	265.0	282.3	300.7	320.3	343.4	369.2
142.5°	211.7	218.1	227.3	237.8	252.5	268.2	284.6	302.1	320.7	341.0	363.2
145°	221.2	226.9	235.0	245.4	258.6	273.7	288.0	303.6	320.3	337.6	355.5
147.5°	230.9	235.8	243.3	252.3	264.0	277.1	290.1	304.2	318.8	334.0	348.1
150°	237.3	241.4	248.8	256.9	266.7	279.4	291.4	304.2	317.4	331.2	343.9
152.5°	243.3	246.9	253.5	261.1	269.9	281.7	292.4	303.7	315.6	328.0	339.3
155°	251.2	254.6	260.3	266.1	274.2	284.0	293.2	302.5	312.3	322.6	332.3
157.5°	258.6	261.5	266.4	271.5	277.5	286.0	293.8	300.9	308.7	317.5	325.5
160°	263.3	265.6	269.6	274.2	279.4	286.9	293.8	299.5	306.5	313.4	320.8
162.5°	267.4	269.7	273.3	277.0	281.2	287.8	293.4	298.2	303.7	309.7	315.8
165°	273.1	274.8	277.6	279.9	283.5	288.0	292.7	296.1	299.5	304.2	308.7
167.5°	277.8	278.8	280.4	282.1	284.2	288.0	291.2	292.9	295.5	298.7	302.1
170°	280.5	281.1	282.3	283.5	285.2	288.0	290.3	291.4	293.2	295.5	298.4
172.5°	282.0	282.5	283.7	284.4	285.2	287.6	289.4	289.6	290.4	292.3	294.3
175°	284.0	284.6	285.2	285.2	285.2	286.9	288.0	287.4	287.4	288.0	289.7
177.5°	285.3	285.3	285.7	285.3	285.3	286.2	286.6	285.7	285.7	286.2	286.6
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7	285.7



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	934.5	934.5	934.5	934.5	934.5	934.5	934.5
2.5°	975.3	975.3	980.6	980.2	983.6	982.4	983.0
5°	1048.4	1054.9	1060.7	1064.5	1070.3	1071.9	1071.1
7.5°	1124.3	1138.7	1145.8	1155.5	1157.2	1162.3	1161.7
10°	1171.1	1185.4	1196.1	1204.6	1208.8	1214.2	1214.6
12.5°	1208.0	1220.0	1229.6	1237.4	1242.5	1244.3	1245.3
15°	1236.8	1250.2	1261.3	1272.4	1279.0	1283.9	1286.7
17.5°	1265.8	1286.5	1306.2	1321.3	1330.3	1338.0	1337.9
20°	1288.2	1312.0	1336.6	1353.8	1371.4	1379.1	1380.3
22.5°	1312.1	1348.5	1380.1	1406.8	1430.1	1438.0	1441.0
25°	1361.8	1409.4	1458.1	1495.7	1522.6	1538.3	1540.7
27.5°	1421.9	1486.3	1537.5	1572.3	1594.6	1606.2	1608.7
30°	1464.3	1523.7	1569.7	1595.9	1606.2	1607.7	1601.9
32.5°	1483.3	1527.7	1546.1	1544.6	1524.3	1510.8	1505.6
35°	1460.1	1450.9	1405.9	1352.2	1311.2	1285.2	1278.2
37.5°	1328.7	1249.3	1166.7	1085.6	1042.4	1020.5	982.7
40°	1199.2	1086.0	1000.1	931.8	883.1	843.9	834.8
42.5°	1053.1	936.2	850.3	791.8	753.0	726.1	714.5
45°	846.3	745.8	674.8	629.9	600.0	580.4	571.6
47.5°	676.8	599.1	547.3	514.1	491.3	474.3	469.6
50°	583.9	521.7	478.0	450.0	432.7	419.7	414.3
52.5°	507.2	457.0	423.3	400.3	384.0	375.8	371.3
55°	418.5	375.2	351.0	332.5	323.4	316.9	313.8
57.5°	342.2	310.9	293.3	280.5	272.1	267.9	266.4
60°	299.6	275.1	258.9	248.9	243.2	237.8	236.3
62.5°	261.9	242.6	230.0	221.4	215.6	213.3	212.4
65°	211.0	198.3	189.1	183.8	179.2	178.3	178.0
67.5°	167.7	160.3	155.4	149.9	148.2	145.5	145.0
70°	143.5	138.5	132.7	130.8	128.9	126.2	126.6
72.5°	121.7	116.7	112.8	110.3	109.6	108.5	109.4
75°	89.0	87.5	85.9	84.0	83.2	83.2	82.9
77.5°	63.5	62.2	60.5	59.4	59.2	57.6	58.2
80°	46.0	44.1	43.3	43.7	42.6	42.2	42.2
82.5°	34.0	33.3	32.6	32.7	32.4	32.1	32.4
85°	18.8	18.4	18.4	18.1	18.1	17.7	17.7
87.5°	9.0	9.4	9.0	8.7	8.7	9.1	9.4
90°	10.9	11.5	12.6	12.6	12.6	13.2	13.2
92.5°	74.1	55.7	47.3	39.9	38.5	37.7	36.8
95°	326.6	255.8	207.4	166.5	149.2	144.6	135.4
97.5°	555.4	486.5	419.1	383.5	351.2	334.6	327.2
100°	680.3	621.0	561.1	521.3	479.9	458.6	449.3
102.5°	756.8	728.3	687.8	645.3	615.8	592.7	585.7
105°	800.1	825.5	819.1	800.7	781.7	770.2	763.3
107.5°	761.5	826.7	856.7	866.1	866.0	862.1	857.5
110°	717.8	799.0	848.0	873.8	884.8	888.9	888.9



TEST NUMBER: P333528-840

CATALOG NUMBER: S125RDIP-S610D590U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	674.5	756.6	814.4	852.2	871.0	881.0	885.1
115°	612.4	691.3	754.1	799.0	826.7	842.7	850.3
117.5°	569.4	637.3	695.0	739.9	768.5	784.5	789.1
120°	544.9	608.3	659.0	701.7	729.3	744.9	749.4
122.5°	527.5	583.9	631.4	669.3	694.7	710.2	714.4
125°	504.0	554.2	595.6	627.9	651.6	664.2	669.9
127.5°	481.7	528.5	567.3	596.5	617.4	629.3	632.0
130°	466.1	511.0	548.4	577.2	596.2	607.7	611.2
132.5°	451.3	492.1	528.2	556.9	575.9	586.5	590.5
135°	428.6	465.4	498.3	523.6	542.6	553.0	556.4
137.5°	408.3	439.0	466.9	489.5	506.9	516.3	520.2
140°	396.4	422.8	447.1	468.4	483.3	491.9	494.8
142.5°	386.2	409.0	430.0	448.1	460.7	468.9	471.3
145°	373.2	391.1	406.7	420.5	430.3	436.7	439.0
147.5°	362.5	376.3	388.0	399.0	406.8	410.5	411.5
150°	356.6	367.5	377.9	386.6	393.4	395.8	396.4
152.5°	350.6	360.6	368.7	376.0	381.4	383.7	384.4
155°	341.6	349.6	356.0	361.7	365.8	367.5	368.1
157.5°	333.1	339.3	344.3	348.7	352.0	353.7	353.6
160°	326.6	332.3	336.4	340.4	343.4	344.5	343.9
162.5°	321.1	325.9	329.5	332.6	335.1	335.3	335.2
165°	312.8	316.3	319.1	321.4	322.6	322.6	322.6
167.5°	304.8	307.4	309.4	310.6	311.6	311.1	311.0
170°	300.1	301.8	303.0	304.2	304.8	304.8	304.2
172.5°	296.0	297.2	297.9	298.2	299.2	298.3	297.7
175°	289.7	290.9	290.9	290.9	291.4	290.3	289.7
177.5°	287.1	287.1	287.1	286.6	287.1	285.7	285.7
180°	285.7	285.7	285.7	285.7	285.7	285.7	285.7

(END OF REPORT)