

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333552-840

Luminaire Tested: **S125RDIP-S850D365U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333552-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D365U840-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4638.0 lumens  
Efficiency: N/A  
Efficacy: 132.5 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	99	95	92	98	94	91	88	85	82	80	76	74	72	68	67	65	61
2	94	87	81	76	89	83	77	73	75	71	67	67	64	61	61	58	56	52
3	87	77	70	64	82	73	67	62	66	61	57	60	56	52	54	51	48	45
4	79	69	61	55	75	65	58	53	59	54	49	54	49	45	49	45	42	39
5	73	61	53	47	69	59	51	46	53	47	43	49	44	40	44	40	37	34
6	68	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	33	30
7	63	50	42	36	59	48	41	35	44	38	33	40	35	31	37	32	29	27
8	58	46	38	32	55	44	37	32	40	34	30	37	32	28	34	29	26	24
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	31	27	24	22
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	25	21	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8250	8250	8250	8250
5°	9491	8261	7295	8261
10°	10887	8218	6437	8218
15°	11760	8134	5722	8134
20°	12967	8036	5283	8036
25°	15007	7906	4903	7906
30°	16330	7770	4653	7770
35°	13775	7611	4424	7611
40°	9620	7325	4226	7325
45°	7136	6940	4032	6940
50°	5690	6539	3867	6539
55°	4829	6040	3719	6040
60°	4173	5594	3481	5594
65°	3718	5113	2997	5113
70°	3269	4683	2732	4683
75°	2827	4057	2565	4057
80°	2146	3414	2146	3414
85°	1786	2682	2023	2682



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.5	2.6
10°-20°	359.0	7.7
20°-30°	569.2	12.3
30°-40°	686.4	14.8
40°-50°	613.0	13.2
50°-60°	470.0	10.1
60°-70°	305.5	6.6
70°-80°	148.5	3.2
80°-90°	36.4	0.8
90°-100°	128.3	2.8
100°-110°	275.8	5.9
110°-120°	258.9	5.6
120°-130°	209.8	4.5
130°-140°	168.4	3.6
140°-150°	127.0	2.7
150°-160°	89.4	1.9
160°-170°	52.7	1.1
170°-180°	17.1	0.4
0°-30°	1050.6	22.7
0°-40°	1737.0	37.5
0°-60°	2820.0	60.8
0°-90°	3310.5	71.4
90°-120°	663.0	14.3
90°-150°	1168.2	25.2
90°-180°	1328.0	28.6
0°-180°	4638.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1277	1277	1277	1277	1277	
5°	1464	1274	1125	1274	1464	146
15°	1759	1217	856	1217	1759	504
25°	2106	1110	688	1110	2106	967
35°	1747	965	561	965	1747	1055
45°	781	760	442	760	781	623
55°	429	536	330	536	429	389
65°	243	335	196	335	243	242
75°	113	163	103	163	113	121
85°	24	36	27	36	24	28
90°	8	0	8	0	8	7
95°	84	12	84	12	84	119
105°	473	40	473	40	473	470
115°	527	72	527	72	527	515
125°	415	100	415	100	415	376
135°	345	117	345	117	345	267
145°	272	136	272	136	272	173
155°	228	156	228	156	228	106
165°	200	170	200	170	200	57
175°	180	177	180	177	180	17
180°	177	177	177	177	177	



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1343.6	1342.8	1344.5	1339.9	1340.3	1333.1	1333.1	1327.7	1320.6	1315.1	1312.6
5°	1464.0	1465.1	1463.0	1455.1	1449.9	1442.0	1433.1	1417.3	1404.2	1391.7	1381.7
7.5°	1588.0	1588.7	1581.9	1579.4	1566.2	1556.5	1536.7	1515.3	1496.3	1472.2	1453.8
10°	1660.1	1659.6	1652.3	1646.5	1635.0	1620.3	1600.9	1575.7	1552.2	1525.9	1500.8
12.5°	1702.1	1700.7	1698.4	1691.4	1680.7	1667.7	1651.2	1626.5	1597.4	1568.7	1539.3
15°	1758.8	1755.0	1748.3	1739.3	1724.1	1708.9	1690.6	1668.6	1640.7	1608.2	1580.9
17.5°	1828.8	1828.9	1818.5	1806.0	1785.3	1758.6	1730.2	1694.7	1656.9	1621.1	1592.1
20°	1886.7	1885.1	1874.6	1850.5	1826.9	1793.3	1760.8	1717.3	1671.1	1624.5	1588.3
22.5°	1969.7	1965.7	1954.8	1923.1	1886.5	1843.3	1793.5	1740.4	1684.6	1631.6	1584.2
25°	2105.9	2102.7	2081.2	2044.6	1993.2	1926.5	1861.5	1788.7	1708.4	1638.7	1580.9
27.5°	2199.0	2195.5	2179.6	2149.1	2101.7	2031.6	1943.6	1846.2	1746.1	1650.1	1566.9
30°	2189.8	2197.7	2195.5	2181.4	2145.8	2082.8	2001.6	1892.0	1772.9	1660.1	1561.0
32.5°	2058.0	2065.1	2083.6	2111.3	2113.4	2088.3	2027.5	1926.3	1803.1	1674.9	1556.4
35°	1747.2	1756.7	1792.3	1848.5	1921.8	1983.2	1995.8	1941.3	1830.6	1692.6	1549.5
37.5°	1343.2	1394.8	1424.8	1483.9	1594.8	1707.7	1816.2	1856.1	1809.1	1685.4	1538.3
40°	1141.0	1153.6	1207.1	1273.7	1367.1	1484.5	1639.2	1750.9	1754.5	1668.6	1520.7
42.5°	976.5	992.5	1029.3	1082.4	1162.4	1279.8	1439.5	1586.9	1655.2	1622.4	1497.6
45°	781.3	793.3	820.1	861.0	922.4	1019.4	1156.8	1327.2	1462.5	1515.4	1435.7
47.5°	641.9	648.3	671.7	702.8	748.2	818.9	925.2	1073.2	1235.5	1349.2	1338.0
50°	566.3	573.7	591.5	615.1	653.4	713.2	798.1	921.3	1088.6	1227.6	1255.4
52.5°	507.6	513.7	524.8	547.1	578.7	624.6	693.2	804.7	955.2	1103.0	1167.2
55°	428.9	433.1	442.0	454.6	479.8	512.8	572.1	649.1	770.8	919.8	1014.1
57.5°	364.2	366.2	371.9	383.5	400.9	425.1	467.9	533.2	620.5	754.6	858.7
60°	323.1	325.1	332.4	340.3	354.0	376.0	409.5	455.1	539.1	649.6	755.1
62.5°	290.3	291.5	294.7	302.6	314.5	331.5	357.9	395.2	461.9	559.1	658.6
65°	243.3	243.9	244.9	251.2	258.5	271.1	288.4	314.6	365.0	438.4	526.4
67.5°	198.2	198.9	202.6	204.8	212.5	219.0	229.2	249.3	284.8	334.3	402.7
70°	173.1	172.5	176.2	178.8	181.5	189.2	196.1	212.4	234.4	272.2	329.3
72.5°	149.6	148.1	149.8	150.7	154.2	159.6	166.3	176.3	193.3	219.2	263.1
75°	113.3	113.8	113.8	114.8	117.4	119.6	121.7	126.9	136.3	153.6	177.2
77.5°	79.5	78.7	80.9	81.2	82.7	85.0	86.8	89.0	92.8	100.0	112.1
80°	57.7	57.7	58.2	59.8	59.3	60.3	62.9	65.0	69.8	73.9	78.2
82.5°	44.2	43.8	44.3	44.6	44.5	45.6	46.6	47.0	48.8	50.9	53.8
85°	24.1	24.1	24.6	24.6	25.1	25.1	25.7	25.7	25.7	26.3	26.8
87.5°	10.9	10.4	10.0	10.0	10.4	11.1	10.6	10.1	10.0	10.0	10.2
90°	8.2	8.2	7.9	7.9	7.9	7.2	6.8	6.5	6.1	5.8	4.9
92.5°	22.7	23.3	23.8	24.7	29.3	34.5	45.8	63.2	93.1	115.0	116.9
95°	83.9	89.6	92.4	103.1	128.5	158.4	202.4	256.6	309.4	316.2	258.0
97.5°	202.7	207.3	217.6	237.6	259.6	301.3	344.2	382.1	391.5	337.7	230.5
100°	278.4	284.1	297.3	323.0	347.6	384.8	421.5	439.0	411.5	322.2	205.6
102.5°	362.9	367.2	381.5	399.8	426.2	451.3	468.9	458.1	399.5	295.2	186.7
105°	472.9	477.2	484.3	496.0	507.6	511.4	495.7	446.9	361.2	258.7	168.4
107.5°	531.3	534.1	536.5	536.5	530.8	512.1	471.8	406.6	322.0	233.7	160.8
110°	550.7	550.7	548.2	541.4	525.3	495.0	444.7	376.9	299.8	222.0	158.4



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	548.5	545.8	539.7	528.0	504.5	468.8	417.9	353.5	283.3	215.1	158.4
115°	526.7	522.1	512.1	495.0	467.2	428.3	379.4	324.1	265.2	207.7	159.6
117.5°	488.9	486.0	476.2	458.4	430.6	394.9	352.7	305.1	254.4	204.1	161.9
120°	464.3	461.5	451.8	434.7	408.3	376.9	337.6	294.8	248.4	202.4	164.2
122.5°	442.6	440.1	430.4	414.8	391.1	361.7	326.8	287.1	243.3	201.0	166.1
125°	415.1	411.5	403.6	389.0	369.0	343.4	312.3	275.9	236.3	199.1	169.6
127.5°	391.5	389.9	382.5	369.6	351.4	327.4	298.4	264.5	229.8	198.3	173.3
130°	378.7	376.6	369.4	357.6	339.8	316.6	288.7	257.3	225.6	197.7	175.6
132.5°	365.8	363.3	356.8	345.1	327.2	304.9	279.6	250.1	222.2	197.7	178.1
135°	344.8	342.6	336.2	324.5	308.7	288.4	265.5	241.0	218.0	197.7	181.7
137.5°	322.2	319.9	314.0	303.3	289.2	272.0	253.0	233.1	214.4	198.1	184.9
140°	306.6	304.8	299.4	290.1	276.9	262.0	245.5	228.7	212.7	198.4	186.3
142.5°	292.1	290.5	285.5	277.6	266.4	253.4	239.2	225.1	211.3	198.7	187.1
145°	272.0	270.5	266.6	260.5	252.0	242.4	231.3	220.3	209.1	198.4	188.0
147.5°	255.0	254.3	252.1	247.2	240.4	233.2	224.6	215.6	206.9	197.5	188.4
150°	245.5	245.2	243.8	239.4	234.1	227.7	221.0	213.1	205.2	196.6	188.4
152.5°	238.1	237.7	236.3	232.9	228.4	223.4	217.2	210.3	203.2	195.5	188.1
155°	228.0	227.7	226.6	224.1	220.6	216.6	211.7	205.9	199.9	193.5	187.3
157.5°	219.0	219.1	218.1	216.1	213.3	210.3	206.3	201.7	196.7	191.3	186.4
160°	213.1	213.4	212.7	211.0	208.4	205.9	202.4	198.8	194.2	189.9	185.6
162.5°	207.6	207.7	207.5	206.1	204.2	202.0	198.9	195.6	191.9	188.1	184.7
165°	199.9	199.9	199.9	199.1	197.7	195.9	193.8	191.3	188.4	185.6	183.5
167.5°	192.7	192.8	193.1	192.5	191.8	190.5	188.8	187.1	185.1	183.1	181.5
170°	188.4	188.8	188.8	188.4	187.7	187.0	185.9	184.9	183.1	181.7	180.6
172.5°	184.4	184.8	185.4	184.7	184.6	184.2	183.4	182.3	181.1	180.0	179.5
175°	179.6	179.9	180.6	180.3	180.3	180.3	179.6	179.6	178.4	178.1	178.1
177.5°	177.0	177.0	177.8	177.6	177.8	177.8	177.8	177.6	177.3	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1312.6	1309.7	1304.2	1299.2	1292.9	1287.5	1283.6	1279.1	1273.1	1266.1	1260.2
5°	1370.7	1359.2	1343.9	1330.9	1314.0	1301.0	1287.4	1274.2	1261.1	1244.4	1229.6
7.5°	1435.1	1411.3	1388.2	1359.0	1332.5	1308.9	1286.3	1263.3	1240.9	1217.1	1194.1
10°	1474.5	1445.7	1413.7	1377.0	1343.4	1311.4	1282.1	1253.2	1222.8	1196.1	1167.2
12.5°	1511.5	1474.2	1437.6	1391.3	1351.0	1311.9	1274.6	1238.6	1206.1	1171.3	1140.4
15°	1544.8	1508.1	1467.2	1410.6	1354.4	1307.3	1263.2	1216.6	1176.2	1137.4	1102.8
17.5°	1557.7	1519.2	1471.7	1417.2	1355.9	1296.6	1239.8	1188.6	1141.1	1095.9	1057.0
20°	1552.7	1515.4	1466.6	1414.7	1349.2	1287.4	1226.0	1169.3	1116.4	1068.6	1027.2
22.5°	1540.4	1502.0	1454.9	1400.1	1337.9	1272.2	1206.7	1146.3	1090.8	1041.4	996.2
25°	1522.3	1469.9	1421.6	1368.1	1308.8	1243.9	1176.2	1109.5	1050.4	1000.0	950.7
27.5°	1503.3	1437.8	1376.4	1323.3	1260.7	1202.6	1137.5	1069.1	1006.9	955.6	905.0
30°	1486.1	1412.7	1345.0	1284.8	1225.5	1170.4	1108.5	1041.9	978.0	925.0	873.6
32.5°	1464.7	1386.6	1312.3	1242.7	1185.6	1130.9	1075.0	1011.3	949.0	894.3	842.1
35°	1437.8	1338.2	1257.5	1183.5	1120.0	1067.1	1016.7	965.3	902.9	846.4	795.5
37.5°	1402.6	1289.5	1196.1	1115.6	1048.6	995.4	955.7	908.8	851.8	797.6	750.3
40°	1381.2	1254.3	1152.1	1072.4	1002.1	945.9	908.8	868.9	817.0	766.1	718.9
42.5°	1352.7	1222.0	1107.6	1024.5	953.8	899.8	862.1	827.4	783.9	735.9	685.4
45°	1296.8	1159.4	1039.4	950.2	878.9	825.9	790.7	759.8	726.8	682.8	638.6
47.5°	1224.0	1094.1	968.4	871.1	801.2	752.0	718.0	693.6	669.9	632.5	589.7
50°	1165.7	1040.4	917.7	823.2	748.8	702.2	670.1	650.8	629.2	595.1	559.5
52.5°	1096.9	985.0	864.7	768.3	698.0	654.3	623.6	604.2	586.4	558.7	524.7
55°	988.5	890.4	780.2	692.7	628.2	584.1	554.8	536.4	525.9	502.3	475.6
57.5°	863.3	793.0	695.9	611.5	554.5	511.0	489.5	473.8	462.0	445.2	426.5
60°	776.1	726.8	639.7	559.5	507.1	465.6	446.3	433.1	422.1	408.0	393.2
62.5°	687.5	651.7	575.9	507.1	458.8	424.1	406.0	394.2	381.4	371.9	357.6
65°	569.0	536.9	484.5	430.5	386.0	358.1	345.1	334.6	326.7	316.2	306.2
67.5°	442.5	429.6	393.3	356.2	324.2	299.4	288.1	280.7	271.4	265.0	258.2
70°	365.0	358.7	333.0	308.3	278.4	261.7	251.2	248.0	236.5	230.2	225.5
72.5°	296.2	293.3	278.4	261.4	240.2	225.6	215.9	212.4	205.0	200.0	196.9
75°	202.9	204.0	201.4	190.4	182.5	173.1	164.6	162.6	157.3	153.1	150.5
77.5°	128.4	133.7	133.9	133.4	130.3	124.5	121.0	119.5	114.3	112.7	112.1
80°	88.1	93.8	99.1	98.6	97.6	95.9	93.3	91.8	89.2	87.6	86.5
82.5°	58.8	64.1	68.5	71.3	71.1	69.6	67.8	67.1	66.4	65.3	65.1
85°	27.8	28.9	30.4	34.1	36.7	37.3	36.7	36.2	34.6	35.1	35.6
87.5°	10.6	10.4	10.8	10.6	10.1	12.0	13.1	13.5	12.7	12.0	11.3
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	81.4	48.8	29.3	18.9	12.7	8.3	5.3	4.3	5.3	8.3	12.7
95°	159.6	81.0	42.8	26.8	18.9	14.9	12.1	11.8	12.1	14.9	18.9
97.5°	127.3	69.8	44.5	33.0	26.0	22.0	20.0	19.6	20.0	22.0	26.0
100°	115.6	69.3	48.6	37.9	31.0	27.2	25.7	24.9	25.7	27.2	31.0
102.5°	110.8	71.8	53.4	43.0	36.8	32.5	31.4	31.0	31.4	32.5	36.8
105°	108.9	77.1	61.4	51.4	45.6	42.1	40.3	40.3	40.3	42.1	45.6
107.5°	112.1	84.9	69.8	60.8	54.8	51.9	50.2	49.5	50.2	51.9	54.8
110°	115.3	90.7	76.0	66.8	61.4	58.2	56.8	56.0	56.8	58.2	61.4





TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	119.3	96.0	82.0	73.0	67.7	64.4	63.3	62.6	63.3	64.4	67.7
115°	125.2	104.6	91.4	82.4	77.1	73.9	72.8	72.1	72.8	73.9	77.1
117.5°	132.1	113.3	100.8	92.2	86.0	82.9	81.7	80.7	81.7	82.9	86.0
120°	136.7	119.6	107.0	98.2	92.1	88.9	87.5	86.3	87.5	88.9	92.1
122.5°	141.8	125.5	113.1	104.1	97.6	94.3	93.1	92.4	93.1	94.3	97.6
125°	148.9	133.5	121.7	112.4	105.6	102.4	100.7	100.0	100.7	102.4	105.6
127.5°	155.2	141.1	129.8	120.5	113.3	109.2	106.9	105.8	106.9	109.2	113.3
130°	159.6	145.9	134.9	125.6	118.2	113.5	110.7	109.6	110.7	113.5	118.2
132.5°	163.3	150.6	139.5	130.2	122.4	117.2	113.8	112.4	113.8	117.2	122.4
135°	168.4	156.6	145.6	136.0	128.5	122.8	118.5	117.0	118.5	122.8	128.5
137.5°	172.3	161.1	151.0	141.1	133.7	127.9	124.0	122.9	124.0	127.9	133.7
140°	174.9	164.2	153.8	144.2	137.4	131.7	127.4	126.3	127.4	131.7	137.4
142.5°	176.3	166.1	156.4	147.3	140.9	135.1	131.1	130.4	131.1	135.1	140.9
145°	178.4	169.6	160.3	152.1	145.6	140.6	137.0	136.3	137.0	140.6	145.6
147.5°	179.8	171.7	163.5	156.3	150.8	146.1	143.0	142.6	143.0	146.1	150.8
150°	180.6	173.1	165.2	159.2	154.2	149.6	147.0	146.3	147.0	149.6	154.2
152.5°	181.2	174.5	167.2	161.8	157.0	153.0	150.8	150.4	150.8	153.0	157.0
155°	181.7	175.9	169.9	164.9	161.3	157.7	155.6	155.6	155.6	157.7	161.3
157.5°	182.0	177.1	172.0	168.1	165.0	162.0	160.3	160.4	160.3	162.0	165.0
160°	182.0	177.7	173.1	169.9	167.0	164.5	163.1	163.5	163.1	164.5	167.0
162.5°	181.8	178.3	174.2	171.6	169.4	167.1	165.7	166.0	165.7	167.1	169.4
165°	181.3	178.4	175.6	173.5	172.0	170.3	169.2	169.9	169.2	170.3	172.0
167.5°	180.5	178.4	176.1	174.7	173.7	172.8	172.1	172.5	172.1	172.8	173.7
170°	179.9	178.4	176.6	175.6	174.9	174.2	173.8	174.2	173.8	174.2	174.9
172.5°	179.4	178.1	176.6	176.1	175.7	175.0	174.7	175.3	174.7	175.0	175.7
175°	178.4	177.7	176.6	176.6	176.6	176.3	175.9	176.6	175.9	176.3	176.6
177.5°	177.6	177.3	176.7	176.7	177.0	176.7	176.7	177.3	176.7	176.7	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1256.0	1250.1	1245.9	1237.5	1231.6	1229.1	1224.6	1223.2	1227.9	1224.6	1224.1
5°	1218.6	1203.5	1191.3	1179.3	1166.2	1157.8	1145.2	1143.2	1139.9	1135.3	1134.2
7.5°	1173.9	1154.1	1138.5	1118.6	1101.3	1087.3	1071.6	1064.2	1060.1	1054.0	1045.8
10°	1143.7	1120.0	1099.0	1079.1	1057.6	1040.4	1024.6	1012.6	1004.7	997.3	994.2
12.5°	1113.9	1089.8	1063.0	1038.8	1014.9	995.4	978.1	970.2	961.5	952.9	945.5
15°	1067.6	1035.6	1006.2	978.5	958.1	937.1	920.3	908.8	895.6	891.9	877.8
17.5°	1018.5	987.1	952.8	923.5	899.8	876.8	858.3	845.2	835.4	821.8	815.3
20°	988.0	950.7	917.2	890.4	864.1	836.9	818.0	807.0	797.6	786.6	781.3
22.5°	955.2	918.8	884.4	853.0	826.4	799.6	786.2	774.7	764.0	753.9	746.9
25°	907.2	870.5	834.2	801.7	774.0	754.6	738.8	725.7	719.9	710.0	702.7
27.5°	859.7	820.6	783.0	750.7	728.9	709.7	696.8	686.4	676.0	667.3	661.0
30°	829.0	789.2	748.3	722.6	699.5	681.2	667.0	657.0	649.1	641.3	636.6
32.5°	798.4	757.3	721.0	693.2	671.4	655.6	641.0	631.5	623.2	614.5	608.9
35°	749.3	707.4	678.0	650.8	629.2	614.6	604.6	591.0	584.1	577.8	572.1
37.5°	703.7	664.7	632.9	609.0	590.4	575.7	562.9	555.5	547.1	541.5	536.6
40°	670.1	634.5	605.6	580.5	566.8	550.6	538.6	529.1	522.8	515.4	510.2
42.5°	640.0	606.8	578.8	556.1	539.2	525.4	513.8	504.3	496.3	491.1	486.8
45°	597.2	564.2	536.9	515.9	500.3	487.2	475.0	470.4	459.9	453.6	451.5
47.5°	553.1	523.5	497.3	477.9	461.8	449.4	438.1	428.4	422.6	416.5	413.1
50°	523.3	495.0	470.4	451.5	435.8	422.1	411.6	405.4	397.5	391.7	387.5
52.5°	493.5	467.4	442.7	424.6	411.0	397.4	385.7	379.3	371.9	368.2	365.3
55°	451.0	423.1	402.2	384.4	370.2	357.6	346.6	340.3	335.6	331.9	330.8
57.5°	402.7	380.7	361.2	345.2	330.4	318.6	308.9	303.0	298.8	298.2	295.1
60°	371.2	351.3	333.5	316.2	303.6	292.6	284.2	277.4	273.2	272.7	271.7
62.5°	339.8	320.7	304.2	288.9	277.6	267.0	259.0	251.4	248.8	246.2	244.0
65°	293.2	275.8	262.2	250.1	238.0	229.1	221.3	216.5	210.8	207.6	201.9
67.5°	247.3	233.9	220.8	210.6	201.2	192.7	186.1	179.2	175.2	172.7	168.5
70°	217.1	206.6	193.5	182.5	175.1	168.3	163.1	155.2	152.6	150.5	148.3
72.5°	188.5	179.4	168.3	159.5	152.1	145.6	139.6	135.9	133.3	131.2	130.0
75°	148.3	139.5	130.1	123.7	118.6	113.3	110.1	107.4	106.4	105.9	103.8
77.5°	109.0	104.2	96.6	91.7	88.2	86.1	83.3	81.9	81.8	79.5	78.8
80°	83.4	80.8	74.4	72.4	69.8	67.7	66.0	63.4	60.8	59.8	58.2
82.5°	62.0	59.4	56.9	53.5	51.3	50.0	48.5	47.5	47.9	46.4	45.6
85°	33.0	30.4	29.4	28.9	27.8	28.9	28.3	27.8	27.3	26.8	27.3
87.5°	11.1	11.2	10.8	11.8	10.6	11.2	11.3	10.9	11.0	11.1	10.8
90°	2.8	3.5	3.9	4.6	4.9	5.8	6.1	6.5	6.8	7.2	7.9
92.5°	18.9	29.3	48.8	81.4	116.9	115.0	93.1	63.2	45.8	34.5	29.3
95°	26.8	42.8	81.0	159.6	258.0	316.2	309.4	256.6	202.4	158.4	128.5
97.5°	33.0	44.5	69.8	127.3	230.5	337.7	391.5	382.1	344.2	301.3	259.6
100°	37.9	48.6	69.3	115.6	205.6	322.2	411.5	439.0	421.5	384.8	347.6
102.5°	43.0	53.4	71.8	110.8	186.7	295.2	399.5	458.1	468.9	451.3	426.2
105°	51.4	61.4	77.1	108.9	168.4	258.7	361.2	446.9	495.7	511.4	507.6
107.5°	60.8	69.8	84.9	112.1	160.8	233.7	322.0	406.6	471.8	512.1	530.8
110°	66.8	76.0	90.7	115.3	158.4	222.0	299.8	376.9	444.7	495.0	525.3



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	73.0	82.0	96.0	119.3	158.4	215.1	283.3	353.5	417.9	468.8	504.5
115°	82.4	91.4	104.6	125.2	159.6	207.7	265.2	324.1	379.4	428.3	467.2
117.5°	92.2	100.8	113.3	132.1	161.9	204.1	254.4	305.1	352.7	394.9	430.6
120°	98.2	107.0	119.6	136.7	164.2	202.4	248.4	294.8	337.6	376.9	408.3
122.5°	104.1	113.1	125.5	141.8	166.1	201.0	243.3	287.1	326.8	361.7	391.1
125°	112.4	121.7	133.5	148.9	169.6	199.1	236.3	275.9	312.3	343.4	369.0
127.5°	120.5	129.8	141.1	155.2	173.3	198.3	229.8	264.5	298.4	327.4	351.4
130°	125.6	134.9	145.9	159.6	175.6	197.7	225.6	257.3	288.7	316.6	339.8
132.5°	130.2	139.5	150.6	163.3	178.1	197.7	222.2	250.1	279.6	304.9	327.2
135°	136.0	145.6	156.6	168.4	181.7	197.7	218.0	241.0	265.5	288.4	308.7
137.5°	141.1	151.0	161.1	172.3	184.9	198.1	214.4	233.1	253.0	272.0	289.2
140°	144.2	153.8	164.2	174.9	186.3	198.4	212.7	228.7	245.5	262.0	276.9
142.5°	147.3	156.4	166.1	176.3	187.1	198.7	211.3	225.1	239.2	253.4	266.4
145°	152.1	160.3	169.6	178.4	188.0	198.4	209.1	220.3	231.3	242.4	252.0
147.5°	156.3	163.5	171.7	179.8	188.4	197.5	206.9	215.6	224.6	233.2	240.4
150°	159.2	165.2	173.1	180.6	188.4	196.6	205.2	213.1	221.0	227.7	234.1
152.5°	161.8	167.2	174.5	181.2	188.1	195.5	203.2	210.3	217.2	223.4	228.4
155°	164.9	169.9	175.9	181.7	187.3	193.5	199.9	205.9	211.7	216.6	220.6
157.5°	168.1	172.0	177.1	182.0	186.4	191.3	196.7	201.7	206.3	210.3	213.3
160°	169.9	173.1	177.7	182.0	185.6	189.9	194.2	198.8	202.4	205.9	208.4
162.5°	171.6	174.2	178.3	181.8	184.7	188.1	191.9	195.6	198.9	202.0	204.2
165°	173.5	175.6	178.4	181.3	183.5	185.6	188.4	191.3	193.8	195.9	197.7
167.5°	174.7	176.1	178.4	180.5	181.5	183.1	185.1	187.1	188.8	190.5	191.8
170°	175.6	176.6	178.4	179.9	180.6	181.7	183.1	184.9	185.9	187.0	187.7
172.5°	176.1	176.6	178.1	179.4	179.5	180.0	181.1	182.3	183.4	184.2	184.6
175°	176.6	176.6	177.7	178.4	178.1	178.1	178.4	179.6	179.6	180.3	180.3
177.5°	176.7	176.7	177.3	177.6	177.0	177.0	177.3	177.6	177.8	177.8	177.8
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1223.7	1219.1	1217.8	1219.5	1217.8	1219.1	1223.7	1224.1	1224.6	1227.9	1223.2
5°	1128.9	1123.8	1126.3	1125.3	1126.3	1123.8	1128.9	1134.2	1135.3	1139.9	1143.2
7.5°	1045.7	1039.2	1032.3	1034.5	1032.3	1039.2	1045.7	1045.8	1054.0	1060.1	1064.2
10°	987.3	982.2	979.0	981.6	979.0	982.2	987.3	994.2	997.3	1004.7	1012.6
12.5°	938.3	935.1	932.4	931.3	932.4	935.1	938.3	945.5	952.9	961.5	970.2
15°	871.5	865.3	862.6	855.8	862.6	865.3	871.5	877.8	891.9	895.6	908.8
17.5°	809.9	807.9	801.0	798.1	801.0	807.9	809.9	815.3	821.8	835.4	845.2
20°	773.5	771.3	764.6	768.7	764.6	771.3	773.5	781.3	786.6	797.6	807.0
22.5°	743.3	738.6	736.4	735.2	736.4	738.6	743.3	746.9	753.9	764.0	774.7
25°	700.5	693.8	691.2	688.0	691.2	693.8	700.5	702.7	710.0	719.9	725.7
27.5°	658.0	654.3	650.9	650.1	650.9	654.3	658.0	661.0	667.3	676.0	686.4
30°	630.3	626.6	624.0	624.0	624.0	626.6	630.3	636.6	641.3	649.1	657.0
32.5°	605.5	602.7	600.1	599.7	600.1	602.7	605.5	608.9	614.5	623.2	631.5
35°	569.5	565.3	564.2	561.1	564.2	565.3	569.5	572.1	577.8	584.1	591.0
37.5°	532.0	528.6	528.5	528.2	528.5	528.6	532.0	536.6	541.5	547.1	555.5
40°	508.2	505.5	504.9	501.3	504.9	505.5	508.2	510.2	515.4	522.8	529.1
42.5°	482.5	481.2	479.4	477.8	479.4	481.2	482.5	486.8	491.1	496.3	504.3
45°	447.8	444.1	444.1	441.5	444.1	444.1	447.8	451.5	453.6	459.9	470.4
47.5°	411.9	409.1	409.4	406.7	409.4	409.1	411.9	413.1	416.5	422.6	428.4
50°	388.0	386.5	386.0	384.9	386.0	386.5	388.0	387.5	391.7	397.5	405.4
52.5°	364.2	363.3	365.4	363.0	365.4	363.3	364.2	365.3	368.2	371.9	379.3
55°	331.9	330.3	333.5	330.3	333.5	330.3	331.9	330.8	331.9	335.6	340.3
57.5°	294.9	293.5	296.3	294.7	296.3	293.5	294.9	295.1	298.2	298.8	303.0
60°	270.5	267.4	269.0	269.5	269.0	267.4	270.5	271.7	272.7	273.2	277.4
62.5°	241.7	239.7	240.9	238.5	240.9	239.7	241.7	244.0	246.2	248.8	251.4
65°	200.9	199.2	197.1	196.1	197.1	199.2	200.9	201.9	207.6	210.8	216.5
67.5°	168.7	165.0	164.9	165.7	164.9	165.0	168.7	168.5	172.7	175.2	179.2
70°	145.2	145.2	144.7	144.7	144.7	145.2	145.2	148.3	150.5	152.6	155.2
72.5°	128.9	128.5	127.5	127.1	127.5	128.5	128.9	130.0	131.2	133.3	135.9
75°	103.8	104.3	103.3	102.8	103.3	104.3	103.8	103.8	105.9	106.4	107.4
77.5°	76.6	74.4	75.6	74.4	75.6	74.4	76.6	78.8	79.5	81.8	81.9
80°	58.2	57.7	59.3	57.7	59.3	57.7	58.2	58.2	59.8	60.8	63.4
82.5°	46.0	45.5	46.3	45.1	46.3	45.5	46.0	45.6	46.4	47.9	47.5
85°	27.8	27.3	26.8	27.3	26.8	27.3	27.8	27.3	26.8	27.3	27.8
87.5°	11.2	10.8	10.9	10.9	10.9	10.8	11.2	10.8	11.1	11.0	10.9
90°	7.9	7.9	8.2	8.2	8.2	7.9	7.9	7.9	7.2	6.8	6.5
92.5°	24.7	23.8	23.3	22.7	23.3	23.8	24.7	29.3	34.5	45.8	63.2
95°	103.1	92.4	89.6	83.9	89.6	92.4	103.1	128.5	158.4	202.4	256.6
97.5°	237.6	217.6	207.3	202.7	207.3	217.6	237.6	259.6	301.3	344.2	382.1
100°	323.0	297.3	284.1	278.4	284.1	297.3	323.0	347.6	384.8	421.5	439.0
102.5°	399.8	381.5	367.2	362.9	367.2	381.5	399.8	426.2	451.3	468.9	458.1
105°	496.0	484.3	477.2	472.9	477.2	484.3	496.0	507.6	511.4	495.7	446.9
107.5°	536.5	536.5	534.1	531.3	534.1	536.5	536.5	530.8	512.1	471.8	406.6
110°	541.4	548.2	550.7	550.7	550.7	548.2	541.4	525.3	495.0	444.7	376.9



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	528.0	539.7	545.8	548.5	545.8	539.7	528.0	504.5	468.8	417.9	353.5
115°	495.0	512.1	522.1	526.7	522.1	512.1	495.0	467.2	428.3	379.4	324.1
117.5°	458.4	476.2	486.0	488.9	486.0	476.2	458.4	430.6	394.9	352.7	305.1
120°	434.7	451.8	461.5	464.3	461.5	451.8	434.7	408.3	376.9	337.6	294.8
122.5°	414.8	430.4	440.1	442.6	440.1	430.4	414.8	391.1	361.7	326.8	287.1
125°	389.0	403.6	411.5	415.1	411.5	403.6	389.0	369.0	343.4	312.3	275.9
127.5°	369.6	382.5	389.9	391.5	389.9	382.5	369.6	351.4	327.4	298.4	264.5
130°	357.6	369.4	376.6	378.7	376.6	369.4	357.6	339.8	316.6	288.7	257.3
132.5°	345.1	356.8	363.3	365.8	363.3	356.8	345.1	327.2	304.9	279.6	250.1
135°	324.5	336.2	342.6	344.8	342.6	336.2	324.5	308.7	288.4	265.5	241.0
137.5°	303.3	314.0	319.9	322.2	319.9	314.0	303.3	289.2	272.0	253.0	233.1
140°	290.1	299.4	304.8	306.6	304.8	299.4	290.1	276.9	262.0	245.5	228.7
142.5°	277.6	285.5	290.5	292.1	290.5	285.5	277.6	266.4	253.4	239.2	225.1
145°	260.5	266.6	270.5	272.0	270.5	266.6	260.5	252.0	242.4	231.3	220.3
147.5°	247.2	252.1	254.3	255.0	254.3	252.1	247.2	240.4	233.2	224.6	215.6
150°	239.4	243.8	245.2	245.5	245.2	243.8	239.4	234.1	227.7	221.0	213.1
152.5°	232.9	236.3	237.7	238.1	237.7	236.3	232.9	228.4	223.4	217.2	210.3
155°	224.1	226.6	227.7	228.0	227.7	226.6	224.1	220.6	216.6	211.7	205.9
157.5°	216.1	218.1	219.1	219.0	219.1	218.1	216.1	213.3	210.3	206.3	201.7
160°	211.0	212.7	213.4	213.1	213.4	212.7	211.0	208.4	205.9	202.4	198.8
162.5°	206.1	207.5	207.7	207.6	207.7	207.5	206.1	204.2	202.0	198.9	195.6
165°	199.1	199.9	199.9	199.9	199.9	199.9	199.1	197.7	195.9	193.8	191.3
167.5°	192.5	193.1	192.8	192.7	192.8	193.1	192.5	191.8	190.5	188.8	187.1
170°	188.4	188.8	188.8	188.4	188.8	188.8	188.4	187.7	187.0	185.9	184.9
172.5°	184.7	185.4	184.8	184.4	184.8	185.4	184.7	184.6	184.2	183.4	182.3
175°	180.3	180.6	179.9	179.6	179.9	180.6	180.3	180.3	180.3	179.6	179.6
177.5°	177.6	177.8	177.0	177.0	177.0	177.8	177.6	177.8	177.8	177.8	177.6
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1224.6	1229.1	1231.6	1237.5	1245.9	1250.1	1256.0	1260.2	1266.1	1273.1	1279.1
5°	1145.2	1157.8	1166.2	1179.3	1191.3	1203.5	1218.6	1229.6	1244.4	1261.1	1274.2
7.5°	1071.6	1087.3	1101.3	1118.6	1138.5	1154.1	1173.9	1194.1	1217.1	1240.9	1263.3
10°	1024.6	1040.4	1057.6	1079.1	1099.0	1120.0	1143.7	1167.2	1196.1	1222.8	1253.2
12.5°	978.1	995.4	1014.9	1038.8	1063.0	1089.8	1113.9	1140.4	1171.3	1206.1	1238.6
15°	920.3	937.1	958.1	978.5	1006.2	1035.6	1067.6	1102.8	1137.4	1176.2	1216.6
17.5°	858.3	876.8	899.8	923.5	952.8	987.1	1018.5	1057.0	1095.9	1141.1	1188.6
20°	818.0	836.9	864.1	890.4	917.2	950.7	988.0	1027.2	1068.6	1116.4	1169.3
22.5°	786.2	799.6	826.4	853.0	884.4	918.8	955.2	996.2	1041.4	1090.8	1146.3
25°	738.8	754.6	774.0	801.7	834.2	870.5	907.2	950.7	1000.0	1050.4	1109.5
27.5°	696.8	709.7	728.9	750.7	783.0	820.6	859.7	905.0	955.6	1006.9	1069.1
30°	667.0	681.2	699.5	722.6	748.3	789.2	829.0	873.6	925.0	978.0	1041.9
32.5°	641.0	655.6	671.4	693.2	721.0	757.3	798.4	842.1	894.3	949.0	1011.3
35°	604.6	614.6	629.2	650.8	678.0	707.4	749.3	795.5	846.4	902.9	965.3
37.5°	562.9	575.7	590.4	609.0	632.9	664.7	703.7	750.3	797.6	851.8	908.8
40°	538.6	550.6	566.8	580.5	605.6	634.5	670.1	718.9	766.1	817.0	868.9
42.5°	513.8	525.4	539.2	556.1	578.8	606.8	640.0	685.4	735.9	783.9	827.4
45°	475.0	487.2	500.3	515.9	536.9	564.2	597.2	638.6	682.8	726.8	759.8
47.5°	438.1	449.4	461.8	477.9	497.3	523.5	553.1	589.7	632.5	669.9	693.6
50°	411.6	422.1	435.8	451.5	470.4	495.0	523.3	559.5	595.1	629.2	650.8
52.5°	385.7	397.4	411.0	424.6	442.7	467.4	493.5	524.7	558.7	586.4	604.2
55°	346.6	357.6	370.2	384.4	402.2	423.1	451.0	475.6	502.3	525.9	536.4
57.5°	308.9	318.6	330.4	345.2	361.2	380.7	402.7	426.5	445.2	462.0	473.8
60°	284.2	292.6	303.6	316.2	333.5	351.3	371.2	393.2	408.0	422.1	433.1
62.5°	259.0	267.0	277.6	288.9	304.2	320.7	339.8	357.6	371.9	381.4	394.2
65°	221.3	229.1	238.0	250.1	262.2	275.8	293.2	306.2	316.2	326.7	334.6
67.5°	186.1	192.7	201.2	210.6	220.8	233.9	247.3	258.2	265.0	271.4	280.7
70°	163.1	168.3	175.1	182.5	193.5	206.6	217.1	225.5	230.2	236.5	248.0
72.5°	139.6	145.6	152.1	159.5	168.3	179.4	188.5	196.9	200.0	205.0	212.4
75°	110.1	113.3	118.6	123.7	130.1	139.5	148.3	150.5	153.1	157.3	162.6
77.5°	83.3	86.1	88.2	91.7	96.6	104.2	109.0	112.1	112.7	114.3	119.5
80°	66.0	67.7	69.8	72.4	74.4	80.8	83.4	86.5	87.6	89.2	91.8
82.5°	48.5	50.0	51.3	53.5	56.9	59.4	62.0	65.1	65.3	66.4	67.1
85°	28.3	28.9	27.8	28.9	29.4	30.4	33.0	35.6	35.1	34.6	36.2
87.5°	11.3	11.2	10.6	11.8	10.8	11.2	11.1	11.3	12.0	12.7	13.5
90°	6.1	5.8	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	93.1	115.0	116.9	81.4	48.8	29.3	18.9	12.7	8.3	5.3	4.3
95°	309.4	316.2	258.0	159.6	81.0	42.8	26.8	18.9	14.9	12.1	11.8
97.5°	391.5	337.7	230.5	127.3	69.8	44.5	33.0	26.0	22.0	20.0	19.6
100°	411.5	322.2	205.6	115.6	69.3	48.6	37.9	31.0	27.2	25.7	24.9
102.5°	399.5	295.2	186.7	110.8	71.8	53.4	43.0	36.8	32.5	31.4	31.0
105°	361.2	258.7	168.4	108.9	77.1	61.4	51.4	45.6	42.1	40.3	40.3
107.5°	322.0	233.7	160.8	112.1	84.9	69.8	60.8	54.8	51.9	50.2	49.5
110°	299.8	222.0	158.4	115.3	90.7	76.0	66.8	61.4	58.2	56.8	56.0



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.3	215.1	158.4	119.3	96.0	82.0	73.0	67.7	64.4	63.3	62.6
115°	265.2	207.7	159.6	125.2	104.6	91.4	82.4	77.1	73.9	72.8	72.1
117.5°	254.4	204.1	161.9	132.1	113.3	100.8	92.2	86.0	82.9	81.7	80.7
120°	248.4	202.4	164.2	136.7	119.6	107.0	98.2	92.1	88.9	87.5	86.3
122.5°	243.3	201.0	166.1	141.8	125.5	113.1	104.1	97.6	94.3	93.1	92.4
125°	236.3	199.1	169.6	148.9	133.5	121.7	112.4	105.6	102.4	100.7	100.0
127.5°	229.8	198.3	173.3	155.2	141.1	129.8	120.5	113.3	109.2	106.9	105.8
130°	225.6	197.7	175.6	159.6	145.9	134.9	125.6	118.2	113.5	110.7	109.6
132.5°	222.2	197.7	178.1	163.3	150.6	139.5	130.2	122.4	117.2	113.8	112.4
135°	218.0	197.7	181.7	168.4	156.6	145.6	136.0	128.5	122.8	118.5	117.0
137.5°	214.4	198.1	184.9	172.3	161.1	151.0	141.1	133.7	127.9	124.0	122.9
140°	212.7	198.4	186.3	174.9	164.2	153.8	144.2	137.4	131.7	127.4	126.3
142.5°	211.3	198.7	187.1	176.3	166.1	156.4	147.3	140.9	135.1	131.1	130.4
145°	209.1	198.4	188.0	178.4	169.6	160.3	152.1	145.6	140.6	137.0	136.3
147.5°	206.9	197.5	188.4	179.8	171.7	163.5	156.3	150.8	146.1	143.0	142.6
150°	205.2	196.6	188.4	180.6	173.1	165.2	159.2	154.2	149.6	147.0	146.3
152.5°	203.2	195.5	188.1	181.2	174.5	167.2	161.8	157.0	153.0	150.8	150.4
155°	199.9	193.5	187.3	181.7	175.9	169.9	164.9	161.3	157.7	155.6	155.6
157.5°	196.7	191.3	186.4	182.0	177.1	172.0	168.1	165.0	162.0	160.3	160.4
160°	194.2	189.9	185.6	182.0	177.7	173.1	169.9	167.0	164.5	163.1	163.5
162.5°	191.9	188.1	184.7	181.8	178.3	174.2	171.6	169.4	167.1	165.7	166.0
165°	188.4	185.6	183.5	181.3	178.4	175.6	173.5	172.0	170.3	169.2	169.9
167.5°	185.1	183.1	181.5	180.5	178.4	176.1	174.7	173.7	172.8	172.1	172.5
170°	183.1	181.7	180.6	179.9	178.4	176.6	175.6	174.9	174.2	173.8	174.2
172.5°	181.1	180.0	179.5	179.4	178.1	176.6	176.1	175.7	175.0	174.7	175.3
175°	178.4	178.1	178.1	178.4	177.7	176.6	176.6	176.6	176.3	175.9	176.6
177.5°	177.3	177.0	177.0	177.6	177.3	176.7	176.7	177.0	176.7	176.7	177.3
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1283.6	1287.5	1292.9	1299.2	1304.2	1309.7	1312.6	1312.6	1315.1	1320.6	1327.7
5°	1287.4	1301.0	1314.0	1330.9	1343.9	1359.2	1370.7	1381.7	1391.7	1404.2	1417.3
7.5°	1286.3	1308.9	1332.5	1359.0	1388.2	1411.3	1435.1	1453.8	1472.2	1496.3	1515.3
10°	1282.1	1311.4	1343.4	1377.0	1413.7	1445.7	1474.5	1500.8	1525.9	1552.2	1575.7
12.5°	1274.6	1311.9	1351.0	1391.3	1437.6	1474.2	1511.5	1539.3	1568.7	1597.4	1626.5
15°	1263.2	1307.3	1354.4	1410.6	1467.2	1508.1	1544.8	1580.9	1608.2	1640.7	1668.6
17.5°	1239.8	1296.6	1355.9	1417.2	1471.7	1519.2	1557.7	1592.1	1621.1	1656.9	1694.7
20°	1226.0	1287.4	1349.2	1414.7	1466.6	1515.4	1552.7	1588.3	1624.5	1671.1	1717.3
22.5°	1206.7	1272.2	1337.9	1400.1	1454.9	1502.0	1540.4	1584.2	1631.6	1684.6	1740.4
25°	1176.2	1243.9	1308.8	1368.1	1421.6	1469.9	1522.3	1580.9	1638.7	1708.4	1788.7
27.5°	1137.5	1202.6	1260.7	1323.3	1376.4	1437.8	1503.3	1566.9	1650.1	1746.1	1846.2
30°	1108.5	1170.4	1225.5	1284.8	1345.0	1412.7	1486.1	1561.0	1660.1	1772.9	1892.0
32.5°	1075.0	1130.9	1185.6	1242.7	1312.3	1386.6	1464.7	1556.4	1674.9	1803.1	1926.3
35°	1016.7	1067.1	1120.0	1183.5	1257.5	1338.2	1437.8	1549.5	1692.6	1830.6	1941.3
37.5°	955.7	995.4	1048.6	1115.6	1196.1	1289.5	1402.6	1538.3	1685.4	1809.1	1856.1
40°	908.8	945.9	1002.1	1072.4	1152.1	1254.3	1381.2	1520.7	1668.6	1754.5	1750.9
42.5°	862.1	899.8	953.8	1024.5	1107.6	1222.0	1352.7	1497.6	1622.4	1655.2	1586.9
45°	790.7	825.9	878.9	950.2	1039.4	1159.4	1296.8	1435.7	1515.4	1462.5	1327.2
47.5°	718.0	752.0	801.2	871.1	968.4	1094.1	1224.0	1338.0	1349.2	1235.5	1073.2
50°	670.1	702.2	748.8	823.2	917.7	1040.4	1165.7	1255.4	1227.6	1088.6	921.3
52.5°	623.6	654.3	698.0	768.3	864.7	985.0	1096.9	1167.2	1103.0	955.2	804.7
55°	554.8	584.1	628.2	692.7	780.2	890.4	988.5	1014.1	919.8	770.8	649.1
57.5°	489.5	511.0	554.5	611.5	695.9	793.0	863.3	858.7	754.6	620.5	533.2
60°	446.3	465.6	507.1	559.5	639.7	726.8	776.1	755.1	649.6	539.1	455.1
62.5°	406.0	424.1	458.8	507.1	575.9	651.7	687.5	658.6	559.1	461.9	395.2
65°	345.1	358.1	386.0	430.5	484.5	536.9	569.0	526.4	438.4	365.0	314.6
67.5°	288.1	299.4	324.2	356.2	393.3	429.6	442.5	402.7	334.3	284.8	249.3
70°	251.2	261.7	278.4	308.3	333.0	358.7	365.0	329.3	272.2	234.4	212.4
72.5°	215.9	225.6	240.2	261.4	278.4	293.3	296.2	263.1	219.2	193.3	176.3
75°	164.6	173.1	182.5	190.4	201.4	204.0	202.9	177.2	153.6	136.3	126.9
77.5°	121.0	124.5	130.3	133.4	133.9	133.7	128.4	112.1	100.0	92.8	89.0
80°	93.3	95.9	97.6	98.6	99.1	93.8	88.1	78.2	73.9	69.8	65.0
82.5°	67.8	69.6	71.1	71.3	68.5	64.1	58.8	53.8	50.9	48.8	47.0
85°	36.7	37.3	36.7	34.1	30.4	28.9	27.8	26.8	26.3	25.7	25.7
87.5°	13.1	12.0	10.1	10.6	10.8	10.4	10.6	10.2	10.0	10.0	10.1
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.8	6.1	6.5
92.5°	5.3	8.3	12.7	18.9	29.3	48.8	81.4	116.9	115.0	93.1	63.2
95°	12.1	14.9	18.9	26.8	42.8	81.0	159.6	258.0	316.2	309.4	256.6
97.5°	20.0	22.0	26.0	33.0	44.5	69.8	127.3	230.5	337.7	391.5	382.1
100°	25.7	27.2	31.0	37.9	48.6	69.3	115.6	205.6	322.2	411.5	439.0
102.5°	31.4	32.5	36.8	43.0	53.4	71.8	110.8	186.7	295.2	399.5	458.1
105°	40.3	42.1	45.6	51.4	61.4	77.1	108.9	168.4	258.7	361.2	446.9
107.5°	50.2	51.9	54.8	60.8	69.8	84.9	112.1	160.8	233.7	322.0	406.6
110°	56.8	58.2	61.4	66.8	76.0	90.7	115.3	158.4	222.0	299.8	376.9





TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	63.3	64.4	67.7	73.0	82.0	96.0	119.3	158.4	215.1	283.3	353.5
115°	72.8	73.9	77.1	82.4	91.4	104.6	125.2	159.6	207.7	265.2	324.1
117.5°	81.7	82.9	86.0	92.2	100.8	113.3	132.1	161.9	204.1	254.4	305.1
120°	87.5	88.9	92.1	98.2	107.0	119.6	136.7	164.2	202.4	248.4	294.8
122.5°	93.1	94.3	97.6	104.1	113.1	125.5	141.8	166.1	201.0	243.3	287.1
125°	100.7	102.4	105.6	112.4	121.7	133.5	148.9	169.6	199.1	236.3	275.9
127.5°	106.9	109.2	113.3	120.5	129.8	141.1	155.2	173.3	198.3	229.8	264.5
130°	110.7	113.5	118.2	125.6	134.9	145.9	159.6	175.6	197.7	225.6	257.3
132.5°	113.8	117.2	122.4	130.2	139.5	150.6	163.3	178.1	197.7	222.2	250.1
135°	118.5	122.8	128.5	136.0	145.6	156.6	168.4	181.7	197.7	218.0	241.0
137.5°	124.0	127.9	133.7	141.1	151.0	161.1	172.3	184.9	198.1	214.4	233.1
140°	127.4	131.7	137.4	144.2	153.8	164.2	174.9	186.3	198.4	212.7	228.7
142.5°	131.1	135.1	140.9	147.3	156.4	166.1	176.3	187.1	198.7	211.3	225.1
145°	137.0	140.6	145.6	152.1	160.3	169.6	178.4	188.0	198.4	209.1	220.3
147.5°	143.0	146.1	150.8	156.3	163.5	171.7	179.8	188.4	197.5	206.9	215.6
150°	147.0	149.6	154.2	159.2	165.2	173.1	180.6	188.4	196.6	205.2	213.1
152.5°	150.8	153.0	157.0	161.8	167.2	174.5	181.2	188.1	195.5	203.2	210.3
155°	155.6	157.7	161.3	164.9	169.9	175.9	181.7	187.3	193.5	199.9	205.9
157.5°	160.3	162.0	165.0	168.1	172.0	177.1	182.0	186.4	191.3	196.7	201.7
160°	163.1	164.5	167.0	169.9	173.1	177.7	182.0	185.6	189.9	194.2	198.8
162.5°	165.7	167.1	169.4	171.6	174.2	178.3	181.8	184.7	188.1	191.9	195.6
165°	169.2	170.3	172.0	173.5	175.6	178.4	181.3	183.5	185.6	188.4	191.3
167.5°	172.1	172.8	173.7	174.7	176.1	178.4	180.5	181.5	183.1	185.1	187.1
170°	173.8	174.2	174.9	175.6	176.6	178.4	179.9	180.6	181.7	183.1	184.9
172.5°	174.7	175.0	175.7	176.1	176.6	178.1	179.4	179.5	180.0	181.1	182.3
175°	175.9	176.3	176.6	176.6	176.6	177.7	178.4	178.1	178.1	178.4	179.6
177.5°	176.7	176.7	177.0	176.7	176.7	177.3	177.6	177.0	177.0	177.3	177.6
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0	177.0



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4	1277.4
2.5°	1333.1	1333.1	1340.3	1339.9	1344.5	1342.8	1343.6
5°	1433.1	1442.0	1449.9	1455.1	1463.0	1465.1	1464.0
7.5°	1536.7	1556.5	1566.2	1579.4	1581.9	1588.7	1588.0
10°	1600.9	1620.3	1635.0	1646.5	1652.3	1659.6	1660.1
12.5°	1651.2	1667.7	1680.7	1691.4	1698.4	1700.7	1702.1
15°	1690.6	1708.9	1724.1	1739.3	1748.3	1755.0	1758.8
17.5°	1730.2	1758.6	1785.3	1806.0	1818.5	1828.9	1828.8
20°	1760.8	1793.3	1826.9	1850.5	1874.6	1885.1	1886.7
22.5°	1793.5	1843.3	1886.5	1923.1	1954.8	1965.7	1969.7
25°	1861.5	1926.5	1993.2	2044.6	2081.2	2102.7	2105.9
27.5°	1943.6	2031.6	2101.7	2149.1	2179.6	2195.5	2199.0
30°	2001.6	2082.8	2145.8	2181.4	2195.5	2197.7	2189.8
32.5°	2027.5	2088.3	2113.4	2111.3	2083.6	2065.1	2058.0
35°	1995.8	1983.2	1921.8	1848.5	1792.3	1756.7	1747.2
37.5°	1816.2	1707.7	1594.8	1483.9	1424.8	1394.8	1343.2
40°	1639.2	1484.5	1367.1	1273.7	1207.1	1153.6	1141.0
42.5°	1439.5	1279.8	1162.4	1082.4	1029.3	992.5	976.5
45°	1156.8	1019.4	922.4	861.0	820.1	793.3	781.3
47.5°	925.2	818.9	748.2	702.8	671.7	648.3	641.9
50°	798.1	713.2	653.4	615.1	591.5	573.7	566.3
52.5°	693.2	624.6	578.7	547.1	524.8	513.7	507.6
55°	572.1	512.8	479.8	454.6	442.0	433.1	428.9
57.5°	467.9	425.1	400.9	383.5	371.9	366.2	364.2
60°	409.5	376.0	354.0	340.3	332.4	325.1	323.1
62.5°	357.9	331.5	314.5	302.6	294.7	291.5	290.3
65°	288.4	271.1	258.5	251.2	244.9	243.9	243.3
67.5°	229.2	219.0	212.5	204.8	202.6	198.9	198.2
70°	196.1	189.2	181.5	178.8	176.2	172.5	173.1
72.5°	166.3	159.6	154.2	150.7	149.8	148.1	149.6
75°	121.7	119.6	117.4	114.8	113.8	113.8	113.3
77.5°	86.8	85.0	82.7	81.2	80.9	78.7	79.5
80°	62.9	60.3	59.3	59.8	58.2	57.7	57.7
82.5°	46.6	45.6	44.5	44.6	44.3	43.8	44.2
85°	25.7	25.1	25.1	24.6	24.6	24.1	24.1
87.5°	10.6	11.1	10.4	10.0	10.0	10.4	10.9
90°	6.8	7.2	7.9	7.9	7.9	8.2	8.2
92.5°	45.8	34.5	29.3	24.7	23.8	23.3	22.7
95°	202.4	158.4	128.5	103.1	92.4	89.6	83.9
97.5°	344.2	301.3	259.6	237.6	217.6	207.3	202.7
100°	421.5	384.8	347.6	323.0	297.3	284.1	278.4
102.5°	468.9	451.3	426.2	399.8	381.5	367.2	362.9
105°	495.7	511.4	507.6	496.0	484.3	477.2	472.9
107.5°	471.8	512.1	530.8	536.5	536.5	534.1	531.3
110°	444.7	495.0	525.3	541.4	548.2	550.7	550.7



TEST NUMBER: P333552-840

CATALOG NUMBER: S125RDIP-S850D365U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	417.9	468.8	504.5	528.0	539.7	545.8	548.5
115°	379.4	428.3	467.2	495.0	512.1	522.1	526.7
117.5°	352.7	394.9	430.6	458.4	476.2	486.0	488.9
120°	337.6	376.9	408.3	434.7	451.8	461.5	464.3
122.5°	326.8	361.7	391.1	414.8	430.4	440.1	442.6
125°	312.3	343.4	369.0	389.0	403.6	411.5	415.1
127.5°	298.4	327.4	351.4	369.6	382.5	389.9	391.5
130°	288.7	316.6	339.8	357.6	369.4	376.6	378.7
132.5°	279.6	304.9	327.2	345.1	356.8	363.3	365.8
135°	265.5	288.4	308.7	324.5	336.2	342.6	344.8
137.5°	253.0	272.0	289.2	303.3	314.0	319.9	322.2
140°	245.5	262.0	276.9	290.1	299.4	304.8	306.6
142.5°	239.2	253.4	266.4	277.6	285.5	290.5	292.1
145°	231.3	242.4	252.0	260.5	266.6	270.5	272.0
147.5°	224.6	233.2	240.4	247.2	252.1	254.3	255.0
150°	221.0	227.7	234.1	239.4	243.8	245.2	245.5
152.5°	217.2	223.4	228.4	232.9	236.3	237.7	238.1
155°	211.7	216.6	220.6	224.1	226.6	227.7	228.0
157.5°	206.3	210.3	213.3	216.1	218.1	219.1	219.0
160°	202.4	205.9	208.4	211.0	212.7	213.4	213.1
162.5°	198.9	202.0	204.2	206.1	207.5	207.7	207.6
165°	193.8	195.9	197.7	199.1	199.9	199.9	199.9
167.5°	188.8	190.5	191.8	192.5	193.1	192.8	192.7
170°	185.9	187.0	187.7	188.4	188.8	188.8	188.4
172.5°	183.4	184.2	184.6	184.7	185.4	184.8	184.4
175°	179.6	180.3	180.3	180.3	180.6	179.9	179.6
177.5°	177.8	177.8	177.8	177.6	177.8	177.0	177.0
180°	177.0	177.0	177.0	177.0	177.0	177.0	177.0

(END OF REPORT)