

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333266-940

Luminaire Tested: **S125DIP-S1090D590U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333266-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D590U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5784.9 lumens  
Efficiency: N/A  
Efficacy: 118.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333266-940

CATALOG NUMBER: S125DIP-S1090D590U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333266-940

CATALOG NUMBER: S125DIP-S1090D590U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	62	57
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	58	63	58	53	57	52	49	50	47	44	41
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38	35
5	71	59	51	44	67	56	48	43	51	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29	27
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	28	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9827	9827	9827
5°	9849	9756	9818
10°	9789	9686	9742
15°	9682	9570	9610
20°	9531	9407	9423
25°	9368	9213	9204
30°	9165	9004	8959
35°	8949	8779	8656
40°	8728	8535	8413
45°	8488	8312	8147
50°	8225	8043	7801
55°	7970	7739	7523
60°	7665	7432	7167
65°	7303	7065	6825
70°	6956	6637	6411
75°	6338	6128	5916
80°	5642	5553	5415
85°	4905	4994	4728



TEST NUMBER: P333266-940

CATALOG NUMBER: S125DIP-S1090D590U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.5	2.5
10°-20°	405.3	7.0
20°-30°	598.4	10.3
30°-40°	698.2	12.1
40°-50°	701.3	12.1
50°-60°	615.6	10.6
60°-70°	458.7	7.9
70°-80°	262.3	4.5
80°-90°	77.7	1.3
90°-100°	43.8	0.8
100°-110°	129.3	2.2
110°-120°	219.0	3.8
120°-130°	288.2	5.0
130°-140°	322.9	5.6
140°-150°	316.5	5.5
150°-160°	265.8	4.6
160°-170°	176.7	3.1
170°-180°	61.8	1.1
0°-30°	1147.1	19.8
0°-40°	1845.3	31.9
0°-60°	3162.2	54.7
0°-90°	3960.8	68.5
90°-120°	392.0	6.8
90°-150°	1319.7	22.8
90°-180°	1824.0	31.5
0°-180°	5784.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1522	1522	1522	1522	1522	
5°	1519	1516	1505	1515	1514	144
15°	1448	1444	1431	1437	1437	408
25°	1315	1308	1293	1295	1292	605
35°	1135	1130	1114	1107	1098	710
45°	929	924	910	896	892	716
55°	708	703	687	677	668	632
65°	478	475	462	452	447	474
75°	254	251	246	242	237	271
85°	66	67	67	66	64	74
90°	0	5	8	11	12	5
95°	33	34	39	43	44	35
105°	116	119	122	125	126	124
115°	219	221	222	222	221	217
125°	320	323	324	322	322	286
135°	416	419	420	420	418	321
145°	504	506	508	508	506	315
155°	577	577	577	579	577	266
165°	627	626	627	628	626	177
175°	652	650	650	653	650	62
180°	654	654	654	654	654	



TEST NUMBER: P333266-940

CATALOG NUMBER: S125DIP-S1090D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1525.4	1524.8	1524.1	1523.5	1522.9	1521.4	1519.3	1517.2	1515.0	1512.9	1515.0
5°	1519.2	1518.7	1518.1	1517.6	1517.1	1515.5	1512.8	1510.1	1507.4	1504.8	1507.2
7.5°	1505.2	1504.7	1504.1	1503.6	1503.1	1501.3	1498.3	1495.4	1492.5	1489.5	1491.9
10°	1492.7	1492.2	1491.7	1491.1	1490.6	1488.8	1485.9	1482.9	1480.0	1477.0	1479.2
12.5°	1477.3	1476.3	1475.3	1474.4	1473.5	1471.6	1468.8	1466.2	1463.4	1460.6	1462.4
15°	1448.1	1447.3	1446.5	1445.7	1444.9	1443.1	1440.1	1437.2	1434.2	1431.3	1432.6
17.5°	1414.7	1413.5	1412.3	1411.1	1410.0	1407.8	1404.8	1401.8	1398.7	1395.6	1397.3
20°	1386.8	1386.3	1385.7	1385.2	1384.6	1382.6	1379.1	1375.6	1372.2	1368.7	1370.6
22.5°	1358.8	1357.9	1356.9	1355.9	1355.0	1352.8	1349.6	1346.3	1343.1	1339.8	1341.0
25°	1314.6	1313.2	1311.9	1310.5	1309.2	1306.8	1303.3	1299.8	1296.4	1292.9	1293.4
27.5°	1262.8	1261.9	1261.1	1260.3	1259.5	1257.4	1253.7	1250.2	1246.6	1243.0	1243.1
30°	1229.0	1228.2	1227.4	1226.6	1225.8	1223.4	1219.4	1215.4	1211.4	1207.4	1206.8
32.5°	1192.5	1191.2	1190.0	1188.7	1187.6	1185.2	1181.5	1177.9	1174.4	1170.8	1169.8
35°	1135.1	1134.1	1133.0	1131.9	1130.9	1128.5	1124.7	1121.0	1117.2	1113.5	1112.1
37.5°	1075.7	1074.3	1073.0	1071.7	1070.3	1067.9	1064.3	1060.9	1057.3	1053.8	1051.8
40°	1035.3	1033.9	1032.6	1031.3	1029.9	1027.3	1023.6	1019.8	1016.1	1012.4	1010.0
42.5°	991.9	990.8	989.7	988.6	987.4	985.0	981.2	977.5	973.7	970.0	967.8
45°	929.3	928.3	927.2	926.1	925.1	922.9	919.7	916.5	913.3	910.1	906.9
47.5°	861.9	861.9	862.0	862.1	862.1	860.2	856.4	852.5	848.6	844.8	841.5
50°	818.6	817.8	817.0	816.2	815.4	813.3	810.1	806.9	803.7	800.5	797.0
52.5°	774.3	773.6	773.1	772.5	772.0	769.9	766.5	763.0	759.6	756.2	753.1
55°	707.8	707.0	706.2	705.4	704.6	702.3	698.6	694.8	691.1	687.3	684.9
57.5°	637.8	637.3	636.9	636.5	636.1	634.3	631.1	627.9	624.8	621.6	618.5
60°	593.4	592.4	591.3	590.2	589.2	587.2	584.2	581.3	578.4	575.4	572.7
62.5°	547.2	546.4	545.5	544.7	543.9	542.2	539.6	537.1	534.6	532.1	529.1
65°	477.9	477.3	476.8	476.3	475.7	474.0	471.1	468.1	465.2	462.3	459.9
67.5°	410.7	409.6	408.5	407.3	406.3	404.6	402.3	400.2	398.0	395.8	393.8
70°	368.4	367.0	365.7	364.4	363.0	361.1	358.7	356.3	353.9	351.5	349.9
72.5°	322.2	321.2	320.3	319.4	318.5	317.3	315.8	314.1	312.6	311.0	309.2
75°	254.0	253.4	252.9	252.4	251.8	250.9	249.6	248.3	246.9	245.6	244.8
77.5°	191.2	190.9	190.7	190.6	190.3	189.8	189.0	188.3	187.6	186.8	186.4
80°	151.7	151.7	151.7	151.7	151.7	151.4	150.9	150.3	149.8	149.3	149.0
82.5°	117.0	116.5	116.2	115.7	115.3	115.0	114.9	114.9	114.7	114.6	114.1
85°	66.2	66.4	66.7	67.0	67.2	67.4	67.4	67.4	67.4	67.4	67.1
87.5°	26.1	26.3	26.5	26.7	26.8	26.9	26.8	26.8	26.8	26.7	26.8
90°	0.5	1.4	2.3	3.2	4.1	5.0	5.8	6.6	7.3	8.1	8.7
92.5°	12.3	12.9	13.6	14.2	14.8	15.6	16.6	17.6	18.5	19.5	20.2
95°	33.1	33.3	33.5	33.7	34.0	34.7	35.8	36.9	38.1	39.1	39.9
97.5°	54.9	55.0	55.1	55.2	55.3	56.1	57.7	59.2	60.8	62.3	63.1
100°	71.2	71.2	71.2	71.2	71.2	72.0	73.4	74.9	76.3	77.8	78.8
102.5°	88.7	89.2	89.6	90.1	90.5	91.1	91.8	92.6	93.4	94.1	95.2
105°	116.0	116.5	117.1	117.7	118.2	118.9	119.6	120.2	120.9	121.5	122.3
107.5°	146.1	146.7	147.2	147.8	148.4	148.9	149.5	149.9	150.4	151.0	151.3
110°	166.8	167.4	168.0	168.5	169.2	169.6	169.9	170.2	170.6	170.9	171.3



TEST NUMBER: P333266-940

CATALOG NUMBER: S125DIP-S1090D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.0	188.3	188.6	188.9	189.2	189.6	190.0	190.4	190.8	191.3	191.5
115°	219.3	219.7	220.2	220.6	221.1	221.4	221.6	221.9	222.0	222.3	222.2
117.5°	250.6	250.7	251.0	251.2	251.4	251.6	251.8	252.0	252.2	252.4	252.5
120°	270.1	270.7	271.3	271.8	272.4	272.7	272.9	273.0	273.0	273.1	273.1
122.5°	291.3	291.5	291.7	291.9	292.1	292.3	292.7	292.9	293.2	293.6	293.5
125°	319.9	320.7	321.3	322.0	322.7	323.1	323.2	323.3	323.4	323.5	323.3
127.5°	350.5	350.9	351.2	351.6	352.0	352.3	352.4	352.6	352.7	352.8	352.8
130°	368.8	369.3	370.0	370.5	371.0	371.5	371.7	371.9	372.1	372.4	372.3
132.5°	387.1	388.1	389.0	389.9	390.8	391.3	391.2	391.2	391.1	391.1	391.0
135°	416.1	416.8	417.5	418.1	418.8	419.2	419.4	419.5	419.5	419.6	419.6
137.5°	443.4	444.1	444.7	445.3	446.0	446.5	446.7	446.9	447.2	447.5	447.5
140°	460.8	461.5	462.0	462.5	463.2	463.6	464.0	464.3	464.6	464.9	465.2
142.5°	478.4	478.8	479.3	479.8	480.3	480.7	481.2	481.6	482.1	482.4	482.6
145°	504.1	504.5	505.1	505.5	506.0	506.3	506.7	507.0	507.4	507.7	507.7
147.5°	527.9	528.2	528.4	528.7	529.0	529.1	529.4	529.8	530.0	530.3	530.6
150°	543.8	543.7	543.6	543.5	543.3	543.5	543.9	544.4	544.8	545.3	545.3
152.5°	556.8	557.0	557.1	557.3	557.4	557.6	557.8	557.9	558.1	558.4	558.7
155°	576.8	576.8	576.8	576.8	576.8	576.9	577.0	577.1	577.3	577.4	577.8
157.5°	594.8	594.5	594.2	594.1	593.8	593.7	593.8	594.0	594.1	594.1	594.6
160°	605.4	605.0	604.7	604.3	604.0	603.9	604.0	604.1	604.2	604.3	604.8
162.5°	614.7	614.5	614.2	613.9	613.7	613.6	613.6	613.7	613.7	613.7	614.2
165°	627.2	627.0	626.8	626.5	626.3	626.2	626.3	626.5	626.6	626.7	627.1
167.5°	637.8	637.4	636.9	636.4	636.0	635.8	635.8	635.8	635.8	635.8	636.4
170°	643.5	643.0	642.6	642.1	641.7	641.5	641.5	641.5	641.5	641.5	642.1
172.5°	647.6	647.1	646.7	646.2	645.8	645.5	645.5	645.5	645.5	645.5	646.2
175°	652.1	651.7	651.2	650.8	650.3	650.1	650.1	650.1	650.1	650.1	650.8
177.5°	654.5	654.2	653.8	653.4	653.0	652.8	652.7	652.6	652.6	652.5	653.0
180°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7



TEST NUMBER: P333266-940

CATALOG NUMBER: S125DIP-S1090D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
2.5°	1517.2	1519.3	1521.4	1522.4	1522.2	1522.0	1521.8	1521.6
5°	1509.6	1512.0	1514.4	1515.5	1515.2	1514.9	1514.7	1514.4
7.5°	1494.2	1496.6	1499.0	1500.0	1499.8	1499.5	1499.2	1499.0
10°	1481.3	1483.5	1485.6	1486.6	1486.3	1486.0	1485.8	1485.5
12.5°	1464.1	1465.8	1467.5	1468.4	1468.3	1468.2	1468.2	1468.1
15°	1434.0	1435.3	1436.6	1437.3	1437.3	1437.3	1437.3	1437.3
17.5°	1399.0	1400.6	1402.3	1402.5	1401.1	1399.8	1398.5	1397.1
20°	1372.4	1374.3	1376.2	1376.4	1375.1	1373.8	1372.4	1371.1
22.5°	1342.3	1343.5	1344.7	1344.9	1344.0	1343.1	1342.2	1341.2
25°	1294.0	1294.5	1295.0	1294.9	1294.1	1293.2	1292.4	1291.6
27.5°	1243.2	1243.3	1243.5	1243.1	1242.3	1241.5	1240.7	1239.9
30°	1206.3	1205.8	1205.2	1204.6	1203.8	1203.0	1202.2	1201.4
32.5°	1168.9	1167.9	1167.0	1165.7	1164.3	1162.9	1161.4	1159.9
35°	1110.8	1109.5	1108.1	1106.4	1104.3	1102.2	1100.0	1097.9
37.5°	1049.8	1047.8	1045.9	1044.3	1043.0	1041.8	1040.5	1039.4
40°	1007.5	1005.1	1002.7	1001.1	1000.3	999.5	998.7	997.9
42.5°	965.6	963.4	961.3	959.5	958.3	957.1	955.8	954.6
45°	903.7	900.4	897.2	895.2	894.4	893.6	892.8	892.0
47.5°	838.3	835.0	831.8	829.2	827.3	825.5	823.6	821.7
50°	793.5	790.1	786.6	783.9	782.0	780.2	778.3	776.4
52.5°	750.1	747.1	744.0	741.5	739.3	737.3	735.2	733.1
55°	682.5	680.1	677.7	675.6	673.7	671.8	669.9	668.1
57.5°	615.5	612.3	609.2	607.2	606.2	605.1	604.1	603.1
60°	570.1	567.4	564.7	562.4	560.5	558.7	556.8	554.9
62.5°	526.3	523.4	520.5	518.4	516.9	515.5	514.0	512.6
65°	457.4	455.0	452.6	450.8	449.8	448.7	447.6	446.6
67.5°	391.7	389.7	387.6	386.3	385.7	385.0	384.4	383.8
70°	348.3	346.7	345.1	343.8	342.7	341.6	340.5	339.5
72.5°	307.5	305.6	303.8	302.4	301.3	300.2	299.2	298.1
75°	244.0	243.2	242.4	241.4	240.3	239.2	238.2	237.1
77.5°	185.8	185.4	184.9	184.3	183.5	182.8	182.0	181.3
80°	148.7	148.5	148.2	147.8	147.2	146.7	146.2	145.6
82.5°	113.6	113.2	112.7	112.4	112.3	112.2	112.1	111.9
85°	66.9	66.6	66.3	65.9	65.4	64.8	64.3	63.8
87.5°	26.9	27.0	27.1	27.0	26.7	26.3	25.9	25.6
90°	9.3	9.8	10.4	10.9	11.2	11.5	11.9	12.2
92.5°	21.0	21.8	22.6	23.0	23.3	23.5	23.7	24.0
95°	40.8	41.6	42.4	42.8	43.1	43.3	43.5	43.8
97.5°	63.8	64.6	65.4	65.8	65.9	66.1	66.2	66.3
100°	79.9	80.9	81.9	82.5	82.8	83.0	83.2	83.5
102.5°	96.3	97.5	98.5	99.2	99.6	99.9	100.2	100.5
105°	123.0	123.6	124.3	124.8	125.1	125.5	125.8	126.2
107.5°	151.7	152.0	152.3	152.5	152.5	152.5	152.4	152.4
110°	171.6	171.9	172.3	172.4	172.3	172.2	172.0	171.9





TEST NUMBER: P333266-940

CATALOG NUMBER: S125DIP-S1090D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.6	191.7	191.9	191.9	191.7	191.5	191.3	191.1
115°	222.0	221.9	221.9	221.8	221.6	221.5	221.4	221.3
117.5°	252.6	252.7	252.8	252.6	252.2	251.7	251.3	250.7
120°	273.1	273.1	273.1	273.0	272.5	272.1	271.6	271.2
122.5°	293.4	293.3	293.2	292.9	292.6	292.2	291.9	291.5
125°	323.1	322.9	322.6	322.4	322.4	322.3	322.1	322.0
127.5°	352.6	352.5	352.4	352.2	352.0	351.8	351.5	351.3
130°	372.1	372.0	371.9	371.8	371.5	371.3	371.0	370.9
132.5°	390.8	390.7	390.7	390.4	390.1	389.8	389.5	389.1
135°	419.6	419.6	419.6	419.5	419.0	418.6	418.1	417.7
137.5°	447.7	447.8	448.0	447.8	447.2	446.7	446.1	445.5
140°	465.4	465.7	465.8	465.7	465.1	464.6	464.0	463.4
142.5°	482.7	482.9	483.0	482.8	482.2	481.6	481.1	480.5
145°	507.7	507.7	507.7	507.5	507.2	506.8	506.5	506.1
147.5°	530.8	531.1	531.4	531.1	530.3	529.6	528.8	528.1
150°	545.3	545.3	545.3	545.2	545.0	544.7	544.6	544.3
152.5°	558.9	559.2	559.5	559.4	558.9	558.6	558.1	557.8
155°	578.3	578.7	579.2	579.2	578.5	578.0	577.4	576.8
157.5°	595.0	595.5	595.9	595.8	595.0	594.3	593.6	592.8
160°	605.2	605.6	606.1	606.1	605.6	604.9	604.4	603.9
162.5°	614.7	615.3	615.9	615.8	615.2	614.5	613.9	613.1
165°	627.6	628.0	628.6	628.4	627.8	627.1	626.3	625.7
167.5°	637.1	637.8	638.5	638.5	637.8	637.0	636.3	635.7
170°	642.8	643.5	644.2	644.1	643.4	642.6	641.8	641.0
172.5°	646.9	647.6	648.3	648.3	647.6	646.8	646.1	645.4
175°	651.5	652.1	652.8	652.7	652.0	651.2	650.4	649.6
177.5°	653.5	654.1	654.6	654.6	654.0	653.4	652.6	652.0
180°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7

(END OF REPORT)