

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333311-940

Luminaire Tested: **S125DIP-S1270D590U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333311-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D590U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6398.3 lumens  
Efficiency: N/A  
Efficacy: 116.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333311-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333311-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	61	80	72	65	59	65	59	54	58	54	50	52	49	46	42
4	78	67	58	52	74	63	56	50	57	51	47	52	47	43	47	43	39	36
5	72	60	51	45	68	57	49	43	51	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	28
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11349	11349	11349
5°	11374	11267	11339
10°	11305	11187	11252
15°	11183	11053	11099
20°	11008	10864	10883
25°	10819	10641	10630
30°	10586	10399	10347
35°	10336	10139	9996
40°	10080	9857	9716
45°	9803	9600	9409
50°	9499	9289	9010
55°	9205	8939	8688
60°	8853	8584	8280
65°	8436	8159	7882
70°	8033	7666	7404
75°	7321	7079	6832
80°	6512	6412	6259
85°	5669	5765	5461



TEST NUMBER: P333311-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.7	2.6
10°-20°	468.1	7.3
20°-30°	691.1	10.8
30°-40°	806.4	12.6
40°-50°	809.9	12.7
50°-60°	710.9	11.1
60°-70°	529.7	8.3
70°-80°	302.9	4.7
80°-90°	89.6	1.4
90°-100°	43.8	0.7
100°-110°	129.3	2.0
110°-120°	219.0	3.4
120°-130°	288.2	4.5
130°-140°	322.9	5.0
140°-150°	316.5	4.9
150°-160°	265.8	4.2
160°-170°	176.7	2.8
170°-180°	61.8	1.0
0°-30°	1324.8	20.7
0°-40°	2131.2	33.3
0°-60°	3652.1	57.1
0°-90°	4574.3	71.5
90°-120°	392.0	6.1
90°-150°	1319.7	20.6
90°-180°	1824.0	28.5
0°-180°	6398.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1757	1757	1757	1757	1757	
5°	1754	1751	1738	1750	1749	166
15°	1672	1668	1653	1660	1660	471
25°	1518	1511	1493	1496	1492	698
35°	1311	1305	1286	1279	1268	820
45°	1073	1067	1051	1035	1030	827
55°	818	812	794	781	772	730
65°	552	548	534	522	516	548
75°	293	290	284	279	274	313
85°	76	78	78	76	74	85
90°	0	5	8	11	12	6
95°	33	34	39	43	44	35
105°	116	119	122	125	126	124
115°	219	221	222	222	221	217
125°	320	323	324	322	322	286
135°	416	419	420	420	418	321
145°	504	506	508	508	506	315
155°	577	577	577	579	577	266
165°	627	626	627	628	626	177
175°	652	650	650	653	650	62
180°	654	654	654	654	654	



TEST NUMBER: P333311-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1761.8	1761.0	1760.3	1759.5	1758.8	1757.2	1754.7	1752.2	1749.8	1747.3	1749.8
5°	1754.5	1753.9	1753.3	1752.7	1752.0	1750.2	1747.1	1744.0	1741.0	1737.9	1740.6
7.5°	1738.4	1737.8	1737.1	1736.5	1735.9	1733.9	1730.5	1727.2	1723.8	1720.4	1723.1
10°	1723.9	1723.3	1722.7	1722.1	1721.4	1719.5	1716.1	1712.7	1709.2	1705.8	1708.3
12.5°	1706.1	1705.0	1704.0	1702.8	1701.7	1699.6	1696.4	1693.3	1690.1	1686.9	1689.0
15°	1672.5	1671.6	1670.6	1669.7	1668.8	1666.6	1663.2	1659.8	1656.4	1653.1	1654.6
17.5°	1633.9	1632.5	1631.1	1629.8	1628.4	1625.9	1622.5	1618.9	1615.4	1611.9	1613.8
20°	1601.6	1601.0	1600.4	1599.7	1599.1	1596.8	1592.8	1588.8	1584.7	1580.7	1582.9
22.5°	1569.3	1568.3	1567.1	1566.0	1564.9	1562.5	1558.7	1555.0	1551.1	1547.4	1548.8
25°	1518.2	1516.6	1515.1	1513.6	1512.0	1509.2	1505.2	1501.2	1497.2	1493.2	1493.8
27.5°	1458.4	1457.5	1456.5	1455.6	1454.7	1452.2	1448.0	1443.9	1439.8	1435.6	1435.7
30°	1419.5	1418.5	1417.6	1416.7	1415.8	1413.0	1408.4	1403.7	1399.1	1394.5	1393.8
32.5°	1377.2	1375.8	1374.4	1373.0	1371.5	1368.8	1364.6	1360.5	1356.3	1352.2	1351.1
35°	1311.0	1309.8	1308.6	1307.3	1306.1	1303.3	1299.0	1294.7	1290.3	1286.0	1284.5
37.5°	1242.3	1240.8	1239.3	1237.7	1236.2	1233.3	1229.3	1225.2	1221.1	1217.1	1214.8
40°	1195.6	1194.1	1192.6	1191.0	1189.5	1186.5	1182.2	1177.9	1173.6	1169.2	1166.4
42.5°	1145.6	1144.3	1143.0	1141.7	1140.4	1137.6	1133.3	1128.9	1124.6	1120.3	1117.8
45°	1073.3	1072.1	1070.9	1069.6	1068.4	1065.9	1062.2	1058.5	1054.8	1051.1	1047.3
47.5°	995.4	995.5	995.6	995.6	995.7	993.5	989.1	984.6	980.2	975.7	972.0
50°	945.4	944.5	943.5	942.6	941.6	939.3	935.7	931.9	928.3	924.5	920.5
52.5°	894.2	893.6	892.9	892.2	891.5	889.2	885.2	881.3	877.4	873.3	869.9
55°	817.5	816.5	815.6	814.7	813.8	811.2	806.8	802.5	798.2	793.9	791.0
57.5°	736.6	736.1	735.6	735.1	734.6	732.5	728.9	725.2	721.6	717.9	714.3
60°	685.4	684.2	683.0	681.7	680.5	678.1	674.8	671.4	668.0	664.6	661.5
62.5°	632.0	631.1	630.1	629.0	628.0	626.2	623.2	620.3	617.4	614.5	611.2
65°	552.0	551.3	550.7	550.1	549.5	547.4	544.0	540.6	537.3	533.9	531.1
67.5°	474.4	473.1	471.8	470.5	469.2	467.3	464.8	462.2	459.7	457.1	454.8
70°	425.4	423.9	422.3	420.8	419.3	417.1	414.3	411.5	408.8	406.0	404.1
72.5°	372.0	371.0	370.0	368.9	367.8	366.4	364.6	362.8	361.1	359.3	357.1
75°	293.4	292.7	292.1	291.5	290.9	289.8	288.3	286.7	285.2	283.7	282.7
77.5°	220.8	220.5	220.3	220.1	219.8	219.3	218.4	217.5	216.6	215.8	215.3
80°	175.1	175.1	175.1	175.1	175.1	174.9	174.2	173.6	173.0	172.4	172.1
82.5°	135.1	134.6	134.1	133.7	133.1	132.9	132.7	132.6	132.5	132.3	131.8
85°	76.5	76.8	77.0	77.4	77.7	77.8	77.8	77.8	77.8	77.8	77.6
87.5°	30.1	30.3	30.5	30.7	30.9	30.9	30.9	30.8	30.7	30.6	30.7
90°	0.5	1.4	2.3	3.2	4.1	5.0	5.8	6.6	7.3	8.1	8.7
92.5°	12.3	12.9	13.6	14.2	14.8	15.6	16.6	17.6	18.5	19.5	20.2
95°	33.1	33.3	33.5	33.7	34.0	34.7	35.8	36.9	38.1	39.1	39.9
97.5°	54.9	55.0	55.1	55.2	55.3	56.1	57.7	59.2	60.8	62.3	63.1
100°	71.2	71.2	71.2	71.2	71.2	72.0	73.4	74.9	76.3	77.8	78.8
102.5°	88.7	89.2	89.6	90.1	90.5	91.1	91.8	92.6	93.4	94.1	95.2
105°	116.0	116.5	117.1	117.7	118.2	118.9	119.6	120.2	120.9	121.5	122.3
107.5°	146.1	146.7	147.2	147.8	148.4	148.9	149.5	149.9	150.4	151.0	151.3
110°	166.8	167.4	168.0	168.5	169.2	169.6	169.9	170.2	170.6	170.9	171.3



TEST NUMBER: P333311-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.0	188.3	188.6	188.9	189.2	189.6	190.0	190.4	190.8	191.3	191.5
115°	219.3	219.7	220.2	220.6	221.1	221.4	221.6	221.9	222.0	222.3	222.2
117.5°	250.6	250.7	251.0	251.2	251.4	251.6	251.8	252.0	252.2	252.4	252.5
120°	270.1	270.7	271.3	271.8	272.4	272.7	272.9	273.0	273.0	273.1	273.1
122.5°	291.3	291.5	291.7	291.9	292.1	292.3	292.7	292.9	293.2	293.6	293.5
125°	319.9	320.7	321.3	322.0	322.7	323.1	323.2	323.3	323.4	323.5	323.3
127.5°	350.5	350.9	351.2	351.6	352.0	352.3	352.4	352.6	352.7	352.8	352.8
130°	368.8	369.3	370.0	370.5	371.0	371.5	371.7	371.9	372.1	372.4	372.3
132.5°	387.1	388.1	389.0	389.9	390.8	391.3	391.2	391.2	391.1	391.1	391.0
135°	416.1	416.8	417.5	418.1	418.8	419.2	419.4	419.5	419.5	419.6	419.6
137.5°	443.4	444.1	444.7	445.3	446.0	446.5	446.7	446.9	447.2	447.5	447.5
140°	460.8	461.5	462.0	462.5	463.2	463.6	464.0	464.3	464.6	464.9	465.2
142.5°	478.4	478.8	479.3	479.8	480.3	480.7	481.2	481.6	482.1	482.4	482.6
145°	504.1	504.5	505.1	505.5	506.0	506.3	506.7	507.0	507.4	507.7	507.7
147.5°	527.9	528.2	528.4	528.7	529.0	529.1	529.4	529.8	530.0	530.3	530.6
150°	543.8	543.7	543.6	543.5	543.3	543.5	543.9	544.4	544.8	545.3	545.3
152.5°	556.8	557.0	557.1	557.3	557.4	557.6	557.8	557.9	558.1	558.4	558.7
155°	576.8	576.8	576.8	576.8	576.8	576.9	577.0	577.1	577.3	577.4	577.8
157.5°	594.8	594.5	594.2	594.1	593.8	593.7	593.8	594.0	594.1	594.1	594.6
160°	605.4	605.0	604.7	604.3	604.0	603.9	604.0	604.1	604.2	604.3	604.8
162.5°	614.7	614.5	614.2	613.9	613.7	613.6	613.6	613.7	613.7	613.7	614.2
165°	627.2	627.0	626.8	626.5	626.3	626.2	626.3	626.5	626.6	626.7	627.1
167.5°	637.8	637.4	636.9	636.4	636.0	635.8	635.8	635.8	635.8	635.8	636.4
170°	643.5	643.0	642.6	642.1	641.7	641.5	641.5	641.5	641.5	641.5	642.1
172.5°	647.6	647.1	646.7	646.2	645.8	645.5	645.5	645.5	645.5	645.5	646.2
175°	652.1	651.7	651.2	650.8	650.3	650.1	650.1	650.1	650.1	650.1	650.8
177.5°	654.5	654.2	653.8	653.4	653.0	652.8	652.7	652.6	652.6	652.5	653.0
180°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7



TEST NUMBER: P333311-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3	1757.3
2.5°	1752.2	1754.7	1757.2	1758.3	1758.1	1757.8	1757.6	1757.3
5°	1743.4	1746.2	1749.0	1750.2	1749.9	1749.6	1749.3	1749.0
7.5°	1725.7	1728.5	1731.2	1732.4	1732.1	1731.8	1731.5	1731.2
10°	1710.8	1713.3	1715.7	1716.8	1716.5	1716.2	1715.9	1715.7
12.5°	1691.0	1692.9	1694.9	1695.9	1695.8	1695.7	1695.7	1695.6
15°	1656.2	1657.7	1659.2	1660.0	1660.0	1660.0	1660.0	1660.0
17.5°	1615.7	1617.7	1619.5	1619.7	1618.2	1616.7	1615.1	1613.6
20°	1585.1	1587.2	1589.4	1589.7	1588.1	1586.6	1585.1	1583.5
22.5°	1550.2	1551.7	1553.1	1553.3	1552.2	1551.1	1550.1	1549.1
25°	1494.4	1495.0	1495.7	1495.5	1494.6	1493.6	1492.7	1491.7
27.5°	1435.8	1436.0	1436.1	1435.7	1434.8	1433.9	1432.9	1432.0
30°	1393.2	1392.6	1392.0	1391.2	1390.3	1389.4	1388.4	1387.5
32.5°	1350.0	1348.9	1347.7	1346.3	1344.7	1343.0	1341.3	1339.7
35°	1282.9	1281.4	1279.9	1277.8	1275.3	1272.9	1270.4	1267.9
37.5°	1212.5	1210.2	1207.9	1206.0	1204.6	1203.2	1201.8	1200.3
40°	1163.7	1160.9	1158.1	1156.3	1155.3	1154.4	1153.4	1152.5
42.5°	1115.3	1112.7	1110.2	1108.2	1106.8	1105.4	1103.9	1102.5
45°	1043.7	1039.9	1036.3	1033.9	1033.0	1032.1	1031.1	1030.2
47.5°	968.1	964.4	960.6	957.7	955.5	953.3	951.2	949.0
50°	916.5	912.5	908.5	905.4	903.2	901.1	898.9	896.7
52.5°	866.3	862.8	859.3	856.3	853.9	851.5	849.1	846.7
55°	788.3	785.5	782.7	780.2	778.1	776.0	773.7	771.6
57.5°	710.8	707.2	703.6	701.2	700.1	698.9	697.7	696.5
60°	658.4	655.3	652.2	649.6	647.4	645.2	643.1	641.0
62.5°	607.8	604.5	601.2	598.7	597.0	595.3	593.6	592.0
65°	528.3	525.5	522.7	520.8	519.5	518.3	517.0	515.8
67.5°	452.5	450.0	447.7	446.2	445.4	444.7	444.0	443.2
70°	402.3	400.4	398.5	397.0	395.7	394.5	393.3	392.1
72.5°	355.1	352.9	350.9	349.2	347.9	346.7	345.4	344.2
75°	281.8	280.8	279.9	278.8	277.6	276.3	275.1	273.8
77.5°	214.6	214.1	213.6	212.9	212.0	211.1	210.3	209.4
80°	171.7	171.5	171.1	170.7	170.0	169.4	168.8	168.3
82.5°	131.3	130.7	130.1	129.8	129.7	129.6	129.4	129.3
85°	77.2	77.0	76.6	76.2	75.5	74.9	74.3	73.7
87.5°	30.8	30.9	31.0	30.9	30.4	30.0	29.6	29.2
90°	9.3	9.8	10.4	10.9	11.2	11.5	11.9	12.2
92.5°	21.0	21.8	22.6	23.0	23.3	23.5	23.7	24.0
95°	40.8	41.6	42.4	42.8	43.1	43.3	43.5	43.8
97.5°	63.8	64.6	65.4	65.8	65.9	66.1	66.2	66.3
100°	79.9	80.9	81.9	82.5	82.8	83.0	83.2	83.5
102.5°	96.3	97.5	98.5	99.2	99.6	99.9	100.2	100.5
105°	123.0	123.6	124.3	124.8	125.1	125.5	125.8	126.2
107.5°	151.7	152.0	152.3	152.5	152.5	152.5	152.4	152.4
110°	171.6	171.9	172.3	172.4	172.3	172.2	172.0	171.9





TEST NUMBER: P333311-940

CATALOG NUMBER: S125DIP-S1270D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.6	191.7	191.9	191.9	191.7	191.5	191.3	191.1
115°	222.0	221.9	221.9	221.8	221.6	221.5	221.4	221.3
117.5°	252.6	252.7	252.8	252.6	252.2	251.7	251.3	250.7
120°	273.1	273.1	273.1	273.0	272.5	272.1	271.6	271.2
122.5°	293.4	293.3	293.2	292.9	292.6	292.2	291.9	291.5
125°	323.1	322.9	322.6	322.4	322.4	322.3	322.1	322.0
127.5°	352.6	352.5	352.4	352.2	352.0	351.8	351.5	351.3
130°	372.1	372.0	371.9	371.8	371.5	371.3	371.0	370.9
132.5°	390.8	390.7	390.7	390.4	390.1	389.8	389.5	389.1
135°	419.6	419.6	419.6	419.5	419.0	418.6	418.1	417.7
137.5°	447.7	447.8	448.0	447.8	447.2	446.7	446.1	445.5
140°	465.4	465.7	465.8	465.7	465.1	464.6	464.0	463.4
142.5°	482.7	482.9	483.0	482.8	482.2	481.6	481.1	480.5
145°	507.7	507.7	507.7	507.5	507.2	506.8	506.5	506.1
147.5°	530.8	531.1	531.4	531.1	530.3	529.6	528.8	528.1
150°	545.3	545.3	545.3	545.2	545.0	544.7	544.6	544.3
152.5°	558.9	559.2	559.5	559.4	558.9	558.6	558.1	557.8
155°	578.3	578.7	579.2	579.2	578.5	578.0	577.4	576.8
157.5°	595.0	595.5	595.9	595.8	595.0	594.3	593.6	592.8
160°	605.2	605.6	606.1	606.1	605.6	604.9	604.4	603.9
162.5°	614.7	615.3	615.9	615.8	615.2	614.5	613.9	613.1
165°	627.6	628.0	628.6	628.4	627.8	627.1	626.3	625.7
167.5°	637.1	637.8	638.5	638.5	637.8	637.0	636.3	635.7
170°	642.8	643.5	644.2	644.1	643.4	642.6	641.8	641.0
172.5°	646.9	647.6	648.3	648.3	647.6	646.8	646.1	645.4
175°	651.5	652.1	652.8	652.7	652.0	651.2	650.4	649.6
177.5°	653.5	654.1	654.6	654.6	654.0	653.4	652.6	652.0
180°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7

(END OF REPORT)