

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333144-940

Luminaire Tested: **S125DIP-S375D1035U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333144-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1035U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4683.3 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3135	3135	3135	3135
5°	3630	3146	2755	3146
10°	4224	3129	2413	3129
15°	4676	3107	2226	3107
20°	5234	3070	2076	3070
25°	6131	3029	2003	3029
30°	6623	2988	1939	2988
35°	5445	2912	1898	2912
40°	3871	2807	1851	2807
45°	2974	2665	1825	2665
50°	2538	2488	1822	2488
55°	2260	2315	1838	2315
60°	2038	2126	1885	2126
65°	1883	1936	1933	1936
70°	1713	1739	1962	1739
75°	1510	1532	1941	1532
80°	1272	1250	1778	1250
85°	1008	897	1438	897



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	1.0
10°-20°	139.1	3.0
20°-30°	225.9	4.8
30°-40°	275.6	5.9
40°-50°	250.7	5.4
50°-60°	199.7	4.3
60°-70°	139.1	3.0
70°-80°	74.2	1.6
80°-90°	21.2	0.5
90°-100°	320.0	6.8
100°-110°	688.0	14.7
110°-120°	645.7	13.8
120°-130°	523.3	11.2
130°-140°	419.9	9.0
140°-150°	316.9	6.8
150°-160°	223.1	4.8
160°-170°	131.5	2.8
170°-180°	42.8	0.9
0°-30°	411.8	8.8
0°-40°	687.4	14.7
0°-60°	1137.8	24.3
0°-90°	1372.3	29.3
90°-120°	1653.7	35.3
90°-150°	2913.7	62.2
90°-180°	3311.0	70.7
0°-180°	4683.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	560	485	425	485	560	56
15°	699	465	333	465	699	200
25°	860	425	281	425	860	393
35°	691	369	241	369	691	423
45°	326	292	200	292	326	261
55°	201	206	163	206	201	181
65°	123	127	126	127	123	122
75°	60	61	78	61	60	65
85°	14	12	19	12	14	16
90°	20	1	20	1	20	14
95°	209	29	209	29	209	296
105°	1180	101	1180	101	1180	1172
115°	1314	180	1314	180	1314	1284
125°	1035	249	1035	249	1035	937
135°	860	292	860	292	860	666
145°	678	340	678	340	678	431
155°	569	388	569	388	569	265
165°	498	424	498	424	498	143
175°	448	441	448	441	448	44
180°	442	442	442	442	442	



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	513.4	512.8	512.1	510.9	511.8	509.0	507.7	505.4	502.6	501.6	500.4
5°	560.0	561.1	562.1	557.8	558.2	555.3	548.7	543.3	539.0	533.4	529.5
7.5°	616.1	613.7	613.4	610.6	605.8	601.9	595.0	586.2	577.7	567.9	559.9
10°	644.1	644.4	642.5	639.2	634.0	630.3	621.3	612.6	602.1	589.7	580.9
12.5°	665.2	666.1	663.7	659.2	656.7	648.5	641.3	631.1	618.6	608.7	595.2
15°	699.3	697.1	695.4	689.8	685.5	676.9	665.6	654.8	641.2	628.7	616.1
17.5°	732.2	734.1	730.9	725.9	712.4	702.3	687.2	672.4	655.5	638.6	623.7
20°	761.5	763.2	758.5	749.6	733.5	723.4	703.5	684.5	664.9	643.3	626.8
22.5°	798.2	796.8	790.4	776.9	763.0	744.4	722.7	699.6	675.1	650.7	628.7
25°	860.4	851.8	847.8	831.2	812.9	785.4	755.8	722.0	691.5	659.2	631.2
27.5°	895.0	892.2	887.9	876.3	857.0	827.7	792.7	751.5	708.6	667.7	631.0
30°	888.1	888.5	888.9	885.2	872.8	850.8	815.9	771.7	720.5	674.6	632.1
32.5°	826.7	834.2	841.4	849.9	853.4	849.1	827.3	787.3	734.7	682.5	631.5
35°	690.6	692.9	716.2	739.3	770.6	795.0	811.2	793.4	749.2	689.2	630.7
37.5°	538.5	549.7	565.8	591.8	637.0	677.5	729.6	753.5	739.2	691.4	629.3
40°	459.1	469.4	479.9	506.5	544.6	593.6	652.7	703.2	715.0	684.5	624.3
42.5°	397.8	405.9	417.6	437.6	469.4	512.8	569.4	635.3	675.9	664.4	613.9
45°	325.6	330.7	339.7	355.6	378.7	412.7	462.5	534.7	597.5	618.3	589.3
47.5°	278.7	278.7	285.7	296.6	313.3	342.1	379.1	435.5	502.7	552.3	550.0
50°	252.6	251.6	257.2	266.6	279.8	299.0	334.2	379.3	443.8	500.1	515.8
52.5°	230.2	230.3	233.7	240.8	251.8	268.1	294.4	335.2	390.2	448.0	477.5
55°	200.7	199.8	203.8	208.5	216.6	227.3	246.2	277.3	322.1	378.9	417.2
57.5°	173.6	175.9	177.5	180.7	187.4	194.7	210.6	233.4	268.9	317.7	358.2
60°	157.8	160.1	161.3	164.6	170.0	176.2	188.5	207.1	236.9	279.0	319.1
62.5°	143.7	145.4	145.9	148.8	153.2	159.2	168.9	184.5	208.1	244.9	284.2
65°	123.2	123.2	124.0	127.2	129.2	134.6	142.0	153.3	172.3	200.9	234.5
67.5°	103.5	104.5	104.3	105.7	107.5	111.7	117.0	126.4	140.4	161.3	188.2
70°	90.7	91.5	91.3	92.3	94.3	97.0	101.4	110.2	120.3	138.2	161.3
72.5°	79.1	79.5	78.9	80.3	81.5	83.8	88.7	93.5	102.8	118.0	137.0
75°	60.5	61.0	61.4	62.2	63.5	64.7	67.1	71.9	78.1	89.4	101.6
77.5°	45.4	44.6	45.7	45.5	46.2	47.2	49.3	51.8	56.9	64.1	73.5
80°	34.2	34.4	34.4	34.6	35.7	36.3	38.1	39.9	43.9	49.2	55.8
82.5°	25.0	25.5	25.1	25.6	26.4	26.8	27.9	29.4	31.7	35.9	40.7
85°	13.6	12.6	13.0	13.4	13.4	13.6	14.4	15.1	16.3	17.9	19.8
87.5°	8.0	8.4	8.4	8.4	8.6	8.2	8.6	8.5	8.8	9.1	9.5
90°	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1	15.2	14.3	12.5
92.5°	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7	232.3	287.0	291.6
95°	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1	771.8	788.7	643.6
97.5°	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2	976.5	842.3	574.7
100°	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9	1026.4	803.8	512.7
102.5°	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6	996.5	736.2	465.7
105°	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5	900.9	645.3	420.2
107.5°	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1	803.3	582.9	400.9
110°	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0	747.7	553.7	395.2



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6	706.4	536.6	395.2
115°	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2	661.4	518.1	397.9
117.5°	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9	634.5	509.0	403.8
120°	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3	619.6	504.7	409.5
122.5°	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0	606.7	501.1	414.5
125°	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1	589.3	496.7	422.8
127.5°	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6	573.3	494.5	432.3
130°	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9	562.6	493.1	438.0
132.5°	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0	554.0	493.1	444.3
135°	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8	543.9	493.1	453.1
137.5°	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3	534.8	494.2	461.1
140°	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6	530.6	494.9	464.7
142.5°	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3	527.0	495.6	466.8
145°	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2	521.7	494.9	469.1
147.5°	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9	516.1	492.6	470.0
150°	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5	511.8	490.4	470.0
152.5°	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3	506.8	487.7	469.3
155°	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6	498.5	482.5	467.3
157.5°	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9	490.6	477.2	465.0
160°	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8	484.3	473.6	462.9
162.5°	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0	478.6	469.3	460.7
165°	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2	470.0	462.9	457.5
167.5°	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8	461.6	456.6	452.5
170°	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1	456.6	453.1	450.4
172.5°	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7	451.7	448.8	447.5
175°	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7	445.1	444.2	444.2
177.5°	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9	442.2	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	499.4	498.3	497.0	494.6	491.9	490.4	488.1	486.6	483.7	481.2	478.5
5°	524.8	519.4	514.5	508.1	501.1	496.6	491.2	485.3	479.0	472.7	465.7
7.5°	551.1	541.5	531.3	520.2	509.3	499.4	489.8	480.5	471.8	461.2	452.3
10°	568.6	556.7	543.9	529.0	514.2	501.5	488.6	477.2	465.7	453.3	442.4
12.5°	586.3	570.4	552.3	535.8	518.3	502.8	487.6	473.1	458.6	444.9	432.1
15°	598.8	584.8	568.1	544.6	524.8	503.5	483.4	464.7	447.1	431.9	415.8
17.5°	607.0	588.9	571.0	548.5	522.5	498.8	475.9	454.4	434.7	415.4	399.9
20°	608.4	589.9	571.1	549.1	522.5	495.3	472.4	446.7	425.5	405.5	386.6
22.5°	608.0	586.9	566.5	543.9	517.9	492.8	465.2	439.0	415.9	396.3	376.5
25°	603.3	580.9	555.3	532.4	506.8	480.3	452.3	425.1	401.6	379.2	359.5
27.5°	599.4	570.3	541.4	514.7	490.0	465.7	438.8	411.0	385.0	362.2	343.8
30°	594.7	562.7	530.1	502.3	477.0	453.3	427.9	400.7	373.5	351.3	331.5
32.5°	590.4	553.1	518.8	488.5	461.6	438.6	415.3	389.4	362.7	340.1	320.3
35°	582.1	539.0	499.6	465.5	436.8	413.1	393.5	369.4	344.9	323.1	304.2
37.5°	571.6	520.5	478.2	442.4	411.0	386.0	367.8	349.3	325.7	304.7	287.6
40°	563.3	507.3	462.5	425.9	393.3	367.4	350.4	333.0	313.4	293.8	275.7
42.5°	552.9	495.4	446.7	407.2	375.1	349.7	332.0	317.2	299.9	281.6	264.8
45°	533.9	473.9	421.2	378.7	346.2	321.2	302.9	291.8	278.7	261.4	247.3
47.5°	505.8	448.1	393.5	349.7	316.1	293.0	275.8	265.1	256.0	243.2	230.2
50°	480.9	428.8	373.5	330.1	296.5	273.2	257.3	247.6	239.9	230.0	219.0
52.5°	453.1	404.6	353.9	310.9	277.7	254.8	239.2	230.7	224.2	217.1	206.3
55°	408.8	367.6	320.6	279.8	249.1	226.7	213.0	205.6	200.3	194.9	188.3
57.5°	360.1	327.8	286.2	248.9	220.6	200.2	187.5	180.3	176.1	173.3	169.5
60°	325.7	298.2	262.3	228.3	200.7	182.5	170.2	164.6	161.1	158.9	156.0
62.5°	293.9	271.3	238.1	207.1	182.9	165.8	154.7	149.3	146.0	144.8	142.5
65°	247.1	229.5	202.2	176.4	155.8	141.2	131.9	126.7	124.7	123.4	123.6
67.5°	200.8	190.2	168.2	146.2	129.7	117.5	110.0	106.1	105.0	103.4	103.4
70°	172.6	164.6	146.1	126.9	112.3	102.8	96.2	92.1	91.0	90.2	90.1
72.5°	147.8	140.7	124.7	109.3	96.1	87.8	82.4	79.9	78.2	77.8	77.7
75°	111.0	107.2	94.3	82.2	73.1	67.4	63.7	61.4	60.2	59.9	60.2
77.5°	78.9	75.5	67.4	58.8	53.1	48.7	45.6	44.8	43.4	43.4	43.2
80°	59.3	57.1	51.9	45.1	40.4	36.6	35.0	33.6	33.2	32.5	33.2
82.5°	43.0	40.6	37.1	32.7	28.8	26.7	25.0	24.5	24.3	24.0	24.1
85°	21.2	21.4	19.4	16.1	14.4	13.2	12.1	12.1	11.9	11.8	11.9
87.5°	9.5	8.9	8.0	7.2	6.0	5.2	4.6	4.6	4.3	4.5	5.0
90°	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9	1.8	3.6	5.4
92.5°	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9	13.2	20.7	31.7
95°	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3	30.2	37.4	47.2
97.5°	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8	49.8	54.8	64.6
100°	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3	64.1	67.7	77.4
102.5°	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3	78.3	81.1	91.7
105°	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6	100.6	105.0	114.0
107.5°	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4	125.2	129.4	136.7
110°	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7	141.5	145.1	153.1



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1	157.9	160.8	168.8
115°	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9	181.6	184.2	192.3
117.5°	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2	203.8	206.7	214.7
120°	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4	218.1	221.7	229.7
122.5°	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4	232.3	235.1	243.2
125°	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2	251.0	255.5	263.5
127.5°	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0	266.7	272.4	282.6
130°	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3	276.0	283.1	294.6
132.5°	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4	283.7	292.3	305.3
135°	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9	295.5	306.2	320.5
137.5°	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6	309.2	319.2	333.5
140°	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1	317.8	328.5	342.7
142.5°	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1	327.1	337.0	351.2
145°	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0	341.8	350.7	363.2
147.5°	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7	356.8	364.4	376.0
150°	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0	366.8	373.0	384.6
152.5°	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0	376.0	381.6	391.6
155°	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1	388.1	393.4	402.3
157.5°	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8	399.7	403.9	411.6
160°	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7	406.8	410.4	416.6
162.5°	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1	413.2	416.8	422.3
165°	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7	422.0	424.6	429.1
167.5°	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2	429.3	430.9	433.4
170°	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4	433.5	434.4	436.2
172.5°	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3	435.7	436.6	438.3
175°	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6	438.8	439.7	440.6
177.5°	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2	440.8	440.8	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	477.1	475.2	473.8	470.5	468.6	466.2	464.2	466.4	464.0	465.0	463.5
5°	462.2	456.4	452.3	446.3	441.1	436.4	432.9	432.3	430.6	429.8	427.3
7.5°	444.3	437.0	430.0	422.1	415.5	408.8	404.6	401.0	398.7	395.6	393.4
10°	433.7	424.0	415.8	406.4	398.1	390.8	385.1	382.2	379.5	375.6	374.2
12.5°	420.7	410.7	400.6	390.5	382.5	374.5	369.6	365.2	363.4	359.0	358.6
15°	405.1	390.0	380.1	369.9	358.9	352.3	348.2	343.5	341.4	338.3	336.1
17.5°	386.5	373.0	360.7	350.0	340.6	335.1	329.9	326.7	323.2	321.1	317.4
20°	372.9	360.2	347.8	336.4	329.2	322.9	318.8	315.7	311.9	310.9	307.2
22.5°	361.6	347.5	335.6	326.1	318.3	311.0	306.6	304.4	301.9	298.7	298.0
25°	343.0	328.4	318.3	308.9	301.8	295.2	292.2	289.5	287.0	284.7	283.9
27.5°	327.1	314.0	302.0	293.5	287.3	281.3	278.7	275.4	273.6	271.7	269.5
30°	315.8	302.5	291.9	283.7	277.1	271.8	268.9	266.6	265.0	263.3	262.1
32.5°	304.3	291.9	281.8	273.7	267.1	263.1	260.5	258.9	257.1	255.1	253.5
35°	289.1	275.4	265.6	258.6	253.4	250.3	247.4	246.0	244.0	244.0	242.3
37.5°	271.9	260.1	251.4	245.0	240.4	237.6	234.5	233.5	232.2	231.3	230.8
40°	261.7	250.7	242.5	236.1	231.2	228.9	226.4	224.8	224.0	222.9	222.6
42.5°	251.1	240.7	232.8	226.9	222.6	220.7	218.4	217.2	215.5	214.2	213.9
45°	235.1	225.0	217.8	213.0	209.4	207.1	205.6	203.1	202.3	200.7	200.5
47.5°	219.9	210.2	203.1	199.2	196.0	194.1	191.9	189.4	188.4	187.6	187.5
50°	208.5	199.7	193.1	189.4	186.3	183.6	181.3	179.7	179.1	179.1	179.5
52.5°	197.0	189.4	183.9	179.3	176.4	173.5	171.4	170.4	169.5	170.5	171.2
55°	180.1	172.5	168.4	164.0	161.1	157.8	156.8	156.4	155.8	157.4	158.3
57.5°	162.2	156.9	152.0	147.8	145.2	143.2	141.9	141.6	142.8	143.6	146.2
60°	150.8	144.6	140.4	137.1	133.9	132.7	132.2	131.9	132.7	134.9	138.5
62.5°	138.3	133.3	128.6	126.2	123.9	121.8	121.7	122.0	123.6	126.3	129.7
65°	119.9	115.6	112.5	109.6	107.7	106.6	106.9	107.7	109.6	113.2	117.0
67.5°	101.2	98.3	95.5	93.2	91.4	91.4	91.8	93.1	95.2	99.2	102.8
70°	89.3	86.0	83.6	82.7	81.1	80.3	81.6	83.6	85.5	89.3	92.3
72.5°	77.2	74.4	72.6	71.9	71.2	70.6	71.1	73.3	75.8	79.5	83.1
75°	59.3	58.3	57.1	56.3	55.6	56.1	56.4	58.5	60.5	64.5	68.6
77.5°	43.3	42.3	41.5	41.3	40.9	41.2	42.4	43.9	45.8	48.7	51.8
80°	32.7	32.4	31.9	31.7	31.7	31.9	33.6	34.6	36.5	39.1	41.6
82.5°	23.9	23.6	23.5	23.5	23.6	23.7	24.7	26.0	27.6	29.6	31.7
85°	12.6	12.1	12.8	13.0	12.6	13.2	13.6	14.4	15.1	16.1	17.1
87.5°	5.5	6.2	6.2	6.8	7.0	7.7	7.7	8.5	9.0	9.5	9.7
90°	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1	16.9	17.8	19.6
92.5°	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7	114.5	86.1	73.0
95°	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1	504.7	395.2	320.5
97.5°	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2	858.3	751.6	647.6
100°	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9	1051.3	959.6	867.0
102.5°	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6	1169.5	1125.5	1062.8
105°	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5	1236.4	1275.6	1265.8
107.5°	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1	1176.8	1277.4	1323.8
110°	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0	1109.1	1234.7	1310.4



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6	1042.2	1169.1	1258.4
115°	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2	946.3	1068.2	1165.2
117.5°	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9	879.9	984.9	1073.9
120°	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3	842.1	940.0	1018.3
122.5°	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0	815.0	902.2	975.6
125°	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1	778.9	856.3	920.4
127.5°	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6	744.4	816.6	876.6
130°	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9	720.1	789.6	847.5
132.5°	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0	697.3	760.4	816.1
135°	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8	662.3	719.3	770.0
137.5°	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3	631.0	678.3	721.4
140°	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6	612.4	653.4	690.8
142.5°	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3	596.7	632.0	664.4
145°	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2	576.8	604.4	628.5
147.5°	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9	560.3	581.5	599.6
150°	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5	551.0	567.9	584.0
152.5°	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3	541.7	557.2	569.7
155°	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6	527.9	540.4	550.1
157.5°	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9	514.7	524.3	532.0
160°	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8	504.7	513.6	519.9
162.5°	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0	496.1	503.6	509.2
165°	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2	483.4	488.7	493.1
167.5°	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8	470.9	475.0	478.2
170°	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1	463.8	466.5	468.2
172.5°	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7	457.4	459.3	460.4
175°	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7	447.7	449.5	449.5
177.5°	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9	443.6	443.6	443.6
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	462.5	463.7	462.7	464.0	462.7	463.7	462.5	463.5	465.0	464.0	466.4
5°	426.3	424.5	425.7	424.9	425.7	424.5	426.3	427.3	429.8	430.6	432.3
7.5°	392.9	391.1	389.1	388.1	389.1	391.1	392.9	393.4	395.6	398.7	401.0
10°	371.9	369.6	369.4	368.0	369.4	369.6	371.9	374.2	375.6	379.5	382.2
12.5°	356.6	354.5	352.1	351.5	352.1	354.5	356.6	358.6	359.0	363.4	365.2
15°	334.8	333.1	331.7	333.0	331.7	333.1	334.8	336.1	338.3	341.4	343.5
17.5°	316.7	315.4	315.1	313.6	315.1	315.4	316.7	317.4	321.1	323.2	326.7
20°	305.3	304.3	304.8	302.0	304.8	304.3	305.3	307.2	310.9	311.9	315.7
22.5°	296.3	294.3	294.0	293.5	294.0	294.3	296.3	298.0	298.7	301.9	304.4
25°	282.0	281.1	280.0	281.1	280.0	281.1	282.0	283.9	284.7	287.0	289.5
27.5°	269.7	268.4	268.1	268.3	268.1	268.4	269.7	269.5	271.7	273.6	275.4
30°	262.1	260.0	260.2	260.0	260.2	260.0	262.1	262.1	263.3	265.0	266.6
32.5°	253.9	252.4	252.2	251.8	252.2	252.4	253.9	253.5	255.1	257.1	258.9
35°	241.7	241.7	240.7	240.7	240.7	241.7	241.7	242.3	244.0	244.0	246.0
37.5°	230.2	230.1	229.4	229.5	229.4	230.1	230.2	230.8	231.3	232.2	233.5
40°	221.7	221.5	220.9	219.6	220.9	221.5	221.7	222.6	222.9	224.0	224.8
42.5°	213.5	212.8	212.5	212.0	212.5	212.8	213.5	213.9	214.2	215.5	217.2
45°	200.5	200.5	200.1	199.8	200.1	200.5	200.5	200.5	200.7	202.3	203.1
47.5°	187.9	188.2	189.0	188.9	189.0	188.2	187.9	187.5	187.6	188.4	189.4
50°	180.3	180.5	181.1	181.3	181.1	180.5	180.3	179.5	179.1	179.1	179.7
52.5°	171.9	173.1	173.9	173.7	173.9	173.1	171.9	171.2	170.5	169.5	170.4
55°	160.1	161.6	163.0	163.2	163.0	161.6	160.1	158.3	157.4	155.8	156.4
57.5°	148.5	150.4	151.9	152.5	151.9	150.4	148.5	146.2	143.6	142.8	141.6
60°	140.5	143.2	145.1	145.9	145.1	143.2	140.5	138.5	134.9	132.7	131.9
62.5°	133.0	136.0	137.8	137.9	137.8	136.0	133.0	129.7	126.3	123.6	122.0
65°	120.6	123.6	125.3	126.5	125.3	123.6	120.6	117.0	113.2	109.6	107.7
67.5°	107.2	110.3	112.1	113.1	112.1	110.3	107.2	102.8	99.2	95.2	93.1
70°	97.5	100.6	103.0	103.9	103.0	100.6	97.5	92.3	89.3	85.5	83.6
72.5°	87.9	90.7	92.6	93.6	92.6	90.7	87.9	83.1	79.5	75.8	73.3
75°	71.2	75.0	76.9	77.8	76.9	75.0	71.2	68.6	64.5	60.5	58.5
77.5°	54.9	58.3	59.5	60.0	59.5	58.3	54.9	51.8	48.7	45.8	43.9
80°	44.1	46.2	47.6	47.8	47.6	46.2	44.1	41.6	39.1	36.5	34.6
82.5°	33.9	35.6	36.0	36.6	36.0	35.6	33.9	31.7	29.6	27.6	26.0
85°	18.5	19.4	19.6	19.4	19.6	19.4	18.5	17.1	16.1	15.1	14.4
87.5°	10.0	9.8	10.0	10.3	10.0	9.8	10.0	9.7	9.5	9.0	8.5
90°	19.6	19.6	20.5	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1
92.5°	61.6	59.5	58.2	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7
95°	257.3	230.6	223.5	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1
97.5°	592.7	542.8	517.0	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2
100°	805.6	741.5	708.6	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9
102.5°	997.2	951.6	915.8	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6
105°	1237.3	1208.0	1190.2	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5
107.5°	1338.3	1338.1	1332.2	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1
110°	1350.4	1367.3	1373.5	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1316.9	1345.9	1361.5	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6
115°	1234.7	1277.4	1302.3	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2
117.5°	1143.4	1187.5	1212.2	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9
120°	1084.2	1126.9	1151.0	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3
122.5°	1034.4	1073.5	1097.6	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0
125°	970.3	1006.7	1026.4	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1
127.5°	921.9	954.0	972.6	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6
130°	892.0	921.3	939.1	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9
132.5°	860.6	890.0	906.3	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0
135°	809.1	838.6	854.5	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8
137.5°	756.4	783.2	798.0	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3
140°	723.7	746.9	760.2	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6
142.5°	692.4	711.9	724.6	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3
145°	649.8	664.9	674.8	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2
147.5°	616.5	628.7	634.4	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9
150°	597.3	608.0	611.5	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5
152.5°	580.9	589.5	593.0	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3
155°	559.0	565.3	567.9	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6
157.5°	539.0	544.0	546.5	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9
160°	526.1	530.6	532.4	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8
162.5°	514.0	517.7	518.1	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0
165°	496.7	498.5	498.5	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2
167.5°	480.0	481.6	480.9	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8
170°	470.0	470.9	470.9	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1
172.5°	460.7	462.4	460.9	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7
175°	449.5	450.4	448.6	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7
177.5°	442.9	443.6	441.5	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	464.2	466.2	468.6	470.5	473.8	475.2	477.1	478.5	481.2	483.7	486.6
5°	432.9	436.4	441.1	446.3	452.3	456.4	462.2	465.7	472.7	479.0	485.3
7.5°	404.6	408.8	415.5	422.1	430.0	437.0	444.3	452.3	461.2	471.8	480.5
10°	385.1	390.8	398.1	406.4	415.8	424.0	433.7	442.4	453.3	465.7	477.2
12.5°	369.6	374.5	382.5	390.5	400.6	410.7	420.7	432.1	444.9	458.6	473.1
15°	348.2	352.3	358.9	369.9	380.1	390.0	405.1	415.8	431.9	447.1	464.7
17.5°	329.9	335.1	340.6	350.0	360.7	373.0	386.5	399.9	415.4	434.7	454.4
20°	318.8	322.9	329.2	336.4	347.8	360.2	372.9	386.6	405.5	425.5	446.7
22.5°	306.6	311.0	318.3	326.1	335.6	347.5	361.6	376.5	396.3	415.9	439.0
25°	292.2	295.2	301.8	308.9	318.3	328.4	343.0	359.5	379.2	401.6	425.1
27.5°	278.7	281.3	287.3	293.5	302.0	314.0	327.1	343.8	362.2	385.0	411.0
30°	268.9	271.8	277.1	283.7	291.9	302.5	315.8	331.5	351.3	373.5	400.7
32.5°	260.5	263.1	267.1	273.7	281.8	291.9	304.3	320.3	340.1	362.7	389.4
35°	247.4	250.3	253.4	258.6	265.6	275.4	289.1	304.2	323.1	344.9	369.4
37.5°	234.5	237.6	240.4	245.0	251.4	260.1	271.9	287.6	304.7	325.7	349.3
40°	226.4	228.9	231.2	236.1	242.5	250.7	261.7	275.7	293.8	313.4	333.0
42.5°	218.4	220.7	222.6	226.9	232.8	240.7	251.1	264.8	281.6	299.9	317.2
45°	205.6	207.1	209.4	213.0	217.8	225.0	235.1	247.3	261.4	278.7	291.8
47.5°	191.9	194.1	196.0	199.2	203.1	210.2	219.9	230.2	243.2	256.0	265.1
50°	181.3	183.6	186.3	189.4	193.1	199.7	208.5	219.0	230.0	239.9	247.6
52.5°	171.4	173.5	176.4	179.3	183.9	189.4	197.0	206.3	217.1	224.2	230.7
55°	156.8	157.8	161.1	164.0	168.4	172.5	180.1	188.3	194.9	200.3	205.6
57.5°	141.9	143.2	145.2	147.8	152.0	156.9	162.2	169.5	173.3	176.1	180.3
60°	132.2	132.7	133.9	137.1	140.4	144.6	150.8	156.0	158.9	161.1	164.6
62.5°	121.7	121.8	123.9	126.2	128.6	133.3	138.3	142.5	144.8	146.0	149.3
65°	106.9	106.6	107.7	109.6	112.5	115.6	119.9	123.6	123.4	124.7	126.7
67.5°	91.8	91.4	91.4	93.2	95.5	98.3	101.2	103.4	103.4	105.0	106.1
70°	81.6	80.3	81.1	82.7	83.6	86.0	89.3	90.1	90.2	91.0	92.1
72.5°	71.1	70.6	71.2	71.9	72.6	74.4	77.2	77.7	77.8	78.2	79.9
75°	56.4	56.1	55.6	56.3	57.1	58.3	59.3	60.2	59.9	60.2	61.4
77.5°	42.4	41.2	40.9	41.3	41.5	42.3	43.3	43.2	43.4	43.4	44.8
80°	33.6	31.9	31.7	31.7	31.9	32.4	32.7	33.2	32.5	33.2	33.6
82.5°	24.7	23.7	23.6	23.5	23.5	23.6	23.9	24.1	24.0	24.3	24.5
85°	13.6	13.2	12.6	13.0	12.8	12.1	12.6	11.9	11.8	11.9	12.1
87.5°	7.7	7.7	7.0	6.8	6.2	6.2	5.5	5.0	4.5	4.3	4.6
90°	15.2	14.3	12.5	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9
92.5°	232.3	287.0	291.6	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9
95°	771.8	788.7	643.6	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3
97.5°	976.5	842.3	574.7	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8
100°	1026.4	803.8	512.7	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3
102.5°	996.5	736.2	465.7	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3
105°	900.9	645.3	420.2	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6
107.5°	803.3	582.9	400.9	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4
110°	747.7	553.7	395.2	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	706.4	536.6	395.2	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1
115°	661.4	518.1	397.9	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9
117.5°	634.5	509.0	403.8	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2
120°	619.6	504.7	409.5	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4
122.5°	606.7	501.1	414.5	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4
125°	589.3	496.7	422.8	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2
127.5°	573.3	494.5	432.3	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0
130°	562.6	493.1	438.0	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3
132.5°	554.0	493.1	444.3	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4
135°	543.9	493.1	453.1	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9
137.5°	534.8	494.2	461.1	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6
140°	530.6	494.9	464.7	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1
142.5°	527.0	495.6	466.8	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1
145°	521.7	494.9	469.1	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0
147.5°	516.1	492.6	470.0	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7
150°	511.8	490.4	470.0	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0
152.5°	506.8	487.7	469.3	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0
155°	498.5	482.5	467.3	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1
157.5°	490.6	477.2	465.0	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8
160°	484.3	473.6	462.9	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7
162.5°	478.6	469.3	460.7	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1
165°	470.0	462.9	457.5	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7
167.5°	461.6	456.6	452.5	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2
170°	456.6	453.1	450.4	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4
172.5°	451.7	448.8	447.5	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3
175°	445.1	444.2	444.2	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6
177.5°	442.2	441.5	441.5	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	488.1	490.4	491.9	494.6	497.0	498.3	499.4	500.4	501.6	502.6	505.4
5°	491.2	496.6	501.1	508.1	514.5	519.4	524.8	529.5	533.4	539.0	543.3
7.5°	489.8	499.4	509.3	520.2	531.3	541.5	551.1	559.9	567.9	577.7	586.2
10°	488.6	501.5	514.2	529.0	543.9	556.7	568.6	580.9	589.7	602.1	612.6
12.5°	487.6	502.8	518.3	535.8	552.3	570.4	586.3	595.2	608.7	618.6	631.1
15°	483.4	503.5	524.8	544.6	568.1	584.8	598.8	616.1	628.7	641.2	654.8
17.5°	475.9	498.8	522.5	548.5	571.0	588.9	607.0	623.7	638.6	655.5	672.4
20°	472.4	495.3	522.5	549.1	571.1	589.9	608.4	626.8	643.3	664.9	684.5
22.5°	465.2	492.8	517.9	543.9	566.5	586.9	608.0	628.7	650.7	675.1	699.6
25°	452.3	480.3	506.8	532.4	555.3	580.9	603.3	631.2	659.2	691.5	722.0
27.5°	438.8	465.7	490.0	514.7	541.4	570.3	599.4	631.0	667.7	708.6	751.5
30°	427.9	453.3	477.0	502.3	530.1	562.7	594.7	632.1	674.6	720.5	771.7
32.5°	415.3	438.6	461.6	488.5	518.8	553.1	590.4	631.5	682.5	734.7	787.3
35°	393.5	413.1	436.8	465.5	499.6	539.0	582.1	630.7	689.2	749.2	793.4
37.5°	367.8	386.0	411.0	442.4	478.2	520.5	571.6	629.3	691.4	739.2	753.5
40°	350.4	367.4	393.3	425.9	462.5	507.3	563.3	624.3	684.5	715.0	703.2
42.5°	332.0	349.7	375.1	407.2	446.7	495.4	552.9	613.9	664.4	675.9	635.3
45°	302.9	321.2	346.2	378.7	421.2	473.9	533.9	589.3	618.3	597.5	534.7
47.5°	275.8	293.0	316.1	349.7	393.5	448.1	505.8	550.0	552.3	502.7	435.5
50°	257.3	273.2	296.5	330.1	373.5	428.8	480.9	515.8	500.1	443.8	379.3
52.5°	239.2	254.8	277.7	310.9	353.9	404.6	453.1	477.5	448.0	390.2	335.2
55°	213.0	226.7	249.1	279.8	320.6	367.6	408.8	417.2	378.9	322.1	277.3
57.5°	187.5	200.2	220.6	248.9	286.2	327.8	360.1	358.2	317.7	268.9	233.4
60°	170.2	182.5	200.7	228.3	262.3	298.2	325.7	319.1	279.0	236.9	207.1
62.5°	154.7	165.8	182.9	207.1	238.1	271.3	293.9	284.2	244.9	208.1	184.5
65°	131.9	141.2	155.8	176.4	202.2	229.5	247.1	234.5	200.9	172.3	153.3
67.5°	110.0	117.5	129.7	146.2	168.2	190.2	200.8	188.2	161.3	140.4	126.4
70°	96.2	102.8	112.3	126.9	146.1	164.6	172.6	161.3	138.2	120.3	110.2
72.5°	82.4	87.8	96.1	109.3	124.7	140.7	147.8	137.0	118.0	102.8	93.5
75°	63.7	67.4	73.1	82.2	94.3	107.2	111.0	101.6	89.4	78.1	71.9
77.5°	45.6	48.7	53.1	58.8	67.4	75.5	78.9	73.5	64.1	56.9	51.8
80°	35.0	36.6	40.4	45.1	51.9	57.1	59.3	55.8	49.2	43.9	39.9
82.5°	25.0	26.7	28.8	32.7	37.1	40.6	43.0	40.7	35.9	31.7	29.4
85°	12.1	13.2	14.4	16.1	19.4	21.4	21.2	19.8	17.9	16.3	15.1
87.5°	4.6	5.2	6.0	7.2	8.0	8.9	9.5	9.5	9.1	8.8	8.5
90°	1.8	3.6	5.4	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1
92.5°	13.2	20.7	31.7	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7
95°	30.2	37.4	47.2	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1
97.5°	49.8	54.8	64.6	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2
100°	64.1	67.7	77.4	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9
102.5°	78.3	81.1	91.7	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6
105°	100.6	105.0	114.0	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5
107.5°	125.2	129.4	136.7	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1
110°	141.5	145.1	153.1	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.9	160.8	168.8	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6
115°	181.6	184.2	192.3	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2
117.5°	203.8	206.7	214.7	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9
120°	218.1	221.7	229.7	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3
122.5°	232.3	235.1	243.2	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0
125°	251.0	255.5	263.5	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1
127.5°	266.7	272.4	282.6	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6
130°	276.0	283.1	294.6	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9
132.5°	283.7	292.3	305.3	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0
135°	295.5	306.2	320.5	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8
137.5°	309.2	319.2	333.5	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3
140°	317.8	328.5	342.7	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6
142.5°	327.1	337.0	351.2	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3
145°	341.8	350.7	363.2	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2
147.5°	356.8	364.4	376.0	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9
150°	366.8	373.0	384.6	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5
152.5°	376.0	381.6	391.6	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3
155°	388.1	393.4	402.3	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6
157.5°	399.7	403.9	411.6	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9
160°	406.8	410.4	416.6	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8
162.5°	413.2	416.8	422.3	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0
165°	422.0	424.6	429.1	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2
167.5°	429.3	430.9	433.4	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8
170°	433.5	434.4	436.2	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1
172.5°	435.7	436.6	438.3	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7
175°	438.8	439.7	440.6	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7
177.5°	440.8	440.8	441.5	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	507.7	509.0	511.8	510.9	512.1	512.8	513.4
5°	548.7	555.3	558.2	557.8	562.1	561.1	560.0
7.5°	595.0	601.9	605.8	610.6	613.4	613.7	616.1
10°	621.3	630.3	634.0	639.2	642.5	644.4	644.1
12.5°	641.3	648.5	656.7	659.2	663.7	666.1	665.2
15°	665.6	676.9	685.5	689.8	695.4	697.1	699.3
17.5°	687.2	702.3	712.4	725.9	730.9	734.1	732.2
20°	703.5	723.4	733.5	749.6	758.5	763.2	761.5
22.5°	722.7	744.4	763.0	776.9	790.4	796.8	798.2
25°	755.8	785.4	812.9	831.2	847.8	851.8	860.4
27.5°	792.7	827.7	857.0	876.3	887.9	892.2	895.0
30°	815.9	850.8	872.8	885.2	888.9	888.5	888.1
32.5°	827.3	849.1	853.4	849.9	841.4	834.2	826.7
35°	811.2	795.0	770.6	739.3	716.2	692.9	690.6
37.5°	729.6	677.5	637.0	591.8	565.8	549.7	538.5
40°	652.7	593.6	544.6	506.5	479.9	469.4	459.1
42.5°	569.4	512.8	469.4	437.6	417.6	405.9	397.8
45°	462.5	412.7	378.7	355.6	339.7	330.7	325.6
47.5°	379.1	342.1	313.3	296.6	285.7	278.7	278.7
50°	334.2	299.0	279.8	266.6	257.2	251.6	252.6
52.5°	294.4	268.1	251.8	240.8	233.7	230.3	230.2
55°	246.2	227.3	216.6	208.5	203.8	199.8	200.7
57.5°	210.6	194.7	187.4	180.7	177.5	175.9	173.6
60°	188.5	176.2	170.0	164.6	161.3	160.1	157.8
62.5°	168.9	159.2	153.2	148.8	145.9	145.4	143.7
65°	142.0	134.6	129.2	127.2	124.0	123.2	123.2
67.5°	117.0	111.7	107.5	105.7	104.3	104.5	103.5
70°	101.4	97.0	94.3	92.3	91.3	91.5	90.7
72.5°	88.7	83.8	81.5	80.3	78.9	79.5	79.1
75°	67.1	64.7	63.5	62.2	61.4	61.0	60.5
77.5°	49.3	47.2	46.2	45.5	45.7	44.6	45.4
80°	38.1	36.3	35.7	34.6	34.4	34.4	34.2
82.5°	27.9	26.8	26.4	25.6	25.1	25.5	25.0
85°	14.4	13.6	13.4	13.4	13.0	12.6	13.6
87.5°	8.6	8.2	8.6	8.4	8.4	8.4	8.0
90°	16.9	17.8	19.6	19.6	19.6	20.5	20.5
92.5°	114.5	86.1	73.0	61.6	59.5	58.2	56.8
95°	504.7	395.2	320.5	257.3	230.6	223.5	209.2
97.5°	858.3	751.6	647.6	592.7	542.8	517.0	505.6
100°	1051.3	959.6	867.0	805.6	741.5	708.6	694.4
102.5°	1169.5	1125.5	1062.8	997.2	951.6	915.8	905.1
105°	1236.4	1275.6	1265.8	1237.3	1208.0	1190.2	1179.5
107.5°	1176.8	1277.4	1323.8	1338.3	1338.1	1332.2	1325.1
110°	1109.1	1234.7	1310.4	1350.4	1367.3	1373.5	1373.5



TEST NUMBER: P333144-940

CATALOG NUMBER: S125DIP-S375D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1042.2	1169.1	1258.4	1316.9	1345.9	1361.5	1367.8
115°	946.3	1068.2	1165.2	1234.7	1277.4	1302.3	1313.9
117.5°	879.9	984.9	1073.9	1143.4	1187.5	1212.2	1219.3
120°	842.1	940.0	1018.3	1084.2	1126.9	1151.0	1158.2
122.5°	815.0	902.2	975.6	1034.4	1073.5	1097.6	1104.0
125°	778.9	856.3	920.4	970.3	1006.7	1026.4	1035.3
127.5°	744.4	816.6	876.6	921.9	954.0	972.6	976.5
130°	720.1	789.6	847.5	892.0	921.3	939.1	944.5
132.5°	697.3	760.4	816.1	860.6	890.0	906.3	912.4
135°	662.3	719.3	770.0	809.1	838.6	854.5	859.9
137.5°	631.0	678.3	721.4	756.4	783.2	798.0	803.8
140°	612.4	653.4	690.8	723.7	746.9	760.2	764.6
142.5°	596.7	632.0	664.4	692.4	711.9	724.6	728.3
145°	576.8	604.4	628.5	649.8	664.9	674.8	678.3
147.5°	560.3	581.5	599.6	616.5	628.7	634.4	636.0
150°	551.0	567.9	584.0	597.3	608.0	611.5	612.4
152.5°	541.7	557.2	569.7	580.9	589.5	593.0	593.9
155°	527.9	540.4	550.1	559.0	565.3	567.9	568.8
157.5°	514.7	524.3	532.0	539.0	544.0	546.5	546.4
160°	504.7	513.6	519.9	526.1	530.6	532.4	531.5
162.5°	496.1	503.6	509.2	514.0	517.7	518.1	517.9
165°	483.4	488.7	493.1	496.7	498.5	498.5	498.5
167.5°	470.9	475.0	478.2	480.0	481.6	480.9	480.7
170°	463.8	466.5	468.2	470.0	470.9	470.9	470.0
172.5°	457.4	459.3	460.4	460.7	462.4	460.9	460.0
175°	447.7	449.5	449.5	449.5	450.4	448.6	447.7
177.5°	443.6	443.6	443.6	442.9	443.6	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5

(END OF REPORT)