

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333153-940

Luminaire Tested: **S125DIP-S375D1205U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333153-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1205U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5226.6 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	71	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	22	21	16
4	70	60	53	47	63	54	47	43	42	38	34	31	28	26	21	20	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3135	3135	3135	3135
5°	3630	3146	2755	3146
10°	4224	3129	2413	3129
15°	4676	3107	2226	3107
20°	5234	3070	2076	3070
25°	6131	3029	2003	3029
30°	6623	2988	1939	2988
35°	5445	2912	1898	2912
40°	3871	2807	1851	2807
45°	2974	2665	1825	2665
50°	2538	2488	1822	2488
55°	2260	2315	1838	2315
60°	2038	2126	1885	2126
65°	1883	1936	1933	1936
70°	1713	1739	1962	1739
75°	1510	1532	1941	1532
80°	1272	1250	1778	1250
85°	1008	897	1438	897



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	0.9
10°-20°	139.1	2.7
20°-30°	225.9	4.3
30°-40°	275.6	5.3
40°-50°	250.7	4.8
50°-60°	199.7	3.8
60°-70°	139.1	2.7
70°-80°	74.2	1.4
80°-90°	21.6	0.4
90°-100°	372.5	7.1
100°-110°	800.8	15.3
110°-120°	751.5	14.4
120°-130°	609.1	11.7
130°-140°	488.8	9.4
140°-150°	368.8	7.1
150°-160°	259.6	5.0
160°-170°	153.0	2.9
170°-180°	49.8	1.0
0°-30°	411.8	7.9
0°-40°	687.4	13.2
0°-60°	1137.8	21.8
0°-90°	1372.7	26.3
90°-120°	1924.8	36.8
90°-150°	3391.5	64.9
90°-180°	3854.0	73.7
0°-180°	5226.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	560	485	425	485	560	56
15°	699	465	333	465	699	200
25°	860	425	281	425	860	393
35°	691	369	241	369	691	423
45°	326	292	200	292	326	261
55°	201	206	163	206	201	181
65°	123	127	126	127	123	122
75°	60	61	78	61	60	65
85°	14	12	19	12	14	16
90°	24	1	24	1	24	17
95°	244	34	244	34	244	345
105°	1373	117	1373	117	1373	1365
115°	1529	209	1529	209	1529	1494
125°	1205	290	1205	290	1205	1090
135°	1001	340	1001	340	1001	776
145°	790	396	790	396	790	502
155°	662	452	662	452	662	309
165°	580	493	580	493	580	166
175°	521	513	521	513	521	51
180°	514	514	514	514	514	



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	513.4	512.8	512.1	510.9	511.8	509.0	507.7	505.4	502.6	501.6	500.4
5°	560.0	561.1	562.1	557.8	558.2	555.3	548.7	543.3	539.0	533.4	529.5
7.5°	616.1	613.7	613.4	610.6	605.8	601.9	595.0	586.2	577.7	567.9	559.9
10°	644.1	644.4	642.5	639.2	634.0	630.3	621.3	612.6	602.1	589.7	580.9
12.5°	665.2	666.1	663.7	659.2	656.7	648.5	641.3	631.1	618.6	608.7	595.2
15°	699.3	697.1	695.4	689.8	685.5	676.9	665.6	654.8	641.2	628.7	616.1
17.5°	732.2	734.1	730.9	725.9	712.4	702.3	687.2	672.4	655.5	638.6	623.7
20°	761.5	763.2	758.5	749.6	733.5	723.4	703.5	684.5	664.9	643.3	626.8
22.5°	798.2	796.8	790.4	776.9	763.0	744.4	722.7	699.6	675.1	650.7	628.7
25°	860.4	851.8	847.8	831.2	812.9	785.4	755.8	722.0	691.5	659.2	631.2
27.5°	895.0	892.2	887.9	876.3	857.0	827.7	792.7	751.5	708.6	667.7	631.0
30°	888.1	888.5	888.9	885.2	872.8	850.8	815.9	771.7	720.5	674.6	632.1
32.5°	826.7	834.2	841.4	849.9	853.4	849.1	827.3	787.3	734.7	682.5	631.5
35°	690.6	692.9	716.2	739.3	770.6	795.0	811.2	793.4	749.2	689.2	630.7
37.5°	538.5	549.7	565.8	591.8	637.0	677.5	729.6	753.5	739.2	691.4	629.3
40°	459.1	469.4	479.9	506.5	544.6	593.6	652.7	703.2	715.0	684.5	624.3
42.5°	397.8	405.9	417.6	437.6	469.4	512.8	569.4	635.3	675.9	664.4	613.9
45°	325.6	330.7	339.7	355.6	378.7	412.7	462.5	534.7	597.5	618.3	589.3
47.5°	278.7	278.7	285.7	296.6	313.3	342.1	379.1	435.5	502.7	552.3	550.0
50°	252.6	251.6	257.2	266.6	279.8	299.0	334.2	379.3	443.8	500.1	515.8
52.5°	230.2	230.3	233.7	240.8	251.8	268.1	294.4	335.2	390.2	448.0	477.5
55°	200.7	199.8	203.8	208.5	216.6	227.3	246.2	277.3	322.1	378.9	417.2
57.5°	173.6	175.9	177.5	180.7	187.4	194.7	210.6	233.4	268.9	317.7	358.2
60°	157.8	160.1	161.3	164.6	170.0	176.2	188.5	207.1	236.9	279.0	319.1
62.5°	143.7	145.4	145.9	148.8	153.2	159.2	168.9	184.5	208.1	244.9	284.2
65°	123.2	123.2	124.0	127.2	129.2	134.6	142.0	153.3	172.3	200.9	234.5
67.5°	103.5	104.5	104.3	105.7	107.5	111.7	117.0	126.4	140.4	161.3	188.2
70°	90.7	91.5	91.3	92.3	94.3	97.0	101.4	110.2	120.3	138.2	161.3
72.5°	79.1	79.5	78.9	80.3	81.5	83.8	88.7	93.5	102.8	118.0	137.0
75°	60.5	61.0	61.4	62.2	63.5	64.7	67.1	71.9	78.1	89.4	101.6
77.5°	45.4	44.6	45.7	45.5	46.2	47.2	49.3	51.8	56.9	64.1	73.5
80°	34.2	34.4	34.4	34.6	35.7	36.3	38.1	39.9	43.9	49.2	55.8
82.5°	25.0	25.5	25.1	25.6	26.4	26.8	27.9	29.4	31.7	35.9	40.7
85°	13.6	12.6	13.0	13.4	13.4	13.6	14.4	15.1	16.3	17.9	19.8
87.5°	8.7	9.1	9.0	9.0	9.2	8.7	9.2	9.0	9.3	9.5	9.8
90°	23.8	23.8	22.8	22.8	22.8	20.7	19.7	18.6	17.7	16.6	14.5
92.5°	66.1	67.8	69.2	71.7	85.0	100.3	133.2	183.6	270.5	334.0	339.5
95°	243.5	260.1	268.3	299.4	373.0	460.0	587.5	744.9	898.3	918.0	749.1
97.5°	588.5	601.8	631.9	689.8	753.9	874.9	999.1	1109.5	1136.7	980.3	669.0
100°	808.2	824.7	863.1	937.7	1009.1	1117.0	1223.7	1274.4	1194.6	935.6	596.8
102.5°	1053.6	1066.0	1107.6	1160.7	1237.2	1310.1	1361.3	1330.0	1159.8	856.8	542.1
105°	1372.9	1385.3	1406.0	1440.2	1473.4	1484.8	1439.2	1297.3	1048.6	751.2	489.0
107.5°	1542.4	1550.7	1557.6	1557.7	1541.0	1486.8	1369.8	1180.4	935.0	678.4	466.6
110°	1598.7	1598.7	1591.5	1571.8	1525.2	1437.1	1291.0	1094.1	870.3	644.4	460.0



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1592.1	1584.7	1566.6	1532.9	1464.6	1360.8	1213.1	1026.2	822.2	624.6	460.0
115°	1529.3	1515.8	1486.8	1437.1	1356.3	1243.3	1101.4	940.8	769.8	603.1	463.2
117.5°	1419.2	1411.0	1382.2	1330.8	1250.0	1146.4	1024.1	885.6	738.5	592.5	470.0
120°	1348.0	1339.7	1311.7	1262.0	1185.4	1094.1	980.2	855.9	721.1	587.5	476.6
122.5°	1285.0	1277.6	1249.6	1204.0	1135.6	1050.3	948.7	833.5	706.2	583.4	482.4
125°	1205.1	1194.6	1171.9	1129.4	1071.4	996.8	906.6	800.9	685.9	578.2	492.1
127.5°	1136.7	1132.1	1110.5	1073.0	1020.4	950.6	866.4	767.8	667.3	575.7	503.1
130°	1099.3	1093.1	1072.4	1038.2	986.4	919.1	838.2	747.1	654.9	574.0	509.8
132.5°	1062.0	1055.0	1035.9	1001.7	949.9	885.0	811.7	726.3	644.9	574.0	517.2
135°	1000.9	994.7	976.1	941.8	896.3	837.2	770.9	699.4	633.1	574.0	527.4
137.5°	935.6	928.8	911.6	880.5	839.7	789.5	734.4	676.6	622.5	575.2	536.7
140°	890.0	884.8	869.3	842.4	804.1	760.5	712.8	664.1	617.5	576.0	540.8
142.5°	847.7	843.4	828.7	805.9	773.4	735.7	694.6	653.4	613.4	576.9	543.3
145°	789.5	785.4	774.0	756.3	731.5	703.6	671.4	639.3	607.2	576.0	546.1
147.5°	740.2	738.3	731.7	717.6	697.9	676.8	652.1	626.1	600.7	573.4	547.1
150°	712.8	711.9	707.7	695.3	679.7	661.0	641.4	618.6	595.8	570.9	547.1
152.5°	691.3	690.3	686.1	676.2	663.2	648.6	630.6	610.3	590.0	567.6	546.3
155°	662.1	661.0	657.9	650.7	640.3	628.9	614.4	597.8	580.2	561.6	543.9
157.5°	636.0	636.1	633.3	627.2	619.2	610.3	599.1	585.4	571.1	555.4	541.3
160°	618.6	619.6	617.5	612.3	605.1	597.8	587.5	577.1	563.7	551.3	538.8
162.5°	602.8	603.1	602.6	598.2	592.6	586.2	577.6	568.0	557.1	546.3	536.3
165°	580.2	580.2	580.2	578.2	574.0	568.8	562.6	555.4	547.1	538.8	532.5
167.5°	559.5	559.7	560.5	558.7	556.6	552.9	548.1	543.3	537.3	531.5	526.7
170°	547.1	548.1	548.1	547.1	545.0	543.0	539.8	536.7	531.5	527.4	524.3
172.5°	535.5	536.5	538.1	536.3	535.9	534.7	532.4	529.2	525.8	522.5	520.9
175°	521.2	522.2	524.3	523.3	523.3	523.3	521.2	521.2	518.1	517.0	517.0
177.5°	513.9	513.9	516.4	515.6	516.4	516.4	516.4	515.6	514.8	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	499.4	498.3	497.0	494.6	491.9	490.4	488.1	486.6	483.7	481.2	478.5
5°	524.8	519.4	514.5	508.1	501.1	496.6	491.2	485.3	479.0	472.7	465.7
7.5°	551.1	541.5	531.3	520.2	509.3	499.4	489.8	480.5	471.8	461.2	452.3
10°	568.6	556.7	543.9	529.0	514.2	501.5	488.6	477.2	465.7	453.3	442.4
12.5°	586.3	570.4	552.3	535.8	518.3	502.8	487.6	473.1	458.6	444.9	432.1
15°	598.8	584.8	568.1	544.6	524.8	503.5	483.4	464.7	447.1	431.9	415.8
17.5°	607.0	588.9	571.0	548.5	522.5	498.8	475.9	454.4	434.7	415.4	399.9
20°	608.4	589.9	571.1	549.1	522.5	495.3	472.4	446.7	425.5	405.5	386.6
22.5°	608.0	586.9	566.5	543.9	517.9	492.8	465.2	439.0	415.9	396.3	376.5
25°	603.3	580.9	555.3	532.4	506.8	480.3	452.3	425.1	401.6	379.2	359.5
27.5°	599.4	570.3	541.4	514.7	490.0	465.7	438.8	411.0	385.0	362.2	343.8
30°	594.7	562.7	530.1	502.3	477.0	453.3	427.9	400.7	373.5	351.3	331.5
32.5°	590.4	553.1	518.8	488.5	461.6	438.6	415.3	389.4	362.7	340.1	320.3
35°	582.1	539.0	499.6	465.5	436.8	413.1	393.5	369.4	344.9	323.1	304.2
37.5°	571.6	520.5	478.2	442.4	411.0	386.0	367.8	349.3	325.7	304.7	287.6
40°	563.3	507.3	462.5	425.9	393.3	367.4	350.4	333.0	313.4	293.8	275.7
42.5°	552.9	495.4	446.7	407.2	375.1	349.7	332.0	317.2	299.9	281.6	264.8
45°	533.9	473.9	421.2	378.7	346.2	321.2	302.9	291.8	278.7	261.4	247.3
47.5°	505.8	448.1	393.5	349.7	316.1	293.0	275.8	265.1	256.0	243.2	230.2
50°	480.9	428.8	373.5	330.1	296.5	273.2	257.3	247.6	239.9	230.0	219.0
52.5°	453.1	404.6	353.9	310.9	277.7	254.8	239.2	230.7	224.2	217.1	206.3
55°	408.8	367.6	320.6	279.8	249.1	226.7	213.0	205.6	200.3	194.9	188.3
57.5°	360.1	327.8	286.2	248.9	220.6	200.2	187.5	180.3	176.1	173.3	169.5
60°	325.7	298.2	262.3	228.3	200.7	182.5	170.2	164.6	161.1	158.9	156.0
62.5°	293.9	271.3	238.1	207.1	182.9	165.8	154.7	149.3	146.0	144.8	142.5
65°	247.1	229.5	202.2	176.4	155.8	141.2	131.9	126.7	124.7	123.4	123.6
67.5°	200.8	190.2	168.2	146.2	129.7	117.5	110.0	106.1	105.0	103.4	103.4
70°	172.6	164.6	146.1	126.9	112.3	102.8	96.2	92.1	91.0	90.2	90.1
72.5°	147.8	140.7	124.7	109.3	96.1	87.8	82.4	79.9	78.2	77.8	77.7
75°	111.0	107.2	94.3	82.2	73.1	67.4	63.7	61.4	60.2	59.9	60.2
77.5°	78.9	75.5	67.4	58.8	53.1	48.7	45.6	44.8	43.4	43.4	43.2
80°	59.3	57.1	51.9	45.1	40.4	36.6	35.0	33.6	33.2	32.5	33.2
82.5°	43.0	40.6	37.1	32.7	28.8	26.7	25.0	24.5	24.3	24.0	24.1
85°	21.2	21.4	19.4	16.1	14.4	13.2	12.1	12.1	11.9	11.8	11.9
87.5°	10.0	9.2	8.3	7.4	6.2	5.3	4.7	4.6	4.4	4.6	5.2
90°	13.5	11.4	10.3	8.3	6.2	4.1	2.1	1.1	2.1	4.1	6.2
92.5°	236.5	141.5	85.0	54.8	36.9	24.1	15.3	12.7	15.3	24.1	36.9
95°	463.2	235.2	124.3	77.7	54.9	43.5	35.2	34.2	35.2	43.5	54.9
97.5°	369.7	202.7	129.3	95.8	75.3	63.8	58.1	56.8	58.1	63.8	75.3
100°	335.7	201.0	140.9	109.9	90.2	78.7	74.6	72.5	74.6	78.7	90.2
102.5°	321.6	208.5	155.0	124.8	106.7	94.5	91.2	90.0	91.2	94.5	106.7
105°	316.0	223.8	178.3	149.2	132.6	122.3	117.1	117.1	117.1	122.3	132.6
107.5°	325.6	246.6	202.4	176.4	159.2	150.6	145.7	143.6	145.7	150.6	159.2
110°	334.7	263.1	220.7	193.8	178.3	168.9	164.8	162.6	164.8	168.9	178.3



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	346.3	278.9	238.1	212.0	196.4	187.1	183.8	181.7	183.8	187.1	196.4
115°	363.6	303.6	265.3	239.3	223.8	214.5	211.3	209.3	211.3	214.5	223.8
117.5°	383.6	328.9	292.6	267.5	249.9	240.6	237.3	234.2	237.3	240.6	249.9
120°	396.8	347.1	310.9	284.9	267.3	258.0	253.9	250.7	253.9	258.0	267.3
122.5°	411.8	364.5	328.2	302.4	283.0	273.8	270.5	268.1	270.5	273.8	283.0
125°	432.0	387.5	353.3	326.4	306.7	297.4	292.2	290.1	292.2	297.4	306.7
127.5°	450.8	409.7	376.7	349.8	328.9	317.1	310.4	307.3	310.4	317.1	328.9
130°	463.2	423.7	391.6	364.7	343.0	329.5	321.2	318.1	321.2	329.5	343.0
132.5°	473.9	437.0	404.9	378.0	355.4	340.3	330.3	326.4	330.3	340.3	355.4
135°	489.0	454.9	422.8	394.8	373.0	356.4	344.0	339.8	344.0	356.4	373.0
137.5°	500.2	467.5	438.3	409.5	388.2	371.6	360.0	356.9	360.0	371.6	388.2
140°	507.7	476.6	446.6	418.6	399.0	382.4	369.9	366.8	369.9	382.4	399.0
142.5°	511.8	482.4	454.1	427.8	408.8	392.3	380.7	378.4	380.7	392.3	408.8
145°	518.1	492.1	465.2	441.4	422.8	408.2	397.9	395.8	397.9	408.2	422.8
147.5°	521.8	498.4	474.7	453.8	437.7	424.2	415.3	414.0	415.3	424.2	437.7
150°	524.3	502.5	479.7	462.1	447.6	434.2	426.9	424.8	426.9	434.2	447.6
152.5°	525.9	506.7	485.5	469.6	455.9	444.1	437.7	436.4	437.7	444.1	455.9
155°	527.4	510.8	493.2	478.7	468.3	458.0	451.7	451.7	451.7	458.0	468.3
157.5°	528.4	514.3	499.2	488.2	479.1	470.2	465.2	465.5	465.2	470.2	479.1
160°	528.4	516.0	502.5	493.2	484.9	477.7	473.5	474.6	473.5	477.7	484.9
162.5°	527.6	517.6	505.9	498.2	491.5	485.1	481.0	482.0	481.0	485.1	491.5
165°	526.4	518.1	509.8	503.5	499.4	494.3	491.2	493.2	491.2	494.3	499.4
167.5°	523.9	518.1	511.2	507.3	504.4	501.5	499.6	500.7	499.6	501.5	504.4
170°	522.2	518.1	512.9	509.8	507.7	505.6	504.6	505.6	504.6	505.6	507.7
172.5°	520.6	517.2	512.9	511.4	510.1	508.1	507.1	509.0	507.1	508.1	510.1
175°	518.1	516.0	512.9	512.9	512.9	511.8	510.8	512.9	510.8	511.8	512.9
177.5°	515.6	514.8	513.1	513.1	513.9	513.1	513.1	514.8	513.1	513.1	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	477.1	475.2	473.8	470.5	468.6	466.2	464.2	466.4	464.0	465.0	463.5
5°	462.2	456.4	452.3	446.3	441.1	436.4	432.9	432.3	430.6	429.8	427.3
7.5°	444.3	437.0	430.0	422.1	415.5	408.8	404.6	401.0	398.7	395.6	393.4
10°	433.7	424.0	415.8	406.4	398.1	390.8	385.1	382.2	379.5	375.6	374.2
12.5°	420.7	410.7	400.6	390.5	382.5	374.5	369.6	365.2	363.4	359.0	358.6
15°	405.1	390.0	380.1	369.9	358.9	352.3	348.2	343.5	341.4	338.3	336.1
17.5°	386.5	373.0	360.7	350.0	340.6	335.1	329.9	326.7	323.2	321.1	317.4
20°	372.9	360.2	347.8	336.4	329.2	322.9	318.8	315.7	311.9	310.9	307.2
22.5°	361.6	347.5	335.6	326.1	318.3	311.0	306.6	304.4	301.9	298.7	298.0
25°	343.0	328.4	318.3	308.9	301.8	295.2	292.2	289.5	287.0	284.7	283.9
27.5°	327.1	314.0	302.0	293.5	287.3	281.3	278.7	275.4	273.6	271.7	269.5
30°	315.8	302.5	291.9	283.7	277.1	271.8	268.9	266.6	265.0	263.3	262.1
32.5°	304.3	291.9	281.8	273.7	267.1	263.1	260.5	258.9	257.1	255.1	253.5
35°	289.1	275.4	265.6	258.6	253.4	250.3	247.4	246.0	244.0	244.0	242.3
37.5°	271.9	260.1	251.4	245.0	240.4	237.6	234.5	233.5	232.2	231.3	230.8
40°	261.7	250.7	242.5	236.1	231.2	228.9	226.4	224.8	224.0	222.9	222.6
42.5°	251.1	240.7	232.8	226.9	222.6	220.7	218.4	217.2	215.5	214.2	213.9
45°	235.1	225.0	217.8	213.0	209.4	207.1	205.6	203.1	202.3	200.7	200.5
47.5°	219.9	210.2	203.1	199.2	196.0	194.1	191.9	189.4	188.4	187.6	187.5
50°	208.5	199.7	193.1	189.4	186.3	183.6	181.3	179.7	179.1	179.1	179.5
52.5°	197.0	189.4	183.9	179.3	176.4	173.5	171.4	170.4	169.5	170.5	171.2
55°	180.1	172.5	168.4	164.0	161.1	157.8	156.8	156.4	155.8	157.4	158.3
57.5°	162.2	156.9	152.0	147.8	145.2	143.2	141.9	141.6	142.8	143.6	146.2
60°	150.8	144.6	140.4	137.1	133.9	132.7	132.2	131.9	132.7	134.9	138.5
62.5°	138.3	133.3	128.6	126.2	123.9	121.8	121.7	122.0	123.6	126.3	129.7
65°	119.9	115.6	112.5	109.6	107.7	106.6	106.9	107.7	109.6	113.2	117.0
67.5°	101.2	98.3	95.5	93.2	91.4	91.4	91.8	93.1	95.2	99.2	102.8
70°	89.3	86.0	83.6	82.7	81.1	80.3	81.6	83.6	85.5	89.3	92.3
72.5°	77.2	74.4	72.6	71.9	71.2	70.6	71.1	73.3	75.8	79.5	83.1
75°	59.3	58.3	57.1	56.3	55.6	56.1	56.4	58.5	60.5	64.5	68.6
77.5°	43.3	42.3	41.5	41.3	40.9	41.2	42.4	43.9	45.8	48.7	51.8
80°	32.7	32.4	31.9	31.7	31.7	31.9	33.6	34.6	36.5	39.1	41.6
82.5°	23.9	23.6	23.5	23.5	23.6	23.7	24.7	26.0	27.6	29.6	31.7
85°	12.6	12.1	12.8	13.0	12.6	13.2	13.6	14.4	15.1	16.1	17.1
87.5°	5.8	6.5	6.6	7.1	7.3	8.1	8.1	9.0	9.5	10.1	10.3
90°	8.3	10.3	11.4	13.5	14.5	16.6	17.7	18.6	19.7	20.7	22.8
92.5°	54.8	85.0	141.5	236.5	339.5	334.0	270.5	183.6	133.2	100.3	85.0
95°	77.7	124.3	235.2	463.2	749.1	918.0	898.3	744.9	587.5	460.0	373.0
97.5°	95.8	129.3	202.7	369.7	669.0	980.3	1136.7	1109.5	999.1	874.9	753.9
100°	109.9	140.9	201.0	335.7	596.8	935.6	1194.6	1274.4	1223.7	1117.0	1009.1
102.5°	124.8	155.0	208.5	321.6	542.1	856.8	1159.8	1330.0	1361.3	1310.1	1237.2
105°	149.2	178.3	223.8	316.0	489.0	751.2	1048.6	1297.3	1439.2	1484.8	1473.4
107.5°	176.4	202.4	246.6	325.6	466.6	678.4	935.0	1180.4	1369.8	1486.8	1541.0
110°	193.8	220.7	263.1	334.7	460.0	644.4	870.3	1094.1	1291.0	1437.1	1525.2



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	212.0	238.1	278.9	346.3	460.0	624.6	822.2	1026.2	1213.1	1360.8	1464.6
115°	239.3	265.3	303.6	363.6	463.2	603.1	769.8	940.8	1101.4	1243.3	1356.3
117.5°	267.5	292.6	328.9	383.6	470.0	592.5	738.5	885.6	1024.1	1146.4	1250.0
120°	284.9	310.9	347.1	396.8	476.6	587.5	721.1	855.9	980.2	1094.1	1185.4
122.5°	302.4	328.2	364.5	411.8	482.4	583.4	706.2	833.5	948.7	1050.3	1135.6
125°	326.4	353.3	387.5	432.0	492.1	578.2	685.9	800.9	906.6	996.8	1071.4
127.5°	349.8	376.7	409.7	450.8	503.1	575.7	667.3	767.8	866.4	950.6	1020.4
130°	364.7	391.6	423.7	463.2	509.8	574.0	654.9	747.1	838.2	919.1	986.4
132.5°	378.0	404.9	437.0	473.9	517.2	574.0	644.9	726.3	811.7	885.0	949.9
135°	394.8	422.8	454.9	489.0	527.4	574.0	633.1	699.4	770.9	837.2	896.3
137.5°	409.5	438.3	467.5	500.2	536.7	575.2	622.5	676.6	734.4	789.5	839.7
140°	418.6	446.6	476.6	507.7	540.8	576.0	617.5	664.1	712.8	760.5	804.1
142.5°	427.8	454.1	482.4	511.8	543.3	576.9	613.4	653.4	694.6	735.7	773.4
145°	441.4	465.2	492.1	518.1	546.1	576.0	607.2	639.3	671.4	703.6	731.5
147.5°	453.8	474.7	498.4	521.8	547.1	573.4	600.7	626.1	652.1	676.8	697.9
150°	462.1	479.7	502.5	524.3	547.1	570.9	595.8	618.6	641.4	661.0	679.7
152.5°	469.6	485.5	506.7	525.9	546.3	567.6	590.0	610.3	630.6	648.6	663.2
155°	478.7	493.2	510.8	527.4	543.9	561.6	580.2	597.8	614.4	628.9	640.3
157.5°	488.2	499.2	514.3	528.4	541.3	555.4	571.1	585.4	599.1	610.3	619.2
160°	493.2	502.5	516.0	528.4	538.8	551.3	563.7	577.1	587.5	597.8	605.1
162.5°	498.2	505.9	517.6	527.6	536.3	546.3	557.1	568.0	577.6	586.2	592.6
165°	503.5	509.8	518.1	526.4	532.5	538.8	547.1	555.4	562.6	568.8	574.0
167.5°	507.3	511.2	518.1	523.9	526.7	531.5	537.3	543.3	548.1	552.9	556.6
170°	509.8	512.9	518.1	522.2	524.3	527.4	531.5	536.7	539.8	543.0	545.0
172.5°	511.4	512.9	517.2	520.6	520.9	522.5	525.8	529.2	532.4	534.7	535.9
175°	512.9	512.9	516.0	518.1	517.0	517.0	518.1	521.2	521.2	523.3	523.3
177.5°	513.1	513.1	514.8	515.6	513.9	513.9	514.8	515.6	516.4	516.4	516.4
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	462.5	463.7	462.7	464.0	462.7	463.7	462.5	463.5	465.0	464.0	466.4
5°	426.3	424.5	425.7	424.9	425.7	424.5	426.3	427.3	429.8	430.6	432.3
7.5°	392.9	391.1	389.1	388.1	389.1	391.1	392.9	393.4	395.6	398.7	401.0
10°	371.9	369.6	369.4	368.0	369.4	369.6	371.9	374.2	375.6	379.5	382.2
12.5°	356.6	354.5	352.1	351.5	352.1	354.5	356.6	358.6	359.0	363.4	365.2
15°	334.8	333.1	331.7	333.0	331.7	333.1	334.8	336.1	338.3	341.4	343.5
17.5°	316.7	315.4	315.1	313.6	315.1	315.4	316.7	317.4	321.1	323.2	326.7
20°	305.3	304.3	304.8	302.0	304.8	304.3	305.3	307.2	310.9	311.9	315.7
22.5°	296.3	294.3	294.0	293.5	294.0	294.3	296.3	298.0	298.7	301.9	304.4
25°	282.0	281.1	280.0	281.1	280.0	281.1	282.0	283.9	284.7	287.0	289.5
27.5°	269.7	268.4	268.1	268.3	268.1	268.4	269.7	269.5	271.7	273.6	275.4
30°	262.1	260.0	260.2	260.0	260.2	260.0	262.1	262.1	263.3	265.0	266.6
32.5°	253.9	252.4	252.2	251.8	252.2	252.4	253.9	253.5	255.1	257.1	258.9
35°	241.7	241.7	240.7	240.7	240.7	241.7	241.7	242.3	244.0	244.0	246.0
37.5°	230.2	230.1	229.4	229.5	229.4	230.1	230.2	230.8	231.3	232.2	233.5
40°	221.7	221.5	220.9	219.6	220.9	221.5	221.7	222.6	222.9	224.0	224.8
42.5°	213.5	212.8	212.5	212.0	212.5	212.8	213.5	213.9	214.2	215.5	217.2
45°	200.5	200.5	200.1	199.8	200.1	200.5	200.5	200.5	200.7	202.3	203.1
47.5°	187.9	188.2	189.0	188.9	189.0	188.2	187.9	187.5	187.6	188.4	189.4
50°	180.3	180.5	181.1	181.3	181.1	180.5	180.3	179.5	179.1	179.1	179.7
52.5°	171.9	173.1	173.9	173.7	173.9	173.1	171.9	171.2	170.5	169.5	170.4
55°	160.1	161.6	163.0	163.2	163.0	161.6	160.1	158.3	157.4	155.8	156.4
57.5°	148.5	150.4	151.9	152.5	151.9	150.4	148.5	146.2	143.6	142.8	141.6
60°	140.5	143.2	145.1	145.9	145.1	143.2	140.5	138.5	134.9	132.7	131.9
62.5°	133.0	136.0	137.8	137.9	137.8	136.0	133.0	129.7	126.3	123.6	122.0
65°	120.6	123.6	125.3	126.5	125.3	123.6	120.6	117.0	113.2	109.6	107.7
67.5°	107.2	110.3	112.1	113.1	112.1	110.3	107.2	102.8	99.2	95.2	93.1
70°	97.5	100.6	103.0	103.9	103.0	100.6	97.5	92.3	89.3	85.5	83.6
72.5°	87.9	90.7	92.6	93.6	92.6	90.7	87.9	83.1	79.5	75.8	73.3
75°	71.2	75.0	76.9	77.8	76.9	75.0	71.2	68.6	64.5	60.5	58.5
77.5°	54.9	58.3	59.5	60.0	59.5	58.3	54.9	51.8	48.7	45.8	43.9
80°	44.1	46.2	47.6	47.8	47.6	46.2	44.1	41.6	39.1	36.5	34.6
82.5°	33.9	35.6	36.0	36.6	36.0	35.6	33.9	31.7	29.6	27.6	26.0
85°	18.5	19.4	19.6	19.4	19.6	19.4	18.5	17.1	16.1	15.1	14.4
87.5°	10.7	10.5	10.7	11.1	10.7	10.5	10.7	10.3	10.1	9.5	9.0
90°	22.8	22.8	23.8	23.8	23.8	22.8	22.8	22.8	20.7	19.7	18.6
92.5°	71.7	69.2	67.8	66.1	67.8	69.2	71.7	85.0	100.3	133.2	183.6
95°	299.4	268.3	260.1	243.5	260.1	268.3	299.4	373.0	460.0	587.5	744.9
97.5°	689.8	631.9	601.8	588.5	601.8	631.9	689.8	753.9	874.9	999.1	1109.5
100°	937.7	863.1	824.7	808.2	824.7	863.1	937.7	1009.1	1117.0	1223.7	1274.4
102.5°	1160.7	1107.6	1066.0	1053.6	1066.0	1107.6	1160.7	1237.2	1310.1	1361.3	1330.0
105°	1440.2	1406.0	1385.3	1372.9	1385.3	1406.0	1440.2	1473.4	1484.8	1439.2	1297.3
107.5°	1557.7	1557.6	1550.7	1542.4	1550.7	1557.6	1557.7	1541.0	1486.8	1369.8	1180.4
110°	1571.8	1591.5	1598.7	1598.7	1598.7	1591.5	1571.8	1525.2	1437.1	1291.0	1094.1



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1532.9	1566.6	1584.7	1592.1	1584.7	1566.6	1532.9	1464.6	1360.8	1213.1	1026.2
115°	1437.1	1486.8	1515.8	1529.3	1515.8	1486.8	1437.1	1356.3	1243.3	1101.4	940.8
117.5°	1330.8	1382.2	1411.0	1419.2	1411.0	1382.2	1330.8	1250.0	1146.4	1024.1	885.6
120°	1262.0	1311.7	1339.7	1348.0	1339.7	1311.7	1262.0	1185.4	1094.1	980.2	855.9
122.5°	1204.0	1249.6	1277.6	1285.0	1277.6	1249.6	1204.0	1135.6	1050.3	948.7	833.5
125°	1129.4	1171.9	1194.6	1205.1	1194.6	1171.9	1129.4	1071.4	996.8	906.6	800.9
127.5°	1073.0	1110.5	1132.1	1136.7	1132.1	1110.5	1073.0	1020.4	950.6	866.4	767.8
130°	1038.2	1072.4	1093.1	1099.3	1093.1	1072.4	1038.2	986.4	919.1	838.2	747.1
132.5°	1001.7	1035.9	1055.0	1062.0	1055.0	1035.9	1001.7	949.9	885.0	811.7	726.3
135°	941.8	976.1	994.7	1000.9	994.7	976.1	941.8	896.3	837.2	770.9	699.4
137.5°	880.5	911.6	928.8	935.6	928.8	911.6	880.5	839.7	789.5	734.4	676.6
140°	842.4	869.3	884.8	890.0	884.8	869.3	842.4	804.1	760.5	712.8	664.1
142.5°	805.9	828.7	843.4	847.7	843.4	828.7	805.9	773.4	735.7	694.6	653.4
145°	756.3	774.0	785.4	789.5	785.4	774.0	756.3	731.5	703.6	671.4	639.3
147.5°	717.6	731.7	738.3	740.2	738.3	731.7	717.6	697.9	676.8	652.1	626.1
150°	695.3	707.7	711.9	712.8	711.9	707.7	695.3	679.7	661.0	641.4	618.6
152.5°	676.2	686.1	690.3	691.3	690.3	686.1	676.2	663.2	648.6	630.6	610.3
155°	650.7	657.9	661.0	662.1	661.0	657.9	650.7	640.3	628.9	614.4	597.8
157.5°	627.2	633.3	636.1	636.0	636.1	633.3	627.2	619.2	610.3	599.1	585.4
160°	612.3	617.5	619.6	618.6	619.6	617.5	612.3	605.1	597.8	587.5	577.1
162.5°	598.2	602.6	603.1	602.8	603.1	602.6	598.2	592.6	586.2	577.6	568.0
165°	578.2	580.2	580.2	580.2	580.2	580.2	578.2	574.0	568.8	562.6	555.4
167.5°	558.7	560.5	559.7	559.5	559.7	560.5	558.7	556.6	552.9	548.1	543.3
170°	547.1	548.1	548.1	547.1	548.1	548.1	547.1	545.0	543.0	539.8	536.7
172.5°	536.3	538.1	536.5	535.5	536.5	538.1	536.3	535.9	534.7	532.4	529.2
175°	523.3	524.3	522.2	521.2	522.2	524.3	523.3	523.3	523.3	521.2	521.2
177.5°	515.6	516.4	513.9	513.9	513.9	516.4	515.6	516.4	516.4	516.4	515.6
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	464.2	466.2	468.6	470.5	473.8	475.2	477.1	478.5	481.2	483.7	486.6
5°	432.9	436.4	441.1	446.3	452.3	456.4	462.2	465.7	472.7	479.0	485.3
7.5°	404.6	408.8	415.5	422.1	430.0	437.0	444.3	452.3	461.2	471.8	480.5
10°	385.1	390.8	398.1	406.4	415.8	424.0	433.7	442.4	453.3	465.7	477.2
12.5°	369.6	374.5	382.5	390.5	400.6	410.7	420.7	432.1	444.9	458.6	473.1
15°	348.2	352.3	358.9	369.9	380.1	390.0	405.1	415.8	431.9	447.1	464.7
17.5°	329.9	335.1	340.6	350.0	360.7	373.0	386.5	399.9	415.4	434.7	454.4
20°	318.8	322.9	329.2	336.4	347.8	360.2	372.9	386.6	405.5	425.5	446.7
22.5°	306.6	311.0	318.3	326.1	335.6	347.5	361.6	376.5	396.3	415.9	439.0
25°	292.2	295.2	301.8	308.9	318.3	328.4	343.0	359.5	379.2	401.6	425.1
27.5°	278.7	281.3	287.3	293.5	302.0	314.0	327.1	343.8	362.2	385.0	411.0
30°	268.9	271.8	277.1	283.7	291.9	302.5	315.8	331.5	351.3	373.5	400.7
32.5°	260.5	263.1	267.1	273.7	281.8	291.9	304.3	320.3	340.1	362.7	389.4
35°	247.4	250.3	253.4	258.6	265.6	275.4	289.1	304.2	323.1	344.9	369.4
37.5°	234.5	237.6	240.4	245.0	251.4	260.1	271.9	287.6	304.7	325.7	349.3
40°	226.4	228.9	231.2	236.1	242.5	250.7	261.7	275.7	293.8	313.4	333.0
42.5°	218.4	220.7	222.6	226.9	232.8	240.7	251.1	264.8	281.6	299.9	317.2
45°	205.6	207.1	209.4	213.0	217.8	225.0	235.1	247.3	261.4	278.7	291.8
47.5°	191.9	194.1	196.0	199.2	203.1	210.2	219.9	230.2	243.2	256.0	265.1
50°	181.3	183.6	186.3	189.4	193.1	199.7	208.5	219.0	230.0	239.9	247.6
52.5°	171.4	173.5	176.4	179.3	183.9	189.4	197.0	206.3	217.1	224.2	230.7
55°	156.8	157.8	161.1	164.0	168.4	172.5	180.1	188.3	194.9	200.3	205.6
57.5°	141.9	143.2	145.2	147.8	152.0	156.9	162.2	169.5	173.3	176.1	180.3
60°	132.2	132.7	133.9	137.1	140.4	144.6	150.8	156.0	158.9	161.1	164.6
62.5°	121.7	121.8	123.9	126.2	128.6	133.3	138.3	142.5	144.8	146.0	149.3
65°	106.9	106.6	107.7	109.6	112.5	115.6	119.9	123.6	123.4	124.7	126.7
67.5°	91.8	91.4	91.4	93.2	95.5	98.3	101.2	103.4	103.4	105.0	106.1
70°	81.6	80.3	81.1	82.7	83.6	86.0	89.3	90.1	90.2	91.0	92.1
72.5°	71.1	70.6	71.2	71.9	72.6	74.4	77.2	77.7	77.8	78.2	79.9
75°	56.4	56.1	55.6	56.3	57.1	58.3	59.3	60.2	59.9	60.2	61.4
77.5°	42.4	41.2	40.9	41.3	41.5	42.3	43.3	43.2	43.4	43.4	44.8
80°	33.6	31.9	31.7	31.7	31.9	32.4	32.7	33.2	32.5	33.2	33.6
82.5°	24.7	23.7	23.6	23.5	23.5	23.6	23.9	24.1	24.0	24.3	24.5
85°	13.6	13.2	12.6	13.0	12.8	12.1	12.6	11.9	11.8	11.9	12.1
87.5°	8.1	8.1	7.3	7.1	6.6	6.5	5.8	5.2	4.6	4.4	4.6
90°	17.7	16.6	14.5	13.5	11.4	10.3	8.3	6.2	4.1	2.1	1.1
92.5°	270.5	334.0	339.5	236.5	141.5	85.0	54.8	36.9	24.1	15.3	12.7
95°	898.3	918.0	749.1	463.2	235.2	124.3	77.7	54.9	43.5	35.2	34.2
97.5°	1136.7	980.3	669.0	369.7	202.7	129.3	95.8	75.3	63.8	58.1	56.8
100°	1194.6	935.6	596.8	335.7	201.0	140.9	109.9	90.2	78.7	74.6	72.5
102.5°	1159.8	856.8	542.1	321.6	208.5	155.0	124.8	106.7	94.5	91.2	90.0
105°	1048.6	751.2	489.0	316.0	223.8	178.3	149.2	132.6	122.3	117.1	117.1
107.5°	935.0	678.4	466.6	325.6	246.6	202.4	176.4	159.2	150.6	145.7	143.6
110°	870.3	644.4	460.0	334.7	263.1	220.7	193.8	178.3	168.9	164.8	162.6



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	822.2	624.6	460.0	346.3	278.9	238.1	212.0	196.4	187.1	183.8	181.7
115°	769.8	603.1	463.2	363.6	303.6	265.3	239.3	223.8	214.5	211.3	209.3
117.5°	738.5	592.5	470.0	383.6	328.9	292.6	267.5	249.9	240.6	237.3	234.2
120°	721.1	587.5	476.6	396.8	347.1	310.9	284.9	267.3	258.0	253.9	250.7
122.5°	706.2	583.4	482.4	411.8	364.5	328.2	302.4	283.0	273.8	270.5	268.1
125°	685.9	578.2	492.1	432.0	387.5	353.3	326.4	306.7	297.4	292.2	290.1
127.5°	667.3	575.7	503.1	450.8	409.7	376.7	349.8	328.9	317.1	310.4	307.3
130°	654.9	574.0	509.8	463.2	423.7	391.6	364.7	343.0	329.5	321.2	318.1
132.5°	644.9	574.0	517.2	473.9	437.0	404.9	378.0	355.4	340.3	330.3	326.4
135°	633.1	574.0	527.4	489.0	454.9	422.8	394.8	373.0	356.4	344.0	339.8
137.5°	622.5	575.2	536.7	500.2	467.5	438.3	409.5	388.2	371.6	360.0	356.9
140°	617.5	576.0	540.8	507.7	476.6	446.6	418.6	399.0	382.4	369.9	366.8
142.5°	613.4	576.9	543.3	511.8	482.4	454.1	427.8	408.8	392.3	380.7	378.4
145°	607.2	576.0	546.1	518.1	492.1	465.2	441.4	422.8	408.2	397.9	395.8
147.5°	600.7	573.4	547.1	521.8	498.4	474.7	453.8	437.7	424.2	415.3	414.0
150°	595.8	570.9	547.1	524.3	502.5	479.7	462.1	447.6	434.2	426.9	424.8
152.5°	590.0	567.6	546.3	525.9	506.7	485.5	469.6	455.9	444.1	437.7	436.4
155°	580.2	561.6	543.9	527.4	510.8	493.2	478.7	468.3	458.0	451.7	451.7
157.5°	571.1	555.4	541.3	528.4	514.3	499.2	488.2	479.1	470.2	465.2	465.5
160°	563.7	551.3	538.8	528.4	516.0	502.5	493.2	484.9	477.7	473.5	474.6
162.5°	557.1	546.3	536.3	527.6	517.6	505.9	498.2	491.5	485.1	481.0	482.0
165°	547.1	538.8	532.5	526.4	518.1	509.8	503.5	499.4	494.3	491.2	493.2
167.5°	537.3	531.5	526.7	523.9	518.1	511.2	507.3	504.4	501.5	499.6	500.7
170°	531.5	527.4	524.3	522.2	518.1	512.9	509.8	507.7	505.6	504.6	505.6
172.5°	525.8	522.5	520.9	520.6	517.2	512.9	511.4	510.1	508.1	507.1	509.0
175°	518.1	517.0	517.0	518.1	516.0	512.9	512.9	512.9	511.8	510.8	512.9
177.5°	514.8	513.9	513.9	515.6	514.8	513.1	513.1	513.9	513.1	513.1	514.8
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	488.1	490.4	491.9	494.6	497.0	498.3	499.4	500.4	501.6	502.6	505.4
5°	491.2	496.6	501.1	508.1	514.5	519.4	524.8	529.5	533.4	539.0	543.3
7.5°	489.8	499.4	509.3	520.2	531.3	541.5	551.1	559.9	567.9	577.7	586.2
10°	488.6	501.5	514.2	529.0	543.9	556.7	568.6	580.9	589.7	602.1	612.6
12.5°	487.6	502.8	518.3	535.8	552.3	570.4	586.3	595.2	608.7	618.6	631.1
15°	483.4	503.5	524.8	544.6	568.1	584.8	598.8	616.1	628.7	641.2	654.8
17.5°	475.9	498.8	522.5	548.5	571.0	588.9	607.0	623.7	638.6	655.5	672.4
20°	472.4	495.3	522.5	549.1	571.1	589.9	608.4	626.8	643.3	664.9	684.5
22.5°	465.2	492.8	517.9	543.9	566.5	586.9	608.0	628.7	650.7	675.1	699.6
25°	452.3	480.3	506.8	532.4	555.3	580.9	603.3	631.2	659.2	691.5	722.0
27.5°	438.8	465.7	490.0	514.7	541.4	570.3	599.4	631.0	667.7	708.6	751.5
30°	427.9	453.3	477.0	502.3	530.1	562.7	594.7	632.1	674.6	720.5	771.7
32.5°	415.3	438.6	461.6	488.5	518.8	553.1	590.4	631.5	682.5	734.7	787.3
35°	393.5	413.1	436.8	465.5	499.6	539.0	582.1	630.7	689.2	749.2	793.4
37.5°	367.8	386.0	411.0	442.4	478.2	520.5	571.6	629.3	691.4	739.2	753.5
40°	350.4	367.4	393.3	425.9	462.5	507.3	563.3	624.3	684.5	715.0	703.2
42.5°	332.0	349.7	375.1	407.2	446.7	495.4	552.9	613.9	664.4	675.9	635.3
45°	302.9	321.2	346.2	378.7	421.2	473.9	533.9	589.3	618.3	597.5	534.7
47.5°	275.8	293.0	316.1	349.7	393.5	448.1	505.8	550.0	552.3	502.7	435.5
50°	257.3	273.2	296.5	330.1	373.5	428.8	480.9	515.8	500.1	443.8	379.3
52.5°	239.2	254.8	277.7	310.9	353.9	404.6	453.1	477.5	448.0	390.2	335.2
55°	213.0	226.7	249.1	279.8	320.6	367.6	408.8	417.2	378.9	322.1	277.3
57.5°	187.5	200.2	220.6	248.9	286.2	327.8	360.1	358.2	317.7	268.9	233.4
60°	170.2	182.5	200.7	228.3	262.3	298.2	325.7	319.1	279.0	236.9	207.1
62.5°	154.7	165.8	182.9	207.1	238.1	271.3	293.9	284.2	244.9	208.1	184.5
65°	131.9	141.2	155.8	176.4	202.2	229.5	247.1	234.5	200.9	172.3	153.3
67.5°	110.0	117.5	129.7	146.2	168.2	190.2	200.8	188.2	161.3	140.4	126.4
70°	96.2	102.8	112.3	126.9	146.1	164.6	172.6	161.3	138.2	120.3	110.2
72.5°	82.4	87.8	96.1	109.3	124.7	140.7	147.8	137.0	118.0	102.8	93.5
75°	63.7	67.4	73.1	82.2	94.3	107.2	111.0	101.6	89.4	78.1	71.9
77.5°	45.6	48.7	53.1	58.8	67.4	75.5	78.9	73.5	64.1	56.9	51.8
80°	35.0	36.6	40.4	45.1	51.9	57.1	59.3	55.8	49.2	43.9	39.9
82.5°	25.0	26.7	28.8	32.7	37.1	40.6	43.0	40.7	35.9	31.7	29.4
85°	12.1	13.2	14.4	16.1	19.4	21.4	21.2	19.8	17.9	16.3	15.1
87.5°	4.7	5.3	6.2	7.4	8.3	9.2	10.0	9.8	9.5	9.3	9.0
90°	2.1	4.1	6.2	8.3	10.3	11.4	13.5	14.5	16.6	17.7	18.6
92.5°	15.3	24.1	36.9	54.8	85.0	141.5	236.5	339.5	334.0	270.5	183.6
95°	35.2	43.5	54.9	77.7	124.3	235.2	463.2	749.1	918.0	898.3	744.9
97.5°	58.1	63.8	75.3	95.8	129.3	202.7	369.7	669.0	980.3	1136.7	1109.5
100°	74.6	78.7	90.2	109.9	140.9	201.0	335.7	596.8	935.6	1194.6	1274.4
102.5°	91.2	94.5	106.7	124.8	155.0	208.5	321.6	542.1	856.8	1159.8	1330.0
105°	117.1	122.3	132.6	149.2	178.3	223.8	316.0	489.0	751.2	1048.6	1297.3
107.5°	145.7	150.6	159.2	176.4	202.4	246.6	325.6	466.6	678.4	935.0	1180.4
110°	164.8	168.9	178.3	193.8	220.7	263.1	334.7	460.0	644.4	870.3	1094.1



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.8	187.1	196.4	212.0	238.1	278.9	346.3	460.0	624.6	822.2	1026.2
115°	211.3	214.5	223.8	239.3	265.3	303.6	363.6	463.2	603.1	769.8	940.8
117.5°	237.3	240.6	249.9	267.5	292.6	328.9	383.6	470.0	592.5	738.5	885.6
120°	253.9	258.0	267.3	284.9	310.9	347.1	396.8	476.6	587.5	721.1	855.9
122.5°	270.5	273.8	283.0	302.4	328.2	364.5	411.8	482.4	583.4	706.2	833.5
125°	292.2	297.4	306.7	326.4	353.3	387.5	432.0	492.1	578.2	685.9	800.9
127.5°	310.4	317.1	328.9	349.8	376.7	409.7	450.8	503.1	575.7	667.3	767.8
130°	321.2	329.5	343.0	364.7	391.6	423.7	463.2	509.8	574.0	654.9	747.1
132.5°	330.3	340.3	355.4	378.0	404.9	437.0	473.9	517.2	574.0	644.9	726.3
135°	344.0	356.4	373.0	394.8	422.8	454.9	489.0	527.4	574.0	633.1	699.4
137.5°	360.0	371.6	388.2	409.5	438.3	467.5	500.2	536.7	575.2	622.5	676.6
140°	369.9	382.4	399.0	418.6	446.6	476.6	507.7	540.8	576.0	617.5	664.1
142.5°	380.7	392.3	408.8	427.8	454.1	482.4	511.8	543.3	576.9	613.4	653.4
145°	397.9	408.2	422.8	441.4	465.2	492.1	518.1	546.1	576.0	607.2	639.3
147.5°	415.3	424.2	437.7	453.8	474.7	498.4	521.8	547.1	573.4	600.7	626.1
150°	426.9	434.2	447.6	462.1	479.7	502.5	524.3	547.1	570.9	595.8	618.6
152.5°	437.7	444.1	455.9	469.6	485.5	506.7	525.9	546.3	567.6	590.0	610.3
155°	451.7	458.0	468.3	478.7	493.2	510.8	527.4	543.9	561.6	580.2	597.8
157.5°	465.2	470.2	479.1	488.2	499.2	514.3	528.4	541.3	555.4	571.1	585.4
160°	473.5	477.7	484.9	493.2	502.5	516.0	528.4	538.8	551.3	563.7	577.1
162.5°	481.0	485.1	491.5	498.2	505.9	517.6	527.6	536.3	546.3	557.1	568.0
165°	491.2	494.3	499.4	503.5	509.8	518.1	526.4	532.5	538.8	547.1	555.4
167.5°	499.6	501.5	504.4	507.3	511.2	518.1	523.9	526.7	531.5	537.3	543.3
170°	504.6	505.6	507.7	509.8	512.9	518.1	522.2	524.3	527.4	531.5	536.7
172.5°	507.1	508.1	510.1	511.4	512.9	517.2	520.6	520.9	522.5	525.8	529.2
175°	510.8	511.8	512.9	512.9	512.9	516.0	518.1	517.0	517.0	518.1	521.2
177.5°	513.1	513.1	513.9	513.1	513.1	514.8	515.6	513.9	513.9	514.8	515.6
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.4	485.4	485.4	485.4	485.4	485.4	485.4
2.5°	507.7	509.0	511.8	510.9	512.1	512.8	513.4
5°	548.7	555.3	558.2	557.8	562.1	561.1	560.0
7.5°	595.0	601.9	605.8	610.6	613.4	613.7	616.1
10°	621.3	630.3	634.0	639.2	642.5	644.4	644.1
12.5°	641.3	648.5	656.7	659.2	663.7	666.1	665.2
15°	665.6	676.9	685.5	689.8	695.4	697.1	699.3
17.5°	687.2	702.3	712.4	725.9	730.9	734.1	732.2
20°	703.5	723.4	733.5	749.6	758.5	763.2	761.5
22.5°	722.7	744.4	763.0	776.9	790.4	796.8	798.2
25°	755.8	785.4	812.9	831.2	847.8	851.8	860.4
27.5°	792.7	827.7	857.0	876.3	887.9	892.2	895.0
30°	815.9	850.8	872.8	885.2	888.9	888.5	888.1
32.5°	827.3	849.1	853.4	849.9	841.4	834.2	826.7
35°	811.2	795.0	770.6	739.3	716.2	692.9	690.6
37.5°	729.6	677.5	637.0	591.8	565.8	549.7	538.5
40°	652.7	593.6	544.6	506.5	479.9	469.4	459.1
42.5°	569.4	512.8	469.4	437.6	417.6	405.9	397.8
45°	462.5	412.7	378.7	355.6	339.7	330.7	325.6
47.5°	379.1	342.1	313.3	296.6	285.7	278.7	278.7
50°	334.2	299.0	279.8	266.6	257.2	251.6	252.6
52.5°	294.4	268.1	251.8	240.8	233.7	230.3	230.2
55°	246.2	227.3	216.6	208.5	203.8	199.8	200.7
57.5°	210.6	194.7	187.4	180.7	177.5	175.9	173.6
60°	188.5	176.2	170.0	164.6	161.3	160.1	157.8
62.5°	168.9	159.2	153.2	148.8	145.9	145.4	143.7
65°	142.0	134.6	129.2	127.2	124.0	123.2	123.2
67.5°	117.0	111.7	107.5	105.7	104.3	104.5	103.5
70°	101.4	97.0	94.3	92.3	91.3	91.5	90.7
72.5°	88.7	83.8	81.5	80.3	78.9	79.5	79.1
75°	67.1	64.7	63.5	62.2	61.4	61.0	60.5
77.5°	49.3	47.2	46.2	45.5	45.7	44.6	45.4
80°	38.1	36.3	35.7	34.6	34.4	34.4	34.2
82.5°	27.9	26.8	26.4	25.6	25.1	25.5	25.0
85°	14.4	13.6	13.4	13.4	13.0	12.6	13.6
87.5°	9.2	8.7	9.2	9.0	9.0	9.1	8.7
90°	19.7	20.7	22.8	22.8	22.8	23.8	23.8
92.5°	133.2	100.3	85.0	71.7	69.2	67.8	66.1
95°	587.5	460.0	373.0	299.4	268.3	260.1	243.5
97.5°	999.1	874.9	753.9	689.8	631.9	601.8	588.5
100°	1223.7	1117.0	1009.1	937.7	863.1	824.7	808.2
102.5°	1361.3	1310.1	1237.2	1160.7	1107.6	1066.0	1053.6
105°	1439.2	1484.8	1473.4	1440.2	1406.0	1385.3	1372.9
107.5°	1369.8	1486.8	1541.0	1557.7	1557.6	1550.7	1542.4
110°	1291.0	1437.1	1525.2	1571.8	1591.5	1598.7	1598.7



TEST NUMBER: P333153-940

CATALOG NUMBER: S125DIP-S375D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1213.1	1360.8	1464.6	1532.9	1566.6	1584.7	1592.1
115°	1101.4	1243.3	1356.3	1437.1	1486.8	1515.8	1529.3
117.5°	1024.1	1146.4	1250.0	1330.8	1382.2	1411.0	1419.2
120°	980.2	1094.1	1185.4	1262.0	1311.7	1339.7	1348.0
122.5°	948.7	1050.3	1135.6	1204.0	1249.6	1277.6	1285.0
125°	906.6	996.8	1071.4	1129.4	1171.9	1194.6	1205.1
127.5°	866.4	950.6	1020.4	1073.0	1110.5	1132.1	1136.7
130°	838.2	919.1	986.4	1038.2	1072.4	1093.1	1099.3
132.5°	811.7	885.0	949.9	1001.7	1035.9	1055.0	1062.0
135°	770.9	837.2	896.3	941.8	976.1	994.7	1000.9
137.5°	734.4	789.5	839.7	880.5	911.6	928.8	935.6
140°	712.8	760.5	804.1	842.4	869.3	884.8	890.0
142.5°	694.6	735.7	773.4	805.9	828.7	843.4	847.7
145°	671.4	703.6	731.5	756.3	774.0	785.4	789.5
147.5°	652.1	676.8	697.9	717.6	731.7	738.3	740.2
150°	641.4	661.0	679.7	695.3	707.7	711.9	712.8
152.5°	630.6	648.6	663.2	676.2	686.1	690.3	691.3
155°	614.4	628.9	640.3	650.7	657.9	661.0	662.1
157.5°	599.1	610.3	619.2	627.2	633.3	636.1	636.0
160°	587.5	597.8	605.1	612.3	617.5	619.6	618.6
162.5°	577.6	586.2	592.6	598.2	602.6	603.1	602.8
165°	562.6	568.8	574.0	578.2	580.2	580.2	580.2
167.5°	548.1	552.9	556.6	558.7	560.5	559.7	559.5
170°	539.8	543.0	545.0	547.1	548.1	548.1	547.1
172.5°	532.4	534.7	535.9	536.3	538.1	536.5	535.5
175°	521.2	523.3	523.3	523.3	524.3	522.2	521.2
177.5°	516.4	516.4	516.4	515.6	516.4	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9

(END OF REPORT)