

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333162-940

Luminaire Tested: **S125DIP-S610D365U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333162-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D365U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3425.1 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56
2	93	85	79	74	87	81	75	70	72	67	64	63	60	57	56	53	51	47
3	85	75	68	62	80	71	65	59	63	58	54	56	52	49	50	46	44	40
4	78	67	59	53	73	63	56	50	57	51	46	50	46	42	44	41	38	35
5	71	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	45	40	62	51	43	38	46	40	35	41	36	32	36	32	29	27
7	61	49	40	35	57	46	39	34	42	35	31	37	32	29	33	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	31	26	23	21
9	53	40	33	28	50	39	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5154	5154	5154	5154
5°	5969	5172	4528	5172
10°	6944	5145	3968	5145
15°	7687	5107	3660	5107
20°	8605	5047	3413	5047
25°	10080	4980	3293	4980
30°	10888	4914	3188	4914
35°	8952	4788	3120	4788
40°	6363	4615	3044	4615
45°	4888	4381	3001	4381
50°	4173	4091	2995	4091
55°	3715	3806	3021	3806
60°	3352	3495	3099	3495
65°	3096	3183	3177	3183
70°	2814	2859	3225	2859
75°	2485	2518	3194	2518
80°	2094	2053	2923	2053
85°	1660	1482	2356	1482



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	2.2
10°-20°	228.8	6.7
20°-30°	371.4	10.8
30°-40°	453.1	13.2
40°-50°	412.2	12.0
50°-60°	328.3	9.6
60°-70°	228.7	6.7
70°-80°	121.9	3.6
80°-90°	31.6	0.9
90°-100°	113.3	3.3
100°-110°	243.6	7.1
110°-120°	228.6	6.7
120°-130°	185.2	5.4
130°-140°	148.7	4.3
140°-150°	112.2	3.3
150°-160°	79.0	2.3
160°-170°	46.5	1.4
170°-180°	15.1	0.4
0°-30°	677.0	19.8
0°-40°	1130.1	33.0
0°-60°	1870.6	54.6
0°-90°	2252.9	65.8
90°-120°	585.4	17.1
90°-150°	1031.5	30.1
90°-180°	1172.0	34.2
0°-180°	3425.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	921	798	698	798	921	93
15°	1150	764	547	764	1150	329
25°	1415	699	462	699	1415	646
35°	1135	607	396	607	1135	695
45°	535	480	329	480	535	428
55°	330	338	268	338	330	297
65°	203	208	208	208	203	201
75°	100	101	128	101	100	107
85°	22	20	32	20	22	26
90°	7	0	7	0	7	6
95°	74	10	74	10	74	105
105°	418	36	418	36	418	415
115°	465	64	465	64	465	454
125°	366	88	366	88	366	332
135°	304	103	304	103	304	236
145°	240	120	240	120	240	153
155°	201	137	201	137	201	94
165°	176	150	176	150	176	50
175°	158	156	158	156	158	15
180°	156	156	156	156	156	



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	844.2	843.0	842.0	839.8	841.4	836.8	834.6	830.9	826.3	824.7	822.7
5°	920.7	922.4	924.1	916.9	917.7	912.9	902.1	893.2	886.2	877.0	870.6
7.5°	1012.8	1008.8	1008.5	1003.9	996.0	989.6	978.2	963.7	949.7	933.7	920.5
10°	1058.9	1059.3	1056.2	1050.8	1042.3	1036.2	1021.3	1007.1	989.8	969.5	954.9
12.5°	1093.6	1095.0	1091.2	1083.9	1079.7	1066.0	1054.4	1037.4	1016.9	1000.7	978.5
15°	1149.7	1145.9	1143.3	1134.1	1126.9	1112.8	1094.1	1076.5	1054.2	1033.5	1012.8
17.5°	1203.7	1206.8	1201.7	1193.3	1171.3	1154.6	1129.6	1105.5	1077.6	1050.0	1025.3
20°	1252.0	1254.7	1246.9	1232.3	1205.9	1189.3	1156.5	1125.2	1093.1	1057.6	1030.5
22.5°	1312.2	1310.0	1299.5	1277.3	1254.5	1223.7	1188.2	1150.2	1109.9	1069.7	1033.7
25°	1414.6	1400.3	1393.9	1366.5	1336.3	1291.3	1242.5	1187.0	1136.8	1083.6	1037.6
27.5°	1471.3	1466.9	1459.7	1440.6	1408.9	1360.8	1303.2	1235.6	1164.8	1097.7	1037.3
30°	1460.0	1460.6	1461.3	1455.2	1434.9	1398.6	1341.4	1268.5	1184.5	1109.0	1039.3
32.5°	1359.1	1371.5	1383.3	1397.2	1402.9	1396.0	1360.1	1294.3	1207.9	1122.0	1038.1
35°	1135.4	1139.2	1177.5	1215.4	1266.9	1306.9	1333.6	1304.5	1231.6	1133.1	1036.9
37.5°	885.3	903.7	930.1	973.0	1047.3	1113.8	1199.4	1238.8	1215.2	1136.7	1034.5
40°	754.7	771.7	788.9	832.6	895.3	975.9	1073.1	1156.1	1175.5	1125.2	1026.4
42.5°	653.9	667.4	686.5	719.3	771.7	843.1	936.0	1044.5	1111.2	1092.3	1009.3
45°	535.2	543.7	558.6	584.7	622.6	678.5	760.5	879.0	982.3	1016.6	968.8
47.5°	458.1	458.1	469.7	487.7	515.1	562.5	623.1	716.0	826.3	908.0	904.2
50°	415.3	413.6	422.8	438.4	460.0	491.5	549.5	623.7	729.7	822.2	847.8
52.5°	378.4	378.6	384.2	395.7	413.9	440.9	484.1	551.0	641.6	736.5	785.0
55°	329.9	328.6	335.0	342.8	356.1	373.6	404.8	455.9	529.4	622.9	685.9
57.5°	285.5	289.2	291.8	297.2	308.2	319.9	346.3	383.8	442.1	522.4	589.0
60°	259.5	263.2	265.2	270.6	279.5	289.6	310.0	340.5	389.6	458.7	524.7
62.5°	236.1	239.1	239.8	244.6	251.8	261.7	277.7	303.3	342.1	402.5	467.3
65°	202.6	202.6	203.9	209.0	212.4	221.2	233.4	252.0	283.2	330.3	385.5
67.5°	170.1	171.8	171.5	173.7	176.8	183.7	192.4	207.8	230.9	265.2	309.4
70°	149.0	150.4	150.1	151.8	155.2	159.5	166.7	181.2	197.8	227.3	265.2
72.5°	130.1	130.6	129.7	132.0	134.0	137.9	145.8	153.6	169.1	193.9	225.2
75°	99.6	100.2	100.9	102.3	104.3	106.4	110.4	118.2	128.4	147.0	167.0
77.5°	74.6	73.4	75.0	74.8	76.0	77.5	81.1	85.2	93.5	105.3	120.8
80°	56.3	56.5	56.5	56.9	58.6	59.7	62.7	65.7	72.1	81.0	91.8
82.5°	41.0	41.9	41.4	42.0	43.4	44.1	45.8	48.3	52.1	59.0	66.9
85°	22.4	20.7	21.3	22.0	22.0	22.4	23.7	24.7	26.8	29.4	32.5
87.5°	7.9	8.5	8.7	8.7	9.0	8.8	9.9	9.8	10.5	11.3	12.3
90°	7.2	7.2	7.0	7.0	7.0	6.3	6.0	5.7	5.4	5.1	4.4
92.5°	20.1	20.6	21.0	21.8	25.9	30.5	40.5	55.8	82.2	101.6	103.3
95°	74.1	79.1	81.6	91.0	113.4	139.9	178.7	226.6	273.2	279.2	227.8
97.5°	179.0	183.1	192.2	209.8	229.3	266.1	303.9	337.4	345.7	298.2	203.5
100°	245.8	250.8	262.5	285.2	306.9	339.7	372.2	387.6	363.4	284.5	181.6
102.5°	320.5	324.2	336.9	353.0	376.3	398.5	414.0	404.5	352.8	260.6	164.9
105°	417.6	421.3	427.7	438.0	448.2	451.6	437.7	394.6	319.0	228.5	148.7
107.5°	469.1	471.6	473.8	473.8	468.7	452.2	416.6	359.0	284.4	206.3	142.0
110°	486.2	486.2	484.0	478.0	463.9	437.1	392.7	332.8	264.7	196.0	139.9



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.3	482.0	476.5	466.2	445.5	413.9	369.0	312.1	250.1	189.9	139.9
115°	465.1	461.0	452.2	437.1	412.5	378.2	335.0	286.1	234.2	183.4	140.9
117.5°	431.7	429.2	420.4	404.7	380.2	348.7	311.5	269.4	224.6	180.2	142.9
120°	410.0	407.5	399.0	383.9	360.5	332.8	298.1	260.3	219.4	178.7	145.0
122.5°	390.8	388.6	380.0	366.2	345.4	319.4	288.6	253.5	214.8	177.5	146.7
125°	366.5	363.4	356.4	343.5	325.8	303.2	275.7	243.6	208.7	175.8	149.7
127.5°	345.7	344.3	337.8	326.4	310.3	289.1	263.5	233.5	203.0	175.1	153.0
130°	334.4	332.5	326.2	315.8	300.1	279.6	254.9	227.2	199.2	174.6	155.1
132.5°	323.0	320.8	315.0	304.7	288.9	269.2	246.9	220.9	196.2	174.6	157.3
135°	304.4	302.6	296.9	286.5	272.6	254.7	234.4	212.8	192.5	174.6	160.4
137.5°	284.5	282.5	277.2	267.8	255.4	240.1	223.4	205.8	189.3	175.0	163.3
140°	270.7	269.1	264.4	256.2	244.5	231.3	216.8	202.0	187.8	175.2	164.5
142.5°	257.9	256.5	252.1	245.1	235.2	223.7	211.2	198.8	186.5	175.5	165.2
145°	240.1	238.9	235.4	230.1	222.5	214.0	204.2	194.5	184.7	175.2	166.0
147.5°	225.2	224.5	222.6	218.3	212.3	205.9	198.3	190.4	182.7	174.4	166.4
150°	216.8	216.5	215.3	211.4	206.7	201.1	195.1	188.2	181.2	173.6	166.4
152.5°	210.3	209.9	208.7	205.6	201.7	197.2	191.8	185.7	179.4	172.6	166.1
155°	201.3	201.1	200.1	197.9	194.7	191.3	186.9	181.8	176.5	170.9	165.4
157.5°	193.4	193.5	192.6	190.8	188.3	185.7	182.2	178.1	173.7	168.9	164.6
160°	188.2	188.4	187.8	186.3	184.0	181.8	178.7	175.6	171.5	167.6	163.9
162.5°	183.3	183.4	183.2	182.0	180.3	178.3	175.7	172.7	169.4	166.1	163.1
165°	176.5	176.5	176.5	175.8	174.6	173.0	171.1	168.9	166.4	163.9	162.0
167.5°	170.1	170.2	170.5	170.0	169.3	168.2	166.7	165.2	163.5	161.7	160.2
170°	166.4	166.7	166.7	166.4	165.8	165.1	164.2	163.3	161.7	160.4	159.4
172.5°	162.8	163.2	163.7	163.1	163.0	162.6	161.9	161.0	159.9	158.9	158.5
175°	158.5	158.8	159.4	159.2	159.2	159.2	158.5	158.5	157.6	157.3	157.3
177.5°	156.3	156.3	157.0	156.9	157.0	157.0	157.0	156.9	156.6	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	821.1	819.2	817.1	813.2	808.6	806.2	802.5	800.0	795.0	791.0	786.7
5°	862.7	854.0	845.9	835.4	823.9	816.4	807.5	797.7	787.6	777.0	765.5
7.5°	905.9	890.4	873.4	855.2	837.4	821.0	805.3	790.0	775.6	758.2	743.5
10°	935.0	915.3	894.3	869.5	845.5	824.5	803.2	784.5	765.5	745.2	727.3
12.5°	963.9	937.7	908.1	880.9	852.0	826.7	801.6	777.8	753.9	731.4	710.5
15°	984.4	961.4	933.9	895.3	862.7	827.9	794.7	763.8	735.0	710.0	683.6
17.5°	997.8	968.2	938.7	901.7	859.1	820.0	782.4	747.2	714.7	682.9	657.5
20°	1000.3	969.8	939.0	902.8	859.1	814.3	776.8	734.4	699.5	666.6	635.4
22.5°	999.5	964.9	931.4	894.0	851.5	810.3	764.8	721.7	683.8	651.5	618.9
25°	991.8	954.9	912.9	875.3	833.3	789.6	743.5	698.8	660.2	623.3	591.1
27.5°	985.4	937.5	890.0	846.1	805.6	765.5	721.5	675.6	632.8	595.4	565.1
30°	977.6	925.1	871.6	825.8	784.2	745.2	703.6	658.9	614.1	577.6	545.0
32.5°	970.5	909.4	852.9	803.1	759.0	721.1	682.7	640.2	596.3	559.1	526.6
35°	957.0	886.2	821.4	765.2	718.1	679.2	647.0	607.3	567.0	531.1	500.0
37.5°	939.7	855.7	786.2	727.3	675.6	634.6	604.7	574.3	535.6	501.0	472.8
40°	926.1	834.0	760.5	700.2	646.7	604.0	576.2	547.4	515.2	483.0	453.3
42.5°	909.0	814.5	734.4	669.6	616.6	575.0	545.8	521.4	493.0	463.0	435.3
45°	877.7	779.1	692.4	622.6	569.1	528.1	497.9	479.7	458.3	429.9	406.5
47.5°	831.5	736.6	646.9	574.9	519.7	481.7	453.4	435.9	420.9	399.8	378.5
50°	790.6	704.9	614.1	542.7	487.4	449.2	423.1	407.2	394.3	378.0	360.1
52.5°	744.8	665.0	581.9	511.2	456.6	418.8	393.2	379.2	368.5	356.9	339.2
55°	672.1	604.3	527.1	460.0	409.6	372.6	350.3	338.0	329.2	320.5	309.6
57.5°	591.9	539.0	470.5	409.2	362.7	329.1	308.3	296.4	289.5	285.0	278.7
60°	535.6	490.2	431.2	375.3	329.9	300.1	279.8	270.6	264.9	261.2	256.5
62.5°	483.2	445.9	391.4	340.4	300.7	272.5	254.3	245.5	240.0	238.2	234.2
65°	406.2	377.4	332.3	290.0	256.1	232.0	216.8	208.3	204.9	202.9	203.2
67.5°	330.2	312.6	276.5	240.4	213.3	193.1	180.9	174.4	172.7	170.0	170.0
70°	283.8	270.6	240.1	208.7	184.6	169.1	158.2	151.4	149.7	148.4	148.0
72.5°	242.9	231.4	204.9	179.7	158.1	144.4	135.5	131.3	128.6	127.8	127.7
75°	182.6	176.1	155.2	135.2	120.3	110.8	104.7	100.9	98.9	98.5	98.9
77.5°	129.8	124.2	110.8	96.7	87.3	80.1	74.9	73.7	71.3	71.4	71.1
80°	97.6	93.8	85.3	74.2	66.4	60.3	57.6	55.2	54.6	53.5	54.6
82.5°	70.7	66.7	61.0	53.9	47.4	43.8	41.0	40.3	39.9	39.4	39.6
85°	34.9	35.2	31.8	26.4	23.7	21.7	20.0	20.0	19.6	19.4	19.6
87.5°	12.8	12.0	11.0	10.0	8.5	7.6	7.1	7.4	6.6	6.5	6.9
90°	4.1	3.5	3.1	2.5	1.9	1.2	0.6	0.4	0.6	1.2	1.9
92.5°	71.9	43.1	25.9	16.7	11.2	7.3	4.6	3.8	4.6	7.3	11.2
95°	140.9	71.5	37.8	23.6	16.7	13.2	10.7	10.4	10.7	13.2	16.7
97.5°	112.4	61.6	39.3	29.2	22.9	19.4	17.7	17.3	17.7	19.4	22.9
100°	102.1	61.2	42.9	33.4	27.4	24.0	22.6	22.0	22.6	24.0	27.4
102.5°	97.8	63.4	47.2	38.0	32.5	28.7	27.7	27.4	27.7	28.7	32.5
105°	96.1	68.0	54.2	45.4	40.3	37.2	35.6	35.6	35.6	37.2	40.3
107.5°	99.0	75.0	61.6	53.7	48.4	45.8	44.3	43.7	44.3	45.8	48.4
110°	101.8	80.1	67.1	58.9	54.2	51.4	50.1	49.5	50.1	51.4	54.2



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	105.3	84.8	72.4	64.5	59.7	56.9	55.9	55.3	55.9	56.9	59.7
115°	110.6	92.4	80.7	72.8	68.0	65.3	64.3	63.7	64.3	65.3	68.0
117.5°	116.6	100.0	89.0	81.4	76.0	73.2	72.1	71.2	72.1	73.2	76.0
120°	120.7	105.6	94.5	86.7	81.3	78.5	77.2	76.2	77.2	78.5	81.3
122.5°	125.2	110.8	99.9	91.9	86.1	83.3	82.2	81.6	82.2	83.3	86.1
125°	131.4	117.9	107.5	99.2	93.3	90.4	88.9	88.3	88.9	90.4	93.3
127.5°	137.1	124.6	114.6	106.4	100.0	96.4	94.4	93.5	94.4	96.4	100.0
130°	140.9	128.9	119.1	110.9	104.3	100.2	97.7	96.8	97.7	100.2	104.3
132.5°	144.2	133.0	123.1	114.9	108.1	103.5	100.5	99.2	100.5	103.5	108.1
135°	148.7	138.3	128.6	120.1	113.4	108.4	104.6	103.3	104.6	108.4	113.4
137.5°	152.1	142.2	133.3	124.6	118.1	113.0	109.5	108.5	109.5	113.0	118.1
140°	154.4	145.0	135.8	127.3	121.4	116.3	112.5	111.6	112.5	116.3	121.4
142.5°	155.7	146.7	138.1	130.1	124.4	119.3	115.7	115.1	115.7	119.3	124.4
145°	157.6	149.7	141.5	134.3	128.6	124.1	121.0	120.4	121.0	124.1	128.6
147.5°	158.7	151.6	144.4	138.0	133.1	129.0	126.3	125.9	126.3	129.0	133.1
150°	159.4	152.8	145.9	140.5	136.2	132.1	129.8	129.2	129.8	132.1	136.2
152.5°	160.0	154.1	147.7	142.9	138.7	135.1	133.1	132.8	133.1	135.1	138.7
155°	160.4	155.3	150.0	145.6	142.4	139.3	137.4	137.4	137.4	139.3	142.4
157.5°	160.7	156.4	151.9	148.5	145.7	143.0	141.5	141.6	141.5	143.0	145.7
160°	160.7	156.9	152.8	150.0	147.5	145.3	144.0	144.4	144.0	145.3	147.5
162.5°	160.5	157.5	153.8	151.5	149.5	147.6	146.3	146.6	146.3	147.6	149.5
165°	160.1	157.6	155.1	153.2	151.9	150.3	149.4	150.0	149.4	150.3	151.9
167.5°	159.3	157.6	155.5	154.3	153.4	152.6	151.9	152.3	151.9	152.6	153.4
170°	158.8	157.6	156.0	155.1	154.4	153.8	153.5	153.8	153.5	153.8	154.4
172.5°	158.4	157.3	156.0	155.5	155.2	154.5	154.3	154.8	154.3	154.5	155.2
175°	157.6	156.9	156.0	156.0	156.0	155.7	155.3	156.0	155.3	155.7	156.0
177.5°	156.9	156.6	156.0	156.0	156.3	156.0	156.0	156.6	156.0	156.0	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	784.3	781.2	778.8	773.4	770.4	766.3	763.1	766.6	762.9	764.5	762.1
5°	759.8	750.3	743.5	733.7	725.2	717.5	711.7	710.7	707.9	706.6	702.6
7.5°	730.4	718.5	706.9	694.0	683.1	672.2	665.0	659.2	655.4	650.3	646.8
10°	713.0	697.1	683.6	668.0	654.4	642.6	633.1	628.4	623.9	617.5	615.2
12.5°	691.6	675.2	658.6	641.9	629.0	615.7	607.6	600.5	597.4	590.1	589.4
15°	665.9	641.2	625.0	608.1	590.0	579.3	572.5	564.7	561.3	556.2	552.5
17.5°	635.3	613.2	592.9	575.4	560.0	550.9	542.4	537.1	531.3	528.0	521.8
20°	613.1	592.1	571.8	553.1	541.3	530.8	524.1	519.0	512.8	511.1	505.1
22.5°	594.4	571.2	551.7	536.1	523.2	511.3	504.0	500.5	496.3	491.1	489.9
25°	564.0	539.9	523.3	507.7	496.2	485.4	480.4	475.9	471.9	468.1	466.8
27.5°	537.7	516.2	496.5	482.4	472.4	462.5	458.1	452.7	449.7	446.7	443.1
30°	519.3	497.3	480.0	466.5	455.6	446.8	442.0	438.4	435.6	432.9	430.9
32.5°	500.3	479.9	463.2	450.0	439.1	432.5	428.2	425.6	422.6	419.4	416.8
35°	475.3	452.9	436.7	425.1	416.6	411.5	406.8	404.5	401.1	401.1	398.3
37.5°	447.0	427.7	413.3	402.8	395.2	390.7	385.6	384.0	381.7	380.3	379.4
40°	430.2	412.2	398.7	388.2	380.0	376.3	372.3	369.5	368.2	366.5	365.9
42.5°	412.9	395.7	382.7	373.0	366.0	362.7	359.0	357.1	354.4	352.1	351.8
45°	386.5	369.9	358.0	350.3	344.2	340.5	338.0	334.0	332.6	329.9	329.6
47.5°	361.5	345.5	333.9	327.5	322.2	319.1	315.4	311.4	309.8	308.4	308.4
50°	342.8	328.2	317.4	311.3	306.2	301.8	298.1	295.4	294.4	294.4	295.1
52.5°	323.9	311.5	302.2	294.8	290.0	285.3	281.9	280.2	278.7	280.3	281.5
55°	296.0	283.6	276.8	269.7	264.9	259.5	257.8	257.1	256.1	258.8	260.1
57.5°	266.6	257.9	249.9	242.9	238.6	235.5	233.2	232.8	234.7	235.9	240.4
60°	248.0	237.8	230.7	225.2	220.2	218.1	217.5	216.8	218.1	221.9	227.7
62.5°	227.4	219.1	211.4	207.4	203.7	200.3	200.1	200.5	203.2	207.5	213.3
65°	197.2	190.0	184.9	180.2	177.2	175.1	175.8	177.2	180.2	186.0	192.4
67.5°	166.5	161.6	157.0	153.2	150.3	150.3	151.0	153.0	156.6	163.2	169.1
70°	146.7	141.2	137.5	135.8	133.5	132.2	134.1	137.5	140.5	146.7	151.8
72.5°	126.9	122.3	119.4	118.2	117.2	116.1	116.8	120.5	124.6	130.7	136.6
75°	97.6	95.9	93.8	92.5	91.5	92.1	92.8	96.2	99.6	106.0	112.8
77.5°	71.2	69.5	68.2	67.9	67.3	67.7	69.6	72.1	75.4	80.1	85.2
80°	53.9	53.1	52.5	52.2	52.2	52.5	55.2	56.9	59.9	64.4	68.4
82.5°	39.2	38.8	38.7	38.6	38.9	39.0	40.6	42.8	45.3	48.7	52.2
85°	20.7	20.0	21.0	21.3	20.7	21.7	22.4	23.7	24.7	26.4	28.1
87.5°	7.3	7.9	7.8	8.1	8.2	8.8	8.6	9.8	10.4	11.1	10.9
90°	2.5	3.1	3.5	4.1	4.4	5.1	5.4	5.7	6.0	6.3	7.0
92.5°	16.7	25.9	43.1	71.9	103.3	101.6	82.2	55.8	40.5	30.5	25.9
95°	23.6	37.8	71.5	140.9	227.8	279.2	273.2	226.6	178.7	139.9	113.4
97.5°	29.2	39.3	61.6	112.4	203.5	298.2	345.7	337.4	303.9	266.1	229.3
100°	33.4	42.9	61.2	102.1	181.6	284.5	363.4	387.6	372.2	339.7	306.9
102.5°	38.0	47.2	63.4	97.8	164.9	260.6	352.8	404.5	414.0	398.5	376.3
105°	45.4	54.2	68.0	96.1	148.7	228.5	319.0	394.6	437.7	451.6	448.2
107.5°	53.7	61.6	75.0	99.0	142.0	206.3	284.4	359.0	416.6	452.2	468.7
110°	58.9	67.1	80.1	101.8	139.9	196.0	264.7	332.8	392.7	437.1	463.9



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	64.5	72.4	84.8	105.3	139.9	189.9	250.1	312.1	369.0	413.9	445.5
115°	72.8	80.7	92.4	110.6	140.9	183.4	234.2	286.1	335.0	378.2	412.5
117.5°	81.4	89.0	100.0	116.6	142.9	180.2	224.6	269.4	311.5	348.7	380.2
120°	86.7	94.5	105.6	120.7	145.0	178.7	219.4	260.3	298.1	332.8	360.5
122.5°	91.9	99.9	110.8	125.2	146.7	177.5	214.8	253.5	288.6	319.4	345.4
125°	99.2	107.5	117.9	131.4	149.7	175.8	208.7	243.6	275.7	303.2	325.8
127.5°	106.4	114.6	124.6	137.1	153.0	175.1	203.0	233.5	263.5	289.1	310.3
130°	110.9	119.1	128.9	140.9	155.1	174.6	199.2	227.2	254.9	279.6	300.1
132.5°	114.9	123.1	133.0	144.2	157.3	174.6	196.2	220.9	246.9	269.2	288.9
135°	120.1	128.6	138.3	148.7	160.4	174.6	192.5	212.8	234.4	254.7	272.6
137.5°	124.6	133.3	142.2	152.1	163.3	175.0	189.3	205.8	223.4	240.1	255.4
140°	127.3	135.8	145.0	154.4	164.5	175.2	187.8	202.0	216.8	231.3	244.5
142.5°	130.1	138.1	146.7	155.7	165.2	175.5	186.5	198.8	211.2	223.7	235.2
145°	134.3	141.5	149.7	157.6	166.0	175.2	184.7	194.5	204.2	214.0	222.5
147.5°	138.0	144.4	151.6	158.7	166.4	174.4	182.7	190.4	198.3	205.9	212.3
150°	140.5	145.9	152.8	159.4	166.4	173.6	181.2	188.2	195.1	201.1	206.7
152.5°	142.9	147.7	154.1	160.0	166.1	172.6	179.4	185.7	191.8	197.2	201.7
155°	145.6	150.0	155.3	160.4	165.4	170.9	176.5	181.8	186.9	191.3	194.7
157.5°	148.5	151.9	156.4	160.7	164.6	168.9	173.7	178.1	182.2	185.7	188.3
160°	150.0	152.8	156.9	160.7	163.9	167.6	171.5	175.6	178.7	181.8	184.0
162.5°	151.5	153.8	157.5	160.5	163.1	166.1	169.4	172.7	175.7	178.3	180.3
165°	153.2	155.1	157.6	160.1	162.0	163.9	166.4	168.9	171.1	173.0	174.6
167.5°	154.3	155.5	157.6	159.3	160.2	161.7	163.5	165.2	166.7	168.2	169.3
170°	155.1	156.0	157.6	158.8	159.4	160.4	161.7	163.3	164.2	165.1	165.8
172.5°	155.5	156.0	157.3	158.4	158.5	158.9	159.9	161.0	161.9	162.6	163.0
175°	156.0	156.0	156.9	157.6	157.3	157.3	157.6	158.5	158.5	159.2	159.2
177.5°	156.0	156.0	156.6	156.9	156.3	156.3	156.6	156.9	157.0	157.0	157.0
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	760.4	762.3	760.7	762.9	760.7	762.3	760.4	762.1	764.5	762.9	766.6
5°	700.9	697.8	699.8	698.5	699.8	697.8	700.9	702.6	706.6	707.9	710.7
7.5°	645.9	642.9	639.6	638.0	639.6	642.9	645.9	646.8	650.3	655.4	659.2
10°	611.4	607.7	607.3	605.0	607.3	607.7	611.4	615.2	617.5	623.9	628.4
12.5°	586.2	582.7	578.9	577.9	578.9	582.7	586.2	589.4	590.1	597.4	600.5
15°	550.5	547.8	545.4	547.4	545.4	547.8	550.5	552.5	556.2	561.3	564.7
17.5°	520.7	518.4	518.1	515.6	518.1	518.4	520.7	521.8	528.0	531.3	537.1
20°	502.0	500.3	501.0	496.6	501.0	500.3	502.0	505.1	511.1	512.8	519.0
22.5°	487.1	483.8	483.4	482.5	483.4	483.8	487.1	489.9	491.1	496.3	500.5
25°	463.8	462.1	460.4	462.1	460.4	462.1	463.8	466.8	468.1	471.9	475.9
27.5°	443.4	441.3	440.9	441.0	440.9	441.3	443.4	443.1	446.7	449.7	452.7
30°	430.9	427.5	427.8	427.5	427.8	427.5	430.9	430.9	432.9	435.6	438.4
32.5°	417.3	415.0	414.6	413.9	414.6	415.0	417.3	416.8	419.4	422.6	425.6
35°	397.3	397.3	395.7	395.7	395.7	397.3	397.3	398.3	401.1	401.1	404.5
37.5°	378.5	378.3	377.2	377.4	377.2	378.3	378.5	379.4	380.3	381.7	384.0
40°	364.4	364.2	363.1	361.1	363.1	364.2	364.4	365.9	366.5	368.2	369.5
42.5°	351.0	349.8	349.3	348.7	349.3	349.8	351.0	351.8	352.1	354.4	357.1
45°	329.6	329.6	329.0	328.6	329.0	329.6	329.6	329.6	329.9	332.6	334.0
47.5°	308.9	309.5	310.8	310.6	310.8	309.5	308.9	308.4	308.4	309.8	311.4
50°	296.4	296.8	297.7	298.1	297.7	296.8	296.4	295.1	294.4	294.4	295.4
52.5°	282.6	284.5	285.8	285.6	285.8	284.5	282.6	281.5	280.3	278.7	280.2
55°	263.2	265.6	268.0	268.3	268.0	265.6	263.2	260.1	258.8	256.1	257.1
57.5°	244.1	247.4	249.9	250.7	249.9	247.4	244.1	240.4	235.9	234.7	232.8
60°	231.0	235.4	238.4	239.9	238.4	235.4	231.0	227.7	221.9	218.1	216.8
62.5°	218.6	223.5	226.6	226.9	226.6	223.5	218.6	213.3	207.5	203.2	200.5
65°	198.1	203.2	206.0	207.9	206.0	203.2	198.1	192.4	186.0	180.2	177.2
67.5°	176.2	181.3	184.3	185.9	184.3	181.3	176.2	169.1	163.2	156.6	153.0
70°	160.2	165.3	169.3	170.8	169.3	165.3	160.2	151.8	146.7	140.5	137.5
72.5°	144.5	149.0	152.3	153.9	152.3	149.0	144.5	136.6	130.7	124.6	120.5
75°	117.2	123.3	126.4	128.0	126.4	123.3	117.2	112.8	106.0	99.6	96.2
77.5°	90.4	95.9	97.7	98.6	97.7	95.9	90.4	85.2	80.1	75.4	72.1
80°	72.5	75.9	78.3	78.6	78.3	75.9	72.5	68.4	64.4	59.9	56.9
82.5°	55.7	58.5	59.3	60.2	59.3	58.5	55.7	52.2	48.7	45.3	42.8
85°	30.5	31.8	32.2	31.8	32.2	31.8	30.5	28.1	26.4	24.7	23.7
87.5°	11.4	11.1	11.2	11.8	11.2	11.1	11.4	10.9	11.1	10.4	9.8
90°	7.0	7.0	7.2	7.2	7.2	7.0	7.0	7.0	6.3	6.0	5.7
92.5°	21.8	21.0	20.6	20.1	20.6	21.0	21.8	25.9	30.5	40.5	55.8
95°	91.0	81.6	79.1	74.1	79.1	81.6	91.0	113.4	139.9	178.7	226.6
97.5°	209.8	192.2	183.1	179.0	183.1	192.2	209.8	229.3	266.1	303.9	337.4
100°	285.2	262.5	250.8	245.8	250.8	262.5	285.2	306.9	339.7	372.2	387.6
102.5°	353.0	336.9	324.2	320.5	324.2	336.9	353.0	376.3	398.5	414.0	404.5
105°	438.0	427.7	421.3	417.6	421.3	427.7	438.0	448.2	451.6	437.7	394.6
107.5°	473.8	473.8	471.6	469.1	471.6	473.8	473.8	468.7	452.2	416.6	359.0
110°	478.0	484.0	486.2	486.2	486.2	484.0	478.0	463.9	437.1	392.7	332.8



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	466.2	476.5	482.0	484.3	482.0	476.5	466.2	445.5	413.9	369.0	312.1
115°	437.1	452.2	461.0	465.1	461.0	452.2	437.1	412.5	378.2	335.0	286.1
117.5°	404.7	420.4	429.2	431.7	429.2	420.4	404.7	380.2	348.7	311.5	269.4
120°	383.9	399.0	407.5	410.0	407.5	399.0	383.9	360.5	332.8	298.1	260.3
122.5°	366.2	380.0	388.6	390.8	388.6	380.0	366.2	345.4	319.4	288.6	253.5
125°	343.5	356.4	363.4	366.5	363.4	356.4	343.5	325.8	303.2	275.7	243.6
127.5°	326.4	337.8	344.3	345.7	344.3	337.8	326.4	310.3	289.1	263.5	233.5
130°	315.8	326.2	332.5	334.4	332.5	326.2	315.8	300.1	279.6	254.9	227.2
132.5°	304.7	315.0	320.8	323.0	320.8	315.0	304.7	288.9	269.2	246.9	220.9
135°	286.5	296.9	302.6	304.4	302.6	296.9	286.5	272.6	254.7	234.4	212.8
137.5°	267.8	277.2	282.5	284.5	282.5	277.2	267.8	255.4	240.1	223.4	205.8
140°	256.2	264.4	269.1	270.7	269.1	264.4	256.2	244.5	231.3	216.8	202.0
142.5°	245.1	252.1	256.5	257.9	256.5	252.1	245.1	235.2	223.7	211.2	198.8
145°	230.1	235.4	238.9	240.1	238.9	235.4	230.1	222.5	214.0	204.2	194.5
147.5°	218.3	222.6	224.5	225.2	224.5	222.6	218.3	212.3	205.9	198.3	190.4
150°	211.4	215.3	216.5	216.8	216.5	215.3	211.4	206.7	201.1	195.1	188.2
152.5°	205.6	208.7	209.9	210.3	209.9	208.7	205.6	201.7	197.2	191.8	185.7
155°	197.9	200.1	201.1	201.3	201.1	200.1	197.9	194.7	191.3	186.9	181.8
157.5°	190.8	192.6	193.5	193.4	193.5	192.6	190.8	188.3	185.7	182.2	178.1
160°	186.3	187.8	188.4	188.2	188.4	187.8	186.3	184.0	181.8	178.7	175.6
162.5°	182.0	183.2	183.4	183.3	183.4	183.2	182.0	180.3	178.3	175.7	172.7
165°	175.8	176.5	176.5	176.5	176.5	176.5	175.8	174.6	173.0	171.1	168.9
167.5°	170.0	170.5	170.2	170.1	170.2	170.5	170.0	169.3	168.2	166.7	165.2
170°	166.4	166.7	166.7	166.4	166.7	166.7	166.4	165.8	165.1	164.2	163.3
172.5°	163.1	163.7	163.2	162.8	163.2	163.7	163.1	163.0	162.6	161.9	161.0
175°	159.2	159.4	158.8	158.5	158.8	159.4	159.2	159.2	159.2	158.5	158.5
177.5°	156.9	157.0	156.3	156.3	156.3	157.0	156.9	157.0	157.0	157.0	156.9
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	763.1	766.3	770.4	773.4	778.8	781.2	784.3	786.7	791.0	795.0	800.0
5°	711.7	717.5	725.2	733.7	743.5	750.3	759.8	765.5	777.0	787.6	797.7
7.5°	665.0	672.2	683.1	694.0	706.9	718.5	730.4	743.5	758.2	775.6	790.0
10°	633.1	642.6	654.4	668.0	683.6	697.1	713.0	727.3	745.2	765.5	784.5
12.5°	607.6	615.7	629.0	641.9	658.6	675.2	691.6	710.5	731.4	753.9	777.8
15°	572.5	579.3	590.0	608.1	625.0	641.2	665.9	683.6	710.0	735.0	763.8
17.5°	542.4	550.9	560.0	575.4	592.9	613.2	635.3	657.5	682.9	714.7	747.2
20°	524.1	530.8	541.3	553.1	571.8	592.1	613.1	635.4	666.6	699.5	734.4
22.5°	504.0	511.3	523.2	536.1	551.7	571.2	594.4	618.9	651.5	683.8	721.7
25°	480.4	485.4	496.2	507.7	523.3	539.9	564.0	591.1	623.3	660.2	698.8
27.5°	458.1	462.5	472.4	482.4	496.5	516.2	537.7	565.1	595.4	632.8	675.6
30°	442.0	446.8	455.6	466.5	480.0	497.3	519.3	545.0	577.6	614.1	658.9
32.5°	428.2	432.5	439.1	450.0	463.2	479.9	500.3	526.6	559.1	596.3	640.2
35°	406.8	411.5	416.6	425.1	436.7	452.9	475.3	500.0	531.1	567.0	607.3
37.5°	385.6	390.7	395.2	402.8	413.3	427.7	447.0	472.8	501.0	535.6	574.3
40°	372.3	376.3	380.0	388.2	398.7	412.2	430.2	453.3	483.0	515.2	547.4
42.5°	359.0	362.7	366.0	373.0	382.7	395.7	412.9	435.3	463.0	493.0	521.4
45°	338.0	340.5	344.2	350.3	358.0	369.9	386.5	406.5	429.9	458.3	479.7
47.5°	315.4	319.1	322.2	327.5	333.9	345.5	361.5	378.5	399.8	420.9	435.9
50°	298.1	301.8	306.2	311.3	317.4	328.2	342.8	360.1	378.0	394.3	407.2
52.5°	281.9	285.3	290.0	294.8	302.2	311.5	323.9	339.2	356.9	368.5	379.2
55°	257.8	259.5	264.9	269.7	276.8	283.6	296.0	309.6	320.5	329.2	338.0
57.5°	233.2	235.5	238.6	242.9	249.9	257.9	266.6	278.7	285.0	289.5	296.4
60°	217.5	218.1	220.2	225.2	230.7	237.8	248.0	256.5	261.2	264.9	270.6
62.5°	200.1	200.3	203.7	207.4	211.4	219.1	227.4	234.2	238.2	240.0	245.5
65°	175.8	175.1	177.2	180.2	184.9	190.0	197.2	203.2	202.9	204.9	208.3
67.5°	151.0	150.3	150.3	153.2	157.0	161.6	166.5	170.0	170.0	172.7	174.4
70°	134.1	132.2	133.5	135.8	137.5	141.2	146.7	148.0	148.4	149.7	151.4
72.5°	116.8	116.1	117.2	118.2	119.4	122.3	126.9	127.7	127.8	128.6	131.3
75°	92.8	92.1	91.5	92.5	93.8	95.9	97.6	98.9	98.5	98.9	100.9
77.5°	69.6	67.7	67.3	67.9	68.2	69.5	71.2	71.1	71.4	71.3	73.7
80°	55.2	52.5	52.2	52.2	52.5	53.1	53.9	54.6	53.5	54.6	55.2
82.5°	40.6	39.0	38.9	38.6	38.7	38.8	39.2	39.6	39.4	39.9	40.3
85°	22.4	21.7	20.7	21.3	21.0	20.0	20.7	19.6	19.4	19.6	20.0
87.5°	8.6	8.8	8.2	8.1	7.8	7.9	7.3	6.9	6.5	6.6	7.4
90°	5.4	5.1	4.4	4.1	3.5	3.1	2.5	1.9	1.2	0.6	0.4
92.5°	82.2	101.6	103.3	71.9	43.1	25.9	16.7	11.2	7.3	4.6	3.8
95°	273.2	279.2	227.8	140.9	71.5	37.8	23.6	16.7	13.2	10.7	10.4
97.5°	345.7	298.2	203.5	112.4	61.6	39.3	29.2	22.9	19.4	17.7	17.3
100°	363.4	284.5	181.6	102.1	61.2	42.9	33.4	27.4	24.0	22.6	22.0
102.5°	352.8	260.6	164.9	97.8	63.4	47.2	38.0	32.5	28.7	27.7	27.4
105°	319.0	228.5	148.7	96.1	68.0	54.2	45.4	40.3	37.2	35.6	35.6
107.5°	284.4	206.3	142.0	99.0	75.0	61.6	53.7	48.4	45.8	44.3	43.7
110°	264.7	196.0	139.9	101.8	80.1	67.1	58.9	54.2	51.4	50.1	49.5



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	250.1	189.9	139.9	105.3	84.8	72.4	64.5	59.7	56.9	55.9	55.3
115°	234.2	183.4	140.9	110.6	92.4	80.7	72.8	68.0	65.3	64.3	63.7
117.5°	224.6	180.2	142.9	116.6	100.0	89.0	81.4	76.0	73.2	72.1	71.2
120°	219.4	178.7	145.0	120.7	105.6	94.5	86.7	81.3	78.5	77.2	76.2
122.5°	214.8	177.5	146.7	125.2	110.8	99.9	91.9	86.1	83.3	82.2	81.6
125°	208.7	175.8	149.7	131.4	117.9	107.5	99.2	93.3	90.4	88.9	88.3
127.5°	203.0	175.1	153.0	137.1	124.6	114.6	106.4	100.0	96.4	94.4	93.5
130°	199.2	174.6	155.1	140.9	128.9	119.1	110.9	104.3	100.2	97.7	96.8
132.5°	196.2	174.6	157.3	144.2	133.0	123.1	114.9	108.1	103.5	100.5	99.2
135°	192.5	174.6	160.4	148.7	138.3	128.6	120.1	113.4	108.4	104.6	103.3
137.5°	189.3	175.0	163.3	152.1	142.2	133.3	124.6	118.1	113.0	109.5	108.5
140°	187.8	175.2	164.5	154.4	145.0	135.8	127.3	121.4	116.3	112.5	111.6
142.5°	186.5	175.5	165.2	155.7	146.7	138.1	130.1	124.4	119.3	115.7	115.1
145°	184.7	175.2	166.0	157.6	149.7	141.5	134.3	128.6	124.1	121.0	120.4
147.5°	182.7	174.4	166.4	158.7	151.6	144.4	138.0	133.1	129.0	126.3	125.9
150°	181.2	173.6	166.4	159.4	152.8	145.9	140.5	136.2	132.1	129.8	129.2
152.5°	179.4	172.6	166.1	160.0	154.1	147.7	142.9	138.7	135.1	133.1	132.8
155°	176.5	170.9	165.4	160.4	155.3	150.0	145.6	142.4	139.3	137.4	137.4
157.5°	173.7	168.9	164.6	160.7	156.4	151.9	148.5	145.7	143.0	141.5	141.6
160°	171.5	167.6	163.9	160.7	156.9	152.8	150.0	147.5	145.3	144.0	144.4
162.5°	169.4	166.1	163.1	160.5	157.5	153.8	151.5	149.5	147.6	146.3	146.6
165°	166.4	163.9	162.0	160.1	157.6	155.1	153.2	151.9	150.3	149.4	150.0
167.5°	163.5	161.7	160.2	159.3	157.6	155.5	154.3	153.4	152.6	151.9	152.3
170°	161.7	160.4	159.4	158.8	157.6	156.0	155.1	154.4	153.8	153.5	153.8
172.5°	159.9	158.9	158.5	158.4	157.3	156.0	155.5	155.2	154.5	154.3	154.8
175°	157.6	157.3	157.3	157.6	156.9	156.0	156.0	156.0	155.7	155.3	156.0
177.5°	156.6	156.3	156.3	156.9	156.6	156.0	156.0	156.3	156.0	156.0	156.6
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	802.5	806.2	808.6	813.2	817.1	819.2	821.1	822.7	824.7	826.3	830.9
5°	807.5	816.4	823.9	835.4	845.9	854.0	862.7	870.6	877.0	886.2	893.2
7.5°	805.3	821.0	837.4	855.2	873.4	890.4	905.9	920.5	933.7	949.7	963.7
10°	803.2	824.5	845.5	869.5	894.3	915.3	935.0	954.9	969.5	989.8	1007.1
12.5°	801.6	826.7	852.0	880.9	908.1	937.7	963.9	978.5	1000.7	1016.9	1037.4
15°	794.7	827.9	862.7	895.3	933.9	961.4	984.4	1012.8	1033.5	1054.2	1076.5
17.5°	782.4	820.0	859.1	901.7	938.7	968.2	997.8	1025.3	1050.0	1077.6	1105.5
20°	776.8	814.3	859.1	902.8	939.0	969.8	1000.3	1030.5	1057.6	1093.1	1125.2
22.5°	764.8	810.3	851.5	894.0	931.4	964.9	999.5	1033.7	1069.7	1109.9	1150.2
25°	743.5	789.6	833.3	875.3	912.9	954.9	991.8	1037.6	1083.6	1136.8	1187.0
27.5°	721.5	765.5	805.6	846.1	890.0	937.5	985.4	1037.3	1097.7	1164.8	1235.6
30°	703.6	745.2	784.2	825.8	871.6	925.1	977.6	1039.3	1109.0	1184.5	1268.5
32.5°	682.7	721.1	759.0	803.1	852.9	909.4	970.5	1038.1	1122.0	1207.9	1294.3
35°	647.0	679.2	718.1	765.2	821.4	886.2	957.0	1036.9	1133.1	1231.6	1304.5
37.5°	604.7	634.6	675.6	727.3	786.2	855.7	939.7	1034.5	1136.7	1215.2	1238.8
40°	576.2	604.0	646.7	700.2	760.5	834.0	926.1	1026.4	1125.2	1175.5	1156.1
42.5°	545.8	575.0	616.6	669.6	734.4	814.5	909.0	1009.3	1092.3	1111.2	1044.5
45°	497.9	528.1	569.1	622.6	692.4	779.1	877.7	968.8	1016.6	982.3	879.0
47.5°	453.4	481.7	519.7	574.9	646.9	736.6	831.5	904.2	908.0	826.3	716.0
50°	423.1	449.2	487.4	542.7	614.1	704.9	790.6	847.8	822.2	729.7	623.7
52.5°	393.2	418.8	456.6	511.2	581.9	665.0	744.8	785.0	736.5	641.6	551.0
55°	350.3	372.6	409.6	460.0	527.1	604.3	672.1	685.9	622.9	529.4	455.9
57.5°	308.3	329.1	362.7	409.2	470.5	539.0	591.9	589.0	522.4	442.1	383.8
60°	279.8	300.1	329.9	375.3	431.2	490.2	535.6	524.7	458.7	389.6	340.5
62.5°	254.3	272.5	300.7	340.4	391.4	445.9	483.2	467.3	402.5	342.1	303.3
65°	216.8	232.0	256.1	290.0	332.3	377.4	406.2	385.5	330.3	283.2	252.0
67.5°	180.9	193.1	213.3	240.4	276.5	312.6	330.2	309.4	265.2	230.9	207.8
70°	158.2	169.1	184.6	208.7	240.1	270.6	283.8	265.2	227.3	197.8	181.2
72.5°	135.5	144.4	158.1	179.7	204.9	231.4	242.9	225.2	193.9	169.1	153.6
75°	104.7	110.8	120.3	135.2	155.2	176.1	182.6	167.0	147.0	128.4	118.2
77.5°	74.9	80.1	87.3	96.7	110.8	124.2	129.8	120.8	105.3	93.5	85.2
80°	57.6	60.3	66.4	74.2	85.3	93.8	97.6	91.8	81.0	72.1	65.7
82.5°	41.0	43.8	47.4	53.9	61.0	66.7	70.7	66.9	59.0	52.1	48.3
85°	20.0	21.7	23.7	26.4	31.8	35.2	34.9	32.5	29.4	26.8	24.7
87.5°	7.1	7.6	8.5	10.0	11.0	12.0	12.8	12.3	11.3	10.5	9.8
90°	0.6	1.2	1.9	2.5	3.1	3.5	4.1	4.4	5.1	5.4	5.7
92.5°	4.6	7.3	11.2	16.7	25.9	43.1	71.9	103.3	101.6	82.2	55.8
95°	10.7	13.2	16.7	23.6	37.8	71.5	140.9	227.8	279.2	273.2	226.6
97.5°	17.7	19.4	22.9	29.2	39.3	61.6	112.4	203.5	298.2	345.7	337.4
100°	22.6	24.0	27.4	33.4	42.9	61.2	102.1	181.6	284.5	363.4	387.6
102.5°	27.7	28.7	32.5	38.0	47.2	63.4	97.8	164.9	260.6	352.8	404.5
105°	35.6	37.2	40.3	45.4	54.2	68.0	96.1	148.7	228.5	319.0	394.6
107.5°	44.3	45.8	48.4	53.7	61.6	75.0	99.0	142.0	206.3	284.4	359.0
110°	50.1	51.4	54.2	58.9	67.1	80.1	101.8	139.9	196.0	264.7	332.8



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.9	56.9	59.7	64.5	72.4	84.8	105.3	139.9	189.9	250.1	312.1
115°	64.3	65.3	68.0	72.8	80.7	92.4	110.6	140.9	183.4	234.2	286.1
117.5°	72.1	73.2	76.0	81.4	89.0	100.0	116.6	142.9	180.2	224.6	269.4
120°	77.2	78.5	81.3	86.7	94.5	105.6	120.7	145.0	178.7	219.4	260.3
122.5°	82.2	83.3	86.1	91.9	99.9	110.8	125.2	146.7	177.5	214.8	253.5
125°	88.9	90.4	93.3	99.2	107.5	117.9	131.4	149.7	175.8	208.7	243.6
127.5°	94.4	96.4	100.0	106.4	114.6	124.6	137.1	153.0	175.1	203.0	233.5
130°	97.7	100.2	104.3	110.9	119.1	128.9	140.9	155.1	174.6	199.2	227.2
132.5°	100.5	103.5	108.1	114.9	123.1	133.0	144.2	157.3	174.6	196.2	220.9
135°	104.6	108.4	113.4	120.1	128.6	138.3	148.7	160.4	174.6	192.5	212.8
137.5°	109.5	113.0	118.1	124.6	133.3	142.2	152.1	163.3	175.0	189.3	205.8
140°	112.5	116.3	121.4	127.3	135.8	145.0	154.4	164.5	175.2	187.8	202.0
142.5°	115.7	119.3	124.4	130.1	138.1	146.7	155.7	165.2	175.5	186.5	198.8
145°	121.0	124.1	128.6	134.3	141.5	149.7	157.6	166.0	175.2	184.7	194.5
147.5°	126.3	129.0	133.1	138.0	144.4	151.6	158.7	166.4	174.4	182.7	190.4
150°	129.8	132.1	136.2	140.5	145.9	152.8	159.4	166.4	173.6	181.2	188.2
152.5°	133.1	135.1	138.7	142.9	147.7	154.1	160.0	166.1	172.6	179.4	185.7
155°	137.4	139.3	142.4	145.6	150.0	155.3	160.4	165.4	170.9	176.5	181.8
157.5°	141.5	143.0	145.7	148.5	151.9	156.4	160.7	164.6	168.9	173.7	178.1
160°	144.0	145.3	147.5	150.0	152.8	156.9	160.7	163.9	167.6	171.5	175.6
162.5°	146.3	147.6	149.5	151.5	153.8	157.5	160.5	163.1	166.1	169.4	172.7
165°	149.4	150.3	151.9	153.2	155.1	157.6	160.1	162.0	163.9	166.4	168.9
167.5°	151.9	152.6	153.4	154.3	155.5	157.6	159.3	160.2	161.7	163.5	165.2
170°	153.5	153.8	154.4	155.1	156.0	157.6	158.8	159.4	160.4	161.7	163.3
172.5°	154.3	154.5	155.2	155.5	156.0	157.3	158.4	158.5	158.9	159.9	161.0
175°	155.3	155.7	156.0	156.0	156.0	156.9	157.6	157.3	157.3	157.6	158.5
177.5°	156.0	156.0	156.3	156.0	156.0	156.6	156.9	156.3	156.3	156.6	156.9
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	834.6	836.8	841.4	839.8	842.0	843.0	844.2
5°	902.1	912.9	917.7	916.9	924.1	922.4	920.7
7.5°	978.2	989.6	996.0	1003.9	1008.5	1008.8	1012.8
10°	1021.3	1036.2	1042.3	1050.8	1056.2	1059.3	1058.9
12.5°	1054.4	1066.0	1079.7	1083.9	1091.2	1095.0	1093.6
15°	1094.1	1112.8	1126.9	1134.1	1143.3	1145.9	1149.7
17.5°	1129.6	1154.6	1171.3	1193.3	1201.7	1206.8	1203.7
20°	1156.5	1189.3	1205.9	1232.3	1246.9	1254.7	1252.0
22.5°	1188.2	1223.7	1254.5	1277.3	1299.5	1310.0	1312.2
25°	1242.5	1291.3	1336.3	1366.5	1393.9	1400.3	1414.6
27.5°	1303.2	1360.8	1408.9	1440.6	1459.7	1466.9	1471.3
30°	1341.4	1398.6	1434.9	1455.2	1461.3	1460.6	1460.0
32.5°	1360.1	1396.0	1402.9	1397.2	1383.3	1371.5	1359.1
35°	1333.6	1306.9	1266.9	1215.4	1177.5	1139.2	1135.4
37.5°	1199.4	1113.8	1047.3	973.0	930.1	903.7	885.3
40°	1073.1	975.9	895.3	832.6	788.9	771.7	754.7
42.5°	936.0	843.1	771.7	719.3	686.5	667.4	653.9
45°	760.5	678.5	622.6	584.7	558.6	543.7	535.2
47.5°	623.1	562.5	515.1	487.7	469.7	458.1	458.1
50°	549.5	491.5	460.0	438.4	422.8	413.6	415.3
52.5°	484.1	440.9	413.9	395.7	384.2	378.6	378.4
55°	404.8	373.6	356.1	342.8	335.0	328.6	329.9
57.5°	346.3	319.9	308.2	297.2	291.8	289.2	285.5
60°	310.0	289.6	279.5	270.6	265.2	263.2	259.5
62.5°	277.7	261.7	251.8	244.6	239.8	239.1	236.1
65°	233.4	221.2	212.4	209.0	203.9	202.6	202.6
67.5°	192.4	183.7	176.8	173.7	171.5	171.8	170.1
70°	166.7	159.5	155.2	151.8	150.1	150.4	149.0
72.5°	145.8	137.9	134.0	132.0	129.7	130.6	130.1
75°	110.4	106.4	104.3	102.3	100.9	100.2	99.6
77.5°	81.1	77.5	76.0	74.8	75.0	73.4	74.6
80°	62.7	59.7	58.6	56.9	56.5	56.5	56.3
82.5°	45.8	44.1	43.4	42.0	41.4	41.9	41.0
85°	23.7	22.4	22.0	22.0	21.3	20.7	22.4
87.5°	9.9	8.8	9.0	8.7	8.7	8.5	7.9
90°	6.0	6.3	7.0	7.0	7.0	7.2	7.2
92.5°	40.5	30.5	25.9	21.8	21.0	20.6	20.1
95°	178.7	139.9	113.4	91.0	81.6	79.1	74.1
97.5°	303.9	266.1	229.3	209.8	192.2	183.1	179.0
100°	372.2	339.7	306.9	285.2	262.5	250.8	245.8
102.5°	414.0	398.5	376.3	353.0	336.9	324.2	320.5
105°	437.7	451.6	448.2	438.0	427.7	421.3	417.6
107.5°	416.6	452.2	468.7	473.8	473.8	471.6	469.1
110°	392.7	437.1	463.9	478.0	484.0	486.2	486.2



TEST NUMBER: P333162-940

CATALOG NUMBER: S125DIP-S610D365U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	369.0	413.9	445.5	466.2	476.5	482.0	484.3
115°	335.0	378.2	412.5	437.1	452.2	461.0	465.1
117.5°	311.5	348.7	380.2	404.7	420.4	429.2	431.7
120°	298.1	332.8	360.5	383.9	399.0	407.5	410.0
122.5°	288.6	319.4	345.4	366.2	380.0	388.6	390.8
125°	275.7	303.2	325.8	343.5	356.4	363.4	366.5
127.5°	263.5	289.1	310.3	326.4	337.8	344.3	345.7
130°	254.9	279.6	300.1	315.8	326.2	332.5	334.4
132.5°	246.9	269.2	288.9	304.7	315.0	320.8	323.0
135°	234.4	254.7	272.6	286.5	296.9	302.6	304.4
137.5°	223.4	240.1	255.4	267.8	277.2	282.5	284.5
140°	216.8	231.3	244.5	256.2	264.4	269.1	270.7
142.5°	211.2	223.7	235.2	245.1	252.1	256.5	257.9
145°	204.2	214.0	222.5	230.1	235.4	238.9	240.1
147.5°	198.3	205.9	212.3	218.3	222.6	224.5	225.2
150°	195.1	201.1	206.7	211.4	215.3	216.5	216.8
152.5°	191.8	197.2	201.7	205.6	208.7	209.9	210.3
155°	186.9	191.3	194.7	197.9	200.1	201.1	201.3
157.5°	182.2	185.7	188.3	190.8	192.6	193.5	193.4
160°	178.7	181.8	184.0	186.3	187.8	188.4	188.2
162.5°	175.7	178.3	180.3	182.0	183.2	183.4	183.3
165°	171.1	173.0	174.6	175.8	176.5	176.5	176.5
167.5°	166.7	168.2	169.3	170.0	170.5	170.2	170.1
170°	164.2	165.1	165.8	166.4	166.7	166.7	166.4
172.5°	161.9	162.6	163.0	163.1	163.7	163.2	162.8
175°	158.5	159.2	159.2	159.2	159.4	158.8	158.5
177.5°	157.0	157.0	157.0	156.9	157.0	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3

(END OF REPORT)