

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333171-940

Luminaire Tested: **S125DIP-S610D590U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333171-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4145.4 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	54	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	40	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5154	5154	5154	5154
5°	5969	5172	4528	5172
10°	6944	5145	3968	5145
15°	7687	5107	3660	5107
20°	8605	5047	3413	5047
25°	10080	4980	3293	4980
30°	10888	4914	3188	4914
35°	8952	4788	3120	4788
40°	6363	4615	3044	4615
45°	4888	4381	3001	4381
50°	4173	4091	2995	4091
55°	3715	3806	3021	3806
60°	3352	3495	3099	3495
65°	3096	3183	3177	3183
70°	2814	2859	3225	2859
75°	2485	2518	3194	2518
80°	2094	2053	2923	2053
85°	1660	1482	2356	1482



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.9
10°-20°	228.8	5.5
20°-30°	371.4	9.0
30°-40°	453.1	10.9
40°-50°	412.2	9.9
50°-60°	328.3	7.9
60°-70°	228.7	5.5
70°-80°	121.9	2.9
80°-90°	32.2	0.8
90°-100°	182.9	4.4
100°-110°	393.1	9.5
110°-120°	369.0	8.9
120°-130°	299.0	7.2
130°-140°	240.0	5.8
140°-150°	181.1	4.4
150°-160°	127.5	3.1
160°-170°	75.1	1.8
170°-180°	24.4	0.6
0°-30°	677.0	16.3
0°-40°	1130.1	27.3
0°-60°	1870.6	45.1
0°-90°	2253.4	54.4
90°-120°	945.0	22.8
90°-150°	1665.0	40.2
90°-180°	1892.0	45.6
0°-180°	4145.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	921	798	698	798	921	93
15°	1150	764	547	764	1150	329
25°	1415	699	462	699	1415	646
35°	1135	607	396	607	1135	695
45°	535	480	329	480	535	428
55°	330	338	268	338	330	297
65°	203	208	208	208	203	201
75°	100	101	128	101	100	107
85°	22	20	32	20	22	26
90°	12	0	12	0	12	9
95°	120	17	120	17	120	169
105°	674	58	674	58	674	670
115°	751	103	751	103	751	734
125°	592	142	592	142	592	535
135°	491	167	491	167	491	381
145°	388	194	388	194	388	246
155°	325	222	325	222	325	151
165°	285	242	285	242	285	81
175°	256	252	256	252	256	25
180°	252	252	252	252	252	



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	844.2	843.0	842.0	839.8	841.4	836.8	834.6	830.9	826.3	824.7	822.7
5°	920.7	922.4	924.1	916.9	917.7	912.9	902.1	893.2	886.2	877.0	870.6
7.5°	1012.8	1008.8	1008.5	1003.9	996.0	989.6	978.2	963.7	949.7	933.7	920.5
10°	1058.9	1059.3	1056.2	1050.8	1042.3	1036.2	1021.3	1007.1	989.8	969.5	954.9
12.5°	1093.6	1095.0	1091.2	1083.9	1079.7	1066.0	1054.4	1037.4	1016.9	1000.7	978.5
15°	1149.7	1145.9	1143.3	1134.1	1126.9	1112.8	1094.1	1076.5	1054.2	1033.5	1012.8
17.5°	1203.7	1206.8	1201.7	1193.3	1171.3	1154.6	1129.6	1105.5	1077.6	1050.0	1025.3
20°	1252.0	1254.7	1246.9	1232.3	1205.9	1189.3	1156.5	1125.2	1093.1	1057.6	1030.5
22.5°	1312.2	1310.0	1299.5	1277.3	1254.5	1223.7	1188.2	1150.2	1109.9	1069.7	1033.7
25°	1414.6	1400.3	1393.9	1366.5	1336.3	1291.3	1242.5	1187.0	1136.8	1083.6	1037.6
27.5°	1471.3	1466.9	1459.7	1440.6	1408.9	1360.8	1303.2	1235.6	1164.8	1097.7	1037.3
30°	1460.0	1460.6	1461.3	1455.2	1434.9	1398.6	1341.4	1268.5	1184.5	1109.0	1039.3
32.5°	1359.1	1371.5	1383.3	1397.2	1402.9	1396.0	1360.1	1294.3	1207.9	1122.0	1038.1
35°	1135.4	1139.2	1177.5	1215.4	1266.9	1306.9	1333.6	1304.5	1231.6	1133.1	1036.9
37.5°	885.3	903.7	930.1	973.0	1047.3	1113.8	1199.4	1238.8	1215.2	1136.7	1034.5
40°	754.7	771.7	788.9	832.6	895.3	975.9	1073.1	1156.1	1175.5	1125.2	1026.4
42.5°	653.9	667.4	686.5	719.3	771.7	843.1	936.0	1044.5	1111.2	1092.3	1009.3
45°	535.2	543.7	558.6	584.7	622.6	678.5	760.5	879.0	982.3	1016.6	968.8
47.5°	458.1	458.1	469.7	487.7	515.1	562.5	623.1	716.0	826.3	908.0	904.2
50°	415.3	413.6	422.8	438.4	460.0	491.5	549.5	623.7	729.7	822.2	847.8
52.5°	378.4	378.6	384.2	395.7	413.9	440.9	484.1	551.0	641.6	736.5	785.0
55°	329.9	328.6	335.0	342.8	356.1	373.6	404.8	455.9	529.4	622.9	685.9
57.5°	285.5	289.2	291.8	297.2	308.2	319.9	346.3	383.8	442.1	522.4	589.0
60°	259.5	263.2	265.2	270.6	279.5	289.6	310.0	340.5	389.6	458.7	524.7
62.5°	236.1	239.1	239.8	244.6	251.8	261.7	277.7	303.3	342.1	402.5	467.3
65°	202.6	202.6	203.9	209.0	212.4	221.2	233.4	252.0	283.2	330.3	385.5
67.5°	170.1	171.8	171.5	173.7	176.8	183.7	192.4	207.8	230.9	265.2	309.4
70°	149.0	150.4	150.1	151.8	155.2	159.5	166.7	181.2	197.8	227.3	265.2
72.5°	130.1	130.6	129.7	132.0	134.0	137.9	145.8	153.6	169.1	193.9	225.2
75°	99.6	100.2	100.9	102.3	104.3	106.4	110.4	118.2	128.4	147.0	167.0
77.5°	74.6	73.4	75.0	74.8	76.0	77.5	81.1	85.2	93.5	105.3	120.8
80°	56.3	56.5	56.5	56.9	58.6	59.7	62.7	65.7	72.1	81.0	91.8
82.5°	41.0	41.9	41.4	42.0	43.4	44.1	45.8	48.3	52.1	59.0	66.9
85°	22.4	20.7	21.3	22.0	22.0	22.4	23.7	24.7	26.8	29.4	32.5
87.5°	8.8	9.4	9.5	9.5	9.8	9.6	10.6	10.5	11.2	11.9	12.8
90°	11.7	11.7	11.1	11.1	11.1	10.2	9.6	9.2	8.6	8.1	7.1
92.5°	32.5	33.3	34.0	35.2	41.7	49.2	65.5	90.2	132.8	164.0	166.7
95°	119.6	127.7	131.7	147.0	183.2	225.9	288.4	365.7	441.0	450.7	367.7
97.5°	288.9	295.4	310.1	338.7	370.1	429.5	490.4	544.7	558.0	481.3	328.4
100°	396.7	404.9	423.7	460.3	495.4	548.3	600.7	625.6	586.5	459.3	293.0
102.5°	517.2	523.3	543.8	569.8	607.3	643.1	668.2	652.9	569.4	420.6	266.1
105°	674.0	680.1	690.3	707.0	723.3	728.9	706.5	636.9	514.8	368.8	240.0
107.5°	757.2	761.3	764.6	764.7	756.4	730.0	672.4	579.4	459.1	333.1	229.1
110°	784.9	784.9	781.3	771.6	748.8	705.5	633.8	537.2	427.3	316.4	225.9



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	781.6	777.9	769.1	752.5	719.1	668.1	595.6	503.8	403.7	306.7	225.9
115°	750.8	744.1	730.0	705.5	665.8	610.4	540.7	461.8	377.9	296.0	227.4
117.5°	696.8	692.7	678.6	653.4	613.7	562.8	502.7	434.8	362.6	290.9	230.7
120°	661.7	657.7	644.0	619.6	581.9	537.2	481.2	420.2	354.0	288.4	234.0
122.5°	630.8	627.1	613.4	591.0	557.5	515.6	465.7	409.2	346.7	286.4	236.8
125°	591.6	586.5	575.3	554.5	525.9	489.4	445.1	393.2	336.7	283.8	241.7
127.5°	558.0	555.7	545.2	526.7	501.0	466.6	425.3	376.9	327.6	282.6	247.0
130°	539.7	536.6	526.5	509.7	484.2	451.2	411.5	366.8	321.5	281.8	250.3
132.5°	521.4	517.9	508.5	491.8	466.4	434.5	398.5	356.6	316.6	281.8	254.0
135°	491.3	488.3	479.1	462.4	440.0	411.0	378.4	343.3	310.8	281.8	258.9
137.5°	459.3	455.9	447.5	432.2	412.2	387.6	360.5	332.2	305.6	282.4	263.5
140°	436.9	434.4	426.8	413.6	394.8	373.4	350.0	326.0	303.2	282.9	265.6
142.5°	416.2	414.0	406.8	395.7	379.7	361.1	341.0	320.7	301.1	283.2	266.7
145°	387.6	385.6	380.0	371.3	359.1	345.4	329.6	313.9	298.1	282.9	268.0
147.5°	363.4	362.5	359.2	352.3	342.6	332.3	320.1	307.4	294.9	281.5	268.6
150°	350.0	349.5	347.4	341.3	333.7	324.5	314.9	303.6	292.5	280.3	268.6
152.5°	339.4	338.9	336.8	332.0	325.6	318.4	309.6	299.6	289.6	278.7	268.1
155°	325.0	324.5	323.0	319.4	314.3	308.7	301.7	293.5	284.8	275.7	267.1
157.5°	312.2	312.3	310.9	307.9	304.0	299.6	294.1	287.4	280.4	272.6	265.7
160°	303.6	304.2	303.2	300.6	297.0	293.5	288.4	283.3	276.7	270.6	264.5
162.5°	296.0	296.0	295.9	293.7	291.0	287.8	283.6	278.8	273.5	268.1	263.3
165°	284.8	284.8	284.8	283.8	281.8	279.3	276.2	272.6	268.6	264.5	261.4
167.5°	274.6	274.7	275.2	274.3	273.2	271.4	269.1	266.7	263.8	260.9	258.6
170°	268.6	269.1	269.1	268.6	267.5	266.5	265.0	263.5	260.9	258.9	257.3
172.5°	262.9	263.4	264.2	263.3	263.1	262.4	261.4	259.8	258.1	256.5	255.7
175°	255.8	256.4	257.3	256.9	256.9	256.9	255.8	255.8	254.3	253.8	253.8
177.5°	252.3	252.3	253.5	253.1	253.5	253.5	253.5	253.1	252.7	252.3	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	821.1	819.2	817.1	813.2	808.6	806.2	802.5	800.0	795.0	791.0	786.7
5°	862.7	854.0	845.9	835.4	823.9	816.4	807.5	797.7	787.6	777.0	765.5
7.5°	905.9	890.4	873.4	855.2	837.4	821.0	805.3	790.0	775.6	758.2	743.5
10°	935.0	915.3	894.3	869.5	845.5	824.5	803.2	784.5	765.5	745.2	727.3
12.5°	963.9	937.7	908.1	880.9	852.0	826.7	801.6	777.8	753.9	731.4	710.5
15°	984.4	961.4	933.9	895.3	862.7	827.9	794.7	763.8	735.0	710.0	683.6
17.5°	997.8	968.2	938.7	901.7	859.1	820.0	782.4	747.2	714.7	682.9	657.5
20°	1000.3	969.8	939.0	902.8	859.1	814.3	776.8	734.4	699.5	666.6	635.4
22.5°	999.5	964.9	931.4	894.0	851.5	810.3	764.8	721.7	683.8	651.5	618.9
25°	991.8	954.9	912.9	875.3	833.3	789.6	743.5	698.8	660.2	623.3	591.1
27.5°	985.4	937.5	890.0	846.1	805.6	765.5	721.5	675.6	632.8	595.4	565.1
30°	977.6	925.1	871.6	825.8	784.2	745.2	703.6	658.9	614.1	577.6	545.0
32.5°	970.5	909.4	852.9	803.1	759.0	721.1	682.7	640.2	596.3	559.1	526.6
35°	957.0	886.2	821.4	765.2	718.1	679.2	647.0	607.3	567.0	531.1	500.0
37.5°	939.7	855.7	786.2	727.3	675.6	634.6	604.7	574.3	535.6	501.0	472.8
40°	926.1	834.0	760.5	700.2	646.7	604.0	576.2	547.4	515.2	483.0	453.3
42.5°	909.0	814.5	734.4	669.6	616.6	575.0	545.8	521.4	493.0	463.0	435.3
45°	877.7	779.1	692.4	622.6	569.1	528.1	497.9	479.7	458.3	429.9	406.5
47.5°	831.5	736.6	646.9	574.9	519.7	481.7	453.4	435.9	420.9	399.8	378.5
50°	790.6	704.9	614.1	542.7	487.4	449.2	423.1	407.2	394.3	378.0	360.1
52.5°	744.8	665.0	581.9	511.2	456.6	418.8	393.2	379.2	368.5	356.9	339.2
55°	672.1	604.3	527.1	460.0	409.6	372.6	350.3	338.0	329.2	320.5	309.6
57.5°	591.9	539.0	470.5	409.2	362.7	329.1	308.3	296.4	289.5	285.0	278.7
60°	535.6	490.2	431.2	375.3	329.9	300.1	279.8	270.6	264.9	261.2	256.5
62.5°	483.2	445.9	391.4	340.4	300.7	272.5	254.3	245.5	240.0	238.2	234.2
65°	406.2	377.4	332.3	290.0	256.1	232.0	216.8	208.3	204.9	202.9	203.2
67.5°	330.2	312.6	276.5	240.4	213.3	193.1	180.9	174.4	172.7	170.0	170.0
70°	283.8	270.6	240.1	208.7	184.6	169.1	158.2	151.4	149.7	148.4	148.0
72.5°	242.9	231.4	204.9	179.7	158.1	144.4	135.5	131.3	128.6	127.8	127.7
75°	182.6	176.1	155.2	135.2	120.3	110.8	104.7	100.9	98.9	98.5	98.9
77.5°	129.8	124.2	110.8	96.7	87.3	80.1	74.9	73.7	71.3	71.4	71.1
80°	97.6	93.8	85.3	74.2	66.4	60.3	57.6	55.2	54.6	53.5	54.6
82.5°	70.7	66.7	61.0	53.9	47.4	43.8	41.0	40.3	39.9	39.4	39.6
85°	34.9	35.2	31.8	26.4	23.7	21.7	20.0	20.0	19.6	19.4	19.6
87.5°	13.3	12.5	11.3	10.3	8.7	7.8	7.2	7.4	6.7	6.6	7.1
90°	6.6	5.6	5.1	4.1	3.0	2.1	1.0	0.5	1.0	2.1	3.0
92.5°	116.1	69.5	41.7	26.8	18.1	11.8	7.5	6.2	7.5	11.8	18.1
95°	227.4	115.5	61.1	38.2	26.9	21.4	17.3	16.8	17.3	21.4	26.9
97.5°	181.5	99.5	63.5	47.0	36.9	31.3	28.4	27.9	28.4	31.3	36.9
100°	164.8	98.7	69.2	53.9	44.2	38.7	36.6	35.6	36.6	38.7	44.2
102.5°	157.9	102.4	76.1	61.3	52.4	46.4	44.8	44.1	44.8	46.4	52.4
105°	155.2	109.9	87.5	73.2	65.1	60.0	57.5	57.5	57.5	60.0	65.1
107.5°	159.8	121.1	99.4	86.6	78.1	73.9	71.5	70.5	71.5	73.9	78.1
110°	164.3	129.2	108.3	95.1	87.5	82.9	80.9	79.9	80.9	82.9	87.5



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	170.0	137.0	116.9	104.1	96.5	91.8	90.2	89.3	90.2	91.8	96.5
115°	178.5	149.0	130.2	117.5	109.9	105.3	103.8	102.7	103.8	105.3	109.9
117.5°	188.3	161.5	143.7	131.3	122.7	118.2	116.5	114.9	116.5	118.2	122.7
120°	194.8	170.4	152.6	139.9	131.3	126.6	124.7	123.1	124.7	126.6	131.3
122.5°	202.2	179.0	161.1	148.5	138.9	134.4	132.8	131.6	132.8	134.4	138.9
125°	212.1	190.2	173.4	160.2	150.5	146.0	143.5	142.4	143.5	146.0	150.5
127.5°	221.2	201.1	184.9	171.7	161.5	155.7	152.4	150.9	152.4	155.7	161.5
130°	227.4	208.0	192.3	179.1	168.4	161.8	157.7	156.1	157.7	161.8	168.4
132.5°	232.6	214.5	198.8	185.6	174.5	167.0	162.2	160.2	162.2	167.0	174.5
135°	240.0	223.3	207.5	193.8	183.2	175.0	168.9	166.8	168.9	175.0	183.2
137.5°	245.6	229.5	215.2	201.0	190.6	182.4	176.7	175.2	176.7	182.4	190.6
140°	249.2	234.0	219.3	205.5	195.8	187.7	181.6	180.0	181.6	187.7	195.8
142.5°	251.3	236.8	222.9	210.0	200.7	192.6	186.9	185.7	186.9	192.6	200.7
145°	254.3	241.7	228.4	216.7	207.5	200.4	195.3	194.3	195.3	200.4	207.5
147.5°	256.2	244.7	233.1	222.7	214.8	208.2	203.8	203.2	203.8	208.2	214.8
150°	257.3	246.7	235.5	226.9	219.7	213.1	209.6	208.6	209.6	213.1	219.7
152.5°	258.2	248.7	238.4	230.5	223.8	218.0	214.8	214.3	214.8	218.0	223.8
155°	258.9	250.7	242.1	235.0	229.9	224.8	221.8	221.8	221.8	224.8	229.9
157.5°	259.4	252.5	245.0	239.7	235.2	230.9	228.4	228.5	228.4	230.9	235.2
160°	259.4	253.3	246.7	242.1	238.1	234.5	232.5	233.0	232.5	234.5	238.1
162.5°	259.0	254.1	248.3	244.6	241.3	238.2	236.1	236.7	236.1	238.2	241.3
165°	258.4	254.3	250.3	247.2	245.1	242.6	241.1	242.1	241.1	242.6	245.1
167.5°	257.2	254.3	250.9	249.1	247.6	246.2	245.3	245.8	245.3	246.2	247.6
170°	256.4	254.3	251.8	250.3	249.2	248.3	247.7	248.3	247.7	248.3	249.2
172.5°	255.6	254.0	251.8	251.1	250.5	249.4	249.0	249.9	249.0	249.4	250.5
175°	254.3	253.3	251.8	251.8	251.8	251.3	250.7	251.8	250.7	251.3	251.8
177.5°	253.1	252.7	251.9	251.9	252.3	251.9	251.9	252.7	251.9	251.9	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	784.3	781.2	778.8	773.4	770.4	766.3	763.1	766.6	762.9	764.5	762.1
5°	759.8	750.3	743.5	733.7	725.2	717.5	711.7	710.7	707.9	706.6	702.6
7.5°	730.4	718.5	706.9	694.0	683.1	672.2	665.0	659.2	655.4	650.3	646.8
10°	713.0	697.1	683.6	668.0	654.4	642.6	633.1	628.4	623.9	617.5	615.2
12.5°	691.6	675.2	658.6	641.9	629.0	615.7	607.6	600.5	597.4	590.1	589.4
15°	665.9	641.2	625.0	608.1	590.0	579.3	572.5	564.7	561.3	556.2	552.5
17.5°	635.3	613.2	592.9	575.4	560.0	550.9	542.4	537.1	531.3	528.0	521.8
20°	613.1	592.1	571.8	553.1	541.3	530.8	524.1	519.0	512.8	511.1	505.1
22.5°	594.4	571.2	551.7	536.1	523.2	511.3	504.0	500.5	496.3	491.1	489.9
25°	564.0	539.9	523.3	507.7	496.2	485.4	480.4	475.9	471.9	468.1	466.8
27.5°	537.7	516.2	496.5	482.4	472.4	462.5	458.1	452.7	449.7	446.7	443.1
30°	519.3	497.3	480.0	466.5	455.6	446.8	442.0	438.4	435.6	432.9	430.9
32.5°	500.3	479.9	463.2	450.0	439.1	432.5	428.2	425.6	422.6	419.4	416.8
35°	475.3	452.9	436.7	425.1	416.6	411.5	406.8	404.5	401.1	401.1	398.3
37.5°	447.0	427.7	413.3	402.8	395.2	390.7	385.6	384.0	381.7	380.3	379.4
40°	430.2	412.2	398.7	388.2	380.0	376.3	372.3	369.5	368.2	366.5	365.9
42.5°	412.9	395.7	382.7	373.0	366.0	362.7	359.0	357.1	354.4	352.1	351.8
45°	386.5	369.9	358.0	350.3	344.2	340.5	338.0	334.0	332.6	329.9	329.6
47.5°	361.5	345.5	333.9	327.5	322.2	319.1	315.4	311.4	309.8	308.4	308.4
50°	342.8	328.2	317.4	311.3	306.2	301.8	298.1	295.4	294.4	294.4	295.1
52.5°	323.9	311.5	302.2	294.8	290.0	285.3	281.9	280.2	278.7	280.3	281.5
55°	296.0	283.6	276.8	269.7	264.9	259.5	257.8	257.1	256.1	258.8	260.1
57.5°	266.6	257.9	249.9	242.9	238.6	235.5	233.2	232.8	234.7	235.9	240.4
60°	248.0	237.8	230.7	225.2	220.2	218.1	217.5	216.8	218.1	221.9	227.7
62.5°	227.4	219.1	211.4	207.4	203.7	200.3	200.1	200.5	203.2	207.5	213.3
65°	197.2	190.0	184.9	180.2	177.2	175.1	175.8	177.2	180.2	186.0	192.4
67.5°	166.5	161.6	157.0	153.2	150.3	150.3	151.0	153.0	156.6	163.2	169.1
70°	146.7	141.2	137.5	135.8	133.5	132.2	134.1	137.5	140.5	146.7	151.8
72.5°	126.9	122.3	119.4	118.2	117.2	116.1	116.8	120.5	124.6	130.7	136.6
75°	97.6	95.9	93.8	92.5	91.5	92.1	92.8	96.2	99.6	106.0	112.8
77.5°	71.2	69.5	68.2	67.9	67.3	67.7	69.6	72.1	75.4	80.1	85.2
80°	53.9	53.1	52.5	52.2	52.2	52.5	55.2	56.9	59.9	64.4	68.4
82.5°	39.2	38.8	38.7	38.6	38.9	39.0	40.6	42.8	45.3	48.7	52.2
85°	20.7	20.0	21.0	21.3	20.7	21.7	22.4	23.7	24.7	26.4	28.1
87.5°	7.6	8.3	8.2	8.6	8.7	9.5	9.3	10.5	11.1	11.8	11.7
90°	4.1	5.1	5.6	6.6	7.1	8.1	8.6	9.2	9.6	10.2	11.1
92.5°	26.8	41.7	69.5	116.1	166.7	164.0	132.8	90.2	65.5	49.2	41.7
95°	38.2	61.1	115.5	227.4	367.7	450.7	441.0	365.7	288.4	225.9	183.2
97.5°	47.0	63.5	99.5	181.5	328.4	481.3	558.0	544.7	490.4	429.5	370.1
100°	53.9	69.2	98.7	164.8	293.0	459.3	586.5	625.6	600.7	548.3	495.4
102.5°	61.3	76.1	102.4	157.9	266.1	420.6	569.4	652.9	668.2	643.1	607.3
105°	73.2	87.5	109.9	155.2	240.0	368.8	514.8	636.9	706.5	728.9	723.3
107.5°	86.6	99.4	121.1	159.8	229.1	333.1	459.1	579.4	672.4	730.0	756.4
110°	95.1	108.3	129.2	164.3	225.9	316.4	427.3	537.2	633.8	705.5	748.8



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	104.1	116.9	137.0	170.0	225.9	306.7	403.7	503.8	595.6	668.1	719.1
115°	117.5	130.2	149.0	178.5	227.4	296.0	377.9	461.8	540.7	610.4	665.8
117.5°	131.3	143.7	161.5	188.3	230.7	290.9	362.6	434.8	502.7	562.8	613.7
120°	139.9	152.6	170.4	194.8	234.0	288.4	354.0	420.2	481.2	537.2	581.9
122.5°	148.5	161.1	179.0	202.2	236.8	286.4	346.7	409.2	465.7	515.6	557.5
125°	160.2	173.4	190.2	212.1	241.7	283.8	336.7	393.2	445.1	489.4	525.9
127.5°	171.7	184.9	201.1	221.2	247.0	282.6	327.6	376.9	425.3	466.6	501.0
130°	179.1	192.3	208.0	227.4	250.3	281.8	321.5	366.8	411.5	451.2	484.2
132.5°	185.6	198.8	214.5	232.6	254.0	281.8	316.6	356.6	398.5	434.5	466.4
135°	193.8	207.5	223.3	240.0	258.9	281.8	310.8	343.3	378.4	411.0	440.0
137.5°	201.0	215.2	229.5	245.6	263.5	282.4	305.6	332.2	360.5	387.6	412.2
140°	205.5	219.3	234.0	249.2	265.6	282.9	303.2	326.0	350.0	373.4	394.8
142.5°	210.0	222.9	236.8	251.3	266.7	283.2	301.1	320.7	341.0	361.1	379.7
145°	216.7	228.4	241.7	254.3	268.0	282.9	298.1	313.9	329.6	345.4	359.1
147.5°	222.7	233.1	244.7	256.2	268.6	281.5	294.9	307.4	320.1	332.3	342.6
150°	226.9	235.5	246.7	257.3	268.6	280.3	292.5	303.6	314.9	324.5	333.7
152.5°	230.5	238.4	248.7	258.2	268.1	278.7	289.6	299.6	309.6	318.4	325.6
155°	235.0	242.1	250.7	258.9	267.1	275.7	284.8	293.5	301.7	308.7	314.3
157.5°	239.7	245.0	252.5	259.4	265.7	272.6	280.4	287.4	294.1	299.6	304.0
160°	242.1	246.7	253.3	259.4	264.5	270.6	276.7	283.3	288.4	293.5	297.0
162.5°	244.6	248.3	254.1	259.0	263.3	268.1	273.5	278.8	283.6	287.8	291.0
165°	247.2	250.3	254.3	258.4	261.4	264.5	268.6	272.6	276.2	279.3	281.8
167.5°	249.1	250.9	254.3	257.2	258.6	260.9	263.8	266.7	269.1	271.4	273.2
170°	250.3	251.8	254.3	256.4	257.3	258.9	260.9	263.5	265.0	266.5	267.5
172.5°	251.1	251.8	254.0	255.6	255.7	256.5	258.1	259.8	261.4	262.4	263.1
175°	251.8	251.8	253.3	254.3	253.8	253.8	254.3	255.8	255.8	256.9	256.9
177.5°	251.9	251.9	252.7	253.1	252.3	252.3	252.7	253.1	253.5	253.5	253.5
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	760.4	762.3	760.7	762.9	760.7	762.3	760.4	762.1	764.5	762.9	766.6
5°	700.9	697.8	699.8	698.5	699.8	697.8	700.9	702.6	706.6	707.9	710.7
7.5°	645.9	642.9	639.6	638.0	639.6	642.9	645.9	646.8	650.3	655.4	659.2
10°	611.4	607.7	607.3	605.0	607.3	607.7	611.4	615.2	617.5	623.9	628.4
12.5°	586.2	582.7	578.9	577.9	578.9	582.7	586.2	589.4	590.1	597.4	600.5
15°	550.5	547.8	545.4	547.4	545.4	547.8	550.5	552.5	556.2	561.3	564.7
17.5°	520.7	518.4	518.1	515.6	518.1	518.4	520.7	521.8	528.0	531.3	537.1
20°	502.0	500.3	501.0	496.6	501.0	500.3	502.0	505.1	511.1	512.8	519.0
22.5°	487.1	483.8	483.4	482.5	483.4	483.8	487.1	489.9	491.1	496.3	500.5
25°	463.8	462.1	460.4	462.1	460.4	462.1	463.8	466.8	468.1	471.9	475.9
27.5°	443.4	441.3	440.9	441.0	440.9	441.3	443.4	443.1	446.7	449.7	452.7
30°	430.9	427.5	427.8	427.5	427.8	427.5	430.9	430.9	432.9	435.6	438.4
32.5°	417.3	415.0	414.6	413.9	414.6	415.0	417.3	416.8	419.4	422.6	425.6
35°	397.3	397.3	395.7	395.7	395.7	397.3	397.3	398.3	401.1	401.1	404.5
37.5°	378.5	378.3	377.2	377.4	377.2	378.3	378.5	379.4	380.3	381.7	384.0
40°	364.4	364.2	363.1	361.1	363.1	364.2	364.4	365.9	366.5	368.2	369.5
42.5°	351.0	349.8	349.3	348.7	349.3	349.8	351.0	351.8	352.1	354.4	357.1
45°	329.6	329.6	329.0	328.6	329.0	329.6	329.6	329.6	329.9	332.6	334.0
47.5°	308.9	309.5	310.8	310.6	310.8	309.5	308.9	308.4	308.4	309.8	311.4
50°	296.4	296.8	297.7	298.1	297.7	296.8	296.4	295.1	294.4	294.4	295.4
52.5°	282.6	284.5	285.8	285.6	285.8	284.5	282.6	281.5	280.3	278.7	280.2
55°	263.2	265.6	268.0	268.3	268.0	265.6	263.2	260.1	258.8	256.1	257.1
57.5°	244.1	247.4	249.9	250.7	249.9	247.4	244.1	240.4	235.9	234.7	232.8
60°	231.0	235.4	238.4	239.9	238.4	235.4	231.0	227.7	221.9	218.1	216.8
62.5°	218.6	223.5	226.6	226.9	226.6	223.5	218.6	213.3	207.5	203.2	200.5
65°	198.1	203.2	206.0	207.9	206.0	203.2	198.1	192.4	186.0	180.2	177.2
67.5°	176.2	181.3	184.3	185.9	184.3	181.3	176.2	169.1	163.2	156.6	153.0
70°	160.2	165.3	169.3	170.8	169.3	165.3	160.2	151.8	146.7	140.5	137.5
72.5°	144.5	149.0	152.3	153.9	152.3	149.0	144.5	136.6	130.7	124.6	120.5
75°	117.2	123.3	126.4	128.0	126.4	123.3	117.2	112.8	106.0	99.6	96.2
77.5°	90.4	95.9	97.7	98.6	97.7	95.9	90.4	85.2	80.1	75.4	72.1
80°	72.5	75.9	78.3	78.6	78.3	75.9	72.5	68.4	64.4	59.9	56.9
82.5°	55.7	58.5	59.3	60.2	59.3	58.5	55.7	52.2	48.7	45.3	42.8
85°	30.5	31.8	32.2	31.8	32.2	31.8	30.5	28.1	26.4	24.7	23.7
87.5°	12.3	12.0	12.1	12.7	12.1	12.0	12.3	11.7	11.8	11.1	10.5
90°	11.1	11.1	11.7	11.7	11.7	11.1	11.1	11.1	10.2	9.6	9.2
92.5°	35.2	34.0	33.3	32.5	33.3	34.0	35.2	41.7	49.2	65.5	90.2
95°	147.0	131.7	127.7	119.6	127.7	131.7	147.0	183.2	225.9	288.4	365.7
97.5°	338.7	310.1	295.4	288.9	295.4	310.1	338.7	370.1	429.5	490.4	544.7
100°	460.3	423.7	404.9	396.7	404.9	423.7	460.3	495.4	548.3	600.7	625.6
102.5°	569.8	543.8	523.3	517.2	523.3	543.8	569.8	607.3	643.1	668.2	652.9
105°	707.0	690.3	680.1	674.0	680.1	690.3	707.0	723.3	728.9	706.5	636.9
107.5°	764.7	764.6	761.3	757.2	761.3	764.6	764.7	756.4	730.0	672.4	579.4
110°	771.6	781.3	784.9	784.9	784.9	781.3	771.6	748.8	705.5	633.8	537.2



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	752.5	769.1	777.9	781.6	777.9	769.1	752.5	719.1	668.1	595.6	503.8
115°	705.5	730.0	744.1	750.8	744.1	730.0	705.5	665.8	610.4	540.7	461.8
117.5°	653.4	678.6	692.7	696.8	692.7	678.6	653.4	613.7	562.8	502.7	434.8
120°	619.6	644.0	657.7	661.7	657.7	644.0	619.6	581.9	537.2	481.2	420.2
122.5°	591.0	613.4	627.1	630.8	627.1	613.4	591.0	557.5	515.6	465.7	409.2
125°	554.5	575.3	586.5	591.6	586.5	575.3	554.5	525.9	489.4	445.1	393.2
127.5°	526.7	545.2	555.7	558.0	555.7	545.2	526.7	501.0	466.6	425.3	376.9
130°	509.7	526.5	536.6	539.7	536.6	526.5	509.7	484.2	451.2	411.5	366.8
132.5°	491.8	508.5	517.9	521.4	517.9	508.5	491.8	466.4	434.5	398.5	356.6
135°	462.4	479.1	488.3	491.3	488.3	479.1	462.4	440.0	411.0	378.4	343.3
137.5°	432.2	447.5	455.9	459.3	455.9	447.5	432.2	412.2	387.6	360.5	332.2
140°	413.6	426.8	434.4	436.9	434.4	426.8	413.6	394.8	373.4	350.0	326.0
142.5°	395.7	406.8	414.0	416.2	414.0	406.8	395.7	379.7	361.1	341.0	320.7
145°	371.3	380.0	385.6	387.6	385.6	380.0	371.3	359.1	345.4	329.6	313.9
147.5°	352.3	359.2	362.5	363.4	362.5	359.2	352.3	342.6	332.3	320.1	307.4
150°	341.3	347.4	349.5	350.0	349.5	347.4	341.3	333.7	324.5	314.9	303.6
152.5°	332.0	336.8	338.9	339.4	338.9	336.8	332.0	325.6	318.4	309.6	299.6
155°	319.4	323.0	324.5	325.0	324.5	323.0	319.4	314.3	308.7	301.7	293.5
157.5°	307.9	310.9	312.3	312.2	312.3	310.9	307.9	304.0	299.6	294.1	287.4
160°	300.6	303.2	304.2	303.6	304.2	303.2	300.6	297.0	293.5	288.4	283.3
162.5°	293.7	295.9	296.0	296.0	296.0	295.9	293.7	291.0	287.8	283.6	278.8
165°	283.8	284.8	284.8	284.8	284.8	284.8	283.8	281.8	279.3	276.2	272.6
167.5°	274.3	275.2	274.7	274.6	274.7	275.2	274.3	273.2	271.4	269.1	266.7
170°	268.6	269.1	269.1	268.6	269.1	269.1	268.6	267.5	266.5	265.0	263.5
172.5°	263.3	264.2	263.4	262.9	263.4	264.2	263.3	263.1	262.4	261.4	259.8
175°	256.9	257.3	256.4	255.8	256.4	257.3	256.9	256.9	256.9	255.8	255.8
177.5°	253.1	253.5	252.3	252.3	252.3	253.5	253.1	253.5	253.5	253.5	253.1
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	763.1	766.3	770.4	773.4	778.8	781.2	784.3	786.7	791.0	795.0	800.0
5°	711.7	717.5	725.2	733.7	743.5	750.3	759.8	765.5	777.0	787.6	797.7
7.5°	665.0	672.2	683.1	694.0	706.9	718.5	730.4	743.5	758.2	775.6	790.0
10°	633.1	642.6	654.4	668.0	683.6	697.1	713.0	727.3	745.2	765.5	784.5
12.5°	607.6	615.7	629.0	641.9	658.6	675.2	691.6	710.5	731.4	753.9	777.8
15°	572.5	579.3	590.0	608.1	625.0	641.2	665.9	683.6	710.0	735.0	763.8
17.5°	542.4	550.9	560.0	575.4	592.9	613.2	635.3	657.5	682.9	714.7	747.2
20°	524.1	530.8	541.3	553.1	571.8	592.1	613.1	635.4	666.6	699.5	734.4
22.5°	504.0	511.3	523.2	536.1	551.7	571.2	594.4	618.9	651.5	683.8	721.7
25°	480.4	485.4	496.2	507.7	523.3	539.9	564.0	591.1	623.3	660.2	698.8
27.5°	458.1	462.5	472.4	482.4	496.5	516.2	537.7	565.1	595.4	632.8	675.6
30°	442.0	446.8	455.6	466.5	480.0	497.3	519.3	545.0	577.6	614.1	658.9
32.5°	428.2	432.5	439.1	450.0	463.2	479.9	500.3	526.6	559.1	596.3	640.2
35°	406.8	411.5	416.6	425.1	436.7	452.9	475.3	500.0	531.1	567.0	607.3
37.5°	385.6	390.7	395.2	402.8	413.3	427.7	447.0	472.8	501.0	535.6	574.3
40°	372.3	376.3	380.0	388.2	398.7	412.2	430.2	453.3	483.0	515.2	547.4
42.5°	359.0	362.7	366.0	373.0	382.7	395.7	412.9	435.3	463.0	493.0	521.4
45°	338.0	340.5	344.2	350.3	358.0	369.9	386.5	406.5	429.9	458.3	479.7
47.5°	315.4	319.1	322.2	327.5	333.9	345.5	361.5	378.5	399.8	420.9	435.9
50°	298.1	301.8	306.2	311.3	317.4	328.2	342.8	360.1	378.0	394.3	407.2
52.5°	281.9	285.3	290.0	294.8	302.2	311.5	323.9	339.2	356.9	368.5	379.2
55°	257.8	259.5	264.9	269.7	276.8	283.6	296.0	309.6	320.5	329.2	338.0
57.5°	233.2	235.5	238.6	242.9	249.9	257.9	266.6	278.7	285.0	289.5	296.4
60°	217.5	218.1	220.2	225.2	230.7	237.8	248.0	256.5	261.2	264.9	270.6
62.5°	200.1	200.3	203.7	207.4	211.4	219.1	227.4	234.2	238.2	240.0	245.5
65°	175.8	175.1	177.2	180.2	184.9	190.0	197.2	203.2	202.9	204.9	208.3
67.5°	151.0	150.3	150.3	153.2	157.0	161.6	166.5	170.0	170.0	172.7	174.4
70°	134.1	132.2	133.5	135.8	137.5	141.2	146.7	148.0	148.4	149.7	151.4
72.5°	116.8	116.1	117.2	118.2	119.4	122.3	126.9	127.7	127.8	128.6	131.3
75°	92.8	92.1	91.5	92.5	93.8	95.9	97.6	98.9	98.5	98.9	100.9
77.5°	69.6	67.7	67.3	67.9	68.2	69.5	71.2	71.1	71.4	71.3	73.7
80°	55.2	52.5	52.2	52.2	52.5	53.1	53.9	54.6	53.5	54.6	55.2
82.5°	40.6	39.0	38.9	38.6	38.7	38.8	39.2	39.6	39.4	39.9	40.3
85°	22.4	21.7	20.7	21.3	21.0	20.0	20.7	19.6	19.4	19.6	20.0
87.5°	9.3	9.5	8.7	8.6	8.2	8.3	7.6	7.1	6.6	6.7	7.4
90°	8.6	8.1	7.1	6.6	5.6	5.1	4.1	3.0	2.1	1.0	0.5
92.5°	132.8	164.0	166.7	116.1	69.5	41.7	26.8	18.1	11.8	7.5	6.2
95°	441.0	450.7	367.7	227.4	115.5	61.1	38.2	26.9	21.4	17.3	16.8
97.5°	558.0	481.3	328.4	181.5	99.5	63.5	47.0	36.9	31.3	28.4	27.9
100°	586.5	459.3	293.0	164.8	98.7	69.2	53.9	44.2	38.7	36.6	35.6
102.5°	569.4	420.6	266.1	157.9	102.4	76.1	61.3	52.4	46.4	44.8	44.1
105°	514.8	368.8	240.0	155.2	109.9	87.5	73.2	65.1	60.0	57.5	57.5
107.5°	459.1	333.1	229.1	159.8	121.1	99.4	86.6	78.1	73.9	71.5	70.5
110°	427.3	316.4	225.9	164.3	129.2	108.3	95.1	87.5	82.9	80.9	79.9



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	403.7	306.7	225.9	170.0	137.0	116.9	104.1	96.5	91.8	90.2	89.3
115°	377.9	296.0	227.4	178.5	149.0	130.2	117.5	109.9	105.3	103.8	102.7
117.5°	362.6	290.9	230.7	188.3	161.5	143.7	131.3	122.7	118.2	116.5	114.9
120°	354.0	288.4	234.0	194.8	170.4	152.6	139.9	131.3	126.6	124.7	123.1
122.5°	346.7	286.4	236.8	202.2	179.0	161.1	148.5	138.9	134.4	132.8	131.6
125°	336.7	283.8	241.7	212.1	190.2	173.4	160.2	150.5	146.0	143.5	142.4
127.5°	327.6	282.6	247.0	221.2	201.1	184.9	171.7	161.5	155.7	152.4	150.9
130°	321.5	281.8	250.3	227.4	208.0	192.3	179.1	168.4	161.8	157.7	156.1
132.5°	316.6	281.8	254.0	232.6	214.5	198.8	185.6	174.5	167.0	162.2	160.2
135°	310.8	281.8	258.9	240.0	223.3	207.5	193.8	183.2	175.0	168.9	166.8
137.5°	305.6	282.4	263.5	245.6	229.5	215.2	201.0	190.6	182.4	176.7	175.2
140°	303.2	282.9	265.6	249.2	234.0	219.3	205.5	195.8	187.7	181.6	180.0
142.5°	301.1	283.2	266.7	251.3	236.8	222.9	210.0	200.7	192.6	186.9	185.7
145°	298.1	282.9	268.0	254.3	241.7	228.4	216.7	207.5	200.4	195.3	194.3
147.5°	294.9	281.5	268.6	256.2	244.7	233.1	222.7	214.8	208.2	203.8	203.2
150°	292.5	280.3	268.6	257.3	246.7	235.5	226.9	219.7	213.1	209.6	208.6
152.5°	289.6	278.7	268.1	258.2	248.7	238.4	230.5	223.8	218.0	214.8	214.3
155°	284.8	275.7	267.1	258.9	250.7	242.1	235.0	229.9	224.8	221.8	221.8
157.5°	280.4	272.6	265.7	259.4	252.5	245.0	239.7	235.2	230.9	228.4	228.5
160°	276.7	270.6	264.5	259.4	253.3	246.7	242.1	238.1	234.5	232.5	233.0
162.5°	273.5	268.1	263.3	259.0	254.1	248.3	244.6	241.3	238.2	236.1	236.7
165°	268.6	264.5	261.4	258.4	254.3	250.3	247.2	245.1	242.6	241.1	242.1
167.5°	263.8	260.9	258.6	257.2	254.3	250.9	249.1	247.6	246.2	245.3	245.8
170°	260.9	258.9	257.3	256.4	254.3	251.8	250.3	249.2	248.3	247.7	248.3
172.5°	258.1	256.5	255.7	255.6	254.0	251.8	251.1	250.5	249.4	249.0	249.9
175°	254.3	253.8	253.8	254.3	253.3	251.8	251.8	251.8	251.3	250.7	251.8
177.5°	252.7	252.3	252.3	253.1	252.7	251.9	251.9	252.3	251.9	251.9	252.7
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	802.5	806.2	808.6	813.2	817.1	819.2	821.1	822.7	824.7	826.3	830.9
5°	807.5	816.4	823.9	835.4	845.9	854.0	862.7	870.6	877.0	886.2	893.2
7.5°	805.3	821.0	837.4	855.2	873.4	890.4	905.9	920.5	933.7	949.7	963.7
10°	803.2	824.5	845.5	869.5	894.3	915.3	935.0	954.9	969.5	989.8	1007.1
12.5°	801.6	826.7	852.0	880.9	908.1	937.7	963.9	978.5	1000.7	1016.9	1037.4
15°	794.7	827.9	862.7	895.3	933.9	961.4	984.4	1012.8	1033.5	1054.2	1076.5
17.5°	782.4	820.0	859.1	901.7	938.7	968.2	997.8	1025.3	1050.0	1077.6	1105.5
20°	776.8	814.3	859.1	902.8	939.0	969.8	1000.3	1030.5	1057.6	1093.1	1125.2
22.5°	764.8	810.3	851.5	894.0	931.4	964.9	999.5	1033.7	1069.7	1109.9	1150.2
25°	743.5	789.6	833.3	875.3	912.9	954.9	991.8	1037.6	1083.6	1136.8	1187.0
27.5°	721.5	765.5	805.6	846.1	890.0	937.5	985.4	1037.3	1097.7	1164.8	1235.6
30°	703.6	745.2	784.2	825.8	871.6	925.1	977.6	1039.3	1109.0	1184.5	1268.5
32.5°	682.7	721.1	759.0	803.1	852.9	909.4	970.5	1038.1	1122.0	1207.9	1294.3
35°	647.0	679.2	718.1	765.2	821.4	886.2	957.0	1036.9	1133.1	1231.6	1304.5
37.5°	604.7	634.6	675.6	727.3	786.2	855.7	939.7	1034.5	1136.7	1215.2	1238.8
40°	576.2	604.0	646.7	700.2	760.5	834.0	926.1	1026.4	1125.2	1175.5	1156.1
42.5°	545.8	575.0	616.6	669.6	734.4	814.5	909.0	1009.3	1092.3	1111.2	1044.5
45°	497.9	528.1	569.1	622.6	692.4	779.1	877.7	968.8	1016.6	982.3	879.0
47.5°	453.4	481.7	519.7	574.9	646.9	736.6	831.5	904.2	908.0	826.3	716.0
50°	423.1	449.2	487.4	542.7	614.1	704.9	790.6	847.8	822.2	729.7	623.7
52.5°	393.2	418.8	456.6	511.2	581.9	665.0	744.8	785.0	736.5	641.6	551.0
55°	350.3	372.6	409.6	460.0	527.1	604.3	672.1	685.9	622.9	529.4	455.9
57.5°	308.3	329.1	362.7	409.2	470.5	539.0	591.9	589.0	522.4	442.1	383.8
60°	279.8	300.1	329.9	375.3	431.2	490.2	535.6	524.7	458.7	389.6	340.5
62.5°	254.3	272.5	300.7	340.4	391.4	445.9	483.2	467.3	402.5	342.1	303.3
65°	216.8	232.0	256.1	290.0	332.3	377.4	406.2	385.5	330.3	283.2	252.0
67.5°	180.9	193.1	213.3	240.4	276.5	312.6	330.2	309.4	265.2	230.9	207.8
70°	158.2	169.1	184.6	208.7	240.1	270.6	283.8	265.2	227.3	197.8	181.2
72.5°	135.5	144.4	158.1	179.7	204.9	231.4	242.9	225.2	193.9	169.1	153.6
75°	104.7	110.8	120.3	135.2	155.2	176.1	182.6	167.0	147.0	128.4	118.2
77.5°	74.9	80.1	87.3	96.7	110.8	124.2	129.8	120.8	105.3	93.5	85.2
80°	57.6	60.3	66.4	74.2	85.3	93.8	97.6	91.8	81.0	72.1	65.7
82.5°	41.0	43.8	47.4	53.9	61.0	66.7	70.7	66.9	59.0	52.1	48.3
85°	20.0	21.7	23.7	26.4	31.8	35.2	34.9	32.5	29.4	26.8	24.7
87.5°	7.2	7.8	8.7	10.3	11.3	12.5	13.3	12.8	11.9	11.2	10.5
90°	1.0	2.1	3.0	4.1	5.1	5.6	6.6	7.1	8.1	8.6	9.2
92.5°	7.5	11.8	18.1	26.8	41.7	69.5	116.1	166.7	164.0	132.8	90.2
95°	17.3	21.4	26.9	38.2	61.1	115.5	227.4	367.7	450.7	441.0	365.7
97.5°	28.4	31.3	36.9	47.0	63.5	99.5	181.5	328.4	481.3	558.0	544.7
100°	36.6	38.7	44.2	53.9	69.2	98.7	164.8	293.0	459.3	586.5	625.6
102.5°	44.8	46.4	52.4	61.3	76.1	102.4	157.9	266.1	420.6	569.4	652.9
105°	57.5	60.0	65.1	73.2	87.5	109.9	155.2	240.0	368.8	514.8	636.9
107.5°	71.5	73.9	78.1	86.6	99.4	121.1	159.8	229.1	333.1	459.1	579.4
110°	80.9	82.9	87.5	95.1	108.3	129.2	164.3	225.9	316.4	427.3	537.2



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	90.2	91.8	96.5	104.1	116.9	137.0	170.0	225.9	306.7	403.7	503.8
115°	103.8	105.3	109.9	117.5	130.2	149.0	178.5	227.4	296.0	377.9	461.8
117.5°	116.5	118.2	122.7	131.3	143.7	161.5	188.3	230.7	290.9	362.6	434.8
120°	124.7	126.6	131.3	139.9	152.6	170.4	194.8	234.0	288.4	354.0	420.2
122.5°	132.8	134.4	138.9	148.5	161.1	179.0	202.2	236.8	286.4	346.7	409.2
125°	143.5	146.0	150.5	160.2	173.4	190.2	212.1	241.7	283.8	336.7	393.2
127.5°	152.4	155.7	161.5	171.7	184.9	201.1	221.2	247.0	282.6	327.6	376.9
130°	157.7	161.8	168.4	179.1	192.3	208.0	227.4	250.3	281.8	321.5	366.8
132.5°	162.2	167.0	174.5	185.6	198.8	214.5	232.6	254.0	281.8	316.6	356.6
135°	168.9	175.0	183.2	193.8	207.5	223.3	240.0	258.9	281.8	310.8	343.3
137.5°	176.7	182.4	190.6	201.0	215.2	229.5	245.6	263.5	282.4	305.6	332.2
140°	181.6	187.7	195.8	205.5	219.3	234.0	249.2	265.6	282.9	303.2	326.0
142.5°	186.9	192.6	200.7	210.0	222.9	236.8	251.3	266.7	283.2	301.1	320.7
145°	195.3	200.4	207.5	216.7	228.4	241.7	254.3	268.0	282.9	298.1	313.9
147.5°	203.8	208.2	214.8	222.7	233.1	244.7	256.2	268.6	281.5	294.9	307.4
150°	209.6	213.1	219.7	226.9	235.5	246.7	257.3	268.6	280.3	292.5	303.6
152.5°	214.8	218.0	223.8	230.5	238.4	248.7	258.2	268.1	278.7	289.6	299.6
155°	221.8	224.8	229.9	235.0	242.1	250.7	258.9	267.1	275.7	284.8	293.5
157.5°	228.4	230.9	235.2	239.7	245.0	252.5	259.4	265.7	272.6	280.4	287.4
160°	232.5	234.5	238.1	242.1	246.7	253.3	259.4	264.5	270.6	276.7	283.3
162.5°	236.1	238.2	241.3	244.6	248.3	254.1	259.0	263.3	268.1	273.5	278.8
165°	241.1	242.6	245.1	247.2	250.3	254.3	258.4	261.4	264.5	268.6	272.6
167.5°	245.3	246.2	247.6	249.1	250.9	254.3	257.2	258.6	260.9	263.8	266.7
170°	247.7	248.3	249.2	250.3	251.8	254.3	256.4	257.3	258.9	260.9	263.5
172.5°	249.0	249.4	250.5	251.1	251.8	254.0	255.6	255.7	256.5	258.1	259.8
175°	250.7	251.3	251.8	251.8	251.8	253.3	254.3	253.8	253.8	254.3	255.8
177.5°	251.9	251.9	252.3	251.9	251.9	252.7	253.1	252.3	252.3	252.7	253.1
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3	252.3



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	834.6	836.8	841.4	839.8	842.0	843.0	844.2
5°	902.1	912.9	917.7	916.9	924.1	922.4	920.7
7.5°	978.2	989.6	996.0	1003.9	1008.5	1008.8	1012.8
10°	1021.3	1036.2	1042.3	1050.8	1056.2	1059.3	1058.9
12.5°	1054.4	1066.0	1079.7	1083.9	1091.2	1095.0	1093.6
15°	1094.1	1112.8	1126.9	1134.1	1143.3	1145.9	1149.7
17.5°	1129.6	1154.6	1171.3	1193.3	1201.7	1206.8	1203.7
20°	1156.5	1189.3	1205.9	1232.3	1246.9	1254.7	1252.0
22.5°	1188.2	1223.7	1254.5	1277.3	1299.5	1310.0	1312.2
25°	1242.5	1291.3	1336.3	1366.5	1393.9	1400.3	1414.6
27.5°	1303.2	1360.8	1408.9	1440.6	1459.7	1466.9	1471.3
30°	1341.4	1398.6	1434.9	1455.2	1461.3	1460.6	1460.0
32.5°	1360.1	1396.0	1402.9	1397.2	1383.3	1371.5	1359.1
35°	1333.6	1306.9	1266.9	1215.4	1177.5	1139.2	1135.4
37.5°	1199.4	1113.8	1047.3	973.0	930.1	903.7	885.3
40°	1073.1	975.9	895.3	832.6	788.9	771.7	754.7
42.5°	936.0	843.1	771.7	719.3	686.5	667.4	653.9
45°	760.5	678.5	622.6	584.7	558.6	543.7	535.2
47.5°	623.1	562.5	515.1	487.7	469.7	458.1	458.1
50°	549.5	491.5	460.0	438.4	422.8	413.6	415.3
52.5°	484.1	440.9	413.9	395.7	384.2	378.6	378.4
55°	404.8	373.6	356.1	342.8	335.0	328.6	329.9
57.5°	346.3	319.9	308.2	297.2	291.8	289.2	285.5
60°	310.0	289.6	279.5	270.6	265.2	263.2	259.5
62.5°	277.7	261.7	251.8	244.6	239.8	239.1	236.1
65°	233.4	221.2	212.4	209.0	203.9	202.6	202.6
67.5°	192.4	183.7	176.8	173.7	171.5	171.8	170.1
70°	166.7	159.5	155.2	151.8	150.1	150.4	149.0
72.5°	145.8	137.9	134.0	132.0	129.7	130.6	130.1
75°	110.4	106.4	104.3	102.3	100.9	100.2	99.6
77.5°	81.1	77.5	76.0	74.8	75.0	73.4	74.6
80°	62.7	59.7	58.6	56.9	56.5	56.5	56.3
82.5°	45.8	44.1	43.4	42.0	41.4	41.9	41.0
85°	23.7	22.4	22.0	22.0	21.3	20.7	22.4
87.5°	10.6	9.6	9.8	9.5	9.5	9.4	8.8
90°	9.6	10.2	11.1	11.1	11.1	11.7	11.7
92.5°	65.5	49.2	41.7	35.2	34.0	33.3	32.5
95°	288.4	225.9	183.2	147.0	131.7	127.7	119.6
97.5°	490.4	429.5	370.1	338.7	310.1	295.4	288.9
100°	600.7	548.3	495.4	460.3	423.7	404.9	396.7
102.5°	668.2	643.1	607.3	569.8	543.8	523.3	517.2
105°	706.5	728.9	723.3	707.0	690.3	680.1	674.0
107.5°	672.4	730.0	756.4	764.7	764.6	761.3	757.2
110°	633.8	705.5	748.8	771.6	781.3	784.9	784.9



TEST NUMBER: P333171-940

CATALOG NUMBER: S125DIP-S610D590U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	595.6	668.1	719.1	752.5	769.1	777.9	781.6
115°	540.7	610.4	665.8	705.5	730.0	744.1	750.8
117.5°	502.7	562.8	613.7	653.4	678.6	692.7	696.8
120°	481.2	537.2	581.9	619.6	644.0	657.7	661.7
122.5°	465.7	515.6	557.5	591.0	613.4	627.1	630.8
125°	445.1	489.4	525.9	554.5	575.3	586.5	591.6
127.5°	425.3	466.6	501.0	526.7	545.2	555.7	558.0
130°	411.5	451.2	484.2	509.7	526.5	536.6	539.7
132.5°	398.5	434.5	466.4	491.8	508.5	517.9	521.4
135°	378.4	411.0	440.0	462.4	479.1	488.3	491.3
137.5°	360.5	387.6	412.2	432.2	447.5	455.9	459.3
140°	350.0	373.4	394.8	413.6	426.8	434.4	436.9
142.5°	341.0	361.1	379.7	395.7	406.8	414.0	416.2
145°	329.6	345.4	359.1	371.3	380.0	385.6	387.6
147.5°	320.1	332.3	342.6	352.3	359.2	362.5	363.4
150°	314.9	324.5	333.7	341.3	347.4	349.5	350.0
152.5°	309.6	318.4	325.6	332.0	336.8	338.9	339.4
155°	301.7	308.7	314.3	319.4	323.0	324.5	325.0
157.5°	294.1	299.6	304.0	307.9	310.9	312.3	312.2
160°	288.4	293.5	297.0	300.6	303.2	304.2	303.6
162.5°	283.6	287.8	291.0	293.7	295.9	296.0	296.0
165°	276.2	279.3	281.8	283.8	284.8	284.8	284.8
167.5°	269.1	271.4	273.2	274.3	275.2	274.7	274.6
170°	265.0	266.5	267.5	268.6	269.1	269.1	268.6
172.5°	261.4	262.4	263.1	263.3	264.2	263.4	262.9
175°	255.8	256.9	256.9	256.9	257.3	256.4	255.8
177.5°	253.5	253.5	253.5	253.1	253.5	252.3	252.3
180°	252.3	252.3	252.3	252.3	252.3	252.3	252.3

(END OF REPORT)