

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333180-940

Luminaire Tested: **S125DIP-S610D810U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333180-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4847.3 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	46
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	33
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	31	28	25
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	32	26	22	28	23	19	24	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5154	5154	5154	5154
5°	5969	5172	4528	5172
10°	6944	5145	3968	5145
15°	7687	5107	3660	5107
20°	8605	5047	3413	5047
25°	10080	4980	3293	4980
30°	10888	4914	3188	4914
35°	8952	4788	3120	4788
40°	6363	4615	3044	4615
45°	4888	4381	3001	4381
50°	4173	4091	2995	4091
55°	3715	3806	3021	3806
60°	3352	3495	3099	3495
65°	3096	3183	3177	3183
70°	2814	2859	3225	2859
75°	2485	2518	3194	2518
80°	2094	2053	2923	2053
85°	1660	1482	2356	1482



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.6
10°-20°	228.8	4.7
20°-30°	371.4	7.7
30°-40°	453.1	9.3
40°-50°	412.2	8.5
50°-60°	328.3	6.8
60°-70°	228.7	4.7
70°-80°	121.9	2.5
80°-90°	32.7	0.7
90°-100°	250.7	5.2
100°-110°	538.9	11.1
110°-120°	505.7	10.4
120°-130°	409.8	8.5
130°-140°	328.9	6.8
140°-150°	248.2	5.1
150°-160°	174.7	3.6
160°-170°	103.0	2.1
170°-180°	33.5	0.7
0°-30°	677.0	14.0
0°-40°	1130.1	23.3
0°-60°	1870.6	38.6
0°-90°	2253.9	46.5
90°-120°	1295.2	26.7
90°-150°	2282.2	47.1
90°-180°	2593.0	53.5
0°-180°	4847.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	921	798	698	798	921	93
15°	1150	764	547	764	1150	329
25°	1415	699	462	699	1415	646
35°	1135	607	396	607	1135	695
45°	535	480	329	480	535	428
55°	330	338	268	338	330	297
65°	203	208	208	208	203	201
75°	100	101	128	101	100	107
85°	22	20	32	20	22	26
90°	16	1	16	1	16	12
95°	164	23	164	23	164	232
105°	924	79	924	79	924	918
115°	1029	141	1029	141	1029	1005
125°	811	195	811	195	811	734
135°	674	229	674	229	674	522
145°	531	266	531	266	531	338
155°	446	304	446	304	446	208
165°	390	332	390	332	390	112
175°	351	345	351	345	351	34
180°	346	346	346	346	346	



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	844.2	843.0	842.0	839.8	841.4	836.8	834.6	830.9	826.3	824.7	822.7
5°	920.7	922.4	924.1	916.9	917.7	912.9	902.1	893.2	886.2	877.0	870.6
7.5°	1012.8	1008.8	1008.5	1003.9	996.0	989.6	978.2	963.7	949.7	933.7	920.5
10°	1058.9	1059.3	1056.2	1050.8	1042.3	1036.2	1021.3	1007.1	989.8	969.5	954.9
12.5°	1093.6	1095.0	1091.2	1083.9	1079.7	1066.0	1054.4	1037.4	1016.9	1000.7	978.5
15°	1149.7	1145.9	1143.3	1134.1	1126.9	1112.8	1094.1	1076.5	1054.2	1033.5	1012.8
17.5°	1203.7	1206.8	1201.7	1193.3	1171.3	1154.6	1129.6	1105.5	1077.6	1050.0	1025.3
20°	1252.0	1254.7	1246.9	1232.3	1205.9	1189.3	1156.5	1125.2	1093.1	1057.6	1030.5
22.5°	1312.2	1310.0	1299.5	1277.3	1254.5	1223.7	1188.2	1150.2	1109.9	1069.7	1033.7
25°	1414.6	1400.3	1393.9	1366.5	1336.3	1291.3	1242.5	1187.0	1136.8	1083.6	1037.6
27.5°	1471.3	1466.9	1459.7	1440.6	1408.9	1360.8	1303.2	1235.6	1164.8	1097.7	1037.3
30°	1460.0	1460.6	1461.3	1455.2	1434.9	1398.6	1341.4	1268.5	1184.5	1109.0	1039.3
32.5°	1359.1	1371.5	1383.3	1397.2	1402.9	1396.0	1360.1	1294.3	1207.9	1122.0	1038.1
35°	1135.4	1139.2	1177.5	1215.4	1266.9	1306.9	1333.6	1304.5	1231.6	1133.1	1036.9
37.5°	885.3	903.7	930.1	973.0	1047.3	1113.8	1199.4	1238.8	1215.2	1136.7	1034.5
40°	754.7	771.7	788.9	832.6	895.3	975.9	1073.1	1156.1	1175.5	1125.2	1026.4
42.5°	653.9	667.4	686.5	719.3	771.7	843.1	936.0	1044.5	1111.2	1092.3	1009.3
45°	535.2	543.7	558.6	584.7	622.6	678.5	760.5	879.0	982.3	1016.6	968.8
47.5°	458.1	458.1	469.7	487.7	515.1	562.5	623.1	716.0	826.3	908.0	904.2
50°	415.3	413.6	422.8	438.4	460.0	491.5	549.5	623.7	729.7	822.2	847.8
52.5°	378.4	378.6	384.2	395.7	413.9	440.9	484.1	551.0	641.6	736.5	785.0
55°	329.9	328.6	335.0	342.8	356.1	373.6	404.8	455.9	529.4	622.9	685.9
57.5°	285.5	289.2	291.8	297.2	308.2	319.9	346.3	383.8	442.1	522.4	589.0
60°	259.5	263.2	265.2	270.6	279.5	289.6	310.0	340.5	389.6	458.7	524.7
62.5°	236.1	239.1	239.8	244.6	251.8	261.7	277.7	303.3	342.1	402.5	467.3
65°	202.6	202.6	203.9	209.0	212.4	221.2	233.4	252.0	283.2	330.3	385.5
67.5°	170.1	171.8	171.5	173.7	176.8	183.7	192.4	207.8	230.9	265.2	309.4
70°	149.0	150.4	150.1	151.8	155.2	159.5	166.7	181.2	197.8	227.3	265.2
72.5°	130.1	130.6	129.7	132.0	134.0	137.9	145.8	153.6	169.1	193.9	225.2
75°	99.6	100.2	100.9	102.3	104.3	106.4	110.4	118.2	128.4	147.0	167.0
77.5°	74.6	73.4	75.0	74.8	76.0	77.5	81.1	85.2	93.5	105.3	120.8
80°	56.3	56.5	56.5	56.9	58.6	59.7	62.7	65.7	72.1	81.0	91.8
82.5°	41.0	41.9	41.4	42.0	43.4	44.1	45.8	48.3	52.1	59.0	66.9
85°	22.4	20.7	21.3	22.0	22.0	22.4	23.7	24.7	26.8	29.4	32.5
87.5°	9.7	10.3	10.3	10.3	10.6	10.3	11.3	11.1	11.9	12.6	13.4
90°	16.1	16.1	15.3	15.3	15.3	13.9	13.3	12.6	11.9	11.1	9.7
92.5°	44.5	45.6	46.5	48.2	57.2	67.5	89.7	123.6	182.0	224.8	228.4
95°	163.8	175.0	180.6	201.5	251.0	309.6	395.3	501.3	604.5	617.8	504.1
97.5°	396.0	404.9	425.2	464.2	507.3	588.7	672.3	746.6	764.8	659.7	450.1
100°	543.9	555.0	580.8	631.0	679.1	751.6	823.4	857.6	803.9	629.6	401.6
102.5°	708.9	717.3	745.3	781.0	832.5	881.5	916.1	894.9	780.5	576.6	364.8
105°	923.8	932.2	946.1	969.1	991.5	999.2	968.5	872.9	705.6	505.5	329.1
107.5°	1037.9	1043.5	1048.0	1048.2	1036.9	1000.5	921.8	794.2	629.2	456.6	314.1
110°	1075.8	1075.8	1070.9	1057.7	1026.3	967.1	868.7	736.3	585.7	433.6	309.6



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1071.4	1066.3	1054.2	1031.4	985.6	915.7	816.3	690.5	553.3	420.3	309.6
115°	1029.1	1020.0	1000.5	967.1	912.7	836.7	741.2	633.1	518.0	405.8	311.7
117.5°	955.0	949.5	930.1	895.5	841.2	771.4	689.1	596.0	497.0	398.7	316.3
120°	907.0	901.5	882.7	849.2	797.6	736.3	659.6	575.9	485.3	395.3	320.7
122.5°	864.7	859.7	840.9	810.2	764.2	706.7	638.4	560.9	475.2	392.5	324.6
125°	810.8	803.9	788.5	760.0	720.9	670.7	610.1	539.0	461.5	389.1	331.2
127.5°	764.8	761.8	747.3	722.0	686.6	639.6	583.0	516.7	449.0	387.4	338.6
130°	739.8	735.6	721.7	698.7	663.8	618.4	564.1	502.7	440.7	386.3	343.0
132.5°	714.6	709.9	697.1	674.0	639.2	595.6	546.2	488.7	434.0	386.3	348.0
135°	673.5	669.3	656.7	633.7	603.1	563.4	518.7	470.6	426.0	386.3	354.9
137.5°	629.6	625.0	613.4	592.5	565.0	531.3	494.2	455.3	418.9	387.1	361.1
140°	598.9	595.4	585.0	566.9	541.0	511.8	479.7	446.9	415.5	387.6	363.9
142.5°	570.4	567.6	557.7	542.3	520.4	495.0	467.4	439.7	412.8	388.3	365.6
145°	531.3	528.5	520.8	509.0	492.2	473.4	451.8	430.2	408.6	387.6	367.5
147.5°	498.1	496.9	492.4	482.9	469.7	455.4	438.8	421.2	404.2	385.8	368.1
150°	479.7	479.0	476.2	467.9	457.4	444.8	431.6	416.3	400.9	384.1	368.1
152.5°	465.2	464.5	461.7	455.0	446.2	436.5	424.4	410.6	397.0	381.9	367.6
155°	445.5	444.8	442.7	437.8	430.9	423.2	413.5	402.3	390.5	377.9	366.0
157.5°	427.9	428.1	426.1	422.1	416.7	410.6	403.1	394.0	384.3	373.7	364.3
160°	416.3	417.0	415.5	412.1	407.2	402.3	395.3	388.3	379.3	371.0	362.6
162.5°	405.6	405.8	405.5	402.6	398.8	394.5	388.6	382.2	374.8	367.6	360.9
165°	390.5	390.5	390.5	389.1	386.3	382.8	378.6	373.7	368.1	362.6	358.4
167.5°	376.5	376.7	377.2	375.9	374.5	372.0	368.8	365.6	361.6	357.7	354.5
170°	368.1	368.8	368.8	368.1	366.8	365.3	363.3	361.1	357.7	354.9	352.8
172.5°	360.3	361.1	362.1	360.9	360.6	359.8	358.2	356.1	353.7	351.5	350.5
175°	350.7	351.4	352.8	352.1	352.1	352.1	350.7	350.7	348.6	347.9	347.9
177.5°	345.8	345.8	347.5	347.0	347.5	347.5	347.5	347.0	346.3	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	821.1	819.2	817.1	813.2	808.6	806.2	802.5	800.0	795.0	791.0	786.7
5°	862.7	854.0	845.9	835.4	823.9	816.4	807.5	797.7	787.6	777.0	765.5
7.5°	905.9	890.4	873.4	855.2	837.4	821.0	805.3	790.0	775.6	758.2	743.5
10°	935.0	915.3	894.3	869.5	845.5	824.5	803.2	784.5	765.5	745.2	727.3
12.5°	963.9	937.7	908.1	880.9	852.0	826.7	801.6	777.8	753.9	731.4	710.5
15°	984.4	961.4	933.9	895.3	862.7	827.9	794.7	763.8	735.0	710.0	683.6
17.5°	997.8	968.2	938.7	901.7	859.1	820.0	782.4	747.2	714.7	682.9	657.5
20°	1000.3	969.8	939.0	902.8	859.1	814.3	776.8	734.4	699.5	666.6	635.4
22.5°	999.5	964.9	931.4	894.0	851.5	810.3	764.8	721.7	683.8	651.5	618.9
25°	991.8	954.9	912.9	875.3	833.3	789.6	743.5	698.8	660.2	623.3	591.1
27.5°	985.4	937.5	890.0	846.1	805.6	765.5	721.5	675.6	632.8	595.4	565.1
30°	977.6	925.1	871.6	825.8	784.2	745.2	703.6	658.9	614.1	577.6	545.0
32.5°	970.5	909.4	852.9	803.1	759.0	721.1	682.7	640.2	596.3	559.1	526.6
35°	957.0	886.2	821.4	765.2	718.1	679.2	647.0	607.3	567.0	531.1	500.0
37.5°	939.7	855.7	786.2	727.3	675.6	634.6	604.7	574.3	535.6	501.0	472.8
40°	926.1	834.0	760.5	700.2	646.7	604.0	576.2	547.4	515.2	483.0	453.3
42.5°	909.0	814.5	734.4	669.6	616.6	575.0	545.8	521.4	493.0	463.0	435.3
45°	877.7	779.1	692.4	622.6	569.1	528.1	497.9	479.7	458.3	429.9	406.5
47.5°	831.5	736.6	646.9	574.9	519.7	481.7	453.4	435.9	420.9	399.8	378.5
50°	790.6	704.9	614.1	542.7	487.4	449.2	423.1	407.2	394.3	378.0	360.1
52.5°	744.8	665.0	581.9	511.2	456.6	418.8	393.2	379.2	368.5	356.9	339.2
55°	672.1	604.3	527.1	460.0	409.6	372.6	350.3	338.0	329.2	320.5	309.6
57.5°	591.9	539.0	470.5	409.2	362.7	329.1	308.3	296.4	289.5	285.0	278.7
60°	535.6	490.2	431.2	375.3	329.9	300.1	279.8	270.6	264.9	261.2	256.5
62.5°	483.2	445.9	391.4	340.4	300.7	272.5	254.3	245.5	240.0	238.2	234.2
65°	406.2	377.4	332.3	290.0	256.1	232.0	216.8	208.3	204.9	202.9	203.2
67.5°	330.2	312.6	276.5	240.4	213.3	193.1	180.9	174.4	172.7	170.0	170.0
70°	283.8	270.6	240.1	208.7	184.6	169.1	158.2	151.4	149.7	148.4	148.0
72.5°	242.9	231.4	204.9	179.7	158.1	144.4	135.5	131.3	128.6	127.8	127.7
75°	182.6	176.1	155.2	135.2	120.3	110.8	104.7	100.9	98.9	98.5	98.9
77.5°	129.8	124.2	110.8	96.7	87.3	80.1	74.9	73.7	71.3	71.4	71.1
80°	97.6	93.8	85.3	74.2	66.4	60.3	57.6	55.2	54.6	53.5	54.6
82.5°	70.7	66.7	61.0	53.9	47.4	43.8	41.0	40.3	39.9	39.4	39.6
85°	34.9	35.2	31.8	26.4	23.7	21.7	20.0	20.0	19.6	19.4	19.6
87.5°	13.7	12.9	11.7	10.6	9.0	7.8	7.3	7.5	6.8	6.8	7.3
90°	9.1	7.7	7.0	5.6	4.2	2.8	1.4	0.7	1.4	2.8	4.2
92.5°	159.1	95.2	57.2	36.8	24.8	16.1	10.3	8.5	10.3	16.1	24.8
95°	311.7	158.3	83.6	52.3	36.9	29.2	23.7	23.0	23.7	29.2	36.9
97.5°	248.8	136.3	87.0	64.4	50.6	43.0	39.1	38.2	39.1	43.0	50.6
100°	225.9	135.3	94.8	73.9	60.6	53.0	50.2	48.8	50.2	53.0	60.6
102.5°	216.4	140.3	104.3	83.9	71.8	63.6	61.3	60.5	61.3	63.6	71.8
105°	212.7	150.6	119.9	100.4	89.3	82.3	78.8	78.8	78.8	82.3	89.3
107.5°	219.1	165.9	136.3	118.7	107.1	101.4	98.0	96.7	98.0	101.4	107.1
110°	225.2	177.1	148.5	130.4	119.9	113.6	110.8	109.5	110.8	113.6	119.9



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	233.0	187.7	160.2	142.7	132.2	125.9	123.7	122.3	123.7	125.9	132.2
115°	244.7	204.3	178.5	161.0	150.6	144.4	142.2	140.8	142.2	144.4	150.6
117.5°	258.2	221.3	196.9	180.0	168.2	161.9	159.7	157.6	159.7	161.9	168.2
120°	267.1	233.5	209.2	191.7	179.9	173.6	170.9	168.7	170.9	173.6	179.9
122.5°	277.1	245.3	220.9	203.5	190.5	184.2	182.0	180.5	182.0	184.2	190.5
125°	290.7	260.7	237.7	219.6	206.3	200.1	196.6	195.2	196.6	200.1	206.3
127.5°	303.3	275.7	253.5	235.4	221.3	213.4	208.9	206.8	208.9	213.4	221.3
130°	311.7	285.2	263.6	245.4	230.8	221.7	216.2	214.0	216.2	221.7	230.8
132.5°	318.9	294.1	272.5	254.3	239.2	229.0	222.3	219.6	222.3	229.0	239.2
135°	329.1	306.1	284.5	265.6	251.0	239.9	231.5	228.7	231.5	239.9	251.0
137.5°	336.6	314.6	294.9	275.5	261.2	250.0	242.2	240.1	242.2	250.0	261.2
140°	341.6	320.7	300.5	281.7	268.4	257.3	248.9	246.8	248.9	257.3	268.4
142.5°	344.5	324.6	305.5	287.8	275.1	263.9	256.2	254.6	256.2	263.9	275.1
145°	348.6	331.2	313.1	297.0	284.5	274.7	267.7	266.4	267.7	274.7	284.5
147.5°	351.2	335.4	319.5	305.4	294.5	285.4	279.5	278.6	279.5	285.4	294.5
150°	352.8	338.1	322.8	310.9	301.2	292.1	287.2	285.9	287.2	292.1	301.2
152.5°	353.9	340.9	326.7	316.0	306.7	298.8	294.5	293.6	294.5	298.8	306.7
155°	354.9	343.8	331.9	322.1	315.1	308.2	304.0	304.0	304.0	308.2	315.1
157.5°	355.6	346.1	335.9	328.5	322.4	316.4	313.1	313.2	313.1	316.4	322.4
160°	355.6	347.2	338.1	331.9	326.3	321.5	318.6	319.3	318.6	321.5	326.3
162.5°	355.0	348.3	340.4	335.2	330.7	326.5	323.7	324.3	323.7	326.5	330.7
165°	354.2	348.6	343.0	338.9	336.1	332.6	330.5	331.9	330.5	332.6	336.1
167.5°	352.5	348.6	344.0	341.3	339.4	337.4	336.2	336.9	336.2	337.4	339.4
170°	351.4	348.6	345.1	343.0	341.6	340.3	339.6	340.3	339.6	340.3	341.6
172.5°	350.3	348.0	345.1	344.1	343.3	341.9	341.3	342.5	341.3	341.9	343.3
175°	348.6	347.2	345.1	345.1	345.1	344.5	343.8	345.1	343.8	344.5	345.1
177.5°	347.0	346.3	345.3	345.3	345.8	345.3	345.3	346.3	345.3	345.3	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	784.3	781.2	778.8	773.4	770.4	766.3	763.1	766.6	762.9	764.5	762.1
5°	759.8	750.3	743.5	733.7	725.2	717.5	711.7	710.7	707.9	706.6	702.6
7.5°	730.4	718.5	706.9	694.0	683.1	672.2	665.0	659.2	655.4	650.3	646.8
10°	713.0	697.1	683.6	668.0	654.4	642.6	633.1	628.4	623.9	617.5	615.2
12.5°	691.6	675.2	658.6	641.9	629.0	615.7	607.6	600.5	597.4	590.1	589.4
15°	665.9	641.2	625.0	608.1	590.0	579.3	572.5	564.7	561.3	556.2	552.5
17.5°	635.3	613.2	592.9	575.4	560.0	550.9	542.4	537.1	531.3	528.0	521.8
20°	613.1	592.1	571.8	553.1	541.3	530.8	524.1	519.0	512.8	511.1	505.1
22.5°	594.4	571.2	551.7	536.1	523.2	511.3	504.0	500.5	496.3	491.1	489.9
25°	564.0	539.9	523.3	507.7	496.2	485.4	480.4	475.9	471.9	468.1	466.8
27.5°	537.7	516.2	496.5	482.4	472.4	462.5	458.1	452.7	449.7	446.7	443.1
30°	519.3	497.3	480.0	466.5	455.6	446.8	442.0	438.4	435.6	432.9	430.9
32.5°	500.3	479.9	463.2	450.0	439.1	432.5	428.2	425.6	422.6	419.4	416.8
35°	475.3	452.9	436.7	425.1	416.6	411.5	406.8	404.5	401.1	401.1	398.3
37.5°	447.0	427.7	413.3	402.8	395.2	390.7	385.6	384.0	381.7	380.3	379.4
40°	430.2	412.2	398.7	388.2	380.0	376.3	372.3	369.5	368.2	366.5	365.9
42.5°	412.9	395.7	382.7	373.0	366.0	362.7	359.0	357.1	354.4	352.1	351.8
45°	386.5	369.9	358.0	350.3	344.2	340.5	338.0	334.0	332.6	329.9	329.6
47.5°	361.5	345.5	333.9	327.5	322.2	319.1	315.4	311.4	309.8	308.4	308.4
50°	342.8	328.2	317.4	311.3	306.2	301.8	298.1	295.4	294.4	294.4	295.1
52.5°	323.9	311.5	302.2	294.8	290.0	285.3	281.9	280.2	278.7	280.3	281.5
55°	296.0	283.6	276.8	269.7	264.9	259.5	257.8	257.1	256.1	258.8	260.1
57.5°	266.6	257.9	249.9	242.9	238.6	235.5	233.2	232.8	234.7	235.9	240.4
60°	248.0	237.8	230.7	225.2	220.2	218.1	217.5	216.8	218.1	221.9	227.7
62.5°	227.4	219.1	211.4	207.4	203.7	200.3	200.1	200.5	203.2	207.5	213.3
65°	197.2	190.0	184.9	180.2	177.2	175.1	175.8	177.2	180.2	186.0	192.4
67.5°	166.5	161.6	157.0	153.2	150.3	150.3	151.0	153.0	156.6	163.2	169.1
70°	146.7	141.2	137.5	135.8	133.5	132.2	134.1	137.5	140.5	146.7	151.8
72.5°	126.9	122.3	119.4	118.2	117.2	116.1	116.8	120.5	124.6	130.7	136.6
75°	97.6	95.9	93.8	92.5	91.5	92.1	92.8	96.2	99.6	106.0	112.8
77.5°	71.2	69.5	68.2	67.9	67.3	67.7	69.6	72.1	75.4	80.1	85.2
80°	53.9	53.1	52.5	52.2	52.2	52.5	55.2	56.9	59.9	64.4	68.4
82.5°	39.2	38.8	38.7	38.6	38.9	39.0	40.6	42.8	45.3	48.7	52.2
85°	20.7	20.0	21.0	21.3	20.7	21.7	22.4	23.7	24.7	26.4	28.1
87.5°	7.8	8.7	8.6	9.1	9.3	10.1	10.0	11.1	11.9	12.6	12.6
90°	5.6	7.0	7.7	9.1	9.7	11.1	11.9	12.6	13.3	13.9	15.3
92.5°	36.8	57.2	95.2	159.1	228.4	224.8	182.0	123.6	89.7	67.5	57.2
95°	52.3	83.6	158.3	311.7	504.1	617.8	604.5	501.3	395.3	309.6	251.0
97.5°	64.4	87.0	136.3	248.8	450.1	659.7	764.8	746.6	672.3	588.7	507.3
100°	73.9	94.8	135.3	225.9	401.6	629.6	803.9	857.6	823.4	751.6	679.1
102.5°	83.9	104.3	140.3	216.4	364.8	576.6	780.5	894.9	916.1	881.5	832.5
105°	100.4	119.9	150.6	212.7	329.1	505.5	705.6	872.9	968.5	999.2	991.5
107.5°	118.7	136.3	165.9	219.1	314.1	456.6	629.2	794.2	921.8	1000.5	1036.9
110°	130.4	148.5	177.1	225.2	309.6	433.6	585.7	736.3	868.7	967.1	1026.3



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.7	160.2	187.7	233.0	309.6	420.3	553.3	690.5	816.3	915.7	985.6
115°	161.0	178.5	204.3	244.7	311.7	405.8	518.0	633.1	741.2	836.7	912.7
117.5°	180.0	196.9	221.3	258.2	316.3	398.7	497.0	596.0	689.1	771.4	841.2
120°	191.7	209.2	233.5	267.1	320.7	395.3	485.3	575.9	659.6	736.3	797.6
122.5°	203.5	220.9	245.3	277.1	324.6	392.5	475.2	560.9	638.4	706.7	764.2
125°	219.6	237.7	260.7	290.7	331.2	389.1	461.5	539.0	610.1	670.7	720.9
127.5°	235.4	253.5	275.7	303.3	338.6	387.4	449.0	516.7	583.0	639.6	686.6
130°	245.4	263.6	285.2	311.7	343.0	386.3	440.7	502.7	564.1	618.4	663.8
132.5°	254.3	272.5	294.1	318.9	348.0	386.3	434.0	488.7	546.2	595.6	639.2
135°	265.6	284.5	306.1	329.1	354.9	386.3	426.0	470.6	518.7	563.4	603.1
137.5°	275.5	294.9	314.6	336.6	361.1	387.1	418.9	455.3	494.2	531.3	565.0
140°	281.7	300.5	320.7	341.6	363.9	387.6	415.5	446.9	479.7	511.8	541.0
142.5°	287.8	305.5	324.6	344.5	365.6	388.3	412.8	439.7	467.4	495.0	520.4
145°	297.0	313.1	331.2	348.6	367.5	387.6	408.6	430.2	451.8	473.4	492.2
147.5°	305.4	319.5	335.4	351.2	368.1	385.8	404.2	421.2	438.8	455.4	469.7
150°	310.9	322.8	338.1	352.8	368.1	384.1	400.9	416.3	431.6	444.8	457.4
152.5°	316.0	326.7	340.9	353.9	367.6	381.9	397.0	410.6	424.4	436.5	446.2
155°	322.1	331.9	343.8	354.9	366.0	377.9	390.5	402.3	413.5	423.2	430.9
157.5°	328.5	335.9	346.1	355.6	364.3	373.7	384.3	394.0	403.1	410.6	416.7
160°	331.9	338.1	347.2	355.6	362.6	371.0	379.3	388.3	395.3	402.3	407.2
162.5°	335.2	340.4	348.3	355.0	360.9	367.6	374.8	382.2	388.6	394.5	398.8
165°	338.9	343.0	348.6	354.2	358.4	362.6	368.1	373.7	378.6	382.8	386.3
167.5°	341.3	344.0	348.6	352.5	354.5	357.7	361.6	365.6	368.8	372.0	374.5
170°	343.0	345.1	348.6	351.4	352.8	354.9	357.7	361.1	363.3	365.3	366.8
172.5°	344.1	345.1	348.0	350.3	350.5	351.5	353.7	356.1	358.2	359.8	360.6
175°	345.1	345.1	347.2	348.6	347.9	347.9	348.6	350.7	350.7	352.1	352.1
177.5°	345.3	345.3	346.3	347.0	345.8	345.8	346.3	347.0	347.5	347.5	347.5
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	760.4	762.3	760.7	762.9	760.7	762.3	760.4	762.1	764.5	762.9	766.6
5°	700.9	697.8	699.8	698.5	699.8	697.8	700.9	702.6	706.6	707.9	710.7
7.5°	645.9	642.9	639.6	638.0	639.6	642.9	645.9	646.8	650.3	655.4	659.2
10°	611.4	607.7	607.3	605.0	607.3	607.7	611.4	615.2	617.5	623.9	628.4
12.5°	586.2	582.7	578.9	577.9	578.9	582.7	586.2	589.4	590.1	597.4	600.5
15°	550.5	547.8	545.4	547.4	545.4	547.8	550.5	552.5	556.2	561.3	564.7
17.5°	520.7	518.4	518.1	515.6	518.1	518.4	520.7	521.8	528.0	531.3	537.1
20°	502.0	500.3	501.0	496.6	501.0	500.3	502.0	505.1	511.1	512.8	519.0
22.5°	487.1	483.8	483.4	482.5	483.4	483.8	487.1	489.9	491.1	496.3	500.5
25°	463.8	462.1	460.4	462.1	460.4	462.1	463.8	466.8	468.1	471.9	475.9
27.5°	443.4	441.3	440.9	441.0	440.9	441.3	443.4	443.1	446.7	449.7	452.7
30°	430.9	427.5	427.8	427.5	427.8	427.5	430.9	430.9	432.9	435.6	438.4
32.5°	417.3	415.0	414.6	413.9	414.6	415.0	417.3	416.8	419.4	422.6	425.6
35°	397.3	397.3	395.7	395.7	395.7	397.3	397.3	398.3	401.1	401.1	404.5
37.5°	378.5	378.3	377.2	377.4	377.2	378.3	378.5	379.4	380.3	381.7	384.0
40°	364.4	364.2	363.1	361.1	363.1	364.2	364.4	365.9	366.5	368.2	369.5
42.5°	351.0	349.8	349.3	348.7	349.3	349.8	351.0	351.8	352.1	354.4	357.1
45°	329.6	329.6	329.0	328.6	329.0	329.6	329.6	329.6	329.9	332.6	334.0
47.5°	308.9	309.5	310.8	310.6	310.8	309.5	308.9	308.4	308.4	309.8	311.4
50°	296.4	296.8	297.7	298.1	297.7	296.8	296.4	295.1	294.4	294.4	295.4
52.5°	282.6	284.5	285.8	285.6	285.8	284.5	282.6	281.5	280.3	278.7	280.2
55°	263.2	265.6	268.0	268.3	268.0	265.6	263.2	260.1	258.8	256.1	257.1
57.5°	244.1	247.4	249.9	250.7	249.9	247.4	244.1	240.4	235.9	234.7	232.8
60°	231.0	235.4	238.4	239.9	238.4	235.4	231.0	227.7	221.9	218.1	216.8
62.5°	218.6	223.5	226.6	226.9	226.6	223.5	218.6	213.3	207.5	203.2	200.5
65°	198.1	203.2	206.0	207.9	206.0	203.2	198.1	192.4	186.0	180.2	177.2
67.5°	176.2	181.3	184.3	185.9	184.3	181.3	176.2	169.1	163.2	156.6	153.0
70°	160.2	165.3	169.3	170.8	169.3	165.3	160.2	151.8	146.7	140.5	137.5
72.5°	144.5	149.0	152.3	153.9	152.3	149.0	144.5	136.6	130.7	124.6	120.5
75°	117.2	123.3	126.4	128.0	126.4	123.3	117.2	112.8	106.0	99.6	96.2
77.5°	90.4	95.9	97.7	98.6	97.7	95.9	90.4	85.2	80.1	75.4	72.1
80°	72.5	75.9	78.3	78.6	78.3	75.9	72.5	68.4	64.4	59.9	56.9
82.5°	55.7	58.5	59.3	60.2	59.3	58.5	55.7	52.2	48.7	45.3	42.8
85°	30.5	31.8	32.2	31.8	32.2	31.8	30.5	28.1	26.4	24.7	23.7
87.5°	13.1	12.8	12.9	13.5	12.9	12.8	13.1	12.6	12.6	11.9	11.1
90°	15.3	15.3	16.1	16.1	16.1	15.3	15.3	15.3	13.9	13.3	12.6
92.5°	48.2	46.5	45.6	44.5	45.6	46.5	48.2	57.2	67.5	89.7	123.6
95°	201.5	180.6	175.0	163.8	175.0	180.6	201.5	251.0	309.6	395.3	501.3
97.5°	464.2	425.2	404.9	396.0	404.9	425.2	464.2	507.3	588.7	672.3	746.6
100°	631.0	580.8	555.0	543.9	555.0	580.8	631.0	679.1	751.6	823.4	857.6
102.5°	781.0	745.3	717.3	708.9	717.3	745.3	781.0	832.5	881.5	916.1	894.9
105°	969.1	946.1	932.2	923.8	932.2	946.1	969.1	991.5	999.2	968.5	872.9
107.5°	1048.2	1048.0	1043.5	1037.9	1043.5	1048.0	1048.2	1036.9	1000.5	921.8	794.2
110°	1057.7	1070.9	1075.8	1075.8	1075.8	1070.9	1057.7	1026.3	967.1	868.7	736.3



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1031.4	1054.2	1066.3	1071.4	1066.3	1054.2	1031.4	985.6	915.7	816.3	690.5
115°	967.1	1000.5	1020.0	1029.1	1020.0	1000.5	967.1	912.7	836.7	741.2	633.1
117.5°	895.5	930.1	949.5	955.0	949.5	930.1	895.5	841.2	771.4	689.1	596.0
120°	849.2	882.7	901.5	907.0	901.5	882.7	849.2	797.6	736.3	659.6	575.9
122.5°	810.2	840.9	859.7	864.7	859.7	840.9	810.2	764.2	706.7	638.4	560.9
125°	760.0	788.5	803.9	810.8	803.9	788.5	760.0	720.9	670.7	610.1	539.0
127.5°	722.0	747.3	761.8	764.8	761.8	747.3	722.0	686.6	639.6	583.0	516.7
130°	698.7	721.7	735.6	739.8	735.6	721.7	698.7	663.8	618.4	564.1	502.7
132.5°	674.0	697.1	709.9	714.6	709.9	697.1	674.0	639.2	595.6	546.2	488.7
135°	633.7	656.7	669.3	673.5	669.3	656.7	633.7	603.1	563.4	518.7	470.6
137.5°	592.5	613.4	625.0	629.6	625.0	613.4	592.5	565.0	531.3	494.2	455.3
140°	566.9	585.0	595.4	598.9	595.4	585.0	566.9	541.0	511.8	479.7	446.9
142.5°	542.3	557.7	567.6	570.4	567.6	557.7	542.3	520.4	495.0	467.4	439.7
145°	509.0	520.8	528.5	531.3	528.5	520.8	509.0	492.2	473.4	451.8	430.2
147.5°	482.9	492.4	496.9	498.1	496.9	492.4	482.9	469.7	455.4	438.8	421.2
150°	467.9	476.2	479.0	479.7	479.0	476.2	467.9	457.4	444.8	431.6	416.3
152.5°	455.0	461.7	464.5	465.2	464.5	461.7	455.0	446.2	436.5	424.4	410.6
155°	437.8	442.7	444.8	445.5	444.8	442.7	437.8	430.9	423.2	413.5	402.3
157.5°	422.1	426.1	428.1	427.9	428.1	426.1	422.1	416.7	410.6	403.1	394.0
160°	412.1	415.5	417.0	416.3	417.0	415.5	412.1	407.2	402.3	395.3	388.3
162.5°	402.6	405.5	405.8	405.6	405.8	405.5	402.6	398.8	394.5	388.6	382.2
165°	389.1	390.5	390.5	390.5	390.5	390.5	389.1	386.3	382.8	378.6	373.7
167.5°	375.9	377.2	376.7	376.5	376.7	377.2	375.9	374.5	372.0	368.8	365.6
170°	368.1	368.8	368.8	368.1	368.8	368.8	368.1	366.8	365.3	363.3	361.1
172.5°	360.9	362.1	361.1	360.3	361.1	362.1	360.9	360.6	359.8	358.2	356.1
175°	352.1	352.8	351.4	350.7	351.4	352.8	352.1	352.1	352.1	350.7	350.7
177.5°	347.0	347.5	345.8	345.8	345.8	347.5	347.0	347.5	347.5	347.5	347.0
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	763.1	766.3	770.4	773.4	778.8	781.2	784.3	786.7	791.0	795.0	800.0
5°	711.7	717.5	725.2	733.7	743.5	750.3	759.8	765.5	777.0	787.6	797.7
7.5°	665.0	672.2	683.1	694.0	706.9	718.5	730.4	743.5	758.2	775.6	790.0
10°	633.1	642.6	654.4	668.0	683.6	697.1	713.0	727.3	745.2	765.5	784.5
12.5°	607.6	615.7	629.0	641.9	658.6	675.2	691.6	710.5	731.4	753.9	777.8
15°	572.5	579.3	590.0	608.1	625.0	641.2	665.9	683.6	710.0	735.0	763.8
17.5°	542.4	550.9	560.0	575.4	592.9	613.2	635.3	657.5	682.9	714.7	747.2
20°	524.1	530.8	541.3	553.1	571.8	592.1	613.1	635.4	666.6	699.5	734.4
22.5°	504.0	511.3	523.2	536.1	551.7	571.2	594.4	618.9	651.5	683.8	721.7
25°	480.4	485.4	496.2	507.7	523.3	539.9	564.0	591.1	623.3	660.2	698.8
27.5°	458.1	462.5	472.4	482.4	496.5	516.2	537.7	565.1	595.4	632.8	675.6
30°	442.0	446.8	455.6	466.5	480.0	497.3	519.3	545.0	577.6	614.1	658.9
32.5°	428.2	432.5	439.1	450.0	463.2	479.9	500.3	526.6	559.1	596.3	640.2
35°	406.8	411.5	416.6	425.1	436.7	452.9	475.3	500.0	531.1	567.0	607.3
37.5°	385.6	390.7	395.2	402.8	413.3	427.7	447.0	472.8	501.0	535.6	574.3
40°	372.3	376.3	380.0	388.2	398.7	412.2	430.2	453.3	483.0	515.2	547.4
42.5°	359.0	362.7	366.0	373.0	382.7	395.7	412.9	435.3	463.0	493.0	521.4
45°	338.0	340.5	344.2	350.3	358.0	369.9	386.5	406.5	429.9	458.3	479.7
47.5°	315.4	319.1	322.2	327.5	333.9	345.5	361.5	378.5	399.8	420.9	435.9
50°	298.1	301.8	306.2	311.3	317.4	328.2	342.8	360.1	378.0	394.3	407.2
52.5°	281.9	285.3	290.0	294.8	302.2	311.5	323.9	339.2	356.9	368.5	379.2
55°	257.8	259.5	264.9	269.7	276.8	283.6	296.0	309.6	320.5	329.2	338.0
57.5°	233.2	235.5	238.6	242.9	249.9	257.9	266.6	278.7	285.0	289.5	296.4
60°	217.5	218.1	220.2	225.2	230.7	237.8	248.0	256.5	261.2	264.9	270.6
62.5°	200.1	200.3	203.7	207.4	211.4	219.1	227.4	234.2	238.2	240.0	245.5
65°	175.8	175.1	177.2	180.2	184.9	190.0	197.2	203.2	202.9	204.9	208.3
67.5°	151.0	150.3	150.3	153.2	157.0	161.6	166.5	170.0	170.0	172.7	174.4
70°	134.1	132.2	133.5	135.8	137.5	141.2	146.7	148.0	148.4	149.7	151.4
72.5°	116.8	116.1	117.2	118.2	119.4	122.3	126.9	127.7	127.8	128.6	131.3
75°	92.8	92.1	91.5	92.5	93.8	95.9	97.6	98.9	98.5	98.9	100.9
77.5°	69.6	67.7	67.3	67.9	68.2	69.5	71.2	71.1	71.4	71.3	73.7
80°	55.2	52.5	52.2	52.2	52.5	53.1	53.9	54.6	53.5	54.6	55.2
82.5°	40.6	39.0	38.9	38.6	38.7	38.8	39.2	39.6	39.4	39.9	40.3
85°	22.4	21.7	20.7	21.3	21.0	20.0	20.7	19.6	19.4	19.6	20.0
87.5°	10.0	10.1	9.3	9.1	8.6	8.7	7.8	7.3	6.8	6.8	7.5
90°	11.9	11.1	9.7	9.1	7.7	7.0	5.6	4.2	2.8	1.4	0.7
92.5°	182.0	224.8	228.4	159.1	95.2	57.2	36.8	24.8	16.1	10.3	8.5
95°	604.5	617.8	504.1	311.7	158.3	83.6	52.3	36.9	29.2	23.7	23.0
97.5°	764.8	659.7	450.1	248.8	136.3	87.0	64.4	50.6	43.0	39.1	38.2
100°	803.9	629.6	401.6	225.9	135.3	94.8	73.9	60.6	53.0	50.2	48.8
102.5°	780.5	576.6	364.8	216.4	140.3	104.3	83.9	71.8	63.6	61.3	60.5
105°	705.6	505.5	329.1	212.7	150.6	119.9	100.4	89.3	82.3	78.8	78.8
107.5°	629.2	456.6	314.1	219.1	165.9	136.3	118.7	107.1	101.4	98.0	96.7
110°	585.7	433.6	309.6	225.2	177.1	148.5	130.4	119.9	113.6	110.8	109.5



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	553.3	420.3	309.6	233.0	187.7	160.2	142.7	132.2	125.9	123.7	122.3
115°	518.0	405.8	311.7	244.7	204.3	178.5	161.0	150.6	144.4	142.2	140.8
117.5°	497.0	398.7	316.3	258.2	221.3	196.9	180.0	168.2	161.9	159.7	157.6
120°	485.3	395.3	320.7	267.1	233.5	209.2	191.7	179.9	173.6	170.9	168.7
122.5°	475.2	392.5	324.6	277.1	245.3	220.9	203.5	190.5	184.2	182.0	180.5
125°	461.5	389.1	331.2	290.7	260.7	237.7	219.6	206.3	200.1	196.6	195.2
127.5°	449.0	387.4	338.6	303.3	275.7	253.5	235.4	221.3	213.4	208.9	206.8
130°	440.7	386.3	343.0	311.7	285.2	263.6	245.4	230.8	221.7	216.2	214.0
132.5°	434.0	386.3	348.0	318.9	294.1	272.5	254.3	239.2	229.0	222.3	219.6
135°	426.0	386.3	354.9	329.1	306.1	284.5	265.6	251.0	239.9	231.5	228.7
137.5°	418.9	387.1	361.1	336.6	314.6	294.9	275.5	261.2	250.0	242.2	240.1
140°	415.5	387.6	363.9	341.6	320.7	300.5	281.7	268.4	257.3	248.9	246.8
142.5°	412.8	388.3	365.6	344.5	324.6	305.5	287.8	275.1	263.9	256.2	254.6
145°	408.6	387.6	367.5	348.6	331.2	313.1	297.0	284.5	274.7	267.7	266.4
147.5°	404.2	385.8	368.1	351.2	335.4	319.5	305.4	294.5	285.4	279.5	278.6
150°	400.9	384.1	368.1	352.8	338.1	322.8	310.9	301.2	292.1	287.2	285.9
152.5°	397.0	381.9	367.6	353.9	340.9	326.7	316.0	306.7	298.8	294.5	293.6
155°	390.5	377.9	366.0	354.9	343.8	331.9	322.1	315.1	308.2	304.0	304.0
157.5°	384.3	373.7	364.3	355.6	346.1	335.9	328.5	322.4	316.4	313.1	313.2
160°	379.3	371.0	362.6	355.6	347.2	338.1	331.9	326.3	321.5	318.6	319.3
162.5°	374.8	367.6	360.9	355.0	348.3	340.4	335.2	330.7	326.5	323.7	324.3
165°	368.1	362.6	358.4	354.2	348.6	343.0	338.9	336.1	332.6	330.5	331.9
167.5°	361.6	357.7	354.5	352.5	348.6	344.0	341.3	339.4	337.4	336.2	336.9
170°	357.7	354.9	352.8	351.4	348.6	345.1	343.0	341.6	340.3	339.6	340.3
172.5°	353.7	351.5	350.5	350.3	348.0	345.1	344.1	343.3	341.9	341.3	342.5
175°	348.6	347.9	347.9	348.6	347.2	345.1	345.1	345.1	344.5	343.8	345.1
177.5°	346.3	345.8	345.8	347.0	346.3	345.3	345.3	345.8	345.3	345.3	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	802.5	806.2	808.6	813.2	817.1	819.2	821.1	822.7	824.7	826.3	830.9
5°	807.5	816.4	823.9	835.4	845.9	854.0	862.7	870.6	877.0	886.2	893.2
7.5°	805.3	821.0	837.4	855.2	873.4	890.4	905.9	920.5	933.7	949.7	963.7
10°	803.2	824.5	845.5	869.5	894.3	915.3	935.0	954.9	969.5	989.8	1007.1
12.5°	801.6	826.7	852.0	880.9	908.1	937.7	963.9	978.5	1000.7	1016.9	1037.4
15°	794.7	827.9	862.7	895.3	933.9	961.4	984.4	1012.8	1033.5	1054.2	1076.5
17.5°	782.4	820.0	859.1	901.7	938.7	968.2	997.8	1025.3	1050.0	1077.6	1105.5
20°	776.8	814.3	859.1	902.8	939.0	969.8	1000.3	1030.5	1057.6	1093.1	1125.2
22.5°	764.8	810.3	851.5	894.0	931.4	964.9	999.5	1033.7	1069.7	1109.9	1150.2
25°	743.5	789.6	833.3	875.3	912.9	954.9	991.8	1037.6	1083.6	1136.8	1187.0
27.5°	721.5	765.5	805.6	846.1	890.0	937.5	985.4	1037.3	1097.7	1164.8	1235.6
30°	703.6	745.2	784.2	825.8	871.6	925.1	977.6	1039.3	1109.0	1184.5	1268.5
32.5°	682.7	721.1	759.0	803.1	852.9	909.4	970.5	1038.1	1122.0	1207.9	1294.3
35°	647.0	679.2	718.1	765.2	821.4	886.2	957.0	1036.9	1133.1	1231.6	1304.5
37.5°	604.7	634.6	675.6	727.3	786.2	855.7	939.7	1034.5	1136.7	1215.2	1238.8
40°	576.2	604.0	646.7	700.2	760.5	834.0	926.1	1026.4	1125.2	1175.5	1156.1
42.5°	545.8	575.0	616.6	669.6	734.4	814.5	909.0	1009.3	1092.3	1111.2	1044.5
45°	497.9	528.1	569.1	622.6	692.4	779.1	877.7	968.8	1016.6	982.3	879.0
47.5°	453.4	481.7	519.7	574.9	646.9	736.6	831.5	904.2	908.0	826.3	716.0
50°	423.1	449.2	487.4	542.7	614.1	704.9	790.6	847.8	822.2	729.7	623.7
52.5°	393.2	418.8	456.6	511.2	581.9	665.0	744.8	785.0	736.5	641.6	551.0
55°	350.3	372.6	409.6	460.0	527.1	604.3	672.1	685.9	622.9	529.4	455.9
57.5°	308.3	329.1	362.7	409.2	470.5	539.0	591.9	589.0	522.4	442.1	383.8
60°	279.8	300.1	329.9	375.3	431.2	490.2	535.6	524.7	458.7	389.6	340.5
62.5°	254.3	272.5	300.7	340.4	391.4	445.9	483.2	467.3	402.5	342.1	303.3
65°	216.8	232.0	256.1	290.0	332.3	377.4	406.2	385.5	330.3	283.2	252.0
67.5°	180.9	193.1	213.3	240.4	276.5	312.6	330.2	309.4	265.2	230.9	207.8
70°	158.2	169.1	184.6	208.7	240.1	270.6	283.8	265.2	227.3	197.8	181.2
72.5°	135.5	144.4	158.1	179.7	204.9	231.4	242.9	225.2	193.9	169.1	153.6
75°	104.7	110.8	120.3	135.2	155.2	176.1	182.6	167.0	147.0	128.4	118.2
77.5°	74.9	80.1	87.3	96.7	110.8	124.2	129.8	120.8	105.3	93.5	85.2
80°	57.6	60.3	66.4	74.2	85.3	93.8	97.6	91.8	81.0	72.1	65.7
82.5°	41.0	43.8	47.4	53.9	61.0	66.7	70.7	66.9	59.0	52.1	48.3
85°	20.0	21.7	23.7	26.4	31.8	35.2	34.9	32.5	29.4	26.8	24.7
87.5°	7.3	7.8	9.0	10.6	11.7	12.9	13.7	13.4	12.6	11.9	11.1
90°	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9	12.6
92.5°	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0	123.6
95°	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5	501.3
97.5°	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8	746.6
100°	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9	857.6
102.5°	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5	894.9
105°	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6	872.9
107.5°	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2	794.2
110°	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7	736.3



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3	690.5
115°	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0	633.1
117.5°	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0	596.0
120°	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3	575.9
122.5°	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2	560.9
125°	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5	539.0
127.5°	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0	516.7
130°	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7	502.7
132.5°	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0	488.7
135°	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0	470.6
137.5°	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9	455.3
140°	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5	446.9
142.5°	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8	439.7
145°	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6	430.2
147.5°	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2	421.2
150°	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9	416.3
152.5°	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0	410.6
155°	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5	402.3
157.5°	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3	394.0
160°	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3	388.3
162.5°	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8	382.2
165°	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1	373.7
167.5°	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6	365.6
170°	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7	361.1
172.5°	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7	356.1
175°	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6	350.7
177.5°	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3	347.0
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	798.1	798.1	798.1	798.1	798.1	798.1	798.1
2.5°	834.6	836.8	841.4	839.8	842.0	843.0	844.2
5°	902.1	912.9	917.7	916.9	924.1	922.4	920.7
7.5°	978.2	989.6	996.0	1003.9	1008.5	1008.8	1012.8
10°	1021.3	1036.2	1042.3	1050.8	1056.2	1059.3	1058.9
12.5°	1054.4	1066.0	1079.7	1083.9	1091.2	1095.0	1093.6
15°	1094.1	1112.8	1126.9	1134.1	1143.3	1145.9	1149.7
17.5°	1129.6	1154.6	1171.3	1193.3	1201.7	1206.8	1203.7
20°	1156.5	1189.3	1205.9	1232.3	1246.9	1254.7	1252.0
22.5°	1188.2	1223.7	1254.5	1277.3	1299.5	1310.0	1312.2
25°	1242.5	1291.3	1336.3	1366.5	1393.9	1400.3	1414.6
27.5°	1303.2	1360.8	1408.9	1440.6	1459.7	1466.9	1471.3
30°	1341.4	1398.6	1434.9	1455.2	1461.3	1460.6	1460.0
32.5°	1360.1	1396.0	1402.9	1397.2	1383.3	1371.5	1359.1
35°	1333.6	1306.9	1266.9	1215.4	1177.5	1139.2	1135.4
37.5°	1199.4	1113.8	1047.3	973.0	930.1	903.7	885.3
40°	1073.1	975.9	895.3	832.6	788.9	771.7	754.7
42.5°	936.0	843.1	771.7	719.3	686.5	667.4	653.9
45°	760.5	678.5	622.6	584.7	558.6	543.7	535.2
47.5°	623.1	562.5	515.1	487.7	469.7	458.1	458.1
50°	549.5	491.5	460.0	438.4	422.8	413.6	415.3
52.5°	484.1	440.9	413.9	395.7	384.2	378.6	378.4
55°	404.8	373.6	356.1	342.8	335.0	328.6	329.9
57.5°	346.3	319.9	308.2	297.2	291.8	289.2	285.5
60°	310.0	289.6	279.5	270.6	265.2	263.2	259.5
62.5°	277.7	261.7	251.8	244.6	239.8	239.1	236.1
65°	233.4	221.2	212.4	209.0	203.9	202.6	202.6
67.5°	192.4	183.7	176.8	173.7	171.5	171.8	170.1
70°	166.7	159.5	155.2	151.8	150.1	150.4	149.0
72.5°	145.8	137.9	134.0	132.0	129.7	130.6	130.1
75°	110.4	106.4	104.3	102.3	100.9	100.2	99.6
77.5°	81.1	77.5	76.0	74.8	75.0	73.4	74.6
80°	62.7	59.7	58.6	56.9	56.5	56.5	56.3
82.5°	45.8	44.1	43.4	42.0	41.4	41.9	41.0
85°	23.7	22.4	22.0	22.0	21.3	20.7	22.4
87.5°	11.3	10.3	10.6	10.3	10.3	10.3	9.7
90°	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333180-940

CATALOG NUMBER: S125DIP-S610D810U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)