

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333599-940

Luminaire Tested: **S125RDIP-S1090D1035U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333599-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6993.1 lumens  
Efficiency: N/A  
Efficacy: 115.6 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	63	57	59	55	51	51	47	44	43	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	46	41	38	38	36	33	30
5	70	59	51	45	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	33	29	34	29	26	29	26	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9469	9469	9469	9469
5°	10893	9481	8373	9481
10°	12496	9433	7389	9433
15°	13497	9336	6567	9336
20°	14882	9224	6064	9224
25°	17224	9075	5627	9075
30°	18744	8918	5341	8918
35°	15811	8736	5077	8736
40°	11042	8408	4850	8408
45°	8191	7965	4629	7965
50°	6531	7504	4439	7504
55°	5543	6933	4270	6933
60°	4790	6421	3995	6421
65°	4268	5868	3440	5868
70°	3750	5374	3136	5374
75°	3244	4654	2944	4654
80°	2462	3916	2462	3916
85°	2045	3083	2319	3083



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.6	2.0
10°-20°	412.0	5.9
20°-30°	653.3	9.3
30°-40°	787.8	11.3
40°-50°	703.5	10.1
50°-60°	539.5	7.7
60°-70°	350.6	5.0
70°-80°	170.5	2.4
80°-90°	43.2	0.6
90°-100°	76.6	1.1
100°-110°	226.3	3.2
110°-120°	383.2	5.5
120°-130°	504.3	7.2
130°-140°	565.1	8.1
140°-150°	553.9	7.9
150°-160°	465.2	6.7
160°-170°	309.2	4.4
170°-180°	108.2	1.5
0°-30°	1205.9	17.2
0°-40°	1993.7	28.5
0°-60°	3236.7	46.3
0°-90°	3801.0	54.4
90°-120°	686.1	9.8
90°-150°	2309.5	33.0
90°-180°	3192.0	45.6
0°-180°	6993.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1466	1466	1466	1466	1466	
5°	1680	1462	1292	1462	1680	168
15°	2019	1396	982	1396	2019	578
25°	2417	1274	790	1274	2417	1110
35°	2005	1108	644	1108	2005	1211
45°	897	872	507	872	897	716
55°	492	616	379	616	492	447
65°	279	384	225	384	279	278
75°	130	186	118	186	130	138
85°	28	42	31	42	28	32
90°	21	1	21	1	21	14
95°	77	58	77	58	77	78
105°	221	203	221	203	221	234
115°	387	384	387	384	387	383
125°	564	560	564	560	564	503
135°	731	728	731	728	731	564
145°	886	882	886	882	886	553
155°	1010	1010	1010	1010	1010	465
165°	1095	1098	1095	1098	1095	309
175°	1137	1141	1137	1141	1137	108
180°	1144	1144	1144	1144	1144	



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1542.2	1541.2	1543.2	1537.8	1538.4	1530.2	1530.2	1523.9	1515.7	1509.5	1506.5
5°	1680.3	1681.6	1679.2	1670.2	1664.1	1655.1	1644.8	1626.8	1611.8	1597.3	1585.9
7.5°	1822.7	1823.5	1815.5	1812.8	1797.6	1786.5	1763.8	1739.2	1717.4	1689.8	1668.6
10°	1905.5	1904.9	1896.4	1889.8	1876.6	1859.8	1837.5	1808.6	1781.5	1751.4	1722.5
12.5°	1953.6	1952.0	1949.4	1941.3	1929.0	1914.1	1895.2	1866.8	1833.4	1800.5	1766.8
15°	2018.7	2014.4	2006.6	1996.4	1978.9	1961.4	1940.4	1915.1	1883.2	1845.8	1814.6
17.5°	2099.0	2099.2	2087.1	2072.9	2049.2	2018.4	1985.8	1945.1	1901.8	1860.7	1827.4
20°	2165.4	2163.6	2151.6	2124.0	2096.9	2058.3	2021.1	1971.0	1918.1	1864.6	1823.0
22.5°	2260.8	2256.1	2243.5	2207.3	2165.3	2115.7	2058.6	1997.5	1933.5	1872.7	1818.2
25°	2417.1	2413.4	2388.7	2346.6	2287.7	2211.2	2136.5	2052.9	1960.9	1880.8	1814.6
27.5°	2523.9	2520.0	2501.7	2466.7	2412.3	2331.8	2230.8	2119.0	2004.0	1893.9	1798.5
30°	2513.4	2522.4	2520.0	2503.7	2462.8	2390.6	2297.3	2171.5	2034.9	1905.5	1791.7
32.5°	2362.1	2370.3	2391.4	2423.3	2425.7	2396.8	2327.1	2211.0	2069.6	1922.4	1786.5
35°	2005.4	2016.2	2057.2	2121.6	2205.8	2276.2	2290.6	2228.0	2101.0	1942.8	1778.5
37.5°	1541.7	1600.9	1635.4	1703.2	1830.5	1960.0	2084.6	2130.5	2076.3	1934.4	1765.6
40°	1309.7	1324.1	1385.5	1461.9	1569.1	1703.9	1881.4	2009.6	2013.8	1915.1	1745.3
42.5°	1120.9	1139.2	1181.3	1242.3	1334.1	1468.9	1652.3	1821.3	1899.7	1862.2	1718.9
45°	896.8	910.6	941.3	988.3	1058.6	1170.0	1327.7	1523.3	1678.6	1739.4	1647.9
47.5°	736.6	744.1	770.9	806.6	858.7	939.9	1061.9	1231.7	1418.0	1548.5	1535.7
50°	650.0	658.4	678.9	706.0	749.9	818.5	916.1	1057.5	1249.5	1408.9	1440.8
52.5°	582.6	589.6	602.4	627.9	664.2	716.9	795.7	923.6	1096.4	1266.0	1339.7
55°	492.3	497.1	507.4	521.8	550.7	588.6	656.7	745.1	884.8	1055.6	1164.0
57.5°	417.9	420.4	426.9	440.2	460.2	487.9	537.0	612.0	712.1	866.0	985.6
60°	370.8	373.2	381.6	390.6	406.3	431.5	470.0	522.4	618.7	745.7	866.7
62.5°	333.1	334.7	338.2	347.2	361.0	380.5	410.8	453.5	530.1	641.7	755.9
65°	279.3	279.8	281.1	288.3	296.7	311.1	331.0	361.1	418.9	503.2	604.2
67.5°	227.5	228.4	232.6	235.1	243.9	251.5	263.1	286.1	326.8	383.6	462.3
70°	198.6	198.0	202.2	205.3	208.2	217.3	225.1	243.8	269.0	312.4	378.0
72.5°	171.7	170.0	171.9	173.0	176.9	183.1	190.9	202.3	221.9	251.7	301.9
75°	130.0	130.6	130.6	131.8	134.8	137.2	139.6	145.6	156.5	176.4	203.4
77.5°	91.2	90.2	92.8	93.2	95.0	97.6	99.7	102.1	106.6	114.7	128.7
80°	66.2	66.2	66.8	68.6	68.0	69.2	72.2	74.6	80.1	84.9	89.7
82.5°	50.8	50.3	50.9	51.3	51.2	52.3	53.4	53.9	56.0	58.4	61.7
85°	27.6	27.6	28.3	28.3	28.9	28.9	29.5	29.5	29.5	30.1	30.7
87.5°	14.9	14.3	13.6	13.6	13.9	14.7	14.0	13.4	13.2	12.9	13.2
90°	21.4	20.8	20.2	19.6	19.0	18.2	17.2	16.2	15.2	14.3	12.8
92.5°	42.0	41.6	41.1	40.8	40.3	39.4	38.1	36.8	35.5	34.2	32.5
95°	76.6	76.2	75.8	75.3	75.0	74.1	72.7	71.3	69.9	68.6	66.6
97.5°	116.1	115.8	115.7	115.4	115.1	114.4	113.1	111.7	110.5	109.1	106.4
100°	146.0	145.6	145.2	144.8	144.5	143.3	141.5	139.7	137.9	136.2	133.7
102.5°	175.9	175.4	174.8	174.2	173.7	172.5	170.5	168.5	166.7	164.7	163.4
105°	220.8	220.2	219.6	219.0	218.4	217.5	216.3	215.2	213.9	212.8	211.6
107.5°	266.7	266.8	266.8	266.8	266.9	266.6	266.0	265.4	264.8	264.2	263.3
110°	300.9	301.1	301.3	301.5	301.7	301.5	300.9	300.3	299.7	299.1	298.5



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	334.4	334.7	335.1	335.5	335.8	335.8	335.6	335.3	335.0	334.7	333.9
115°	387.3	387.4	387.6	387.8	388.1	388.3	388.4	388.6	388.9	389.1	388.6
117.5°	438.9	439.7	440.5	441.2	442.0	442.4	442.2	442.0	441.9	441.8	441.4
120°	474.5	475.3	476.1	476.9	477.7	478.0	478.0	478.0	478.0	478.0	477.9
122.5°	510.1	510.8	511.4	512.0	512.6	513.0	513.2	513.4	513.5	513.6	513.2
125°	563.6	563.7	563.9	564.1	564.3	564.6	565.0	565.4	565.8	566.2	566.0
127.5°	614.8	615.2	615.5	616.0	616.4	616.7	616.9	617.1	617.2	617.5	617.2
130°	649.0	649.3	649.8	650.1	650.6	650.9	651.0	651.2	651.5	651.7	651.2
132.5°	681.0	681.6	682.2	682.7	683.2	683.6	683.9	684.0	684.2	684.4	684.5
135°	730.8	731.6	732.5	733.3	734.1	734.4	734.4	734.4	734.4	734.4	734.2
137.5°	779.7	780.7	781.7	782.7	783.6	784.0	783.7	783.5	783.3	783.0	782.7
140°	811.0	812.0	813.0	814.0	814.9	815.3	814.8	814.5	814.0	813.7	813.1
142.5°	840.9	842.0	842.9	843.9	844.9	845.3	845.0	844.8	844.5	844.3	843.6
145°	885.8	886.4	887.0	887.6	888.1	888.5	888.5	888.5	888.5	888.5	887.9
147.5°	924.1	925.4	926.8	928.1	929.4	929.9	929.4	928.9	928.4	928.0	927.5
150°	952.5	953.0	953.3	953.8	954.1	954.3	954.3	954.3	954.3	954.3	953.5
152.5°	976.1	976.8	977.5	978.2	978.9	979.0	978.6	978.1	977.6	977.1	976.8
155°	1009.5	1010.5	1011.5	1012.5	1013.5	1013.6	1012.8	1012.0	1011.2	1010.4	1010.2
157.5°	1037.5	1038.8	1040.1	1041.4	1042.7	1042.9	1042.1	1041.3	1040.6	1039.8	1039.6
160°	1056.7	1057.7	1058.7	1059.7	1060.7	1060.8	1060.0	1059.2	1058.4	1057.6	1057.4
162.5°	1073.1	1074.2	1075.4	1076.6	1077.7	1077.8	1076.8	1075.8	1075.0	1074.0	1074.0
165°	1095.0	1096.2	1097.3	1098.6	1099.7	1099.9	1099.1	1098.3	1097.6	1096.8	1096.5
167.5°	1112.4	1113.7	1114.9	1116.2	1117.3	1117.4	1116.2	1115.0	1113.8	1112.6	1112.6
170°	1121.7	1123.1	1124.4	1125.9	1127.2	1127.3	1126.1	1125.0	1123.8	1122.6	1122.6
172.5°	1129.5	1130.8	1132.0	1133.2	1134.4	1134.4	1133.3	1132.1	1130.9	1129.7	1129.7
175°	1136.8	1138.2	1139.6	1141.0	1142.4	1142.5	1141.3	1140.1	1138.9	1137.7	1137.7
177.5°	1141.1	1142.2	1143.4	1144.4	1145.6	1145.6	1144.7	1143.7	1142.8	1141.8	1142.0
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1506.5	1503.2	1496.9	1491.1	1483.9	1477.7	1473.4	1468.0	1461.3	1453.1	1446.4
5°	1573.2	1560.0	1542.6	1527.5	1508.2	1493.2	1477.6	1462.5	1447.4	1428.2	1411.3
7.5°	1647.2	1619.8	1593.2	1559.8	1529.5	1502.4	1476.3	1450.0	1424.2	1396.9	1370.6
10°	1692.4	1659.3	1622.6	1580.5	1541.9	1505.2	1471.5	1438.4	1403.6	1372.8	1339.7
12.5°	1734.8	1692.0	1650.0	1596.9	1550.6	1505.7	1462.9	1421.6	1384.3	1344.4	1308.9
15°	1773.1	1730.9	1684.0	1619.0	1554.6	1500.4	1449.8	1396.3	1350.0	1305.4	1265.7
17.5°	1787.9	1743.7	1689.2	1626.7	1556.3	1488.2	1423.0	1364.3	1309.7	1257.8	1213.2
20°	1782.1	1739.4	1683.4	1623.8	1548.5	1477.6	1407.1	1342.1	1281.4	1226.5	1179.0
22.5°	1768.1	1723.9	1669.9	1607.0	1535.5	1460.2	1385.0	1315.6	1252.0	1195.2	1143.4
25°	1747.2	1687.0	1631.7	1570.2	1502.3	1427.6	1350.0	1273.5	1205.5	1147.7	1091.2
27.5°	1725.4	1650.3	1579.8	1518.9	1447.0	1380.4	1305.6	1227.2	1155.7	1096.8	1038.8
30°	1705.7	1621.4	1543.7	1474.5	1406.5	1343.4	1272.3	1195.9	1122.5	1061.7	1002.7
32.5°	1681.1	1591.5	1506.2	1426.4	1360.8	1298.1	1233.8	1160.7	1089.2	1026.5	966.6
35°	1650.3	1536.0	1443.2	1358.3	1285.6	1224.8	1167.0	1108.0	1036.4	971.4	913.0
37.5°	1609.8	1480.1	1372.8	1280.4	1203.5	1142.5	1096.9	1043.0	977.7	915.4	861.2
40°	1585.3	1439.7	1322.2	1230.8	1150.1	1085.7	1043.0	997.3	937.7	879.3	825.1
42.5°	1552.6	1402.6	1271.2	1175.9	1094.8	1032.8	989.5	949.6	899.6	844.6	786.6
45°	1488.4	1330.7	1192.8	1090.6	1008.7	947.9	907.6	872.1	834.2	783.6	733.1
47.5°	1404.8	1255.7	1111.5	999.8	919.6	863.2	824.0	796.0	768.9	725.9	676.8
50°	1337.9	1194.1	1053.2	944.9	859.4	805.8	769.2	746.9	722.2	683.1	642.2
52.5°	1258.9	1130.5	992.6	881.8	801.2	751.0	715.7	693.5	673.2	641.2	602.2
55°	1134.5	1022.0	895.5	795.0	721.0	670.5	636.8	615.7	603.7	576.6	545.9
57.5°	990.9	910.3	798.8	701.9	636.4	586.5	561.8	543.9	530.2	511.1	489.5
60°	890.7	834.2	734.2	642.2	582.0	534.4	512.2	497.1	484.5	468.2	451.4
62.5°	789.2	748.0	661.1	582.0	526.6	486.8	465.9	452.4	437.8	426.9	410.5
65°	653.0	616.3	556.1	494.1	443.0	411.1	396.0	384.0	375.0	362.9	351.5
67.5°	508.0	493.0	451.5	408.8	372.0	343.7	330.6	322.3	311.4	304.2	296.3
70°	418.9	411.7	382.2	353.9	319.6	300.3	288.3	284.6	271.4	264.2	258.8
72.5°	339.9	336.5	319.6	300.0	275.8	259.0	247.8	243.8	235.3	229.5	226.0
75°	232.9	234.2	231.1	218.5	209.5	198.6	189.0	186.5	180.6	175.8	172.7
77.5°	147.3	153.5	153.7	153.1	149.5	142.9	138.9	137.1	131.2	129.4	128.7
80°	101.1	107.7	113.8	113.2	111.9	110.1	107.1	105.3	102.3	100.5	99.3
82.5°	67.4	73.6	78.6	81.9	81.6	79.8	77.8	77.0	76.3	75.0	74.7
85°	31.9	33.1	34.9	39.1	42.1	42.7	42.1	41.6	39.7	40.3	40.9
87.5°	13.4	13.1	13.3	13.0	12.2	14.3	15.4	15.6	15.0	14.3	13.6
90°	11.5	10.1	8.7	7.2	5.6	4.0	2.5	0.9	2.5	4.0	5.6
92.5°	30.8	29.1	27.4	25.9	24.9	23.7	22.6	21.6	22.6	23.7	24.9
95°	64.6	62.6	60.6	59.5	59.0	58.7	58.2	57.9	58.2	58.7	59.0
97.5°	103.7	100.9	98.3	96.8	96.7	96.5	96.3	96.1	96.3	96.5	96.7
100°	131.1	128.5	125.9	124.7	124.7	124.7	124.7	124.7	124.7	124.7	124.7
102.5°	162.1	160.8	159.4	158.5	157.7	156.9	156.0	155.2	156.0	156.9	157.7
105°	210.4	209.2	208.0	207.0	206.0	204.9	203.9	203.0	203.9	204.9	206.0
107.5°	262.4	261.4	260.6	259.7	258.7	257.6	256.6	255.7	256.6	257.6	258.7
110°	297.9	297.3	296.8	296.0	295.0	294.0	293.0	292.0	293.0	294.0	295.0





TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.2	332.5	331.7	331.1	330.6	330.0	329.6	329.0	329.6	330.0	330.6
115°	388.3	387.8	387.4	386.8	386.1	385.3	384.5	383.7	384.5	385.3	386.1
117.5°	441.0	440.7	440.3	440.0	439.6	439.3	438.9	438.5	438.9	439.3	439.6
120°	477.7	477.4	477.2	476.7	475.7	474.7	473.7	472.7	473.7	474.7	475.7
122.5°	512.6	512.1	511.6	511.2	510.9	510.5	510.1	509.8	510.1	510.5	510.9
125°	565.8	565.6	565.4	564.7	563.6	562.3	561.2	560.0	561.2	562.3	563.6
127.5°	617.0	616.8	616.5	616.1	615.4	614.7	614.0	613.4	614.0	614.7	615.4
130°	650.9	650.5	650.1	649.3	648.4	647.4	646.4	645.4	646.4	647.4	648.4
132.5°	684.6	684.7	684.7	683.9	682.3	680.7	679.1	677.4	679.1	680.7	682.3
135°	734.1	733.9	733.7	733.0	731.7	730.6	729.4	728.3	729.4	730.6	731.7
137.5°	782.2	781.8	781.3	780.5	779.4	778.2	777.0	776.0	777.0	778.2	779.4
140°	812.5	811.9	811.3	810.5	809.5	808.5	807.5	806.6	807.5	808.5	809.5
142.5°	842.8	842.0	841.3	840.5	839.6	838.8	838.0	837.1	838.0	838.8	839.6
145°	887.3	886.7	886.1	885.4	884.6	883.8	883.1	882.3	883.1	883.8	884.6
147.5°	927.0	926.6	926.1	925.6	925.2	924.8	924.3	923.9	924.3	924.8	925.2
150°	952.8	952.0	951.2	950.9	951.1	951.3	951.5	951.6	951.5	951.3	951.1
152.5°	976.5	976.2	975.9	975.5	975.3	975.0	974.7	974.5	974.7	975.0	975.3
155°	1010.0	1009.9	1009.6	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5
157.5°	1039.4	1039.2	1039.0	1039.1	1039.6	1040.0	1040.4	1040.9	1040.4	1040.0	1039.6
160°	1057.2	1057.0	1056.9	1057.0	1057.6	1058.2	1058.8	1059.4	1058.8	1058.2	1057.6
162.5°	1073.9	1073.9	1073.8	1074.1	1074.4	1074.9	1075.3	1075.8	1075.3	1074.9	1074.4
165°	1096.4	1096.2	1096.0	1096.1	1096.4	1096.9	1097.3	1097.7	1097.3	1096.9	1096.4
167.5°	1112.6	1112.6	1112.6	1113.0	1113.8	1114.6	1115.4	1116.2	1115.4	1114.6	1113.8
170°	1122.6	1122.6	1122.6	1123.0	1123.8	1124.5	1125.3	1126.1	1125.3	1124.5	1123.8
172.5°	1129.7	1129.7	1129.7	1130.2	1130.9	1131.7	1132.5	1133.3	1132.5	1131.7	1130.9
175°	1137.7	1137.7	1137.7	1138.1	1138.9	1139.7	1140.5	1141.3	1140.5	1139.7	1138.9
177.5°	1142.1	1142.3	1142.5	1142.8	1143.4	1144.2	1144.8	1145.4	1144.8	1144.2	1143.4
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1441.5	1434.9	1430.0	1420.4	1413.6	1410.8	1405.4	1404.0	1409.3	1405.4	1405.0
5°	1398.7	1381.3	1367.4	1353.5	1338.5	1328.9	1314.5	1312.1	1308.4	1303.0	1301.8
7.5°	1347.3	1324.5	1306.7	1283.9	1264.0	1248.0	1229.9	1221.4	1216.7	1209.7	1200.3
10°	1312.6	1285.6	1261.5	1238.6	1214.0	1194.1	1176.0	1162.2	1153.2	1144.7	1141.1
12.5°	1278.4	1250.9	1220.0	1192.4	1164.8	1142.5	1122.6	1113.6	1103.6	1093.7	1085.3
15°	1225.4	1188.7	1154.9	1123.0	1099.6	1075.5	1056.2	1043.0	1028.0	1023.8	1007.5
17.5°	1169.0	1133.0	1093.6	1060.0	1032.8	1006.3	985.1	970.1	958.8	943.3	935.8
20°	1133.9	1091.2	1052.7	1022.0	991.8	960.6	938.9	926.2	915.4	902.8	896.8
22.5°	1096.4	1054.5	1015.1	979.1	948.5	917.7	902.3	889.2	876.9	865.2	857.3
25°	1041.2	999.1	957.5	920.2	888.3	866.0	848.0	832.9	826.3	814.9	806.5
27.5°	986.7	941.9	898.8	861.6	836.6	814.6	799.8	787.8	775.9	765.9	758.6
30°	951.5	905.8	858.8	829.4	802.9	781.8	765.5	754.1	745.1	736.1	730.7
32.5°	916.4	869.2	827.5	795.7	770.6	752.4	735.7	724.8	715.2	705.3	698.8
35°	860.1	811.9	778.2	746.9	722.2	705.3	693.9	678.3	670.5	663.3	656.7
37.5°	807.7	762.9	726.5	699.0	677.5	660.8	646.0	637.6	627.9	621.4	615.9
40°	769.2	728.3	695.2	666.3	650.6	632.0	618.1	607.3	600.0	591.7	585.6
42.5°	734.5	696.4	664.3	638.3	618.8	603.1	589.7	578.9	569.7	563.7	558.7
45°	685.5	647.6	616.3	592.2	574.2	559.1	545.3	539.8	527.8	520.6	518.2
47.5°	634.8	600.9	570.7	548.5	530.0	515.8	502.7	491.7	485.1	478.0	474.1
50°	600.7	568.1	539.8	518.2	500.2	484.5	472.4	465.2	456.2	449.6	444.8
52.5°	566.5	536.4	508.1	487.4	471.7	456.1	442.6	435.4	426.9	422.6	419.3
55°	517.6	485.7	461.6	441.1	424.9	410.5	397.8	390.6	385.2	380.9	379.8
57.5°	462.3	436.9	414.6	396.1	379.2	365.7	354.6	347.8	343.0	342.3	338.8
60°	426.1	403.2	382.8	362.9	348.5	335.8	326.2	318.3	313.5	313.0	311.7
62.5°	390.0	368.1	349.1	331.6	318.6	306.5	297.3	288.6	285.6	282.7	280.0
65°	336.4	316.6	301.0	287.0	273.2	263.0	254.0	248.6	241.9	238.4	231.8
67.5°	283.8	268.4	253.4	241.7	230.9	221.1	213.7	205.6	201.2	198.2	193.4
70°	249.1	237.1	222.1	209.5	201.0	193.2	187.2	178.2	175.1	172.7	170.3
72.5°	216.4	205.8	193.2	183.0	174.5	167.2	160.2	156.0	153.0	150.6	149.2
75°	170.3	160.1	149.3	142.0	136.0	130.0	126.4	123.4	122.2	121.5	119.1
77.5°	125.1	119.7	111.0	105.2	101.2	98.8	95.6	94.0	93.9	91.2	90.4
80°	95.7	92.6	85.4	83.0	80.1	77.7	75.8	72.9	69.8	68.6	66.8
82.5°	71.2	68.1	65.3	61.3	58.9	57.4	55.6	54.5	54.9	53.2	52.3
85°	37.9	34.9	33.7	33.1	31.9	33.1	32.5	31.9	31.3	30.7	31.3
87.5°	13.5	13.8	13.6	14.8	13.6	14.4	14.6	14.4	14.5	14.7	14.4
90°	7.2	8.7	10.1	11.5	12.8	14.3	15.2	16.2	17.2	18.2	19.0
92.5°	25.9	27.4	29.1	30.8	32.5	34.2	35.5	36.8	38.1	39.4	40.3
95°	59.5	60.6	62.6	64.6	66.6	68.6	69.9	71.3	72.7	74.1	75.0
97.5°	96.8	98.3	100.9	103.7	106.4	109.1	110.5	111.7	113.1	114.4	115.1
100°	124.7	125.9	128.5	131.1	133.7	136.2	137.9	139.7	141.5	143.3	144.5
102.5°	158.5	159.4	160.8	162.1	163.4	164.7	166.7	168.5	170.5	172.5	173.7
105°	207.0	208.0	209.2	210.4	211.6	212.8	213.9	215.2	216.3	217.5	218.4
107.5°	259.7	260.6	261.4	262.4	263.3	264.2	264.8	265.4	266.0	266.6	266.9
110°	296.0	296.8	297.3	297.9	298.5	299.1	299.7	300.3	300.9	301.5	301.7



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	331.1	331.7	332.5	333.2	333.9	334.7	335.0	335.3	335.6	335.8	335.8
115°	386.8	387.4	387.8	388.3	388.6	389.1	388.9	388.6	388.4	388.3	388.1
117.5°	440.0	440.3	440.7	441.0	441.4	441.8	441.9	442.0	442.2	442.4	442.0
120°	476.7	477.2	477.4	477.7	477.9	478.0	478.0	478.0	478.0	478.0	477.7
122.5°	511.2	511.6	512.1	512.6	513.2	513.6	513.5	513.4	513.2	513.0	512.6
125°	564.7	565.4	565.6	565.8	566.0	566.2	565.8	565.4	565.0	564.6	564.3
127.5°	616.1	616.5	616.8	617.0	617.2	617.5	617.2	617.1	616.9	616.7	616.4
130°	649.3	650.1	650.5	650.9	651.2	651.7	651.5	651.2	651.0	650.9	650.6
132.5°	683.9	684.7	684.7	684.6	684.5	684.4	684.2	684.0	683.9	683.6	683.2
135°	733.0	733.7	733.9	734.1	734.2	734.4	734.4	734.4	734.4	734.4	734.1
137.5°	780.5	781.3	781.8	782.2	782.7	783.0	783.3	783.5	783.7	784.0	783.6
140°	810.5	811.3	811.9	812.5	813.1	813.7	814.0	814.5	814.8	815.3	814.9
142.5°	840.5	841.3	842.0	842.8	843.6	844.3	844.5	844.8	845.0	845.3	844.9
145°	885.4	886.1	886.7	887.3	887.9	888.5	888.5	888.5	888.5	888.5	888.1
147.5°	925.6	926.1	926.6	927.0	927.5	928.0	928.4	928.9	929.4	929.9	929.4
150°	950.9	951.2	952.0	952.8	953.5	954.3	954.3	954.3	954.3	954.3	954.1
152.5°	975.5	975.9	976.2	976.5	976.8	977.1	977.6	978.1	978.6	979.0	978.9
155°	1009.5	1009.6	1009.9	1010.0	1010.2	1010.4	1011.2	1012.0	1012.8	1013.6	1013.5
157.5°	1039.1	1039.0	1039.2	1039.4	1039.6	1039.8	1040.6	1041.3	1042.1	1042.9	1042.7
160°	1057.0	1056.9	1057.0	1057.2	1057.4	1057.6	1058.4	1059.2	1060.0	1060.8	1060.7
162.5°	1074.1	1073.8	1073.9	1073.9	1074.0	1074.0	1075.0	1075.8	1076.8	1077.8	1077.7
165°	1096.1	1096.0	1096.2	1096.4	1096.5	1096.8	1097.6	1098.3	1099.1	1099.9	1099.7
167.5°	1113.0	1112.6	1112.6	1112.6	1112.6	1112.6	1113.8	1115.0	1116.2	1117.4	1117.3
170°	1123.0	1122.6	1122.6	1122.6	1122.6	1122.6	1123.8	1125.0	1126.1	1127.3	1127.2
172.5°	1130.2	1129.7	1129.7	1129.7	1129.7	1129.7	1130.9	1132.1	1133.3	1134.4	1134.4
175°	1138.1	1137.7	1137.7	1137.7	1137.7	1137.7	1138.9	1140.1	1141.3	1142.5	1142.4
177.5°	1142.8	1142.5	1142.3	1142.1	1142.0	1141.8	1142.8	1143.7	1144.7	1145.6	1145.6
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1404.4	1399.2	1397.8	1399.6	1397.8	1399.2	1404.4	1405.0	1405.4	1409.3	1404.0
5°	1295.8	1289.8	1292.8	1291.6	1292.8	1289.8	1295.8	1301.8	1303.0	1308.4	1312.1
7.5°	1200.2	1192.8	1184.8	1187.3	1184.8	1192.8	1200.2	1200.3	1209.7	1216.7	1221.4
10°	1133.3	1127.3	1123.6	1126.7	1123.6	1127.3	1133.3	1141.1	1144.7	1153.2	1162.2
12.5°	1076.9	1073.4	1070.2	1068.9	1070.2	1073.4	1076.9	1085.3	1093.7	1103.6	1113.6
15°	1000.3	993.1	990.1	982.2	990.1	993.1	1000.3	1007.5	1023.8	1028.0	1043.0
17.5°	929.6	927.2	919.4	916.1	919.4	927.2	929.6	935.8	943.3	958.8	970.1
20°	887.7	885.3	877.5	882.3	877.5	885.3	887.7	896.8	902.8	915.4	926.2
22.5°	853.1	847.7	845.3	843.8	845.3	847.7	853.1	857.3	865.2	876.9	889.2
25°	804.1	796.2	793.3	789.6	793.3	796.2	804.1	806.5	814.9	826.3	832.9
27.5°	755.2	751.0	747.0	746.1	747.0	751.0	755.2	758.6	765.9	775.9	787.8
30°	723.4	719.3	716.2	716.2	716.2	719.3	723.4	730.7	736.1	745.1	754.1
32.5°	695.0	691.8	688.8	688.3	688.8	691.8	695.0	698.8	705.3	715.2	724.8
35°	653.6	648.8	647.6	644.0	647.6	648.8	653.6	656.7	663.3	670.5	678.3
37.5°	610.6	606.6	606.5	606.2	606.5	606.6	610.6	615.9	621.4	627.9	637.6
40°	583.2	580.1	579.6	575.3	579.6	580.1	583.2	585.6	591.7	600.0	607.3
42.5°	553.8	552.2	550.2	548.4	550.2	552.2	553.8	558.7	563.7	569.7	578.9
45°	514.0	509.8	509.8	506.8	509.8	509.8	514.0	518.2	520.6	527.8	539.8
47.5°	472.8	469.6	469.9	466.8	469.9	469.6	472.8	474.1	478.0	485.1	491.7
50°	445.4	443.5	443.0	441.8	443.0	443.5	445.4	444.8	449.6	456.2	465.2
52.5°	417.9	417.1	419.4	416.7	419.4	417.1	417.9	419.3	422.6	426.9	435.4
55°	380.9	379.2	382.8	379.2	382.8	379.2	380.9	379.8	380.9	385.2	390.6
57.5°	338.5	336.8	340.0	338.2	340.0	336.8	338.5	338.8	342.3	343.0	347.8
60°	310.6	306.9	308.7	309.3	308.7	306.9	310.6	311.7	313.0	313.5	318.3
62.5°	277.3	275.2	276.5	273.8	276.5	275.2	277.3	280.0	282.7	285.6	288.6
65°	230.5	228.7	226.3	225.1	226.3	228.7	230.5	231.8	238.4	241.9	248.6
67.5°	193.7	189.3	189.2	190.2	189.2	189.3	193.7	193.4	198.2	201.2	205.6
70°	166.7	166.7	166.1	166.1	166.1	166.7	166.7	170.3	172.7	175.1	178.2
72.5°	147.9	147.5	146.3	145.9	146.3	147.5	147.9	149.2	150.6	153.0	156.0
75°	119.1	119.8	118.6	118.0	118.6	119.8	119.1	119.1	121.5	122.2	123.4
77.5°	88.0	85.4	86.8	85.4	86.8	85.4	88.0	90.4	91.2	93.9	94.0
80°	66.8	66.2	68.0	66.2	68.0	66.2	66.8	66.8	68.6	69.8	72.9
82.5°	52.9	52.3	53.1	51.7	53.1	52.3	52.9	52.3	53.2	54.9	54.5
85°	31.9	31.3	30.7	31.3	30.7	31.3	31.9	31.3	30.7	31.3	31.9
87.5°	15.0	14.6	14.7	14.9	14.7	14.6	15.0	14.4	14.7	14.5	14.4
90°	19.6	20.2	20.8	21.4	20.8	20.2	19.6	19.0	18.2	17.2	16.2
92.5°	40.8	41.1	41.6	42.0	41.6	41.1	40.8	40.3	39.4	38.1	36.8
95°	75.3	75.8	76.2	76.6	76.2	75.8	75.3	75.0	74.1	72.7	71.3
97.5°	115.4	115.7	115.8	116.1	115.8	115.7	115.4	115.1	114.4	113.1	111.7
100°	144.8	145.2	145.6	146.0	145.6	145.2	144.8	144.5	143.3	141.5	139.7
102.5°	174.2	174.8	175.4	175.9	175.4	174.8	174.2	173.7	172.5	170.5	168.5
105°	219.0	219.6	220.2	220.8	220.2	219.6	219.0	218.4	217.5	216.3	215.2
107.5°	266.8	266.8	266.8	266.7	266.8	266.8	266.8	266.9	266.6	266.0	265.4
110°	301.5	301.3	301.1	300.9	301.1	301.3	301.5	301.7	301.5	300.9	300.3



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	335.5	335.1	334.7	334.4	334.7	335.1	335.5	335.8	335.8	335.6	335.3
115°	387.8	387.6	387.4	387.3	387.4	387.6	387.8	388.1	388.3	388.4	388.6
117.5°	441.2	440.5	439.7	438.9	439.7	440.5	441.2	442.0	442.4	442.2	442.0
120°	476.9	476.1	475.3	474.5	475.3	476.1	476.9	477.7	478.0	478.0	478.0
122.5°	512.0	511.4	510.8	510.1	510.8	511.4	512.0	512.6	513.0	513.2	513.4
125°	564.1	563.9	563.7	563.6	563.7	563.9	564.1	564.3	564.6	565.0	565.4
127.5°	616.0	615.5	615.2	614.8	615.2	615.5	616.0	616.4	616.7	616.9	617.1
130°	650.1	649.8	649.3	649.0	649.3	649.8	650.1	650.6	650.9	651.0	651.2
132.5°	682.7	682.2	681.6	681.0	681.6	682.2	682.7	683.2	683.6	683.9	684.0
135°	733.3	732.5	731.6	730.8	731.6	732.5	733.3	734.1	734.4	734.4	734.4
137.5°	782.7	781.7	780.7	779.7	780.7	781.7	782.7	783.6	784.0	783.7	783.5
140°	814.0	813.0	812.0	811.0	812.0	813.0	814.0	814.9	815.3	814.8	814.5
142.5°	843.9	842.9	842.0	840.9	842.0	842.9	843.9	844.9	845.3	845.0	844.8
145°	887.6	887.0	886.4	885.8	886.4	887.0	887.6	888.1	888.5	888.5	888.5
147.5°	928.1	926.8	925.4	924.1	925.4	926.8	928.1	929.4	929.9	929.4	928.9
150°	953.8	953.3	953.0	952.5	953.0	953.3	953.8	954.1	954.3	954.3	954.3
152.5°	978.2	977.5	976.8	976.1	976.8	977.5	978.2	978.9	979.0	978.6	978.1
155°	1012.5	1011.5	1010.5	1009.5	1010.5	1011.5	1012.5	1013.5	1013.6	1012.8	1012.0
157.5°	1041.4	1040.1	1038.8	1037.5	1038.8	1040.1	1041.4	1042.7	1042.9	1042.1	1041.3
160°	1059.7	1058.7	1057.7	1056.7	1057.7	1058.7	1059.7	1060.7	1060.8	1060.0	1059.2
162.5°	1076.6	1075.4	1074.2	1073.1	1074.2	1075.4	1076.6	1077.7	1077.8	1076.8	1075.8
165°	1098.6	1097.3	1096.2	1095.0	1096.2	1097.3	1098.6	1099.7	1099.9	1099.1	1098.3
167.5°	1116.2	1114.9	1113.7	1112.4	1113.7	1114.9	1116.2	1117.3	1117.4	1116.2	1115.0
170°	1125.9	1124.4	1123.1	1121.7	1123.1	1124.4	1125.9	1127.2	1127.3	1126.1	1125.0
172.5°	1133.2	1132.0	1130.8	1129.5	1130.8	1132.0	1133.2	1134.4	1134.4	1133.3	1132.1
175°	1141.0	1139.6	1138.2	1136.8	1138.2	1139.6	1141.0	1142.4	1142.5	1141.3	1140.1
177.5°	1144.4	1143.4	1142.2	1141.1	1142.2	1143.4	1144.4	1145.6	1145.6	1144.7	1143.7
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1405.4	1410.8	1413.6	1420.4	1430.0	1434.9	1441.5	1446.4	1453.1	1461.3	1468.0
5°	1314.5	1328.9	1338.5	1353.5	1367.4	1381.3	1398.7	1411.3	1428.2	1447.4	1462.5
7.5°	1229.9	1248.0	1264.0	1283.9	1306.7	1324.5	1347.3	1370.6	1396.9	1424.2	1450.0
10°	1176.0	1194.1	1214.0	1238.6	1261.5	1285.6	1312.6	1339.7	1372.8	1403.6	1438.4
12.5°	1122.6	1142.5	1164.8	1192.4	1220.0	1250.9	1278.4	1308.9	1344.4	1384.3	1421.6
15°	1056.2	1075.5	1099.6	1123.0	1154.9	1188.7	1225.4	1265.7	1305.4	1350.0	1396.3
17.5°	985.1	1006.3	1032.8	1060.0	1093.6	1133.0	1169.0	1213.2	1257.8	1309.7	1364.3
20°	938.9	960.6	991.8	1022.0	1052.7	1091.2	1133.9	1179.0	1226.5	1281.4	1342.1
22.5°	902.3	917.7	948.5	979.1	1015.1	1054.5	1096.4	1143.4	1195.2	1252.0	1315.6
25°	848.0	866.0	888.3	920.2	957.5	999.1	1041.2	1091.2	1147.7	1205.5	1273.5
27.5°	799.8	814.6	836.6	861.6	898.8	941.9	986.7	1038.8	1096.8	1155.7	1227.2
30°	765.5	781.8	802.9	829.4	858.8	905.8	951.5	1002.7	1061.7	1122.5	1195.9
32.5°	735.7	752.4	770.6	795.7	827.5	869.2	916.4	966.6	1026.5	1089.2	1160.7
35°	693.9	705.3	722.2	746.9	778.2	811.9	860.1	913.0	971.4	1036.4	1108.0
37.5°	646.0	660.8	677.5	699.0	726.5	762.9	807.7	861.2	915.4	977.7	1043.0
40°	618.1	632.0	650.6	666.3	695.2	728.3	769.2	825.1	879.3	937.7	997.3
42.5°	589.7	603.1	618.8	638.3	664.3	696.4	734.5	786.6	844.6	899.6	949.6
45°	545.3	559.1	574.2	592.2	616.3	647.6	685.5	733.1	783.6	834.2	872.1
47.5°	502.7	515.8	530.0	548.5	570.7	600.9	634.8	676.8	725.9	768.9	796.0
50°	472.4	484.5	500.2	518.2	539.8	568.1	600.7	642.2	683.1	722.2	746.9
52.5°	442.6	456.1	471.7	487.4	508.1	536.4	566.5	602.2	641.2	673.2	693.5
55°	397.8	410.5	424.9	441.1	461.6	485.7	517.6	545.9	576.6	603.7	615.7
57.5°	354.6	365.7	379.2	396.1	414.6	436.9	462.3	489.5	511.1	530.2	543.9
60°	326.2	335.8	348.5	362.9	382.8	403.2	426.1	451.4	468.2	484.5	497.1
62.5°	297.3	306.5	318.6	331.6	349.1	368.1	390.0	410.5	426.9	437.8	452.4
65°	254.0	263.0	273.2	287.0	301.0	316.6	336.4	351.5	362.9	375.0	384.0
67.5°	213.7	221.1	230.9	241.7	253.4	268.4	283.8	296.3	304.2	311.4	322.3
70°	187.2	193.2	201.0	209.5	222.1	237.1	249.1	258.8	264.2	271.4	284.6
72.5°	160.2	167.2	174.5	183.0	193.2	205.8	216.4	226.0	229.5	235.3	243.8
75°	126.4	130.0	136.0	142.0	149.3	160.1	170.3	172.7	175.8	180.6	186.5
77.5°	95.6	98.8	101.2	105.2	111.0	119.7	125.1	128.7	129.4	131.2	137.1
80°	75.8	77.7	80.1	83.0	85.4	92.6	95.7	99.3	100.5	102.3	105.3
82.5°	55.6	57.4	58.9	61.3	65.3	68.1	71.2	74.7	75.0	76.3	77.0
85°	32.5	33.1	31.9	33.1	33.7	34.9	37.9	40.9	40.3	39.7	41.6
87.5°	14.6	14.4	13.6	14.8	13.6	13.8	13.5	13.6	14.3	15.0	15.6
90°	15.2	14.3	12.8	11.5	10.1	8.7	7.2	5.6	4.0	2.5	0.9
92.5°	35.5	34.2	32.5	30.8	29.1	27.4	25.9	24.9	23.7	22.6	21.6
95°	69.9	68.6	66.6	64.6	62.6	60.6	59.5	59.0	58.7	58.2	57.9
97.5°	110.5	109.1	106.4	103.7	100.9	98.3	96.8	96.7	96.5	96.3	96.1
100°	137.9	136.2	133.7	131.1	128.5	125.9	124.7	124.7	124.7	124.7	124.7
102.5°	166.7	164.7	163.4	162.1	160.8	159.4	158.5	157.7	156.9	156.0	155.2
105°	213.9	212.8	211.6	210.4	209.2	208.0	207.0	206.0	204.9	203.9	203.0
107.5°	264.8	264.2	263.3	262.4	261.4	260.6	259.7	258.7	257.6	256.6	255.7
110°	299.7	299.1	298.5	297.9	297.3	296.8	296.0	295.0	294.0	293.0	292.0



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	335.0	334.7	333.9	333.2	332.5	331.7	331.1	330.6	330.0	329.6	329.0
115°	388.9	389.1	388.6	388.3	387.8	387.4	386.8	386.1	385.3	384.5	383.7
117.5°	441.9	441.8	441.4	441.0	440.7	440.3	440.0	439.6	439.3	438.9	438.5
120°	478.0	478.0	477.9	477.7	477.4	477.2	476.7	475.7	474.7	473.7	472.7
122.5°	513.5	513.6	513.2	512.6	512.1	511.6	511.2	510.9	510.5	510.1	509.8
125°	565.8	566.2	566.0	565.8	565.6	565.4	564.7	563.6	562.3	561.2	560.0
127.5°	617.2	617.5	617.2	617.0	616.8	616.5	616.1	615.4	614.7	614.0	613.4
130°	651.5	651.7	651.2	650.9	650.5	650.1	649.3	648.4	647.4	646.4	645.4
132.5°	684.2	684.4	684.5	684.6	684.7	684.7	683.9	682.3	680.7	679.1	677.4
135°	734.4	734.4	734.2	734.1	733.9	733.7	733.0	731.7	730.6	729.4	728.3
137.5°	783.3	783.0	782.7	782.2	781.8	781.3	780.5	779.4	778.2	777.0	776.0
140°	814.0	813.7	813.1	812.5	811.9	811.3	810.5	809.5	808.5	807.5	806.6
142.5°	844.5	844.3	843.6	842.8	842.0	841.3	840.5	839.6	838.8	838.0	837.1
145°	888.5	888.5	887.9	887.3	886.7	886.1	885.4	884.6	883.8	883.1	882.3
147.5°	928.4	928.0	927.5	927.0	926.6	926.1	925.6	925.2	924.8	924.3	923.9
150°	954.3	954.3	953.5	952.8	952.0	951.2	950.9	951.1	951.3	951.5	951.6
152.5°	977.6	977.1	976.8	976.5	976.2	975.9	975.5	975.3	975.0	974.7	974.5
155°	1011.2	1010.4	1010.2	1010.0	1009.9	1009.6	1009.5	1009.5	1009.5	1009.5	1009.5
157.5°	1040.6	1039.8	1039.6	1039.4	1039.2	1039.0	1039.1	1039.6	1040.0	1040.4	1040.9
160°	1058.4	1057.6	1057.4	1057.2	1057.0	1056.9	1057.0	1057.6	1058.2	1058.8	1059.4
162.5°	1075.0	1074.0	1074.0	1073.9	1073.9	1073.8	1074.1	1074.4	1074.9	1075.3	1075.8
165°	1097.6	1096.8	1096.5	1096.4	1096.2	1096.0	1096.1	1096.4	1096.9	1097.3	1097.7
167.5°	1113.8	1112.6	1112.6	1112.6	1112.6	1112.6	1113.0	1113.8	1114.6	1115.4	1116.2
170°	1123.8	1122.6	1122.6	1122.6	1122.6	1122.6	1123.0	1123.8	1124.5	1125.3	1126.1
172.5°	1130.9	1129.7	1129.7	1129.7	1129.7	1129.7	1130.2	1130.9	1131.7	1132.5	1133.3
175°	1138.9	1137.7	1137.7	1137.7	1137.7	1137.7	1138.1	1138.9	1139.7	1140.5	1141.3
177.5°	1142.8	1141.8	1142.0	1142.1	1142.3	1142.5	1142.8	1143.4	1144.2	1144.8	1145.4
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1473.4	1477.7	1483.9	1491.1	1496.9	1503.2	1506.5	1506.5	1509.5	1515.7	1523.9
5°	1477.6	1493.2	1508.2	1527.5	1542.6	1560.0	1573.2	1585.9	1597.3	1611.8	1626.8
7.5°	1476.3	1502.4	1529.5	1559.8	1593.2	1619.8	1647.2	1668.6	1689.8	1717.4	1739.2
10°	1471.5	1505.2	1541.9	1580.5	1622.6	1659.3	1692.4	1722.5	1751.4	1781.5	1808.6
12.5°	1462.9	1505.7	1550.6	1596.9	1650.0	1692.0	1734.8	1766.8	1800.5	1833.4	1866.8
15°	1449.8	1500.4	1554.6	1619.0	1684.0	1730.9	1773.1	1814.6	1845.8	1883.2	1915.1
17.5°	1423.0	1488.2	1556.3	1626.7	1689.2	1743.7	1787.9	1827.4	1860.7	1901.8	1945.1
20°	1407.1	1477.6	1548.5	1623.8	1683.4	1739.4	1782.1	1823.0	1864.6	1918.1	1971.0
22.5°	1385.0	1460.2	1535.5	1607.0	1669.9	1723.9	1768.1	1818.2	1872.7	1933.5	1997.5
25°	1350.0	1427.6	1502.3	1570.2	1631.7	1687.0	1747.2	1814.6	1880.8	1960.9	2052.9
27.5°	1305.6	1380.4	1447.0	1518.9	1579.8	1650.3	1725.4	1798.5	1893.9	2004.0	2119.0
30°	1272.3	1343.4	1406.5	1474.5	1543.7	1621.4	1705.7	1791.7	1905.5	2034.9	2171.5
32.5°	1233.8	1298.1	1360.8	1426.4	1506.2	1591.5	1681.1	1786.5	1922.4	2069.6	2211.0
35°	1167.0	1224.8	1285.6	1358.3	1443.2	1536.0	1650.3	1778.5	1942.8	2101.0	2228.0
37.5°	1096.9	1142.5	1203.5	1280.4	1372.8	1480.1	1609.8	1765.6	1934.4	2076.3	2130.5
40°	1043.0	1085.7	1150.1	1230.8	1322.2	1439.7	1585.3	1745.3	1915.1	2013.8	2009.6
42.5°	989.5	1032.8	1094.8	1175.9	1271.2	1402.6	1552.6	1718.9	1862.2	1899.7	1821.3
45°	907.6	947.9	1008.7	1090.6	1192.8	1330.7	1488.4	1647.9	1739.4	1678.6	1523.3
47.5°	824.0	863.2	919.6	999.8	1111.5	1255.7	1404.8	1535.7	1548.5	1418.0	1231.7
50°	769.2	805.8	859.4	944.9	1053.2	1194.1	1337.9	1440.8	1408.9	1249.5	1057.5
52.5°	715.7	751.0	801.2	881.8	992.6	1130.5	1258.9	1339.7	1266.0	1096.4	923.6
55°	636.8	670.5	721.0	795.0	895.5	1022.0	1134.5	1164.0	1055.6	884.8	745.1
57.5°	561.8	586.5	636.4	701.9	798.8	910.3	990.9	985.6	866.0	712.1	612.0
60°	512.2	534.4	582.0	642.2	734.2	834.2	890.7	866.7	745.7	618.7	522.4
62.5°	465.9	486.8	526.6	582.0	661.1	748.0	789.2	755.9	641.7	530.1	453.5
65°	396.0	411.1	443.0	494.1	556.1	616.3	653.0	604.2	503.2	418.9	361.1
67.5°	330.6	343.7	372.0	408.8	451.5	493.0	508.0	462.3	383.6	326.8	286.1
70°	288.3	300.3	319.6	353.9	382.2	411.7	418.9	378.0	312.4	269.0	243.8
72.5°	247.8	259.0	275.8	300.0	319.6	336.5	339.9	301.9	251.7	221.9	202.3
75°	189.0	198.6	209.5	218.5	231.1	234.2	232.9	203.4	176.4	156.5	145.6
77.5°	138.9	142.9	149.5	153.1	153.7	153.5	147.3	128.7	114.7	106.6	102.1
80°	107.1	110.1	111.9	113.2	113.8	107.7	101.1	89.7	84.9	80.1	74.6
82.5°	77.8	79.8	81.6	81.9	78.6	73.6	67.4	61.7	58.4	56.0	53.9
85°	42.1	42.7	42.1	39.1	34.9	33.1	31.9	30.7	30.1	29.5	29.5
87.5°	15.4	14.3	12.2	13.0	13.3	13.1	13.4	13.2	12.9	13.2	13.4
90°	2.5	4.0	5.6	7.2	8.7	10.1	11.5	12.8	14.3	15.2	16.2
92.5°	22.6	23.7	24.9	25.9	27.4	29.1	30.8	32.5	34.2	35.5	36.8
95°	58.2	58.7	59.0	59.5	60.6	62.6	64.6	66.6	68.6	69.9	71.3
97.5°	96.3	96.5	96.7	96.8	98.3	100.9	103.7	106.4	109.1	110.5	111.7
100°	124.7	124.7	124.7	124.7	125.9	128.5	131.1	133.7	136.2	137.9	139.7
102.5°	156.0	156.9	157.7	158.5	159.4	160.8	162.1	163.4	164.7	166.7	168.5
105°	203.9	204.9	206.0	207.0	208.0	209.2	210.4	211.6	212.8	213.9	215.2
107.5°	256.6	257.6	258.7	259.7	260.6	261.4	262.4	263.3	264.2	264.8	265.4
110°	293.0	294.0	295.0	296.0	296.8	297.3	297.9	298.5	299.1	299.7	300.3





TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	329.6	330.0	330.6	331.1	331.7	332.5	333.2	333.9	334.7	335.0	335.3
115°	384.5	385.3	386.1	386.8	387.4	387.8	388.3	388.6	389.1	388.9	388.6
117.5°	438.9	439.3	439.6	440.0	440.3	440.7	441.0	441.4	441.8	441.9	442.0
120°	473.7	474.7	475.7	476.7	477.2	477.4	477.7	477.9	478.0	478.0	478.0
122.5°	510.1	510.5	510.9	511.2	511.6	512.1	512.6	513.2	513.6	513.5	513.4
125°	561.2	562.3	563.6	564.7	565.4	565.6	565.8	566.0	566.2	565.8	565.4
127.5°	614.0	614.7	615.4	616.1	616.5	616.8	617.0	617.2	617.5	617.2	617.1
130°	646.4	647.4	648.4	649.3	650.1	650.5	650.9	651.2	651.7	651.5	651.2
132.5°	679.1	680.7	682.3	683.9	684.7	684.7	684.6	684.5	684.4	684.2	684.0
135°	729.4	730.6	731.7	733.0	733.7	733.9	734.1	734.2	734.4	734.4	734.4
137.5°	777.0	778.2	779.4	780.5	781.3	781.8	782.2	782.7	783.0	783.3	783.5
140°	807.5	808.5	809.5	810.5	811.3	811.9	812.5	813.1	813.7	814.0	814.5
142.5°	838.0	838.8	839.6	840.5	841.3	842.0	842.8	843.6	844.3	844.5	844.8
145°	883.1	883.8	884.6	885.4	886.1	886.7	887.3	887.9	888.5	888.5	888.5
147.5°	924.3	924.8	925.2	925.6	926.1	926.6	927.0	927.5	928.0	928.4	928.9
150°	951.5	951.3	951.1	950.9	951.2	952.0	952.8	953.5	954.3	954.3	954.3
152.5°	974.7	975.0	975.3	975.5	975.9	976.2	976.5	976.8	977.1	977.6	978.1
155°	1009.5	1009.5	1009.5	1009.5	1009.6	1009.9	1010.0	1010.2	1010.4	1011.2	1012.0
157.5°	1040.4	1040.0	1039.6	1039.1	1039.0	1039.2	1039.4	1039.6	1039.8	1040.6	1041.3
160°	1058.8	1058.2	1057.6	1057.0	1056.9	1057.0	1057.2	1057.4	1057.6	1058.4	1059.2
162.5°	1075.3	1074.9	1074.4	1074.1	1073.8	1073.9	1073.9	1074.0	1074.0	1075.0	1075.8
165°	1097.3	1096.9	1096.4	1096.1	1096.0	1096.2	1096.4	1096.5	1096.8	1097.6	1098.3
167.5°	1115.4	1114.6	1113.8	1113.0	1112.6	1112.6	1112.6	1112.6	1112.6	1113.8	1115.0
170°	1125.3	1124.5	1123.8	1123.0	1122.6	1122.6	1122.6	1122.6	1122.6	1123.8	1125.0
172.5°	1132.5	1131.7	1130.9	1130.2	1129.7	1129.7	1129.7	1129.7	1129.7	1130.9	1132.1
175°	1140.5	1139.7	1138.9	1138.1	1137.7	1137.7	1137.7	1137.7	1137.7	1138.9	1140.1
177.5°	1144.8	1144.2	1143.4	1142.8	1142.5	1142.3	1142.1	1142.0	1141.8	1142.8	1143.7
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1530.2	1530.2	1538.4	1537.8	1543.2	1541.2	1542.2
5°	1644.8	1655.1	1664.1	1670.2	1679.2	1681.6	1680.3
7.5°	1763.8	1786.5	1797.6	1812.8	1815.5	1823.5	1822.7
10°	1837.5	1859.8	1876.6	1889.8	1896.4	1904.9	1905.5
12.5°	1895.2	1914.1	1929.0	1941.3	1949.4	1952.0	1953.6
15°	1940.4	1961.4	1978.9	1996.4	2006.6	2014.4	2018.7
17.5°	1985.8	2018.4	2049.2	2072.9	2087.1	2099.2	2099.0
20°	2021.1	2058.3	2096.9	2124.0	2151.6	2163.6	2165.4
22.5°	2058.6	2115.7	2165.3	2207.3	2243.5	2256.1	2260.8
25°	2136.5	2211.2	2287.7	2346.6	2388.7	2413.4	2417.1
27.5°	2230.8	2331.8	2412.3	2466.7	2501.7	2520.0	2523.9
30°	2297.3	2390.6	2462.8	2503.7	2520.0	2522.4	2513.4
32.5°	2327.1	2396.8	2425.7	2423.3	2391.4	2370.3	2362.1
35°	2290.6	2276.2	2205.8	2121.6	2057.2	2016.2	2005.4
37.5°	2084.6	1960.0	1830.5	1703.2	1635.4	1600.9	1541.7
40°	1881.4	1703.9	1569.1	1461.9	1385.5	1324.1	1309.7
42.5°	1652.3	1468.9	1334.1	1242.3	1181.3	1139.2	1120.9
45°	1327.7	1170.0	1058.6	988.3	941.3	910.6	896.8
47.5°	1061.9	939.9	858.7	806.6	770.9	744.1	736.6
50°	916.1	818.5	749.9	706.0	678.9	658.4	650.0
52.5°	795.7	716.9	664.2	627.9	602.4	589.6	582.6
55°	656.7	588.6	550.7	521.8	507.4	497.1	492.3
57.5°	537.0	487.9	460.2	440.2	426.9	420.4	417.9
60°	470.0	431.5	406.3	390.6	381.6	373.2	370.8
62.5°	410.8	380.5	361.0	347.2	338.2	334.7	333.1
65°	331.0	311.1	296.7	288.3	281.1	279.8	279.3
67.5°	263.1	251.5	243.9	235.1	232.6	228.4	227.5
70°	225.1	217.3	208.2	205.3	202.2	198.0	198.6
72.5°	190.9	183.1	176.9	173.0	171.9	170.0	171.7
75°	139.6	137.2	134.8	131.8	130.6	130.6	130.0
77.5°	99.7	97.6	95.0	93.2	92.8	90.2	91.2
80°	72.2	69.2	68.0	68.6	66.8	66.2	66.2
82.5°	53.4	52.3	51.2	51.3	50.9	50.3	50.8
85°	29.5	28.9	28.9	28.3	28.3	27.6	27.6
87.5°	14.0	14.7	13.9	13.6	13.6	14.3	14.9
90°	17.2	18.2	19.0	19.6	20.2	20.8	21.4
92.5°	38.1	39.4	40.3	40.8	41.1	41.6	42.0
95°	72.7	74.1	75.0	75.3	75.8	76.2	76.6
97.5°	113.1	114.4	115.1	115.4	115.7	115.8	116.1
100°	141.5	143.3	144.5	144.8	145.2	145.6	146.0
102.5°	170.5	172.5	173.7	174.2	174.8	175.4	175.9
105°	216.3	217.5	218.4	219.0	219.6	220.2	220.8
107.5°	266.0	266.6	266.9	266.8	266.8	266.8	266.7
110°	300.9	301.5	301.7	301.5	301.3	301.1	300.9



TEST NUMBER: P333599-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	335.6	335.8	335.8	335.5	335.1	334.7	334.4
115°	388.4	388.3	388.1	387.8	387.6	387.4	387.3
117.5°	442.2	442.4	442.0	441.2	440.5	439.7	438.9
120°	478.0	478.0	477.7	476.9	476.1	475.3	474.5
122.5°	513.2	513.0	512.6	512.0	511.4	510.8	510.1
125°	565.0	564.6	564.3	564.1	563.9	563.7	563.6
127.5°	616.9	616.7	616.4	616.0	615.5	615.2	614.8
130°	651.0	650.9	650.6	650.1	649.8	649.3	649.0
132.5°	683.9	683.6	683.2	682.7	682.2	681.6	681.0
135°	734.4	734.4	734.1	733.3	732.5	731.6	730.8
137.5°	783.7	784.0	783.6	782.7	781.7	780.7	779.7
140°	814.8	815.3	814.9	814.0	813.0	812.0	811.0
142.5°	845.0	845.3	844.9	843.9	842.9	842.0	840.9
145°	888.5	888.5	888.1	887.6	887.0	886.4	885.8
147.5°	929.4	929.9	929.4	928.1	926.8	925.4	924.1
150°	954.3	954.3	954.1	953.8	953.3	953.0	952.5
152.5°	978.6	979.0	978.9	978.2	977.5	976.8	976.1
155°	1012.8	1013.6	1013.5	1012.5	1011.5	1010.5	1009.5
157.5°	1042.1	1042.9	1042.7	1041.4	1040.1	1038.8	1037.5
160°	1060.0	1060.8	1060.7	1059.7	1058.7	1057.7	1056.7
162.5°	1076.8	1077.8	1077.7	1076.6	1075.4	1074.2	1073.1
165°	1099.1	1099.9	1099.7	1098.6	1097.3	1096.2	1095.0
167.5°	1116.2	1117.4	1117.3	1116.2	1114.9	1113.7	1112.4
170°	1126.1	1127.3	1127.2	1125.9	1124.4	1123.1	1121.7
172.5°	1133.3	1134.4	1134.4	1133.2	1132.0	1130.8	1129.5
175°	1141.3	1142.5	1142.4	1141.0	1139.6	1138.2	1136.8
177.5°	1144.7	1145.6	1145.6	1144.4	1143.4	1142.2	1141.1
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0

(END OF REPORT)