

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333600-940

Luminaire Tested: **S125RDIP-S1090D1035U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333600-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7112.0 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46				46
2	91	83	77	72	84	78	72	68	67	63	59	57	54	51	47	45	44	39				39
3	83	74	66	61	77	69	62	57	59	54	50	50	47	44	42	40	38	34				34
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33	29				29
5	70	58	50	44	65	55	47	42	47	42	38	41	36	33	34	31	29	25				25
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22				22
7	60	47	40	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20				20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18				18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16				16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	22	19	17	15				15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9469	9469	9469	9469
5°	10893	9481	8373	9481
10°	12496	9433	7389	9433
15°	13497	9336	6567	9336
20°	14882	9224	6064	9224
25°	17224	9075	5627	9075
30°	18744	8918	5341	8918
35°	15811	8736	5077	8736
40°	11042	8408	4850	8408
45°	8191	7965	4629	7965
50°	6531	7504	4439	7504
55°	5543	6933	4270	6933
60°	4790	6421	3995	6421
65°	4268	5868	3440	5868
70°	3750	5374	3136	5374
75°	3244	4654	2944	4654
80°	2462	3916	2462	3916
85°	2045	3083	2319	3083



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	2.0
10°-20°	412.0	5.8
20°-30°	653.3	9.2
30°-40°	787.8	11.1
40°-50°	703.5	9.9
50°-60°	539.5	7.6
60°-70°	350.6	4.9
70°-80°	170.5	2.4
80°-90°	43.2	0.6
90°-100°	320.0	4.5
100°-110°	688.0	9.7
110°-120°	645.7	9.1
120°-130°	523.3	7.4
130°-140°	419.9	5.9
140°-150°	316.9	4.5
150°-160°	223.1	3.1
160°-170°	131.5	1.8
170°-180°	42.8	0.6
0°-30°	1205.9	17.0
0°-40°	1993.7	28.0
0°-60°	3236.7	45.5
0°-90°	3800.9	53.4
90°-120°	1653.7	23.3
90°-150°	2913.7	41.0
90°-180°	3311.0	46.6
0°-180°	7112.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1466	1466	1466	1466	1466	
5°	1680	1462	1292	1462	1680	168
15°	2019	1396	982	1396	2019	578
25°	2417	1274	790	1274	2417	1110
35°	2005	1108	644	1108	2005	1211
45°	897	872	507	872	897	716
55°	492	616	379	616	492	447
65°	279	384	225	384	279	278
75°	130	186	118	186	130	138
85°	28	42	31	42	28	32
90°	20	1	20	1	20	15
95°	209	29	209	29	209	296
105°	1180	101	1180	101	1180	1172
115°	1314	180	1314	180	1314	1284
125°	1035	249	1035	249	1035	937
135°	860	292	860	292	860	666
145°	678	340	678	340	678	431
155°	569	388	569	388	569	265
165°	498	424	498	424	498	143
175°	448	441	448	441	448	44
180°	442	442	442	442	442	



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1542.2	1541.2	1543.2	1537.8	1538.4	1530.2	1530.2	1523.9	1515.7	1509.5	1506.5
5°	1680.3	1681.6	1679.2	1670.2	1664.1	1655.1	1644.8	1626.8	1611.8	1597.3	1585.9
7.5°	1822.7	1823.5	1815.5	1812.8	1797.6	1786.5	1763.8	1739.2	1717.4	1689.8	1668.6
10°	1905.5	1904.9	1896.4	1889.8	1876.6	1859.8	1837.5	1808.6	1781.5	1751.4	1722.5
12.5°	1953.6	1952.0	1949.4	1941.3	1929.0	1914.1	1895.2	1866.8	1833.4	1800.5	1766.8
15°	2018.7	2014.4	2006.6	1996.4	1978.9	1961.4	1940.4	1915.1	1883.2	1845.8	1814.6
17.5°	2099.0	2099.2	2087.1	2072.9	2049.2	2018.4	1985.8	1945.1	1901.8	1860.7	1827.4
20°	2165.4	2163.6	2151.6	2124.0	2096.9	2058.3	2021.1	1971.0	1918.1	1864.6	1823.0
22.5°	2260.8	2256.1	2243.5	2207.3	2165.3	2115.7	2058.6	1997.5	1933.5	1872.7	1818.2
25°	2417.1	2413.4	2388.7	2346.6	2287.7	2211.2	2136.5	2052.9	1960.9	1880.8	1814.6
27.5°	2523.9	2520.0	2501.7	2466.7	2412.3	2331.8	2230.8	2119.0	2004.0	1893.9	1798.5
30°	2513.4	2522.4	2520.0	2503.7	2462.8	2390.6	2297.3	2171.5	2034.9	1905.5	1791.7
32.5°	2362.1	2370.3	2391.4	2423.3	2425.7	2396.8	2327.1	2211.0	2069.6	1922.4	1786.5
35°	2005.4	2016.2	2057.2	2121.6	2205.8	2276.2	2290.6	2228.0	2101.0	1942.8	1778.5
37.5°	1541.7	1600.9	1635.4	1703.2	1830.5	1960.0	2084.6	2130.5	2076.3	1934.4	1765.6
40°	1309.7	1324.1	1385.5	1461.9	1569.1	1703.9	1881.4	2009.6	2013.8	1915.1	1745.3
42.5°	1120.9	1139.2	1181.3	1242.3	1334.1	1468.9	1652.3	1821.3	1899.7	1862.2	1718.9
45°	896.8	910.6	941.3	988.3	1058.6	1170.0	1327.7	1523.3	1678.6	1739.4	1647.9
47.5°	736.6	744.1	770.9	806.6	858.7	939.9	1061.9	1231.7	1418.0	1548.5	1535.7
50°	650.0	658.4	678.9	706.0	749.9	818.5	916.1	1057.5	1249.5	1408.9	1440.8
52.5°	582.6	589.6	602.4	627.9	664.2	716.9	795.7	923.6	1096.4	1266.0	1339.7
55°	492.3	497.1	507.4	521.8	550.7	588.6	656.7	745.1	884.8	1055.6	1164.0
57.5°	417.9	420.4	426.9	440.2	460.2	487.9	537.0	612.0	712.1	866.0	985.6
60°	370.8	373.2	381.6	390.6	406.3	431.5	470.0	522.4	618.7	745.7	866.7
62.5°	333.1	334.7	338.2	347.2	361.0	380.5	410.8	453.5	530.1	641.7	755.9
65°	279.3	279.8	281.1	288.3	296.7	311.1	331.0	361.1	418.9	503.2	604.2
67.5°	227.5	228.4	232.6	235.1	243.9	251.5	263.1	286.1	326.8	383.6	462.3
70°	198.6	198.0	202.2	205.3	208.2	217.3	225.1	243.8	269.0	312.4	378.0
72.5°	171.7	170.0	171.9	173.0	176.9	183.1	190.9	202.3	221.9	251.7	301.9
75°	130.0	130.6	130.6	131.8	134.8	137.2	139.6	145.6	156.5	176.4	203.4
77.5°	91.2	90.2	92.8	93.2	95.0	97.6	99.7	102.1	106.6	114.7	128.7
80°	66.2	66.2	66.8	68.6	68.0	69.2	72.2	74.6	80.1	84.9	89.7
82.5°	50.8	50.3	50.9	51.3	51.2	52.3	53.4	53.9	56.0	58.4	61.7
85°	27.6	27.6	28.3	28.3	28.9	28.9	29.5	29.5	29.5	30.1	30.7
87.5°	14.7	14.2	13.6	13.6	14.0	14.6	14.0	13.3	13.1	12.9	13.1
90°	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1	15.2	14.3	12.5
92.5°	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7	232.3	287.0	291.6
95°	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1	771.8	788.7	643.6
97.5°	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2	976.5	842.3	574.7
100°	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9	1026.4	803.8	512.7
102.5°	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6	996.5	736.2	465.7
105°	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5	900.9	645.3	420.2
107.5°	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1	803.3	582.9	400.9
110°	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0	747.7	553.7	395.2



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6	706.4	536.6	395.2
115°	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2	661.4	518.1	397.9
117.5°	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9	634.5	509.0	403.8
120°	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3	619.6	504.7	409.5
122.5°	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0	606.7	501.1	414.5
125°	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1	589.3	496.7	422.8
127.5°	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6	573.3	494.5	432.3
130°	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9	562.6	493.1	438.0
132.5°	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0	554.0	493.1	444.3
135°	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8	543.9	493.1	453.1
137.5°	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3	534.8	494.2	461.1
140°	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6	530.6	494.9	464.7
142.5°	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3	527.0	495.6	466.8
145°	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2	521.7	494.9	469.1
147.5°	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9	516.1	492.6	470.0
150°	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5	511.8	490.4	470.0
152.5°	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3	506.8	487.7	469.3
155°	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6	498.5	482.5	467.3
157.5°	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9	490.6	477.2	465.0
160°	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8	484.3	473.6	462.9
162.5°	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0	478.6	469.3	460.7
165°	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2	470.0	462.9	457.5
167.5°	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8	461.6	456.6	452.5
170°	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1	456.6	453.1	450.4
172.5°	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7	451.7	448.8	447.5
175°	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7	445.1	444.2	444.2
177.5°	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9	442.2	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1506.5	1503.2	1496.9	1491.1	1483.9	1477.7	1473.4	1468.0	1461.3	1453.1	1446.4
5°	1573.2	1560.0	1542.6	1527.5	1508.2	1493.2	1477.6	1462.5	1447.4	1428.2	1411.3
7.5°	1647.2	1619.8	1593.2	1559.8	1529.5	1502.4	1476.3	1450.0	1424.2	1396.9	1370.6
10°	1692.4	1659.3	1622.6	1580.5	1541.9	1505.2	1471.5	1438.4	1403.6	1372.8	1339.7
12.5°	1734.8	1692.0	1650.0	1596.9	1550.6	1505.7	1462.9	1421.6	1384.3	1344.4	1308.9
15°	1773.1	1730.9	1684.0	1619.0	1554.6	1500.4	1449.8	1396.3	1350.0	1305.4	1265.7
17.5°	1787.9	1743.7	1689.2	1626.7	1556.3	1488.2	1423.0	1364.3	1309.7	1257.8	1213.2
20°	1782.1	1739.4	1683.4	1623.8	1548.5	1477.6	1407.1	1342.1	1281.4	1226.5	1179.0
22.5°	1768.1	1723.9	1669.9	1607.0	1535.5	1460.2	1385.0	1315.6	1252.0	1195.2	1143.4
25°	1747.2	1687.0	1631.7	1570.2	1502.3	1427.6	1350.0	1273.5	1205.5	1147.7	1091.2
27.5°	1725.4	1650.3	1579.8	1518.9	1447.0	1380.4	1305.6	1227.2	1155.7	1096.8	1038.8
30°	1705.7	1621.4	1543.7	1474.5	1406.5	1343.4	1272.3	1195.9	1122.5	1061.7	1002.7
32.5°	1681.1	1591.5	1506.2	1426.4	1360.8	1298.1	1233.8	1160.7	1089.2	1026.5	966.6
35°	1650.3	1536.0	1443.2	1358.3	1285.6	1224.8	1167.0	1108.0	1036.4	971.4	913.0
37.5°	1609.8	1480.1	1372.8	1280.4	1203.5	1142.5	1096.9	1043.0	977.7	915.4	861.2
40°	1585.3	1439.7	1322.2	1230.8	1150.1	1085.7	1043.0	997.3	937.7	879.3	825.1
42.5°	1552.6	1402.6	1271.2	1175.9	1094.8	1032.8	989.5	949.6	899.6	844.6	786.6
45°	1488.4	1330.7	1192.8	1090.6	1008.7	947.9	907.6	872.1	834.2	783.6	733.1
47.5°	1404.8	1255.7	1111.5	999.8	919.6	863.2	824.0	796.0	768.9	725.9	676.8
50°	1337.9	1194.1	1053.2	944.9	859.4	805.8	769.2	746.9	722.2	683.1	642.2
52.5°	1258.9	1130.5	992.6	881.8	801.2	751.0	715.7	693.5	673.2	641.2	602.2
55°	1134.5	1022.0	895.5	795.0	721.0	670.5	636.8	615.7	603.7	576.6	545.9
57.5°	990.9	910.3	798.8	701.9	636.4	586.5	561.8	543.9	530.2	511.1	489.5
60°	890.7	834.2	734.2	642.2	582.0	534.4	512.2	497.1	484.5	468.2	451.4
62.5°	789.2	748.0	661.1	582.0	526.6	486.8	465.9	452.4	437.8	426.9	410.5
65°	653.0	616.3	556.1	494.1	443.0	411.1	396.0	384.0	375.0	362.9	351.5
67.5°	508.0	493.0	451.5	408.8	372.0	343.7	330.6	322.3	311.4	304.2	296.3
70°	418.9	411.7	382.2	353.9	319.6	300.3	288.3	284.6	271.4	264.2	258.8
72.5°	339.9	336.5	319.6	300.0	275.8	259.0	247.8	243.8	235.3	229.5	226.0
75°	232.9	234.2	231.1	218.5	209.5	198.6	189.0	186.5	180.6	175.8	172.7
77.5°	147.3	153.5	153.7	153.1	149.5	142.9	138.9	137.1	131.2	129.4	128.7
80°	101.1	107.7	113.8	113.2	111.9	110.1	107.1	105.3	102.3	100.5	99.3
82.5°	67.4	73.6	78.6	81.9	81.6	79.8	77.8	77.0	76.3	75.0	74.7
85°	31.9	33.1	34.9	39.1	42.1	42.7	42.1	41.6	39.7	40.3	40.9
87.5°	13.4	13.0	13.4	13.0	12.1	14.2	15.2	15.6	14.8	14.2	13.6
90°	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9	1.8	3.6	5.4
92.5°	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9	13.2	20.7	31.7
95°	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3	30.2	37.4	47.2
97.5°	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8	49.8	54.8	64.6
100°	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3	64.1	67.7	77.4
102.5°	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3	78.3	81.1	91.7
105°	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6	100.6	105.0	114.0
107.5°	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4	125.2	129.4	136.7
110°	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7	141.5	145.1	153.1



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1	157.9	160.8	168.8
115°	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9	181.6	184.2	192.3
117.5°	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2	203.8	206.7	214.7
120°	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4	218.1	221.7	229.7
122.5°	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4	232.3	235.1	243.2
125°	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2	251.0	255.5	263.5
127.5°	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0	266.7	272.4	282.6
130°	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3	276.0	283.1	294.6
132.5°	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4	283.7	292.3	305.3
135°	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9	295.5	306.2	320.5
137.5°	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6	309.2	319.2	333.5
140°	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1	317.8	328.5	342.7
142.5°	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1	327.1	337.0	351.2
145°	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0	341.8	350.7	363.2
147.5°	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7	356.8	364.4	376.0
150°	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0	366.8	373.0	384.6
152.5°	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0	376.0	381.6	391.6
155°	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1	388.1	393.4	402.3
157.5°	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8	399.7	403.9	411.6
160°	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7	406.8	410.4	416.6
162.5°	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1	413.2	416.8	422.3
165°	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7	422.0	424.6	429.1
167.5°	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2	429.3	430.9	433.4
170°	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4	433.5	434.4	436.2
172.5°	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3	435.7	436.6	438.3
175°	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6	438.8	439.7	440.6
177.5°	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2	440.8	440.8	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1441.5	1434.9	1430.0	1420.4	1413.6	1410.8	1405.4	1404.0	1409.3	1405.4	1405.0
5°	1398.7	1381.3	1367.4	1353.5	1338.5	1328.9	1314.5	1312.1	1308.4	1303.0	1301.8
7.5°	1347.3	1324.5	1306.7	1283.9	1264.0	1248.0	1229.9	1221.4	1216.7	1209.7	1200.3
10°	1312.6	1285.6	1261.5	1238.6	1214.0	1194.1	1176.0	1162.2	1153.2	1144.7	1141.1
12.5°	1278.4	1250.9	1220.0	1192.4	1164.8	1142.5	1122.6	1113.6	1103.6	1093.7	1085.3
15°	1225.4	1188.7	1154.9	1123.0	1099.6	1075.5	1056.2	1043.0	1028.0	1023.8	1007.5
17.5°	1169.0	1133.0	1093.6	1060.0	1032.8	1006.3	985.1	970.1	958.8	943.3	935.8
20°	1133.9	1091.2	1052.7	1022.0	991.8	960.6	938.9	926.2	915.4	902.8	896.8
22.5°	1096.4	1054.5	1015.1	979.1	948.5	917.7	902.3	889.2	876.9	865.2	857.3
25°	1041.2	999.1	957.5	920.2	888.3	866.0	848.0	832.9	826.3	814.9	806.5
27.5°	986.7	941.9	898.8	861.6	836.6	814.6	799.8	787.8	775.9	765.9	758.6
30°	951.5	905.8	858.8	829.4	802.9	781.8	765.5	754.1	745.1	736.1	730.7
32.5°	916.4	869.2	827.5	795.7	770.6	752.4	735.7	724.8	715.2	705.3	698.8
35°	860.1	811.9	778.2	746.9	722.2	705.3	693.9	678.3	670.5	663.3	656.7
37.5°	807.7	762.9	726.5	699.0	677.5	660.8	646.0	637.6	627.9	621.4	615.9
40°	769.2	728.3	695.2	666.3	650.6	632.0	618.1	607.3	600.0	591.7	585.6
42.5°	734.5	696.4	664.3	638.3	618.8	603.1	589.7	578.9	569.7	563.7	558.7
45°	685.5	647.6	616.3	592.2	574.2	559.1	545.3	539.8	527.8	520.6	518.2
47.5°	634.8	600.9	570.7	548.5	530.0	515.8	502.7	491.7	485.1	478.0	474.1
50°	600.7	568.1	539.8	518.2	500.2	484.5	472.4	465.2	456.2	449.6	444.8
52.5°	566.5	536.4	508.1	487.4	471.7	456.1	442.6	435.4	426.9	422.6	419.3
55°	517.6	485.7	461.6	441.1	424.9	410.5	397.8	390.6	385.2	380.9	379.8
57.5°	462.3	436.9	414.6	396.1	379.2	365.7	354.6	347.8	343.0	342.3	338.8
60°	426.1	403.2	382.8	362.9	348.5	335.8	326.2	318.3	313.5	313.0	311.7
62.5°	390.0	368.1	349.1	331.6	318.6	306.5	297.3	288.6	285.6	282.7	280.0
65°	336.4	316.6	301.0	287.0	273.2	263.0	254.0	248.6	241.9	238.4	231.8
67.5°	283.8	268.4	253.4	241.7	230.9	221.1	213.7	205.6	201.2	198.2	193.4
70°	249.1	237.1	222.1	209.5	201.0	193.2	187.2	178.2	175.1	172.7	170.3
72.5°	216.4	205.8	193.2	183.0	174.5	167.2	160.2	156.0	153.0	150.6	149.2
75°	170.3	160.1	149.3	142.0	136.0	130.0	126.4	123.4	122.2	121.5	119.1
77.5°	125.1	119.7	111.0	105.2	101.2	98.8	95.6	94.0	93.9	91.2	90.4
80°	95.7	92.6	85.4	83.0	80.1	77.7	75.8	72.9	69.8	68.6	66.8
82.5°	71.2	68.1	65.3	61.3	58.9	57.4	55.6	54.5	54.9	53.2	52.3
85°	37.9	34.9	33.7	33.1	31.9	33.1	32.5	31.9	31.3	30.7	31.3
87.5°	13.5	13.8	13.6	14.8	13.6	14.4	14.6	14.3	14.4	14.6	14.5
90°	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1	16.9	17.8	19.6
92.5°	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7	114.5	86.1	73.0
95°	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1	504.7	395.2	320.5
97.5°	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2	858.3	751.6	647.6
100°	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9	1051.3	959.6	867.0
102.5°	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6	1169.5	1125.5	1062.8
105°	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5	1236.4	1275.6	1265.8
107.5°	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1	1176.8	1277.4	1323.8
110°	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0	1109.1	1234.7	1310.4



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6	1042.2	1169.1	1258.4
115°	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2	946.3	1068.2	1165.2
117.5°	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9	879.9	984.9	1073.9
120°	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3	842.1	940.0	1018.3
122.5°	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0	815.0	902.2	975.6
125°	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1	778.9	856.3	920.4
127.5°	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6	744.4	816.6	876.6
130°	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9	720.1	789.6	847.5
132.5°	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0	697.3	760.4	816.1
135°	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8	662.3	719.3	770.0
137.5°	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3	631.0	678.3	721.4
140°	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6	612.4	653.4	690.8
142.5°	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3	596.7	632.0	664.4
145°	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2	576.8	604.4	628.5
147.5°	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9	560.3	581.5	599.6
150°	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5	551.0	567.9	584.0
152.5°	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3	541.7	557.2	569.7
155°	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6	527.9	540.4	550.1
157.5°	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9	514.7	524.3	532.0
160°	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8	504.7	513.6	519.9
162.5°	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0	496.1	503.6	509.2
165°	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2	483.4	488.7	493.1
167.5°	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8	470.9	475.0	478.2
170°	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1	463.8	466.5	468.2
172.5°	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7	457.4	459.3	460.4
175°	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7	447.7	449.5	449.5
177.5°	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9	443.6	443.6	443.6
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1404.4	1399.2	1397.8	1399.6	1397.8	1399.2	1404.4	1405.0	1405.4	1409.3	1404.0
5°	1295.8	1289.8	1292.8	1291.6	1292.8	1289.8	1295.8	1301.8	1303.0	1308.4	1312.1
7.5°	1200.2	1192.8	1184.8	1187.3	1184.8	1192.8	1200.2	1200.3	1209.7	1216.7	1221.4
10°	1133.3	1127.3	1123.6	1126.7	1123.6	1127.3	1133.3	1141.1	1144.7	1153.2	1162.2
12.5°	1076.9	1073.4	1070.2	1068.9	1070.2	1073.4	1076.9	1085.3	1093.7	1103.6	1113.6
15°	1000.3	993.1	990.1	982.2	990.1	993.1	1000.3	1007.5	1023.8	1028.0	1043.0
17.5°	929.6	927.2	919.4	916.1	919.4	927.2	929.6	935.8	943.3	958.8	970.1
20°	887.7	885.3	877.5	882.3	877.5	885.3	887.7	896.8	902.8	915.4	926.2
22.5°	853.1	847.7	845.3	843.8	845.3	847.7	853.1	857.3	865.2	876.9	889.2
25°	804.1	796.2	793.3	789.6	793.3	796.2	804.1	806.5	814.9	826.3	832.9
27.5°	755.2	751.0	747.0	746.1	747.0	751.0	755.2	758.6	765.9	775.9	787.8
30°	723.4	719.3	716.2	716.2	716.2	719.3	723.4	730.7	736.1	745.1	754.1
32.5°	695.0	691.8	688.8	688.3	688.8	691.8	695.0	698.8	705.3	715.2	724.8
35°	653.6	648.8	647.6	644.0	647.6	648.8	653.6	656.7	663.3	670.5	678.3
37.5°	610.6	606.6	606.5	606.2	606.5	606.6	610.6	615.9	621.4	627.9	637.6
40°	583.2	580.1	579.6	575.3	579.6	580.1	583.2	585.6	591.7	600.0	607.3
42.5°	553.8	552.2	550.2	548.4	550.2	552.2	553.8	558.7	563.7	569.7	578.9
45°	514.0	509.8	509.8	506.8	509.8	509.8	514.0	518.2	520.6	527.8	539.8
47.5°	472.8	469.6	469.9	466.8	469.9	469.6	472.8	474.1	478.0	485.1	491.7
50°	445.4	443.5	443.0	441.8	443.0	443.5	445.4	444.8	449.6	456.2	465.2
52.5°	417.9	417.1	419.4	416.7	419.4	417.1	417.9	419.3	422.6	426.9	435.4
55°	380.9	379.2	382.8	379.2	382.8	379.2	380.9	379.8	380.9	385.2	390.6
57.5°	338.5	336.8	340.0	338.2	340.0	336.8	338.5	338.8	342.3	343.0	347.8
60°	310.6	306.9	308.7	309.3	308.7	306.9	310.6	311.7	313.0	313.5	318.3
62.5°	277.3	275.2	276.5	273.8	276.5	275.2	277.3	280.0	282.7	285.6	288.6
65°	230.5	228.7	226.3	225.1	226.3	228.7	230.5	231.8	238.4	241.9	248.6
67.5°	193.7	189.3	189.2	190.2	189.2	189.3	193.7	193.4	198.2	201.2	205.6
70°	166.7	166.7	166.1	166.1	166.1	166.7	166.7	170.3	172.7	175.1	178.2
72.5°	147.9	147.5	146.3	145.9	146.3	147.5	147.9	149.2	150.6	153.0	156.0
75°	119.1	119.8	118.6	118.0	118.6	119.8	119.1	119.1	121.5	122.2	123.4
77.5°	88.0	85.4	86.8	85.4	86.8	85.4	88.0	90.4	91.2	93.9	94.0
80°	66.8	66.2	68.0	66.2	68.0	66.2	66.8	66.8	68.6	69.8	72.9
82.5°	52.9	52.3	53.1	51.7	53.1	52.3	52.9	52.3	53.2	54.9	54.5
85°	31.9	31.3	30.7	31.3	30.7	31.3	31.9	31.3	30.7	31.3	31.9
87.5°	15.0	14.5	14.7	14.7	14.7	14.5	15.0	14.5	14.6	14.4	14.3
90°	19.6	19.6	20.5	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1
92.5°	61.6	59.5	58.2	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7
95°	257.3	230.6	223.5	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1
97.5°	592.7	542.8	517.0	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2
100°	805.6	741.5	708.6	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9
102.5°	997.2	951.6	915.8	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6
105°	1237.3	1208.0	1190.2	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5
107.5°	1338.3	1338.1	1332.2	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1
110°	1350.4	1367.3	1373.5	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1316.9	1345.9	1361.5	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6
115°	1234.7	1277.4	1302.3	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2
117.5°	1143.4	1187.5	1212.2	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9
120°	1084.2	1126.9	1151.0	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3
122.5°	1034.4	1073.5	1097.6	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0
125°	970.3	1006.7	1026.4	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1
127.5°	921.9	954.0	972.6	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6
130°	892.0	921.3	939.1	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9
132.5°	860.6	890.0	906.3	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0
135°	809.1	838.6	854.5	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8
137.5°	756.4	783.2	798.0	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3
140°	723.7	746.9	760.2	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6
142.5°	692.4	711.9	724.6	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3
145°	649.8	664.9	674.8	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2
147.5°	616.5	628.7	634.4	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9
150°	597.3	608.0	611.5	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5
152.5°	580.9	589.5	593.0	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3
155°	559.0	565.3	567.9	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6
157.5°	539.0	544.0	546.5	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9
160°	526.1	530.6	532.4	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8
162.5°	514.0	517.7	518.1	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0
165°	496.7	498.5	498.5	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2
167.5°	480.0	481.6	480.9	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8
170°	470.0	470.9	470.9	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1
172.5°	460.7	462.4	460.9	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7
175°	449.5	450.4	448.6	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7
177.5°	442.9	443.6	441.5	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1405.4	1410.8	1413.6	1420.4	1430.0	1434.9	1441.5	1446.4	1453.1	1461.3	1468.0
5°	1314.5	1328.9	1338.5	1353.5	1367.4	1381.3	1398.7	1411.3	1428.2	1447.4	1462.5
7.5°	1229.9	1248.0	1264.0	1283.9	1306.7	1324.5	1347.3	1370.6	1396.9	1424.2	1450.0
10°	1176.0	1194.1	1214.0	1238.6	1261.5	1285.6	1312.6	1339.7	1372.8	1403.6	1438.4
12.5°	1122.6	1142.5	1164.8	1192.4	1220.0	1250.9	1278.4	1308.9	1344.4	1384.3	1421.6
15°	1056.2	1075.5	1099.6	1123.0	1154.9	1188.7	1225.4	1265.7	1305.4	1350.0	1396.3
17.5°	985.1	1006.3	1032.8	1060.0	1093.6	1133.0	1169.0	1213.2	1257.8	1309.7	1364.3
20°	938.9	960.6	991.8	1022.0	1052.7	1091.2	1133.9	1179.0	1226.5	1281.4	1342.1
22.5°	902.3	917.7	948.5	979.1	1015.1	1054.5	1096.4	1143.4	1195.2	1252.0	1315.6
25°	848.0	866.0	888.3	920.2	957.5	999.1	1041.2	1091.2	1147.7	1205.5	1273.5
27.5°	799.8	814.6	836.6	861.6	898.8	941.9	986.7	1038.8	1096.8	1155.7	1227.2
30°	765.5	781.8	802.9	829.4	858.8	905.8	951.5	1002.7	1061.7	1122.5	1195.9
32.5°	735.7	752.4	770.6	795.7	827.5	869.2	916.4	966.6	1026.5	1089.2	1160.7
35°	693.9	705.3	722.2	746.9	778.2	811.9	860.1	913.0	971.4	1036.4	1108.0
37.5°	646.0	660.8	677.5	699.0	726.5	762.9	807.7	861.2	915.4	977.7	1043.0
40°	618.1	632.0	650.6	666.3	695.2	728.3	769.2	825.1	879.3	937.7	997.3
42.5°	589.7	603.1	618.8	638.3	664.3	696.4	734.5	786.6	844.6	899.6	949.6
45°	545.3	559.1	574.2	592.2	616.3	647.6	685.5	733.1	783.6	834.2	872.1
47.5°	502.7	515.8	530.0	548.5	570.7	600.9	634.8	676.8	725.9	768.9	796.0
50°	472.4	484.5	500.2	518.2	539.8	568.1	600.7	642.2	683.1	722.2	746.9
52.5°	442.6	456.1	471.7	487.4	508.1	536.4	566.5	602.2	641.2	673.2	693.5
55°	397.8	410.5	424.9	441.1	461.6	485.7	517.6	545.9	576.6	603.7	615.7
57.5°	354.6	365.7	379.2	396.1	414.6	436.9	462.3	489.5	511.1	530.2	543.9
60°	326.2	335.8	348.5	362.9	382.8	403.2	426.1	451.4	468.2	484.5	497.1
62.5°	297.3	306.5	318.6	331.6	349.1	368.1	390.0	410.5	426.9	437.8	452.4
65°	254.0	263.0	273.2	287.0	301.0	316.6	336.4	351.5	362.9	375.0	384.0
67.5°	213.7	221.1	230.9	241.7	253.4	268.4	283.8	296.3	304.2	311.4	322.3
70°	187.2	193.2	201.0	209.5	222.1	237.1	249.1	258.8	264.2	271.4	284.6
72.5°	160.2	167.2	174.5	183.0	193.2	205.8	216.4	226.0	229.5	235.3	243.8
75°	126.4	130.0	136.0	142.0	149.3	160.1	170.3	172.7	175.8	180.6	186.5
77.5°	95.6	98.8	101.2	105.2	111.0	119.7	125.1	128.7	129.4	131.2	137.1
80°	75.8	77.7	80.1	83.0	85.4	92.6	95.7	99.3	100.5	102.3	105.3
82.5°	55.6	57.4	58.9	61.3	65.3	68.1	71.2	74.7	75.0	76.3	77.0
85°	32.5	33.1	31.9	33.1	33.7	34.9	37.9	40.9	40.3	39.7	41.6
87.5°	14.6	14.4	13.6	14.8	13.6	13.8	13.5	13.6	14.2	14.8	15.6
90°	15.2	14.3	12.5	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9
92.5°	232.3	287.0	291.6	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9
95°	771.8	788.7	643.6	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3
97.5°	976.5	842.3	574.7	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8
100°	1026.4	803.8	512.7	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3
102.5°	996.5	736.2	465.7	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3
105°	900.9	645.3	420.2	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6
107.5°	803.3	582.9	400.9	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4
110°	747.7	553.7	395.2	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	706.4	536.6	395.2	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1
115°	661.4	518.1	397.9	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9
117.5°	634.5	509.0	403.8	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2
120°	619.6	504.7	409.5	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4
122.5°	606.7	501.1	414.5	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4
125°	589.3	496.7	422.8	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2
127.5°	573.3	494.5	432.3	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0
130°	562.6	493.1	438.0	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3
132.5°	554.0	493.1	444.3	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4
135°	543.9	493.1	453.1	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9
137.5°	534.8	494.2	461.1	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6
140°	530.6	494.9	464.7	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1
142.5°	527.0	495.6	466.8	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1
145°	521.7	494.9	469.1	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0
147.5°	516.1	492.6	470.0	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7
150°	511.8	490.4	470.0	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0
152.5°	506.8	487.7	469.3	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0
155°	498.5	482.5	467.3	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1
157.5°	490.6	477.2	465.0	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8
160°	484.3	473.6	462.9	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7
162.5°	478.6	469.3	460.7	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1
165°	470.0	462.9	457.5	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7
167.5°	461.6	456.6	452.5	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2
170°	456.6	453.1	450.4	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4
172.5°	451.7	448.8	447.5	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3
175°	445.1	444.2	444.2	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6
177.5°	442.2	441.5	441.5	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1473.4	1477.7	1483.9	1491.1	1496.9	1503.2	1506.5	1506.5	1509.5	1515.7	1523.9
5°	1477.6	1493.2	1508.2	1527.5	1542.6	1560.0	1573.2	1585.9	1597.3	1611.8	1626.8
7.5°	1476.3	1502.4	1529.5	1559.8	1593.2	1619.8	1647.2	1668.6	1689.8	1717.4	1739.2
10°	1471.5	1505.2	1541.9	1580.5	1622.6	1659.3	1692.4	1722.5	1751.4	1781.5	1808.6
12.5°	1462.9	1505.7	1550.6	1596.9	1650.0	1692.0	1734.8	1766.8	1800.5	1833.4	1866.8
15°	1449.8	1500.4	1554.6	1619.0	1684.0	1730.9	1773.1	1814.6	1845.8	1883.2	1915.1
17.5°	1423.0	1488.2	1556.3	1626.7	1689.2	1743.7	1787.9	1827.4	1860.7	1901.8	1945.1
20°	1407.1	1477.6	1548.5	1623.8	1683.4	1739.4	1782.1	1823.0	1864.6	1918.1	1971.0
22.5°	1385.0	1460.2	1535.5	1607.0	1669.9	1723.9	1768.1	1818.2	1872.7	1933.5	1997.5
25°	1350.0	1427.6	1502.3	1570.2	1631.7	1687.0	1747.2	1814.6	1880.8	1960.9	2052.9
27.5°	1305.6	1380.4	1447.0	1518.9	1579.8	1650.3	1725.4	1798.5	1893.9	2004.0	2119.0
30°	1272.3	1343.4	1406.5	1474.5	1543.7	1621.4	1705.7	1791.7	1905.5	2034.9	2171.5
32.5°	1233.8	1298.1	1360.8	1426.4	1506.2	1591.5	1681.1	1786.5	1922.4	2069.6	2211.0
35°	1167.0	1224.8	1285.6	1358.3	1443.2	1536.0	1650.3	1778.5	1942.8	2101.0	2228.0
37.5°	1096.9	1142.5	1203.5	1280.4	1372.8	1480.1	1609.8	1765.6	1934.4	2076.3	2130.5
40°	1043.0	1085.7	1150.1	1230.8	1322.2	1439.7	1585.3	1745.3	1915.1	2013.8	2009.6
42.5°	989.5	1032.8	1094.8	1175.9	1271.2	1402.6	1552.6	1718.9	1862.2	1899.7	1821.3
45°	907.6	947.9	1008.7	1090.6	1192.8	1330.7	1488.4	1647.9	1739.4	1678.6	1523.3
47.5°	824.0	863.2	919.6	999.8	1111.5	1255.7	1404.8	1535.7	1548.5	1418.0	1231.7
50°	769.2	805.8	859.4	944.9	1053.2	1194.1	1337.9	1440.8	1408.9	1249.5	1057.5
52.5°	715.7	751.0	801.2	881.8	992.6	1130.5	1258.9	1339.7	1266.0	1096.4	923.6
55°	636.8	670.5	721.0	795.0	895.5	1022.0	1134.5	1164.0	1055.6	884.8	745.1
57.5°	561.8	586.5	636.4	701.9	798.8	910.3	990.9	985.6	866.0	712.1	612.0
60°	512.2	534.4	582.0	642.2	734.2	834.2	890.7	866.7	745.7	618.7	522.4
62.5°	465.9	486.8	526.6	582.0	661.1	748.0	789.2	755.9	641.7	530.1	453.5
65°	396.0	411.1	443.0	494.1	556.1	616.3	653.0	604.2	503.2	418.9	361.1
67.5°	330.6	343.7	372.0	408.8	451.5	493.0	508.0	462.3	383.6	326.8	286.1
70°	288.3	300.3	319.6	353.9	382.2	411.7	418.9	378.0	312.4	269.0	243.8
72.5°	247.8	259.0	275.8	300.0	319.6	336.5	339.9	301.9	251.7	221.9	202.3
75°	189.0	198.6	209.5	218.5	231.1	234.2	232.9	203.4	176.4	156.5	145.6
77.5°	138.9	142.9	149.5	153.1	153.7	153.5	147.3	128.7	114.7	106.6	102.1
80°	107.1	110.1	111.9	113.2	113.8	107.7	101.1	89.7	84.9	80.1	74.6
82.5°	77.8	79.8	81.6	81.9	78.6	73.6	67.4	61.7	58.4	56.0	53.9
85°	42.1	42.7	42.1	39.1	34.9	33.1	31.9	30.7	30.1	29.5	29.5
87.5°	15.2	14.2	12.1	13.0	13.4	13.0	13.4	13.1	12.9	13.1	13.3
90°	1.8	3.6	5.4	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1
92.5°	13.2	20.7	31.7	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7
95°	30.2	37.4	47.2	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1
97.5°	49.8	54.8	64.6	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2
100°	64.1	67.7	77.4	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9
102.5°	78.3	81.1	91.7	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6
105°	100.6	105.0	114.0	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5
107.5°	125.2	129.4	136.7	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1
110°	141.5	145.1	153.1	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.9	160.8	168.8	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6
115°	181.6	184.2	192.3	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2
117.5°	203.8	206.7	214.7	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9
120°	218.1	221.7	229.7	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3
122.5°	232.3	235.1	243.2	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0
125°	251.0	255.5	263.5	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1
127.5°	266.7	272.4	282.6	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6
130°	276.0	283.1	294.6	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9
132.5°	283.7	292.3	305.3	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0
135°	295.5	306.2	320.5	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8
137.5°	309.2	319.2	333.5	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3
140°	317.8	328.5	342.7	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6
142.5°	327.1	337.0	351.2	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3
145°	341.8	350.7	363.2	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2
147.5°	356.8	364.4	376.0	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9
150°	366.8	373.0	384.6	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5
152.5°	376.0	381.6	391.6	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3
155°	388.1	393.4	402.3	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6
157.5°	399.7	403.9	411.6	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9
160°	406.8	410.4	416.6	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8
162.5°	413.2	416.8	422.3	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0
165°	422.0	424.6	429.1	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2
167.5°	429.3	430.9	433.4	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8
170°	433.5	434.4	436.2	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1
172.5°	435.7	436.6	438.3	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7
175°	438.8	439.7	440.6	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7
177.5°	440.8	440.8	441.5	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1530.2	1530.2	1538.4	1537.8	1543.2	1541.2	1542.2
5°	1644.8	1655.1	1664.1	1670.2	1679.2	1681.6	1680.3
7.5°	1763.8	1786.5	1797.6	1812.8	1815.5	1823.5	1822.7
10°	1837.5	1859.8	1876.6	1889.8	1896.4	1904.9	1905.5
12.5°	1895.2	1914.1	1929.0	1941.3	1949.4	1952.0	1953.6
15°	1940.4	1961.4	1978.9	1996.4	2006.6	2014.4	2018.7
17.5°	1985.8	2018.4	2049.2	2072.9	2087.1	2099.2	2099.0
20°	2021.1	2058.3	2096.9	2124.0	2151.6	2163.6	2165.4
22.5°	2058.6	2115.7	2165.3	2207.3	2243.5	2256.1	2260.8
25°	2136.5	2211.2	2287.7	2346.6	2388.7	2413.4	2417.1
27.5°	2230.8	2331.8	2412.3	2466.7	2501.7	2520.0	2523.9
30°	2297.3	2390.6	2462.8	2503.7	2520.0	2522.4	2513.4
32.5°	2327.1	2396.8	2425.7	2423.3	2391.4	2370.3	2362.1
35°	2290.6	2276.2	2205.8	2121.6	2057.2	2016.2	2005.4
37.5°	2084.6	1960.0	1830.5	1703.2	1635.4	1600.9	1541.7
40°	1881.4	1703.9	1569.1	1461.9	1385.5	1324.1	1309.7
42.5°	1652.3	1468.9	1334.1	1242.3	1181.3	1139.2	1120.9
45°	1327.7	1170.0	1058.6	988.3	941.3	910.6	896.8
47.5°	1061.9	939.9	858.7	806.6	770.9	744.1	736.6
50°	916.1	818.5	749.9	706.0	678.9	658.4	650.0
52.5°	795.7	716.9	664.2	627.9	602.4	589.6	582.6
55°	656.7	588.6	550.7	521.8	507.4	497.1	492.3
57.5°	537.0	487.9	460.2	440.2	426.9	420.4	417.9
60°	470.0	431.5	406.3	390.6	381.6	373.2	370.8
62.5°	410.8	380.5	361.0	347.2	338.2	334.7	333.1
65°	331.0	311.1	296.7	288.3	281.1	279.8	279.3
67.5°	263.1	251.5	243.9	235.1	232.6	228.4	227.5
70°	225.1	217.3	208.2	205.3	202.2	198.0	198.6
72.5°	190.9	183.1	176.9	173.0	171.9	170.0	171.7
75°	139.6	137.2	134.8	131.8	130.6	130.6	130.0
77.5°	99.7	97.6	95.0	93.2	92.8	90.2	91.2
80°	72.2	69.2	68.0	68.6	66.8	66.2	66.2
82.5°	53.4	52.3	51.2	51.3	50.9	50.3	50.8
85°	29.5	28.9	28.9	28.3	28.3	27.6	27.6
87.5°	14.0	14.6	14.0	13.6	13.6	14.2	14.7
90°	16.9	17.8	19.6	19.6	19.6	20.5	20.5
92.5°	114.5	86.1	73.0	61.6	59.5	58.2	56.8
95°	504.7	395.2	320.5	257.3	230.6	223.5	209.2
97.5°	858.3	751.6	647.6	592.7	542.8	517.0	505.6
100°	1051.3	959.6	867.0	805.6	741.5	708.6	694.4
102.5°	1169.5	1125.5	1062.8	997.2	951.6	915.8	905.1
105°	1236.4	1275.6	1265.8	1237.3	1208.0	1190.2	1179.5
107.5°	1176.8	1277.4	1323.8	1338.3	1338.1	1332.2	1325.1
110°	1109.1	1234.7	1310.4	1350.4	1367.3	1373.5	1373.5



TEST NUMBER: P333600-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1042.2	1169.1	1258.4	1316.9	1345.9	1361.5	1367.8
115°	946.3	1068.2	1165.2	1234.7	1277.4	1302.3	1313.9
117.5°	879.9	984.9	1073.9	1143.4	1187.5	1212.2	1219.3
120°	842.1	940.0	1018.3	1084.2	1126.9	1151.0	1158.2
122.5°	815.0	902.2	975.6	1034.4	1073.5	1097.6	1104.0
125°	778.9	856.3	920.4	970.3	1006.7	1026.4	1035.3
127.5°	744.4	816.6	876.6	921.9	954.0	972.6	976.5
130°	720.1	789.6	847.5	892.0	921.3	939.1	944.5
132.5°	697.3	760.4	816.1	860.6	890.0	906.3	912.4
135°	662.3	719.3	770.0	809.1	838.6	854.5	859.9
137.5°	631.0	678.3	721.4	756.4	783.2	798.0	803.8
140°	612.4	653.4	690.8	723.7	746.9	760.2	764.6
142.5°	596.7	632.0	664.4	692.4	711.9	724.6	728.3
145°	576.8	604.4	628.5	649.8	664.9	674.8	678.3
147.5°	560.3	581.5	599.6	616.5	628.7	634.4	636.0
150°	551.0	567.9	584.0	597.3	608.0	611.5	612.4
152.5°	541.7	557.2	569.7	580.9	589.5	593.0	593.9
155°	527.9	540.4	550.1	559.0	565.3	567.9	568.8
157.5°	514.7	524.3	532.0	539.0	544.0	546.5	546.4
160°	504.7	513.6	519.9	526.1	530.6	532.4	531.5
162.5°	496.1	503.6	509.2	514.0	517.7	518.1	517.9
165°	483.4	488.7	493.1	496.7	498.5	498.5	498.5
167.5°	470.9	475.0	478.2	480.0	481.6	480.9	480.7
170°	463.8	466.5	468.2	470.0	470.9	470.9	470.0
172.5°	457.4	459.3	460.4	460.7	462.4	460.9	460.0
175°	447.7	449.5	449.5	449.5	450.4	448.6	447.7
177.5°	443.6	443.6	443.6	442.9	443.6	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5

(END OF REPORT)