

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333601-940

Luminaire Tested: **S125RDIP-S1090D1035U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333601-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1035U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7456.1 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333601-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333601-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	90	87	84	81	74	71	69	62	60	58	50	49	48	43
2	90	82	76	71	82	76	71	66	65	61	58	54	52	49	45	43	41	36
3	82	72	65	59	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10293	10293	10293
5°	10317	10200	10263
10°	10239	10105	10105
15°	10117	9900	9819
20°	9961	9614	9498
25°	9779	9333	9128
30°	9552	9004	8717
35°	9320	8665	8257
40°	9104	8312	7804
45°	8840	7916	7311
50°	8575	7486	6797
55°	8268	7076	6248
60°	7962	6577	5660
65°	7597	5997	4985
70°	7183	5274	4296
75°	6608	4447	3573
80°	5821	3492	2998
85°	4905	2853	2675



TEST NUMBER: P333601-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.0
10°-20°	418.8	5.6
20°-30°	607.3	8.1
30°-40°	692.2	9.3
40°-50°	674.7	9.0
50°-60°	567.9	7.6
60°-70°	398.1	5.3
70°-80°	204.6	2.7
80°-90°	54.2	0.7
90°-100°	43.6	0.6
100°-110°	269.0	3.6
110°-120°	487.9	6.5
120°-130°	626.1	8.4
130°-140°	673.4	9.0
140°-150°	632.1	8.5
150°-160°	511.3	6.9
160°-170°	330.7	4.4
170°-180°	114.1	1.5
0°-30°	1176.0	15.8
0°-40°	1868.2	25.1
0°-60°	3110.9	41.7
0°-90°	3767.8	50.5
90°-120°	800.5	10.7
90°-150°	2732.2	36.6
90°-180°	3688.0	49.5
0°-180°	7456.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1591	1586	1573	1585	1583	151
15°	1513	1505	1481	1479	1469	426
25°	1372	1353	1310	1294	1281	631
35°	1182	1152	1099	1065	1047	740
45°	968	931	867	820	800	746
55°	734	694	628	576	555	657
65°	497	455	392	346	326	492
75°	265	228	178	153	143	280
85°	66	45	38	37	36	74
90°	1	8	14	19	21	5
95°	51	46	14	18	19	65
105°	262	265	265	265	264	277
115°	492	496	497	493	488	487
125°	699	705	705	702	699	624
135°	872	877	875	873	868	672
145°	1011	1012	1012	1013	1008	632
155°	1113	1108	1109	1112	1105	513
165°	1174	1169	1170	1175	1168	332
175°	1201	1196	1197	1203	1196	114
180°	1201	1201	1201	1201	1201	



TEST NUMBER: P333601-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1596.7	1596.1	1595.4	1594.7	1594.1	1592.8	1590.6	1588.5	1586.4	1584.2	1586.4
5°	1591.4	1590.4	1589.3	1588.2	1587.2	1585.1	1582.2	1579.2	1576.3	1573.3	1576.0
7.5°	1575.7	1574.8	1573.7	1572.7	1571.6	1569.4	1565.8	1562.4	1558.8	1555.3	1557.2
10°	1561.3	1560.5	1559.7	1558.9	1558.1	1555.9	1552.1	1548.4	1544.6	1540.9	1541.7
12.5°	1544.9	1543.9	1542.9	1541.9	1540.9	1537.8	1532.9	1527.8	1522.8	1517.7	1518.3
15°	1513.1	1511.5	1509.9	1508.3	1506.7	1503.2	1497.5	1491.9	1486.3	1480.7	1480.4
17.5°	1477.3	1474.8	1472.4	1469.9	1467.4	1462.7	1455.6	1448.6	1441.5	1434.4	1433.1
20°	1449.4	1446.7	1444.0	1441.4	1438.7	1433.1	1424.5	1415.9	1407.4	1398.8	1397.5
22.5°	1418.5	1415.9	1413.2	1410.5	1407.8	1402.0	1393.0	1384.0	1375.0	1366.0	1363.4
25°	1372.3	1368.3	1364.3	1360.3	1356.3	1349.3	1339.4	1329.5	1319.6	1309.7	1306.3
27.5°	1319.4	1314.5	1309.6	1304.8	1299.8	1292.2	1281.6	1271.0	1260.3	1249.7	1244.9
30°	1280.9	1275.8	1270.7	1265.6	1260.5	1252.3	1241.1	1229.8	1218.6	1207.4	1201.2
32.5°	1243.2	1237.3	1231.4	1225.5	1219.5	1210.9	1199.4	1187.9	1176.4	1165.0	1158.2
35°	1182.1	1175.7	1169.3	1162.9	1156.5	1147.2	1135.1	1123.1	1111.1	1099.0	1091.3
37.5°	1122.1	1114.4	1106.5	1098.8	1090.9	1080.8	1068.4	1056.0	1043.6	1031.2	1021.8
40°	1079.8	1071.7	1063.7	1055.7	1047.7	1037.2	1024.4	1011.6	998.7	985.9	975.7
42.5°	1035.5	1027.3	1019.0	1010.8	1002.6	991.8	978.5	965.3	952.0	938.7	929.0
45°	967.9	960.1	952.3	944.6	936.8	925.6	910.9	896.2	881.5	866.7	856.0
47.5°	897.8	889.6	881.4	873.3	865.0	853.5	838.7	823.9	809.0	794.2	783.2
50°	853.5	844.6	835.8	827.0	818.1	806.1	790.9	775.6	760.4	745.1	733.9
52.5°	805.3	796.3	787.2	778.2	769.2	757.4	743.1	728.6	714.3	699.9	687.8
55°	734.3	725.8	717.2	708.6	700.1	688.3	673.3	658.4	643.4	628.4	616.4
57.5°	662.5	653.4	644.3	635.1	626.0	614.2	599.8	585.3	570.9	556.4	544.7
60°	616.4	607.0	597.6	588.3	578.9	566.9	552.5	538.1	523.6	509.2	497.4
62.5°	567.2	558.3	549.4	540.4	531.5	519.7	505.1	490.4	475.7	461.0	450.1
65°	497.1	488.0	478.9	469.8	460.7	449.2	435.0	420.8	406.6	392.4	381.7
67.5°	427.6	418.5	409.4	400.3	391.2	379.9	366.2	352.7	339.1	325.5	315.8
70°	380.4	371.3	362.2	353.1	344.0	332.8	319.4	306.0	292.7	279.3	271.0
72.5°	334.2	325.3	316.4	307.6	298.6	287.9	275.4	262.9	250.4	237.9	230.2
75°	264.8	256.8	248.8	240.8	232.7	223.1	211.9	200.6	189.4	178.2	172.3
77.5°	196.0	189.6	183.2	176.7	170.3	162.6	153.6	144.6	135.6	126.6	122.5
80°	156.5	150.1	143.7	137.2	130.8	123.9	116.4	108.9	101.4	93.9	91.5
82.5°	118.0	112.2	106.4	100.7	94.9	89.4	84.3	79.1	74.0	68.8	67.8
85°	66.2	61.3	56.5	51.7	46.9	43.9	42.5	41.2	39.9	38.5	38.3
87.5°	22.3	21.1	20.0	18.8	17.6	17.0	17.1	17.2	17.2	17.3	17.5
90°	0.9	2.5	4.0	5.6	7.2	8.7	10.1	11.5	12.8	14.3	15.2
92.5°	13.7	12.6	11.5	10.3	9.3	9.4	10.5	11.8	13.0	14.3	15.2
95°	50.7	50.1	49.6	49.0	48.4	44.3	36.8	29.2	21.8	14.3	15.2
97.5°	105.9	107.0	108.1	109.1	110.2	103.3	88.5	73.6	58.7	43.8	38.3
100°	148.6	149.3	149.9	150.4	151.1	151.8	152.6	153.4	154.1	154.9	125.5
102.5°	192.2	192.9	193.7	194.4	195.1	195.7	196.3	196.7	197.2	197.7	192.1
105°	261.7	262.5	263.3	264.1	264.9	265.3	265.3	265.3	265.3	265.3	265.3
107.5°	334.0	334.0	334.0	334.0	334.0	334.2	334.7	335.0	335.5	335.8	335.9
110°	381.0	381.0	381.0	381.0	381.0	381.3	381.7	382.1	382.5	382.8	382.3



TEST NUMBER: P333601-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	425.3	425.7	426.1	426.7	427.1	427.5	427.8	427.9	428.2	428.5	427.7
115°	491.5	492.5	493.5	494.5	495.4	496.1	496.2	496.4	496.6	496.8	496.1
117.5°	560.0	560.0	559.9	559.9	559.9	560.3	561.0	561.7	562.5	563.2	562.2
120°	602.8	602.5	602.4	602.2	602.0	602.2	602.8	603.3	604.0	604.6	604.1
122.5°	640.5	641.2	642.0	642.7	643.5	644.0	644.4	644.6	644.9	645.2	644.7
125°	698.9	700.3	701.7	703.1	704.5	705.2	705.2	705.2	705.2	705.2	704.4
127.5°	754.7	755.6	756.6	757.6	758.6	759.0	758.9	758.8	758.7	758.6	758.1
130°	788.8	789.9	790.9	791.8	792.8	793.4	793.6	793.8	794.0	794.2	793.6
132.5°	823.0	824.2	825.4	826.4	827.6	828.0	827.5	827.2	826.7	826.3	826.1
135°	871.6	872.8	874.1	875.2	876.4	876.8	876.4	876.0	875.6	875.2	874.8
137.5°	916.3	917.4	918.4	919.4	920.4	920.8	920.4	920.1	919.7	919.4	919.4
140°	945.6	945.9	946.4	946.7	947.1	947.3	947.0	946.8	946.6	946.5	946.8
142.5°	971.9	972.1	972.4	972.6	972.9	973.1	973.4	973.7	973.9	974.2	974.3
145°	1010.6	1010.9	1011.3	1011.7	1012.1	1012.4	1012.4	1012.4	1012.4	1012.4	1012.5
147.5°	1044.4	1044.3	1044.2	1044.1	1044.0	1044.1	1044.4	1044.6	1044.8	1045.1	1045.4
150°	1065.8	1065.3	1065.0	1064.5	1064.2	1064.2	1064.5	1065.0	1065.3	1065.8	1066.1
152.5°	1086.4	1085.6	1084.7	1083.8	1082.9	1082.7	1083.1	1083.4	1083.9	1084.2	1084.7
155°	1112.9	1111.8	1110.5	1109.4	1108.2	1107.8	1108.2	1108.6	1108.9	1109.4	1110.0
157.5°	1133.4	1132.7	1132.0	1131.3	1130.6	1130.2	1130.2	1130.3	1130.3	1130.4	1131.0
160°	1147.6	1146.5	1145.3	1144.1	1142.9	1142.4	1142.6	1142.8	1143.0	1143.2	1144.0
162.5°	1159.0	1157.9	1156.6	1155.5	1154.3	1153.8	1154.0	1154.2	1154.4	1154.6	1155.7
165°	1174.4	1173.1	1172.0	1170.8	1169.7	1169.1	1169.3	1169.5	1169.7	1169.9	1171.1
167.5°	1185.8	1184.5	1183.3	1182.1	1180.9	1180.4	1180.5	1180.7	1180.9	1181.2	1182.6
170°	1192.1	1190.8	1189.4	1188.0	1186.6	1186.1	1186.2	1186.4	1186.6	1186.9	1188.4
172.5°	1196.4	1195.1	1193.6	1192.3	1190.9	1190.4	1190.7	1191.1	1191.4	1191.8	1193.2
175°	1201.0	1199.9	1198.7	1197.5	1196.3	1195.9	1196.1	1196.2	1196.4	1196.6	1198.2
177.5°	1203.2	1202.3	1201.3	1200.3	1199.4	1199.0	1199.2	1199.4	1199.5	1199.6	1200.8
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0



TEST NUMBER: P333601-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1588.5	1590.6	1592.8	1593.7	1593.5	1593.3	1593.0	1592.9
5°	1578.7	1581.4	1584.0	1585.1	1584.6	1584.0	1583.5	1583.0
7.5°	1559.1	1560.9	1562.8	1563.4	1562.8	1562.3	1561.7	1561.0
10°	1542.5	1543.3	1544.1	1544.1	1543.3	1542.5	1541.7	1540.9
12.5°	1518.9	1519.5	1520.1	1519.7	1518.5	1517.3	1516.1	1514.8
15°	1480.2	1479.9	1479.6	1478.3	1475.9	1473.5	1471.1	1468.6
17.5°	1431.7	1430.4	1429.1	1427.5	1425.4	1423.4	1421.5	1419.5
20°	1396.2	1394.8	1393.5	1391.6	1389.2	1386.8	1384.4	1382.0
22.5°	1360.8	1358.2	1355.6	1353.3	1351.3	1349.3	1347.3	1345.3
25°	1302.8	1299.3	1295.8	1292.6	1289.7	1286.7	1283.8	1280.9
27.5°	1240.0	1235.2	1230.3	1226.5	1223.6	1220.8	1217.9	1215.1
30°	1195.1	1188.9	1182.8	1178.5	1176.1	1173.7	1171.3	1168.9
32.5°	1151.5	1144.6	1137.8	1132.9	1129.9	1126.9	1123.7	1120.7
35°	1083.5	1075.8	1068.0	1062.3	1058.5	1054.8	1051.1	1047.3
37.5°	1012.5	1003.3	993.9	987.5	983.8	980.2	976.5	972.9
40°	965.5	955.4	945.2	938.5	935.3	932.1	928.9	925.7
42.5°	919.3	909.5	899.7	892.5	887.8	883.2	878.4	873.7
45°	845.3	834.6	823.9	816.5	812.5	808.5	804.5	800.5
47.5°	772.2	761.2	750.2	742.4	738.0	733.5	729.2	724.7
50°	722.6	711.4	700.2	692.6	688.6	684.6	680.6	676.5
52.5°	675.7	663.6	651.5	643.5	639.4	635.4	631.4	627.4
55°	604.3	592.3	580.2	572.0	567.8	563.5	559.2	554.9
57.5°	532.9	521.1	509.3	501.5	497.8	493.9	490.1	486.3
60°	485.6	473.9	462.1	454.2	450.2	446.2	442.2	438.2
62.5°	439.3	428.3	417.4	409.9	405.9	401.9	397.9	393.9
65°	371.0	360.3	349.6	342.2	338.2	334.2	330.2	326.2
67.5°	305.9	296.1	286.3	279.8	276.6	273.4	270.2	267.0
70°	262.7	254.4	246.1	240.3	237.1	233.9	230.7	227.5
72.5°	222.6	214.9	207.2	202.3	200.2	198.0	195.9	193.8
75°	166.4	160.5	154.6	150.7	148.8	147.0	145.1	143.2
77.5°	118.4	114.3	110.1	107.4	106.0	104.6	103.3	101.8
80°	89.1	86.7	84.3	82.8	82.2	81.7	81.1	80.6
82.5°	66.6	65.5	64.4	63.7	63.3	63.0	62.7	62.3
85°	38.0	37.7	37.5	37.2	36.9	36.6	36.4	36.1
87.5°	17.7	17.9	18.1	18.1	18.0	17.9	17.8	17.7
90°	16.2	17.2	18.2	19.0	19.6	20.2	20.8	21.4
92.5°	16.2	17.2	18.2	18.8	19.1	19.4	19.7	20.0
95°	16.2	17.2	18.2	18.7	18.7	18.7	18.7	18.7
97.5°	32.6	27.1	21.5	18.7	18.7	18.7	18.7	18.7
100°	95.9	66.5	37.0	21.8	21.0	20.2	19.5	18.7
102.5°	186.5	180.9	175.3	165.9	152.4	138.9	125.5	112.0
105°	265.3	265.3	265.3	265.2	265.0	264.8	264.7	264.4
107.5°	335.9	336.0	336.0	335.7	335.1	334.6	333.9	333.3
110°	381.7	381.0	380.5	380.3	380.5	380.7	380.8	381.0



TEST NUMBER: P333601-940

CATALOG NUMBER: S125RDIP-S1090D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	427.0	426.1	425.4	424.9	424.6	424.4	424.1	423.8
115°	495.3	494.5	493.7	492.7	491.5	490.3	489.1	487.9
117.5°	561.2	560.2	559.1	558.3	557.9	557.3	556.8	556.2
120°	603.8	603.3	603.0	602.3	601.3	600.3	599.3	598.3
122.5°	644.4	644.0	643.5	642.7	641.7	640.5	639.4	638.2
125°	703.6	702.8	702.0	701.3	700.7	700.1	699.5	698.9
127.5°	757.7	757.2	756.8	755.9	754.4	753.0	751.5	750.0
130°	793.0	792.4	791.8	791.0	790.1	789.1	788.1	787.0
132.5°	826.0	825.9	825.7	825.2	824.2	823.2	822.2	821.3
135°	874.4	874.1	873.6	872.8	871.6	870.5	869.2	868.1
137.5°	919.5	919.6	919.7	919.2	918.2	917.1	916.1	915.1
140°	947.3	947.6	948.0	947.6	946.5	945.2	944.1	942.9
142.5°	974.4	974.5	974.6	974.0	972.8	971.6	970.4	969.2
145°	1012.7	1012.9	1013.1	1012.6	1011.5	1010.2	1009.1	1007.9
147.5°	1045.5	1045.8	1046.1	1045.4	1044.0	1042.6	1041.2	1039.7
150°	1066.6	1066.9	1067.3	1066.8	1065.1	1063.5	1061.9	1060.4
152.5°	1085.0	1085.5	1085.8	1085.3	1083.9	1082.4	1081.0	1079.6
155°	1110.5	1111.2	1111.8	1111.3	1109.6	1108.0	1106.5	1104.9
157.5°	1131.7	1132.3	1132.9	1132.5	1130.9	1129.3	1127.7	1126.1
160°	1144.8	1145.6	1146.4	1145.9	1144.4	1142.8	1141.2	1139.6
162.5°	1156.8	1157.9	1159.0	1158.7	1157.0	1155.2	1153.5	1151.7
165°	1172.2	1173.5	1174.7	1174.5	1172.9	1171.3	1169.7	1168.1
167.5°	1184.0	1185.4	1186.9	1186.7	1184.9	1183.1	1181.3	1179.6
170°	1190.0	1191.6	1193.2	1193.0	1191.2	1189.5	1187.8	1186.0
172.5°	1194.6	1196.1	1197.5	1197.3	1195.5	1193.7	1191.9	1190.3
175°	1199.8	1201.4	1202.9	1202.8	1201.0	1199.3	1197.5	1195.7
177.5°	1201.8	1203.0	1204.1	1204.0	1202.7	1201.5	1200.2	1198.9
180°	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0	1201.0

(END OF REPORT)