

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333605-940

Luminaire Tested: **S125RDIP-S1090D1205U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333605-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7516.9 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	32	28	32	28	25	27	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9469	9469	9469	9469
5°	10893	9481	8373	9481
10°	12496	9433	7389	9433
15°	13497	9336	6567	9336
20°	14882	9224	6064	9224
25°	17224	9075	5627	9075
30°	18744	8918	5341	8918
35°	15811	8736	5077	8736
40°	11042	8408	4850	8408
45°	8191	7965	4629	7965
50°	6531	7504	4439	7504
55°	5543	6933	4270	6933
60°	4790	6421	3995	6421
65°	4268	5868	3440	5868
70°	3750	5374	3136	5374
75°	3244	4654	2944	4654
80°	2462	3916	2462	3916
85°	2045	3083	2319	3083



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.6	1.9
10°-20°	412.0	5.5
20°-30°	653.3	8.7
30°-40°	787.8	10.5
40°-50°	703.5	9.4
50°-60°	539.5	7.2
60°-70°	350.6	4.7
70°-80°	170.5	2.3
80°-90°	43.6	0.6
90°-100°	89.2	1.2
100°-110°	263.4	3.5
110°-120°	446.1	5.9
120°-130°	587.0	7.8
130°-140°	657.8	8.8
140°-150°	644.7	8.6
150°-160°	541.5	7.2
160°-170°	359.9	4.8
170°-180°	126.0	1.7
0°-30°	1205.9	16.0
0°-40°	1993.7	26.5
0°-60°	3236.7	43.1
0°-90°	3801.4	50.6
90°-120°	798.6	10.6
90°-150°	2688.1	35.8
90°-180°	3716.0	49.4
0°-180°	7516.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1466	1466	1466	1466	1466	
5°	1680	1462	1292	1462	1680	168
15°	2019	1396	982	1396	2019	578
25°	2417	1274	790	1274	2417	1110
35°	2005	1108	644	1108	2005	1211
45°	897	872	507	872	897	716
55°	492	616	379	616	492	447
65°	279	384	225	384	279	278
75°	130	186	118	186	130	138
85°	28	42	31	42	28	32
90°	25	1	25	1	25	16
95°	89	67	89	67	89	91
105°	257	236	257	236	257	272
115°	451	447	451	447	451	446
125°	656	652	656	652	656	586
135°	851	848	851	848	851	656
145°	1031	1027	1031	1027	1031	644
155°	1175	1175	1175	1175	1175	541
165°	1274	1278	1274	1278	1274	359
175°	1323	1328	1323	1328	1323	126
180°	1332	1332	1332	1332	1332	



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1542.2	1541.2	1543.2	1537.8	1538.4	1530.2	1530.2	1523.9	1515.7	1509.5	1506.5
5°	1680.3	1681.6	1679.2	1670.2	1664.1	1655.1	1644.8	1626.8	1611.8	1597.3	1585.9
7.5°	1822.7	1823.5	1815.5	1812.8	1797.6	1786.5	1763.8	1739.2	1717.4	1689.8	1668.6
10°	1905.5	1904.9	1896.4	1889.8	1876.6	1859.8	1837.5	1808.6	1781.5	1751.4	1722.5
12.5°	1953.6	1952.0	1949.4	1941.3	1929.0	1914.1	1895.2	1866.8	1833.4	1800.5	1766.8
15°	2018.7	2014.4	2006.6	1996.4	1978.9	1961.4	1940.4	1915.1	1883.2	1845.8	1814.6
17.5°	2099.0	2099.2	2087.1	2072.9	2049.2	2018.4	1985.8	1945.1	1901.8	1860.7	1827.4
20°	2165.4	2163.6	2151.6	2124.0	2096.9	2058.3	2021.1	1971.0	1918.1	1864.6	1823.0
22.5°	2260.8	2256.1	2243.5	2207.3	2165.3	2115.7	2058.6	1997.5	1933.5	1872.7	1818.2
25°	2417.1	2413.4	2388.7	2346.6	2287.7	2211.2	2136.5	2052.9	1960.9	1880.8	1814.6
27.5°	2523.9	2520.0	2501.7	2466.7	2412.3	2331.8	2230.8	2119.0	2004.0	1893.9	1798.5
30°	2513.4	2522.4	2520.0	2503.7	2462.8	2390.6	2297.3	2171.5	2034.9	1905.5	1791.7
32.5°	2362.1	2370.3	2391.4	2423.3	2425.7	2396.8	2327.1	2211.0	2069.6	1922.4	1786.5
35°	2005.4	2016.2	2057.2	2121.6	2205.8	2276.2	2290.6	2228.0	2101.0	1942.8	1778.5
37.5°	1541.7	1600.9	1635.4	1703.2	1830.5	1960.0	2084.6	2130.5	2076.3	1934.4	1765.6
40°	1309.7	1324.1	1385.5	1461.9	1569.1	1703.9	1881.4	2009.6	2013.8	1915.1	1745.3
42.5°	1120.9	1139.2	1181.3	1242.3	1334.1	1468.9	1652.3	1821.3	1899.7	1862.2	1718.9
45°	896.8	910.6	941.3	988.3	1058.6	1170.0	1327.7	1523.3	1678.6	1739.4	1647.9
47.5°	736.6	744.1	770.9	806.6	858.7	939.9	1061.9	1231.7	1418.0	1548.5	1535.7
50°	650.0	658.4	678.9	706.0	749.9	818.5	916.1	1057.5	1249.5	1408.9	1440.8
52.5°	582.6	589.6	602.4	627.9	664.2	716.9	795.7	923.6	1096.4	1266.0	1339.7
55°	492.3	497.1	507.4	521.8	550.7	588.6	656.7	745.1	884.8	1055.6	1164.0
57.5°	417.9	420.4	426.9	440.2	460.2	487.9	537.0	612.0	712.1	866.0	985.6
60°	370.8	373.2	381.6	390.6	406.3	431.5	470.0	522.4	618.7	745.7	866.7
62.5°	333.1	334.7	338.2	347.2	361.0	380.5	410.8	453.5	530.1	641.7	755.9
65°	279.3	279.8	281.1	288.3	296.7	311.1	331.0	361.1	418.9	503.2	604.2
67.5°	227.5	228.4	232.6	235.1	243.9	251.5	263.1	286.1	326.8	383.6	462.3
70°	198.6	198.0	202.2	205.3	208.2	217.3	225.1	243.8	269.0	312.4	378.0
72.5°	171.7	170.0	171.9	173.0	176.9	183.1	190.9	202.3	221.9	251.7	301.9
75°	130.0	130.6	130.6	131.8	134.8	137.2	139.6	145.6	156.5	176.4	203.4
77.5°	91.2	90.2	92.8	93.2	95.0	97.6	99.7	102.1	106.6	114.7	128.7
80°	66.2	66.2	66.8	68.6	68.0	69.2	72.2	74.6	80.1	84.9	89.7
82.5°	50.8	50.3	50.9	51.3	51.2	52.3	53.4	53.9	56.0	58.4	61.7
85°	27.6	27.6	28.3	28.3	28.9	28.9	29.5	29.5	29.5	30.1	30.7
87.5°	15.6	15.0	14.4	14.2	14.5	15.3	14.6	13.9	13.6	13.5	13.6
90°	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9	17.7	16.6	15.0
92.5°	48.9	48.4	47.9	47.3	46.9	45.8	44.3	42.8	41.3	39.8	37.8
95°	89.1	88.6	88.2	87.7	87.3	86.2	84.6	83.0	81.4	79.8	77.5
97.5°	135.1	134.8	134.6	134.3	134.0	133.1	131.6	130.1	128.6	127.1	123.9
100°	170.0	169.5	169.0	168.5	168.1	166.8	164.8	162.6	160.6	158.5	155.5
102.5°	204.7	204.1	203.5	202.9	202.2	200.7	198.5	196.2	193.9	191.7	190.2
105°	257.0	256.3	255.6	254.9	254.2	253.2	251.8	250.4	249.1	247.6	246.3
107.5°	310.4	310.5	310.6	310.6	310.7	310.3	309.6	308.9	308.3	307.6	306.5
110°	350.3	350.4	350.7	350.9	351.2	350.9	350.3	349.6	348.8	348.1	347.5



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	389.2	389.6	390.0	390.5	390.8	390.9	390.6	390.3	389.9	389.6	388.7
115°	450.8	450.9	451.2	451.5	451.7	451.9	452.1	452.4	452.6	452.8	452.4
117.5°	510.9	511.8	512.7	513.6	514.5	514.9	514.7	514.5	514.3	514.2	513.7
120°	552.3	553.2	554.1	555.1	556.0	556.4	556.4	556.4	556.4	556.4	556.2
122.5°	593.8	594.5	595.2	595.9	596.7	597.2	597.4	597.5	597.7	597.9	597.3
125°	655.9	656.1	656.4	656.7	656.8	657.2	657.6	658.1	658.5	659.1	658.8
127.5°	715.6	716.0	716.5	717.0	717.5	717.8	718.0	718.3	718.5	718.7	718.5
130°	755.4	755.8	756.3	756.8	757.2	757.6	757.8	758.0	758.3	758.5	758.0
132.5°	792.7	793.4	794.0	794.6	795.3	795.7	795.9	796.2	796.4	796.7	796.7
135°	850.7	851.7	852.6	853.5	854.4	854.9	854.9	854.9	854.9	854.9	854.6
137.5°	907.5	908.7	909.8	911.0	912.1	912.6	912.3	912.0	911.7	911.4	911.0
140°	944.0	945.1	946.3	947.4	948.6	949.0	948.5	948.0	947.5	947.1	946.4
142.5°	978.8	980.0	981.1	982.2	983.4	983.8	983.6	983.3	983.0	982.8	981.9
145°	1031.0	1031.7	1032.4	1033.1	1033.8	1034.1	1034.1	1034.1	1034.1	1034.1	1033.4
147.5°	1075.6	1077.2	1078.7	1080.3	1081.8	1082.4	1081.8	1081.3	1080.7	1080.1	1079.6
150°	1108.8	1109.2	1109.6	1110.1	1110.6	1110.8	1110.8	1110.8	1110.8	1110.8	1109.9
152.5°	1136.1	1136.9	1137.7	1138.6	1139.4	1139.5	1139.0	1138.4	1137.9	1137.4	1137.0
155°	1175.1	1176.3	1177.3	1178.5	1179.6	1179.8	1178.8	1177.9	1177.1	1176.1	1175.9
157.5°	1207.6	1209.2	1210.7	1212.2	1213.7	1214.0	1213.1	1212.1	1211.2	1210.3	1210.1
160°	1230.0	1231.1	1232.3	1233.4	1234.6	1234.7	1233.8	1232.9	1231.9	1231.0	1230.8
162.5°	1249.0	1250.4	1251.7	1253.0	1254.4	1254.5	1253.4	1252.3	1251.2	1250.1	1250.0
165°	1274.5	1275.9	1277.3	1278.7	1280.1	1280.3	1279.3	1278.4	1277.6	1276.6	1276.4
167.5°	1294.9	1296.3	1297.7	1299.1	1300.6	1300.6	1299.2	1297.8	1296.5	1295.0	1295.0
170°	1305.6	1307.2	1308.9	1310.5	1312.1	1312.2	1310.8	1309.4	1308.1	1306.6	1306.6
172.5°	1314.7	1316.2	1317.6	1319.0	1320.4	1320.4	1319.1	1317.7	1316.3	1314.9	1314.9
175°	1323.2	1324.8	1326.5	1328.1	1329.7	1329.8	1328.4	1327.0	1325.6	1324.3	1324.3
177.5°	1328.2	1329.5	1330.8	1332.1	1333.4	1333.5	1332.4	1331.2	1330.2	1329.0	1329.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1506.5	1503.2	1496.9	1491.1	1483.9	1477.7	1473.4	1468.0	1461.3	1453.1	1446.4
5°	1573.2	1560.0	1542.6	1527.5	1508.2	1493.2	1477.6	1462.5	1447.4	1428.2	1411.3
7.5°	1647.2	1619.8	1593.2	1559.8	1529.5	1502.4	1476.3	1450.0	1424.2	1396.9	1370.6
10°	1692.4	1659.3	1622.6	1580.5	1541.9	1505.2	1471.5	1438.4	1403.6	1372.8	1339.7
12.5°	1734.8	1692.0	1650.0	1596.9	1550.6	1505.7	1462.9	1421.6	1384.3	1344.4	1308.9
15°	1773.1	1730.9	1684.0	1619.0	1554.6	1500.4	1449.8	1396.3	1350.0	1305.4	1265.7
17.5°	1787.9	1743.7	1689.2	1626.7	1556.3	1488.2	1423.0	1364.3	1309.7	1257.8	1213.2
20°	1782.1	1739.4	1683.4	1623.8	1548.5	1477.6	1407.1	1342.1	1281.4	1226.5	1179.0
22.5°	1768.1	1723.9	1669.9	1607.0	1535.5	1460.2	1385.0	1315.6	1252.0	1195.2	1143.4
25°	1747.2	1687.0	1631.7	1570.2	1502.3	1427.6	1350.0	1273.5	1205.5	1147.7	1091.2
27.5°	1725.4	1650.3	1579.8	1518.9	1447.0	1380.4	1305.6	1227.2	1155.7	1096.8	1038.8
30°	1705.7	1621.4	1543.7	1474.5	1406.5	1343.4	1272.3	1195.9	1122.5	1061.7	1002.7
32.5°	1681.1	1591.5	1506.2	1426.4	1360.8	1298.1	1233.8	1160.7	1089.2	1026.5	966.6
35°	1650.3	1536.0	1443.2	1358.3	1285.6	1224.8	1167.0	1108.0	1036.4	971.4	913.0
37.5°	1609.8	1480.1	1372.8	1280.4	1203.5	1142.5	1096.9	1043.0	977.7	915.4	861.2
40°	1585.3	1439.7	1322.2	1230.8	1150.1	1085.7	1043.0	997.3	937.7	879.3	825.1
42.5°	1552.6	1402.6	1271.2	1175.9	1094.8	1032.8	989.5	949.6	899.6	844.6	786.6
45°	1488.4	1330.7	1192.8	1090.6	1008.7	947.9	907.6	872.1	834.2	783.6	733.1
47.5°	1404.8	1255.7	1111.5	999.8	919.6	863.2	824.0	796.0	768.9	725.9	676.8
50°	1337.9	1194.1	1053.2	944.9	859.4	805.8	769.2	746.9	722.2	683.1	642.2
52.5°	1258.9	1130.5	992.6	881.8	801.2	751.0	715.7	693.5	673.2	641.2	602.2
55°	1134.5	1022.0	895.5	795.0	721.0	670.5	636.8	615.7	603.7	576.6	545.9
57.5°	990.9	910.3	798.8	701.9	636.4	586.5	561.8	543.9	530.2	511.1	489.5
60°	890.7	834.2	734.2	642.2	582.0	534.4	512.2	497.1	484.5	468.2	451.4
62.5°	789.2	748.0	661.1	582.0	526.6	486.8	465.9	452.4	437.8	426.9	410.5
65°	653.0	616.3	556.1	494.1	443.0	411.1	396.0	384.0	375.0	362.9	351.5
67.5°	508.0	493.0	451.5	408.8	372.0	343.7	330.6	322.3	311.4	304.2	296.3
70°	418.9	411.7	382.2	353.9	319.6	300.3	288.3	284.6	271.4	264.2	258.8
72.5°	339.9	336.5	319.6	300.0	275.8	259.0	247.8	243.8	235.3	229.5	226.0
75°	232.9	234.2	231.1	218.5	209.5	198.6	189.0	186.5	180.6	175.8	172.7
77.5°	147.3	153.5	153.7	153.1	149.5	142.9	138.9	137.1	131.2	129.4	128.7
80°	101.1	107.7	113.8	113.2	111.9	110.1	107.1	105.3	102.3	100.5	99.3
82.5°	67.4	73.6	78.6	81.9	81.6	79.8	77.8	77.0	76.3	75.0	74.7
85°	31.9	33.1	34.9	39.1	42.1	42.7	42.1	41.6	39.7	40.3	40.9
87.5°	13.7	13.5	13.6	13.2	12.4	14.4	15.5	15.6	15.0	14.4	13.8
90°	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1	2.9	4.7	6.6
92.5°	35.8	33.9	31.8	30.2	29.0	27.6	26.4	25.1	26.4	27.6	29.0
95°	75.2	72.9	70.5	69.2	68.8	68.3	67.8	67.3	67.8	68.3	68.8
97.5°	120.6	117.5	114.3	112.6	112.4	112.3	112.1	111.9	112.1	112.3	112.4
100°	152.6	149.5	146.6	145.1	145.1	145.1	145.1	145.1	145.1	145.1	145.1
102.5°	188.7	187.2	185.7	184.4	183.5	182.5	181.6	180.7	181.6	182.5	183.5
105°	244.9	243.5	242.1	240.9	239.7	238.5	237.4	236.2	237.4	238.5	239.7
107.5°	305.4	304.3	303.3	302.2	301.0	299.9	298.7	297.6	298.7	299.9	301.0
110°	346.8	346.1	345.4	344.5	343.3	342.1	341.0	339.9	341.0	342.1	343.3



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	387.9	387.0	386.1	385.4	384.8	384.1	383.6	383.0	383.6	384.1	384.8
115°	451.9	451.5	450.9	450.3	449.3	448.4	447.5	446.6	447.5	448.4	449.3
117.5°	513.4	512.9	512.5	512.1	511.7	511.3	510.9	510.4	510.9	511.3	511.7
120°	556.0	555.7	555.5	554.8	553.7	552.5	551.3	550.2	551.3	552.5	553.7
122.5°	596.7	596.1	595.5	594.9	594.6	594.1	593.8	593.3	593.8	594.1	594.6
125°	658.5	658.4	658.1	657.3	655.9	654.5	653.2	651.8	653.2	654.5	655.9
127.5°	718.2	717.9	717.6	717.1	716.3	715.5	714.7	714.0	714.7	715.5	716.3
130°	757.6	757.2	756.7	755.8	754.7	753.6	752.4	751.3	752.4	753.6	754.7
132.5°	796.8	796.9	797.0	796.1	794.2	792.4	790.4	788.5	790.4	792.4	794.2
135°	854.4	854.2	854.0	853.2	851.8	850.4	849.0	847.7	849.0	850.4	851.8
137.5°	910.4	909.9	909.5	908.5	907.1	905.8	904.5	903.1	904.5	905.8	907.1
140°	945.7	945.0	944.3	943.4	942.3	941.1	940.0	938.8	940.0	941.1	942.3
142.5°	981.0	980.1	979.3	978.3	977.3	976.4	975.4	974.5	975.4	976.4	977.3
145°	1032.8	1032.1	1031.4	1030.6	1029.7	1028.8	1027.8	1026.9	1027.8	1028.8	1029.7
147.5°	1079.1	1078.5	1077.9	1077.4	1076.9	1076.4	1075.8	1075.4	1075.8	1076.4	1076.9
150°	1108.9	1108.0	1107.1	1106.8	1107.1	1107.2	1107.5	1107.7	1107.5	1107.2	1107.1
152.5°	1136.6	1136.2	1135.9	1135.5	1135.2	1134.9	1134.5	1134.3	1134.5	1134.9	1135.2
155°	1175.6	1175.5	1175.2	1175.1	1175.1	1175.1	1175.1	1175.1	1175.1	1175.1	1175.1
157.5°	1209.9	1209.6	1209.3	1209.5	1210.1	1210.5	1211.0	1211.6	1211.0	1210.5	1210.1
160°	1230.6	1230.3	1230.1	1230.3	1231.0	1231.7	1232.4	1233.1	1232.4	1231.7	1231.0
162.5°	1250.0	1249.9	1249.9	1250.1	1250.6	1251.2	1251.7	1252.1	1251.7	1251.2	1250.6
165°	1276.1	1275.9	1275.7	1275.8	1276.3	1276.8	1277.2	1277.6	1277.2	1276.8	1276.3
167.5°	1295.0	1295.0	1295.0	1295.5	1296.5	1297.4	1298.2	1299.2	1298.2	1297.4	1296.5
170°	1306.6	1306.6	1306.6	1307.2	1308.1	1308.9	1309.9	1310.8	1309.9	1308.9	1308.1
172.5°	1314.9	1314.9	1314.9	1315.5	1316.3	1317.2	1318.2	1319.1	1318.2	1317.2	1316.3
175°	1324.3	1324.3	1324.3	1324.7	1325.6	1326.6	1327.5	1328.4	1327.5	1326.6	1325.6
177.5°	1329.5	1329.6	1329.8	1330.3	1331.0	1331.7	1332.5	1333.2	1332.5	1331.7	1331.0
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1441.5	1434.9	1430.0	1420.4	1413.6	1410.8	1405.4	1404.0	1409.3	1405.4	1405.0
5°	1398.7	1381.3	1367.4	1353.5	1338.5	1328.9	1314.5	1312.1	1308.4	1303.0	1301.8
7.5°	1347.3	1324.5	1306.7	1283.9	1264.0	1248.0	1229.9	1221.4	1216.7	1209.7	1200.3
10°	1312.6	1285.6	1261.5	1238.6	1214.0	1194.1	1176.0	1162.2	1153.2	1144.7	1141.1
12.5°	1278.4	1250.9	1220.0	1192.4	1164.8	1142.5	1122.6	1113.6	1103.6	1093.7	1085.3
15°	1225.4	1188.7	1154.9	1123.0	1099.6	1075.5	1056.2	1043.0	1028.0	1023.8	1007.5
17.5°	1169.0	1133.0	1093.6	1060.0	1032.8	1006.3	985.1	970.1	958.8	943.3	935.8
20°	1133.9	1091.2	1052.7	1022.0	991.8	960.6	938.9	926.2	915.4	902.8	896.8
22.5°	1096.4	1054.5	1015.1	979.1	948.5	917.7	902.3	889.2	876.9	865.2	857.3
25°	1041.2	999.1	957.5	920.2	888.3	866.0	848.0	832.9	826.3	814.9	806.5
27.5°	986.7	941.9	898.8	861.6	836.6	814.6	799.8	787.8	775.9	765.9	758.6
30°	951.5	905.8	858.8	829.4	802.9	781.8	765.5	754.1	745.1	736.1	730.7
32.5°	916.4	869.2	827.5	795.7	770.6	752.4	735.7	724.8	715.2	705.3	698.8
35°	860.1	811.9	778.2	746.9	722.2	705.3	693.9	678.3	670.5	663.3	656.7
37.5°	807.7	762.9	726.5	699.0	677.5	660.8	646.0	637.6	627.9	621.4	615.9
40°	769.2	728.3	695.2	666.3	650.6	632.0	618.1	607.3	600.0	591.7	585.6
42.5°	734.5	696.4	664.3	638.3	618.8	603.1	589.7	578.9	569.7	563.7	558.7
45°	685.5	647.6	616.3	592.2	574.2	559.1	545.3	539.8	527.8	520.6	518.2
47.5°	634.8	600.9	570.7	548.5	530.0	515.8	502.7	491.7	485.1	478.0	474.1
50°	600.7	568.1	539.8	518.2	500.2	484.5	472.4	465.2	456.2	449.6	444.8
52.5°	566.5	536.4	508.1	487.4	471.7	456.1	442.6	435.4	426.9	422.6	419.3
55°	517.6	485.7	461.6	441.1	424.9	410.5	397.8	390.6	385.2	380.9	379.8
57.5°	462.3	436.9	414.6	396.1	379.2	365.7	354.6	347.8	343.0	342.3	338.8
60°	426.1	403.2	382.8	362.9	348.5	335.8	326.2	318.3	313.5	313.0	311.7
62.5°	390.0	368.1	349.1	331.6	318.6	306.5	297.3	288.6	285.6	282.7	280.0
65°	336.4	316.6	301.0	287.0	273.2	263.0	254.0	248.6	241.9	238.4	231.8
67.5°	283.8	268.4	253.4	241.7	230.9	221.1	213.7	205.6	201.2	198.2	193.4
70°	249.1	237.1	222.1	209.5	201.0	193.2	187.2	178.2	175.1	172.7	170.3
72.5°	216.4	205.8	193.2	183.0	174.5	167.2	160.2	156.0	153.0	150.6	149.2
75°	170.3	160.1	149.3	142.0	136.0	130.0	126.4	123.4	122.2	121.5	119.1
77.5°	125.1	119.7	111.0	105.2	101.2	98.8	95.6	94.0	93.9	91.2	90.4
80°	95.7	92.6	85.4	83.0	80.1	77.7	75.8	72.9	69.8	68.6	66.8
82.5°	71.2	68.1	65.3	61.3	58.9	57.4	55.6	54.5	54.9	53.2	52.3
85°	37.9	34.9	33.7	33.1	31.9	33.1	32.5	31.9	31.3	30.7	31.3
87.5°	13.7	14.1	13.9	15.2	14.1	14.9	15.1	14.9	15.1	15.3	15.0
90°	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9	20.1	21.2	22.1
92.5°	30.2	31.8	33.9	35.8	37.8	39.8	41.3	42.8	44.3	45.8	46.9
95°	69.2	70.5	72.9	75.2	77.5	79.8	81.4	83.0	84.6	86.2	87.3
97.5°	112.6	114.3	117.5	120.6	123.9	127.1	128.6	130.1	131.6	133.1	134.0
100°	145.1	146.6	149.5	152.6	155.5	158.5	160.6	162.6	164.8	166.8	168.1
102.5°	184.4	185.7	187.2	188.7	190.2	191.7	193.9	196.2	198.5	200.7	202.2
105°	240.9	242.1	243.5	244.9	246.3	247.6	249.1	250.4	251.8	253.2	254.2
107.5°	302.2	303.3	304.3	305.4	306.5	307.6	308.3	308.9	309.6	310.3	310.7
110°	344.5	345.4	346.1	346.8	347.5	348.1	348.8	349.6	350.3	350.9	351.2



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	385.4	386.1	387.0	387.9	388.7	389.6	389.9	390.3	390.6	390.9	390.8
115°	450.3	450.9	451.5	451.9	452.4	452.8	452.6	452.4	452.1	451.9	451.7
117.5°	512.1	512.5	512.9	513.4	513.7	514.2	514.3	514.5	514.7	514.9	514.5
120°	554.8	555.5	555.7	556.0	556.2	556.4	556.4	556.4	556.4	556.4	556.0
122.5°	594.9	595.5	596.1	596.7	597.3	597.9	597.7	597.5	597.4	597.2	596.7
125°	657.3	658.1	658.4	658.5	658.8	659.1	658.5	658.1	657.6	657.2	656.8
127.5°	717.1	717.6	717.9	718.2	718.5	718.7	718.5	718.3	718.0	717.8	717.5
130°	755.8	756.7	757.2	757.6	758.0	758.5	758.3	758.0	757.8	757.6	757.2
132.5°	796.1	797.0	796.9	796.8	796.7	796.7	796.4	796.2	795.9	795.7	795.3
135°	853.2	854.0	854.2	854.4	854.6	854.9	854.9	854.9	854.9	854.9	854.4
137.5°	908.5	909.5	909.9	910.4	911.0	911.4	911.7	912.0	912.3	912.6	912.1
140°	943.4	944.3	945.0	945.7	946.4	947.1	947.5	948.0	948.5	949.0	948.6
142.5°	978.3	979.3	980.1	981.0	981.9	982.8	983.0	983.3	983.6	983.8	983.4
145°	1030.6	1031.4	1032.1	1032.8	1033.4	1034.1	1034.1	1034.1	1034.1	1034.1	1033.8
147.5°	1077.4	1077.9	1078.5	1079.1	1079.6	1080.1	1080.7	1081.3	1081.8	1082.4	1081.8
150°	1106.8	1107.1	1108.0	1108.9	1109.9	1110.8	1110.8	1110.8	1110.8	1110.8	1110.6
152.5°	1135.5	1135.9	1136.2	1136.6	1137.0	1137.4	1137.9	1138.4	1139.0	1139.5	1139.4
155°	1175.1	1175.2	1175.5	1175.6	1175.9	1176.1	1177.1	1177.9	1178.8	1179.8	1179.6
157.5°	1209.5	1209.3	1209.6	1209.9	1210.1	1210.3	1211.2	1212.1	1213.1	1214.0	1213.7
160°	1230.3	1230.1	1230.3	1230.6	1230.8	1231.0	1231.9	1232.9	1233.8	1234.7	1234.6
162.5°	1250.1	1249.9	1249.9	1250.0	1250.0	1250.1	1251.2	1252.3	1253.4	1254.5	1254.4
165°	1275.8	1275.7	1275.9	1276.1	1276.4	1276.6	1277.6	1278.4	1279.3	1280.3	1280.1
167.5°	1295.5	1295.0	1295.0	1295.0	1295.0	1295.0	1296.5	1297.8	1299.2	1300.6	1300.6
170°	1307.2	1306.6	1306.6	1306.6	1306.6	1306.6	1308.1	1309.4	1310.8	1312.2	1312.1
172.5°	1315.5	1314.9	1314.9	1314.9	1314.9	1314.9	1316.3	1317.7	1319.1	1320.4	1320.4
175°	1324.7	1324.3	1324.3	1324.3	1324.3	1324.3	1325.6	1327.0	1328.4	1329.8	1329.7
177.5°	1330.3	1329.8	1329.6	1329.5	1329.2	1329.0	1330.2	1331.2	1332.4	1333.5	1333.4
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1404.4	1399.2	1397.8	1399.6	1397.8	1399.2	1404.4	1405.0	1405.4	1409.3	1404.0
5°	1295.8	1289.8	1292.8	1291.6	1292.8	1289.8	1295.8	1301.8	1303.0	1308.4	1312.1
7.5°	1200.2	1192.8	1184.8	1187.3	1184.8	1192.8	1200.2	1200.3	1209.7	1216.7	1221.4
10°	1133.3	1127.3	1123.6	1126.7	1123.6	1127.3	1133.3	1141.1	1144.7	1153.2	1162.2
12.5°	1076.9	1073.4	1070.2	1068.9	1070.2	1073.4	1076.9	1085.3	1093.7	1103.6	1113.6
15°	1000.3	993.1	990.1	982.2	990.1	993.1	1000.3	1007.5	1023.8	1028.0	1043.0
17.5°	929.6	927.2	919.4	916.1	919.4	927.2	929.6	935.8	943.3	958.8	970.1
20°	887.7	885.3	877.5	882.3	877.5	885.3	887.7	896.8	902.8	915.4	926.2
22.5°	853.1	847.7	845.3	843.8	845.3	847.7	853.1	857.3	865.2	876.9	889.2
25°	804.1	796.2	793.3	789.6	793.3	796.2	804.1	806.5	814.9	826.3	832.9
27.5°	755.2	751.0	747.0	746.1	747.0	751.0	755.2	758.6	765.9	775.9	787.8
30°	723.4	719.3	716.2	716.2	716.2	719.3	723.4	730.7	736.1	745.1	754.1
32.5°	695.0	691.8	688.8	688.3	688.8	691.8	695.0	698.8	705.3	715.2	724.8
35°	653.6	648.8	647.6	644.0	647.6	648.8	653.6	656.7	663.3	670.5	678.3
37.5°	610.6	606.6	606.5	606.2	606.5	606.6	610.6	615.9	621.4	627.9	637.6
40°	583.2	580.1	579.6	575.3	579.6	580.1	583.2	585.6	591.7	600.0	607.3
42.5°	553.8	552.2	550.2	548.4	550.2	552.2	553.8	558.7	563.7	569.7	578.9
45°	514.0	509.8	509.8	506.8	509.8	509.8	514.0	518.2	520.6	527.8	539.8
47.5°	472.8	469.6	469.9	466.8	469.9	469.6	472.8	474.1	478.0	485.1	491.7
50°	445.4	443.5	443.0	441.8	443.0	443.5	445.4	444.8	449.6	456.2	465.2
52.5°	417.9	417.1	419.4	416.7	419.4	417.1	417.9	419.3	422.6	426.9	435.4
55°	380.9	379.2	382.8	379.2	382.8	379.2	380.9	379.8	380.9	385.2	390.6
57.5°	338.5	336.8	340.0	338.2	340.0	336.8	338.5	338.8	342.3	343.0	347.8
60°	310.6	306.9	308.7	309.3	308.7	306.9	310.6	311.7	313.0	313.5	318.3
62.5°	277.3	275.2	276.5	273.8	276.5	275.2	277.3	280.0	282.7	285.6	288.6
65°	230.5	228.7	226.3	225.1	226.3	228.7	230.5	231.8	238.4	241.9	248.6
67.5°	193.7	189.3	189.2	190.2	189.2	189.3	193.7	193.4	198.2	201.2	205.6
70°	166.7	166.7	166.1	166.1	166.1	166.7	166.7	170.3	172.7	175.1	178.2
72.5°	147.9	147.5	146.3	145.9	146.3	147.5	147.9	149.2	150.6	153.0	156.0
75°	119.1	119.8	118.6	118.0	118.6	119.8	119.1	119.1	121.5	122.2	123.4
77.5°	88.0	85.4	86.8	85.4	86.8	85.4	88.0	90.4	91.2	93.9	94.0
80°	66.8	66.2	68.0	66.2	68.0	66.2	66.8	66.8	68.6	69.8	72.9
82.5°	52.9	52.3	53.1	51.7	53.1	52.3	52.9	52.3	53.2	54.9	54.5
85°	31.9	31.3	30.7	31.3	30.7	31.3	31.9	31.3	30.7	31.3	31.9
87.5°	15.6	15.2	15.4	15.6	15.4	15.2	15.6	15.0	15.3	15.1	14.9
90°	22.8	23.5	24.2	24.9	24.2	23.5	22.8	22.1	21.2	20.1	18.9
92.5°	47.3	47.9	48.4	48.9	48.4	47.9	47.3	46.9	45.8	44.3	42.8
95°	87.7	88.2	88.6	89.1	88.6	88.2	87.7	87.3	86.2	84.6	83.0
97.5°	134.3	134.6	134.8	135.1	134.8	134.6	134.3	134.0	133.1	131.6	130.1
100°	168.5	169.0	169.5	170.0	169.5	169.0	168.5	168.1	166.8	164.8	162.6
102.5°	202.9	203.5	204.1	204.7	204.1	203.5	202.9	202.2	200.7	198.5	196.2
105°	254.9	255.6	256.3	257.0	256.3	255.6	254.9	254.2	253.2	251.8	250.4
107.5°	310.6	310.6	310.5	310.4	310.5	310.6	310.6	310.7	310.3	309.6	308.9
110°	350.9	350.7	350.4	350.3	350.4	350.7	350.9	351.2	350.9	350.3	349.6



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	390.5	390.0	389.6	389.2	389.6	390.0	390.5	390.8	390.9	390.6	390.3
115°	451.5	451.2	450.9	450.8	450.9	451.2	451.5	451.7	451.9	452.1	452.4
117.5°	513.6	512.7	511.8	510.9	511.8	512.7	513.6	514.5	514.9	514.7	514.5
120°	555.1	554.1	553.2	552.3	553.2	554.1	555.1	556.0	556.4	556.4	556.4
122.5°	595.9	595.2	594.5	593.8	594.5	595.2	595.9	596.7	597.2	597.4	597.5
125°	656.7	656.4	656.1	655.9	656.1	656.4	656.7	656.8	657.2	657.6	658.1
127.5°	717.0	716.5	716.0	715.6	716.0	716.5	717.0	717.5	717.8	718.0	718.3
130°	756.8	756.3	755.8	755.4	755.8	756.3	756.8	757.2	757.6	757.8	758.0
132.5°	794.6	794.0	793.4	792.7	793.4	794.0	794.6	795.3	795.7	795.9	796.2
135°	853.5	852.6	851.7	850.7	851.7	852.6	853.5	854.4	854.9	854.9	854.9
137.5°	911.0	909.8	908.7	907.5	908.7	909.8	911.0	912.1	912.6	912.3	912.0
140°	947.4	946.3	945.1	944.0	945.1	946.3	947.4	948.6	949.0	948.5	948.0
142.5°	982.2	981.1	980.0	978.8	980.0	981.1	982.2	983.4	983.8	983.6	983.3
145°	1033.1	1032.4	1031.7	1031.0	1031.7	1032.4	1033.1	1033.8	1034.1	1034.1	1034.1
147.5°	1080.3	1078.7	1077.2	1075.6	1077.2	1078.7	1080.3	1081.8	1082.4	1081.8	1081.3
150°	1110.1	1109.6	1109.2	1108.8	1109.2	1109.6	1110.1	1110.6	1110.8	1110.8	1110.8
152.5°	1138.6	1137.7	1136.9	1136.1	1136.9	1137.7	1138.6	1139.4	1139.5	1139.0	1138.4
155°	1178.5	1177.3	1176.3	1175.1	1176.3	1177.3	1178.5	1179.6	1179.8	1178.8	1177.9
157.5°	1212.2	1210.7	1209.2	1207.6	1209.2	1210.7	1212.2	1213.7	1214.0	1213.1	1212.1
160°	1233.4	1232.3	1231.1	1230.0	1231.1	1232.3	1233.4	1234.6	1234.7	1233.8	1232.9
162.5°	1253.0	1251.7	1250.4	1249.0	1250.4	1251.7	1253.0	1254.4	1254.5	1253.4	1252.3
165°	1278.7	1277.3	1275.9	1274.5	1275.9	1277.3	1278.7	1280.1	1280.3	1279.3	1278.4
167.5°	1299.1	1297.7	1296.3	1294.9	1296.3	1297.7	1299.1	1300.6	1300.6	1299.2	1297.8
170°	1310.5	1308.9	1307.2	1305.6	1307.2	1308.9	1310.5	1312.1	1312.2	1310.8	1309.4
172.5°	1319.0	1317.6	1316.2	1314.7	1316.2	1317.6	1319.0	1320.4	1320.4	1319.1	1317.7
175°	1328.1	1326.5	1324.8	1323.2	1324.8	1326.5	1328.1	1329.7	1329.8	1328.4	1327.0
177.5°	1332.1	1330.8	1329.5	1328.2	1329.5	1330.8	1332.1	1333.4	1333.5	1332.4	1331.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1405.4	1410.8	1413.6	1420.4	1430.0	1434.9	1441.5	1446.4	1453.1	1461.3	1468.0
5°	1314.5	1328.9	1338.5	1353.5	1367.4	1381.3	1398.7	1411.3	1428.2	1447.4	1462.5
7.5°	1229.9	1248.0	1264.0	1283.9	1306.7	1324.5	1347.3	1370.6	1396.9	1424.2	1450.0
10°	1176.0	1194.1	1214.0	1238.6	1261.5	1285.6	1312.6	1339.7	1372.8	1403.6	1438.4
12.5°	1122.6	1142.5	1164.8	1192.4	1220.0	1250.9	1278.4	1308.9	1344.4	1384.3	1421.6
15°	1056.2	1075.5	1099.6	1123.0	1154.9	1188.7	1225.4	1265.7	1305.4	1350.0	1396.3
17.5°	985.1	1006.3	1032.8	1060.0	1093.6	1133.0	1169.0	1213.2	1257.8	1309.7	1364.3
20°	938.9	960.6	991.8	1022.0	1052.7	1091.2	1133.9	1179.0	1226.5	1281.4	1342.1
22.5°	902.3	917.7	948.5	979.1	1015.1	1054.5	1096.4	1143.4	1195.2	1252.0	1315.6
25°	848.0	866.0	888.3	920.2	957.5	999.1	1041.2	1091.2	1147.7	1205.5	1273.5
27.5°	799.8	814.6	836.6	861.6	898.8	941.9	986.7	1038.8	1096.8	1155.7	1227.2
30°	765.5	781.8	802.9	829.4	858.8	905.8	951.5	1002.7	1061.7	1122.5	1195.9
32.5°	735.7	752.4	770.6	795.7	827.5	869.2	916.4	966.6	1026.5	1089.2	1160.7
35°	693.9	705.3	722.2	746.9	778.2	811.9	860.1	913.0	971.4	1036.4	1108.0
37.5°	646.0	660.8	677.5	699.0	726.5	762.9	807.7	861.2	915.4	977.7	1043.0
40°	618.1	632.0	650.6	666.3	695.2	728.3	769.2	825.1	879.3	937.7	997.3
42.5°	589.7	603.1	618.8	638.3	664.3	696.4	734.5	786.6	844.6	899.6	949.6
45°	545.3	559.1	574.2	592.2	616.3	647.6	685.5	733.1	783.6	834.2	872.1
47.5°	502.7	515.8	530.0	548.5	570.7	600.9	634.8	676.8	725.9	768.9	796.0
50°	472.4	484.5	500.2	518.2	539.8	568.1	600.7	642.2	683.1	722.2	746.9
52.5°	442.6	456.1	471.7	487.4	508.1	536.4	566.5	602.2	641.2	673.2	693.5
55°	397.8	410.5	424.9	441.1	461.6	485.7	517.6	545.9	576.6	603.7	615.7
57.5°	354.6	365.7	379.2	396.1	414.6	436.9	462.3	489.5	511.1	530.2	543.9
60°	326.2	335.8	348.5	362.9	382.8	403.2	426.1	451.4	468.2	484.5	497.1
62.5°	297.3	306.5	318.6	331.6	349.1	368.1	390.0	410.5	426.9	437.8	452.4
65°	254.0	263.0	273.2	287.0	301.0	316.6	336.4	351.5	362.9	375.0	384.0
67.5°	213.7	221.1	230.9	241.7	253.4	268.4	283.8	296.3	304.2	311.4	322.3
70°	187.2	193.2	201.0	209.5	222.1	237.1	249.1	258.8	264.2	271.4	284.6
72.5°	160.2	167.2	174.5	183.0	193.2	205.8	216.4	226.0	229.5	235.3	243.8
75°	126.4	130.0	136.0	142.0	149.3	160.1	170.3	172.7	175.8	180.6	186.5
77.5°	95.6	98.8	101.2	105.2	111.0	119.7	125.1	128.7	129.4	131.2	137.1
80°	75.8	77.7	80.1	83.0	85.4	92.6	95.7	99.3	100.5	102.3	105.3
82.5°	55.6	57.4	58.9	61.3	65.3	68.1	71.2	74.7	75.0	76.3	77.0
85°	32.5	33.1	31.9	33.1	33.7	34.9	37.9	40.9	40.3	39.7	41.6
87.5°	15.1	14.9	14.1	15.2	13.9	14.1	13.7	13.8	14.4	15.0	15.6
90°	17.7	16.6	15.0	13.4	11.8	10.2	8.4	6.6	4.7	2.9	1.1
92.5°	41.3	39.8	37.8	35.8	33.9	31.8	30.2	29.0	27.6	26.4	25.1
95°	81.4	79.8	77.5	75.2	72.9	70.5	69.2	68.8	68.3	67.8	67.3
97.5°	128.6	127.1	123.9	120.6	117.5	114.3	112.6	112.4	112.3	112.1	111.9
100°	160.6	158.5	155.5	152.6	149.5	146.6	145.1	145.1	145.1	145.1	145.1
102.5°	193.9	191.7	190.2	188.7	187.2	185.7	184.4	183.5	182.5	181.6	180.7
105°	249.1	247.6	246.3	244.9	243.5	242.1	240.9	239.7	238.5	237.4	236.2
107.5°	308.3	307.6	306.5	305.4	304.3	303.3	302.2	301.0	299.9	298.7	297.6
110°	348.8	348.1	347.5	346.8	346.1	345.4	344.5	343.3	342.1	341.0	339.9



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	389.9	389.6	388.7	387.9	387.0	386.1	385.4	384.8	384.1	383.6	383.0
115°	452.6	452.8	452.4	451.9	451.5	450.9	450.3	449.3	448.4	447.5	446.6
117.5°	514.3	514.2	513.7	513.4	512.9	512.5	512.1	511.7	511.3	510.9	510.4
120°	556.4	556.4	556.2	556.0	555.7	555.5	554.8	553.7	552.5	551.3	550.2
122.5°	597.7	597.9	597.3	596.7	596.1	595.5	594.9	594.6	594.1	593.8	593.3
125°	658.5	659.1	658.8	658.5	658.4	658.1	657.3	655.9	654.5	653.2	651.8
127.5°	718.5	718.7	718.5	718.2	717.9	717.6	717.1	716.3	715.5	714.7	714.0
130°	758.3	758.5	758.0	757.6	757.2	756.7	755.8	754.7	753.6	752.4	751.3
132.5°	796.4	796.7	796.7	796.8	796.9	797.0	796.1	794.2	792.4	790.4	788.5
135°	854.9	854.9	854.6	854.4	854.2	854.0	853.2	851.8	850.4	849.0	847.7
137.5°	911.7	911.4	911.0	910.4	909.9	909.5	908.5	907.1	905.8	904.5	903.1
140°	947.5	947.1	946.4	945.7	945.0	944.3	943.4	942.3	941.1	940.0	938.8
142.5°	983.0	982.8	981.9	981.0	980.1	979.3	978.3	977.3	976.4	975.4	974.5
145°	1034.1	1034.1	1033.4	1032.8	1032.1	1031.4	1030.6	1029.7	1028.8	1027.8	1026.9
147.5°	1080.7	1080.1	1079.6	1079.1	1078.5	1077.9	1077.4	1076.9	1076.4	1075.8	1075.4
150°	1110.8	1110.8	1109.9	1108.9	1108.0	1107.1	1106.8	1107.1	1107.2	1107.5	1107.7
152.5°	1137.9	1137.4	1137.0	1136.6	1136.2	1135.9	1135.5	1135.2	1134.9	1134.5	1134.3
155°	1177.1	1176.1	1175.9	1175.6	1175.5	1175.2	1175.1	1175.1	1175.1	1175.1	1175.1
157.5°	1211.2	1210.3	1210.1	1209.9	1209.6	1209.3	1209.5	1210.1	1210.5	1211.0	1211.6
160°	1231.9	1231.0	1230.8	1230.6	1230.3	1230.1	1230.3	1231.0	1231.7	1232.4	1233.1
162.5°	1251.2	1250.1	1250.0	1250.0	1249.9	1249.9	1250.1	1250.6	1251.2	1251.7	1252.1
165°	1277.6	1276.6	1276.4	1276.1	1275.9	1275.7	1275.8	1276.3	1276.8	1277.2	1277.6
167.5°	1296.5	1295.0	1295.0	1295.0	1295.0	1295.0	1295.5	1296.5	1297.4	1298.2	1299.2
170°	1308.1	1306.6	1306.6	1306.6	1306.6	1306.6	1307.2	1308.1	1308.9	1309.9	1310.8
172.5°	1316.3	1314.9	1314.9	1314.9	1314.9	1314.9	1315.5	1316.3	1317.2	1318.2	1319.1
175°	1325.6	1324.3	1324.3	1324.3	1324.3	1324.3	1324.7	1325.6	1326.6	1327.5	1328.4
177.5°	1330.2	1329.0	1329.2	1329.5	1329.6	1329.8	1330.3	1331.0	1331.7	1332.5	1333.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1473.4	1477.7	1483.9	1491.1	1496.9	1503.2	1506.5	1506.5	1509.5	1515.7	1523.9
5°	1477.6	1493.2	1508.2	1527.5	1542.6	1560.0	1573.2	1585.9	1597.3	1611.8	1626.8
7.5°	1476.3	1502.4	1529.5	1559.8	1593.2	1619.8	1647.2	1668.6	1689.8	1717.4	1739.2
10°	1471.5	1505.2	1541.9	1580.5	1622.6	1659.3	1692.4	1722.5	1751.4	1781.5	1808.6
12.5°	1462.9	1505.7	1550.6	1596.9	1650.0	1692.0	1734.8	1766.8	1800.5	1833.4	1866.8
15°	1449.8	1500.4	1554.6	1619.0	1684.0	1730.9	1773.1	1814.6	1845.8	1883.2	1915.1
17.5°	1423.0	1488.2	1556.3	1626.7	1689.2	1743.7	1787.9	1827.4	1860.7	1901.8	1945.1
20°	1407.1	1477.6	1548.5	1623.8	1683.4	1739.4	1782.1	1823.0	1864.6	1918.1	1971.0
22.5°	1385.0	1460.2	1535.5	1607.0	1669.9	1723.9	1768.1	1818.2	1872.7	1933.5	1997.5
25°	1350.0	1427.6	1502.3	1570.2	1631.7	1687.0	1747.2	1814.6	1880.8	1960.9	2052.9
27.5°	1305.6	1380.4	1447.0	1518.9	1579.8	1650.3	1725.4	1798.5	1893.9	2004.0	2119.0
30°	1272.3	1343.4	1406.5	1474.5	1543.7	1621.4	1705.7	1791.7	1905.5	2034.9	2171.5
32.5°	1233.8	1298.1	1360.8	1426.4	1506.2	1591.5	1681.1	1786.5	1922.4	2069.6	2211.0
35°	1167.0	1224.8	1285.6	1358.3	1443.2	1536.0	1650.3	1778.5	1942.8	2101.0	2228.0
37.5°	1096.9	1142.5	1203.5	1280.4	1372.8	1480.1	1609.8	1765.6	1934.4	2076.3	2130.5
40°	1043.0	1085.7	1150.1	1230.8	1322.2	1439.7	1585.3	1745.3	1915.1	2013.8	2009.6
42.5°	989.5	1032.8	1094.8	1175.9	1271.2	1402.6	1552.6	1718.9	1862.2	1899.7	1821.3
45°	907.6	947.9	1008.7	1090.6	1192.8	1330.7	1488.4	1647.9	1739.4	1678.6	1523.3
47.5°	824.0	863.2	919.6	999.8	1111.5	1255.7	1404.8	1535.7	1548.5	1418.0	1231.7
50°	769.2	805.8	859.4	944.9	1053.2	1194.1	1337.9	1440.8	1408.9	1249.5	1057.5
52.5°	715.7	751.0	801.2	881.8	992.6	1130.5	1258.9	1339.7	1266.0	1096.4	923.6
55°	636.8	670.5	721.0	795.0	895.5	1022.0	1134.5	1164.0	1055.6	884.8	745.1
57.5°	561.8	586.5	636.4	701.9	798.8	910.3	990.9	985.6	866.0	712.1	612.0
60°	512.2	534.4	582.0	642.2	734.2	834.2	890.7	866.7	745.7	618.7	522.4
62.5°	465.9	486.8	526.6	582.0	661.1	748.0	789.2	755.9	641.7	530.1	453.5
65°	396.0	411.1	443.0	494.1	556.1	616.3	653.0	604.2	503.2	418.9	361.1
67.5°	330.6	343.7	372.0	408.8	451.5	493.0	508.0	462.3	383.6	326.8	286.1
70°	288.3	300.3	319.6	353.9	382.2	411.7	418.9	378.0	312.4	269.0	243.8
72.5°	247.8	259.0	275.8	300.0	319.6	336.5	339.9	301.9	251.7	221.9	202.3
75°	189.0	198.6	209.5	218.5	231.1	234.2	232.9	203.4	176.4	156.5	145.6
77.5°	138.9	142.9	149.5	153.1	153.7	153.5	147.3	128.7	114.7	106.6	102.1
80°	107.1	110.1	111.9	113.2	113.8	107.7	101.1	89.7	84.9	80.1	74.6
82.5°	77.8	79.8	81.6	81.9	78.6	73.6	67.4	61.7	58.4	56.0	53.9
85°	42.1	42.7	42.1	39.1	34.9	33.1	31.9	30.7	30.1	29.5	29.5
87.5°	15.5	14.4	12.4	13.2	13.6	13.5	13.7	13.6	13.5	13.6	13.9
90°	2.9	4.7	6.6	8.4	10.2	11.8	13.4	15.0	16.6	17.7	18.9
92.5°	26.4	27.6	29.0	30.2	31.8	33.9	35.8	37.8	39.8	41.3	42.8
95°	67.8	68.3	68.8	69.2	70.5	72.9	75.2	77.5	79.8	81.4	83.0
97.5°	112.1	112.3	112.4	112.6	114.3	117.5	120.6	123.9	127.1	128.6	130.1
100°	145.1	145.1	145.1	145.1	146.6	149.5	152.6	155.5	158.5	160.6	162.6
102.5°	181.6	182.5	183.5	184.4	185.7	187.2	188.7	190.2	191.7	193.9	196.2
105°	237.4	238.5	239.7	240.9	242.1	243.5	244.9	246.3	247.6	249.1	250.4
107.5°	298.7	299.9	301.0	302.2	303.3	304.3	305.4	306.5	307.6	308.3	308.9
110°	341.0	342.1	343.3	344.5	345.4	346.1	346.8	347.5	348.1	348.8	349.6



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	383.6	384.1	384.8	385.4	386.1	387.0	387.9	388.7	389.6	389.9	390.3
115°	447.5	448.4	449.3	450.3	450.9	451.5	451.9	452.4	452.8	452.6	452.4
117.5°	510.9	511.3	511.7	512.1	512.5	512.9	513.4	513.7	514.2	514.3	514.5
120°	551.3	552.5	553.7	554.8	555.5	555.7	556.0	556.2	556.4	556.4	556.4
122.5°	593.8	594.1	594.6	594.9	595.5	596.1	596.7	597.3	597.9	597.7	597.5
125°	653.2	654.5	655.9	657.3	658.1	658.4	658.5	658.8	659.1	658.5	658.1
127.5°	714.7	715.5	716.3	717.1	717.6	717.9	718.2	718.5	718.7	718.5	718.3
130°	752.4	753.6	754.7	755.8	756.7	757.2	757.6	758.0	758.5	758.3	758.0
132.5°	790.4	792.4	794.2	796.1	797.0	796.9	796.8	796.7	796.7	796.4	796.2
135°	849.0	850.4	851.8	853.2	854.0	854.2	854.4	854.6	854.9	854.9	854.9
137.5°	904.5	905.8	907.1	908.5	909.5	909.9	910.4	911.0	911.4	911.7	912.0
140°	940.0	941.1	942.3	943.4	944.3	945.0	945.7	946.4	947.1	947.5	948.0
142.5°	975.4	976.4	977.3	978.3	979.3	980.1	981.0	981.9	982.8	983.0	983.3
145°	1027.8	1028.8	1029.7	1030.6	1031.4	1032.1	1032.8	1033.4	1034.1	1034.1	1034.1
147.5°	1075.8	1076.4	1076.9	1077.4	1077.9	1078.5	1079.1	1079.6	1080.1	1080.7	1081.3
150°	1107.5	1107.2	1107.1	1106.8	1107.1	1108.0	1108.9	1109.9	1110.8	1110.8	1110.8
152.5°	1134.5	1134.9	1135.2	1135.5	1135.9	1136.2	1136.6	1137.0	1137.4	1137.9	1138.4
155°	1175.1	1175.1	1175.1	1175.1	1175.2	1175.5	1175.6	1175.9	1176.1	1177.1	1177.9
157.5°	1211.0	1210.5	1210.1	1209.5	1209.3	1209.6	1209.9	1210.1	1210.3	1211.2	1212.1
160°	1232.4	1231.7	1231.0	1230.3	1230.1	1230.3	1230.6	1230.8	1231.0	1231.9	1232.9
162.5°	1251.7	1251.2	1250.6	1250.1	1249.9	1249.9	1250.0	1250.0	1250.1	1251.2	1252.3
165°	1277.2	1276.8	1276.3	1275.8	1275.7	1275.9	1276.1	1276.4	1276.6	1277.6	1278.4
167.5°	1298.2	1297.4	1296.5	1295.5	1295.0	1295.0	1295.0	1295.0	1295.0	1296.5	1297.8
170°	1309.9	1308.9	1308.1	1307.2	1306.6	1306.6	1306.6	1306.6	1306.6	1308.1	1309.4
172.5°	1318.2	1317.2	1316.3	1315.5	1314.9	1314.9	1314.9	1314.9	1314.9	1316.3	1317.7
175°	1327.5	1326.6	1325.6	1324.7	1324.3	1324.3	1324.3	1324.3	1324.3	1325.6	1327.0
177.5°	1332.5	1331.7	1331.0	1330.3	1329.8	1329.6	1329.5	1329.2	1329.0	1330.2	1331.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2	1466.2
2.5°	1530.2	1530.2	1538.4	1537.8	1543.2	1541.2	1542.2
5°	1644.8	1655.1	1664.1	1670.2	1679.2	1681.6	1680.3
7.5°	1763.8	1786.5	1797.6	1812.8	1815.5	1823.5	1822.7
10°	1837.5	1859.8	1876.6	1889.8	1896.4	1904.9	1905.5
12.5°	1895.2	1914.1	1929.0	1941.3	1949.4	1952.0	1953.6
15°	1940.4	1961.4	1978.9	1996.4	2006.6	2014.4	2018.7
17.5°	1985.8	2018.4	2049.2	2072.9	2087.1	2099.2	2099.0
20°	2021.1	2058.3	2096.9	2124.0	2151.6	2163.6	2165.4
22.5°	2058.6	2115.7	2165.3	2207.3	2243.5	2256.1	2260.8
25°	2136.5	2211.2	2287.7	2346.6	2388.7	2413.4	2417.1
27.5°	2230.8	2331.8	2412.3	2466.7	2501.7	2520.0	2523.9
30°	2297.3	2390.6	2462.8	2503.7	2520.0	2522.4	2513.4
32.5°	2327.1	2396.8	2425.7	2423.3	2391.4	2370.3	2362.1
35°	2290.6	2276.2	2205.8	2121.6	2057.2	2016.2	2005.4
37.5°	2084.6	1960.0	1830.5	1703.2	1635.4	1600.9	1541.7
40°	1881.4	1703.9	1569.1	1461.9	1385.5	1324.1	1309.7
42.5°	1652.3	1468.9	1334.1	1242.3	1181.3	1139.2	1120.9
45°	1327.7	1170.0	1058.6	988.3	941.3	910.6	896.8
47.5°	1061.9	939.9	858.7	806.6	770.9	744.1	736.6
50°	916.1	818.5	749.9	706.0	678.9	658.4	650.0
52.5°	795.7	716.9	664.2	627.9	602.4	589.6	582.6
55°	656.7	588.6	550.7	521.8	507.4	497.1	492.3
57.5°	537.0	487.9	460.2	440.2	426.9	420.4	417.9
60°	470.0	431.5	406.3	390.6	381.6	373.2	370.8
62.5°	410.8	380.5	361.0	347.2	338.2	334.7	333.1
65°	331.0	311.1	296.7	288.3	281.1	279.8	279.3
67.5°	263.1	251.5	243.9	235.1	232.6	228.4	227.5
70°	225.1	217.3	208.2	205.3	202.2	198.0	198.6
72.5°	190.9	183.1	176.9	173.0	171.9	170.0	171.7
75°	139.6	137.2	134.8	131.8	130.6	130.6	130.0
77.5°	99.7	97.6	95.0	93.2	92.8	90.2	91.2
80°	72.2	69.2	68.0	68.6	66.8	66.2	66.2
82.5°	53.4	52.3	51.2	51.3	50.9	50.3	50.8
85°	29.5	28.9	28.9	28.3	28.3	27.6	27.6
87.5°	14.6	15.3	14.5	14.2	14.4	15.0	15.6
90°	20.1	21.2	22.1	22.8	23.5	24.2	24.9
92.5°	44.3	45.8	46.9	47.3	47.9	48.4	48.9
95°	84.6	86.2	87.3	87.7	88.2	88.6	89.1
97.5°	131.6	133.1	134.0	134.3	134.6	134.8	135.1
100°	164.8	166.8	168.1	168.5	169.0	169.5	170.0
102.5°	198.5	200.7	202.2	202.9	203.5	204.1	204.7
105°	251.8	253.2	254.2	254.9	255.6	256.3	257.0
107.5°	309.6	310.3	310.7	310.6	310.6	310.5	310.4
110°	350.3	350.9	351.2	350.9	350.7	350.4	350.3



TEST NUMBER: P333605-940

CATALOG NUMBER: S125RDIP-S1090D1205U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	390.6	390.9	390.8	390.5	390.0	389.6	389.2
115°	452.1	451.9	451.7	451.5	451.2	450.9	450.8
117.5°	514.7	514.9	514.5	513.6	512.7	511.8	510.9
120°	556.4	556.4	556.0	555.1	554.1	553.2	552.3
122.5°	597.4	597.2	596.7	595.9	595.2	594.5	593.8
125°	657.6	657.2	656.8	656.7	656.4	656.1	655.9
127.5°	718.0	717.8	717.5	717.0	716.5	716.0	715.6
130°	757.8	757.6	757.2	756.8	756.3	755.8	755.4
132.5°	795.9	795.7	795.3	794.6	794.0	793.4	792.7
135°	854.9	854.9	854.4	853.5	852.6	851.7	850.7
137.5°	912.3	912.6	912.1	911.0	909.8	908.7	907.5
140°	948.5	949.0	948.6	947.4	946.3	945.1	944.0
142.5°	983.6	983.8	983.4	982.2	981.1	980.0	978.8
145°	1034.1	1034.1	1033.8	1033.1	1032.4	1031.7	1031.0
147.5°	1081.8	1082.4	1081.8	1080.3	1078.7	1077.2	1075.6
150°	1110.8	1110.8	1110.6	1110.1	1109.6	1109.2	1108.8
152.5°	1139.0	1139.5	1139.4	1138.6	1137.7	1136.9	1136.1
155°	1178.8	1179.8	1179.6	1178.5	1177.3	1176.3	1175.1
157.5°	1213.1	1214.0	1213.7	1212.2	1210.7	1209.2	1207.6
160°	1233.8	1234.7	1234.6	1233.4	1232.3	1231.1	1230.0
162.5°	1253.4	1254.5	1254.4	1253.0	1251.7	1250.4	1249.0
165°	1279.3	1280.3	1280.1	1278.7	1277.3	1275.9	1274.5
167.5°	1299.2	1300.6	1300.6	1299.1	1297.7	1296.3	1294.9
170°	1310.8	1312.2	1312.1	1310.5	1308.9	1307.2	1305.6
172.5°	1319.1	1320.4	1320.4	1319.0	1317.6	1316.2	1314.7
175°	1328.4	1329.8	1329.7	1328.1	1326.5	1324.8	1323.2
177.5°	1332.4	1333.5	1333.4	1332.1	1330.8	1329.5	1328.2
180°	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5	1331.5

(END OF REPORT)