

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333583-940

Luminaire Tested: **S125RDIP-S1090D365U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333583-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D365U940-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5071.9 lumens  
Efficiency: N/A  
Efficacy: 116.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333583-940

CATALOG NUMBER: S125RDIP-S1090D365U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333583-940

CATALOG NUMBER: S125RDIP-S1090D365U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97		87	87	87		78	78	78	74
1	104	99	95	92	98	94	91	88	86	83	80		77	75	74		70	68	67	63
2	95	87	81	76	90	83	77	73	75	71	67		68	65	62		62	59	57	53
3	87	77	69	63	82	73	67	61	67	61	57		61	56	53		55	52	49	46
4	79	68	60	54	75	65	58	52	60	54	49		54	49	45		49	46	42	39
5	73	61	53	47	69	59	51	45	54	47	42		49	44	40		45	40	37	34
6	68	55	47	41	64	53	45	40	48	42	37		44	39	35		41	36	33	30
7	63	50	42	36	59	48	40	35	44	38	33		41	35	31		37	33	29	27
8	58	46	38	32	55	44	36	31	40	34	30		37	32	28		34	30	26	24
9	54	42	34	29	52	40	33	28	37	31	27		34	29	25		32	27	24	22
10	51	39	31	26	48	37	30	26	34	28	24		32	27	23		29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10293	10293	10293
5°	10317	10200	10263
10°	10239	10105	10105
15°	10117	9900	9819
20°	9961	9614	9498
25°	9779	9333	9128
30°	9552	9004	8717
35°	9320	8665	8257
40°	9104	8312	7804
45°	8840	7916	7311
50°	8575	7486	6797
55°	8268	7076	6248
60°	7962	6577	5660
65°	7597	5997	4985
70°	7183	5274	4296
75°	6608	4447	3573
80°	5821	3492	2998
85°	4905	2853	2675



TEST NUMBER: P333583-940

CATALOG NUMBER: S125RDIP-S1090D365U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.9	3.0
10°-20°	418.8	8.3
20°-30°	607.3	12.0
30°-40°	692.2	13.6
40°-50°	674.7	13.3
50°-60°	567.9	11.2
60°-70°	398.1	7.8
70°-80°	204.6	4.0
80°-90°	52.6	1.0
90°-100°	15.5	0.3
100°-110°	95.2	1.9
110°-120°	172.7	3.4
120°-130°	221.7	4.4
130°-140°	238.4	4.7
140°-150°	223.8	4.4
150°-160°	181.0	3.6
160°-170°	117.1	2.3
170°-180°	40.4	0.8
0°-30°	1176.0	23.2
0°-40°	1868.2	36.8
0°-60°	3110.9	61.3
0°-90°	3766.2	74.3
90°-120°	283.4	5.6
90°-150°	967.3	19.1
90°-180°	1306.0	25.7
0°-180°	5071.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1591	1586	1573	1585	1583	151
15°	1513	1505	1481	1479	1469	426
25°	1372	1353	1310	1294	1281	631
35°	1182	1152	1099	1065	1047	740
45°	968	931	867	820	800	746
55°	734	694	628	576	555	657
65°	497	455	392	346	326	492
75°	265	228	178	153	143	280
85°	66	45	38	37	36	74
90°	0	3	5	7	8	4
95°	18	16	5	6	7	23
105°	93	94	94	94	94	98
115°	174	176	176	175	173	172
125°	247	250	250	248	247	221
135°	309	310	310	309	307	238
145°	358	358	358	359	357	224
155°	394	392	393	394	391	181
165°	416	414	414	416	414	117
175°	425	424	424	426	423	40
180°	425	425	425	425	425	



TEST NUMBER: P333583-940

CATALOG NUMBER: S125RDIP-S1090D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1596.7	1596.1	1595.4	1594.7	1594.1	1592.8	1590.6	1588.5	1586.4	1584.2	1586.4
5°	1591.4	1590.4	1589.3	1588.2	1587.2	1585.1	1582.2	1579.2	1576.3	1573.3	1576.0
7.5°	1575.7	1574.8	1573.7	1572.7	1571.6	1569.4	1565.8	1562.4	1558.8	1555.3	1557.2
10°	1561.3	1560.5	1559.7	1558.9	1558.1	1555.9	1552.1	1548.4	1544.6	1540.9	1541.7
12.5°	1544.9	1543.9	1542.9	1541.9	1540.9	1537.8	1532.9	1527.8	1522.8	1517.7	1518.3
15°	1513.1	1511.5	1509.9	1508.3	1506.7	1503.2	1497.5	1491.9	1486.3	1480.7	1480.4
17.5°	1477.3	1474.8	1472.4	1469.9	1467.4	1462.7	1455.6	1448.6	1441.5	1434.4	1433.1
20°	1449.4	1446.7	1444.0	1441.4	1438.7	1433.1	1424.5	1415.9	1407.4	1398.8	1397.5
22.5°	1418.5	1415.9	1413.2	1410.5	1407.8	1402.0	1393.0	1384.0	1375.0	1366.0	1363.4
25°	1372.3	1368.3	1364.3	1360.3	1356.3	1349.3	1339.4	1329.5	1319.6	1309.7	1306.3
27.5°	1319.4	1314.5	1309.6	1304.8	1299.8	1292.2	1281.6	1271.0	1260.3	1249.7	1244.9
30°	1280.9	1275.8	1270.7	1265.6	1260.5	1252.3	1241.1	1229.8	1218.6	1207.4	1201.2
32.5°	1243.2	1237.3	1231.4	1225.5	1219.5	1210.9	1199.4	1187.9	1176.4	1165.0	1158.2
35°	1182.1	1175.7	1169.3	1162.9	1156.5	1147.2	1135.1	1123.1	1111.1	1099.0	1091.3
37.5°	1122.1	1114.4	1106.5	1098.8	1090.9	1080.8	1068.4	1056.0	1043.6	1031.2	1021.8
40°	1079.8	1071.7	1063.7	1055.7	1047.7	1037.2	1024.4	1011.6	998.7	985.9	975.7
42.5°	1035.5	1027.3	1019.0	1010.8	1002.6	991.8	978.5	965.3	952.0	938.7	929.0
45°	967.9	960.1	952.3	944.6	936.8	925.6	910.9	896.2	881.5	866.7	856.0
47.5°	897.8	889.6	881.4	873.3	865.0	853.5	838.7	823.9	809.0	794.2	783.2
50°	853.5	844.6	835.8	827.0	818.1	806.1	790.9	775.6	760.4	745.1	733.9
52.5°	805.3	796.3	787.2	778.2	769.2	757.4	743.1	728.6	714.3	699.9	687.8
55°	734.3	725.8	717.2	708.6	700.1	688.3	673.3	658.4	643.4	628.4	616.4
57.5°	662.5	653.4	644.3	635.1	626.0	614.2	599.8	585.3	570.9	556.4	544.7
60°	616.4	607.0	597.6	588.3	578.9	566.9	552.5	538.1	523.6	509.2	497.4
62.5°	567.2	558.3	549.4	540.4	531.5	519.7	505.1	490.4	475.7	461.0	450.1
65°	497.1	488.0	478.9	469.8	460.7	449.2	435.0	420.8	406.6	392.4	381.7
67.5°	427.6	418.5	409.4	400.3	391.2	379.9	366.2	352.7	339.1	325.5	315.8
70°	380.4	371.3	362.2	353.1	344.0	332.8	319.4	306.0	292.7	279.3	271.0
72.5°	334.2	325.3	316.4	307.6	298.6	287.9	275.4	262.9	250.4	237.9	230.2
75°	264.8	256.8	248.8	240.8	232.7	223.1	211.9	200.6	189.4	178.2	172.3
77.5°	196.0	189.6	183.2	176.7	170.3	162.6	153.6	144.6	135.6	126.6	122.5
80°	156.5	150.1	143.7	137.2	130.8	123.9	116.4	108.9	101.4	93.9	91.5
82.5°	118.0	112.2	106.4	100.7	94.9	89.4	84.3	79.1	74.0	68.8	67.8
85°	66.2	61.3	56.5	51.7	46.9	43.9	42.5	41.2	39.9	38.5	38.3
87.5°	22.2	20.9	19.4	18.0	16.7	16.0	15.8	15.7	15.6	15.4	15.5
90°	0.4	0.9	1.4	2.0	2.6	3.1	3.6	4.1	4.5	5.1	5.4
92.5°	4.8	4.5	4.1	3.7	3.3	3.3	3.7	4.2	4.6	5.1	5.4
95°	17.9	17.7	17.6	17.3	17.1	15.7	13.0	10.3	7.7	5.1	5.4
97.5°	37.5	37.9	38.3	38.6	39.1	36.6	31.3	26.0	20.8	15.5	13.6
100°	52.6	52.9	53.1	53.2	53.5	53.7	54.0	54.3	54.6	54.8	44.4
102.5°	68.0	68.3	68.6	68.8	69.1	69.3	69.5	69.6	69.8	70.0	68.0
105°	92.6	92.9	93.3	93.5	93.8	93.9	93.9	93.9	93.9	93.9	93.9
107.5°	118.2	118.2	118.2	118.2	118.2	118.3	118.5	118.6	118.8	118.9	118.9
110°	134.9	134.9	134.9	134.9	134.9	135.0	135.1	135.3	135.4	135.5	135.4



TEST NUMBER: P333583-940

CATALOG NUMBER: S125RDIP-S1090D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.5	150.7	150.9	151.1	151.2	151.3	151.4	151.5	151.6	151.7	151.4
115°	174.0	174.3	174.7	175.0	175.4	175.6	175.7	175.8	175.8	175.8	175.6
117.5°	198.2	198.2	198.2	198.2	198.2	198.3	198.6	198.9	199.1	199.4	199.0
120°	213.4	213.3	213.3	213.2	213.1	213.2	213.4	213.6	213.8	214.0	213.9
122.5°	226.8	227.0	227.3	227.6	227.8	228.0	228.1	228.2	228.3	228.4	228.3
125°	247.4	247.9	248.4	248.9	249.4	249.7	249.7	249.7	249.7	249.7	249.3
127.5°	267.2	267.5	267.9	268.2	268.6	268.8	268.7	268.7	268.6	268.6	268.4
130°	279.3	279.6	280.0	280.4	280.7	280.9	281.0	281.0	281.1	281.2	281.0
132.5°	291.4	291.8	292.2	292.6	293.0	293.1	293.0	292.8	292.7	292.5	292.5
135°	308.6	309.0	309.4	309.9	310.2	310.4	310.2	310.1	310.0	309.9	309.7
137.5°	324.4	324.8	325.1	325.5	325.8	326.0	325.8	325.7	325.6	325.5	325.5
140°	334.7	334.9	335.0	335.2	335.3	335.4	335.3	335.2	335.1	335.1	335.2
142.5°	344.1	344.2	344.3	344.3	344.4	344.5	344.6	344.7	344.8	344.9	344.9
145°	357.8	357.9	358.0	358.2	358.3	358.4	358.4	358.4	358.4	358.4	358.5
147.5°	369.7	369.7	369.7	369.6	369.6	369.6	369.7	369.8	369.9	370.0	370.1
150°	377.3	377.2	377.0	376.8	376.7	376.7	376.8	377.0	377.2	377.3	377.5
152.5°	384.6	384.3	384.0	383.7	383.3	383.3	383.4	383.6	383.7	383.9	384.0
155°	394.0	393.6	393.2	392.7	392.4	392.2	392.4	392.4	392.6	392.7	393.0
157.5°	401.3	401.0	400.7	400.5	400.3	400.1	400.1	400.2	400.2	400.2	400.4
160°	406.3	405.9	405.5	405.0	404.7	404.5	404.5	404.6	404.7	404.7	405.0
162.5°	410.4	409.9	409.5	409.0	408.7	408.5	408.6	408.6	408.7	408.8	409.1
165°	415.7	415.4	414.9	414.5	414.1	413.9	413.9	414.0	414.1	414.2	414.6
167.5°	419.8	419.4	418.9	418.5	418.0	417.9	417.9	418.0	418.1	418.1	418.7
170°	422.0	421.6	421.1	420.6	420.1	419.9	420.0	420.0	420.1	420.2	420.7
172.5°	423.6	423.1	422.6	422.1	421.6	421.4	421.5	421.7	421.8	422.0	422.4
175°	425.2	424.8	424.4	423.9	423.6	423.4	423.4	423.5	423.6	423.7	424.2
177.5°	426.0	425.6	425.3	425.0	424.6	424.5	424.5	424.6	424.6	424.7	425.1
180°	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2



TEST NUMBER: P333583-940

CATALOG NUMBER: S125RDIP-S1090D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1588.5	1590.6	1592.8	1593.7	1593.5	1593.3	1593.0	1592.9
5°	1578.7	1581.4	1584.0	1585.1	1584.6	1584.0	1583.5	1583.0
7.5°	1559.1	1560.9	1562.8	1563.4	1562.8	1562.3	1561.7	1561.0
10°	1542.5	1543.3	1544.1	1544.1	1543.3	1542.5	1541.7	1540.9
12.5°	1518.9	1519.5	1520.1	1519.7	1518.5	1517.3	1516.1	1514.8
15°	1480.2	1479.9	1479.6	1478.3	1475.9	1473.5	1471.1	1468.6
17.5°	1431.7	1430.4	1429.1	1427.5	1425.4	1423.4	1421.5	1419.5
20°	1396.2	1394.8	1393.5	1391.6	1389.2	1386.8	1384.4	1382.0
22.5°	1360.8	1358.2	1355.6	1353.3	1351.3	1349.3	1347.3	1345.3
25°	1302.8	1299.3	1295.8	1292.6	1289.7	1286.7	1283.8	1280.9
27.5°	1240.0	1235.2	1230.3	1226.5	1223.6	1220.8	1217.9	1215.1
30°	1195.1	1188.9	1182.8	1178.5	1176.1	1173.7	1171.3	1168.9
32.5°	1151.5	1144.6	1137.8	1132.9	1129.9	1126.9	1123.7	1120.7
35°	1083.5	1075.8	1068.0	1062.3	1058.5	1054.8	1051.1	1047.3
37.5°	1012.5	1003.3	993.9	987.5	983.8	980.2	976.5	972.9
40°	965.5	955.4	945.2	938.5	935.3	932.1	928.9	925.7
42.5°	919.3	909.5	899.7	892.5	887.8	883.2	878.4	873.7
45°	845.3	834.6	823.9	816.5	812.5	808.5	804.5	800.5
47.5°	772.2	761.2	750.2	742.4	738.0	733.5	729.2	724.7
50°	722.6	711.4	700.2	692.6	688.6	684.6	680.6	676.5
52.5°	675.7	663.6	651.5	643.5	639.4	635.4	631.4	627.4
55°	604.3	592.3	580.2	572.0	567.8	563.5	559.2	554.9
57.5°	532.9	521.1	509.3	501.5	497.8	493.9	490.1	486.3
60°	485.6	473.9	462.1	454.2	450.2	446.2	442.2	438.2
62.5°	439.3	428.3	417.4	409.9	405.9	401.9	397.9	393.9
65°	371.0	360.3	349.6	342.2	338.2	334.2	330.2	326.2
67.5°	305.9	296.1	286.3	279.8	276.6	273.4	270.2	267.0
70°	262.7	254.4	246.1	240.3	237.1	233.9	230.7	227.5
72.5°	222.6	214.9	207.2	202.3	200.2	198.0	195.9	193.8
75°	166.4	160.5	154.6	150.7	148.8	147.0	145.1	143.2
77.5°	118.4	114.3	110.1	107.4	106.0	104.6	103.3	101.8
80°	89.1	86.7	84.3	82.8	82.2	81.7	81.1	80.6
82.5°	66.6	65.5	64.4	63.7	63.3	63.0	62.7	62.3
85°	38.0	37.7	37.5	37.2	36.9	36.6	36.4	36.1
87.5°	15.6	15.7	15.7	15.7	15.5	15.3	15.2	15.0
90°	5.7	6.1	6.4	6.7	7.0	7.1	7.3	7.6
92.5°	5.7	6.1	6.4	6.7	6.8	6.9	7.0	7.0
95°	5.7	6.1	6.4	6.6	6.6	6.6	6.6	6.6
97.5°	11.6	9.5	7.6	6.6	6.6	6.6	6.6	6.6
100°	34.0	23.5	13.1	7.8	7.5	7.2	6.9	6.6
102.5°	66.0	64.0	62.1	58.7	53.9	49.2	44.4	39.7
105°	93.9	93.9	93.9	93.9	93.8	93.7	93.7	93.6
107.5°	119.0	119.0	119.0	118.9	118.7	118.4	118.2	118.0
110°	135.1	134.9	134.7	134.6	134.7	134.7	134.8	134.9





TEST NUMBER: P333583-940

CATALOG NUMBER: S125RDIP-S1090D365U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	151.1	150.9	150.6	150.4	150.3	150.3	150.2	150.1
115°	175.3	175.0	174.8	174.4	174.0	173.6	173.2	172.7
117.5°	198.7	198.3	198.0	197.7	197.5	197.3	197.2	197.0
120°	213.7	213.6	213.5	213.2	212.9	212.5	212.1	211.8
122.5°	228.1	228.0	227.8	227.6	227.1	226.8	226.3	226.0
125°	249.1	248.8	248.5	248.3	248.1	247.9	247.6	247.4
127.5°	268.2	268.0	268.0	267.6	267.1	266.5	266.1	265.6
130°	280.7	280.5	280.4	280.0	279.7	279.4	279.0	278.7
132.5°	292.4	292.4	292.3	292.1	291.8	291.4	291.1	290.8
135°	309.6	309.4	309.2	309.0	308.6	308.2	307.7	307.3
137.5°	325.6	325.6	325.6	325.4	325.0	324.7	324.3	324.0
140°	335.4	335.5	335.6	335.5	335.1	334.7	334.2	333.8
142.5°	344.9	345.0	345.0	344.8	344.4	343.9	343.6	343.1
145°	358.6	358.6	358.6	358.5	358.1	357.7	357.2	356.8
147.5°	370.1	370.2	370.3	370.1	369.6	369.1	368.6	368.1
150°	377.6	377.7	377.8	377.6	377.1	376.6	375.9	375.4
152.5°	384.1	384.2	384.4	384.2	383.7	383.3	382.7	382.2
155°	393.2	393.3	393.6	393.4	392.9	392.3	391.7	391.2
157.5°	400.6	400.8	401.1	400.9	400.4	399.8	399.2	398.7
160°	405.3	405.6	405.8	405.7	405.1	404.6	404.0	403.5
162.5°	409.6	409.9	410.4	410.2	409.6	408.9	408.4	407.8
165°	415.0	415.4	415.9	415.8	415.3	414.6	414.1	413.6
167.5°	419.2	419.6	420.2	420.1	419.5	418.8	418.2	417.6
170°	421.2	421.9	422.4	422.4	421.8	421.2	420.4	419.8
172.5°	422.9	423.5	423.9	423.9	423.3	422.6	422.0	421.3
175°	424.7	425.3	425.9	425.9	425.2	424.5	423.9	423.3
177.5°	425.5	425.9	426.2	426.2	425.8	425.3	424.9	424.5
180°	425.2	425.2	425.2	425.2	425.2	425.2	425.2	425.2

(END OF REPORT)