

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333590-940

Luminaire Tested: **S125RDIP-S1090D590U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333590-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D590U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5590.8 lumens  
Efficiency: N/A  
Efficacy: 114.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333590-940

CATALOG NUMBER: S125RDIP-S1090D590U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333590-940

CATALOG NUMBER: S125RDIP-S1090D590U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	79	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49
3	85	76	68	62	80	72	65	60	64	59	54	57	53	50	51	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10293	10293	10293
5°	10317	10200	10263
10°	10239	10105	10105
15°	10117	9900	9819
20°	9961	9614	9498
25°	9779	9333	9128
30°	9552	9004	8717
35°	9320	8665	8257
40°	9104	8312	7804
45°	8840	7916	7311
50°	8575	7486	6797
55°	8268	7076	6248
60°	7962	6577	5660
65°	7597	5997	4985
70°	7183	5274	4296
75°	6608	4447	3573
80°	5821	3492	2998
85°	4905	2853	2675



TEST NUMBER: P333590-940

CATALOG NUMBER: S125RDIP-S1090D590U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.9	2.7
10°-20°	418.8	7.5
20°-30°	607.3	10.9
30°-40°	692.2	12.4
40°-50°	674.7	12.1
50°-60°	567.9	10.2
60°-70°	398.1	7.1
70°-80°	204.6	3.7
80°-90°	53.1	1.0
90°-100°	43.8	0.8
100°-110°	129.3	2.3
110°-120°	219.0	3.9
120°-130°	288.2	5.2
130°-140°	322.9	5.8
140°-150°	316.5	5.7
150°-160°	265.8	4.8
160°-170°	176.7	3.2
170°-180°	61.8	1.1
0°-30°	1176.0	21.0
0°-40°	1868.2	33.4
0°-60°	3110.9	55.6
0°-90°	3766.7	67.4
90°-120°	392.0	7.0
90°-150°	1319.7	23.6
90°-180°	1824.0	32.6
0°-180°	5590.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1591	1586	1573	1585	1583	151
15°	1513	1505	1481	1479	1469	426
25°	1372	1353	1310	1294	1281	631
35°	1182	1152	1099	1065	1047	740
45°	968	931	867	820	800	746
55°	734	694	628	576	555	657
65°	497	455	392	346	326	492
75°	265	228	178	153	143	280
85°	66	45	38	37	36	74
90°	0	5	8	11	12	5
95°	33	34	39	43	44	35
105°	116	119	122	125	126	124
115°	219	221	222	222	221	217
125°	320	323	324	322	322	286
135°	416	419	420	420	418	321
145°	504	506	508	508	506	315
155°	577	577	577	579	577	266
165°	627	626	627	628	626	177
175°	652	650	650	653	650	62
180°	654	654	654	654	654	



TEST NUMBER: P333590-940

CATALOG NUMBER: S125RDIP-S1090D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1596.7	1596.1	1595.4	1594.7	1594.1	1592.8	1590.6	1588.5	1586.4	1584.2	1586.4
5°	1591.4	1590.4	1589.3	1588.2	1587.2	1585.1	1582.2	1579.2	1576.3	1573.3	1576.0
7.5°	1575.7	1574.8	1573.7	1572.7	1571.6	1569.4	1565.8	1562.4	1558.8	1555.3	1557.2
10°	1561.3	1560.5	1559.7	1558.9	1558.1	1555.9	1552.1	1548.4	1544.6	1540.9	1541.7
12.5°	1544.9	1543.9	1542.9	1541.9	1540.9	1537.8	1532.9	1527.8	1522.8	1517.7	1518.3
15°	1513.1	1511.5	1509.9	1508.3	1506.7	1503.2	1497.5	1491.9	1486.3	1480.7	1480.4
17.5°	1477.3	1474.8	1472.4	1469.9	1467.4	1462.7	1455.6	1448.6	1441.5	1434.4	1433.1
20°	1449.4	1446.7	1444.0	1441.4	1438.7	1433.1	1424.5	1415.9	1407.4	1398.8	1397.5
22.5°	1418.5	1415.9	1413.2	1410.5	1407.8	1402.0	1393.0	1384.0	1375.0	1366.0	1363.4
25°	1372.3	1368.3	1364.3	1360.3	1356.3	1349.3	1339.4	1329.5	1319.6	1309.7	1306.3
27.5°	1319.4	1314.5	1309.6	1304.8	1299.8	1292.2	1281.6	1271.0	1260.3	1249.7	1244.9
30°	1280.9	1275.8	1270.7	1265.6	1260.5	1252.3	1241.1	1229.8	1218.6	1207.4	1201.2
32.5°	1243.2	1237.3	1231.4	1225.5	1219.5	1210.9	1199.4	1187.9	1176.4	1165.0	1158.2
35°	1182.1	1175.7	1169.3	1162.9	1156.5	1147.2	1135.1	1123.1	1111.1	1099.0	1091.3
37.5°	1122.1	1114.4	1106.5	1098.8	1090.9	1080.8	1068.4	1056.0	1043.6	1031.2	1021.8
40°	1079.8	1071.7	1063.7	1055.7	1047.7	1037.2	1024.4	1011.6	998.7	985.9	975.7
42.5°	1035.5	1027.3	1019.0	1010.8	1002.6	991.8	978.5	965.3	952.0	938.7	929.0
45°	967.9	960.1	952.3	944.6	936.8	925.6	910.9	896.2	881.5	866.7	856.0
47.5°	897.8	889.6	881.4	873.3	865.0	853.5	838.7	823.9	809.0	794.2	783.2
50°	853.5	844.6	835.8	827.0	818.1	806.1	790.9	775.6	760.4	745.1	733.9
52.5°	805.3	796.3	787.2	778.2	769.2	757.4	743.1	728.6	714.3	699.9	687.8
55°	734.3	725.8	717.2	708.6	700.1	688.3	673.3	658.4	643.4	628.4	616.4
57.5°	662.5	653.4	644.3	635.1	626.0	614.2	599.8	585.3	570.9	556.4	544.7
60°	616.4	607.0	597.6	588.3	578.9	566.9	552.5	538.1	523.6	509.2	497.4
62.5°	567.2	558.3	549.4	540.4	531.5	519.7	505.1	490.4	475.7	461.0	450.1
65°	497.1	488.0	478.9	469.8	460.7	449.2	435.0	420.8	406.6	392.4	381.7
67.5°	427.6	418.5	409.4	400.3	391.2	379.9	366.2	352.7	339.1	325.5	315.8
70°	380.4	371.3	362.2	353.1	344.0	332.8	319.4	306.0	292.7	279.3	271.0
72.5°	334.2	325.3	316.4	307.6	298.6	287.9	275.4	262.9	250.4	237.9	230.2
75°	264.8	256.8	248.8	240.8	232.7	223.1	211.9	200.6	189.4	178.2	172.3
77.5°	196.0	189.6	183.2	176.7	170.3	162.6	153.6	144.6	135.6	126.6	122.5
80°	156.5	150.1	143.7	137.2	130.8	123.9	116.4	108.9	101.4	93.9	91.5
82.5°	118.0	112.2	106.4	100.7	94.9	89.4	84.3	79.1	74.0	68.8	67.8
85°	66.2	61.3	56.5	51.7	46.9	43.9	42.5	41.2	39.9	38.5	38.3
87.5°	22.3	21.0	19.6	18.3	16.9	16.3	16.2	16.2	16.1	16.1	16.2
90°	0.5	1.4	2.3	3.2	4.1	5.0	5.8	6.6	7.3	8.1	8.7
92.5°	12.3	12.9	13.6	14.2	14.8	15.6	16.6	17.6	18.5	19.5	20.2
95°	33.1	33.3	33.5	33.7	34.0	34.7	35.8	36.9	38.1	39.1	39.9
97.5°	54.9	55.0	55.1	55.2	55.3	56.1	57.7	59.2	60.8	62.3	63.1
100°	71.2	71.2	71.2	71.2	71.2	72.0	73.4	74.9	76.3	77.8	78.8
102.5°	88.7	89.2	89.6	90.1	90.5	91.1	91.8	92.6	93.4	94.1	95.2
105°	116.0	116.5	117.1	117.7	118.2	118.9	119.6	120.2	120.9	121.5	122.3
107.5°	146.1	146.7	147.2	147.8	148.4	148.9	149.5	149.9	150.4	151.0	151.3
110°	166.8	167.4	168.0	168.5	169.2	169.6	169.9	170.2	170.6	170.9	171.3



TEST NUMBER: P333590-940

CATALOG NUMBER: S125RDIP-S1090D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.0	188.3	188.6	188.9	189.2	189.6	190.0	190.4	190.8	191.3	191.5
115°	219.3	219.7	220.2	220.6	221.1	221.4	221.6	221.9	222.0	222.3	222.2
117.5°	250.6	250.7	251.0	251.2	251.4	251.6	251.8	252.0	252.2	252.4	252.5
120°	270.1	270.7	271.3	271.8	272.4	272.7	272.9	273.0	273.0	273.1	273.1
122.5°	291.3	291.5	291.7	291.9	292.1	292.3	292.7	292.9	293.2	293.6	293.5
125°	319.9	320.7	321.3	322.0	322.7	323.1	323.2	323.3	323.4	323.5	323.3
127.5°	350.5	350.9	351.2	351.6	352.0	352.3	352.4	352.6	352.7	352.8	352.8
130°	368.8	369.3	370.0	370.5	371.0	371.5	371.7	371.9	372.1	372.4	372.3
132.5°	387.1	388.1	389.0	389.9	390.8	391.3	391.2	391.2	391.1	391.1	391.0
135°	416.1	416.8	417.5	418.1	418.8	419.2	419.4	419.5	419.5	419.6	419.6
137.5°	443.4	444.1	444.7	445.3	446.0	446.5	446.7	446.9	447.2	447.5	447.5
140°	460.8	461.5	462.0	462.5	463.2	463.6	464.0	464.3	464.6	464.9	465.2
142.5°	478.4	478.8	479.3	479.8	480.3	480.7	481.2	481.6	482.1	482.4	482.6
145°	504.1	504.5	505.1	505.5	506.0	506.3	506.7	507.0	507.4	507.7	507.7
147.5°	527.9	528.2	528.4	528.7	529.0	529.1	529.4	529.8	530.0	530.3	530.6
150°	543.8	543.7	543.6	543.5	543.3	543.5	543.9	544.4	544.8	545.3	545.3
152.5°	556.8	557.0	557.1	557.3	557.4	557.6	557.8	557.9	558.1	558.4	558.7
155°	576.8	576.8	576.8	576.8	576.8	576.9	577.0	577.1	577.3	577.4	577.8
157.5°	594.8	594.5	594.2	594.1	593.8	593.7	593.8	594.0	594.1	594.1	594.6
160°	605.4	605.0	604.7	604.3	604.0	603.9	604.0	604.1	604.2	604.3	604.8
162.5°	614.7	614.5	614.2	613.9	613.7	613.6	613.6	613.7	613.7	613.7	614.2
165°	627.2	627.0	626.8	626.5	626.3	626.2	626.3	626.5	626.6	626.7	627.1
167.5°	637.8	637.4	636.9	636.4	636.0	635.8	635.8	635.8	635.8	635.8	636.4
170°	643.5	643.0	642.6	642.1	641.7	641.5	641.5	641.5	641.5	641.5	642.1
172.5°	647.6	647.1	646.7	646.2	645.8	645.5	645.5	645.5	645.5	645.5	646.2
175°	652.1	651.7	651.2	650.8	650.3	650.1	650.1	650.1	650.1	650.1	650.8
177.5°	654.5	654.2	653.8	653.4	653.0	652.8	652.7	652.6	652.6	652.5	653.0
180°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7



TEST NUMBER: P333590-940

CATALOG NUMBER: S125RDIP-S1090D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1588.5	1590.6	1592.8	1593.7	1593.5	1593.3	1593.0	1592.9
5°	1578.7	1581.4	1584.0	1585.1	1584.6	1584.0	1583.5	1583.0
7.5°	1559.1	1560.9	1562.8	1563.4	1562.8	1562.3	1561.7	1561.0
10°	1542.5	1543.3	1544.1	1544.1	1543.3	1542.5	1541.7	1540.9
12.5°	1518.9	1519.5	1520.1	1519.7	1518.5	1517.3	1516.1	1514.8
15°	1480.2	1479.9	1479.6	1478.3	1475.9	1473.5	1471.1	1468.6
17.5°	1431.7	1430.4	1429.1	1427.5	1425.4	1423.4	1421.5	1419.5
20°	1396.2	1394.8	1393.5	1391.6	1389.2	1386.8	1384.4	1382.0
22.5°	1360.8	1358.2	1355.6	1353.3	1351.3	1349.3	1347.3	1345.3
25°	1302.8	1299.3	1295.8	1292.6	1289.7	1286.7	1283.8	1280.9
27.5°	1240.0	1235.2	1230.3	1226.5	1223.6	1220.8	1217.9	1215.1
30°	1195.1	1188.9	1182.8	1178.5	1176.1	1173.7	1171.3	1168.9
32.5°	1151.5	1144.6	1137.8	1132.9	1129.9	1126.9	1123.7	1120.7
35°	1083.5	1075.8	1068.0	1062.3	1058.5	1054.8	1051.1	1047.3
37.5°	1012.5	1003.3	993.9	987.5	983.8	980.2	976.5	972.9
40°	965.5	955.4	945.2	938.5	935.3	932.1	928.9	925.7
42.5°	919.3	909.5	899.7	892.5	887.8	883.2	878.4	873.7
45°	845.3	834.6	823.9	816.5	812.5	808.5	804.5	800.5
47.5°	772.2	761.2	750.2	742.4	738.0	733.5	729.2	724.7
50°	722.6	711.4	700.2	692.6	688.6	684.6	680.6	676.5
52.5°	675.7	663.6	651.5	643.5	639.4	635.4	631.4	627.4
55°	604.3	592.3	580.2	572.0	567.8	563.5	559.2	554.9
57.5°	532.9	521.1	509.3	501.5	497.8	493.9	490.1	486.3
60°	485.6	473.9	462.1	454.2	450.2	446.2	442.2	438.2
62.5°	439.3	428.3	417.4	409.9	405.9	401.9	397.9	393.9
65°	371.0	360.3	349.6	342.2	338.2	334.2	330.2	326.2
67.5°	305.9	296.1	286.3	279.8	276.6	273.4	270.2	267.0
70°	262.7	254.4	246.1	240.3	237.1	233.9	230.7	227.5
72.5°	222.6	214.9	207.2	202.3	200.2	198.0	195.9	193.8
75°	166.4	160.5	154.6	150.7	148.8	147.0	145.1	143.2
77.5°	118.4	114.3	110.1	107.4	106.0	104.6	103.3	101.8
80°	89.1	86.7	84.3	82.8	82.2	81.7	81.1	80.6
82.5°	66.6	65.5	64.4	63.7	63.3	63.0	62.7	62.3
85°	38.0	37.7	37.5	37.2	36.9	36.6	36.4	36.1
87.5°	16.3	16.4	16.5	16.5	16.3	16.2	16.1	16.0
90°	9.3	9.8	10.4	10.9	11.2	11.5	11.9	12.2
92.5°	21.0	21.8	22.6	23.0	23.3	23.5	23.7	24.0
95°	40.8	41.6	42.4	42.8	43.1	43.3	43.5	43.8
97.5°	63.8	64.6	65.4	65.8	65.9	66.1	66.2	66.3
100°	79.9	80.9	81.9	82.5	82.8	83.0	83.2	83.5
102.5°	96.3	97.5	98.5	99.2	99.6	99.9	100.2	100.5
105°	123.0	123.6	124.3	124.8	125.1	125.5	125.8	126.2
107.5°	151.7	152.0	152.3	152.5	152.5	152.5	152.4	152.4
110°	171.6	171.9	172.3	172.4	172.3	172.2	172.0	171.9





TEST NUMBER: P333590-940

CATALOG NUMBER: S125RDIP-S1090D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.6	191.7	191.9	191.9	191.7	191.5	191.3	191.1
115°	222.0	221.9	221.9	221.8	221.6	221.5	221.4	221.3
117.5°	252.6	252.7	252.8	252.6	252.2	251.7	251.3	250.7
120°	273.1	273.1	273.1	273.0	272.5	272.1	271.6	271.2
122.5°	293.4	293.3	293.2	292.9	292.6	292.2	291.9	291.5
125°	323.1	322.9	322.6	322.4	322.4	322.3	322.1	322.0
127.5°	352.6	352.5	352.4	352.2	352.0	351.8	351.5	351.3
130°	372.1	372.0	371.9	371.8	371.5	371.3	371.0	370.9
132.5°	390.8	390.7	390.7	390.4	390.1	389.8	389.5	389.1
135°	419.6	419.6	419.6	419.5	419.0	418.6	418.1	417.7
137.5°	447.7	447.8	448.0	447.8	447.2	446.7	446.1	445.5
140°	465.4	465.7	465.8	465.7	465.1	464.6	464.0	463.4
142.5°	482.7	482.9	483.0	482.8	482.2	481.6	481.1	480.5
145°	507.7	507.7	507.7	507.5	507.2	506.8	506.5	506.1
147.5°	530.8	531.1	531.4	531.1	530.3	529.6	528.8	528.1
150°	545.3	545.3	545.3	545.2	545.0	544.7	544.6	544.3
152.5°	558.9	559.2	559.5	559.4	558.9	558.6	558.1	557.8
155°	578.3	578.7	579.2	579.2	578.5	578.0	577.4	576.8
157.5°	595.0	595.5	595.9	595.8	595.0	594.3	593.6	592.8
160°	605.2	605.6	606.1	606.1	605.6	604.9	604.4	603.9
162.5°	614.7	615.3	615.9	615.8	615.2	614.5	613.9	613.1
165°	627.6	628.0	628.6	628.4	627.8	627.1	626.3	625.7
167.5°	637.1	637.8	638.5	638.5	637.8	637.0	636.3	635.7
170°	642.8	643.5	644.2	644.1	643.4	642.6	641.8	641.0
172.5°	646.9	647.6	648.3	648.3	647.6	646.8	646.1	645.4
175°	651.5	652.1	652.8	652.7	652.0	651.2	650.4	649.6
177.5°	653.5	654.1	654.6	654.6	654.0	653.4	652.6	652.0
180°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7

(END OF REPORT)