

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333596-940

Luminaire Tested: **S125RDIP-S1090D810U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333596-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6267.5 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333596-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333596-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20		
RC	80					70					50					30					10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																							
0	110	110	110	110		102	102	102	102		89	89	89		77	77	77			65	65	65	60
1	100	96	92	89		94	90	87	84		78	76	74		68	66	64			58	57	56	51
2	92	84	78	73		85	79	74	69		69	65	61		60	57	54			52	49	47	43
3	84	74	67	61		78	70	63	58		61	56	52		53	49	46			46	43	41	37
4	77	66	58	52		71	62	55	49		55	49	45		48	43	40			41	38	35	32
5	71	59	51	45		66	55	48	43		49	43	39		43	38	35			37	34	31	28
6	65	53	45	39		61	50	43	37		44	38	34		39	34	30			34	30	27	25
7	60	48	40	34		56	45	38	33		40	34	30		35	31	27			31	27	24	22
8	56	44	36	30		52	41	34	29		37	31	27		32	28	24			28	25	22	20
9	52	40	32	27		49	38	31	26		34	28	24		30	25	22			26	23	20	18
10	49	37	29	25		46	35	28	24		31	26	22		28	23	20			24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10293	10293	10293
5°	10317	10200	10263
10°	10239	10105	10105
15°	10117	9900	9819
20°	9961	9614	9498
25°	9779	9333	9128
30°	9552	9004	8717
35°	9320	8665	8257
40°	9104	8312	7804
45°	8840	7916	7311
50°	8575	7486	6797
55°	8268	7076	6248
60°	7962	6577	5660
65°	7597	5997	4985
70°	7183	5274	4296
75°	6608	4447	3573
80°	5821	3492	2998
85°	4905	2853	2675



TEST NUMBER: P333596-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.4
10°-20°	418.8	6.7
20°-30°	607.3	9.7
30°-40°	692.2	11.0
40°-50°	674.7	10.8
50°-60°	567.9	9.1
60°-70°	398.1	6.4
70°-80°	204.6	3.3
80°-90°	53.6	0.9
90°-100°	60.0	1.0
100°-110°	177.2	2.8
110°-120°	300.2	4.8
120°-130°	395.0	6.3
130°-140°	442.6	7.1
140°-150°	433.8	6.9
150°-160°	364.4	5.8
160°-170°	242.2	3.9
170°-180°	84.8	1.4
0°-30°	1176.0	18.8
0°-40°	1868.2	29.8
0°-60°	3110.9	49.6
0°-90°	3767.2	60.1
90°-120°	537.4	8.6
90°-150°	1808.9	28.9
90°-180°	2500.0	39.9
0°-180°	6267.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1591	1586	1573	1585	1583	151
15°	1513	1505	1481	1479	1469	426
25°	1372	1353	1310	1294	1281	631
35°	1182	1152	1099	1065	1047	740
45°	968	931	867	820	800	746
55°	734	694	628	576	555	657
65°	497	455	392	346	326	492
75°	265	228	178	153	143	280
85°	66	45	38	37	36	74
90°	1	6	11	15	17	6
95°	45	47	54	58	60	48
105°	159	162	167	171	173	170
115°	300	303	305	304	303	297
125°	438	443	443	442	441	393
135°	570	574	575	575	572	439
145°	691	694	696	696	694	432
155°	791	791	791	794	791	364
165°	860	858	859	861	858	242
175°	894	891	891	895	890	85
180°	896	896	896	896	896	



TEST NUMBER: P333596-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1596.7	1596.1	1595.4	1594.7	1594.1	1592.8	1590.6	1588.5	1586.4	1584.2	1586.4
5°	1591.4	1590.4	1589.3	1588.2	1587.2	1585.1	1582.2	1579.2	1576.3	1573.3	1576.0
7.5°	1575.7	1574.8	1573.7	1572.7	1571.6	1569.4	1565.8	1562.4	1558.8	1555.3	1557.2
10°	1561.3	1560.5	1559.7	1558.9	1558.1	1555.9	1552.1	1548.4	1544.6	1540.9	1541.7
12.5°	1544.9	1543.9	1542.9	1541.9	1540.9	1537.8	1532.9	1527.8	1522.8	1517.7	1518.3
15°	1513.1	1511.5	1509.9	1508.3	1506.7	1503.2	1497.5	1491.9	1486.3	1480.7	1480.4
17.5°	1477.3	1474.8	1472.4	1469.9	1467.4	1462.7	1455.6	1448.6	1441.5	1434.4	1433.1
20°	1449.4	1446.7	1444.0	1441.4	1438.7	1433.1	1424.5	1415.9	1407.4	1398.8	1397.5
22.5°	1418.5	1415.9	1413.2	1410.5	1407.8	1402.0	1393.0	1384.0	1375.0	1366.0	1363.4
25°	1372.3	1368.3	1364.3	1360.3	1356.3	1349.3	1339.4	1329.5	1319.6	1309.7	1306.3
27.5°	1319.4	1314.5	1309.6	1304.8	1299.8	1292.2	1281.6	1271.0	1260.3	1249.7	1244.9
30°	1280.9	1275.8	1270.7	1265.6	1260.5	1252.3	1241.1	1229.8	1218.6	1207.4	1201.2
32.5°	1243.2	1237.3	1231.4	1225.5	1219.5	1210.9	1199.4	1187.9	1176.4	1165.0	1158.2
35°	1182.1	1175.7	1169.3	1162.9	1156.5	1147.2	1135.1	1123.1	1111.1	1099.0	1091.3
37.5°	1122.1	1114.4	1106.5	1098.8	1090.9	1080.8	1068.4	1056.0	1043.6	1031.2	1021.8
40°	1079.8	1071.7	1063.7	1055.7	1047.7	1037.2	1024.4	1011.6	998.7	985.9	975.7
42.5°	1035.5	1027.3	1019.0	1010.8	1002.6	991.8	978.5	965.3	952.0	938.7	929.0
45°	967.9	960.1	952.3	944.6	936.8	925.6	910.9	896.2	881.5	866.7	856.0
47.5°	897.8	889.6	881.4	873.3	865.0	853.5	838.7	823.9	809.0	794.2	783.2
50°	853.5	844.6	835.8	827.0	818.1	806.1	790.9	775.6	760.4	745.1	733.9
52.5°	805.3	796.3	787.2	778.2	769.2	757.4	743.1	728.6	714.3	699.9	687.8
55°	734.3	725.8	717.2	708.6	700.1	688.3	673.3	658.4	643.4	628.4	616.4
57.5°	662.5	653.4	644.3	635.1	626.0	614.2	599.8	585.3	570.9	556.4	544.7
60°	616.4	607.0	597.6	588.3	578.9	566.9	552.5	538.1	523.6	509.2	497.4
62.5°	567.2	558.3	549.4	540.4	531.5	519.7	505.1	490.4	475.7	461.0	450.1
65°	497.1	488.0	478.9	469.8	460.7	449.2	435.0	420.8	406.6	392.4	381.7
67.5°	427.6	418.5	409.4	400.3	391.2	379.9	366.2	352.7	339.1	325.5	315.8
70°	380.4	371.3	362.2	353.1	344.0	332.8	319.4	306.0	292.7	279.3	271.0
72.5°	334.2	325.3	316.4	307.6	298.6	287.9	275.4	262.9	250.4	237.9	230.2
75°	264.8	256.8	248.8	240.8	232.7	223.1	211.9	200.6	189.4	178.2	172.3
77.5°	196.0	189.6	183.2	176.7	170.3	162.6	153.6	144.6	135.6	126.6	122.5
80°	156.5	150.1	143.7	137.2	130.8	123.9	116.4	108.9	101.4	93.9	91.5
82.5°	118.0	112.2	106.4	100.7	94.9	89.4	84.3	79.1	74.0	68.8	67.8
85°	66.2	61.3	56.5	51.7	46.9	43.9	42.5	41.2	39.9	38.5	38.3
87.5°	22.3	21.0	19.8	18.5	17.3	16.7	16.7	16.7	16.7	16.7	16.9
90°	0.7	2.0	3.2	4.5	5.6	6.8	7.9	9.0	10.1	11.1	11.9
92.5°	16.9	17.7	18.6	19.4	20.3	21.4	22.7	24.1	25.4	26.8	27.8
95°	45.3	45.7	45.9	46.3	46.5	47.5	49.0	50.6	52.2	53.7	54.8
97.5°	75.3	75.4	75.5	75.7	75.8	77.0	79.1	81.2	83.4	85.5	86.5
100°	97.6	97.6	97.6	97.6	97.6	98.6	100.7	102.6	104.7	106.6	108.1
102.5°	121.6	122.3	122.9	123.5	124.1	124.9	125.9	127.0	128.0	129.0	130.5
105°	159.0	159.8	160.5	161.3	162.1	162.9	163.9	164.8	165.7	166.7	167.6
107.5°	200.3	201.0	201.8	202.6	203.4	204.1	204.8	205.5	206.3	207.0	207.4
110°	228.7	229.5	230.2	231.0	231.8	232.5	232.9	233.4	233.8	234.3	234.8



TEST NUMBER: P333596-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.7	258.2	258.5	259.0	259.3	259.8	260.4	261.0	261.6	262.2	262.4
115°	300.5	301.1	301.8	302.4	303.0	303.4	303.8	304.1	304.4	304.7	304.5
117.5°	343.5	343.8	344.0	344.3	344.6	344.9	345.2	345.4	345.7	346.0	346.1
120°	370.2	371.0	371.8	372.6	373.4	373.8	374.0	374.2	374.3	374.4	374.4
122.5°	399.2	399.6	399.8	400.1	400.4	400.7	401.1	401.5	401.9	402.3	402.2
125°	438.5	439.5	440.4	441.4	442.3	442.8	443.0	443.2	443.3	443.4	443.2
127.5°	480.5	481.0	481.4	482.0	482.5	482.9	483.0	483.2	483.5	483.7	483.5
130°	505.5	506.3	507.1	507.8	508.6	509.2	509.4	509.8	510.1	510.4	510.2
132.5°	530.7	531.9	533.2	534.4	535.7	536.3	536.3	536.2	536.1	536.1	535.9
135°	570.3	571.3	572.2	573.2	574.1	574.6	574.8	575.0	575.1	575.2	575.2
137.5°	607.8	608.7	609.6	610.5	611.4	612.0	612.3	612.6	613.0	613.3	613.5
140°	631.8	632.5	633.3	634.1	634.8	635.4	635.9	636.4	636.9	637.3	637.7
142.5°	655.8	656.4	657.0	657.6	658.4	659.0	659.5	660.1	660.7	661.3	661.5
145°	691.0	691.6	692.2	692.9	693.5	694.0	694.5	694.9	695.4	695.9	695.9
147.5°	723.6	724.0	724.3	724.7	725.0	725.3	725.8	726.1	726.5	726.8	727.2
150°	745.4	745.2	745.1	744.9	744.8	745.0	745.6	746.3	746.9	747.5	747.5
152.5°	763.2	763.5	763.7	763.9	764.1	764.4	764.6	764.8	765.1	765.4	765.7
155°	790.7	790.7	790.7	790.7	790.7	790.8	790.9	791.1	791.2	791.4	792.0
157.5°	815.3	814.9	814.6	814.2	813.9	813.8	814.0	814.1	814.2	814.4	815.0
160°	829.7	829.3	828.8	828.4	827.9	827.8	827.9	828.0	828.2	828.4	829.0
162.5°	842.6	842.2	841.9	841.6	841.2	841.1	841.1	841.2	841.2	841.2	842.0
165°	859.8	859.4	859.2	858.8	858.5	858.4	858.5	858.7	858.9	859.1	859.7
167.5°	874.2	873.6	873.0	872.4	871.7	871.5	871.5	871.5	871.5	871.5	872.4
170°	882.1	881.5	880.8	880.2	879.6	879.2	879.2	879.2	879.2	879.2	880.2
172.5°	887.6	887.0	886.4	885.7	885.1	884.8	884.8	884.8	884.8	884.8	885.7
175°	893.9	893.3	892.7	892.1	891.4	891.1	891.1	891.1	891.1	891.1	892.1
177.5°	897.2	896.6	896.2	895.6	895.1	894.8	894.7	894.6	894.5	894.3	895.1
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0



TEST NUMBER: P333596-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1588.5	1590.6	1592.8	1593.7	1593.5	1593.3	1593.0	1592.9
5°	1578.7	1581.4	1584.0	1585.1	1584.6	1584.0	1583.5	1583.0
7.5°	1559.1	1560.9	1562.8	1563.4	1562.8	1562.3	1561.7	1561.0
10°	1542.5	1543.3	1544.1	1544.1	1543.3	1542.5	1541.7	1540.9
12.5°	1518.9	1519.5	1520.1	1519.7	1518.5	1517.3	1516.1	1514.8
15°	1480.2	1479.9	1479.6	1478.3	1475.9	1473.5	1471.1	1468.6
17.5°	1431.7	1430.4	1429.1	1427.5	1425.4	1423.4	1421.5	1419.5
20°	1396.2	1394.8	1393.5	1391.6	1389.2	1386.8	1384.4	1382.0
22.5°	1360.8	1358.2	1355.6	1353.3	1351.3	1349.3	1347.3	1345.3
25°	1302.8	1299.3	1295.8	1292.6	1289.7	1286.7	1283.8	1280.9
27.5°	1240.0	1235.2	1230.3	1226.5	1223.6	1220.8	1217.9	1215.1
30°	1195.1	1188.9	1182.8	1178.5	1176.1	1173.7	1171.3	1168.9
32.5°	1151.5	1144.6	1137.8	1132.9	1129.9	1126.9	1123.7	1120.7
35°	1083.5	1075.8	1068.0	1062.3	1058.5	1054.8	1051.1	1047.3
37.5°	1012.5	1003.3	993.9	987.5	983.8	980.2	976.5	972.9
40°	965.5	955.4	945.2	938.5	935.3	932.1	928.9	925.7
42.5°	919.3	909.5	899.7	892.5	887.8	883.2	878.4	873.7
45°	845.3	834.6	823.9	816.5	812.5	808.5	804.5	800.5
47.5°	772.2	761.2	750.2	742.4	738.0	733.5	729.2	724.7
50°	722.6	711.4	700.2	692.6	688.6	684.6	680.6	676.5
52.5°	675.7	663.6	651.5	643.5	639.4	635.4	631.4	627.4
55°	604.3	592.3	580.2	572.0	567.8	563.5	559.2	554.9
57.5°	532.9	521.1	509.3	501.5	497.8	493.9	490.1	486.3
60°	485.6	473.9	462.1	454.2	450.2	446.2	442.2	438.2
62.5°	439.3	428.3	417.4	409.9	405.9	401.9	397.9	393.9
65°	371.0	360.3	349.6	342.2	338.2	334.2	330.2	326.2
67.5°	305.9	296.1	286.3	279.8	276.6	273.4	270.2	267.0
70°	262.7	254.4	246.1	240.3	237.1	233.9	230.7	227.5
72.5°	222.6	214.9	207.2	202.3	200.2	198.0	195.9	193.8
75°	166.4	160.5	154.6	150.7	148.8	147.0	145.1	143.2
77.5°	118.4	114.3	110.1	107.4	106.0	104.6	103.3	101.8
80°	89.1	86.7	84.3	82.8	82.2	81.7	81.1	80.6
82.5°	66.6	65.5	64.4	63.7	63.3	63.0	62.7	62.3
85°	38.0	37.7	37.5	37.2	36.9	36.6	36.4	36.1
87.5°	16.9	17.1	17.3	17.3	17.2	17.0	16.9	16.9
90°	12.7	13.5	14.3	14.9	15.3	15.8	16.2	16.8
92.5°	28.8	29.9	30.9	31.6	31.9	32.2	32.5	32.9
95°	55.8	57.0	58.1	58.8	59.0	59.4	59.7	59.9
97.5°	87.6	88.5	89.6	90.2	90.3	90.5	90.8	91.0
100°	109.5	110.8	112.3	113.2	113.4	113.7	114.0	114.3
102.5°	132.1	133.6	135.1	136.1	136.5	136.9	137.3	137.8
105°	168.5	169.4	170.4	171.0	171.6	172.0	172.5	172.9
107.5°	207.9	208.3	208.8	209.0	209.0	208.9	208.9	208.9
110°	235.2	235.7	236.1	236.3	236.1	235.9	235.9	235.7



TEST NUMBER: P333596-940

CATALOG NUMBER: S125RDIP-S1090D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	262.6	262.8	263.1	263.1	262.7	262.4	262.2	261.9
115°	304.4	304.3	304.1	303.9	303.8	303.6	303.4	303.4
117.5°	346.3	346.3	346.5	346.3	345.6	345.0	344.4	343.8
120°	374.4	374.4	374.4	374.2	373.5	372.9	372.3	371.7
122.5°	402.1	402.0	401.8	401.5	401.0	400.6	400.0	399.6
125°	442.8	442.6	442.2	442.0	441.8	441.7	441.6	441.4
127.5°	483.3	483.1	483.0	482.8	482.5	482.1	481.9	481.5
130°	510.1	510.0	509.8	509.5	509.3	508.9	508.6	508.3
132.5°	535.7	535.6	535.5	535.1	534.8	534.3	533.9	533.4
135°	575.2	575.2	575.2	575.0	574.4	573.7	573.1	572.5
137.5°	613.7	613.9	614.0	613.8	613.0	612.2	611.4	610.6
140°	637.9	638.2	638.6	638.3	637.6	636.8	636.0	635.3
142.5°	661.6	661.8	662.0	661.7	660.9	660.2	659.4	658.6
145°	695.9	695.9	695.9	695.6	695.2	694.7	694.3	693.8
147.5°	727.5	728.0	728.3	728.0	726.9	725.9	724.9	723.8
150°	747.5	747.5	747.5	747.3	747.0	746.7	746.4	746.1
152.5°	766.1	766.4	766.8	766.7	766.2	765.6	765.1	764.5
155°	792.6	793.3	793.9	793.8	793.0	792.3	791.5	790.7
157.5°	815.6	816.3	816.9	816.7	815.6	814.7	813.6	812.6
160°	829.6	830.2	830.8	830.8	830.0	829.2	828.4	827.7
162.5°	842.7	843.5	844.2	844.1	843.2	842.3	841.4	840.5
165°	860.3	860.9	861.5	861.4	860.4	859.5	858.5	857.6
167.5°	873.3	874.2	875.2	875.1	874.2	873.3	872.3	871.3
170°	881.1	882.1	883.0	882.9	881.8	880.7	879.7	878.6
172.5°	886.7	887.6	888.6	888.6	887.6	886.6	885.6	884.7
175°	893.0	893.9	894.8	894.7	893.7	892.6	891.5	890.5
177.5°	895.8	896.5	897.3	897.2	896.3	895.5	894.7	893.8
180°	896.0	896.0	896.0	896.0	896.0	896.0	896.0	896.0

(END OF REPORT)