

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333629-940

Luminaire Tested: **S125RDIP-S1270D1035U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333629-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7581.6 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	51	48	47	42
3	84	74	67	62	78	70	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	41	37	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	38	44	38	34	39	34	31	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10936	10936	10936	10936
5°	12582	10950	9671	10950
10°	14432	10895	8533	10895
15°	15588	10783	7585	10783
20°	17189	10654	7003	10654
25°	19892	10481	6499	10481
30°	21647	10300	6169	10300
35°	18260	10089	5864	10089
40°	12752	9711	5602	9711
45°	9460	9199	5345	9199
50°	7543	8667	5126	8667
55°	6402	8007	4931	8007
60°	5531	7417	4615	7417
65°	4928	6776	3972	6776
70°	4330	6209	3622	6209
75°	3748	5375	3401	5375
80°	2841	4523	2841	4523
85°	2371	3557	2675	3557



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.4	2.1
10°-20°	475.9	6.3
20°-30°	754.5	10.0
30°-40°	909.8	12.0
40°-50°	812.5	10.7
50°-60°	623.1	8.2
60°-70°	404.9	5.3
70°-80°	196.9	2.6
80°-90°	49.5	0.7
90°-100°	76.6	1.0
100°-110°	226.3	3.0
110°-120°	383.2	5.1
120°-130°	504.3	6.7
130°-140°	565.1	7.5
140°-150°	553.9	7.3
150°-160°	465.2	6.1
160°-170°	309.2	4.1
170°-180°	108.2	1.4
0°-30°	1392.7	18.4
0°-40°	2302.6	30.4
0°-60°	3738.2	49.3
0°-90°	4389.5	57.9
90°-120°	686.1	9.0
90°-150°	2309.5	30.5
90°-180°	3192.0	42.1
0°-180°	7581.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1693	1693	1693	1693	1693	
5°	1941	1689	1492	1689	1941	194
15°	2331	1613	1134	1613	2331	668
25°	2792	1471	912	1471	2792	1282
35°	2316	1280	744	1280	2316	1399
45°	1036	1007	585	1007	1036	826
55°	569	711	438	711	569	516
65°	322	443	260	443	322	321
75°	150	215	136	215	150	160
85°	32	48	36	48	32	37
90°	21	1	21	1	21	14
95°	77	58	77	58	77	78
105°	221	203	221	203	221	234
115°	387	384	387	384	387	383
125°	564	560	564	560	564	503
135°	731	728	731	728	731	564
145°	886	882	886	882	886	553
155°	1010	1010	1010	1010	1010	465
165°	1095	1098	1095	1098	1095	309
175°	1137	1141	1137	1141	1137	108
180°	1144	1144	1144	1144	1144	



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1781.1	1780.0	1782.3	1776.1	1776.6	1767.2	1767.2	1760.0	1750.5	1743.3	1740.0
5°	1940.7	1942.1	1939.3	1928.9	1922.0	1911.6	1899.7	1878.8	1861.4	1844.8	1831.6
7.5°	2105.1	2106.0	2096.9	2093.6	2076.1	2063.3	2037.0	2008.7	1983.5	1951.6	1927.1
10°	2200.7	2200.0	2190.2	2182.6	2167.3	2147.9	2122.2	2088.7	2057.5	2022.8	1989.4
12.5°	2256.3	2254.5	2251.4	2242.1	2227.9	2210.7	2188.9	2156.1	2117.5	2079.5	2040.5
15°	2331.4	2326.5	2317.5	2305.6	2285.5	2265.3	2241.0	2211.8	2175.0	2131.9	2095.7
17.5°	2424.2	2424.4	2410.5	2394.1	2366.7	2331.1	2293.6	2246.4	2196.4	2148.9	2110.5
20°	2501.0	2498.8	2485.0	2453.0	2421.7	2377.2	2334.1	2276.4	2215.3	2153.4	2105.4
22.5°	2611.1	2605.7	2591.2	2549.2	2500.7	2443.4	2377.5	2307.0	2233.1	2162.8	2099.9
25°	2791.5	2787.3	2758.9	2710.2	2642.0	2553.8	2467.6	2371.0	2264.7	2172.2	2095.7
27.5°	2915.0	2910.4	2889.2	2848.8	2786.0	2693.1	2576.4	2447.3	2314.5	2187.4	2077.1
30°	2902.7	2913.1	2910.4	2891.6	2844.4	2760.9	2653.2	2507.9	2350.1	2200.7	2069.3
32.5°	2728.1	2737.5	2761.9	2798.7	2801.5	2768.1	2687.7	2553.5	2390.1	2220.2	2063.2
35°	2316.0	2328.6	2375.9	2450.2	2547.5	2628.9	2645.5	2573.3	2426.6	2243.8	2054.1
37.5°	1780.6	1849.0	1888.7	1967.0	2114.1	2263.7	2407.5	2460.5	2398.1	2234.1	2039.2
40°	1512.5	1529.2	1600.1	1688.4	1812.1	1967.8	2172.9	2320.9	2325.8	2211.8	2015.8
42.5°	1294.6	1315.7	1364.3	1434.9	1540.8	1696.5	1908.2	2103.5	2194.1	2150.6	1985.2
45°	1035.7	1051.7	1087.2	1141.4	1222.7	1351.3	1533.4	1759.3	1938.7	2008.8	1903.2
47.5°	850.8	859.4	890.3	931.6	991.8	1085.5	1226.5	1422.5	1637.6	1788.5	1773.6
50°	750.7	760.5	784.1	815.4	866.1	945.3	1057.9	1221.3	1443.1	1627.2	1664.1
52.5°	672.9	680.9	695.6	725.2	767.1	828.0	918.9	1066.7	1266.2	1462.0	1547.3
55°	568.6	574.2	585.9	602.6	636.1	679.8	758.3	860.5	1021.8	1219.2	1344.3
57.5°	482.7	485.4	492.9	508.4	531.5	563.5	620.2	706.8	822.4	1000.2	1138.3
60°	428.2	431.0	440.7	451.1	469.2	498.4	542.9	603.3	714.5	861.2	1000.9
62.5°	384.8	386.5	390.7	401.1	417.0	439.4	474.5	523.8	612.2	741.1	873.1
65°	322.5	323.2	324.6	333.0	342.7	359.4	382.3	417.1	483.8	581.1	697.9
67.5°	262.8	263.7	268.6	271.5	281.7	290.4	303.9	330.5	377.5	443.1	533.9
70°	229.3	228.7	233.5	237.0	240.5	250.9	259.9	281.5	310.7	360.8	436.5
72.5°	198.2	196.4	198.5	199.7	204.4	211.4	220.5	233.7	256.2	290.7	348.7
75°	150.2	150.9	150.9	152.2	155.7	158.5	161.2	168.2	180.7	203.7	235.0
77.5°	105.4	104.2	107.2	107.6	109.7	112.7	115.1	117.9	123.1	132.5	148.6
80°	76.4	76.4	77.1	79.3	78.6	79.9	83.4	86.2	92.5	98.0	103.5
82.5°	58.7	58.1	58.8	59.2	59.1	60.5	61.7	62.2	64.6	67.4	71.3
85°	32.0	32.0	32.6	32.6	33.3	33.3	34.1	34.1	34.1	34.8	35.5
87.5°	16.5	15.9	15.2	15.1	15.5	16.4	15.7	14.9	14.7	14.5	14.8
90°	21.4	20.8	20.2	19.6	19.0	18.2	17.2	16.2	15.2	14.3	12.8
92.5°	42.0	41.6	41.1	40.8	40.3	39.4	38.1	36.8	35.5	34.2	32.5
95°	76.6	76.2	75.8	75.3	75.0	74.1	72.7	71.3	69.9	68.6	66.6
97.5°	116.1	115.8	115.7	115.4	115.1	114.4	113.1	111.7	110.5	109.1	106.4
100°	146.0	145.6	145.2	144.8	144.5	143.3	141.5	139.7	137.9	136.2	133.7
102.5°	175.9	175.4	174.8	174.2	173.7	172.5	170.5	168.5	166.7	164.7	163.4
105°	220.8	220.2	219.6	219.0	218.4	217.5	216.3	215.2	213.9	212.8	211.6
107.5°	266.7	266.8	266.8	266.8	266.9	266.6	266.0	265.4	264.8	264.2	263.3
110°	300.9	301.1	301.3	301.5	301.7	301.5	300.9	300.3	299.7	299.1	298.5



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	334.4	334.7	335.1	335.5	335.8	335.8	335.6	335.3	335.0	334.7	333.9
115°	387.3	387.4	387.6	387.8	388.1	388.3	388.4	388.6	388.9	389.1	388.6
117.5°	438.9	439.7	440.5	441.2	442.0	442.4	442.2	442.0	441.9	441.8	441.4
120°	474.5	475.3	476.1	476.9	477.7	478.0	478.0	478.0	478.0	478.0	477.9
122.5°	510.1	510.8	511.4	512.0	512.6	513.0	513.2	513.4	513.5	513.6	513.2
125°	563.6	563.7	563.9	564.1	564.3	564.6	565.0	565.4	565.8	566.2	566.0
127.5°	614.8	615.2	615.5	616.0	616.4	616.7	616.9	617.1	617.2	617.5	617.2
130°	649.0	649.3	649.8	650.1	650.6	650.9	651.0	651.2	651.5	651.7	651.2
132.5°	681.0	681.6	682.2	682.7	683.2	683.6	683.9	684.0	684.2	684.4	684.5
135°	730.8	731.6	732.5	733.3	734.1	734.4	734.4	734.4	734.4	734.4	734.2
137.5°	779.7	780.7	781.7	782.7	783.6	784.0	783.7	783.5	783.3	783.0	782.7
140°	811.0	812.0	813.0	814.0	814.9	815.3	814.8	814.5	814.0	813.7	813.1
142.5°	840.9	842.0	842.9	843.9	844.9	845.3	845.0	844.8	844.5	844.3	843.6
145°	885.8	886.4	887.0	887.6	888.1	888.5	888.5	888.5	888.5	888.5	887.9
147.5°	924.1	925.4	926.8	928.1	929.4	929.9	929.4	928.9	928.4	928.0	927.5
150°	952.5	953.0	953.3	953.8	954.1	954.3	954.3	954.3	954.3	954.3	953.5
152.5°	976.1	976.8	977.5	978.2	978.9	979.0	978.6	978.1	977.6	977.1	976.8
155°	1009.5	1010.5	1011.5	1012.5	1013.5	1013.6	1012.8	1012.0	1011.2	1010.4	1010.2
157.5°	1037.5	1038.8	1040.1	1041.4	1042.7	1042.9	1042.1	1041.3	1040.6	1039.8	1039.6
160°	1056.7	1057.7	1058.7	1059.7	1060.7	1060.8	1060.0	1059.2	1058.4	1057.6	1057.4
162.5°	1073.1	1074.2	1075.4	1076.6	1077.7	1077.8	1076.8	1075.8	1075.0	1074.0	1074.0
165°	1095.0	1096.2	1097.3	1098.6	1099.7	1099.9	1099.1	1098.3	1097.6	1096.8	1096.5
167.5°	1112.4	1113.7	1114.9	1116.2	1117.3	1117.4	1116.2	1115.0	1113.8	1112.6	1112.6
170°	1121.7	1123.1	1124.4	1125.9	1127.2	1127.3	1126.1	1125.0	1123.8	1122.6	1122.6
172.5°	1129.5	1130.8	1132.0	1133.2	1134.4	1134.4	1133.3	1132.1	1130.9	1129.7	1129.7
175°	1136.8	1138.2	1139.6	1141.0	1142.4	1142.5	1141.3	1140.1	1138.9	1137.7	1137.7
177.5°	1141.1	1142.2	1143.4	1144.4	1145.6	1145.6	1144.7	1143.7	1142.8	1141.8	1142.0
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1740.0	1736.1	1728.8	1722.2	1713.9	1706.6	1701.6	1695.5	1687.7	1678.3	1670.4
5°	1816.9	1801.7	1781.5	1764.2	1742.0	1724.6	1706.5	1689.1	1671.7	1649.5	1630.0
7.5°	1902.4	1870.8	1840.0	1801.4	1766.4	1735.1	1705.0	1674.6	1644.8	1613.3	1582.9
10°	1954.6	1916.4	1874.0	1825.3	1780.8	1738.5	1699.5	1661.3	1621.0	1585.6	1547.3
12.5°	2003.6	1954.2	1905.7	1844.2	1790.8	1739.0	1689.5	1641.8	1598.7	1552.7	1511.7
15°	2047.7	1999.1	1944.9	1869.8	1795.5	1732.9	1674.5	1612.7	1559.1	1507.7	1461.8
17.5°	2064.8	2013.8	1950.9	1878.7	1797.4	1718.7	1643.5	1575.7	1512.7	1452.8	1401.1
20°	2058.2	2008.8	1944.2	1875.4	1788.5	1706.5	1625.1	1550.1	1479.9	1416.6	1361.7
22.5°	2042.1	1991.0	1928.6	1855.9	1773.4	1686.5	1599.6	1519.5	1445.9	1380.5	1320.5
25°	2017.9	1948.4	1884.5	1813.5	1735.0	1648.8	1559.1	1470.8	1392.3	1325.5	1260.3
27.5°	1992.7	1905.9	1824.6	1754.2	1671.2	1594.3	1507.8	1417.3	1334.7	1266.8	1199.7
30°	1969.9	1872.6	1782.9	1703.0	1624.4	1551.5	1469.5	1381.2	1296.4	1226.2	1158.1
32.5°	1941.5	1838.1	1739.5	1647.3	1571.6	1499.2	1425.0	1340.6	1258.0	1185.5	1116.3
35°	1905.9	1773.9	1666.9	1568.9	1484.7	1414.5	1347.8	1279.7	1196.9	1121.9	1054.4
37.5°	1859.2	1709.4	1585.6	1478.7	1390.1	1319.6	1266.9	1204.6	1129.1	1057.2	994.7
40°	1830.9	1662.7	1527.1	1421.5	1328.3	1253.9	1204.6	1151.8	1083.0	1015.6	953.0
42.5°	1793.1	1619.9	1468.2	1358.1	1264.4	1192.8	1142.9	1096.7	1039.0	975.5	908.5
45°	1719.0	1536.9	1377.7	1259.5	1165.0	1094.8	1048.2	1007.2	963.4	905.0	846.6
47.5°	1622.5	1450.3	1283.7	1154.7	1062.1	996.9	951.7	919.4	888.1	838.4	781.7
50°	1545.2	1379.1	1216.4	1091.3	992.6	930.8	888.3	862.6	834.1	788.9	741.6
52.5°	1454.0	1305.6	1146.4	1018.4	925.3	867.4	826.6	800.9	777.4	740.6	695.5
55°	1310.3	1180.3	1034.3	918.2	832.8	774.4	735.4	711.1	697.2	665.9	630.4
57.5°	1144.4	1051.2	922.6	810.7	735.0	677.3	648.8	628.1	612.4	590.3	565.3
60°	1028.8	963.4	848.0	741.6	672.2	617.2	591.6	574.2	559.5	540.8	521.3
62.5°	911.4	863.9	763.5	672.2	608.2	562.2	538.1	522.5	505.6	492.9	474.0
65°	754.2	711.8	642.3	570.7	511.6	474.7	457.4	443.4	433.0	419.1	405.9
67.5°	586.7	569.4	521.5	472.1	429.7	396.9	381.9	372.2	359.6	351.3	342.2
70°	483.8	475.5	441.4	408.8	369.1	346.9	333.0	328.8	313.5	305.1	298.9
72.5°	392.6	388.7	369.1	346.4	318.5	299.0	286.2	281.5	271.8	265.1	261.1
75°	269.0	270.4	266.9	252.4	241.9	229.3	218.3	215.4	208.6	203.0	199.5
77.5°	170.1	177.3	177.5	176.8	172.6	165.1	160.4	158.4	151.5	149.5	148.6
80°	116.8	124.4	131.3	130.6	129.3	127.2	123.8	121.6	118.2	116.1	114.7
82.5°	77.8	85.0	90.8	94.5	94.3	92.2	89.8	88.8	88.1	86.6	86.3
85°	36.8	38.3	40.3	45.2	48.7	49.3	48.7	48.0	45.8	46.5	47.3
87.5°	15.1	14.8	15.1	14.8	13.9	16.4	17.7	18.0	17.2	16.4	15.6
90°	11.5	10.1	8.7	7.2	5.6	4.0	2.5	0.9	2.5	4.0	5.6
92.5°	30.8	29.1	27.4	25.9	24.9	23.7	22.6	21.6	22.6	23.7	24.9
95°	64.6	62.6	60.6	59.5	59.0	58.7	58.2	57.9	58.2	58.7	59.0
97.5°	103.7	100.9	98.3	96.8	96.7	96.5	96.3	96.1	96.3	96.5	96.7
100°	131.1	128.5	125.9	124.7	124.7	124.7	124.7	124.7	124.7	124.7	124.7
102.5°	162.1	160.8	159.4	158.5	157.7	156.9	156.0	155.2	156.0	156.9	157.7
105°	210.4	209.2	208.0	207.0	206.0	204.9	203.9	203.0	203.9	204.9	206.0
107.5°	262.4	261.4	260.6	259.7	258.7	257.6	256.6	255.7	256.6	257.6	258.7
110°	297.9	297.3	296.8	296.0	295.0	294.0	293.0	292.0	293.0	294.0	295.0



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.2	332.5	331.7	331.1	330.6	330.0	329.6	329.0	329.6	330.0	330.6
115°	388.3	387.8	387.4	386.8	386.1	385.3	384.5	383.7	384.5	385.3	386.1
117.5°	441.0	440.7	440.3	440.0	439.6	439.3	438.9	438.5	438.9	439.3	439.6
120°	477.7	477.4	477.2	476.7	475.7	474.7	473.7	472.7	473.7	474.7	475.7
122.5°	512.6	512.1	511.6	511.2	510.9	510.5	510.1	509.8	510.1	510.5	510.9
125°	565.8	565.6	565.4	564.7	563.6	562.3	561.2	560.0	561.2	562.3	563.6
127.5°	617.0	616.8	616.5	616.1	615.4	614.7	614.0	613.4	614.0	614.7	615.4
130°	650.9	650.5	650.1	649.3	648.4	647.4	646.4	645.4	646.4	647.4	648.4
132.5°	684.6	684.7	684.7	683.9	682.3	680.7	679.1	677.4	679.1	680.7	682.3
135°	734.1	733.9	733.7	733.0	731.7	730.6	729.4	728.3	729.4	730.6	731.7
137.5°	782.2	781.8	781.3	780.5	779.4	778.2	777.0	776.0	777.0	778.2	779.4
140°	812.5	811.9	811.3	810.5	809.5	808.5	807.5	806.6	807.5	808.5	809.5
142.5°	842.8	842.0	841.3	840.5	839.6	838.8	838.0	837.1	838.0	838.8	839.6
145°	887.3	886.7	886.1	885.4	884.6	883.8	883.1	882.3	883.1	883.8	884.6
147.5°	927.0	926.6	926.1	925.6	925.2	924.8	924.3	923.9	924.3	924.8	925.2
150°	952.8	952.0	951.2	950.9	951.1	951.3	951.5	951.6	951.5	951.3	951.1
152.5°	976.5	976.2	975.9	975.5	975.3	975.0	974.7	974.5	974.7	975.0	975.3
155°	1010.0	1009.9	1009.6	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5	1009.5
157.5°	1039.4	1039.2	1039.0	1039.1	1039.6	1040.0	1040.4	1040.9	1040.4	1040.0	1039.6
160°	1057.2	1057.0	1056.9	1057.0	1057.6	1058.2	1058.8	1059.4	1058.8	1058.2	1057.6
162.5°	1073.9	1073.9	1073.8	1074.1	1074.4	1074.9	1075.3	1075.8	1075.3	1074.9	1074.4
165°	1096.4	1096.2	1096.0	1096.1	1096.4	1096.9	1097.3	1097.7	1097.3	1096.9	1096.4
167.5°	1112.6	1112.6	1112.6	1113.0	1113.8	1114.6	1115.4	1116.2	1115.4	1114.6	1113.8
170°	1122.6	1122.6	1122.6	1123.0	1123.8	1124.5	1125.3	1126.1	1125.3	1124.5	1123.8
172.5°	1129.7	1129.7	1129.7	1130.2	1130.9	1131.7	1132.5	1133.3	1132.5	1131.7	1130.9
175°	1137.7	1137.7	1137.7	1138.1	1138.9	1139.7	1140.5	1141.3	1140.5	1139.7	1138.9
177.5°	1142.1	1142.3	1142.5	1142.8	1143.4	1144.2	1144.8	1145.4	1144.8	1144.2	1143.4
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1664.9	1657.2	1651.5	1640.4	1632.6	1629.3	1623.2	1621.5	1627.6	1623.2	1622.6
5°	1615.4	1595.3	1579.3	1563.3	1545.9	1534.8	1518.1	1515.3	1511.2	1504.9	1503.5
7.5°	1556.0	1529.8	1509.2	1482.8	1459.8	1441.4	1420.5	1410.6	1405.2	1397.1	1386.3
10°	1516.0	1484.7	1457.0	1430.5	1402.0	1379.1	1358.3	1342.2	1331.8	1322.1	1317.9
12.5°	1476.5	1444.7	1409.1	1377.2	1345.3	1319.6	1296.5	1286.1	1274.5	1263.1	1253.4
15°	1415.2	1372.8	1333.9	1297.1	1270.0	1242.2	1219.9	1204.6	1187.2	1182.4	1163.6
17.5°	1350.1	1308.6	1263.0	1224.2	1192.8	1162.2	1137.7	1120.3	1107.3	1089.4	1080.8
20°	1309.6	1260.3	1215.8	1180.3	1145.5	1109.4	1084.3	1069.8	1057.2	1042.7	1035.7
22.5°	1266.2	1218.0	1172.3	1130.8	1095.5	1059.9	1042.1	1027.0	1012.7	999.3	990.1
25°	1202.6	1153.9	1105.9	1062.8	1026.0	1000.2	979.4	962.0	954.4	941.2	931.4
27.5°	1139.5	1087.8	1038.0	995.1	966.2	940.8	923.6	909.9	896.1	884.6	876.1
30°	1098.9	1046.2	991.9	957.9	927.3	902.9	884.1	870.9	860.5	850.1	843.8
32.5°	1058.4	1003.9	955.7	918.9	890.0	869.0	849.7	837.0	826.1	814.5	807.2
35°	993.3	937.7	898.8	862.6	834.1	814.7	801.5	783.4	774.4	766.0	758.3
37.5°	932.8	881.1	839.0	807.3	782.6	763.2	746.1	736.4	725.2	717.7	711.4
40°	888.3	841.1	802.8	769.5	751.4	729.9	713.9	701.3	693.0	683.3	676.4
42.5°	848.3	804.4	767.2	737.3	714.7	696.5	681.1	668.5	658.0	651.0	645.2
45°	791.8	748.0	711.8	683.9	663.2	645.8	629.7	623.5	609.6	601.3	598.5
47.5°	733.2	694.0	659.1	633.5	612.1	595.7	580.7	567.9	560.3	552.1	547.6
50°	693.8	656.2	623.5	598.5	577.7	559.5	545.6	537.3	526.9	519.2	513.7
52.5°	654.2	619.5	586.8	562.8	544.8	526.7	511.2	502.8	492.9	488.1	484.2
55°	597.8	561.0	533.2	509.5	490.7	474.0	459.5	451.1	444.9	440.0	438.6
57.5°	533.9	504.6	478.8	457.5	438.0	422.3	409.6	401.6	396.1	395.4	391.2
60°	492.1	465.7	442.1	419.1	402.4	387.9	376.7	367.7	362.1	361.4	360.1
62.5°	450.4	425.1	403.1	383.0	368.0	353.9	343.4	333.2	329.9	326.5	323.3
65°	388.5	365.6	347.6	331.5	315.6	303.7	293.4	287.0	279.5	275.3	267.6
67.5°	327.8	310.0	292.7	279.2	266.6	255.4	246.7	237.5	232.3	229.0	223.4
70°	287.8	273.8	256.5	241.9	232.2	223.1	216.2	205.7	202.2	199.5	196.7
72.5°	249.9	237.7	223.1	211.3	201.6	193.1	185.0	180.1	176.7	173.9	172.3
75°	196.7	184.9	172.4	164.1	157.1	150.2	146.0	142.5	141.1	140.4	137.6
77.5°	144.5	138.2	128.1	121.5	116.9	114.1	110.4	108.6	108.4	105.4	104.4
80°	110.5	107.0	98.7	95.9	92.5	89.7	87.6	84.1	80.6	79.3	77.1
82.5°	82.1	78.6	75.3	70.9	67.9	66.3	64.2	63.0	63.4	61.4	60.5
85°	43.8	40.3	39.0	38.3	36.8	38.3	37.5	36.8	36.1	35.5	36.1
87.5°	15.3	15.6	15.3	16.8	15.3	16.2	16.4	16.1	16.2	16.4	16.1
90°	7.2	8.7	10.1	11.5	12.8	14.3	15.2	16.2	17.2	18.2	19.0
92.5°	25.9	27.4	29.1	30.8	32.5	34.2	35.5	36.8	38.1	39.4	40.3
95°	59.5	60.6	62.6	64.6	66.6	68.6	69.9	71.3	72.7	74.1	75.0
97.5°	96.8	98.3	100.9	103.7	106.4	109.1	110.5	111.7	113.1	114.4	115.1
100°	124.7	125.9	128.5	131.1	133.7	136.2	137.9	139.7	141.5	143.3	144.5
102.5°	158.5	159.4	160.8	162.1	163.4	164.7	166.7	168.5	170.5	172.5	173.7
105°	207.0	208.0	209.2	210.4	211.6	212.8	213.9	215.2	216.3	217.5	218.4
107.5°	259.7	260.6	261.4	262.4	263.3	264.2	264.8	265.4	266.0	266.6	266.9
110°	296.0	296.8	297.3	297.9	298.5	299.1	299.7	300.3	300.9	301.5	301.7



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	331.1	331.7	332.5	333.2	333.9	334.7	335.0	335.3	335.6	335.8	335.8
115°	386.8	387.4	387.8	388.3	388.6	389.1	388.9	388.6	388.4	388.3	388.1
117.5°	440.0	440.3	440.7	441.0	441.4	441.8	441.9	442.0	442.2	442.4	442.0
120°	476.7	477.2	477.4	477.7	477.9	478.0	478.0	478.0	478.0	478.0	477.7
122.5°	511.2	511.6	512.1	512.6	513.2	513.6	513.5	513.4	513.2	513.0	512.6
125°	564.7	565.4	565.6	565.8	566.0	566.2	565.8	565.4	565.0	564.6	564.3
127.5°	616.1	616.5	616.8	617.0	617.2	617.5	617.2	617.1	616.9	616.7	616.4
130°	649.3	650.1	650.5	650.9	651.2	651.7	651.5	651.2	651.0	650.9	650.6
132.5°	683.9	684.7	684.7	684.6	684.5	684.4	684.2	684.0	683.9	683.6	683.2
135°	733.0	733.7	733.9	734.1	734.2	734.4	734.4	734.4	734.4	734.4	734.1
137.5°	780.5	781.3	781.8	782.2	782.7	783.0	783.3	783.5	783.7	784.0	783.6
140°	810.5	811.3	811.9	812.5	813.1	813.7	814.0	814.5	814.8	815.3	814.9
142.5°	840.5	841.3	842.0	842.8	843.6	844.3	844.5	844.8	845.0	845.3	844.9
145°	885.4	886.1	886.7	887.3	887.9	888.5	888.5	888.5	888.5	888.5	888.1
147.5°	925.6	926.1	926.6	927.0	927.5	928.0	928.4	928.9	929.4	929.9	929.4
150°	950.9	951.2	952.0	952.8	953.5	954.3	954.3	954.3	954.3	954.3	954.1
152.5°	975.5	975.9	976.2	976.5	976.8	977.1	977.6	978.1	978.6	979.0	978.9
155°	1009.5	1009.6	1009.9	1010.0	1010.2	1010.4	1011.2	1012.0	1012.8	1013.6	1013.5
157.5°	1039.1	1039.0	1039.2	1039.4	1039.6	1039.8	1040.6	1041.3	1042.1	1042.9	1042.7
160°	1057.0	1056.9	1057.0	1057.2	1057.4	1057.6	1058.4	1059.2	1060.0	1060.8	1060.7
162.5°	1074.1	1073.8	1073.9	1073.9	1074.0	1074.0	1075.0	1075.8	1076.8	1077.8	1077.7
165°	1096.1	1096.0	1096.2	1096.4	1096.5	1096.8	1097.6	1098.3	1099.1	1099.9	1099.7
167.5°	1113.0	1112.6	1112.6	1112.6	1112.6	1112.6	1113.8	1115.0	1116.2	1117.4	1117.3
170°	1123.0	1122.6	1122.6	1122.6	1122.6	1122.6	1123.8	1125.0	1126.1	1127.3	1127.2
172.5°	1130.2	1129.7	1129.7	1129.7	1129.7	1129.7	1130.9	1132.1	1133.3	1134.4	1134.4
175°	1138.1	1137.7	1137.7	1137.7	1137.7	1137.7	1138.9	1140.1	1141.3	1142.5	1142.4
177.5°	1142.8	1142.5	1142.3	1142.1	1142.0	1141.8	1142.8	1143.7	1144.7	1145.6	1145.6
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1622.1	1616.0	1614.3	1616.5	1614.3	1616.0	1622.1	1622.6	1623.2	1627.6	1621.5
5°	1496.6	1489.6	1493.1	1491.7	1493.1	1489.6	1496.6	1503.5	1504.9	1511.2	1515.3
7.5°	1386.2	1377.5	1368.3	1371.3	1368.3	1377.5	1386.2	1386.3	1397.1	1405.2	1410.6
10°	1308.9	1301.9	1297.7	1301.2	1297.7	1301.9	1308.9	1317.9	1322.1	1331.8	1342.2
12.5°	1243.8	1239.7	1236.0	1234.5	1236.0	1239.7	1243.8	1253.4	1263.1	1274.5	1286.1
15°	1155.2	1146.9	1143.4	1134.4	1143.4	1146.9	1155.2	1163.6	1182.4	1187.2	1204.6
17.5°	1073.6	1070.9	1061.8	1057.9	1061.8	1070.9	1073.6	1080.8	1089.4	1107.3	1120.3
20°	1025.3	1022.5	1013.4	1019.0	1013.4	1022.5	1025.3	1035.7	1042.7	1057.2	1069.8
22.5°	985.3	979.1	976.2	974.6	976.2	979.1	985.3	990.1	999.3	1012.7	1027.0
25°	928.6	919.6	916.1	912.0	916.1	919.6	928.6	931.4	941.2	954.4	962.0
27.5°	872.2	867.4	862.7	861.7	862.7	867.4	872.2	876.1	884.6	896.1	909.9
30°	835.5	830.6	827.2	827.2	827.2	830.6	835.5	843.8	850.1	860.5	870.9
32.5°	802.7	799.0	795.5	795.0	795.5	799.0	802.7	807.2	814.5	826.1	837.0
35°	754.9	749.3	748.0	743.8	748.0	749.3	754.9	758.3	766.0	774.4	783.4
37.5°	705.3	700.6	700.5	700.1	700.5	700.6	705.3	711.4	717.7	725.2	736.4
40°	673.5	670.0	669.4	664.5	669.4	670.0	673.5	676.4	683.3	693.0	701.3
42.5°	639.6	637.8	635.4	633.4	635.4	637.8	639.6	645.2	651.0	658.0	668.5
45°	593.6	588.7	588.7	585.2	588.7	588.7	593.6	598.5	601.3	609.6	623.5
47.5°	546.1	542.3	542.7	539.1	542.7	542.3	546.1	547.6	552.1	560.3	567.9
50°	514.3	512.3	511.6	510.2	511.6	512.3	514.3	513.7	519.2	526.9	537.3
52.5°	482.7	481.7	484.4	481.3	484.4	481.7	482.7	484.2	488.1	492.9	502.8
55°	440.0	437.9	442.1	437.9	442.1	437.9	440.0	438.6	440.0	444.9	451.1
57.5°	390.9	389.0	392.7	390.7	392.7	389.0	390.9	391.2	395.4	396.1	401.6
60°	358.6	354.5	356.6	357.3	356.6	354.5	358.6	360.1	361.4	362.1	367.7
62.5°	320.3	317.8	319.3	316.1	319.3	317.8	320.3	323.3	326.5	329.9	333.2
65°	266.3	264.1	261.4	259.9	261.4	264.1	266.3	267.6	275.3	279.5	287.0
67.5°	223.6	218.6	218.6	219.6	218.6	218.6	223.6	223.4	229.0	232.3	237.5
70°	192.5	192.5	191.8	191.8	191.8	192.5	192.5	196.7	199.5	202.2	205.7
72.5°	170.9	170.3	169.1	168.5	169.1	170.3	170.9	172.3	173.9	176.7	180.1
75°	137.6	138.3	137.0	136.3	137.0	138.3	137.6	137.6	140.4	141.1	142.5
77.5°	101.7	98.7	100.2	98.7	100.2	98.7	101.7	104.4	105.4	108.4	108.6
80°	77.1	76.4	78.6	76.4	78.6	76.4	77.1	77.1	79.3	80.6	84.1
82.5°	61.0	60.4	61.3	59.7	61.3	60.4	61.0	60.5	61.4	63.4	63.0
85°	36.8	36.1	35.5	36.1	35.5	36.1	36.8	36.1	35.5	36.1	36.8
87.5°	16.7	16.2	16.4	16.5	16.4	16.2	16.7	16.1	16.4	16.2	16.1
90°	19.6	20.2	20.8	21.4	20.8	20.2	19.6	19.0	18.2	17.2	16.2
92.5°	40.8	41.1	41.6	42.0	41.6	41.1	40.8	40.3	39.4	38.1	36.8
95°	75.3	75.8	76.2	76.6	76.2	75.8	75.3	75.0	74.1	72.7	71.3
97.5°	115.4	115.7	115.8	116.1	115.8	115.7	115.4	115.1	114.4	113.1	111.7
100°	144.8	145.2	145.6	146.0	145.6	145.2	144.8	144.5	143.3	141.5	139.7
102.5°	174.2	174.8	175.4	175.9	175.4	174.8	174.2	173.7	172.5	170.5	168.5
105°	219.0	219.6	220.2	220.8	220.2	219.6	219.0	218.4	217.5	216.3	215.2
107.5°	266.8	266.8	266.8	266.7	266.8	266.8	266.8	266.9	266.6	266.0	265.4
110°	301.5	301.3	301.1	300.9	301.1	301.3	301.5	301.7	301.5	300.9	300.3



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	335.5	335.1	334.7	334.4	334.7	335.1	335.5	335.8	335.8	335.6	335.3
115°	387.8	387.6	387.4	387.3	387.4	387.6	387.8	388.1	388.3	388.4	388.6
117.5°	441.2	440.5	439.7	438.9	439.7	440.5	441.2	442.0	442.4	442.2	442.0
120°	476.9	476.1	475.3	474.5	475.3	476.1	476.9	477.7	478.0	478.0	478.0
122.5°	512.0	511.4	510.8	510.1	510.8	511.4	512.0	512.6	513.0	513.2	513.4
125°	564.1	563.9	563.7	563.6	563.7	563.9	564.1	564.3	564.6	565.0	565.4
127.5°	616.0	615.5	615.2	614.8	615.2	615.5	616.0	616.4	616.7	616.9	617.1
130°	650.1	649.8	649.3	649.0	649.3	649.8	650.1	650.6	650.9	651.0	651.2
132.5°	682.7	682.2	681.6	681.0	681.6	682.2	682.7	683.2	683.6	683.9	684.0
135°	733.3	732.5	731.6	730.8	731.6	732.5	733.3	734.1	734.4	734.4	734.4
137.5°	782.7	781.7	780.7	779.7	780.7	781.7	782.7	783.6	784.0	783.7	783.5
140°	814.0	813.0	812.0	811.0	812.0	813.0	814.0	814.9	815.3	814.8	814.5
142.5°	843.9	842.9	842.0	840.9	842.0	842.9	843.9	844.9	845.3	845.0	844.8
145°	887.6	887.0	886.4	885.8	886.4	887.0	887.6	888.1	888.5	888.5	888.5
147.5°	928.1	926.8	925.4	924.1	925.4	926.8	928.1	929.4	929.9	929.4	928.9
150°	953.8	953.3	953.0	952.5	953.0	953.3	953.8	954.1	954.3	954.3	954.3
152.5°	978.2	977.5	976.8	976.1	976.8	977.5	978.2	978.9	979.0	978.6	978.1
155°	1012.5	1011.5	1010.5	1009.5	1010.5	1011.5	1012.5	1013.5	1013.6	1012.8	1012.0
157.5°	1041.4	1040.1	1038.8	1037.5	1038.8	1040.1	1041.4	1042.7	1042.9	1042.1	1041.3
160°	1059.7	1058.7	1057.7	1056.7	1057.7	1058.7	1059.7	1060.7	1060.8	1060.0	1059.2
162.5°	1076.6	1075.4	1074.2	1073.1	1074.2	1075.4	1076.6	1077.7	1077.8	1076.8	1075.8
165°	1098.6	1097.3	1096.2	1095.0	1096.2	1097.3	1098.6	1099.7	1099.9	1099.1	1098.3
167.5°	1116.2	1114.9	1113.7	1112.4	1113.7	1114.9	1116.2	1117.3	1117.4	1116.2	1115.0
170°	1125.9	1124.4	1123.1	1121.7	1123.1	1124.4	1125.9	1127.2	1127.3	1126.1	1125.0
172.5°	1133.2	1132.0	1130.8	1129.5	1130.8	1132.0	1133.2	1134.4	1134.4	1133.3	1132.1
175°	1141.0	1139.6	1138.2	1136.8	1138.2	1139.6	1141.0	1142.4	1142.5	1141.3	1140.1
177.5°	1144.4	1143.4	1142.2	1141.1	1142.2	1143.4	1144.4	1145.6	1145.6	1144.7	1143.7
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1623.2	1629.3	1632.6	1640.4	1651.5	1657.2	1664.9	1670.4	1678.3	1687.7	1695.5
5°	1518.1	1534.8	1545.9	1563.3	1579.3	1595.3	1615.4	1630.0	1649.5	1671.7	1689.1
7.5°	1420.5	1441.4	1459.8	1482.8	1509.2	1529.8	1556.0	1582.9	1613.3	1644.8	1674.6
10°	1358.3	1379.1	1402.0	1430.5	1457.0	1484.7	1516.0	1547.3	1585.6	1621.0	1661.3
12.5°	1296.5	1319.6	1345.3	1377.2	1409.1	1444.7	1476.5	1511.7	1552.7	1598.7	1641.8
15°	1219.9	1242.2	1270.0	1297.1	1333.9	1372.8	1415.2	1461.8	1507.7	1559.1	1612.7
17.5°	1137.7	1162.2	1192.8	1224.2	1263.0	1308.6	1350.1	1401.1	1452.8	1512.7	1575.7
20°	1084.3	1109.4	1145.5	1180.3	1215.8	1260.3	1309.6	1361.7	1416.6	1479.9	1550.1
22.5°	1042.1	1059.9	1095.5	1130.8	1172.3	1218.0	1266.2	1320.5	1380.5	1445.9	1519.5
25°	979.4	1000.2	1026.0	1062.8	1105.9	1153.9	1202.6	1260.3	1325.5	1392.3	1470.8
27.5°	923.6	940.8	966.2	995.1	1038.0	1087.8	1139.5	1199.7	1266.8	1334.7	1417.3
30°	884.1	902.9	927.3	957.9	991.9	1046.2	1098.9	1158.1	1226.2	1296.4	1381.2
32.5°	849.7	869.0	890.0	918.9	955.7	1003.9	1058.4	1116.3	1185.5	1258.0	1340.6
35°	801.5	814.7	834.1	862.6	898.8	937.7	993.3	1054.4	1121.9	1196.9	1279.7
37.5°	746.1	763.2	782.6	807.3	839.0	881.1	932.8	994.7	1057.2	1129.1	1204.6
40°	713.9	729.9	751.4	769.5	802.8	841.1	888.3	953.0	1015.6	1083.0	1151.8
42.5°	681.1	696.5	714.7	737.3	767.2	804.4	848.3	908.5	975.5	1039.0	1096.7
45°	629.7	645.8	663.2	683.9	711.8	748.0	791.8	846.6	905.0	963.4	1007.2
47.5°	580.7	595.7	612.1	633.5	659.1	694.0	733.2	781.7	838.4	888.1	919.4
50°	545.6	559.5	577.7	598.5	623.5	656.2	693.8	741.6	788.9	834.1	862.6
52.5°	511.2	526.7	544.8	562.8	586.8	619.5	654.2	695.5	740.6	777.4	800.9
55°	459.5	474.0	490.7	509.5	533.2	561.0	597.8	630.4	665.9	697.2	711.1
57.5°	409.6	422.3	438.0	457.5	478.8	504.6	533.9	565.3	590.3	612.4	628.1
60°	376.7	387.9	402.4	419.1	442.1	465.7	492.1	521.3	540.8	559.5	574.2
62.5°	343.4	353.9	368.0	383.0	403.1	425.1	450.4	474.0	492.9	505.6	522.5
65°	293.4	303.7	315.6	331.5	347.6	365.6	388.5	405.9	419.1	433.0	443.4
67.5°	246.7	255.4	266.6	279.2	292.7	310.0	327.8	342.2	351.3	359.6	372.2
70°	216.2	223.1	232.2	241.9	256.5	273.8	287.8	298.9	305.1	313.5	328.8
72.5°	185.0	193.1	201.6	211.3	223.1	237.7	249.9	261.1	265.1	271.8	281.5
75°	146.0	150.2	157.1	164.1	172.4	184.9	196.7	199.5	203.0	208.6	215.4
77.5°	110.4	114.1	116.9	121.5	128.1	138.2	144.5	148.6	149.5	151.5	158.4
80°	87.6	89.7	92.5	95.9	98.7	107.0	110.5	114.7	116.1	118.2	121.6
82.5°	64.2	66.3	67.9	70.9	75.3	78.6	82.1	86.3	86.6	88.1	88.8
85°	37.5	38.3	36.8	38.3	39.0	40.3	43.8	47.3	46.5	45.8	48.0
87.5°	16.4	16.2	15.3	16.8	15.3	15.6	15.3	15.6	16.4	17.2	18.0
90°	15.2	14.3	12.8	11.5	10.1	8.7	7.2	5.6	4.0	2.5	0.9
92.5°	35.5	34.2	32.5	30.8	29.1	27.4	25.9	24.9	23.7	22.6	21.6
95°	69.9	68.6	66.6	64.6	62.6	60.6	59.5	59.0	58.7	58.2	57.9
97.5°	110.5	109.1	106.4	103.7	100.9	98.3	96.8	96.7	96.5	96.3	96.1
100°	137.9	136.2	133.7	131.1	128.5	125.9	124.7	124.7	124.7	124.7	124.7
102.5°	166.7	164.7	163.4	162.1	160.8	159.4	158.5	157.7	156.9	156.0	155.2
105°	213.9	212.8	211.6	210.4	209.2	208.0	207.0	206.0	204.9	203.9	203.0
107.5°	264.8	264.2	263.3	262.4	261.4	260.6	259.7	258.7	257.6	256.6	255.7
110°	299.7	299.1	298.5	297.9	297.3	296.8	296.0	295.0	294.0	293.0	292.0



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	335.0	334.7	333.9	333.2	332.5	331.7	331.1	330.6	330.0	329.6	329.0
115°	388.9	389.1	388.6	388.3	387.8	387.4	386.8	386.1	385.3	384.5	383.7
117.5°	441.9	441.8	441.4	441.0	440.7	440.3	440.0	439.6	439.3	438.9	438.5
120°	478.0	478.0	477.9	477.7	477.4	477.2	476.7	475.7	474.7	473.7	472.7
122.5°	513.5	513.6	513.2	512.6	512.1	511.6	511.2	510.9	510.5	510.1	509.8
125°	565.8	566.2	566.0	565.8	565.6	565.4	564.7	563.6	562.3	561.2	560.0
127.5°	617.2	617.5	617.2	617.0	616.8	616.5	616.1	615.4	614.7	614.0	613.4
130°	651.5	651.7	651.2	650.9	650.5	650.1	649.3	648.4	647.4	646.4	645.4
132.5°	684.2	684.4	684.5	684.6	684.7	684.7	683.9	682.3	680.7	679.1	677.4
135°	734.4	734.4	734.2	734.1	733.9	733.7	733.0	731.7	730.6	729.4	728.3
137.5°	783.3	783.0	782.7	782.2	781.8	781.3	780.5	779.4	778.2	777.0	776.0
140°	814.0	813.7	813.1	812.5	811.9	811.3	810.5	809.5	808.5	807.5	806.6
142.5°	844.5	844.3	843.6	842.8	842.0	841.3	840.5	839.6	838.8	838.0	837.1
145°	888.5	888.5	887.9	887.3	886.7	886.1	885.4	884.6	883.8	883.1	882.3
147.5°	928.4	928.0	927.5	927.0	926.6	926.1	925.6	925.2	924.8	924.3	923.9
150°	954.3	954.3	953.5	952.8	952.0	951.2	950.9	951.1	951.3	951.5	951.6
152.5°	977.6	977.1	976.8	976.5	976.2	975.9	975.5	975.3	975.0	974.7	974.5
155°	1011.2	1010.4	1010.2	1010.0	1009.9	1009.6	1009.5	1009.5	1009.5	1009.5	1009.5
157.5°	1040.6	1039.8	1039.6	1039.4	1039.2	1039.0	1039.1	1039.6	1040.0	1040.4	1040.9
160°	1058.4	1057.6	1057.4	1057.2	1057.0	1056.9	1057.0	1057.6	1058.2	1058.8	1059.4
162.5°	1075.0	1074.0	1074.0	1073.9	1073.9	1073.8	1074.1	1074.4	1074.9	1075.3	1075.8
165°	1097.6	1096.8	1096.5	1096.4	1096.2	1096.0	1096.1	1096.4	1096.9	1097.3	1097.7
167.5°	1113.8	1112.6	1112.6	1112.6	1112.6	1112.6	1113.0	1113.8	1114.6	1115.4	1116.2
170°	1123.8	1122.6	1122.6	1122.6	1122.6	1122.6	1123.0	1123.8	1124.5	1125.3	1126.1
172.5°	1130.9	1129.7	1129.7	1129.7	1129.7	1129.7	1130.2	1130.9	1131.7	1132.5	1133.3
175°	1138.9	1137.7	1137.7	1137.7	1137.7	1137.7	1138.1	1138.9	1139.7	1140.5	1141.3
177.5°	1142.8	1141.8	1142.0	1142.1	1142.3	1142.5	1142.8	1143.4	1144.2	1144.8	1145.4
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1701.6	1706.6	1713.9	1722.2	1728.8	1736.1	1740.0	1740.0	1743.3	1750.5	1760.0
5°	1706.5	1724.6	1742.0	1764.2	1781.5	1801.7	1816.9	1831.6	1844.8	1861.4	1878.8
7.5°	1705.0	1735.1	1766.4	1801.4	1840.0	1870.8	1902.4	1927.1	1951.6	1983.5	2008.7
10°	1699.5	1738.5	1780.8	1825.3	1874.0	1916.4	1954.6	1989.4	2022.8	2057.5	2088.7
12.5°	1689.5	1739.0	1790.8	1844.2	1905.7	1954.2	2003.6	2040.5	2079.5	2117.5	2156.1
15°	1674.5	1732.9	1795.5	1869.8	1944.9	1999.1	2047.7	2095.7	2131.9	2175.0	2211.8
17.5°	1643.5	1718.7	1797.4	1878.7	1950.9	2013.8	2064.8	2110.5	2148.9	2196.4	2246.4
20°	1625.1	1706.5	1788.5	1875.4	1944.2	2008.8	2058.2	2105.4	2153.4	2215.3	2276.4
22.5°	1599.6	1686.5	1773.4	1855.9	1928.6	1991.0	2042.1	2099.9	2162.8	2233.1	2307.0
25°	1559.1	1648.8	1735.0	1813.5	1884.5	1948.4	2017.9	2095.7	2172.2	2264.7	2371.0
27.5°	1507.8	1594.3	1671.2	1754.2	1824.6	1905.9	1992.7	2077.1	2187.4	2314.5	2447.3
30°	1469.5	1551.5	1624.4	1703.0	1782.9	1872.6	1969.9	2069.3	2200.7	2350.1	2507.9
32.5°	1425.0	1499.2	1571.6	1647.3	1739.5	1838.1	1941.5	2063.2	2220.2	2390.1	2553.5
35°	1347.8	1414.5	1484.7	1568.9	1666.9	1773.9	1905.9	2054.1	2243.8	2426.6	2573.3
37.5°	1266.9	1319.6	1390.1	1478.7	1585.6	1709.4	1859.2	2039.2	2234.1	2398.1	2460.5
40°	1204.6	1253.9	1328.3	1421.5	1527.1	1662.7	1830.9	2015.8	2211.8	2325.8	2320.9
42.5°	1142.9	1192.8	1264.4	1358.1	1468.2	1619.9	1793.1	1985.2	2150.6	2194.1	2103.5
45°	1048.2	1094.8	1165.0	1259.5	1377.7	1536.9	1719.0	1903.2	2008.8	1938.7	1759.3
47.5°	951.7	996.9	1062.1	1154.7	1283.7	1450.3	1622.5	1773.6	1788.5	1637.6	1422.5
50°	888.3	930.8	992.6	1091.3	1216.4	1379.1	1545.2	1664.1	1627.2	1443.1	1221.3
52.5°	826.6	867.4	925.3	1018.4	1146.4	1305.6	1454.0	1547.3	1462.0	1266.2	1066.7
55°	735.4	774.4	832.8	918.2	1034.3	1180.3	1310.3	1344.3	1219.2	1021.8	860.5
57.5°	648.8	677.3	735.0	810.7	922.6	1051.2	1144.4	1138.3	1000.2	822.4	706.8
60°	591.6	617.2	672.2	741.6	848.0	963.4	1028.8	1000.9	861.2	714.5	603.3
62.5°	538.1	562.2	608.2	672.2	763.5	863.9	911.4	873.1	741.1	612.2	523.8
65°	457.4	474.7	511.6	570.7	642.3	711.8	754.2	697.9	581.1	483.8	417.1
67.5°	381.9	396.9	429.7	472.1	521.5	569.4	586.7	533.9	443.1	377.5	330.5
70°	333.0	346.9	369.1	408.8	441.4	475.5	483.8	436.5	360.8	310.7	281.5
72.5°	286.2	299.0	318.5	346.4	369.1	388.7	392.6	348.7	290.7	256.2	233.7
75°	218.3	229.3	241.9	252.4	266.9	270.4	269.0	235.0	203.7	180.7	168.2
77.5°	160.4	165.1	172.6	176.8	177.5	177.3	170.1	148.6	132.5	123.1	117.9
80°	123.8	127.2	129.3	130.6	131.3	124.4	116.8	103.5	98.0	92.5	86.2
82.5°	89.8	92.2	94.3	94.5	90.8	85.0	77.8	71.3	67.4	64.6	62.2
85°	48.7	49.3	48.7	45.2	40.3	38.3	36.8	35.5	34.8	34.1	34.1
87.5°	17.7	16.4	13.9	14.8	15.1	14.8	15.1	14.8	14.5	14.7	14.9
90°	2.5	4.0	5.6	7.2	8.7	10.1	11.5	12.8	14.3	15.2	16.2
92.5°	22.6	23.7	24.9	25.9	27.4	29.1	30.8	32.5	34.2	35.5	36.8
95°	58.2	58.7	59.0	59.5	60.6	62.6	64.6	66.6	68.6	69.9	71.3
97.5°	96.3	96.5	96.7	96.8	98.3	100.9	103.7	106.4	109.1	110.5	111.7
100°	124.7	124.7	124.7	124.7	125.9	128.5	131.1	133.7	136.2	137.9	139.7
102.5°	156.0	156.9	157.7	158.5	159.4	160.8	162.1	163.4	164.7	166.7	168.5
105°	203.9	204.9	206.0	207.0	208.0	209.2	210.4	211.6	212.8	213.9	215.2
107.5°	256.6	257.6	258.7	259.7	260.6	261.4	262.4	263.3	264.2	264.8	265.4
110°	293.0	294.0	295.0	296.0	296.8	297.3	297.9	298.5	299.1	299.7	300.3



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	329.6	330.0	330.6	331.1	331.7	332.5	333.2	333.9	334.7	335.0	335.3
115°	384.5	385.3	386.1	386.8	387.4	387.8	388.3	388.6	389.1	388.9	388.6
117.5°	438.9	439.3	439.6	440.0	440.3	440.7	441.0	441.4	441.8	441.9	442.0
120°	473.7	474.7	475.7	476.7	477.2	477.4	477.7	477.9	478.0	478.0	478.0
122.5°	510.1	510.5	510.9	511.2	511.6	512.1	512.6	513.2	513.6	513.5	513.4
125°	561.2	562.3	563.6	564.7	565.4	565.6	565.8	566.0	566.2	565.8	565.4
127.5°	614.0	614.7	615.4	616.1	616.5	616.8	617.0	617.2	617.5	617.2	617.1
130°	646.4	647.4	648.4	649.3	650.1	650.5	650.9	651.2	651.7	651.5	651.2
132.5°	679.1	680.7	682.3	683.9	684.7	684.7	684.6	684.5	684.4	684.2	684.0
135°	729.4	730.6	731.7	733.0	733.7	733.9	734.1	734.2	734.4	734.4	734.4
137.5°	777.0	778.2	779.4	780.5	781.3	781.8	782.2	782.7	783.0	783.3	783.5
140°	807.5	808.5	809.5	810.5	811.3	811.9	812.5	813.1	813.7	814.0	814.5
142.5°	838.0	838.8	839.6	840.5	841.3	842.0	842.8	843.6	844.3	844.5	844.8
145°	883.1	883.8	884.6	885.4	886.1	886.7	887.3	887.9	888.5	888.5	888.5
147.5°	924.3	924.8	925.2	925.6	926.1	926.6	927.0	927.5	928.0	928.4	928.9
150°	951.5	951.3	951.1	950.9	951.2	952.0	952.8	953.5	954.3	954.3	954.3
152.5°	974.7	975.0	975.3	975.5	975.9	976.2	976.5	976.8	977.1	977.6	978.1
155°	1009.5	1009.5	1009.5	1009.5	1009.6	1009.9	1010.0	1010.2	1010.4	1011.2	1012.0
157.5°	1040.4	1040.0	1039.6	1039.1	1039.0	1039.2	1039.4	1039.6	1039.8	1040.6	1041.3
160°	1058.8	1058.2	1057.6	1057.0	1056.9	1057.0	1057.2	1057.4	1057.6	1058.4	1059.2
162.5°	1075.3	1074.9	1074.4	1074.1	1073.8	1073.9	1073.9	1074.0	1074.0	1075.0	1075.8
165°	1097.3	1096.9	1096.4	1096.1	1096.0	1096.2	1096.4	1096.5	1096.8	1097.6	1098.3
167.5°	1115.4	1114.6	1113.8	1113.0	1112.6	1112.6	1112.6	1112.6	1112.6	1113.8	1115.0
170°	1125.3	1124.5	1123.8	1123.0	1122.6	1122.6	1122.6	1122.6	1122.6	1123.8	1125.0
172.5°	1132.5	1131.7	1130.9	1130.2	1129.7	1129.7	1129.7	1129.7	1129.7	1130.9	1132.1
175°	1140.5	1139.7	1138.9	1138.1	1137.7	1137.7	1137.7	1137.7	1137.7	1138.9	1140.1
177.5°	1144.8	1144.2	1143.4	1142.8	1142.5	1142.3	1142.1	1142.0	1141.8	1142.8	1143.7
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1767.2	1767.2	1776.6	1776.1	1782.3	1780.0	1781.1
5°	1899.7	1911.6	1922.0	1928.9	1939.3	1942.1	1940.7
7.5°	2037.0	2063.3	2076.1	2093.6	2096.9	2106.0	2105.1
10°	2122.2	2147.9	2167.3	2182.6	2190.2	2200.0	2200.7
12.5°	2188.9	2210.7	2227.9	2242.1	2251.4	2254.5	2256.3
15°	2241.0	2265.3	2285.5	2305.6	2317.5	2326.5	2331.4
17.5°	2293.6	2331.1	2366.7	2394.1	2410.5	2424.4	2424.2
20°	2334.1	2377.2	2421.7	2453.0	2485.0	2498.8	2501.0
22.5°	2377.5	2443.4	2500.7	2549.2	2591.2	2605.7	2611.1
25°	2467.6	2553.8	2642.0	2710.2	2758.9	2787.3	2791.5
27.5°	2576.4	2693.1	2786.0	2848.8	2889.2	2910.4	2915.0
30°	2653.2	2760.9	2844.4	2891.6	2910.4	2913.1	2902.7
32.5°	2687.7	2768.1	2801.5	2798.7	2761.9	2737.5	2728.1
35°	2645.5	2628.9	2547.5	2450.2	2375.9	2328.6	2316.0
37.5°	2407.5	2263.7	2114.1	1967.0	1888.7	1849.0	1780.6
40°	2172.9	1967.8	1812.1	1688.4	1600.1	1529.2	1512.5
42.5°	1908.2	1696.5	1540.8	1434.9	1364.3	1315.7	1294.6
45°	1533.4	1351.3	1222.7	1141.4	1087.2	1051.7	1035.7
47.5°	1226.5	1085.5	991.8	931.6	890.3	859.4	850.8
50°	1057.9	945.3	866.1	815.4	784.1	760.5	750.7
52.5°	918.9	828.0	767.1	725.2	695.6	680.9	672.9
55°	758.3	679.8	636.1	602.6	585.9	574.2	568.6
57.5°	620.2	563.5	531.5	508.4	492.9	485.4	482.7
60°	542.9	498.4	469.2	451.1	440.7	431.0	428.2
62.5°	474.5	439.4	417.0	401.1	390.7	386.5	384.8
65°	382.3	359.4	342.7	333.0	324.6	323.2	322.5
67.5°	303.9	290.4	281.7	271.5	268.6	263.7	262.8
70°	259.9	250.9	240.5	237.0	233.5	228.7	229.3
72.5°	220.5	211.4	204.4	199.7	198.5	196.4	198.2
75°	161.2	158.5	155.7	152.2	150.9	150.9	150.2
77.5°	115.1	112.7	109.7	107.6	107.2	104.2	105.4
80°	83.4	79.9	78.6	79.3	77.1	76.4	76.4
82.5°	61.7	60.5	59.1	59.2	58.8	58.1	58.7
85°	34.1	33.3	33.3	32.6	32.6	32.0	32.0
87.5°	15.7	16.4	15.5	15.1	15.2	15.9	16.5
90°	17.2	18.2	19.0	19.6	20.2	20.8	21.4
92.5°	38.1	39.4	40.3	40.8	41.1	41.6	42.0
95°	72.7	74.1	75.0	75.3	75.8	76.2	76.6
97.5°	113.1	114.4	115.1	115.4	115.7	115.8	116.1
100°	141.5	143.3	144.5	144.8	145.2	145.6	146.0
102.5°	170.5	172.5	173.7	174.2	174.8	175.4	175.9
105°	216.3	217.5	218.4	219.0	219.6	220.2	220.8
107.5°	266.0	266.6	266.9	266.8	266.8	266.8	266.7
110°	300.9	301.5	301.7	301.5	301.3	301.1	300.9



TEST NUMBER: P333629-940

CATALOG NUMBER: S125RDIP-S1270D1035U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	335.6	335.8	335.8	335.5	335.1	334.7	334.4
115°	388.4	388.3	388.1	387.8	387.6	387.4	387.3
117.5°	442.2	442.4	442.0	441.2	440.5	439.7	438.9
120°	478.0	478.0	477.7	476.9	476.1	475.3	474.5
122.5°	513.2	513.0	512.6	512.0	511.4	510.8	510.1
125°	565.0	564.6	564.3	564.1	563.9	563.7	563.6
127.5°	616.9	616.7	616.4	616.0	615.5	615.2	614.8
130°	651.0	650.9	650.6	650.1	649.8	649.3	649.0
132.5°	683.9	683.6	683.2	682.7	682.2	681.6	681.0
135°	734.4	734.4	734.1	733.3	732.5	731.6	730.8
137.5°	783.7	784.0	783.6	782.7	781.7	780.7	779.7
140°	814.8	815.3	814.9	814.0	813.0	812.0	811.0
142.5°	845.0	845.3	844.9	843.9	842.9	842.0	840.9
145°	888.5	888.5	888.1	887.6	887.0	886.4	885.8
147.5°	929.4	929.9	929.4	928.1	926.8	925.4	924.1
150°	954.3	954.3	954.1	953.8	953.3	953.0	952.5
152.5°	978.6	979.0	978.9	978.2	977.5	976.8	976.1
155°	1012.8	1013.6	1013.5	1012.5	1011.5	1010.5	1009.5
157.5°	1042.1	1042.9	1042.7	1041.4	1040.1	1038.8	1037.5
160°	1060.0	1060.8	1060.7	1059.7	1058.7	1057.7	1056.7
162.5°	1076.8	1077.8	1077.7	1076.6	1075.4	1074.2	1073.1
165°	1099.1	1099.9	1099.7	1098.6	1097.3	1096.2	1095.0
167.5°	1116.2	1117.4	1117.3	1116.2	1114.9	1113.7	1112.4
170°	1126.1	1127.3	1127.2	1125.9	1124.4	1123.1	1121.7
172.5°	1133.3	1134.4	1134.4	1133.2	1132.0	1130.8	1129.5
175°	1141.3	1142.5	1142.4	1141.0	1139.6	1138.2	1136.8
177.5°	1144.7	1145.6	1145.6	1144.4	1143.4	1142.2	1141.1
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0

(END OF REPORT)