

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333612-940

Luminaire Tested: **S125RDIP-S1270D365U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333612-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D365U940-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5560.0 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68
2	96	89	83	77	92	85	80	75	78	74	70	72	68	65	66	63	61	58
3	88	79	71	65	84	75	69	63	70	64	60	64	60	56	59	56	53	50
4	81	70	62	56	77	67	60	54	62	56	51	58	53	49	53	49	46	43
5	75	63	54	48	71	60	53	47	56	50	45	52	47	42	48	44	40	38
6	69	57	48	42	66	55	47	41	51	44	39	47	42	37	44	39	36	33
7	64	51	43	38	61	50	42	37	46	40	35	43	37	33	40	35	32	30
8	60	47	39	33	57	45	38	33	42	36	31	39	34	30	37	32	29	26
9	56	43	35	30	53	42	34	29	39	33	28	36	31	27	34	29	26	24
10	52	40	32	27	50	38	31	27	36	30	26	34	28	25	32	27	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10936	10936	10936	10936
5°	12582	10950	9671	10950
10°	14432	10895	8533	10895
15°	15588	10783	7585	10783
20°	17189	10654	7003	10654
25°	19892	10481	6499	10481
30°	21647	10300	6169	10300
35°	18260	10089	5864	10089
40°	12752	9711	5602	9711
45°	9460	9199	5345	9199
50°	7543	8667	5126	8667
55°	6402	8007	4931	8007
60°	5531	7417	4615	7417
65°	4928	6776	3972	6776
70°	4330	6209	3622	6209
75°	3748	5375	3401	5375
80°	2841	4523	2841	4523
85°	2371	3557	2675	3557



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.4	2.9
10°-20°	475.9	8.6
20°-30°	754.5	13.6
30°-40°	909.8	16.4
40°-50°	812.5	14.6
50°-60°	623.1	11.2
60°-70°	404.9	7.3
70°-80°	196.9	3.5
80°-90°	47.9	0.9
90°-100°	113.3	2.0
100°-110°	243.6	4.4
110°-120°	228.6	4.1
120°-130°	185.2	3.3
130°-140°	148.7	2.7
140°-150°	112.2	2.0
150°-160°	79.0	1.4
160°-170°	46.5	0.8
170°-180°	15.1	0.3
0°-30°	1392.7	25.0
0°-40°	2302.6	41.4
0°-60°	3738.2	67.2
0°-90°	4387.8	78.9
90°-120°	585.4	10.5
90°-150°	1031.5	18.6
90°-180°	1172.0	21.1
0°-180°	5560.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1693	1693	1693	1693	1693	
5°	1941	1689	1492	1689	1941	194
15°	2331	1613	1134	1613	2331	668
25°	2792	1471	912	1471	2792	1282
35°	2316	1280	744	1280	2316	1399
45°	1036	1007	585	1007	1036	826
55°	569	711	438	711	569	516
65°	322	443	260	443	322	321
75°	150	215	136	215	150	160
85°	32	48	36	48	32	37
90°	7	0	7	0	7	7
95°	74	10	74	10	74	105
105°	418	36	418	36	418	415
115°	465	64	465	64	465	454
125°	366	88	366	88	366	332
135°	304	103	304	103	304	236
145°	240	120	240	120	240	153
155°	201	137	201	137	201	94
165°	176	150	176	150	176	50
175°	158	156	158	156	158	15
180°	156	156	156	156	156	



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1781.1	1780.0	1782.3	1776.1	1776.6	1767.2	1767.2	1760.0	1750.5	1743.3	1740.0
5°	1940.7	1942.1	1939.3	1928.9	1922.0	1911.6	1899.7	1878.8	1861.4	1844.8	1831.6
7.5°	2105.1	2106.0	2096.9	2093.6	2076.1	2063.3	2037.0	2008.7	1983.5	1951.6	1927.1
10°	2200.7	2200.0	2190.2	2182.6	2167.3	2147.9	2122.2	2088.7	2057.5	2022.8	1989.4
12.5°	2256.3	2254.5	2251.4	2242.1	2227.9	2210.7	2188.9	2156.1	2117.5	2079.5	2040.5
15°	2331.4	2326.5	2317.5	2305.6	2285.5	2265.3	2241.0	2211.8	2175.0	2131.9	2095.7
17.5°	2424.2	2424.4	2410.5	2394.1	2366.7	2331.1	2293.6	2246.4	2196.4	2148.9	2110.5
20°	2501.0	2498.8	2485.0	2453.0	2421.7	2377.2	2334.1	2276.4	2215.3	2153.4	2105.4
22.5°	2611.1	2605.7	2591.2	2549.2	2500.7	2443.4	2377.5	2307.0	2233.1	2162.8	2099.9
25°	2791.5	2787.3	2758.9	2710.2	2642.0	2553.8	2467.6	2371.0	2264.7	2172.2	2095.7
27.5°	2915.0	2910.4	2889.2	2848.8	2786.0	2693.1	2576.4	2447.3	2314.5	2187.4	2077.1
30°	2902.7	2913.1	2910.4	2891.6	2844.4	2760.9	2653.2	2507.9	2350.1	2200.7	2069.3
32.5°	2728.1	2737.5	2761.9	2798.7	2801.5	2768.1	2687.7	2553.5	2390.1	2220.2	2063.2
35°	2316.0	2328.6	2375.9	2450.2	2547.5	2628.9	2645.5	2573.3	2426.6	2243.8	2054.1
37.5°	1780.6	1849.0	1888.7	1967.0	2114.1	2263.7	2407.5	2460.5	2398.1	2234.1	2039.2
40°	1512.5	1529.2	1600.1	1688.4	1812.1	1967.8	2172.9	2320.9	2325.8	2211.8	2015.8
42.5°	1294.6	1315.7	1364.3	1434.9	1540.8	1696.5	1908.2	2103.5	2194.1	2150.6	1985.2
45°	1035.7	1051.7	1087.2	1141.4	1222.7	1351.3	1533.4	1759.3	1938.7	2008.8	1903.2
47.5°	850.8	859.4	890.3	931.6	991.8	1085.5	1226.5	1422.5	1637.6	1788.5	1773.6
50°	750.7	760.5	784.1	815.4	866.1	945.3	1057.9	1221.3	1443.1	1627.2	1664.1
52.5°	672.9	680.9	695.6	725.2	767.1	828.0	918.9	1066.7	1266.2	1462.0	1547.3
55°	568.6	574.2	585.9	602.6	636.1	679.8	758.3	860.5	1021.8	1219.2	1344.3
57.5°	482.7	485.4	492.9	508.4	531.5	563.5	620.2	706.8	822.4	1000.2	1138.3
60°	428.2	431.0	440.7	451.1	469.2	498.4	542.9	603.3	714.5	861.2	1000.9
62.5°	384.8	386.5	390.7	401.1	417.0	439.4	474.5	523.8	612.2	741.1	873.1
65°	322.5	323.2	324.6	333.0	342.7	359.4	382.3	417.1	483.8	581.1	697.9
67.5°	262.8	263.7	268.6	271.5	281.7	290.4	303.9	330.5	377.5	443.1	533.9
70°	229.3	228.7	233.5	237.0	240.5	250.9	259.9	281.5	310.7	360.8	436.5
72.5°	198.2	196.4	198.5	199.7	204.4	211.4	220.5	233.7	256.2	290.7	348.7
75°	150.2	150.9	150.9	152.2	155.7	158.5	161.2	168.2	180.7	203.7	235.0
77.5°	105.4	104.2	107.2	107.6	109.7	112.7	115.1	117.9	123.1	132.5	148.6
80°	76.4	76.4	77.1	79.3	78.6	79.9	83.4	86.2	92.5	98.0	103.5
82.5°	58.7	58.1	58.8	59.2	59.1	60.5	61.7	62.2	64.6	67.4	71.3
85°	32.0	32.0	32.6	32.6	33.3	33.3	34.1	34.1	34.1	34.8	35.5
87.5°	13.6	13.1	12.5	12.5	13.1	14.1	13.5	12.8	12.8	12.7	13.1
90°	7.2	7.2	7.0	7.0	7.0	6.3	6.0	5.7	5.4	5.1	4.4
92.5°	20.1	20.6	21.0	21.8	25.9	30.5	40.5	55.8	82.2	101.6	103.3
95°	74.1	79.1	81.6	91.0	113.4	139.9	178.7	226.6	273.2	279.2	227.8
97.5°	179.0	183.1	192.2	209.8	229.3	266.1	303.9	337.4	345.7	298.2	203.5
100°	245.8	250.8	262.5	285.2	306.9	339.7	372.2	387.6	363.4	284.5	181.6
102.5°	320.5	324.2	336.9	353.0	376.3	398.5	414.0	404.5	352.8	260.6	164.9
105°	417.6	421.3	427.7	438.0	448.2	451.6	437.7	394.6	319.0	228.5	148.7
107.5°	469.1	471.6	473.8	473.8	468.7	452.2	416.6	359.0	284.4	206.3	142.0
110°	486.2	486.2	484.0	478.0	463.9	437.1	392.7	332.8	264.7	196.0	139.9



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.3	482.0	476.5	466.2	445.5	413.9	369.0	312.1	250.1	189.9	139.9
115°	465.1	461.0	452.2	437.1	412.5	378.2	335.0	286.1	234.2	183.4	140.9
117.5°	431.7	429.2	420.4	404.7	380.2	348.7	311.5	269.4	224.6	180.2	142.9
120°	410.0	407.5	399.0	383.9	360.5	332.8	298.1	260.3	219.4	178.7	145.0
122.5°	390.8	388.6	380.0	366.2	345.4	319.4	288.6	253.5	214.8	177.5	146.7
125°	366.5	363.4	356.4	343.5	325.8	303.2	275.7	243.6	208.7	175.8	149.7
127.5°	345.7	344.3	337.8	326.4	310.3	289.1	263.5	233.5	203.0	175.1	153.0
130°	334.4	332.5	326.2	315.8	300.1	279.6	254.9	227.2	199.2	174.6	155.1
132.5°	323.0	320.8	315.0	304.7	288.9	269.2	246.9	220.9	196.2	174.6	157.3
135°	304.4	302.6	296.9	286.5	272.6	254.7	234.4	212.8	192.5	174.6	160.4
137.5°	284.5	282.5	277.2	267.8	255.4	240.1	223.4	205.8	189.3	175.0	163.3
140°	270.7	269.1	264.4	256.2	244.5	231.3	216.8	202.0	187.8	175.2	164.5
142.5°	257.9	256.5	252.1	245.1	235.2	223.7	211.2	198.8	186.5	175.5	165.2
145°	240.1	238.9	235.4	230.1	222.5	214.0	204.2	194.5	184.7	175.2	166.0
147.5°	225.2	224.5	222.6	218.3	212.3	205.9	198.3	190.4	182.7	174.4	166.4
150°	216.8	216.5	215.3	211.4	206.7	201.1	195.1	188.2	181.2	173.6	166.4
152.5°	210.3	209.9	208.7	205.6	201.7	197.2	191.8	185.7	179.4	172.6	166.1
155°	201.3	201.1	200.1	197.9	194.7	191.3	186.9	181.8	176.5	170.9	165.4
157.5°	193.4	193.5	192.6	190.8	188.3	185.7	182.2	178.1	173.7	168.9	164.6
160°	188.2	188.4	187.8	186.3	184.0	181.8	178.7	175.6	171.5	167.6	163.9
162.5°	183.3	183.4	183.2	182.0	180.3	178.3	175.7	172.7	169.4	166.1	163.1
165°	176.5	176.5	176.5	175.8	174.6	173.0	171.1	168.9	166.4	163.9	162.0
167.5°	170.1	170.2	170.5	170.0	169.3	168.2	166.7	165.2	163.5	161.7	160.2
170°	166.4	166.7	166.7	166.4	165.8	165.1	164.2	163.3	161.7	160.4	159.4
172.5°	162.8	163.2	163.7	163.1	163.0	162.6	161.9	161.0	159.9	158.9	158.5
175°	158.5	158.8	159.4	159.2	159.2	159.2	158.5	158.5	157.6	157.3	157.3
177.5°	156.3	156.3	157.0	156.9	157.0	157.0	157.0	156.9	156.6	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1740.0	1736.1	1728.8	1722.2	1713.9	1706.6	1701.6	1695.5	1687.7	1678.3	1670.4
5°	1816.9	1801.7	1781.5	1764.2	1742.0	1724.6	1706.5	1689.1	1671.7	1649.5	1630.0
7.5°	1902.4	1870.8	1840.0	1801.4	1766.4	1735.1	1705.0	1674.6	1644.8	1613.3	1582.9
10°	1954.6	1916.4	1874.0	1825.3	1780.8	1738.5	1699.5	1661.3	1621.0	1585.6	1547.3
12.5°	2003.6	1954.2	1905.7	1844.2	1790.8	1739.0	1689.5	1641.8	1598.7	1552.7	1511.7
15°	2047.7	1999.1	1944.9	1869.8	1795.5	1732.9	1674.5	1612.7	1559.1	1507.7	1461.8
17.5°	2064.8	2013.8	1950.9	1878.7	1797.4	1718.7	1643.5	1575.7	1512.7	1452.8	1401.1
20°	2058.2	2008.8	1944.2	1875.4	1788.5	1706.5	1625.1	1550.1	1479.9	1416.6	1361.7
22.5°	2042.1	1991.0	1928.6	1855.9	1773.4	1686.5	1599.6	1519.5	1445.9	1380.5	1320.5
25°	2017.9	1948.4	1884.5	1813.5	1735.0	1648.8	1559.1	1470.8	1392.3	1325.5	1260.3
27.5°	1992.7	1905.9	1824.6	1754.2	1671.2	1594.3	1507.8	1417.3	1334.7	1266.8	1199.7
30°	1969.9	1872.6	1782.9	1703.0	1624.4	1551.5	1469.5	1381.2	1296.4	1226.2	1158.1
32.5°	1941.5	1838.1	1739.5	1647.3	1571.6	1499.2	1425.0	1340.6	1258.0	1185.5	1116.3
35°	1905.9	1773.9	1666.9	1568.9	1484.7	1414.5	1347.8	1279.7	1196.9	1121.9	1054.4
37.5°	1859.2	1709.4	1585.6	1478.7	1390.1	1319.6	1266.9	1204.6	1129.1	1057.2	994.7
40°	1830.9	1662.7	1527.1	1421.5	1328.3	1253.9	1204.6	1151.8	1083.0	1015.6	953.0
42.5°	1793.1	1619.9	1468.2	1358.1	1264.4	1192.8	1142.9	1096.7	1039.0	975.5	908.5
45°	1719.0	1536.9	1377.7	1259.5	1165.0	1094.8	1048.2	1007.2	963.4	905.0	846.6
47.5°	1622.5	1450.3	1283.7	1154.7	1062.1	996.9	951.7	919.4	888.1	838.4	781.7
50°	1545.2	1379.1	1216.4	1091.3	992.6	930.8	888.3	862.6	834.1	788.9	741.6
52.5°	1454.0	1305.6	1146.4	1018.4	925.3	867.4	826.6	800.9	777.4	740.6	695.5
55°	1310.3	1180.3	1034.3	918.2	832.8	774.4	735.4	711.1	697.2	665.9	630.4
57.5°	1144.4	1051.2	922.6	810.7	735.0	677.3	648.8	628.1	612.4	590.3	565.3
60°	1028.8	963.4	848.0	741.6	672.2	617.2	591.6	574.2	559.5	540.8	521.3
62.5°	911.4	863.9	763.5	672.2	608.2	562.2	538.1	522.5	505.6	492.9	474.0
65°	754.2	711.8	642.3	570.7	511.6	474.7	457.4	443.4	433.0	419.1	405.9
67.5°	586.7	569.4	521.5	472.1	429.7	396.9	381.9	372.2	359.6	351.3	342.2
70°	483.8	475.5	441.4	408.8	369.1	346.9	333.0	328.8	313.5	305.1	298.9
72.5°	392.6	388.7	369.1	346.4	318.5	299.0	286.2	281.5	271.8	265.1	261.1
75°	269.0	270.4	266.9	252.4	241.9	229.3	218.3	215.4	208.6	203.0	199.5
77.5°	170.1	177.3	177.5	176.8	172.6	165.1	160.4	158.4	151.5	149.5	148.6
80°	116.8	124.4	131.3	130.6	129.3	127.2	123.8	121.6	118.2	116.1	114.7
82.5°	77.8	85.0	90.8	94.5	94.3	92.2	89.8	88.8	88.1	86.6	86.3
85°	36.8	38.3	40.3	45.2	48.7	49.3	48.7	48.0	45.8	46.5	47.3
87.5°	13.6	13.5	14.0	13.8	13.2	15.8	17.4	17.8	16.8	15.8	14.8
90°	4.1	3.5	3.1	2.5	1.9	1.2	0.6	0.4	0.6	1.2	1.9
92.5°	71.9	43.1	25.9	16.7	11.2	7.3	4.6	3.8	4.6	7.3	11.2
95°	140.9	71.5	37.8	23.6	16.7	13.2	10.7	10.4	10.7	13.2	16.7
97.5°	112.4	61.6	39.3	29.2	22.9	19.4	17.7	17.3	17.7	19.4	22.9
100°	102.1	61.2	42.9	33.4	27.4	24.0	22.6	22.0	22.6	24.0	27.4
102.5°	97.8	63.4	47.2	38.0	32.5	28.7	27.7	27.4	27.7	28.7	32.5
105°	96.1	68.0	54.2	45.4	40.3	37.2	35.6	35.6	35.6	37.2	40.3
107.5°	99.0	75.0	61.6	53.7	48.4	45.8	44.3	43.7	44.3	45.8	48.4
110°	101.8	80.1	67.1	58.9	54.2	51.4	50.1	49.5	50.1	51.4	54.2





TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	105.3	84.8	72.4	64.5	59.7	56.9	55.9	55.3	55.9	56.9	59.7
115°	110.6	92.4	80.7	72.8	68.0	65.3	64.3	63.7	64.3	65.3	68.0
117.5°	116.6	100.0	89.0	81.4	76.0	73.2	72.1	71.2	72.1	73.2	76.0
120°	120.7	105.6	94.5	86.7	81.3	78.5	77.2	76.2	77.2	78.5	81.3
122.5°	125.2	110.8	99.9	91.9	86.1	83.3	82.2	81.6	82.2	83.3	86.1
125°	131.4	117.9	107.5	99.2	93.3	90.4	88.9	88.3	88.9	90.4	93.3
127.5°	137.1	124.6	114.6	106.4	100.0	96.4	94.4	93.5	94.4	96.4	100.0
130°	140.9	128.9	119.1	110.9	104.3	100.2	97.7	96.8	97.7	100.2	104.3
132.5°	144.2	133.0	123.1	114.9	108.1	103.5	100.5	99.2	100.5	103.5	108.1
135°	148.7	138.3	128.6	120.1	113.4	108.4	104.6	103.3	104.6	108.4	113.4
137.5°	152.1	142.2	133.3	124.6	118.1	113.0	109.5	108.5	109.5	113.0	118.1
140°	154.4	145.0	135.8	127.3	121.4	116.3	112.5	111.6	112.5	116.3	121.4
142.5°	155.7	146.7	138.1	130.1	124.4	119.3	115.7	115.1	115.7	119.3	124.4
145°	157.6	149.7	141.5	134.3	128.6	124.1	121.0	120.4	121.0	124.1	128.6
147.5°	158.7	151.6	144.4	138.0	133.1	129.0	126.3	125.9	126.3	129.0	133.1
150°	159.4	152.8	145.9	140.5	136.2	132.1	129.8	129.2	129.8	132.1	136.2
152.5°	160.0	154.1	147.7	142.9	138.7	135.1	133.1	132.8	133.1	135.1	138.7
155°	160.4	155.3	150.0	145.6	142.4	139.3	137.4	137.4	137.4	139.3	142.4
157.5°	160.7	156.4	151.9	148.5	145.7	143.0	141.5	141.6	141.5	143.0	145.7
160°	160.7	156.9	152.8	150.0	147.5	145.3	144.0	144.4	144.0	145.3	147.5
162.5°	160.5	157.5	153.8	151.5	149.5	147.6	146.3	146.6	146.3	147.6	149.5
165°	160.1	157.6	155.1	153.2	151.9	150.3	149.4	150.0	149.4	150.3	151.9
167.5°	159.3	157.6	155.5	154.3	153.4	152.6	151.9	152.3	151.9	152.6	153.4
170°	158.8	157.6	156.0	155.1	154.4	153.8	153.5	153.8	153.5	153.8	154.4
172.5°	158.4	157.3	156.0	155.5	155.2	154.5	154.3	154.8	154.3	154.5	155.2
175°	157.6	156.9	156.0	156.0	156.0	155.7	155.3	156.0	155.3	155.7	156.0
177.5°	156.9	156.6	156.0	156.0	156.3	156.0	156.0	156.6	156.0	156.0	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1664.9	1657.2	1651.5	1640.4	1632.6	1629.3	1623.2	1621.5	1627.6	1623.2	1622.6
5°	1615.4	1595.3	1579.3	1563.3	1545.9	1534.8	1518.1	1515.3	1511.2	1504.9	1503.5
7.5°	1556.0	1529.8	1509.2	1482.8	1459.8	1441.4	1420.5	1410.6	1405.2	1397.1	1386.3
10°	1516.0	1484.7	1457.0	1430.5	1402.0	1379.1	1358.3	1342.2	1331.8	1322.1	1317.9
12.5°	1476.5	1444.7	1409.1	1377.2	1345.3	1319.6	1296.5	1286.1	1274.5	1263.1	1253.4
15°	1415.2	1372.8	1333.9	1297.1	1270.0	1242.2	1219.9	1204.6	1187.2	1182.4	1163.6
17.5°	1350.1	1308.6	1263.0	1224.2	1192.8	1162.2	1137.7	1120.3	1107.3	1089.4	1080.8
20°	1309.6	1260.3	1215.8	1180.3	1145.5	1109.4	1084.3	1069.8	1057.2	1042.7	1035.7
22.5°	1266.2	1218.0	1172.3	1130.8	1095.5	1059.9	1042.1	1027.0	1012.7	999.3	990.1
25°	1202.6	1153.9	1105.9	1062.8	1026.0	1000.2	979.4	962.0	954.4	941.2	931.4
27.5°	1139.5	1087.8	1038.0	995.1	966.2	940.8	923.6	909.9	896.1	884.6	876.1
30°	1098.9	1046.2	991.9	957.9	927.3	902.9	884.1	870.9	860.5	850.1	843.8
32.5°	1058.4	1003.9	955.7	918.9	890.0	869.0	849.7	837.0	826.1	814.5	807.2
35°	993.3	937.7	898.8	862.6	834.1	814.7	801.5	783.4	774.4	766.0	758.3
37.5°	932.8	881.1	839.0	807.3	782.6	763.2	746.1	736.4	725.2	717.7	711.4
40°	888.3	841.1	802.8	769.5	751.4	729.9	713.9	701.3	693.0	683.3	676.4
42.5°	848.3	804.4	767.2	737.3	714.7	696.5	681.1	668.5	658.0	651.0	645.2
45°	791.8	748.0	711.8	683.9	663.2	645.8	629.7	623.5	609.6	601.3	598.5
47.5°	733.2	694.0	659.1	633.5	612.1	595.7	580.7	567.9	560.3	552.1	547.6
50°	693.8	656.2	623.5	598.5	577.7	559.5	545.6	537.3	526.9	519.2	513.7
52.5°	654.2	619.5	586.8	562.8	544.8	526.7	511.2	502.8	492.9	488.1	484.2
55°	597.8	561.0	533.2	509.5	490.7	474.0	459.5	451.1	444.9	440.0	438.6
57.5°	533.9	504.6	478.8	457.5	438.0	422.3	409.6	401.6	396.1	395.4	391.2
60°	492.1	465.7	442.1	419.1	402.4	387.9	376.7	367.7	362.1	361.4	360.1
62.5°	450.4	425.1	403.1	383.0	368.0	353.9	343.4	333.2	329.9	326.5	323.3
65°	388.5	365.6	347.6	331.5	315.6	303.7	293.4	287.0	279.5	275.3	267.6
67.5°	327.8	310.0	292.7	279.2	266.6	255.4	246.7	237.5	232.3	229.0	223.4
70°	287.8	273.8	256.5	241.9	232.2	223.1	216.2	205.7	202.2	199.5	196.7
72.5°	249.9	237.7	223.1	211.3	201.6	193.1	185.0	180.1	176.7	173.9	172.3
75°	196.7	184.9	172.4	164.1	157.1	150.2	146.0	142.5	141.1	140.4	137.6
77.5°	144.5	138.2	128.1	121.5	116.9	114.1	110.4	108.6	108.4	105.4	104.4
80°	110.5	107.0	98.7	95.9	92.5	89.7	87.6	84.1	80.6	79.3	77.1
82.5°	82.1	78.6	75.3	70.9	67.9	66.3	64.2	63.0	63.4	61.4	60.5
85°	43.8	40.3	39.0	38.3	36.8	38.3	37.5	36.8	36.1	35.5	36.1
87.5°	14.4	14.5	14.0	15.2	13.6	14.4	14.4	13.9	14.0	14.1	13.6
90°	2.5	3.1	3.5	4.1	4.4	5.1	5.4	5.7	6.0	6.3	7.0
92.5°	16.7	25.9	43.1	71.9	103.3	101.6	82.2	55.8	40.5	30.5	25.9
95°	23.6	37.8	71.5	140.9	227.8	279.2	273.2	226.6	178.7	139.9	113.4
97.5°	29.2	39.3	61.6	112.4	203.5	298.2	345.7	337.4	303.9	266.1	229.3
100°	33.4	42.9	61.2	102.1	181.6	284.5	363.4	387.6	372.2	339.7	306.9
102.5°	38.0	47.2	63.4	97.8	164.9	260.6	352.8	404.5	414.0	398.5	376.3
105°	45.4	54.2	68.0	96.1	148.7	228.5	319.0	394.6	437.7	451.6	448.2
107.5°	53.7	61.6	75.0	99.0	142.0	206.3	284.4	359.0	416.6	452.2	468.7
110°	58.9	67.1	80.1	101.8	139.9	196.0	264.7	332.8	392.7	437.1	463.9



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	64.5	72.4	84.8	105.3	139.9	189.9	250.1	312.1	369.0	413.9	445.5
115°	72.8	80.7	92.4	110.6	140.9	183.4	234.2	286.1	335.0	378.2	412.5
117.5°	81.4	89.0	100.0	116.6	142.9	180.2	224.6	269.4	311.5	348.7	380.2
120°	86.7	94.5	105.6	120.7	145.0	178.7	219.4	260.3	298.1	332.8	360.5
122.5°	91.9	99.9	110.8	125.2	146.7	177.5	214.8	253.5	288.6	319.4	345.4
125°	99.2	107.5	117.9	131.4	149.7	175.8	208.7	243.6	275.7	303.2	325.8
127.5°	106.4	114.6	124.6	137.1	153.0	175.1	203.0	233.5	263.5	289.1	310.3
130°	110.9	119.1	128.9	140.9	155.1	174.6	199.2	227.2	254.9	279.6	300.1
132.5°	114.9	123.1	133.0	144.2	157.3	174.6	196.2	220.9	246.9	269.2	288.9
135°	120.1	128.6	138.3	148.7	160.4	174.6	192.5	212.8	234.4	254.7	272.6
137.5°	124.6	133.3	142.2	152.1	163.3	175.0	189.3	205.8	223.4	240.1	255.4
140°	127.3	135.8	145.0	154.4	164.5	175.2	187.8	202.0	216.8	231.3	244.5
142.5°	130.1	138.1	146.7	155.7	165.2	175.5	186.5	198.8	211.2	223.7	235.2
145°	134.3	141.5	149.7	157.6	166.0	175.2	184.7	194.5	204.2	214.0	222.5
147.5°	138.0	144.4	151.6	158.7	166.4	174.4	182.7	190.4	198.3	205.9	212.3
150°	140.5	145.9	152.8	159.4	166.4	173.6	181.2	188.2	195.1	201.1	206.7
152.5°	142.9	147.7	154.1	160.0	166.1	172.6	179.4	185.7	191.8	197.2	201.7
155°	145.6	150.0	155.3	160.4	165.4	170.9	176.5	181.8	186.9	191.3	194.7
157.5°	148.5	151.9	156.4	160.7	164.6	168.9	173.7	178.1	182.2	185.7	188.3
160°	150.0	152.8	156.9	160.7	163.9	167.6	171.5	175.6	178.7	181.8	184.0
162.5°	151.5	153.8	157.5	160.5	163.1	166.1	169.4	172.7	175.7	178.3	180.3
165°	153.2	155.1	157.6	160.1	162.0	163.9	166.4	168.9	171.1	173.0	174.6
167.5°	154.3	155.5	157.6	159.3	160.2	161.7	163.5	165.2	166.7	168.2	169.3
170°	155.1	156.0	157.6	158.8	159.4	160.4	161.7	163.3	164.2	165.1	165.8
172.5°	155.5	156.0	157.3	158.4	158.5	158.9	159.9	161.0	161.9	162.6	163.0
175°	156.0	156.0	156.9	157.6	157.3	157.3	157.6	158.5	158.5	159.2	159.2
177.5°	156.0	156.0	156.6	156.9	156.3	156.3	156.6	156.9	157.0	157.0	157.0
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1622.1	1616.0	1614.3	1616.5	1614.3	1616.0	1622.1	1622.6	1623.2	1627.6	1621.5
5°	1496.6	1489.6	1493.1	1491.7	1493.1	1489.6	1496.6	1503.5	1504.9	1511.2	1515.3
7.5°	1386.2	1377.5	1368.3	1371.3	1368.3	1377.5	1386.2	1386.3	1397.1	1405.2	1410.6
10°	1308.9	1301.9	1297.7	1301.2	1297.7	1301.9	1308.9	1317.9	1322.1	1331.8	1342.2
12.5°	1243.8	1239.7	1236.0	1234.5	1236.0	1239.7	1243.8	1253.4	1263.1	1274.5	1286.1
15°	1155.2	1146.9	1143.4	1134.4	1143.4	1146.9	1155.2	1163.6	1182.4	1187.2	1204.6
17.5°	1073.6	1070.9	1061.8	1057.9	1061.8	1070.9	1073.6	1080.8	1089.4	1107.3	1120.3
20°	1025.3	1022.5	1013.4	1019.0	1013.4	1022.5	1025.3	1035.7	1042.7	1057.2	1069.8
22.5°	985.3	979.1	976.2	974.6	976.2	979.1	985.3	990.1	999.3	1012.7	1027.0
25°	928.6	919.6	916.1	912.0	916.1	919.6	928.6	931.4	941.2	954.4	962.0
27.5°	872.2	867.4	862.7	861.7	862.7	867.4	872.2	876.1	884.6	896.1	909.9
30°	835.5	830.6	827.2	827.2	827.2	830.6	835.5	843.8	850.1	860.5	870.9
32.5°	802.7	799.0	795.5	795.0	795.5	799.0	802.7	807.2	814.5	826.1	837.0
35°	754.9	749.3	748.0	743.8	748.0	749.3	754.9	758.3	766.0	774.4	783.4
37.5°	705.3	700.6	700.5	700.1	700.5	700.6	705.3	711.4	717.7	725.2	736.4
40°	673.5	670.0	669.4	664.5	669.4	670.0	673.5	676.4	683.3	693.0	701.3
42.5°	639.6	637.8	635.4	633.4	635.4	637.8	639.6	645.2	651.0	658.0	668.5
45°	593.6	588.7	588.7	585.2	588.7	588.7	593.6	598.5	601.3	609.6	623.5
47.5°	546.1	542.3	542.7	539.1	542.7	542.3	546.1	547.6	552.1	560.3	567.9
50°	514.3	512.3	511.6	510.2	511.6	512.3	514.3	513.7	519.2	526.9	537.3
52.5°	482.7	481.7	484.4	481.3	484.4	481.7	482.7	484.2	488.1	492.9	502.8
55°	440.0	437.9	442.1	437.9	442.1	437.9	440.0	438.6	440.0	444.9	451.1
57.5°	390.9	389.0	392.7	390.7	392.7	389.0	390.9	391.2	395.4	396.1	401.6
60°	358.6	354.5	356.6	357.3	356.6	354.5	358.6	360.1	361.4	362.1	367.7
62.5°	320.3	317.8	319.3	316.1	319.3	317.8	320.3	323.3	326.5	329.9	333.2
65°	266.3	264.1	261.4	259.9	261.4	264.1	266.3	267.6	275.3	279.5	287.0
67.5°	223.6	218.6	218.6	219.6	218.6	218.6	223.6	223.4	229.0	232.3	237.5
70°	192.5	192.5	191.8	191.8	191.8	192.5	192.5	196.7	199.5	202.2	205.7
72.5°	170.9	170.3	169.1	168.5	169.1	170.3	170.9	172.3	173.9	176.7	180.1
75°	137.6	138.3	137.0	136.3	137.0	138.3	137.6	137.6	140.4	141.1	142.5
77.5°	101.7	98.7	100.2	98.7	100.2	98.7	101.7	104.4	105.4	108.4	108.6
80°	77.1	76.4	78.6	76.4	78.6	76.4	77.1	77.1	79.3	80.6	84.1
82.5°	61.0	60.4	61.3	59.7	61.3	60.4	61.0	60.5	61.4	63.4	63.0
85°	36.8	36.1	35.5	36.1	35.5	36.1	36.8	36.1	35.5	36.1	36.8
87.5°	14.2	13.6	13.6	13.6	13.6	13.6	14.2	13.6	14.1	14.0	13.9
90°	7.0	7.0	7.2	7.2	7.2	7.0	7.0	7.0	6.3	6.0	5.7
92.5°	21.8	21.0	20.6	20.1	20.6	21.0	21.8	25.9	30.5	40.5	55.8
95°	91.0	81.6	79.1	74.1	79.1	81.6	91.0	113.4	139.9	178.7	226.6
97.5°	209.8	192.2	183.1	179.0	183.1	192.2	209.8	229.3	266.1	303.9	337.4
100°	285.2	262.5	250.8	245.8	250.8	262.5	285.2	306.9	339.7	372.2	387.6
102.5°	353.0	336.9	324.2	320.5	324.2	336.9	353.0	376.3	398.5	414.0	404.5
105°	438.0	427.7	421.3	417.6	421.3	427.7	438.0	448.2	451.6	437.7	394.6
107.5°	473.8	473.8	471.6	469.1	471.6	473.8	473.8	468.7	452.2	416.6	359.0
110°	478.0	484.0	486.2	486.2	486.2	484.0	478.0	463.9	437.1	392.7	332.8



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	466.2	476.5	482.0	484.3	482.0	476.5	466.2	445.5	413.9	369.0	312.1
115°	437.1	452.2	461.0	465.1	461.0	452.2	437.1	412.5	378.2	335.0	286.1
117.5°	404.7	420.4	429.2	431.7	429.2	420.4	404.7	380.2	348.7	311.5	269.4
120°	383.9	399.0	407.5	410.0	407.5	399.0	383.9	360.5	332.8	298.1	260.3
122.5°	366.2	380.0	388.6	390.8	388.6	380.0	366.2	345.4	319.4	288.6	253.5
125°	343.5	356.4	363.4	366.5	363.4	356.4	343.5	325.8	303.2	275.7	243.6
127.5°	326.4	337.8	344.3	345.7	344.3	337.8	326.4	310.3	289.1	263.5	233.5
130°	315.8	326.2	332.5	334.4	332.5	326.2	315.8	300.1	279.6	254.9	227.2
132.5°	304.7	315.0	320.8	323.0	320.8	315.0	304.7	288.9	269.2	246.9	220.9
135°	286.5	296.9	302.6	304.4	302.6	296.9	286.5	272.6	254.7	234.4	212.8
137.5°	267.8	277.2	282.5	284.5	282.5	277.2	267.8	255.4	240.1	223.4	205.8
140°	256.2	264.4	269.1	270.7	269.1	264.4	256.2	244.5	231.3	216.8	202.0
142.5°	245.1	252.1	256.5	257.9	256.5	252.1	245.1	235.2	223.7	211.2	198.8
145°	230.1	235.4	238.9	240.1	238.9	235.4	230.1	222.5	214.0	204.2	194.5
147.5°	218.3	222.6	224.5	225.2	224.5	222.6	218.3	212.3	205.9	198.3	190.4
150°	211.4	215.3	216.5	216.8	216.5	215.3	211.4	206.7	201.1	195.1	188.2
152.5°	205.6	208.7	209.9	210.3	209.9	208.7	205.6	201.7	197.2	191.8	185.7
155°	197.9	200.1	201.1	201.3	201.1	200.1	197.9	194.7	191.3	186.9	181.8
157.5°	190.8	192.6	193.5	193.4	193.5	192.6	190.8	188.3	185.7	182.2	178.1
160°	186.3	187.8	188.4	188.2	188.4	187.8	186.3	184.0	181.8	178.7	175.6
162.5°	182.0	183.2	183.4	183.3	183.4	183.2	182.0	180.3	178.3	175.7	172.7
165°	175.8	176.5	176.5	176.5	176.5	176.5	175.8	174.6	173.0	171.1	168.9
167.5°	170.0	170.5	170.2	170.1	170.2	170.5	170.0	169.3	168.2	166.7	165.2
170°	166.4	166.7	166.7	166.4	166.7	166.7	166.4	165.8	165.1	164.2	163.3
172.5°	163.1	163.7	163.2	162.8	163.2	163.7	163.1	163.0	162.6	161.9	161.0
175°	159.2	159.4	158.8	158.5	158.8	159.4	159.2	159.2	159.2	158.5	158.5
177.5°	156.9	157.0	156.3	156.3	156.3	157.0	156.9	157.0	157.0	157.0	156.9
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1623.2	1629.3	1632.6	1640.4	1651.5	1657.2	1664.9	1670.4	1678.3	1687.7	1695.5
5°	1518.1	1534.8	1545.9	1563.3	1579.3	1595.3	1615.4	1630.0	1649.5	1671.7	1689.1
7.5°	1420.5	1441.4	1459.8	1482.8	1509.2	1529.8	1556.0	1582.9	1613.3	1644.8	1674.6
10°	1358.3	1379.1	1402.0	1430.5	1457.0	1484.7	1516.0	1547.3	1585.6	1621.0	1661.3
12.5°	1296.5	1319.6	1345.3	1377.2	1409.1	1444.7	1476.5	1511.7	1552.7	1598.7	1641.8
15°	1219.9	1242.2	1270.0	1297.1	1333.9	1372.8	1415.2	1461.8	1507.7	1559.1	1612.7
17.5°	1137.7	1162.2	1192.8	1224.2	1263.0	1308.6	1350.1	1401.1	1452.8	1512.7	1575.7
20°	1084.3	1109.4	1145.5	1180.3	1215.8	1260.3	1309.6	1361.7	1416.6	1479.9	1550.1
22.5°	1042.1	1059.9	1095.5	1130.8	1172.3	1218.0	1266.2	1320.5	1380.5	1445.9	1519.5
25°	979.4	1000.2	1026.0	1062.8	1105.9	1153.9	1202.6	1260.3	1325.5	1392.3	1470.8
27.5°	923.6	940.8	966.2	995.1	1038.0	1087.8	1139.5	1199.7	1266.8	1334.7	1417.3
30°	884.1	902.9	927.3	957.9	991.9	1046.2	1098.9	1158.1	1226.2	1296.4	1381.2
32.5°	849.7	869.0	890.0	918.9	955.7	1003.9	1058.4	1116.3	1185.5	1258.0	1340.6
35°	801.5	814.7	834.1	862.6	898.8	937.7	993.3	1054.4	1121.9	1196.9	1279.7
37.5°	746.1	763.2	782.6	807.3	839.0	881.1	932.8	994.7	1057.2	1129.1	1204.6
40°	713.9	729.9	751.4	769.5	802.8	841.1	888.3	953.0	1015.6	1083.0	1151.8
42.5°	681.1	696.5	714.7	737.3	767.2	804.4	848.3	908.5	975.5	1039.0	1096.7
45°	629.7	645.8	663.2	683.9	711.8	748.0	791.8	846.6	905.0	963.4	1007.2
47.5°	580.7	595.7	612.1	633.5	659.1	694.0	733.2	781.7	838.4	888.1	919.4
50°	545.6	559.5	577.7	598.5	623.5	656.2	693.8	741.6	788.9	834.1	862.6
52.5°	511.2	526.7	544.8	562.8	586.8	619.5	654.2	695.5	740.6	777.4	800.9
55°	459.5	474.0	490.7	509.5	533.2	561.0	597.8	630.4	665.9	697.2	711.1
57.5°	409.6	422.3	438.0	457.5	478.8	504.6	533.9	565.3	590.3	612.4	628.1
60°	376.7	387.9	402.4	419.1	442.1	465.7	492.1	521.3	540.8	559.5	574.2
62.5°	343.4	353.9	368.0	383.0	403.1	425.1	450.4	474.0	492.9	505.6	522.5
65°	293.4	303.7	315.6	331.5	347.6	365.6	388.5	405.9	419.1	433.0	443.4
67.5°	246.7	255.4	266.6	279.2	292.7	310.0	327.8	342.2	351.3	359.6	372.2
70°	216.2	223.1	232.2	241.9	256.5	273.8	287.8	298.9	305.1	313.5	328.8
72.5°	185.0	193.1	201.6	211.3	223.1	237.7	249.9	261.1	265.1	271.8	281.5
75°	146.0	150.2	157.1	164.1	172.4	184.9	196.7	199.5	203.0	208.6	215.4
77.5°	110.4	114.1	116.9	121.5	128.1	138.2	144.5	148.6	149.5	151.5	158.4
80°	87.6	89.7	92.5	95.9	98.7	107.0	110.5	114.7	116.1	118.2	121.6
82.5°	64.2	66.3	67.9	70.9	75.3	78.6	82.1	86.3	86.6	88.1	88.8
85°	37.5	38.3	36.8	38.3	39.0	40.3	43.8	47.3	46.5	45.8	48.0
87.5°	14.4	14.4	13.6	15.2	14.0	14.5	14.4	14.8	15.8	16.8	17.8
90°	5.4	5.1	4.4	4.1	3.5	3.1	2.5	1.9	1.2	0.6	0.4
92.5°	82.2	101.6	103.3	71.9	43.1	25.9	16.7	11.2	7.3	4.6	3.8
95°	273.2	279.2	227.8	140.9	71.5	37.8	23.6	16.7	13.2	10.7	10.4
97.5°	345.7	298.2	203.5	112.4	61.6	39.3	29.2	22.9	19.4	17.7	17.3
100°	363.4	284.5	181.6	102.1	61.2	42.9	33.4	27.4	24.0	22.6	22.0
102.5°	352.8	260.6	164.9	97.8	63.4	47.2	38.0	32.5	28.7	27.7	27.4
105°	319.0	228.5	148.7	96.1	68.0	54.2	45.4	40.3	37.2	35.6	35.6
107.5°	284.4	206.3	142.0	99.0	75.0	61.6	53.7	48.4	45.8	44.3	43.7
110°	264.7	196.0	139.9	101.8	80.1	67.1	58.9	54.2	51.4	50.1	49.5



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	250.1	189.9	139.9	105.3	84.8	72.4	64.5	59.7	56.9	55.9	55.3
115°	234.2	183.4	140.9	110.6	92.4	80.7	72.8	68.0	65.3	64.3	63.7
117.5°	224.6	180.2	142.9	116.6	100.0	89.0	81.4	76.0	73.2	72.1	71.2
120°	219.4	178.7	145.0	120.7	105.6	94.5	86.7	81.3	78.5	77.2	76.2
122.5°	214.8	177.5	146.7	125.2	110.8	99.9	91.9	86.1	83.3	82.2	81.6
125°	208.7	175.8	149.7	131.4	117.9	107.5	99.2	93.3	90.4	88.9	88.3
127.5°	203.0	175.1	153.0	137.1	124.6	114.6	106.4	100.0	96.4	94.4	93.5
130°	199.2	174.6	155.1	140.9	128.9	119.1	110.9	104.3	100.2	97.7	96.8
132.5°	196.2	174.6	157.3	144.2	133.0	123.1	114.9	108.1	103.5	100.5	99.2
135°	192.5	174.6	160.4	148.7	138.3	128.6	120.1	113.4	108.4	104.6	103.3
137.5°	189.3	175.0	163.3	152.1	142.2	133.3	124.6	118.1	113.0	109.5	108.5
140°	187.8	175.2	164.5	154.4	145.0	135.8	127.3	121.4	116.3	112.5	111.6
142.5°	186.5	175.5	165.2	155.7	146.7	138.1	130.1	124.4	119.3	115.7	115.1
145°	184.7	175.2	166.0	157.6	149.7	141.5	134.3	128.6	124.1	121.0	120.4
147.5°	182.7	174.4	166.4	158.7	151.6	144.4	138.0	133.1	129.0	126.3	125.9
150°	181.2	173.6	166.4	159.4	152.8	145.9	140.5	136.2	132.1	129.8	129.2
152.5°	179.4	172.6	166.1	160.0	154.1	147.7	142.9	138.7	135.1	133.1	132.8
155°	176.5	170.9	165.4	160.4	155.3	150.0	145.6	142.4	139.3	137.4	137.4
157.5°	173.7	168.9	164.6	160.7	156.4	151.9	148.5	145.7	143.0	141.5	141.6
160°	171.5	167.6	163.9	160.7	156.9	152.8	150.0	147.5	145.3	144.0	144.4
162.5°	169.4	166.1	163.1	160.5	157.5	153.8	151.5	149.5	147.6	146.3	146.6
165°	166.4	163.9	162.0	160.1	157.6	155.1	153.2	151.9	150.3	149.4	150.0
167.5°	163.5	161.7	160.2	159.3	157.6	155.5	154.3	153.4	152.6	151.9	152.3
170°	161.7	160.4	159.4	158.8	157.6	156.0	155.1	154.4	153.8	153.5	153.8
172.5°	159.9	158.9	158.5	158.4	157.3	156.0	155.5	155.2	154.5	154.3	154.8
175°	157.6	157.3	157.3	157.6	156.9	156.0	156.0	156.0	155.7	155.3	156.0
177.5°	156.6	156.3	156.3	156.9	156.6	156.0	156.0	156.3	156.0	156.0	156.6
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1701.6	1706.6	1713.9	1722.2	1728.8	1736.1	1740.0	1740.0	1743.3	1750.5	1760.0
5°	1706.5	1724.6	1742.0	1764.2	1781.5	1801.7	1816.9	1831.6	1844.8	1861.4	1878.8
7.5°	1705.0	1735.1	1766.4	1801.4	1840.0	1870.8	1902.4	1927.1	1951.6	1983.5	2008.7
10°	1699.5	1738.5	1780.8	1825.3	1874.0	1916.4	1954.6	1989.4	2022.8	2057.5	2088.7
12.5°	1689.5	1739.0	1790.8	1844.2	1905.7	1954.2	2003.6	2040.5	2079.5	2117.5	2156.1
15°	1674.5	1732.9	1795.5	1869.8	1944.9	1999.1	2047.7	2095.7	2131.9	2175.0	2211.8
17.5°	1643.5	1718.7	1797.4	1878.7	1950.9	2013.8	2064.8	2110.5	2148.9	2196.4	2246.4
20°	1625.1	1706.5	1788.5	1875.4	1944.2	2008.8	2058.2	2105.4	2153.4	2215.3	2276.4
22.5°	1599.6	1686.5	1773.4	1855.9	1928.6	1991.0	2042.1	2099.9	2162.8	2233.1	2307.0
25°	1559.1	1648.8	1735.0	1813.5	1884.5	1948.4	2017.9	2095.7	2172.2	2264.7	2371.0
27.5°	1507.8	1594.3	1671.2	1754.2	1824.6	1905.9	1992.7	2077.1	2187.4	2314.5	2447.3
30°	1469.5	1551.5	1624.4	1703.0	1782.9	1872.6	1969.9	2069.3	2200.7	2350.1	2507.9
32.5°	1425.0	1499.2	1571.6	1647.3	1739.5	1838.1	1941.5	2063.2	2220.2	2390.1	2553.5
35°	1347.8	1414.5	1484.7	1568.9	1666.9	1773.9	1905.9	2054.1	2243.8	2426.6	2573.3
37.5°	1266.9	1319.6	1390.1	1478.7	1585.6	1709.4	1859.2	2039.2	2234.1	2398.1	2460.5
40°	1204.6	1253.9	1328.3	1421.5	1527.1	1662.7	1830.9	2015.8	2211.8	2325.8	2320.9
42.5°	1142.9	1192.8	1264.4	1358.1	1468.2	1619.9	1793.1	1985.2	2150.6	2194.1	2103.5
45°	1048.2	1094.8	1165.0	1259.5	1377.7	1536.9	1719.0	1903.2	2008.8	1938.7	1759.3
47.5°	951.7	996.9	1062.1	1154.7	1283.7	1450.3	1622.5	1773.6	1788.5	1637.6	1422.5
50°	888.3	930.8	992.6	1091.3	1216.4	1379.1	1545.2	1664.1	1627.2	1443.1	1221.3
52.5°	826.6	867.4	925.3	1018.4	1146.4	1305.6	1454.0	1547.3	1462.0	1266.2	1066.7
55°	735.4	774.4	832.8	918.2	1034.3	1180.3	1310.3	1344.3	1219.2	1021.8	860.5
57.5°	648.8	677.3	735.0	810.7	922.6	1051.2	1144.4	1138.3	1000.2	822.4	706.8
60°	591.6	617.2	672.2	741.6	848.0	963.4	1028.8	1000.9	861.2	714.5	603.3
62.5°	538.1	562.2	608.2	672.2	763.5	863.9	911.4	873.1	741.1	612.2	523.8
65°	457.4	474.7	511.6	570.7	642.3	711.8	754.2	697.9	581.1	483.8	417.1
67.5°	381.9	396.9	429.7	472.1	521.5	569.4	586.7	533.9	443.1	377.5	330.5
70°	333.0	346.9	369.1	408.8	441.4	475.5	483.8	436.5	360.8	310.7	281.5
72.5°	286.2	299.0	318.5	346.4	369.1	388.7	392.6	348.7	290.7	256.2	233.7
75°	218.3	229.3	241.9	252.4	266.9	270.4	269.0	235.0	203.7	180.7	168.2
77.5°	160.4	165.1	172.6	176.8	177.5	177.3	170.1	148.6	132.5	123.1	117.9
80°	123.8	127.2	129.3	130.6	131.3	124.4	116.8	103.5	98.0	92.5	86.2
82.5°	89.8	92.2	94.3	94.5	90.8	85.0	77.8	71.3	67.4	64.6	62.2
85°	48.7	49.3	48.7	45.2	40.3	38.3	36.8	35.5	34.8	34.1	34.1
87.5°	17.4	15.8	13.2	13.8	14.0	13.5	13.6	13.1	12.7	12.8	12.8
90°	0.6	1.2	1.9	2.5	3.1	3.5	4.1	4.4	5.1	5.4	5.7
92.5°	4.6	7.3	11.2	16.7	25.9	43.1	71.9	103.3	101.6	82.2	55.8
95°	10.7	13.2	16.7	23.6	37.8	71.5	140.9	227.8	279.2	273.2	226.6
97.5°	17.7	19.4	22.9	29.2	39.3	61.6	112.4	203.5	298.2	345.7	337.4
100°	22.6	24.0	27.4	33.4	42.9	61.2	102.1	181.6	284.5	363.4	387.6
102.5°	27.7	28.7	32.5	38.0	47.2	63.4	97.8	164.9	260.6	352.8	404.5
105°	35.6	37.2	40.3	45.4	54.2	68.0	96.1	148.7	228.5	319.0	394.6
107.5°	44.3	45.8	48.4	53.7	61.6	75.0	99.0	142.0	206.3	284.4	359.0
110°	50.1	51.4	54.2	58.9	67.1	80.1	101.8	139.9	196.0	264.7	332.8





TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.9	56.9	59.7	64.5	72.4	84.8	105.3	139.9	189.9	250.1	312.1
115°	64.3	65.3	68.0	72.8	80.7	92.4	110.6	140.9	183.4	234.2	286.1
117.5°	72.1	73.2	76.0	81.4	89.0	100.0	116.6	142.9	180.2	224.6	269.4
120°	77.2	78.5	81.3	86.7	94.5	105.6	120.7	145.0	178.7	219.4	260.3
122.5°	82.2	83.3	86.1	91.9	99.9	110.8	125.2	146.7	177.5	214.8	253.5
125°	88.9	90.4	93.3	99.2	107.5	117.9	131.4	149.7	175.8	208.7	243.6
127.5°	94.4	96.4	100.0	106.4	114.6	124.6	137.1	153.0	175.1	203.0	233.5
130°	97.7	100.2	104.3	110.9	119.1	128.9	140.9	155.1	174.6	199.2	227.2
132.5°	100.5	103.5	108.1	114.9	123.1	133.0	144.2	157.3	174.6	196.2	220.9
135°	104.6	108.4	113.4	120.1	128.6	138.3	148.7	160.4	174.6	192.5	212.8
137.5°	109.5	113.0	118.1	124.6	133.3	142.2	152.1	163.3	175.0	189.3	205.8
140°	112.5	116.3	121.4	127.3	135.8	145.0	154.4	164.5	175.2	187.8	202.0
142.5°	115.7	119.3	124.4	130.1	138.1	146.7	155.7	165.2	175.5	186.5	198.8
145°	121.0	124.1	128.6	134.3	141.5	149.7	157.6	166.0	175.2	184.7	194.5
147.5°	126.3	129.0	133.1	138.0	144.4	151.6	158.7	166.4	174.4	182.7	190.4
150°	129.8	132.1	136.2	140.5	145.9	152.8	159.4	166.4	173.6	181.2	188.2
152.5°	133.1	135.1	138.7	142.9	147.7	154.1	160.0	166.1	172.6	179.4	185.7
155°	137.4	139.3	142.4	145.6	150.0	155.3	160.4	165.4	170.9	176.5	181.8
157.5°	141.5	143.0	145.7	148.5	151.9	156.4	160.7	164.6	168.9	173.7	178.1
160°	144.0	145.3	147.5	150.0	152.8	156.9	160.7	163.9	167.6	171.5	175.6
162.5°	146.3	147.6	149.5	151.5	153.8	157.5	160.5	163.1	166.1	169.4	172.7
165°	149.4	150.3	151.9	153.2	155.1	157.6	160.1	162.0	163.9	166.4	168.9
167.5°	151.9	152.6	153.4	154.3	155.5	157.6	159.3	160.2	161.7	163.5	165.2
170°	153.5	153.8	154.4	155.1	156.0	157.6	158.8	159.4	160.4	161.7	163.3
172.5°	154.3	154.5	155.2	155.5	156.0	157.3	158.4	158.5	158.9	159.9	161.0
175°	155.3	155.7	156.0	156.0	156.0	156.9	157.6	157.3	157.3	157.6	158.5
177.5°	156.0	156.0	156.3	156.0	156.0	156.6	156.9	156.3	156.3	156.6	156.9
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1767.2	1767.2	1776.6	1776.1	1782.3	1780.0	1781.1
5°	1899.7	1911.6	1922.0	1928.9	1939.3	1942.1	1940.7
7.5°	2037.0	2063.3	2076.1	2093.6	2096.9	2106.0	2105.1
10°	2122.2	2147.9	2167.3	2182.6	2190.2	2200.0	2200.7
12.5°	2188.9	2210.7	2227.9	2242.1	2251.4	2254.5	2256.3
15°	2241.0	2265.3	2285.5	2305.6	2317.5	2326.5	2331.4
17.5°	2293.6	2331.1	2366.7	2394.1	2410.5	2424.4	2424.2
20°	2334.1	2377.2	2421.7	2453.0	2485.0	2498.8	2501.0
22.5°	2377.5	2443.4	2500.7	2549.2	2591.2	2605.7	2611.1
25°	2467.6	2553.8	2642.0	2710.2	2758.9	2787.3	2791.5
27.5°	2576.4	2693.1	2786.0	2848.8	2889.2	2910.4	2915.0
30°	2653.2	2760.9	2844.4	2891.6	2910.4	2913.1	2902.7
32.5°	2687.7	2768.1	2801.5	2798.7	2761.9	2737.5	2728.1
35°	2645.5	2628.9	2547.5	2450.2	2375.9	2328.6	2316.0
37.5°	2407.5	2263.7	2114.1	1967.0	1888.7	1849.0	1780.6
40°	2172.9	1967.8	1812.1	1688.4	1600.1	1529.2	1512.5
42.5°	1908.2	1696.5	1540.8	1434.9	1364.3	1315.7	1294.6
45°	1533.4	1351.3	1222.7	1141.4	1087.2	1051.7	1035.7
47.5°	1226.5	1085.5	991.8	931.6	890.3	859.4	850.8
50°	1057.9	945.3	866.1	815.4	784.1	760.5	750.7
52.5°	918.9	828.0	767.1	725.2	695.6	680.9	672.9
55°	758.3	679.8	636.1	602.6	585.9	574.2	568.6
57.5°	620.2	563.5	531.5	508.4	492.9	485.4	482.7
60°	542.9	498.4	469.2	451.1	440.7	431.0	428.2
62.5°	474.5	439.4	417.0	401.1	390.7	386.5	384.8
65°	382.3	359.4	342.7	333.0	324.6	323.2	322.5
67.5°	303.9	290.4	281.7	271.5	268.6	263.7	262.8
70°	259.9	250.9	240.5	237.0	233.5	228.7	229.3
72.5°	220.5	211.4	204.4	199.7	198.5	196.4	198.2
75°	161.2	158.5	155.7	152.2	150.9	150.9	150.2
77.5°	115.1	112.7	109.7	107.6	107.2	104.2	105.4
80°	83.4	79.9	78.6	79.3	77.1	76.4	76.4
82.5°	61.7	60.5	59.1	59.2	58.8	58.1	58.7
85°	34.1	33.3	33.3	32.6	32.6	32.0	32.0
87.5°	13.5	14.1	13.1	12.5	12.5	13.1	13.6
90°	6.0	6.3	7.0	7.0	7.0	7.2	7.2
92.5°	40.5	30.5	25.9	21.8	21.0	20.6	20.1
95°	178.7	139.9	113.4	91.0	81.6	79.1	74.1
97.5°	303.9	266.1	229.3	209.8	192.2	183.1	179.0
100°	372.2	339.7	306.9	285.2	262.5	250.8	245.8
102.5°	414.0	398.5	376.3	353.0	336.9	324.2	320.5
105°	437.7	451.6	448.2	438.0	427.7	421.3	417.6
107.5°	416.6	452.2	468.7	473.8	473.8	471.6	469.1
110°	392.7	437.1	463.9	478.0	484.0	486.2	486.2



TEST NUMBER: P333612-940

CATALOG NUMBER: S125RDIP-S1270D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	369.0	413.9	445.5	466.2	476.5	482.0	484.3
115°	335.0	378.2	412.5	437.1	452.2	461.0	465.1
117.5°	311.5	348.7	380.2	404.7	420.4	429.2	431.7
120°	298.1	332.8	360.5	383.9	399.0	407.5	410.0
122.5°	288.6	319.4	345.4	366.2	380.0	388.6	390.8
125°	275.7	303.2	325.8	343.5	356.4	363.4	366.5
127.5°	263.5	289.1	310.3	326.4	337.8	344.3	345.7
130°	254.9	279.6	300.1	315.8	326.2	332.5	334.4
132.5°	246.9	269.2	288.9	304.7	315.0	320.8	323.0
135°	234.4	254.7	272.6	286.5	296.9	302.6	304.4
137.5°	223.4	240.1	255.4	267.8	277.2	282.5	284.5
140°	216.8	231.3	244.5	256.2	264.4	269.1	270.7
142.5°	211.2	223.7	235.2	245.1	252.1	256.5	257.9
145°	204.2	214.0	222.5	230.1	235.4	238.9	240.1
147.5°	198.3	205.9	212.3	218.3	222.6	224.5	225.2
150°	195.1	201.1	206.7	211.4	215.3	216.5	216.8
152.5°	191.8	197.2	201.7	205.6	208.7	209.9	210.3
155°	186.9	191.3	194.7	197.9	200.1	201.1	201.3
157.5°	182.2	185.7	188.3	190.8	192.6	193.5	193.4
160°	178.7	181.8	184.0	186.3	187.8	188.4	188.2
162.5°	175.7	178.3	180.3	182.0	183.2	183.4	183.3
165°	171.1	173.0	174.6	175.8	176.5	176.5	176.5
167.5°	166.7	168.2	169.3	170.0	170.5	170.2	170.1
170°	164.2	165.1	165.8	166.4	166.7	166.7	166.4
172.5°	161.9	162.6	163.0	163.1	163.7	163.2	162.8
175°	158.5	159.2	159.2	159.2	159.4	158.8	158.5
177.5°	157.0	157.0	157.0	156.9	157.0	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3

(END OF REPORT)