

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333627-940

Luminaire Tested: **S125RDIP-S1270D810U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333627-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D810U940-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6943.9 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333627-940

CATALOG NUMBER: S125RDIP-S1270D810U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333627-940

CATALOG NUMBER: S125RDIP-S1270D810U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90		79	79	79		68	68	68	63
1	101	97	93	89	94	91	87	84	80	77	75		70	68	66		60	59	58	53
2	92	85	79	73	86	80	74	70	70	66	62		61	58	56		53	51	49	45
3	84	75	67	61	79	70	64	59	62	57	53		55	51	47		48	45	42	38
4	77	66	58	52	72	63	55	50	55	50	45		49	44	41		43	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39		44	39	36		39	35	32	29
6	66	53	45	39	61	50	43	38	45	39	34		40	35	31		35	31	28	26
7	61	48	40	35	57	46	38	33	41	35	31		36	31	28		32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27		33	28	25		30	26	23	20
9	53	40	33	28	49	38	31	27	34	29	25		31	26	22		27	23	21	18
10	49	37	30	25	46	35	28	24	32	26	22		28	24	20		25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11889	11889	11889
5°	11916	11780	11852
10°	11825	11671	11671
15°	11685	11433	11340
20°	11504	11103	10970
25°	11294	10779	10541
30°	11032	10399	10068
35°	10764	10008	9536
40°	10514	9599	9014
45°	10209	9143	8444
50°	9904	8647	7850
55°	9549	8172	7218
60°	9195	7596	6536
65°	8775	6927	5757
70°	8295	6090	4962
75°	7633	5133	4127
80°	6721	4032	3466
85°	5669	3298	3090



TEST NUMBER: P333627-940

CATALOG NUMBER: S125RDIP-S1270D810U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	2.5
10°-20°	483.7	7.0
20°-30°	701.4	10.1
30°-40°	799.4	11.5
40°-50°	779.2	11.2
50°-60°	655.9	9.4
60°-70°	459.8	6.6
70°-80°	236.3	3.4
80°-90°	61.6	0.9
90°-100°	250.7	3.6
100°-110°	538.9	7.8
110°-120°	505.7	7.3
120°-130°	409.8	5.9
130°-140°	328.9	4.7
140°-150°	248.2	3.6
150°-160°	174.7	2.5
160°-170°	103.0	1.5
170°-180°	33.5	0.5
0°-30°	1358.2	19.6
0°-40°	2157.6	31.1
0°-60°	3592.8	51.7
0°-90°	4350.6	62.7
90°-120°	1295.2	18.7
90°-150°	2282.2	32.9
90°-180°	2593.0	37.3
0°-180°	6943.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1841	1841	1841	1841	1841	
5°	1838	1832	1817	1830	1828	174
15°	1748	1738	1710	1708	1696	492
25°	1585	1562	1513	1495	1479	729
35°	1365	1330	1269	1230	1210	854
45°	1118	1075	1001	947	924	862
55°	848	802	726	665	641	758
65°	574	525	453	400	377	569
75°	306	263	206	176	165	324
85°	76	52	44	43	42	86
90°	1	6	11	15	16	5
95°	23	68	618	280	164	24
105°	79	110	506	995	924	83
115°	141	170	406	875	1029	139
125°	195	229	389	696	811	173
135°	229	275	386	583	674	178
145°	266	305	388	483	531	167
155°	304	327	378	427	446	140
165°	332	341	363	385	390	93
175°	345	345	348	352	351	33
180°	346	346	346	346	346	



TEST NUMBER: P333627-940

CATALOG NUMBER: S125RDIP-S1270D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1844.1	1843.3	1842.5	1841.8	1841.1	1839.5	1837.0	1834.5	1832.1	1829.6	1832.1
5°	1838.0	1836.7	1835.5	1834.2	1833.0	1830.7	1827.3	1823.9	1820.5	1817.1	1820.2
7.5°	1819.9	1818.7	1817.6	1816.3	1815.2	1812.6	1808.5	1804.4	1800.4	1796.3	1798.4
10°	1803.2	1802.2	1801.3	1800.5	1799.5	1796.9	1792.5	1788.2	1783.9	1779.6	1780.5
12.5°	1784.3	1783.2	1781.9	1780.7	1779.6	1776.1	1770.3	1764.5	1758.6	1752.8	1753.5
15°	1747.6	1745.7	1743.9	1742.0	1740.2	1736.0	1729.5	1723.1	1716.5	1710.0	1709.8
17.5°	1706.1	1703.3	1700.5	1697.6	1694.8	1689.3	1681.1	1672.9	1664.8	1656.6	1655.1
20°	1673.9	1670.8	1667.7	1664.6	1661.5	1655.0	1645.2	1635.3	1625.4	1615.5	1614.0
22.5°	1638.3	1635.2	1632.1	1629.1	1625.9	1619.3	1608.8	1598.5	1588.0	1577.7	1574.7
25°	1584.9	1580.3	1575.7	1571.0	1566.4	1558.4	1546.9	1535.5	1524.0	1512.6	1508.6
27.5°	1523.8	1518.1	1512.5	1506.9	1501.3	1492.4	1480.1	1467.8	1455.6	1443.4	1437.8
30°	1479.3	1473.4	1467.5	1461.7	1455.8	1446.4	1433.3	1420.4	1407.4	1394.5	1387.3
32.5°	1435.9	1429.1	1422.2	1415.3	1408.5	1398.4	1385.2	1372.0	1358.7	1345.5	1337.7
35°	1365.3	1357.8	1350.4	1343.0	1335.6	1324.9	1311.0	1297.2	1283.3	1269.4	1260.3
37.5°	1296.0	1287.0	1278.0	1269.0	1259.9	1248.2	1233.9	1219.6	1205.2	1190.9	1180.2
40°	1247.1	1237.8	1228.5	1219.2	1210.1	1197.9	1183.1	1168.3	1153.4	1138.6	1126.9
42.5°	1196.0	1186.4	1176.9	1167.3	1157.9	1145.4	1130.2	1114.8	1099.5	1084.1	1072.9
45°	1117.8	1108.8	1099.8	1090.9	1081.9	1069.0	1052.0	1035.0	1018.0	1001.0	988.6
47.5°	1036.9	1027.4	1018.0	1008.5	999.1	985.8	968.7	951.5	934.4	917.3	904.6
50°	985.7	975.5	965.3	955.1	944.9	931.0	913.4	895.8	878.2	860.6	847.6
52.5°	930.1	919.6	909.2	898.8	888.3	874.8	858.2	841.6	824.9	808.3	794.3
55°	848.1	838.2	828.3	818.4	808.5	795.0	777.7	760.4	743.1	725.8	711.9
57.5°	765.2	754.7	744.0	733.5	722.9	709.4	692.7	675.9	659.2	642.6	629.0
60°	711.9	701.0	690.2	679.4	668.6	654.8	638.1	621.4	604.8	588.1	574.5
62.5°	655.1	644.8	634.5	624.1	613.9	600.2	583.3	566.3	549.4	532.4	519.9
65°	574.2	563.7	553.2	542.7	532.2	518.7	502.4	486.0	469.6	453.3	440.9
67.5°	493.8	483.3	472.8	462.4	451.8	438.7	423.0	407.3	391.6	375.9	364.6
70°	439.3	428.8	418.3	407.8	397.3	384.3	368.9	353.5	338.0	322.5	313.0
72.5°	385.9	375.7	365.4	355.2	344.9	332.5	318.1	303.6	289.2	274.7	265.9
75°	305.9	296.6	287.3	278.0	268.8	257.7	244.7	231.8	218.7	205.7	198.9
77.5°	226.3	218.9	211.5	204.1	196.7	187.8	177.4	167.0	156.7	146.2	141.5
80°	180.7	173.3	165.9	158.5	151.1	143.0	134.4	125.7	117.1	108.4	105.7
82.5°	136.3	129.6	122.9	116.2	109.6	103.3	97.3	91.4	85.4	79.5	78.2
85°	76.5	70.9	65.4	59.7	54.2	50.6	49.1	47.6	46.0	44.5	44.1
87.5°	25.7	24.2	22.6	21.2	19.8	19.1	19.0	19.0	18.9	18.9	19.1
90°	0.7	1.4	2.8	4.2	5.6	7.0	7.7	9.1	9.7	11.1	11.9
92.5°	8.5	10.3	16.1	24.8	36.8	57.2	95.2	159.1	228.4	224.8	182.0
95°	23.0	23.7	29.2	36.9	52.3	83.6	158.3	311.7	504.1	617.8	604.5
97.5°	38.2	39.1	43.0	50.6	64.4	87.0	136.3	248.8	450.1	659.7	764.8
100°	48.8	50.2	53.0	60.6	73.9	94.8	135.3	225.9	401.6	629.6	803.9
102.5°	60.5	61.3	63.6	71.8	83.9	104.3	140.3	216.4	364.8	576.6	780.5
105°	78.8	78.8	82.3	89.3	100.4	119.9	150.6	212.7	329.1	505.5	705.6
107.5°	96.7	98.0	101.4	107.1	118.7	136.3	165.9	219.1	314.1	456.6	629.2
110°	109.5	110.8	113.6	119.9	130.4	148.5	177.1	225.2	309.6	433.6	585.7



TEST NUMBER: P333627-940

CATALOG NUMBER: S125RDIP-S1270D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	122.3	123.7	125.9	132.2	142.7	160.2	187.7	233.0	309.6	420.3	553.3
115°	140.8	142.2	144.4	150.6	161.0	178.5	204.3	244.7	311.7	405.8	518.0
117.5°	157.6	159.7	161.9	168.2	180.0	196.9	221.3	258.2	316.3	398.7	497.0
120°	168.7	170.9	173.6	179.9	191.7	209.2	233.5	267.1	320.7	395.3	485.3
122.5°	180.5	182.0	184.2	190.5	203.5	220.9	245.3	277.1	324.6	392.5	475.2
125°	195.2	196.6	200.1	206.3	219.6	237.7	260.7	290.7	331.2	389.1	461.5
127.5°	206.8	208.9	213.4	221.3	235.4	253.5	275.7	303.3	338.6	387.4	449.0
130°	214.0	216.2	221.7	230.8	245.4	263.6	285.2	311.7	343.0	386.3	440.7
132.5°	219.6	222.3	229.0	239.2	254.3	272.5	294.1	318.9	348.0	386.3	434.0
135°	228.7	231.5	239.9	251.0	265.6	284.5	306.1	329.1	354.9	386.3	426.0
137.5°	240.1	242.2	250.0	261.2	275.5	294.9	314.6	336.6	361.1	387.1	418.9
140°	246.8	248.9	257.3	268.4	281.7	300.5	320.7	341.6	363.9	387.6	415.5
142.5°	254.6	256.2	263.9	275.1	287.8	305.5	324.6	344.5	365.6	388.3	412.8
145°	266.4	267.7	274.7	284.5	297.0	313.1	331.2	348.6	367.5	387.6	408.6
147.5°	278.6	279.5	285.4	294.5	305.4	319.5	335.4	351.2	368.1	385.8	404.2
150°	285.9	287.2	292.1	301.2	310.9	322.8	338.1	352.8	368.1	384.1	400.9
152.5°	293.6	294.5	298.8	306.7	316.0	326.7	340.9	353.9	367.6	381.9	397.0
155°	304.0	304.0	308.2	315.1	322.1	331.9	343.8	354.9	366.0	377.9	390.5
157.5°	313.2	313.1	316.4	322.4	328.5	335.9	346.1	355.6	364.3	373.7	384.3
160°	319.3	318.6	321.5	326.3	331.9	338.1	347.2	355.6	362.6	371.0	379.3
162.5°	324.3	323.7	326.5	330.7	335.2	340.4	348.3	355.0	360.9	367.6	374.8
165°	331.9	330.5	332.6	336.1	338.9	343.0	348.6	354.2	358.4	362.6	368.1
167.5°	336.9	336.2	337.4	339.4	341.3	344.0	348.6	352.5	354.5	357.7	361.6
170°	340.3	339.6	340.3	341.6	343.0	345.1	348.6	351.4	352.8	354.9	357.7
172.5°	342.5	341.3	341.9	343.3	344.1	345.1	348.0	350.3	350.5	351.5	353.7
175°	345.1	343.8	344.5	345.1	345.1	345.1	347.2	348.6	347.9	347.9	348.6
177.5°	346.3	345.3	345.3	345.8	345.3	345.3	346.3	347.0	345.8	345.8	346.3
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8



TEST NUMBER: P333627-940

CATALOG NUMBER: S125RDIP-S1270D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1834.5	1837.0	1839.5	1840.6	1840.4	1840.1	1839.9	1839.6
5°	1823.3	1826.4	1829.4	1830.7	1830.1	1829.4	1828.8	1828.2
7.5°	1800.5	1802.8	1804.9	1805.6	1804.9	1804.3	1803.6	1803.0
10°	1781.4	1782.4	1783.2	1783.2	1782.4	1781.4	1780.5	1779.6
12.5°	1754.3	1754.9	1755.6	1755.2	1753.8	1752.4	1751.0	1749.5
15°	1709.4	1709.1	1708.8	1707.3	1704.5	1701.7	1698.9	1696.1
17.5°	1653.6	1652.0	1650.5	1648.6	1646.3	1644.0	1641.7	1639.4
20°	1612.4	1610.9	1609.4	1607.1	1604.4	1601.6	1598.8	1596.1
22.5°	1571.6	1568.6	1565.6	1562.9	1560.7	1558.4	1556.0	1553.8
25°	1504.6	1500.6	1496.6	1492.8	1489.4	1486.0	1482.6	1479.3
27.5°	1432.2	1426.6	1420.9	1416.5	1413.2	1409.9	1406.6	1403.4
30°	1380.3	1373.1	1366.0	1361.1	1358.3	1355.5	1352.7	1350.0
32.5°	1329.8	1322.0	1314.1	1308.4	1304.9	1301.4	1297.9	1294.3
35°	1251.4	1242.4	1233.5	1226.8	1222.5	1218.2	1213.9	1209.5
37.5°	1169.4	1158.7	1147.9	1140.4	1136.2	1132.0	1127.8	1123.6
40°	1115.2	1103.4	1091.7	1084.0	1080.2	1076.6	1072.8	1069.2
42.5°	1061.7	1050.4	1039.2	1030.8	1025.4	1019.9	1014.5	1009.1
45°	976.2	963.9	951.5	943.1	938.4	933.8	929.2	924.5
47.5°	891.9	879.1	866.4	857.5	852.3	847.2	842.0	837.0
50°	834.6	821.6	808.7	799.9	795.2	790.6	786.0	781.3
52.5°	780.3	766.4	752.4	743.2	738.5	733.9	729.2	724.6
55°	697.9	684.0	670.1	660.7	655.8	650.8	645.9	641.0
57.5°	615.4	601.8	588.2	579.3	574.8	570.4	566.1	561.7
60°	560.9	547.3	533.7	524.6	520.0	515.3	510.7	506.0
62.5°	507.3	494.6	482.1	473.4	468.8	464.1	459.5	454.9
65°	428.6	416.2	403.8	395.3	390.7	386.0	381.4	376.7
67.5°	353.3	342.0	330.7	323.2	319.5	315.8	312.1	308.4
70°	303.4	293.8	284.3	277.6	273.8	270.2	266.4	262.8
72.5°	257.1	248.3	239.3	233.7	231.2	228.8	226.3	223.8
75°	192.2	185.4	178.6	174.1	171.9	169.8	167.6	165.4
77.5°	136.7	132.0	127.2	124.0	122.4	120.8	119.2	117.6
80°	102.9	100.1	97.3	95.6	95.0	94.3	93.8	93.2
82.5°	77.0	75.6	74.4	73.5	73.1	72.8	72.4	72.1
85°	43.9	43.6	43.2	43.0	42.6	42.4	42.0	41.7
87.5°	19.2	19.4	19.4	19.6	19.4	19.2	19.0	18.8
90°	12.6	13.3	13.9	15.3	15.3	15.3	16.1	16.1
92.5°	123.6	89.7	67.5	57.2	48.2	46.5	45.6	44.5
95°	501.3	395.3	309.6	251.0	201.5	180.6	175.0	163.8
97.5°	746.6	672.3	588.7	507.3	464.2	425.2	404.9	396.0
100°	857.6	823.4	751.6	679.1	631.0	580.8	555.0	543.9
102.5°	894.9	916.1	881.5	832.5	781.0	745.3	717.3	708.9
105°	872.9	968.5	999.2	991.5	969.1	946.1	932.2	923.8
107.5°	794.2	921.8	1000.5	1036.9	1048.2	1048.0	1043.5	1037.9
110°	736.3	868.7	967.1	1026.3	1057.7	1070.9	1075.8	1075.8



TEST NUMBER: P333627-940

CATALOG NUMBER: S125RDIP-S1270D810U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	690.5	816.3	915.7	985.6	1031.4	1054.2	1066.3	1071.4
115°	633.1	741.2	836.7	912.7	967.1	1000.5	1020.0	1029.1
117.5°	596.0	689.1	771.4	841.2	895.5	930.1	949.5	955.0
120°	575.9	659.6	736.3	797.6	849.2	882.7	901.5	907.0
122.5°	560.9	638.4	706.7	764.2	810.2	840.9	859.7	864.7
125°	539.0	610.1	670.7	720.9	760.0	788.5	803.9	810.8
127.5°	516.7	583.0	639.6	686.6	722.0	747.3	761.8	764.8
130°	502.7	564.1	618.4	663.8	698.7	721.7	735.6	739.8
132.5°	488.7	546.2	595.6	639.2	674.0	697.1	709.9	714.6
135°	470.6	518.7	563.4	603.1	633.7	656.7	669.3	673.5
137.5°	455.3	494.2	531.3	565.0	592.5	613.4	625.0	629.6
140°	446.9	479.7	511.8	541.0	566.9	585.0	595.4	598.9
142.5°	439.7	467.4	495.0	520.4	542.3	557.7	567.6	570.4
145°	430.2	451.8	473.4	492.2	509.0	520.8	528.5	531.3
147.5°	421.2	438.8	455.4	469.7	482.9	492.4	496.9	498.1
150°	416.3	431.6	444.8	457.4	467.9	476.2	479.0	479.7
152.5°	410.6	424.4	436.5	446.2	455.0	461.7	464.5	465.2
155°	402.3	413.5	423.2	430.9	437.8	442.7	444.8	445.5
157.5°	394.0	403.1	410.6	416.7	422.1	426.1	428.1	427.9
160°	388.3	395.3	402.3	407.2	412.1	415.5	417.0	416.3
162.5°	382.2	388.6	394.5	398.8	402.6	405.5	405.8	405.6
165°	373.7	378.6	382.8	386.3	389.1	390.5	390.5	390.5
167.5°	365.6	368.8	372.0	374.5	375.9	377.2	376.7	376.5
170°	361.1	363.3	365.3	366.8	368.1	368.8	368.8	368.1
172.5°	356.1	358.2	359.8	360.6	360.9	362.1	361.1	360.3
175°	350.7	350.7	352.1	352.1	352.1	352.8	351.4	350.7
177.5°	347.0	347.5	347.5	347.5	347.0	347.5	345.8	345.8
180°	345.8	345.8	345.8	345.8	345.8	345.8	345.8	345.8

(END OF REPORT)