

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333510-940

Luminaire Tested: **S125RDIP-S375D1035U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333510-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1035U940-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4613.9 lumens  
Efficiency: N/A  
Efficacy: 123.7 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	48	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	48	36	29	24	43	33	26	22	26	21	18	20	17	15	14	12	11	9
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3241	3241	3241	3241
5°	3729	3246	2867	3246
10°	4278	3229	2530	3229
15°	4621	3196	2249	3196
20°	5096	3158	2076	3158
25°	5897	3107	1927	3107
30°	6416	3053	1829	3053
35°	5412	2990	1738	2990
40°	3780	2878	1661	2878
45°	2804	2726	1585	2726
50°	2237	2569	1519	2569
55°	1897	2374	1462	2374
60°	1639	2198	1368	2198
65°	1461	2008	1177	2008
70°	1284	1841	1074	1841
75°	1110	1592	1008	1592
80°	841	1339	841	1339
85°	704	1052	793	1052



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.1	1.0
10°-20°	141.1	3.1
20°-30°	223.6	4.8
30°-40°	269.7	5.8
40°-50°	240.9	5.2
50°-60°	184.7	4.0
60°-70°	120.0	2.6
70°-80°	58.3	1.3
80°-90°	16.4	0.4
90°-100°	320.0	6.9
100°-110°	688.0	14.9
110°-120°	645.7	14.0
120°-130°	523.3	11.3
130°-140°	419.9	9.1
140°-150°	316.9	6.9
150°-160°	223.1	4.8
160°-170°	131.5	2.8
170°-180°	42.8	0.9
0°-30°	412.8	8.9
0°-40°	682.5	14.8
0°-60°	1108.1	24.0
0°-90°	1302.9	28.2
90°-120°	1653.7	35.8
90°-150°	2913.7	63.2
90°-180°	3311.0	71.8
0°-180°	4613.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	502	502	502	502	502	
5°	575	501	442	501	575	57
15°	691	478	336	478	691	198
25°	828	436	270	436	828	380
35°	686	379	220	379	686	415
45°	307	298	174	298	307	245
55°	168	211	130	211	168	153
65°	96	131	77	131	96	95
75°	44	64	40	64	44	47
85°	10	14	11	14	10	11
90°	20	1	20	1	20	14
95°	209	29	209	29	209	296
105°	1180	101	1180	101	1180	1172
115°	1314	180	1314	180	1314	1284
125°	1035	249	1035	249	1035	937
135°	860	292	860	292	860	666
145°	678	340	678	340	678	431
155°	569	388	569	388	569	265
165°	498	424	498	424	498	143
175°	448	441	448	441	448	44
180°	442	442	442	442	442	



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	528.0	527.6	528.3	526.5	526.6	523.9	523.9	521.7	518.9	516.7	515.8
5°	575.2	575.7	574.9	571.8	569.7	566.6	563.1	557.0	551.8	546.8	543.0
7.5°	624.0	624.3	621.5	620.6	615.4	611.6	603.9	595.4	588.0	578.5	571.2
10°	652.4	652.1	649.3	646.9	642.5	636.7	629.0	619.2	609.9	599.6	589.7
12.5°	668.8	668.2	667.4	664.6	660.4	655.3	648.8	639.1	627.7	616.4	604.8
15°	691.1	689.6	687.0	683.4	677.4	671.5	664.3	655.7	644.7	632.0	621.3
17.5°	718.6	718.6	714.5	709.6	701.5	691.0	679.8	665.9	651.0	637.0	625.6
20°	741.4	740.7	736.6	727.1	717.8	704.6	691.9	674.8	656.7	638.3	624.1
22.5°	774.0	772.4	768.1	755.6	741.3	724.2	704.7	683.9	661.9	641.1	622.4
25°	827.5	826.3	817.8	803.3	783.2	757.0	731.5	702.8	671.3	643.9	621.3
27.5°	864.1	862.7	856.4	844.5	825.8	798.3	763.8	725.4	686.1	648.4	615.7
30°	860.4	863.5	862.7	857.1	843.1	818.4	786.5	743.4	696.6	652.4	613.4
32.5°	808.7	811.5	818.7	829.6	830.5	820.6	796.7	756.9	708.5	658.1	611.5
35°	686.5	690.3	704.3	726.3	755.2	779.3	784.2	762.8	719.3	665.1	608.9
37.5°	527.8	548.0	559.9	583.1	626.7	671.0	713.6	729.3	710.9	662.2	604.5
40°	448.4	453.3	474.3	500.5	537.2	583.3	644.1	688.0	689.4	655.7	597.5
42.5°	383.7	390.0	404.4	425.3	456.7	502.8	565.6	623.6	650.3	637.5	588.4
45°	307.0	311.7	322.3	338.3	362.4	400.6	454.5	521.5	574.6	595.5	564.2
47.5°	252.2	254.8	263.9	276.2	294.0	321.7	363.6	421.7	485.4	530.1	525.8
50°	222.6	225.4	232.4	241.7	256.7	280.2	313.6	362.0	427.8	482.3	493.3
52.5°	199.5	201.9	206.3	215.0	227.4	245.4	272.4	316.2	375.3	433.4	458.7
55°	168.5	170.2	173.7	178.6	188.5	201.5	224.8	255.1	302.9	361.4	398.5
57.5°	143.1	143.9	146.2	150.7	157.6	167.0	183.9	209.5	243.8	296.5	337.4
60°	126.9	127.8	130.6	133.8	139.1	147.8	161.0	178.9	211.8	255.3	296.7
62.5°	114.0	114.6	115.8	118.9	123.6	130.3	140.6	155.2	181.5	219.7	258.8
65°	95.6	95.8	96.2	98.7	101.6	106.6	113.3	123.6	143.4	172.3	206.9
67.5°	77.8	78.2	79.6	80.5	83.5	86.1	90.1	97.9	111.9	131.3	158.3
70°	68.0	67.8	69.2	70.3	71.2	74.4	77.0	83.5	92.1	106.9	129.4
72.5°	58.8	58.2	58.9	59.2	60.5	62.7	65.4	69.3	76.0	86.1	103.3
75°	44.5	44.7	44.7	45.1	46.2	47.0	47.8	49.8	53.6	60.4	69.6
77.5°	31.2	30.9	31.7	31.9	32.5	33.4	34.2	35.0	36.5	39.2	44.1
80°	22.6	22.6	22.8	23.5	23.3	23.7	24.7	25.6	27.4	29.1	30.7
82.5°	17.4	17.2	17.4	17.6	17.5	17.9	18.3	18.5	19.2	20.0	21.1
85°	9.5	9.5	9.7	9.7	9.9	9.9	10.1	10.1	10.1	10.3	10.5
87.5°	7.8	7.6	7.2	7.2	7.4	7.3	7.0	6.7	6.5	6.3	6.2
90°	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1	15.2	14.3	12.5
92.5°	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7	232.3	287.0	291.6
95°	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1	771.8	788.7	643.6
97.5°	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2	976.5	842.3	574.7
100°	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9	1026.4	803.8	512.7
102.5°	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6	996.5	736.2	465.7
105°	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5	900.9	645.3	420.2
107.5°	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1	803.3	582.9	400.9
110°	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0	747.7	553.7	395.2



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6	706.4	536.6	395.2
115°	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2	661.4	518.1	397.9
117.5°	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9	634.5	509.0	403.8
120°	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3	619.6	504.7	409.5
122.5°	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0	606.7	501.1	414.5
125°	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1	589.3	496.7	422.8
127.5°	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6	573.3	494.5	432.3
130°	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9	562.6	493.1	438.0
132.5°	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0	554.0	493.1	444.3
135°	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8	543.9	493.1	453.1
137.5°	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3	534.8	494.2	461.1
140°	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6	530.6	494.9	464.7
142.5°	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3	527.0	495.6	466.8
145°	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2	521.7	494.9	469.1
147.5°	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9	516.1	492.6	470.0
150°	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5	511.8	490.4	470.0
152.5°	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3	506.8	487.7	469.3
155°	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6	498.5	482.5	467.3
157.5°	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9	490.6	477.2	465.0
160°	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8	484.3	473.6	462.9
162.5°	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0	478.6	469.3	460.7
165°	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2	470.0	462.9	457.5
167.5°	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8	461.6	456.6	452.5
170°	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1	456.6	453.1	450.4
172.5°	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7	451.7	448.8	447.5
175°	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7	445.1	444.2	444.2
177.5°	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9	442.2	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	515.8	514.6	512.5	510.5	508.0	505.9	504.4	502.6	500.2	497.5	495.2
5°	538.6	534.0	528.1	522.9	516.3	511.2	505.9	500.7	495.5	488.9	483.1
7.5°	563.9	554.6	545.5	534.0	523.6	514.3	505.4	496.4	487.6	478.2	469.2
10°	579.4	568.0	555.5	541.1	527.9	515.3	503.8	492.4	480.5	470.0	458.7
12.5°	593.9	579.3	564.9	546.7	530.8	515.5	500.8	486.7	473.9	460.3	448.1
15°	607.0	592.5	576.5	554.3	532.2	513.6	496.3	478.0	462.2	446.9	433.3
17.5°	612.1	596.9	578.3	556.9	532.8	509.4	487.1	467.1	448.4	430.6	415.4
20°	610.1	595.5	576.3	555.9	530.1	505.9	481.7	459.5	438.6	419.9	403.7
22.5°	605.3	590.2	571.7	550.1	525.7	499.9	474.1	450.4	428.6	409.2	391.5
25°	598.2	577.6	558.6	537.5	514.2	488.7	462.2	436.0	412.7	392.9	373.5
27.5°	590.7	565.0	540.8	520.0	495.3	472.6	446.9	420.1	395.7	375.5	355.6
30°	583.9	555.1	528.5	504.8	481.5	459.9	435.6	409.4	384.2	363.5	343.3
32.5°	575.5	544.8	515.7	488.3	465.8	444.4	422.4	397.3	372.9	351.4	330.9
35°	565.0	525.8	494.1	465.0	440.1	419.3	399.5	379.3	354.8	332.5	312.5
37.5°	551.2	506.7	470.0	438.4	412.1	391.2	375.5	357.0	334.7	313.4	294.9
40°	542.7	492.8	452.7	421.3	393.8	371.7	357.0	341.4	321.0	301.0	282.5
42.5°	531.5	480.2	435.2	402.6	374.8	353.6	338.8	325.1	308.0	289.2	269.3
45°	509.5	455.6	408.4	373.4	345.4	324.5	310.7	298.5	285.6	268.2	250.9
47.5°	481.0	429.9	380.5	342.2	314.9	295.5	282.1	272.5	263.2	248.5	231.8
50°	458.1	408.8	360.6	323.5	294.3	275.9	263.3	255.7	247.3	233.9	219.8
52.5°	431.0	387.0	339.8	301.9	274.3	257.1	245.0	237.4	230.4	219.5	206.2
55°	388.4	349.8	306.6	272.2	246.8	229.5	218.0	210.8	206.7	197.4	186.9
57.5°	339.2	311.7	273.5	240.3	217.8	200.8	192.3	186.2	181.6	175.0	167.6
60°	305.0	285.6	251.4	219.8	199.2	183.0	175.3	170.2	165.9	160.3	154.5
62.5°	270.2	256.1	226.3	199.2	180.3	166.7	159.5	154.9	149.9	146.2	140.5
65°	223.6	211.0	190.4	169.2	151.7	140.7	135.5	131.4	128.4	124.2	120.3
67.5°	173.9	168.8	154.5	139.9	127.3	117.6	113.2	110.3	106.6	104.2	101.5
70°	143.4	140.9	130.8	121.2	109.4	102.8	98.7	97.5	92.9	90.4	88.6
72.5°	116.4	115.2	109.4	102.7	94.4	88.6	84.9	83.5	80.5	78.6	77.4
75°	79.7	80.2	79.1	74.8	71.7	68.0	64.7	63.8	61.8	60.2	59.1
77.5°	50.5	52.5	52.6	52.4	51.2	49.0	47.5	46.9	44.9	44.3	44.1
80°	34.6	36.9	39.0	38.7	38.3	37.7	36.6	36.0	35.0	34.4	34.0
82.5°	23.1	25.1	26.9	28.0	27.9	27.3	26.7	26.3	26.1	25.7	25.6
85°	10.9	11.3	11.9	13.4	14.4	14.6	14.4	14.2	13.6	13.8	14.0
87.5°	6.1	5.7	5.7	5.4	4.8	5.4	5.4	5.4	5.3	5.4	5.4
90°	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9	1.8	3.6	5.4
92.5°	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9	13.2	20.7	31.7
95°	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3	30.2	37.4	47.2
97.5°	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8	49.8	54.8	64.6
100°	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3	64.1	67.7	77.4
102.5°	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3	78.3	81.1	91.7
105°	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6	100.6	105.0	114.0
107.5°	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4	125.2	129.4	136.7
110°	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7	141.5	145.1	153.1





TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1	157.9	160.8	168.8
115°	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9	181.6	184.2	192.3
117.5°	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2	203.8	206.7	214.7
120°	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4	218.1	221.7	229.7
122.5°	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4	232.3	235.1	243.2
125°	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2	251.0	255.5	263.5
127.5°	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0	266.7	272.4	282.6
130°	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3	276.0	283.1	294.6
132.5°	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4	283.7	292.3	305.3
135°	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9	295.5	306.2	320.5
137.5°	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6	309.2	319.2	333.5
140°	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1	317.8	328.5	342.7
142.5°	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1	327.1	337.0	351.2
145°	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0	341.8	350.7	363.2
147.5°	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7	356.8	364.4	376.0
150°	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0	366.8	373.0	384.6
152.5°	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0	376.0	381.6	391.6
155°	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1	388.1	393.4	402.3
157.5°	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8	399.7	403.9	411.6
160°	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7	406.8	410.4	416.6
162.5°	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1	413.2	416.8	422.3
165°	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7	422.0	424.6	429.1
167.5°	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2	429.3	430.9	433.4
170°	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4	433.5	434.4	436.2
172.5°	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3	435.7	436.6	438.3
175°	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6	438.8	439.7	440.6
177.5°	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2	440.8	440.8	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	493.5	491.2	489.5	486.2	483.9	483.0	481.2	480.6	482.5	481.2	481.0
5°	478.8	472.9	468.1	463.4	458.3	455.0	450.0	449.2	447.9	446.1	445.7
7.5°	461.3	453.4	447.4	439.5	432.7	427.2	421.1	418.1	416.5	414.1	410.9
10°	449.4	440.1	431.9	424.0	415.6	408.8	402.6	397.9	394.8	391.9	390.7
12.5°	437.7	428.2	417.7	408.2	398.8	391.2	384.3	381.2	377.8	374.4	371.6
15°	419.5	407.0	395.4	384.5	376.5	368.2	361.6	357.0	352.0	350.4	344.9
17.5°	400.2	387.9	374.3	362.9	353.6	344.5	337.2	332.1	328.2	322.9	320.4
20°	388.2	373.5	360.3	349.8	339.6	328.9	321.5	317.1	313.4	309.1	307.0
22.5°	375.3	361.1	347.5	335.2	324.8	314.1	308.9	304.4	300.2	296.2	293.5
25°	356.4	342.1	327.8	315.0	304.2	296.5	290.3	285.2	282.9	279.0	276.1
27.5°	337.8	322.4	307.7	295.0	286.4	278.8	273.8	269.7	265.6	262.3	259.7
30°	325.7	310.1	294.0	283.9	274.8	267.7	262.1	258.2	255.1	252.0	250.1
32.5°	313.7	297.6	283.3	272.4	263.9	257.6	251.9	248.1	244.9	241.5	239.2
35°	294.4	277.9	266.4	255.7	247.3	241.5	237.6	232.2	229.5	227.0	224.8
37.5°	276.5	261.2	248.7	239.3	231.9	226.2	221.1	218.3	215.0	212.8	210.9
40°	263.3	249.3	238.0	228.1	222.7	216.3	211.6	207.9	205.5	202.5	200.5
42.5°	251.5	238.4	227.4	218.6	211.9	206.4	201.9	198.1	195.0	193.0	191.3
45°	234.7	221.7	211.0	202.8	196.5	191.5	186.6	184.9	180.7	178.3	177.4
47.5°	217.3	205.7	195.4	187.8	181.5	176.6	172.1	168.4	166.0	163.6	162.3
50°	205.6	194.5	184.9	177.4	171.2	165.9	161.8	159.3	156.1	153.9	152.3
52.5°	193.9	183.6	174.0	166.8	161.5	156.1	151.5	149.1	146.2	144.7	143.6
55°	177.2	166.3	158.0	151.1	145.4	140.5	136.2	133.8	131.9	130.5	130.0
57.5°	158.3	149.6	142.0	135.6	129.8	125.2	121.4	119.0	117.4	117.2	115.9
60°	145.9	138.0	131.1	124.2	119.3	114.9	111.6	109.0	107.4	107.2	106.7
62.5°	133.5	126.0	119.5	113.5	109.1	105.0	101.7	98.8	97.8	96.8	95.9
65°	115.2	108.3	103.0	98.3	93.5	90.1	86.9	85.1	82.8	81.6	79.4
67.5°	97.2	91.9	86.8	82.8	79.0	75.7	73.1	70.4	68.8	67.9	66.3
70°	85.3	81.1	76.1	71.7	68.8	66.2	64.1	61.0	59.9	59.1	58.3
72.5°	74.1	70.4	66.2	62.6	59.7	57.2	54.8	53.4	52.3	51.5	51.1
75°	58.3	54.8	51.1	48.6	46.5	44.5	43.2	42.3	41.8	41.6	40.8
77.5°	42.8	40.9	38.0	36.0	34.7	33.8	32.7	32.2	32.1	31.2	30.9
80°	32.7	31.7	29.2	28.4	27.4	26.6	25.9	25.0	23.9	23.5	22.8
82.5°	24.3	23.4	22.3	21.0	20.2	19.6	19.1	18.6	18.8	18.2	17.9
85°	13.0	11.9	11.5	11.3	10.9	11.3	11.1	10.9	10.7	10.5	10.7
87.5°	5.5	5.9	5.9	6.6	6.2	6.8	7.0	7.0	7.1	7.3	7.6
90°	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1	16.9	17.8	19.6
92.5°	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7	114.5	86.1	73.0
95°	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1	504.7	395.2	320.5
97.5°	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2	858.3	751.6	647.6
100°	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9	1051.3	959.6	867.0
102.5°	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6	1169.5	1125.5	1062.8
105°	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5	1236.4	1275.6	1265.8
107.5°	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1	1176.8	1277.4	1323.8
110°	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0	1109.1	1234.7	1310.4



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6	1042.2	1169.1	1258.4
115°	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2	946.3	1068.2	1165.2
117.5°	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9	879.9	984.9	1073.9
120°	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3	842.1	940.0	1018.3
122.5°	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0	815.0	902.2	975.6
125°	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1	778.9	856.3	920.4
127.5°	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6	744.4	816.6	876.6
130°	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9	720.1	789.6	847.5
132.5°	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0	697.3	760.4	816.1
135°	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8	662.3	719.3	770.0
137.5°	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3	631.0	678.3	721.4
140°	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6	612.4	653.4	690.8
142.5°	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3	596.7	632.0	664.4
145°	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2	576.8	604.4	628.5
147.5°	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9	560.3	581.5	599.6
150°	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5	551.0	567.9	584.0
152.5°	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3	541.7	557.2	569.7
155°	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6	527.9	540.4	550.1
157.5°	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9	514.7	524.3	532.0
160°	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8	504.7	513.6	519.9
162.5°	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0	496.1	503.6	509.2
165°	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2	483.4	488.7	493.1
167.5°	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8	470.9	475.0	478.2
170°	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1	463.8	466.5	468.2
172.5°	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7	457.4	459.3	460.4
175°	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7	447.7	449.5	449.5
177.5°	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9	443.6	443.6	443.6
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	480.8	479.0	478.5	479.2	478.5	479.0	480.8	481.0	481.2	482.5	480.6
5°	443.6	441.6	442.6	442.2	442.6	441.6	443.6	445.7	446.1	447.9	449.2
7.5°	410.9	408.3	405.6	406.4	405.6	408.3	410.9	410.9	414.1	416.5	418.1
10°	388.0	385.9	384.7	385.8	384.7	385.9	388.0	390.7	391.9	394.8	397.9
12.5°	368.7	367.5	366.4	366.0	366.4	367.5	368.7	371.6	374.4	377.8	381.2
15°	342.4	340.0	338.9	336.3	338.9	340.0	342.4	344.9	350.4	352.0	357.0
17.5°	318.3	317.4	314.8	313.6	314.8	317.4	318.3	320.4	322.9	328.2	332.1
20°	303.9	303.1	300.4	302.0	300.4	303.1	303.9	307.0	309.1	313.4	317.1
22.5°	292.0	290.3	289.4	288.9	289.4	290.3	292.0	293.5	296.2	300.2	304.4
25°	275.3	272.6	271.5	270.4	271.5	272.6	275.3	276.1	279.0	282.9	285.2
27.5°	258.5	257.1	255.7	255.4	255.7	257.1	258.5	259.7	262.3	265.6	269.7
30°	247.6	246.2	245.2	245.2	245.2	246.2	247.6	250.1	252.0	255.1	258.2
32.5°	237.9	236.8	235.8	235.6	235.8	236.8	237.9	239.2	241.5	244.9	248.1
35°	223.7	222.1	221.7	220.4	221.7	222.1	223.7	224.8	227.0	229.5	232.2
37.5°	209.0	207.7	207.7	207.5	207.7	207.7	209.0	210.9	212.8	215.0	218.3
40°	199.7	198.6	198.4	197.0	198.4	198.6	199.7	200.5	202.5	205.5	207.9
42.5°	189.6	189.0	188.3	187.7	188.3	189.0	189.6	191.3	193.0	195.0	198.1
45°	175.9	174.5	174.5	173.5	174.5	174.5	175.9	177.4	178.3	180.7	184.9
47.5°	161.8	160.8	160.9	159.8	160.9	160.8	161.8	162.3	163.6	166.0	168.4
50°	152.5	151.9	151.7	151.2	151.7	151.9	152.5	152.3	153.9	156.1	159.3
52.5°	143.1	142.8	143.6	142.7	143.6	142.8	143.1	143.6	144.7	146.2	149.1
55°	130.5	129.8	131.1	129.8	131.1	129.8	130.5	130.0	130.5	131.9	133.8
57.5°	115.9	115.3	116.5	115.8	116.5	115.3	115.9	115.9	117.2	117.4	119.0
60°	106.3	105.0	105.7	105.9	105.7	105.0	106.3	106.7	107.2	107.4	109.0
62.5°	95.0	94.2	94.7	93.7	94.7	94.2	95.0	95.9	96.8	97.8	98.8
65°	78.9	78.3	77.5	77.0	77.5	78.3	78.9	79.4	81.6	82.8	85.1
67.5°	66.3	64.8	64.7	65.1	64.7	64.8	66.3	66.3	67.9	68.8	70.4
70°	57.1	57.1	56.9	56.9	56.9	57.1	57.1	58.3	59.1	59.9	61.0
72.5°	50.6	50.5	50.1	49.9	50.1	50.5	50.6	51.1	51.5	52.3	53.4
75°	40.8	41.0	40.6	40.4	40.6	41.0	40.8	40.8	41.6	41.8	42.3
77.5°	30.1	29.2	29.7	29.2	29.7	29.2	30.1	30.9	31.2	32.1	32.2
80°	22.8	22.6	23.3	22.6	23.3	22.6	22.8	22.8	23.5	23.9	25.0
82.5°	18.1	17.9	18.2	17.7	18.2	17.9	18.1	17.9	18.2	18.8	18.6
85°	10.9	10.7	10.5	10.7	10.5	10.7	10.9	10.7	10.5	10.7	10.9
87.5°	7.7	7.6	7.8	7.8	7.8	7.6	7.7	7.6	7.3	7.1	7.0
90°	19.6	19.6	20.5	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1
92.5°	61.6	59.5	58.2	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7
95°	257.3	230.6	223.5	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1
97.5°	592.7	542.8	517.0	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2
100°	805.6	741.5	708.6	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9
102.5°	997.2	951.6	915.8	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6
105°	1237.3	1208.0	1190.2	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5
107.5°	1338.3	1338.1	1332.2	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1
110°	1350.4	1367.3	1373.5	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1316.9	1345.9	1361.5	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6
115°	1234.7	1277.4	1302.3	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2
117.5°	1143.4	1187.5	1212.2	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9
120°	1084.2	1126.9	1151.0	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3
122.5°	1034.4	1073.5	1097.6	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0
125°	970.3	1006.7	1026.4	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1
127.5°	921.9	954.0	972.6	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6
130°	892.0	921.3	939.1	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9
132.5°	860.6	890.0	906.3	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0
135°	809.1	838.6	854.5	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8
137.5°	756.4	783.2	798.0	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3
140°	723.7	746.9	760.2	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6
142.5°	692.4	711.9	724.6	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3
145°	649.8	664.9	674.8	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2
147.5°	616.5	628.7	634.4	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9
150°	597.3	608.0	611.5	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5
152.5°	580.9	589.5	593.0	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3
155°	559.0	565.3	567.9	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6
157.5°	539.0	544.0	546.5	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9
160°	526.1	530.6	532.4	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8
162.5°	514.0	517.7	518.1	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0
165°	496.7	498.5	498.5	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2
167.5°	480.0	481.6	480.9	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8
170°	470.0	470.9	470.9	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1
172.5°	460.7	462.4	460.9	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7
175°	449.5	450.4	448.6	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7
177.5°	442.9	443.6	441.5	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	481.2	483.0	483.9	486.2	489.5	491.2	493.5	495.2	497.5	500.2	502.6
5°	450.0	455.0	458.3	463.4	468.1	472.9	478.8	483.1	488.9	495.5	500.7
7.5°	421.1	427.2	432.7	439.5	447.4	453.4	461.3	469.2	478.2	487.6	496.4
10°	402.6	408.8	415.6	424.0	431.9	440.1	449.4	458.7	470.0	480.5	492.4
12.5°	384.3	391.2	398.8	408.2	417.7	428.2	437.7	448.1	460.3	473.9	486.7
15°	361.6	368.2	376.5	384.5	395.4	407.0	419.5	433.3	446.9	462.2	478.0
17.5°	337.2	344.5	353.6	362.9	374.3	387.9	400.2	415.4	430.6	448.4	467.1
20°	321.5	328.9	339.6	349.8	360.3	373.5	388.2	403.7	419.9	438.6	459.5
22.5°	308.9	314.1	324.8	335.2	347.5	361.1	375.3	391.5	409.2	428.6	450.4
25°	290.3	296.5	304.2	315.0	327.8	342.1	356.4	373.5	392.9	412.7	436.0
27.5°	273.8	278.8	286.4	295.0	307.7	322.4	337.8	355.6	375.5	395.7	420.1
30°	262.1	267.7	274.8	283.9	294.0	310.1	325.7	343.3	363.5	384.2	409.4
32.5°	251.9	257.6	263.9	272.4	283.3	297.6	313.7	330.9	351.4	372.9	397.3
35°	237.6	241.5	247.3	255.7	266.4	277.9	294.4	312.5	332.5	354.8	379.3
37.5°	221.1	226.2	231.9	239.3	248.7	261.2	276.5	294.9	313.4	334.7	357.0
40°	211.6	216.3	222.7	228.1	238.0	249.3	263.3	282.5	301.0	321.0	341.4
42.5°	201.9	206.4	211.9	218.6	227.4	238.4	251.5	269.3	289.2	308.0	325.1
45°	186.6	191.5	196.5	202.8	211.0	221.7	234.7	250.9	268.2	285.6	298.5
47.5°	172.1	176.6	181.5	187.8	195.4	205.7	217.3	231.8	248.5	263.2	272.5
50°	161.8	165.9	171.2	177.4	184.9	194.5	205.6	219.8	233.9	247.3	255.7
52.5°	151.5	156.1	161.5	166.8	174.0	183.6	193.9	206.2	219.5	230.4	237.4
55°	136.2	140.5	145.4	151.1	158.0	166.3	177.2	186.9	197.4	206.7	210.8
57.5°	121.4	125.2	129.8	135.6	142.0	149.6	158.3	167.6	175.0	181.6	186.2
60°	111.6	114.9	119.3	124.2	131.1	138.0	145.9	154.5	160.3	165.9	170.2
62.5°	101.7	105.0	109.1	113.5	119.5	126.0	133.5	140.5	146.2	149.9	154.9
65°	86.9	90.1	93.5	98.3	103.0	108.3	115.2	120.3	124.2	128.4	131.4
67.5°	73.1	75.7	79.0	82.8	86.8	91.9	97.2	101.5	104.2	106.6	110.3
70°	64.1	66.2	68.8	71.7	76.1	81.1	85.3	88.6	90.4	92.9	97.5
72.5°	54.8	57.2	59.7	62.6	66.2	70.4	74.1	77.4	78.6	80.5	83.5
75°	43.2	44.5	46.5	48.6	51.1	54.8	58.3	59.1	60.2	61.8	63.8
77.5°	32.7	33.8	34.7	36.0	38.0	40.9	42.8	44.1	44.3	44.9	46.9
80°	25.9	26.6	27.4	28.4	29.2	31.7	32.7	34.0	34.4	35.0	36.0
82.5°	19.1	19.6	20.2	21.0	22.3	23.4	24.3	25.6	25.7	26.1	26.3
85°	11.1	11.3	10.9	11.3	11.5	11.9	13.0	14.0	13.8	13.6	14.2
87.5°	7.0	6.8	6.2	6.6	5.9	5.9	5.5	5.4	5.4	5.3	5.4
90°	15.2	14.3	12.5	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9
92.5°	232.3	287.0	291.6	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9
95°	771.8	788.7	643.6	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3
97.5°	976.5	842.3	574.7	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8
100°	1026.4	803.8	512.7	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3
102.5°	996.5	736.2	465.7	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3
105°	900.9	645.3	420.2	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6
107.5°	803.3	582.9	400.9	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4
110°	747.7	553.7	395.2	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	706.4	536.6	395.2	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1
115°	661.4	518.1	397.9	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9
117.5°	634.5	509.0	403.8	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2
120°	619.6	504.7	409.5	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4
122.5°	606.7	501.1	414.5	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4
125°	589.3	496.7	422.8	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2
127.5°	573.3	494.5	432.3	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0
130°	562.6	493.1	438.0	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3
132.5°	554.0	493.1	444.3	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4
135°	543.9	493.1	453.1	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9
137.5°	534.8	494.2	461.1	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6
140°	530.6	494.9	464.7	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1
142.5°	527.0	495.6	466.8	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1
145°	521.7	494.9	469.1	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0
147.5°	516.1	492.6	470.0	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7
150°	511.8	490.4	470.0	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0
152.5°	506.8	487.7	469.3	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0
155°	498.5	482.5	467.3	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1
157.5°	490.6	477.2	465.0	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8
160°	484.3	473.6	462.9	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7
162.5°	478.6	469.3	460.7	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1
165°	470.0	462.9	457.5	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7
167.5°	461.6	456.6	452.5	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2
170°	456.6	453.1	450.4	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4
172.5°	451.7	448.8	447.5	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3
175°	445.1	444.2	444.2	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6
177.5°	442.2	441.5	441.5	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	504.4	505.9	508.0	510.5	512.5	514.6	515.8	515.8	516.7	518.9	521.7
5°	505.9	511.2	516.3	522.9	528.1	534.0	538.6	543.0	546.8	551.8	557.0
7.5°	505.4	514.3	523.6	534.0	545.5	554.6	563.9	571.2	578.5	588.0	595.4
10°	503.8	515.3	527.9	541.1	555.5	568.0	579.4	589.7	599.6	609.9	619.2
12.5°	500.8	515.5	530.8	546.7	564.9	579.3	593.9	604.8	616.4	627.7	639.1
15°	496.3	513.6	532.2	554.3	576.5	592.5	607.0	621.3	632.0	644.7	655.7
17.5°	487.1	509.4	532.8	556.9	578.3	596.9	612.1	625.6	637.0	651.0	665.9
20°	481.7	505.9	530.1	555.9	576.3	595.5	610.1	624.1	638.3	656.7	674.8
22.5°	474.1	499.9	525.7	550.1	571.7	590.2	605.3	622.4	641.1	661.9	683.9
25°	462.2	488.7	514.2	537.5	558.6	577.6	598.2	621.3	643.9	671.3	702.8
27.5°	446.9	472.6	495.3	520.0	540.8	565.0	590.7	615.7	648.4	686.1	725.4
30°	435.6	459.9	481.5	504.8	528.5	555.1	583.9	613.4	652.4	696.6	743.4
32.5°	422.4	444.4	465.8	488.3	515.7	544.8	575.5	611.5	658.1	708.5	756.9
35°	399.5	419.3	440.1	465.0	494.1	525.8	565.0	608.9	665.1	719.3	762.8
37.5°	375.5	391.2	412.1	438.4	470.0	506.7	551.2	604.5	662.2	710.9	729.3
40°	357.0	371.7	393.8	421.3	452.7	492.8	542.7	597.5	655.7	689.4	688.0
42.5°	338.8	353.6	374.8	402.6	435.2	480.2	531.5	588.4	637.5	650.3	623.6
45°	310.7	324.5	345.4	373.4	408.4	455.6	509.5	564.2	595.5	574.6	521.5
47.5°	282.1	295.5	314.9	342.2	380.5	429.9	481.0	525.8	530.1	485.4	421.7
50°	263.3	275.9	294.3	323.5	360.6	408.8	458.1	493.3	482.3	427.8	362.0
52.5°	245.0	257.1	274.3	301.9	339.8	387.0	431.0	458.7	433.4	375.3	316.2
55°	218.0	229.5	246.8	272.2	306.6	349.8	388.4	398.5	361.4	302.9	255.1
57.5°	192.3	200.8	217.8	240.3	273.5	311.7	339.2	337.4	296.5	243.8	209.5
60°	175.3	183.0	199.2	219.8	251.4	285.6	305.0	296.7	255.3	211.8	178.9
62.5°	159.5	166.7	180.3	199.2	226.3	256.1	270.2	258.8	219.7	181.5	155.2
65°	135.5	140.7	151.7	169.2	190.4	211.0	223.6	206.9	172.3	143.4	123.6
67.5°	113.2	117.6	127.3	139.9	154.5	168.8	173.9	158.3	131.3	111.9	97.9
70°	98.7	102.8	109.4	121.2	130.8	140.9	143.4	129.4	106.9	92.1	83.5
72.5°	84.9	88.6	94.4	102.7	109.4	115.2	116.4	103.3	86.1	76.0	69.3
75°	64.7	68.0	71.7	74.8	79.1	80.2	79.7	69.6	60.4	53.6	49.8
77.5°	47.5	49.0	51.2	52.4	52.6	52.5	50.5	44.1	39.2	36.5	35.0
80°	36.6	37.7	38.3	38.7	39.0	36.9	34.6	30.7	29.1	27.4	25.6
82.5°	26.7	27.3	27.9	28.0	26.9	25.1	23.1	21.1	20.0	19.2	18.5
85°	14.4	14.6	14.4	13.4	11.9	11.3	10.9	10.5	10.3	10.1	10.1
87.5°	5.4	5.4	4.8	5.4	5.7	5.7	6.1	6.2	6.3	6.5	6.7
90°	1.8	3.6	5.4	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1
92.5°	13.2	20.7	31.7	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7
95°	30.2	37.4	47.2	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1
97.5°	49.8	54.8	64.6	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2
100°	64.1	67.7	77.4	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9
102.5°	78.3	81.1	91.7	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6
105°	100.6	105.0	114.0	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5
107.5°	125.2	129.4	136.7	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1
110°	141.5	145.1	153.1	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0





TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.9	160.8	168.8	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6
115°	181.6	184.2	192.3	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2
117.5°	203.8	206.7	214.7	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9
120°	218.1	221.7	229.7	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3
122.5°	232.3	235.1	243.2	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0
125°	251.0	255.5	263.5	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1
127.5°	266.7	272.4	282.6	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6
130°	276.0	283.1	294.6	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9
132.5°	283.7	292.3	305.3	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0
135°	295.5	306.2	320.5	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8
137.5°	309.2	319.2	333.5	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3
140°	317.8	328.5	342.7	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6
142.5°	327.1	337.0	351.2	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3
145°	341.8	350.7	363.2	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2
147.5°	356.8	364.4	376.0	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9
150°	366.8	373.0	384.6	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5
152.5°	376.0	381.6	391.6	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3
155°	388.1	393.4	402.3	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6
157.5°	399.7	403.9	411.6	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9
160°	406.8	410.4	416.6	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8
162.5°	413.2	416.8	422.3	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0
165°	422.0	424.6	429.1	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2
167.5°	429.3	430.9	433.4	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8
170°	433.5	434.4	436.2	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1
172.5°	435.7	436.6	438.3	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7
175°	438.8	439.7	440.6	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7
177.5°	440.8	440.8	441.5	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	523.9	523.9	526.6	526.5	528.3	527.6	528.0
5°	563.1	566.6	569.7	571.8	574.9	575.7	575.2
7.5°	603.9	611.6	615.4	620.6	621.5	624.3	624.0
10°	629.0	636.7	642.5	646.9	649.3	652.1	652.4
12.5°	648.8	655.3	660.4	664.6	667.4	668.2	668.8
15°	664.3	671.5	677.4	683.4	687.0	689.6	691.1
17.5°	679.8	691.0	701.5	709.6	714.5	718.6	718.6
20°	691.9	704.6	717.8	727.1	736.6	740.7	741.4
22.5°	704.7	724.2	741.3	755.6	768.1	772.4	774.0
25°	731.5	757.0	783.2	803.3	817.8	826.3	827.5
27.5°	763.8	798.3	825.8	844.5	856.4	862.7	864.1
30°	786.5	818.4	843.1	857.1	862.7	863.5	860.4
32.5°	796.7	820.6	830.5	829.6	818.7	811.5	808.7
35°	784.2	779.3	755.2	726.3	704.3	690.3	686.5
37.5°	713.6	671.0	626.7	583.1	559.9	548.0	527.8
40°	644.1	583.3	537.2	500.5	474.3	453.3	448.4
42.5°	565.6	502.8	456.7	425.3	404.4	390.0	383.7
45°	454.5	400.6	362.4	338.3	322.3	311.7	307.0
47.5°	363.6	321.7	294.0	276.2	263.9	254.8	252.2
50°	313.6	280.2	256.7	241.7	232.4	225.4	222.6
52.5°	272.4	245.4	227.4	215.0	206.3	201.9	199.5
55°	224.8	201.5	188.5	178.6	173.7	170.2	168.5
57.5°	183.9	167.0	157.6	150.7	146.2	143.9	143.1
60°	161.0	147.8	139.1	133.8	130.6	127.8	126.9
62.5°	140.6	130.3	123.6	118.9	115.8	114.6	114.0
65°	113.3	106.6	101.6	98.7	96.2	95.8	95.6
67.5°	90.1	86.1	83.5	80.5	79.6	78.2	77.8
70°	77.0	74.4	71.2	70.3	69.2	67.8	68.0
72.5°	65.4	62.7	60.5	59.2	58.9	58.2	58.8
75°	47.8	47.0	46.2	45.1	44.7	44.7	44.5
77.5°	34.2	33.4	32.5	31.9	31.7	30.9	31.2
80°	24.7	23.7	23.3	23.5	22.8	22.6	22.6
82.5°	18.3	17.9	17.5	17.6	17.4	17.2	17.4
85°	10.1	9.9	9.9	9.7	9.7	9.5	9.5
87.5°	7.0	7.3	7.4	7.2	7.2	7.6	7.8
90°	16.9	17.8	19.6	19.6	19.6	20.5	20.5
92.5°	114.5	86.1	73.0	61.6	59.5	58.2	56.8
95°	504.7	395.2	320.5	257.3	230.6	223.5	209.2
97.5°	858.3	751.6	647.6	592.7	542.8	517.0	505.6
100°	1051.3	959.6	867.0	805.6	741.5	708.6	694.4
102.5°	1169.5	1125.5	1062.8	997.2	951.6	915.8	905.1
105°	1236.4	1275.6	1265.8	1237.3	1208.0	1190.2	1179.5
107.5°	1176.8	1277.4	1323.8	1338.3	1338.1	1332.2	1325.1
110°	1109.1	1234.7	1310.4	1350.4	1367.3	1373.5	1373.5



TEST NUMBER: P333510-940

CATALOG NUMBER: S125RDIP-S375D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1042.2	1169.1	1258.4	1316.9	1345.9	1361.5	1367.8
115°	946.3	1068.2	1165.2	1234.7	1277.4	1302.3	1313.9
117.5°	879.9	984.9	1073.9	1143.4	1187.5	1212.2	1219.3
120°	842.1	940.0	1018.3	1084.2	1126.9	1151.0	1158.2
122.5°	815.0	902.2	975.6	1034.4	1073.5	1097.6	1104.0
125°	778.9	856.3	920.4	970.3	1006.7	1026.4	1035.3
127.5°	744.4	816.6	876.6	921.9	954.0	972.6	976.5
130°	720.1	789.6	847.5	892.0	921.3	939.1	944.5
132.5°	697.3	760.4	816.1	860.6	890.0	906.3	912.4
135°	662.3	719.3	770.0	809.1	838.6	854.5	859.9
137.5°	631.0	678.3	721.4	756.4	783.2	798.0	803.8
140°	612.4	653.4	690.8	723.7	746.9	760.2	764.6
142.5°	596.7	632.0	664.4	692.4	711.9	724.6	728.3
145°	576.8	604.4	628.5	649.8	664.9	674.8	678.3
147.5°	560.3	581.5	599.6	616.5	628.7	634.4	636.0
150°	551.0	567.9	584.0	597.3	608.0	611.5	612.4
152.5°	541.7	557.2	569.7	580.9	589.5	593.0	593.9
155°	527.9	540.4	550.1	559.0	565.3	567.9	568.8
157.5°	514.7	524.3	532.0	539.0	544.0	546.5	546.4
160°	504.7	513.6	519.9	526.1	530.6	532.4	531.5
162.5°	496.1	503.6	509.2	514.0	517.7	518.1	517.9
165°	483.4	488.7	493.1	496.7	498.5	498.5	498.5
167.5°	470.9	475.0	478.2	480.0	481.6	480.9	480.7
170°	463.8	466.5	468.2	470.0	470.9	470.9	470.0
172.5°	457.4	459.3	460.4	460.7	462.4	460.9	460.0
175°	447.7	449.5	449.5	449.5	450.4	448.6	447.7
177.5°	443.6	443.6	443.6	442.9	443.6	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5

(END OF REPORT)