

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333492-940

Luminaire Tested: **S125RDIP-S375D365U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333492-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D365U940-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2473.5 lumens  
Efficiency: N/A  
Efficacy: 121.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43	39
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	52	70	61	54	49	52	47	43	45	41	38	37	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	42	37	33	36	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3241	3241	3241	3241
5°	3729	3246	2867	3246
10°	4278	3229	2530	3229
15°	4621	3196	2249	3196
20°	5096	3158	2076	3158
25°	5897	3107	1927	3107
30°	6416	3053	1829	3053
35°	5412	2990	1738	2990
40°	3780	2878	1661	2878
45°	2804	2726	1585	2726
50°	2237	2569	1519	2569
55°	1897	2374	1462	2374
60°	1639	2198	1368	2198
65°	1461	2008	1177	2008
70°	1284	1841	1074	1841
75°	1110	1592	1008	1592
80°	841	1339	841	1339
85°	704	1052	793	1052



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.1	1.9
10°-20°	141.1	5.7
20°-30°	223.6	9.0
30°-40°	269.7	10.9
40°-50°	240.9	9.7
50°-60°	184.7	7.5
60°-70°	120.0	4.9
70°-80°	58.3	2.4
80°-90°	14.8	0.6
90°-100°	113.3	4.6
100°-110°	243.6	9.8
110°-120°	228.6	9.2
120°-130°	185.2	7.5
130°-140°	148.7	6.0
140°-150°	112.2	4.5
150°-160°	79.0	3.2
160°-170°	46.5	1.9
170°-180°	15.1	0.6
0°-30°	412.8	16.7
0°-40°	682.5	27.6
0°-60°	1108.1	44.8
0°-90°	1301.3	52.6
90°-120°	585.4	23.7
90°-150°	1031.5	41.7
90°-180°	1172.0	47.4
0°-180°	2473.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	502	502	502	502	502	
5°	575	501	442	501	575	57
15°	691	478	336	478	691	198
25°	828	436	270	436	828	380
35°	686	379	220	379	686	415
45°	307	298	174	298	307	245
55°	168	211	130	211	168	153
65°	96	131	77	131	96	95
75°	44	64	40	64	44	47
85°	10	14	11	14	10	11
90°	7	0	7	0	7	5
95°	74	10	74	10	74	105
105°	418	36	418	36	418	415
115°	465	64	465	64	465	454
125°	366	88	366	88	366	332
135°	304	103	304	103	304	236
145°	240	120	240	120	240	153
155°	201	137	201	137	201	94
165°	176	150	176	150	176	50
175°	158	156	158	156	158	15
180°	156	156	156	156	156	



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	528.0	527.6	528.3	526.5	526.6	523.9	523.9	521.7	518.9	516.7	515.8
5°	575.2	575.7	574.9	571.8	569.7	566.6	563.1	557.0	551.8	546.8	543.0
7.5°	624.0	624.3	621.5	620.6	615.4	611.6	603.9	595.4	588.0	578.5	571.2
10°	652.4	652.1	649.3	646.9	642.5	636.7	629.0	619.2	609.9	599.6	589.7
12.5°	668.8	668.2	667.4	664.6	660.4	655.3	648.8	639.1	627.7	616.4	604.8
15°	691.1	689.6	687.0	683.4	677.4	671.5	664.3	655.7	644.7	632.0	621.3
17.5°	718.6	718.6	714.5	709.6	701.5	691.0	679.8	665.9	651.0	637.0	625.6
20°	741.4	740.7	736.6	727.1	717.8	704.6	691.9	674.8	656.7	638.3	624.1
22.5°	774.0	772.4	768.1	755.6	741.3	724.2	704.7	683.9	661.9	641.1	622.4
25°	827.5	826.3	817.8	803.3	783.2	757.0	731.5	702.8	671.3	643.9	621.3
27.5°	864.1	862.7	856.4	844.5	825.8	798.3	763.8	725.4	686.1	648.4	615.7
30°	860.4	863.5	862.7	857.1	843.1	818.4	786.5	743.4	696.6	652.4	613.4
32.5°	808.7	811.5	818.7	829.6	830.5	820.6	796.7	756.9	708.5	658.1	611.5
35°	686.5	690.3	704.3	726.3	755.2	779.3	784.2	762.8	719.3	665.1	608.9
37.5°	527.8	548.0	559.9	583.1	626.7	671.0	713.6	729.3	710.9	662.2	604.5
40°	448.4	453.3	474.3	500.5	537.2	583.3	644.1	688.0	689.4	655.7	597.5
42.5°	383.7	390.0	404.4	425.3	456.7	502.8	565.6	623.6	650.3	637.5	588.4
45°	307.0	311.7	322.3	338.3	362.4	400.6	454.5	521.5	574.6	595.5	564.2
47.5°	252.2	254.8	263.9	276.2	294.0	321.7	363.6	421.7	485.4	530.1	525.8
50°	222.6	225.4	232.4	241.7	256.7	280.2	313.6	362.0	427.8	482.3	493.3
52.5°	199.5	201.9	206.3	215.0	227.4	245.4	272.4	316.2	375.3	433.4	458.7
55°	168.5	170.2	173.7	178.6	188.5	201.5	224.8	255.1	302.9	361.4	398.5
57.5°	143.1	143.9	146.2	150.7	157.6	167.0	183.9	209.5	243.8	296.5	337.4
60°	126.9	127.8	130.6	133.8	139.1	147.8	161.0	178.9	211.8	255.3	296.7
62.5°	114.0	114.6	115.8	118.9	123.6	130.3	140.6	155.2	181.5	219.7	258.8
65°	95.6	95.8	96.2	98.7	101.6	106.6	113.3	123.6	143.4	172.3	206.9
67.5°	77.8	78.2	79.6	80.5	83.5	86.1	90.1	97.9	111.9	131.3	158.3
70°	68.0	67.8	69.2	70.3	71.2	74.4	77.0	83.5	92.1	106.9	129.4
72.5°	58.8	58.2	58.9	59.2	60.5	62.7	65.4	69.3	76.0	86.1	103.3
75°	44.5	44.7	44.7	45.1	46.2	47.0	47.8	49.8	53.6	60.4	69.6
77.5°	31.2	30.9	31.7	31.9	32.5	33.4	34.2	35.0	36.5	39.2	44.1
80°	22.6	22.6	22.8	23.5	23.3	23.7	24.7	25.6	27.4	29.1	30.7
82.5°	17.4	17.2	17.4	17.6	17.5	17.9	18.3	18.5	19.2	20.0	21.1
85°	9.5	9.5	9.7	9.7	9.9	9.9	10.1	10.1	10.1	10.3	10.5
87.5°	5.1	4.9	4.7	4.7	4.8	5.1	4.8	4.6	4.5	4.5	4.5
90°	7.2	7.2	7.0	7.0	7.0	6.3	6.0	5.7	5.4	5.1	4.4
92.5°	20.1	20.6	21.0	21.8	25.9	30.5	40.5	55.8	82.2	101.6	103.3
95°	74.1	79.1	81.6	91.0	113.4	139.9	178.7	226.6	273.2	279.2	227.8
97.5°	179.0	183.1	192.2	209.8	229.3	266.1	303.9	337.4	345.7	298.2	203.5
100°	245.8	250.8	262.5	285.2	306.9	339.7	372.2	387.6	363.4	284.5	181.6
102.5°	320.5	324.2	336.9	353.0	376.3	398.5	414.0	404.5	352.8	260.6	164.9
105°	417.6	421.3	427.7	438.0	448.2	451.6	437.7	394.6	319.0	228.5	148.7
107.5°	469.1	471.6	473.8	473.8	468.7	452.2	416.6	359.0	284.4	206.3	142.0
110°	486.2	486.2	484.0	478.0	463.9	437.1	392.7	332.8	264.7	196.0	139.9



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	484.3	482.0	476.5	466.2	445.5	413.9	369.0	312.1	250.1	189.9	139.9
115°	465.1	461.0	452.2	437.1	412.5	378.2	335.0	286.1	234.2	183.4	140.9
117.5°	431.7	429.2	420.4	404.7	380.2	348.7	311.5	269.4	224.6	180.2	142.9
120°	410.0	407.5	399.0	383.9	360.5	332.8	298.1	260.3	219.4	178.7	145.0
122.5°	390.8	388.6	380.0	366.2	345.4	319.4	288.6	253.5	214.8	177.5	146.7
125°	366.5	363.4	356.4	343.5	325.8	303.2	275.7	243.6	208.7	175.8	149.7
127.5°	345.7	344.3	337.8	326.4	310.3	289.1	263.5	233.5	203.0	175.1	153.0
130°	334.4	332.5	326.2	315.8	300.1	279.6	254.9	227.2	199.2	174.6	155.1
132.5°	323.0	320.8	315.0	304.7	288.9	269.2	246.9	220.9	196.2	174.6	157.3
135°	304.4	302.6	296.9	286.5	272.6	254.7	234.4	212.8	192.5	174.6	160.4
137.5°	284.5	282.5	277.2	267.8	255.4	240.1	223.4	205.8	189.3	175.0	163.3
140°	270.7	269.1	264.4	256.2	244.5	231.3	216.8	202.0	187.8	175.2	164.5
142.5°	257.9	256.5	252.1	245.1	235.2	223.7	211.2	198.8	186.5	175.5	165.2
145°	240.1	238.9	235.4	230.1	222.5	214.0	204.2	194.5	184.7	175.2	166.0
147.5°	225.2	224.5	222.6	218.3	212.3	205.9	198.3	190.4	182.7	174.4	166.4
150°	216.8	216.5	215.3	211.4	206.7	201.1	195.1	188.2	181.2	173.6	166.4
152.5°	210.3	209.9	208.7	205.6	201.7	197.2	191.8	185.7	179.4	172.6	166.1
155°	201.3	201.1	200.1	197.9	194.7	191.3	186.9	181.8	176.5	170.9	165.4
157.5°	193.4	193.5	192.6	190.8	188.3	185.7	182.2	178.1	173.7	168.9	164.6
160°	188.2	188.4	187.8	186.3	184.0	181.8	178.7	175.6	171.5	167.6	163.9
162.5°	183.3	183.4	183.2	182.0	180.3	178.3	175.7	172.7	169.4	166.1	163.1
165°	176.5	176.5	176.5	175.8	174.6	173.0	171.1	168.9	166.4	163.9	162.0
167.5°	170.1	170.2	170.5	170.0	169.3	168.2	166.7	165.2	163.5	161.7	160.2
170°	166.4	166.7	166.7	166.4	165.8	165.1	164.2	163.3	161.7	160.4	159.4
172.5°	162.8	163.2	163.7	163.1	163.0	162.6	161.9	161.0	159.9	158.9	158.5
175°	158.5	158.8	159.4	159.2	159.2	159.2	158.5	158.5	157.6	157.3	157.3
177.5°	156.3	156.3	157.0	156.9	157.0	157.0	157.0	156.9	156.6	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	515.8	514.6	512.5	510.5	508.0	505.9	504.4	502.6	500.2	497.5	495.2
5°	538.6	534.0	528.1	522.9	516.3	511.2	505.9	500.7	495.5	488.9	483.1
7.5°	563.9	554.6	545.5	534.0	523.6	514.3	505.4	496.4	487.6	478.2	469.2
10°	579.4	568.0	555.5	541.1	527.9	515.3	503.8	492.4	480.5	470.0	458.7
12.5°	593.9	579.3	564.9	546.7	530.8	515.5	500.8	486.7	473.9	460.3	448.1
15°	607.0	592.5	576.5	554.3	532.2	513.6	496.3	478.0	462.2	446.9	433.3
17.5°	612.1	596.9	578.3	556.9	532.8	509.4	487.1	467.1	448.4	430.6	415.4
20°	610.1	595.5	576.3	555.9	530.1	505.9	481.7	459.5	438.6	419.9	403.7
22.5°	605.3	590.2	571.7	550.1	525.7	499.9	474.1	450.4	428.6	409.2	391.5
25°	598.2	577.6	558.6	537.5	514.2	488.7	462.2	436.0	412.7	392.9	373.5
27.5°	590.7	565.0	540.8	520.0	495.3	472.6	446.9	420.1	395.7	375.5	355.6
30°	583.9	555.1	528.5	504.8	481.5	459.9	435.6	409.4	384.2	363.5	343.3
32.5°	575.5	544.8	515.7	488.3	465.8	444.4	422.4	397.3	372.9	351.4	330.9
35°	565.0	525.8	494.1	465.0	440.1	419.3	399.5	379.3	354.8	332.5	312.5
37.5°	551.2	506.7	470.0	438.4	412.1	391.2	375.5	357.0	334.7	313.4	294.9
40°	542.7	492.8	452.7	421.3	393.8	371.7	357.0	341.4	321.0	301.0	282.5
42.5°	531.5	480.2	435.2	402.6	374.8	353.6	338.8	325.1	308.0	289.2	269.3
45°	509.5	455.6	408.4	373.4	345.4	324.5	310.7	298.5	285.6	268.2	250.9
47.5°	481.0	429.9	380.5	342.2	314.9	295.5	282.1	272.5	263.2	248.5	231.8
50°	458.1	408.8	360.6	323.5	294.3	275.9	263.3	255.7	247.3	233.9	219.8
52.5°	431.0	387.0	339.8	301.9	274.3	257.1	245.0	237.4	230.4	219.5	206.2
55°	388.4	349.8	306.6	272.2	246.8	229.5	218.0	210.8	206.7	197.4	186.9
57.5°	339.2	311.7	273.5	240.3	217.8	200.8	192.3	186.2	181.6	175.0	167.6
60°	305.0	285.6	251.4	219.8	199.2	183.0	175.3	170.2	165.9	160.3	154.5
62.5°	270.2	256.1	226.3	199.2	180.3	166.7	159.5	154.9	149.9	146.2	140.5
65°	223.6	211.0	190.4	169.2	151.7	140.7	135.5	131.4	128.4	124.2	120.3
67.5°	173.9	168.8	154.5	139.9	127.3	117.6	113.2	110.3	106.6	104.2	101.5
70°	143.4	140.9	130.8	121.2	109.4	102.8	98.7	97.5	92.9	90.4	88.6
72.5°	116.4	115.2	109.4	102.7	94.4	88.6	84.9	83.5	80.5	78.6	77.4
75°	79.7	80.2	79.1	74.8	71.7	68.0	64.7	63.8	61.8	60.2	59.1
77.5°	50.5	52.5	52.6	52.4	51.2	49.0	47.5	46.9	44.9	44.3	44.1
80°	34.6	36.9	39.0	38.7	38.3	37.7	36.6	36.0	35.0	34.4	34.0
82.5°	23.1	25.1	26.9	28.0	27.9	27.3	26.7	26.3	26.1	25.7	25.6
85°	10.9	11.3	11.9	13.4	14.4	14.6	14.4	14.2	13.6	13.8	14.0
87.5°	4.6	4.5	4.5	4.5	4.2	4.9	5.3	5.4	5.1	4.9	4.6
90°	4.1	3.5	3.1	2.5	1.9	1.2	0.6	0.4	0.6	1.2	1.9
92.5°	71.9	43.1	25.9	16.7	11.2	7.3	4.6	3.8	4.6	7.3	11.2
95°	140.9	71.5	37.8	23.6	16.7	13.2	10.7	10.4	10.7	13.2	16.7
97.5°	112.4	61.6	39.3	29.2	22.9	19.4	17.7	17.3	17.7	19.4	22.9
100°	102.1	61.2	42.9	33.4	27.4	24.0	22.6	22.0	22.6	24.0	27.4
102.5°	97.8	63.4	47.2	38.0	32.5	28.7	27.7	27.4	27.7	28.7	32.5
105°	96.1	68.0	54.2	45.4	40.3	37.2	35.6	35.6	35.6	37.2	40.3
107.5°	99.0	75.0	61.6	53.7	48.4	45.8	44.3	43.7	44.3	45.8	48.4
110°	101.8	80.1	67.1	58.9	54.2	51.4	50.1	49.5	50.1	51.4	54.2





TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	105.3	84.8	72.4	64.5	59.7	56.9	55.9	55.3	55.9	56.9	59.7
115°	110.6	92.4	80.7	72.8	68.0	65.3	64.3	63.7	64.3	65.3	68.0
117.5°	116.6	100.0	89.0	81.4	76.0	73.2	72.1	71.2	72.1	73.2	76.0
120°	120.7	105.6	94.5	86.7	81.3	78.5	77.2	76.2	77.2	78.5	81.3
122.5°	125.2	110.8	99.9	91.9	86.1	83.3	82.2	81.6	82.2	83.3	86.1
125°	131.4	117.9	107.5	99.2	93.3	90.4	88.9	88.3	88.9	90.4	93.3
127.5°	137.1	124.6	114.6	106.4	100.0	96.4	94.4	93.5	94.4	96.4	100.0
130°	140.9	128.9	119.1	110.9	104.3	100.2	97.7	96.8	97.7	100.2	104.3
132.5°	144.2	133.0	123.1	114.9	108.1	103.5	100.5	99.2	100.5	103.5	108.1
135°	148.7	138.3	128.6	120.1	113.4	108.4	104.6	103.3	104.6	108.4	113.4
137.5°	152.1	142.2	133.3	124.6	118.1	113.0	109.5	108.5	109.5	113.0	118.1
140°	154.4	145.0	135.8	127.3	121.4	116.3	112.5	111.6	112.5	116.3	121.4
142.5°	155.7	146.7	138.1	130.1	124.4	119.3	115.7	115.1	115.7	119.3	124.4
145°	157.6	149.7	141.5	134.3	128.6	124.1	121.0	120.4	121.0	124.1	128.6
147.5°	158.7	151.6	144.4	138.0	133.1	129.0	126.3	125.9	126.3	129.0	133.1
150°	159.4	152.8	145.9	140.5	136.2	132.1	129.8	129.2	129.8	132.1	136.2
152.5°	160.0	154.1	147.7	142.9	138.7	135.1	133.1	132.8	133.1	135.1	138.7
155°	160.4	155.3	150.0	145.6	142.4	139.3	137.4	137.4	137.4	139.3	142.4
157.5°	160.7	156.4	151.9	148.5	145.7	143.0	141.5	141.6	141.5	143.0	145.7
160°	160.7	156.9	152.8	150.0	147.5	145.3	144.0	144.4	144.0	145.3	147.5
162.5°	160.5	157.5	153.8	151.5	149.5	147.6	146.3	146.6	146.3	147.6	149.5
165°	160.1	157.6	155.1	153.2	151.9	150.3	149.4	150.0	149.4	150.3	151.9
167.5°	159.3	157.6	155.5	154.3	153.4	152.6	151.9	152.3	151.9	152.6	153.4
170°	158.8	157.6	156.0	155.1	154.4	153.8	153.5	153.8	153.5	153.8	154.4
172.5°	158.4	157.3	156.0	155.5	155.2	154.5	154.3	154.8	154.3	154.5	155.2
175°	157.6	156.9	156.0	156.0	156.0	155.7	155.3	156.0	155.3	155.7	156.0
177.5°	156.9	156.6	156.0	156.0	156.3	156.0	156.0	156.6	156.0	156.0	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	493.5	491.2	489.5	486.2	483.9	483.0	481.2	480.6	482.5	481.2	481.0
5°	478.8	472.9	468.1	463.4	458.3	455.0	450.0	449.2	447.9	446.1	445.7
7.5°	461.3	453.4	447.4	439.5	432.7	427.2	421.1	418.1	416.5	414.1	410.9
10°	449.4	440.1	431.9	424.0	415.6	408.8	402.6	397.9	394.8	391.9	390.7
12.5°	437.7	428.2	417.7	408.2	398.8	391.2	384.3	381.2	377.8	374.4	371.6
15°	419.5	407.0	395.4	384.5	376.5	368.2	361.6	357.0	352.0	350.4	344.9
17.5°	400.2	387.9	374.3	362.9	353.6	344.5	337.2	332.1	328.2	322.9	320.4
20°	388.2	373.5	360.3	349.8	339.6	328.9	321.5	317.1	313.4	309.1	307.0
22.5°	375.3	361.1	347.5	335.2	324.8	314.1	308.9	304.4	300.2	296.2	293.5
25°	356.4	342.1	327.8	315.0	304.2	296.5	290.3	285.2	282.9	279.0	276.1
27.5°	337.8	322.4	307.7	295.0	286.4	278.8	273.8	269.7	265.6	262.3	259.7
30°	325.7	310.1	294.0	283.9	274.8	267.7	262.1	258.2	255.1	252.0	250.1
32.5°	313.7	297.6	283.3	272.4	263.9	257.6	251.9	248.1	244.9	241.5	239.2
35°	294.4	277.9	266.4	255.7	247.3	241.5	237.6	232.2	229.5	227.0	224.8
37.5°	276.5	261.2	248.7	239.3	231.9	226.2	221.1	218.3	215.0	212.8	210.9
40°	263.3	249.3	238.0	228.1	222.7	216.3	211.6	207.9	205.5	202.5	200.5
42.5°	251.5	238.4	227.4	218.6	211.9	206.4	201.9	198.1	195.0	193.0	191.3
45°	234.7	221.7	211.0	202.8	196.5	191.5	186.6	184.9	180.7	178.3	177.4
47.5°	217.3	205.7	195.4	187.8	181.5	176.6	172.1	168.4	166.0	163.6	162.3
50°	205.6	194.5	184.9	177.4	171.2	165.9	161.8	159.3	156.1	153.9	152.3
52.5°	193.9	183.6	174.0	166.8	161.5	156.1	151.5	149.1	146.2	144.7	143.6
55°	177.2	166.3	158.0	151.1	145.4	140.5	136.2	133.8	131.9	130.5	130.0
57.5°	158.3	149.6	142.0	135.6	129.8	125.2	121.4	119.0	117.4	117.2	115.9
60°	145.9	138.0	131.1	124.2	119.3	114.9	111.6	109.0	107.4	107.2	106.7
62.5°	133.5	126.0	119.5	113.5	109.1	105.0	101.7	98.8	97.8	96.8	95.9
65°	115.2	108.3	103.0	98.3	93.5	90.1	86.9	85.1	82.8	81.6	79.4
67.5°	97.2	91.9	86.8	82.8	79.0	75.7	73.1	70.4	68.8	67.9	66.3
70°	85.3	81.1	76.1	71.7	68.8	66.2	64.1	61.0	59.9	59.1	58.3
72.5°	74.1	70.4	66.2	62.6	59.7	57.2	54.8	53.4	52.3	51.5	51.1
75°	58.3	54.8	51.1	48.6	46.5	44.5	43.2	42.3	41.8	41.6	40.8
77.5°	42.8	40.9	38.0	36.0	34.7	33.8	32.7	32.2	32.1	31.2	30.9
80°	32.7	31.7	29.2	28.4	27.4	26.6	25.9	25.0	23.9	23.5	22.8
82.5°	24.3	23.4	22.3	21.0	20.2	19.6	19.1	18.6	18.8	18.2	17.9
85°	13.0	11.9	11.5	11.3	10.9	11.3	11.1	10.9	10.7	10.5	10.7
87.5°	4.6	4.7	4.6	5.1	4.6	5.0	5.0	4.9	5.0	5.1	5.0
90°	2.5	3.1	3.5	4.1	4.4	5.1	5.4	5.7	6.0	6.3	7.0
92.5°	16.7	25.9	43.1	71.9	103.3	101.6	82.2	55.8	40.5	30.5	25.9
95°	23.6	37.8	71.5	140.9	227.8	279.2	273.2	226.6	178.7	139.9	113.4
97.5°	29.2	39.3	61.6	112.4	203.5	298.2	345.7	337.4	303.9	266.1	229.3
100°	33.4	42.9	61.2	102.1	181.6	284.5	363.4	387.6	372.2	339.7	306.9
102.5°	38.0	47.2	63.4	97.8	164.9	260.6	352.8	404.5	414.0	398.5	376.3
105°	45.4	54.2	68.0	96.1	148.7	228.5	319.0	394.6	437.7	451.6	448.2
107.5°	53.7	61.6	75.0	99.0	142.0	206.3	284.4	359.0	416.6	452.2	468.7
110°	58.9	67.1	80.1	101.8	139.9	196.0	264.7	332.8	392.7	437.1	463.9



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	64.5	72.4	84.8	105.3	139.9	189.9	250.1	312.1	369.0	413.9	445.5
115°	72.8	80.7	92.4	110.6	140.9	183.4	234.2	286.1	335.0	378.2	412.5
117.5°	81.4	89.0	100.0	116.6	142.9	180.2	224.6	269.4	311.5	348.7	380.2
120°	86.7	94.5	105.6	120.7	145.0	178.7	219.4	260.3	298.1	332.8	360.5
122.5°	91.9	99.9	110.8	125.2	146.7	177.5	214.8	253.5	288.6	319.4	345.4
125°	99.2	107.5	117.9	131.4	149.7	175.8	208.7	243.6	275.7	303.2	325.8
127.5°	106.4	114.6	124.6	137.1	153.0	175.1	203.0	233.5	263.5	289.1	310.3
130°	110.9	119.1	128.9	140.9	155.1	174.6	199.2	227.2	254.9	279.6	300.1
132.5°	114.9	123.1	133.0	144.2	157.3	174.6	196.2	220.9	246.9	269.2	288.9
135°	120.1	128.6	138.3	148.7	160.4	174.6	192.5	212.8	234.4	254.7	272.6
137.5°	124.6	133.3	142.2	152.1	163.3	175.0	189.3	205.8	223.4	240.1	255.4
140°	127.3	135.8	145.0	154.4	164.5	175.2	187.8	202.0	216.8	231.3	244.5
142.5°	130.1	138.1	146.7	155.7	165.2	175.5	186.5	198.8	211.2	223.7	235.2
145°	134.3	141.5	149.7	157.6	166.0	175.2	184.7	194.5	204.2	214.0	222.5
147.5°	138.0	144.4	151.6	158.7	166.4	174.4	182.7	190.4	198.3	205.9	212.3
150°	140.5	145.9	152.8	159.4	166.4	173.6	181.2	188.2	195.1	201.1	206.7
152.5°	142.9	147.7	154.1	160.0	166.1	172.6	179.4	185.7	191.8	197.2	201.7
155°	145.6	150.0	155.3	160.4	165.4	170.9	176.5	181.8	186.9	191.3	194.7
157.5°	148.5	151.9	156.4	160.7	164.6	168.9	173.7	178.1	182.2	185.7	188.3
160°	150.0	152.8	156.9	160.7	163.9	167.6	171.5	175.6	178.7	181.8	184.0
162.5°	151.5	153.8	157.5	160.5	163.1	166.1	169.4	172.7	175.7	178.3	180.3
165°	153.2	155.1	157.6	160.1	162.0	163.9	166.4	168.9	171.1	173.0	174.6
167.5°	154.3	155.5	157.6	159.3	160.2	161.7	163.5	165.2	166.7	168.2	169.3
170°	155.1	156.0	157.6	158.8	159.4	160.4	161.7	163.3	164.2	165.1	165.8
172.5°	155.5	156.0	157.3	158.4	158.5	158.9	159.9	161.0	161.9	162.6	163.0
175°	156.0	156.0	156.9	157.6	157.3	157.3	157.6	158.5	158.5	159.2	159.2
177.5°	156.0	156.0	156.6	156.9	156.3	156.3	156.6	156.9	157.0	157.0	157.0
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	480.8	479.0	478.5	479.2	478.5	479.0	480.8	481.0	481.2	482.5	480.6
5°	443.6	441.6	442.6	442.2	442.6	441.6	443.6	445.7	446.1	447.9	449.2
7.5°	410.9	408.3	405.6	406.4	405.6	408.3	410.9	410.9	414.1	416.5	418.1
10°	388.0	385.9	384.7	385.8	384.7	385.9	388.0	390.7	391.9	394.8	397.9
12.5°	368.7	367.5	366.4	366.0	366.4	367.5	368.7	371.6	374.4	377.8	381.2
15°	342.4	340.0	338.9	336.3	338.9	340.0	342.4	344.9	350.4	352.0	357.0
17.5°	318.3	317.4	314.8	313.6	314.8	317.4	318.3	320.4	322.9	328.2	332.1
20°	303.9	303.1	300.4	302.0	300.4	303.1	303.9	307.0	309.1	313.4	317.1
22.5°	292.0	290.3	289.4	288.9	289.4	290.3	292.0	293.5	296.2	300.2	304.4
25°	275.3	272.6	271.5	270.4	271.5	272.6	275.3	276.1	279.0	282.9	285.2
27.5°	258.5	257.1	255.7	255.4	255.7	257.1	258.5	259.7	262.3	265.6	269.7
30°	247.6	246.2	245.2	245.2	245.2	246.2	247.6	250.1	252.0	255.1	258.2
32.5°	237.9	236.8	235.8	235.6	235.8	236.8	237.9	239.2	241.5	244.9	248.1
35°	223.7	222.1	221.7	220.4	221.7	222.1	223.7	224.8	227.0	229.5	232.2
37.5°	209.0	207.7	207.7	207.5	207.7	207.7	209.0	210.9	212.8	215.0	218.3
40°	199.7	198.6	198.4	197.0	198.4	198.6	199.7	200.5	202.5	205.5	207.9
42.5°	189.6	189.0	188.3	187.7	188.3	189.0	189.6	191.3	193.0	195.0	198.1
45°	175.9	174.5	174.5	173.5	174.5	174.5	175.9	177.4	178.3	180.7	184.9
47.5°	161.8	160.8	160.9	159.8	160.9	160.8	161.8	162.3	163.6	166.0	168.4
50°	152.5	151.9	151.7	151.2	151.7	151.9	152.5	152.3	153.9	156.1	159.3
52.5°	143.1	142.8	143.6	142.7	143.6	142.8	143.1	143.6	144.7	146.2	149.1
55°	130.5	129.8	131.1	129.8	131.1	129.8	130.5	130.0	130.5	131.9	133.8
57.5°	115.9	115.3	116.5	115.8	116.5	115.3	115.9	115.9	117.2	117.4	119.0
60°	106.3	105.0	105.7	105.9	105.7	105.0	106.3	106.7	107.2	107.4	109.0
62.5°	95.0	94.2	94.7	93.7	94.7	94.2	95.0	95.9	96.8	97.8	98.8
65°	78.9	78.3	77.5	77.0	77.5	78.3	78.9	79.4	81.6	82.8	85.1
67.5°	66.3	64.8	64.7	65.1	64.7	64.8	66.3	66.3	67.9	68.8	70.4
70°	57.1	57.1	56.9	56.9	56.9	57.1	57.1	58.3	59.1	59.9	61.0
72.5°	50.6	50.5	50.1	49.9	50.1	50.5	50.6	51.1	51.5	52.3	53.4
75°	40.8	41.0	40.6	40.4	40.6	41.0	40.8	40.8	41.6	41.8	42.3
77.5°	30.1	29.2	29.7	29.2	29.7	29.2	30.1	30.9	31.2	32.1	32.2
80°	22.8	22.6	23.3	22.6	23.3	22.6	22.8	22.8	23.5	23.9	25.0
82.5°	18.1	17.9	18.2	17.7	18.2	17.9	18.1	17.9	18.2	18.8	18.6
85°	10.9	10.7	10.5	10.7	10.5	10.7	10.9	10.7	10.5	10.7	10.9
87.5°	5.2	5.0	5.1	5.1	5.1	5.0	5.2	5.0	5.1	5.0	4.9
90°	7.0	7.0	7.2	7.2	7.2	7.0	7.0	7.0	6.3	6.0	5.7
92.5°	21.8	21.0	20.6	20.1	20.6	21.0	21.8	25.9	30.5	40.5	55.8
95°	91.0	81.6	79.1	74.1	79.1	81.6	91.0	113.4	139.9	178.7	226.6
97.5°	209.8	192.2	183.1	179.0	183.1	192.2	209.8	229.3	266.1	303.9	337.4
100°	285.2	262.5	250.8	245.8	250.8	262.5	285.2	306.9	339.7	372.2	387.6
102.5°	353.0	336.9	324.2	320.5	324.2	336.9	353.0	376.3	398.5	414.0	404.5
105°	438.0	427.7	421.3	417.6	421.3	427.7	438.0	448.2	451.6	437.7	394.6
107.5°	473.8	473.8	471.6	469.1	471.6	473.8	473.8	468.7	452.2	416.6	359.0
110°	478.0	484.0	486.2	486.2	486.2	484.0	478.0	463.9	437.1	392.7	332.8



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	466.2	476.5	482.0	484.3	482.0	476.5	466.2	445.5	413.9	369.0	312.1
115°	437.1	452.2	461.0	465.1	461.0	452.2	437.1	412.5	378.2	335.0	286.1
117.5°	404.7	420.4	429.2	431.7	429.2	420.4	404.7	380.2	348.7	311.5	269.4
120°	383.9	399.0	407.5	410.0	407.5	399.0	383.9	360.5	332.8	298.1	260.3
122.5°	366.2	380.0	388.6	390.8	388.6	380.0	366.2	345.4	319.4	288.6	253.5
125°	343.5	356.4	363.4	366.5	363.4	356.4	343.5	325.8	303.2	275.7	243.6
127.5°	326.4	337.8	344.3	345.7	344.3	337.8	326.4	310.3	289.1	263.5	233.5
130°	315.8	326.2	332.5	334.4	332.5	326.2	315.8	300.1	279.6	254.9	227.2
132.5°	304.7	315.0	320.8	323.0	320.8	315.0	304.7	288.9	269.2	246.9	220.9
135°	286.5	296.9	302.6	304.4	302.6	296.9	286.5	272.6	254.7	234.4	212.8
137.5°	267.8	277.2	282.5	284.5	282.5	277.2	267.8	255.4	240.1	223.4	205.8
140°	256.2	264.4	269.1	270.7	269.1	264.4	256.2	244.5	231.3	216.8	202.0
142.5°	245.1	252.1	256.5	257.9	256.5	252.1	245.1	235.2	223.7	211.2	198.8
145°	230.1	235.4	238.9	240.1	238.9	235.4	230.1	222.5	214.0	204.2	194.5
147.5°	218.3	222.6	224.5	225.2	224.5	222.6	218.3	212.3	205.9	198.3	190.4
150°	211.4	215.3	216.5	216.8	216.5	215.3	211.4	206.7	201.1	195.1	188.2
152.5°	205.6	208.7	209.9	210.3	209.9	208.7	205.6	201.7	197.2	191.8	185.7
155°	197.9	200.1	201.1	201.3	201.1	200.1	197.9	194.7	191.3	186.9	181.8
157.5°	190.8	192.6	193.5	193.4	193.5	192.6	190.8	188.3	185.7	182.2	178.1
160°	186.3	187.8	188.4	188.2	188.4	187.8	186.3	184.0	181.8	178.7	175.6
162.5°	182.0	183.2	183.4	183.3	183.4	183.2	182.0	180.3	178.3	175.7	172.7
165°	175.8	176.5	176.5	176.5	176.5	176.5	175.8	174.6	173.0	171.1	168.9
167.5°	170.0	170.5	170.2	170.1	170.2	170.5	170.0	169.3	168.2	166.7	165.2
170°	166.4	166.7	166.7	166.4	166.7	166.7	166.4	165.8	165.1	164.2	163.3
172.5°	163.1	163.7	163.2	162.8	163.2	163.7	163.1	163.0	162.6	161.9	161.0
175°	159.2	159.4	158.8	158.5	158.8	159.4	159.2	159.2	159.2	158.5	158.5
177.5°	156.9	157.0	156.3	156.3	156.3	157.0	156.9	157.0	157.0	157.0	156.9
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	481.2	483.0	483.9	486.2	489.5	491.2	493.5	495.2	497.5	500.2	502.6
5°	450.0	455.0	458.3	463.4	468.1	472.9	478.8	483.1	488.9	495.5	500.7
7.5°	421.1	427.2	432.7	439.5	447.4	453.4	461.3	469.2	478.2	487.6	496.4
10°	402.6	408.8	415.6	424.0	431.9	440.1	449.4	458.7	470.0	480.5	492.4
12.5°	384.3	391.2	398.8	408.2	417.7	428.2	437.7	448.1	460.3	473.9	486.7
15°	361.6	368.2	376.5	384.5	395.4	407.0	419.5	433.3	446.9	462.2	478.0
17.5°	337.2	344.5	353.6	362.9	374.3	387.9	400.2	415.4	430.6	448.4	467.1
20°	321.5	328.9	339.6	349.8	360.3	373.5	388.2	403.7	419.9	438.6	459.5
22.5°	308.9	314.1	324.8	335.2	347.5	361.1	375.3	391.5	409.2	428.6	450.4
25°	290.3	296.5	304.2	315.0	327.8	342.1	356.4	373.5	392.9	412.7	436.0
27.5°	273.8	278.8	286.4	295.0	307.7	322.4	337.8	355.6	375.5	395.7	420.1
30°	262.1	267.7	274.8	283.9	294.0	310.1	325.7	343.3	363.5	384.2	409.4
32.5°	251.9	257.6	263.9	272.4	283.3	297.6	313.7	330.9	351.4	372.9	397.3
35°	237.6	241.5	247.3	255.7	266.4	277.9	294.4	312.5	332.5	354.8	379.3
37.5°	221.1	226.2	231.9	239.3	248.7	261.2	276.5	294.9	313.4	334.7	357.0
40°	211.6	216.3	222.7	228.1	238.0	249.3	263.3	282.5	301.0	321.0	341.4
42.5°	201.9	206.4	211.9	218.6	227.4	238.4	251.5	269.3	289.2	308.0	325.1
45°	186.6	191.5	196.5	202.8	211.0	221.7	234.7	250.9	268.2	285.6	298.5
47.5°	172.1	176.6	181.5	187.8	195.4	205.7	217.3	231.8	248.5	263.2	272.5
50°	161.8	165.9	171.2	177.4	184.9	194.5	205.6	219.8	233.9	247.3	255.7
52.5°	151.5	156.1	161.5	166.8	174.0	183.6	193.9	206.2	219.5	230.4	237.4
55°	136.2	140.5	145.4	151.1	158.0	166.3	177.2	186.9	197.4	206.7	210.8
57.5°	121.4	125.2	129.8	135.6	142.0	149.6	158.3	167.6	175.0	181.6	186.2
60°	111.6	114.9	119.3	124.2	131.1	138.0	145.9	154.5	160.3	165.9	170.2
62.5°	101.7	105.0	109.1	113.5	119.5	126.0	133.5	140.5	146.2	149.9	154.9
65°	86.9	90.1	93.5	98.3	103.0	108.3	115.2	120.3	124.2	128.4	131.4
67.5°	73.1	75.7	79.0	82.8	86.8	91.9	97.2	101.5	104.2	106.6	110.3
70°	64.1	66.2	68.8	71.7	76.1	81.1	85.3	88.6	90.4	92.9	97.5
72.5°	54.8	57.2	59.7	62.6	66.2	70.4	74.1	77.4	78.6	80.5	83.5
75°	43.2	44.5	46.5	48.6	51.1	54.8	58.3	59.1	60.2	61.8	63.8
77.5°	32.7	33.8	34.7	36.0	38.0	40.9	42.8	44.1	44.3	44.9	46.9
80°	25.9	26.6	27.4	28.4	29.2	31.7	32.7	34.0	34.4	35.0	36.0
82.5°	19.1	19.6	20.2	21.0	22.3	23.4	24.3	25.6	25.7	26.1	26.3
85°	11.1	11.3	10.9	11.3	11.5	11.9	13.0	14.0	13.8	13.6	14.2
87.5°	5.0	5.0	4.6	5.1	4.6	4.7	4.6	4.6	4.9	5.1	5.4
90°	5.4	5.1	4.4	4.1	3.5	3.1	2.5	1.9	1.2	0.6	0.4
92.5°	82.2	101.6	103.3	71.9	43.1	25.9	16.7	11.2	7.3	4.6	3.8
95°	273.2	279.2	227.8	140.9	71.5	37.8	23.6	16.7	13.2	10.7	10.4
97.5°	345.7	298.2	203.5	112.4	61.6	39.3	29.2	22.9	19.4	17.7	17.3
100°	363.4	284.5	181.6	102.1	61.2	42.9	33.4	27.4	24.0	22.6	22.0
102.5°	352.8	260.6	164.9	97.8	63.4	47.2	38.0	32.5	28.7	27.7	27.4
105°	319.0	228.5	148.7	96.1	68.0	54.2	45.4	40.3	37.2	35.6	35.6
107.5°	284.4	206.3	142.0	99.0	75.0	61.6	53.7	48.4	45.8	44.3	43.7
110°	264.7	196.0	139.9	101.8	80.1	67.1	58.9	54.2	51.4	50.1	49.5



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	250.1	189.9	139.9	105.3	84.8	72.4	64.5	59.7	56.9	55.9	55.3
115°	234.2	183.4	140.9	110.6	92.4	80.7	72.8	68.0	65.3	64.3	63.7
117.5°	224.6	180.2	142.9	116.6	100.0	89.0	81.4	76.0	73.2	72.1	71.2
120°	219.4	178.7	145.0	120.7	105.6	94.5	86.7	81.3	78.5	77.2	76.2
122.5°	214.8	177.5	146.7	125.2	110.8	99.9	91.9	86.1	83.3	82.2	81.6
125°	208.7	175.8	149.7	131.4	117.9	107.5	99.2	93.3	90.4	88.9	88.3
127.5°	203.0	175.1	153.0	137.1	124.6	114.6	106.4	100.0	96.4	94.4	93.5
130°	199.2	174.6	155.1	140.9	128.9	119.1	110.9	104.3	100.2	97.7	96.8
132.5°	196.2	174.6	157.3	144.2	133.0	123.1	114.9	108.1	103.5	100.5	99.2
135°	192.5	174.6	160.4	148.7	138.3	128.6	120.1	113.4	108.4	104.6	103.3
137.5°	189.3	175.0	163.3	152.1	142.2	133.3	124.6	118.1	113.0	109.5	108.5
140°	187.8	175.2	164.5	154.4	145.0	135.8	127.3	121.4	116.3	112.5	111.6
142.5°	186.5	175.5	165.2	155.7	146.7	138.1	130.1	124.4	119.3	115.7	115.1
145°	184.7	175.2	166.0	157.6	149.7	141.5	134.3	128.6	124.1	121.0	120.4
147.5°	182.7	174.4	166.4	158.7	151.6	144.4	138.0	133.1	129.0	126.3	125.9
150°	181.2	173.6	166.4	159.4	152.8	145.9	140.5	136.2	132.1	129.8	129.2
152.5°	179.4	172.6	166.1	160.0	154.1	147.7	142.9	138.7	135.1	133.1	132.8
155°	176.5	170.9	165.4	160.4	155.3	150.0	145.6	142.4	139.3	137.4	137.4
157.5°	173.7	168.9	164.6	160.7	156.4	151.9	148.5	145.7	143.0	141.5	141.6
160°	171.5	167.6	163.9	160.7	156.9	152.8	150.0	147.5	145.3	144.0	144.4
162.5°	169.4	166.1	163.1	160.5	157.5	153.8	151.5	149.5	147.6	146.3	146.6
165°	166.4	163.9	162.0	160.1	157.6	155.1	153.2	151.9	150.3	149.4	150.0
167.5°	163.5	161.7	160.2	159.3	157.6	155.5	154.3	153.4	152.6	151.9	152.3
170°	161.7	160.4	159.4	158.8	157.6	156.0	155.1	154.4	153.8	153.5	153.8
172.5°	159.9	158.9	158.5	158.4	157.3	156.0	155.5	155.2	154.5	154.3	154.8
175°	157.6	157.3	157.3	157.6	156.9	156.0	156.0	156.0	155.7	155.3	156.0
177.5°	156.6	156.3	156.3	156.9	156.6	156.0	156.0	156.3	156.0	156.0	156.6
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	504.4	505.9	508.0	510.5	512.5	514.6	515.8	515.8	516.7	518.9	521.7
5°	505.9	511.2	516.3	522.9	528.1	534.0	538.6	543.0	546.8	551.8	557.0
7.5°	505.4	514.3	523.6	534.0	545.5	554.6	563.9	571.2	578.5	588.0	595.4
10°	503.8	515.3	527.9	541.1	555.5	568.0	579.4	589.7	599.6	609.9	619.2
12.5°	500.8	515.5	530.8	546.7	564.9	579.3	593.9	604.8	616.4	627.7	639.1
15°	496.3	513.6	532.2	554.3	576.5	592.5	607.0	621.3	632.0	644.7	655.7
17.5°	487.1	509.4	532.8	556.9	578.3	596.9	612.1	625.6	637.0	651.0	665.9
20°	481.7	505.9	530.1	555.9	576.3	595.5	610.1	624.1	638.3	656.7	674.8
22.5°	474.1	499.9	525.7	550.1	571.7	590.2	605.3	622.4	641.1	661.9	683.9
25°	462.2	488.7	514.2	537.5	558.6	577.6	598.2	621.3	643.9	671.3	702.8
27.5°	446.9	472.6	495.3	520.0	540.8	565.0	590.7	615.7	648.4	686.1	725.4
30°	435.6	459.9	481.5	504.8	528.5	555.1	583.9	613.4	652.4	696.6	743.4
32.5°	422.4	444.4	465.8	488.3	515.7	544.8	575.5	611.5	658.1	708.5	756.9
35°	399.5	419.3	440.1	465.0	494.1	525.8	565.0	608.9	665.1	719.3	762.8
37.5°	375.5	391.2	412.1	438.4	470.0	506.7	551.2	604.5	662.2	710.9	729.3
40°	357.0	371.7	393.8	421.3	452.7	492.8	542.7	597.5	655.7	689.4	688.0
42.5°	338.8	353.6	374.8	402.6	435.2	480.2	531.5	588.4	637.5	650.3	623.6
45°	310.7	324.5	345.4	373.4	408.4	455.6	509.5	564.2	595.5	574.6	521.5
47.5°	282.1	295.5	314.9	342.2	380.5	429.9	481.0	525.8	530.1	485.4	421.7
50°	263.3	275.9	294.3	323.5	360.6	408.8	458.1	493.3	482.3	427.8	362.0
52.5°	245.0	257.1	274.3	301.9	339.8	387.0	431.0	458.7	433.4	375.3	316.2
55°	218.0	229.5	246.8	272.2	306.6	349.8	388.4	398.5	361.4	302.9	255.1
57.5°	192.3	200.8	217.8	240.3	273.5	311.7	339.2	337.4	296.5	243.8	209.5
60°	175.3	183.0	199.2	219.8	251.4	285.6	305.0	296.7	255.3	211.8	178.9
62.5°	159.5	166.7	180.3	199.2	226.3	256.1	270.2	258.8	219.7	181.5	155.2
65°	135.5	140.7	151.7	169.2	190.4	211.0	223.6	206.9	172.3	143.4	123.6
67.5°	113.2	117.6	127.3	139.9	154.5	168.8	173.9	158.3	131.3	111.9	97.9
70°	98.7	102.8	109.4	121.2	130.8	140.9	143.4	129.4	106.9	92.1	83.5
72.5°	84.9	88.6	94.4	102.7	109.4	115.2	116.4	103.3	86.1	76.0	69.3
75°	64.7	68.0	71.7	74.8	79.1	80.2	79.7	69.6	60.4	53.6	49.8
77.5°	47.5	49.0	51.2	52.4	52.6	52.5	50.5	44.1	39.2	36.5	35.0
80°	36.6	37.7	38.3	38.7	39.0	36.9	34.6	30.7	29.1	27.4	25.6
82.5°	26.7	27.3	27.9	28.0	26.9	25.1	23.1	21.1	20.0	19.2	18.5
85°	14.4	14.6	14.4	13.4	11.9	11.3	10.9	10.5	10.3	10.1	10.1
87.5°	5.3	4.9	4.2	4.5	4.5	4.5	4.6	4.5	4.5	4.5	4.6
90°	0.6	1.2	1.9	2.5	3.1	3.5	4.1	4.4	5.1	5.4	5.7
92.5°	4.6	7.3	11.2	16.7	25.9	43.1	71.9	103.3	101.6	82.2	55.8
95°	10.7	13.2	16.7	23.6	37.8	71.5	140.9	227.8	279.2	273.2	226.6
97.5°	17.7	19.4	22.9	29.2	39.3	61.6	112.4	203.5	298.2	345.7	337.4
100°	22.6	24.0	27.4	33.4	42.9	61.2	102.1	181.6	284.5	363.4	387.6
102.5°	27.7	28.7	32.5	38.0	47.2	63.4	97.8	164.9	260.6	352.8	404.5
105°	35.6	37.2	40.3	45.4	54.2	68.0	96.1	148.7	228.5	319.0	394.6
107.5°	44.3	45.8	48.4	53.7	61.6	75.0	99.0	142.0	206.3	284.4	359.0
110°	50.1	51.4	54.2	58.9	67.1	80.1	101.8	139.9	196.0	264.7	332.8





TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.9	56.9	59.7	64.5	72.4	84.8	105.3	139.9	189.9	250.1	312.1
115°	64.3	65.3	68.0	72.8	80.7	92.4	110.6	140.9	183.4	234.2	286.1
117.5°	72.1	73.2	76.0	81.4	89.0	100.0	116.6	142.9	180.2	224.6	269.4
120°	77.2	78.5	81.3	86.7	94.5	105.6	120.7	145.0	178.7	219.4	260.3
122.5°	82.2	83.3	86.1	91.9	99.9	110.8	125.2	146.7	177.5	214.8	253.5
125°	88.9	90.4	93.3	99.2	107.5	117.9	131.4	149.7	175.8	208.7	243.6
127.5°	94.4	96.4	100.0	106.4	114.6	124.6	137.1	153.0	175.1	203.0	233.5
130°	97.7	100.2	104.3	110.9	119.1	128.9	140.9	155.1	174.6	199.2	227.2
132.5°	100.5	103.5	108.1	114.9	123.1	133.0	144.2	157.3	174.6	196.2	220.9
135°	104.6	108.4	113.4	120.1	128.6	138.3	148.7	160.4	174.6	192.5	212.8
137.5°	109.5	113.0	118.1	124.6	133.3	142.2	152.1	163.3	175.0	189.3	205.8
140°	112.5	116.3	121.4	127.3	135.8	145.0	154.4	164.5	175.2	187.8	202.0
142.5°	115.7	119.3	124.4	130.1	138.1	146.7	155.7	165.2	175.5	186.5	198.8
145°	121.0	124.1	128.6	134.3	141.5	149.7	157.6	166.0	175.2	184.7	194.5
147.5°	126.3	129.0	133.1	138.0	144.4	151.6	158.7	166.4	174.4	182.7	190.4
150°	129.8	132.1	136.2	140.5	145.9	152.8	159.4	166.4	173.6	181.2	188.2
152.5°	133.1	135.1	138.7	142.9	147.7	154.1	160.0	166.1	172.6	179.4	185.7
155°	137.4	139.3	142.4	145.6	150.0	155.3	160.4	165.4	170.9	176.5	181.8
157.5°	141.5	143.0	145.7	148.5	151.9	156.4	160.7	164.6	168.9	173.7	178.1
160°	144.0	145.3	147.5	150.0	152.8	156.9	160.7	163.9	167.6	171.5	175.6
162.5°	146.3	147.6	149.5	151.5	153.8	157.5	160.5	163.1	166.1	169.4	172.7
165°	149.4	150.3	151.9	153.2	155.1	157.6	160.1	162.0	163.9	166.4	168.9
167.5°	151.9	152.6	153.4	154.3	155.5	157.6	159.3	160.2	161.7	163.5	165.2
170°	153.5	153.8	154.4	155.1	156.0	157.6	158.8	159.4	160.4	161.7	163.3
172.5°	154.3	154.5	155.2	155.5	156.0	157.3	158.4	158.5	158.9	159.9	161.0
175°	155.3	155.7	156.0	156.0	156.0	156.9	157.6	157.3	157.3	157.6	158.5
177.5°	156.0	156.0	156.3	156.0	156.0	156.6	156.9	156.3	156.3	156.6	156.9
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	501.9	501.9	501.9	501.9	501.9	501.9	501.9
2.5°	523.9	523.9	526.6	526.5	528.3	527.6	528.0
5°	563.1	566.6	569.7	571.8	574.9	575.7	575.2
7.5°	603.9	611.6	615.4	620.6	621.5	624.3	624.0
10°	629.0	636.7	642.5	646.9	649.3	652.1	652.4
12.5°	648.8	655.3	660.4	664.6	667.4	668.2	668.8
15°	664.3	671.5	677.4	683.4	687.0	689.6	691.1
17.5°	679.8	691.0	701.5	709.6	714.5	718.6	718.6
20°	691.9	704.6	717.8	727.1	736.6	740.7	741.4
22.5°	704.7	724.2	741.3	755.6	768.1	772.4	774.0
25°	731.5	757.0	783.2	803.3	817.8	826.3	827.5
27.5°	763.8	798.3	825.8	844.5	856.4	862.7	864.1
30°	786.5	818.4	843.1	857.1	862.7	863.5	860.4
32.5°	796.7	820.6	830.5	829.6	818.7	811.5	808.7
35°	784.2	779.3	755.2	726.3	704.3	690.3	686.5
37.5°	713.6	671.0	626.7	583.1	559.9	548.0	527.8
40°	644.1	583.3	537.2	500.5	474.3	453.3	448.4
42.5°	565.6	502.8	456.7	425.3	404.4	390.0	383.7
45°	454.5	400.6	362.4	338.3	322.3	311.7	307.0
47.5°	363.6	321.7	294.0	276.2	263.9	254.8	252.2
50°	313.6	280.2	256.7	241.7	232.4	225.4	222.6
52.5°	272.4	245.4	227.4	215.0	206.3	201.9	199.5
55°	224.8	201.5	188.5	178.6	173.7	170.2	168.5
57.5°	183.9	167.0	157.6	150.7	146.2	143.9	143.1
60°	161.0	147.8	139.1	133.8	130.6	127.8	126.9
62.5°	140.6	130.3	123.6	118.9	115.8	114.6	114.0
65°	113.3	106.6	101.6	98.7	96.2	95.8	95.6
67.5°	90.1	86.1	83.5	80.5	79.6	78.2	77.8
70°	77.0	74.4	71.2	70.3	69.2	67.8	68.0
72.5°	65.4	62.7	60.5	59.2	58.9	58.2	58.8
75°	47.8	47.0	46.2	45.1	44.7	44.7	44.5
77.5°	34.2	33.4	32.5	31.9	31.7	30.9	31.2
80°	24.7	23.7	23.3	23.5	22.8	22.6	22.6
82.5°	18.3	17.9	17.5	17.6	17.4	17.2	17.4
85°	10.1	9.9	9.9	9.7	9.7	9.5	9.5
87.5°	4.8	5.1	4.8	4.7	4.7	4.9	5.1
90°	6.0	6.3	7.0	7.0	7.0	7.2	7.2
92.5°	40.5	30.5	25.9	21.8	21.0	20.6	20.1
95°	178.7	139.9	113.4	91.0	81.6	79.1	74.1
97.5°	303.9	266.1	229.3	209.8	192.2	183.1	179.0
100°	372.2	339.7	306.9	285.2	262.5	250.8	245.8
102.5°	414.0	398.5	376.3	353.0	336.9	324.2	320.5
105°	437.7	451.6	448.2	438.0	427.7	421.3	417.6
107.5°	416.6	452.2	468.7	473.8	473.8	471.6	469.1
110°	392.7	437.1	463.9	478.0	484.0	486.2	486.2



TEST NUMBER: P333492-940

CATALOG NUMBER: S125RDIP-S375D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	369.0	413.9	445.5	466.2	476.5	482.0	484.3
115°	335.0	378.2	412.5	437.1	452.2	461.0	465.1
117.5°	311.5	348.7	380.2	404.7	420.4	429.2	431.7
120°	298.1	332.8	360.5	383.9	399.0	407.5	410.0
122.5°	288.6	319.4	345.4	366.2	380.0	388.6	390.8
125°	275.7	303.2	325.8	343.5	356.4	363.4	366.5
127.5°	263.5	289.1	310.3	326.4	337.8	344.3	345.7
130°	254.9	279.6	300.1	315.8	326.2	332.5	334.4
132.5°	246.9	269.2	288.9	304.7	315.0	320.8	323.0
135°	234.4	254.7	272.6	286.5	296.9	302.6	304.4
137.5°	223.4	240.1	255.4	267.8	277.2	282.5	284.5
140°	216.8	231.3	244.5	256.2	264.4	269.1	270.7
142.5°	211.2	223.7	235.2	245.1	252.1	256.5	257.9
145°	204.2	214.0	222.5	230.1	235.4	238.9	240.1
147.5°	198.3	205.9	212.3	218.3	222.6	224.5	225.2
150°	195.1	201.1	206.7	211.4	215.3	216.5	216.8
152.5°	191.8	197.2	201.7	205.6	208.7	209.9	210.3
155°	186.9	191.3	194.7	197.9	200.1	201.1	201.3
157.5°	182.2	185.7	188.3	190.8	192.6	193.5	193.4
160°	178.7	181.8	184.0	186.3	187.8	188.4	188.2
162.5°	175.7	178.3	180.3	182.0	183.2	183.4	183.3
165°	171.1	173.0	174.6	175.8	176.5	176.5	176.5
167.5°	166.7	168.2	169.3	170.0	170.5	170.2	170.1
170°	164.2	165.1	165.8	166.4	166.7	166.7	166.4
172.5°	161.9	162.6	163.0	163.1	163.7	163.2	162.8
175°	158.5	159.2	159.2	159.2	159.4	158.8	158.5
177.5°	157.0	157.0	157.0	156.9	157.0	156.3	156.3
180°	156.3	156.3	156.3	156.3	156.3	156.3	156.3

(END OF REPORT)