

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333500-940

Luminaire Tested: **S125RDIP-S375D590U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333500-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D590U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3114.5 lumens  
Efficiency: N/A  
Efficacy: 121.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333500-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333500-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35																				
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30																				
3	80	71	64	58	73	65	59	54	54	49	45	43	40	38	34	32	30	25																				
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22																				
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19																				
6	62	50	42	36	56	46	39	34	39	33	29	31	28	25	25	22	20	17																				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																				
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13																				
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12																				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3524	3524	3524
5°	3532	3492	3513
10°	3505	3459	3459
15°	3463	3389	3361
20°	3410	3291	3252
25°	3348	3195	3125
30°	3270	3082	2984
35°	3191	2967	2827
40°	3117	2845	2672
45°	3027	2711	2503
50°	2936	2563	2327
55°	2831	2422	2139
60°	2725	2251	1938
65°	2601	2054	1705
70°	2459	1805	1469
75°	2263	1522	1223
80°	1993	1194	1027
85°	1675	978	919



TEST NUMBER: P333500-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.3	1.6
10°-20°	143.4	4.6
20°-30°	207.9	6.7
30°-40°	237.0	7.6
40°-50°	231.0	7.4
50°-60°	194.4	6.2
60°-70°	136.3	4.4
70°-80°	70.1	2.2
80°-90°	19.1	0.6
90°-100°	43.8	1.4
100°-110°	129.3	4.2
110°-120°	219.0	7.0
120°-130°	288.2	9.3
130°-140°	322.9	10.4
140°-150°	316.5	10.2
150°-160°	265.8	8.5
160°-170°	176.7	5.7
170°-180°	61.8	2.0
0°-30°	402.6	12.9
0°-40°	639.6	20.5
0°-60°	1065.0	34.2
0°-90°	1290.5	41.4
90°-120°	392.0	12.6
90°-150°	1319.7	42.4
90°-180°	1824.0	58.6
0°-180°	3114.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	546	546	546	546	546	
5°	545	543	539	542	542	52
15°	518	515	507	506	503	146
25°	470	463	448	443	438	216
35°	405	394	376	365	359	253
45°	331	319	297	281	274	256
55°	251	238	215	197	190	225
65°	170	156	134	118	112	169
75°	91	78	61	52	49	96
85°	23	16	13	13	12	25
90°	0	5	8	11	12	3
95°	33	34	39	43	44	35
105°	116	119	122	125	126	124
115°	219	221	222	222	221	217
125°	320	323	324	322	322	286
135°	416	419	420	420	418	321
145°	504	506	508	508	506	315
155°	577	577	577	579	577	266
165°	627	626	627	628	626	177
175°	652	650	650	653	650	62
180°	654	654	654	654	654	



TEST NUMBER: P333500-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	546.6	546.4	546.2	546.0	545.7	545.3	544.6	543.8	543.1	542.3	543.1
5°	544.8	544.5	544.1	543.7	543.3	542.7	541.6	540.6	539.7	538.6	539.6
7.5°	539.5	539.1	538.8	538.4	538.1	537.3	536.1	534.8	533.7	532.4	533.1
10°	534.5	534.2	534.0	533.7	533.4	532.6	531.4	530.0	528.8	527.5	527.8
12.5°	528.9	528.5	528.2	527.9	527.5	526.5	524.8	523.1	521.3	519.6	519.8
15°	518.0	517.5	516.9	516.4	515.9	514.6	512.6	510.8	508.8	506.9	506.8
17.5°	505.8	504.9	504.1	503.2	502.4	500.8	498.3	495.9	493.5	491.1	490.6
20°	496.1	495.3	494.4	493.5	492.5	490.6	487.7	484.7	481.8	478.8	478.4
22.5°	485.6	484.7	483.8	482.9	482.0	480.0	476.9	473.9	470.7	467.7	466.8
25°	469.8	468.4	467.1	465.7	464.3	461.9	458.5	455.1	451.7	448.4	447.2
27.5°	451.7	450.0	448.4	446.7	445.0	442.4	438.7	435.1	431.5	427.8	426.1
30°	438.5	436.8	435.0	433.3	431.5	428.7	424.9	421.1	417.2	413.3	411.3
32.5°	425.6	423.6	421.6	419.5	417.5	414.6	410.6	406.7	402.8	398.9	396.5
35°	404.7	402.5	400.3	398.1	395.9	392.7	388.6	384.5	380.4	376.3	373.6
37.5°	384.1	381.5	378.8	376.1	373.4	370.0	365.8	361.5	357.3	353.0	349.8
40°	369.7	366.9	364.2	361.4	358.6	355.1	350.7	346.3	341.9	337.5	334.0
42.5°	354.5	351.7	348.8	346.1	343.2	339.6	335.0	330.5	325.9	321.4	318.1
45°	331.4	328.7	326.0	323.3	320.7	316.8	311.8	306.8	301.8	296.8	293.0
47.5°	307.4	304.5	301.8	298.9	296.1	292.2	287.1	282.0	277.0	271.9	268.1
50°	292.2	289.2	286.1	283.1	280.1	276.0	270.7	265.6	260.3	255.1	251.3
52.5°	275.7	272.6	269.5	266.4	263.3	259.3	254.4	249.4	244.5	239.6	235.5
55°	251.4	248.4	245.5	242.6	239.7	235.7	230.5	225.3	220.3	215.1	211.0
57.5°	226.9	223.7	220.5	217.4	214.3	210.3	205.3	200.4	195.5	190.5	186.5
60°	211.0	207.8	204.6	201.3	198.1	194.1	189.1	184.2	179.2	174.3	170.3
62.5°	194.2	191.1	188.1	185.0	181.9	177.9	172.9	167.9	162.8	157.8	154.1
65°	170.2	167.1	164.0	160.9	157.7	153.7	148.9	144.1	139.2	134.4	130.7
67.5°	146.4	143.3	140.2	137.1	133.9	130.0	125.4	120.7	116.1	111.5	108.1
70°	130.2	127.2	124.0	120.9	117.8	114.0	109.3	104.8	100.2	95.6	92.7
72.5°	114.4	111.4	108.3	105.3	102.3	98.5	94.3	90.0	85.7	81.4	78.8
75°	90.7	87.9	85.2	82.4	79.7	76.4	72.5	68.7	64.8	61.0	58.9
77.5°	67.1	64.9	62.7	60.5	58.3	55.6	52.6	49.5	46.5	43.3	41.9
80°	53.6	51.4	49.2	47.0	44.8	42.4	39.9	37.3	34.7	32.1	31.3
82.5°	40.4	38.4	36.5	34.4	32.5	30.6	28.9	27.1	25.3	23.5	23.2
85°	22.6	21.0	19.4	17.7	16.1	15.0	14.5	14.1	13.6	13.2	13.1
87.5°	7.7	7.3	7.0	6.7	6.3	6.2	6.3	6.4	6.5	6.6	6.7
90°	0.5	1.4	2.3	3.2	4.1	5.0	5.8	6.6	7.3	8.1	8.7
92.5°	12.3	12.9	13.6	14.2	14.8	15.6	16.6	17.6	18.5	19.5	20.2
95°	33.1	33.3	33.5	33.7	34.0	34.7	35.8	36.9	38.1	39.1	39.9
97.5°	54.9	55.0	55.1	55.2	55.3	56.1	57.7	59.2	60.8	62.3	63.1
100°	71.2	71.2	71.2	71.2	71.2	72.0	73.4	74.9	76.3	77.8	78.8
102.5°	88.7	89.2	89.6	90.1	90.5	91.1	91.8	92.6	93.4	94.1	95.2
105°	116.0	116.5	117.1	117.7	118.2	118.9	119.6	120.2	120.9	121.5	122.3
107.5°	146.1	146.7	147.2	147.8	148.4	148.9	149.5	149.9	150.4	151.0	151.3
110°	166.8	167.4	168.0	168.5	169.2	169.6	169.9	170.2	170.6	170.9	171.3



TEST NUMBER: P333500-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.0	188.3	188.6	188.9	189.2	189.6	190.0	190.4	190.8	191.3	191.5
115°	219.3	219.7	220.2	220.6	221.1	221.4	221.6	221.9	222.0	222.3	222.2
117.5°	250.6	250.7	251.0	251.2	251.4	251.6	251.8	252.0	252.2	252.4	252.5
120°	270.1	270.7	271.3	271.8	272.4	272.7	272.9	273.0	273.0	273.1	273.1
122.5°	291.3	291.5	291.7	291.9	292.1	292.3	292.7	292.9	293.2	293.6	293.5
125°	319.9	320.7	321.3	322.0	322.7	323.1	323.2	323.3	323.4	323.5	323.3
127.5°	350.5	350.9	351.2	351.6	352.0	352.3	352.4	352.6	352.7	352.8	352.8
130°	368.8	369.3	370.0	370.5	371.0	371.5	371.7	371.9	372.1	372.4	372.3
132.5°	387.1	388.1	389.0	389.9	390.8	391.3	391.2	391.2	391.1	391.1	391.0
135°	416.1	416.8	417.5	418.1	418.8	419.2	419.4	419.5	419.5	419.6	419.6
137.5°	443.4	444.1	444.7	445.3	446.0	446.5	446.7	446.9	447.2	447.5	447.5
140°	460.8	461.5	462.0	462.5	463.2	463.6	464.0	464.3	464.6	464.9	465.2
142.5°	478.4	478.8	479.3	479.8	480.3	480.7	481.2	481.6	482.1	482.4	482.6
145°	504.1	504.5	505.1	505.5	506.0	506.3	506.7	507.0	507.4	507.7	507.7
147.5°	527.9	528.2	528.4	528.7	529.0	529.1	529.4	529.8	530.0	530.3	530.6
150°	543.8	543.7	543.6	543.5	543.3	543.5	543.9	544.4	544.8	545.3	545.3
152.5°	556.8	557.0	557.1	557.3	557.4	557.6	557.8	557.9	558.1	558.4	558.7
155°	576.8	576.8	576.8	576.8	576.8	576.9	577.0	577.1	577.3	577.4	577.8
157.5°	594.8	594.5	594.2	594.1	593.8	593.7	593.8	594.0	594.1	594.1	594.6
160°	605.4	605.0	604.7	604.3	604.0	603.9	604.0	604.1	604.2	604.3	604.8
162.5°	614.7	614.5	614.2	613.9	613.7	613.6	613.6	613.7	613.7	613.7	614.2
165°	627.2	627.0	626.8	626.5	626.3	626.2	626.3	626.5	626.6	626.7	627.1
167.5°	637.8	637.4	636.9	636.4	636.0	635.8	635.8	635.8	635.8	635.8	636.4
170°	643.5	643.0	642.6	642.1	641.7	641.5	641.5	641.5	641.5	641.5	642.1
172.5°	647.6	647.1	646.7	646.2	645.8	645.5	645.5	645.5	645.5	645.5	646.2
175°	652.1	651.7	651.2	650.8	650.3	650.1	650.1	650.1	650.1	650.1	650.8
177.5°	654.5	654.2	653.8	653.4	653.0	652.8	652.7	652.6	652.6	652.5	653.0
180°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7



TEST NUMBER: P333500-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	545.6	545.6	545.6	545.6	545.6	545.6	545.6	545.6
2.5°	543.8	544.6	545.3	545.6	545.5	545.5	545.4	545.3
5°	540.5	541.4	542.2	542.7	542.5	542.2	542.1	541.9
7.5°	533.7	534.4	535.0	535.2	535.0	534.8	534.7	534.4
10°	528.1	528.3	528.6	528.6	528.3	528.1	527.8	527.5
12.5°	520.0	520.2	520.4	520.3	519.9	519.4	519.1	518.6
15°	506.7	506.6	506.5	506.0	505.2	504.4	503.6	502.7
17.5°	490.2	489.7	489.3	488.7	488.0	487.3	486.6	486.0
20°	478.0	477.5	477.1	476.4	475.5	474.7	473.9	473.1
22.5°	465.8	464.9	464.0	463.2	462.6	461.9	461.3	460.6
25°	446.0	444.8	443.6	442.6	441.5	440.5	439.5	438.5
27.5°	424.5	422.8	421.2	419.9	418.9	417.9	417.0	416.0
30°	409.1	407.1	404.9	403.5	402.6	401.8	401.0	400.2
32.5°	394.2	391.9	389.5	387.9	386.8	385.8	384.7	383.7
35°	371.0	368.3	365.6	363.6	362.4	361.1	359.8	358.6
37.5°	346.6	343.5	340.3	338.0	336.8	335.6	334.3	333.1
40°	330.6	327.1	323.6	321.3	320.2	319.1	318.0	316.9
42.5°	314.7	311.4	308.0	305.6	304.0	302.3	300.7	299.1
45°	289.4	285.7	282.0	279.6	278.2	276.8	275.4	274.0
47.5°	264.4	260.6	256.8	254.1	252.6	251.1	249.6	248.1
50°	247.4	243.5	239.7	237.1	235.8	234.3	233.0	231.6
52.5°	231.3	227.2	223.0	220.3	218.9	217.6	216.2	214.8
55°	206.9	202.8	198.7	195.8	194.4	192.9	191.5	190.0
57.5°	182.4	178.4	174.3	171.7	170.4	169.1	167.8	166.5
60°	166.3	162.2	158.2	155.5	154.1	152.8	151.4	150.0
62.5°	150.3	146.6	142.9	140.4	138.9	137.6	136.3	134.8
65°	127.0	123.3	119.7	117.2	115.8	114.4	113.1	111.6
67.5°	104.7	101.4	98.0	95.8	94.7	93.6	92.5	91.4
70°	90.0	87.1	84.3	82.3	81.1	80.1	79.0	77.8
72.5°	76.2	73.6	71.0	69.3	68.6	67.9	67.1	66.3
75°	57.0	54.9	53.0	51.6	51.0	50.3	49.7	49.0
77.5°	40.6	39.1	37.7	36.7	36.3	35.8	35.3	34.9
80°	30.5	29.7	28.9	28.4	28.2	28.0	27.8	27.6
82.5°	22.8	22.4	22.0	21.8	21.7	21.6	21.5	21.3
85°	13.0	12.9	12.8	12.8	12.7	12.6	12.5	12.4
87.5°	6.8	7.0	7.0	7.0	7.0	7.0	7.0	7.0
90°	9.3	9.8	10.4	10.9	11.2	11.5	11.9	12.2
92.5°	21.0	21.8	22.6	23.0	23.3	23.5	23.7	24.0
95°	40.8	41.6	42.4	42.8	43.1	43.3	43.5	43.8
97.5°	63.8	64.6	65.4	65.8	65.9	66.1	66.2	66.3
100°	79.9	80.9	81.9	82.5	82.8	83.0	83.2	83.5
102.5°	96.3	97.5	98.5	99.2	99.6	99.9	100.2	100.5
105°	123.0	123.6	124.3	124.8	125.1	125.5	125.8	126.2
107.5°	151.7	152.0	152.3	152.5	152.5	152.5	152.4	152.4
110°	171.6	171.9	172.3	172.4	172.3	172.2	172.0	171.9





TEST NUMBER: P333500-940

CATALOG NUMBER: S125RDIP-S375D590U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	191.6	191.7	191.9	191.9	191.7	191.5	191.3	191.1
115°	222.0	221.9	221.9	221.8	221.6	221.5	221.4	221.3
117.5°	252.6	252.7	252.8	252.6	252.2	251.7	251.3	250.7
120°	273.1	273.1	273.1	273.0	272.5	272.1	271.6	271.2
122.5°	293.4	293.3	293.2	292.9	292.6	292.2	291.9	291.5
125°	323.1	322.9	322.6	322.4	322.4	322.3	322.1	322.0
127.5°	352.6	352.5	352.4	352.2	352.0	351.8	351.5	351.3
130°	372.1	372.0	371.9	371.8	371.5	371.3	371.0	370.9
132.5°	390.8	390.7	390.7	390.4	390.1	389.8	389.5	389.1
135°	419.6	419.6	419.6	419.5	419.0	418.6	418.1	417.7
137.5°	447.7	447.8	448.0	447.8	447.2	446.7	446.1	445.5
140°	465.4	465.7	465.8	465.7	465.1	464.6	464.0	463.4
142.5°	482.7	482.9	483.0	482.8	482.2	481.6	481.1	480.5
145°	507.7	507.7	507.7	507.5	507.2	506.8	506.5	506.1
147.5°	530.8	531.1	531.4	531.1	530.3	529.6	528.8	528.1
150°	545.3	545.3	545.3	545.2	545.0	544.7	544.6	544.3
152.5°	558.9	559.2	559.5	559.4	558.9	558.6	558.1	557.8
155°	578.3	578.7	579.2	579.2	578.5	578.0	577.4	576.8
157.5°	595.0	595.5	595.9	595.8	595.0	594.3	593.6	592.8
160°	605.2	605.6	606.1	606.1	605.6	604.9	604.4	603.9
162.5°	614.7	615.3	615.9	615.8	615.2	614.5	613.9	613.1
165°	627.6	628.0	628.6	628.4	627.8	627.1	626.3	625.7
167.5°	637.1	637.8	638.5	638.5	637.8	637.0	636.3	635.7
170°	642.8	643.5	644.2	644.1	643.4	642.6	641.8	641.0
172.5°	646.9	647.6	648.3	648.3	647.6	646.8	646.1	645.4
175°	651.5	652.1	652.8	652.7	652.0	651.2	650.4	649.6
177.5°	653.5	654.1	654.6	654.6	654.0	653.4	652.6	652.0
180°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7

(END OF REPORT)