

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333570-940

Luminaire Tested: **S125RDIP-S850D1035U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333570-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D1035U940-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6235.7 lumens  
Efficiency: N/A  
Efficacy: 119.9 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46				40	
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	42	41	39				34	
3	81	72	65	60	75	67	61	56	56	52	48	47	44	41	38	36	34				29	
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	31	29				26	
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26				22	
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23				20	
7	58	46	39	33	54	43	36	31	37	31	28	31	27	24	26	23	20				18	
8	54	42	35	29	50	39	32	28	34	28	24	28	24	21	23	20	18				16	
9	51	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16				14	
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7284	7284	7284	7284
5°	8381	7295	6442	7295
10°	9613	7257	5684	7257
15°	10384	7182	5052	7182
20°	11450	7096	4665	7096
25°	13251	6981	4329	6981
30°	14420	6861	4109	6861
35°	12163	6720	3906	6720
40°	8494	6468	3731	6468
45°	6301	6128	3561	6128
50°	5025	5773	3414	5773
55°	4264	5334	3284	5334
60°	3685	4941	3074	4941
65°	3283	4514	2647	4514
70°	2885	4135	2413	4135
75°	2495	3583	2266	3583
80°	1893	3016	1893	3016
85°	1578	2364	1786	2364



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.2	1.7
10°-20°	317.0	5.1
20°-30°	502.6	8.1
30°-40°	606.1	9.7
40°-50°	541.2	8.7
50°-60°	415.1	6.7
60°-70°	269.7	4.3
70°-80°	131.1	2.1
80°-90°	33.8	0.5
90°-100°	320.0	5.1
100°-110°	688.0	11.0
110°-120°	645.7	10.4
120°-130°	523.3	8.4
130°-140°	419.9	6.7
140°-150°	316.9	5.1
150°-160°	223.1	3.6
160°-170°	131.5	2.1
170°-180°	42.8	0.7
0°-30°	927.7	14.9
0°-40°	1533.8	24.6
0°-60°	2490.1	39.9
0°-90°	2924.7	46.9
90°-120°	1653.7	26.5
90°-150°	2913.7	46.7
90°-180°	3311.0	53.1
0°-180°	6235.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1128	1128	1128	1128	1128	
5°	1293	1125	994	1125	1293	129
15°	1553	1074	756	1074	1553	445
25°	1860	980	608	980	1860	854
35°	1543	852	495	852	1543	932
45°	690	671	390	671	690	550
55°	379	474	292	474	379	344
65°	215	295	173	295	215	214
75°	100	144	91	144	100	106
85°	21	32	24	32	21	25
90°	20	1	20	1	20	15
95°	209	29	209	29	209	296
105°	1180	101	1180	101	1180	1172
115°	1314	180	1314	180	1314	1284
125°	1035	249	1035	249	1035	937
135°	860	292	860	292	860	666
145°	678	340	678	340	678	431
155°	569	388	569	388	569	265
165°	498	424	498	424	498	143
175°	448	441	448	441	448	44
180°	442	442	442	442	442	



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1186.4	1185.7	1187.2	1183.1	1183.5	1177.1	1177.1	1172.3	1166.1	1161.3	1159.0
5°	1292.7	1293.7	1291.8	1284.9	1280.2	1273.3	1265.4	1251.5	1239.9	1228.9	1220.0
7.5°	1402.2	1402.8	1396.8	1394.6	1383.0	1374.4	1356.9	1338.0	1321.2	1299.9	1283.7
10°	1465.9	1465.4	1459.0	1453.8	1443.7	1430.7	1413.6	1391.3	1370.6	1347.4	1325.2
12.5°	1503.0	1501.7	1499.7	1493.5	1484.1	1472.6	1458.0	1436.2	1410.5	1385.2	1359.2
15°	1553.0	1549.7	1543.7	1535.8	1522.4	1509.0	1492.8	1473.4	1448.8	1420.0	1396.0
17.5°	1614.8	1614.9	1605.7	1594.7	1576.5	1552.8	1527.8	1496.4	1463.0	1431.5	1405.8
20°	1666.0	1664.6	1655.3	1634.0	1613.2	1583.5	1554.8	1516.4	1475.6	1434.4	1402.5
22.5°	1739.3	1735.7	1726.1	1698.1	1665.8	1627.6	1583.7	1536.8	1487.5	1440.7	1398.8
25°	1859.5	1856.7	1837.7	1805.4	1760.0	1701.1	1643.7	1579.4	1508.5	1447.0	1396.0
27.5°	1941.7	1938.7	1924.6	1897.6	1855.8	1793.9	1716.2	1630.2	1541.8	1457.1	1383.6
30°	1933.6	1940.5	1938.7	1926.2	1894.7	1839.2	1767.4	1670.6	1565.5	1465.9	1378.4
32.5°	1817.2	1823.5	1839.8	1864.3	1866.2	1844.0	1790.3	1700.9	1592.1	1478.9	1374.3
35°	1542.7	1551.1	1582.6	1632.2	1696.9	1751.1	1762.3	1714.1	1616.4	1494.6	1368.2
37.5°	1186.1	1231.6	1258.1	1310.3	1408.2	1507.9	1603.7	1639.0	1597.4	1488.2	1358.3
40°	1007.5	1018.6	1065.9	1124.7	1207.1	1310.8	1447.4	1546.0	1549.3	1473.4	1342.7
42.5°	862.3	876.4	908.8	955.7	1026.4	1130.1	1271.0	1401.2	1461.5	1432.6	1322.4
45°	689.9	700.5	724.2	760.3	814.5	900.1	1021.5	1171.9	1291.4	1338.1	1267.7
47.5°	566.8	572.5	593.1	620.5	660.7	723.1	817.0	947.6	1090.9	1191.3	1181.4
50°	500.1	506.6	522.3	543.1	576.9	629.7	704.7	813.5	961.3	1084.0	1108.5
52.5°	448.2	453.6	463.4	483.1	511.0	551.5	612.1	710.5	843.5	973.9	1030.6
55°	378.7	382.5	390.3	401.4	423.7	452.8	505.2	573.2	680.6	812.2	895.5
57.5°	321.6	323.3	328.4	338.7	354.0	375.3	413.1	470.8	547.9	666.3	758.2
60°	285.3	287.0	293.6	300.5	312.5	332.0	361.6	401.9	476.0	573.6	666.7
62.5°	256.4	257.4	260.2	267.2	277.7	292.7	316.0	348.9	407.9	493.7	581.6
65°	214.8	215.3	216.2	221.8	228.3	239.4	254.7	277.8	322.3	387.1	464.8
67.5°	175.0	175.7	178.9	180.8	187.6	193.4	202.4	220.2	251.5	295.2	355.6
70°	152.8	152.3	155.6	157.9	160.2	167.1	173.2	187.5	207.0	240.3	290.8
72.5°	132.1	130.8	132.2	133.0	136.2	140.9	146.9	155.7	170.7	193.6	232.3
75°	100.0	100.5	100.5	101.4	103.7	105.6	107.5	112.1	120.4	135.6	156.5
77.5°	70.2	69.5	71.4	71.7	73.0	75.1	76.7	78.6	81.9	88.3	99.0
80°	50.9	50.9	51.4	52.8	52.3	53.2	55.6	57.4	61.6	65.3	69.0
82.5°	39.1	38.7	39.1	39.4	39.3	40.3	41.1	41.5	43.1	44.9	47.5
85°	21.3	21.3	21.8	21.8	22.2	22.2	22.6	22.6	22.6	23.2	23.6
87.5°	12.2	11.9	11.3	11.3	11.7	12.0	11.5	11.0	10.8	10.6	10.6
90°	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1	15.2	14.3	12.5
92.5°	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7	232.3	287.0	291.6
95°	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1	771.8	788.7	643.6
97.5°	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2	976.5	842.3	574.7
100°	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9	1026.4	803.8	512.7
102.5°	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6	996.5	736.2	465.7
105°	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5	900.9	645.3	420.2
107.5°	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1	803.3	582.9	400.9
110°	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0	747.7	553.7	395.2



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6	706.4	536.6	395.2
115°	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2	661.4	518.1	397.9
117.5°	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9	634.5	509.0	403.8
120°	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3	619.6	504.7	409.5
122.5°	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0	606.7	501.1	414.5
125°	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1	589.3	496.7	422.8
127.5°	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6	573.3	494.5	432.3
130°	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9	562.6	493.1	438.0
132.5°	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0	554.0	493.1	444.3
135°	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8	543.9	493.1	453.1
137.5°	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3	534.8	494.2	461.1
140°	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6	530.6	494.9	464.7
142.5°	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3	527.0	495.6	466.8
145°	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2	521.7	494.9	469.1
147.5°	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9	516.1	492.6	470.0
150°	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5	511.8	490.4	470.0
152.5°	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3	506.8	487.7	469.3
155°	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6	498.5	482.5	467.3
157.5°	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9	490.6	477.2	465.0
160°	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8	484.3	473.6	462.9
162.5°	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0	478.6	469.3	460.7
165°	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2	470.0	462.9	457.5
167.5°	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8	461.6	456.6	452.5
170°	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1	456.6	453.1	450.4
172.5°	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7	451.7	448.8	447.5
175°	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7	445.1	444.2	444.2
177.5°	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9	442.2	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1159.0	1156.5	1151.6	1147.2	1141.7	1136.8	1133.5	1129.4	1124.2	1117.9	1112.8
5°	1210.3	1200.2	1186.7	1175.2	1160.3	1148.8	1136.8	1125.2	1113.6	1098.8	1085.7
7.5°	1267.2	1246.2	1225.7	1200.0	1176.6	1155.7	1135.8	1115.5	1095.7	1074.7	1054.4
10°	1302.0	1276.6	1248.3	1215.8	1186.2	1158.0	1132.1	1106.6	1079.8	1056.1	1030.6
12.5°	1334.6	1301.7	1269.4	1228.5	1192.9	1158.4	1125.4	1093.7	1065.0	1034.3	1007.0
15°	1364.1	1331.7	1295.6	1245.5	1196.0	1154.3	1115.4	1074.2	1038.6	1004.3	973.7
17.5°	1375.5	1341.5	1299.5	1251.4	1197.3	1144.9	1094.8	1049.5	1007.6	967.7	933.4
20°	1371.0	1338.1	1295.0	1249.2	1191.3	1136.8	1082.5	1032.5	985.8	943.6	907.0
22.5°	1360.2	1326.2	1284.7	1236.3	1181.3	1123.4	1065.5	1012.2	963.1	919.5	879.7
25°	1344.2	1297.9	1255.3	1208.0	1155.7	1098.3	1038.6	979.7	927.5	883.0	839.5
27.5°	1327.4	1269.6	1215.4	1168.5	1113.2	1061.9	1004.4	944.1	889.1	843.8	799.2
30°	1312.2	1247.4	1187.7	1134.4	1082.1	1033.5	978.8	920.0	863.5	816.8	771.4
32.5°	1293.3	1224.4	1158.8	1097.3	1046.9	998.6	949.2	893.0	837.9	789.7	743.6
35°	1269.6	1181.6	1110.4	1045.0	989.0	942.3	897.8	852.4	797.3	747.3	702.4
37.5°	1238.5	1138.6	1056.1	985.1	926.0	879.0	843.9	802.5	752.2	704.3	662.5
40°	1219.6	1107.5	1017.3	946.9	884.8	835.3	802.5	767.2	721.4	676.5	634.8
42.5°	1194.4	1079.1	978.0	904.6	842.2	794.5	761.3	730.6	692.1	649.8	605.2
45°	1145.0	1023.8	917.7	839.0	776.1	729.2	698.2	670.9	641.8	602.9	563.9
47.5°	1080.8	966.1	855.1	769.2	707.5	664.1	634.0	612.4	591.6	558.5	520.7
50°	1029.3	918.6	810.3	726.9	661.2	620.0	591.7	574.6	555.6	525.5	494.0
52.5°	968.6	869.8	763.6	678.4	616.4	577.7	550.6	533.5	517.8	493.3	463.3
55°	872.8	786.2	688.9	611.6	554.7	515.8	489.9	473.7	464.4	443.5	420.0
57.5°	762.3	700.3	614.5	539.9	489.6	451.2	432.2	418.4	408.0	393.2	376.6
60°	685.3	641.8	564.9	494.0	447.7	411.2	394.0	382.5	372.7	360.3	347.2
62.5°	607.1	575.4	508.5	447.7	405.1	374.5	358.5	348.0	336.8	328.4	315.8
65°	502.4	474.1	427.8	380.1	340.8	316.2	304.7	295.4	288.5	279.2	270.4
67.5°	390.7	379.3	347.3	314.5	286.2	264.4	254.4	247.9	239.6	234.0	228.0
70°	322.3	316.7	294.0	272.2	245.8	231.0	221.8	219.0	208.8	203.3	199.1
72.5°	261.5	259.0	245.8	230.8	212.1	199.2	190.6	187.5	181.0	176.6	173.9
75°	179.1	180.1	177.8	168.1	161.1	152.8	145.3	143.6	138.9	135.2	132.9
77.5°	113.3	118.1	118.2	117.8	115.0	109.9	106.8	105.5	100.9	99.5	99.0
80°	77.8	82.8	87.5	87.0	86.1	84.7	82.4	81.1	78.7	77.3	76.4
82.5°	51.9	56.6	60.5	63.0	62.8	61.4	59.8	59.2	58.7	57.7	57.5
85°	24.5	25.5	26.8	30.1	32.4	32.9	32.4	31.9	30.6	31.0	31.5
87.5°	10.8	10.5	10.7	10.3	9.6	11.1	11.9	12.0	11.5	11.1	10.7
90°	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9	1.8	3.6	5.4
92.5°	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9	13.2	20.7	31.7
95°	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3	30.2	37.4	47.2
97.5°	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8	49.8	54.8	64.6
100°	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3	64.1	67.7	77.4
102.5°	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3	78.3	81.1	91.7
105°	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6	100.6	105.0	114.0
107.5°	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4	125.2	129.4	136.7
110°	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7	141.5	145.1	153.1





TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1	157.9	160.8	168.8
115°	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9	181.6	184.2	192.3
117.5°	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2	203.8	206.7	214.7
120°	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4	218.1	221.7	229.7
122.5°	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4	232.3	235.1	243.2
125°	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2	251.0	255.5	263.5
127.5°	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0	266.7	272.4	282.6
130°	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3	276.0	283.1	294.6
132.5°	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4	283.7	292.3	305.3
135°	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9	295.5	306.2	320.5
137.5°	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6	309.2	319.2	333.5
140°	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1	317.8	328.5	342.7
142.5°	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1	327.1	337.0	351.2
145°	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0	341.8	350.7	363.2
147.5°	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7	356.8	364.4	376.0
150°	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0	366.8	373.0	384.6
152.5°	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0	376.0	381.6	391.6
155°	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1	388.1	393.4	402.3
157.5°	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8	399.7	403.9	411.6
160°	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7	406.8	410.4	416.6
162.5°	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1	413.2	416.8	422.3
165°	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7	422.0	424.6	429.1
167.5°	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2	429.3	430.9	433.4
170°	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4	433.5	434.4	436.2
172.5°	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3	435.7	436.6	438.3
175°	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6	438.8	439.7	440.6
177.5°	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2	440.8	440.8	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1109.0	1103.8	1100.1	1092.7	1087.5	1085.3	1081.3	1080.1	1084.2	1081.3	1080.8
5°	1076.0	1062.7	1052.0	1041.3	1029.7	1022.3	1011.2	1009.4	1006.6	1002.5	1001.5
7.5°	1036.5	1019.0	1005.3	987.7	972.4	960.1	946.2	939.7	936.0	930.7	923.5
10°	1009.9	989.0	970.4	952.9	933.9	918.6	904.7	894.1	887.2	880.7	877.9
12.5°	983.6	962.3	938.6	917.3	896.2	879.0	863.6	856.7	849.0	841.4	834.9
15°	942.7	914.4	888.5	864.0	846.0	827.4	812.6	802.5	790.9	787.6	775.1
17.5°	899.4	871.6	841.3	815.5	794.5	774.2	757.9	746.3	737.6	725.7	719.9
20°	872.4	839.5	809.9	786.2	763.0	739.0	722.3	712.6	704.3	694.6	689.9
22.5°	843.5	811.3	781.0	753.2	729.7	706.1	694.2	684.0	674.6	665.7	659.5
25°	801.0	768.7	736.6	707.9	683.4	666.3	652.4	640.8	635.7	627.0	620.5
27.5°	759.1	724.6	691.4	662.9	643.6	626.7	615.3	606.1	596.9	589.2	583.6
30°	732.0	696.9	660.8	638.0	617.7	601.5	589.0	580.1	573.2	566.2	562.1
32.5°	705.0	668.7	636.7	612.1	592.8	578.9	566.0	557.6	550.3	542.6	537.7
35°	661.6	624.6	598.7	574.6	555.6	542.7	533.9	521.8	515.8	510.2	505.2
37.5°	621.3	586.9	558.8	537.8	521.3	508.4	497.0	490.5	483.1	478.1	473.9
40°	591.7	560.3	534.8	512.6	500.5	486.2	475.5	467.2	461.6	455.1	450.5
42.5°	565.1	535.8	511.0	491.1	476.1	464.0	453.7	445.3	438.3	433.6	429.8
45°	527.4	498.2	474.1	455.6	441.8	430.2	419.5	415.4	406.1	400.6	398.7
47.5°	488.4	462.3	439.1	422.0	407.8	396.8	386.8	378.3	373.2	367.7	364.8
50°	462.1	437.1	415.4	398.7	384.8	372.7	363.5	357.9	351.0	345.9	342.1
52.5°	435.8	412.7	390.9	375.0	362.9	350.9	340.5	334.9	328.4	325.1	322.5
55°	398.2	373.6	355.2	339.4	326.9	315.8	306.0	300.5	296.3	293.1	292.1
57.5°	355.6	336.2	319.0	304.8	291.8	281.3	272.8	267.5	263.9	263.3	260.6
60°	327.8	310.2	294.4	279.2	268.0	258.3	250.9	245.0	241.2	240.8	239.9
62.5°	300.1	283.2	268.6	255.1	245.1	235.8	228.7	221.9	219.7	217.4	215.4
65°	258.9	243.5	231.5	220.9	210.2	202.3	195.4	191.2	186.1	183.3	178.3
67.5°	218.4	206.5	194.9	185.9	177.6	170.1	164.3	158.2	154.7	152.5	148.8
70°	191.7	182.4	170.9	161.1	154.6	148.6	144.0	137.1	134.7	132.9	131.0
72.5°	166.5	158.4	148.6	140.8	134.3	128.6	123.2	120.0	117.7	115.8	114.8
75°	131.0	123.1	114.9	109.2	104.7	100.0	97.2	94.9	94.0	93.5	91.7
77.5°	96.2	92.0	85.3	81.0	77.8	76.1	73.6	72.3	72.2	70.2	69.6
80°	73.7	71.3	65.7	63.9	61.6	59.7	58.3	56.0	53.7	52.8	51.4
82.5°	54.8	52.4	50.2	47.3	45.3	44.1	42.8	41.9	42.3	40.9	40.3
85°	29.2	26.8	25.9	25.5	24.5	25.5	25.0	24.5	24.1	23.6	24.1
87.5°	10.7	11.1	10.9	11.9	11.0	11.8	11.9	11.7	11.9	12.0	12.0
90°	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1	16.9	17.8	19.6
92.5°	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7	114.5	86.1	73.0
95°	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1	504.7	395.2	320.5
97.5°	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2	858.3	751.6	647.6
100°	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9	1051.3	959.6	867.0
102.5°	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6	1169.5	1125.5	1062.8
105°	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5	1236.4	1275.6	1265.8
107.5°	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1	1176.8	1277.4	1323.8
110°	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0	1109.1	1234.7	1310.4



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6	1042.2	1169.1	1258.4
115°	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2	946.3	1068.2	1165.2
117.5°	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9	879.9	984.9	1073.9
120°	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3	842.1	940.0	1018.3
122.5°	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0	815.0	902.2	975.6
125°	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1	778.9	856.3	920.4
127.5°	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6	744.4	816.6	876.6
130°	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9	720.1	789.6	847.5
132.5°	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0	697.3	760.4	816.1
135°	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8	662.3	719.3	770.0
137.5°	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3	631.0	678.3	721.4
140°	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6	612.4	653.4	690.8
142.5°	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3	596.7	632.0	664.4
145°	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2	576.8	604.4	628.5
147.5°	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9	560.3	581.5	599.6
150°	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5	551.0	567.9	584.0
152.5°	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3	541.7	557.2	569.7
155°	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6	527.9	540.4	550.1
157.5°	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9	514.7	524.3	532.0
160°	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8	504.7	513.6	519.9
162.5°	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0	496.1	503.6	509.2
165°	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2	483.4	488.7	493.1
167.5°	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8	470.9	475.0	478.2
170°	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1	463.8	466.5	468.2
172.5°	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7	457.4	459.3	460.4
175°	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7	447.7	449.5	449.5
177.5°	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9	443.6	443.6	443.6
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1080.5	1076.5	1075.3	1076.8	1075.3	1076.5	1080.5	1080.8	1081.3	1084.2	1080.1
5°	996.8	992.3	994.5	993.6	994.5	992.3	996.8	1001.5	1002.5	1006.6	1009.4
7.5°	923.4	917.6	911.5	913.5	911.5	917.6	923.4	923.5	930.7	936.0	939.7
10°	871.8	867.3	864.4	866.7	864.4	867.3	871.8	877.9	880.7	887.2	894.1
12.5°	828.5	825.7	823.3	822.3	823.3	825.7	828.5	834.9	841.4	849.0	856.7
15°	769.5	764.0	761.7	755.6	761.7	764.0	769.5	775.1	787.6	790.9	802.5
17.5°	715.2	713.4	707.3	704.7	707.3	713.4	715.2	719.9	725.7	737.6	746.3
20°	683.0	681.1	675.1	678.8	675.1	681.1	683.0	689.9	694.6	704.3	712.6
22.5°	656.3	652.2	650.2	649.2	650.2	652.2	656.3	659.5	665.7	674.6	684.0
25°	618.6	612.6	610.3	607.5	610.3	612.6	618.6	620.5	627.0	635.7	640.8
27.5°	581.0	577.7	574.7	574.0	574.7	577.7	581.0	583.6	589.2	596.9	606.1
30°	556.5	553.3	551.0	551.0	551.0	553.3	556.5	562.1	566.2	573.2	580.1
32.5°	534.7	532.2	529.9	529.5	529.9	532.2	534.7	537.7	542.6	550.3	557.6
35°	502.8	499.2	498.2	495.4	498.2	499.2	502.8	505.2	510.2	515.8	521.8
37.5°	469.8	466.7	466.6	466.4	466.6	466.7	469.8	473.9	478.1	483.1	490.5
40°	448.7	446.4	445.9	442.6	445.9	446.4	448.7	450.5	455.1	461.6	467.2
42.5°	426.1	424.9	423.3	421.9	423.3	424.9	426.1	429.8	433.6	438.3	445.3
45°	395.4	392.2	392.2	389.9	392.2	392.2	395.4	398.7	400.6	406.1	415.4
47.5°	363.7	361.2	361.5	359.1	361.5	361.2	363.7	364.8	367.7	373.2	378.3
50°	342.6	341.3	340.8	339.8	340.8	341.3	342.6	342.1	345.9	351.0	357.9
52.5°	321.6	320.8	322.6	320.6	322.6	320.8	321.6	322.5	325.1	328.4	334.9
55°	293.1	291.7	294.4	291.7	294.4	291.7	293.1	292.1	293.1	296.3	300.5
57.5°	260.4	259.1	261.6	260.2	261.6	259.1	260.4	260.6	263.3	263.9	267.5
60°	238.9	236.1	237.6	238.0	237.6	236.1	238.9	239.9	240.8	241.2	245.0
62.5°	213.4	211.7	212.7	210.6	212.7	211.7	213.4	215.4	217.4	219.7	221.9
65°	177.4	175.9	174.1	173.2	174.1	175.9	177.4	178.3	183.3	186.1	191.2
67.5°	149.0	145.7	145.6	146.3	145.6	145.7	149.0	148.8	152.5	154.7	158.2
70°	128.2	128.2	127.8	127.8	127.8	128.2	128.2	131.0	132.9	134.7	137.1
72.5°	113.8	113.4	112.6	112.3	112.6	113.4	113.8	114.8	115.8	117.7	120.0
75°	91.7	92.1	91.2	90.8	91.2	92.1	91.7	91.7	93.5	94.0	94.9
77.5°	67.7	65.7	66.8	65.7	66.8	65.7	67.7	69.6	70.2	72.2	72.3
80°	51.4	50.9	52.3	50.9	52.3	50.9	51.4	51.4	52.8	53.7	56.0
82.5°	40.7	40.2	40.8	39.9	40.8	40.2	40.7	40.3	40.9	42.3	41.9
85°	24.5	24.1	23.6	24.1	23.6	24.1	24.5	24.1	23.6	24.1	24.5
87.5°	12.4	12.0	12.2	12.2	12.2	12.0	12.4	12.0	12.0	11.9	11.7
90°	19.6	19.6	20.5	20.5	20.5	19.6	19.6	19.6	17.8	16.9	16.1
92.5°	61.6	59.5	58.2	56.8	58.2	59.5	61.6	73.0	86.1	114.5	157.7
95°	257.3	230.6	223.5	209.2	223.5	230.6	257.3	320.5	395.2	504.7	640.1
97.5°	592.7	542.8	517.0	505.6	517.0	542.8	592.7	647.6	751.6	858.3	953.2
100°	805.6	741.5	708.6	694.4	708.6	741.5	805.6	867.0	959.6	1051.3	1094.9
102.5°	997.2	951.6	915.8	905.1	915.8	951.6	997.2	1062.8	1125.5	1169.5	1142.6
105°	1237.3	1208.0	1190.2	1179.5	1190.2	1208.0	1237.3	1265.8	1275.6	1236.4	1114.5
107.5°	1338.3	1338.1	1332.2	1325.1	1332.2	1338.1	1338.3	1323.8	1277.4	1176.8	1014.1
110°	1350.4	1367.3	1373.5	1373.5	1373.5	1367.3	1350.4	1310.4	1234.7	1109.1	940.0



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1316.9	1345.9	1361.5	1367.8	1361.5	1345.9	1316.9	1258.4	1169.1	1042.2	881.6
115°	1234.7	1277.4	1302.3	1313.9	1302.3	1277.4	1234.7	1165.2	1068.2	946.3	808.2
117.5°	1143.4	1187.5	1212.2	1219.3	1212.2	1187.5	1143.4	1073.9	984.9	879.9	760.9
120°	1084.2	1126.9	1151.0	1158.2	1151.0	1126.9	1084.2	1018.3	940.0	842.1	735.3
122.5°	1034.4	1073.5	1097.6	1104.0	1097.6	1073.5	1034.4	975.6	902.2	815.0	716.0
125°	970.3	1006.7	1026.4	1035.3	1026.4	1006.7	970.3	920.4	856.3	778.9	688.1
127.5°	921.9	954.0	972.6	976.5	972.6	954.0	921.9	876.6	816.6	744.4	659.6
130°	892.0	921.3	939.1	944.5	939.1	921.3	892.0	847.5	789.6	720.1	641.9
132.5°	860.6	890.0	906.3	912.4	906.3	890.0	860.6	816.1	760.4	697.3	624.0
135°	809.1	838.6	854.5	859.9	854.5	838.6	809.1	770.0	719.3	662.3	600.8
137.5°	756.4	783.2	798.0	803.8	798.0	783.2	756.4	721.4	678.3	631.0	581.3
140°	723.7	746.9	760.2	764.6	760.2	746.9	723.7	690.8	653.4	612.4	570.6
142.5°	692.4	711.9	724.6	728.3	724.6	711.9	692.4	664.4	632.0	596.7	561.3
145°	649.8	664.9	674.8	678.3	674.8	664.9	649.8	628.5	604.4	576.8	549.2
147.5°	616.5	628.7	634.4	636.0	634.4	628.7	616.5	599.6	581.5	560.3	537.9
150°	597.3	608.0	611.5	612.4	611.5	608.0	597.3	584.0	567.9	551.0	531.5
152.5°	580.9	589.5	593.0	593.9	593.0	589.5	580.9	569.7	557.2	541.7	524.3
155°	559.0	565.3	567.9	568.8	567.9	565.3	559.0	550.1	540.4	527.9	513.6
157.5°	539.0	544.0	546.5	546.4	546.5	544.0	539.0	532.0	524.3	514.7	502.9
160°	526.1	530.6	532.4	531.5	532.4	530.6	526.1	519.9	513.6	504.7	495.8
162.5°	514.0	517.7	518.1	517.9	518.1	517.7	514.0	509.2	503.6	496.1	488.0
165°	496.7	498.5	498.5	498.5	498.5	498.5	496.7	493.1	488.7	483.4	477.2
167.5°	480.0	481.6	480.9	480.7	480.9	481.6	480.0	478.2	475.0	470.9	466.8
170°	470.0	470.9	470.9	470.0	470.9	470.9	470.0	468.2	466.5	463.8	461.1
172.5°	460.7	462.4	460.9	460.0	460.9	462.4	460.7	460.4	459.3	457.4	454.7
175°	449.5	450.4	448.6	447.7	448.6	450.4	449.5	449.5	449.5	447.7	447.7
177.5°	442.9	443.6	441.5	441.5	441.5	443.6	442.9	443.6	443.6	443.6	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1081.3	1085.3	1087.5	1092.7	1100.1	1103.8	1109.0	1112.8	1117.9	1124.2	1129.4
5°	1011.2	1022.3	1029.7	1041.3	1052.0	1062.7	1076.0	1085.7	1098.8	1113.6	1125.2
7.5°	946.2	960.1	972.4	987.7	1005.3	1019.0	1036.5	1054.4	1074.7	1095.7	1115.5
10°	904.7	918.6	933.9	952.9	970.4	989.0	1009.9	1030.6	1056.1	1079.8	1106.6
12.5°	863.6	879.0	896.2	917.3	938.6	962.3	983.6	1007.0	1034.3	1065.0	1093.7
15°	812.6	827.4	846.0	864.0	888.5	914.4	942.7	973.7	1004.3	1038.6	1074.2
17.5°	757.9	774.2	794.5	815.5	841.3	871.6	899.4	933.4	967.7	1007.6	1049.5
20°	722.3	739.0	763.0	786.2	809.9	839.5	872.4	907.0	943.6	985.8	1032.5
22.5°	694.2	706.1	729.7	753.2	781.0	811.3	843.5	879.7	919.5	963.1	1012.2
25°	652.4	666.3	683.4	707.9	736.6	768.7	801.0	839.5	883.0	927.5	979.7
27.5°	615.3	626.7	643.6	662.9	691.4	724.6	759.1	799.2	843.8	889.1	944.1
30°	589.0	601.5	617.7	638.0	660.8	696.9	732.0	771.4	816.8	863.5	920.0
32.5°	566.0	578.9	592.8	612.1	636.7	668.7	705.0	743.6	789.7	837.9	893.0
35°	533.9	542.7	555.6	574.6	598.7	624.6	661.6	702.4	747.3	797.3	852.4
37.5°	497.0	508.4	521.3	537.8	558.8	586.9	621.3	662.5	704.3	752.2	802.5
40°	475.5	486.2	500.5	512.6	534.8	560.3	591.7	634.8	676.5	721.4	767.2
42.5°	453.7	464.0	476.1	491.1	511.0	535.8	565.1	605.2	649.8	692.1	730.6
45°	419.5	430.2	441.8	455.6	474.1	498.2	527.4	563.9	602.9	641.8	670.9
47.5°	386.8	396.8	407.8	422.0	439.1	462.3	488.4	520.7	558.5	591.6	612.4
50°	363.5	372.7	384.8	398.7	415.4	437.1	462.1	494.0	525.5	555.6	574.6
52.5°	340.5	350.9	362.9	375.0	390.9	412.7	435.8	463.3	493.3	517.8	533.5
55°	306.0	315.8	326.9	339.4	355.2	373.6	398.2	420.0	443.5	464.4	473.7
57.5°	272.8	281.3	291.8	304.8	319.0	336.2	355.6	376.6	393.2	408.0	418.4
60°	250.9	258.3	268.0	279.2	294.4	310.2	327.8	347.2	360.3	372.7	382.5
62.5°	228.7	235.8	245.1	255.1	268.6	283.2	300.1	315.8	328.4	336.8	348.0
65°	195.4	202.3	210.2	220.9	231.5	243.5	258.9	270.4	279.2	288.5	295.4
67.5°	164.3	170.1	177.6	185.9	194.9	206.5	218.4	228.0	234.0	239.6	247.9
70°	144.0	148.6	154.6	161.1	170.9	182.4	191.7	199.1	203.3	208.8	219.0
72.5°	123.2	128.6	134.3	140.8	148.6	158.4	166.5	173.9	176.6	181.0	187.5
75°	97.2	100.0	104.7	109.2	114.9	123.1	131.0	132.9	135.2	138.9	143.6
77.5°	73.6	76.1	77.8	81.0	85.3	92.0	96.2	99.0	99.5	100.9	105.5
80°	58.3	59.7	61.6	63.9	65.7	71.3	73.7	76.4	77.3	78.7	81.1
82.5°	42.8	44.1	45.3	47.3	50.2	52.4	54.8	57.5	57.7	58.7	59.2
85°	25.0	25.5	24.5	25.5	25.9	26.8	29.2	31.5	31.0	30.6	31.9
87.5°	11.9	11.8	11.0	11.9	10.9	11.1	10.7	10.7	11.1	11.5	12.0
90°	15.2	14.3	12.5	11.6	9.8	8.9	7.1	5.4	3.6	1.8	0.9
92.5°	232.3	287.0	291.6	203.1	121.6	73.0	47.0	31.7	20.7	13.2	10.9
95°	771.8	788.7	643.6	397.9	202.1	106.8	66.8	47.2	37.4	30.2	29.3
97.5°	976.5	842.3	574.7	317.6	174.2	111.1	82.2	64.6	54.8	49.8	48.8
100°	1026.4	803.8	512.7	288.4	172.7	121.1	94.3	77.4	67.7	64.1	62.3
102.5°	996.5	736.2	465.7	276.3	179.1	133.1	107.2	91.7	81.1	78.3	77.3
105°	900.9	645.3	420.2	271.5	192.3	153.1	128.2	114.0	105.0	100.6	100.6
107.5°	803.3	582.9	400.9	279.7	211.9	174.0	151.5	136.7	129.4	125.2	123.4
110°	747.7	553.7	395.2	287.5	226.1	189.6	166.5	153.1	145.1	141.5	139.7



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	706.4	536.6	395.2	297.5	239.6	204.6	182.1	168.8	160.8	157.9	156.1
115°	661.4	518.1	397.9	312.5	260.8	227.9	205.6	192.3	184.2	181.6	179.9
117.5°	634.5	509.0	403.8	329.6	282.6	251.4	229.9	214.7	206.7	203.8	201.2
120°	619.6	504.7	409.5	340.9	298.2	267.1	244.8	229.7	221.7	218.1	215.4
122.5°	606.7	501.1	414.5	353.7	313.2	282.0	259.8	243.2	235.1	232.3	230.4
125°	589.3	496.7	422.8	371.2	333.0	303.5	280.4	263.5	255.5	251.0	249.2
127.5°	573.3	494.5	432.3	387.2	352.0	323.7	300.5	282.6	272.4	266.7	264.0
130°	562.6	493.1	438.0	397.9	364.1	336.4	313.3	294.6	283.1	276.0	273.3
132.5°	554.0	493.1	444.3	407.2	375.5	347.9	324.8	305.3	292.3	283.7	280.4
135°	543.9	493.1	453.1	420.2	390.7	363.2	339.1	320.5	306.2	295.5	291.9
137.5°	534.8	494.2	461.1	429.8	401.6	376.6	351.8	333.5	319.2	309.2	306.6
140°	530.6	494.9	464.7	436.2	409.5	383.7	359.6	342.7	328.5	317.8	315.1
142.5°	527.0	495.6	466.8	439.7	414.5	390.0	367.5	351.2	337.0	327.1	325.1
145°	521.7	494.9	469.1	445.1	422.8	399.7	379.2	363.2	350.7	341.8	340.0
147.5°	516.1	492.6	470.0	448.3	428.2	407.9	389.9	376.0	364.4	356.8	355.7
150°	511.8	490.4	470.0	450.4	431.8	412.1	397.0	384.6	373.0	366.8	365.0
152.5°	506.8	487.7	469.3	451.8	435.3	417.1	403.4	391.6	381.6	376.0	375.0
155°	498.5	482.5	467.3	453.1	438.8	423.7	411.3	402.3	393.4	388.1	388.1
157.5°	490.6	477.2	465.0	454.0	441.8	428.9	419.5	411.6	403.9	399.7	399.8
160°	484.3	473.6	462.9	454.0	443.3	431.8	423.7	416.6	410.4	406.8	407.7
162.5°	478.6	469.3	460.7	453.3	444.7	434.6	428.0	422.3	416.8	413.2	414.1
165°	470.0	462.9	457.5	452.2	445.1	438.0	432.7	429.1	424.6	422.0	423.7
167.5°	461.6	456.6	452.5	450.0	445.1	439.2	435.9	433.4	430.9	429.3	430.2
170°	456.6	453.1	450.4	448.6	445.1	440.6	438.0	436.2	434.4	433.5	434.4
172.5°	451.7	448.8	447.5	447.2	444.3	440.6	439.3	438.3	436.6	435.7	437.3
175°	445.1	444.2	444.2	445.1	443.3	440.6	440.6	440.6	439.7	438.8	440.6
177.5°	442.2	441.5	441.5	442.9	442.2	440.8	440.8	441.5	440.8	440.8	442.2
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1133.5	1136.8	1141.7	1147.2	1151.6	1156.5	1159.0	1159.0	1161.3	1166.1	1172.3
5°	1136.8	1148.8	1160.3	1175.2	1186.7	1200.2	1210.3	1220.0	1228.9	1239.9	1251.5
7.5°	1135.8	1155.7	1176.6	1200.0	1225.7	1246.2	1267.2	1283.7	1299.9	1321.2	1338.0
10°	1132.1	1158.0	1186.2	1215.8	1248.3	1276.6	1302.0	1325.2	1347.4	1370.6	1391.3
12.5°	1125.4	1158.4	1192.9	1228.5	1269.4	1301.7	1334.6	1359.2	1385.2	1410.5	1436.2
15°	1115.4	1154.3	1196.0	1245.5	1295.6	1331.7	1364.1	1396.0	1420.0	1448.8	1473.4
17.5°	1094.8	1144.9	1197.3	1251.4	1299.5	1341.5	1375.5	1405.8	1431.5	1463.0	1496.4
20°	1082.5	1136.8	1191.3	1249.2	1295.0	1338.1	1371.0	1402.5	1434.4	1475.6	1516.4
22.5°	1065.5	1123.4	1181.3	1236.3	1284.7	1326.2	1360.2	1398.8	1440.7	1487.5	1536.8
25°	1038.6	1098.3	1155.7	1208.0	1255.3	1297.9	1344.2	1396.0	1447.0	1508.5	1579.4
27.5°	1004.4	1061.9	1113.2	1168.5	1215.4	1269.6	1327.4	1383.6	1457.1	1541.8	1630.2
30°	978.8	1033.5	1082.1	1134.4	1187.7	1247.4	1312.2	1378.4	1465.9	1565.5	1670.6
32.5°	949.2	998.6	1046.9	1097.3	1158.8	1224.4	1293.3	1374.3	1478.9	1592.1	1700.9
35°	897.8	942.3	989.0	1045.0	1110.4	1181.6	1269.6	1368.2	1494.6	1616.4	1714.1
37.5°	843.9	879.0	926.0	985.1	1056.1	1138.6	1238.5	1358.3	1488.2	1597.4	1639.0
40°	802.5	835.3	884.8	946.9	1017.3	1107.5	1219.6	1342.7	1473.4	1549.3	1546.0
42.5°	761.3	794.5	842.2	904.6	978.0	1079.1	1194.4	1322.4	1432.6	1461.5	1401.2
45°	698.2	729.2	776.1	839.0	917.7	1023.8	1145.0	1267.7	1338.1	1291.4	1171.9
47.5°	634.0	664.1	707.5	769.2	855.1	966.1	1080.8	1181.4	1191.3	1090.9	947.6
50°	591.7	620.0	661.2	726.9	810.3	918.6	1029.3	1108.5	1084.0	961.3	813.5
52.5°	550.6	577.7	616.4	678.4	763.6	869.8	968.6	1030.6	973.9	843.5	710.5
55°	489.9	515.8	554.7	611.6	688.9	786.2	872.8	895.5	812.2	680.6	573.2
57.5°	432.2	451.2	489.6	539.9	614.5	700.3	762.3	758.2	666.3	547.9	470.8
60°	394.0	411.2	447.7	494.0	564.9	641.8	685.3	666.7	573.6	476.0	401.9
62.5°	358.5	374.5	405.1	447.7	508.5	575.4	607.1	581.6	493.7	407.9	348.9
65°	304.7	316.2	340.8	380.1	427.8	474.1	502.4	464.8	387.1	322.3	277.8
67.5°	254.4	264.4	286.2	314.5	347.3	379.3	390.7	355.6	295.2	251.5	220.2
70°	221.8	231.0	245.8	272.2	294.0	316.7	322.3	290.8	240.3	207.0	187.5
72.5°	190.6	199.2	212.1	230.8	245.8	259.0	261.5	232.3	193.6	170.7	155.7
75°	145.3	152.8	161.1	168.1	177.8	180.1	179.1	156.5	135.6	120.4	112.1
77.5°	106.8	109.9	115.0	117.8	118.2	118.1	113.3	99.0	88.3	81.9	78.6
80°	82.4	84.7	86.1	87.0	87.5	82.8	77.8	69.0	65.3	61.6	57.4
82.5°	59.8	61.4	62.8	63.0	60.5	56.6	51.9	47.5	44.9	43.1	41.5
85°	32.4	32.9	32.4	30.1	26.8	25.5	24.5	23.6	23.2	22.6	22.6
87.5°	11.9	11.1	9.6	10.3	10.7	10.5	10.8	10.6	10.6	10.8	11.0
90°	1.8	3.6	5.4	7.1	8.9	9.8	11.6	12.5	14.3	15.2	16.1
92.5°	13.2	20.7	31.7	47.0	73.0	121.6	203.1	291.6	287.0	232.3	157.7
95°	30.2	37.4	47.2	66.8	106.8	202.1	397.9	643.6	788.7	771.8	640.1
97.5°	49.8	54.8	64.6	82.2	111.1	174.2	317.6	574.7	842.3	976.5	953.2
100°	64.1	67.7	77.4	94.3	121.1	172.7	288.4	512.7	803.8	1026.4	1094.9
102.5°	78.3	81.1	91.7	107.2	133.1	179.1	276.3	465.7	736.2	996.5	1142.6
105°	100.6	105.0	114.0	128.2	153.1	192.3	271.5	420.2	645.3	900.9	1114.5
107.5°	125.2	129.4	136.7	151.5	174.0	211.9	279.7	400.9	582.9	803.3	1014.1
110°	141.5	145.1	153.1	166.5	189.6	226.1	287.5	395.2	553.7	747.7	940.0





TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.9	160.8	168.8	182.1	204.6	239.6	297.5	395.2	536.6	706.4	881.6
115°	181.6	184.2	192.3	205.6	227.9	260.8	312.5	397.9	518.1	661.4	808.2
117.5°	203.8	206.7	214.7	229.9	251.4	282.6	329.6	403.8	509.0	634.5	760.9
120°	218.1	221.7	229.7	244.8	267.1	298.2	340.9	409.5	504.7	619.6	735.3
122.5°	232.3	235.1	243.2	259.8	282.0	313.2	353.7	414.5	501.1	606.7	716.0
125°	251.0	255.5	263.5	280.4	303.5	333.0	371.2	422.8	496.7	589.3	688.1
127.5°	266.7	272.4	282.6	300.5	323.7	352.0	387.2	432.3	494.5	573.3	659.6
130°	276.0	283.1	294.6	313.3	336.4	364.1	397.9	438.0	493.1	562.6	641.9
132.5°	283.7	292.3	305.3	324.8	347.9	375.5	407.2	444.3	493.1	554.0	624.0
135°	295.5	306.2	320.5	339.1	363.2	390.7	420.2	453.1	493.1	543.9	600.8
137.5°	309.2	319.2	333.5	351.8	376.6	401.6	429.8	461.1	494.2	534.8	581.3
140°	317.8	328.5	342.7	359.6	383.7	409.5	436.2	464.7	494.9	530.6	570.6
142.5°	327.1	337.0	351.2	367.5	390.0	414.5	439.7	466.8	495.6	527.0	561.3
145°	341.8	350.7	363.2	379.2	399.7	422.8	445.1	469.1	494.9	521.7	549.2
147.5°	356.8	364.4	376.0	389.9	407.9	428.2	448.3	470.0	492.6	516.1	537.9
150°	366.8	373.0	384.6	397.0	412.1	431.8	450.4	470.0	490.4	511.8	531.5
152.5°	376.0	381.6	391.6	403.4	417.1	435.3	451.8	469.3	487.7	506.8	524.3
155°	388.1	393.4	402.3	411.3	423.7	438.8	453.1	467.3	482.5	498.5	513.6
157.5°	399.7	403.9	411.6	419.5	428.9	441.8	454.0	465.0	477.2	490.6	502.9
160°	406.8	410.4	416.6	423.7	431.8	443.3	454.0	462.9	473.6	484.3	495.8
162.5°	413.2	416.8	422.3	428.0	434.6	444.7	453.3	460.7	469.3	478.6	488.0
165°	422.0	424.6	429.1	432.7	438.0	445.1	452.2	457.5	462.9	470.0	477.2
167.5°	429.3	430.9	433.4	435.9	439.2	445.1	450.0	452.5	456.6	461.6	466.8
170°	433.5	434.4	436.2	438.0	440.6	445.1	448.6	450.4	453.1	456.6	461.1
172.5°	435.7	436.6	438.3	439.3	440.6	444.3	447.2	447.5	448.8	451.7	454.7
175°	438.8	439.7	440.6	440.6	440.6	443.3	445.1	444.2	444.2	445.1	447.7
177.5°	440.8	440.8	441.5	440.8	440.8	442.2	442.9	441.5	441.5	442.2	442.9
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5	441.5



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1177.1	1177.1	1183.5	1183.1	1187.2	1185.7	1186.4
5°	1265.4	1273.3	1280.2	1284.9	1291.8	1293.7	1292.7
7.5°	1356.9	1374.4	1383.0	1394.6	1396.8	1402.8	1402.2
10°	1413.6	1430.7	1443.7	1453.8	1459.0	1465.4	1465.9
12.5°	1458.0	1472.6	1484.1	1493.5	1499.7	1501.7	1503.0
15°	1492.8	1509.0	1522.4	1535.8	1543.7	1549.7	1553.0
17.5°	1527.8	1552.8	1576.5	1594.7	1605.7	1614.9	1614.8
20°	1554.8	1583.5	1613.2	1634.0	1655.3	1664.6	1666.0
22.5°	1583.7	1627.6	1665.8	1698.1	1726.1	1735.7	1739.3
25°	1643.7	1701.1	1760.0	1805.4	1837.7	1856.7	1859.5
27.5°	1716.2	1793.9	1855.8	1897.6	1924.6	1938.7	1941.7
30°	1767.4	1839.2	1894.7	1926.2	1938.7	1940.5	1933.6
32.5°	1790.3	1844.0	1866.2	1864.3	1839.8	1823.5	1817.2
35°	1762.3	1751.1	1696.9	1632.2	1582.6	1551.1	1542.7
37.5°	1603.7	1507.9	1408.2	1310.3	1258.1	1231.6	1186.1
40°	1447.4	1310.8	1207.1	1124.7	1065.9	1018.6	1007.5
42.5°	1271.0	1130.1	1026.4	955.7	908.8	876.4	862.3
45°	1021.5	900.1	814.5	760.3	724.2	700.5	689.9
47.5°	817.0	723.1	660.7	620.5	593.1	572.5	566.8
50°	704.7	629.7	576.9	543.1	522.3	506.6	500.1
52.5°	612.1	551.5	511.0	483.1	463.4	453.6	448.2
55°	505.2	452.8	423.7	401.4	390.3	382.5	378.7
57.5°	413.1	375.3	354.0	338.7	328.4	323.3	321.6
60°	361.6	332.0	312.5	300.5	293.6	287.0	285.3
62.5°	316.0	292.7	277.7	267.2	260.2	257.4	256.4
65°	254.7	239.4	228.3	221.8	216.2	215.3	214.8
67.5°	202.4	193.4	187.6	180.8	178.9	175.7	175.0
70°	173.2	167.1	160.2	157.9	155.6	152.3	152.8
72.5°	146.9	140.9	136.2	133.0	132.2	130.8	132.1
75°	107.5	105.6	103.7	101.4	100.5	100.5	100.0
77.5°	76.7	75.1	73.0	71.7	71.4	69.5	70.2
80°	55.6	53.2	52.3	52.8	51.4	50.9	50.9
82.5°	41.1	40.3	39.3	39.4	39.1	38.7	39.1
85°	22.6	22.2	22.2	21.8	21.8	21.3	21.3
87.5°	11.5	12.0	11.7	11.3	11.3	11.9	12.2
90°	16.9	17.8	19.6	19.6	19.6	20.5	20.5
92.5°	114.5	86.1	73.0	61.6	59.5	58.2	56.8
95°	504.7	395.2	320.5	257.3	230.6	223.5	209.2
97.5°	858.3	751.6	647.6	592.7	542.8	517.0	505.6
100°	1051.3	959.6	867.0	805.6	741.5	708.6	694.4
102.5°	1169.5	1125.5	1062.8	997.2	951.6	915.8	905.1
105°	1236.4	1275.6	1265.8	1237.3	1208.0	1190.2	1179.5
107.5°	1176.8	1277.4	1323.8	1338.3	1338.1	1332.2	1325.1
110°	1109.1	1234.7	1310.4	1350.4	1367.3	1373.5	1373.5



TEST NUMBER: P333570-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1042.2	1169.1	1258.4	1316.9	1345.9	1361.5	1367.8
115°	946.3	1068.2	1165.2	1234.7	1277.4	1302.3	1313.9
117.5°	879.9	984.9	1073.9	1143.4	1187.5	1212.2	1219.3
120°	842.1	940.0	1018.3	1084.2	1126.9	1151.0	1158.2
122.5°	815.0	902.2	975.6	1034.4	1073.5	1097.6	1104.0
125°	778.9	856.3	920.4	970.3	1006.7	1026.4	1035.3
127.5°	744.4	816.6	876.6	921.9	954.0	972.6	976.5
130°	720.1	789.6	847.5	892.0	921.3	939.1	944.5
132.5°	697.3	760.4	816.1	860.6	890.0	906.3	912.4
135°	662.3	719.3	770.0	809.1	838.6	854.5	859.9
137.5°	631.0	678.3	721.4	756.4	783.2	798.0	803.8
140°	612.4	653.4	690.8	723.7	746.9	760.2	764.6
142.5°	596.7	632.0	664.4	692.4	711.9	724.6	728.3
145°	576.8	604.4	628.5	649.8	664.9	674.8	678.3
147.5°	560.3	581.5	599.6	616.5	628.7	634.4	636.0
150°	551.0	567.9	584.0	597.3	608.0	611.5	612.4
152.5°	541.7	557.2	569.7	580.9	589.5	593.0	593.9
155°	527.9	540.4	550.1	559.0	565.3	567.9	568.8
157.5°	514.7	524.3	532.0	539.0	544.0	546.5	546.4
160°	504.7	513.6	519.9	526.1	530.6	532.4	531.5
162.5°	496.1	503.6	509.2	514.0	517.7	518.1	517.9
165°	483.4	488.7	493.1	496.7	498.5	498.5	498.5
167.5°	470.9	475.0	478.2	480.0	481.6	480.9	480.7
170°	463.8	466.5	468.2	470.0	470.9	470.9	470.0
172.5°	457.4	459.3	460.4	460.7	462.4	460.9	460.0
175°	447.7	449.5	449.5	449.5	450.4	448.6	447.7
177.5°	443.6	443.6	443.6	442.9	443.6	441.5	441.5
180°	441.5	441.5	441.5	441.5	441.5	441.5	441.5

(END OF REPORT)