

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333572-940

Luminaire Tested: **S125RDIP-S850D1035U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333572-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D1035U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6091.4 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333572-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333572-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	75	70	66	63	60	56	53	50	47	42	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22				19	
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7919	7919	7919
5°	7937	7847	7895
10°	7877	7774	7774
15°	7783	7616	7554
20°	7663	7396	7307
25°	7524	7180	7021
30°	7348	6927	6706
35°	7171	6666	6352
40°	7003	6395	6004
45°	6801	6090	5624
50°	6597	5760	5230
55°	6361	5443	4808
60°	6124	5059	4354
65°	5845	4614	3834
70°	5527	4056	3305
75°	5085	3421	2750
80°	4478	2685	2310
85°	3772	2193	2060



TEST NUMBER: P333572-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.3	1.9
10°-20°	322.2	5.3
20°-30°	467.2	7.7
30°-40°	532.5	8.7
40°-50°	519.1	8.5
50°-60°	436.9	7.2
60°-70°	306.3	5.0
70°-80°	157.4	2.6
80°-90°	42.3	0.7
90°-100°	76.6	1.3
100°-110°	226.3	3.7
110°-120°	383.2	6.3
120°-130°	504.3	8.3
130°-140°	565.1	9.3
140°-150°	553.9	9.1
150°-160°	465.2	7.6
160°-170°	309.2	5.1
170°-180°	108.2	1.8
0°-30°	904.7	14.9
0°-40°	1437.3	23.6
0°-60°	2393.2	39.3
0°-90°	2899.2	47.6
90°-120°	686.1	11.3
90°-150°	2309.5	37.9
90°-180°	3192.0	52.4
0°-180°	6091.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1226	1226	1226	1226	1226	
5°	1224	1220	1210	1219	1218	116
15°	1164	1158	1139	1138	1130	328
25°	1056	1041	1008	996	985	486
35°	910	886	846	819	806	569
45°	745	716	667	631	616	574
55°	565	534	483	443	427	505
65°	382	350	302	266	251	379
75°	204	175	137	118	110	216
85°	51	35	30	29	28	57
90°	1	8	14	19	21	6
95°	58	60	69	75	77	62
105°	203	208	213	218	221	217
115°	384	387	389	388	387	379
125°	560	565	566	564	564	501
135°	728	733	734	734	731	561
145°	882	886	888	888	886	551
155°	1010	1010	1010	1014	1010	465
165°	1098	1096	1097	1100	1095	310
175°	1141	1138	1138	1142	1137	108
180°	1144	1144	1144	1144	1144	



TEST NUMBER: P333572-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1228.3	1227.9	1227.4	1226.9	1226.4	1225.3	1223.7	1222.0	1220.4	1218.7	1220.4
5°	1224.3	1223.5	1222.6	1221.8	1221.0	1219.5	1217.2	1215.0	1212.6	1210.4	1212.5
7.5°	1212.3	1211.5	1210.7	1209.9	1209.2	1207.4	1204.7	1201.9	1199.3	1196.5	1197.9
10°	1201.1	1200.5	1199.9	1199.3	1198.6	1196.9	1194.1	1191.1	1188.3	1185.4	1186.0
12.5°	1188.6	1187.8	1187.0	1186.2	1185.4	1183.1	1179.2	1175.4	1171.5	1167.6	1168.1
15°	1164.1	1162.9	1161.6	1160.4	1159.1	1156.4	1152.1	1147.7	1143.4	1139.1	1138.9
17.5°	1136.5	1134.6	1132.7	1130.9	1128.9	1125.2	1119.8	1114.4	1108.9	1103.5	1102.5
20°	1115.0	1112.9	1110.9	1108.8	1106.8	1102.4	1095.9	1089.3	1082.7	1076.1	1075.1
22.5°	1091.3	1089.2	1087.2	1085.1	1083.1	1078.6	1071.7	1064.8	1057.8	1051.0	1048.9
25°	1055.8	1052.7	1049.5	1046.5	1043.4	1038.0	1030.5	1022.8	1015.2	1007.6	1005.0
27.5°	1015.0	1011.3	1007.5	1003.8	1000.1	994.1	986.0	977.8	969.6	961.4	957.7
30°	985.3	981.4	977.6	973.7	969.7	963.4	954.8	946.2	937.5	928.9	924.2
32.5°	956.4	951.9	947.4	942.8	938.2	931.5	922.7	913.9	905.1	896.3	891.1
35°	909.5	904.5	899.6	894.6	889.7	882.5	873.3	864.1	854.8	845.5	839.5
37.5°	863.3	857.3	851.3	845.3	839.3	831.5	822.0	812.3	802.8	793.3	786.1
40°	830.7	824.6	818.3	812.2	806.0	798.0	788.1	778.2	768.4	758.5	750.6
42.5°	796.7	790.3	784.0	777.6	771.2	763.0	752.8	742.6	732.4	722.2	714.7
45°	744.6	738.6	732.6	726.7	720.7	712.0	700.7	689.5	678.1	666.8	658.5
47.5°	690.7	684.4	678.1	671.8	665.5	656.7	645.2	633.8	622.4	611.0	602.5
50°	656.6	649.8	643.0	636.2	629.5	620.2	608.4	596.7	585.0	573.3	564.6
52.5°	619.6	612.6	605.6	598.7	591.7	582.7	571.7	560.6	549.5	538.4	529.1
55°	564.9	558.3	551.8	545.2	538.6	529.5	518.0	506.5	495.0	483.4	474.1
57.5°	509.7	502.7	495.6	488.6	481.6	472.5	461.4	450.2	439.2	428.0	419.0
60°	474.1	467.0	459.8	452.5	445.3	436.2	425.1	413.9	402.9	391.7	382.7
62.5°	436.4	429.5	422.7	415.7	408.8	399.8	388.5	377.3	366.0	354.7	346.3
65°	382.5	375.5	368.5	361.5	354.5	345.5	334.7	323.7	312.8	301.9	293.6
67.5°	329.0	321.9	315.0	308.0	301.0	292.2	281.8	271.3	260.9	250.4	242.9
70°	292.7	285.6	278.7	271.6	264.7	256.0	245.8	235.4	225.2	214.8	208.5
72.5°	257.1	250.2	243.4	236.6	229.8	221.5	211.9	202.2	192.6	183.0	177.1
75°	203.8	197.6	191.4	185.2	179.1	171.7	163.0	154.4	145.7	137.1	132.5
77.5°	150.8	145.8	140.9	136.0	131.0	125.1	118.2	111.3	104.3	97.5	94.3
80°	120.4	115.5	110.5	105.6	100.7	95.3	89.5	83.7	78.0	72.2	70.4
82.5°	90.8	86.3	81.9	77.4	72.9	68.8	64.8	60.9	56.9	53.0	52.1
85°	50.9	47.3	43.5	39.9	36.1	33.7	32.7	31.7	30.7	29.6	29.4
87.5°	17.2	16.4	15.5	14.7	13.9	13.6	13.6	13.7	13.8	14.0	14.2
90°	0.9	2.5	4.0	5.6	7.2	8.7	10.1	11.5	12.8	14.3	15.2
92.5°	21.6	22.6	23.7	24.9	25.9	27.4	29.1	30.8	32.5	34.2	35.5
95°	57.9	58.2	58.7	59.0	59.5	60.6	62.6	64.6	66.6	68.6	69.9
97.5°	96.1	96.3	96.5	96.7	96.8	98.3	100.9	103.7	106.4	109.1	110.5
100°	124.7	124.7	124.7	124.7	124.7	125.9	128.5	131.1	133.7	136.2	137.9
102.5°	155.2	156.0	156.9	157.7	158.5	159.4	160.8	162.1	163.4	164.7	166.7
105°	203.0	203.9	204.9	206.0	207.0	208.0	209.2	210.4	211.6	212.8	213.9
107.5°	255.7	256.6	257.6	258.7	259.7	260.6	261.4	262.4	263.3	264.2	264.8
110°	292.0	293.0	294.0	295.0	296.0	296.8	297.3	297.9	298.5	299.1	299.7



TEST NUMBER: P333572-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.0	329.6	330.0	330.6	331.1	331.7	332.5	333.2	333.9	334.7	335.0
115°	383.7	384.5	385.3	386.1	386.8	387.4	387.8	388.3	388.6	389.1	388.9
117.5°	438.5	438.9	439.3	439.6	440.0	440.3	440.7	441.0	441.4	441.8	441.9
120°	472.7	473.7	474.7	475.7	476.7	477.2	477.4	477.7	477.9	478.0	478.0
122.5°	509.8	510.1	510.5	510.9	511.2	511.6	512.1	512.6	513.2	513.6	513.5
125°	560.0	561.2	562.3	563.6	564.7	565.4	565.6	565.8	566.0	566.2	565.8
127.5°	613.4	614.0	614.7	615.4	616.1	616.5	616.8	617.0	617.2	617.5	617.2
130°	645.4	646.4	647.4	648.4	649.3	650.1	650.5	650.9	651.2	651.7	651.5
132.5°	677.4	679.1	680.7	682.3	683.9	684.7	684.7	684.6	684.5	684.4	684.2
135°	728.3	729.4	730.6	731.7	733.0	733.7	733.9	734.1	734.2	734.4	734.4
137.5°	776.0	777.0	778.2	779.4	780.5	781.3	781.8	782.2	782.7	783.0	783.3
140°	806.6	807.5	808.5	809.5	810.5	811.3	811.9	812.5	813.1	813.7	814.0
142.5°	837.1	838.0	838.8	839.6	840.5	841.3	842.0	842.8	843.6	844.3	844.5
145°	882.3	883.1	883.8	884.6	885.4	886.1	886.7	887.3	887.9	888.5	888.5
147.5°	923.9	924.3	924.8	925.2	925.6	926.1	926.6	927.0	927.5	928.0	928.4
150°	951.6	951.5	951.3	951.1	950.9	951.2	952.0	952.8	953.5	954.3	954.3
152.5°	974.5	974.7	975.0	975.3	975.5	975.9	976.2	976.5	976.8	977.1	977.6
155°	1009.5	1009.5	1009.5	1009.5	1009.5	1009.6	1009.9	1010.0	1010.2	1010.4	1011.2
157.5°	1040.9	1040.4	1040.0	1039.6	1039.1	1039.0	1039.2	1039.4	1039.6	1039.8	1040.6
160°	1059.4	1058.8	1058.2	1057.6	1057.0	1056.9	1057.0	1057.2	1057.4	1057.6	1058.4
162.5°	1075.8	1075.3	1074.9	1074.4	1074.1	1073.8	1073.9	1073.9	1074.0	1074.0	1075.0
165°	1097.7	1097.3	1096.9	1096.4	1096.1	1096.0	1096.2	1096.4	1096.5	1096.8	1097.6
167.5°	1116.2	1115.4	1114.6	1113.8	1113.0	1112.6	1112.6	1112.6	1112.6	1112.6	1113.8
170°	1126.1	1125.3	1124.5	1123.8	1123.0	1122.6	1122.6	1122.6	1122.6	1122.6	1123.8
172.5°	1133.3	1132.5	1131.7	1130.9	1130.2	1129.7	1129.7	1129.7	1129.7	1129.7	1130.9
175°	1141.3	1140.5	1139.7	1138.9	1138.1	1137.7	1137.7	1137.7	1137.7	1137.7	1138.9
177.5°	1145.4	1144.8	1144.2	1143.4	1142.8	1142.5	1142.3	1142.1	1142.0	1141.8	1142.8
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0



TEST NUMBER: P333572-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2	1226.2
2.5°	1222.0	1223.7	1225.3	1226.1	1225.9	1225.7	1225.6	1225.4
5°	1214.5	1216.6	1218.6	1219.5	1219.1	1218.6	1218.3	1217.8
7.5°	1199.4	1200.9	1202.3	1202.7	1202.3	1201.8	1201.4	1201.0
10°	1186.6	1187.2	1187.8	1187.8	1187.2	1186.6	1186.0	1185.4
12.5°	1168.5	1168.9	1169.4	1169.2	1168.2	1167.2	1166.4	1165.4
15°	1138.7	1138.4	1138.3	1137.3	1135.4	1133.5	1131.7	1129.8
17.5°	1101.4	1100.5	1099.4	1098.1	1096.6	1095.1	1093.6	1092.1
20°	1074.1	1073.0	1072.0	1070.6	1068.7	1066.8	1065.0	1063.2
22.5°	1046.9	1044.9	1042.9	1041.1	1039.6	1038.0	1036.5	1035.0
25°	1002.3	999.6	996.9	994.4	992.1	989.9	987.7	985.3
27.5°	954.0	950.2	946.5	943.5	941.4	939.1	937.0	934.8
30°	919.4	914.7	909.9	906.7	904.8	902.9	901.1	899.2
32.5°	885.8	880.6	875.4	871.6	869.2	866.9	864.5	862.2
35°	833.6	827.6	821.6	817.3	814.3	811.5	808.6	805.7
37.5°	779.0	771.8	764.6	759.6	756.9	754.0	751.3	748.5
40°	742.8	735.0	727.2	722.0	719.6	717.1	714.6	712.2
42.5°	707.2	699.7	692.2	686.6	683.1	679.4	675.7	672.2
45°	650.3	642.1	633.8	628.2	625.1	622.1	618.9	615.8
47.5°	594.1	585.6	577.1	571.1	567.8	564.4	560.9	557.5
50°	556.0	547.3	538.7	532.8	529.8	526.6	523.5	520.5
52.5°	519.9	510.5	501.2	495.0	492.0	488.8	485.8	482.7
55°	464.9	455.7	446.4	440.1	436.8	433.5	430.3	427.0
57.5°	409.9	400.9	391.8	385.8	382.9	380.0	377.1	374.2
60°	373.6	364.5	355.5	349.5	346.3	343.3	340.2	337.1
62.5°	337.9	329.5	321.1	315.4	312.3	309.2	306.1	303.0
65°	285.4	277.2	268.9	263.3	260.2	257.2	254.0	250.9
67.5°	235.3	227.8	220.3	215.3	212.9	210.4	207.9	205.5
70°	202.1	195.7	189.3	184.9	182.4	179.9	177.5	175.0
72.5°	171.2	165.3	159.4	155.7	154.0	152.4	150.8	149.1
75°	128.0	123.5	119.0	116.0	114.5	113.1	111.6	110.2
77.5°	91.0	87.9	84.7	82.7	81.6	80.5	79.5	78.4
80°	68.6	66.7	64.8	63.7	63.3	62.9	62.4	62.1
82.5°	51.3	50.4	49.5	49.0	48.7	48.5	48.2	48.0
85°	29.2	29.0	28.8	28.6	28.4	28.2	28.0	27.8
87.5°	14.4	14.5	14.7	14.8	14.8	14.7	14.7	14.6
90°	16.2	17.2	18.2	19.0	19.6	20.2	20.8	21.4
92.5°	36.8	38.1	39.4	40.3	40.8	41.1	41.6	42.0
95°	71.3	72.7	74.1	75.0	75.3	75.8	76.2	76.6
97.5°	111.7	113.1	114.4	115.1	115.4	115.7	115.8	116.1
100°	139.7	141.5	143.3	144.5	144.8	145.2	145.6	146.0
102.5°	168.5	170.5	172.5	173.7	174.2	174.8	175.4	175.9
105°	215.2	216.3	217.5	218.4	219.0	219.6	220.2	220.8
107.5°	265.4	266.0	266.6	266.9	266.8	266.8	266.8	266.7
110°	300.3	300.9	301.5	301.7	301.5	301.3	301.1	300.9





TEST NUMBER: P333572-940

CATALOG NUMBER: S125RDIP-S850D1035U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	335.3	335.6	335.8	335.8	335.5	335.1	334.7	334.4
115°	388.6	388.4	388.3	388.1	387.8	387.6	387.4	387.3
117.5°	442.0	442.2	442.4	442.0	441.2	440.5	439.7	438.9
120°	478.0	478.0	478.0	477.7	476.9	476.1	475.3	474.5
122.5°	513.4	513.2	513.0	512.6	512.0	511.4	510.8	510.1
125°	565.4	565.0	564.6	564.3	564.1	563.9	563.7	563.6
127.5°	617.1	616.9	616.7	616.4	616.0	615.5	615.2	614.8
130°	651.2	651.0	650.9	650.6	650.1	649.8	649.3	649.0
132.5°	684.0	683.9	683.6	683.2	682.7	682.2	681.6	681.0
135°	734.4	734.4	734.4	734.1	733.3	732.5	731.6	730.8
137.5°	783.5	783.7	784.0	783.6	782.7	781.7	780.7	779.7
140°	814.5	814.8	815.3	814.9	814.0	813.0	812.0	811.0
142.5°	844.8	845.0	845.3	844.9	843.9	842.9	842.0	840.9
145°	888.5	888.5	888.5	888.1	887.6	887.0	886.4	885.8
147.5°	928.9	929.4	929.9	929.4	928.1	926.8	925.4	924.1
150°	954.3	954.3	954.3	954.1	953.8	953.3	953.0	952.5
152.5°	978.1	978.6	979.0	978.9	978.2	977.5	976.8	976.1
155°	1012.0	1012.8	1013.6	1013.5	1012.5	1011.5	1010.5	1009.5
157.5°	1041.3	1042.1	1042.9	1042.7	1041.4	1040.1	1038.8	1037.5
160°	1059.2	1060.0	1060.8	1060.7	1059.7	1058.7	1057.7	1056.7
162.5°	1075.8	1076.8	1077.8	1077.7	1076.6	1075.4	1074.2	1073.1
165°	1098.3	1099.1	1099.9	1099.7	1098.6	1097.3	1096.2	1095.0
167.5°	1115.0	1116.2	1117.4	1117.3	1116.2	1114.9	1113.7	1112.4
170°	1125.0	1126.1	1127.3	1127.2	1125.9	1124.4	1123.1	1121.7
172.5°	1132.1	1133.3	1134.4	1134.4	1133.2	1132.0	1130.8	1129.5
175°	1140.1	1141.3	1142.5	1142.4	1141.0	1139.6	1138.2	1136.8
177.5°	1143.7	1144.7	1145.6	1145.6	1144.4	1143.4	1142.2	1141.1
180°	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0	1144.0

(END OF REPORT)