

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333576-940

Luminaire Tested: **S125RDIP-S850D1205U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333576-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1205U940-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6779.1 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43				43
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37				37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32				32
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31	27				27
4	74	63	56	50	67	58	52	47	49	44	40	40	36	34	32	29	27	24				24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21				21
6	63	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18				18
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19	16				16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14				14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				13
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7284	7284	7284	7284
5°	8381	7295	6442	7295
10°	9613	7257	5684	7257
15°	10384	7182	5052	7182
20°	11450	7096	4665	7096
25°	13251	6981	4329	6981
30°	14420	6861	4109	6861
35°	12163	6720	3906	6720
40°	8494	6468	3731	6468
45°	6301	6128	3561	6128
50°	5025	5773	3414	5773
55°	4264	5334	3284	5334
60°	3685	4941	3074	4941
65°	3283	4514	2647	4514
70°	2885	4135	2413	4135
75°	2495	3583	2266	3583
80°	1893	3016	1893	3016
85°	1578	2364	1786	2364



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.2	1.6
10°-20°	317.0	4.7
20°-30°	502.6	7.4
30°-40°	606.1	8.9
40°-50°	541.2	8.0
50°-60°	415.1	6.1
60°-70°	269.7	4.0
70°-80°	131.1	1.9
80°-90°	34.2	0.5
90°-100°	372.5	5.5
100°-110°	800.8	11.8
110°-120°	751.5	11.1
120°-130°	609.1	9.0
130°-140°	488.8	7.2
140°-150°	368.8	5.4
150°-160°	259.6	3.8
160°-170°	153.0	2.3
170°-180°	49.8	0.7
0°-30°	927.7	13.7
0°-40°	1533.8	22.6
0°-60°	2490.1	36.7
0°-90°	2925.1	43.1
90°-120°	1924.8	28.4
90°-150°	3391.5	50.0
90°-180°	3854.0	56.9
0°-180°	6779.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1128	1128	1128	1128	1128	
5°	1293	1125	994	1125	1293	129
15°	1553	1074	756	1074	1553	445
25°	1860	980	608	980	1860	854
35°	1543	852	495	852	1543	932
45°	690	671	390	671	690	550
55°	379	474	292	474	379	344
65°	215	295	173	295	215	214
75°	100	144	91	144	100	106
85°	21	32	24	32	21	25
90°	24	1	24	1	24	17
95°	244	34	244	34	244	345
105°	1373	117	1373	117	1373	1365
115°	1529	209	1529	209	1529	1494
125°	1205	290	1205	290	1205	1090
135°	1001	340	1001	340	1001	776
145°	790	396	790	396	790	502
155°	662	452	662	452	662	309
165°	580	493	580	493	580	166
175°	521	513	521	513	521	51
180°	514	514	514	514	514	



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1186.4	1185.7	1187.2	1183.1	1183.5	1177.1	1177.1	1172.3	1166.1	1161.3	1159.0
5°	1292.7	1293.7	1291.8	1284.9	1280.2	1273.3	1265.4	1251.5	1239.9	1228.9	1220.0
7.5°	1402.2	1402.8	1396.8	1394.6	1383.0	1374.4	1356.9	1338.0	1321.2	1299.9	1283.7
10°	1465.9	1465.4	1459.0	1453.8	1443.7	1430.7	1413.6	1391.3	1370.6	1347.4	1325.2
12.5°	1503.0	1501.7	1499.7	1493.5	1484.1	1472.6	1458.0	1436.2	1410.5	1385.2	1359.2
15°	1553.0	1549.7	1543.7	1535.8	1522.4	1509.0	1492.8	1473.4	1448.8	1420.0	1396.0
17.5°	1614.8	1614.9	1605.7	1594.7	1576.5	1552.8	1527.8	1496.4	1463.0	1431.5	1405.8
20°	1666.0	1664.6	1655.3	1634.0	1613.2	1583.5	1554.8	1516.4	1475.6	1434.4	1402.5
22.5°	1739.3	1735.7	1726.1	1698.1	1665.8	1627.6	1583.7	1536.8	1487.5	1440.7	1398.8
25°	1859.5	1856.7	1837.7	1805.4	1760.0	1701.1	1643.7	1579.4	1508.5	1447.0	1396.0
27.5°	1941.7	1938.7	1924.6	1897.6	1855.8	1793.9	1716.2	1630.2	1541.8	1457.1	1383.6
30°	1933.6	1940.5	1938.7	1926.2	1894.7	1839.2	1767.4	1670.6	1565.5	1465.9	1378.4
32.5°	1817.2	1823.5	1839.8	1864.3	1866.2	1844.0	1790.3	1700.9	1592.1	1478.9	1374.3
35°	1542.7	1551.1	1582.6	1632.2	1696.9	1751.1	1762.3	1714.1	1616.4	1494.6	1368.2
37.5°	1186.1	1231.6	1258.1	1310.3	1408.2	1507.9	1603.7	1639.0	1597.4	1488.2	1358.3
40°	1007.5	1018.6	1065.9	1124.7	1207.1	1310.8	1447.4	1546.0	1549.3	1473.4	1342.7
42.5°	862.3	876.4	908.8	955.7	1026.4	1130.1	1271.0	1401.2	1461.5	1432.6	1322.4
45°	689.9	700.5	724.2	760.3	814.5	900.1	1021.5	1171.9	1291.4	1338.1	1267.7
47.5°	566.8	572.5	593.1	620.5	660.7	723.1	817.0	947.6	1090.9	1191.3	1181.4
50°	500.1	506.6	522.3	543.1	576.9	629.7	704.7	813.5	961.3	1084.0	1108.5
52.5°	448.2	453.6	463.4	483.1	511.0	551.5	612.1	710.5	843.5	973.9	1030.6
55°	378.7	382.5	390.3	401.4	423.7	452.8	505.2	573.2	680.6	812.2	895.5
57.5°	321.6	323.3	328.4	338.7	354.0	375.3	413.1	470.8	547.9	666.3	758.2
60°	285.3	287.0	293.6	300.5	312.5	332.0	361.6	401.9	476.0	573.6	666.7
62.5°	256.4	257.4	260.2	267.2	277.7	292.7	316.0	348.9	407.9	493.7	581.6
65°	214.8	215.3	216.2	221.8	228.3	239.4	254.7	277.8	322.3	387.1	464.8
67.5°	175.0	175.7	178.9	180.8	187.6	193.4	202.4	220.2	251.5	295.2	355.6
70°	152.8	152.3	155.6	157.9	160.2	167.1	173.2	187.5	207.0	240.3	290.8
72.5°	132.1	130.8	132.2	133.0	136.2	140.9	146.9	155.7	170.7	193.6	232.3
75°	100.0	100.5	100.5	101.4	103.7	105.6	107.5	112.1	120.4	135.6	156.5
77.5°	70.2	69.5	71.4	71.7	73.0	75.1	76.7	78.6	81.9	88.3	99.0
80°	50.9	50.9	51.4	52.8	52.3	53.2	55.6	57.4	61.6	65.3	69.0
82.5°	39.1	38.7	39.1	39.4	39.3	40.3	41.1	41.5	43.1	44.9	47.5
85°	21.3	21.3	21.8	21.8	22.2	22.2	22.6	22.6	22.6	23.2	23.6
87.5°	12.9	12.6	11.9	11.9	12.3	12.7	12.1	11.5	11.3	11.1	11.1
90°	23.8	23.8	22.8	22.8	22.8	20.7	19.7	18.6	17.7	16.6	14.5
92.5°	66.1	67.8	69.2	71.7	85.0	100.3	133.2	183.6	270.5	334.0	339.5
95°	243.5	260.1	268.3	299.4	373.0	460.0	587.5	744.9	898.3	918.0	749.1
97.5°	588.5	601.8	631.9	689.8	753.9	874.9	999.1	1109.5	1136.7	980.3	669.0
100°	808.2	824.7	863.1	937.7	1009.1	1117.0	1223.7	1274.4	1194.6	935.6	596.8
102.5°	1053.6	1066.0	1107.6	1160.7	1237.2	1310.1	1361.3	1330.0	1159.8	856.8	542.1
105°	1372.9	1385.3	1406.0	1440.2	1473.4	1484.8	1439.2	1297.3	1048.6	751.2	489.0
107.5°	1542.4	1550.7	1557.6	1557.7	1541.0	1486.8	1369.8	1180.4	935.0	678.4	466.6
110°	1598.7	1598.7	1591.5	1571.8	1525.2	1437.1	1291.0	1094.1	870.3	644.4	460.0



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1592.1	1584.7	1566.6	1532.9	1464.6	1360.8	1213.1	1026.2	822.2	624.6	460.0
115°	1529.3	1515.8	1486.8	1437.1	1356.3	1243.3	1101.4	940.8	769.8	603.1	463.2
117.5°	1419.2	1411.0	1382.2	1330.8	1250.0	1146.4	1024.1	885.6	738.5	592.5	470.0
120°	1348.0	1339.7	1311.7	1262.0	1185.4	1094.1	980.2	855.9	721.1	587.5	476.6
122.5°	1285.0	1277.6	1249.6	1204.0	1135.6	1050.3	948.7	833.5	706.2	583.4	482.4
125°	1205.1	1194.6	1171.9	1129.4	1071.4	996.8	906.6	800.9	685.9	578.2	492.1
127.5°	1136.7	1132.1	1110.5	1073.0	1020.4	950.6	866.4	767.8	667.3	575.7	503.1
130°	1099.3	1093.1	1072.4	1038.2	986.4	919.1	838.2	747.1	654.9	574.0	509.8
132.5°	1062.0	1055.0	1035.9	1001.7	949.9	885.0	811.7	726.3	644.9	574.0	517.2
135°	1000.9	994.7	976.1	941.8	896.3	837.2	770.9	699.4	633.1	574.0	527.4
137.5°	935.6	928.8	911.6	880.5	839.7	789.5	734.4	676.6	622.5	575.2	536.7
140°	890.0	884.8	869.3	842.4	804.1	760.5	712.8	664.1	617.5	576.0	540.8
142.5°	847.7	843.4	828.7	805.9	773.4	735.7	694.6	653.4	613.4	576.9	543.3
145°	789.5	785.4	774.0	756.3	731.5	703.6	671.4	639.3	607.2	576.0	546.1
147.5°	740.2	738.3	731.7	717.6	697.9	676.8	652.1	626.1	600.7	573.4	547.1
150°	712.8	711.9	707.7	695.3	679.7	661.0	641.4	618.6	595.8	570.9	547.1
152.5°	691.3	690.3	686.1	676.2	663.2	648.6	630.6	610.3	590.0	567.6	546.3
155°	662.1	661.0	657.9	650.7	640.3	628.9	614.4	597.8	580.2	561.6	543.9
157.5°	636.0	636.1	633.3	627.2	619.2	610.3	599.1	585.4	571.1	555.4	541.3
160°	618.6	619.6	617.5	612.3	605.1	597.8	587.5	577.1	563.7	551.3	538.8
162.5°	602.8	603.1	602.6	598.2	592.6	586.2	577.6	568.0	557.1	546.3	536.3
165°	580.2	580.2	580.2	578.2	574.0	568.8	562.6	555.4	547.1	538.8	532.5
167.5°	559.5	559.7	560.5	558.7	556.6	552.9	548.1	543.3	537.3	531.5	526.7
170°	547.1	548.1	548.1	547.1	545.0	543.0	539.8	536.7	531.5	527.4	524.3
172.5°	535.5	536.5	538.1	536.3	535.9	534.7	532.4	529.2	525.8	522.5	520.9
175°	521.2	522.2	524.3	523.3	523.3	523.3	521.2	521.2	518.1	517.0	517.0
177.5°	513.9	513.9	516.4	515.6	516.4	516.4	516.4	515.6	514.8	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1159.0	1156.5	1151.6	1147.2	1141.7	1136.8	1133.5	1129.4	1124.2	1117.9	1112.8
5°	1210.3	1200.2	1186.7	1175.2	1160.3	1148.8	1136.8	1125.2	1113.6	1098.8	1085.7
7.5°	1267.2	1246.2	1225.7	1200.0	1176.6	1155.7	1135.8	1115.5	1095.7	1074.7	1054.4
10°	1302.0	1276.6	1248.3	1215.8	1186.2	1158.0	1132.1	1106.6	1079.8	1056.1	1030.6
12.5°	1334.6	1301.7	1269.4	1228.5	1192.9	1158.4	1125.4	1093.7	1065.0	1034.3	1007.0
15°	1364.1	1331.7	1295.6	1245.5	1196.0	1154.3	1115.4	1074.2	1038.6	1004.3	973.7
17.5°	1375.5	1341.5	1299.5	1251.4	1197.3	1144.9	1094.8	1049.5	1007.6	967.7	933.4
20°	1371.0	1338.1	1295.0	1249.2	1191.3	1136.8	1082.5	1032.5	985.8	943.6	907.0
22.5°	1360.2	1326.2	1284.7	1236.3	1181.3	1123.4	1065.5	1012.2	963.1	919.5	879.7
25°	1344.2	1297.9	1255.3	1208.0	1155.7	1098.3	1038.6	979.7	927.5	883.0	839.5
27.5°	1327.4	1269.6	1215.4	1168.5	1113.2	1061.9	1004.4	944.1	889.1	843.8	799.2
30°	1312.2	1247.4	1187.7	1134.4	1082.1	1033.5	978.8	920.0	863.5	816.8	771.4
32.5°	1293.3	1224.4	1158.8	1097.3	1046.9	998.6	949.2	893.0	837.9	789.7	743.6
35°	1269.6	1181.6	1110.4	1045.0	989.0	942.3	897.8	852.4	797.3	747.3	702.4
37.5°	1238.5	1138.6	1056.1	985.1	926.0	879.0	843.9	802.5	752.2	704.3	662.5
40°	1219.6	1107.5	1017.3	946.9	884.8	835.3	802.5	767.2	721.4	676.5	634.8
42.5°	1194.4	1079.1	978.0	904.6	842.2	794.5	761.3	730.6	692.1	649.8	605.2
45°	1145.0	1023.8	917.7	839.0	776.1	729.2	698.2	670.9	641.8	602.9	563.9
47.5°	1080.8	966.1	855.1	769.2	707.5	664.1	634.0	612.4	591.6	558.5	520.7
50°	1029.3	918.6	810.3	726.9	661.2	620.0	591.7	574.6	555.6	525.5	494.0
52.5°	968.6	869.8	763.6	678.4	616.4	577.7	550.6	533.5	517.8	493.3	463.3
55°	872.8	786.2	688.9	611.6	554.7	515.8	489.9	473.7	464.4	443.5	420.0
57.5°	762.3	700.3	614.5	539.9	489.6	451.2	432.2	418.4	408.0	393.2	376.6
60°	685.3	641.8	564.9	494.0	447.7	411.2	394.0	382.5	372.7	360.3	347.2
62.5°	607.1	575.4	508.5	447.7	405.1	374.5	358.5	348.0	336.8	328.4	315.8
65°	502.4	474.1	427.8	380.1	340.8	316.2	304.7	295.4	288.5	279.2	270.4
67.5°	390.7	379.3	347.3	314.5	286.2	264.4	254.4	247.9	239.6	234.0	228.0
70°	322.3	316.7	294.0	272.2	245.8	231.0	221.8	219.0	208.8	203.3	199.1
72.5°	261.5	259.0	245.8	230.8	212.1	199.2	190.6	187.5	181.0	176.6	173.9
75°	179.1	180.1	177.8	168.1	161.1	152.8	145.3	143.6	138.9	135.2	132.9
77.5°	113.3	118.1	118.2	117.8	115.0	109.9	106.8	105.5	100.9	99.5	99.0
80°	77.8	82.8	87.5	87.0	86.1	84.7	82.4	81.1	78.7	77.3	76.4
82.5°	51.9	56.6	60.5	63.0	62.8	61.4	59.8	59.2	58.7	57.7	57.5
85°	24.5	25.5	26.8	30.1	32.4	32.9	32.4	31.9	30.6	31.0	31.5
87.5°	11.2	10.8	11.0	10.5	9.7	11.2	11.9	12.0	11.5	11.2	10.9
90°	13.5	11.4	10.3	8.3	6.2	4.1	2.1	1.1	2.1	4.1	6.2
92.5°	236.5	141.5	85.0	54.8	36.9	24.1	15.3	12.7	15.3	24.1	36.9
95°	463.2	235.2	124.3	77.7	54.9	43.5	35.2	34.2	35.2	43.5	54.9
97.5°	369.7	202.7	129.3	95.8	75.3	63.8	58.1	56.8	58.1	63.8	75.3
100°	335.7	201.0	140.9	109.9	90.2	78.7	74.6	72.5	74.6	78.7	90.2
102.5°	321.6	208.5	155.0	124.8	106.7	94.5	91.2	90.0	91.2	94.5	106.7
105°	316.0	223.8	178.3	149.2	132.6	122.3	117.1	117.1	117.1	122.3	132.6
107.5°	325.6	246.6	202.4	176.4	159.2	150.6	145.7	143.6	145.7	150.6	159.2
110°	334.7	263.1	220.7	193.8	178.3	168.9	164.8	162.6	164.8	168.9	178.3



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	346.3	278.9	238.1	212.0	196.4	187.1	183.8	181.7	183.8	187.1	196.4
115°	363.6	303.6	265.3	239.3	223.8	214.5	211.3	209.3	211.3	214.5	223.8
117.5°	383.6	328.9	292.6	267.5	249.9	240.6	237.3	234.2	237.3	240.6	249.9
120°	396.8	347.1	310.9	284.9	267.3	258.0	253.9	250.7	253.9	258.0	267.3
122.5°	411.8	364.5	328.2	302.4	283.0	273.8	270.5	268.1	270.5	273.8	283.0
125°	432.0	387.5	353.3	326.4	306.7	297.4	292.2	290.1	292.2	297.4	306.7
127.5°	450.8	409.7	376.7	349.8	328.9	317.1	310.4	307.3	310.4	317.1	328.9
130°	463.2	423.7	391.6	364.7	343.0	329.5	321.2	318.1	321.2	329.5	343.0
132.5°	473.9	437.0	404.9	378.0	355.4	340.3	330.3	326.4	330.3	340.3	355.4
135°	489.0	454.9	422.8	394.8	373.0	356.4	344.0	339.8	344.0	356.4	373.0
137.5°	500.2	467.5	438.3	409.5	388.2	371.6	360.0	356.9	360.0	371.6	388.2
140°	507.7	476.6	446.6	418.6	399.0	382.4	369.9	366.8	369.9	382.4	399.0
142.5°	511.8	482.4	454.1	427.8	408.8	392.3	380.7	378.4	380.7	392.3	408.8
145°	518.1	492.1	465.2	441.4	422.8	408.2	397.9	395.8	397.9	408.2	422.8
147.5°	521.8	498.4	474.7	453.8	437.7	424.2	415.3	414.0	415.3	424.2	437.7
150°	524.3	502.5	479.7	462.1	447.6	434.2	426.9	424.8	426.9	434.2	447.6
152.5°	525.9	506.7	485.5	469.6	455.9	444.1	437.7	436.4	437.7	444.1	455.9
155°	527.4	510.8	493.2	478.7	468.3	458.0	451.7	451.7	451.7	458.0	468.3
157.5°	528.4	514.3	499.2	488.2	479.1	470.2	465.2	465.5	465.2	470.2	479.1
160°	528.4	516.0	502.5	493.2	484.9	477.7	473.5	474.6	473.5	477.7	484.9
162.5°	527.6	517.6	505.9	498.2	491.5	485.1	481.0	482.0	481.0	485.1	491.5
165°	526.4	518.1	509.8	503.5	499.4	494.3	491.2	493.2	491.2	494.3	499.4
167.5°	523.9	518.1	511.2	507.3	504.4	501.5	499.6	500.7	499.6	501.5	504.4
170°	522.2	518.1	512.9	509.8	507.7	505.6	504.6	505.6	504.6	505.6	507.7
172.5°	520.6	517.2	512.9	511.4	510.1	508.1	507.1	509.0	507.1	508.1	510.1
175°	518.1	516.0	512.9	512.9	512.9	511.8	510.8	512.9	510.8	511.8	512.9
177.5°	515.6	514.8	513.1	513.1	513.9	513.1	513.1	514.8	513.1	513.1	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1109.0	1103.8	1100.1	1092.7	1087.5	1085.3	1081.3	1080.1	1084.2	1081.3	1080.8
5°	1076.0	1062.7	1052.0	1041.3	1029.7	1022.3	1011.2	1009.4	1006.6	1002.5	1001.5
7.5°	1036.5	1019.0	1005.3	987.7	972.4	960.1	946.2	939.7	936.0	930.7	923.5
10°	1009.9	989.0	970.4	952.9	933.9	918.6	904.7	894.1	887.2	880.7	877.9
12.5°	983.6	962.3	938.6	917.3	896.2	879.0	863.6	856.7	849.0	841.4	834.9
15°	942.7	914.4	888.5	864.0	846.0	827.4	812.6	802.5	790.9	787.6	775.1
17.5°	899.4	871.6	841.3	815.5	794.5	774.2	757.9	746.3	737.6	725.7	719.9
20°	872.4	839.5	809.9	786.2	763.0	739.0	722.3	712.6	704.3	694.6	689.9
22.5°	843.5	811.3	781.0	753.2	729.7	706.1	694.2	684.0	674.6	665.7	659.5
25°	801.0	768.7	736.6	707.9	683.4	666.3	652.4	640.8	635.7	627.0	620.5
27.5°	759.1	724.6	691.4	662.9	643.6	626.7	615.3	606.1	596.9	589.2	583.6
30°	732.0	696.9	660.8	638.0	617.7	601.5	589.0	580.1	573.2	566.2	562.1
32.5°	705.0	668.7	636.7	612.1	592.8	578.9	566.0	557.6	550.3	542.6	537.7
35°	661.6	624.6	598.7	574.6	555.6	542.7	533.9	521.8	515.8	510.2	505.2
37.5°	621.3	586.9	558.8	537.8	521.3	508.4	497.0	490.5	483.1	478.1	473.9
40°	591.7	560.3	534.8	512.6	500.5	486.2	475.5	467.2	461.6	455.1	450.5
42.5°	565.1	535.8	511.0	491.1	476.1	464.0	453.7	445.3	438.3	433.6	429.8
45°	527.4	498.2	474.1	455.6	441.8	430.2	419.5	415.4	406.1	400.6	398.7
47.5°	488.4	462.3	439.1	422.0	407.8	396.8	386.8	378.3	373.2	367.7	364.8
50°	462.1	437.1	415.4	398.7	384.8	372.7	363.5	357.9	351.0	345.9	342.1
52.5°	435.8	412.7	390.9	375.0	362.9	350.9	340.5	334.9	328.4	325.1	322.5
55°	398.2	373.6	355.2	339.4	326.9	315.8	306.0	300.5	296.3	293.1	292.1
57.5°	355.6	336.2	319.0	304.8	291.8	281.3	272.8	267.5	263.9	263.3	260.6
60°	327.8	310.2	294.4	279.2	268.0	258.3	250.9	245.0	241.2	240.8	239.9
62.5°	300.1	283.2	268.6	255.1	245.1	235.8	228.7	221.9	219.7	217.4	215.4
65°	258.9	243.5	231.5	220.9	210.2	202.3	195.4	191.2	186.1	183.3	178.3
67.5°	218.4	206.5	194.9	185.9	177.6	170.1	164.3	158.2	154.7	152.5	148.8
70°	191.7	182.4	170.9	161.1	154.6	148.6	144.0	137.1	134.7	132.9	131.0
72.5°	166.5	158.4	148.6	140.8	134.3	128.6	123.2	120.0	117.7	115.8	114.8
75°	131.0	123.1	114.9	109.2	104.7	100.0	97.2	94.9	94.0	93.5	91.7
77.5°	96.2	92.0	85.3	81.0	77.8	76.1	73.6	72.3	72.2	70.2	69.6
80°	73.7	71.3	65.7	63.9	61.6	59.7	58.3	56.0	53.7	52.8	51.4
82.5°	54.8	52.4	50.2	47.3	45.3	44.1	42.8	41.9	42.3	40.9	40.3
85°	29.2	26.8	25.9	25.5	24.5	25.5	25.0	24.5	24.1	23.6	24.1
87.5°	10.9	11.3	11.1	12.3	11.4	12.2	12.4	12.2	12.5	12.7	12.8
90°	8.3	10.3	11.4	13.5	14.5	16.6	17.7	18.6	19.7	20.7	22.8
92.5°	54.8	85.0	141.5	236.5	339.5	334.0	270.5	183.6	133.2	100.3	85.0
95°	77.7	124.3	235.2	463.2	749.1	918.0	898.3	744.9	587.5	460.0	373.0
97.5°	95.8	129.3	202.7	369.7	669.0	980.3	1136.7	1109.5	999.1	874.9	753.9
100°	109.9	140.9	201.0	335.7	596.8	935.6	1194.6	1274.4	1223.7	1117.0	1009.1
102.5°	124.8	155.0	208.5	321.6	542.1	856.8	1159.8	1330.0	1361.3	1310.1	1237.2
105°	149.2	178.3	223.8	316.0	489.0	751.2	1048.6	1297.3	1439.2	1484.8	1473.4
107.5°	176.4	202.4	246.6	325.6	466.6	678.4	935.0	1180.4	1369.8	1486.8	1541.0
110°	193.8	220.7	263.1	334.7	460.0	644.4	870.3	1094.1	1291.0	1437.1	1525.2



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	212.0	238.1	278.9	346.3	460.0	624.6	822.2	1026.2	1213.1	1360.8	1464.6
115°	239.3	265.3	303.6	363.6	463.2	603.1	769.8	940.8	1101.4	1243.3	1356.3
117.5°	267.5	292.6	328.9	383.6	470.0	592.5	738.5	885.6	1024.1	1146.4	1250.0
120°	284.9	310.9	347.1	396.8	476.6	587.5	721.1	855.9	980.2	1094.1	1185.4
122.5°	302.4	328.2	364.5	411.8	482.4	583.4	706.2	833.5	948.7	1050.3	1135.6
125°	326.4	353.3	387.5	432.0	492.1	578.2	685.9	800.9	906.6	996.8	1071.4
127.5°	349.8	376.7	409.7	450.8	503.1	575.7	667.3	767.8	866.4	950.6	1020.4
130°	364.7	391.6	423.7	463.2	509.8	574.0	654.9	747.1	838.2	919.1	986.4
132.5°	378.0	404.9	437.0	473.9	517.2	574.0	644.9	726.3	811.7	885.0	949.9
135°	394.8	422.8	454.9	489.0	527.4	574.0	633.1	699.4	770.9	837.2	896.3
137.5°	409.5	438.3	467.5	500.2	536.7	575.2	622.5	676.6	734.4	789.5	839.7
140°	418.6	446.6	476.6	507.7	540.8	576.0	617.5	664.1	712.8	760.5	804.1
142.5°	427.8	454.1	482.4	511.8	543.3	576.9	613.4	653.4	694.6	735.7	773.4
145°	441.4	465.2	492.1	518.1	546.1	576.0	607.2	639.3	671.4	703.6	731.5
147.5°	453.8	474.7	498.4	521.8	547.1	573.4	600.7	626.1	652.1	676.8	697.9
150°	462.1	479.7	502.5	524.3	547.1	570.9	595.8	618.6	641.4	661.0	679.7
152.5°	469.6	485.5	506.7	525.9	546.3	567.6	590.0	610.3	630.6	648.6	663.2
155°	478.7	493.2	510.8	527.4	543.9	561.6	580.2	597.8	614.4	628.9	640.3
157.5°	488.2	499.2	514.3	528.4	541.3	555.4	571.1	585.4	599.1	610.3	619.2
160°	493.2	502.5	516.0	528.4	538.8	551.3	563.7	577.1	587.5	597.8	605.1
162.5°	498.2	505.9	517.6	527.6	536.3	546.3	557.1	568.0	577.6	586.2	592.6
165°	503.5	509.8	518.1	526.4	532.5	538.8	547.1	555.4	562.6	568.8	574.0
167.5°	507.3	511.2	518.1	523.9	526.7	531.5	537.3	543.3	548.1	552.9	556.6
170°	509.8	512.9	518.1	522.2	524.3	527.4	531.5	536.7	539.8	543.0	545.0
172.5°	511.4	512.9	517.2	520.6	520.9	522.5	525.8	529.2	532.4	534.7	535.9
175°	512.9	512.9	516.0	518.1	517.0	517.0	518.1	521.2	521.2	523.3	523.3
177.5°	513.1	513.1	514.8	515.6	513.9	513.9	514.8	515.6	516.4	516.4	516.4
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1080.5	1076.5	1075.3	1076.8	1075.3	1076.5	1080.5	1080.8	1081.3	1084.2	1080.1
5°	996.8	992.3	994.5	993.6	994.5	992.3	996.8	1001.5	1002.5	1006.6	1009.4
7.5°	923.4	917.6	911.5	913.5	911.5	917.6	923.4	923.5	930.7	936.0	939.7
10°	871.8	867.3	864.4	866.7	864.4	867.3	871.8	877.9	880.7	887.2	894.1
12.5°	828.5	825.7	823.3	822.3	823.3	825.7	828.5	834.9	841.4	849.0	856.7
15°	769.5	764.0	761.7	755.6	761.7	764.0	769.5	775.1	787.6	790.9	802.5
17.5°	715.2	713.4	707.3	704.7	707.3	713.4	715.2	719.9	725.7	737.6	746.3
20°	683.0	681.1	675.1	678.8	675.1	681.1	683.0	689.9	694.6	704.3	712.6
22.5°	656.3	652.2	650.2	649.2	650.2	652.2	656.3	659.5	665.7	674.6	684.0
25°	618.6	612.6	610.3	607.5	610.3	612.6	618.6	620.5	627.0	635.7	640.8
27.5°	581.0	577.7	574.7	574.0	574.7	577.7	581.0	583.6	589.2	596.9	606.1
30°	556.5	553.3	551.0	551.0	551.0	553.3	556.5	562.1	566.2	573.2	580.1
32.5°	534.7	532.2	529.9	529.5	529.9	532.2	534.7	537.7	542.6	550.3	557.6
35°	502.8	499.2	498.2	495.4	498.2	499.2	502.8	505.2	510.2	515.8	521.8
37.5°	469.8	466.7	466.6	466.4	466.6	466.7	469.8	473.9	478.1	483.1	490.5
40°	448.7	446.4	445.9	442.6	445.9	446.4	448.7	450.5	455.1	461.6	467.2
42.5°	426.1	424.9	423.3	421.9	423.3	424.9	426.1	429.8	433.6	438.3	445.3
45°	395.4	392.2	392.2	389.9	392.2	392.2	395.4	398.7	400.6	406.1	415.4
47.5°	363.7	361.2	361.5	359.1	361.5	361.2	363.7	364.8	367.7	373.2	378.3
50°	342.6	341.3	340.8	339.8	340.8	341.3	342.6	342.1	345.9	351.0	357.9
52.5°	321.6	320.8	322.6	320.6	322.6	320.8	321.6	322.5	325.1	328.4	334.9
55°	293.1	291.7	294.4	291.7	294.4	291.7	293.1	292.1	293.1	296.3	300.5
57.5°	260.4	259.1	261.6	260.2	261.6	259.1	260.4	260.6	263.3	263.9	267.5
60°	238.9	236.1	237.6	238.0	237.6	236.1	238.9	239.9	240.8	241.2	245.0
62.5°	213.4	211.7	212.7	210.6	212.7	211.7	213.4	215.4	217.4	219.7	221.9
65°	177.4	175.9	174.1	173.2	174.1	175.9	177.4	178.3	183.3	186.1	191.2
67.5°	149.0	145.7	145.6	146.3	145.6	145.7	149.0	148.8	152.5	154.7	158.2
70°	128.2	128.2	127.8	127.8	127.8	128.2	128.2	131.0	132.9	134.7	137.1
72.5°	113.8	113.4	112.6	112.3	112.6	113.4	113.8	114.8	115.8	117.7	120.0
75°	91.7	92.1	91.2	90.8	91.2	92.1	91.7	91.7	93.5	94.0	94.9
77.5°	67.7	65.7	66.8	65.7	66.8	65.7	67.7	69.6	70.2	72.2	72.3
80°	51.4	50.9	52.3	50.9	52.3	50.9	51.4	51.4	52.8	53.7	56.0
82.5°	40.7	40.2	40.8	39.9	40.8	40.2	40.7	40.3	40.9	42.3	41.9
85°	24.5	24.1	23.6	24.1	23.6	24.1	24.5	24.1	23.6	24.1	24.5
87.5°	13.1	12.8	12.9	12.9	12.9	12.8	13.1	12.8	12.7	12.5	12.2
90°	22.8	22.8	23.8	23.8	23.8	22.8	22.8	22.8	20.7	19.7	18.6
92.5°	71.7	69.2	67.8	66.1	67.8	69.2	71.7	85.0	100.3	133.2	183.6
95°	299.4	268.3	260.1	243.5	260.1	268.3	299.4	373.0	460.0	587.5	744.9
97.5°	689.8	631.9	601.8	588.5	601.8	631.9	689.8	753.9	874.9	999.1	1109.5
100°	937.7	863.1	824.7	808.2	824.7	863.1	937.7	1009.1	1117.0	1223.7	1274.4
102.5°	1160.7	1107.6	1066.0	1053.6	1066.0	1107.6	1160.7	1237.2	1310.1	1361.3	1330.0
105°	1440.2	1406.0	1385.3	1372.9	1385.3	1406.0	1440.2	1473.4	1484.8	1439.2	1297.3
107.5°	1557.7	1557.6	1550.7	1542.4	1550.7	1557.6	1557.7	1541.0	1486.8	1369.8	1180.4
110°	1571.8	1591.5	1598.7	1598.7	1598.7	1591.5	1571.8	1525.2	1437.1	1291.0	1094.1



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1532.9	1566.6	1584.7	1592.1	1584.7	1566.6	1532.9	1464.6	1360.8	1213.1	1026.2
115°	1437.1	1486.8	1515.8	1529.3	1515.8	1486.8	1437.1	1356.3	1243.3	1101.4	940.8
117.5°	1330.8	1382.2	1411.0	1419.2	1411.0	1382.2	1330.8	1250.0	1146.4	1024.1	885.6
120°	1262.0	1311.7	1339.7	1348.0	1339.7	1311.7	1262.0	1185.4	1094.1	980.2	855.9
122.5°	1204.0	1249.6	1277.6	1285.0	1277.6	1249.6	1204.0	1135.6	1050.3	948.7	833.5
125°	1129.4	1171.9	1194.6	1205.1	1194.6	1171.9	1129.4	1071.4	996.8	906.6	800.9
127.5°	1073.0	1110.5	1132.1	1136.7	1132.1	1110.5	1073.0	1020.4	950.6	866.4	767.8
130°	1038.2	1072.4	1093.1	1099.3	1093.1	1072.4	1038.2	986.4	919.1	838.2	747.1
132.5°	1001.7	1035.9	1055.0	1062.0	1055.0	1035.9	1001.7	949.9	885.0	811.7	726.3
135°	941.8	976.1	994.7	1000.9	994.7	976.1	941.8	896.3	837.2	770.9	699.4
137.5°	880.5	911.6	928.8	935.6	928.8	911.6	880.5	839.7	789.5	734.4	676.6
140°	842.4	869.3	884.8	890.0	884.8	869.3	842.4	804.1	760.5	712.8	664.1
142.5°	805.9	828.7	843.4	847.7	843.4	828.7	805.9	773.4	735.7	694.6	653.4
145°	756.3	774.0	785.4	789.5	785.4	774.0	756.3	731.5	703.6	671.4	639.3
147.5°	717.6	731.7	738.3	740.2	738.3	731.7	717.6	697.9	676.8	652.1	626.1
150°	695.3	707.7	711.9	712.8	711.9	707.7	695.3	679.7	661.0	641.4	618.6
152.5°	676.2	686.1	690.3	691.3	690.3	686.1	676.2	663.2	648.6	630.6	610.3
155°	650.7	657.9	661.0	662.1	661.0	657.9	650.7	640.3	628.9	614.4	597.8
157.5°	627.2	633.3	636.1	636.0	636.1	633.3	627.2	619.2	610.3	599.1	585.4
160°	612.3	617.5	619.6	618.6	619.6	617.5	612.3	605.1	597.8	587.5	577.1
162.5°	598.2	602.6	603.1	602.8	603.1	602.6	598.2	592.6	586.2	577.6	568.0
165°	578.2	580.2	580.2	580.2	580.2	580.2	578.2	574.0	568.8	562.6	555.4
167.5°	558.7	560.5	559.7	559.5	559.7	560.5	558.7	556.6	552.9	548.1	543.3
170°	547.1	548.1	548.1	547.1	548.1	548.1	547.1	545.0	543.0	539.8	536.7
172.5°	536.3	538.1	536.5	535.5	536.5	538.1	536.3	535.9	534.7	532.4	529.2
175°	523.3	524.3	522.2	521.2	522.2	524.3	523.3	523.3	523.3	521.2	521.2
177.5°	515.6	516.4	513.9	513.9	513.9	516.4	515.6	516.4	516.4	516.4	515.6
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1081.3	1085.3	1087.5	1092.7	1100.1	1103.8	1109.0	1112.8	1117.9	1124.2	1129.4
5°	1011.2	1022.3	1029.7	1041.3	1052.0	1062.7	1076.0	1085.7	1098.8	1113.6	1125.2
7.5°	946.2	960.1	972.4	987.7	1005.3	1019.0	1036.5	1054.4	1074.7	1095.7	1115.5
10°	904.7	918.6	933.9	952.9	970.4	989.0	1009.9	1030.6	1056.1	1079.8	1106.6
12.5°	863.6	879.0	896.2	917.3	938.6	962.3	983.6	1007.0	1034.3	1065.0	1093.7
15°	812.6	827.4	846.0	864.0	888.5	914.4	942.7	973.7	1004.3	1038.6	1074.2
17.5°	757.9	774.2	794.5	815.5	841.3	871.6	899.4	933.4	967.7	1007.6	1049.5
20°	722.3	739.0	763.0	786.2	809.9	839.5	872.4	907.0	943.6	985.8	1032.5
22.5°	694.2	706.1	729.7	753.2	781.0	811.3	843.5	879.7	919.5	963.1	1012.2
25°	652.4	666.3	683.4	707.9	736.6	768.7	801.0	839.5	883.0	927.5	979.7
27.5°	615.3	626.7	643.6	662.9	691.4	724.6	759.1	799.2	843.8	889.1	944.1
30°	589.0	601.5	617.7	638.0	660.8	696.9	732.0	771.4	816.8	863.5	920.0
32.5°	566.0	578.9	592.8	612.1	636.7	668.7	705.0	743.6	789.7	837.9	893.0
35°	533.9	542.7	555.6	574.6	598.7	624.6	661.6	702.4	747.3	797.3	852.4
37.5°	497.0	508.4	521.3	537.8	558.8	586.9	621.3	662.5	704.3	752.2	802.5
40°	475.5	486.2	500.5	512.6	534.8	560.3	591.7	634.8	676.5	721.4	767.2
42.5°	453.7	464.0	476.1	491.1	511.0	535.8	565.1	605.2	649.8	692.1	730.6
45°	419.5	430.2	441.8	455.6	474.1	498.2	527.4	563.9	602.9	641.8	670.9
47.5°	386.8	396.8	407.8	422.0	439.1	462.3	488.4	520.7	558.5	591.6	612.4
50°	363.5	372.7	384.8	398.7	415.4	437.1	462.1	494.0	525.5	555.6	574.6
52.5°	340.5	350.9	362.9	375.0	390.9	412.7	435.8	463.3	493.3	517.8	533.5
55°	306.0	315.8	326.9	339.4	355.2	373.6	398.2	420.0	443.5	464.4	473.7
57.5°	272.8	281.3	291.8	304.8	319.0	336.2	355.6	376.6	393.2	408.0	418.4
60°	250.9	258.3	268.0	279.2	294.4	310.2	327.8	347.2	360.3	372.7	382.5
62.5°	228.7	235.8	245.1	255.1	268.6	283.2	300.1	315.8	328.4	336.8	348.0
65°	195.4	202.3	210.2	220.9	231.5	243.5	258.9	270.4	279.2	288.5	295.4
67.5°	164.3	170.1	177.6	185.9	194.9	206.5	218.4	228.0	234.0	239.6	247.9
70°	144.0	148.6	154.6	161.1	170.9	182.4	191.7	199.1	203.3	208.8	219.0
72.5°	123.2	128.6	134.3	140.8	148.6	158.4	166.5	173.9	176.6	181.0	187.5
75°	97.2	100.0	104.7	109.2	114.9	123.1	131.0	132.9	135.2	138.9	143.6
77.5°	73.6	76.1	77.8	81.0	85.3	92.0	96.2	99.0	99.5	100.9	105.5
80°	58.3	59.7	61.6	63.9	65.7	71.3	73.7	76.4	77.3	78.7	81.1
82.5°	42.8	44.1	45.3	47.3	50.2	52.4	54.8	57.5	57.7	58.7	59.2
85°	25.0	25.5	24.5	25.5	25.9	26.8	29.2	31.5	31.0	30.6	31.9
87.5°	12.4	12.2	11.4	12.3	11.1	11.3	10.9	10.9	11.2	11.5	12.0
90°	17.7	16.6	14.5	13.5	11.4	10.3	8.3	6.2	4.1	2.1	1.1
92.5°	270.5	334.0	339.5	236.5	141.5	85.0	54.8	36.9	24.1	15.3	12.7
95°	898.3	918.0	749.1	463.2	235.2	124.3	77.7	54.9	43.5	35.2	34.2
97.5°	1136.7	980.3	669.0	369.7	202.7	129.3	95.8	75.3	63.8	58.1	56.8
100°	1194.6	935.6	596.8	335.7	201.0	140.9	109.9	90.2	78.7	74.6	72.5
102.5°	1159.8	856.8	542.1	321.6	208.5	155.0	124.8	106.7	94.5	91.2	90.0
105°	1048.6	751.2	489.0	316.0	223.8	178.3	149.2	132.6	122.3	117.1	117.1
107.5°	935.0	678.4	466.6	325.6	246.6	202.4	176.4	159.2	150.6	145.7	143.6
110°	870.3	644.4	460.0	334.7	263.1	220.7	193.8	178.3	168.9	164.8	162.6



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	822.2	624.6	460.0	346.3	278.9	238.1	212.0	196.4	187.1	183.8	181.7
115°	769.8	603.1	463.2	363.6	303.6	265.3	239.3	223.8	214.5	211.3	209.3
117.5°	738.5	592.5	470.0	383.6	328.9	292.6	267.5	249.9	240.6	237.3	234.2
120°	721.1	587.5	476.6	396.8	347.1	310.9	284.9	267.3	258.0	253.9	250.7
122.5°	706.2	583.4	482.4	411.8	364.5	328.2	302.4	283.0	273.8	270.5	268.1
125°	685.9	578.2	492.1	432.0	387.5	353.3	326.4	306.7	297.4	292.2	290.1
127.5°	667.3	575.7	503.1	450.8	409.7	376.7	349.8	328.9	317.1	310.4	307.3
130°	654.9	574.0	509.8	463.2	423.7	391.6	364.7	343.0	329.5	321.2	318.1
132.5°	644.9	574.0	517.2	473.9	437.0	404.9	378.0	355.4	340.3	330.3	326.4
135°	633.1	574.0	527.4	489.0	454.9	422.8	394.8	373.0	356.4	344.0	339.8
137.5°	622.5	575.2	536.7	500.2	467.5	438.3	409.5	388.2	371.6	360.0	356.9
140°	617.5	576.0	540.8	507.7	476.6	446.6	418.6	399.0	382.4	369.9	366.8
142.5°	613.4	576.9	543.3	511.8	482.4	454.1	427.8	408.8	392.3	380.7	378.4
145°	607.2	576.0	546.1	518.1	492.1	465.2	441.4	422.8	408.2	397.9	395.8
147.5°	600.7	573.4	547.1	521.8	498.4	474.7	453.8	437.7	424.2	415.3	414.0
150°	595.8	570.9	547.1	524.3	502.5	479.7	462.1	447.6	434.2	426.9	424.8
152.5°	590.0	567.6	546.3	525.9	506.7	485.5	469.6	455.9	444.1	437.7	436.4
155°	580.2	561.6	543.9	527.4	510.8	493.2	478.7	468.3	458.0	451.7	451.7
157.5°	571.1	555.4	541.3	528.4	514.3	499.2	488.2	479.1	470.2	465.2	465.5
160°	563.7	551.3	538.8	528.4	516.0	502.5	493.2	484.9	477.7	473.5	474.6
162.5°	557.1	546.3	536.3	527.6	517.6	505.9	498.2	491.5	485.1	481.0	482.0
165°	547.1	538.8	532.5	526.4	518.1	509.8	503.5	499.4	494.3	491.2	493.2
167.5°	537.3	531.5	526.7	523.9	518.1	511.2	507.3	504.4	501.5	499.6	500.7
170°	531.5	527.4	524.3	522.2	518.1	512.9	509.8	507.7	505.6	504.6	505.6
172.5°	525.8	522.5	520.9	520.6	517.2	512.9	511.4	510.1	508.1	507.1	509.0
175°	518.1	517.0	517.0	518.1	516.0	512.9	512.9	512.9	511.8	510.8	512.9
177.5°	514.8	513.9	513.9	515.6	514.8	513.1	513.1	513.9	513.1	513.1	514.8
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1133.5	1136.8	1141.7	1147.2	1151.6	1156.5	1159.0	1159.0	1161.3	1166.1	1172.3
5°	1136.8	1148.8	1160.3	1175.2	1186.7	1200.2	1210.3	1220.0	1228.9	1239.9	1251.5
7.5°	1135.8	1155.7	1176.6	1200.0	1225.7	1246.2	1267.2	1283.7	1299.9	1321.2	1338.0
10°	1132.1	1158.0	1186.2	1215.8	1248.3	1276.6	1302.0	1325.2	1347.4	1370.6	1391.3
12.5°	1125.4	1158.4	1192.9	1228.5	1269.4	1301.7	1334.6	1359.2	1385.2	1410.5	1436.2
15°	1115.4	1154.3	1196.0	1245.5	1295.6	1331.7	1364.1	1396.0	1420.0	1448.8	1473.4
17.5°	1094.8	1144.9	1197.3	1251.4	1299.5	1341.5	1375.5	1405.8	1431.5	1463.0	1496.4
20°	1082.5	1136.8	1191.3	1249.2	1295.0	1338.1	1371.0	1402.5	1434.4	1475.6	1516.4
22.5°	1065.5	1123.4	1181.3	1236.3	1284.7	1326.2	1360.2	1398.8	1440.7	1487.5	1536.8
25°	1038.6	1098.3	1155.7	1208.0	1255.3	1297.9	1344.2	1396.0	1447.0	1508.5	1579.4
27.5°	1004.4	1061.9	1113.2	1168.5	1215.4	1269.6	1327.4	1383.6	1457.1	1541.8	1630.2
30°	978.8	1033.5	1082.1	1134.4	1187.7	1247.4	1312.2	1378.4	1465.9	1565.5	1670.6
32.5°	949.2	998.6	1046.9	1097.3	1158.8	1224.4	1293.3	1374.3	1478.9	1592.1	1700.9
35°	897.8	942.3	989.0	1045.0	1110.4	1181.6	1269.6	1368.2	1494.6	1616.4	1714.1
37.5°	843.9	879.0	926.0	985.1	1056.1	1138.6	1238.5	1358.3	1488.2	1597.4	1639.0
40°	802.5	835.3	884.8	946.9	1017.3	1107.5	1219.6	1342.7	1473.4	1549.3	1546.0
42.5°	761.3	794.5	842.2	904.6	978.0	1079.1	1194.4	1322.4	1432.6	1461.5	1401.2
45°	698.2	729.2	776.1	839.0	917.7	1023.8	1145.0	1267.7	1338.1	1291.4	1171.9
47.5°	634.0	664.1	707.5	769.2	855.1	966.1	1080.8	1181.4	1191.3	1090.9	947.6
50°	591.7	620.0	661.2	726.9	810.3	918.6	1029.3	1108.5	1084.0	961.3	813.5
52.5°	550.6	577.7	616.4	678.4	763.6	869.8	968.6	1030.6	973.9	843.5	710.5
55°	489.9	515.8	554.7	611.6	688.9	786.2	872.8	895.5	812.2	680.6	573.2
57.5°	432.2	451.2	489.6	539.9	614.5	700.3	762.3	758.2	666.3	547.9	470.8
60°	394.0	411.2	447.7	494.0	564.9	641.8	685.3	666.7	573.6	476.0	401.9
62.5°	358.5	374.5	405.1	447.7	508.5	575.4	607.1	581.6	493.7	407.9	348.9
65°	304.7	316.2	340.8	380.1	427.8	474.1	502.4	464.8	387.1	322.3	277.8
67.5°	254.4	264.4	286.2	314.5	347.3	379.3	390.7	355.6	295.2	251.5	220.2
70°	221.8	231.0	245.8	272.2	294.0	316.7	322.3	290.8	240.3	207.0	187.5
72.5°	190.6	199.2	212.1	230.8	245.8	259.0	261.5	232.3	193.6	170.7	155.7
75°	145.3	152.8	161.1	168.1	177.8	180.1	179.1	156.5	135.6	120.4	112.1
77.5°	106.8	109.9	115.0	117.8	118.2	118.1	113.3	99.0	88.3	81.9	78.6
80°	82.4	84.7	86.1	87.0	87.5	82.8	77.8	69.0	65.3	61.6	57.4
82.5°	59.8	61.4	62.8	63.0	60.5	56.6	51.9	47.5	44.9	43.1	41.5
85°	32.4	32.9	32.4	30.1	26.8	25.5	24.5	23.6	23.2	22.6	22.6
87.5°	11.9	11.2	9.7	10.5	11.0	10.8	11.2	11.1	11.1	11.3	11.5
90°	2.1	4.1	6.2	8.3	10.3	11.4	13.5	14.5	16.6	17.7	18.6
92.5°	15.3	24.1	36.9	54.8	85.0	141.5	236.5	339.5	334.0	270.5	183.6
95°	35.2	43.5	54.9	77.7	124.3	235.2	463.2	749.1	918.0	898.3	744.9
97.5°	58.1	63.8	75.3	95.8	129.3	202.7	369.7	669.0	980.3	1136.7	1109.5
100°	74.6	78.7	90.2	109.9	140.9	201.0	335.7	596.8	935.6	1194.6	1274.4
102.5°	91.2	94.5	106.7	124.8	155.0	208.5	321.6	542.1	856.8	1159.8	1330.0
105°	117.1	122.3	132.6	149.2	178.3	223.8	316.0	489.0	751.2	1048.6	1297.3
107.5°	145.7	150.6	159.2	176.4	202.4	246.6	325.6	466.6	678.4	935.0	1180.4
110°	164.8	168.9	178.3	193.8	220.7	263.1	334.7	460.0	644.4	870.3	1094.1



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.8	187.1	196.4	212.0	238.1	278.9	346.3	460.0	624.6	822.2	1026.2
115°	211.3	214.5	223.8	239.3	265.3	303.6	363.6	463.2	603.1	769.8	940.8
117.5°	237.3	240.6	249.9	267.5	292.6	328.9	383.6	470.0	592.5	738.5	885.6
120°	253.9	258.0	267.3	284.9	310.9	347.1	396.8	476.6	587.5	721.1	855.9
122.5°	270.5	273.8	283.0	302.4	328.2	364.5	411.8	482.4	583.4	706.2	833.5
125°	292.2	297.4	306.7	326.4	353.3	387.5	432.0	492.1	578.2	685.9	800.9
127.5°	310.4	317.1	328.9	349.8	376.7	409.7	450.8	503.1	575.7	667.3	767.8
130°	321.2	329.5	343.0	364.7	391.6	423.7	463.2	509.8	574.0	654.9	747.1
132.5°	330.3	340.3	355.4	378.0	404.9	437.0	473.9	517.2	574.0	644.9	726.3
135°	344.0	356.4	373.0	394.8	422.8	454.9	489.0	527.4	574.0	633.1	699.4
137.5°	360.0	371.6	388.2	409.5	438.3	467.5	500.2	536.7	575.2	622.5	676.6
140°	369.9	382.4	399.0	418.6	446.6	476.6	507.7	540.8	576.0	617.5	664.1
142.5°	380.7	392.3	408.8	427.8	454.1	482.4	511.8	543.3	576.9	613.4	653.4
145°	397.9	408.2	422.8	441.4	465.2	492.1	518.1	546.1	576.0	607.2	639.3
147.5°	415.3	424.2	437.7	453.8	474.7	498.4	521.8	547.1	573.4	600.7	626.1
150°	426.9	434.2	447.6	462.1	479.7	502.5	524.3	547.1	570.9	595.8	618.6
152.5°	437.7	444.1	455.9	469.6	485.5	506.7	525.9	546.3	567.6	590.0	610.3
155°	451.7	458.0	468.3	478.7	493.2	510.8	527.4	543.9	561.6	580.2	597.8
157.5°	465.2	470.2	479.1	488.2	499.2	514.3	528.4	541.3	555.4	571.1	585.4
160°	473.5	477.7	484.9	493.2	502.5	516.0	528.4	538.8	551.3	563.7	577.1
162.5°	481.0	485.1	491.5	498.2	505.9	517.6	527.6	536.3	546.3	557.1	568.0
165°	491.2	494.3	499.4	503.5	509.8	518.1	526.4	532.5	538.8	547.1	555.4
167.5°	499.6	501.5	504.4	507.3	511.2	518.1	523.9	526.7	531.5	537.3	543.3
170°	504.6	505.6	507.7	509.8	512.9	518.1	522.2	524.3	527.4	531.5	536.7
172.5°	507.1	508.1	510.1	511.4	512.9	517.2	520.6	520.9	522.5	525.8	529.2
175°	510.8	511.8	512.9	512.9	512.9	516.0	518.1	517.0	517.0	518.1	521.2
177.5°	513.1	513.1	513.9	513.1	513.1	514.8	515.6	513.9	513.9	514.8	515.6
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9	1127.9
2.5°	1177.1	1177.1	1183.5	1183.1	1187.2	1185.7	1186.4
5°	1265.4	1273.3	1280.2	1284.9	1291.8	1293.7	1292.7
7.5°	1356.9	1374.4	1383.0	1394.6	1396.8	1402.8	1402.2
10°	1413.6	1430.7	1443.7	1453.8	1459.0	1465.4	1465.9
12.5°	1458.0	1472.6	1484.1	1493.5	1499.7	1501.7	1503.0
15°	1492.8	1509.0	1522.4	1535.8	1543.7	1549.7	1553.0
17.5°	1527.8	1552.8	1576.5	1594.7	1605.7	1614.9	1614.8
20°	1554.8	1583.5	1613.2	1634.0	1655.3	1664.6	1666.0
22.5°	1583.7	1627.6	1665.8	1698.1	1726.1	1735.7	1739.3
25°	1643.7	1701.1	1760.0	1805.4	1837.7	1856.7	1859.5
27.5°	1716.2	1793.9	1855.8	1897.6	1924.6	1938.7	1941.7
30°	1767.4	1839.2	1894.7	1926.2	1938.7	1940.5	1933.6
32.5°	1790.3	1844.0	1866.2	1864.3	1839.8	1823.5	1817.2
35°	1762.3	1751.1	1696.9	1632.2	1582.6	1551.1	1542.7
37.5°	1603.7	1507.9	1408.2	1310.3	1258.1	1231.6	1186.1
40°	1447.4	1310.8	1207.1	1124.7	1065.9	1018.6	1007.5
42.5°	1271.0	1130.1	1026.4	955.7	908.8	876.4	862.3
45°	1021.5	900.1	814.5	760.3	724.2	700.5	689.9
47.5°	817.0	723.1	660.7	620.5	593.1	572.5	566.8
50°	704.7	629.7	576.9	543.1	522.3	506.6	500.1
52.5°	612.1	551.5	511.0	483.1	463.4	453.6	448.2
55°	505.2	452.8	423.7	401.4	390.3	382.5	378.7
57.5°	413.1	375.3	354.0	338.7	328.4	323.3	321.6
60°	361.6	332.0	312.5	300.5	293.6	287.0	285.3
62.5°	316.0	292.7	277.7	267.2	260.2	257.4	256.4
65°	254.7	239.4	228.3	221.8	216.2	215.3	214.8
67.5°	202.4	193.4	187.6	180.8	178.9	175.7	175.0
70°	173.2	167.1	160.2	157.9	155.6	152.3	152.8
72.5°	146.9	140.9	136.2	133.0	132.2	130.8	132.1
75°	107.5	105.6	103.7	101.4	100.5	100.5	100.0
77.5°	76.7	75.1	73.0	71.7	71.4	69.5	70.2
80°	55.6	53.2	52.3	52.8	51.4	50.9	50.9
82.5°	41.1	40.3	39.3	39.4	39.1	38.7	39.1
85°	22.6	22.2	22.2	21.8	21.8	21.3	21.3
87.5°	12.1	12.7	12.3	11.9	11.9	12.6	12.9
90°	19.7	20.7	22.8	22.8	22.8	23.8	23.8
92.5°	133.2	100.3	85.0	71.7	69.2	67.8	66.1
95°	587.5	460.0	373.0	299.4	268.3	260.1	243.5
97.5°	999.1	874.9	753.9	689.8	631.9	601.8	588.5
100°	1223.7	1117.0	1009.1	937.7	863.1	824.7	808.2
102.5°	1361.3	1310.1	1237.2	1160.7	1107.6	1066.0	1053.6
105°	1439.2	1484.8	1473.4	1440.2	1406.0	1385.3	1372.9
107.5°	1369.8	1486.8	1541.0	1557.7	1557.6	1550.7	1542.4
110°	1291.0	1437.1	1525.2	1571.8	1591.5	1598.7	1598.7



TEST NUMBER: P333576-940

CATALOG NUMBER: S125RDIP-S850D1205U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1213.1	1360.8	1464.6	1532.9	1566.6	1584.7	1592.1
115°	1101.4	1243.3	1356.3	1437.1	1486.8	1515.8	1529.3
117.5°	1024.1	1146.4	1250.0	1330.8	1382.2	1411.0	1419.2
120°	980.2	1094.1	1185.4	1262.0	1311.7	1339.7	1348.0
122.5°	948.7	1050.3	1135.6	1204.0	1249.6	1277.6	1285.0
125°	906.6	996.8	1071.4	1129.4	1171.9	1194.6	1205.1
127.5°	866.4	950.6	1020.4	1073.0	1110.5	1132.1	1136.7
130°	838.2	919.1	986.4	1038.2	1072.4	1093.1	1099.3
132.5°	811.7	885.0	949.9	1001.7	1035.9	1055.0	1062.0
135°	770.9	837.2	896.3	941.8	976.1	994.7	1000.9
137.5°	734.4	789.5	839.7	880.5	911.6	928.8	935.6
140°	712.8	760.5	804.1	842.4	869.3	884.8	890.0
142.5°	694.6	735.7	773.4	805.9	828.7	843.4	847.7
145°	671.4	703.6	731.5	756.3	774.0	785.4	789.5
147.5°	652.1	676.8	697.9	717.6	731.7	738.3	740.2
150°	641.4	661.0	679.7	695.3	707.7	711.9	712.8
152.5°	630.6	648.6	663.2	676.2	686.1	690.3	691.3
155°	614.4	628.9	640.3	650.7	657.9	661.0	662.1
157.5°	599.1	610.3	619.2	627.2	633.3	636.1	636.0
160°	587.5	597.8	605.1	612.3	617.5	619.6	618.6
162.5°	577.6	586.2	592.6	598.2	602.6	603.1	602.8
165°	562.6	568.8	574.0	578.2	580.2	580.2	580.2
167.5°	548.1	552.9	556.6	558.7	560.5	559.7	559.5
170°	539.8	543.0	545.0	547.1	548.1	548.1	547.1
172.5°	532.4	534.7	535.9	536.3	538.1	536.5	535.5
175°	521.2	523.3	523.3	523.3	524.3	522.2	521.2
177.5°	516.4	516.4	516.4	515.6	516.4	513.9	513.9
180°	513.9	513.9	513.9	513.9	513.9	513.9	513.9

(END OF REPORT)