

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331251-927

Luminaire Tested: **SA2XXDIP-C290D530U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331251-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2669.9 lumens  
Efficiency: N/A  
Efficacy: 104.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	96	92	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	33				
2	87	80	74	70	79	73	68	64	60	57	53	48	45	43	37	35	34	29				
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25				
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	29	27	25	21				
5	67	56	48	43	61	51	45	40	43	38	34	34	31	28	27	24	22	19				
6	62	50	43	37	56	46	40	35	39	33	30	31	27	25	24	22	20	17				
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18	15				
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	21	18	16	14				
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	15	12				
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.6	1.7
10°-20°	129.6	4.9
20°-30°	188.1	7.0
30°-40°	198.5	7.4
40°-50°	175.8	6.6
50°-60°	140.3	5.3
60°-70°	95.4	3.6
70°-80°	48.9	1.8
80°-90°	13.9	0.5
90°-100°	93.9	3.5
100°-110°	318.8	11.9
110°-120°	338.6	12.7
120°-130°	278.8	10.4
130°-140°	223.9	8.4
140°-150°	169.2	6.3
150°-160°	118.9	4.5
160°-170°	70.0	2.6
170°-180°	22.8	0.9
0°-30°	362.4	13.6
0°-40°	560.9	21.0
0°-60°	877.0	32.8
0°-90°	1035.2	38.8
90°-120°	751.3	28.1
90°-150°	1423.1	53.3
90°-180°	1635.0	61.2
0°-180°	2669.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	15	0	15	0	15	8
95°	52	16	52	16	52	67
105°	509	55	509	55	509	493
115°	670	97	670	97	670	656
125°	544	136	544	136	544	491
135°	450	159	450	159	450	350
145°	360	182	360	182	360	228
155°	302	206	302	206	302	141
165°	265	225	265	225	265	76
175°	239	234	239	234	239	23
180°	235	235	235	235	235	



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	6.7	6.7	6.9	6.7	6.7	6.8	6.6	6.7	6.9	7.1	7.1
90°	14.9	14.9	14.9	14.9	14.9	14.4	13.5	14.4	14.9	15.4	14.9
92.5°	25.0	25.7	25.4	26.9	27.2	30.0	33.8	39.4	49.6	58.7	57.9
95°	51.5	51.0	52.4	56.0	61.9	71.9	90.8	118.4	155.0	177.1	156.8
97.5°	101.4	105.2	111.8	122.9	144.5	177.1	226.0	276.2	317.1	302.3	227.7
100°	161.8	169.8	183.0	202.4	239.9	294.5	356.5	412.5	421.9	356.9	245.7
102.5°	284.6	295.6	312.0	345.2	385.9	443.9	489.1	501.8	461.0	358.7	238.9
105°	509.1	515.5	534.9	562.9	590.9	605.9	599.9	548.9	455.0	334.8	225.5
107.5°	650.4	658.8	662.7	664.2	660.7	638.8	591.8	514.9	415.3	309.1	218.7
110°	693.0	693.5	689.4	680.8	661.4	624.3	566.5	485.7	390.3	296.8	217.3



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	692.3	689.8	682.1	667.8	640.8	598.3	536.5	458.9	373.0	288.8	217.7
115°	669.9	665.9	654.2	633.3	601.3	554.8	495.6	426.0	351.5	280.1	219.6
117.5°	630.1	626.7	614.3	592.4	559.7	516.0	462.3	401.2	337.9	275.8	222.8
120°	604.4	599.9	586.8	565.6	534.0	492.9	445.0	389.0	330.7	273.3	225.0
122.5°	577.7	573.9	562.3	541.4	513.0	475.9	430.6	379.2	324.6	271.9	227.5
125°	543.5	539.9	528.5	511.4	485.2	451.3	411.5	365.0	315.8	269.3	231.3
127.5°	513.5	510.6	500.8	484.7	461.9	430.6	393.2	351.0	307.7	267.8	235.2
130°	496.5	492.9	483.9	468.5	446.3	416.5	380.9	342.0	302.2	267.0	238.1
132.5°	478.8	475.5	467.2	451.9	430.1	402.1	369.3	333.4	297.9	266.6	241.0
135°	450.4	448.6	440.5	425.6	406.2	380.9	351.0	321.2	291.8	266.1	244.4
137.5°	422.6	419.9	412.7	399.9	382.2	360.1	336.5	311.6	287.6	266.0	247.5
140°	403.5	400.7	394.0	382.2	367.7	347.8	327.1	305.4	285.1	265.6	248.9
142.5°	384.3	383.7	377.7	367.0	353.3	336.7	318.8	300.3	282.6	265.6	250.0
145°	359.6	358.2	353.7	346.0	335.3	322.1	308.1	293.2	279.2	264.7	251.2
147.5°	338.9	338.1	335.0	328.9	320.0	310.4	299.4	287.7	275.8	263.1	251.5
150°	326.6	326.1	323.4	318.1	311.2	303.2	293.7	283.7	272.9	262.1	251.2
152.5°	316.2	316.1	314.1	309.3	304.0	297.0	289.0	279.7	270.4	260.2	250.5
155°	302.2	303.2	301.3	298.2	293.2	288.2	281.5	274.3	265.6	257.1	249.4
157.5°	290.4	290.4	289.6	286.9	283.4	279.6	273.9	267.8	261.2	253.8	247.3
160°	282.8	282.8	282.3	280.1	276.9	273.8	268.8	263.8	257.9	251.7	246.2
162.5°	275.6	275.9	275.5	273.9	270.8	268.4	264.1	259.8	255.1	249.9	245.1
165°	265.2	265.6	265.6	263.8	262.1	260.2	257.1	253.9	250.3	246.2	243.0
167.5°	255.6	256.2	256.3	255.2	254.4	252.8	250.6	248.2	245.6	243.0	241.0
170°	249.9	250.7	251.2	249.9	249.4	248.5	246.7	245.3	243.0	241.2	239.9
172.5°	245.1	245.7	246.1	245.5	245.0	244.5	243.0	242.1	240.5	239.1	238.4
175°	239.0	239.9	240.3	239.9	239.9	239.5	239.0	238.5	237.2	236.7	236.3
177.5°	235.3	236.0	236.4	236.4	236.4	236.4	236.0	236.0	235.3	234.9	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	6.7	6.1	5.7	5.7	5.1	4.9	4.0	3.2	3.4	3.6	3.5
90°	12.2	9.0	6.8	5.4	4.5	3.6	1.8	0.5	1.8	3.6	4.5
92.5°	45.1	30.7	20.5	16.2	13.2	11.2	7.9	5.5	7.9	11.2	13.2
95°	104.3	65.0	44.3	33.4	26.2	22.1	17.6	15.8	17.6	22.1	26.2
97.5°	140.6	85.9	59.7	47.5	39.1	33.0	28.2	25.7	28.2	33.0	39.1
100°	148.2	93.1	69.2	56.5	47.5	40.2	36.1	34.8	36.1	40.2	47.5
102.5°	148.5	99.6	77.4	64.8	55.4	48.2	44.1	43.1	44.1	48.2	55.4
105°	150.9	110.7	89.4	76.8	66.9	60.0	57.0	55.1	57.0	60.0	66.9
107.5°	157.1	122.1	101.5	88.7	78.9	72.6	69.6	68.1	69.6	72.6	78.9
110°	162.2	129.7	109.8	96.6	87.2	81.4	78.6	76.8	78.6	81.4	87.2





TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	167.6	136.9	117.7	104.3	95.1	89.6	86.6	84.8	86.6	89.6	95.1
115°	175.7	148.2	128.7	116.5	107.5	102.1	99.4	97.1	99.4	102.1	107.5
117.5°	184.4	158.6	140.6	127.9	119.3	114.5	111.8	110.0	111.8	114.5	119.3
120°	190.2	165.8	148.2	135.5	126.5	122.4	119.7	117.9	119.7	122.4	126.5
122.5°	195.3	172.7	156.1	143.1	134.1	129.7	127.0	125.5	127.0	129.7	134.1
125°	203.3	183.0	166.7	154.1	145.0	139.6	136.9	135.5	136.9	139.6	145.0
127.5°	210.8	192.6	176.7	163.7	155.0	149.1	145.3	143.5	145.3	149.1	155.0
130°	215.5	198.4	182.5	169.8	160.8	154.5	150.0	148.2	150.0	154.5	160.8
132.5°	220.2	203.4	188.3	175.6	166.3	159.5	154.7	152.5	154.7	159.5	166.3
135°	226.3	210.6	196.1	183.4	173.0	166.3	160.8	159.0	160.8	166.3	173.0
137.5°	231.0	216.3	202.0	190.3	180.0	172.8	167.3	165.2	167.3	172.8	180.0
140°	233.5	219.6	206.0	194.2	184.3	177.1	171.7	169.8	171.7	177.1	184.3
142.5°	235.8	222.1	208.9	197.9	188.3	181.1	176.0	174.6	176.0	181.1	188.3
145°	238.5	225.9	213.7	203.7	194.7	187.9	183.4	181.6	183.4	187.9	194.7
147.5°	240.1	228.9	217.5	208.7	201.1	194.9	190.5	189.2	190.5	194.9	201.1
150°	240.8	230.4	220.0	211.9	205.1	199.2	195.6	194.2	195.6	199.2	205.1
152.5°	241.1	231.9	222.5	215.2	208.7	203.6	199.9	199.3	199.9	203.6	208.7
155°	241.7	234.0	226.3	219.6	214.6	209.6	206.9	206.4	206.9	209.6	214.6
157.5°	241.7	235.5	229.0	223.4	219.4	215.1	212.9	212.4	212.9	215.1	219.4
160°	241.7	236.3	230.8	225.9	222.3	218.6	216.8	216.4	216.8	218.6	222.3
162.5°	241.3	236.6	232.0	228.1	224.8	221.9	220.1	220.4	220.1	221.9	224.8
165°	240.3	237.2	233.1	230.4	228.1	225.5	224.5	225.0	224.5	225.5	228.1
167.5°	239.7	237.1	234.1	232.4	230.8	229.0	228.2	228.8	228.2	229.0	230.8
170°	239.0	236.7	234.5	233.1	232.2	230.8	230.4	231.3	230.4	230.8	232.2
172.5°	237.9	236.4	234.8	233.9	233.3	232.0	232.2	232.7	232.2	232.0	233.3
175°	236.7	235.8	234.9	234.5	234.5	233.5	234.0	234.5	234.0	233.5	234.5
177.5°	236.0	235.3	234.9	234.9	234.9	234.2	234.6	235.3	234.6	234.2	234.9
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	3.6	3.6	4.0	4.6	5.0	4.9	4.7	4.6	4.4	4.4	4.4
90°	5.4	6.8	9.0	12.2	14.9	15.4	14.9	14.4	13.5	14.4	14.9
92.5°	16.2	20.5	30.7	45.1	57.9	58.7	49.6	39.4	33.8	30.0	27.2
95°	33.4	44.3	65.0	104.3	156.8	177.1	155.0	118.4	90.8	71.9	61.9
97.5°	47.5	59.7	85.9	140.6	227.7	302.3	317.1	276.2	226.0	177.1	144.5
100°	56.5	69.2	93.1	148.2	245.7	356.9	421.9	412.5	356.5	294.5	239.9
102.5°	64.8	77.4	99.6	148.5	238.9	358.7	461.0	501.8	489.1	443.9	385.9
105°	76.8	89.4	110.7	150.9	225.5	334.8	455.0	548.9	599.9	605.9	590.9
107.5°	88.7	101.5	122.1	157.1	218.7	309.1	415.3	514.9	591.8	638.8	660.7
110°	96.6	109.8	129.7	162.2	217.3	296.8	390.3	485.7	566.5	624.3	661.4



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	104.3	117.7	136.9	167.6	217.7	288.8	373.0	458.9	536.5	598.3	640.8
115°	116.5	128.7	148.2	175.7	219.6	280.1	351.5	426.0	495.6	554.8	601.3
117.5°	127.9	140.6	158.6	184.4	222.8	275.8	337.9	401.2	462.3	516.0	559.7
120°	135.5	148.2	165.8	190.2	225.0	273.3	330.7	389.0	445.0	492.9	534.0
122.5°	143.1	156.1	172.7	195.3	227.5	271.9	324.6	379.2	430.6	475.9	513.0
125°	154.1	166.7	183.0	203.3	231.3	269.3	315.8	365.0	411.5	451.3	485.2
127.5°	163.7	176.7	192.6	210.8	235.2	267.8	307.7	351.0	393.2	430.6	461.9
130°	169.8	182.5	198.4	215.5	238.1	267.0	302.2	342.0	380.9	416.5	446.3
132.5°	175.6	188.3	203.4	220.2	241.0	266.6	297.9	333.4	369.3	402.1	430.1
135°	183.4	196.1	210.6	226.3	244.4	266.1	291.8	321.2	351.0	380.9	406.2
137.5°	190.3	202.0	216.3	231.0	247.5	266.0	287.6	311.6	336.5	360.1	382.2
140°	194.2	206.0	219.6	233.5	248.9	265.6	285.1	305.4	327.1	347.8	367.7
142.5°	197.9	208.9	222.1	235.8	250.0	265.6	282.6	300.3	318.8	336.7	353.3
145°	203.7	213.7	225.9	238.5	251.2	264.7	279.2	293.2	308.1	322.1	335.3
147.5°	208.7	217.5	228.9	240.1	251.5	263.1	275.8	287.7	299.4	310.4	320.0
150°	211.9	220.0	230.4	240.8	251.2	262.1	272.9	283.7	293.7	303.2	311.2
152.5°	215.2	222.5	231.9	241.1	250.5	260.2	270.4	279.7	289.0	297.0	304.0
155°	219.6	226.3	234.0	241.7	249.4	257.1	265.6	274.3	281.5	288.2	293.2
157.5°	223.4	229.0	235.5	241.7	247.3	253.8	261.2	267.8	273.9	279.6	283.4
160°	225.9	230.8	236.3	241.7	246.2	251.7	257.9	263.8	268.8	273.8	276.9
162.5°	228.1	232.0	236.6	241.3	245.1	249.9	255.1	259.8	264.1	268.4	270.8
165°	230.4	233.1	237.2	240.3	243.0	246.2	250.3	253.9	257.1	260.2	262.1
167.5°	232.4	234.1	237.1	239.7	241.0	243.0	245.6	248.2	250.6	252.8	254.4
170°	233.1	234.5	236.7	239.0	239.9	241.2	243.0	245.3	246.7	248.5	249.4
172.5°	233.9	234.8	236.4	237.9	238.4	239.1	240.5	242.1	243.0	244.5	245.0
175°	234.5	234.9	235.8	236.7	236.3	236.7	237.2	238.5	239.0	239.5	239.9
177.5°	234.9	234.9	235.3	236.0	235.3	234.9	235.3	236.0	236.0	236.4	236.4
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	4.4	4.3	4.3	4.1	4.3	4.3	4.4	4.4	4.4	4.4	4.6
90°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.4	13.5	14.4
92.5°	26.9	25.4	25.7	25.0	25.7	25.4	26.9	27.2	30.0	33.8	39.4
95°	56.0	52.4	51.0	51.5	51.0	52.4	56.0	61.9	71.9	90.8	118.4
97.5°	122.9	111.8	105.2	101.4	105.2	111.8	122.9	144.5	177.1	226.0	276.2
100°	202.4	183.0	169.8	161.8	169.8	183.0	202.4	239.9	294.5	356.5	412.5
102.5°	345.2	312.0	295.6	284.6	295.6	312.0	345.2	385.9	443.9	489.1	501.8
105°	562.9	534.9	515.5	509.1	515.5	534.9	562.9	590.9	605.9	599.9	548.9
107.5°	664.2	662.7	658.8	650.4	658.8	662.7	664.2	660.7	638.8	591.8	514.9
110°	680.8	689.4	693.5	693.0	693.5	689.4	680.8	661.4	624.3	566.5	485.7



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	667.8	682.1	689.8	692.3	689.8	682.1	667.8	640.8	598.3	536.5	458.9
115°	633.3	654.2	665.9	669.9	665.9	654.2	633.3	601.3	554.8	495.6	426.0
117.5°	592.4	614.3	626.7	630.1	626.7	614.3	592.4	559.7	516.0	462.3	401.2
120°	565.6	586.8	599.9	604.4	599.9	586.8	565.6	534.0	492.9	445.0	389.0
122.5°	541.4	562.3	573.9	577.7	573.9	562.3	541.4	513.0	475.9	430.6	379.2
125°	511.4	528.5	539.9	543.5	539.9	528.5	511.4	485.2	451.3	411.5	365.0
127.5°	484.7	500.8	510.6	513.5	510.6	500.8	484.7	461.9	430.6	393.2	351.0
130°	468.5	483.9	492.9	496.5	492.9	483.9	468.5	446.3	416.5	380.9	342.0
132.5°	451.9	467.2	475.5	478.8	475.5	467.2	451.9	430.1	402.1	369.3	333.4
135°	425.6	440.5	448.6	450.4	448.6	440.5	425.6	406.2	380.9	351.0	321.2
137.5°	399.9	412.7	419.9	422.6	419.9	412.7	399.9	382.2	360.1	336.5	311.6
140°	382.2	394.0	400.7	403.5	400.7	394.0	382.2	367.7	347.8	327.1	305.4
142.5°	367.0	377.7	383.7	384.3	383.7	377.7	367.0	353.3	336.7	318.8	300.3
145°	346.0	353.7	358.2	359.6	358.2	353.7	346.0	335.3	322.1	308.1	293.2
147.5°	328.9	335.0	338.1	338.9	338.1	335.0	328.9	320.0	310.4	299.4	287.7
150°	318.1	323.4	326.1	326.6	326.1	323.4	318.1	311.2	303.2	293.7	283.7
152.5°	309.3	314.1	316.1	316.2	316.1	314.1	309.3	304.0	297.0	289.0	279.7
155°	298.2	301.3	303.2	302.2	303.2	301.3	298.2	293.2	288.2	281.5	274.3
157.5°	286.9	289.6	290.4	290.4	290.4	289.6	286.9	283.4	279.6	273.9	267.8
160°	280.1	282.3	282.8	282.8	282.8	282.3	280.1	276.9	273.8	268.8	263.8
162.5°	273.9	275.5	275.9	275.6	275.9	275.5	273.9	270.8	268.4	264.1	259.8
165°	263.8	265.6	265.6	265.2	265.6	265.6	263.8	262.1	260.2	257.1	253.9
167.5°	255.2	256.3	256.2	255.6	256.2	256.3	255.2	254.4	252.8	250.6	248.2
170°	249.9	251.2	250.7	249.9	250.7	251.2	249.9	249.4	248.5	246.7	245.3
172.5°	245.5	246.1	245.7	245.1	245.7	246.1	245.5	245.0	244.5	243.0	242.1
175°	239.9	240.3	239.9	239.0	239.9	240.3	239.9	239.9	239.5	239.0	238.5
177.5°	236.4	236.4	236.0	235.3	236.0	236.4	236.4	236.4	236.4	236.0	236.0
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	4.7	4.9	5.0	4.6	4.0	3.6	3.6	3.5	3.6	3.4	3.2
90°	14.9	15.4	14.9	12.2	9.0	6.8	5.4	4.5	3.6	1.8	0.5
92.5°	49.6	58.7	57.9	45.1	30.7	20.5	16.2	13.2	11.2	7.9	5.5
95°	155.0	177.1	156.8	104.3	65.0	44.3	33.4	26.2	22.1	17.6	15.8
97.5°	317.1	302.3	227.7	140.6	85.9	59.7	47.5	39.1	33.0	28.2	25.7
100°	421.9	356.9	245.7	148.2	93.1	69.2	56.5	47.5	40.2	36.1	34.8
102.5°	461.0	358.7	238.9	148.5	99.6	77.4	64.8	55.4	48.2	44.1	43.1
105°	455.0	334.8	225.5	150.9	110.7	89.4	76.8	66.9	60.0	57.0	55.1
107.5°	415.3	309.1	218.7	157.1	122.1	101.5	88.7	78.9	72.6	69.6	68.1
110°	390.3	296.8	217.3	162.2	129.7	109.8	96.6	87.2	81.4	78.6	76.8



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	373.0	288.8	217.7	167.6	136.9	117.7	104.3	95.1	89.6	86.6	84.8
115°	351.5	280.1	219.6	175.7	148.2	128.7	116.5	107.5	102.1	99.4	97.1
117.5°	337.9	275.8	222.8	184.4	158.6	140.6	127.9	119.3	114.5	111.8	110.0
120°	330.7	273.3	225.0	190.2	165.8	148.2	135.5	126.5	122.4	119.7	117.9
122.5°	324.6	271.9	227.5	195.3	172.7	156.1	143.1	134.1	129.7	127.0	125.5
125°	315.8	269.3	231.3	203.3	183.0	166.7	154.1	145.0	139.6	136.9	135.5
127.5°	307.7	267.8	235.2	210.8	192.6	176.7	163.7	155.0	149.1	145.3	143.5
130°	302.2	267.0	238.1	215.5	198.4	182.5	169.8	160.8	154.5	150.0	148.2
132.5°	297.9	266.6	241.0	220.2	203.4	188.3	175.6	166.3	159.5	154.7	152.5
135°	291.8	266.1	244.4	226.3	210.6	196.1	183.4	173.0	166.3	160.8	159.0
137.5°	287.6	266.0	247.5	231.0	216.3	202.0	190.3	180.0	172.8	167.3	165.2
140°	285.1	265.6	248.9	233.5	219.6	206.0	194.2	184.3	177.1	171.7	169.8
142.5°	282.6	265.6	250.0	235.8	222.1	208.9	197.9	188.3	181.1	176.0	174.6
145°	279.2	264.7	251.2	238.5	225.9	213.7	203.7	194.7	187.9	183.4	181.6
147.5°	275.8	263.1	251.5	240.1	228.9	217.5	208.7	201.1	194.9	190.5	189.2
150°	272.9	262.1	251.2	240.8	230.4	220.0	211.9	205.1	199.2	195.6	194.2
152.5°	270.4	260.2	250.5	241.1	231.9	222.5	215.2	208.7	203.6	199.9	199.3
155°	265.6	257.1	249.4	241.7	234.0	226.3	219.6	214.6	209.6	206.9	206.4
157.5°	261.2	253.8	247.3	241.7	235.5	229.0	223.4	219.4	215.1	212.9	212.4
160°	257.9	251.7	246.2	241.7	236.3	230.8	225.9	222.3	218.6	216.8	216.4
162.5°	255.1	249.9	245.1	241.3	236.6	232.0	228.1	224.8	221.9	220.1	220.4
165°	250.3	246.2	243.0	240.3	237.2	233.1	230.4	228.1	225.5	224.5	225.0
167.5°	245.6	243.0	241.0	239.7	237.1	234.1	232.4	230.8	229.0	228.2	228.8
170°	243.0	241.2	239.9	239.0	236.7	234.5	233.1	232.2	230.8	230.4	231.3
172.5°	240.5	239.1	238.4	237.9	236.4	234.8	233.9	233.3	232.0	232.2	232.7
175°	237.2	236.7	236.3	236.7	235.8	234.9	234.5	234.5	233.5	234.0	234.5
177.5°	235.3	234.9	235.3	236.0	235.3	234.9	234.9	234.9	234.2	234.6	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.0	4.9	5.1	5.7	5.7	6.1	6.7	7.1	7.1	6.9	6.7
90°	1.8	3.6	4.5	5.4	6.8	9.0	12.2	14.9	15.4	14.9	14.4
92.5°	7.9	11.2	13.2	16.2	20.5	30.7	45.1	57.9	58.7	49.6	39.4
95°	17.6	22.1	26.2	33.4	44.3	65.0	104.3	156.8	177.1	155.0	118.4
97.5°	28.2	33.0	39.1	47.5	59.7	85.9	140.6	227.7	302.3	317.1	276.2
100°	36.1	40.2	47.5	56.5	69.2	93.1	148.2	245.7	356.9	421.9	412.5
102.5°	44.1	48.2	55.4	64.8	77.4	99.6	148.5	238.9	358.7	461.0	501.8
105°	57.0	60.0	66.9	76.8	89.4	110.7	150.9	225.5	334.8	455.0	548.9
107.5°	69.6	72.6	78.9	88.7	101.5	122.1	157.1	218.7	309.1	415.3	514.9
110°	78.6	81.4	87.2	96.6	109.8	129.7	162.2	217.3	296.8	390.3	485.7





TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	86.6	89.6	95.1	104.3	117.7	136.9	167.6	217.7	288.8	373.0	458.9
115°	99.4	102.1	107.5	116.5	128.7	148.2	175.7	219.6	280.1	351.5	426.0
117.5°	111.8	114.5	119.3	127.9	140.6	158.6	184.4	222.8	275.8	337.9	401.2
120°	119.7	122.4	126.5	135.5	148.2	165.8	190.2	225.0	273.3	330.7	389.0
122.5°	127.0	129.7	134.1	143.1	156.1	172.7	195.3	227.5	271.9	324.6	379.2
125°	136.9	139.6	145.0	154.1	166.7	183.0	203.3	231.3	269.3	315.8	365.0
127.5°	145.3	149.1	155.0	163.7	176.7	192.6	210.8	235.2	267.8	307.7	351.0
130°	150.0	154.5	160.8	169.8	182.5	198.4	215.5	238.1	267.0	302.2	342.0
132.5°	154.7	159.5	166.3	175.6	188.3	203.4	220.2	241.0	266.6	297.9	333.4
135°	160.8	166.3	173.0	183.4	196.1	210.6	226.3	244.4	266.1	291.8	321.2
137.5°	167.3	172.8	180.0	190.3	202.0	216.3	231.0	247.5	266.0	287.6	311.6
140°	171.7	177.1	184.3	194.2	206.0	219.6	233.5	248.9	265.6	285.1	305.4
142.5°	176.0	181.1	188.3	197.9	208.9	222.1	235.8	250.0	265.6	282.6	300.3
145°	183.4	187.9	194.7	203.7	213.7	225.9	238.5	251.2	264.7	279.2	293.2
147.5°	190.5	194.9	201.1	208.7	217.5	228.9	240.1	251.5	263.1	275.8	287.7
150°	195.6	199.2	205.1	211.9	220.0	230.4	240.8	251.2	262.1	272.9	283.7
152.5°	199.9	203.6	208.7	215.2	222.5	231.9	241.1	250.5	260.2	270.4	279.7
155°	206.9	209.6	214.6	219.6	226.3	234.0	241.7	249.4	257.1	265.6	274.3
157.5°	212.9	215.1	219.4	223.4	229.0	235.5	241.7	247.3	253.8	261.2	267.8
160°	216.8	218.6	222.3	225.9	230.8	236.3	241.7	246.2	251.7	257.9	263.8
162.5°	220.1	221.9	224.8	228.1	232.0	236.6	241.3	245.1	249.9	255.1	259.8
165°	224.5	225.5	228.1	230.4	233.1	237.2	240.3	243.0	246.2	250.3	253.9
167.5°	228.2	229.0	230.8	232.4	234.1	237.1	239.7	241.0	243.0	245.6	248.2
170°	230.4	230.8	232.2	233.1	234.5	236.7	239.0	239.9	241.2	243.0	245.3
172.5°	232.2	232.0	233.3	233.9	234.8	236.4	237.9	238.4	239.1	240.5	242.1
175°	234.0	233.5	234.5	234.5	234.9	235.8	236.7	236.3	236.7	237.2	238.5
177.5°	234.6	234.2	234.9	234.9	234.9	235.3	236.0	235.3	234.9	235.3	236.0
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9	234.9



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	6.6	6.8	6.7	6.7	6.9	6.7	6.7
90°	13.5	14.4	14.9	14.9	14.9	14.9	14.9
92.5°	33.8	30.0	27.2	26.9	25.4	25.7	25.0
95°	90.8	71.9	61.9	56.0	52.4	51.0	51.5
97.5°	226.0	177.1	144.5	122.9	111.8	105.2	101.4
100°	356.5	294.5	239.9	202.4	183.0	169.8	161.8
102.5°	489.1	443.9	385.9	345.2	312.0	295.6	284.6
105°	599.9	605.9	590.9	562.9	534.9	515.5	509.1
107.5°	591.8	638.8	660.7	664.2	662.7	658.8	650.4
110°	566.5	624.3	661.4	680.8	689.4	693.5	693.0



TEST NUMBER: P331251-927

CATALOG NUMBER: SA2XXDIP-C290D530U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	536.5	598.3	640.8	667.8	682.1	689.8	692.3
115°	495.6	554.8	601.3	633.3	654.2	665.9	669.9
117.5°	462.3	516.0	559.7	592.4	614.3	626.7	630.1
120°	445.0	492.9	534.0	565.6	586.8	599.9	604.4
122.5°	430.6	475.9	513.0	541.4	562.3	573.9	577.7
125°	411.5	451.3	485.2	511.4	528.5	539.9	543.5
127.5°	393.2	430.6	461.9	484.7	500.8	510.6	513.5
130°	380.9	416.5	446.3	468.5	483.9	492.9	496.5
132.5°	369.3	402.1	430.1	451.9	467.2	475.5	478.8
135°	351.0	380.9	406.2	425.6	440.5	448.6	450.4
137.5°	336.5	360.1	382.2	399.9	412.7	419.9	422.6
140°	327.1	347.8	367.7	382.2	394.0	400.7	403.5
142.5°	318.8	336.7	353.3	367.0	377.7	383.7	384.3
145°	308.1	322.1	335.3	346.0	353.7	358.2	359.6
147.5°	299.4	310.4	320.0	328.9	335.0	338.1	338.9
150°	293.7	303.2	311.2	318.1	323.4	326.1	326.6
152.5°	289.0	297.0	304.0	309.3	314.1	316.1	316.2
155°	281.5	288.2	293.2	298.2	301.3	303.2	302.2
157.5°	273.9	279.6	283.4	286.9	289.6	290.4	290.4
160°	268.8	273.8	276.9	280.1	282.3	282.8	282.8
162.5°	264.1	268.4	270.8	273.9	275.5	275.9	275.6
165°	257.1	260.2	262.1	263.8	265.6	265.6	265.2
167.5°	250.6	252.8	254.4	255.2	256.3	256.2	255.6
170°	246.7	248.5	249.4	249.9	251.2	250.7	249.9
172.5°	243.0	244.5	245.0	245.5	246.1	245.7	245.1
175°	239.0	239.5	239.9	239.9	240.3	239.9	239.0
177.5°	236.0	236.4	236.4	236.4	236.4	236.0	235.3
180°	234.9	234.9	234.9	234.9	234.9	234.9	234.9

(END OF REPORT)