

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331287-830

Luminaire Tested: **SA2XXDIP-C485D330U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331287-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3227.3 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331287-830
CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63				
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54				
2	93	85	79	74	87	80	75	71	71	67	64	62	59	57	54	52	50	46				
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43	40				
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35				
5	72	60	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33	31				
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27				
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	24				
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22				
9	54	42	34	29	50	39	33	28	36	30	26	32	27	24	29	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14788	14788	14788	14788
5°	16579	14885	13190	14885
10°	18998	14762	11416	14762
15°	21018	14492	10084	14492
20°	20697	14201	9194	14201
25°	18661	13814	8630	13814
30°	15422	13196	8216	13196
35°	11239	12552	7924	12552
40°	8977	11788	7761	11788
45°	7846	10908	7540	10908
50°	7375	10052	7392	10052
55°	6798	9185	7192	9185
60°	6229	8263	6888	8263
65°	5673	7435	6590	7435
70°	5150	6628	6151	6628
75°	4566	5733	5446	5733
80°	3924	4751	4379	4751
85°	3520	3520	2594	3520



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	2.7
10°-20°	253.6	7.9
20°-30°	368.0	11.4
30°-40°	388.4	12.0
40°-50°	343.9	10.7
50°-60°	274.4	8.5
60°-70°	186.5	5.8
70°-80°	95.6	3.0
80°-90°	24.6	0.8
90°-100°	69.2	2.1
100°-110°	235.0	7.3
110°-120°	249.6	7.7
120°-130°	205.5	6.4
130°-140°	165.0	5.1
140°-150°	124.7	3.9
150°-160°	87.6	2.7
160°-170°	51.6	1.6
170°-180°	16.8	0.5
0°-30°	708.8	22.0
0°-40°	1097.2	34.0
0°-60°	1715.5	53.2
0°-90°	2022.2	62.7
90°-120°	553.8	17.2
90°-150°	1049.0	32.5
90°-180°	1205.0	37.3
0°-180°	3227.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	916	916	916	916	916	
5°	1023	918	814	918	1023	102
15°	1257	867	603	867	1257	347
25°	1048	775	484	775	1048	473
35°	570	637	402	637	570	371
45°	344	478	330	478	344	270
55°	242	326	256	326	242	217
65°	148	195	172	195	148	148
75°	73	92	87	92	73	78
85°	19	19	14	19	19	21
90°	11	0	11	0	11	7
95°	38	12	38	12	38	49
105°	375	41	375	41	375	363
115°	494	72	494	72	494	484
125°	401	100	401	100	401	362
135°	332	117	332	117	332	258
145°	265	134	265	134	265	168
155°	223	152	223	152	223	104
165°	196	166	196	166	196	56
175°	176	173	176	173	176	17
180°	173	173	173	173	173	



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	958.2	958.5	958.9	954.5	953.9	953.9	950.0	946.6	942.6	937.3	937.8
5°	1022.9	1026.8	1028.2	1024.0	1017.7	1016.9	1011.0	1001.1	991.9	984.6	979.3
7.5°	1100.2	1101.7	1098.3	1092.8	1088.1	1079.6	1068.5	1057.5	1042.3	1028.2	1017.9
10°	1158.8	1160.9	1154.9	1146.8	1140.1	1130.3	1114.1	1097.5	1077.5	1058.1	1042.6
12.5°	1203.2	1208.5	1200.8	1199.8	1188.3	1174.8	1155.5	1147.1	1118.9	1091.9	1075.3
15°	1257.4	1257.0	1257.7	1251.0	1242.6	1240.5	1220.0	1197.9	1158.1	1142.3	1114.7
17.5°	1241.7	1247.1	1249.5	1249.4	1249.2	1247.9	1241.3	1227.4	1207.4	1181.8	1150.1
20°	1204.6	1211.5	1212.7	1220.8	1225.3	1231.3	1233.8	1229.9	1217.6	1196.1	1168.7
22.5°	1147.1	1149.1	1152.4	1165.0	1174.9	1189.9	1197.7	1210.7	1206.0	1195.5	1172.6
25°	1047.5	1044.1	1056.3	1062.7	1085.5	1109.5	1126.7	1145.8	1162.6	1172.9	1166.2
27.5°	928.0	922.7	941.2	958.0	976.6	1002.5	1029.4	1061.1	1087.5	1120.6	1131.9
30°	827.2	830.4	848.0	865.9	894.1	930.7	960.9	995.8	1033.5	1070.4	1096.1
32.5°	718.5	730.7	741.8	769.3	794.1	834.9	879.3	922.8	969.9	1011.8	1051.6
35°	570.2	584.3	599.8	619.9	654.7	695.2	738.5	797.3	861.4	918.7	965.9
37.5°	479.9	477.8	486.6	501.1	529.3	562.0	611.8	670.0	745.4	812.8	879.3
40°	425.9	424.5	430.8	444.2	465.7	489.7	533.3	584.3	654.4	736.7	816.0
42.5°	388.7	389.6	393.1	402.6	417.3	437.0	469.7	513.1	577.2	654.8	739.9
45°	343.6	346.0	349.9	354.5	362.9	379.1	397.4	428.4	479.1	543.8	627.6
47.5°	311.0	311.1	315.0	319.1	324.0	333.2	348.2	367.6	403.3	456.1	528.1
50°	293.6	291.1	293.9	297.1	302.4	308.7	318.6	336.9	360.8	403.4	463.5
52.5°	272.2	272.2	274.8	276.0	280.7	287.0	296.1	308.7	330.4	363.7	413.2
55°	241.5	243.3	244.7	246.8	251.0	255.5	262.6	271.1	287.9	312.9	349.5
57.5°	212.6	213.2	214.6	218.6	221.3	225.5	232.1	239.9	250.8	269.4	296.9
60°	192.9	192.9	195.7	197.5	201.0	205.2	210.5	217.9	227.7	242.9	265.0
62.5°	174.8	174.6	175.7	178.6	181.3	185.2	190.5	196.8	206.0	219.5	237.7
65°	148.5	147.9	150.0	150.6	153.4	157.3	161.6	168.2	175.7	185.5	201.7
67.5°	123.2	124.0	125.2	126.5	128.1	132.1	135.0	139.7	145.9	154.1	165.1
70°	109.1	109.1	109.1	110.2	112.3	114.4	117.3	121.1	127.1	134.1	143.9
72.5°	93.3	94.4	95.6	95.0	97.6	98.9	102.3	104.4	110.2	114.7	123.4
75°	73.2	73.2	73.2	74.9	76.1	77.1	79.2	81.3	84.2	89.7	94.3
77.5°	54.7	54.5	54.9	55.2	56.4	57.7	58.2	60.2	62.8	65.4	69.3
80°	42.2	43.0	43.3	44.0	44.0	44.7	45.1	47.5	49.3	51.1	53.5
82.5°	32.7	32.8	32.9	33.0	33.3	33.7	34.6	35.4	36.0	37.5	39.4
85°	19.0	18.7	18.7	19.3	19.0	19.0	19.7	20.5	20.5	20.7	21.9
87.5°	9.5	9.5	9.8	9.5	9.5	9.7	9.6	9.4	9.8	10.2	10.4
90°	11.0	11.0	11.0	11.0	11.0	10.7	10.0	10.7	11.0	11.3	11.0
92.5°	18.5	18.9	18.8	19.8	20.1	22.1	24.9	29.0	36.6	43.3	42.7
95°	38.0	37.6	38.6	41.3	45.6	53.0	66.9	87.3	114.2	130.5	115.6
97.5°	74.7	77.6	82.4	90.6	106.5	130.5	166.5	203.6	233.8	222.8	167.9
100°	119.2	125.3	134.9	149.2	176.8	217.2	262.8	304.1	311.0	263.1	181.2
102.5°	209.8	217.9	230.0	254.4	284.5	327.2	360.5	369.9	339.8	264.4	176.1
105°	375.3	379.9	394.3	414.9	435.6	446.6	442.2	404.6	335.4	246.8	166.2
107.5°	479.5	485.6	488.5	489.7	487.0	470.9	436.3	379.6	306.1	227.8	161.3
110°	510.9	511.2	508.2	501.9	487.6	460.2	417.6	358.0	287.8	218.8	160.2



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	510.3	508.5	502.8	492.3	472.4	441.0	395.5	338.3	274.9	212.9	160.4
115°	493.9	490.9	482.2	466.9	443.3	409.0	365.3	314.1	259.1	206.5	161.8
117.5°	464.5	461.9	452.9	436.7	412.6	380.4	340.8	295.8	249.1	203.3	164.3
120°	445.6	442.2	432.6	417.0	393.6	363.4	328.0	286.7	243.7	201.5	165.9
122.5°	425.8	423.1	414.5	399.1	378.1	350.8	317.4	279.6	239.2	200.4	167.7
125°	400.7	397.9	389.6	377.0	357.7	332.7	303.4	269.1	232.8	198.5	170.5
127.5°	378.5	376.4	369.2	357.3	340.4	317.4	289.8	258.7	226.8	197.4	173.3
130°	366.0	363.4	356.7	345.3	329.0	307.1	280.8	252.1	222.8	196.8	175.5
132.5°	353.0	350.5	344.4	333.1	317.1	296.4	272.2	245.7	219.6	196.5	177.7
135°	332.1	330.7	324.7	313.7	299.4	280.8	258.7	236.8	215.1	196.1	180.2
137.5°	311.5	309.5	304.3	294.8	281.7	265.5	248.1	229.7	212.0	196.0	182.5
140°	297.4	295.4	290.4	281.7	271.1	256.5	241.1	225.1	210.1	195.9	183.5
142.5°	283.2	282.9	278.4	270.5	260.4	248.2	235.0	221.4	208.3	195.9	184.3
145°	265.0	264.1	260.8	255.1	247.1	237.4	227.2	216.1	205.9	195.1	185.1
147.5°	249.9	249.2	246.9	242.4	235.8	228.8	220.7	212.1	203.3	194.0	185.4
150°	240.8	240.4	238.5	234.4	229.4	223.5	216.5	209.2	201.1	193.1	185.1
152.5°	233.1	233.0	231.5	228.1	224.1	219.0	213.0	206.2	199.3	191.8	184.6
155°	222.8	223.5	222.2	219.8	216.1	212.4	207.5	202.2	195.9	189.5	183.8
157.5°	214.1	214.1	213.5	211.5	209.0	206.0	201.9	197.5	192.6	187.1	182.3
160°	208.5	208.5	208.1	206.5	204.2	201.8	198.1	194.4	190.1	185.5	181.5
162.5°	203.1	203.4	203.1	202.0	199.6	197.8	194.7	191.5	188.0	184.2	180.7
165°	195.5	195.9	195.9	194.4	193.1	191.8	189.5	187.2	184.5	181.5	179.2
167.5°	188.4	188.8	188.9	188.1	187.6	186.3	184.7	182.9	181.1	179.2	177.7
170°	184.2	184.8	185.1	184.2	183.8	183.1	181.8	180.9	179.2	177.9	176.8
172.5°	180.7	181.1	181.4	181.0	180.6	180.2	179.2	178.4	177.3	176.3	175.8
175°	176.2	176.8	177.2	176.8	176.8	176.5	176.2	175.9	174.8	174.5	174.2
177.5°	173.4	174.0	174.3	174.3	174.3	174.3	174.0	174.0	173.4	173.1	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	939.8	937.5	936.1	931.1	926.6	922.1	920.7	921.2	915.0	909.2	906.6
5°	976.5	969.4	962.7	953.2	942.0	929.6	923.3	918.4	906.1	892.7	885.0
7.5°	1009.3	999.2	986.3	968.5	952.1	932.6	920.3	909.5	891.4	872.5	861.0
10°	1029.3	1015.5	999.0	977.1	957.1	933.5	917.0	900.4	879.3	856.8	842.7
12.5°	1046.4	1027.9	1011.6	983.6	959.9	930.4	910.8	887.5	865.3	838.5	824.6
15°	1087.3	1053.2	1022.2	990.5	961.3	920.1	898.3	867.0	837.7	804.6	788.8
17.5°	1118.9	1080.5	1031.8	991.6	957.4	911.8	879.8	842.3	807.7	769.9	748.4
20°	1137.0	1093.0	1040.5	992.7	951.8	899.8	864.9	826.5	786.0	743.4	720.2
22.5°	1147.6	1101.5	1049.5	988.4	940.6	889.9	846.0	804.0	762.9	717.0	692.6
25°	1151.0	1108.8	1053.9	984.9	926.4	869.1	816.2	775.4	725.9	682.9	647.3
27.5°	1134.3	1104.0	1051.2	978.3	910.2	843.1	784.3	738.0	685.6	639.0	603.2
30°	1113.7	1096.1	1044.7	971.5	897.2	825.1	760.3	707.8	655.8	608.6	572.0
32.5°	1081.9	1078.1	1032.9	962.0	883.4	802.3	735.3	682.2	624.5	578.2	543.3
35°	1019.4	1036.3	1007.8	940.6	857.4	769.9	697.3	636.8	576.9	532.5	499.8
37.5°	935.7	977.6	970.2	909.2	822.4	734.5	654.4	591.2	534.1	489.4	457.2
40°	877.9	931.4	939.1	885.2	797.7	707.2	622.4	559.3	503.7	462.9	430.5
42.5°	816.0	878.4	899.8	856.6	770.6	678.4	593.6	528.4	473.3	433.6	404.9
45°	712.1	794.8	833.2	808.5	725.5	631.1	543.8	477.7	427.7	390.4	368.2
47.5°	615.0	705.4	757.1	748.3	675.2	581.8	495.6	432.1	383.4	353.6	333.8
50°	546.3	639.2	701.5	704.4	639.2	546.7	460.1	400.2	355.5	327.7	311.5
52.5°	486.6	575.3	643.3	658.2	599.0	510.0	428.2	368.7	329.3	303.8	289.3
55°	408.7	483.6	559.0	586.4	538.9	454.4	378.7	326.3	289.4	271.7	259.1
57.5°	339.8	402.3	471.8	502.2	472.9	400.6	329.6	284.1	254.1	238.7	228.9
60°	303.4	352.7	414.6	450.9	425.6	361.2	299.2	255.9	231.3	217.5	208.4
62.5°	269.7	313.3	365.6	398.8	385.0	324.2	268.8	230.5	209.3	196.4	189.8
65°	222.4	256.9	297.5	328.1	319.0	272.8	227.4	194.6	177.8	167.6	162.3
67.5°	183.1	208.1	236.2	263.0	255.6	222.9	186.5	161.0	148.4	139.6	136.5
70°	158.4	177.4	202.4	223.9	217.9	191.1	162.3	140.4	129.5	122.2	118.9
72.5°	134.8	150.3	169.5	187.0	182.9	160.7	136.7	120.2	111.8	105.0	102.4
75°	101.7	113.7	125.4	137.0	135.9	118.7	104.5	91.9	85.2	79.9	78.9
77.5°	75.1	81.8	89.7	96.6	94.7	84.8	73.8	66.5	61.6	58.1	57.5
80°	57.4	61.3	66.9	71.8	69.4	65.1	56.4	51.1	47.5	44.0	42.6
82.5°	41.6	45.5	48.8	51.6	49.7	45.7	40.2	36.7	34.6	32.1	31.6
85°	21.9	23.9	25.4	26.0	25.4	22.9	20.5	19.0	17.2	16.2	15.8
87.5°	10.3	9.8	9.4	9.8	8.9	8.7	7.4	6.2	6.2	6.1	5.7
90°	9.0	6.7	5.0	4.0	3.3	2.6	1.3	0.4	1.3	2.6	3.3
92.5°	33.3	22.6	15.1	12.0	9.7	8.3	5.8	4.1	5.8	8.3	9.7
95°	76.9	48.0	32.6	24.6	19.3	16.3	13.0	11.7	13.0	16.3	19.3
97.5°	103.7	63.2	44.0	35.0	28.8	24.3	20.7	18.9	20.7	24.3	28.8
100°	109.2	68.6	51.0	41.7	35.0	29.6	26.7	25.6	26.7	29.6	35.0
102.5°	109.5	73.4	57.1	47.8	40.8	35.5	32.5	31.8	32.5	35.5	40.8
105°	111.2	81.6	66.0	56.6	49.3	44.3	41.9	40.6	41.9	44.3	49.3
107.5°	115.8	90.0	74.8	65.4	58.2	53.5	51.3	50.2	51.3	53.5	58.2
110°	119.5	95.6	81.0	71.3	64.3	59.9	58.0	56.6	58.0	59.9	64.3



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	123.6	100.9	86.8	76.8	70.1	66.1	63.8	62.5	63.8	66.1	70.1
115°	129.5	109.2	94.9	86.0	79.3	75.3	73.2	71.6	73.2	75.3	79.3
117.5°	135.9	116.9	103.7	94.3	87.9	84.4	82.4	81.1	82.4	84.4	87.9
120°	140.3	122.2	109.2	99.9	93.2	90.3	88.2	86.9	88.2	90.3	93.2
122.5°	143.9	127.2	115.1	105.5	98.9	95.6	93.6	92.6	93.6	95.6	98.9
125°	149.9	134.9	122.9	113.6	106.9	102.9	100.9	99.9	100.9	102.9	106.9
127.5°	155.4	141.9	130.3	120.6	114.3	109.9	107.1	105.8	107.1	109.9	114.3
130°	158.8	146.2	134.5	125.3	118.6	113.9	110.6	109.2	110.6	113.9	118.6
132.5°	162.3	150.0	138.8	129.5	122.5	117.6	114.0	112.4	114.0	117.6	122.5
135°	166.8	155.2	144.5	135.3	127.5	122.5	118.6	117.3	118.6	122.5	127.5
137.5°	170.3	159.5	148.9	140.3	132.7	127.3	123.4	121.8	123.4	127.3	132.7
140°	172.2	161.8	151.8	143.2	135.9	130.5	126.6	125.3	126.6	130.5	135.9
142.5°	173.8	163.7	154.0	145.9	138.8	133.5	129.8	128.7	129.8	133.5	138.8
145°	175.9	166.5	157.5	150.2	143.5	138.6	135.3	133.8	135.3	138.6	143.5
147.5°	177.0	168.8	160.3	153.8	148.3	143.6	140.4	139.5	140.4	143.6	148.3
150°	177.5	169.8	162.2	156.2	151.2	146.8	144.2	143.2	144.2	146.8	151.2
152.5°	177.8	170.9	164.0	158.6	153.8	150.1	147.4	146.9	147.4	150.1	153.8
155°	178.1	172.5	166.8	161.8	158.2	154.5	152.5	152.2	152.5	154.5	158.2
157.5°	178.1	173.6	168.8	164.7	161.7	158.5	156.9	156.6	156.9	158.5	161.7
160°	178.1	174.2	170.2	166.5	163.8	161.2	159.9	159.5	159.9	161.2	163.8
162.5°	177.9	174.5	171.0	168.1	165.7	163.6	162.2	162.5	162.2	163.6	165.7
165°	177.2	174.8	171.8	169.8	168.1	166.2	165.5	165.9	165.5	166.2	168.1
167.5°	176.7	174.7	172.6	171.4	170.1	168.8	168.2	168.6	168.2	168.8	170.1
170°	176.2	174.5	172.9	171.8	171.2	170.2	169.8	170.5	169.8	170.2	171.2
172.5°	175.4	174.3	173.1	172.4	172.0	171.0	171.2	171.5	171.2	171.0	172.0
175°	174.5	173.8	173.1	172.9	172.9	172.2	172.5	172.9	172.5	172.2	172.9
177.5°	174.0	173.4	173.1	173.1	173.1	172.7	172.9	173.4	172.9	172.7	173.1
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	903.8	902.1	896.2	893.1	888.1	883.3	880.1	881.6	882.7	882.1	881.3
5°	877.9	871.2	861.0	852.2	845.8	834.2	829.3	826.9	824.7	822.3	819.8
7.5°	847.1	836.5	821.9	809.4	797.5	783.1	774.9	769.9	764.8	759.2	754.3
10°	825.1	810.3	794.8	777.2	763.2	750.1	738.5	730.8	723.7	717.0	712.1
12.5°	802.0	784.9	765.8	741.8	726.2	707.6	705.9	692.2	681.2	677.0	671.3
15°	765.3	741.3	717.0	688.5	676.2	659.3	648.8	638.2	628.7	622.0	620.2
17.5°	723.5	692.5	668.4	647.9	627.7	610.4	600.7	592.2	584.4	575.4	574.3
20°	691.6	665.0	638.6	620.6	599.8	582.2	570.2	561.8	555.1	549.8	545.3
22.5°	661.6	632.3	608.1	588.4	568.0	553.7	544.3	536.2	530.7	524.8	520.5
25°	613.2	590.3	563.9	541.8	524.8	515.7	507.9	500.9	497.4	493.5	488.6
27.5°	570.9	545.4	520.8	503.6	488.7	480.6	475.1	470.3	467.0	464.8	461.9
30°	541.0	515.3	496.0	479.1	466.7	458.6	455.2	452.3	448.5	447.0	445.6
32.5°	512.3	489.2	472.6	458.0	446.2	440.9	437.7	435.2	432.2	430.7	427.9
35°	471.6	452.3	436.1	428.0	418.5	414.0	411.5	407.9	405.2	403.8	403.4
37.5°	433.5	416.6	406.0	395.6	391.5	388.7	385.4	383.0	382.1	381.9	381.5
40°	408.7	394.9	385.4	377.0	375.2	371.0	368.2	366.1	366.1	366.5	366.1
42.5°	386.2	373.8	365.4	358.2	356.1	353.5	350.7	350.6	351.2	352.3	351.2
45°	352.0	343.2	337.2	333.7	329.8	327.3	327.0	328.1	328.4	328.8	329.8
47.5°	320.6	314.7	309.3	305.5	303.8	303.3	302.9	304.7	306.4	307.1	308.7
50°	302.0	295.3	290.8	288.3	286.9	286.2	286.9	289.0	290.4	292.2	293.2
52.5°	281.2	276.4	273.3	271.4	270.8	271.3	271.4	273.8	276.1	276.6	277.2
55°	252.4	248.8	248.2	245.0	246.4	246.0	247.8	249.2	251.3	253.4	253.8
57.5°	223.7	220.8	219.0	219.2	219.6	221.2	222.6	225.2	227.4	229.6	229.9
60°	204.5	203.1	202.1	202.1	202.7	204.9	206.6	209.1	210.5	211.9	212.9
62.5°	187.1	185.7	184.5	185.1	187.0	188.2	190.3	191.6	193.0	194.4	194.9
65°	159.5	158.7	159.9	160.5	160.9	162.6	165.1	166.2	167.6	168.2	170.7
67.5°	134.0	134.2	134.0	135.1	137.0	137.5	139.8	142.3	142.6	143.9	145.5
70°	116.9	117.5	118.3	118.9	120.7	121.4	123.2	124.2	125.6	126.7	127.8
72.5°	101.1	101.2	102.0	101.8	103.3	104.8	106.3	107.4	108.8	110.1	111.1
75°	77.8	77.8	78.5	78.9	80.6	82.4	82.0	82.8	84.2	85.6	86.2
77.5°	56.8	56.1	56.8	57.1	57.7	59.2	59.5	60.5	62.1	61.6	62.4
80°	43.3	42.2	43.3	43.6	43.6	45.4	45.4	46.1	47.1	46.1	47.1
82.5°	30.9	30.4	31.2	31.3	31.9	31.9	32.4	32.6	33.6	33.2	33.6
85°	15.5	15.2	15.5	15.2	15.5	15.8	15.8	15.5	15.5	16.2	15.2
87.5°	5.6	5.5	5.6	6.0	6.1	5.9	5.6	5.5	5.4	4.9	5.0
90°	4.0	5.0	6.7	9.0	11.0	11.3	11.0	10.7	10.0	10.7	11.0
92.5°	12.0	15.1	22.6	33.3	42.7	43.3	36.6	29.0	24.9	22.1	20.1
95°	24.6	32.6	48.0	76.9	115.6	130.5	114.2	87.3	66.9	53.0	45.6
97.5°	35.0	44.0	63.2	103.7	167.9	222.8	233.8	203.6	166.5	130.5	106.5
100°	41.7	51.0	68.6	109.2	181.2	263.1	311.0	304.1	262.8	217.2	176.8
102.5°	47.8	57.1	73.4	109.5	176.1	264.4	339.8	369.9	360.5	327.2	284.5
105°	56.6	66.0	81.6	111.2	166.2	246.8	335.4	404.6	442.2	446.6	435.6
107.5°	65.4	74.8	90.0	115.8	161.3	227.8	306.1	379.6	436.3	470.9	487.0
110°	71.3	81.0	95.6	119.5	160.2	218.8	287.8	358.0	417.6	460.2	487.6



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	76.8	86.8	100.9	123.6	160.4	212.9	274.9	338.3	395.5	441.0	472.4
115°	86.0	94.9	109.2	129.5	161.8	206.5	259.1	314.1	365.3	409.0	443.3
117.5°	94.3	103.7	116.9	135.9	164.3	203.3	249.1	295.8	340.8	380.4	412.6
120°	99.9	109.2	122.2	140.3	165.9	201.5	243.7	286.7	328.0	363.4	393.6
122.5°	105.5	115.1	127.2	143.9	167.7	200.4	239.2	279.6	317.4	350.8	378.1
125°	113.6	122.9	134.9	149.9	170.5	198.5	232.8	269.1	303.4	332.7	357.7
127.5°	120.6	130.3	141.9	155.4	173.3	197.4	226.8	258.7	289.8	317.4	340.4
130°	125.3	134.5	146.2	158.8	175.5	196.8	222.8	252.1	280.8	307.1	329.0
132.5°	129.5	138.8	150.0	162.3	177.7	196.5	219.6	245.7	272.2	296.4	317.1
135°	135.3	144.5	155.2	166.8	180.2	196.1	215.1	236.8	258.7	280.8	299.4
137.5°	140.3	148.9	159.5	170.3	182.5	196.0	212.0	229.7	248.1	265.5	281.7
140°	143.2	151.8	161.8	172.2	183.5	195.9	210.1	225.1	241.1	256.5	271.1
142.5°	145.9	154.0	163.7	173.8	184.3	195.9	208.3	221.4	235.0	248.2	260.4
145°	150.2	157.5	166.5	175.9	185.1	195.1	205.9	216.1	227.2	237.4	247.1
147.5°	153.8	160.3	168.8	177.0	185.4	194.0	203.3	212.1	220.7	228.8	235.8
150°	156.2	162.2	169.8	177.5	185.1	193.1	201.1	209.2	216.5	223.5	229.4
152.5°	158.6	164.0	170.9	177.8	184.6	191.8	199.3	206.2	213.0	219.0	224.1
155°	161.8	166.8	172.5	178.1	183.8	189.5	195.9	202.2	207.5	212.4	216.1
157.5°	164.7	168.8	173.6	178.1	182.3	187.1	192.6	197.5	201.9	206.0	209.0
160°	166.5	170.2	174.2	178.1	181.5	185.5	190.1	194.4	198.1	201.8	204.2
162.5°	168.1	171.0	174.5	177.9	180.7	184.2	188.0	191.5	194.7	197.8	199.6
165°	169.8	171.8	174.8	177.2	179.2	181.5	184.5	187.2	189.5	191.8	193.1
167.5°	171.4	172.6	174.7	176.7	177.7	179.2	181.1	182.9	184.7	186.3	187.6
170°	171.8	172.9	174.5	176.2	176.8	177.9	179.2	180.9	181.8	183.1	183.8
172.5°	172.4	173.1	174.3	175.4	175.8	176.3	177.3	178.4	179.2	180.2	180.6
175°	172.9	173.1	173.8	174.5	174.2	174.5	174.8	175.9	176.2	176.5	176.8
177.5°	173.1	173.1	173.4	174.0	173.4	173.1	173.4	174.0	174.0	174.3	174.3
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331287-830
 CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	878.4	877.9	877.9	875.3	877.9	877.9	878.4	881.3	882.1	882.7	881.6
5°	814.9	813.8	812.1	813.8	812.1	813.8	814.9	819.8	822.3	824.7	826.9
7.5°	752.1	747.8	747.2	743.0	747.2	747.8	752.1	754.3	759.2	764.8	769.9
10°	706.2	703.3	702.9	696.3	702.9	703.3	706.2	712.1	717.0	723.7	730.8
12.5°	671.2	664.4	665.8	661.9	665.8	664.4	671.2	671.3	677.0	681.2	692.2
15°	610.7	610.7	609.4	603.3	609.4	610.7	610.7	620.2	622.0	628.7	638.2
17.5°	567.3	566.6	563.2	564.9	563.2	566.6	567.3	574.3	575.4	584.4	592.2
20°	541.4	539.2	535.1	535.1	535.1	539.2	541.4	545.3	549.8	555.1	561.8
22.5°	516.9	516.7	512.3	513.7	512.3	516.7	516.9	520.5	524.8	530.7	536.2
25°	488.2	485.4	483.3	484.4	483.3	485.4	488.2	488.6	493.5	497.4	500.9
27.5°	461.1	459.5	459.4	456.5	459.4	459.5	461.1	461.9	464.8	467.0	470.3
30°	445.3	441.8	442.4	440.7	442.4	441.8	445.3	445.6	447.0	448.5	452.3
32.5°	427.3	426.0	425.3	423.8	425.3	426.0	427.3	427.9	430.7	432.2	435.2
35°	402.7	403.0	401.2	402.0	401.2	403.0	402.7	403.4	403.8	405.2	407.9
37.5°	381.3	382.4	381.5	381.7	381.5	382.4	381.3	381.5	381.9	382.1	383.0
40°	367.1	367.1	367.1	368.2	367.1	367.1	367.1	366.1	366.5	366.1	366.1
42.5°	353.6	353.1	352.5	352.4	352.5	353.1	353.6	351.2	352.3	351.2	350.6
45°	330.5	331.6	332.0	330.2	332.0	331.6	330.5	329.8	328.8	328.4	328.1
47.5°	309.6	309.7	309.6	311.1	309.6	309.7	309.6	308.7	307.1	306.4	304.7
50°	295.0	294.3	295.0	294.3	295.0	294.3	295.0	293.2	292.2	290.4	289.0
52.5°	279.5	279.7	279.2	279.1	279.2	279.7	279.5	277.2	276.6	276.1	273.8
55°	255.2	255.9	255.5	255.5	255.5	255.9	255.2	253.8	253.4	251.3	249.2
57.5°	230.1	230.7	231.2	229.6	231.2	230.7	230.1	229.9	229.6	227.4	225.2
60°	212.6	214.3	214.1	213.3	214.1	214.3	212.6	212.9	211.9	210.5	209.1
62.5°	196.5	197.2	197.1	197.0	197.1	197.2	196.5	194.9	194.4	193.0	191.6
65°	171.7	172.5	171.4	172.5	171.4	172.5	171.7	170.7	168.2	167.6	166.2
67.5°	145.1	145.3	146.1	146.6	146.1	145.3	145.1	145.5	143.9	142.6	142.3
70°	128.5	128.1	129.2	130.3	129.2	128.1	128.5	127.8	126.7	125.6	124.2
72.5°	111.0	111.8	111.4	112.3	111.4	111.8	111.0	111.1	110.1	108.8	107.4
75°	85.6	86.6	86.2	87.3	86.2	86.6	85.6	86.2	85.6	84.2	82.8
77.5°	61.8	61.9	61.8	62.4	61.8	61.9	61.8	62.4	61.6	62.1	60.5
80°	47.1	46.5	45.7	47.1	45.7	46.5	47.1	47.1	46.1	47.1	46.1
82.5°	32.8	33.3	32.5	32.5	32.5	33.3	32.8	33.6	33.2	33.6	32.6
85°	15.2	14.8	14.0	14.0	14.0	14.8	15.2	15.2	16.2	15.5	15.5
87.5°	5.0	4.7	4.7	4.4	4.7	4.7	5.0	5.0	4.9	5.4	5.5
90°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	10.7	10.0	10.7
92.5°	19.8	18.8	18.9	18.5	18.9	18.8	19.8	20.1	22.1	24.9	29.0
95°	41.3	38.6	37.6	38.0	37.6	38.6	41.3	45.6	53.0	66.9	87.3
97.5°	90.6	82.4	77.6	74.7	77.6	82.4	90.6	106.5	130.5	166.5	203.6
100°	149.2	134.9	125.3	119.2	125.3	134.9	149.2	176.8	217.2	262.8	304.1
102.5°	254.4	230.0	217.9	209.8	217.9	230.0	254.4	284.5	327.2	360.5	369.9
105°	414.9	394.3	379.9	375.3	379.9	394.3	414.9	435.6	446.6	442.2	404.6
107.5°	489.7	488.5	485.6	479.5	485.6	488.5	489.7	487.0	470.9	436.3	379.6
110°	501.9	508.2	511.2	510.9	511.2	508.2	501.9	487.6	460.2	417.6	358.0



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.3	502.8	508.5	510.3	508.5	502.8	492.3	472.4	441.0	395.5	338.3
115°	466.9	482.2	490.9	493.9	490.9	482.2	466.9	443.3	409.0	365.3	314.1
117.5°	436.7	452.9	461.9	464.5	461.9	452.9	436.7	412.6	380.4	340.8	295.8
120°	417.0	432.6	442.2	445.6	442.2	432.6	417.0	393.6	363.4	328.0	286.7
122.5°	399.1	414.5	423.1	425.8	423.1	414.5	399.1	378.1	350.8	317.4	279.6
125°	377.0	389.6	397.9	400.7	397.9	389.6	377.0	357.7	332.7	303.4	269.1
127.5°	357.3	369.2	376.4	378.5	376.4	369.2	357.3	340.4	317.4	289.8	258.7
130°	345.3	356.7	363.4	366.0	363.4	356.7	345.3	329.0	307.1	280.8	252.1
132.5°	333.1	344.4	350.5	353.0	350.5	344.4	333.1	317.1	296.4	272.2	245.7
135°	313.7	324.7	330.7	332.1	330.7	324.7	313.7	299.4	280.8	258.7	236.8
137.5°	294.8	304.3	309.5	311.5	309.5	304.3	294.8	281.7	265.5	248.1	229.7
140°	281.7	290.4	295.4	297.4	295.4	290.4	281.7	271.1	256.5	241.1	225.1
142.5°	270.5	278.4	282.9	283.2	282.9	278.4	270.5	260.4	248.2	235.0	221.4
145°	255.1	260.8	264.1	265.0	264.1	260.8	255.1	247.1	237.4	227.2	216.1
147.5°	242.4	246.9	249.2	249.9	249.2	246.9	242.4	235.8	228.8	220.7	212.1
150°	234.4	238.5	240.4	240.8	240.4	238.5	234.4	229.4	223.5	216.5	209.2
152.5°	228.1	231.5	233.0	233.1	233.0	231.5	228.1	224.1	219.0	213.0	206.2
155°	219.8	222.2	223.5	222.8	223.5	222.2	219.8	216.1	212.4	207.5	202.2
157.5°	211.5	213.5	214.1	214.1	214.1	213.5	211.5	209.0	206.0	201.9	197.5
160°	206.5	208.1	208.5	208.5	208.5	208.1	206.5	204.2	201.8	198.1	194.4
162.5°	202.0	203.1	203.4	203.1	203.4	203.1	202.0	199.6	197.8	194.7	191.5
165°	194.4	195.9	195.9	195.5	195.9	195.9	194.4	193.1	191.8	189.5	187.2
167.5°	188.1	188.9	188.8	188.4	188.8	188.9	188.1	187.6	186.3	184.7	182.9
170°	184.2	185.1	184.8	184.2	184.8	185.1	184.2	183.8	183.1	181.8	180.9
172.5°	181.0	181.4	181.1	180.7	181.1	181.4	181.0	180.6	180.2	179.2	178.4
175°	176.8	177.2	176.8	176.2	176.8	177.2	176.8	176.8	176.5	176.2	175.9
177.5°	174.3	174.3	174.0	173.4	174.0	174.3	174.3	174.3	174.3	174.0	174.0
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	880.1	883.3	888.1	893.1	896.2	902.1	903.8	906.6	909.2	915.0	921.2
5°	829.3	834.2	845.8	852.2	861.0	871.2	877.9	885.0	892.7	906.1	918.4
7.5°	774.9	783.1	797.5	809.4	821.9	836.5	847.1	861.0	872.5	891.4	909.5
10°	738.5	750.1	763.2	777.2	794.8	810.3	825.1	842.7	856.8	879.3	900.4
12.5°	705.9	707.6	726.2	741.8	765.8	784.9	802.0	824.6	838.5	865.3	887.5
15°	648.8	659.3	676.2	688.5	717.0	741.3	765.3	788.8	804.6	837.7	867.0
17.5°	600.7	610.4	627.7	647.9	668.4	692.5	723.5	748.4	769.9	807.7	842.3
20°	570.2	582.2	599.8	620.6	638.6	665.0	691.6	720.2	743.4	786.0	826.5
22.5°	544.3	553.7	568.0	588.4	608.1	632.3	661.6	692.6	717.0	762.9	804.0
25°	507.9	515.7	524.8	541.8	563.9	590.3	613.2	647.3	682.9	725.9	775.4
27.5°	475.1	480.6	488.7	503.6	520.8	545.4	570.9	603.2	639.0	685.6	738.0
30°	455.2	458.6	466.7	479.1	496.0	515.3	541.0	572.0	608.6	655.8	707.8
32.5°	437.7	440.9	446.2	458.0	472.6	489.2	512.3	543.3	578.2	624.5	682.2
35°	411.5	414.0	418.5	428.0	436.1	452.3	471.6	499.8	532.5	576.9	636.8
37.5°	385.4	388.7	391.5	395.6	406.0	416.6	433.5	457.2	489.4	534.1	591.2
40°	368.2	371.0	375.2	377.0	385.4	394.9	408.7	430.5	462.9	503.7	559.3
42.5°	350.7	353.5	356.1	358.2	365.4	373.8	386.2	404.9	433.6	473.3	528.4
45°	327.0	327.3	329.8	333.7	337.2	343.2	352.0	368.2	390.4	427.7	477.7
47.5°	302.9	303.3	303.8	305.5	309.3	314.7	320.6	333.8	353.6	383.4	432.1
50°	286.9	286.2	286.9	288.3	290.8	295.3	302.0	311.5	327.7	355.5	400.2
52.5°	271.4	271.3	270.8	271.4	273.3	276.4	281.2	289.3	303.8	329.3	368.7
55°	247.8	246.0	246.4	245.0	248.2	248.8	252.4	259.1	271.7	289.4	326.3
57.5°	222.6	221.2	219.6	219.2	219.0	220.8	223.7	228.9	238.7	254.1	284.1
60°	206.6	204.9	202.7	202.1	202.1	203.1	204.5	208.4	217.5	231.3	255.9
62.5°	190.3	188.2	187.0	185.1	184.5	185.7	187.1	189.8	196.4	209.3	230.5
65°	165.1	162.6	160.9	160.5	159.9	158.7	159.5	162.3	167.6	177.8	194.6
67.5°	139.8	137.5	137.0	135.1	134.0	134.2	134.0	136.5	139.6	148.4	161.0
70°	123.2	121.4	120.7	118.9	118.3	117.5	116.9	118.9	122.2	129.5	140.4
72.5°	106.3	104.8	103.3	101.8	102.0	101.2	101.1	102.4	105.0	111.8	120.2
75°	82.0	82.4	80.6	78.9	78.5	77.8	77.8	78.9	79.9	85.2	91.9
77.5°	59.5	59.2	57.7	57.1	56.8	56.1	56.8	57.5	58.1	61.6	66.5
80°	45.4	45.4	43.6	43.6	43.3	42.2	43.3	42.6	44.0	47.5	51.1
82.5°	32.4	31.9	31.9	31.3	31.2	30.4	30.9	31.6	32.1	34.6	36.7
85°	15.8	15.8	15.5	15.2	15.5	15.2	15.5	15.8	16.2	17.2	19.0
87.5°	5.6	5.9	6.1	6.0	5.6	5.5	5.6	5.7	6.1	6.2	6.2
90°	11.0	11.3	11.0	9.0	6.7	5.0	4.0	3.3	2.6	1.3	0.4
92.5°	36.6	43.3	42.7	33.3	22.6	15.1	12.0	9.7	8.3	5.8	4.1
95°	114.2	130.5	115.6	76.9	48.0	32.6	24.6	19.3	16.3	13.0	11.7
97.5°	233.8	222.8	167.9	103.7	63.2	44.0	35.0	28.8	24.3	20.7	18.9
100°	311.0	263.1	181.2	109.2	68.6	51.0	41.7	35.0	29.6	26.7	25.6
102.5°	339.8	264.4	176.1	109.5	73.4	57.1	47.8	40.8	35.5	32.5	31.8
105°	335.4	246.8	166.2	111.2	81.6	66.0	56.6	49.3	44.3	41.9	40.6
107.5°	306.1	227.8	161.3	115.8	90.0	74.8	65.4	58.2	53.5	51.3	50.2
110°	287.8	218.8	160.2	119.5	95.6	81.0	71.3	64.3	59.9	58.0	56.6



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.9	212.9	160.4	123.6	100.9	86.8	76.8	70.1	66.1	63.8	62.5
115°	259.1	206.5	161.8	129.5	109.2	94.9	86.0	79.3	75.3	73.2	71.6
117.5°	249.1	203.3	164.3	135.9	116.9	103.7	94.3	87.9	84.4	82.4	81.1
120°	243.7	201.5	165.9	140.3	122.2	109.2	99.9	93.2	90.3	88.2	86.9
122.5°	239.2	200.4	167.7	143.9	127.2	115.1	105.5	98.9	95.6	93.6	92.6
125°	232.8	198.5	170.5	149.9	134.9	122.9	113.6	106.9	102.9	100.9	99.9
127.5°	226.8	197.4	173.3	155.4	141.9	130.3	120.6	114.3	109.9	107.1	105.8
130°	222.8	196.8	175.5	158.8	146.2	134.5	125.3	118.6	113.9	110.6	109.2
132.5°	219.6	196.5	177.7	162.3	150.0	138.8	129.5	122.5	117.6	114.0	112.4
135°	215.1	196.1	180.2	166.8	155.2	144.5	135.3	127.5	122.5	118.6	117.3
137.5°	212.0	196.0	182.5	170.3	159.5	148.9	140.3	132.7	127.3	123.4	121.8
140°	210.1	195.9	183.5	172.2	161.8	151.8	143.2	135.9	130.5	126.6	125.3
142.5°	208.3	195.9	184.3	173.8	163.7	154.0	145.9	138.8	133.5	129.8	128.7
145°	205.9	195.1	185.1	175.9	166.5	157.5	150.2	143.5	138.6	135.3	133.8
147.5°	203.3	194.0	185.4	177.0	168.8	160.3	153.8	148.3	143.6	140.4	139.5
150°	201.1	193.1	185.1	177.5	169.8	162.2	156.2	151.2	146.8	144.2	143.2
152.5°	199.3	191.8	184.6	177.8	170.9	164.0	158.6	153.8	150.1	147.4	146.9
155°	195.9	189.5	183.8	178.1	172.5	166.8	161.8	158.2	154.5	152.5	152.2
157.5°	192.6	187.1	182.3	178.1	173.6	168.8	164.7	161.7	158.5	156.9	156.6
160°	190.1	185.5	181.5	178.1	174.2	170.2	166.5	163.8	161.2	159.9	159.5
162.5°	188.0	184.2	180.7	177.9	174.5	171.0	168.1	165.7	163.6	162.2	162.5
165°	184.5	181.5	179.2	177.2	174.8	171.8	169.8	168.1	166.2	165.5	165.9
167.5°	181.1	179.2	177.7	176.7	174.7	172.6	171.4	170.1	168.8	168.2	168.6
170°	179.2	177.9	176.8	176.2	174.5	172.9	171.8	171.2	170.2	169.8	170.5
172.5°	177.3	176.3	175.8	175.4	174.3	173.1	172.4	172.0	171.0	171.2	171.5
175°	174.8	174.5	174.2	174.5	173.8	173.1	172.9	172.9	172.2	172.5	172.9
177.5°	173.4	173.1	173.4	174.0	173.4	173.1	173.1	173.1	172.7	172.9	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	920.7	922.1	926.6	931.1	936.1	937.5	939.8	937.8	937.3	942.6	946.6
5°	923.3	929.6	942.0	953.2	962.7	969.4	976.5	979.3	984.6	991.9	1001.1
7.5°	920.3	932.6	952.1	968.5	986.3	999.2	1009.3	1017.9	1028.2	1042.3	1057.5
10°	917.0	933.5	957.1	977.1	999.0	1015.5	1029.3	1042.6	1058.1	1077.5	1097.5
12.5°	910.8	930.4	959.9	983.6	1011.6	1027.9	1046.4	1075.3	1091.9	1118.9	1147.1
15°	898.3	920.1	961.3	990.5	1022.2	1053.2	1087.3	1114.7	1142.3	1158.1	1197.9
17.5°	879.8	911.8	957.4	991.6	1031.8	1080.5	1118.9	1150.1	1181.8	1207.4	1227.4
20°	864.9	899.8	951.8	992.7	1040.5	1093.0	1137.0	1168.7	1196.1	1217.6	1229.9
22.5°	846.0	889.9	940.6	988.4	1049.5	1101.5	1147.6	1172.6	1195.5	1206.0	1210.7
25°	816.2	869.1	926.4	984.9	1053.9	1108.8	1151.0	1166.2	1172.9	1162.6	1145.8
27.5°	784.3	843.1	910.2	978.3	1051.2	1104.0	1134.3	1131.9	1120.6	1087.5	1061.1
30°	760.3	825.1	897.2	971.5	1044.7	1096.1	1113.7	1096.1	1070.4	1033.5	995.8
32.5°	735.3	802.3	883.4	962.0	1032.9	1078.1	1081.9	1051.6	1011.8	969.9	922.8
35°	697.3	769.9	857.4	940.6	1007.8	1036.3	1019.4	965.9	918.7	861.4	797.3
37.5°	654.4	734.5	822.4	909.2	970.2	977.6	935.7	879.3	812.8	745.4	670.0
40°	622.4	707.2	797.7	885.2	939.1	931.4	877.9	816.0	736.7	654.4	584.3
42.5°	593.6	678.4	770.6	856.6	899.8	878.4	816.0	739.9	654.8	577.2	513.1
45°	543.8	631.1	725.5	808.5	833.2	794.8	712.1	627.6	543.8	479.1	428.4
47.5°	495.6	581.8	675.2	748.3	757.1	705.4	615.0	528.1	456.1	403.3	367.6
50°	460.1	546.7	639.2	704.4	701.5	639.2	546.3	463.5	403.4	360.8	336.9
52.5°	428.2	510.0	599.0	658.2	643.3	575.3	486.6	413.2	363.7	330.4	308.7
55°	378.7	454.4	538.9	586.4	559.0	483.6	408.7	349.5	312.9	287.9	271.1
57.5°	329.6	400.6	472.9	502.2	471.8	402.3	339.8	296.9	269.4	250.8	239.9
60°	299.2	361.2	425.6	450.9	414.6	352.7	303.4	265.0	242.9	227.7	217.9
62.5°	268.8	324.2	385.0	398.8	365.6	313.3	269.7	237.7	219.5	206.0	196.8
65°	227.4	272.8	319.0	328.1	297.5	256.9	222.4	201.7	185.5	175.7	168.2
67.5°	186.5	222.9	255.6	263.0	236.2	208.1	183.1	165.1	154.1	145.9	139.7
70°	162.3	191.1	217.9	223.9	202.4	177.4	158.4	143.9	134.1	127.1	121.1
72.5°	136.7	160.7	182.9	187.0	169.5	150.3	134.8	123.4	114.7	110.2	104.4
75°	104.5	118.7	135.9	137.0	125.4	113.7	101.7	94.3	89.7	84.2	81.3
77.5°	73.8	84.8	94.7	96.6	89.7	81.8	75.1	69.3	65.4	62.8	60.2
80°	56.4	65.1	69.4	71.8	66.9	61.3	57.4	53.5	51.1	49.3	47.5
82.5°	40.2	45.7	49.7	51.6	48.8	45.5	41.6	39.4	37.5	36.0	35.4
85°	20.5	22.9	25.4	26.0	25.4	23.9	21.9	21.9	20.7	20.5	20.5
87.5°	7.4	8.7	8.9	9.8	9.4	9.8	10.3	10.4	10.2	9.8	9.4
90°	1.3	2.6	3.3	4.0	5.0	6.7	9.0	11.0	11.3	11.0	10.7
92.5°	5.8	8.3	9.7	12.0	15.1	22.6	33.3	42.7	43.3	36.6	29.0
95°	13.0	16.3	19.3	24.6	32.6	48.0	76.9	115.6	130.5	114.2	87.3
97.5°	20.7	24.3	28.8	35.0	44.0	63.2	103.7	167.9	222.8	233.8	203.6
100°	26.7	29.6	35.0	41.7	51.0	68.6	109.2	181.2	263.1	311.0	304.1
102.5°	32.5	35.5	40.8	47.8	57.1	73.4	109.5	176.1	264.4	339.8	369.9
105°	41.9	44.3	49.3	56.6	66.0	81.6	111.2	166.2	246.8	335.4	404.6
107.5°	51.3	53.5	58.2	65.4	74.8	90.0	115.8	161.3	227.8	306.1	379.6
110°	58.0	59.9	64.3	71.3	81.0	95.6	119.5	160.2	218.8	287.8	358.0



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	63.8	66.1	70.1	76.8	86.8	100.9	123.6	160.4	212.9	274.9	338.3
115°	73.2	75.3	79.3	86.0	94.9	109.2	129.5	161.8	206.5	259.1	314.1
117.5°	82.4	84.4	87.9	94.3	103.7	116.9	135.9	164.3	203.3	249.1	295.8
120°	88.2	90.3	93.2	99.9	109.2	122.2	140.3	165.9	201.5	243.7	286.7
122.5°	93.6	95.6	98.9	105.5	115.1	127.2	143.9	167.7	200.4	239.2	279.6
125°	100.9	102.9	106.9	113.6	122.9	134.9	149.9	170.5	198.5	232.8	269.1
127.5°	107.1	109.9	114.3	120.6	130.3	141.9	155.4	173.3	197.4	226.8	258.7
130°	110.6	113.9	118.6	125.3	134.5	146.2	158.8	175.5	196.8	222.8	252.1
132.5°	114.0	117.6	122.5	129.5	138.8	150.0	162.3	177.7	196.5	219.6	245.7
135°	118.6	122.5	127.5	135.3	144.5	155.2	166.8	180.2	196.1	215.1	236.8
137.5°	123.4	127.3	132.7	140.3	148.9	159.5	170.3	182.5	196.0	212.0	229.7
140°	126.6	130.5	135.9	143.2	151.8	161.8	172.2	183.5	195.9	210.1	225.1
142.5°	129.8	133.5	138.8	145.9	154.0	163.7	173.8	184.3	195.9	208.3	221.4
145°	135.3	138.6	143.5	150.2	157.5	166.5	175.9	185.1	195.1	205.9	216.1
147.5°	140.4	143.6	148.3	153.8	160.3	168.8	177.0	185.4	194.0	203.3	212.1
150°	144.2	146.8	151.2	156.2	162.2	169.8	177.5	185.1	193.1	201.1	209.2
152.5°	147.4	150.1	153.8	158.6	164.0	170.9	177.8	184.6	191.8	199.3	206.2
155°	152.5	154.5	158.2	161.8	166.8	172.5	178.1	183.8	189.5	195.9	202.2
157.5°	156.9	158.5	161.7	164.7	168.8	173.6	178.1	182.3	187.1	192.6	197.5
160°	159.9	161.2	163.8	166.5	170.2	174.2	178.1	181.5	185.5	190.1	194.4
162.5°	162.2	163.6	165.7	168.1	171.0	174.5	177.9	180.7	184.2	188.0	191.5
165°	165.5	166.2	168.1	169.8	171.8	174.8	177.2	179.2	181.5	184.5	187.2
167.5°	168.2	168.8	170.1	171.4	172.6	174.7	176.7	177.7	179.2	181.1	182.9
170°	169.8	170.2	171.2	171.8	172.9	174.5	176.2	176.8	177.9	179.2	180.9
172.5°	171.2	171.0	172.0	172.4	173.1	174.3	175.4	175.8	176.3	177.3	178.4
175°	172.5	172.2	172.9	172.9	173.1	173.8	174.5	174.2	174.5	174.8	175.9
177.5°	172.9	172.7	173.1	173.1	173.1	173.4	174.0	173.4	173.1	173.4	174.0
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331287-830
 CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	950.0	953.9	953.9	954.5	958.9	958.5	958.2
5°	1011.0	1016.9	1017.7	1024.0	1028.2	1026.8	1022.9
7.5°	1068.5	1079.6	1088.1	1092.8	1098.3	1101.7	1100.2
10°	1114.1	1130.3	1140.1	1146.8	1154.9	1160.9	1158.8
12.5°	1155.5	1174.8	1188.3	1199.8	1200.8	1208.5	1203.2
15°	1220.0	1240.5	1242.6	1251.0	1257.7	1257.0	1257.4
17.5°	1241.3	1247.9	1249.2	1249.4	1249.5	1247.1	1241.7
20°	1233.8	1231.3	1225.3	1220.8	1212.7	1211.5	1204.6
22.5°	1197.7	1189.9	1174.9	1165.0	1152.4	1149.1	1147.1
25°	1126.7	1109.5	1085.5	1062.7	1056.3	1044.1	1047.5
27.5°	1029.4	1002.5	976.6	958.0	941.2	922.7	928.0
30°	960.9	930.7	894.1	865.9	848.0	830.4	827.2
32.5°	879.3	834.9	794.1	769.3	741.8	730.7	718.5
35°	738.5	695.2	654.7	619.9	599.8	584.3	570.2
37.5°	611.8	562.0	529.3	501.1	486.6	477.8	479.9
40°	533.3	489.7	465.7	444.2	430.8	424.5	425.9
42.5°	469.7	437.0	417.3	402.6	393.1	389.6	388.7
45°	397.4	379.1	362.9	354.5	349.9	346.0	343.6
47.5°	348.2	333.2	324.0	319.1	315.0	311.1	311.0
50°	318.6	308.7	302.4	297.1	293.9	291.1	293.6
52.5°	296.1	287.0	280.7	276.0	274.8	272.2	272.2
55°	262.6	255.5	251.0	246.8	244.7	243.3	241.5
57.5°	232.1	225.5	221.3	218.6	214.6	213.2	212.6
60°	210.5	205.2	201.0	197.5	195.7	192.9	192.9
62.5°	190.5	185.2	181.3	178.6	175.7	174.6	174.8
65°	161.6	157.3	153.4	150.6	150.0	147.9	148.5
67.5°	135.0	132.1	128.1	126.5	125.2	124.0	123.2
70°	117.3	114.4	112.3	110.2	109.1	109.1	109.1
72.5°	102.3	98.9	97.6	95.0	95.6	94.4	93.3
75°	79.2	77.1	76.1	74.9	73.2	73.2	73.2
77.5°	58.2	57.7	56.4	55.2	54.9	54.5	54.7
80°	45.1	44.7	44.0	44.0	43.3	43.0	42.2
82.5°	34.6	33.7	33.3	33.0	32.9	32.8	32.7
85°	19.7	19.0	19.0	19.3	18.7	18.7	19.0
87.5°	9.6	9.7	9.5	9.5	9.8	9.5	9.5
90°	10.0	10.7	11.0	11.0	11.0	11.0	11.0
92.5°	24.9	22.1	20.1	19.8	18.8	18.9	18.5
95°	66.9	53.0	45.6	41.3	38.6	37.6	38.0
97.5°	166.5	130.5	106.5	90.6	82.4	77.6	74.7
100°	262.8	217.2	176.8	149.2	134.9	125.3	119.2
102.5°	360.5	327.2	284.5	254.4	230.0	217.9	209.8
105°	442.2	446.6	435.6	414.9	394.3	379.9	375.3
107.5°	436.3	470.9	487.0	489.7	488.5	485.6	479.5
110°	417.6	460.2	487.6	501.9	508.2	511.2	510.9



TEST NUMBER: P331287-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	395.5	441.0	472.4	492.3	502.8	508.5	510.3
115°	365.3	409.0	443.3	466.9	482.2	490.9	493.9
117.5°	340.8	380.4	412.6	436.7	452.9	461.9	464.5
120°	328.0	363.4	393.6	417.0	432.6	442.2	445.6
122.5°	317.4	350.8	378.1	399.1	414.5	423.1	425.8
125°	303.4	332.7	357.7	377.0	389.6	397.9	400.7
127.5°	289.8	317.4	340.4	357.3	369.2	376.4	378.5
130°	280.8	307.1	329.0	345.3	356.7	363.4	366.0
132.5°	272.2	296.4	317.1	333.1	344.4	350.5	353.0
135°	258.7	280.8	299.4	313.7	324.7	330.7	332.1
137.5°	248.1	265.5	281.7	294.8	304.3	309.5	311.5
140°	241.1	256.5	271.1	281.7	290.4	295.4	297.4
142.5°	235.0	248.2	260.4	270.5	278.4	282.9	283.2
145°	227.2	237.4	247.1	255.1	260.8	264.1	265.0
147.5°	220.7	228.8	235.8	242.4	246.9	249.2	249.9
150°	216.5	223.5	229.4	234.4	238.5	240.4	240.8
152.5°	213.0	219.0	224.1	228.1	231.5	233.0	233.1
155°	207.5	212.4	216.1	219.8	222.2	223.5	222.8
157.5°	201.9	206.0	209.0	211.5	213.5	214.1	214.1
160°	198.1	201.8	204.2	206.5	208.1	208.5	208.5
162.5°	194.7	197.8	199.6	202.0	203.1	203.4	203.1
165°	189.5	191.8	193.1	194.4	195.9	195.9	195.5
167.5°	184.7	186.3	187.6	188.1	188.9	188.8	188.4
170°	181.8	183.1	183.8	184.2	185.1	184.8	184.2
172.5°	179.2	180.2	180.6	181.0	181.4	181.1	180.7
175°	176.2	176.5	176.8	176.8	177.2	176.8	176.2
177.5°	174.0	174.3	174.3	174.3	174.3	174.0	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1

(END OF REPORT)