

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331269-930

Luminaire Tested: **SA2XXDIP-C290D925U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331269-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4011.3 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331269-930  
CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25	20				
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17				
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15				
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13				
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15	11				
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10				
8	51	39	32	27	46	36	29	25	28	24	20	22	19	16	15	13	12	9				
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7781	7781	7781	7781
5°	8723	7831	6940	7831
10°	9996	7768	6005	7768
15°	11057	7626	5307	7626
20°	10890	7472	4837	7472
25°	9818	7269	4541	7269
30°	8114	6943	4323	6943
35°	5913	6603	4169	6603
40°	4723	6203	4083	6203
45°	4128	5740	3966	5740
50°	3881	5290	3888	5290
55°	3575	4833	3783	4833
60°	3278	4346	3626	4346
65°	2988	3912	3465	3912
70°	2710	3489	3238	3489
75°	2408	3013	2863	3013
80°	2073	2492	2306	2492
85°	1853	1853	1371	1853



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.9	1.1
10°-20°	133.4	3.3
20°-30°	193.6	4.8
30°-40°	204.3	5.1
40°-50°	180.9	4.5
50°-60°	144.4	3.6
60°-70°	98.1	2.4
70°-80°	50.3	1.3
80°-90°	15.9	0.4
90°-100°	169.2	4.2
100°-110°	574.1	14.3
110°-120°	609.9	15.2
120°-130°	502.1	12.5
130°-140°	403.2	10.1
140°-150°	304.7	7.6
150°-160°	214.1	5.3
160°-170°	126.0	3.1
170°-180°	41.0	1.0
0°-30°	373.0	9.3
0°-40°	577.3	14.4
0°-60°	902.6	22.5
0°-90°	1067.0	26.6
90°-120°	1353.2	33.7
90°-150°	2563.1	63.9
90°-180°	2944.0	73.4
0°-180°	4011.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	482	482	482	482	482	
5°	538	483	428	483	538	54
15°	662	456	318	456	662	183
25°	551	408	255	408	551	249
35°	300	335	212	335	300	195
45°	181	251	174	251	181	142
55°	127	172	134	172	127	114
65°	78	102	91	102	78	78
75°	39	48	46	48	39	41
85°	10	10	7	10	10	12
90°	27	1	27	1	27	15
95°	93	28	93	28	93	121
105°	917	99	917	99	917	887
115°	1207	175	1207	175	1207	1182
125°	979	244	979	244	979	885
135°	811	286	811	286	811	630
145°	648	327	648	327	648	411
155°	544	372	544	372	544	254
165°	478	405	478	405	478	137
175°	430	422	430	422	430	42
180°	423	423	423	423	423	



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	504.1	504.3	504.6	502.2	501.9	501.9	499.9	498.1	495.9	493.2	493.5
5°	538.2	540.2	541.0	538.7	535.4	535.1	531.9	526.8	521.9	518.0	515.3
7.5°	578.9	579.7	577.9	574.9	572.5	568.0	562.1	556.4	548.4	541.0	535.6
10°	609.7	610.8	607.6	603.4	599.9	594.7	586.2	577.5	567.0	556.8	548.6
12.5°	633.1	635.9	631.8	631.3	625.3	618.1	608.0	603.6	588.7	574.5	565.7
15°	661.5	661.4	661.8	658.2	653.8	652.6	642.0	630.2	609.4	601.0	586.5
17.5°	653.3	656.2	657.5	657.4	657.3	656.6	653.1	645.8	635.3	621.7	605.1
20°	633.8	637.5	638.1	642.3	644.7	647.8	649.1	647.1	640.7	629.3	614.9
22.5°	603.6	604.6	606.3	612.9	618.2	626.1	630.1	637.1	634.5	629.0	616.9
25°	551.1	549.3	555.8	559.1	571.2	583.8	592.9	602.8	611.7	617.1	613.6
27.5°	488.3	485.5	495.2	504.1	513.8	527.5	541.6	558.3	572.2	589.6	595.6
30°	435.2	436.9	446.1	455.6	470.4	489.7	505.6	523.9	543.8	563.2	576.7
32.5°	378.1	384.4	390.3	404.8	417.8	439.3	462.7	485.6	510.3	532.4	553.3
35°	300.0	307.4	315.6	326.1	344.5	365.7	388.6	419.5	453.2	483.4	508.2
37.5°	252.6	251.4	256.0	263.7	278.5	295.7	322.0	352.5	392.2	427.6	462.7
40°	224.1	223.4	226.7	233.7	245.0	257.6	280.6	307.4	344.3	387.7	429.3
42.5°	204.6	205.0	206.8	211.8	219.6	229.9	247.1	269.9	303.7	344.5	389.3
45°	180.8	182.1	184.1	186.5	190.9	199.5	209.1	225.4	252.1	286.2	330.2
47.5°	163.6	163.7	165.8	167.9	170.5	175.3	183.2	193.4	212.2	239.9	277.9
50°	154.5	153.2	154.7	156.3	159.1	162.4	167.6	177.2	189.8	212.2	243.9
52.5°	143.2	143.2	144.6	145.2	147.7	151.0	155.7	162.4	173.8	191.4	217.4
55°	127.0	128.0	128.7	129.8	132.1	134.4	138.2	142.6	151.5	164.6	183.9
57.5°	111.9	112.2	112.9	115.0	116.4	118.6	122.1	126.2	132.0	141.7	156.2
60°	101.5	101.5	103.0	103.9	105.7	107.9	110.7	114.6	119.8	127.8	139.5
62.5°	92.0	91.9	92.5	94.0	95.4	97.4	100.2	103.5	108.4	115.5	125.1
65°	78.2	77.8	78.9	79.2	80.7	82.8	85.0	88.5	92.5	97.6	106.2
67.5°	64.8	65.3	65.9	66.5	67.3	69.5	71.0	73.5	76.8	81.1	86.8
70°	57.4	57.4	57.4	58.0	59.1	60.2	61.6	63.7	66.9	70.5	75.7
72.5°	49.1	49.7	50.3	50.0	51.4	52.0	53.8	55.0	58.0	60.3	64.9
75°	38.6	38.6	38.6	39.5	40.0	40.5	41.7	42.8	44.3	47.2	49.7
77.5°	28.8	28.7	28.9	29.1	29.7	30.3	30.7	31.6	33.0	34.4	36.4
80°	22.3	22.6	22.7	23.2	23.2	23.5	23.7	25.0	25.9	26.8	28.1
82.5°	17.2	17.3	17.3	17.4	17.5	17.8	18.3	18.7	19.0	19.7	20.7
85°	10.0	9.8	9.8	10.2	10.0	10.0	10.4	10.8	10.8	10.9	11.5
87.5°	9.2	9.2	9.4	9.2	9.2	9.2	8.9	9.0	9.4	9.7	9.7
90°	26.8	26.8	26.8	26.8	26.8	26.0	24.4	26.0	26.8	27.6	26.8
92.5°	45.1	46.4	45.7	48.3	49.0	54.1	60.9	70.9	89.4	105.7	104.3
95°	92.8	92.0	94.4	100.9	111.5	129.4	163.5	213.2	279.1	318.9	282.3
97.5°	182.6	189.4	201.3	221.4	260.2	318.9	407.0	497.5	571.2	544.5	410.1
100°	291.3	306.0	329.5	364.5	432.1	530.5	642.0	742.9	760.0	642.8	442.6
102.5°	512.7	532.5	561.9	621.7	695.0	799.4	880.9	903.7	830.3	646.0	430.3
105°	917.0	928.4	963.4	1013.8	1064.3	1091.2	1080.6	988.6	819.4	602.9	406.0
107.5°	1171.4	1186.5	1193.5	1196.3	1189.9	1150.6	1065.9	927.5	748.0	556.8	394.0
110°	1248.2	1249.0	1241.7	1226.2	1191.2	1124.5	1020.3	874.7	703.0	534.6	391.4



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1246.9	1242.5	1228.7	1202.8	1154.1	1077.7	966.4	826.6	671.8	520.2	392.0
115°	1206.7	1199.4	1178.2	1140.8	1083.0	999.2	892.6	767.3	633.1	504.5	395.4
117.5°	1134.9	1128.8	1106.4	1066.9	1008.0	929.4	832.7	722.7	608.6	496.8	401.3
120°	1088.8	1080.6	1057.0	1018.7	961.8	887.7	801.5	700.6	595.7	492.3	405.2
122.5°	1040.6	1033.7	1012.7	975.1	924.1	857.1	775.4	683.0	584.6	489.7	409.8
125°	978.8	972.3	952.0	921.1	873.9	812.9	741.3	657.5	568.8	484.9	416.6
127.5°	924.9	919.7	902.0	873.1	831.9	775.6	708.1	632.3	554.2	482.2	423.6
130°	894.2	887.7	871.5	843.8	804.0	750.2	685.9	616.0	544.4	480.9	428.8
132.5°	862.3	856.5	841.6	813.8	774.6	724.1	665.1	600.3	536.5	480.2	434.0
135°	811.2	808.0	793.4	766.5	731.5	685.9	632.3	578.5	525.6	479.2	440.2
137.5°	761.2	756.3	743.4	720.3	688.4	648.7	606.0	561.1	518.0	479.1	445.7
140°	726.6	721.8	709.6	688.4	662.3	626.6	589.1	550.1	513.5	478.4	448.3
142.5°	692.1	691.1	680.3	661.0	636.3	606.3	574.1	541.0	508.9	478.4	450.3
145°	647.7	645.2	637.2	623.3	603.7	580.2	555.0	528.1	502.9	476.8	452.4
147.5°	610.4	608.9	603.4	592.4	576.3	559.0	539.3	518.1	496.7	473.9	453.1
150°	588.3	587.5	582.6	572.8	560.6	546.0	528.9	511.0	491.5	472.0	452.4
152.5°	569.4	569.2	565.7	557.2	547.6	534.9	520.4	503.9	486.9	468.7	451.1
155°	544.4	546.0	542.7	537.0	528.1	519.1	507.0	493.9	478.4	463.0	449.1
157.5°	523.0	523.0	521.5	516.8	510.5	503.5	493.3	482.3	470.5	457.1	445.4
160°	509.4	509.4	508.6	504.5	498.8	493.1	484.1	475.2	464.6	453.2	443.4
162.5°	496.4	497.0	496.2	493.4	487.7	483.3	475.6	468.1	459.4	450.0	441.5
165°	477.6	478.4	478.4	475.2	472.0	468.7	463.0	457.3	450.8	443.4	437.7
167.5°	460.4	461.4	461.5	459.7	458.3	455.3	451.4	447.0	442.3	437.7	434.0
170°	450.0	451.6	452.4	450.0	449.1	447.5	444.3	441.8	437.7	434.5	432.1
172.5°	441.5	442.5	443.3	442.1	441.3	440.3	437.7	435.9	433.3	430.6	429.5
175°	430.5	432.1	432.9	432.1	432.1	431.3	430.5	429.7	427.2	426.4	425.6
177.5°	423.8	425.1	425.7	425.7	425.7	425.7	425.1	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	494.5	493.3	492.6	489.9	487.5	485.2	484.5	484.7	481.4	478.3	477.0
5°	513.8	510.1	506.5	501.6	495.6	489.1	485.8	483.2	476.7	469.7	465.6
7.5°	531.0	525.7	518.9	509.6	500.9	490.7	484.2	478.5	469.0	459.1	453.0
10°	541.5	534.3	525.6	514.1	503.6	491.1	482.5	473.8	462.7	450.8	443.4
12.5°	550.6	540.9	532.3	517.6	505.1	489.5	479.2	466.9	455.3	441.2	433.9
15°	572.1	554.2	537.9	521.1	505.8	484.1	472.6	456.2	440.8	423.4	415.1
17.5°	588.7	568.5	542.9	521.7	503.8	479.7	462.9	443.2	425.0	405.1	393.8
20°	598.2	575.0	547.5	522.3	500.8	473.4	455.0	434.9	413.6	391.2	379.0
22.5°	603.8	579.5	552.2	520.1	494.9	468.2	445.2	423.0	401.5	377.2	364.4
25°	605.6	583.4	554.5	518.2	487.5	457.3	429.5	408.0	381.9	359.3	340.6
27.5°	596.8	580.9	553.1	514.7	478.9	443.6	412.6	388.3	360.8	336.2	317.4
30°	586.0	576.7	549.7	511.2	472.1	434.1	400.1	372.4	345.0	320.2	300.9
32.5°	569.2	567.3	543.5	506.1	464.8	422.2	386.9	359.0	328.6	304.2	285.8
35°	536.4	545.3	530.3	494.9	451.2	405.0	366.9	335.0	303.5	280.2	263.0
37.5°	492.3	514.4	510.5	478.4	432.7	386.5	344.3	311.0	281.0	257.5	240.6
40°	461.9	490.1	494.2	465.8	419.7	372.1	327.4	294.3	265.1	243.5	226.5
42.5°	429.3	462.2	473.4	450.7	405.4	356.9	312.3	278.0	249.0	228.1	213.0
45°	374.7	418.2	438.4	425.4	381.7	332.1	286.2	251.4	225.0	205.4	193.7
47.5°	323.6	371.1	398.3	393.7	355.3	306.1	260.7	227.3	201.7	186.1	175.6
50°	287.5	336.3	369.1	370.6	336.3	287.6	242.1	210.6	187.0	172.4	163.9
52.5°	256.0	302.7	338.4	346.3	315.1	268.4	225.3	194.0	173.3	159.8	152.2
55°	215.0	254.5	294.1	308.6	283.6	239.1	199.3	171.7	152.2	143.0	136.3
57.5°	178.8	211.7	248.3	264.2	248.8	210.8	173.4	149.4	133.7	125.6	120.4
60°	159.6	185.6	218.2	237.3	223.9	190.0	157.4	134.6	121.6	114.5	109.7
62.5°	141.9	164.9	192.4	209.9	202.6	170.6	141.5	121.3	110.1	103.4	99.9
65°	117.1	135.2	156.5	172.6	167.8	143.6	119.6	102.4	93.5	88.1	85.4
67.5°	96.4	109.5	124.3	138.4	134.5	117.3	98.2	84.7	78.1	73.5	71.7
70°	83.3	93.4	106.5	117.8	114.6	100.6	85.4	73.9	68.2	64.2	62.6
72.5°	70.9	79.1	89.2	98.4	96.3	84.5	71.9	63.3	58.8	55.2	53.9
75°	53.6	59.8	66.0	72.1	71.5	62.5	55.0	48.3	44.8	42.1	41.5
77.5°	39.5	43.0	47.2	50.8	49.8	44.6	38.8	35.0	32.4	30.6	30.2
80°	30.2	32.2	35.2	37.7	36.5	34.2	29.6	26.8	25.0	23.2	22.4
82.5°	21.9	23.9	25.7	27.1	26.1	24.1	21.2	19.3	18.2	17.0	16.6
85°	11.5	12.6	13.4	13.7	13.4	12.1	10.8	10.0	9.0	8.5	8.3
87.5°	8.8	7.7	6.8	6.7	6.0	5.6	4.3	3.4	3.8	4.2	4.3
90°	21.9	16.3	12.2	9.8	8.2	6.5	3.3	0.8	3.3	6.5	8.2
92.5°	81.2	55.4	36.9	29.3	23.7	20.2	14.3	9.9	14.3	20.2	23.7
95°	187.9	117.2	79.7	60.3	47.2	39.9	31.7	28.5	31.7	39.9	47.2
97.5°	253.2	154.6	107.5	85.4	70.4	59.4	50.8	46.4	50.8	59.4	70.4
100°	266.9	167.6	124.5	101.7	85.4	72.4	65.1	62.6	65.1	72.4	85.4
102.5°	267.6	179.4	139.5	116.7	99.8	86.7	79.4	77.6	79.4	86.7	99.8
105°	271.7	199.3	161.1	138.4	120.4	108.2	102.6	99.3	102.6	108.2	120.4
107.5°	283.0	219.9	182.8	159.8	142.1	130.9	125.3	122.7	125.3	130.9	142.1
110°	292.1	233.5	197.7	174.1	157.0	146.4	141.6	138.4	141.6	146.4	157.0





TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	301.9	246.5	212.1	187.8	171.4	161.4	155.9	152.6	155.9	161.4	171.4
115°	316.5	266.9	231.9	209.9	193.6	183.9	179.0	175.0	179.0	183.9	193.6
117.5°	332.2	285.6	253.2	230.4	214.8	206.2	201.3	198.0	201.3	206.2	214.8
120°	342.6	298.6	266.9	244.1	227.8	220.5	215.6	212.4	215.6	220.5	227.8
122.5°	351.6	311.0	281.2	257.8	241.5	233.5	228.6	226.1	228.6	233.5	241.5
125°	366.2	329.5	300.3	277.4	261.2	251.4	246.5	244.1	246.5	251.4	261.2
127.5°	379.7	346.8	318.3	294.9	279.2	268.5	261.7	258.4	261.7	268.5	279.2
130°	388.2	357.2	328.7	306.0	289.7	278.3	270.1	266.9	270.1	278.3	289.7
132.5°	396.6	366.3	339.2	316.3	299.5	287.4	278.6	274.7	278.6	287.4	299.5
135°	407.6	379.2	353.1	330.4	311.6	299.5	289.7	286.4	289.7	299.5	311.6
137.5°	416.1	389.6	363.9	342.8	324.2	311.1	301.4	297.5	301.4	311.1	324.2
140°	420.7	395.4	371.0	349.9	332.0	318.9	309.2	306.0	309.2	318.9	332.0
142.5°	424.6	400.0	376.3	356.4	339.2	326.1	317.0	314.4	317.0	326.1	339.2
145°	429.7	406.8	384.9	367.0	350.7	338.5	330.4	327.1	330.4	338.5	350.7
147.5°	432.4	412.4	391.8	375.8	362.2	351.0	343.2	340.8	343.2	351.0	362.2
150°	433.7	415.0	396.2	381.6	369.4	358.8	352.3	349.9	352.3	358.8	369.4
152.5°	434.3	417.6	400.8	387.5	375.9	366.6	360.1	359.0	360.1	366.6	375.9
155°	435.3	421.5	407.6	395.4	386.5	377.6	372.7	371.9	372.7	377.6	386.5
157.5°	435.3	424.3	412.5	402.3	395.1	387.3	383.4	382.6	383.4	387.3	395.1
160°	435.3	425.6	415.8	406.8	400.3	393.8	390.6	389.8	390.6	393.8	400.3
162.5°	434.6	426.2	417.8	410.7	404.9	399.7	396.4	396.9	396.4	399.7	404.9
165°	432.9	427.2	419.9	415.0	410.9	406.0	404.4	405.2	404.4	406.0	410.9
167.5°	431.8	427.1	421.7	418.6	415.6	412.5	411.1	412.1	411.1	412.5	415.6
170°	430.5	426.4	422.3	419.9	418.2	415.8	415.0	416.6	415.0	415.8	418.2
172.5°	428.5	425.7	423.0	421.2	420.2	417.8	418.2	419.2	418.2	417.8	420.2
175°	426.4	424.8	423.1	422.3	422.3	420.7	421.5	422.3	421.5	420.7	422.3
177.5°	425.1	423.8	423.1	423.1	423.1	421.8	422.5	423.8	422.5	421.8	423.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	475.6	474.7	471.6	469.9	467.2	464.7	463.1	463.8	464.4	464.1	463.7
5°	461.9	458.4	453.0	448.4	445.1	439.0	436.3	435.0	433.9	432.7	431.4
7.5°	445.6	440.1	432.4	425.8	419.6	412.0	407.6	405.1	402.4	399.5	396.9
10°	434.1	426.3	418.2	409.0	401.5	394.7	388.6	384.5	380.7	377.2	374.7
12.5°	422.0	413.0	402.9	390.3	382.1	372.3	371.4	364.2	358.4	356.2	353.2
15°	402.7	390.0	377.2	362.2	355.8	346.9	341.4	335.7	330.8	327.3	326.4
17.5°	380.7	364.4	351.6	340.9	330.3	321.1	316.0	311.6	307.4	302.8	302.1
20°	363.9	349.8	336.0	326.5	315.6	306.3	300.0	295.6	292.0	289.3	286.9
22.5°	348.1	332.6	319.9	309.7	298.9	291.4	286.4	282.1	279.2	276.1	273.9
25°	322.6	310.6	296.7	285.0	276.1	271.3	267.3	263.6	261.7	259.7	257.1
27.5°	300.4	287.0	274.0	265.0	257.1	252.9	250.0	247.4	245.7	244.5	243.0
30°	284.7	271.2	261.0	252.1	245.6	241.3	239.5	238.0	235.9	235.2	234.5
32.5°	269.5	257.4	248.7	240.9	234.8	232.0	230.3	228.9	227.4	226.7	225.1
35°	248.2	238.0	229.5	225.2	220.2	217.8	216.5	214.7	213.2	212.5	212.2
37.5°	228.0	219.2	213.6	208.1	206.0	204.6	202.8	201.5	201.1	201.0	200.7
40°	215.0	207.8	202.8	198.4	197.5	195.2	193.7	192.7	192.7	192.8	192.7
42.5°	203.2	196.7	192.2	188.4	187.4	186.1	184.5	184.5	184.7	185.4	184.7
45°	185.2	180.6	177.4	175.6	173.6	172.3	172.0	172.6	172.8	173.0	173.6
47.5°	168.7	165.6	162.7	160.7	159.8	159.6	159.4	160.4	161.3	161.6	162.4
50°	158.9	155.4	153.0	151.6	150.9	150.6	150.9	152.1	152.8	153.7	154.3
52.5°	148.0	145.4	143.8	142.8	142.5	142.8	142.8	144.1	145.2	145.6	145.9
55°	132.8	130.9	130.6	128.9	129.6	129.5	130.4	131.1	132.2	133.4	133.5
57.5°	117.6	116.2	115.2	115.4	115.6	116.4	117.2	118.5	119.6	120.8	120.9
60°	107.6	106.9	106.3	106.3	106.6	107.8	108.7	110.0	110.7	111.5	112.0
62.5°	98.4	97.7	97.1	97.4	98.4	99.1	100.1	100.9	101.6	102.3	102.6
65°	83.9	83.6	84.1	84.5	84.6	85.5	86.8	87.4	88.1	88.5	89.8
67.5°	70.5	70.6	70.5	71.0	72.2	72.3	73.5	74.8	75.0	75.7	76.6
70°	61.5	61.9	62.2	62.6	63.5	63.9	64.8	65.4	66.1	66.7	67.3
72.5°	53.2	53.2	53.6	53.6	54.4	55.1	55.9	56.5	57.2	58.0	58.5
75°	40.9	40.9	41.3	41.5	42.4	43.4	43.1	43.5	44.3	45.0	45.4
77.5°	29.9	29.5	29.9	30.1	30.4	31.1	31.3	31.8	32.7	32.4	32.9
80°	22.7	22.3	22.7	23.0	23.0	23.9	23.9	24.3	24.8	24.3	24.8
82.5°	16.2	16.0	16.4	16.5	16.7	16.8	17.0	17.1	17.7	17.4	17.7
85°	8.2	8.0	8.2	8.0	8.2	8.3	8.3	8.2	8.2	8.5	8.0
87.5°	4.5	4.8	5.5	6.6	7.4	7.4	7.2	7.0	6.7	6.7	6.8
90°	9.8	12.2	16.3	21.9	26.8	27.6	26.8	26.0	24.4	26.0	26.8
92.5°	29.3	36.9	55.4	81.2	104.3	105.7	89.4	70.9	60.9	54.1	49.0
95°	60.3	79.7	117.2	187.9	282.3	318.9	279.1	213.2	163.5	129.4	111.5
97.5°	85.4	107.5	154.6	253.2	410.1	544.5	571.2	497.5	407.0	318.9	260.2
100°	101.7	124.5	167.6	266.9	442.6	642.8	760.0	742.9	642.0	530.5	432.1
102.5°	116.7	139.5	179.4	267.6	430.3	646.0	830.3	903.7	880.9	799.4	695.0
105°	138.4	161.1	199.3	271.7	406.0	602.9	819.4	988.6	1080.6	1091.2	1064.3
107.5°	159.8	182.8	219.9	283.0	394.0	556.8	748.0	927.5	1065.9	1150.6	1189.9
110°	174.1	197.7	233.5	292.1	391.4	534.6	703.0	874.7	1020.3	1124.5	1191.2



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	187.8	212.1	246.5	301.9	392.0	520.2	671.8	826.6	966.4	1077.7	1154.1
115°	209.9	231.9	266.9	316.5	395.4	504.5	633.1	767.3	892.6	999.2	1083.0
117.5°	230.4	253.2	285.6	332.2	401.3	496.8	608.6	722.7	832.7	929.4	1008.0
120°	244.1	266.9	298.6	342.6	405.2	492.3	595.7	700.6	801.5	887.7	961.8
122.5°	257.8	281.2	311.0	351.6	409.8	489.7	584.6	683.0	775.4	857.1	924.1
125°	277.4	300.3	329.5	366.2	416.6	484.9	568.8	657.5	741.3	812.9	873.9
127.5°	294.9	318.3	346.8	379.7	423.6	482.2	554.2	632.3	708.1	775.6	831.9
130°	306.0	328.7	357.2	388.2	428.8	480.9	544.4	616.0	685.9	750.2	804.0
132.5°	316.3	339.2	366.3	396.6	434.0	480.2	536.5	600.3	665.1	724.1	774.6
135°	330.4	353.1	379.2	407.6	440.2	479.2	525.6	578.5	632.3	685.9	731.5
137.5°	342.8	363.9	389.6	416.1	445.7	479.1	518.0	561.1	606.0	648.7	688.4
140°	349.9	371.0	395.4	420.7	448.3	478.4	513.5	550.1	589.1	626.6	662.3
142.5°	356.4	376.3	400.0	424.6	450.3	478.4	508.9	541.0	574.1	606.3	636.3
145°	367.0	384.9	406.8	429.7	452.4	476.8	502.9	528.1	555.0	580.2	603.7
147.5°	375.8	391.8	412.4	432.4	453.1	473.9	496.7	518.1	539.3	559.0	576.3
150°	381.6	396.2	415.0	433.7	452.4	472.0	491.5	511.0	528.9	546.0	560.6
152.5°	387.5	400.8	417.6	434.3	451.1	468.7	486.9	503.9	520.4	534.9	547.6
155°	395.4	407.6	421.5	435.3	449.1	463.0	478.4	493.9	507.0	519.1	528.1
157.5°	402.3	412.5	424.3	435.3	445.4	457.1	470.5	482.3	493.3	503.5	510.5
160°	406.8	415.8	425.6	435.3	443.4	453.2	464.6	475.2	484.1	493.1	498.8
162.5°	410.7	417.8	426.2	434.6	441.5	450.0	459.4	468.1	475.6	483.3	487.7
165°	415.0	419.9	427.2	432.9	437.7	443.4	450.8	457.3	463.0	468.7	472.0
167.5°	418.6	421.7	427.1	431.8	434.0	437.7	442.3	447.0	451.4	455.3	458.3
170°	419.9	422.3	426.4	430.5	432.1	434.5	437.7	441.8	444.3	447.5	449.1
172.5°	421.2	423.0	425.7	428.5	429.5	430.6	433.3	435.9	437.7	440.3	441.3
175°	422.3	423.1	424.8	426.4	425.6	426.4	427.2	429.7	430.5	431.3	432.1
177.5°	423.1	423.1	423.8	425.1	423.8	423.1	423.8	425.1	425.1	425.7	425.7
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	462.2	461.9	461.9	460.6	461.9	461.9	462.2	463.7	464.1	464.4	463.8
5°	428.8	428.2	427.3	428.2	427.3	428.2	428.8	431.4	432.7	433.9	435.0
7.5°	395.7	393.5	393.1	390.9	393.1	393.5	395.7	396.9	399.5	402.4	405.1
10°	371.5	370.1	369.8	366.3	369.8	370.1	371.5	374.7	377.2	380.7	384.5
12.5°	353.2	349.6	350.3	348.3	350.3	349.6	353.2	353.2	356.2	358.4	364.2
15°	321.3	321.3	320.6	317.5	320.6	321.3	321.3	326.4	327.3	330.8	335.7
17.5°	298.5	298.1	296.4	297.3	296.4	298.1	298.5	302.1	302.8	307.4	311.6
20°	284.9	283.7	281.5	281.5	281.5	283.7	284.9	286.9	289.3	292.0	295.6
22.5°	272.0	271.9	269.5	270.3	269.5	271.9	272.0	273.9	276.1	279.2	282.1
25°	256.9	255.4	254.3	254.9	254.3	255.4	256.9	257.1	259.7	261.7	263.6
27.5°	242.6	241.7	241.7	240.2	241.7	241.7	242.6	243.0	244.5	245.7	247.4
30°	234.3	232.4	232.8	231.9	232.8	232.4	234.3	234.5	235.2	235.9	238.0
32.5°	224.8	224.1	223.8	223.0	223.8	224.1	224.8	225.1	226.7	227.4	228.9
35°	211.9	212.1	211.2	211.5	211.2	212.1	211.9	212.2	212.5	213.2	214.7
37.5°	200.6	201.1	200.7	200.8	200.7	201.1	200.6	200.7	201.0	201.1	201.5
40°	193.1	193.1	193.1	193.7	193.1	193.1	193.1	192.7	192.8	192.7	192.7
42.5°	186.1	185.7	185.5	185.4	185.5	185.7	186.1	184.7	185.4	184.7	184.5
45°	173.9	174.5	174.6	173.7	174.6	174.5	173.9	173.6	173.0	172.8	172.6
47.5°	162.9	163.0	162.9	163.7	162.9	163.0	162.9	162.4	161.6	161.3	160.4
50°	155.2	154.8	155.2	154.8	155.2	154.8	155.2	154.3	153.7	152.8	152.1
52.5°	147.1	147.2	146.9	146.8	146.9	147.2	147.1	145.9	145.6	145.2	144.1
55°	134.3	134.6	134.4	134.4	134.4	134.6	134.3	133.5	133.4	132.2	131.1
57.5°	121.1	121.4	121.6	120.8	121.6	121.4	121.1	120.9	120.8	119.6	118.5
60°	111.9	112.8	112.6	112.3	112.6	112.8	111.9	112.0	111.5	110.7	110.0
62.5°	103.4	103.8	103.7	103.6	103.7	103.8	103.4	102.6	102.3	101.6	100.9
65°	90.4	90.7	90.2	90.7	90.2	90.7	90.4	89.8	88.5	88.1	87.4
67.5°	76.3	76.5	76.9	77.1	76.9	76.5	76.3	76.6	75.7	75.0	74.8
70°	67.6	67.4	68.0	68.6	68.0	67.4	67.6	67.3	66.7	66.1	65.4
72.5°	58.4	58.8	58.6	59.0	58.6	58.8	58.4	58.5	58.0	57.2	56.5
75°	45.0	45.6	45.4	45.9	45.4	45.6	45.0	45.4	45.0	44.3	43.5
77.5°	32.5	32.6	32.5	32.9	32.5	32.6	32.5	32.9	32.4	32.7	31.8
80°	24.8	24.5	24.1	24.8	24.1	24.5	24.8	24.8	24.3	24.8	24.3
82.5°	17.3	17.4	17.1	17.1	17.1	17.4	17.3	17.7	17.4	17.7	17.1
85°	8.0	7.7	7.4	7.4	7.4	7.7	8.0	8.0	8.5	8.2	8.2
87.5°	6.8	6.7	6.7	6.5	6.7	6.7	6.8	6.8	6.7	6.7	7.0
90°	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.0	24.4	26.0
92.5°	48.3	45.7	46.4	45.1	46.4	45.7	48.3	49.0	54.1	60.9	70.9
95°	100.9	94.4	92.0	92.8	92.0	94.4	100.9	111.5	129.4	163.5	213.2
97.5°	221.4	201.3	189.4	182.6	189.4	201.3	221.4	260.2	318.9	407.0	497.5
100°	364.5	329.5	306.0	291.3	306.0	329.5	364.5	432.1	530.5	642.0	742.9
102.5°	621.7	561.9	532.5	512.7	532.5	561.9	621.7	695.0	799.4	880.9	903.7
105°	1013.8	963.4	928.4	917.0	928.4	963.4	1013.8	1064.3	1091.2	1080.6	988.6
107.5°	1196.3	1193.5	1186.5	1171.4	1186.5	1193.5	1196.3	1189.9	1150.6	1065.9	927.5
110°	1226.2	1241.7	1249.0	1248.2	1249.0	1241.7	1226.2	1191.2	1124.5	1020.3	874.7



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1202.8	1228.7	1242.5	1246.9	1242.5	1228.7	1202.8	1154.1	1077.7	966.4	826.6
115°	1140.8	1178.2	1199.4	1206.7	1199.4	1178.2	1140.8	1083.0	999.2	892.6	767.3
117.5°	1066.9	1106.4	1128.8	1134.9	1128.8	1106.4	1066.9	1008.0	929.4	832.7	722.7
120°	1018.7	1057.0	1080.6	1088.8	1080.6	1057.0	1018.7	961.8	887.7	801.5	700.6
122.5°	975.1	1012.7	1033.7	1040.6	1033.7	1012.7	975.1	924.1	857.1	775.4	683.0
125°	921.1	952.0	972.3	978.8	972.3	952.0	921.1	873.9	812.9	741.3	657.5
127.5°	873.1	902.0	919.7	924.9	919.7	902.0	873.1	831.9	775.6	708.1	632.3
130°	843.8	871.5	887.7	894.2	887.7	871.5	843.8	804.0	750.2	685.9	616.0
132.5°	813.8	841.6	856.5	862.3	856.5	841.6	813.8	774.6	724.1	665.1	600.3
135°	766.5	793.4	808.0	811.2	808.0	793.4	766.5	731.5	685.9	632.3	578.5
137.5°	720.3	743.4	756.3	761.2	756.3	743.4	720.3	688.4	648.7	606.0	561.1
140°	688.4	709.6	721.8	726.6	721.8	709.6	688.4	662.3	626.6	589.1	550.1
142.5°	661.0	680.3	691.1	692.1	691.1	680.3	661.0	636.3	606.3	574.1	541.0
145°	623.3	637.2	645.2	647.7	645.2	637.2	623.3	603.7	580.2	555.0	528.1
147.5°	592.4	603.4	608.9	610.4	608.9	603.4	592.4	576.3	559.0	539.3	518.1
150°	572.8	582.6	587.5	588.3	587.5	582.6	572.8	560.6	546.0	528.9	511.0
152.5°	557.2	565.7	569.2	569.4	569.2	565.7	557.2	547.6	534.9	520.4	503.9
155°	537.0	542.7	546.0	544.4	546.0	542.7	537.0	528.1	519.1	507.0	493.9
157.5°	516.8	521.5	523.0	523.0	523.0	521.5	516.8	510.5	503.5	493.3	482.3
160°	504.5	508.6	509.4	509.4	509.4	508.6	504.5	498.8	493.1	484.1	475.2
162.5°	493.4	496.2	497.0	496.4	497.0	496.2	493.4	487.7	483.3	475.6	468.1
165°	475.2	478.4	478.4	477.6	478.4	478.4	475.2	472.0	468.7	463.0	457.3
167.5°	459.7	461.5	461.4	460.4	461.4	461.5	459.7	458.3	455.3	451.4	447.0
170°	450.0	452.4	451.6	450.0	451.6	452.4	450.0	449.1	447.5	444.3	441.8
172.5°	442.1	443.3	442.5	441.5	442.5	443.3	442.1	441.3	440.3	437.7	435.9
175°	432.1	432.9	432.1	430.5	432.1	432.9	432.1	432.1	431.3	430.5	429.7
177.5°	425.7	425.7	425.1	423.8	425.1	425.7	425.7	425.7	425.7	425.1	425.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	463.1	464.7	467.2	469.9	471.6	474.7	475.6	477.0	478.3	481.4	484.7
5°	436.3	439.0	445.1	448.4	453.0	458.4	461.9	465.6	469.7	476.7	483.2
7.5°	407.6	412.0	419.6	425.8	432.4	440.1	445.6	453.0	459.1	469.0	478.5
10°	388.6	394.7	401.5	409.0	418.2	426.3	434.1	443.4	450.8	462.7	473.8
12.5°	371.4	372.3	382.1	390.3	402.9	413.0	422.0	433.9	441.2	455.3	466.9
15°	341.4	346.9	355.8	362.2	377.2	390.0	402.7	415.1	423.4	440.8	456.2
17.5°	316.0	321.1	330.3	340.9	351.6	364.4	380.7	393.8	405.1	425.0	443.2
20°	300.0	306.3	315.6	326.5	336.0	349.8	363.9	379.0	391.2	413.6	434.9
22.5°	286.4	291.4	298.9	309.7	319.9	332.6	348.1	364.4	377.2	401.5	423.0
25°	267.3	271.3	276.1	285.0	296.7	310.6	322.6	340.6	359.3	381.9	408.0
27.5°	250.0	252.9	257.1	265.0	274.0	287.0	300.4	317.4	336.2	360.8	388.3
30°	239.5	241.3	245.6	252.1	261.0	271.2	284.7	300.9	320.2	345.0	372.4
32.5°	230.3	232.0	234.8	240.9	248.7	257.4	269.5	285.8	304.2	328.6	359.0
35°	216.5	217.8	220.2	225.2	229.5	238.0	248.2	263.0	280.2	303.5	335.0
37.5°	202.8	204.6	206.0	208.1	213.6	219.2	228.0	240.6	257.5	281.0	311.0
40°	193.7	195.2	197.5	198.4	202.8	207.8	215.0	226.5	243.5	265.1	294.3
42.5°	184.5	186.1	187.4	188.4	192.2	196.7	203.2	213.0	228.1	249.0	278.0
45°	172.0	172.3	173.6	175.6	177.4	180.6	185.2	193.7	205.4	225.0	251.4
47.5°	159.4	159.6	159.8	160.7	162.7	165.6	168.7	175.6	186.1	201.7	227.3
50°	150.9	150.6	150.9	151.6	153.0	155.4	158.9	163.9	172.4	187.0	210.6
52.5°	142.8	142.8	142.5	142.8	143.8	145.4	148.0	152.2	159.8	173.3	194.0
55°	130.4	129.5	129.6	128.9	130.6	130.9	132.8	136.3	143.0	152.2	171.7
57.5°	117.2	116.4	115.6	115.4	115.2	116.2	117.6	120.4	125.6	133.7	149.4
60°	108.7	107.8	106.6	106.3	106.3	106.9	107.6	109.7	114.5	121.6	134.6
62.5°	100.1	99.1	98.4	97.4	97.1	97.7	98.4	99.9	103.4	110.1	121.3
65°	86.8	85.5	84.6	84.5	84.1	83.6	83.9	85.4	88.1	93.5	102.4
67.5°	73.5	72.3	72.2	71.0	70.5	70.6	70.5	71.7	73.5	78.1	84.7
70°	64.8	63.9	63.5	62.6	62.2	61.9	61.5	62.6	64.2	68.2	73.9
72.5°	55.9	55.1	54.4	53.6	53.6	53.2	53.2	53.9	55.2	58.8	63.3
75°	43.1	43.4	42.4	41.5	41.3	40.9	40.9	41.5	42.1	44.8	48.3
77.5°	31.3	31.1	30.4	30.1	29.9	29.5	29.9	30.2	30.6	32.4	35.0
80°	23.9	23.9	23.0	23.0	22.7	22.3	22.7	22.4	23.2	25.0	26.8
82.5°	17.0	16.8	16.7	16.5	16.4	16.0	16.2	16.6	17.0	18.2	19.3
85°	8.3	8.3	8.2	8.0	8.2	8.0	8.2	8.3	8.5	9.0	10.0
87.5°	7.2	7.4	7.4	6.6	5.5	4.8	4.5	4.3	4.2	3.8	3.4
90°	26.8	27.6	26.8	21.9	16.3	12.2	9.8	8.2	6.5	3.3	0.8
92.5°	89.4	105.7	104.3	81.2	55.4	36.9	29.3	23.7	20.2	14.3	9.9
95°	279.1	318.9	282.3	187.9	117.2	79.7	60.3	47.2	39.9	31.7	28.5
97.5°	571.2	544.5	410.1	253.2	154.6	107.5	85.4	70.4	59.4	50.8	46.4
100°	760.0	642.8	442.6	266.9	167.6	124.5	101.7	85.4	72.4	65.1	62.6
102.5°	830.3	646.0	430.3	267.6	179.4	139.5	116.7	99.8	86.7	79.4	77.6
105°	819.4	602.9	406.0	271.7	199.3	161.1	138.4	120.4	108.2	102.6	99.3
107.5°	748.0	556.8	394.0	283.0	219.9	182.8	159.8	142.1	130.9	125.3	122.7
110°	703.0	534.6	391.4	292.1	233.5	197.7	174.1	157.0	146.4	141.6	138.4



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.8	520.2	392.0	301.9	246.5	212.1	187.8	171.4	161.4	155.9	152.6
115°	633.1	504.5	395.4	316.5	266.9	231.9	209.9	193.6	183.9	179.0	175.0
117.5°	608.6	496.8	401.3	332.2	285.6	253.2	230.4	214.8	206.2	201.3	198.0
120°	595.7	492.3	405.2	342.6	298.6	266.9	244.1	227.8	220.5	215.6	212.4
122.5°	584.6	489.7	409.8	351.6	311.0	281.2	257.8	241.5	233.5	228.6	226.1
125°	568.8	484.9	416.6	366.2	329.5	300.3	277.4	261.2	251.4	246.5	244.1
127.5°	554.2	482.2	423.6	379.7	346.8	318.3	294.9	279.2	268.5	261.7	258.4
130°	544.4	480.9	428.8	388.2	357.2	328.7	306.0	289.7	278.3	270.1	266.9
132.5°	536.5	480.2	434.0	396.6	366.3	339.2	316.3	299.5	287.4	278.6	274.7
135°	525.6	479.2	440.2	407.6	379.2	353.1	330.4	311.6	299.5	289.7	286.4
137.5°	518.0	479.1	445.7	416.1	389.6	363.9	342.8	324.2	311.1	301.4	297.5
140°	513.5	478.4	448.3	420.7	395.4	371.0	349.9	332.0	318.9	309.2	306.0
142.5°	508.9	478.4	450.3	424.6	400.0	376.3	356.4	339.2	326.1	317.0	314.4
145°	502.9	476.8	452.4	429.7	406.8	384.9	367.0	350.7	338.5	330.4	327.1
147.5°	496.7	473.9	453.1	432.4	412.4	391.8	375.8	362.2	351.0	343.2	340.8
150°	491.5	472.0	452.4	433.7	415.0	396.2	381.6	369.4	358.8	352.3	349.9
152.5°	486.9	468.7	451.1	434.3	417.6	400.8	387.5	375.9	366.6	360.1	359.0
155°	478.4	463.0	449.1	435.3	421.5	407.6	395.4	386.5	377.6	372.7	371.9
157.5°	470.5	457.1	445.4	435.3	424.3	412.5	402.3	395.1	387.3	383.4	382.6
160°	464.6	453.2	443.4	435.3	425.6	415.8	406.8	400.3	393.8	390.6	389.8
162.5°	459.4	450.0	441.5	434.6	426.2	417.8	410.7	404.9	399.7	396.4	396.9
165°	450.8	443.4	437.7	432.9	427.2	419.9	415.0	410.9	406.0	404.4	405.2
167.5°	442.3	437.7	434.0	431.8	427.1	421.7	418.6	415.6	412.5	411.1	412.1
170°	437.7	434.5	432.1	430.5	426.4	422.3	419.9	418.2	415.8	415.0	416.6
172.5°	433.3	430.6	429.5	428.5	425.7	423.0	421.2	420.2	417.8	418.2	419.2
175°	427.2	426.4	425.6	426.4	424.8	423.1	422.3	422.3	420.7	421.5	422.3
177.5°	423.8	423.1	423.8	425.1	423.8	423.1	423.1	423.1	421.8	422.5	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	484.5	485.2	487.5	489.9	492.6	493.3	494.5	493.5	493.2	495.9	498.1
5°	485.8	489.1	495.6	501.6	506.5	510.1	513.8	515.3	518.0	521.9	526.8
7.5°	484.2	490.7	500.9	509.6	518.9	525.7	531.0	535.6	541.0	548.4	556.4
10°	482.5	491.1	503.6	514.1	525.6	534.3	541.5	548.6	556.8	567.0	577.5
12.5°	479.2	489.5	505.1	517.6	532.3	540.9	550.6	565.7	574.5	588.7	603.6
15°	472.6	484.1	505.8	521.1	537.9	554.2	572.1	586.5	601.0	609.4	630.2
17.5°	462.9	479.7	503.8	521.7	542.9	568.5	588.7	605.1	621.7	635.3	645.8
20°	455.0	473.4	500.8	522.3	547.5	575.0	598.2	614.9	629.3	640.7	647.1
22.5°	445.2	468.2	494.9	520.1	552.2	579.5	603.8	616.9	629.0	634.5	637.1
25°	429.5	457.3	487.5	518.2	554.5	583.4	605.6	613.6	617.1	611.7	602.8
27.5°	412.6	443.6	478.9	514.7	553.1	580.9	596.8	595.6	589.6	572.2	558.3
30°	400.1	434.1	472.1	511.2	549.7	576.7	586.0	576.7	563.2	543.8	523.9
32.5°	386.9	422.2	464.8	506.1	543.5	567.3	569.2	553.3	532.4	510.3	485.6
35°	366.9	405.0	451.2	494.9	530.3	545.3	536.4	508.2	483.4	453.2	419.5
37.5°	344.3	386.5	432.7	478.4	510.5	514.4	492.3	462.7	427.6	392.2	352.5
40°	327.4	372.1	419.7	465.8	494.2	490.1	461.9	429.3	387.7	344.3	307.4
42.5°	312.3	356.9	405.4	450.7	473.4	462.2	429.3	389.3	344.5	303.7	269.9
45°	286.2	332.1	381.7	425.4	438.4	418.2	374.7	330.2	286.2	252.1	225.4
47.5°	260.7	306.1	355.3	393.7	398.3	371.1	323.6	277.9	239.9	212.2	193.4
50°	242.1	287.6	336.3	370.6	369.1	336.3	287.5	243.9	212.2	189.8	177.2
52.5°	225.3	268.4	315.1	346.3	338.4	302.7	256.0	217.4	191.4	173.8	162.4
55°	199.3	239.1	283.6	308.6	294.1	254.5	215.0	183.9	164.6	151.5	142.6
57.5°	173.4	210.8	248.8	264.2	248.3	211.7	178.8	156.2	141.7	132.0	126.2
60°	157.4	190.0	223.9	237.3	218.2	185.6	159.6	139.5	127.8	119.8	114.6
62.5°	141.5	170.6	202.6	209.9	192.4	164.9	141.9	125.1	115.5	108.4	103.5
65°	119.6	143.6	167.8	172.6	156.5	135.2	117.1	106.2	97.6	92.5	88.5
67.5°	98.2	117.3	134.5	138.4	124.3	109.5	96.4	86.8	81.1	76.8	73.5
70°	85.4	100.6	114.6	117.8	106.5	93.4	83.3	75.7	70.5	66.9	63.7
72.5°	71.9	84.5	96.3	98.4	89.2	79.1	70.9	64.9	60.3	58.0	55.0
75°	55.0	62.5	71.5	72.1	66.0	59.8	53.6	49.7	47.2	44.3	42.8
77.5°	38.8	44.6	49.8	50.8	47.2	43.0	39.5	36.4	34.4	33.0	31.6
80°	29.6	34.2	36.5	37.7	35.2	32.2	30.2	28.1	26.8	25.9	25.0
82.5°	21.2	24.1	26.1	27.1	25.7	23.9	21.9	20.7	19.7	19.0	18.7
85°	10.8	12.1	13.4	13.7	13.4	12.6	11.5	11.5	10.9	10.8	10.8
87.5°	4.3	5.6	6.0	6.7	6.8	7.7	8.8	9.7	9.7	9.4	9.0
90°	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8	26.0
92.5°	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4	70.9
95°	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1	213.2
97.5°	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2	497.5
100°	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0	742.9
102.5°	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3	903.7
105°	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4	988.6
107.5°	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0	927.5
110°	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0	874.7





TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8	826.6
115°	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1	767.3
117.5°	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6	722.7
120°	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7	700.6
122.5°	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6	683.0
125°	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8	657.5
127.5°	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2	632.3
130°	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4	616.0
132.5°	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5	600.3
135°	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6	578.5
137.5°	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0	561.1
140°	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5	550.1
142.5°	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9	541.0
145°	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9	528.1
147.5°	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7	518.1
150°	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5	511.0
152.5°	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9	503.9
155°	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4	493.9
157.5°	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5	482.3
160°	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6	475.2
162.5°	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4	468.1
165°	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8	457.3
167.5°	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3	447.0
170°	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7	441.8
172.5°	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3	435.9
175°	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2	429.7
177.5°	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8	425.1
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	481.9	481.9	481.9	481.9	481.9	481.9	481.9
2.5°	499.9	501.9	501.9	502.2	504.6	504.3	504.1
5°	531.9	535.1	535.4	538.7	541.0	540.2	538.2
7.5°	562.1	568.0	572.5	574.9	577.9	579.7	578.9
10°	586.2	594.7	599.9	603.4	607.6	610.8	609.7
12.5°	608.0	618.1	625.3	631.3	631.8	635.9	633.1
15°	642.0	652.6	653.8	658.2	661.8	661.4	661.5
17.5°	653.1	656.6	657.3	657.4	657.5	656.2	653.3
20°	649.1	647.8	644.7	642.3	638.1	637.5	633.8
22.5°	630.1	626.1	618.2	612.9	606.3	604.6	603.6
25°	592.9	583.8	571.2	559.1	555.8	549.3	551.1
27.5°	541.6	527.5	513.8	504.1	495.2	485.5	488.3
30°	505.6	489.7	470.4	455.6	446.1	436.9	435.2
32.5°	462.7	439.3	417.8	404.8	390.3	384.4	378.1
35°	388.6	365.7	344.5	326.1	315.6	307.4	300.0
37.5°	322.0	295.7	278.5	263.7	256.0	251.4	252.6
40°	280.6	257.6	245.0	233.7	226.7	223.4	224.1
42.5°	247.1	229.9	219.6	211.8	206.8	205.0	204.6
45°	209.1	199.5	190.9	186.5	184.1	182.1	180.8
47.5°	183.2	175.3	170.5	167.9	165.8	163.7	163.6
50°	167.6	162.4	159.1	156.3	154.7	153.2	154.5
52.5°	155.7	151.0	147.7	145.2	144.6	143.2	143.2
55°	138.2	134.4	132.1	129.8	128.7	128.0	127.0
57.5°	122.1	118.6	116.4	115.0	112.9	112.2	111.9
60°	110.7	107.9	105.7	103.9	103.0	101.5	101.5
62.5°	100.2	97.4	95.4	94.0	92.5	91.9	92.0
65°	85.0	82.8	80.7	79.2	78.9	77.8	78.2
67.5°	71.0	69.5	67.3	66.5	65.9	65.3	64.8
70°	61.6	60.2	59.1	58.0	57.4	57.4	57.4
72.5°	53.8	52.0	51.4	50.0	50.3	49.7	49.1
75°	41.7	40.5	40.0	39.5	38.6	38.6	38.6
77.5°	30.7	30.3	29.7	29.1	28.9	28.7	28.8
80°	23.7	23.5	23.2	23.2	22.7	22.6	22.3
82.5°	18.3	17.8	17.5	17.4	17.3	17.3	17.2
85°	10.4	10.0	10.0	10.2	9.8	9.8	10.0
87.5°	8.9	9.2	9.2	9.2	9.4	9.2	9.2
90°	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2



TEST NUMBER: P331269-930

CATALOG NUMBER: SA2XXDIP-C290D925U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)