

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331623-930

Luminaire Tested: **SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331623-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2605.8 lumens  
Efficiency: N/A  
Efficacy: 101.8 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331623-930  
CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35				
1	95	91	87	84	86	83	80	77	67	65	63	52	51	49	39	38	37	31				
2	87	80	74	70	79	73	68	64	59	56	53	46	44	42	35	33	32	27				
3	80	71	64	59	72	65	59	54	53	48	45	42	39	36	31	29	28	23				
4	73	63	56	50	66	58	51	46	47	43	39	37	34	32	28	26	25	21				
5	67	56	49	43	61	52	45	40	42	38	34	34	30	28	26	24	22	18				
6	62	51	43	38	56	47	40	35	38	34	30	31	27	25	24	21	20	17				
7	58	46	39	33	52	42	36	31	35	30	27	28	25	22	22	19	18	15				
8	54	42	35	30	49	39	32	28	32	27	24	26	22	20	20	18	16	14				
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	19	16	15	12				
10	47	35	28	24	42	32	26	22	27	23	19	22	19	16	18	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8606	8606	8606	8606
5°	9611	8660	7679	8660
10°	10663	8599	6655	8599
15°	11188	8473	5244	8473
20°	9699	8285	4538	8285
25°	6360	8031	4051	8031
30°	4282	7720	3667	7720
35°	3467	7330	3307	7330
40°	3084	6905	3060	6905
45°	2790	6405	2731	6405
50°	2539	5913	2532	5913
55°	2387	5362	2356	5362
60°	1999	4863	1973	4863
65°	1685	4413	1910	4413
70°	1553	3942	1803	3942
75°	1454	3431	1666	3431
80°	1339	2827	1478	2827
85°	1241	2242	1297	2242



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.5	1.9
10°-20°	140.8	5.4
20°-30°	181.4	7.0
30°-40°	172.4	6.6
40°-50°	147.7	5.7
50°-60°	112.5	4.3
60°-70°	71.1	2.7
70°-80°	35.5	1.4
80°-90°	11.4	0.4
90°-100°	96.7	3.7
100°-110°	328.1	12.6
110°-120°	348.5	13.4
120°-130°	286.9	11.0
130°-140°	230.4	8.8
140°-150°	174.1	6.7
150°-160°	122.4	4.7
160°-170°	72.0	2.8
170°-180°	23.4	0.9
0°-30°	372.7	14.3
0°-40°	545.1	20.9
0°-60°	805.3	30.9
0°-90°	923.3	35.4
90°-120°	773.2	29.7
90°-150°	1464.6	56.2
90°-180°	1682.0	64.5
0°-180°	2605.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	533	533	533	533	533	
5°	593	534	474	534	593	59
15°	669	507	314	507	669	181
25°	357	451	227	451	357	169
35°	176	372	168	372	176	113
45°	122	280	120	280	122	95
55°	85	190	84	190	85	74
65°	44	116	50	116	44	45
75°	23	55	27	55	23	25
85°	7	12	7	12	7	8
90°	15	0	15	0	15	8
95°	53	16	53	16	53	69
105°	524	57	524	57	524	507
115°	690	100	690	100	690	675
125°	559	140	559	140	559	505
135°	464	164	464	164	464	360
145°	370	187	370	187	370	235
155°	311	212	311	212	311	145
165°	273	232	273	232	273	78
175°	246	241	246	241	246	24
180°	242	242	242	242	242	



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	554.6	555.1	555.5	554.5	554.5	553.6	551.6	550.2	546.0	545.4	545.4
5°	593.0	592.6	593.4	590.9	587.7	586.9	583.3	578.7	573.9	568.6	567.4
7.5°	631.1	630.6	629.1	628.7	626.1	620.5	614.9	608.9	600.9	593.0	589.1
10°	650.4	656.6	652.8	646.4	647.6	639.0	634.3	626.3	619.6	608.0	605.4
12.5°	669.4	671.8	670.6	666.9	665.3	659.3	653.0	646.0	633.7	623.3	614.2
15°	669.3	672.8	673.8	672.6	673.5	673.2	669.8	664.1	653.4	641.9	631.9
17.5°	619.9	622.3	628.4	632.5	637.7	648.7	654.1	656.2	654.6	648.0	641.0
20°	564.5	560.4	577.5	586.1	593.5	612.0	628.0	634.1	643.9	643.8	641.9
22.5°	485.9	486.9	503.0	513.4	535.0	553.6	571.7	594.7	613.7	626.2	633.6
25°	357.0	364.1	380.2	394.3	418.3	452.8	484.1	520.4	554.6	581.7	607.5
27.5°	268.2	268.7	281.4	294.5	308.8	337.0	376.4	419.7	468.6	508.9	555.2
30°	229.7	228.5	233.9	241.9	254.1	276.0	305.6	348.1	396.9	457.6	511.7
32.5°	202.4	202.4	206.5	212.4	222.5	237.3	257.6	292.2	338.2	397.9	461.3
35°	175.9	175.8	178.7	183.0	187.2	196.7	210.6	228.7	260.4	316.1	380.9
37.5°	156.9	157.8	159.2	161.9	166.6	171.9	180.2	192.4	214.9	247.9	302.4
40°	146.3	146.7	148.7	150.9	153.7	157.8	164.6	174.5	190.9	217.2	257.1
42.5°	136.6	136.9	138.4	140.4	142.6	146.7	152.4	160.9	174.2	194.7	227.6
45°	122.2	122.2	123.5	124.4	126.9	130.5	135.2	142.3	151.5	166.6	188.5
47.5°	108.8	108.8	109.7	111.3	112.8	115.7	120.3	126.0	132.7	144.5	163.1
50°	101.1	101.3	101.8	103.1	104.1	106.6	110.2	115.2	122.2	131.3	146.8
52.5°	94.9	94.8	95.5	96.0	96.7	98.5	101.2	105.6	111.9	119.8	132.6
55°	84.8	84.1	85.2	86.1	86.7	87.4	88.9	91.6	97.0	103.7	113.3
57.5°	72.2	71.9	72.7	73.5	75.3	77.3	78.6	80.3	83.1	87.9	97.4
60°	61.9	61.9	63.5	64.1	66.1	68.7	71.3	72.8	75.6	78.7	85.8
62.5°	52.7	52.8	53.6	54.1	55.3	58.5	62.1	65.4	68.0	71.0	75.7
65°	44.1	44.4	44.4	44.8	45.6	46.3	47.8	50.4	55.0	59.3	62.8
67.5°	37.4	37.5	37.7	38.0	38.2	39.0	39.6	40.8	41.8	45.8	50.2
70°	32.9	33.5	33.3	33.7	33.9	34.2	35.0	35.5	37.3	38.2	40.8
72.5°	28.8	29.2	29.2	29.4	29.9	30.0	30.6	31.1	32.2	32.9	34.4
75°	23.3	23.2	23.3	23.7	23.9	24.1	24.1	24.8	25.4	26.1	27.1
77.5°	18.0	18.2	18.2	18.2	18.3	18.6	18.5	18.8	19.4	19.8	20.2
80°	14.4	14.6	14.4	14.6	14.8	15.0	14.8	15.0	15.6	15.9	15.9
82.5°	11.2	11.3	11.3	11.3	11.4	11.4	11.7	11.7	12.1	12.1	12.2
85°	6.7	6.5	6.5	6.5	6.7	6.8	6.7	6.7	6.8	6.8	6.8
87.5°	5.5	5.6	5.6	5.6	5.6	5.5	5.3	5.6	5.6	5.8	5.6
90°	15.3	15.3	15.3	15.3	15.3	14.8	13.9	14.8	15.3	15.8	15.3
92.5°	25.8	26.5	26.2	27.6	28.0	30.9	34.8	40.5	51.0	60.4	59.6
95°	53.0	52.5	54.0	57.6	63.7	73.9	93.4	121.8	159.5	182.3	161.3
97.5°	104.4	108.3	115.0	126.5	148.7	182.3	232.6	284.3	326.4	311.1	234.3
100°	166.5	174.8	188.3	208.3	246.9	303.1	366.9	424.5	434.2	367.3	252.9
102.5°	292.9	304.3	321.1	355.2	397.1	456.8	503.4	516.4	474.4	369.2	245.9
105°	524.0	530.5	550.5	579.4	608.1	623.5	617.4	564.9	468.2	344.5	232.0
107.5°	669.4	678.0	682.0	683.5	680.0	657.5	609.1	529.9	427.4	318.1	225.1
110°	713.2	713.7	709.6	700.7	680.7	642.5	583.0	499.9	401.7	305.5	223.6



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	712.5	710.0	702.1	687.3	659.5	615.8	552.2	472.3	383.8	297.3	224.0
115°	689.5	685.3	673.3	651.8	618.9	571.0	510.1	438.5	361.7	288.3	226.0
117.5°	648.5	645.0	632.3	609.7	576.0	531.1	475.8	412.9	347.8	283.9	229.3
120°	622.1	617.4	604.0	582.1	549.6	507.3	458.0	400.3	340.4	281.3	231.5
122.5°	594.6	590.7	578.7	557.2	528.0	489.8	443.1	390.3	334.0	279.8	234.2
125°	559.4	555.6	544.0	526.4	499.4	464.5	423.5	375.7	325.0	277.1	238.1
127.5°	528.5	525.5	515.4	498.9	475.4	443.2	404.6	361.3	316.7	275.6	242.1
130°	510.9	507.3	498.0	482.2	459.3	428.7	392.0	352.0	311.0	274.8	245.0
132.5°	492.8	489.4	480.9	465.0	442.6	413.8	380.1	343.1	306.6	274.4	248.0
135°	463.6	461.7	453.3	438.0	418.0	392.0	361.3	330.6	300.4	273.9	251.5
137.5°	434.9	432.1	424.8	411.6	393.4	370.6	346.3	320.7	296.0	273.8	254.7
140°	415.2	412.4	405.4	393.4	378.5	358.0	336.6	314.3	293.4	273.4	256.2
142.5°	395.5	394.9	388.7	377.7	363.6	346.5	328.1	309.1	290.8	273.4	257.3
145°	370.1	368.7	364.0	356.1	345.0	331.5	317.1	301.7	287.3	272.5	258.5
147.5°	348.8	348.0	344.8	338.5	329.3	319.4	308.2	296.1	283.8	270.8	258.9
150°	336.1	335.7	332.9	327.3	320.3	312.0	302.2	292.0	280.9	269.7	258.5
152.5°	325.4	325.3	323.3	318.4	312.9	305.7	297.4	287.9	278.3	267.8	257.8
155°	311.0	312.0	310.1	306.9	301.7	296.6	289.7	282.3	273.4	264.6	256.7
157.5°	298.9	298.9	298.1	295.3	291.7	287.7	281.8	275.7	268.8	261.2	254.5
160°	291.1	291.1	290.6	288.3	285.0	281.8	276.6	271.5	265.5	259.0	253.4
162.5°	283.6	284.0	283.6	281.9	278.7	276.2	271.8	267.4	262.5	257.1	252.3
165°	273.0	273.4	273.4	271.5	269.7	267.8	264.6	261.3	257.6	253.4	250.1
167.5°	263.1	263.7	263.7	262.7	261.9	260.2	258.0	255.4	252.7	250.1	248.0
170°	257.1	258.0	258.5	257.1	256.7	255.8	253.9	252.5	250.1	248.3	246.9
172.5°	252.3	252.8	253.3	252.7	252.2	251.6	250.1	249.2	247.5	246.1	245.4
175°	246.0	246.9	247.4	246.9	246.9	246.5	246.0	245.5	244.1	243.6	243.2
177.5°	242.1	242.9	243.3	243.3	243.3	243.3	242.9	242.9	242.1	241.7	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	545.8	544.5	543.5	540.9	539.5	536.5	536.1	536.0	532.1	528.4	527.3
5°	564.5	561.5	557.1	551.9	546.5	541.0	537.3	534.3	526.8	519.8	515.8
7.5°	583.3	577.0	569.3	559.5	551.3	542.2	535.3	529.2	518.7	508.6	501.8
10°	597.5	587.1	576.9	563.4	552.8	542.4	532.8	524.5	512.7	499.3	489.8
12.5°	606.2	594.8	580.7	567.5	553.8	540.6	527.7	517.1	503.1	489.3	478.2
15°	618.0	605.8	588.7	569.8	552.3	535.0	520.2	506.9	488.8	472.2	458.5
17.5°	627.7	610.8	592.6	570.7	550.3	528.5	509.4	492.4	472.1	452.2	436.1
20°	630.8	614.1	593.0	571.1	547.1	521.3	500.8	482.2	460.6	438.9	420.4
22.5°	628.8	615.9	592.4	566.2	541.6	514.7	491.5	469.9	445.9	423.8	402.4
25°	615.8	611.3	589.1	560.6	532.5	501.2	474.3	450.8	423.4	399.7	376.3
27.5°	585.3	594.9	581.1	550.7	519.4	485.9	455.7	428.9	400.5	373.8	350.6
30°	556.0	578.0	572.1	543.9	508.9	476.0	442.1	414.1	383.8	356.3	333.4
32.5°	515.8	552.2	558.0	534.4	498.2	462.0	426.5	398.7	367.0	338.1	315.7
35°	451.8	506.3	531.3	516.3	480.0	440.9	404.3	371.9	340.0	311.5	289.3
37.5°	375.6	449.8	491.5	492.5	459.2	418.6	378.6	346.4	313.8	285.8	261.8
40°	326.1	406.5	460.8	472.8	444.7	400.8	360.4	327.6	295.8	268.3	240.8
42.5°	281.7	361.7	428.4	449.4	427.1	383.4	342.9	308.7	277.7	251.8	223.6
45°	227.8	297.8	371.3	408.7	396.3	356.0	313.2	280.5	251.5	229.1	202.0
47.5°	192.2	241.5	312.7	363.2	363.1	326.2	284.1	252.9	225.9	204.9	183.0
50°	171.9	214.8	275.0	332.4	337.2	306.3	266.3	235.4	210.2	188.2	170.6
52.5°	153.6	189.1	243.1	298.2	311.9	285.1	246.3	217.8	193.3	173.0	158.0
55°	129.8	157.3	198.4	249.8	270.6	251.7	217.2	190.5	170.7	153.7	140.7
57.5°	109.8	130.4	163.4	204.8	228.9	217.1	188.7	167.0	150.0	134.6	124.4
60°	97.3	114.1	142.0	176.7	203.3	195.0	170.7	150.6	136.2	122.8	113.2
62.5°	85.4	99.9	123.8	152.0	176.3	172.9	153.1	136.2	123.5	111.4	103.2
65°	68.7	79.2	98.0	120.0	139.7	141.3	127.0	115.5	104.3	94.7	87.4
67.5°	54.7	61.6	74.8	93.4	108.0	113.3	104.6	95.8	86.8	79.4	73.1
70°	46.1	51.7	61.3	76.3	89.8	95.4	90.3	83.5	75.7	69.6	64.2
72.5°	37.3	42.8	49.9	60.9	72.5	78.5	76.7	71.8	65.6	60.4	55.4
75°	28.1	29.8	34.7	42.1	51.1	56.3	57.6	55.0	50.0	46.1	43.1
77.5°	20.8	21.9	24.1	28.0	33.9	38.6	40.4	40.1	36.7	34.5	31.6
80°	16.6	17.2	18.3	20.0	24.5	29.1	30.4	30.4	28.0	27.1	24.3
82.5°	12.6	13.0	13.8	14.7	16.7	20.8	22.3	22.5	21.0	19.8	17.6
85°	7.3	7.0	7.4	8.0	8.3	9.5	11.7	12.1	11.7	10.2	9.6
87.5°	5.1	4.6	4.1	3.7	3.6	3.6	3.9	4.4	4.1	4.0	3.9
90°	12.6	9.3	7.0	5.5	4.6	3.8	1.9	0.5	1.9	3.8	4.6
92.5°	46.4	31.6	21.1	16.7	13.6	11.5	8.2	5.7	8.2	11.5	13.6
95°	107.4	66.9	45.6	34.4	27.0	22.7	18.1	16.3	18.1	22.7	27.0
97.5°	144.7	88.4	61.5	48.8	40.3	33.9	29.0	26.5	29.0	33.9	40.3
100°	152.5	95.8	71.2	58.1	48.8	41.4	37.2	35.8	37.2	41.4	48.8
102.5°	152.9	102.5	79.7	66.7	57.0	49.6	45.4	44.4	45.4	49.6	57.0
105°	155.3	113.9	92.0	79.0	68.8	61.8	58.6	56.7	58.6	61.8	68.8
107.5°	161.7	125.6	104.4	91.3	81.2	74.8	71.6	70.1	71.6	74.8	81.2
110°	166.9	133.5	113.0	99.5	89.8	83.7	80.9	79.0	80.9	83.7	89.8





TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	172.5	140.9	121.2	107.3	97.9	92.2	89.1	87.2	89.1	92.2	97.9
115°	180.8	152.5	132.5	119.9	110.6	105.1	102.3	100.0	102.3	105.1	110.6
117.5°	189.8	163.2	144.7	131.7	122.8	117.8	115.0	113.2	115.0	117.8	122.8
120°	195.8	170.6	152.5	139.5	130.2	126.0	123.2	121.3	123.2	126.0	130.2
122.5°	201.0	177.7	160.7	147.3	138.0	133.5	130.7	129.1	130.7	133.5	138.0
125°	209.2	188.3	171.5	158.6	149.3	143.7	140.9	139.5	140.9	143.7	149.3
127.5°	217.0	198.2	181.9	168.5	159.6	153.4	149.5	147.7	149.5	153.4	159.6
130°	221.8	204.2	187.8	174.8	165.5	159.0	154.3	152.5	154.3	159.0	165.5
132.5°	226.7	209.3	193.8	180.8	171.1	164.2	159.2	156.9	159.2	164.2	171.1
135°	232.9	216.7	201.8	188.7	178.1	171.1	165.5	163.6	165.5	171.1	178.1
137.5°	237.7	222.7	207.9	195.8	185.2	177.8	172.2	170.0	172.2	177.8	185.2
140°	240.4	226.0	212.1	199.9	189.7	182.3	176.7	174.8	176.7	182.3	189.7
142.5°	242.6	228.6	215.0	203.7	193.8	186.4	181.2	179.7	181.2	186.4	193.8
145°	245.5	232.4	219.9	209.7	200.4	193.4	188.7	186.9	188.7	193.4	200.4
147.5°	247.1	235.6	223.8	214.7	207.0	200.6	196.1	194.7	196.1	200.6	207.0
150°	247.9	237.1	226.4	218.1	211.1	205.0	201.3	199.9	201.3	205.0	211.1
152.5°	248.2	238.6	229.0	221.4	214.8	209.5	205.8	205.1	205.8	209.5	214.8
155°	248.7	240.8	232.9	226.0	220.9	215.7	213.0	212.5	213.0	215.7	220.9
157.5°	248.7	242.4	235.7	229.9	225.8	221.4	219.1	218.6	219.1	221.4	225.8
160°	248.7	243.2	237.6	232.4	228.8	225.0	223.1	222.7	223.1	225.0	228.8
162.5°	248.3	243.5	238.7	234.7	231.4	228.4	226.5	226.8	226.5	228.4	231.4
165°	247.4	244.1	239.9	237.1	234.8	232.0	231.1	231.5	231.1	232.0	234.8
167.5°	246.7	244.0	240.9	239.2	237.5	235.7	234.9	235.5	234.9	235.7	237.5
170°	246.0	243.6	241.3	239.9	239.0	237.6	237.1	238.1	237.1	237.6	239.0
172.5°	244.8	243.3	241.7	240.7	240.1	238.7	239.0	239.5	239.0	238.7	240.1
175°	243.6	242.7	241.7	241.3	241.3	240.4	240.8	241.3	240.8	240.4	241.3
177.5°	242.9	242.1	241.7	241.7	241.7	241.0	241.4	242.1	241.4	241.0	241.7
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	525.5	524.4	522.4	519.5	517.7	514.6	512.6	513.7	514.0	513.7	513.5
5°	511.4	507.4	502.1	496.8	492.0	486.9	483.9	482.7	480.0	478.6	477.8
7.5°	494.2	487.5	480.0	470.9	463.3	455.2	451.1	449.1	443.8	440.9	438.4
10°	481.5	470.9	463.3	451.5	444.3	433.7	426.5	426.7	419.5	415.4	412.5
12.5°	467.4	455.8	443.2	432.5	422.5	414.0	405.3	401.8	394.1	390.2	382.2
15°	444.1	430.6	417.3	402.8	392.6	379.4	366.9	351.5	339.1	328.3	325.4
17.5°	418.7	401.9	388.5	371.5	354.1	332.0	317.4	308.4	301.0	295.3	291.1
20°	401.1	384.1	369.8	344.3	320.7	305.7	295.1	288.1	280.4	274.3	270.9
22.5°	382.8	365.0	345.5	317.0	298.6	286.7	277.1	269.2	263.9	259.2	256.1
25°	356.7	337.2	305.2	285.6	270.8	258.1	251.5	246.7	241.2	234.6	231.7
27.5°	329.1	298.2	275.2	260.6	246.5	238.3	232.3	225.1	220.1	217.2	214.1
30°	308.5	277.6	259.7	243.7	233.7	224.6	217.6	213.5	208.7	203.7	201.7
32.5°	285.6	260.9	243.6	230.4	220.2	212.5	206.9	200.3	196.9	193.8	189.6
35°	257.1	238.3	222.6	211.9	202.2	195.9	189.5	185.6	179.3	176.7	175.0
37.5°	232.9	216.7	205.0	193.6	186.0	179.0	175.0	168.8	166.2	162.5	159.0
40°	219.2	203.3	192.1	182.8	174.2	169.1	164.1	159.1	155.0	153.4	149.1
42.5°	205.4	192.4	181.1	171.0	165.3	159.7	153.4	149.8	145.5	142.8	140.2
45°	186.1	174.6	165.0	156.7	150.3	144.6	140.6	134.4	132.1	126.7	124.4
47.5°	169.3	158.6	149.4	141.5	135.3	131.6	125.6	120.8	117.0	113.7	110.8
50°	157.3	148.3	139.4	132.4	126.9	121.5	115.4	113.0	107.0	105.3	103.7
52.5°	146.3	137.8	129.7	122.8	117.2	112.0	106.6	103.5	99.5	97.8	96.6
55°	130.9	122.8	115.0	108.9	103.4	98.0	94.7	90.7	88.9	87.6	86.1
57.5°	115.5	108.2	102.2	96.0	90.4	86.2	82.3	80.0	78.1	76.4	74.6
60°	105.7	98.7	93.4	87.6	81.9	78.4	75.4	72.6	70.4	67.8	67.0
62.5°	95.4	89.2	84.3	78.7	73.7	70.5	67.7	65.1	62.4	58.6	57.6
65°	81.1	76.3	71.1	66.4	62.0	58.9	54.8	51.9	50.7	50.4	50.2
67.5°	68.2	63.7	59.2	54.5	50.5	47.5	45.4	45.0	44.2	44.0	43.5
70°	59.6	55.4	51.0	46.5	42.6	42.1	41.3	40.5	39.6	39.3	38.9
72.5°	51.9	47.5	43.0	39.5	37.8	37.2	36.4	35.6	35.1	34.7	34.5
75°	39.8	35.7	32.8	31.5	30.6	30.0	28.9	28.4	28.0	27.4	27.2
77.5°	28.7	26.3	25.0	24.2	23.2	22.7	22.0	21.4	21.0	21.0	20.6
80°	21.9	20.7	19.8	18.7	18.3	17.6	17.4	16.9	17.0	16.5	16.5
82.5°	17.0	15.6	14.8	14.3	13.9	13.3	13.1	12.9	12.9	12.5	12.5
85°	8.7	8.3	8.0	7.6	7.6	7.0	7.3	7.0	7.0	6.7	6.5
87.5°	3.9	4.1	4.2	4.9	5.5	5.4	5.3	5.1	4.9	5.1	5.0
90°	5.5	7.0	9.3	12.6	15.3	15.8	15.3	14.8	13.9	14.8	15.3
92.5°	16.7	21.1	31.6	46.4	59.6	60.4	51.0	40.5	34.8	30.9	28.0
95°	34.4	45.6	66.9	107.4	161.3	182.3	159.5	121.8	93.4	73.9	63.7
97.5°	48.8	61.5	88.4	144.7	234.3	311.1	326.4	284.3	232.6	182.3	148.7
100°	58.1	71.2	95.8	152.5	252.9	367.3	434.2	424.5	366.9	303.1	246.9
102.5°	66.7	79.7	102.5	152.9	245.9	369.2	474.4	516.4	503.4	456.8	397.1
105°	79.0	92.0	113.9	155.3	232.0	344.5	468.2	564.9	617.4	623.5	608.1
107.5°	91.3	104.4	125.6	161.7	225.1	318.1	427.4	529.9	609.1	657.5	680.0
110°	99.5	113.0	133.5	166.9	223.6	305.5	401.7	499.9	583.0	642.5	680.7



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	107.3	121.2	140.9	172.5	224.0	297.3	383.8	472.3	552.2	615.8	659.5
115°	119.9	132.5	152.5	180.8	226.0	288.3	361.7	438.5	510.1	571.0	618.9
117.5°	131.7	144.7	163.2	189.8	229.3	283.9	347.8	412.9	475.8	531.1	576.0
120°	139.5	152.5	170.6	195.8	231.5	281.3	340.4	400.3	458.0	507.3	549.6
122.5°	147.3	160.7	177.7	201.0	234.2	279.8	334.0	390.3	443.1	489.8	528.0
125°	158.6	171.5	188.3	209.2	238.1	277.1	325.0	375.7	423.5	464.5	499.4
127.5°	168.5	181.9	198.2	217.0	242.1	275.6	316.7	361.3	404.6	443.2	475.4
130°	174.8	187.8	204.2	221.8	245.0	274.8	311.0	352.0	392.0	428.7	459.3
132.5°	180.8	193.8	209.3	226.7	248.0	274.4	306.6	343.1	380.1	413.8	442.6
135°	188.7	201.8	216.7	232.9	251.5	273.9	300.4	330.6	361.3	392.0	418.0
137.5°	195.8	207.9	222.7	237.7	254.7	273.8	296.0	320.7	346.3	370.6	393.4
140°	199.9	212.1	226.0	240.4	256.2	273.4	293.4	314.3	336.6	358.0	378.5
142.5°	203.7	215.0	228.6	242.6	257.3	273.4	290.8	309.1	328.1	346.5	363.6
145°	209.7	219.9	232.4	245.5	258.5	272.5	287.3	301.7	317.1	331.5	345.0
147.5°	214.7	223.8	235.6	247.1	258.9	270.8	283.8	296.1	308.2	319.4	329.3
150°	218.1	226.4	237.1	247.9	258.5	269.7	280.9	292.0	302.2	312.0	320.3
152.5°	221.4	229.0	238.6	248.2	257.8	267.8	278.3	287.9	297.4	305.7	312.9
155°	226.0	232.9	240.8	248.7	256.7	264.6	273.4	282.3	289.7	296.6	301.7
157.5°	229.9	235.7	242.4	248.7	254.5	261.2	268.8	275.7	281.8	287.7	291.7
160°	232.4	237.6	243.2	248.7	253.4	259.0	265.5	271.5	276.6	281.8	285.0
162.5°	234.7	238.7	243.5	248.3	252.3	257.1	262.5	267.4	271.8	276.2	278.7
165°	237.1	239.9	244.1	247.4	250.1	253.4	257.6	261.3	264.6	267.8	269.7
167.5°	239.2	240.9	244.0	246.7	248.0	250.1	252.7	255.4	258.0	260.2	261.9
170°	239.9	241.3	243.6	246.0	246.9	248.3	250.1	252.5	253.9	255.8	256.7
172.5°	240.7	241.7	243.3	244.8	245.4	246.1	247.5	249.2	250.1	251.6	252.2
175°	241.3	241.7	242.7	243.6	243.2	243.6	244.1	245.5	246.0	246.5	246.9
177.5°	241.7	241.7	242.1	242.9	242.1	241.7	242.1	242.9	242.9	243.3	243.3
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	511.8	512.1	511.7	511.9	511.7	512.1	511.8	513.5	513.7	514.0	513.7
5°	476.9	474.7	474.3	473.8	474.3	474.7	476.9	477.8	478.6	480.0	482.7
7.5°	435.2	434.9	433.9	432.6	433.9	434.9	435.2	438.4	440.9	443.8	449.1
10°	408.4	407.4	407.2	405.9	407.2	407.4	408.4	412.5	415.4	419.5	426.7
12.5°	376.9	371.0	370.4	367.1	370.4	371.0	376.9	382.2	390.2	394.1	401.8
15°	321.0	319.8	316.1	313.7	316.1	319.8	321.0	325.4	328.3	339.1	351.5
17.5°	288.9	285.3	284.1	283.6	284.1	285.3	288.9	291.1	295.3	301.0	308.4
20°	268.3	265.1	264.5	264.1	264.5	265.1	268.3	270.9	274.3	280.4	288.1
22.5°	254.1	250.6	249.2	248.1	249.2	250.6	254.1	256.1	259.2	263.9	269.2
25°	229.8	228.5	227.8	227.4	227.8	228.5	229.8	231.7	234.6	241.2	246.7
27.5°	210.8	208.0	207.4	206.4	207.4	208.0	210.8	214.1	217.2	220.1	225.1
30°	200.0	199.1	197.8	196.7	197.8	199.1	200.0	201.7	203.7	208.7	213.5
32.5°	187.3	186.5	185.3	184.8	185.3	186.5	187.3	189.6	193.8	196.9	200.3
35°	173.2	170.6	169.4	167.8	169.4	170.6	173.2	175.0	176.7	179.3	185.6
37.5°	158.2	156.9	155.3	155.9	155.3	156.9	158.2	159.0	162.5	166.2	168.8
40°	146.7	145.8	145.4	145.2	145.4	145.8	146.7	149.1	153.4	155.0	159.1
42.5°	137.5	134.9	134.0	134.0	134.0	134.9	137.5	140.2	142.8	145.5	149.8
45°	123.5	121.2	119.4	119.6	119.4	121.2	123.5	124.4	126.7	132.1	134.4
47.5°	109.3	109.2	108.1	108.4	108.1	109.2	109.3	110.8	113.7	117.0	120.8
50°	102.4	101.3	100.5	100.8	100.5	101.3	102.4	103.7	105.3	107.0	113.0
52.5°	95.9	94.9	94.3	95.1	94.3	94.9	95.9	96.6	97.8	99.5	103.5
55°	85.2	84.1	83.9	83.7	83.9	84.1	85.2	86.1	87.6	88.9	90.7
57.5°	73.2	72.5	71.3	70.9	71.3	72.5	73.2	74.6	76.4	78.1	80.0
60°	64.7	63.2	61.3	61.1	61.3	63.2	64.7	67.0	67.8	70.4	72.6
62.5°	56.7	56.5	56.1	56.1	56.1	56.5	56.7	57.6	58.6	62.4	65.1
65°	49.8	49.7	49.8	50.0	49.8	49.7	49.8	50.2	50.4	50.7	51.9
67.5°	43.4	43.0	42.7	42.9	42.7	43.0	43.4	43.5	44.0	44.2	45.0
70°	38.5	38.3	38.2	38.2	38.2	38.3	38.5	38.9	39.3	39.6	40.5
72.5°	33.8	33.8	33.6	33.4	33.6	33.8	33.8	34.5	34.7	35.1	35.6
75°	27.1	26.7	26.7	26.7	26.7	26.7	27.1	27.2	27.4	28.0	28.4
77.5°	20.6	20.4	20.2	20.1	20.2	20.4	20.6	20.6	21.0	21.0	21.4
80°	16.3	16.1	15.9	15.9	15.9	16.1	16.3	16.5	16.5	17.0	16.9
82.5°	12.5	12.2	12.2	12.1	12.2	12.2	12.5	12.5	12.5	12.9	12.9
85°	6.7	6.8	6.7	7.0	6.7	6.8	6.7	6.5	6.7	7.0	7.0
87.5°	5.0	4.8	5.0	4.8	5.0	4.8	5.0	5.0	5.1	4.9	5.1
90°	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	14.8	13.9	14.8
92.5°	27.6	26.2	26.5	25.8	26.5	26.2	27.6	28.0	30.9	34.8	40.5
95°	57.6	54.0	52.5	53.0	52.5	54.0	57.6	63.7	73.9	93.4	121.8
97.5°	126.5	115.0	108.3	104.4	108.3	115.0	126.5	148.7	182.3	232.6	284.3
100°	208.3	188.3	174.8	166.5	174.8	188.3	208.3	246.9	303.1	366.9	424.5
102.5°	355.2	321.1	304.3	292.9	304.3	321.1	355.2	397.1	456.8	503.4	516.4
105°	579.4	550.5	530.5	524.0	530.5	550.5	579.4	608.1	623.5	617.4	564.9
107.5°	683.5	682.0	678.0	669.4	678.0	682.0	683.5	680.0	657.5	609.1	529.9
110°	700.7	709.6	713.7	713.2	713.7	709.6	700.7	680.7	642.5	583.0	499.9



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	687.3	702.1	710.0	712.5	710.0	702.1	687.3	659.5	615.8	552.2	472.3
115°	651.8	673.3	685.3	689.5	685.3	673.3	651.8	618.9	571.0	510.1	438.5
117.5°	609.7	632.3	645.0	648.5	645.0	632.3	609.7	576.0	531.1	475.8	412.9
120°	582.1	604.0	617.4	622.1	617.4	604.0	582.1	549.6	507.3	458.0	400.3
122.5°	557.2	578.7	590.7	594.6	590.7	578.7	557.2	528.0	489.8	443.1	390.3
125°	526.4	544.0	555.6	559.4	555.6	544.0	526.4	499.4	464.5	423.5	375.7
127.5°	498.9	515.4	525.5	528.5	525.5	515.4	498.9	475.4	443.2	404.6	361.3
130°	482.2	498.0	507.3	510.9	507.3	498.0	482.2	459.3	428.7	392.0	352.0
132.5°	465.0	480.9	489.4	492.8	489.4	480.9	465.0	442.6	413.8	380.1	343.1
135°	438.0	453.3	461.7	463.6	461.7	453.3	438.0	418.0	392.0	361.3	330.6
137.5°	411.6	424.8	432.1	434.9	432.1	424.8	411.6	393.4	370.6	346.3	320.7
140°	393.4	405.4	412.4	415.2	412.4	405.4	393.4	378.5	358.0	336.6	314.3
142.5°	377.7	388.7	394.9	395.5	394.9	388.7	377.7	363.6	346.5	328.1	309.1
145°	356.1	364.0	368.7	370.1	368.7	364.0	356.1	345.0	331.5	317.1	301.7
147.5°	338.5	344.8	348.0	348.8	348.0	344.8	338.5	329.3	319.4	308.2	296.1
150°	327.3	332.9	335.7	336.1	335.7	332.9	327.3	320.3	312.0	302.2	292.0
152.5°	318.4	323.3	325.3	325.4	325.3	323.3	318.4	312.9	305.7	297.4	287.9
155°	306.9	310.1	312.0	311.0	312.0	310.1	306.9	301.7	296.6	289.7	282.3
157.5°	295.3	298.1	298.9	298.9	298.9	298.1	295.3	291.7	287.7	281.8	275.7
160°	288.3	290.6	291.1	291.1	291.1	290.6	288.3	285.0	281.8	276.6	271.5
162.5°	281.9	283.6	284.0	283.6	284.0	283.6	281.9	278.7	276.2	271.8	267.4
165°	271.5	273.4	273.4	273.0	273.4	273.4	271.5	269.7	267.8	264.6	261.3
167.5°	262.7	263.7	263.7	263.1	263.7	263.7	262.7	261.9	260.2	258.0	255.4
170°	257.1	258.5	258.0	257.1	258.0	258.5	257.1	256.7	255.8	253.9	252.5
172.5°	252.7	253.3	252.8	252.3	252.8	253.3	252.7	252.2	251.6	250.1	249.2
175°	246.9	247.4	246.9	246.0	246.9	247.4	246.9	246.9	246.5	246.0	245.5
177.5°	243.3	243.3	242.9	242.1	242.9	243.3	243.3	243.3	243.3	242.9	242.9
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	512.6	514.6	517.7	519.5	522.4	524.4	525.5	527.3	528.4	532.1	536.0
5°	483.9	486.9	492.0	496.8	502.1	507.4	511.4	515.8	519.8	526.8	534.3
7.5°	451.1	455.2	463.3	470.9	480.0	487.5	494.2	501.8	508.6	518.7	529.2
10°	426.5	433.7	444.3	451.5	463.3	470.9	481.5	489.8	499.3	512.7	524.5
12.5°	405.3	414.0	422.5	432.5	443.2	455.8	467.4	478.2	489.3	503.1	517.1
15°	366.9	379.4	392.6	402.8	417.3	430.6	444.1	458.5	472.2	488.8	506.9
17.5°	317.4	332.0	354.1	371.5	388.5	401.9	418.7	436.1	452.2	472.1	492.4
20°	295.1	305.7	320.7	344.3	369.8	384.1	401.1	420.4	438.9	460.6	482.2
22.5°	277.1	286.7	298.6	317.0	345.5	365.0	382.8	402.4	423.8	445.9	469.9
25°	251.5	258.1	270.8	285.6	305.2	337.2	356.7	376.3	399.7	423.4	450.8
27.5°	232.3	238.3	246.5	260.6	275.2	298.2	329.1	350.6	373.8	400.5	428.9
30°	217.6	224.6	233.7	243.7	259.7	277.6	308.5	333.4	356.3	383.8	414.1
32.5°	206.9	212.5	220.2	230.4	243.6	260.9	285.6	315.7	338.1	367.0	398.7
35°	189.5	195.9	202.2	211.9	222.6	238.3	257.1	289.3	311.5	340.0	371.9
37.5°	175.0	179.0	186.0	193.6	205.0	216.7	232.9	261.8	285.8	313.8	346.4
40°	164.1	169.1	174.2	182.8	192.1	203.3	219.2	240.8	268.3	295.8	327.6
42.5°	153.4	159.7	165.3	171.0	181.1	192.4	205.4	223.6	251.8	277.7	308.7
45°	140.6	144.6	150.3	156.7	165.0	174.6	186.1	202.0	229.1	251.5	280.5
47.5°	125.6	131.6	135.3	141.5	149.4	158.6	169.3	183.0	204.9	225.9	252.9
50°	115.4	121.5	126.9	132.4	139.4	148.3	157.3	170.6	188.2	210.2	235.4
52.5°	106.6	112.0	117.2	122.8	129.7	137.8	146.3	158.0	173.0	193.3	217.8
55°	94.7	98.0	103.4	108.9	115.0	122.8	130.9	140.7	153.7	170.7	190.5
57.5°	82.3	86.2	90.4	96.0	102.2	108.2	115.5	124.4	134.6	150.0	167.0
60°	75.4	78.4	81.9	87.6	93.4	98.7	105.7	113.2	122.8	136.2	150.6
62.5°	67.7	70.5	73.7	78.7	84.3	89.2	95.4	103.2	111.4	123.5	136.2
65°	54.8	58.9	62.0	66.4	71.1	76.3	81.1	87.4	94.7	104.3	115.5
67.5°	45.4	47.5	50.5	54.5	59.2	63.7	68.2	73.1	79.4	86.8	95.8
70°	41.3	42.1	42.6	46.5	51.0	55.4	59.6	64.2	69.6	75.7	83.5
72.5°	36.4	37.2	37.8	39.5	43.0	47.5	51.9	55.4	60.4	65.6	71.8
75°	28.9	30.0	30.6	31.5	32.8	35.7	39.8	43.1	46.1	50.0	55.0
77.5°	22.0	22.7	23.2	24.2	25.0	26.3	28.7	31.6	34.5	36.7	40.1
80°	17.4	17.6	18.3	18.7	19.8	20.7	21.9	24.3	27.1	28.0	30.4
82.5°	13.1	13.3	13.9	14.3	14.8	15.6	17.0	17.6	19.8	21.0	22.5
85°	7.3	7.0	7.6	7.6	8.0	8.3	8.7	9.6	10.2	11.7	12.1
87.5°	5.3	5.4	5.5	4.9	4.2	4.1	3.9	3.9	4.0	4.1	4.4
90°	15.3	15.8	15.3	12.6	9.3	7.0	5.5	4.6	3.8	1.9	0.5
92.5°	51.0	60.4	59.6	46.4	31.6	21.1	16.7	13.6	11.5	8.2	5.7
95°	159.5	182.3	161.3	107.4	66.9	45.6	34.4	27.0	22.7	18.1	16.3
97.5°	326.4	311.1	234.3	144.7	88.4	61.5	48.8	40.3	33.9	29.0	26.5
100°	434.2	367.3	252.9	152.5	95.8	71.2	58.1	48.8	41.4	37.2	35.8
102.5°	474.4	369.2	245.9	152.9	102.5	79.7	66.7	57.0	49.6	45.4	44.4
105°	468.2	344.5	232.0	155.3	113.9	92.0	79.0	68.8	61.8	58.6	56.7
107.5°	427.4	318.1	225.1	161.7	125.6	104.4	91.3	81.2	74.8	71.6	70.1
110°	401.7	305.5	223.6	166.9	133.5	113.0	99.5	89.8	83.7	80.9	79.0



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	383.8	297.3	224.0	172.5	140.9	121.2	107.3	97.9	92.2	89.1	87.2
115°	361.7	288.3	226.0	180.8	152.5	132.5	119.9	110.6	105.1	102.3	100.0
117.5°	347.8	283.9	229.3	189.8	163.2	144.7	131.7	122.8	117.8	115.0	113.2
120°	340.4	281.3	231.5	195.8	170.6	152.5	139.5	130.2	126.0	123.2	121.3
122.5°	334.0	279.8	234.2	201.0	177.7	160.7	147.3	138.0	133.5	130.7	129.1
125°	325.0	277.1	238.1	209.2	188.3	171.5	158.6	149.3	143.7	140.9	139.5
127.5°	316.7	275.6	242.1	217.0	198.2	181.9	168.5	159.6	153.4	149.5	147.7
130°	311.0	274.8	245.0	221.8	204.2	187.8	174.8	165.5	159.0	154.3	152.5
132.5°	306.6	274.4	248.0	226.7	209.3	193.8	180.8	171.1	164.2	159.2	156.9
135°	300.4	273.9	251.5	232.9	216.7	201.8	188.7	178.1	171.1	165.5	163.6
137.5°	296.0	273.8	254.7	237.7	222.7	207.9	195.8	185.2	177.8	172.2	170.0
140°	293.4	273.4	256.2	240.4	226.0	212.1	199.9	189.7	182.3	176.7	174.8
142.5°	290.8	273.4	257.3	242.6	228.6	215.0	203.7	193.8	186.4	181.2	179.7
145°	287.3	272.5	258.5	245.5	232.4	219.9	209.7	200.4	193.4	188.7	186.9
147.5°	283.8	270.8	258.9	247.1	235.6	223.8	214.7	207.0	200.6	196.1	194.7
150°	280.9	269.7	258.5	247.9	237.1	226.4	218.1	211.1	205.0	201.3	199.9
152.5°	278.3	267.8	257.8	248.2	238.6	229.0	221.4	214.8	209.5	205.8	205.1
155°	273.4	264.6	256.7	248.7	240.8	232.9	226.0	220.9	215.7	213.0	212.5
157.5°	268.8	261.2	254.5	248.7	242.4	235.7	229.9	225.8	221.4	219.1	218.6
160°	265.5	259.0	253.4	248.7	243.2	237.6	232.4	228.8	225.0	223.1	222.7
162.5°	262.5	257.1	252.3	248.3	243.5	238.7	234.7	231.4	228.4	226.5	226.8
165°	257.6	253.4	250.1	247.4	244.1	239.9	237.1	234.8	232.0	231.1	231.5
167.5°	252.7	250.1	248.0	246.7	244.0	240.9	239.2	237.5	235.7	234.9	235.5
170°	250.1	248.3	246.9	246.0	243.6	241.3	239.9	239.0	237.6	237.1	238.1
172.5°	247.5	246.1	245.4	244.8	243.3	241.7	240.7	240.1	238.7	239.0	239.5
175°	244.1	243.6	243.2	243.6	242.7	241.7	241.3	241.3	240.4	240.8	241.3
177.5°	242.1	241.7	242.1	242.9	242.1	241.7	241.7	241.7	241.0	241.4	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	536.1	536.5	539.5	540.9	543.5	544.5	545.8	545.4	545.4	546.0	550.2
5°	537.3	541.0	546.5	551.9	557.1	561.5	564.5	567.4	568.6	573.9	578.7
7.5°	535.3	542.2	551.3	559.5	569.3	577.0	583.3	589.1	593.0	600.9	608.9
10°	532.8	542.4	552.8	563.4	576.9	587.1	597.5	605.4	608.0	619.6	626.3
12.5°	527.7	540.6	553.8	567.5	580.7	594.8	606.2	614.2	623.3	633.7	646.0
15°	520.2	535.0	552.3	569.8	588.7	605.8	618.0	631.9	641.9	653.4	664.1
17.5°	509.4	528.5	550.3	570.7	592.6	610.8	627.7	641.0	648.0	654.6	656.2
20°	500.8	521.3	547.1	571.1	593.0	614.1	630.8	641.9	643.8	643.9	634.1
22.5°	491.5	514.7	541.6	566.2	592.4	615.9	628.8	633.6	626.2	613.7	594.7
25°	474.3	501.2	532.5	560.6	589.1	611.3	615.8	607.5	581.7	554.6	520.4
27.5°	455.7	485.9	519.4	550.7	581.1	594.9	585.3	555.2	508.9	468.6	419.7
30°	442.1	476.0	508.9	543.9	572.1	578.0	556.0	511.7	457.6	396.9	348.1
32.5°	426.5	462.0	498.2	534.4	558.0	552.2	515.8	461.3	397.9	338.2	292.2
35°	404.3	440.9	480.0	516.3	531.3	506.3	451.8	380.9	316.1	260.4	228.7
37.5°	378.6	418.6	459.2	492.5	491.5	449.8	375.6	302.4	247.9	214.9	192.4
40°	360.4	400.8	444.7	472.8	460.8	406.5	326.1	257.1	217.2	190.9	174.5
42.5°	342.9	383.4	427.1	449.4	428.4	361.7	281.7	227.6	194.7	174.2	160.9
45°	313.2	356.0	396.3	408.7	371.3	297.8	227.8	188.5	166.6	151.5	142.3
47.5°	284.1	326.2	363.1	363.2	312.7	241.5	192.2	163.1	144.5	132.7	126.0
50°	266.3	306.3	337.2	332.4	275.0	214.8	171.9	146.8	131.3	122.2	115.2
52.5°	246.3	285.1	311.9	298.2	243.1	189.1	153.6	132.6	119.8	111.9	105.6
55°	217.2	251.7	270.6	249.8	198.4	157.3	129.8	113.3	103.7	97.0	91.6
57.5°	188.7	217.1	228.9	204.8	163.4	130.4	109.8	97.4	87.9	83.1	80.3
60°	170.7	195.0	203.3	176.7	142.0	114.1	97.3	85.8	78.7	75.6	72.8
62.5°	153.1	172.9	176.3	152.0	123.8	99.9	85.4	75.7	71.0	68.0	65.4
65°	127.0	141.3	139.7	120.0	98.0	79.2	68.7	62.8	59.3	55.0	50.4
67.5°	104.6	113.3	108.0	93.4	74.8	61.6	54.7	50.2	45.8	41.8	40.8
70°	90.3	95.4	89.8	76.3	61.3	51.7	46.1	40.8	38.2	37.3	35.5
72.5°	76.7	78.5	72.5	60.9	49.9	42.8	37.3	34.4	32.9	32.2	31.1
75°	57.6	56.3	51.1	42.1	34.7	29.8	28.1	27.1	26.1	25.4	24.8
77.5°	40.4	38.6	33.9	28.0	24.1	21.9	20.8	20.2	19.8	19.4	18.8
80°	30.4	29.1	24.5	20.0	18.3	17.2	16.6	15.9	15.9	15.6	15.0
82.5°	22.3	20.8	16.7	14.7	13.8	13.0	12.6	12.2	12.1	12.1	11.7
85°	11.7	9.5	8.3	8.0	7.4	7.0	7.3	6.8	6.8	6.8	6.7
87.5°	3.9	3.6	3.6	3.7	4.1	4.6	5.1	5.6	5.8	5.6	5.6
90°	1.9	3.8	4.6	5.5	7.0	9.3	12.6	15.3	15.8	15.3	14.8
92.5°	8.2	11.5	13.6	16.7	21.1	31.6	46.4	59.6	60.4	51.0	40.5
95°	18.1	22.7	27.0	34.4	45.6	66.9	107.4	161.3	182.3	159.5	121.8
97.5°	29.0	33.9	40.3	48.8	61.5	88.4	144.7	234.3	311.1	326.4	284.3
100°	37.2	41.4	48.8	58.1	71.2	95.8	152.5	252.9	367.3	434.2	424.5
102.5°	45.4	49.6	57.0	66.7	79.7	102.5	152.9	245.9	369.2	474.4	516.4
105°	58.6	61.8	68.8	79.0	92.0	113.9	155.3	232.0	344.5	468.2	564.9
107.5°	71.6	74.8	81.2	91.3	104.4	125.6	161.7	225.1	318.1	427.4	529.9
110°	80.9	83.7	89.8	99.5	113.0	133.5	166.9	223.6	305.5	401.7	499.9





TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	89.1	92.2	97.9	107.3	121.2	140.9	172.5	224.0	297.3	383.8	472.3
115°	102.3	105.1	110.6	119.9	132.5	152.5	180.8	226.0	288.3	361.7	438.5
117.5°	115.0	117.8	122.8	131.7	144.7	163.2	189.8	229.3	283.9	347.8	412.9
120°	123.2	126.0	130.2	139.5	152.5	170.6	195.8	231.5	281.3	340.4	400.3
122.5°	130.7	133.5	138.0	147.3	160.7	177.7	201.0	234.2	279.8	334.0	390.3
125°	140.9	143.7	149.3	158.6	171.5	188.3	209.2	238.1	277.1	325.0	375.7
127.5°	149.5	153.4	159.6	168.5	181.9	198.2	217.0	242.1	275.6	316.7	361.3
130°	154.3	159.0	165.5	174.8	187.8	204.2	221.8	245.0	274.8	311.0	352.0
132.5°	159.2	164.2	171.1	180.8	193.8	209.3	226.7	248.0	274.4	306.6	343.1
135°	165.5	171.1	178.1	188.7	201.8	216.7	232.9	251.5	273.9	300.4	330.6
137.5°	172.2	177.8	185.2	195.8	207.9	222.7	237.7	254.7	273.8	296.0	320.7
140°	176.7	182.3	189.7	199.9	212.1	226.0	240.4	256.2	273.4	293.4	314.3
142.5°	181.2	186.4	193.8	203.7	215.0	228.6	242.6	257.3	273.4	290.8	309.1
145°	188.7	193.4	200.4	209.7	219.9	232.4	245.5	258.5	272.5	287.3	301.7
147.5°	196.1	200.6	207.0	214.7	223.8	235.6	247.1	258.9	270.8	283.8	296.1
150°	201.3	205.0	211.1	218.1	226.4	237.1	247.9	258.5	269.7	280.9	292.0
152.5°	205.8	209.5	214.8	221.4	229.0	238.6	248.2	257.8	267.8	278.3	287.9
155°	213.0	215.7	220.9	226.0	232.9	240.8	248.7	256.7	264.6	273.4	282.3
157.5°	219.1	221.4	225.8	229.9	235.7	242.4	248.7	254.5	261.2	268.8	275.7
160°	223.1	225.0	228.8	232.4	237.6	243.2	248.7	253.4	259.0	265.5	271.5
162.5°	226.5	228.4	231.4	234.7	238.7	243.5	248.3	252.3	257.1	262.5	267.4
165°	231.1	232.0	234.8	237.1	239.9	244.1	247.4	250.1	253.4	257.6	261.3
167.5°	234.9	235.7	237.5	239.2	240.9	244.0	246.7	248.0	250.1	252.7	255.4
170°	237.1	237.6	239.0	239.9	241.3	243.6	246.0	246.9	248.3	250.1	252.5
172.5°	239.0	238.7	240.1	240.7	241.7	243.3	244.8	245.4	246.1	247.5	249.2
175°	240.8	240.4	241.3	241.3	241.7	242.7	243.6	243.2	243.6	244.1	245.5
177.5°	241.4	241.0	241.7	241.7	241.7	242.1	242.9	242.1	241.7	242.1	242.9
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	551.6	553.6	554.5	554.5	555.5	555.1	554.6
5°	583.3	586.9	587.7	590.9	593.4	592.6	593.0
7.5°	614.9	620.5	626.1	628.7	629.1	630.6	631.1
10°	634.3	639.0	647.6	646.4	652.8	656.6	650.4
12.5°	653.0	659.3	665.3	666.9	670.6	671.8	669.4
15°	669.8	673.2	673.5	672.6	673.8	672.8	669.3
17.5°	654.1	648.7	637.7	632.5	628.4	622.3	619.9
20°	628.0	612.0	593.5	586.1	577.5	560.4	564.5
22.5°	571.7	553.6	535.0	513.4	503.0	486.9	485.9
25°	484.1	452.8	418.3	394.3	380.2	364.1	357.0
27.5°	376.4	337.0	308.8	294.5	281.4	268.7	268.2
30°	305.6	276.0	254.1	241.9	233.9	228.5	229.7
32.5°	257.6	237.3	222.5	212.4	206.5	202.4	202.4
35°	210.6	196.7	187.2	183.0	178.7	175.8	175.9
37.5°	180.2	171.9	166.6	161.9	159.2	157.8	156.9
40°	164.6	157.8	153.7	150.9	148.7	146.7	146.3
42.5°	152.4	146.7	142.6	140.4	138.4	136.9	136.6
45°	135.2	130.5	126.9	124.4	123.5	122.2	122.2
47.5°	120.3	115.7	112.8	111.3	109.7	108.8	108.8
50°	110.2	106.6	104.1	103.1	101.8	101.3	101.1
52.5°	101.2	98.5	96.7	96.0	95.5	94.8	94.9
55°	88.9	87.4	86.7	86.1	85.2	84.1	84.8
57.5°	78.6	77.3	75.3	73.5	72.7	71.9	72.2
60°	71.3	68.7	66.1	64.1	63.5	61.9	61.9
62.5°	62.1	58.5	55.3	54.1	53.6	52.8	52.7
65°	47.8	46.3	45.6	44.8	44.4	44.4	44.1
67.5°	39.6	39.0	38.2	38.0	37.7	37.5	37.4
70°	35.0	34.2	33.9	33.7	33.3	33.5	32.9
72.5°	30.6	30.0	29.9	29.4	29.2	29.2	28.8
75°	24.1	24.1	23.9	23.7	23.3	23.2	23.3
77.5°	18.5	18.6	18.3	18.2	18.2	18.2	18.0
80°	14.8	15.0	14.8	14.6	14.4	14.6	14.4
82.5°	11.7	11.4	11.4	11.3	11.3	11.3	11.2
85°	6.7	6.8	6.7	6.5	6.5	6.5	6.7
87.5°	5.3	5.5	5.6	5.6	5.6	5.6	5.5
90°	13.9	14.8	15.3	15.3	15.3	15.3	15.3
92.5°	34.8	30.9	28.0	27.6	26.2	26.5	25.8
95°	93.4	73.9	63.7	57.6	54.0	52.5	53.0
97.5°	232.6	182.3	148.7	126.5	115.0	108.3	104.4
100°	366.9	303.1	246.9	208.3	188.3	174.8	166.5
102.5°	503.4	456.8	397.1	355.2	321.1	304.3	292.9
105°	617.4	623.5	608.1	579.4	550.5	530.5	524.0
107.5°	609.1	657.5	680.0	683.5	682.0	678.0	669.4
110°	583.0	642.5	680.7	700.7	709.6	713.7	713.2



TEST NUMBER: P331623-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	552.2	615.8	659.5	687.3	702.1	710.0	712.5
115°	510.1	571.0	618.9	651.8	673.3	685.3	689.5
117.5°	475.8	531.1	576.0	609.7	632.3	645.0	648.5
120°	458.0	507.3	549.6	582.1	604.0	617.4	622.1
122.5°	443.1	489.8	528.0	557.2	578.7	590.7	594.6
125°	423.5	464.5	499.4	526.4	544.0	555.6	559.4
127.5°	404.6	443.2	475.4	498.9	515.4	525.5	528.5
130°	392.0	428.7	459.3	482.2	498.0	507.3	510.9
132.5°	380.1	413.8	442.6	465.0	480.9	489.4	492.8
135°	361.3	392.0	418.0	438.0	453.3	461.7	463.6
137.5°	346.3	370.6	393.4	411.6	424.8	432.1	434.9
140°	336.6	358.0	378.5	393.4	405.4	412.4	415.2
142.5°	328.1	346.5	363.6	377.7	388.7	394.9	395.5
145°	317.1	331.5	345.0	356.1	364.0	368.7	370.1
147.5°	308.2	319.4	329.3	338.5	344.8	348.0	348.8
150°	302.2	312.0	320.3	327.3	332.9	335.7	336.1
152.5°	297.4	305.7	312.9	318.4	323.3	325.3	325.4
155°	289.7	296.6	301.7	306.9	310.1	312.0	311.0
157.5°	281.8	287.7	291.7	295.3	298.1	298.9	298.9
160°	276.6	281.8	285.0	288.3	290.6	291.1	291.1
162.5°	271.8	276.2	278.7	281.9	283.6	284.0	283.6
165°	264.6	267.8	269.7	271.5	273.4	273.4	273.0
167.5°	258.0	260.2	261.9	262.7	263.7	263.7	263.1
170°	253.9	255.8	256.7	257.1	258.5	258.0	257.1
172.5°	250.1	251.6	252.2	252.7	253.3	252.8	252.3
175°	246.0	246.5	246.9	246.9	247.4	246.9	246.0
177.5°	242.9	243.3	243.3	243.3	243.3	242.9	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7

(END OF REPORT)