

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331707-930

Luminaire Tested: **SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331707-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3734.4 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331707-930
CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	104	100	96	93	98	95	92	89	86	83	81	77	75	74	69	68	67	63
2	96	89	83	78	90	84	79	75	76	72	69	69	66	63	62	60	58	55
3	88	79	72	66	83	75	69	64	69	64	60	62	58	55	56	53	51	48
4	81	71	63	58	77	68	61	56	62	56	52	56	52	48	51	48	45	42
5	75	64	56	50	71	61	54	49	56	50	46	51	47	43	47	43	40	38
6	70	58	50	45	66	56	49	43	51	45	41	47	42	38	43	39	36	34
7	65	53	45	40	62	51	44	39	47	41	37	43	38	35	40	36	33	30
8	61	49	41	36	58	47	40	35	43	38	33	40	35	32	37	33	30	28
9	57	45	38	33	54	43	37	32	40	34	30	37	32	29	35	30	27	25
10	54	42	35	30	51	40	34	29	37	32	28	35	30	27	32	28	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25137	25137	25137	25137
5°	28075	25293	22428	25293
10°	31147	25117	19441	25117
15°	32679	24749	15318	24749
20°	28331	24204	13254	24204
25°	18579	23457	11834	23457
30°	12506	22551	10711	22551
35°	10129	21409	9660	21409
40°	9008	20168	8939	20168
45°	8152	18712	7978	18712
50°	7420	17269	7390	17269
55°	6975	15671	6883	15671
60°	5835	14202	5767	14202
65°	4917	12894	5578	12894
70°	4546	11514	5264	11514
75°	4255	10025	4860	10025
80°	3924	8247	4333	8247
85°	3612	6502	3798	6502



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.6	4.0
10°-20°	411.2	11.0
20°-30°	529.9	14.2
30°-40°	503.6	13.5
40°-50°	431.4	11.6
50°-60°	328.5	8.8
60°-70°	207.7	5.6
70°-80°	103.7	2.8
80°-90°	28.3	0.8
90°-100°	59.9	1.6
100°-110°	203.2	5.4
110°-120°	215.9	5.8
120°-130°	177.7	4.8
130°-140°	142.7	3.8
140°-150°	107.9	2.9
150°-160°	75.8	2.0
160°-170°	44.6	1.2
170°-180°	14.5	0.4
0°-30°	1088.7	29.2
0°-40°	1592.3	42.6
0°-60°	2352.3	63.0
0°-90°	2692.0	72.1
90°-120°	479.1	12.8
90°-150°	907.4	24.3
90°-180°	1042.0	27.9
0°-180°	3734.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1557	1557	1557	1557	1557	
5°	1732	1561	1384	1561	1732	171
15°	1955	1481	916	1481	1955	527
25°	1043	1317	664	1317	1043	495
35°	514	1086	490	1086	514	329
45°	357	820	349	820	357	276
55°	248	557	244	557	248	217
65°	129	338	146	338	129	131
75°	68	161	78	161	68	72
85°	20	35	20	35	20	21
90°	10	0	10	0	10	6
95°	33	10	33	10	33	43
105°	325	35	325	35	325	314
115°	427	62	427	62	427	418
125°	347	86	347	86	347	313
135°	287	101	287	101	287	223
145°	229	116	229	116	229	146
155°	193	132	193	132	193	90
165°	169	144	169	144	169	48
175°	152	150	152	150	152	15
180°	150	150	150	150	150	



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1620.1	1621.4	1622.7	1619.6	1619.6	1617.1	1611.4	1607.1	1595.0	1593.3	1593.3
5°	1732.2	1731.0	1733.2	1726.2	1716.4	1714.3	1704.1	1690.5	1676.4	1660.8	1657.5
7.5°	1843.6	1841.9	1837.6	1836.5	1829.0	1812.7	1796.1	1778.5	1755.1	1732.3	1720.8
10°	1899.8	1917.7	1906.9	1887.9	1891.7	1866.3	1852.8	1829.5	1810.0	1776.0	1768.4
12.5°	1955.3	1962.3	1958.8	1948.1	1943.3	1925.6	1907.3	1887.1	1851.1	1820.6	1793.9
15°	1955.0	1965.3	1968.0	1964.8	1967.5	1966.4	1956.6	1939.8	1908.5	1874.9	1845.8
17.5°	1810.7	1817.9	1835.6	1847.5	1862.7	1894.8	1910.6	1916.7	1912.0	1892.9	1872.3
20°	1648.9	1637.0	1686.7	1712.1	1733.7	1787.9	1834.4	1852.3	1880.9	1880.4	1874.9
22.5°	1419.4	1422.3	1469.5	1499.7	1562.8	1616.9	1670.0	1737.2	1792.6	1829.3	1850.7
25°	1042.9	1063.6	1110.6	1151.7	1222.1	1322.7	1414.1	1520.1	1620.2	1699.2	1774.3
27.5°	783.3	784.8	822.1	860.1	901.9	984.3	1099.4	1226.0	1368.7	1486.5	1621.9
30°	670.8	667.6	683.2	706.5	742.2	806.0	892.6	1017.0	1159.3	1336.7	1494.7
32.5°	591.2	591.3	603.2	620.4	650.0	693.1	752.4	853.5	987.9	1162.3	1347.5
35°	513.9	513.4	522.0	534.4	546.9	574.5	615.1	668.1	760.6	923.4	1112.7
37.5°	458.5	460.9	465.1	472.9	486.7	502.0	526.4	562.0	627.9	724.1	883.3
40°	427.4	428.4	434.4	440.9	449.0	460.9	480.9	509.6	557.7	634.5	750.8
42.5°	398.8	399.9	404.1	410.2	416.5	428.4	445.0	469.8	508.8	568.8	664.7
45°	357.0	357.0	360.9	363.5	370.6	381.4	394.9	415.5	442.5	486.9	550.7
47.5°	317.9	318.0	320.5	325.1	329.5	338.0	351.3	368.1	387.8	422.1	476.6
50°	295.4	295.9	297.5	301.3	304.0	311.6	321.9	336.5	357.0	383.5	429.0
52.5°	277.2	276.9	278.9	280.5	282.4	287.8	295.5	308.3	326.8	349.8	387.4
55°	247.8	245.6	248.8	251.5	253.2	255.4	259.7	267.7	283.5	303.0	331.1
57.5°	211.0	210.1	212.4	214.8	220.0	225.8	229.5	234.6	242.8	256.7	284.6
60°	180.7	180.7	185.6	187.2	193.1	200.7	208.3	212.6	220.7	229.9	250.5
62.5°	153.8	154.3	156.5	158.2	161.5	170.8	181.4	190.9	198.6	207.4	221.0
65°	128.7	129.8	129.8	130.9	133.1	135.3	139.6	147.2	160.7	173.1	183.4
67.5°	109.3	109.6	109.9	111.0	111.5	113.9	115.7	119.0	122.1	134.0	146.7
70°	96.3	97.9	97.3	98.5	99.0	100.0	102.2	103.9	108.8	111.5	119.0
72.5°	84.1	85.4	85.3	85.9	87.3	87.6	89.3	90.9	94.0	96.3	100.4
75°	68.2	67.6	68.2	69.2	69.8	70.4	70.4	72.5	74.1	76.3	79.0
77.5°	52.6	53.2	53.0	53.2	53.2	54.2	54.1	55.0	56.7	57.8	59.1
80°	42.2	42.7	42.2	42.7	43.3	43.8	43.3	43.8	45.4	46.6	46.6
82.5°	32.7	32.8	33.1	33.2	33.3	33.4	34.2	34.3	35.5	35.3	35.7
85°	19.5	18.9	18.9	18.9	19.5	20.0	19.5	19.5	20.0	20.0	20.0
87.5°	8.8	9.3	9.3	9.3	9.3	9.2	9.0	9.6	9.3	9.8	9.3
90°	9.5	9.5	9.5	9.5	9.5	9.2	8.6	9.2	9.5	9.8	9.5
92.5°	16.0	16.4	16.2	17.1	17.4	19.2	21.5	25.1	31.6	37.4	36.9
95°	32.9	32.5	33.4	35.7	39.5	45.8	57.9	75.5	98.8	112.9	100.0
97.5°	64.7	67.1	71.3	78.4	92.1	112.9	144.1	176.1	202.2	192.7	145.2
100°	103.1	108.4	116.7	129.1	153.0	187.8	227.3	263.0	269.0	227.6	156.7
102.5°	181.5	188.5	198.9	220.0	246.1	283.0	311.9	319.9	293.9	228.7	152.3
105°	324.7	328.6	341.0	358.9	376.8	386.3	382.5	350.0	290.1	213.4	143.7
107.5°	414.7	420.0	422.6	423.5	421.3	407.3	377.4	328.3	264.8	197.1	139.5
110°	441.9	442.2	439.6	434.1	421.8	398.1	361.3	309.7	248.9	189.2	138.6



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	441.4	439.9	435.0	425.8	408.6	381.5	342.1	292.6	237.8	184.2	138.8
115°	427.2	424.6	417.1	403.9	383.4	353.8	316.0	271.7	224.1	178.6	140.0
117.5°	401.8	399.6	391.8	377.7	356.9	329.1	294.8	255.8	215.5	175.9	142.1
120°	385.5	382.5	374.2	360.7	340.5	314.3	283.7	248.0	210.8	174.3	143.5
122.5°	368.4	366.0	358.6	345.2	327.1	303.5	274.5	241.8	206.9	173.3	145.0
125°	346.6	344.2	337.0	326.1	309.4	287.8	262.4	232.8	201.4	171.7	147.5
127.5°	327.4	325.5	319.4	309.1	294.5	274.6	250.7	223.8	196.2	170.7	149.9
130°	316.6	314.3	308.5	298.7	284.6	265.6	242.9	218.1	192.7	170.2	151.8
132.5°	305.3	303.2	297.9	288.1	274.3	256.4	235.5	212.5	190.0	170.0	153.7
135°	287.2	286.1	280.9	271.3	258.9	242.9	223.8	204.8	186.1	169.7	155.9
137.5°	269.5	267.7	263.2	255.0	243.7	229.7	214.6	198.7	183.4	169.6	157.8
140°	257.2	255.5	251.2	243.7	234.5	221.8	208.6	194.7	181.7	169.4	158.7
142.5°	245.0	244.7	240.8	234.0	225.3	214.7	203.3	191.5	180.2	169.4	159.4
145°	229.3	228.4	225.6	220.6	213.8	205.4	196.5	186.9	178.1	168.8	160.1
147.5°	216.1	215.6	213.6	209.7	204.0	197.9	190.9	183.4	175.9	167.8	160.4
150°	208.3	208.0	206.3	202.8	198.4	193.3	187.3	180.9	174.0	167.1	160.1
152.5°	201.6	201.5	200.2	197.3	193.9	189.4	184.3	178.4	172.4	165.9	159.7
155°	192.7	193.3	192.2	190.1	186.9	183.8	179.4	174.9	169.4	163.9	159.0
157.5°	185.2	185.2	184.7	183.0	180.8	178.2	174.6	170.8	166.6	161.8	157.7
160°	180.3	180.3	180.0	178.6	176.6	174.6	171.4	168.2	164.4	160.5	157.0
162.5°	175.7	175.9	175.7	174.7	172.7	171.1	168.4	165.7	162.7	159.3	156.3
165°	169.1	169.4	169.4	168.2	167.1	165.9	163.9	161.9	159.6	157.0	155.0
167.5°	163.0	163.3	163.4	162.7	162.2	161.2	159.8	158.2	156.6	155.0	153.7
170°	159.3	159.9	160.1	159.3	159.0	158.4	157.3	156.5	155.0	153.8	153.0
172.5°	156.3	156.6	156.9	156.5	156.2	155.9	155.0	154.3	153.4	152.5	152.1
175°	152.4	153.0	153.3	153.0	153.0	152.7	152.4	152.1	151.2	150.9	150.7
177.5°	150.0	150.5	150.7	150.7	150.7	150.7	150.5	150.5	150.0	149.8	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331707-930
 CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1594.1	1590.6	1587.6	1579.8	1575.9	1567.2	1565.9	1565.5	1554.3	1543.4	1540.4
5°	1648.9	1640.2	1627.2	1612.1	1596.4	1580.1	1569.3	1560.6	1539.0	1518.5	1506.6
7.5°	1704.1	1685.4	1663.0	1634.3	1610.5	1583.6	1563.7	1545.8	1515.2	1485.7	1465.9
10°	1745.1	1714.8	1685.1	1645.6	1614.8	1584.5	1556.3	1532.0	1497.4	1458.4	1430.9
12.5°	1770.7	1737.3	1696.3	1657.7	1617.8	1579.2	1541.6	1510.3	1469.7	1429.5	1396.6
15°	1805.2	1769.4	1719.7	1664.5	1613.2	1562.8	1519.6	1480.6	1427.6	1379.4	1339.4
17.5°	1833.4	1784.3	1730.9	1667.0	1607.5	1543.6	1487.8	1438.1	1379.1	1321.0	1273.8
20°	1842.5	1793.8	1732.2	1668.3	1598.0	1522.8	1462.7	1408.7	1345.3	1282.1	1228.0
22.5°	1836.9	1799.0	1730.4	1654.0	1582.0	1503.3	1435.5	1372.7	1302.5	1238.0	1175.2
25°	1798.7	1785.7	1720.8	1637.4	1555.3	1463.9	1385.4	1316.7	1236.6	1167.4	1099.2
27.5°	1709.7	1737.6	1697.5	1608.7	1517.3	1419.3	1331.1	1252.9	1169.8	1091.8	1023.9
30°	1624.0	1688.3	1671.0	1588.8	1486.5	1390.2	1291.3	1209.6	1120.9	1040.8	973.7
32.5°	1506.7	1613.0	1629.9	1561.1	1455.4	1349.6	1245.9	1164.6	1072.0	987.6	922.2
35°	1320.0	1479.0	1552.0	1508.2	1402.2	1288.0	1180.9	1086.2	993.2	909.9	845.0
37.5°	1097.1	1313.8	1435.5	1438.6	1341.2	1222.5	1106.0	1011.9	916.7	834.9	764.7
40°	952.6	1187.4	1345.9	1381.0	1298.9	1170.6	1052.7	956.9	863.9	783.8	703.3
42.5°	822.8	1056.7	1251.6	1312.7	1247.3	1120.0	1001.7	901.6	811.1	735.4	653.1
45°	665.4	869.8	1084.6	1193.9	1157.6	1039.8	914.8	819.5	734.6	669.2	590.2
47.5°	561.3	705.4	913.2	1061.0	1060.4	952.8	829.8	738.7	659.8	598.5	534.6
50°	502.0	627.5	803.3	971.0	985.0	894.7	777.9	687.5	614.0	549.6	498.2
52.5°	448.7	552.2	710.3	871.1	911.1	832.8	719.5	636.1	564.7	505.5	461.5
55°	379.2	459.3	579.4	729.8	790.4	735.2	634.5	556.7	498.8	449.0	411.2
57.5°	320.8	380.8	477.2	598.3	668.9	634.1	551.1	487.9	438.3	393.3	363.4
60°	284.0	333.2	414.9	516.1	593.9	569.6	498.8	439.8	397.6	358.7	330.5
62.5°	249.4	291.7	361.7	443.8	515.2	505.2	447.3	397.8	360.9	325.3	301.5
65°	200.7	231.5	286.2	350.6	407.9	412.8	371.1	337.5	304.6	276.5	255.4
67.5°	159.8	179.9	218.4	272.6	315.6	330.9	305.5	279.9	253.7	232.0	213.7
70°	134.7	150.9	179.0	222.9	262.4	278.6	264.0	243.9	221.3	203.4	187.7
72.5°	109.2	125.0	145.7	177.9	211.7	229.3	224.2	209.8	191.4	176.6	161.8
75°	82.3	87.1	101.2	122.8	149.3	164.4	168.3	160.7	146.0	134.7	126.0
77.5°	60.8	63.8	70.4	81.8	99.1	112.6	118.1	117.2	107.2	100.6	92.5
80°	48.7	50.3	53.6	58.5	71.4	85.0	88.7	88.7	81.7	79.0	70.8
82.5°	37.0	38.2	40.1	42.8	48.9	60.7	64.9	65.8	61.3	57.8	51.4
85°	21.1	20.5	21.6	23.2	24.4	27.6	34.1	35.1	34.1	29.8	28.1
87.5°	8.9	9.0	8.6	8.1	8.4	8.7	10.6	12.6	11.1	9.9	9.2
90°	7.7	5.8	4.3	3.4	2.9	2.3	1.1	0.3	1.1	2.3	2.9
92.5°	28.8	19.6	13.0	10.4	8.4	7.2	5.1	3.5	5.1	7.2	8.4
95°	66.5	41.5	28.2	21.3	16.7	14.1	11.3	10.1	11.3	14.1	16.7
97.5°	89.7	54.7	38.1	30.2	24.9	21.0	17.9	16.4	17.9	21.0	24.9
100°	94.5	59.4	44.1	36.0	30.2	25.6	23.1	22.2	23.1	25.6	30.2
102.5°	94.7	63.5	49.4	41.3	35.3	30.7	28.1	27.5	28.1	30.7	35.3
105°	96.2	70.6	57.1	49.0	42.6	38.3	36.3	35.1	36.3	38.3	42.6
107.5°	100.2	77.9	64.7	56.6	50.3	46.3	44.4	43.5	44.4	46.3	50.3
110°	103.4	82.7	70.0	61.6	55.6	51.9	50.1	49.0	50.1	51.9	55.6



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	106.9	87.3	75.1	66.4	60.7	57.2	55.2	54.1	55.2	57.2	60.7
115°	112.0	94.5	82.1	74.4	68.6	65.1	63.3	62.0	63.3	65.1	68.6
117.5°	117.6	101.1	89.7	81.6	76.1	73.0	71.3	70.1	71.3	73.0	76.1
120°	121.3	105.7	94.5	86.4	80.6	78.1	76.3	75.2	76.3	78.1	80.6
122.5°	124.5	110.1	99.5	91.2	85.5	82.7	81.0	80.1	81.0	82.7	85.5
125°	129.6	116.7	106.3	98.2	92.5	89.0	87.3	86.4	87.3	89.0	92.5
127.5°	134.4	122.8	112.7	104.4	98.9	95.1	92.6	91.5	92.6	95.1	98.9
130°	137.4	126.5	116.3	108.4	102.6	98.5	95.6	94.5	95.6	98.5	102.6
132.5°	140.4	129.7	120.1	112.0	106.0	101.7	98.7	97.3	98.7	101.7	106.0
135°	144.3	134.3	125.0	117.0	110.3	106.0	102.6	101.4	102.6	106.0	110.3
137.5°	147.3	137.9	128.8	121.3	114.8	110.1	106.7	105.3	106.7	110.1	114.8
140°	149.0	140.0	131.3	123.8	117.6	112.9	109.5	108.4	109.5	112.9	117.6
142.5°	150.3	141.6	133.2	126.2	120.1	115.4	112.3	111.3	112.3	115.4	120.1
145°	152.1	144.1	136.2	130.0	124.2	119.8	117.0	115.8	117.0	119.8	124.2
147.5°	153.1	146.0	138.7	133.1	128.2	124.3	121.5	120.7	121.5	124.3	128.2
150°	153.5	146.9	140.3	135.1	130.8	127.0	124.7	123.8	124.7	127.0	130.8
152.5°	153.8	147.8	141.9	137.2	133.1	129.8	127.5	127.1	127.5	129.8	133.1
155°	154.1	149.2	144.3	140.0	136.8	133.6	131.9	131.7	131.9	133.6	136.8
157.5°	154.1	150.2	146.0	142.4	139.9	137.1	135.7	135.4	135.7	137.1	139.9
160°	154.1	150.7	147.2	144.1	141.7	139.4	138.3	137.9	138.3	139.4	141.7
162.5°	153.8	150.9	147.9	145.4	143.3	141.5	140.3	140.6	140.3	141.5	143.3
165°	153.3	151.2	148.6	146.9	145.4	143.7	143.2	143.5	143.2	143.7	145.4
167.5°	152.9	151.2	149.3	148.2	147.2	146.0	145.5	145.9	145.5	146.0	147.2
170°	152.4	150.9	149.5	148.6	148.1	147.2	146.9	147.5	146.9	147.2	148.1
172.5°	151.7	150.7	149.8	149.1	148.8	147.9	148.1	148.4	148.1	147.9	148.8
175°	150.9	150.3	149.8	149.5	149.5	149.0	149.2	149.5	149.2	149.0	149.5
177.5°	150.5	150.0	149.8	149.8	149.8	149.4	149.5	150.0	149.5	149.4	149.8
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1534.8	1531.8	1526.2	1517.5	1512.3	1503.2	1497.1	1500.6	1501.5	1500.6	1499.7
5°	1493.5	1482.2	1466.6	1451.4	1437.3	1422.2	1413.5	1409.7	1402.2	1397.8	1395.7
7.5°	1443.7	1424.2	1401.9	1375.6	1353.2	1329.7	1317.7	1311.7	1296.2	1287.8	1280.4
10°	1406.5	1375.7	1353.5	1318.8	1297.8	1266.9	1245.9	1246.3	1225.2	1213.3	1204.7
12.5°	1365.4	1331.5	1294.6	1263.5	1234.1	1209.3	1184.0	1173.6	1151.3	1139.8	1116.4
15°	1297.2	1257.8	1218.8	1176.6	1146.8	1108.4	1071.6	1026.7	990.5	959.1	950.5
17.5°	1222.8	1173.9	1134.8	1085.2	1034.3	969.7	927.1	901.0	879.1	862.6	850.3
20°	1171.7	1121.9	1080.3	1005.7	936.9	893.2	861.8	841.7	819.0	801.2	791.4
22.5°	1118.0	1066.1	1009.3	926.0	872.5	837.3	809.3	786.4	770.9	757.0	748.1
25°	1041.9	985.0	891.5	834.1	790.8	754.1	734.6	720.6	704.3	685.4	676.7
27.5°	961.4	871.1	803.9	761.2	719.9	696.0	678.5	657.5	642.9	634.5	625.4
30°	901.2	810.9	758.4	711.9	682.7	656.2	635.6	623.7	609.7	595.1	589.1
32.5°	834.1	762.0	711.7	672.9	643.3	620.7	604.5	585.2	575.0	566.1	553.6
35°	750.8	696.2	650.2	618.9	590.8	572.3	553.4	542.0	523.7	516.1	511.2
37.5°	680.3	632.9	598.6	565.5	543.2	522.9	511.3	493.3	485.3	474.7	464.5
40°	640.5	593.9	561.0	533.9	509.1	493.9	479.3	464.7	452.8	447.9	435.5
42.5°	599.8	562.0	529.0	499.3	482.7	466.6	448.2	437.4	425.1	417.2	409.5
45°	543.6	510.1	482.0	457.6	439.3	422.5	410.6	392.7	385.7	370.0	363.5
47.5°	494.3	463.2	436.3	413.2	395.3	384.3	366.9	352.9	341.7	332.1	323.7
50°	459.3	433.3	407.3	386.8	370.6	354.9	337.0	330.0	312.7	307.8	303.0
52.5°	427.2	402.6	378.8	358.7	342.4	327.2	311.4	302.3	290.6	285.8	282.2
55°	382.5	358.7	335.9	318.0	301.8	286.2	276.5	265.1	259.7	255.8	251.5
57.5°	337.5	316.0	298.6	280.5	264.2	251.8	240.5	233.7	228.0	223.1	217.9
60°	308.9	288.3	272.6	255.8	239.1	228.9	220.1	212.1	205.5	198.0	195.8
62.5°	278.6	260.7	246.2	229.9	215.3	205.9	197.6	190.0	182.2	171.1	168.1
65°	236.9	222.9	207.7	194.2	181.2	172.0	160.1	151.5	148.2	147.2	146.6
67.5°	199.3	186.0	173.0	159.1	147.3	138.8	132.7	131.4	129.1	128.5	127.0
70°	174.1	161.8	148.8	135.7	124.4	122.8	120.7	118.5	115.8	114.7	113.6
72.5°	151.6	138.8	125.8	115.4	110.6	108.5	106.3	104.2	102.3	101.3	100.6
75°	116.3	104.4	95.7	92.0	89.3	87.6	84.4	82.8	81.7	80.1	79.5
77.5°	83.7	77.0	73.1	70.7	67.8	66.1	64.2	62.6	61.5	61.1	60.3
80°	63.8	60.6	57.9	54.6	53.6	51.4	50.9	49.2	49.7	48.2	48.2
82.5°	49.6	45.4	43.1	41.7	40.6	38.8	38.3	37.5	37.7	36.4	36.4
85°	25.4	24.4	23.2	22.2	22.2	20.5	21.1	20.5	20.5	19.5	18.9
87.5°	8.9	8.6	8.1	8.5	8.8	8.5	8.4	7.9	7.8	7.9	7.5
90°	3.4	4.3	5.8	7.7	9.5	9.8	9.5	9.2	8.6	9.2	9.5
92.5°	10.4	13.0	19.6	28.8	36.9	37.4	31.6	25.1	21.5	19.2	17.4
95°	21.3	28.2	41.5	66.5	100.0	112.9	98.8	75.5	57.9	45.8	39.5
97.5°	30.2	38.1	54.7	89.7	145.2	192.7	202.2	176.1	144.1	112.9	92.1
100°	36.0	44.1	59.4	94.5	156.7	227.6	269.0	263.0	227.3	187.8	153.0
102.5°	41.3	49.4	63.5	94.7	152.3	228.7	293.9	319.9	311.9	283.0	246.1
105°	49.0	57.1	70.6	96.2	143.7	213.4	290.1	350.0	382.5	386.3	376.8
107.5°	56.6	64.7	77.9	100.2	139.5	197.1	264.8	328.3	377.4	407.3	421.3
110°	61.6	70.0	82.7	103.4	138.6	189.2	248.9	309.7	361.3	398.1	421.8



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	66.4	75.1	87.3	106.9	138.8	184.2	237.8	292.6	342.1	381.5	408.6
115°	74.4	82.1	94.5	112.0	140.0	178.6	224.1	271.7	316.0	353.8	383.4
117.5°	81.6	89.7	101.1	117.6	142.1	175.9	215.5	255.8	294.8	329.1	356.9
120°	86.4	94.5	105.7	121.3	143.5	174.3	210.8	248.0	283.7	314.3	340.5
122.5°	91.2	99.5	110.1	124.5	145.0	173.3	206.9	241.8	274.5	303.5	327.1
125°	98.2	106.3	116.7	129.6	147.5	171.7	201.4	232.8	262.4	287.8	309.4
127.5°	104.4	112.7	122.8	134.4	149.9	170.7	196.2	223.8	250.7	274.6	294.5
130°	108.4	116.3	126.5	137.4	151.8	170.2	192.7	218.1	242.9	265.6	284.6
132.5°	112.0	120.1	129.7	140.4	153.7	170.0	190.0	212.5	235.5	256.4	274.3
135°	117.0	125.0	134.3	144.3	155.9	169.7	186.1	204.8	223.8	242.9	258.9
137.5°	121.3	128.8	137.9	147.3	157.8	169.6	183.4	198.7	214.6	229.7	243.7
140°	123.8	131.3	140.0	149.0	158.7	169.4	181.7	194.7	208.6	221.8	234.5
142.5°	126.2	133.2	141.6	150.3	159.4	169.4	180.2	191.5	203.3	214.7	225.3
145°	130.0	136.2	144.1	152.1	160.1	168.8	178.1	186.9	196.5	205.4	213.8
147.5°	133.1	138.7	146.0	153.1	160.4	167.8	175.9	183.4	190.9	197.9	204.0
150°	135.1	140.3	146.9	153.5	160.1	167.1	174.0	180.9	187.3	193.3	198.4
152.5°	137.2	141.9	147.8	153.8	159.7	165.9	172.4	178.4	184.3	189.4	193.9
155°	140.0	144.3	149.2	154.1	159.0	163.9	169.4	174.9	179.4	183.8	186.9
157.5°	142.4	146.0	150.2	154.1	157.7	161.8	166.6	170.8	174.6	178.2	180.8
160°	144.1	147.2	150.7	154.1	157.0	160.5	164.4	168.2	171.4	174.6	176.6
162.5°	145.4	147.9	150.9	153.8	156.3	159.3	162.7	165.7	168.4	171.1	172.7
165°	146.9	148.6	151.2	153.3	155.0	157.0	159.6	161.9	163.9	165.9	167.1
167.5°	148.2	149.3	151.2	152.9	153.7	155.0	156.6	158.2	159.8	161.2	162.2
170°	148.6	149.5	150.9	152.4	153.0	153.8	155.0	156.5	157.3	158.4	159.0
172.5°	149.1	149.8	150.7	151.7	152.1	152.5	153.4	154.3	155.0	155.9	156.2
175°	149.5	149.8	150.3	150.9	150.7	150.9	151.2	152.1	152.4	152.7	153.0
177.5°	149.8	149.8	150.0	150.5	150.0	149.8	150.0	150.5	150.5	150.7	150.7
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331707-930
 CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1495.0	1495.8	1494.5	1495.4	1494.5	1495.8	1495.0	1499.7	1500.6	1501.5	1500.6
5°	1392.9	1386.5	1385.4	1383.8	1385.4	1386.5	1392.9	1395.7	1397.8	1402.2	1409.7
7.5°	1271.1	1270.2	1267.5	1263.7	1267.5	1270.2	1271.1	1280.4	1287.8	1296.2	1311.7
10°	1192.8	1190.1	1189.6	1185.8	1189.6	1190.1	1192.8	1204.7	1213.3	1225.2	1246.3
12.5°	1101.1	1083.6	1081.8	1072.4	1081.8	1083.6	1101.1	1116.4	1139.8	1151.3	1173.6
15°	937.5	934.3	923.4	916.4	923.4	934.3	937.5	950.5	959.1	990.5	1026.7
17.5°	844.0	833.4	830.1	828.5	830.1	833.4	844.0	850.3	862.6	879.1	901.0
20°	783.8	774.1	772.5	771.4	772.5	774.1	783.8	791.4	801.2	819.0	841.7
22.5°	742.3	732.1	727.9	724.6	727.9	732.1	742.3	748.1	757.0	770.9	786.4
25°	671.3	667.6	665.4	664.3	665.4	667.6	671.3	676.7	685.4	704.3	720.6
27.5°	615.8	607.5	605.8	603.1	605.8	607.5	615.8	625.4	634.5	642.9	657.5
30°	584.2	581.6	577.7	574.5	577.7	581.6	584.2	589.1	595.1	609.7	623.7
32.5°	547.0	544.8	541.4	539.9	541.4	544.8	547.0	553.6	566.1	575.0	585.2
35°	505.8	498.2	495.0	490.1	495.0	498.2	505.8	511.2	516.1	523.7	542.0
37.5°	462.2	458.2	453.6	455.3	453.6	458.2	462.2	464.5	474.7	485.3	493.3
40°	428.4	425.7	424.7	424.1	424.7	425.7	428.4	435.5	447.9	452.8	464.7
42.5°	401.6	394.1	391.3	391.2	391.3	394.1	401.6	409.5	417.2	425.1	437.4
45°	360.9	353.8	348.9	349.4	348.9	353.8	360.9	363.5	370.0	385.7	392.7
47.5°	319.0	318.9	315.8	316.8	315.8	318.9	319.0	323.7	332.1	341.7	352.9
50°	299.1	295.9	293.8	294.2	293.8	295.9	299.1	303.0	307.8	312.7	330.0
52.5°	280.1	277.3	275.6	277.9	275.6	277.3	280.1	282.2	285.8	290.6	302.3
55°	248.8	245.6	245.1	244.5	245.1	245.6	248.8	251.5	255.8	259.7	265.1
57.5°	213.9	211.7	208.5	207.1	208.5	211.7	213.9	217.9	223.1	228.0	233.7
60°	188.8	184.5	179.0	178.6	179.0	184.5	188.8	195.8	198.0	205.5	212.1
62.5°	165.8	165.0	163.9	163.8	163.9	165.0	165.8	168.1	171.1	182.2	190.0
65°	145.5	145.0	145.5	146.0	145.5	145.0	145.5	146.6	147.2	148.2	151.5
67.5°	126.8	125.8	124.8	125.3	124.8	125.8	126.8	127.0	128.5	129.1	131.4
70°	112.5	111.9	111.5	111.5	111.5	111.9	112.5	113.6	114.7	115.8	118.5
72.5°	98.7	98.6	98.0	97.6	98.0	98.6	98.7	100.6	101.3	102.3	104.2
75°	79.0	77.9	77.9	77.9	77.9	77.9	79.0	79.5	80.1	81.7	82.8
77.5°	60.2	59.6	59.1	58.6	59.1	59.6	60.2	60.3	61.1	61.5	62.6
80°	47.6	47.0	46.6	46.6	46.6	47.0	47.6	48.2	48.2	49.7	49.2
82.5°	36.4	35.8	35.7	35.3	35.7	35.8	36.4	36.4	36.4	37.7	37.5
85°	19.5	20.0	19.5	20.5	19.5	20.0	19.5	18.9	19.5	20.5	20.5
87.5°	7.5	7.1	7.5	7.1	7.5	7.1	7.5	7.5	7.9	7.8	7.9
90°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.2	8.6	9.2
92.5°	17.1	16.2	16.4	16.0	16.4	16.2	17.1	17.4	19.2	21.5	25.1
95°	35.7	33.4	32.5	32.9	32.5	33.4	35.7	39.5	45.8	57.9	75.5
97.5°	78.4	71.3	67.1	64.7	67.1	71.3	78.4	92.1	112.9	144.1	176.1
100°	129.1	116.7	108.4	103.1	108.4	116.7	129.1	153.0	187.8	227.3	263.0
102.5°	220.0	198.9	188.5	181.5	188.5	198.9	220.0	246.1	283.0	311.9	319.9
105°	358.9	341.0	328.6	324.7	328.6	341.0	358.9	376.8	386.3	382.5	350.0
107.5°	423.5	422.6	420.0	414.7	420.0	422.6	423.5	421.3	407.3	377.4	328.3
110°	434.1	439.6	442.2	441.9	442.2	439.6	434.1	421.8	398.1	361.3	309.7



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	425.8	435.0	439.9	441.4	439.9	435.0	425.8	408.6	381.5	342.1	292.6
115°	403.9	417.1	424.6	427.2	424.6	417.1	403.9	383.4	353.8	316.0	271.7
117.5°	377.7	391.8	399.6	401.8	399.6	391.8	377.7	356.9	329.1	294.8	255.8
120°	360.7	374.2	382.5	385.5	382.5	374.2	360.7	340.5	314.3	283.7	248.0
122.5°	345.2	358.6	366.0	368.4	366.0	358.6	345.2	327.1	303.5	274.5	241.8
125°	326.1	337.0	344.2	346.6	344.2	337.0	326.1	309.4	287.8	262.4	232.8
127.5°	309.1	319.4	325.5	327.4	325.5	319.4	309.1	294.5	274.6	250.7	223.8
130°	298.7	308.5	314.3	316.6	314.3	308.5	298.7	284.6	265.6	242.9	218.1
132.5°	288.1	297.9	303.2	305.3	303.2	297.9	288.1	274.3	256.4	235.5	212.5
135°	271.3	280.9	286.1	287.2	286.1	280.9	271.3	258.9	242.9	223.8	204.8
137.5°	255.0	263.2	267.7	269.5	267.7	263.2	255.0	243.7	229.7	214.6	198.7
140°	243.7	251.2	255.5	257.2	255.5	251.2	243.7	234.5	221.8	208.6	194.7
142.5°	234.0	240.8	244.7	245.0	244.7	240.8	234.0	225.3	214.7	203.3	191.5
145°	220.6	225.6	228.4	229.3	228.4	225.6	220.6	213.8	205.4	196.5	186.9
147.5°	209.7	213.6	215.6	216.1	215.6	213.6	209.7	204.0	197.9	190.9	183.4
150°	202.8	206.3	208.0	208.3	208.0	206.3	202.8	198.4	193.3	187.3	180.9
152.5°	197.3	200.2	201.5	201.6	201.5	200.2	197.3	193.9	189.4	184.3	178.4
155°	190.1	192.2	193.3	192.7	193.3	192.2	190.1	186.9	183.8	179.4	174.9
157.5°	183.0	184.7	185.2	185.2	185.2	184.7	183.0	180.8	178.2	174.6	170.8
160°	178.6	180.0	180.3	180.3	180.3	180.0	178.6	176.6	174.6	171.4	168.2
162.5°	174.7	175.7	175.9	175.7	175.9	175.7	174.7	172.7	171.1	168.4	165.7
165°	168.2	169.4	169.4	169.1	169.4	169.4	168.2	167.1	165.9	163.9	161.9
167.5°	162.7	163.4	163.3	163.0	163.3	163.4	162.7	162.2	161.2	159.8	158.2
170°	159.3	160.1	159.9	159.3	159.9	160.1	159.3	159.0	158.4	157.3	156.5
172.5°	156.5	156.9	156.6	156.3	156.6	156.9	156.5	156.2	155.9	155.0	154.3
175°	153.0	153.3	153.0	152.4	153.0	153.3	153.0	153.0	152.7	152.4	152.1
177.5°	150.7	150.7	150.5	150.0	150.5	150.7	150.7	150.7	150.7	150.5	150.5
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1497.1	1503.2	1512.3	1517.5	1526.2	1531.8	1534.8	1540.4	1543.4	1554.3	1565.5
5°	1413.5	1422.2	1437.3	1451.4	1466.6	1482.2	1493.5	1506.6	1518.5	1539.0	1560.6
7.5°	1317.7	1329.7	1353.2	1375.6	1401.9	1424.2	1443.7	1465.9	1485.7	1515.2	1545.8
10°	1245.9	1266.9	1297.8	1318.8	1353.5	1375.7	1406.5	1430.9	1458.4	1497.4	1532.0
12.5°	1184.0	1209.3	1234.1	1263.5	1294.6	1331.5	1365.4	1396.6	1429.5	1469.7	1510.3
15°	1071.6	1108.4	1146.8	1176.6	1218.8	1257.8	1297.2	1339.4	1379.4	1427.6	1480.6
17.5°	927.1	969.7	1034.3	1085.2	1134.8	1173.9	1222.8	1273.8	1321.0	1379.1	1438.1
20°	861.8	893.2	936.9	1005.7	1080.3	1121.9	1171.7	1228.0	1282.1	1345.3	1408.7
22.5°	809.3	837.3	872.5	926.0	1009.3	1066.1	1118.0	1175.2	1238.0	1302.5	1372.7
25°	734.6	754.1	790.8	834.1	891.5	985.0	1041.9	1099.2	1167.4	1236.6	1316.7
27.5°	678.5	696.0	719.9	761.2	803.9	871.1	961.4	1023.9	1091.8	1169.8	1252.9
30°	635.6	656.2	682.7	711.9	758.4	810.9	901.2	973.7	1040.8	1120.9	1209.6
32.5°	604.5	620.7	643.3	672.9	711.7	762.0	834.1	922.2	987.6	1072.0	1164.6
35°	553.4	572.3	590.8	618.9	650.2	696.2	750.8	845.0	909.9	993.2	1086.2
37.5°	511.3	522.9	543.2	565.5	598.6	632.9	680.3	764.7	834.9	916.7	1011.9
40°	479.3	493.9	509.1	533.9	561.0	593.9	640.5	703.3	783.8	863.9	956.9
42.5°	448.2	466.6	482.7	499.3	529.0	562.0	599.8	653.1	735.4	811.1	901.6
45°	410.6	422.5	439.3	457.6	482.0	510.1	543.6	590.2	669.2	734.6	819.5
47.5°	366.9	384.3	395.3	413.2	436.3	463.2	494.3	534.6	598.5	659.8	738.7
50°	337.0	354.9	370.6	386.8	407.3	433.3	459.3	498.2	549.6	614.0	687.5
52.5°	311.4	327.2	342.4	358.7	378.8	402.6	427.2	461.5	505.5	564.7	636.1
55°	276.5	286.2	301.8	318.0	335.9	358.7	382.5	411.2	449.0	498.8	556.7
57.5°	240.5	251.8	264.2	280.5	298.6	316.0	337.5	363.4	393.3	438.3	487.9
60°	220.1	228.9	239.1	255.8	272.6	288.3	308.9	330.5	358.7	397.6	439.8
62.5°	197.6	205.9	215.3	229.9	246.2	260.7	278.6	301.5	325.3	360.9	397.8
65°	160.1	172.0	181.2	194.2	207.7	222.9	236.9	255.4	276.5	304.6	337.5
67.5°	132.7	138.8	147.3	159.1	173.0	186.0	199.3	213.7	232.0	253.7	279.9
70°	120.7	122.8	124.4	135.7	148.8	161.8	174.1	187.7	203.4	221.3	243.9
72.5°	106.3	108.5	110.6	115.4	125.8	138.8	151.6	161.8	176.6	191.4	209.8
75°	84.4	87.6	89.3	92.0	95.7	104.4	116.3	126.0	134.7	146.0	160.7
77.5°	64.2	66.1	67.8	70.7	73.1	77.0	83.7	92.5	100.6	107.2	117.2
80°	50.9	51.4	53.6	54.6	57.9	60.6	63.8	70.8	79.0	81.7	88.7
82.5°	38.3	38.8	40.6	41.7	43.1	45.4	49.6	51.4	57.8	61.3	65.8
85°	21.1	20.5	22.2	22.2	23.2	24.4	25.4	28.1	29.8	34.1	35.1
87.5°	8.4	8.5	8.8	8.5	8.1	8.6	8.9	9.2	9.9	11.1	12.6
90°	9.5	9.8	9.5	7.7	5.8	4.3	3.4	2.9	2.3	1.1	0.3
92.5°	31.6	37.4	36.9	28.8	19.6	13.0	10.4	8.4	7.2	5.1	3.5
95°	98.8	112.9	100.0	66.5	41.5	28.2	21.3	16.7	14.1	11.3	10.1
97.5°	202.2	192.7	145.2	89.7	54.7	38.1	30.2	24.9	21.0	17.9	16.4
100°	269.0	227.6	156.7	94.5	59.4	44.1	36.0	30.2	25.6	23.1	22.2
102.5°	293.9	228.7	152.3	94.7	63.5	49.4	41.3	35.3	30.7	28.1	27.5
105°	290.1	213.4	143.7	96.2	70.6	57.1	49.0	42.6	38.3	36.3	35.1
107.5°	264.8	197.1	139.5	100.2	77.9	64.7	56.6	50.3	46.3	44.4	43.5
110°	248.9	189.2	138.6	103.4	82.7	70.0	61.6	55.6	51.9	50.1	49.0



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	237.8	184.2	138.8	106.9	87.3	75.1	66.4	60.7	57.2	55.2	54.1
115°	224.1	178.6	140.0	112.0	94.5	82.1	74.4	68.6	65.1	63.3	62.0
117.5°	215.5	175.9	142.1	117.6	101.1	89.7	81.6	76.1	73.0	71.3	70.1
120°	210.8	174.3	143.5	121.3	105.7	94.5	86.4	80.6	78.1	76.3	75.2
122.5°	206.9	173.3	145.0	124.5	110.1	99.5	91.2	85.5	82.7	81.0	80.1
125°	201.4	171.7	147.5	129.6	116.7	106.3	98.2	92.5	89.0	87.3	86.4
127.5°	196.2	170.7	149.9	134.4	122.8	112.7	104.4	98.9	95.1	92.6	91.5
130°	192.7	170.2	151.8	137.4	126.5	116.3	108.4	102.6	98.5	95.6	94.5
132.5°	190.0	170.0	153.7	140.4	129.7	120.1	112.0	106.0	101.7	98.7	97.3
135°	186.1	169.7	155.9	144.3	134.3	125.0	117.0	110.3	106.0	102.6	101.4
137.5°	183.4	169.6	157.8	147.3	137.9	128.8	121.3	114.8	110.1	106.7	105.3
140°	181.7	169.4	158.7	149.0	140.0	131.3	123.8	117.6	112.9	109.5	108.4
142.5°	180.2	169.4	159.4	150.3	141.6	133.2	126.2	120.1	115.4	112.3	111.3
145°	178.1	168.8	160.1	152.1	144.1	136.2	130.0	124.2	119.8	117.0	115.8
147.5°	175.9	167.8	160.4	153.1	146.0	138.7	133.1	128.2	124.3	121.5	120.7
150°	174.0	167.1	160.1	153.5	146.9	140.3	135.1	130.8	127.0	124.7	123.8
152.5°	172.4	165.9	159.7	153.8	147.8	141.9	137.2	133.1	129.8	127.5	127.1
155°	169.4	163.9	159.0	154.1	149.2	144.3	140.0	136.8	133.6	131.9	131.7
157.5°	166.6	161.8	157.7	154.1	150.2	146.0	142.4	139.9	137.1	135.7	135.4
160°	164.4	160.5	157.0	154.1	150.7	147.2	144.1	141.7	139.4	138.3	137.9
162.5°	162.7	159.3	156.3	153.8	150.9	147.9	145.4	143.3	141.5	140.3	140.6
165°	159.6	157.0	155.0	153.3	151.2	148.6	146.9	145.4	143.7	143.2	143.5
167.5°	156.6	155.0	153.7	152.9	151.2	149.3	148.2	147.2	146.0	145.5	145.9
170°	155.0	153.8	153.0	152.4	150.9	149.5	148.6	148.1	147.2	146.9	147.5
172.5°	153.4	152.5	152.1	151.7	150.7	149.8	149.1	148.8	147.9	148.1	148.4
175°	151.2	150.9	150.7	150.9	150.3	149.8	149.5	149.5	149.0	149.2	149.5
177.5°	150.0	149.8	150.0	150.5	150.0	149.8	149.8	149.8	149.8	149.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1565.9	1567.2	1575.9	1579.8	1587.6	1590.6	1594.1	1593.3	1593.3	1595.0	1607.1
5°	1569.3	1580.1	1596.4	1612.1	1627.2	1640.2	1648.9	1657.5	1660.8	1676.4	1690.5
7.5°	1563.7	1583.6	1610.5	1634.3	1663.0	1685.4	1704.1	1720.8	1732.3	1755.1	1778.5
10°	1556.3	1584.5	1614.8	1645.6	1685.1	1714.8	1745.1	1768.4	1776.0	1810.0	1829.5
12.5°	1541.6	1579.2	1617.8	1657.7	1696.3	1737.3	1770.7	1793.9	1820.6	1851.1	1887.1
15°	1519.6	1562.8	1613.2	1664.5	1719.7	1769.4	1805.2	1845.8	1874.9	1908.5	1939.8
17.5°	1487.8	1543.6	1607.5	1667.0	1730.9	1784.3	1833.4	1872.3	1892.9	1912.0	1916.7
20°	1462.7	1522.8	1598.0	1668.3	1732.2	1793.8	1842.5	1874.9	1880.4	1880.9	1852.3
22.5°	1435.5	1503.3	1582.0	1654.0	1730.4	1799.0	1836.9	1850.7	1829.3	1792.6	1737.2
25°	1385.4	1463.9	1555.3	1637.4	1720.8	1785.7	1798.7	1774.3	1699.2	1620.2	1520.1
27.5°	1331.1	1419.3	1517.3	1608.7	1697.5	1737.6	1709.7	1621.9	1486.5	1368.7	1226.0
30°	1291.3	1390.2	1486.5	1588.8	1671.0	1688.3	1624.0	1494.7	1336.7	1159.3	1017.0
32.5°	1245.9	1349.6	1455.4	1561.1	1629.9	1613.0	1506.7	1347.5	1162.3	987.9	853.5
35°	1180.9	1288.0	1402.2	1508.2	1552.0	1479.0	1320.0	1112.7	923.4	760.6	668.1
37.5°	1106.0	1222.5	1341.2	1438.6	1435.5	1313.8	1097.1	883.3	724.1	627.9	562.0
40°	1052.7	1170.6	1298.9	1381.0	1345.9	1187.4	952.6	750.8	634.5	557.7	509.6
42.5°	1001.7	1120.0	1247.3	1312.7	1251.6	1056.7	822.8	664.7	568.8	508.8	469.8
45°	914.8	1039.8	1157.6	1193.9	1084.6	869.8	665.4	550.7	486.9	442.5	415.5
47.5°	829.8	952.8	1060.4	1061.0	913.2	705.4	561.3	476.6	422.1	387.8	368.1
50°	777.9	894.7	985.0	971.0	803.3	627.5	502.0	429.0	383.5	357.0	336.5
52.5°	719.5	832.8	911.1	871.1	710.3	552.2	448.7	387.4	349.8	326.8	308.3
55°	634.5	735.2	790.4	729.8	579.4	459.3	379.2	331.1	303.0	283.5	267.7
57.5°	551.1	634.1	668.9	598.3	477.2	380.8	320.8	284.6	256.7	242.8	234.6
60°	498.8	569.6	593.9	516.1	414.9	333.2	284.0	250.5	229.9	220.7	212.6
62.5°	447.3	505.2	515.2	443.8	361.7	291.7	249.4	221.0	207.4	198.6	190.9
65°	371.1	412.8	407.9	350.6	286.2	231.5	200.7	183.4	173.1	160.7	147.2
67.5°	305.5	330.9	315.6	272.6	218.4	179.9	159.8	146.7	134.0	122.1	119.0
70°	264.0	278.6	262.4	222.9	179.0	150.9	134.7	119.0	111.5	108.8	103.9
72.5°	224.2	229.3	211.7	177.9	145.7	125.0	109.2	100.4	96.3	94.0	90.9
75°	168.3	164.4	149.3	122.8	101.2	87.1	82.3	79.0	76.3	74.1	72.5
77.5°	118.1	112.6	99.1	81.8	70.4	63.8	60.8	59.1	57.8	56.7	55.0
80°	88.7	85.0	71.4	58.5	53.6	50.3	48.7	46.6	46.6	45.4	43.8
82.5°	64.9	60.7	48.9	42.8	40.1	38.2	37.0	35.7	35.3	35.5	34.3
85°	34.1	27.6	24.4	23.2	21.6	20.5	21.1	20.0	20.0	20.0	19.5
87.5°	10.6	8.7	8.4	8.1	8.6	9.0	8.9	9.3	9.8	9.3	9.6
90°	1.1	2.3	2.9	3.4	4.3	5.8	7.7	9.5	9.8	9.5	9.2
92.5°	5.1	7.2	8.4	10.4	13.0	19.6	28.8	36.9	37.4	31.6	25.1
95°	11.3	14.1	16.7	21.3	28.2	41.5	66.5	100.0	112.9	98.8	75.5
97.5°	17.9	21.0	24.9	30.2	38.1	54.7	89.7	145.2	192.7	202.2	176.1
100°	23.1	25.6	30.2	36.0	44.1	59.4	94.5	156.7	227.6	269.0	263.0
102.5°	28.1	30.7	35.3	41.3	49.4	63.5	94.7	152.3	228.7	293.9	319.9
105°	36.3	38.3	42.6	49.0	57.1	70.6	96.2	143.7	213.4	290.1	350.0
107.5°	44.4	46.3	50.3	56.6	64.7	77.9	100.2	139.5	197.1	264.8	328.3
110°	50.1	51.9	55.6	61.6	70.0	82.7	103.4	138.6	189.2	248.9	309.7



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	55.2	57.2	60.7	66.4	75.1	87.3	106.9	138.8	184.2	237.8	292.6
115°	63.3	65.1	68.6	74.4	82.1	94.5	112.0	140.0	178.6	224.1	271.7
117.5°	71.3	73.0	76.1	81.6	89.7	101.1	117.6	142.1	175.9	215.5	255.8
120°	76.3	78.1	80.6	86.4	94.5	105.7	121.3	143.5	174.3	210.8	248.0
122.5°	81.0	82.7	85.5	91.2	99.5	110.1	124.5	145.0	173.3	206.9	241.8
125°	87.3	89.0	92.5	98.2	106.3	116.7	129.6	147.5	171.7	201.4	232.8
127.5°	92.6	95.1	98.9	104.4	112.7	122.8	134.4	149.9	170.7	196.2	223.8
130°	95.6	98.5	102.6	108.4	116.3	126.5	137.4	151.8	170.2	192.7	218.1
132.5°	98.7	101.7	106.0	112.0	120.1	129.7	140.4	153.7	170.0	190.0	212.5
135°	102.6	106.0	110.3	117.0	125.0	134.3	144.3	155.9	169.7	186.1	204.8
137.5°	106.7	110.1	114.8	121.3	128.8	137.9	147.3	157.8	169.6	183.4	198.7
140°	109.5	112.9	117.6	123.8	131.3	140.0	149.0	158.7	169.4	181.7	194.7
142.5°	112.3	115.4	120.1	126.2	133.2	141.6	150.3	159.4	169.4	180.2	191.5
145°	117.0	119.8	124.2	130.0	136.2	144.1	152.1	160.1	168.8	178.1	186.9
147.5°	121.5	124.3	128.2	133.1	138.7	146.0	153.1	160.4	167.8	175.9	183.4
150°	124.7	127.0	130.8	135.1	140.3	146.9	153.5	160.1	167.1	174.0	180.9
152.5°	127.5	129.8	133.1	137.2	141.9	147.8	153.8	159.7	165.9	172.4	178.4
155°	131.9	133.6	136.8	140.0	144.3	149.2	154.1	159.0	163.9	169.4	174.9
157.5°	135.7	137.1	139.9	142.4	146.0	150.2	154.1	157.7	161.8	166.6	170.8
160°	138.3	139.4	141.7	144.1	147.2	150.7	154.1	157.0	160.5	164.4	168.2
162.5°	140.3	141.5	143.3	145.4	147.9	150.9	153.8	156.3	159.3	162.7	165.7
165°	143.2	143.7	145.4	146.9	148.6	151.2	153.3	155.0	157.0	159.6	161.9
167.5°	145.5	146.0	147.2	148.2	149.3	151.2	152.9	153.7	155.0	156.6	158.2
170°	146.9	147.2	148.1	148.6	149.5	150.9	152.4	153.0	153.8	155.0	156.5
172.5°	148.1	147.9	148.8	149.1	149.8	150.7	151.7	152.1	152.5	153.4	154.3
175°	149.2	149.0	149.5	149.5	149.8	150.3	150.9	150.7	150.9	151.2	152.1
177.5°	149.5	149.4	149.8	149.8	149.8	150.0	150.5	150.0	149.8	150.0	150.5
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331707-930
 CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1611.4	1617.1	1619.6	1619.6	1622.7	1621.4	1620.1
5°	1704.1	1714.3	1716.4	1726.2	1733.2	1731.0	1732.2
7.5°	1796.1	1812.7	1829.0	1836.5	1837.6	1841.9	1843.6
10°	1852.8	1866.3	1891.7	1887.9	1906.9	1917.7	1899.8
12.5°	1907.3	1925.6	1943.3	1948.1	1958.8	1962.3	1955.3
15°	1956.6	1966.4	1967.5	1964.8	1968.0	1965.3	1955.0
17.5°	1910.6	1894.8	1862.7	1847.5	1835.6	1817.9	1810.7
20°	1834.4	1787.9	1733.7	1712.1	1686.7	1637.0	1648.9
22.5°	1670.0	1616.9	1562.8	1499.7	1469.5	1422.3	1419.4
25°	1414.1	1322.7	1222.1	1151.7	1110.6	1063.6	1042.9
27.5°	1099.4	984.3	901.9	860.1	822.1	784.8	783.3
30°	892.6	806.0	742.2	706.5	683.2	667.6	670.8
32.5°	752.4	693.1	650.0	620.4	603.2	591.3	591.2
35°	615.1	574.5	546.9	534.4	522.0	513.4	513.9
37.5°	526.4	502.0	486.7	472.9	465.1	460.9	458.5
40°	480.9	460.9	449.0	440.9	434.4	428.4	427.4
42.5°	445.0	428.4	416.5	410.2	404.1	399.9	398.8
45°	394.9	381.4	370.6	363.5	360.9	357.0	357.0
47.5°	351.3	338.0	329.5	325.1	320.5	318.0	317.9
50°	321.9	311.6	304.0	301.3	297.5	295.9	295.4
52.5°	295.5	287.8	282.4	280.5	278.9	276.9	277.2
55°	259.7	255.4	253.2	251.5	248.8	245.6	247.8
57.5°	229.5	225.8	220.0	214.8	212.4	210.1	211.0
60°	208.3	200.7	193.1	187.2	185.6	180.7	180.7
62.5°	181.4	170.8	161.5	158.2	156.5	154.3	153.8
65°	139.6	135.3	133.1	130.9	129.8	129.8	128.7
67.5°	115.7	113.9	111.5	111.0	109.9	109.6	109.3
70°	102.2	100.0	99.0	98.5	97.3	97.9	96.3
72.5°	89.3	87.6	87.3	85.9	85.3	85.4	84.1
75°	70.4	70.4	69.8	69.2	68.2	67.6	68.2
77.5°	54.1	54.2	53.2	53.2	53.0	53.2	52.6
80°	43.3	43.8	43.3	42.7	42.2	42.7	42.2
82.5°	34.2	33.4	33.3	33.2	33.1	32.8	32.7
85°	19.5	20.0	19.5	18.9	18.9	18.9	19.5
87.5°	9.0	9.2	9.3	9.3	9.3	9.3	8.8
90°	8.6	9.2	9.5	9.5	9.5	9.5	9.5
92.5°	21.5	19.2	17.4	17.1	16.2	16.4	16.0
95°	57.9	45.8	39.5	35.7	33.4	32.5	32.9
97.5°	144.1	112.9	92.1	78.4	71.3	67.1	64.7
100°	227.3	187.8	153.0	129.1	116.7	108.4	103.1
102.5°	311.9	283.0	246.1	220.0	198.9	188.5	181.5
105°	382.5	386.3	376.8	358.9	341.0	328.6	324.7
107.5°	377.4	407.3	421.3	423.5	422.6	420.0	414.7
110°	361.3	398.1	421.8	434.1	439.6	442.2	441.9



TEST NUMBER: P331707-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	342.1	381.5	408.6	425.8	435.0	439.9	441.4
115°	316.0	353.8	383.4	403.9	417.1	424.6	427.2
117.5°	294.8	329.1	356.9	377.7	391.8	399.6	401.8
120°	283.7	314.3	340.5	360.7	374.2	382.5	385.5
122.5°	274.5	303.5	327.1	345.2	358.6	366.0	368.4
125°	262.4	287.8	309.4	326.1	337.0	344.2	346.6
127.5°	250.7	274.6	294.5	309.1	319.4	325.5	327.4
130°	242.9	265.6	284.6	298.7	308.5	314.3	316.6
132.5°	235.5	256.4	274.3	288.1	297.9	303.2	305.3
135°	223.8	242.9	258.9	271.3	280.9	286.1	287.2
137.5°	214.6	229.7	243.7	255.0	263.2	267.7	269.5
140°	208.6	221.8	234.5	243.7	251.2	255.5	257.2
142.5°	203.3	214.7	225.3	234.0	240.8	244.7	245.0
145°	196.5	205.4	213.8	220.6	225.6	228.4	229.3
147.5°	190.9	197.9	204.0	209.7	213.6	215.6	216.1
150°	187.3	193.3	198.4	202.8	206.3	208.0	208.3
152.5°	184.3	189.4	193.9	197.3	200.2	201.5	201.6
155°	179.4	183.8	186.9	190.1	192.2	193.3	192.7
157.5°	174.6	178.2	180.8	183.0	184.7	185.2	185.2
160°	171.4	174.6	176.6	178.6	180.0	180.3	180.3
162.5°	168.4	171.1	172.7	174.7	175.7	175.9	175.7
165°	163.9	165.9	167.1	168.2	169.4	169.4	169.1
167.5°	159.8	161.2	162.2	162.7	163.4	163.3	163.0
170°	157.3	158.4	159.0	159.3	160.1	159.9	159.3
172.5°	155.0	155.9	156.2	156.5	156.9	156.6	156.3
175°	152.4	152.7	153.0	153.0	153.3	153.0	152.4
177.5°	150.5	150.7	150.7	150.7	150.7	150.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8

(END OF REPORT)