

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331260

Luminaire Tested: **SA2XXDIP-C290D725U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331260
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4136.3 lumens
Efficiency: N/A
Efficacy: 132.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331260
CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	17
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9544	9544	9544	9544
5°	10699	9606	8512	9606
10°	12260	9527	7366	9527
15°	13563	9352	6509	9352
20°	13357	9165	5933	9165
25°	12043	8915	5569	8915
30°	9952	8516	5302	8516
35°	7253	8099	5113	8099
40°	5794	7609	5008	7609
45°	5062	7040	4866	7040
50°	4760	6488	4770	6488
55°	4386	5928	4642	5928
60°	4020	5331	4447	5331
65°	3664	4798	4252	4798
70°	3323	4277	3970	4277
75°	2951	3699	3512	3699
80°	2538	3059	2827	3059
85°	2279	2279	1686	2279



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.4
10°-20°	163.7	4.0
20°-30°	237.5	5.7
30°-40°	250.6	6.1
40°-50°	221.9	5.4
50°-60°	177.1	4.3
60°-70°	120.4	2.9
70°-80°	61.7	1.5
80°-90°	18.5	0.4
90°-100°	162.5	3.9
100°-110°	551.5	13.3
110°-120°	585.9	14.2
120°-130°	482.3	11.7
130°-140°	387.3	9.4
140°-150°	292.7	7.1
150°-160°	205.7	5.0
160°-170°	121.1	2.9
170°-180°	39.4	1.0
0°-30°	457.5	11.1
0°-40°	708.1	17.1
0°-60°	1107.1	26.8
0°-90°	1307.7	31.6
90°-120°	1300.0	31.4
90°-150°	2462.4	59.5
90°-180°	2829.0	68.4
0°-180°	4136.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	591	591	591	591	591	
5°	660	593	525	593	660	66
15°	811	560	389	560	811	224
25°	676	500	313	500	676	306
35°	368	411	259	411	368	239
45°	222	308	213	308	222	174
55°	156	211	165	211	156	140
65°	96	126	111	126	96	95
75°	47	59	56	59	47	51
85°	12	12	9	12	12	14
90°	26	1	26	1	26	14
95°	89	27	89	27	89	116
105°	881	95	881	95	881	852
115°	1159	168	1159	168	1159	1135
125°	940	234	940	234	940	850
135°	779	275	779	275	779	605
145°	622	314	622	314	622	395
155°	523	357	523	357	523	244
165°	459	389	459	389	459	131
175°	414	406	414	406	414	40
180°	406	406	406	406	406	



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	618.3	618.5	618.9	616.0	615.6	615.6	613.1	610.9	608.3	604.9	605.3
5°	660.1	662.6	663.5	660.8	656.7	656.3	652.4	646.1	640.1	635.4	632.0
7.5°	710.0	711.0	708.8	705.2	702.2	696.7	689.5	682.5	672.6	663.6	656.9
10°	747.8	749.2	745.3	740.1	735.8	729.4	719.0	708.3	695.4	682.9	672.9
12.5°	776.5	779.9	774.9	774.3	766.9	758.1	745.7	740.3	722.1	704.7	693.9
15°	811.4	811.2	811.7	807.3	801.9	800.5	787.4	773.0	747.4	737.1	719.4
17.5°	801.3	804.8	806.4	806.3	806.2	805.3	801.1	792.1	779.2	762.6	742.2
20°	777.4	781.9	782.6	787.8	790.8	794.6	796.2	793.7	785.8	771.9	754.2
22.5°	740.3	741.6	743.7	751.8	758.2	767.9	772.9	781.4	778.3	771.5	756.7
25°	676.0	673.8	681.7	685.8	700.6	716.0	727.2	739.4	750.3	756.9	752.6
27.5°	598.9	595.5	607.4	618.3	630.2	647.0	664.3	684.8	701.8	723.2	730.5
30°	533.8	535.9	547.2	558.8	577.0	600.6	620.2	642.6	667.0	690.8	707.4
32.5°	463.7	471.5	478.7	496.5	512.5	538.8	567.5	595.6	625.9	653.0	678.7
35°	368.0	377.1	387.1	400.0	422.5	448.6	476.6	514.5	555.9	592.9	623.3
37.5°	309.8	308.3	314.0	323.4	341.6	362.7	394.9	432.3	481.0	524.5	567.5
40°	274.9	274.0	278.0	286.7	300.5	316.0	344.2	377.1	422.3	475.5	526.6
42.5°	250.9	251.4	253.7	259.8	269.3	282.0	303.1	331.1	372.5	422.6	477.5
45°	221.7	223.3	225.8	228.8	234.2	244.7	256.5	276.5	309.2	351.0	405.0
47.5°	200.7	200.8	203.3	205.9	209.1	215.0	224.7	237.2	260.3	294.3	340.8
50°	189.5	187.9	189.7	191.7	195.1	199.2	205.6	217.4	232.8	260.3	299.2
52.5°	175.6	175.7	177.3	178.1	181.1	185.2	191.0	199.2	213.2	234.7	266.6
55°	155.8	157.0	157.9	159.2	162.0	164.9	169.5	174.9	185.8	201.9	225.6
57.5°	137.2	137.6	138.5	141.1	142.8	145.5	149.8	154.8	161.9	173.8	191.6
60°	124.5	124.5	126.3	127.4	129.7	132.4	135.8	140.6	147.0	156.7	171.1
62.5°	112.9	112.7	113.4	115.3	117.0	119.5	122.9	127.0	133.0	141.7	153.4
65°	95.9	95.4	96.8	97.2	99.0	101.5	104.3	108.6	113.4	119.7	130.2
67.5°	79.5	80.1	80.8	81.6	82.6	85.3	87.1	90.1	94.2	99.5	106.5
70°	70.4	70.4	70.4	71.1	72.5	73.8	75.6	78.1	82.0	86.5	92.9
72.5°	60.2	61.0	61.7	61.3	63.0	63.8	66.0	67.4	71.1	74.0	79.6
75°	47.3	47.3	47.3	48.4	49.1	49.7	51.1	52.5	54.3	57.9	60.9
77.5°	35.3	35.2	35.4	35.7	36.4	37.2	37.6	38.8	40.5	42.2	44.7
80°	27.3	27.7	27.9	28.4	28.4	28.8	29.1	30.7	31.8	32.9	34.5
82.5°	21.1	21.2	21.2	21.3	21.5	21.8	22.4	22.9	23.3	24.2	25.4
85°	12.3	12.0	12.0	12.5	12.3	12.3	12.7	13.2	13.2	13.4	14.1
87.5°	9.9	9.9	10.1	9.9	9.9	9.9	9.6	9.7	10.1	10.4	10.4
90°	25.8	25.8	25.8	25.8	25.8	25.0	23.5	25.0	25.8	26.6	25.8
92.5°	43.3	44.6	43.9	46.4	47.1	51.9	58.5	68.2	85.8	101.6	100.2
95°	89.1	88.3	90.7	96.9	107.1	124.3	157.1	204.8	268.1	306.4	271.3
97.5°	175.4	182.0	193.4	212.6	250.0	306.4	391.0	477.9	548.8	523.1	394.0
100°	279.8	293.9	316.6	350.2	415.1	509.7	616.8	713.7	730.1	617.5	425.2
102.5°	492.5	511.5	539.8	597.2	667.7	767.9	846.3	868.2	797.6	620.7	413.4
105°	881.0	891.9	925.5	974.0	1022.5	1048.3	1038.1	949.8	787.2	579.2	390.1
107.5°	1125.3	1139.9	1146.6	1149.3	1143.2	1105.3	1024.0	891.0	718.5	534.8	378.5
110°	1199.1	1199.9	1192.9	1178.0	1144.4	1080.3	980.3	840.3	675.4	513.6	376.0



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1197.9	1193.7	1180.4	1155.5	1108.8	1035.3	928.3	794.1	645.4	499.8	376.6
115°	1159.3	1152.2	1131.9	1095.9	1040.4	959.9	857.5	737.1	608.2	484.7	379.9
117.5°	1090.3	1084.4	1063.0	1025.0	968.4	892.9	800.0	694.3	584.7	477.3	385.5
120°	1045.9	1038.1	1015.4	978.7	924.0	852.8	770.0	673.0	572.2	472.9	389.3
122.5°	999.6	993.1	972.9	936.8	887.7	823.4	745.0	656.2	561.6	470.4	393.7
125°	940.4	934.1	914.6	884.9	839.5	780.9	712.1	631.6	546.4	465.9	400.2
127.5°	888.5	883.5	866.6	838.8	799.2	745.1	680.2	607.4	532.3	463.2	407.0
130°	859.1	852.8	837.2	810.6	772.3	720.7	659.0	591.7	523.0	462.0	412.0
132.5°	828.4	822.8	808.4	781.9	744.2	695.7	639.0	576.7	515.5	461.4	417.0
135°	779.4	776.2	762.2	736.4	702.7	659.0	607.4	555.8	505.0	460.4	422.9
137.5°	731.2	726.5	714.2	692.0	661.3	623.2	582.2	539.1	497.6	460.3	428.2
140°	698.1	693.4	681.6	661.3	636.3	601.9	566.0	528.4	493.3	459.6	430.7
142.5°	664.9	664.0	653.5	635.1	611.3	582.5	551.6	519.7	488.9	459.6	432.6
145°	622.2	619.9	612.1	598.8	580.0	557.4	533.1	507.3	483.1	458.1	434.6
147.5°	586.4	585.0	579.7	569.1	553.6	537.0	518.1	497.8	477.2	455.3	435.3
150°	565.2	564.4	559.7	550.3	538.6	524.5	508.1	490.9	472.1	453.4	434.6
152.5°	547.0	546.9	543.4	535.3	526.1	513.9	500.0	484.0	467.8	450.3	433.4
155°	523.0	524.5	521.4	515.9	507.3	498.7	487.0	474.5	459.6	444.8	431.5
157.5°	502.5	502.5	501.1	496.5	490.4	483.7	473.9	463.4	452.0	439.2	427.9
160°	489.3	489.3	488.6	484.7	479.2	473.7	465.1	456.5	446.4	435.4	426.0
162.5°	476.8	477.5	476.7	474.0	468.6	464.3	457.0	449.6	441.3	432.3	424.2
165°	458.9	459.6	459.6	456.5	453.4	450.3	444.8	439.3	433.1	426.0	420.6
167.5°	442.3	443.2	443.4	441.7	440.3	437.4	433.7	429.5	424.9	420.6	417.0
170°	432.3	433.8	434.6	432.3	431.5	429.9	426.8	424.5	420.6	417.4	415.1
172.5°	424.2	425.1	425.9	424.8	424.0	423.1	420.6	418.8	416.2	413.7	412.6
175°	413.5	415.1	415.9	415.1	415.1	414.3	413.5	412.7	410.4	409.6	408.8
177.5°	407.1	408.4	409.0	409.0	409.0	409.0	408.4	408.4	407.1	406.5	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	606.5	605.1	604.2	600.9	598.0	595.1	594.2	594.5	590.5	586.7	585.1
5°	630.2	625.6	621.3	615.2	607.9	599.9	595.9	592.7	584.7	576.1	571.1
7.5°	651.3	644.8	636.5	625.0	614.4	601.9	593.9	586.9	575.3	563.1	555.6
10°	664.2	655.4	644.7	630.6	617.7	602.4	591.8	581.1	567.5	552.9	543.8
12.5°	675.3	663.4	652.9	634.8	619.5	600.4	587.8	572.7	558.4	541.1	532.2
15°	701.7	679.7	659.7	639.2	620.4	593.8	579.7	559.5	540.7	519.3	509.1
17.5°	722.1	697.3	665.9	639.9	617.9	588.4	567.8	543.6	521.3	496.9	483.0
20°	733.7	705.3	671.5	640.6	614.3	580.6	558.1	533.4	507.3	479.8	464.8
22.5°	740.6	710.8	677.3	637.9	607.0	574.3	546.0	518.8	492.4	462.7	447.0
25°	742.8	715.6	680.1	635.6	597.9	560.9	526.8	500.4	468.4	440.7	417.8
27.5°	732.0	712.5	678.4	631.3	587.4	544.1	506.1	476.3	442.5	412.4	389.3
30°	718.7	707.4	674.2	627.0	579.0	532.5	490.7	456.8	423.2	392.8	369.1
32.5°	698.2	695.8	666.6	620.8	570.1	517.8	474.5	440.3	403.0	373.1	350.6
35°	657.9	668.8	650.4	607.0	553.4	496.8	450.0	410.9	372.3	343.7	322.6
37.5°	603.8	630.9	626.1	586.8	530.7	474.0	422.3	381.5	344.7	315.8	295.1
40°	566.5	601.1	606.1	571.3	514.8	456.4	401.6	361.0	325.1	298.7	277.8
42.5°	526.6	566.9	580.6	552.8	497.3	437.8	383.1	341.0	305.4	279.8	261.3
45°	459.6	512.9	537.7	521.8	468.2	407.3	351.0	308.3	276.0	251.9	237.6
47.5°	396.9	455.2	488.5	482.9	435.8	375.5	319.8	278.8	247.4	228.2	215.4
50°	352.6	412.5	452.7	454.6	412.5	352.8	296.9	258.3	229.4	211.5	201.0
52.5°	314.0	371.3	415.1	424.8	386.5	329.2	276.4	237.9	212.5	196.0	186.7
55°	263.7	312.1	360.7	378.5	347.8	293.3	244.4	210.6	186.7	175.4	167.2
57.5°	219.3	259.6	304.5	324.1	305.2	258.5	212.7	183.3	164.0	154.0	147.7
60°	195.8	227.6	267.6	291.0	274.6	233.1	193.1	165.1	149.2	140.4	134.5
62.5°	174.0	202.2	236.0	257.4	248.5	209.3	173.5	148.8	135.1	126.8	122.5
65°	143.6	165.8	192.0	211.7	205.8	176.1	146.7	125.6	114.7	108.1	104.7
67.5°	118.2	134.3	152.4	169.7	165.0	143.9	120.4	103.9	95.8	90.1	88.0
70°	102.2	114.5	130.6	144.5	140.6	123.4	104.7	90.6	83.6	78.8	76.8
72.5°	87.0	97.0	109.4	120.7	118.1	103.7	88.2	77.6	72.1	67.7	66.1
75°	65.7	73.4	80.9	88.4	87.7	76.6	67.5	59.3	55.0	51.6	50.9
77.5°	48.5	52.8	57.9	62.3	61.1	54.7	47.6	42.9	39.8	37.5	37.1
80°	37.0	39.5	43.2	46.3	44.8	42.0	36.3	32.9	30.7	28.4	27.5
82.5°	26.9	29.3	31.5	33.3	32.0	29.5	26.0	23.7	22.3	20.8	20.4
85°	14.1	15.4	16.4	16.8	16.4	14.8	13.2	12.3	11.1	10.4	10.2
87.5°	9.7	8.6	7.8	7.7	6.8	6.5	5.2	4.2	4.4	4.9	4.8
90°	21.1	15.6	11.7	9.4	7.8	6.3	3.1	0.8	3.1	6.3	7.8
92.5°	78.0	53.2	35.5	28.1	22.8	19.4	13.8	9.5	13.8	19.4	22.8
95°	180.6	112.6	76.6	57.8	45.3	38.3	30.5	27.4	30.5	38.3	45.3
97.5°	243.3	148.5	103.3	82.1	67.7	57.1	48.8	44.6	48.8	57.1	67.7
100°	256.4	161.0	119.6	97.7	82.1	69.6	62.5	60.2	62.5	69.6	82.1
102.5°	257.0	172.3	134.0	112.1	95.8	83.3	76.3	74.6	76.3	83.3	95.8
105°	261.1	191.5	154.8	132.9	115.7	104.0	98.5	95.4	98.5	104.0	115.7
107.5°	271.9	211.2	175.6	153.5	136.5	125.7	120.4	117.9	120.4	125.7	136.5
110°	280.6	224.3	190.0	167.3	150.9	140.7	136.0	132.9	136.0	140.7	150.9



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	290.0	236.9	203.7	180.4	164.6	155.1	149.8	146.6	149.8	155.1	164.6
115°	304.1	256.4	222.8	201.7	186.0	176.7	172.0	168.1	172.0	176.7	186.0
117.5°	319.1	274.4	243.3	221.4	206.4	198.1	193.4	190.3	193.4	198.1	206.4
120°	329.1	286.9	256.4	234.5	218.9	211.8	207.2	204.0	207.2	211.8	218.9
122.5°	337.9	298.8	270.2	247.6	232.0	224.3	219.7	217.2	219.7	224.3	232.0
125°	351.8	316.6	288.4	266.6	250.9	241.5	236.9	234.5	236.9	241.5	250.9
127.5°	364.7	333.2	305.8	283.3	268.3	258.0	251.4	248.3	251.4	258.0	268.3
130°	372.9	343.2	315.8	293.9	278.3	267.3	259.5	256.4	259.5	267.3	278.3
132.5°	381.0	351.9	325.8	303.9	287.7	276.1	267.7	263.9	267.7	276.1	287.7
135°	391.6	364.3	339.3	317.4	299.4	287.7	278.3	275.2	278.3	287.7	299.4
137.5°	399.8	374.3	349.6	329.3	311.4	298.9	289.5	285.8	289.5	298.9	311.4
140°	404.1	379.9	356.5	336.1	318.9	306.4	297.0	293.9	297.0	306.4	318.9
142.5°	407.9	384.3	361.5	342.4	325.8	313.3	304.6	302.0	304.6	313.3	325.8
145°	412.7	390.9	369.7	352.5	336.9	325.2	317.4	314.2	317.4	325.2	336.9
147.5°	415.4	396.2	376.3	361.0	348.0	337.2	329.7	327.4	329.7	337.2	348.0
150°	416.6	398.7	380.7	366.6	354.9	344.7	338.5	336.1	338.5	344.7	354.9
152.5°	417.3	401.2	385.1	372.2	361.1	352.2	346.0	344.9	346.0	352.2	361.1
155°	418.2	404.9	391.6	379.9	371.3	362.7	358.0	357.2	358.0	362.7	371.3
157.5°	418.2	407.6	396.3	386.5	379.6	372.1	368.3	367.6	368.3	372.1	379.6
160°	418.2	408.8	399.4	390.9	384.6	378.3	375.2	374.4	375.2	378.3	384.6
162.5°	417.6	409.5	401.3	394.6	389.0	384.0	380.8	381.3	380.8	384.0	389.0
165°	415.9	410.4	403.4	398.7	394.8	390.1	388.5	389.3	388.5	390.1	394.8
167.5°	414.8	410.2	405.1	402.1	399.3	396.3	394.9	395.9	394.9	396.3	399.3
170°	413.5	409.6	405.7	403.4	401.8	399.4	398.7	400.2	398.7	399.4	401.8
172.5°	411.6	409.0	406.3	404.6	403.7	401.3	401.8	402.7	401.8	401.3	403.7
175°	409.6	408.0	406.5	405.7	405.7	404.1	404.9	405.7	404.9	404.1	405.7
177.5°	408.4	407.1	406.5	406.5	406.5	405.2	405.9	407.1	405.9	405.2	406.5
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	583.3	582.2	578.4	576.4	573.1	570.0	568.0	568.9	569.6	569.3	568.7
5°	566.5	562.2	555.6	550.0	545.9	538.4	535.2	533.6	532.2	530.7	529.1
7.5°	546.6	539.8	530.4	522.3	514.7	505.3	500.0	496.9	493.6	490.0	486.8
10°	532.5	522.9	512.9	501.6	492.5	484.1	476.6	471.6	467.0	462.7	459.6
12.5°	517.6	506.6	494.2	478.7	468.7	456.6	455.5	446.7	439.6	436.9	433.2
15°	493.9	478.4	462.7	444.3	436.4	425.5	418.7	411.8	405.7	401.4	400.3
17.5°	466.9	446.9	431.3	418.1	405.1	393.9	387.6	382.2	377.1	371.4	370.6
20°	446.4	429.1	412.1	400.5	387.1	375.7	368.0	362.6	358.2	354.8	351.9
22.5°	426.9	408.0	392.4	379.8	366.6	357.4	351.3	346.0	342.4	338.7	335.9
25°	395.7	381.0	363.9	349.6	338.7	332.8	327.8	323.3	321.0	318.5	315.3
27.5°	368.4	352.0	336.1	325.0	315.4	310.2	306.6	303.5	301.4	299.9	298.1
30°	349.2	332.6	320.1	309.2	301.2	296.0	293.7	291.9	289.4	288.5	287.6
32.5°	330.6	315.7	305.0	295.5	288.0	284.5	282.5	280.8	278.9	278.0	276.1
35°	304.4	291.9	281.5	276.2	270.1	267.1	265.6	263.3	261.5	260.6	260.3
37.5°	279.7	268.9	262.0	255.3	252.7	250.9	248.7	247.2	246.6	246.5	246.2
40°	263.7	254.9	248.7	243.3	242.2	239.4	237.6	236.3	236.3	236.5	236.3
42.5°	249.2	241.2	235.8	231.1	229.8	228.2	226.3	226.3	226.6	227.4	226.6
45°	227.2	221.5	217.6	215.4	212.9	211.3	211.0	211.7	211.9	212.2	212.9
47.5°	206.9	203.1	199.6	197.1	196.0	195.8	195.5	196.7	197.8	198.2	199.2
50°	194.9	190.6	187.6	186.0	185.1	184.7	185.1	186.5	187.4	188.5	189.2
52.5°	181.5	178.4	176.4	175.1	174.8	175.1	175.1	176.7	178.1	178.6	178.9
55°	162.9	160.6	160.2	158.1	159.0	158.8	159.9	160.8	162.2	163.6	163.8
57.5°	144.3	142.5	141.3	141.5	141.8	142.8	143.7	145.3	146.7	148.2	148.3
60°	132.0	131.1	130.4	130.4	130.8	132.2	133.3	134.9	135.8	136.8	137.4
62.5°	120.7	119.8	119.1	119.5	120.7	121.5	122.8	123.7	124.6	125.5	125.8
65°	102.9	102.5	103.1	103.6	103.8	104.9	106.5	107.2	108.1	108.6	110.2
67.5°	86.5	86.6	86.5	87.1	88.5	88.7	90.2	91.8	92.0	92.9	93.9
70°	75.4	75.9	76.3	76.8	77.9	78.4	79.5	80.2	81.1	81.8	82.5
72.5°	65.2	65.3	65.8	65.7	66.7	67.6	68.6	69.3	70.2	71.1	71.7
75°	50.2	50.2	50.7	50.9	52.0	53.2	52.9	53.4	54.3	55.2	55.7
77.5°	36.7	36.2	36.7	36.9	37.3	38.2	38.4	39.0	40.1	39.8	40.3
80°	27.9	27.3	27.9	28.2	28.2	29.3	29.3	29.8	30.4	29.8	30.4
82.5°	19.9	19.6	20.1	20.2	20.5	20.6	20.9	21.0	21.7	21.4	21.7
85°	10.0	9.8	10.0	9.8	10.0	10.2	10.2	10.0	10.0	10.4	9.8
87.5°	5.0	5.3	5.9	6.9	7.7	7.7	7.3	7.2	6.9	6.8	7.0
90°	9.4	11.7	15.6	21.1	25.8	26.6	25.8	25.0	23.5	25.0	25.8
92.5°	28.1	35.5	53.2	78.0	100.2	101.6	85.8	68.2	58.5	51.9	47.1
95°	57.8	76.6	112.6	180.6	271.3	306.4	268.1	204.8	157.1	124.3	107.1
97.5°	82.1	103.3	148.5	243.3	394.0	523.1	548.8	477.9	391.0	306.4	250.0
100°	97.7	119.6	161.0	256.4	425.2	617.5	730.1	713.7	616.8	509.7	415.1
102.5°	112.1	134.0	172.3	257.0	413.4	620.7	797.6	868.2	846.3	767.9	667.7
105°	132.9	154.8	191.5	261.1	390.1	579.2	787.2	949.8	1038.1	1048.3	1022.5
107.5°	153.5	175.6	211.2	271.9	378.5	534.8	718.5	891.0	1024.0	1105.3	1143.2
110°	167.3	190.0	224.3	280.6	376.0	513.6	675.4	840.3	980.3	1080.3	1144.4



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	180.4	203.7	236.9	290.0	376.6	499.8	645.4	794.1	928.3	1035.3	1108.8
115°	201.7	222.8	256.4	304.1	379.9	484.7	608.2	737.1	857.5	959.9	1040.4
117.5°	221.4	243.3	274.4	319.1	385.5	477.3	584.7	694.3	800.0	892.9	968.4
120°	234.5	256.4	286.9	329.1	389.3	472.9	572.2	673.0	770.0	852.8	924.0
122.5°	247.6	270.2	298.8	337.9	393.7	470.4	561.6	656.2	745.0	823.4	887.7
125°	266.6	288.4	316.6	351.8	400.2	465.9	546.4	631.6	712.1	780.9	839.5
127.5°	283.3	305.8	333.2	364.7	407.0	463.2	532.3	607.4	680.2	745.1	799.2
130°	293.9	315.8	343.2	372.9	412.0	462.0	523.0	591.7	659.0	720.7	772.3
132.5°	303.9	325.8	351.9	381.0	417.0	461.4	515.5	576.7	639.0	695.7	744.2
135°	317.4	339.3	364.3	391.6	422.9	460.4	505.0	555.8	607.4	659.0	702.7
137.5°	329.3	349.6	374.3	399.8	428.2	460.3	497.6	539.1	582.2	623.2	661.3
140°	336.1	356.5	379.9	404.1	430.7	459.6	493.3	528.4	566.0	601.9	636.3
142.5°	342.4	361.5	384.3	407.9	432.6	459.6	488.9	519.7	551.6	582.5	611.3
145°	352.5	369.7	390.9	412.7	434.6	458.1	483.1	507.3	533.1	557.4	580.0
147.5°	361.0	376.3	396.2	415.4	435.3	455.3	477.2	497.8	518.1	537.0	553.6
150°	366.6	380.7	398.7	416.6	434.6	453.4	472.1	490.9	508.1	524.5	538.6
152.5°	372.2	385.1	401.2	417.3	433.4	450.3	467.8	484.0	500.0	513.9	526.1
155°	379.9	391.6	404.9	418.2	431.5	444.8	459.6	474.5	487.0	498.7	507.3
157.5°	386.5	396.3	407.6	418.2	427.9	439.2	452.0	463.4	473.9	483.7	490.4
160°	390.9	399.4	408.8	418.2	426.0	435.4	446.4	456.5	465.1	473.7	479.2
162.5°	394.6	401.3	409.5	417.6	424.2	432.3	441.3	449.6	457.0	464.3	468.6
165°	398.7	403.4	410.4	415.9	420.6	426.0	433.1	439.3	444.8	450.3	453.4
167.5°	402.1	405.1	410.2	414.8	417.0	420.6	424.9	429.5	433.7	437.4	440.3
170°	403.4	405.7	409.6	413.5	415.1	417.4	420.6	424.5	426.8	429.9	431.5
172.5°	404.6	406.3	409.0	411.6	412.6	413.7	416.2	418.8	420.6	423.1	424.0
175°	405.7	406.5	408.0	409.6	408.8	409.6	410.4	412.7	413.5	414.3	415.1
177.5°	406.5	406.5	407.1	408.4	407.1	406.5	407.1	408.4	408.4	409.0	409.0
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	566.9	566.5	566.5	564.9	566.5	566.5	566.9	568.7	569.3	569.6	568.9
5°	525.9	525.2	524.1	525.2	524.1	525.2	525.9	529.1	530.7	532.2	533.6
7.5°	485.3	482.6	482.2	479.5	482.2	482.6	485.3	486.8	490.0	493.6	496.9
10°	455.7	453.9	453.6	449.3	453.6	453.9	455.7	459.6	462.7	467.0	471.6
12.5°	433.2	428.8	429.7	427.2	429.7	428.8	433.2	433.2	436.9	439.6	446.7
15°	394.1	394.1	393.2	389.4	393.2	394.1	394.1	400.3	401.4	405.7	411.8
17.5°	366.1	365.6	363.5	364.6	363.5	365.6	366.1	370.6	371.4	377.1	382.2
20°	349.4	348.0	345.3	345.3	345.3	348.0	349.4	351.9	354.8	358.2	362.6
22.5°	333.6	333.5	330.6	331.5	330.6	333.5	333.6	335.9	338.7	342.4	346.0
25°	315.1	313.3	311.9	312.6	311.9	313.3	315.1	315.3	318.5	321.0	323.3
27.5°	297.5	296.5	296.4	294.6	296.4	296.5	297.5	298.1	299.9	301.4	303.5
30°	287.4	285.1	285.5	284.4	285.5	285.1	287.4	287.6	288.5	289.4	291.9
32.5°	275.7	274.9	274.5	273.5	274.5	274.9	275.7	276.1	278.0	278.9	280.8
35°	259.9	260.1	259.0	259.4	259.0	260.1	259.9	260.3	260.6	261.5	263.3
37.5°	246.0	246.7	246.2	246.3	246.2	246.7	246.0	246.2	246.5	246.6	247.2
40°	236.9	236.9	236.9	237.6	236.9	236.9	236.9	236.3	236.5	236.3	236.3
42.5°	228.2	227.8	227.5	227.4	227.5	227.8	228.2	226.6	227.4	226.6	226.3
45°	213.3	214.0	214.2	213.1	214.2	214.0	213.3	212.9	212.2	211.9	211.7
47.5°	199.8	199.9	199.8	200.8	199.8	199.9	199.8	199.2	198.2	197.8	196.7
50°	190.4	189.9	190.4	189.9	190.4	189.9	190.4	189.2	188.5	187.4	186.5
52.5°	180.4	180.5	180.2	180.1	180.2	180.5	180.4	178.9	178.6	178.1	176.7
55°	164.7	165.1	164.9	164.9	164.9	165.1	164.7	163.8	163.6	162.2	160.8
57.5°	148.5	148.9	149.2	148.2	149.2	148.9	148.5	148.3	148.2	146.7	145.3
60°	137.2	138.3	138.1	137.7	138.1	138.3	137.2	137.4	136.8	135.8	134.9
62.5°	126.8	127.3	127.2	127.1	127.2	127.3	126.8	125.8	125.5	124.6	123.7
65°	110.9	111.3	110.6	111.3	110.6	111.3	110.9	110.2	108.6	108.1	107.2
67.5°	93.6	93.8	94.3	94.6	94.3	93.8	93.6	93.9	92.9	92.0	91.8
70°	82.9	82.7	83.4	84.1	83.4	82.7	82.9	82.5	81.8	81.1	80.2
72.5°	71.6	72.1	71.9	72.4	71.9	72.1	71.6	71.7	71.1	70.2	69.3
75°	55.2	55.9	55.7	56.3	55.7	55.9	55.2	55.7	55.2	54.3	53.4
77.5°	39.9	40.0	39.9	40.3	39.9	40.0	39.9	40.3	39.8	40.1	39.0
80°	30.4	30.0	29.5	30.4	29.5	30.0	30.4	30.4	29.8	30.4	29.8
82.5°	21.2	21.4	21.0	21.0	21.0	21.4	21.2	21.7	21.4	21.7	21.0
85°	9.8	9.5	9.1	9.1	9.1	9.5	9.8	9.8	10.4	10.0	10.0
87.5°	7.0	6.8	6.8	6.6	6.8	6.8	7.0	7.0	6.8	6.9	7.2
90°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.0	23.5	25.0
92.5°	46.4	43.9	44.6	43.3	44.6	43.9	46.4	47.1	51.9	58.5	68.2
95°	96.9	90.7	88.3	89.1	88.3	90.7	96.9	107.1	124.3	157.1	204.8
97.5°	212.6	193.4	182.0	175.4	182.0	193.4	212.6	250.0	306.4	391.0	477.9
100°	350.2	316.6	293.9	279.8	293.9	316.6	350.2	415.1	509.7	616.8	713.7
102.5°	597.2	539.8	511.5	492.5	511.5	539.8	597.2	667.7	767.9	846.3	868.2
105°	974.0	925.5	891.9	881.0	891.9	925.5	974.0	1022.5	1048.3	1038.1	949.8
107.5°	1149.3	1146.6	1139.9	1125.3	1139.9	1146.6	1149.3	1143.2	1105.3	1024.0	891.0
110°	1178.0	1192.9	1199.9	1199.1	1199.9	1192.9	1178.0	1144.4	1080.3	980.3	840.3



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1155.5	1180.4	1193.7	1197.9	1193.7	1180.4	1155.5	1108.8	1035.3	928.3	794.1
115°	1095.9	1131.9	1152.2	1159.3	1152.2	1131.9	1095.9	1040.4	959.9	857.5	737.1
117.5°	1025.0	1063.0	1084.4	1090.3	1084.4	1063.0	1025.0	968.4	892.9	800.0	694.3
120°	978.7	1015.4	1038.1	1045.9	1038.1	1015.4	978.7	924.0	852.8	770.0	673.0
122.5°	936.8	972.9	993.1	999.6	993.1	972.9	936.8	887.7	823.4	745.0	656.2
125°	884.9	914.6	934.1	940.4	934.1	914.6	884.9	839.5	780.9	712.1	631.6
127.5°	838.8	866.6	883.5	888.5	883.5	866.6	838.8	799.2	745.1	680.2	607.4
130°	810.6	837.2	852.8	859.1	852.8	837.2	810.6	772.3	720.7	659.0	591.7
132.5°	781.9	808.4	822.8	828.4	822.8	808.4	781.9	744.2	695.7	639.0	576.7
135°	736.4	762.2	776.2	779.4	776.2	762.2	736.4	702.7	659.0	607.4	555.8
137.5°	692.0	714.2	726.5	731.2	726.5	714.2	692.0	661.3	623.2	582.2	539.1
140°	661.3	681.6	693.4	698.1	693.4	681.6	661.3	636.3	601.9	566.0	528.4
142.5°	635.1	653.5	664.0	664.9	664.0	653.5	635.1	611.3	582.5	551.6	519.7
145°	598.8	612.1	619.9	622.2	619.9	612.1	598.8	580.0	557.4	533.1	507.3
147.5°	569.1	579.7	585.0	586.4	585.0	579.7	569.1	553.6	537.0	518.1	497.8
150°	550.3	559.7	564.4	565.2	564.4	559.7	550.3	538.6	524.5	508.1	490.9
152.5°	535.3	543.4	546.9	547.0	546.9	543.4	535.3	526.1	513.9	500.0	484.0
155°	515.9	521.4	524.5	523.0	524.5	521.4	515.9	507.3	498.7	487.0	474.5
157.5°	496.5	501.1	502.5	502.5	502.5	501.1	496.5	490.4	483.7	473.9	463.4
160°	484.7	488.6	489.3	489.3	489.3	488.6	484.7	479.2	473.7	465.1	456.5
162.5°	474.0	476.7	477.5	476.8	477.5	476.7	474.0	468.6	464.3	457.0	449.6
165°	456.5	459.6	459.6	458.9	459.6	459.6	456.5	453.4	450.3	444.8	439.3
167.5°	441.7	443.4	443.2	442.3	443.2	443.4	441.7	440.3	437.4	433.7	429.5
170°	432.3	434.6	433.8	432.3	433.8	434.6	432.3	431.5	429.9	426.8	424.5
172.5°	424.8	425.9	425.1	424.2	425.1	425.9	424.8	424.0	423.1	420.6	418.8
175°	415.1	415.9	415.1	413.5	415.1	415.9	415.1	415.1	414.3	413.5	412.7
177.5°	409.0	409.0	408.4	407.1	408.4	409.0	409.0	409.0	409.0	408.4	408.4
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	568.0	570.0	573.1	576.4	578.4	582.2	583.3	585.1	586.7	590.5	594.5
5°	535.2	538.4	545.9	550.0	555.6	562.2	566.5	571.1	576.1	584.7	592.7
7.5°	500.0	505.3	514.7	522.3	530.4	539.8	546.6	555.6	563.1	575.3	586.9
10°	476.6	484.1	492.5	501.6	512.9	522.9	532.5	543.8	552.9	567.5	581.1
12.5°	455.5	456.6	468.7	478.7	494.2	506.6	517.6	532.2	541.1	558.4	572.7
15°	418.7	425.5	436.4	444.3	462.7	478.4	493.9	509.1	519.3	540.7	559.5
17.5°	387.6	393.9	405.1	418.1	431.3	446.9	466.9	483.0	496.9	521.3	543.6
20°	368.0	375.7	387.1	400.5	412.1	429.1	446.4	464.8	479.8	507.3	533.4
22.5°	351.3	357.4	366.6	379.8	392.4	408.0	426.9	447.0	462.7	492.4	518.8
25°	327.8	332.8	338.7	349.6	363.9	381.0	395.7	417.8	440.7	468.4	500.4
27.5°	306.6	310.2	315.4	325.0	336.1	352.0	368.4	389.3	412.4	442.5	476.3
30°	293.7	296.0	301.2	309.2	320.1	332.6	349.2	369.1	392.8	423.2	456.8
32.5°	282.5	284.5	288.0	295.5	305.0	315.7	330.6	350.6	373.1	403.0	440.3
35°	265.6	267.1	270.1	276.2	281.5	291.9	304.4	322.6	343.7	372.3	410.9
37.5°	248.7	250.9	252.7	255.3	262.0	268.9	279.7	295.1	315.8	344.7	381.5
40°	237.6	239.4	242.2	243.3	248.7	254.9	263.7	277.8	298.7	325.1	361.0
42.5°	226.3	228.2	229.8	231.1	235.8	241.2	249.2	261.3	279.8	305.4	341.0
45°	211.0	211.3	212.9	215.4	217.6	221.5	227.2	237.6	251.9	276.0	308.3
47.5°	195.5	195.8	196.0	197.1	199.6	203.1	206.9	215.4	228.2	247.4	278.8
50°	185.1	184.7	185.1	186.0	187.6	190.6	194.9	201.0	211.5	229.4	258.3
52.5°	175.1	175.1	174.8	175.1	176.4	178.4	181.5	186.7	196.0	212.5	237.9
55°	159.9	158.8	159.0	158.1	160.2	160.6	162.9	167.2	175.4	186.7	210.6
57.5°	143.7	142.8	141.8	141.5	141.3	142.5	144.3	147.7	154.0	164.0	183.3
60°	133.3	132.2	130.8	130.4	130.4	131.1	132.0	134.5	140.4	149.2	165.1
62.5°	122.8	121.5	120.7	119.5	119.1	119.8	120.7	122.5	126.8	135.1	148.8
65°	106.5	104.9	103.8	103.6	103.1	102.5	102.9	104.7	108.1	114.7	125.6
67.5°	90.2	88.7	88.5	87.1	86.5	86.6	86.5	88.0	90.1	95.8	103.9
70°	79.5	78.4	77.9	76.8	76.3	75.9	75.4	76.8	78.8	83.6	90.6
72.5°	68.6	67.6	66.7	65.7	65.8	65.3	65.2	66.1	67.7	72.1	77.6
75°	52.9	53.2	52.0	50.9	50.7	50.2	50.2	50.9	51.6	55.0	59.3
77.5°	38.4	38.2	37.3	36.9	36.7	36.2	36.7	37.1	37.5	39.8	42.9
80°	29.3	29.3	28.2	28.2	27.9	27.3	27.9	27.5	28.4	30.7	32.9
82.5°	20.9	20.6	20.5	20.2	20.1	19.6	19.9	20.4	20.8	22.3	23.7
85°	10.2	10.2	10.0	9.8	10.0	9.8	10.0	10.2	10.4	11.1	12.3
87.5°	7.3	7.7	7.7	6.9	5.9	5.3	5.0	4.8	4.9	4.4	4.2
90°	25.8	26.6	25.8	21.1	15.6	11.7	9.4	7.8	6.3	3.1	0.8
92.5°	85.8	101.6	100.2	78.0	53.2	35.5	28.1	22.8	19.4	13.8	9.5
95°	268.1	306.4	271.3	180.6	112.6	76.6	57.8	45.3	38.3	30.5	27.4
97.5°	548.8	523.1	394.0	243.3	148.5	103.3	82.1	67.7	57.1	48.8	44.6
100°	730.1	617.5	425.2	256.4	161.0	119.6	97.7	82.1	69.6	62.5	60.2
102.5°	797.6	620.7	413.4	257.0	172.3	134.0	112.1	95.8	83.3	76.3	74.6
105°	787.2	579.2	390.1	261.1	191.5	154.8	132.9	115.7	104.0	98.5	95.4
107.5°	718.5	534.8	378.5	271.9	211.2	175.6	153.5	136.5	125.7	120.4	117.9
110°	675.4	513.6	376.0	280.6	224.3	190.0	167.3	150.9	140.7	136.0	132.9



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.4	499.8	376.6	290.0	236.9	203.7	180.4	164.6	155.1	149.8	146.6
115°	608.2	484.7	379.9	304.1	256.4	222.8	201.7	186.0	176.7	172.0	168.1
117.5°	584.7	477.3	385.5	319.1	274.4	243.3	221.4	206.4	198.1	193.4	190.3
120°	572.2	472.9	389.3	329.1	286.9	256.4	234.5	218.9	211.8	207.2	204.0
122.5°	561.6	470.4	393.7	337.9	298.8	270.2	247.6	232.0	224.3	219.7	217.2
125°	546.4	465.9	400.2	351.8	316.6	288.4	266.6	250.9	241.5	236.9	234.5
127.5°	532.3	463.2	407.0	364.7	333.2	305.8	283.3	268.3	258.0	251.4	248.3
130°	523.0	462.0	412.0	372.9	343.2	315.8	293.9	278.3	267.3	259.5	256.4
132.5°	515.5	461.4	417.0	381.0	351.9	325.8	303.9	287.7	276.1	267.7	263.9
135°	505.0	460.4	422.9	391.6	364.3	339.3	317.4	299.4	287.7	278.3	275.2
137.5°	497.6	460.3	428.2	399.8	374.3	349.6	329.3	311.4	298.9	289.5	285.8
140°	493.3	459.6	430.7	404.1	379.9	356.5	336.1	318.9	306.4	297.0	293.9
142.5°	488.9	459.6	432.6	407.9	384.3	361.5	342.4	325.8	313.3	304.6	302.0
145°	483.1	458.1	434.6	412.7	390.9	369.7	352.5	336.9	325.2	317.4	314.2
147.5°	477.2	455.3	435.3	415.4	396.2	376.3	361.0	348.0	337.2	329.7	327.4
150°	472.1	453.4	434.6	416.6	398.7	380.7	366.6	354.9	344.7	338.5	336.1
152.5°	467.8	450.3	433.4	417.3	401.2	385.1	372.2	361.1	352.2	346.0	344.9
155°	459.6	444.8	431.5	418.2	404.9	391.6	379.9	371.3	362.7	358.0	357.2
157.5°	452.0	439.2	427.9	418.2	407.6	396.3	386.5	379.6	372.1	368.3	367.6
160°	446.4	435.4	426.0	418.2	408.8	399.4	390.9	384.6	378.3	375.2	374.4
162.5°	441.3	432.3	424.2	417.6	409.5	401.3	394.6	389.0	384.0	380.8	381.3
165°	433.1	426.0	420.6	415.9	410.4	403.4	398.7	394.8	390.1	388.5	389.3
167.5°	424.9	420.6	417.0	414.8	410.2	405.1	402.1	399.3	396.3	394.9	395.9
170°	420.6	417.4	415.1	413.5	409.6	405.7	403.4	401.8	399.4	398.7	400.2
172.5°	416.2	413.7	412.6	411.6	409.0	406.3	404.6	403.7	401.3	401.8	402.7
175°	410.4	409.6	408.8	409.6	408.0	406.5	405.7	405.7	404.1	404.9	405.7
177.5°	407.1	406.5	407.1	408.4	407.1	406.5	406.5	406.5	405.2	405.9	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	594.2	595.1	598.0	600.9	604.2	605.1	606.5	605.3	604.9	608.3	610.9
5°	595.9	599.9	607.9	615.2	621.3	625.6	630.2	632.0	635.4	640.1	646.1
7.5°	593.9	601.9	614.4	625.0	636.5	644.8	651.3	656.9	663.6	672.6	682.5
10°	591.8	602.4	617.7	630.6	644.7	655.4	664.2	672.9	682.9	695.4	708.3
12.5°	587.8	600.4	619.5	634.8	652.9	663.4	675.3	693.9	704.7	722.1	740.3
15°	579.7	593.8	620.4	639.2	659.7	679.7	701.7	719.4	737.1	747.4	773.0
17.5°	567.8	588.4	617.9	639.9	665.9	697.3	722.1	742.2	762.6	779.2	792.1
20°	558.1	580.6	614.3	640.6	671.5	705.3	733.7	754.2	771.9	785.8	793.7
22.5°	546.0	574.3	607.0	637.9	677.3	710.8	740.6	756.7	771.5	778.3	781.4
25°	526.8	560.9	597.9	635.6	680.1	715.6	742.8	752.6	756.9	750.3	739.4
27.5°	506.1	544.1	587.4	631.3	678.4	712.5	732.0	730.5	723.2	701.8	684.8
30°	490.7	532.5	579.0	627.0	674.2	707.4	718.7	707.4	690.8	667.0	642.6
32.5°	474.5	517.8	570.1	620.8	666.6	695.8	698.2	678.7	653.0	625.9	595.6
35°	450.0	496.8	553.4	607.0	650.4	668.8	657.9	623.3	592.9	555.9	514.5
37.5°	422.3	474.0	530.7	586.8	626.1	630.9	603.8	567.5	524.5	481.0	432.3
40°	401.6	456.4	514.8	571.3	606.1	601.1	566.5	526.6	475.5	422.3	377.1
42.5°	383.1	437.8	497.3	552.8	580.6	566.9	526.6	477.5	422.6	372.5	331.1
45°	351.0	407.3	468.2	521.8	537.7	512.9	459.6	405.0	351.0	309.2	276.5
47.5°	319.8	375.5	435.8	482.9	488.5	455.2	396.9	340.8	294.3	260.3	237.2
50°	296.9	352.8	412.5	454.6	452.7	412.5	352.6	299.2	260.3	232.8	217.4
52.5°	276.4	329.2	386.5	424.8	415.1	371.3	314.0	266.6	234.7	213.2	199.2
55°	244.4	293.3	347.8	378.5	360.7	312.1	263.7	225.6	201.9	185.8	174.9
57.5°	212.7	258.5	305.2	324.1	304.5	259.6	219.3	191.6	173.8	161.9	154.8
60°	193.1	233.1	274.6	291.0	267.6	227.6	195.8	171.1	156.7	147.0	140.6
62.5°	173.5	209.3	248.5	257.4	236.0	202.2	174.0	153.4	141.7	133.0	127.0
65°	146.7	176.1	205.8	211.7	192.0	165.8	143.6	130.2	119.7	113.4	108.6
67.5°	120.4	143.9	165.0	169.7	152.4	134.3	118.2	106.5	99.5	94.2	90.1
70°	104.7	123.4	140.6	144.5	130.6	114.5	102.2	92.9	86.5	82.0	78.1
72.5°	88.2	103.7	118.1	120.7	109.4	97.0	87.0	79.6	74.0	71.1	67.4
75°	67.5	76.6	87.7	88.4	80.9	73.4	65.7	60.9	57.9	54.3	52.5
77.5°	47.6	54.7	61.1	62.3	57.9	52.8	48.5	44.7	42.2	40.5	38.8
80°	36.3	42.0	44.8	46.3	43.2	39.5	37.0	34.5	32.9	31.8	30.7
82.5°	26.0	29.5	32.0	33.3	31.5	29.3	26.9	25.4	24.2	23.3	22.9
85°	13.2	14.8	16.4	16.8	16.4	15.4	14.1	14.1	13.4	13.2	13.2
87.5°	5.2	6.5	6.8	7.7	7.8	8.6	9.7	10.4	10.4	10.1	9.7
90°	3.1	6.3	7.8	9.4	11.7	15.6	21.1	25.8	26.6	25.8	25.0
92.5°	13.8	19.4	22.8	28.1	35.5	53.2	78.0	100.2	101.6	85.8	68.2
95°	30.5	38.3	45.3	57.8	76.6	112.6	180.6	271.3	306.4	268.1	204.8
97.5°	48.8	57.1	67.7	82.1	103.3	148.5	243.3	394.0	523.1	548.8	477.9
100°	62.5	69.6	82.1	97.7	119.6	161.0	256.4	425.2	617.5	730.1	713.7
102.5°	76.3	83.3	95.8	112.1	134.0	172.3	257.0	413.4	620.7	797.6	868.2
105°	98.5	104.0	115.7	132.9	154.8	191.5	261.1	390.1	579.2	787.2	949.8
107.5°	120.4	125.7	136.5	153.5	175.6	211.2	271.9	378.5	534.8	718.5	891.0
110°	136.0	140.7	150.9	167.3	190.0	224.3	280.6	376.0	513.6	675.4	840.3



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	149.8	155.1	164.6	180.4	203.7	236.9	290.0	376.6	499.8	645.4	794.1
115°	172.0	176.7	186.0	201.7	222.8	256.4	304.1	379.9	484.7	608.2	737.1
117.5°	193.4	198.1	206.4	221.4	243.3	274.4	319.1	385.5	477.3	584.7	694.3
120°	207.2	211.8	218.9	234.5	256.4	286.9	329.1	389.3	472.9	572.2	673.0
122.5°	219.7	224.3	232.0	247.6	270.2	298.8	337.9	393.7	470.4	561.6	656.2
125°	236.9	241.5	250.9	266.6	288.4	316.6	351.8	400.2	465.9	546.4	631.6
127.5°	251.4	258.0	268.3	283.3	305.8	333.2	364.7	407.0	463.2	532.3	607.4
130°	259.5	267.3	278.3	293.9	315.8	343.2	372.9	412.0	462.0	523.0	591.7
132.5°	267.7	276.1	287.7	303.9	325.8	351.9	381.0	417.0	461.4	515.5	576.7
135°	278.3	287.7	299.4	317.4	339.3	364.3	391.6	422.9	460.4	505.0	555.8
137.5°	289.5	298.9	311.4	329.3	349.6	374.3	399.8	428.2	460.3	497.6	539.1
140°	297.0	306.4	318.9	336.1	356.5	379.9	404.1	430.7	459.6	493.3	528.4
142.5°	304.6	313.3	325.8	342.4	361.5	384.3	407.9	432.6	459.6	488.9	519.7
145°	317.4	325.2	336.9	352.5	369.7	390.9	412.7	434.6	458.1	483.1	507.3
147.5°	329.7	337.2	348.0	361.0	376.3	396.2	415.4	435.3	455.3	477.2	497.8
150°	338.5	344.7	354.9	366.6	380.7	398.7	416.6	434.6	453.4	472.1	490.9
152.5°	346.0	352.2	361.1	372.2	385.1	401.2	417.3	433.4	450.3	467.8	484.0
155°	358.0	362.7	371.3	379.9	391.6	404.9	418.2	431.5	444.8	459.6	474.5
157.5°	368.3	372.1	379.6	386.5	396.3	407.6	418.2	427.9	439.2	452.0	463.4
160°	375.2	378.3	384.6	390.9	399.4	408.8	418.2	426.0	435.4	446.4	456.5
162.5°	380.8	384.0	389.0	394.6	401.3	409.5	417.6	424.2	432.3	441.3	449.6
165°	388.5	390.1	394.8	398.7	403.4	410.4	415.9	420.6	426.0	433.1	439.3
167.5°	394.9	396.3	399.3	402.1	405.1	410.2	414.8	417.0	420.6	424.9	429.5
170°	398.7	399.4	401.8	403.4	405.7	409.6	413.5	415.1	417.4	420.6	424.5
172.5°	401.8	401.3	403.7	404.6	406.3	409.0	411.6	412.6	413.7	416.2	418.8
175°	404.9	404.1	405.7	405.7	406.5	408.0	409.6	408.8	409.6	410.4	412.7
177.5°	405.9	405.2	406.5	406.5	406.5	407.1	408.4	407.1	406.5	407.1	408.4
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	613.1	615.6	615.6	616.0	618.9	618.5	618.3
5°	652.4	656.3	656.7	660.8	663.5	662.6	660.1
7.5°	689.5	696.7	702.2	705.2	708.8	711.0	710.0
10°	719.0	729.4	735.8	740.1	745.3	749.2	747.8
12.5°	745.7	758.1	766.9	774.3	774.9	779.9	776.5
15°	787.4	800.5	801.9	807.3	811.7	811.2	811.4
17.5°	801.1	805.3	806.2	806.3	806.4	804.8	801.3
20°	796.2	794.6	790.8	787.8	782.6	781.9	777.4
22.5°	772.9	767.9	758.2	751.8	743.7	741.6	740.3
25°	727.2	716.0	700.6	685.8	681.7	673.8	676.0
27.5°	664.3	647.0	630.2	618.3	607.4	595.5	598.9
30°	620.2	600.6	577.0	558.8	547.2	535.9	533.8
32.5°	567.5	538.8	512.5	496.5	478.7	471.5	463.7
35°	476.6	448.6	422.5	400.0	387.1	377.1	368.0
37.5°	394.9	362.7	341.6	323.4	314.0	308.3	309.8
40°	344.2	316.0	300.5	286.7	278.0	274.0	274.9
42.5°	303.1	282.0	269.3	259.8	253.7	251.4	250.9
45°	256.5	244.7	234.2	228.8	225.8	223.3	221.7
47.5°	224.7	215.0	209.1	205.9	203.3	200.8	200.7
50°	205.6	199.2	195.1	191.7	189.7	187.9	189.5
52.5°	191.0	185.2	181.1	178.1	177.3	175.7	175.6
55°	169.5	164.9	162.0	159.2	157.9	157.0	155.8
57.5°	149.8	145.5	142.8	141.1	138.5	137.6	137.2
60°	135.8	132.4	129.7	127.4	126.3	124.5	124.5
62.5°	122.9	119.5	117.0	115.3	113.4	112.7	112.9
65°	104.3	101.5	99.0	97.2	96.8	95.4	95.9
67.5°	87.1	85.3	82.6	81.6	80.8	80.1	79.5
70°	75.6	73.8	72.5	71.1	70.4	70.4	70.4
72.5°	66.0	63.8	63.0	61.3	61.7	61.0	60.2
75°	51.1	49.7	49.1	48.4	47.3	47.3	47.3
77.5°	37.6	37.2	36.4	35.7	35.4	35.2	35.3
80°	29.1	28.8	28.4	28.4	27.9	27.7	27.3
82.5°	22.4	21.8	21.5	21.3	21.2	21.2	21.1
85°	12.7	12.3	12.3	12.5	12.0	12.0	12.3
87.5°	9.6	9.9	9.9	9.9	10.1	9.9	9.9
90°	23.5	25.0	25.8	25.8	25.8	25.8	25.8
92.5°	58.5	51.9	47.1	46.4	43.9	44.6	43.3
95°	157.1	124.3	107.1	96.9	90.7	88.3	89.1
97.5°	391.0	306.4	250.0	212.6	193.4	182.0	175.4
100°	616.8	509.7	415.1	350.2	316.6	293.9	279.8
102.5°	846.3	767.9	667.7	597.2	539.8	511.5	492.5
105°	1038.1	1048.3	1022.5	974.0	925.5	891.9	881.0
107.5°	1024.0	1105.3	1143.2	1149.3	1146.6	1139.9	1125.3
110°	980.3	1080.3	1144.4	1178.0	1192.9	1199.9	1199.1



TEST NUMBER: P331260

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	928.3	1035.3	1108.8	1155.5	1180.4	1193.7	1197.9
115°	857.5	959.9	1040.4	1095.9	1131.9	1152.2	1159.3
117.5°	800.0	892.9	968.4	1025.0	1063.0	1084.4	1090.3
120°	770.0	852.8	924.0	978.7	1015.4	1038.1	1045.9
122.5°	745.0	823.4	887.7	936.8	972.9	993.1	999.6
125°	712.1	780.9	839.5	884.9	914.6	934.1	940.4
127.5°	680.2	745.1	799.2	838.8	866.6	883.5	888.5
130°	659.0	720.7	772.3	810.6	837.2	852.8	859.1
132.5°	639.0	695.7	744.2	781.9	808.4	822.8	828.4
135°	607.4	659.0	702.7	736.4	762.2	776.2	779.4
137.5°	582.2	623.2	661.3	692.0	714.2	726.5	731.2
140°	566.0	601.9	636.3	661.3	681.6	693.4	698.1
142.5°	551.6	582.5	611.3	635.1	653.5	664.0	664.9
145°	533.1	557.4	580.0	598.8	612.1	619.9	622.2
147.5°	518.1	537.0	553.6	569.1	579.7	585.0	586.4
150°	508.1	524.5	538.6	550.3	559.7	564.4	565.2
152.5°	500.0	513.9	526.1	535.3	543.4	546.9	547.0
155°	487.0	498.7	507.3	515.9	521.4	524.5	523.0
157.5°	473.9	483.7	490.4	496.5	501.1	502.5	502.5
160°	465.1	473.7	479.2	484.7	488.6	489.3	489.3
162.5°	457.0	464.3	468.6	474.0	476.7	477.5	476.8
165°	444.8	450.3	453.4	456.5	459.6	459.6	458.9
167.5°	433.7	437.4	440.3	441.7	443.4	443.2	442.3
170°	426.8	429.9	431.5	432.3	434.6	433.8	432.3
172.5°	420.6	423.1	424.0	424.8	425.9	425.1	424.2
175°	413.5	414.3	415.1	415.1	415.9	415.1	413.5
177.5°	408.4	409.0	409.0	409.0	409.0	408.4	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5

(END OF REPORT)