

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331260-935

Luminaire Tested: **SA2XXDIP-C290D725U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331260-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3561.4 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331260-935
CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32				
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27				
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23				
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20				
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	17				
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15				
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14				
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12				
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11				
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10				
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	1.4
10°-20°	140.9	4.0
20°-30°	204.5	5.7
30°-40°	215.8	6.1
40°-50°	191.1	5.4
50°-60°	152.5	4.3
60°-70°	103.6	2.9
70°-80°	53.1	1.5
80°-90°	16.0	0.4
90°-100°	139.9	3.9
100°-110°	474.9	13.3
110°-120°	504.5	14.2
120°-130°	415.3	11.7
130°-140°	333.5	9.4
140°-150°	252.0	7.1
150°-160°	177.1	5.0
160°-170°	104.3	2.9
170°-180°	33.9	1.0
0°-30°	393.9	11.1
0°-40°	609.7	17.1
0°-60°	953.2	26.8
0°-90°	1125.9	31.6
90°-120°	1119.3	31.4
90°-150°	2120.1	59.5
90°-180°	2435.0	68.4
0°-180°	3561.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	22	1	22	1	22	12
95°	77	24	77	24	77	100
105°	758	82	758	82	758	734
115°	998	145	998	145	998	977
125°	810	202	810	202	810	732
135°	671	237	671	237	671	521
145°	536	270	536	270	536	340
155°	450	308	450	308	450	210
165°	395	335	395	335	395	113
175°	356	349	356	349	356	35
180°	350	350	350	350	350	



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	8.5	8.5	8.7	8.5	8.5	8.5	8.3	8.4	8.7	9.0	9.0
90°	22.2	22.2	22.2	22.2	22.2	21.5	20.2	21.5	22.2	22.9	22.2
92.5°	37.3	38.4	37.8	40.0	40.6	44.7	50.4	58.7	73.9	87.5	86.3
95°	76.7	76.0	78.1	83.4	92.2	107.0	135.3	176.3	230.8	263.8	233.6
97.5°	151.0	156.7	166.5	183.0	215.2	263.8	336.7	411.5	472.5	450.4	339.2
100°	240.9	253.0	272.6	301.5	357.4	438.9	531.1	614.5	628.6	531.7	366.1
102.5°	424.0	440.4	464.8	514.2	574.9	661.2	728.7	747.5	686.7	534.4	355.9
105°	758.5	767.9	796.9	838.6	880.4	902.6	893.8	817.8	677.8	498.7	335.9
107.5°	968.9	981.5	987.2	989.5	984.3	951.7	881.7	767.2	618.6	460.5	325.9
110°	1032.4	1033.1	1027.1	1014.3	985.3	930.1	844.0	723.5	581.5	442.2	323.7



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1031.4	1027.8	1016.3	994.9	954.7	891.4	799.3	683.7	555.7	430.3	324.3
115°	998.2	992.0	974.6	943.6	895.8	826.5	738.3	634.6	523.7	417.3	327.1
117.5°	938.7	933.7	915.2	882.5	833.8	768.8	688.8	597.8	503.4	411.0	331.9
120°	900.5	893.8	874.3	842.7	795.6	734.3	663.0	579.5	492.7	407.2	335.2
122.5°	860.7	855.1	837.7	806.6	764.3	708.9	641.4	565.0	483.5	405.0	339.0
125°	809.7	804.3	787.5	761.9	722.8	672.4	613.1	543.8	470.5	401.1	344.6
127.5°	765.0	760.7	746.1	722.2	688.1	641.5	585.7	523.0	458.3	398.8	350.4
130°	739.7	734.3	720.8	697.9	665.0	620.5	567.4	509.5	450.3	397.8	354.7
132.5°	713.3	708.4	696.0	673.2	640.8	599.0	550.2	496.5	443.8	397.3	359.0
135°	671.1	668.3	656.3	634.0	605.0	567.4	523.0	478.5	434.8	396.4	364.1
137.5°	629.6	625.5	614.9	595.8	569.4	536.6	501.3	464.2	428.4	396.3	368.7
140°	601.1	597.0	586.9	569.4	547.9	518.2	487.3	455.0	424.7	395.7	370.8
142.5°	572.5	571.7	562.7	546.8	526.3	501.5	474.9	447.5	420.9	395.7	372.5
145°	535.7	533.7	527.0	515.6	499.4	479.9	459.0	436.8	415.9	394.4	374.2
147.5°	504.9	503.7	499.1	490.0	476.6	462.4	446.1	428.6	410.9	392.0	374.8
150°	486.6	485.9	481.9	473.8	463.7	451.6	437.5	422.7	406.5	390.4	374.2
152.5°	471.0	470.9	467.9	460.9	453.0	442.5	430.5	416.7	402.8	387.7	373.2
155°	450.3	451.6	448.9	444.2	436.8	429.4	419.3	408.5	395.7	383.0	371.5
157.5°	432.7	432.7	431.4	427.5	422.2	416.5	408.0	399.0	389.2	378.2	368.4
160°	421.3	421.3	420.7	417.3	412.6	407.9	400.5	393.0	384.4	374.9	366.8
162.5°	410.5	411.1	410.4	408.1	403.5	399.8	393.5	387.1	380.0	372.2	365.2
165°	395.1	395.7	395.7	393.0	390.4	387.7	383.0	378.2	372.9	366.8	362.1
167.5°	380.8	381.6	381.8	380.3	379.1	376.6	373.4	369.8	365.8	362.1	359.0
170°	372.2	373.5	374.2	372.2	371.5	370.1	367.5	365.5	362.1	359.4	357.4
172.5°	365.2	366.0	366.7	365.8	365.1	364.3	362.1	360.6	358.3	356.2	355.2
175°	356.0	357.4	358.1	357.4	357.4	356.7	356.0	355.3	353.4	352.7	352.0
177.5°	350.5	351.6	352.1	352.1	352.1	352.1	351.6	351.6	350.5	350.0	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	8.4	7.4	6.7	6.6	5.9	5.6	4.5	3.6	3.8	4.2	4.1
90°	18.2	13.4	10.1	8.1	6.7	5.4	2.7	0.7	2.7	5.4	6.7
92.5°	67.2	45.8	30.6	24.2	19.6	16.7	11.9	8.2	11.9	16.7	19.6
95°	155.5	96.9	66.0	49.8	39.0	33.0	26.3	23.6	26.3	33.0	39.0
97.5°	209.5	127.9	88.9	70.7	58.3	49.2	42.0	38.4	42.0	49.2	58.3
100°	220.8	138.6	103.0	84.1	70.7	59.9	53.8	51.8	53.8	59.9	70.7
102.5°	221.3	148.4	115.4	96.5	82.5	71.7	65.7	64.2	65.7	71.7	82.5
105°	224.8	164.9	133.3	114.4	99.6	89.5	84.8	82.1	84.8	89.5	99.6
107.5°	234.1	181.8	151.2	132.2	117.5	108.2	103.7	101.5	103.7	108.2	117.5
110°	241.6	193.1	163.6	144.0	129.9	121.1	117.1	114.4	117.1	121.1	129.9



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	249.7	204.0	175.4	155.3	141.7	133.5	129.0	126.2	129.0	133.5	141.7
115°	261.8	220.8	191.8	173.7	160.1	152.1	148.1	144.7	148.1	152.1	160.1
117.5°	274.7	236.3	209.5	190.6	177.7	170.6	166.5	163.8	166.5	170.6	177.7
120°	283.4	247.0	220.8	201.9	188.5	182.4	178.4	175.6	178.4	182.4	188.5
122.5°	290.9	257.3	232.6	213.2	199.8	193.1	189.2	187.0	189.2	193.1	199.8
125°	302.9	272.6	248.3	229.5	216.0	207.9	204.0	201.9	204.0	207.9	216.0
127.5°	314.0	286.9	263.3	243.9	231.0	222.1	216.5	213.8	216.5	222.1	231.0
130°	321.1	295.5	271.9	253.0	239.6	230.1	223.4	220.8	223.4	230.1	239.6
132.5°	328.0	303.0	280.5	261.7	247.7	237.7	230.5	227.2	230.5	237.7	247.7
135°	337.2	313.7	292.1	273.3	257.8	247.7	239.6	236.9	239.6	247.7	257.8
137.5°	344.2	322.3	301.0	283.5	268.1	257.4	249.3	246.1	249.3	257.4	268.1
140°	347.9	327.1	306.9	289.4	274.6	263.8	255.7	253.0	255.7	263.8	274.6
142.5°	351.2	330.9	311.3	294.8	280.5	269.8	262.3	260.0	262.3	269.8	280.5
145°	355.3	336.6	318.3	303.5	290.1	280.0	273.3	270.5	273.3	280.0	290.1
147.5°	357.7	341.1	324.0	310.8	299.6	290.3	283.9	281.9	283.9	290.3	299.6
150°	358.7	343.3	327.8	315.6	305.6	296.8	291.4	289.4	291.4	296.8	305.6
152.5°	359.3	345.4	331.6	320.5	310.9	303.2	297.9	297.0	297.9	303.2	310.9
155°	360.1	348.6	337.2	327.1	319.7	312.3	308.2	307.5	308.2	312.3	319.7
157.5°	360.1	350.9	341.2	332.8	326.8	320.4	317.1	316.5	317.1	320.4	326.8
160°	360.1	352.0	343.9	336.6	331.1	325.7	323.0	322.4	323.0	325.7	331.1
162.5°	359.6	352.6	345.5	339.8	334.9	330.6	327.9	328.3	327.9	330.6	334.9
165°	358.1	353.4	347.3	343.3	339.9	335.9	334.5	335.2	334.5	335.9	339.9
167.5°	357.1	353.2	348.8	346.2	343.8	341.2	340.0	340.9	340.0	341.2	343.8
170°	356.0	352.7	349.3	347.3	345.9	343.9	343.3	344.6	343.3	343.9	345.9
172.5°	354.4	352.1	349.8	348.4	347.6	345.5	345.9	346.7	345.9	345.5	347.6
175°	352.7	351.3	350.0	349.3	349.3	347.9	348.6	349.3	348.6	347.9	349.3
177.5°	351.6	350.5	350.0	350.0	350.0	348.9	349.5	350.5	349.5	348.9	350.0
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	4.3	4.6	5.1	5.9	6.6	6.6	6.3	6.2	5.9	5.9	6.0
90°	8.1	10.1	13.4	18.2	22.2	22.9	22.2	21.5	20.2	21.5	22.2
92.5°	24.2	30.6	45.8	67.2	86.3	87.5	73.9	58.7	50.4	44.7	40.6
95°	49.8	66.0	96.9	155.5	233.6	263.8	230.8	176.3	135.3	107.0	92.2
97.5°	70.7	88.9	127.9	209.5	339.2	450.4	472.5	411.5	336.7	263.8	215.2
100°	84.1	103.0	138.6	220.8	366.1	531.7	628.6	614.5	531.1	438.9	357.4
102.5°	96.5	115.4	148.4	221.3	355.9	534.4	686.7	747.5	728.7	661.2	574.9
105°	114.4	133.3	164.9	224.8	335.9	498.7	677.8	817.8	893.8	902.6	880.4
107.5°	132.2	151.2	181.8	234.1	325.9	460.5	618.6	767.2	881.7	951.7	984.3
110°	144.0	163.6	193.1	241.6	323.7	442.2	581.5	723.5	844.0	930.1	985.3



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	155.3	175.4	204.0	249.7	324.3	430.3	555.7	683.7	799.3	891.4	954.7
115°	173.7	191.8	220.8	261.8	327.1	417.3	523.7	634.6	738.3	826.5	895.8
117.5°	190.6	209.5	236.3	274.7	331.9	411.0	503.4	597.8	688.8	768.8	833.8
120°	201.9	220.8	247.0	283.4	335.2	407.2	492.7	579.5	663.0	734.3	795.6
122.5°	213.2	232.6	257.3	290.9	339.0	405.0	483.5	565.0	641.4	708.9	764.3
125°	229.5	248.3	272.6	302.9	344.6	401.1	470.5	543.8	613.1	672.4	722.8
127.5°	243.9	263.3	286.9	314.0	350.4	398.8	458.3	523.0	585.7	641.5	688.1
130°	253.0	271.9	295.5	321.1	354.7	397.8	450.3	509.5	567.4	620.5	665.0
132.5°	261.7	280.5	303.0	328.0	359.0	397.3	443.8	496.5	550.2	599.0	640.8
135°	273.3	292.1	313.7	337.2	364.1	396.4	434.8	478.5	523.0	567.4	605.0
137.5°	283.5	301.0	322.3	344.2	368.7	396.3	428.4	464.2	501.3	536.6	569.4
140°	289.4	306.9	327.1	347.9	370.8	395.7	424.7	455.0	487.3	518.2	547.9
142.5°	294.8	311.3	330.9	351.2	372.5	395.7	420.9	447.5	474.9	501.5	526.3
145°	303.5	318.3	336.6	355.3	374.2	394.4	415.9	436.8	459.0	479.9	499.4
147.5°	310.8	324.0	341.1	357.7	374.8	392.0	410.9	428.6	446.1	462.4	476.6
150°	315.6	327.8	343.3	358.7	374.2	390.4	406.5	422.7	437.5	451.6	463.7
152.5°	320.5	331.6	345.4	359.3	373.2	387.7	402.8	416.7	430.5	442.5	453.0
155°	327.1	337.2	348.6	360.1	371.5	383.0	395.7	408.5	419.3	429.4	436.8
157.5°	332.8	341.2	350.9	360.1	368.4	378.2	389.2	399.0	408.0	416.5	422.2
160°	336.6	343.9	352.0	360.1	366.8	374.9	384.4	393.0	400.5	407.9	412.6
162.5°	339.8	345.5	352.6	359.6	365.2	372.2	380.0	387.1	393.5	399.8	403.5
165°	343.3	347.3	353.4	358.1	362.1	366.8	372.9	378.2	383.0	387.7	390.4
167.5°	346.2	348.8	353.2	357.1	359.0	362.1	365.8	369.8	373.4	376.6	379.1
170°	347.3	349.3	352.7	356.0	357.4	359.4	362.1	365.5	367.5	370.1	371.5
172.5°	348.4	349.8	352.1	354.4	355.2	356.2	358.3	360.6	362.1	364.3	365.1
175°	349.3	350.0	351.3	352.7	352.0	352.7	353.4	355.3	356.0	356.7	357.4
177.5°	350.0	350.0	350.5	351.6	350.5	350.0	350.5	351.6	351.6	352.1	352.1
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	6.0	5.9	5.9	5.7	5.9	5.9	6.0	6.0	5.9	5.9	6.2
90°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.5	20.2	21.5
92.5°	40.0	37.8	38.4	37.3	38.4	37.8	40.0	40.6	44.7	50.4	58.7
95°	83.4	78.1	76.0	76.7	76.0	78.1	83.4	92.2	107.0	135.3	176.3
97.5°	183.0	166.5	156.7	151.0	156.7	166.5	183.0	215.2	263.8	336.7	411.5
100°	301.5	272.6	253.0	240.9	253.0	272.6	301.5	357.4	438.9	531.1	614.5
102.5°	514.2	464.8	440.4	424.0	440.4	464.8	514.2	574.9	661.2	728.7	747.5
105°	838.6	796.9	767.9	758.5	767.9	796.9	838.6	880.4	902.6	893.8	817.8
107.5°	989.5	987.2	981.5	968.9	981.5	987.2	989.5	984.3	951.7	881.7	767.2
110°	1014.3	1027.1	1033.1	1032.4	1033.1	1027.1	1014.3	985.3	930.1	844.0	723.5



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	994.9	1016.3	1027.8	1031.4	1027.8	1016.3	994.9	954.7	891.4	799.3	683.7
115°	943.6	974.6	992.0	998.2	992.0	974.6	943.6	895.8	826.5	738.3	634.6
117.5°	882.5	915.2	933.7	938.7	933.7	915.2	882.5	833.8	768.8	688.8	597.8
120°	842.7	874.3	893.8	900.5	893.8	874.3	842.7	795.6	734.3	663.0	579.5
122.5°	806.6	837.7	855.1	860.7	855.1	837.7	806.6	764.3	708.9	641.4	565.0
125°	761.9	787.5	804.3	809.7	804.3	787.5	761.9	722.8	672.4	613.1	543.8
127.5°	722.2	746.1	760.7	765.0	760.7	746.1	722.2	688.1	641.5	585.7	523.0
130°	697.9	720.8	734.3	739.7	734.3	720.8	697.9	665.0	620.5	567.4	509.5
132.5°	673.2	696.0	708.4	713.3	708.4	696.0	673.2	640.8	599.0	550.2	496.5
135°	634.0	656.3	668.3	671.1	668.3	656.3	634.0	605.0	567.4	523.0	478.5
137.5°	595.8	614.9	625.5	629.6	625.5	614.9	595.8	569.4	536.6	501.3	464.2
140°	569.4	586.9	597.0	601.1	597.0	586.9	569.4	547.9	518.2	487.3	455.0
142.5°	546.8	562.7	571.7	572.5	571.7	562.7	546.8	526.3	501.5	474.9	447.5
145°	515.6	527.0	533.7	535.7	533.7	527.0	515.6	499.4	479.9	459.0	436.8
147.5°	490.0	499.1	503.7	504.9	503.7	499.1	490.0	476.6	462.4	446.1	428.6
150°	473.8	481.9	485.9	486.6	485.9	481.9	473.8	463.7	451.6	437.5	422.7
152.5°	460.9	467.9	470.9	471.0	470.9	467.9	460.9	453.0	442.5	430.5	416.7
155°	444.2	448.9	451.6	450.3	451.6	448.9	444.2	436.8	429.4	419.3	408.5
157.5°	427.5	431.4	432.7	432.7	432.7	431.4	427.5	422.2	416.5	408.0	399.0
160°	417.3	420.7	421.3	421.3	421.3	420.7	417.3	412.6	407.9	400.5	393.0
162.5°	408.1	410.4	411.1	410.5	411.1	410.4	408.1	403.5	399.8	393.5	387.1
165°	393.0	395.7	395.7	395.1	395.7	395.7	393.0	390.4	387.7	383.0	378.2
167.5°	380.3	381.8	381.6	380.8	381.6	381.8	380.3	379.1	376.6	373.4	369.8
170°	372.2	374.2	373.5	372.2	373.5	374.2	372.2	371.5	370.1	367.5	365.5
172.5°	365.8	366.7	366.0	365.2	366.0	366.7	365.8	365.1	364.3	362.1	360.6
175°	357.4	358.1	357.4	356.0	357.4	358.1	357.4	357.4	356.7	356.0	355.3
177.5°	352.1	352.1	351.6	350.5	351.6	352.1	352.1	352.1	352.1	351.6	351.6
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	6.3	6.6	6.6	5.9	5.1	4.6	4.3	4.1	4.2	3.8	3.6
90°	22.2	22.9	22.2	18.2	13.4	10.1	8.1	6.7	5.4	2.7	0.7
92.5°	73.9	87.5	86.3	67.2	45.8	30.6	24.2	19.6	16.7	11.9	8.2
95°	230.8	263.8	233.6	155.5	96.9	66.0	49.8	39.0	33.0	26.3	23.6
97.5°	472.5	450.4	339.2	209.5	127.9	88.9	70.7	58.3	49.2	42.0	38.4
100°	628.6	531.7	366.1	220.8	138.6	103.0	84.1	70.7	59.9	53.8	51.8
102.5°	686.7	534.4	355.9	221.3	148.4	115.4	96.5	82.5	71.7	65.7	64.2
105°	677.8	498.7	335.9	224.8	164.9	133.3	114.4	99.6	89.5	84.8	82.1
107.5°	618.6	460.5	325.9	234.1	181.8	151.2	132.2	117.5	108.2	103.7	101.5
110°	581.5	442.2	323.7	241.6	193.1	163.6	144.0	129.9	121.1	117.1	114.4



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	555.7	430.3	324.3	249.7	204.0	175.4	155.3	141.7	133.5	129.0	126.2
115°	523.7	417.3	327.1	261.8	220.8	191.8	173.7	160.1	152.1	148.1	144.7
117.5°	503.4	411.0	331.9	274.7	236.3	209.5	190.6	177.7	170.6	166.5	163.8
120°	492.7	407.2	335.2	283.4	247.0	220.8	201.9	188.5	182.4	178.4	175.6
122.5°	483.5	405.0	339.0	290.9	257.3	232.6	213.2	199.8	193.1	189.2	187.0
125°	470.5	401.1	344.6	302.9	272.6	248.3	229.5	216.0	207.9	204.0	201.9
127.5°	458.3	398.8	350.4	314.0	286.9	263.3	243.9	231.0	222.1	216.5	213.8
130°	450.3	397.8	354.7	321.1	295.5	271.9	253.0	239.6	230.1	223.4	220.8
132.5°	443.8	397.3	359.0	328.0	303.0	280.5	261.7	247.7	237.7	230.5	227.2
135°	434.8	396.4	364.1	337.2	313.7	292.1	273.3	257.8	247.7	239.6	236.9
137.5°	428.4	396.3	368.7	344.2	322.3	301.0	283.5	268.1	257.4	249.3	246.1
140°	424.7	395.7	370.8	347.9	327.1	306.9	289.4	274.6	263.8	255.7	253.0
142.5°	420.9	395.7	372.5	351.2	330.9	311.3	294.8	280.5	269.8	262.3	260.0
145°	415.9	394.4	374.2	355.3	336.6	318.3	303.5	290.1	280.0	273.3	270.5
147.5°	410.9	392.0	374.8	357.7	341.1	324.0	310.8	299.6	290.3	283.9	281.9
150°	406.5	390.4	374.2	358.7	343.3	327.8	315.6	305.6	296.8	291.4	289.4
152.5°	402.8	387.7	373.2	359.3	345.4	331.6	320.5	310.9	303.2	297.9	297.0
155°	395.7	383.0	371.5	360.1	348.6	337.2	327.1	319.7	312.3	308.2	307.5
157.5°	389.2	378.2	368.4	360.1	350.9	341.2	332.8	326.8	320.4	317.1	316.5
160°	384.4	374.9	366.8	360.1	352.0	343.9	336.6	331.1	325.7	323.0	322.4
162.5°	380.0	372.2	365.2	359.6	352.6	345.5	339.8	334.9	330.6	327.9	328.3
165°	372.9	366.8	362.1	358.1	353.4	347.3	343.3	339.9	335.9	334.5	335.2
167.5°	365.8	362.1	359.0	357.1	353.2	348.8	346.2	343.8	341.2	340.0	340.9
170°	362.1	359.4	357.4	356.0	352.7	349.3	347.3	345.9	343.9	343.3	344.6
172.5°	358.3	356.2	355.2	354.4	352.1	349.8	348.4	347.6	345.5	345.9	346.7
175°	353.4	352.7	352.0	352.7	351.3	350.0	349.3	349.3	347.9	348.6	349.3
177.5°	350.5	350.0	350.5	351.6	350.5	350.0	350.0	350.0	348.9	349.5	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331260-935
 CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.5	5.6	5.9	6.6	6.7	7.4	8.4	9.0	9.0	8.7	8.4
90°	2.7	5.4	6.7	8.1	10.1	13.4	18.2	22.2	22.9	22.2	21.5
92.5°	11.9	16.7	19.6	24.2	30.6	45.8	67.2	86.3	87.5	73.9	58.7
95°	26.3	33.0	39.0	49.8	66.0	96.9	155.5	233.6	263.8	230.8	176.3
97.5°	42.0	49.2	58.3	70.7	88.9	127.9	209.5	339.2	450.4	472.5	411.5
100°	53.8	59.9	70.7	84.1	103.0	138.6	220.8	366.1	531.7	628.6	614.5
102.5°	65.7	71.7	82.5	96.5	115.4	148.4	221.3	355.9	534.4	686.7	747.5
105°	84.8	89.5	99.6	114.4	133.3	164.9	224.8	335.9	498.7	677.8	817.8
107.5°	103.7	108.2	117.5	132.2	151.2	181.8	234.1	325.9	460.5	618.6	767.2
110°	117.1	121.1	129.9	144.0	163.6	193.1	241.6	323.7	442.2	581.5	723.5



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	129.0	133.5	141.7	155.3	175.4	204.0	249.7	324.3	430.3	555.7	683.7
115°	148.1	152.1	160.1	173.7	191.8	220.8	261.8	327.1	417.3	523.7	634.6
117.5°	166.5	170.6	177.7	190.6	209.5	236.3	274.7	331.9	411.0	503.4	597.8
120°	178.4	182.4	188.5	201.9	220.8	247.0	283.4	335.2	407.2	492.7	579.5
122.5°	189.2	193.1	199.8	213.2	232.6	257.3	290.9	339.0	405.0	483.5	565.0
125°	204.0	207.9	216.0	229.5	248.3	272.6	302.9	344.6	401.1	470.5	543.8
127.5°	216.5	222.1	231.0	243.9	263.3	286.9	314.0	350.4	398.8	458.3	523.0
130°	223.4	230.1	239.6	253.0	271.9	295.5	321.1	354.7	397.8	450.3	509.5
132.5°	230.5	237.7	247.7	261.7	280.5	303.0	328.0	359.0	397.3	443.8	496.5
135°	239.6	247.7	257.8	273.3	292.1	313.7	337.2	364.1	396.4	434.8	478.5
137.5°	249.3	257.4	268.1	283.5	301.0	322.3	344.2	368.7	396.3	428.4	464.2
140°	255.7	263.8	274.6	289.4	306.9	327.1	347.9	370.8	395.7	424.7	455.0
142.5°	262.3	269.8	280.5	294.8	311.3	330.9	351.2	372.5	395.7	420.9	447.5
145°	273.3	280.0	290.1	303.5	318.3	336.6	355.3	374.2	394.4	415.9	436.8
147.5°	283.9	290.3	299.6	310.8	324.0	341.1	357.7	374.8	392.0	410.9	428.6
150°	291.4	296.8	305.6	315.6	327.8	343.3	358.7	374.2	390.4	406.5	422.7
152.5°	297.9	303.2	310.9	320.5	331.6	345.4	359.3	373.2	387.7	402.8	416.7
155°	308.2	312.3	319.7	327.1	337.2	348.6	360.1	371.5	383.0	395.7	408.5
157.5°	317.1	320.4	326.8	332.8	341.2	350.9	360.1	368.4	378.2	389.2	399.0
160°	323.0	325.7	331.1	336.6	343.9	352.0	360.1	366.8	374.9	384.4	393.0
162.5°	327.9	330.6	334.9	339.8	345.5	352.6	359.6	365.2	372.2	380.0	387.1
165°	334.5	335.9	339.9	343.3	347.3	353.4	358.1	362.1	366.8	372.9	378.2
167.5°	340.0	341.2	343.8	346.2	348.8	353.2	357.1	359.0	362.1	365.8	369.8
170°	343.3	343.9	345.9	347.3	349.3	352.7	356.0	357.4	359.4	362.1	365.5
172.5°	345.9	345.5	347.6	348.4	349.8	352.1	354.4	355.2	356.2	358.3	360.6
175°	348.6	347.9	349.3	349.3	350.0	351.3	352.7	352.0	352.7	353.4	355.3
177.5°	349.5	348.9	350.0	350.0	350.0	350.5	351.6	350.5	350.0	350.5	351.6
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	8.3	8.5	8.5	8.5	8.7	8.5	8.5
90°	20.2	21.5	22.2	22.2	22.2	22.2	22.2
92.5°	50.4	44.7	40.6	40.0	37.8	38.4	37.3
95°	135.3	107.0	92.2	83.4	78.1	76.0	76.7
97.5°	336.7	263.8	215.2	183.0	166.5	156.7	151.0
100°	531.1	438.9	357.4	301.5	272.6	253.0	240.9
102.5°	728.7	661.2	574.9	514.2	464.8	440.4	424.0
105°	893.8	902.6	880.4	838.6	796.9	767.9	758.5
107.5°	881.7	951.7	984.3	989.5	987.2	981.5	968.9
110°	844.0	930.1	985.3	1014.3	1027.1	1033.1	1032.4



TEST NUMBER: P331260-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	799.3	891.4	954.7	994.9	1016.3	1027.8	1031.4
115°	738.3	826.5	895.8	943.6	974.6	992.0	998.2
117.5°	688.8	768.8	833.8	882.5	915.2	933.7	938.7
120°	663.0	734.3	795.6	842.7	874.3	893.8	900.5
122.5°	641.4	708.9	764.3	806.6	837.7	855.1	860.7
125°	613.1	672.4	722.8	761.9	787.5	804.3	809.7
127.5°	585.7	641.5	688.1	722.2	746.1	760.7	765.0
130°	567.4	620.5	665.0	697.9	720.8	734.3	739.7
132.5°	550.2	599.0	640.8	673.2	696.0	708.4	713.3
135°	523.0	567.4	605.0	634.0	656.3	668.3	671.1
137.5°	501.3	536.6	569.4	595.8	614.9	625.5	629.6
140°	487.3	518.2	547.9	569.4	586.9	597.0	601.1
142.5°	474.9	501.5	526.3	546.8	562.7	571.7	572.5
145°	459.0	479.9	499.4	515.6	527.0	533.7	535.7
147.5°	446.1	462.4	476.6	490.0	499.1	503.7	504.9
150°	437.5	451.6	463.7	473.8	481.9	485.9	486.6
152.5°	430.5	442.5	453.0	460.9	467.9	470.9	471.0
155°	419.3	429.4	436.8	444.2	448.9	451.6	450.3
157.5°	408.0	416.5	422.2	427.5	431.4	432.7	432.7
160°	400.5	407.9	412.6	417.3	420.7	421.3	421.3
162.5°	393.5	399.8	403.5	408.1	410.4	411.1	410.5
165°	383.0	387.7	390.4	393.0	395.7	395.7	395.1
167.5°	373.4	376.6	379.1	380.3	381.8	381.6	380.8
170°	367.5	370.1	371.5	372.2	374.2	373.5	372.2
172.5°	362.1	364.3	365.1	365.8	366.7	366.0	365.2
175°	356.0	356.7	357.4	357.4	358.1	357.4	356.0
177.5°	351.6	352.1	352.1	352.1	352.1	351.6	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0

(END OF REPORT)