

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331269-935

Luminaire Tested: **SA2XXDIP-C290D925U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331269-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4236.2 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331269-935
CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25	20				
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17				
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15				
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13				
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15	11				
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10				
8	51	39	32	27	46	36	29	25	28	24	20	22	19	16	15	13	12	9				
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	1.1
10°-20°	140.9	3.3
20°-30°	204.5	4.8
30°-40°	215.8	5.1
40°-50°	191.1	4.5
50°-60°	152.5	3.6
60°-70°	103.6	2.4
70°-80°	53.1	1.3
80°-90°	16.8	0.4
90°-100°	178.7	4.2
100°-110°	606.3	14.3
110°-120°	644.1	15.2
120°-130°	530.2	12.5
130°-140°	425.8	10.1
140°-150°	321.8	7.6
150°-160°	226.1	5.3
160°-170°	133.1	3.1
170°-180°	43.3	1.0
0°-30°	393.9	9.3
0°-40°	609.7	14.4
0°-60°	953.2	22.5
0°-90°	1126.8	26.6
90°-120°	1429.1	33.7
90°-150°	2706.8	63.9
90°-180°	3109.0	73.4
0°-180°	4236.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	28	1	28	1	28	16
95°	98	30	98	30	98	127
105°	968	105	968	105	968	937
115°	1274	185	1274	185	1274	1248
125°	1034	258	1034	258	1034	934
135°	857	302	857	302	857	666
145°	684	345	684	345	684	434
155°	575	393	575	393	575	268
165°	504	428	504	428	504	144
175°	455	446	455	446	455	44
180°	447	447	447	447	447	



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	9.7	9.7	9.9	9.7	9.7	9.7	9.4	9.6	9.9	10.2	10.2
90°	28.3	28.3	28.3	28.3	28.3	27.5	25.7	27.5	28.3	29.2	28.3
92.5°	47.6	49.0	48.3	51.1	51.7	57.1	64.3	74.9	94.4	111.7	110.1
95°	98.0	97.1	99.7	106.6	117.7	136.6	172.7	225.2	294.7	336.8	298.2
97.5°	192.9	200.0	212.6	233.8	274.8	336.8	429.8	525.4	603.2	575.1	433.1
100°	307.6	323.1	348.0	385.0	456.3	560.3	678.0	784.5	802.6	678.8	467.4
102.5°	541.4	562.3	593.4	656.5	734.0	844.2	930.3	954.3	876.8	682.3	454.4
105°	968.5	980.4	1017.4	1070.7	1123.9	1152.4	1141.2	1044.0	865.3	636.7	428.8
107.5°	1237.1	1253.0	1260.4	1263.3	1256.6	1215.0	1125.7	979.5	789.9	588.0	416.0
110°	1318.2	1319.1	1311.3	1294.9	1258.0	1187.6	1077.5	923.8	742.4	564.6	413.4



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1316.8	1312.2	1297.5	1270.2	1218.8	1138.1	1020.5	872.9	709.5	549.4	414.0
115°	1274.4	1266.6	1244.2	1204.7	1143.8	1055.2	942.6	810.3	668.6	532.8	417.6
117.5°	1198.5	1192.1	1168.5	1126.7	1064.5	981.5	879.4	763.2	642.7	524.7	423.8
120°	1149.8	1141.2	1116.2	1075.8	1015.7	937.5	846.4	739.9	629.0	519.9	427.9
122.5°	1098.9	1091.7	1069.4	1029.8	975.9	905.2	818.9	721.3	617.3	517.1	432.7
125°	1033.7	1026.8	1005.4	972.8	922.9	858.4	782.8	694.3	600.6	512.1	440.0
127.5°	976.7	971.2	952.6	922.0	878.6	819.1	747.8	667.7	585.2	509.2	447.4
130°	944.3	937.5	920.3	891.1	849.0	792.3	724.4	650.5	574.9	507.8	452.9
132.5°	910.7	904.5	888.7	859.5	818.0	764.7	702.4	634.0	566.6	507.1	458.3
135°	856.7	853.3	837.8	809.4	772.5	724.4	667.7	611.0	555.1	506.1	464.9
137.5°	803.8	798.7	785.1	760.7	726.9	685.0	640.0	592.5	547.0	505.9	470.7
140°	767.3	762.2	749.3	726.9	699.5	661.7	622.2	580.9	542.3	505.2	473.5
142.5°	730.9	729.9	718.4	698.1	672.0	640.3	606.3	571.3	537.4	505.2	475.5
145°	684.0	681.4	672.9	658.2	637.6	612.7	586.1	557.7	531.1	503.5	477.8
147.5°	644.6	643.1	637.2	625.6	608.6	590.3	569.6	547.2	524.5	500.5	478.5
150°	621.3	620.4	615.3	604.9	592.0	576.6	558.5	539.7	519.0	498.4	477.8
152.5°	601.3	601.2	597.4	588.4	578.3	564.9	549.6	532.1	514.2	495.0	476.4
155°	574.9	576.6	573.2	567.1	557.7	548.2	535.4	521.6	505.2	489.0	474.3
157.5°	552.3	552.3	550.8	545.8	539.2	531.8	520.9	509.4	496.9	482.8	470.4
160°	538.0	538.0	537.1	532.8	526.8	520.7	511.3	501.8	490.7	478.6	468.3
162.5°	524.2	524.9	524.0	521.1	515.1	510.4	502.3	494.3	485.2	475.2	466.2
165°	504.4	505.2	505.2	501.8	498.4	495.0	489.0	482.9	476.0	468.3	462.3
167.5°	486.2	487.2	487.4	485.5	484.0	480.9	476.7	472.1	467.1	462.3	458.3
170°	475.2	476.9	477.8	475.2	474.3	472.6	469.2	466.6	462.3	458.8	456.3
172.5°	466.2	467.3	468.1	466.9	466.1	465.0	462.3	460.4	457.5	454.8	453.6
175°	454.6	456.3	457.2	456.3	456.3	455.5	454.6	453.7	451.2	450.3	449.4
177.5°	447.5	448.9	449.6	449.6	449.6	449.6	448.9	448.9	447.5	446.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	9.3	8.1	7.2	7.1	6.3	5.9	4.6	3.6	4.0	4.5	4.6
90°	23.2	17.2	12.9	10.3	8.6	6.9	3.4	0.9	3.4	6.9	8.6
92.5°	85.8	58.5	39.0	30.9	25.1	21.4	15.2	10.5	15.2	21.4	25.1
95°	198.5	123.7	84.2	63.6	49.9	42.1	33.5	30.0	33.5	42.1	49.9
97.5°	267.4	163.2	113.6	90.2	74.4	62.8	53.6	49.0	53.6	62.8	74.4
100°	281.9	177.0	131.5	107.5	90.2	76.5	68.7	66.1	68.7	76.5	90.2
102.5°	282.6	189.4	147.3	123.2	105.4	91.6	83.9	82.0	83.9	91.6	105.4
105°	287.0	210.5	170.1	146.1	127.2	114.3	108.3	104.9	108.3	114.3	127.2
107.5°	298.9	232.2	193.0	168.8	150.1	138.2	132.3	129.6	132.3	138.2	150.1
110°	308.5	246.6	208.8	183.9	165.8	154.6	149.6	146.1	149.6	154.6	165.8



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	318.8	260.4	223.9	198.3	181.0	170.5	164.6	161.2	164.6	170.5	181.0
115°	334.2	281.9	244.9	221.7	204.5	194.2	189.1	184.8	189.1	194.2	204.5
117.5°	350.8	301.6	267.4	243.3	226.9	217.7	212.6	209.1	212.6	217.7	226.9
120°	361.8	315.4	281.9	257.8	240.6	232.9	227.7	224.3	227.7	232.9	240.6
122.5°	371.3	328.4	297.0	272.2	255.0	246.6	241.4	238.8	241.4	246.6	255.0
125°	386.7	348.0	317.1	293.0	275.9	265.5	260.4	257.8	260.4	265.5	275.9
127.5°	401.0	366.3	336.1	311.4	294.9	283.5	276.4	272.9	276.4	283.5	294.9
130°	409.9	377.2	347.2	323.1	305.9	293.9	285.2	281.9	285.2	293.9	305.9
132.5°	418.8	386.8	358.2	334.1	316.2	303.5	294.2	290.1	294.2	303.5	316.2
135°	430.5	400.5	372.9	348.9	329.1	316.2	305.9	302.5	305.9	316.2	329.1
137.5°	439.5	411.5	384.3	362.0	342.3	328.6	318.3	314.2	318.3	328.6	342.3
140°	444.3	417.6	391.8	369.5	350.6	336.8	326.6	323.1	326.6	336.8	350.6
142.5°	448.4	422.4	397.4	376.3	358.2	344.4	334.8	332.0	334.8	344.4	358.2
145°	453.7	429.6	406.5	387.5	370.4	357.5	348.9	345.4	348.9	357.5	370.4
147.5°	456.7	435.5	413.7	396.8	382.5	370.7	362.5	359.9	362.5	370.7	382.5
150°	458.0	438.2	418.4	403.0	390.1	378.9	372.0	369.5	372.0	378.9	390.1
152.5°	458.7	441.0	423.3	409.2	397.0	387.2	380.3	379.1	380.3	387.2	397.0
155°	459.7	445.1	430.5	417.6	408.2	398.7	393.6	392.7	393.6	398.7	408.2
157.5°	459.7	448.1	435.7	424.8	417.2	409.1	404.9	404.1	404.9	409.1	417.2
160°	459.7	449.4	439.1	429.6	422.8	415.9	412.5	411.6	412.5	415.9	422.8
162.5°	459.0	450.1	441.2	433.8	427.6	422.1	418.6	419.1	418.6	422.1	427.6
165°	457.2	451.2	443.4	438.2	433.9	428.8	427.1	427.9	427.1	428.8	433.9
167.5°	456.0	451.0	445.3	442.0	438.9	435.7	434.1	435.1	434.1	435.7	438.9
170°	454.6	450.3	446.0	443.4	441.7	439.1	438.2	440.0	438.2	439.1	441.7
172.5°	452.5	449.6	446.7	444.8	443.8	441.2	441.7	442.7	441.7	441.2	443.8
175°	450.3	448.6	446.9	446.0	446.0	444.3	445.1	446.0	445.1	444.3	446.0
177.5°	448.9	447.5	446.9	446.9	446.9	445.5	446.2	447.5	446.2	445.5	446.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	4.7	5.1	5.8	7.0	7.8	7.8	7.6	7.4	7.1	7.1	7.2
90°	10.3	12.9	17.2	23.2	28.3	29.2	28.3	27.5	25.7	27.5	28.3
92.5°	30.9	39.0	58.5	85.8	110.1	111.7	94.4	74.9	64.3	57.1	51.7
95°	63.6	84.2	123.7	198.5	298.2	336.8	294.7	225.2	172.7	136.6	117.7
97.5°	90.2	113.6	163.2	267.4	433.1	575.1	603.2	525.4	429.8	336.8	274.8
100°	107.5	131.5	177.0	281.9	467.4	678.8	802.6	784.5	678.0	560.3	456.3
102.5°	123.2	147.3	189.4	282.6	454.4	682.3	876.8	954.3	930.3	844.2	734.0
105°	146.1	170.1	210.5	287.0	428.8	636.7	865.3	1044.0	1141.2	1152.4	1123.9
107.5°	168.8	193.0	232.2	298.9	416.0	588.0	789.9	979.5	1125.7	1215.0	1256.6
110°	183.9	208.8	246.6	308.5	413.4	564.6	742.4	923.8	1077.5	1187.6	1258.0



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.3	223.9	260.4	318.8	414.0	549.4	709.5	872.9	1020.5	1138.1	1218.8
115°	221.7	244.9	281.9	334.2	417.6	532.8	668.6	810.3	942.6	1055.2	1143.8
117.5°	243.3	267.4	301.6	350.8	423.8	524.7	642.7	763.2	879.4	981.5	1064.5
120°	257.8	281.9	315.4	361.8	427.9	519.9	629.0	739.9	846.4	937.5	1015.7
122.5°	272.2	297.0	328.4	371.3	432.7	517.1	617.3	721.3	818.9	905.2	975.9
125°	293.0	317.1	348.0	386.7	440.0	512.1	600.6	694.3	782.8	858.4	922.9
127.5°	311.4	336.1	366.3	401.0	447.4	509.2	585.2	667.7	747.8	819.1	878.6
130°	323.1	347.2	377.2	409.9	452.9	507.8	574.9	650.5	724.4	792.3	849.0
132.5°	334.1	358.2	386.8	418.8	458.3	507.1	566.6	634.0	702.4	764.7	818.0
135°	348.9	372.9	400.5	430.5	464.9	506.1	555.1	611.0	667.7	724.4	772.5
137.5°	362.0	384.3	411.5	439.5	470.7	505.9	547.0	592.5	640.0	685.0	726.9
140°	369.5	391.8	417.6	444.3	473.5	505.2	542.3	580.9	622.2	661.7	699.5
142.5°	376.3	397.4	422.4	448.4	475.5	505.2	537.4	571.3	606.3	640.3	672.0
145°	387.5	406.5	429.6	453.7	477.8	503.5	531.1	557.7	586.1	612.7	637.6
147.5°	396.8	413.7	435.5	456.7	478.5	500.5	524.5	547.2	569.6	590.3	608.6
150°	403.0	418.4	438.2	458.0	477.8	498.4	519.0	539.7	558.5	576.6	592.0
152.5°	409.2	423.3	441.0	458.7	476.4	495.0	514.2	532.1	549.6	564.9	578.3
155°	417.6	430.5	445.1	459.7	474.3	489.0	505.2	521.6	535.4	548.2	557.7
157.5°	424.8	435.7	448.1	459.7	470.4	482.8	496.9	509.4	520.9	531.8	539.2
160°	429.6	439.1	449.4	459.7	468.3	478.6	490.7	501.8	511.3	520.7	526.8
162.5°	433.8	441.2	450.1	459.0	466.2	475.2	485.2	494.3	502.3	510.4	515.1
165°	438.2	443.4	451.2	457.2	462.3	468.3	476.0	482.9	489.0	495.0	498.4
167.5°	442.0	445.3	451.0	456.0	458.3	462.3	467.1	472.1	476.7	480.9	484.0
170°	443.4	446.0	450.3	454.6	456.3	458.8	462.3	466.6	469.2	472.6	474.3
172.5°	444.8	446.7	449.6	452.5	453.6	454.8	457.5	460.4	462.3	465.0	466.1
175°	446.0	446.9	448.6	450.3	449.4	450.3	451.2	453.7	454.6	455.5	456.3
177.5°	446.9	446.9	447.5	448.9	447.5	446.9	447.5	448.9	448.9	449.6	449.6
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	7.2	7.1	7.1	6.9	7.1	7.1	7.2	7.2	7.1	7.1	7.4
90°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	27.5	25.7	27.5
92.5°	51.1	48.3	49.0	47.6	49.0	48.3	51.1	51.7	57.1	64.3	74.9
95°	106.6	99.7	97.1	98.0	97.1	99.7	106.6	117.7	136.6	172.7	225.2
97.5°	233.8	212.6	200.0	192.9	200.0	212.6	233.8	274.8	336.8	429.8	525.4
100°	385.0	348.0	323.1	307.6	323.1	348.0	385.0	456.3	560.3	678.0	784.5
102.5°	656.5	593.4	562.3	541.4	562.3	593.4	656.5	734.0	844.2	930.3	954.3
105°	1070.7	1017.4	980.4	968.5	980.4	1017.4	1070.7	1123.9	1152.4	1141.2	1044.0
107.5°	1263.3	1260.4	1253.0	1237.1	1253.0	1260.4	1263.3	1256.6	1215.0	1125.7	979.5
110°	1294.9	1311.3	1319.1	1318.2	1319.1	1311.3	1294.9	1258.0	1187.6	1077.5	923.8



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1270.2	1297.5	1312.2	1316.8	1312.2	1297.5	1270.2	1218.8	1138.1	1020.5	872.9
115°	1204.7	1244.2	1266.6	1274.4	1266.6	1244.2	1204.7	1143.8	1055.2	942.6	810.3
117.5°	1126.7	1168.5	1192.1	1198.5	1192.1	1168.5	1126.7	1064.5	981.5	879.4	763.2
120°	1075.8	1116.2	1141.2	1149.8	1141.2	1116.2	1075.8	1015.7	937.5	846.4	739.9
122.5°	1029.8	1069.4	1091.7	1098.9	1091.7	1069.4	1029.8	975.9	905.2	818.9	721.3
125°	972.8	1005.4	1026.8	1033.7	1026.8	1005.4	972.8	922.9	858.4	782.8	694.3
127.5°	922.0	952.6	971.2	976.7	971.2	952.6	922.0	878.6	819.1	747.8	667.7
130°	891.1	920.3	937.5	944.3	937.5	920.3	891.1	849.0	792.3	724.4	650.5
132.5°	859.5	888.7	904.5	910.7	904.5	888.7	859.5	818.0	764.7	702.4	634.0
135°	809.4	837.8	853.3	856.7	853.3	837.8	809.4	772.5	724.4	667.7	611.0
137.5°	760.7	785.1	798.7	803.8	798.7	785.1	760.7	726.9	685.0	640.0	592.5
140°	726.9	749.3	762.2	767.3	762.2	749.3	726.9	699.5	661.7	622.2	580.9
142.5°	698.1	718.4	729.9	730.9	729.9	718.4	698.1	672.0	640.3	606.3	571.3
145°	658.2	672.9	681.4	684.0	681.4	672.9	658.2	637.6	612.7	586.1	557.7
147.5°	625.6	637.2	643.1	644.6	643.1	637.2	625.6	608.6	590.3	569.6	547.2
150°	604.9	615.3	620.4	621.3	620.4	615.3	604.9	592.0	576.6	558.5	539.7
152.5°	588.4	597.4	601.2	601.3	601.2	597.4	588.4	578.3	564.9	549.6	532.1
155°	567.1	573.2	576.6	574.9	576.6	573.2	567.1	557.7	548.2	535.4	521.6
157.5°	545.8	550.8	552.3	552.3	552.3	550.8	545.8	539.2	531.8	520.9	509.4
160°	532.8	537.1	538.0	538.0	538.0	537.1	532.8	526.8	520.7	511.3	501.8
162.5°	521.1	524.0	524.9	524.2	524.9	524.0	521.1	515.1	510.4	502.3	494.3
165°	501.8	505.2	505.2	504.4	505.2	505.2	501.8	498.4	495.0	489.0	482.9
167.5°	485.5	487.4	487.2	486.2	487.2	487.4	485.5	484.0	480.9	476.7	472.1
170°	475.2	477.8	476.9	475.2	476.9	477.8	475.2	474.3	472.6	469.2	466.6
172.5°	466.9	468.1	467.3	466.2	467.3	468.1	466.9	466.1	465.0	462.3	460.4
175°	456.3	457.2	456.3	454.6	456.3	457.2	456.3	456.3	455.5	454.6	453.7
177.5°	449.6	449.6	448.9	447.5	448.9	449.6	449.6	449.6	449.6	448.9	448.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	7.6	7.8	7.8	7.0	5.8	5.1	4.7	4.6	4.5	4.0	3.6
90°	28.3	29.2	28.3	23.2	17.2	12.9	10.3	8.6	6.9	3.4	0.9
92.5°	94.4	111.7	110.1	85.8	58.5	39.0	30.9	25.1	21.4	15.2	10.5
95°	294.7	336.8	298.2	198.5	123.7	84.2	63.6	49.9	42.1	33.5	30.0
97.5°	603.2	575.1	433.1	267.4	163.2	113.6	90.2	74.4	62.8	53.6	49.0
100°	802.6	678.8	467.4	281.9	177.0	131.5	107.5	90.2	76.5	68.7	66.1
102.5°	876.8	682.3	454.4	282.6	189.4	147.3	123.2	105.4	91.6	83.9	82.0
105°	865.3	636.7	428.8	287.0	210.5	170.1	146.1	127.2	114.3	108.3	104.9
107.5°	789.9	588.0	416.0	298.9	232.2	193.0	168.8	150.1	138.2	132.3	129.6
110°	742.4	564.6	413.4	308.5	246.6	208.8	183.9	165.8	154.6	149.6	146.1



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	709.5	549.4	414.0	318.8	260.4	223.9	198.3	181.0	170.5	164.6	161.2
115°	668.6	532.8	417.6	334.2	281.9	244.9	221.7	204.5	194.2	189.1	184.8
117.5°	642.7	524.7	423.8	350.8	301.6	267.4	243.3	226.9	217.7	212.6	209.1
120°	629.0	519.9	427.9	361.8	315.4	281.9	257.8	240.6	232.9	227.7	224.3
122.5°	617.3	517.1	432.7	371.3	328.4	297.0	272.2	255.0	246.6	241.4	238.8
125°	600.6	512.1	440.0	386.7	348.0	317.1	293.0	275.9	265.5	260.4	257.8
127.5°	585.2	509.2	447.4	401.0	366.3	336.1	311.4	294.9	283.5	276.4	272.9
130°	574.9	507.8	452.9	409.9	377.2	347.2	323.1	305.9	293.9	285.2	281.9
132.5°	566.6	507.1	458.3	418.8	386.8	358.2	334.1	316.2	303.5	294.2	290.1
135°	555.1	506.1	464.9	430.5	400.5	372.9	348.9	329.1	316.2	305.9	302.5
137.5°	547.0	505.9	470.7	439.5	411.5	384.3	362.0	342.3	328.6	318.3	314.2
140°	542.3	505.2	473.5	444.3	417.6	391.8	369.5	350.6	336.8	326.6	323.1
142.5°	537.4	505.2	475.5	448.4	422.4	397.4	376.3	358.2	344.4	334.8	332.0
145°	531.1	503.5	477.8	453.7	429.6	406.5	387.5	370.4	357.5	348.9	345.4
147.5°	524.5	500.5	478.5	456.7	435.5	413.7	396.8	382.5	370.7	362.5	359.9
150°	519.0	498.4	477.8	458.0	438.2	418.4	403.0	390.1	378.9	372.0	369.5
152.5°	514.2	495.0	476.4	458.7	441.0	423.3	409.2	397.0	387.2	380.3	379.1
155°	505.2	489.0	474.3	459.7	445.1	430.5	417.6	408.2	398.7	393.6	392.7
157.5°	496.9	482.8	470.4	459.7	448.1	435.7	424.8	417.2	409.1	404.9	404.1
160°	490.7	478.6	468.3	459.7	449.4	439.1	429.6	422.8	415.9	412.5	411.6
162.5°	485.2	475.2	466.2	459.0	450.1	441.2	433.8	427.6	422.1	418.6	419.1
165°	476.0	468.3	462.3	457.2	451.2	443.4	438.2	433.9	428.8	427.1	427.9
167.5°	467.1	462.3	458.3	456.0	451.0	445.3	442.0	438.9	435.7	434.1	435.1
170°	462.3	458.8	456.3	454.6	450.3	446.0	443.4	441.7	439.1	438.2	440.0
172.5°	457.5	454.8	453.6	452.5	449.6	446.7	444.8	443.8	441.2	441.7	442.7
175°	451.2	450.3	449.4	450.3	448.6	446.9	446.0	446.0	444.3	445.1	446.0
177.5°	447.5	446.9	447.5	448.9	447.5	446.9	446.9	446.9	445.5	446.2	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.6	5.9	6.3	7.1	7.2	8.1	9.3	10.2	10.2	9.9	9.6
90°	3.4	6.9	8.6	10.3	12.9	17.2	23.2	28.3	29.2	28.3	27.5
92.5°	15.2	21.4	25.1	30.9	39.0	58.5	85.8	110.1	111.7	94.4	74.9
95°	33.5	42.1	49.9	63.6	84.2	123.7	198.5	298.2	336.8	294.7	225.2
97.5°	53.6	62.8	74.4	90.2	113.6	163.2	267.4	433.1	575.1	603.2	525.4
100°	68.7	76.5	90.2	107.5	131.5	177.0	281.9	467.4	678.8	802.6	784.5
102.5°	83.9	91.6	105.4	123.2	147.3	189.4	282.6	454.4	682.3	876.8	954.3
105°	108.3	114.3	127.2	146.1	170.1	210.5	287.0	428.8	636.7	865.3	1044.0
107.5°	132.3	138.2	150.1	168.8	193.0	232.2	298.9	416.0	588.0	789.9	979.5
110°	149.6	154.6	165.8	183.9	208.8	246.6	308.5	413.4	564.6	742.4	923.8



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	164.6	170.5	181.0	198.3	223.9	260.4	318.8	414.0	549.4	709.5	872.9
115°	189.1	194.2	204.5	221.7	244.9	281.9	334.2	417.6	532.8	668.6	810.3
117.5°	212.6	217.7	226.9	243.3	267.4	301.6	350.8	423.8	524.7	642.7	763.2
120°	227.7	232.9	240.6	257.8	281.9	315.4	361.8	427.9	519.9	629.0	739.9
122.5°	241.4	246.6	255.0	272.2	297.0	328.4	371.3	432.7	517.1	617.3	721.3
125°	260.4	265.5	275.9	293.0	317.1	348.0	386.7	440.0	512.1	600.6	694.3
127.5°	276.4	283.5	294.9	311.4	336.1	366.3	401.0	447.4	509.2	585.2	667.7
130°	285.2	293.9	305.9	323.1	347.2	377.2	409.9	452.9	507.8	574.9	650.5
132.5°	294.2	303.5	316.2	334.1	358.2	386.8	418.8	458.3	507.1	566.6	634.0
135°	305.9	316.2	329.1	348.9	372.9	400.5	430.5	464.9	506.1	555.1	611.0
137.5°	318.3	328.6	342.3	362.0	384.3	411.5	439.5	470.7	505.9	547.0	592.5
140°	326.6	336.8	350.6	369.5	391.8	417.6	444.3	473.5	505.2	542.3	580.9
142.5°	334.8	344.4	358.2	376.3	397.4	422.4	448.4	475.5	505.2	537.4	571.3
145°	348.9	357.5	370.4	387.5	406.5	429.6	453.7	477.8	503.5	531.1	557.7
147.5°	362.5	370.7	382.5	396.8	413.7	435.5	456.7	478.5	500.5	524.5	547.2
150°	372.0	378.9	390.1	403.0	418.4	438.2	458.0	477.8	498.4	519.0	539.7
152.5°	380.3	387.2	397.0	409.2	423.3	441.0	458.7	476.4	495.0	514.2	532.1
155°	393.6	398.7	408.2	417.6	430.5	445.1	459.7	474.3	489.0	505.2	521.6
157.5°	404.9	409.1	417.2	424.8	435.7	448.1	459.7	470.4	482.8	496.9	509.4
160°	412.5	415.9	422.8	429.6	439.1	449.4	459.7	468.3	478.6	490.7	501.8
162.5°	418.6	422.1	427.6	433.8	441.2	450.1	459.0	466.2	475.2	485.2	494.3
165°	427.1	428.8	433.9	438.2	443.4	451.2	457.2	462.3	468.3	476.0	482.9
167.5°	434.1	435.7	438.9	442.0	445.3	451.0	456.0	458.3	462.3	467.1	472.1
170°	438.2	439.1	441.7	443.4	446.0	450.3	454.6	456.3	458.8	462.3	466.6
172.5°	441.7	441.2	443.8	444.8	446.7	449.6	452.5	453.6	454.8	457.5	460.4
175°	445.1	444.3	446.0	446.0	446.9	448.6	450.3	449.4	450.3	451.2	453.7
177.5°	446.2	445.5	446.9	446.9	446.9	447.5	448.9	447.5	446.9	447.5	448.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	9.4	9.7	9.7	9.7	9.9	9.7	9.7
90°	25.7	27.5	28.3	28.3	28.3	28.3	28.3
92.5°	64.3	57.1	51.7	51.1	48.3	49.0	47.6
95°	172.7	136.6	117.7	106.6	99.7	97.1	98.0
97.5°	429.8	336.8	274.8	233.8	212.6	200.0	192.9
100°	678.0	560.3	456.3	385.0	348.0	323.1	307.6
102.5°	930.3	844.2	734.0	656.5	593.4	562.3	541.4
105°	1141.2	1152.4	1123.9	1070.7	1017.4	980.4	968.5
107.5°	1125.7	1215.0	1256.6	1263.3	1260.4	1253.0	1237.1
110°	1077.5	1187.6	1258.0	1294.9	1311.3	1319.1	1318.2



TEST NUMBER: P331269-935

CATALOG NUMBER: SA2XXDIP-C290D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1020.5	1138.1	1218.8	1270.2	1297.5	1312.2	1316.8
115°	942.6	1055.2	1143.8	1204.7	1244.2	1266.6	1274.4
117.5°	879.4	981.5	1064.5	1126.7	1168.5	1192.1	1198.5
120°	846.4	937.5	1015.7	1075.8	1116.2	1141.2	1149.8
122.5°	818.9	905.2	975.9	1029.8	1069.4	1091.7	1098.9
125°	782.8	858.4	922.9	972.8	1005.4	1026.8	1033.7
127.5°	747.8	819.1	878.6	922.0	952.6	971.2	976.7
130°	724.4	792.3	849.0	891.1	920.3	937.5	944.3
132.5°	702.4	764.7	818.0	859.5	888.7	904.5	910.7
135°	667.7	724.4	772.5	809.4	837.8	853.3	856.7
137.5°	640.0	685.0	726.9	760.7	785.1	798.7	803.8
140°	622.2	661.7	699.5	726.9	749.3	762.2	767.3
142.5°	606.3	640.3	672.0	698.1	718.4	729.9	730.9
145°	586.1	612.7	637.6	658.2	672.9	681.4	684.0
147.5°	569.6	590.3	608.6	625.6	637.2	643.1	644.6
150°	558.5	576.6	592.0	604.9	615.3	620.4	621.3
152.5°	549.6	564.9	578.3	588.4	597.4	601.2	601.3
155°	535.4	548.2	557.7	567.1	573.2	576.6	574.9
157.5°	520.9	531.8	539.2	545.8	550.8	552.3	552.3
160°	511.3	520.7	526.8	532.8	537.1	538.0	538.0
162.5°	502.3	510.4	515.1	521.1	524.0	524.9	524.2
165°	489.0	495.0	498.4	501.8	505.2	505.2	504.4
167.5°	476.7	480.9	484.0	485.5	487.4	487.2	486.2
170°	469.2	472.6	474.3	475.2	477.8	476.9	475.2
172.5°	462.3	465.0	466.1	466.9	468.1	467.3	466.2
175°	454.6	455.5	456.3	456.3	457.2	456.3	454.6
177.5°	448.9	449.6	449.6	449.6	449.6	448.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)