

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331623-935

Luminaire Tested: **SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331623-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2751.8 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331623-935
CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	83	80	77	67	65	63	52	51	49	39	38	37	31
2	87	80	74	70	79	73	68	64	59	56	53	46	44	42	35	33	32	27
3	80	71	64	59	72	65	59	54	53	48	45	42	39	36	31	29	28	23
4	73	63	56	50	66	58	51	46	47	43	39	37	34	32	28	26	25	21
5	67	56	49	43	61	52	45	40	42	38	34	34	30	28	26	24	22	18
6	62	51	43	38	56	47	40	35	38	34	30	31	27	25	24	21	20	17
7	58	46	39	33	52	42	36	31	35	30	27	28	25	22	22	19	18	15
8	54	42	35	30	49	39	32	28	32	27	24	26	22	20	20	18	16	14
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	19	16	15	12
10	47	35	28	24	42	32	26	22	27	23	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.9
10°-20°	148.7	5.4
20°-30°	191.6	7.0
30°-40°	182.1	6.6
40°-50°	156.0	5.7
50°-60°	118.8	4.3
60°-70°	75.1	2.7
70°-80°	37.5	1.4
80°-90°	12.1	0.4
90°-100°	102.1	3.7
100°-110°	346.4	12.6
110°-120°	368.0	13.4
120°-130°	303.0	11.0
130°-140°	243.3	8.8
140°-150°	183.9	6.7
150°-160°	129.2	4.7
160°-170°	76.1	2.8
170°-180°	24.8	0.9
0°-30°	393.6	14.3
0°-40°	575.7	20.9
0°-60°	850.4	30.9
0°-90°	975.1	35.4
90°-120°	816.6	29.7
90°-150°	1546.7	56.2
90°-180°	1777.0	64.6
0°-180°	2751.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	16	0	16	0	16	9
95°	56	17	56	17	56	73
105°	553	60	553	60	553	535
115°	728	106	728	106	728	713
125°	591	147	591	147	591	534
135°	490	173	490	173	490	380
145°	391	197	391	197	391	248
155°	328	224	328	224	328	153
165°	288	244	288	244	288	82
175°	260	255	260	255	260	25
180°	255	255	255	255	255	



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	5.8	5.9	5.9	5.9	5.9	5.8	5.6	5.9	5.9	6.1	5.9
90°	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7	16.2	16.7	16.2
92.5°	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8	53.9	63.8	62.9
95°	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6	168.4	192.5	170.4
97.5°	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2	344.7	328.6	247.5
100°	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3	458.6	387.9	267.1
102.5°	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4	501.0	389.9	259.7
105°	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6	494.5	363.9	245.0
107.5°	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6	451.3	336.0	237.7
110°	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9	424.2	322.6	236.2



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8	405.4	313.9	236.6
115°	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0	382.0	304.4	238.7
117.5°	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1	367.3	299.8	242.2
120°	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8	359.5	297.0	244.5
122.5°	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2	352.8	295.5	247.3
125°	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7	343.2	292.7	251.4
127.5°	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5	334.4	291.0	255.6
130°	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7	328.5	290.2	258.7
132.5°	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3	323.7	289.8	261.9
135°	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1	317.2	289.2	265.6
137.5°	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6	312.5	289.1	269.0
140°	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9	309.9	288.7	270.5
142.5°	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4	307.1	288.7	271.7
145°	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7	303.4	287.7	273.0
147.5°	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7	299.7	285.9	273.4
150°	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3	296.6	284.8	273.0
152.5°	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0	293.9	282.8	272.2
155°	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1	288.7	279.4	271.0
157.5°	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1	283.9	275.9	268.8
160°	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7	280.3	273.5	267.6
162.5°	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4	277.2	271.6	266.4
165°	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0	272.0	267.6	264.2
167.5°	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8	266.9	264.2	261.9
170°	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7	264.2	262.2	260.7
172.5°	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1	261.4	259.8	259.2
175°	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2	257.8	257.3	256.8
177.5°	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5	255.7	255.3	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	5.3	4.8	4.3	3.9	3.8	3.8	4.1	4.6	4.3	4.2	4.1
90°	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5	2.0	4.0	4.9
92.5°	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0	8.6	12.1	14.4
95°	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2	19.1	24.0	28.5
97.5°	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0	30.7	35.8	42.5
100°	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8	39.3	43.7	51.6
102.5°	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8	48.0	52.3	60.2
105°	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9	61.9	65.3	72.7
107.5°	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0	75.6	79.0	85.8
110°	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4	85.4	88.4	94.8



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1	94.1	97.4	103.4
115°	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6	108.1	111.0	116.8
117.5°	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5	121.5	124.4	129.7
120°	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1	130.1	133.0	137.5
122.5°	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4	138.0	140.9	145.8
125°	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3	148.8	151.7	157.6
127.5°	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9	157.9	162.0	168.5
130°	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1	163.0	167.9	174.8
132.5°	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7	168.2	173.4	180.7
135°	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8	174.8	180.7	188.0
137.5°	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5	181.8	187.8	195.6
140°	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6	186.6	192.5	200.4
142.5°	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8	191.3	196.8	204.7
145°	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4	199.3	204.2	211.6
147.5°	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6	207.1	211.8	218.6
150°	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1	212.6	216.5	222.9
152.5°	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6	217.3	221.3	226.9
155°	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4	224.9	227.8	233.2
157.5°	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8	231.4	233.8	238.4
160°	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2	235.7	237.6	241.6
162.5°	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5	239.2	241.2	244.4
165°	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5	244.0	245.0	248.0
167.5°	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7	248.1	248.9	250.8
170°	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4	250.4	250.9	252.4
172.5°	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0	252.4	252.1	253.6
175°	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9	254.3	253.8	254.9
177.5°	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7	254.9	254.5	255.3
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	4.1	4.3	4.5	5.2	5.8	5.7	5.6	5.3	5.2	5.3	5.3
90°	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7	14.7	15.7	16.2
92.5°	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8	36.8	32.6	29.5
95°	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6	98.7	78.1	67.2
97.5°	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2	245.6	192.5	157.0
100°	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3	387.4	320.1	260.7
102.5°	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4	531.6	482.4	419.4
105°	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6	652.0	658.5	642.2
107.5°	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6	643.3	694.3	718.1
110°	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9	615.7	678.6	718.8



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8	583.2	650.3	696.5
115°	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0	538.6	603.0	653.6
117.5°	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1	502.5	560.9	608.3
120°	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8	483.6	535.7	580.4
122.5°	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2	468.0	517.2	557.6
125°	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7	447.3	490.5	527.4
127.5°	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5	427.3	468.0	502.0
130°	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7	414.0	452.7	485.1
132.5°	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3	401.4	437.0	467.4
135°	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1	381.5	414.0	441.4
137.5°	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6	365.8	391.4	415.4
140°	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9	355.5	378.1	399.7
142.5°	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4	346.5	365.9	384.0
145°	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7	334.8	350.1	364.4
147.5°	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7	325.5	337.3	347.8
150°	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3	319.2	329.5	338.3
152.5°	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0	314.1	322.8	330.5
155°	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1	305.9	313.2	318.7
157.5°	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1	297.6	303.8	308.1
160°	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7	292.1	297.6	301.0
162.5°	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4	287.1	291.7	294.3
165°	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0	279.4	282.8	284.8
167.5°	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8	272.4	274.7	276.6
170°	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7	268.1	270.1	271.0
172.5°	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1	264.2	265.7	266.3
175°	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2	259.8	260.3	260.7
177.5°	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5	256.5	256.9	256.9
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	5.3	5.1	5.3	5.1	5.3	5.1	5.3	5.3	5.3	5.2	5.3
90°	16.2	16.2	16.2	16.2	16.2	16.2	16.2	16.2	15.7	14.7	15.7
92.5°	29.2	27.6	28.0	27.2	28.0	27.6	29.2	29.5	32.6	36.8	42.8
95°	60.9	57.0	55.4	56.0	55.4	57.0	60.9	67.2	78.1	98.7	128.6
97.5°	133.5	121.5	114.3	110.2	114.3	121.5	133.5	157.0	192.5	245.6	300.2
100°	220.0	198.9	184.6	175.8	184.6	198.9	220.0	260.7	320.1	387.4	448.3
102.5°	375.1	339.1	321.3	309.4	321.3	339.1	375.1	419.4	482.4	531.6	545.4
105°	611.8	581.3	560.3	553.4	560.3	581.3	611.8	642.2	658.5	652.0	596.6
107.5°	721.9	720.2	716.0	706.9	716.0	720.2	721.9	718.1	694.3	643.3	559.6
110°	739.9	749.3	753.7	753.2	753.7	749.3	739.9	718.8	678.6	615.7	527.9



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	725.8	741.4	749.8	752.4	749.8	741.4	725.8	696.5	650.3	583.2	498.8
115°	688.4	711.0	723.8	728.1	723.8	711.0	688.4	653.6	603.0	538.6	463.0
117.5°	643.9	667.7	681.1	684.8	681.1	667.7	643.9	608.3	560.9	502.5	436.1
120°	614.8	637.8	652.0	656.9	652.0	637.8	614.8	580.4	535.7	483.6	422.8
122.5°	588.4	611.1	623.8	627.9	623.8	611.1	588.4	557.6	517.2	468.0	412.2
125°	555.9	574.5	586.8	590.7	586.8	574.5	555.9	527.4	490.5	447.3	396.7
127.5°	526.8	544.3	554.9	558.1	554.9	544.3	526.8	502.0	468.0	427.3	381.5
130°	509.2	525.9	535.7	539.6	535.7	525.9	509.2	485.1	452.7	414.0	371.7
132.5°	491.1	507.8	516.9	520.4	516.9	507.8	491.1	467.4	437.0	401.4	362.3
135°	462.5	478.7	487.6	489.6	487.6	478.7	462.5	441.4	414.0	381.5	349.1
137.5°	434.6	448.6	456.3	459.3	456.3	448.6	434.6	415.4	391.4	365.8	338.6
140°	415.4	428.2	435.5	438.5	435.5	428.2	415.4	399.7	378.1	355.5	331.9
142.5°	398.9	410.5	417.1	417.7	417.1	410.5	398.9	384.0	365.9	346.5	326.4
145°	376.1	384.4	389.3	390.8	389.3	384.4	376.1	364.4	350.1	334.8	318.7
147.5°	357.5	364.1	367.5	368.3	367.5	364.1	357.5	347.8	337.3	325.5	312.7
150°	345.7	351.5	354.5	355.0	354.5	351.5	345.7	338.3	329.5	319.2	308.3
152.5°	336.2	341.4	343.5	343.6	343.5	341.4	336.2	330.5	322.8	314.1	304.0
155°	324.1	327.5	329.5	328.5	329.5	327.5	324.1	318.7	313.2	305.9	298.1
157.5°	311.9	314.8	315.6	315.6	315.6	314.8	311.9	308.1	303.8	297.6	291.1
160°	304.4	306.9	307.4	307.4	307.4	306.9	304.4	301.0	297.6	292.1	286.7
162.5°	297.7	299.5	299.9	299.5	299.9	299.5	297.7	294.3	291.7	287.1	282.4
165°	286.7	288.7	288.7	288.3	288.7	288.7	286.7	284.8	282.8	279.4	276.0
167.5°	277.4	278.5	278.4	277.8	278.4	278.5	277.4	276.6	274.7	272.4	269.8
170°	271.6	273.0	272.5	271.6	272.5	273.0	271.6	271.0	270.1	268.1	266.7
172.5°	266.8	267.5	267.0	266.4	267.0	267.5	266.8	266.3	265.7	264.2	263.1
175°	260.7	261.2	260.7	259.8	260.7	261.2	260.7	260.7	260.3	259.8	259.2
177.5°	256.9	256.9	256.5	255.7	256.5	256.9	256.9	256.9	256.9	256.5	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	5.6	5.7	5.8	5.2	4.5	4.3	4.1	4.1	4.2	4.3	4.6
90°	16.2	16.7	16.2	13.3	9.8	7.4	5.9	4.9	4.0	2.0	0.5
92.5°	53.9	63.8	62.9	49.0	33.4	22.3	17.7	14.4	12.1	8.6	6.0
95°	168.4	192.5	170.4	113.4	70.7	48.1	36.3	28.5	24.0	19.1	17.2
97.5°	344.7	328.6	247.5	152.8	93.3	64.9	51.6	42.5	35.8	30.7	28.0
100°	458.6	387.9	267.1	161.1	101.2	75.2	61.4	51.6	43.7	39.3	37.8
102.5°	501.0	389.9	259.7	161.4	108.2	84.1	70.4	60.2	52.3	48.0	46.8
105°	494.5	363.9	245.0	164.0	120.3	97.2	83.4	72.7	65.3	61.9	59.9
107.5°	451.3	336.0	237.7	170.7	132.7	110.3	96.4	85.8	79.0	75.6	74.0
110°	424.2	322.6	236.2	176.2	140.9	119.3	105.0	94.8	88.4	85.4	83.4



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	405.4	313.9	236.6	182.2	148.8	127.9	113.3	103.4	97.4	94.1	92.1
115°	382.0	304.4	238.7	191.0	161.1	139.9	126.7	116.8	111.0	108.1	105.6
117.5°	367.3	299.8	242.2	200.4	172.4	152.8	139.1	129.7	124.4	121.5	119.5
120°	359.5	297.0	244.5	206.7	180.2	161.1	147.3	137.5	133.0	130.1	128.1
122.5°	352.8	295.5	247.3	212.2	187.7	169.7	155.6	145.8	140.9	138.0	136.4
125°	343.2	292.7	251.4	220.9	198.9	181.2	167.5	157.6	151.7	148.8	147.3
127.5°	334.4	291.0	255.6	229.1	209.3	192.1	178.0	168.5	162.0	157.9	155.9
130°	328.5	290.2	258.7	234.2	215.6	198.4	184.6	174.8	167.9	163.0	161.1
132.5°	323.7	289.8	261.9	239.4	221.0	204.7	190.9	180.7	173.4	168.2	165.7
135°	317.2	289.2	265.6	246.0	228.9	213.1	199.3	188.0	180.7	174.8	172.8
137.5°	312.5	289.1	269.0	251.1	235.1	219.6	206.8	195.6	187.8	181.8	179.5
140°	309.9	288.7	270.5	253.8	238.7	223.9	211.1	200.4	192.5	186.6	184.6
142.5°	307.1	288.7	271.7	256.2	241.4	227.0	215.1	204.7	196.8	191.3	189.8
145°	303.4	287.7	273.0	259.2	245.5	232.2	221.4	211.6	204.2	199.3	197.4
147.5°	299.7	285.9	273.4	261.0	248.8	236.3	226.8	218.6	211.8	207.1	205.6
150°	296.6	284.8	273.0	261.7	250.4	239.1	230.3	222.9	216.5	212.6	211.1
152.5°	293.9	282.8	272.2	262.1	252.0	241.9	233.8	226.9	221.3	217.3	216.6
155°	288.7	279.4	271.0	262.7	254.3	246.0	238.7	233.2	227.8	224.9	224.4
157.5°	283.9	275.9	268.8	262.7	256.0	248.9	242.8	238.4	233.8	231.4	230.8
160°	280.3	273.5	267.6	262.7	256.8	250.9	245.5	241.6	237.6	235.7	235.2
162.5°	277.2	271.6	266.4	262.3	257.2	252.1	247.9	244.4	241.2	239.2	239.5
165°	272.0	267.6	264.2	261.2	257.8	253.4	250.4	248.0	245.0	244.0	244.5
167.5°	266.9	264.2	261.9	260.5	257.7	254.4	252.6	250.8	248.9	248.1	248.7
170°	264.2	262.2	260.7	259.8	257.3	254.9	253.4	252.4	250.9	250.4	251.4
172.5°	261.4	259.8	259.2	258.6	256.9	255.2	254.2	253.6	252.1	252.4	253.0
175°	257.8	257.3	256.8	257.3	256.3	255.3	254.9	254.9	253.8	254.3	254.9
177.5°	255.7	255.3	255.7	256.5	255.7	255.3	255.3	255.3	254.5	254.9	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.1	3.8	3.8	3.9	4.3	4.8	5.3	5.9	6.1	5.9	5.9
90°	2.0	4.0	4.9	5.9	7.4	9.8	13.3	16.2	16.7	16.2	15.7
92.5°	8.6	12.1	14.4	17.7	22.3	33.4	49.0	62.9	63.8	53.9	42.8
95°	19.1	24.0	28.5	36.3	48.1	70.7	113.4	170.4	192.5	168.4	128.6
97.5°	30.7	35.8	42.5	51.6	64.9	93.3	152.8	247.5	328.6	344.7	300.2
100°	39.3	43.7	51.6	61.4	75.2	101.2	161.1	267.1	387.9	458.6	448.3
102.5°	48.0	52.3	60.2	70.4	84.1	108.2	161.4	259.7	389.9	501.0	545.4
105°	61.9	65.3	72.7	83.4	97.2	120.3	164.0	245.0	363.9	494.5	596.6
107.5°	75.6	79.0	85.8	96.4	110.3	132.7	170.7	237.7	336.0	451.3	559.6
110°	85.4	88.4	94.8	105.0	119.3	140.9	176.2	236.2	322.6	424.2	527.9



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	94.1	97.4	103.4	113.3	127.9	148.8	182.2	236.6	313.9	405.4	498.8
115°	108.1	111.0	116.8	126.7	139.9	161.1	191.0	238.7	304.4	382.0	463.0
117.5°	121.5	124.4	129.7	139.1	152.8	172.4	200.4	242.2	299.8	367.3	436.1
120°	130.1	133.0	137.5	147.3	161.1	180.2	206.7	244.5	297.0	359.5	422.8
122.5°	138.0	140.9	145.8	155.6	169.7	187.7	212.2	247.3	295.5	352.8	412.2
125°	148.8	151.7	157.6	167.5	181.2	198.9	220.9	251.4	292.7	343.2	396.7
127.5°	157.9	162.0	168.5	178.0	192.1	209.3	229.1	255.6	291.0	334.4	381.5
130°	163.0	167.9	174.8	184.6	198.4	215.6	234.2	258.7	290.2	328.5	371.7
132.5°	168.2	173.4	180.7	190.9	204.7	221.0	239.4	261.9	289.8	323.7	362.3
135°	174.8	180.7	188.0	199.3	213.1	228.9	246.0	265.6	289.2	317.2	349.1
137.5°	181.8	187.8	195.6	206.8	219.6	235.1	251.1	269.0	289.1	312.5	338.6
140°	186.6	192.5	200.4	211.1	223.9	238.7	253.8	270.5	288.7	309.9	331.9
142.5°	191.3	196.8	204.7	215.1	227.0	241.4	256.2	271.7	288.7	307.1	326.4
145°	199.3	204.2	211.6	221.4	232.2	245.5	259.2	273.0	287.7	303.4	318.7
147.5°	207.1	211.8	218.6	226.8	236.3	248.8	261.0	273.4	285.9	299.7	312.7
150°	212.6	216.5	222.9	230.3	239.1	250.4	261.7	273.0	284.8	296.6	308.3
152.5°	217.3	221.3	226.9	233.8	241.9	252.0	262.1	272.2	282.8	293.9	304.0
155°	224.9	227.8	233.2	238.7	246.0	254.3	262.7	271.0	279.4	288.7	298.1
157.5°	231.4	233.8	238.4	242.8	248.9	256.0	262.7	268.8	275.9	283.9	291.1
160°	235.7	237.6	241.6	245.5	250.9	256.8	262.7	267.6	273.5	280.3	286.7
162.5°	239.2	241.2	244.4	247.9	252.1	257.2	262.3	266.4	271.6	277.2	282.4
165°	244.0	245.0	248.0	250.4	253.4	257.8	261.2	264.2	267.6	272.0	276.0
167.5°	248.1	248.9	250.8	252.6	254.4	257.7	260.5	261.9	264.2	266.9	269.8
170°	250.4	250.9	252.4	253.4	254.9	257.3	259.8	260.7	262.2	264.2	266.7
172.5°	252.4	252.1	253.6	254.2	255.2	256.9	258.6	259.2	259.8	261.4	263.1
175°	254.3	253.8	254.9	254.9	255.3	256.3	257.3	256.8	257.3	257.8	259.2
177.5°	254.9	254.5	255.3	255.3	255.3	255.7	256.5	255.7	255.3	255.7	256.5
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3	255.3



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	5.6	5.8	5.9	5.9	5.9	5.9	5.8
90°	14.7	15.7	16.2	16.2	16.2	16.2	16.2
92.5°	36.8	32.6	29.5	29.2	27.6	28.0	27.2
95°	98.7	78.1	67.2	60.9	57.0	55.4	56.0
97.5°	245.6	192.5	157.0	133.5	121.5	114.3	110.2
100°	387.4	320.1	260.7	220.0	198.9	184.6	175.8
102.5°	531.6	482.4	419.4	375.1	339.1	321.3	309.4
105°	652.0	658.5	642.2	611.8	581.3	560.3	553.4
107.5°	643.3	694.3	718.1	721.9	720.2	716.0	706.9
110°	615.7	678.6	718.8	739.9	749.3	753.7	753.2



TEST NUMBER: P331623-935

CATALOG NUMBER: SA2XXRDIP-C290D530U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.2	650.3	696.5	725.8	741.4	749.8	752.4
115°	538.6	603.0	653.6	688.4	711.0	723.8	728.1
117.5°	502.5	560.9	608.3	643.9	667.7	681.1	684.8
120°	483.6	535.7	580.4	614.8	637.8	652.0	656.9
122.5°	468.0	517.2	557.6	588.4	611.1	623.8	627.9
125°	447.3	490.5	527.4	555.9	574.5	586.8	590.7
127.5°	427.3	468.0	502.0	526.8	544.3	554.9	558.1
130°	414.0	452.7	485.1	509.2	525.9	535.7	539.6
132.5°	401.4	437.0	467.4	491.1	507.8	516.9	520.4
135°	381.5	414.0	441.4	462.5	478.7	487.6	489.6
137.5°	365.8	391.4	415.4	434.6	448.6	456.3	459.3
140°	355.5	378.1	399.7	415.4	428.2	435.5	438.5
142.5°	346.5	365.9	384.0	398.9	410.5	417.1	417.7
145°	334.8	350.1	364.4	376.1	384.4	389.3	390.8
147.5°	325.5	337.3	347.8	357.5	364.1	367.5	368.3
150°	319.2	329.5	338.3	345.7	351.5	354.5	355.0
152.5°	314.1	322.8	330.5	336.2	341.4	343.5	343.6
155°	305.9	313.2	318.7	324.1	327.5	329.5	328.5
157.5°	297.6	303.8	308.1	311.9	314.8	315.6	315.6
160°	292.1	297.6	301.0	304.4	306.9	307.4	307.4
162.5°	287.1	291.7	294.3	297.7	299.5	299.9	299.5
165°	279.4	282.8	284.8	286.7	288.7	288.7	288.3
167.5°	272.4	274.7	276.6	277.4	278.5	278.4	277.8
170°	268.1	270.1	271.0	271.6	273.0	272.5	271.6
172.5°	264.2	265.7	266.3	266.8	267.5	267.0	266.4
175°	259.8	260.3	260.7	260.7	261.2	260.7	259.8
177.5°	256.5	256.9	256.9	256.9	256.9	256.5	255.7
180°	255.3	255.3	255.3	255.3	255.3	255.3	255.3

(END OF REPORT)