

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331659-935

Luminaire Tested: **SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331659-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4037.8 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331659-935
CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35				
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30				
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26				
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23				
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21				
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19				
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17				
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15				
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14				
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14941	14941	14941	14941
5°	16686	15034	13331	15034
10°	18513	14929	11555	14929
15°	19423	14710	9105	14710
20°	16838	14385	7878	14385
25°	11043	13942	7035	13942
30°	7433	13403	6367	13403
35°	6022	12727	5742	12727
40°	5354	11989	5313	11989
45°	4845	11125	4743	11125
50°	4411	10263	4393	10263
55°	4144	9315	4090	9315
60°	3468	8441	3426	8441
65°	2923	7664	3316	7664
70°	2705	6845	3125	6845
75°	2533	5958	2888	5958
80°	2334	4900	2566	4900
85°	2130	3872	2260	3872



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	2.2
10°-20°	244.4	6.1
20°-30°	315.0	7.8
30°-40°	299.3	7.4
40°-50°	256.4	6.4
50°-60°	195.3	4.8
60°-70°	123.4	3.1
70°-80°	61.6	1.5
80°-90°	19.2	0.5
90°-100°	139.9	3.5
100°-110°	474.9	11.8
110°-120°	504.5	12.5
120°-130°	415.3	10.3
130°-140°	333.5	8.3
140°-150°	252.0	6.2
150°-160°	177.1	4.4
160°-170°	104.3	2.6
170°-180°	33.9	0.8
0°-30°	647.1	16.0
0°-40°	946.4	23.4
0°-60°	1398.1	34.6
0°-90°	1602.4	39.7
90°-120°	1119.3	27.7
90°-150°	2120.1	52.5
90°-180°	2435.0	60.3
0°-180°	4037.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1030	928	822	928	1030	102
15°	1162	880	545	880	1162	313
25°	620	783	395	783	620	294
35°	306	646	291	646	306	195
45°	212	487	208	487	212	164
55°	147	331	145	331	147	129
65°	76	201	87	201	76	78
75°	41	96	46	96	41	43
85°	12	21	12	21	12	13
90°	22	1	22	1	22	12
95°	77	24	77	24	77	100
105°	758	82	758	82	758	734
115°	998	145	998	145	998	977
125°	810	202	810	202	810	732
135°	671	237	671	237	671	521
145°	536	270	536	270	536	340
155°	450	308	450	308	450	210
165°	395	335	395	335	395	113
175°	356	349	356	349	356	35
180°	350	350	350	350	350	



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	962.9	963.7	964.5	962.7	962.7	961.1	957.8	955.2	948.0	946.9	946.9
5°	1029.5	1028.9	1030.2	1026.0	1020.2	1018.9	1012.8	1004.8	996.4	987.1	985.2
7.5°	1095.8	1094.8	1092.3	1091.5	1087.1	1077.4	1067.6	1057.0	1043.2	1029.6	1022.8
10°	1129.2	1139.8	1133.4	1122.1	1124.4	1109.3	1101.2	1087.4	1075.8	1055.6	1051.1
12.5°	1162.1	1166.3	1164.2	1157.9	1155.0	1144.5	1133.7	1121.6	1100.3	1082.1	1066.3
15°	1162.0	1168.1	1169.8	1167.8	1169.4	1168.7	1163.0	1153.0	1134.4	1114.4	1097.1
17.5°	1076.2	1080.5	1091.0	1098.1	1107.2	1126.2	1135.6	1139.3	1136.4	1125.1	1112.8
20°	980.0	972.9	1002.5	1017.6	1030.5	1062.6	1090.3	1100.9	1117.9	1117.7	1114.4
22.5°	843.7	845.3	873.4	891.3	928.9	961.0	992.6	1032.5	1065.5	1087.3	1100.0
25°	619.9	632.1	660.1	684.5	726.3	786.2	840.5	903.5	962.9	1010.0	1054.6
27.5°	465.5	466.5	488.6	511.3	536.1	585.0	653.5	728.8	813.6	883.5	964.0
30°	398.7	396.7	406.1	419.9	441.2	479.1	530.5	604.5	689.1	794.5	888.4
32.5°	351.4	351.5	358.5	368.8	386.3	411.9	447.2	507.2	587.2	690.9	800.9
35°	305.5	305.1	310.3	317.7	325.0	341.5	365.6	397.1	452.1	548.9	661.4
37.5°	272.5	274.0	276.5	281.1	289.2	298.3	312.9	334.0	373.2	430.4	525.0
40°	254.0	254.7	258.2	262.1	266.9	274.0	285.9	302.9	331.5	377.1	446.3
42.5°	237.0	237.6	240.2	243.7	247.5	254.7	264.5	279.2	302.5	338.0	395.1
45°	212.2	212.2	214.5	216.0	220.2	226.7	234.7	246.9	263.0	289.4	327.4
47.5°	188.9	189.0	190.5	193.2	195.9	200.9	208.8	218.8	230.5	250.9	283.3
50°	175.6	175.9	176.8	179.1	180.7	185.2	191.3	200.0	212.2	228.0	254.9
52.5°	164.7	164.5	165.7	166.8	167.8	171.1	175.6	183.3	194.2	207.9	230.3
55°	147.2	145.9	147.9	149.5	150.5	151.8	154.3	159.2	168.5	180.0	196.7
57.5°	125.4	124.8	126.2	127.7	130.7	134.2	136.4	139.5	144.3	152.6	169.2
60°	107.4	107.4	110.3	111.2	114.8	119.2	123.8	126.4	131.2	136.6	148.9
62.5°	91.4	91.7	93.1	94.0	96.0	101.5	107.9	113.5	118.0	123.3	131.4
65°	76.5	77.1	77.1	77.8	79.1	80.4	82.9	87.5	95.5	102.9	109.0
67.5°	64.9	65.2	65.3	66.0	66.3	67.7	68.7	70.8	72.6	79.6	87.2
70°	57.3	58.2	57.9	58.5	58.8	59.5	60.8	61.7	64.7	66.2	70.8
72.5°	50.0	50.7	50.7	51.1	51.9	52.0	53.0	54.0	55.9	57.3	59.7
75°	40.6	40.2	40.6	41.2	41.5	41.8	41.8	43.0	44.1	45.4	46.9
77.5°	31.3	31.6	31.5	31.6	31.6	32.2	32.1	32.7	33.7	34.4	35.1
80°	25.1	25.4	25.1	25.4	25.7	26.0	25.7	26.0	27.0	27.6	27.6
82.5°	19.5	19.5	19.7	19.7	19.8	19.9	20.3	20.4	21.1	20.9	21.2
85°	11.5	11.3	11.3	11.3	11.5	11.9	11.5	11.5	11.9	11.9	11.9
87.5°	8.5	8.8	8.8	8.8	8.8	8.7	8.4	9.0	8.8	9.2	8.8
90°	22.2	22.2	22.2	22.2	22.2	21.5	20.2	21.5	22.2	22.9	22.2
92.5°	37.3	38.4	37.8	40.0	40.6	44.7	50.4	58.7	73.9	87.5	86.3
95°	76.7	76.0	78.1	83.4	92.2	107.0	135.3	176.3	230.8	263.8	233.6
97.5°	151.0	156.7	166.5	183.0	215.2	263.8	336.7	411.5	472.5	450.4	339.2
100°	240.9	253.0	272.6	301.5	357.4	438.9	531.1	614.5	628.6	531.7	366.1
102.5°	424.0	440.4	464.8	514.2	574.9	661.2	728.7	747.5	686.7	534.4	355.9
105°	758.5	767.9	796.9	838.6	880.4	902.6	893.8	817.8	677.8	498.7	335.9
107.5°	968.9	981.5	987.2	989.5	984.3	951.7	881.7	767.2	618.6	460.5	325.9
110°	1032.4	1033.1	1027.1	1014.3	985.3	930.1	844.0	723.5	581.5	442.2	323.7



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1031.4	1027.8	1016.3	994.9	954.7	891.4	799.3	683.7	555.7	430.3	324.3
115°	998.2	992.0	974.6	943.6	895.8	826.5	738.3	634.6	523.7	417.3	327.1
117.5°	938.7	933.7	915.2	882.5	833.8	768.8	688.8	597.8	503.4	411.0	331.9
120°	900.5	893.8	874.3	842.7	795.6	734.3	663.0	579.5	492.7	407.2	335.2
122.5°	860.7	855.1	837.7	806.6	764.3	708.9	641.4	565.0	483.5	405.0	339.0
125°	809.7	804.3	787.5	761.9	722.8	672.4	613.1	543.8	470.5	401.1	344.6
127.5°	765.0	760.7	746.1	722.2	688.1	641.5	585.7	523.0	458.3	398.8	350.4
130°	739.7	734.3	720.8	697.9	665.0	620.5	567.4	509.5	450.3	397.8	354.7
132.5°	713.3	708.4	696.0	673.2	640.8	599.0	550.2	496.5	443.8	397.3	359.0
135°	671.1	668.3	656.3	634.0	605.0	567.4	523.0	478.5	434.8	396.4	364.1
137.5°	629.6	625.5	614.9	595.8	569.4	536.6	501.3	464.2	428.4	396.3	368.7
140°	601.1	597.0	586.9	569.4	547.9	518.2	487.3	455.0	424.7	395.7	370.8
142.5°	572.5	571.7	562.7	546.8	526.3	501.5	474.9	447.5	420.9	395.7	372.5
145°	535.7	533.7	527.0	515.6	499.4	479.9	459.0	436.8	415.9	394.4	374.2
147.5°	504.9	503.7	499.1	490.0	476.6	462.4	446.1	428.6	410.9	392.0	374.8
150°	486.6	485.9	481.9	473.8	463.7	451.6	437.5	422.7	406.5	390.4	374.2
152.5°	471.0	470.9	467.9	460.9	453.0	442.5	430.5	416.7	402.8	387.7	373.2
155°	450.3	451.6	448.9	444.2	436.8	429.4	419.3	408.5	395.7	383.0	371.5
157.5°	432.7	432.7	431.4	427.5	422.2	416.5	408.0	399.0	389.2	378.2	368.4
160°	421.3	421.3	420.7	417.3	412.6	407.9	400.5	393.0	384.4	374.9	366.8
162.5°	410.5	411.1	410.4	408.1	403.5	399.8	393.5	387.1	380.0	372.2	365.2
165°	395.1	395.7	395.7	393.0	390.4	387.7	383.0	378.2	372.9	366.8	362.1
167.5°	380.8	381.6	381.8	380.3	379.1	376.6	373.4	369.8	365.8	362.1	359.0
170°	372.2	373.5	374.2	372.2	371.5	370.1	367.5	365.5	362.1	359.4	357.4
172.5°	365.2	366.0	366.7	365.8	365.1	364.3	362.1	360.6	358.3	356.2	355.2
175°	356.0	357.4	358.1	357.4	357.4	356.7	356.0	355.3	353.4	352.7	352.0
177.5°	350.5	351.6	352.1	352.1	352.1	352.1	351.6	351.6	350.5	350.0	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	947.4	945.5	943.7	939.0	936.7	931.5	930.7	930.5	923.9	917.4	915.6
5°	980.0	974.9	967.2	958.1	948.8	939.2	932.7	927.6	914.7	902.5	895.4
7.5°	1012.8	1001.8	988.4	971.4	957.2	941.2	929.4	918.8	900.5	883.0	871.2
10°	1037.2	1019.3	1001.6	978.1	959.8	941.8	925.1	910.6	890.0	866.9	850.4
12.5°	1052.4	1032.6	1008.2	985.3	961.6	938.7	916.3	897.7	873.6	849.6	830.1
15°	1073.0	1051.7	1022.2	989.4	958.8	928.9	903.2	880.0	848.5	819.9	796.1
17.5°	1089.8	1060.5	1028.7	990.8	955.5	917.5	884.3	854.7	819.7	785.1	757.2
20°	1095.1	1066.2	1029.5	991.6	949.8	905.1	869.4	837.2	799.6	762.0	729.9
22.5°	1091.7	1069.3	1028.5	983.1	940.3	893.5	853.3	815.9	774.2	735.8	698.5
25°	1069.1	1061.4	1022.8	973.3	924.4	870.0	823.5	782.6	735.0	693.9	653.3
27.5°	1016.2	1032.9	1008.9	956.1	901.8	843.5	791.2	744.7	695.3	648.9	608.6
30°	965.3	1003.5	993.2	944.3	883.6	826.3	767.5	718.9	666.2	618.6	578.8
32.5°	895.5	958.7	968.8	927.9	865.0	802.1	740.5	692.2	637.1	586.9	548.1
35°	784.5	879.1	922.5	896.4	833.4	765.6	701.9	645.7	590.3	540.8	502.2
37.5°	652.1	780.8	853.3	855.1	797.2	726.7	657.4	601.5	544.8	496.3	454.5
40°	566.2	705.8	800.0	820.9	772.0	695.8	625.7	568.8	513.5	465.9	418.0
42.5°	489.0	628.1	743.9	780.2	741.4	665.7	595.4	535.9	482.1	437.0	388.1
45°	395.5	517.0	644.6	709.6	688.1	617.9	543.7	487.2	436.6	397.7	350.8
47.5°	333.6	419.3	542.8	630.7	630.3	566.3	493.3	439.0	392.2	355.8	317.7
50°	298.3	373.0	477.5	577.1	585.5	531.8	462.4	408.6	365.0	326.7	296.1
52.5°	266.7	328.2	422.1	517.7	541.5	495.0	427.7	378.1	335.6	300.4	274.2
55°	225.4	272.9	344.4	433.8	469.8	437.0	377.1	330.9	296.4	266.9	244.4
57.5°	190.6	226.4	283.6	355.6	397.5	376.9	327.6	290.0	260.5	233.8	216.0
60°	168.8	198.0	246.6	306.8	353.0	338.5	296.4	261.4	236.3	213.2	196.5
62.5°	148.3	173.4	215.0	263.8	306.3	300.2	265.9	236.4	214.5	193.4	179.3
65°	119.2	137.6	170.0	208.4	242.5	245.3	220.6	200.6	181.0	164.3	151.8
67.5°	95.0	106.9	129.8	162.0	187.6	196.7	181.6	166.3	150.8	137.8	127.0
70°	80.1	89.7	106.4	132.5	155.9	165.6	156.9	145.0	131.5	120.9	111.6
72.5°	64.9	74.3	86.6	105.7	125.9	136.3	133.3	124.7	113.7	105.0	96.2
75°	48.9	51.7	60.1	73.0	88.8	97.7	100.0	95.5	86.8	80.1	74.9
77.5°	36.2	37.9	41.8	48.6	58.9	66.9	70.3	69.7	63.7	59.8	55.0
80°	28.9	29.9	31.9	34.7	42.4	50.5	52.7	52.7	48.6	46.9	42.1
82.5°	22.0	22.7	23.8	25.5	29.1	36.1	38.6	39.1	36.4	34.4	30.6
85°	12.6	12.2	12.8	13.9	14.5	16.4	20.2	20.9	20.2	17.7	16.7
87.5°	8.0	7.3	6.6	6.0	5.9	5.9	6.7	7.6	7.0	6.7	6.5
90°	18.2	13.4	10.1	8.1	6.7	5.4	2.7	0.7	2.7	5.4	6.7
92.5°	67.2	45.8	30.6	24.2	19.6	16.7	11.9	8.2	11.9	16.7	19.6
95°	155.5	96.9	66.0	49.8	39.0	33.0	26.3	23.6	26.3	33.0	39.0
97.5°	209.5	127.9	88.9	70.7	58.3	49.2	42.0	38.4	42.0	49.2	58.3
100°	220.8	138.6	103.0	84.1	70.7	59.9	53.8	51.8	53.8	59.9	70.7
102.5°	221.3	148.4	115.4	96.5	82.5	71.7	65.7	64.2	65.7	71.7	82.5
105°	224.8	164.9	133.3	114.4	99.6	89.5	84.8	82.1	84.8	89.5	99.6
107.5°	234.1	181.8	151.2	132.2	117.5	108.2	103.7	101.5	103.7	108.2	117.5
110°	241.6	193.1	163.6	144.0	129.9	121.1	117.1	114.4	117.1	121.1	129.9



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	249.7	204.0	175.4	155.3	141.7	133.5	129.0	126.2	129.0	133.5	141.7
115°	261.8	220.8	191.8	173.7	160.1	152.1	148.1	144.7	148.1	152.1	160.1
117.5°	274.7	236.3	209.5	190.6	177.7	170.6	166.5	163.8	166.5	170.6	177.7
120°	283.4	247.0	220.8	201.9	188.5	182.4	178.4	175.6	178.4	182.4	188.5
122.5°	290.9	257.3	232.6	213.2	199.8	193.1	189.2	187.0	189.2	193.1	199.8
125°	302.9	272.6	248.3	229.5	216.0	207.9	204.0	201.9	204.0	207.9	216.0
127.5°	314.0	286.9	263.3	243.9	231.0	222.1	216.5	213.8	216.5	222.1	231.0
130°	321.1	295.5	271.9	253.0	239.6	230.1	223.4	220.8	223.4	230.1	239.6
132.5°	328.0	303.0	280.5	261.7	247.7	237.7	230.5	227.2	230.5	237.7	247.7
135°	337.2	313.7	292.1	273.3	257.8	247.7	239.6	236.9	239.6	247.7	257.8
137.5°	344.2	322.3	301.0	283.5	268.1	257.4	249.3	246.1	249.3	257.4	268.1
140°	347.9	327.1	306.9	289.4	274.6	263.8	255.7	253.0	255.7	263.8	274.6
142.5°	351.2	330.9	311.3	294.8	280.5	269.8	262.3	260.0	262.3	269.8	280.5
145°	355.3	336.6	318.3	303.5	290.1	280.0	273.3	270.5	273.3	280.0	290.1
147.5°	357.7	341.1	324.0	310.8	299.6	290.3	283.9	281.9	283.9	290.3	299.6
150°	358.7	343.3	327.8	315.6	305.6	296.8	291.4	289.4	291.4	296.8	305.6
152.5°	359.3	345.4	331.6	320.5	310.9	303.2	297.9	297.0	297.9	303.2	310.9
155°	360.1	348.6	337.2	327.1	319.7	312.3	308.2	307.5	308.2	312.3	319.7
157.5°	360.1	350.9	341.2	332.8	326.8	320.4	317.1	316.5	317.1	320.4	326.8
160°	360.1	352.0	343.9	336.6	331.1	325.7	323.0	322.4	323.0	325.7	331.1
162.5°	359.6	352.6	345.5	339.8	334.9	330.6	327.9	328.3	327.9	330.6	334.9
165°	358.1	353.4	347.3	343.3	339.9	335.9	334.5	335.2	334.5	335.9	339.9
167.5°	357.1	353.2	348.8	346.2	343.8	341.2	340.0	340.9	340.0	341.2	343.8
170°	356.0	352.7	349.3	347.3	345.9	343.9	343.3	344.6	343.3	343.9	345.9
172.5°	354.4	352.1	349.8	348.4	347.6	345.5	345.9	346.7	345.9	345.5	347.6
175°	352.7	351.3	350.0	349.3	349.3	347.9	348.6	349.3	348.6	347.9	349.3
177.5°	351.6	350.5	350.0	350.0	350.0	348.9	349.5	350.5	349.5	348.9	350.0
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	912.2	910.4	907.1	902.0	898.9	893.5	889.8	891.9	892.4	891.9	891.4
5°	887.8	881.0	871.7	862.6	854.3	845.3	840.2	837.9	833.4	830.9	829.6
7.5°	858.1	846.4	833.3	817.6	804.3	790.3	783.2	779.6	770.4	765.4	761.0
10°	835.9	817.6	804.4	783.9	771.4	753.0	740.5	740.8	728.2	721.2	716.0
12.5°	811.6	791.4	769.5	751.0	733.6	718.8	703.7	697.6	684.2	677.4	663.6
15°	771.0	747.5	724.4	699.3	681.7	658.8	637.0	610.3	588.8	570.1	564.9
17.5°	726.8	697.8	674.5	645.1	614.8	576.4	551.0	535.5	522.5	512.7	505.4
20°	696.5	666.8	642.1	597.7	556.9	530.8	512.2	500.3	486.8	476.2	470.4
22.5°	664.5	633.7	599.9	550.4	518.6	497.7	481.0	467.4	458.2	450.0	444.7
25°	619.2	585.5	529.9	495.8	470.1	448.2	436.6	428.3	418.6	407.3	402.3
27.5°	571.4	517.7	477.8	452.5	427.9	413.7	403.3	390.8	382.2	377.1	371.8
30°	535.6	482.0	450.8	423.1	405.8	390.0	377.8	370.7	362.4	353.7	350.2
32.5°	495.8	452.9	423.0	400.0	382.4	368.9	359.3	347.8	341.8	336.5	329.1
35°	446.3	413.8	386.5	367.8	351.1	340.2	328.9	322.2	311.3	306.8	303.8
37.5°	404.3	376.2	355.8	336.1	322.9	310.8	303.9	293.2	288.4	282.1	276.0
40°	380.6	353.0	333.5	317.4	302.6	293.5	284.9	276.2	269.1	266.2	258.8
42.5°	356.5	334.0	314.4	296.8	286.9	277.3	266.4	260.0	252.6	248.0	243.4
45°	323.1	303.2	286.5	272.0	261.1	251.2	244.0	233.4	229.3	219.9	216.0
47.5°	293.8	275.3	259.3	245.6	234.9	228.4	218.1	209.7	203.1	197.3	192.4
50°	272.9	257.5	242.1	229.9	220.2	210.9	200.4	196.1	185.8	183.0	180.0
52.5°	253.9	239.3	225.2	213.2	203.5	194.5	185.1	179.7	172.7	169.8	167.7
55°	227.3	213.2	199.7	189.1	179.4	170.0	164.3	157.6	154.3	152.1	149.5
57.5°	200.5	187.9	177.5	166.8	157.0	149.6	142.9	138.9	135.5	132.6	129.5
60°	183.6	171.3	162.0	152.1	142.2	136.0	130.9	126.1	122.2	117.7	116.4
62.5°	165.6	154.9	146.4	136.6	127.9	122.3	117.5	113.0	108.3	101.8	100.0
65°	140.9	132.5	123.5	115.5	107.7	102.3	95.1	90.1	88.1	87.5	87.1
67.5°	118.5	110.6	102.8	94.6	87.6	82.5	78.9	78.1	76.8	76.4	75.5
70°	103.5	96.2	88.4	80.7	74.0	73.0	71.7	70.4	68.8	68.2	67.5
72.5°	90.1	82.5	74.8	68.6	65.7	64.5	63.2	61.9	60.9	60.2	59.8
75°	69.1	62.1	56.9	54.7	53.0	52.1	50.2	49.2	48.6	47.6	47.3
77.5°	49.8	45.8	43.4	42.0	40.3	39.3	38.2	37.2	36.5	36.3	35.8
80°	38.0	36.0	34.4	32.5	31.9	30.6	30.2	29.3	29.6	28.6	28.6
82.5°	29.4	27.0	25.7	24.8	24.1	23.1	22.7	22.3	22.4	21.7	21.7
85°	15.2	14.5	13.9	13.2	13.2	12.2	12.6	12.2	12.2	11.5	11.3
87.5°	6.5	6.6	6.8	7.7	8.5	8.4	8.3	7.9	7.7	7.9	7.7
90°	8.1	10.1	13.4	18.2	22.2	22.9	22.2	21.5	20.2	21.5	22.2
92.5°	24.2	30.6	45.8	67.2	86.3	87.5	73.9	58.7	50.4	44.7	40.6
95°	49.8	66.0	96.9	155.5	233.6	263.8	230.8	176.3	135.3	107.0	92.2
97.5°	70.7	88.9	127.9	209.5	339.2	450.4	472.5	411.5	336.7	263.8	215.2
100°	84.1	103.0	138.6	220.8	366.1	531.7	628.6	614.5	531.1	438.9	357.4
102.5°	96.5	115.4	148.4	221.3	355.9	534.4	686.7	747.5	728.7	661.2	574.9
105°	114.4	133.3	164.9	224.8	335.9	498.7	677.8	817.8	893.8	902.6	880.4
107.5°	132.2	151.2	181.8	234.1	325.9	460.5	618.6	767.2	881.7	951.7	984.3
110°	144.0	163.6	193.1	241.6	323.7	442.2	581.5	723.5	844.0	930.1	985.3



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	155.3	175.4	204.0	249.7	324.3	430.3	555.7	683.7	799.3	891.4	954.7
115°	173.7	191.8	220.8	261.8	327.1	417.3	523.7	634.6	738.3	826.5	895.8
117.5°	190.6	209.5	236.3	274.7	331.9	411.0	503.4	597.8	688.8	768.8	833.8
120°	201.9	220.8	247.0	283.4	335.2	407.2	492.7	579.5	663.0	734.3	795.6
122.5°	213.2	232.6	257.3	290.9	339.0	405.0	483.5	565.0	641.4	708.9	764.3
125°	229.5	248.3	272.6	302.9	344.6	401.1	470.5	543.8	613.1	672.4	722.8
127.5°	243.9	263.3	286.9	314.0	350.4	398.8	458.3	523.0	585.7	641.5	688.1
130°	253.0	271.9	295.5	321.1	354.7	397.8	450.3	509.5	567.4	620.5	665.0
132.5°	261.7	280.5	303.0	328.0	359.0	397.3	443.8	496.5	550.2	599.0	640.8
135°	273.3	292.1	313.7	337.2	364.1	396.4	434.8	478.5	523.0	567.4	605.0
137.5°	283.5	301.0	322.3	344.2	368.7	396.3	428.4	464.2	501.3	536.6	569.4
140°	289.4	306.9	327.1	347.9	370.8	395.7	424.7	455.0	487.3	518.2	547.9
142.5°	294.8	311.3	330.9	351.2	372.5	395.7	420.9	447.5	474.9	501.5	526.3
145°	303.5	318.3	336.6	355.3	374.2	394.4	415.9	436.8	459.0	479.9	499.4
147.5°	310.8	324.0	341.1	357.7	374.8	392.0	410.9	428.6	446.1	462.4	476.6
150°	315.6	327.8	343.3	358.7	374.2	390.4	406.5	422.7	437.5	451.6	463.7
152.5°	320.5	331.6	345.4	359.3	373.2	387.7	402.8	416.7	430.5	442.5	453.0
155°	327.1	337.2	348.6	360.1	371.5	383.0	395.7	408.5	419.3	429.4	436.8
157.5°	332.8	341.2	350.9	360.1	368.4	378.2	389.2	399.0	408.0	416.5	422.2
160°	336.6	343.9	352.0	360.1	366.8	374.9	384.4	393.0	400.5	407.9	412.6
162.5°	339.8	345.5	352.6	359.6	365.2	372.2	380.0	387.1	393.5	399.8	403.5
165°	343.3	347.3	353.4	358.1	362.1	366.8	372.9	378.2	383.0	387.7	390.4
167.5°	346.2	348.8	353.2	357.1	359.0	362.1	365.8	369.8	373.4	376.6	379.1
170°	347.3	349.3	352.7	356.0	357.4	359.4	362.1	365.5	367.5	370.1	371.5
172.5°	348.4	349.8	352.1	354.4	355.2	356.2	358.3	360.6	362.1	364.3	365.1
175°	349.3	350.0	351.3	352.7	352.0	352.7	353.4	355.3	356.0	356.7	357.4
177.5°	350.0	350.0	350.5	351.6	350.5	350.0	350.5	351.6	351.6	352.1	352.1
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.6	889.1	888.3	888.8	888.3	889.1	888.6	891.4	891.9	892.4	891.9
5°	827.9	824.1	823.5	822.5	823.5	824.1	827.9	829.6	830.9	833.4	837.9
7.5°	755.5	754.9	753.4	751.1	753.4	754.9	755.5	761.0	765.4	770.4	779.6
10°	708.9	707.4	707.1	704.8	707.1	707.4	708.9	716.0	721.2	728.2	740.8
12.5°	654.4	644.1	643.0	637.4	643.0	644.1	654.4	663.6	677.4	684.2	697.6
15°	557.2	555.3	548.9	544.7	548.9	555.3	557.2	564.9	570.1	588.8	610.3
17.5°	501.6	495.3	493.4	492.5	493.4	495.3	501.6	505.4	512.7	522.5	535.5
20°	465.9	460.1	459.2	458.5	459.2	460.1	465.9	470.4	476.2	486.8	500.3
22.5°	441.2	435.1	432.7	430.8	432.7	435.1	441.2	444.7	450.0	458.2	467.4
25°	399.0	396.7	395.5	394.9	395.5	396.7	399.0	402.3	407.3	418.6	428.3
27.5°	366.0	361.1	360.1	358.4	360.1	361.1	366.0	371.8	377.1	382.2	390.8
30°	347.2	345.6	343.4	341.5	343.4	345.6	347.2	350.2	353.7	362.4	370.7
32.5°	325.1	323.8	321.8	320.9	321.8	323.8	325.1	329.1	336.5	341.8	347.8
35°	300.7	296.1	294.2	291.3	294.2	296.1	300.7	303.8	306.8	311.3	322.2
37.5°	274.7	272.3	269.7	270.6	269.7	272.3	274.7	276.0	282.1	288.4	293.2
40°	254.7	253.0	252.4	252.1	252.4	253.0	254.7	258.8	266.2	269.1	276.2
42.5°	238.7	234.3	232.6	232.6	232.6	234.3	238.7	243.4	248.0	252.6	260.0
45°	214.5	210.3	207.4	207.7	207.4	210.3	214.5	216.0	219.9	229.3	233.4
47.5°	189.7	189.5	187.7	188.3	187.7	189.5	189.7	192.4	197.3	203.1	209.7
50°	177.8	175.9	174.6	174.9	174.6	175.9	177.8	180.0	183.0	185.8	196.1
52.5°	166.5	164.8	163.8	165.1	163.8	164.8	166.5	167.7	169.8	172.7	179.7
55°	147.9	145.9	145.7	145.3	145.7	145.9	147.9	149.5	152.1	154.3	157.6
57.5°	127.2	125.9	123.9	123.1	123.9	125.9	127.2	129.5	132.6	135.5	138.9
60°	112.2	109.6	106.4	106.1	106.4	109.6	112.2	116.4	117.7	122.2	126.1
62.5°	98.6	98.1	97.5	97.4	97.5	98.1	98.6	100.0	101.8	108.3	113.0
65°	86.5	86.2	86.5	86.8	86.5	86.2	86.5	87.1	87.5	88.1	90.1
67.5°	75.3	74.8	74.2	74.5	74.2	74.8	75.3	75.5	76.4	76.8	78.1
70°	66.9	66.6	66.2	66.2	66.2	66.6	66.9	67.5	68.2	68.8	70.4
72.5°	58.6	58.5	58.3	58.0	58.3	58.5	58.6	59.8	60.2	60.9	61.9
75°	46.9	46.3	46.3	46.3	46.3	46.3	46.9	47.3	47.6	48.6	49.2
77.5°	35.7	35.5	35.1	34.9	35.1	35.5	35.7	35.8	36.3	36.5	37.2
80°	28.3	28.0	27.6	27.6	27.6	28.0	28.3	28.6	28.6	29.6	29.3
82.5°	21.6	21.3	21.2	20.9	21.2	21.3	21.6	21.7	21.7	22.4	22.3
85°	11.5	11.9	11.5	12.2	11.5	11.9	11.5	11.3	11.5	12.2	12.2
87.5°	7.7	7.5	7.7	7.5	7.7	7.5	7.7	7.7	7.9	7.7	7.9
90°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.5	20.2	21.5
92.5°	40.0	37.8	38.4	37.3	38.4	37.8	40.0	40.6	44.7	50.4	58.7
95°	83.4	78.1	76.0	76.7	76.0	78.1	83.4	92.2	107.0	135.3	176.3
97.5°	183.0	166.5	156.7	151.0	156.7	166.5	183.0	215.2	263.8	336.7	411.5
100°	301.5	272.6	253.0	240.9	253.0	272.6	301.5	357.4	438.9	531.1	614.5
102.5°	514.2	464.8	440.4	424.0	440.4	464.8	514.2	574.9	661.2	728.7	747.5
105°	838.6	796.9	767.9	758.5	767.9	796.9	838.6	880.4	902.6	893.8	817.8
107.5°	989.5	987.2	981.5	968.9	981.5	987.2	989.5	984.3	951.7	881.7	767.2
110°	1014.3	1027.1	1033.1	1032.4	1033.1	1027.1	1014.3	985.3	930.1	844.0	723.5



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	994.9	1016.3	1027.8	1031.4	1027.8	1016.3	994.9	954.7	891.4	799.3	683.7
115°	943.6	974.6	992.0	998.2	992.0	974.6	943.6	895.8	826.5	738.3	634.6
117.5°	882.5	915.2	933.7	938.7	933.7	915.2	882.5	833.8	768.8	688.8	597.8
120°	842.7	874.3	893.8	900.5	893.8	874.3	842.7	795.6	734.3	663.0	579.5
122.5°	806.6	837.7	855.1	860.7	855.1	837.7	806.6	764.3	708.9	641.4	565.0
125°	761.9	787.5	804.3	809.7	804.3	787.5	761.9	722.8	672.4	613.1	543.8
127.5°	722.2	746.1	760.7	765.0	760.7	746.1	722.2	688.1	641.5	585.7	523.0
130°	697.9	720.8	734.3	739.7	734.3	720.8	697.9	665.0	620.5	567.4	509.5
132.5°	673.2	696.0	708.4	713.3	708.4	696.0	673.2	640.8	599.0	550.2	496.5
135°	634.0	656.3	668.3	671.1	668.3	656.3	634.0	605.0	567.4	523.0	478.5
137.5°	595.8	614.9	625.5	629.6	625.5	614.9	595.8	569.4	536.6	501.3	464.2
140°	569.4	586.9	597.0	601.1	597.0	586.9	569.4	547.9	518.2	487.3	455.0
142.5°	546.8	562.7	571.7	572.5	571.7	562.7	546.8	526.3	501.5	474.9	447.5
145°	515.6	527.0	533.7	535.7	533.7	527.0	515.6	499.4	479.9	459.0	436.8
147.5°	490.0	499.1	503.7	504.9	503.7	499.1	490.0	476.6	462.4	446.1	428.6
150°	473.8	481.9	485.9	486.6	485.9	481.9	473.8	463.7	451.6	437.5	422.7
152.5°	460.9	467.9	470.9	471.0	470.9	467.9	460.9	453.0	442.5	430.5	416.7
155°	444.2	448.9	451.6	450.3	451.6	448.9	444.2	436.8	429.4	419.3	408.5
157.5°	427.5	431.4	432.7	432.7	432.7	431.4	427.5	422.2	416.5	408.0	399.0
160°	417.3	420.7	421.3	421.3	421.3	420.7	417.3	412.6	407.9	400.5	393.0
162.5°	408.1	410.4	411.1	410.5	411.1	410.4	408.1	403.5	399.8	393.5	387.1
165°	393.0	395.7	395.7	395.1	395.7	395.7	393.0	390.4	387.7	383.0	378.2
167.5°	380.3	381.8	381.6	380.8	381.6	381.8	380.3	379.1	376.6	373.4	369.8
170°	372.2	374.2	373.5	372.2	373.5	374.2	372.2	371.5	370.1	367.5	365.5
172.5°	365.8	366.7	366.0	365.2	366.0	366.7	365.8	365.1	364.3	362.1	360.6
175°	357.4	358.1	357.4	356.0	357.4	358.1	357.4	357.4	356.7	356.0	355.3
177.5°	352.1	352.1	351.6	350.5	351.6	352.1	352.1	352.1	352.1	351.6	351.6
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	889.8	893.5	898.9	902.0	907.1	910.4	912.2	915.6	917.4	923.9	930.5
5°	840.2	845.3	854.3	862.6	871.7	881.0	887.8	895.4	902.5	914.7	927.6
7.5°	783.2	790.3	804.3	817.6	833.3	846.4	858.1	871.2	883.0	900.5	918.8
10°	740.5	753.0	771.4	783.9	804.4	817.6	835.9	850.4	866.9	890.0	910.6
12.5°	703.7	718.8	733.6	751.0	769.5	791.4	811.6	830.1	849.6	873.6	897.7
15°	637.0	658.8	681.7	699.3	724.4	747.5	771.0	796.1	819.9	848.5	880.0
17.5°	551.0	576.4	614.8	645.1	674.5	697.8	726.8	757.2	785.1	819.7	854.7
20°	512.2	530.8	556.9	597.7	642.1	666.8	696.5	729.9	762.0	799.6	837.2
22.5°	481.0	497.7	518.6	550.4	599.9	633.7	664.5	698.5	735.8	774.2	815.9
25°	436.6	448.2	470.1	495.8	529.9	585.5	619.2	653.3	693.9	735.0	782.6
27.5°	403.3	413.7	427.9	452.5	477.8	517.7	571.4	608.6	648.9	695.3	744.7
30°	377.8	390.0	405.8	423.1	450.8	482.0	535.6	578.8	618.6	666.2	718.9
32.5°	359.3	368.9	382.4	400.0	423.0	452.9	495.8	548.1	586.9	637.1	692.2
35°	328.9	340.2	351.1	367.8	386.5	413.8	446.3	502.2	540.8	590.3	645.7
37.5°	303.9	310.8	322.9	336.1	355.8	376.2	404.3	454.5	496.3	544.8	601.5
40°	284.9	293.5	302.6	317.4	333.5	353.0	380.6	418.0	465.9	513.5	568.8
42.5°	266.4	277.3	286.9	296.8	314.4	334.0	356.5	388.1	437.0	482.1	535.9
45°	244.0	251.2	261.1	272.0	286.5	303.2	323.1	350.8	397.7	436.6	487.2
47.5°	218.1	228.4	234.9	245.6	259.3	275.3	293.8	317.7	355.8	392.2	439.0
50°	200.4	210.9	220.2	229.9	242.1	257.5	272.9	296.1	326.7	365.0	408.6
52.5°	185.1	194.5	203.5	213.2	225.2	239.3	253.9	274.2	300.4	335.6	378.1
55°	164.3	170.0	179.4	189.1	199.7	213.2	227.3	244.4	266.9	296.4	330.9
57.5°	142.9	149.6	157.0	166.8	177.5	187.9	200.5	216.0	233.8	260.5	290.0
60°	130.9	136.0	142.2	152.1	162.0	171.3	183.6	196.5	213.2	236.3	261.4
62.5°	117.5	122.3	127.9	136.6	146.4	154.9	165.6	179.3	193.4	214.5	236.4
65°	95.1	102.3	107.7	115.5	123.5	132.5	140.9	151.8	164.3	181.0	200.6
67.5°	78.9	82.5	87.6	94.6	102.8	110.6	118.5	127.0	137.8	150.8	166.3
70°	71.7	73.0	74.0	80.7	88.4	96.2	103.5	111.6	120.9	131.5	145.0
72.5°	63.2	64.5	65.7	68.6	74.8	82.5	90.1	96.2	105.0	113.7	124.7
75°	50.2	52.1	53.0	54.7	56.9	62.1	69.1	74.9	80.1	86.8	95.5
77.5°	38.2	39.3	40.3	42.0	43.4	45.8	49.8	55.0	59.8	63.7	69.7
80°	30.2	30.6	31.9	32.5	34.4	36.0	38.0	42.1	46.9	48.6	52.7
82.5°	22.7	23.1	24.1	24.8	25.7	27.0	29.4	30.6	34.4	36.4	39.1
85°	12.6	12.2	13.2	13.2	13.9	14.5	15.2	16.7	17.7	20.2	20.9
87.5°	8.3	8.4	8.5	7.7	6.8	6.6	6.5	6.5	6.7	7.0	7.6
90°	22.2	22.9	22.2	18.2	13.4	10.1	8.1	6.7	5.4	2.7	0.7
92.5°	73.9	87.5	86.3	67.2	45.8	30.6	24.2	19.6	16.7	11.9	8.2
95°	230.8	263.8	233.6	155.5	96.9	66.0	49.8	39.0	33.0	26.3	23.6
97.5°	472.5	450.4	339.2	209.5	127.9	88.9	70.7	58.3	49.2	42.0	38.4
100°	628.6	531.7	366.1	220.8	138.6	103.0	84.1	70.7	59.9	53.8	51.8
102.5°	686.7	534.4	355.9	221.3	148.4	115.4	96.5	82.5	71.7	65.7	64.2
105°	677.8	498.7	335.9	224.8	164.9	133.3	114.4	99.6	89.5	84.8	82.1
107.5°	618.6	460.5	325.9	234.1	181.8	151.2	132.2	117.5	108.2	103.7	101.5
110°	581.5	442.2	323.7	241.6	193.1	163.6	144.0	129.9	121.1	117.1	114.4



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	555.7	430.3	324.3	249.7	204.0	175.4	155.3	141.7	133.5	129.0	126.2
115°	523.7	417.3	327.1	261.8	220.8	191.8	173.7	160.1	152.1	148.1	144.7
117.5°	503.4	411.0	331.9	274.7	236.3	209.5	190.6	177.7	170.6	166.5	163.8
120°	492.7	407.2	335.2	283.4	247.0	220.8	201.9	188.5	182.4	178.4	175.6
122.5°	483.5	405.0	339.0	290.9	257.3	232.6	213.2	199.8	193.1	189.2	187.0
125°	470.5	401.1	344.6	302.9	272.6	248.3	229.5	216.0	207.9	204.0	201.9
127.5°	458.3	398.8	350.4	314.0	286.9	263.3	243.9	231.0	222.1	216.5	213.8
130°	450.3	397.8	354.7	321.1	295.5	271.9	253.0	239.6	230.1	223.4	220.8
132.5°	443.8	397.3	359.0	328.0	303.0	280.5	261.7	247.7	237.7	230.5	227.2
135°	434.8	396.4	364.1	337.2	313.7	292.1	273.3	257.8	247.7	239.6	236.9
137.5°	428.4	396.3	368.7	344.2	322.3	301.0	283.5	268.1	257.4	249.3	246.1
140°	424.7	395.7	370.8	347.9	327.1	306.9	289.4	274.6	263.8	255.7	253.0
142.5°	420.9	395.7	372.5	351.2	330.9	311.3	294.8	280.5	269.8	262.3	260.0
145°	415.9	394.4	374.2	355.3	336.6	318.3	303.5	290.1	280.0	273.3	270.5
147.5°	410.9	392.0	374.8	357.7	341.1	324.0	310.8	299.6	290.3	283.9	281.9
150°	406.5	390.4	374.2	358.7	343.3	327.8	315.6	305.6	296.8	291.4	289.4
152.5°	402.8	387.7	373.2	359.3	345.4	331.6	320.5	310.9	303.2	297.9	297.0
155°	395.7	383.0	371.5	360.1	348.6	337.2	327.1	319.7	312.3	308.2	307.5
157.5°	389.2	378.2	368.4	360.1	350.9	341.2	332.8	326.8	320.4	317.1	316.5
160°	384.4	374.9	366.8	360.1	352.0	343.9	336.6	331.1	325.7	323.0	322.4
162.5°	380.0	372.2	365.2	359.6	352.6	345.5	339.8	334.9	330.6	327.9	328.3
165°	372.9	366.8	362.1	358.1	353.4	347.3	343.3	339.9	335.9	334.5	335.2
167.5°	365.8	362.1	359.0	357.1	353.2	348.8	346.2	343.8	341.2	340.0	340.9
170°	362.1	359.4	357.4	356.0	352.7	349.3	347.3	345.9	343.9	343.3	344.6
172.5°	358.3	356.2	355.2	354.4	352.1	349.8	348.4	347.6	345.5	345.9	346.7
175°	353.4	352.7	352.0	352.7	351.3	350.0	349.3	349.3	347.9	348.6	349.3
177.5°	350.5	350.0	350.5	351.6	350.5	350.0	350.0	350.0	348.9	349.5	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	930.7	931.5	936.7	939.0	943.7	945.5	947.4	946.9	946.9	948.0	955.2
5°	932.7	939.2	948.8	958.1	967.2	974.9	980.0	985.2	987.1	996.4	1004.8
7.5°	929.4	941.2	957.2	971.4	988.4	1001.8	1012.8	1022.8	1029.6	1043.2	1057.0
10°	925.1	941.8	959.8	978.1	1001.6	1019.3	1037.2	1051.1	1055.6	1075.8	1087.4
12.5°	916.3	938.7	961.6	985.3	1008.2	1032.6	1052.4	1066.3	1082.1	1100.3	1121.6
15°	903.2	928.9	958.8	989.4	1022.2	1051.7	1073.0	1097.1	1114.4	1134.4	1153.0
17.5°	884.3	917.5	955.5	990.8	1028.7	1060.5	1089.8	1112.8	1125.1	1136.4	1139.3
20°	869.4	905.1	949.8	991.6	1029.5	1066.2	1095.1	1114.4	1117.7	1117.9	1100.9
22.5°	853.3	893.5	940.3	983.1	1028.5	1069.3	1091.7	1100.0	1087.3	1065.5	1032.5
25°	823.5	870.0	924.4	973.3	1022.8	1061.4	1069.1	1054.6	1010.0	962.9	903.5
27.5°	791.2	843.5	901.8	956.1	1008.9	1032.9	1016.2	964.0	883.5	813.6	728.8
30°	767.5	826.3	883.6	944.3	993.2	1003.5	965.3	888.4	794.5	689.1	604.5
32.5°	740.5	802.1	865.0	927.9	968.8	958.7	895.5	800.9	690.9	587.2	507.2
35°	701.9	765.6	833.4	896.4	922.5	879.1	784.5	661.4	548.9	452.1	397.1
37.5°	657.4	726.7	797.2	855.1	853.3	780.8	652.1	525.0	430.4	373.2	334.0
40°	625.7	695.8	772.0	820.9	800.0	705.8	566.2	446.3	377.1	331.5	302.9
42.5°	595.4	665.7	741.4	780.2	743.9	628.1	489.0	395.1	338.0	302.5	279.2
45°	543.7	617.9	688.1	709.6	644.6	517.0	395.5	327.4	289.4	263.0	246.9
47.5°	493.3	566.3	630.3	630.7	542.8	419.3	333.6	283.3	250.9	230.5	218.8
50°	462.4	531.8	585.5	577.1	477.5	373.0	298.3	254.9	228.0	212.2	200.0
52.5°	427.7	495.0	541.5	517.7	422.1	328.2	266.7	230.3	207.9	194.2	183.3
55°	377.1	437.0	469.8	433.8	344.4	272.9	225.4	196.7	180.0	168.5	159.2
57.5°	327.6	376.9	397.5	355.6	283.6	226.4	190.6	169.2	152.6	144.3	139.5
60°	296.4	338.5	353.0	306.8	246.6	198.0	168.8	148.9	136.6	131.2	126.4
62.5°	265.9	300.2	306.3	263.8	215.0	173.4	148.3	131.4	123.3	118.0	113.5
65°	220.6	245.3	242.5	208.4	170.0	137.6	119.2	109.0	102.9	95.5	87.5
67.5°	181.6	196.7	187.6	162.0	129.8	106.9	95.0	87.2	79.6	72.6	70.8
70°	156.9	165.6	155.9	132.5	106.4	89.7	80.1	70.8	66.2	64.7	61.7
72.5°	133.3	136.3	125.9	105.7	86.6	74.3	64.9	59.7	57.3	55.9	54.0
75°	100.0	97.7	88.8	73.0	60.1	51.7	48.9	46.9	45.4	44.1	43.0
77.5°	70.3	66.9	58.9	48.6	41.8	37.9	36.2	35.1	34.4	33.7	32.7
80°	52.7	50.5	42.4	34.7	31.9	29.9	28.9	27.6	27.6	27.0	26.0
82.5°	38.6	36.1	29.1	25.5	23.8	22.7	22.0	21.2	20.9	21.1	20.4
85°	20.2	16.4	14.5	13.9	12.8	12.2	12.6	11.9	11.9	11.9	11.5
87.5°	6.7	5.9	5.9	6.0	6.6	7.3	8.0	8.8	9.2	8.8	9.0
90°	2.7	5.4	6.7	8.1	10.1	13.4	18.2	22.2	22.9	22.2	21.5
92.5°	11.9	16.7	19.6	24.2	30.6	45.8	67.2	86.3	87.5	73.9	58.7
95°	26.3	33.0	39.0	49.8	66.0	96.9	155.5	233.6	263.8	230.8	176.3
97.5°	42.0	49.2	58.3	70.7	88.9	127.9	209.5	339.2	450.4	472.5	411.5
100°	53.8	59.9	70.7	84.1	103.0	138.6	220.8	366.1	531.7	628.6	614.5
102.5°	65.7	71.7	82.5	96.5	115.4	148.4	221.3	355.9	534.4	686.7	747.5
105°	84.8	89.5	99.6	114.4	133.3	164.9	224.8	335.9	498.7	677.8	817.8
107.5°	103.7	108.2	117.5	132.2	151.2	181.8	234.1	325.9	460.5	618.6	767.2
110°	117.1	121.1	129.9	144.0	163.6	193.1	241.6	323.7	442.2	581.5	723.5



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	129.0	133.5	141.7	155.3	175.4	204.0	249.7	324.3	430.3	555.7	683.7
115°	148.1	152.1	160.1	173.7	191.8	220.8	261.8	327.1	417.3	523.7	634.6
117.5°	166.5	170.6	177.7	190.6	209.5	236.3	274.7	331.9	411.0	503.4	597.8
120°	178.4	182.4	188.5	201.9	220.8	247.0	283.4	335.2	407.2	492.7	579.5
122.5°	189.2	193.1	199.8	213.2	232.6	257.3	290.9	339.0	405.0	483.5	565.0
125°	204.0	207.9	216.0	229.5	248.3	272.6	302.9	344.6	401.1	470.5	543.8
127.5°	216.5	222.1	231.0	243.9	263.3	286.9	314.0	350.4	398.8	458.3	523.0
130°	223.4	230.1	239.6	253.0	271.9	295.5	321.1	354.7	397.8	450.3	509.5
132.5°	230.5	237.7	247.7	261.7	280.5	303.0	328.0	359.0	397.3	443.8	496.5
135°	239.6	247.7	257.8	273.3	292.1	313.7	337.2	364.1	396.4	434.8	478.5
137.5°	249.3	257.4	268.1	283.5	301.0	322.3	344.2	368.7	396.3	428.4	464.2
140°	255.7	263.8	274.6	289.4	306.9	327.1	347.9	370.8	395.7	424.7	455.0
142.5°	262.3	269.8	280.5	294.8	311.3	330.9	351.2	372.5	395.7	420.9	447.5
145°	273.3	280.0	290.1	303.5	318.3	336.6	355.3	374.2	394.4	415.9	436.8
147.5°	283.9	290.3	299.6	310.8	324.0	341.1	357.7	374.8	392.0	410.9	428.6
150°	291.4	296.8	305.6	315.6	327.8	343.3	358.7	374.2	390.4	406.5	422.7
152.5°	297.9	303.2	310.9	320.5	331.6	345.4	359.3	373.2	387.7	402.8	416.7
155°	308.2	312.3	319.7	327.1	337.2	348.6	360.1	371.5	383.0	395.7	408.5
157.5°	317.1	320.4	326.8	332.8	341.2	350.9	360.1	368.4	378.2	389.2	399.0
160°	323.0	325.7	331.1	336.6	343.9	352.0	360.1	366.8	374.9	384.4	393.0
162.5°	327.9	330.6	334.9	339.8	345.5	352.6	359.6	365.2	372.2	380.0	387.1
165°	334.5	335.9	339.9	343.3	347.3	353.4	358.1	362.1	366.8	372.9	378.2
167.5°	340.0	341.2	343.8	346.2	348.8	353.2	357.1	359.0	362.1	365.8	369.8
170°	343.3	343.9	345.9	347.3	349.3	352.7	356.0	357.4	359.4	362.1	365.5
172.5°	345.9	345.5	347.6	348.4	349.8	352.1	354.4	355.2	356.2	358.3	360.6
175°	348.6	347.9	349.3	349.3	350.0	351.3	352.7	352.0	352.7	353.4	355.3
177.5°	349.5	348.9	350.0	350.0	350.0	350.5	351.6	350.5	350.0	350.5	351.6
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0	350.0



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	957.8	961.1	962.7	962.7	964.5	963.7	962.9
5°	1012.8	1018.9	1020.2	1026.0	1030.2	1028.9	1029.5
7.5°	1067.6	1077.4	1087.1	1091.5	1092.3	1094.8	1095.8
10°	1101.2	1109.3	1124.4	1122.1	1133.4	1139.8	1129.2
12.5°	1133.7	1144.5	1155.0	1157.9	1164.2	1166.3	1162.1
15°	1163.0	1168.7	1169.4	1167.8	1169.8	1168.1	1162.0
17.5°	1135.6	1126.2	1107.2	1098.1	1091.0	1080.5	1076.2
20°	1090.3	1062.6	1030.5	1017.6	1002.5	972.9	980.0
22.5°	992.6	961.0	928.9	891.3	873.4	845.3	843.7
25°	840.5	786.2	726.3	684.5	660.1	632.1	619.9
27.5°	653.5	585.0	536.1	511.3	488.6	466.5	465.5
30°	530.5	479.1	441.2	419.9	406.1	396.7	398.7
32.5°	447.2	411.9	386.3	368.8	358.5	351.5	351.4
35°	365.6	341.5	325.0	317.7	310.3	305.1	305.5
37.5°	312.9	298.3	289.2	281.1	276.5	274.0	272.5
40°	285.9	274.0	266.9	262.1	258.2	254.7	254.0
42.5°	264.5	254.7	247.5	243.7	240.2	237.6	237.0
45°	234.7	226.7	220.2	216.0	214.5	212.2	212.2
47.5°	208.8	200.9	195.9	193.2	190.5	189.0	188.9
50°	191.3	185.2	180.7	179.1	176.8	175.9	175.6
52.5°	175.6	171.1	167.8	166.8	165.7	164.5	164.7
55°	154.3	151.8	150.5	149.5	147.9	145.9	147.2
57.5°	136.4	134.2	130.7	127.7	126.2	124.8	125.4
60°	123.8	119.2	114.8	111.2	110.3	107.4	107.4
62.5°	107.9	101.5	96.0	94.0	93.1	91.7	91.4
65°	82.9	80.4	79.1	77.8	77.1	77.1	76.5
67.5°	68.7	67.7	66.3	66.0	65.3	65.2	64.9
70°	60.8	59.5	58.8	58.5	57.9	58.2	57.3
72.5°	53.0	52.0	51.9	51.1	50.7	50.7	50.0
75°	41.8	41.8	41.5	41.2	40.6	40.2	40.6
77.5°	32.1	32.2	31.6	31.6	31.5	31.6	31.3
80°	25.7	26.0	25.7	25.4	25.1	25.4	25.1
82.5°	20.3	19.9	19.8	19.7	19.7	19.5	19.5
85°	11.5	11.9	11.5	11.3	11.3	11.3	11.5
87.5°	8.4	8.7	8.8	8.8	8.8	8.8	8.5
90°	20.2	21.5	22.2	22.2	22.2	22.2	22.2
92.5°	50.4	44.7	40.6	40.0	37.8	38.4	37.3
95°	135.3	107.0	92.2	83.4	78.1	76.0	76.7
97.5°	336.7	263.8	215.2	183.0	166.5	156.7	151.0
100°	531.1	438.9	357.4	301.5	272.6	253.0	240.9
102.5°	728.7	661.2	574.9	514.2	464.8	440.4	424.0
105°	893.8	902.6	880.4	838.6	796.9	767.9	758.5
107.5°	881.7	951.7	984.3	989.5	987.2	981.5	968.9
110°	844.0	930.1	985.3	1014.3	1027.1	1033.1	1032.4



TEST NUMBER: P331659-935

CATALOG NUMBER: SA2XXRDIP-C485D725U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	799.3	891.4	954.7	994.9	1016.3	1027.8	1031.4
115°	738.3	826.5	895.8	943.6	974.6	992.0	998.2
117.5°	688.8	768.8	833.8	882.5	915.2	933.7	938.7
120°	663.0	734.3	795.6	842.7	874.3	893.8	900.5
122.5°	641.4	708.9	764.3	806.6	837.7	855.1	860.7
125°	613.1	672.4	722.8	761.9	787.5	804.3	809.7
127.5°	585.7	641.5	688.1	722.2	746.1	760.7	765.0
130°	567.4	620.5	665.0	697.9	720.8	734.3	739.7
132.5°	550.2	599.0	640.8	673.2	696.0	708.4	713.3
135°	523.0	567.4	605.0	634.0	656.3	668.3	671.1
137.5°	501.3	536.6	569.4	595.8	614.9	625.5	629.6
140°	487.3	518.2	547.9	569.4	586.9	597.0	601.1
142.5°	474.9	501.5	526.3	546.8	562.7	571.7	572.5
145°	459.0	479.9	499.4	515.6	527.0	533.7	535.7
147.5°	446.1	462.4	476.6	490.0	499.1	503.7	504.9
150°	437.5	451.6	463.7	473.8	481.9	485.9	486.6
152.5°	430.5	442.5	453.0	460.9	467.9	470.9	471.0
155°	419.3	429.4	436.8	444.2	448.9	451.6	450.3
157.5°	408.0	416.5	422.2	427.5	431.4	432.7	432.7
160°	400.5	407.9	412.6	417.3	420.7	421.3	421.3
162.5°	393.5	399.8	403.5	408.1	410.4	411.1	410.5
165°	383.0	387.7	390.4	393.0	395.7	395.7	395.1
167.5°	373.4	376.6	379.1	380.3	381.8	381.6	380.8
170°	367.5	370.1	371.5	372.2	374.2	373.5	372.2
172.5°	362.1	364.3	365.1	365.8	366.7	366.0	365.2
175°	356.0	356.7	357.4	357.4	358.1	357.4	356.0
177.5°	351.6	352.1	352.1	352.1	352.1	351.6	350.5
180°	350.0	350.0	350.0	350.0	350.0	350.0	350.0

(END OF REPORT)