

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331259-840

Luminaire Tested: **SA2XXDIP-C290D725U840-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331259-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3936.2 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29				
2	86	79	73	68	78	72	67	63	58	54	51	45	42	40	33	31	30	25				
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	27	26	21				
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18	15				
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9637	9637	9637	9637
5°	10804	9700	8596	9700
10°	12381	9621	7438	9621
15°	13697	9444	6572	9444
20°	13490	9256	5991	9256
25°	12162	9002	5624	9002
30°	10051	8600	5354	8600
35°	7324	8180	5164	8180
40°	5851	7685	5056	7685
45°	5112	7108	4914	7108
50°	4808	6551	4818	6551
55°	4428	5987	4687	5987
60°	4059	5383	4492	5383
65°	3698	4844	4294	4844
70°	3356	4319	4008	4319
75°	2982	3737	3550	3737
80°	2566	3087	2854	3087
85°	2297	2297	1704	2297



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	1.4
10°-20°	165.3	4.2
20°-30°	239.9	6.1
30°-40°	253.1	6.4
40°-50°	224.1	5.7
50°-60°	178.8	4.5
60°-70°	121.6	3.1
70°-80°	62.3	1.6
80°-90°	18.8	0.5
90°-100°	59.3	1.5
100°-110°	184.1	4.7
110°-120°	314.7	8.0
120°-130°	413.8	10.5
130°-140°	464.4	11.8
140°-150°	455.4	11.6
150°-160°	382.0	9.7
160°-170°	253.3	6.4
170°-180°	88.5	2.2
0°-30°	462.0	11.7
0°-40°	715.1	18.2
0°-60°	1118.0	28.4
0°-90°	1320.7	33.6
90°-120°	558.0	14.2
90°-150°	1891.7	48.1
90°-180°	2616.0	66.5
0°-180°	3936.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	597	597	597	597	597	
5°	667	598	530	598	667	67
15°	819	565	393	565	819	226
25°	683	505	316	505	683	309
35°	372	415	262	415	372	242
45°	224	311	215	311	224	176
55°	157	213	166	213	157	141
65°	97	127	112	127	97	96
75°	48	60	57	60	48	51
85°	12	12	9	12	12	14
90°	27	1	27	1	27	12
95°	49	41	49	41	49	55
105°	175	170	175	170	175	184
115°	316	316	316	316	316	312
125°	461	459	461	459	461	411
135°	602	594	602	594	602	463
145°	729	721	729	721	729	455
155°	831	825	831	825	831	383
165°	898	898	898	898	898	253
175°	931	934	931	934	931	88
180°	935	935	935	935	935	



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	624.4	624.6	625.0	622.1	621.7	621.7	619.1	616.9	614.3	610.9	611.3
5°	666.6	669.1	670.0	667.3	663.2	662.8	658.8	652.5	646.4	641.7	638.2
7.5°	717.0	718.0	715.8	712.2	709.1	703.6	696.3	689.2	679.2	670.1	663.4
10°	755.2	756.6	752.7	747.4	743.1	736.6	726.1	715.3	702.3	689.6	679.5
12.5°	784.2	787.6	782.5	781.9	774.5	765.6	753.1	747.6	729.2	711.7	700.7
15°	819.4	819.2	819.7	815.3	809.8	808.4	795.2	780.6	754.8	744.4	726.5
17.5°	809.2	812.7	814.4	814.3	814.2	813.2	809.0	799.9	786.9	770.1	749.5
20°	785.1	789.6	790.3	795.6	798.6	802.4	804.1	801.5	793.6	779.5	761.6
22.5°	747.6	748.9	751.0	759.2	765.7	775.5	780.5	789.1	786.0	779.1	764.2
25°	682.7	680.4	688.4	692.6	707.5	723.1	734.4	746.7	757.7	764.4	760.0
27.5°	604.8	601.4	613.4	624.4	636.4	653.4	670.9	691.6	708.7	730.3	737.7
30°	539.1	541.2	552.6	564.3	582.7	606.5	626.3	648.9	673.6	697.6	714.4
32.5°	468.3	476.2	483.4	501.4	517.6	544.1	573.1	601.5	632.1	659.4	685.4
35°	371.6	380.8	390.9	403.9	426.7	453.0	481.3	519.6	561.4	598.7	629.4
37.5°	312.9	311.3	317.1	326.6	345.0	366.3	398.8	436.6	485.7	529.7	573.1
40°	277.6	276.7	280.7	289.5	303.5	319.1	347.6	380.8	426.5	480.2	531.8
42.5°	253.4	253.9	256.2	262.4	272.0	284.8	306.1	334.4	376.2	426.8	482.2
45°	223.9	225.5	228.0	231.1	236.5	247.1	259.0	279.2	312.3	354.5	409.0
47.5°	202.7	202.8	205.3	207.9	211.2	217.1	226.9	239.5	262.9	297.2	344.2
50°	191.4	189.8	191.6	193.6	197.0	201.2	207.6	219.5	235.1	262.9	302.2
52.5°	177.3	177.4	179.0	179.9	182.9	187.0	192.9	201.2	215.3	237.0	269.2
55°	157.3	158.5	159.5	160.8	163.6	166.5	171.2	176.6	187.6	203.9	227.8
57.5°	138.6	139.0	139.9	142.5	144.2	146.9	151.3	156.3	163.5	175.5	193.5
60°	125.7	125.7	127.5	128.7	131.0	133.7	137.1	142.0	148.5	158.2	172.8
62.5°	114.0	113.8	114.5	116.4	118.2	120.7	124.1	128.3	134.3	143.1	154.9
65°	96.8	96.3	97.8	98.2	100.0	102.5	105.3	109.7	114.5	120.9	131.5
67.5°	80.3	80.9	81.6	82.4	83.4	86.1	88.0	91.0	95.1	100.5	107.6
70°	71.1	71.1	71.1	71.8	73.2	74.5	76.3	78.9	82.8	87.4	93.8
72.5°	60.8	61.6	62.3	61.9	63.6	64.4	66.7	68.1	71.8	74.7	80.4
75°	47.8	47.8	47.8	48.9	49.6	50.2	51.6	53.0	54.8	58.5	61.5
77.5°	35.6	35.5	35.7	36.1	36.8	37.6	38.0	39.2	40.9	42.6	45.1
80°	27.6	28.0	28.2	28.7	28.7	29.1	29.4	31.0	32.1	33.2	34.8
82.5°	21.3	21.4	21.4	21.5	21.7	22.0	22.6	23.1	23.5	24.4	25.7
85°	12.4	12.1	12.1	12.6	12.4	12.4	12.8	13.3	13.3	13.5	14.2
87.5°	10.1	10.1	10.3	10.0	10.0	10.2	10.3	10.2	10.4	10.7	10.1
90°	26.9	26.7	26.5	26.4	26.2	26.3	26.6	27.0	27.3	27.7	23.7
92.5°	25.5	25.5	25.5	25.4	25.4	25.3	25.3	25.2	25.1	25.1	24.2
95°	49.0	49.3	49.7	50.0	50.4	50.5	50.5	50.5	50.5	50.5	50.2
97.5°	84.7	84.8	84.8	84.9	84.9	84.9	84.9	84.9	84.9	84.9	84.2
100°	108.2	108.4	108.5	108.7	108.9	109.0	109.0	109.0	109.0	109.0	108.4
102.5°	134.6	134.8	135.0	135.2	135.3	135.4	135.2	135.1	134.9	134.8	134.1
105°	175.2	175.2	175.2	175.2	175.2	175.1	174.7	174.4	174.0	173.7	173.3
107.5°	213.5	214.3	215.1	215.9	216.7	217.0	216.8	216.7	216.6	216.4	216.4
110°	243.1	243.7	244.2	244.7	245.2	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.6	272.0	272.3	272.7	273.1	273.5	273.9	274.3	274.8	275.2	275.3
115°	315.8	316.3	316.8	317.3	317.8	318.2	318.4	318.5	318.7	318.9	319.2
117.5°	357.9	358.4	358.9	359.5	360.0	360.4	360.9	361.3	361.7	362.1	363.1
120°	387.6	388.1	388.6	389.1	389.7	389.9	389.9	389.9	389.9	389.9	391.3
122.5°	416.7	417.0	417.4	417.8	418.2	418.6	419.0	419.4	419.8	420.2	421.2
125°	461.0	461.2	461.3	461.5	461.7	462.0	462.5	463.1	463.6	464.1	464.6
127.5°	501.4	502.0	502.5	503.1	503.6	504.2	504.8	505.5	506.1	506.8	507.4
130°	530.5	531.2	531.9	532.5	533.2	533.8	534.1	534.5	534.8	535.2	535.5
132.5°	558.3	558.8	559.4	559.9	560.5	561.2	561.9	562.7	563.5	564.2	564.1
135°	601.5	602.0	602.6	603.1	603.6	603.9	604.1	604.3	604.5	604.6	604.3
137.5°	640.7	641.4	642.1	642.8	643.5	643.9	644.0	644.2	644.3	644.4	644.0
140°	667.8	668.5	669.2	669.9	670.6	671.0	671.0	671.0	671.0	671.0	670.0
142.5°	692.5	693.2	693.8	694.5	695.2	695.5	695.4	695.2	695.1	695.0	694.4
145°	729.3	730.0	730.7	731.4	732.2	732.5	732.3	732.1	732.0	731.7	730.6
147.5°	762.3	763.1	763.7	764.4	765.1	765.2	764.8	764.4	764.0	763.7	763.0
150°	783.9	784.4	784.9	785.4	786.0	786.0	785.4	784.9	784.4	783.9	783.2
152.5°	804.1	804.7	805.4	806.1	806.7	806.7	806.1	805.4	804.7	804.1	803.1
155°	831.2	831.7	832.2	832.7	833.3	833.1	832.2	831.3	830.5	829.6	829.1
157.5°	854.5	855.4	856.3	857.1	857.9	857.8	856.6	855.4	854.1	852.9	852.6
160°	869.1	869.8	870.5	871.2	871.9	871.7	870.7	869.6	868.6	867.5	867.4
162.5°	881.7	882.5	883.4	884.2	885.0	884.9	883.7	882.5	881.3	880.1	880.0
165°	898.3	899.2	900.0	900.9	901.8	901.6	900.4	899.2	898.0	896.7	896.7
167.5°	911.9	912.8	913.7	914.6	915.5	915.3	914.1	912.9	911.7	910.4	910.5
170°	918.8	919.9	920.9	922.0	923.0	922.9	921.7	920.5	919.3	918.0	918.2
172.5°	924.5	925.5	926.6	927.7	928.7	928.6	927.4	926.1	924.9	923.7	923.9
175°	930.7	931.7	932.7	933.8	934.8	934.7	933.5	932.3	931.1	929.9	930.2
177.5°	933.5	934.3	935.1	936.0	936.9	936.9	936.0	935.1	934.3	933.5	933.7
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	612.5	611.1	610.2	606.8	603.9	601.0	600.1	600.4	596.3	592.5	590.9
5°	636.4	631.8	627.4	621.3	613.9	605.8	601.8	598.5	590.5	581.8	576.7
7.5°	657.7	651.2	642.8	631.2	620.5	607.8	599.8	592.7	581.0	568.7	561.1
10°	670.8	661.9	651.1	636.8	623.8	608.3	597.6	586.8	573.1	558.4	549.2
12.5°	682.0	669.9	659.3	641.1	625.6	606.3	593.6	578.3	563.9	546.4	537.5
15°	708.6	686.4	666.2	645.5	626.5	599.7	585.4	565.0	546.0	524.4	514.1
17.5°	729.2	704.2	672.5	646.2	624.0	594.2	573.4	549.0	526.4	501.8	487.8
20°	740.9	712.3	678.1	646.9	620.4	586.3	563.6	538.7	512.3	484.5	469.4
22.5°	747.9	717.8	684.0	644.2	613.0	580.0	551.4	523.9	497.3	467.3	451.4
25°	750.1	722.7	686.8	641.9	603.8	566.4	532.0	505.3	473.0	445.0	421.9
27.5°	739.2	719.5	685.1	637.5	593.2	549.5	511.1	481.0	446.9	416.5	393.1
30°	725.8	714.4	680.9	633.2	584.7	537.8	495.5	461.3	427.4	396.7	372.7
32.5°	705.1	702.7	673.2	626.9	575.7	522.9	479.2	444.6	407.0	376.8	354.1
35°	664.4	675.4	656.8	613.0	558.9	501.7	454.4	415.0	376.0	347.1	325.8
37.5°	609.8	637.1	632.3	592.6	535.9	478.7	426.5	385.3	348.1	318.9	298.0
40°	572.1	607.0	612.1	576.9	519.9	460.9	405.6	364.6	328.3	301.6	280.5
42.5°	531.8	572.5	586.3	558.3	502.2	442.1	386.9	344.4	308.4	282.6	263.9
45°	464.1	518.0	543.0	526.9	472.8	411.3	354.5	311.3	278.7	254.4	239.9
47.5°	400.8	459.7	493.3	487.7	440.1	379.2	323.0	281.6	249.8	230.5	217.5
50°	356.1	416.6	457.2	459.1	416.6	356.3	299.8	260.8	231.7	213.6	203.0
52.5°	317.1	375.0	419.2	429.0	390.3	332.4	279.1	240.2	214.6	197.9	188.5
55°	266.3	315.2	364.3	382.2	351.2	296.2	246.8	212.7	188.5	177.1	168.8
57.5°	221.5	262.2	307.5	327.3	308.2	261.1	214.8	185.1	165.6	155.5	149.2
60°	197.7	229.8	270.2	293.9	277.3	235.4	195.0	166.7	150.7	141.8	135.8
62.5°	175.7	204.2	238.3	259.9	251.0	211.4	175.2	150.3	136.4	128.1	123.7
65°	145.0	167.4	193.9	213.8	207.8	177.8	148.1	126.8	115.8	109.2	105.7
67.5°	119.4	135.6	153.9	171.4	166.6	145.3	121.6	104.9	96.7	91.0	88.9
70°	103.2	115.6	131.9	145.9	142.0	124.6	105.7	91.5	84.4	79.6	77.6
72.5°	87.9	98.0	110.5	121.9	119.3	104.7	89.1	78.4	72.8	68.4	66.8
75°	66.3	74.1	81.7	89.3	88.6	77.4	68.2	59.9	55.5	52.1	51.4
77.5°	49.0	53.3	58.5	62.9	61.7	55.2	48.1	43.3	40.2	37.9	37.5
80°	37.4	39.9	43.6	46.8	45.2	42.4	36.7	33.2	31.0	28.7	27.8
82.5°	27.2	29.6	31.8	33.6	32.3	29.8	26.3	23.9	22.5	21.0	20.6
85°	14.2	15.6	16.6	17.0	16.6	14.9	13.3	12.4	11.2	10.5	10.3
87.5°	9.5	8.7	8.0	7.7	6.8	6.4	5.2	4.2	4.4	4.6	4.7
90°	19.9	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.2	22.3	21.4	20.2	18.7	17.2	15.6	14.0	15.6	17.2	18.7
95°	49.8	49.5	49.1	48.1	46.4	44.5	42.8	41.0	42.8	44.5	46.4
97.5°	83.6	82.9	82.3	81.2	79.6	78.1	76.5	75.0	76.5	78.1	79.6
100°	107.9	107.3	106.8	105.8	104.4	103.0	101.7	100.3	101.7	103.0	104.4
102.5°	133.5	132.8	132.2	131.3	130.2	129.1	127.8	126.7	127.8	129.1	130.2
105°	173.0	172.6	172.3	171.8	171.3	170.8	170.3	169.8	170.3	170.8	171.3
107.5°	216.4	216.4	216.4	216.0	215.3	214.5	213.8	213.0	213.8	214.5	215.3
110°	245.5	245.5	245.5	245.0	243.9	242.9	241.8	240.8	241.8	242.9	243.9



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.5	275.6	275.7	275.3	274.2	273.2	272.2	271.0	272.2	273.2	274.2
115°	319.6	319.9	320.3	319.9	318.9	317.8	316.8	315.8	316.8	317.8	318.9
117.5°	364.2	365.1	366.1	365.9	364.5	363.0	361.6	360.2	361.6	363.0	364.5
120°	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	391.3	392.7	394.2
122.5°	422.2	423.2	424.1	423.8	422.1	420.5	418.8	417.1	418.8	420.5	422.1
125°	465.1	465.7	466.3	465.7	464.1	462.5	461.0	459.4	461.0	462.5	464.1
127.5°	508.1	508.7	509.3	508.6	506.6	504.6	502.6	500.6	502.6	504.6	506.6
130°	535.8	536.2	536.5	535.6	533.3	531.1	528.8	526.5	528.8	531.1	533.3
132.5°	564.1	564.0	563.9	563.0	561.1	559.3	557.4	555.5	557.4	559.3	561.1
135°	603.9	603.6	603.2	602.1	600.2	598.2	596.3	594.4	596.3	598.2	600.2
137.5°	643.5	643.1	642.6	641.6	640.1	638.4	636.8	635.3	636.8	638.4	640.1
140°	669.2	668.3	667.4	666.2	664.6	663.1	661.5	659.9	661.5	663.1	664.6
142.5°	693.8	693.2	692.6	691.5	689.9	688.3	686.7	685.2	686.7	688.3	689.9
145°	729.6	728.6	727.5	726.4	725.2	724.0	722.7	721.4	722.7	724.0	725.2
147.5°	762.2	761.5	760.8	759.7	758.2	756.8	755.3	753.9	755.3	756.8	758.2
150°	782.4	781.7	781.0	780.1	779.1	778.0	777.0	776.0	777.0	778.0	779.1
152.5°	802.3	801.5	800.6	799.7	798.7	797.6	796.6	795.5	796.6	797.6	798.7
155°	828.6	828.0	827.5	827.0	826.5	826.0	825.4	824.9	825.4	826.0	826.5
157.5°	852.3	852.0	851.7	851.4	851.0	850.7	850.3	850.0	850.3	850.7	851.0
160°	867.2	867.0	866.8	866.6	866.2	865.9	865.5	865.2	865.5	865.9	866.2
162.5°	879.8	879.6	879.4	879.3	879.2	879.2	879.1	879.0	879.1	879.2	879.2
165°	896.7	896.7	896.7	896.8	897.0	897.2	897.4	897.5	897.4	897.2	897.0
167.5°	910.5	910.6	910.6	910.9	911.4	911.9	912.4	912.9	912.4	911.9	911.4
170°	918.4	918.6	918.7	919.1	919.6	920.1	920.7	921.2	920.7	920.1	919.6
172.5°	924.0	924.2	924.4	924.7	925.2	925.8	926.3	926.9	926.3	925.8	925.2
175°	930.6	930.9	931.3	931.7	932.2	932.7	933.3	933.8	933.3	932.7	932.2
177.5°	934.0	934.3	934.6	934.9	935.3	935.8	936.2	936.6	936.2	935.8	935.3
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	589.1	587.9	584.1	582.1	578.8	575.6	573.6	574.5	575.2	574.9	574.3
5°	572.1	567.7	561.1	555.4	551.3	543.7	540.5	538.9	537.5	535.9	534.3
7.5°	552.0	545.1	535.6	527.5	519.8	510.3	504.9	501.8	498.5	494.8	491.6
10°	537.8	528.1	518.0	506.5	497.4	488.9	481.3	476.3	471.6	467.3	464.1
12.5°	522.7	511.6	499.1	483.4	473.3	461.1	460.0	451.1	443.9	441.2	437.5
15°	498.8	483.1	467.3	448.7	440.7	429.7	422.8	415.9	409.7	405.4	404.2
17.5°	471.5	451.3	435.6	422.2	409.1	397.8	391.4	386.0	380.8	375.1	374.3
20°	450.8	433.3	416.2	404.5	390.9	379.4	371.6	366.2	361.7	358.3	355.4
22.5°	431.1	412.0	396.3	383.5	370.2	360.9	354.8	349.4	345.8	342.0	339.2
25°	399.6	384.8	367.5	353.0	342.0	336.1	331.0	326.5	324.2	321.6	318.4
27.5°	372.0	355.5	339.4	328.2	318.5	313.3	309.6	306.5	304.4	302.9	301.0
30°	352.6	335.9	323.3	312.3	304.2	298.9	296.6	294.8	292.3	291.3	290.4
32.5°	333.9	318.8	308.0	298.4	290.8	287.3	285.3	283.6	281.7	280.7	278.8
35°	307.4	294.8	284.3	278.9	272.8	269.7	268.2	265.9	264.1	263.2	262.9
37.5°	282.5	271.6	264.6	257.8	255.2	253.4	251.2	249.6	249.0	248.9	248.6
40°	266.3	257.4	251.2	245.7	244.6	241.8	239.9	238.6	238.6	238.8	238.6
42.5°	251.7	243.6	238.1	233.4	232.1	230.5	228.5	228.5	228.8	229.6	228.8
45°	229.4	223.7	219.7	217.5	215.0	213.4	213.1	213.8	214.0	214.3	215.0
47.5°	208.9	205.1	201.6	199.0	197.9	197.7	197.4	198.6	199.8	200.2	201.2
50°	196.8	192.5	189.5	187.8	186.9	186.5	186.9	188.3	189.2	190.4	191.1
52.5°	183.3	180.2	178.1	176.8	176.5	176.8	176.8	178.4	179.9	180.4	180.7
55°	164.5	162.2	161.8	159.7	160.6	160.4	161.5	162.4	163.8	165.2	165.4
57.5°	145.7	143.9	142.7	142.9	143.2	144.2	145.1	146.7	148.1	149.7	149.8
60°	133.3	132.4	131.7	131.7	132.1	133.5	134.6	136.2	137.1	138.1	138.8
62.5°	121.9	121.0	120.3	120.7	121.9	122.7	124.0	124.9	125.8	126.7	127.0
65°	103.9	103.5	104.1	104.6	104.8	105.9	107.6	108.3	109.2	109.7	111.3
67.5°	87.4	87.5	87.4	88.0	89.4	89.6	91.1	92.7	92.9	93.8	94.8
70°	76.1	76.6	77.1	77.6	78.7	79.2	80.3	81.0	81.9	82.6	83.3
72.5°	65.8	65.9	66.4	66.3	67.4	68.3	69.3	70.0	70.9	71.8	72.4
75°	50.7	50.7	51.2	51.4	52.5	53.7	53.4	53.9	54.8	55.7	56.2
77.5°	37.1	36.6	37.1	37.3	37.7	38.6	38.8	39.4	40.5	40.2	40.7
80°	28.2	27.6	28.2	28.5	28.5	29.6	29.6	30.1	30.7	30.1	30.7
82.5°	20.1	19.8	20.3	20.4	20.7	20.8	21.1	21.2	21.9	21.6	21.9
85°	10.1	9.9	10.1	9.9	10.1	10.3	10.3	10.1	10.1	10.5	9.9
87.5°	4.9	5.4	6.0	6.8	7.4	7.9	7.7	7.6	7.5	7.1	7.1
90°	9.2	12.2	16.1	19.9	23.7	27.7	27.3	27.0	26.6	26.3	26.2
92.5°	20.2	21.4	22.3	23.2	24.2	25.1	25.1	25.2	25.3	25.3	25.4
95°	48.1	49.1	49.5	49.8	50.2	50.5	50.5	50.5	50.5	50.5	50.4
97.5°	81.2	82.3	82.9	83.6	84.2	84.9	84.9	84.9	84.9	84.9	84.9
100°	105.8	106.8	107.3	107.9	108.4	109.0	109.0	109.0	109.0	109.0	108.9
102.5°	131.3	132.2	132.8	133.5	134.1	134.8	134.9	135.1	135.2	135.4	135.3
105°	171.8	172.3	172.6	173.0	173.3	173.7	174.0	174.4	174.7	175.1	175.2
107.5°	216.0	216.4	216.4	216.4	216.4	216.4	216.6	216.7	216.8	217.0	216.7
110°	245.0	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.2



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.3	275.7	275.6	275.5	275.3	275.2	274.8	274.3	273.9	273.5	273.1
115°	319.9	320.3	319.9	319.6	319.2	318.9	318.7	318.5	318.4	318.2	317.8
117.5°	365.9	366.1	365.1	364.2	363.1	362.1	361.7	361.3	360.9	360.4	360.0
120°	395.6	395.6	394.2	392.7	391.3	389.9	389.9	389.9	389.9	389.9	389.7
122.5°	423.8	424.1	423.2	422.2	421.2	420.2	419.8	419.4	419.0	418.6	418.2
125°	465.7	466.3	465.7	465.1	464.6	464.1	463.6	463.1	462.5	462.0	461.7
127.5°	508.6	509.3	508.7	508.1	507.4	506.8	506.1	505.5	504.8	504.2	503.6
130°	535.6	536.5	536.2	535.8	535.5	535.2	534.8	534.5	534.1	533.8	533.2
132.5°	563.0	563.9	564.0	564.1	564.1	564.2	563.5	562.7	561.9	561.2	560.5
135°	602.1	603.2	603.6	603.9	604.3	604.6	604.5	604.3	604.1	603.9	603.6
137.5°	641.6	642.6	643.1	643.5	644.0	644.4	644.3	644.2	644.0	643.9	643.5
140°	666.2	667.4	668.3	669.2	670.0	671.0	671.0	671.0	671.0	671.0	670.6
142.5°	691.5	692.6	693.2	693.8	694.4	695.0	695.1	695.2	695.4	695.5	695.2
145°	726.4	727.5	728.6	729.6	730.6	731.7	732.0	732.1	732.3	732.5	732.2
147.5°	759.7	760.8	761.5	762.2	763.0	763.7	764.0	764.4	764.8	765.2	765.1
150°	780.1	781.0	781.7	782.4	783.2	783.9	784.4	784.9	785.4	786.0	786.0
152.5°	799.7	800.6	801.5	802.3	803.1	804.1	804.7	805.4	806.1	806.7	806.7
155°	827.0	827.5	828.0	828.6	829.1	829.6	830.5	831.3	832.2	833.1	833.3
157.5°	851.4	851.7	852.0	852.3	852.6	852.9	854.1	855.4	856.6	857.8	857.9
160°	866.6	866.8	867.0	867.2	867.4	867.5	868.6	869.6	870.7	871.7	871.9
162.5°	879.3	879.4	879.6	879.8	880.0	880.1	881.3	882.5	883.7	884.9	885.0
165°	896.8	896.7	896.7	896.7	896.7	896.7	898.0	899.2	900.4	901.6	901.8
167.5°	910.9	910.6	910.6	910.5	910.5	910.4	911.7	912.9	914.1	915.3	915.5
170°	919.1	918.7	918.6	918.4	918.2	918.0	919.3	920.5	921.7	922.9	923.0
172.5°	924.7	924.4	924.2	924.0	923.9	923.7	924.9	926.1	927.4	928.6	928.7
175°	931.7	931.3	930.9	930.6	930.2	929.9	931.1	932.3	933.5	934.7	934.8
177.5°	934.9	934.6	934.3	934.0	933.7	933.5	934.3	935.1	936.0	936.9	936.9
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	572.5	572.1	572.1	570.5	572.1	572.1	572.5	574.3	574.9	575.2	574.5
5°	531.1	530.4	529.3	530.4	529.3	530.4	531.1	534.3	535.9	537.5	538.9
7.5°	490.1	487.4	487.0	484.2	487.0	487.4	490.1	491.6	494.8	498.5	501.8
10°	460.2	458.4	458.1	453.7	458.1	458.4	460.2	464.1	467.3	471.6	476.3
12.5°	437.5	433.0	433.9	431.4	433.9	433.0	437.5	437.5	441.2	443.9	451.1
15°	398.0	398.0	397.1	393.2	397.1	398.0	398.0	404.2	405.4	409.7	415.9
17.5°	369.7	369.2	367.1	368.2	367.1	369.2	369.7	374.3	375.1	380.8	386.0
20°	352.8	351.4	348.7	348.7	348.7	351.4	352.8	355.4	358.3	361.7	366.2
22.5°	336.9	336.8	333.9	334.8	333.9	336.8	336.9	339.2	342.0	345.8	349.4
25°	318.2	316.4	315.0	315.7	315.0	316.4	318.2	318.4	321.6	324.2	326.5
27.5°	300.4	299.4	299.3	297.5	299.3	299.4	300.4	301.0	302.9	304.4	306.5
30°	290.2	287.9	288.3	287.2	288.3	287.9	290.2	290.4	291.3	292.3	294.8
32.5°	278.4	277.6	277.2	276.2	277.2	277.6	278.4	278.8	280.7	281.7	283.6
35°	262.5	262.7	261.6	262.0	261.6	262.7	262.5	262.9	263.2	264.1	265.9
37.5°	248.4	249.1	248.6	248.7	248.6	249.1	248.4	248.6	248.9	249.0	249.6
40°	239.2	239.2	239.2	239.9	239.2	239.2	239.2	238.6	238.8	238.6	238.6
42.5°	230.5	230.0	229.7	229.6	229.7	230.0	230.5	228.8	229.6	228.8	228.5
45°	215.4	216.1	216.3	215.2	216.3	216.1	215.4	215.0	214.3	214.0	213.8
47.5°	201.8	201.9	201.8	202.8	201.8	201.9	201.8	201.2	200.2	199.8	198.6
50°	192.3	191.8	192.3	191.8	192.3	191.8	192.3	191.1	190.4	189.2	188.3
52.5°	182.2	182.3	182.0	181.9	182.0	182.3	182.2	180.7	180.4	179.9	178.4
55°	166.3	166.7	166.5	166.5	166.5	166.7	166.3	165.4	165.2	163.8	162.4
57.5°	150.0	150.4	150.7	149.7	150.7	150.4	150.0	149.8	149.7	148.1	146.7
60°	138.6	139.7	139.5	139.1	139.5	139.7	138.6	138.8	138.1	137.1	136.2
62.5°	128.1	128.6	128.5	128.4	128.5	128.6	128.1	127.0	126.7	125.8	124.9
65°	112.0	112.4	111.7	112.4	111.7	112.4	112.0	111.3	109.7	109.2	108.3
67.5°	94.5	94.7	95.2	95.5	95.2	94.7	94.5	94.8	93.8	92.9	92.7
70°	83.7	83.5	84.2	84.9	84.2	83.5	83.7	83.3	82.6	81.9	81.0
72.5°	72.3	72.8	72.6	73.1	72.6	72.8	72.3	72.4	71.8	70.9	70.0
75°	55.7	56.5	56.2	56.9	56.2	56.5	55.7	56.2	55.7	54.8	53.9
77.5°	40.3	40.4	40.3	40.7	40.3	40.4	40.3	40.7	40.2	40.5	39.4
80°	30.7	30.3	29.8	30.7	29.8	30.3	30.7	30.7	30.1	30.7	30.1
82.5°	21.4	21.6	21.2	21.2	21.2	21.6	21.4	21.9	21.6	21.9	21.2
85°	9.9	9.6	9.2	9.2	9.2	9.6	9.9	9.9	10.5	10.1	10.1
87.5°	7.1	7.0	7.0	6.9	7.0	7.0	7.1	7.1	7.1	7.5	7.6
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.2	26.3	26.6	27.0
92.5°	25.4	25.5	25.5	25.5	25.5	25.5	25.4	25.4	25.3	25.3	25.2
95°	50.0	49.7	49.3	49.0	49.3	49.7	50.0	50.4	50.5	50.5	50.5
97.5°	84.9	84.8	84.8	84.7	84.8	84.8	84.9	84.9	84.9	84.9	84.9
100°	108.7	108.5	108.4	108.2	108.4	108.5	108.7	108.9	109.0	109.0	109.0
102.5°	135.2	135.0	134.8	134.6	134.8	135.0	135.2	135.3	135.4	135.2	135.1
105°	175.2	175.2	175.2	175.2	175.2	175.2	175.2	175.2	175.1	174.7	174.4
107.5°	215.9	215.1	214.3	213.5	214.3	215.1	215.9	216.7	217.0	216.8	216.7
110°	244.7	244.2	243.7	243.1	243.7	244.2	244.7	245.2	245.5	245.5	245.5



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	272.7	272.3	272.0	271.6	272.0	272.3	272.7	273.1	273.5	273.9	274.3
115°	317.3	316.8	316.3	315.8	316.3	316.8	317.3	317.8	318.2	318.4	318.5
117.5°	359.5	358.9	358.4	357.9	358.4	358.9	359.5	360.0	360.4	360.9	361.3
120°	389.1	388.6	388.1	387.6	388.1	388.6	389.1	389.7	389.9	389.9	389.9
122.5°	417.8	417.4	417.0	416.7	417.0	417.4	417.8	418.2	418.6	419.0	419.4
125°	461.5	461.3	461.2	461.0	461.2	461.3	461.5	461.7	462.0	462.5	463.1
127.5°	503.1	502.5	502.0	501.4	502.0	502.5	503.1	503.6	504.2	504.8	505.5
130°	532.5	531.9	531.2	530.5	531.2	531.9	532.5	533.2	533.8	534.1	534.5
132.5°	559.9	559.4	558.8	558.3	558.8	559.4	559.9	560.5	561.2	561.9	562.7
135°	603.1	602.6	602.0	601.5	602.0	602.6	603.1	603.6	603.9	604.1	604.3
137.5°	642.8	642.1	641.4	640.7	641.4	642.1	642.8	643.5	643.9	644.0	644.2
140°	669.9	669.2	668.5	667.8	668.5	669.2	669.9	670.6	671.0	671.0	671.0
142.5°	694.5	693.8	693.2	692.5	693.2	693.8	694.5	695.2	695.5	695.4	695.2
145°	731.4	730.7	730.0	729.3	730.0	730.7	731.4	732.2	732.5	732.3	732.1
147.5°	764.4	763.7	763.1	762.3	763.1	763.7	764.4	765.1	765.2	764.8	764.4
150°	785.4	784.9	784.4	783.9	784.4	784.9	785.4	786.0	786.0	785.4	784.9
152.5°	806.1	805.4	804.7	804.1	804.7	805.4	806.1	806.7	806.7	806.1	805.4
155°	832.7	832.2	831.7	831.2	831.7	832.2	832.7	833.3	833.1	832.2	831.3
157.5°	857.1	856.3	855.4	854.5	855.4	856.3	857.1	857.9	857.8	856.6	855.4
160°	871.2	870.5	869.8	869.1	869.8	870.5	871.2	871.9	871.7	870.7	869.6
162.5°	884.2	883.4	882.5	881.7	882.5	883.4	884.2	885.0	884.9	883.7	882.5
165°	900.9	900.0	899.2	898.3	899.2	900.0	900.9	901.8	901.6	900.4	899.2
167.5°	914.6	913.7	912.8	911.9	912.8	913.7	914.6	915.5	915.3	914.1	912.9
170°	922.0	920.9	919.9	918.8	919.9	920.9	922.0	923.0	922.9	921.7	920.5
172.5°	927.7	926.6	925.5	924.5	925.5	926.6	927.7	928.7	928.6	927.4	926.1
175°	933.8	932.7	931.7	930.7	931.7	932.7	933.8	934.8	934.7	933.5	932.3
177.5°	936.0	935.1	934.3	933.5	934.3	935.1	936.0	936.9	936.9	936.0	935.1
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	573.6	575.6	578.8	582.1	584.1	587.9	589.1	590.9	592.5	596.3	600.4
5°	540.5	543.7	551.3	555.4	561.1	567.7	572.1	576.7	581.8	590.5	598.5
7.5°	504.9	510.3	519.8	527.5	535.6	545.1	552.0	561.1	568.7	581.0	592.7
10°	481.3	488.9	497.4	506.5	518.0	528.1	537.8	549.2	558.4	573.1	586.8
12.5°	460.0	461.1	473.3	483.4	499.1	511.6	522.7	537.5	546.4	563.9	578.3
15°	422.8	429.7	440.7	448.7	467.3	483.1	498.8	514.1	524.4	546.0	565.0
17.5°	391.4	397.8	409.1	422.2	435.6	451.3	471.5	487.8	501.8	526.4	549.0
20°	371.6	379.4	390.9	404.5	416.2	433.3	450.8	469.4	484.5	512.3	538.7
22.5°	354.8	360.9	370.2	383.5	396.3	412.0	431.1	451.4	467.3	497.3	523.9
25°	331.0	336.1	342.0	353.0	367.5	384.8	399.6	421.9	445.0	473.0	505.3
27.5°	309.6	313.3	318.5	328.2	339.4	355.5	372.0	393.1	416.5	446.9	481.0
30°	296.6	298.9	304.2	312.3	323.3	335.9	352.6	372.7	396.7	427.4	461.3
32.5°	285.3	287.3	290.8	298.4	308.0	318.8	333.9	354.1	376.8	407.0	444.6
35°	268.2	269.7	272.8	278.9	284.3	294.8	307.4	325.8	347.1	376.0	415.0
37.5°	251.2	253.4	255.2	257.8	264.6	271.6	282.5	298.0	318.9	348.1	385.3
40°	239.9	241.8	244.6	245.7	251.2	257.4	266.3	280.5	301.6	328.3	364.6
42.5°	228.5	230.5	232.1	233.4	238.1	243.6	251.7	263.9	282.6	308.4	344.4
45°	213.1	213.4	215.0	217.5	219.7	223.7	229.4	239.9	254.4	278.7	311.3
47.5°	197.4	197.7	197.9	199.0	201.6	205.1	208.9	217.5	230.5	249.8	281.6
50°	186.9	186.5	186.9	187.8	189.5	192.5	196.8	203.0	213.6	231.7	260.8
52.5°	176.8	176.8	176.5	176.8	178.1	180.2	183.3	188.5	197.9	214.6	240.2
55°	161.5	160.4	160.6	159.7	161.8	162.2	164.5	168.8	177.1	188.5	212.7
57.5°	145.1	144.2	143.2	142.9	142.7	143.9	145.7	149.2	155.5	165.6	185.1
60°	134.6	133.5	132.1	131.7	131.7	132.4	133.3	135.8	141.8	150.7	166.7
62.5°	124.0	122.7	121.9	120.7	120.3	121.0	121.9	123.7	128.1	136.4	150.3
65°	107.6	105.9	104.8	104.6	104.1	103.5	103.9	105.7	109.2	115.8	126.8
67.5°	91.1	89.6	89.4	88.0	87.4	87.5	87.4	88.9	91.0	96.7	104.9
70°	80.3	79.2	78.7	77.6	77.1	76.6	76.1	77.6	79.6	84.4	91.5
72.5°	69.3	68.3	67.4	66.3	66.4	65.9	65.8	66.8	68.4	72.8	78.4
75°	53.4	53.7	52.5	51.4	51.2	50.7	50.7	51.4	52.1	55.5	59.9
77.5°	38.8	38.6	37.7	37.3	37.1	36.6	37.1	37.5	37.9	40.2	43.3
80°	29.6	29.6	28.5	28.5	28.2	27.6	28.2	27.8	28.7	31.0	33.2
82.5°	21.1	20.8	20.7	20.4	20.3	19.8	20.1	20.6	21.0	22.5	23.9
85°	10.3	10.3	10.1	9.9	10.1	9.9	10.1	10.3	10.5	11.2	12.4
87.5°	7.7	7.9	7.4	6.8	6.0	5.4	4.9	4.7	4.6	4.4	4.2
90°	27.3	27.7	23.7	19.9	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.1	25.1	24.2	23.2	22.3	21.4	20.2	18.7	17.2	15.6	14.0
95°	50.5	50.5	50.2	49.8	49.5	49.1	48.1	46.4	44.5	42.8	41.0
97.5°	84.9	84.9	84.2	83.6	82.9	82.3	81.2	79.6	78.1	76.5	75.0
100°	109.0	109.0	108.4	107.9	107.3	106.8	105.8	104.4	103.0	101.7	100.3
102.5°	134.9	134.8	134.1	133.5	132.8	132.2	131.3	130.2	129.1	127.8	126.7
105°	174.0	173.7	173.3	173.0	172.6	172.3	171.8	171.3	170.8	170.3	169.8
107.5°	216.6	216.4	216.4	216.4	216.4	216.4	216.0	215.3	214.5	213.8	213.0
110°	245.5	245.5	245.5	245.5	245.5	245.5	245.0	243.9	242.9	241.8	240.8



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.8	275.2	275.3	275.5	275.6	275.7	275.3	274.2	273.2	272.2	271.0
115°	318.7	318.9	319.2	319.6	319.9	320.3	319.9	318.9	317.8	316.8	315.8
117.5°	361.7	362.1	363.1	364.2	365.1	366.1	365.9	364.5	363.0	361.6	360.2
120°	389.9	389.9	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9
122.5°	419.8	420.2	421.2	422.2	423.2	424.1	423.8	422.1	420.5	418.8	417.1
125°	463.6	464.1	464.6	465.1	465.7	466.3	465.7	464.1	462.5	461.0	459.4
127.5°	506.1	506.8	507.4	508.1	508.7	509.3	508.6	506.6	504.6	502.6	500.6
130°	534.8	535.2	535.5	535.8	536.2	536.5	535.6	533.3	531.1	528.8	526.5
132.5°	563.5	564.2	564.1	564.1	564.0	563.9	563.0	561.1	559.3	557.4	555.5
135°	604.5	604.6	604.3	603.9	603.6	603.2	602.1	600.2	598.2	596.3	594.4
137.5°	644.3	644.4	644.0	643.5	643.1	642.6	641.6	640.1	638.4	636.8	635.3
140°	671.0	671.0	670.0	669.2	668.3	667.4	666.2	664.6	663.1	661.5	659.9
142.5°	695.1	695.0	694.4	693.8	693.2	692.6	691.5	689.9	688.3	686.7	685.2
145°	732.0	731.7	730.6	729.6	728.6	727.5	726.4	725.2	724.0	722.7	721.4
147.5°	764.0	763.7	763.0	762.2	761.5	760.8	759.7	758.2	756.8	755.3	753.9
150°	784.4	783.9	783.2	782.4	781.7	781.0	780.1	779.1	778.0	777.0	776.0
152.5°	804.7	804.1	803.1	802.3	801.5	800.6	799.7	798.7	797.6	796.6	795.5
155°	830.5	829.6	829.1	828.6	828.0	827.5	827.0	826.5	826.0	825.4	824.9
157.5°	854.1	852.9	852.6	852.3	852.0	851.7	851.4	851.0	850.7	850.3	850.0
160°	868.6	867.5	867.4	867.2	867.0	866.8	866.6	866.2	865.9	865.5	865.2
162.5°	881.3	880.1	880.0	879.8	879.6	879.4	879.3	879.2	879.2	879.1	879.0
165°	898.0	896.7	896.7	896.7	896.7	896.7	896.8	897.0	897.2	897.4	897.5
167.5°	911.7	910.4	910.5	910.5	910.6	910.6	910.9	911.4	911.9	912.4	912.9
170°	919.3	918.0	918.2	918.4	918.6	918.7	919.1	919.6	920.1	920.7	921.2
172.5°	924.9	923.7	923.9	924.0	924.2	924.4	924.7	925.2	925.8	926.3	926.9
175°	931.1	929.9	930.2	930.6	930.9	931.3	931.7	932.2	932.7	933.3	933.8
177.5°	934.3	933.5	933.7	934.0	934.3	934.6	934.9	935.3	935.8	936.2	936.6
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	600.1	601.0	603.9	606.8	610.2	611.1	612.5	611.3	610.9	614.3	616.9
5°	601.8	605.8	613.9	621.3	627.4	631.8	636.4	638.2	641.7	646.4	652.5
7.5°	599.8	607.8	620.5	631.2	642.8	651.2	657.7	663.4	670.1	679.2	689.2
10°	597.6	608.3	623.8	636.8	651.1	661.9	670.8	679.5	689.6	702.3	715.3
12.5°	593.6	606.3	625.6	641.1	659.3	669.9	682.0	700.7	711.7	729.2	747.6
15°	585.4	599.7	626.5	645.5	666.2	686.4	708.6	726.5	744.4	754.8	780.6
17.5°	573.4	594.2	624.0	646.2	672.5	704.2	729.2	749.5	770.1	786.9	799.9
20°	563.6	586.3	620.4	646.9	678.1	712.3	740.9	761.6	779.5	793.6	801.5
22.5°	551.4	580.0	613.0	644.2	684.0	717.8	747.9	764.2	779.1	786.0	789.1
25°	532.0	566.4	603.8	641.9	686.8	722.7	750.1	760.0	764.4	757.7	746.7
27.5°	511.1	549.5	593.2	637.5	685.1	719.5	739.2	737.7	730.3	708.7	691.6
30°	495.5	537.8	584.7	633.2	680.9	714.4	725.8	714.4	697.6	673.6	648.9
32.5°	479.2	522.9	575.7	626.9	673.2	702.7	705.1	685.4	659.4	632.1	601.5
35°	454.4	501.7	558.9	613.0	656.8	675.4	664.4	629.4	598.7	561.4	519.6
37.5°	426.5	478.7	535.9	592.6	632.3	637.1	609.8	573.1	529.7	485.7	436.6
40°	405.6	460.9	519.9	576.9	612.1	607.0	572.1	531.8	480.2	426.5	380.8
42.5°	386.9	442.1	502.2	558.3	586.3	572.5	531.8	482.2	426.8	376.2	334.4
45°	354.5	411.3	472.8	526.9	543.0	518.0	464.1	409.0	354.5	312.3	279.2
47.5°	323.0	379.2	440.1	487.7	493.3	459.7	400.8	344.2	297.2	262.9	239.5
50°	299.8	356.3	416.6	459.1	457.2	416.6	356.1	302.2	262.9	235.1	219.5
52.5°	279.1	332.4	390.3	429.0	419.2	375.0	317.1	269.2	237.0	215.3	201.2
55°	246.8	296.2	351.2	382.2	364.3	315.2	266.3	227.8	203.9	187.6	176.6
57.5°	214.8	261.1	308.2	327.3	307.5	262.2	221.5	193.5	175.5	163.5	156.3
60°	195.0	235.4	277.3	293.9	270.2	229.8	197.7	172.8	158.2	148.5	142.0
62.5°	175.2	211.4	251.0	259.9	238.3	204.2	175.7	154.9	143.1	134.3	128.3
65°	148.1	177.8	207.8	213.8	193.9	167.4	145.0	131.5	120.9	114.5	109.7
67.5°	121.6	145.3	166.6	171.4	153.9	135.6	119.4	107.6	100.5	95.1	91.0
70°	105.7	124.6	142.0	145.9	131.9	115.6	103.2	93.8	87.4	82.8	78.9
72.5°	89.1	104.7	119.3	121.9	110.5	98.0	87.9	80.4	74.7	71.8	68.1
75°	68.2	77.4	88.6	89.3	81.7	74.1	66.3	61.5	58.5	54.8	53.0
77.5°	48.1	55.2	61.7	62.9	58.5	53.3	49.0	45.1	42.6	40.9	39.2
80°	36.7	42.4	45.2	46.8	43.6	39.9	37.4	34.8	33.2	32.1	31.0
82.5°	26.3	29.8	32.3	33.6	31.8	29.6	27.2	25.7	24.4	23.5	23.1
85°	13.3	14.9	16.6	17.0	16.6	15.6	14.2	14.2	13.5	13.3	13.3
87.5°	5.2	6.4	6.8	7.7	8.0	8.7	9.5	10.1	10.7	10.4	10.2
90°	2.9	5.0	7.1	9.2	12.2	16.1	19.9	23.7	27.7	27.3	27.0
92.5°	15.6	17.2	18.7	20.2	21.4	22.3	23.2	24.2	25.1	25.1	25.2
95°	42.8	44.5	46.4	48.1	49.1	49.5	49.8	50.2	50.5	50.5	50.5
97.5°	76.5	78.1	79.6	81.2	82.3	82.9	83.6	84.2	84.9	84.9	84.9
100°	101.7	103.0	104.4	105.8	106.8	107.3	107.9	108.4	109.0	109.0	109.0
102.5°	127.8	129.1	130.2	131.3	132.2	132.8	133.5	134.1	134.8	134.9	135.1
105°	170.3	170.8	171.3	171.8	172.3	172.6	173.0	173.3	173.7	174.0	174.4
107.5°	213.8	214.5	215.3	216.0	216.4	216.4	216.4	216.4	216.4	216.6	216.7
110°	241.8	242.9	243.9	245.0	245.5	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.2	273.2	274.2	275.3	275.7	275.6	275.5	275.3	275.2	274.8	274.3
115°	316.8	317.8	318.9	319.9	320.3	319.9	319.6	319.2	318.9	318.7	318.5
117.5°	361.6	363.0	364.5	365.9	366.1	365.1	364.2	363.1	362.1	361.7	361.3
120°	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	389.9	389.9
122.5°	418.8	420.5	422.1	423.8	424.1	423.2	422.2	421.2	420.2	419.8	419.4
125°	461.0	462.5	464.1	465.7	466.3	465.7	465.1	464.6	464.1	463.6	463.1
127.5°	502.6	504.6	506.6	508.6	509.3	508.7	508.1	507.4	506.8	506.1	505.5
130°	528.8	531.1	533.3	535.6	536.5	536.2	535.8	535.5	535.2	534.8	534.5
132.5°	557.4	559.3	561.1	563.0	563.9	564.0	564.1	564.1	564.2	563.5	562.7
135°	596.3	598.2	600.2	602.1	603.2	603.6	603.9	604.3	604.6	604.5	604.3
137.5°	636.8	638.4	640.1	641.6	642.6	643.1	643.5	644.0	644.4	644.3	644.2
140°	661.5	663.1	664.6	666.2	667.4	668.3	669.2	670.0	671.0	671.0	671.0
142.5°	686.7	688.3	689.9	691.5	692.6	693.2	693.8	694.4	695.0	695.1	695.2
145°	722.7	724.0	725.2	726.4	727.5	728.6	729.6	730.6	731.7	732.0	732.1
147.5°	755.3	756.8	758.2	759.7	760.8	761.5	762.2	763.0	763.7	764.0	764.4
150°	777.0	778.0	779.1	780.1	781.0	781.7	782.4	783.2	783.9	784.4	784.9
152.5°	796.6	797.6	798.7	799.7	800.6	801.5	802.3	803.1	804.1	804.7	805.4
155°	825.4	826.0	826.5	827.0	827.5	828.0	828.6	829.1	829.6	830.5	831.3
157.5°	850.3	850.7	851.0	851.4	851.7	852.0	852.3	852.6	852.9	854.1	855.4
160°	865.5	865.9	866.2	866.6	866.8	867.0	867.2	867.4	867.5	868.6	869.6
162.5°	879.1	879.2	879.2	879.3	879.4	879.6	879.8	880.0	880.1	881.3	882.5
165°	897.4	897.2	897.0	896.8	896.7	896.7	896.7	896.7	896.7	898.0	899.2
167.5°	912.4	911.9	911.4	910.9	910.6	910.6	910.5	910.5	910.4	911.7	912.9
170°	920.7	920.1	919.6	919.1	918.7	918.6	918.4	918.2	918.0	919.3	920.5
172.5°	926.3	925.8	925.2	924.7	924.4	924.2	924.0	923.9	923.7	924.9	926.1
175°	933.3	932.7	932.2	931.7	931.3	930.9	930.6	930.2	929.9	931.1	932.3
177.5°	936.2	935.8	935.3	934.9	934.6	934.3	934.0	933.7	933.5	934.3	935.1
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	619.1	621.7	621.7	622.1	625.0	624.6	624.4
5°	658.8	662.8	663.2	667.3	670.0	669.1	666.6
7.5°	696.3	703.6	709.1	712.2	715.8	718.0	717.0
10°	726.1	736.6	743.1	747.4	752.7	756.6	755.2
12.5°	753.1	765.6	774.5	781.9	782.5	787.6	784.2
15°	795.2	808.4	809.8	815.3	819.7	819.2	819.4
17.5°	809.0	813.2	814.2	814.3	814.4	812.7	809.2
20°	804.1	802.4	798.6	795.6	790.3	789.6	785.1
22.5°	780.5	775.5	765.7	759.2	751.0	748.9	747.6
25°	734.4	723.1	707.5	692.6	688.4	680.4	682.7
27.5°	670.9	653.4	636.4	624.4	613.4	601.4	604.8
30°	626.3	606.5	582.7	564.3	552.6	541.2	539.1
32.5°	573.1	544.1	517.6	501.4	483.4	476.2	468.3
35°	481.3	453.0	426.7	403.9	390.9	380.8	371.6
37.5°	398.8	366.3	345.0	326.6	317.1	311.3	312.9
40°	347.6	319.1	303.5	289.5	280.7	276.7	277.6
42.5°	306.1	284.8	272.0	262.4	256.2	253.9	253.4
45°	259.0	247.1	236.5	231.1	228.0	225.5	223.9
47.5°	226.9	217.1	211.2	207.9	205.3	202.8	202.7
50°	207.6	201.2	197.0	193.6	191.6	189.8	191.4
52.5°	192.9	187.0	182.9	179.9	179.0	177.4	177.3
55°	171.2	166.5	163.6	160.8	159.5	158.5	157.3
57.5°	151.3	146.9	144.2	142.5	139.9	139.0	138.6
60°	137.1	133.7	131.0	128.7	127.5	125.7	125.7
62.5°	124.1	120.7	118.2	116.4	114.5	113.8	114.0
65°	105.3	102.5	100.0	98.2	97.8	96.3	96.8
67.5°	88.0	86.1	83.4	82.4	81.6	80.9	80.3
70°	76.3	74.5	73.2	71.8	71.1	71.1	71.1
72.5°	66.7	64.4	63.6	61.9	62.3	61.6	60.8
75°	51.6	50.2	49.6	48.9	47.8	47.8	47.8
77.5°	38.0	37.6	36.8	36.1	35.7	35.5	35.6
80°	29.4	29.1	28.7	28.7	28.2	28.0	27.6
82.5°	22.6	22.0	21.7	21.5	21.4	21.4	21.3
85°	12.8	12.4	12.4	12.6	12.1	12.1	12.4
87.5°	10.3	10.2	10.0	10.0	10.3	10.1	10.1
90°	26.6	26.3	26.2	26.4	26.5	26.7	26.9
92.5°	25.3	25.3	25.4	25.4	25.5	25.5	25.5
95°	50.5	50.5	50.4	50.0	49.7	49.3	49.0
97.5°	84.9	84.9	84.9	84.9	84.8	84.8	84.7
100°	109.0	109.0	108.9	108.7	108.5	108.4	108.2
102.5°	135.2	135.4	135.3	135.2	135.0	134.8	134.6
105°	174.7	175.1	175.2	175.2	175.2	175.2	175.2
107.5°	216.8	217.0	216.7	215.9	215.1	214.3	213.5
110°	245.5	245.5	245.2	244.7	244.2	243.7	243.1



TEST NUMBER: P331259-840

CATALOG NUMBER: SA2XXDIP-C290D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	273.9	273.5	273.1	272.7	272.3	272.0	271.6
115°	318.4	318.2	317.8	317.3	316.8	316.3	315.8
117.5°	360.9	360.4	360.0	359.5	358.9	358.4	357.9
120°	389.9	389.9	389.7	389.1	388.6	388.1	387.6
122.5°	419.0	418.6	418.2	417.8	417.4	417.0	416.7
125°	462.5	462.0	461.7	461.5	461.3	461.2	461.0
127.5°	504.8	504.2	503.6	503.1	502.5	502.0	501.4
130°	534.1	533.8	533.2	532.5	531.9	531.2	530.5
132.5°	561.9	561.2	560.5	559.9	559.4	558.8	558.3
135°	604.1	603.9	603.6	603.1	602.6	602.0	601.5
137.5°	644.0	643.9	643.5	642.8	642.1	641.4	640.7
140°	671.0	671.0	670.6	669.9	669.2	668.5	667.8
142.5°	695.4	695.5	695.2	694.5	693.8	693.2	692.5
145°	732.3	732.5	732.2	731.4	730.7	730.0	729.3
147.5°	764.8	765.2	765.1	764.4	763.7	763.1	762.3
150°	785.4	786.0	786.0	785.4	784.9	784.4	783.9
152.5°	806.1	806.7	806.7	806.1	805.4	804.7	804.1
155°	832.2	833.1	833.3	832.7	832.2	831.7	831.2
157.5°	856.6	857.8	857.9	857.1	856.3	855.4	854.5
160°	870.7	871.7	871.9	871.2	870.5	869.8	869.1
162.5°	883.7	884.9	885.0	884.2	883.4	882.5	881.7
165°	900.4	901.6	901.8	900.9	900.0	899.2	898.3
167.5°	914.1	915.3	915.5	914.6	913.7	912.8	911.9
170°	921.7	922.9	923.0	922.0	920.9	919.9	918.8
172.5°	927.4	928.6	928.7	927.7	926.6	925.5	924.5
175°	933.5	934.7	934.8	933.8	932.7	931.7	930.7
177.5°	936.0	936.9	936.9	936.0	935.1	934.3	933.5
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3

(END OF REPORT)